



When light really matters

GreenPerform Panel RC099V G3

GreenPerform panel RC099V G3 is an affordable LED panel delivering comfortable light with excellent uniformity. It offers 3 types, 600x600, 300x1200, and 600x1200mm with max: 140lm/w. Its UGR19 brings more visual comfort in the office. Equipped with Dali, Interact and EcoSet, RC099V G2 offers easy connection to control system to bring better energy saving.

Benefits

- Full range offer from 600x600, 300x1200 to 600x1200mm to cover key applications
- Low glare UGR19 to provide visual comfort
- Dali , Interact, EcoSet interface are available for system control

Features

- System efficiency 140lm/W(max)
- 3800lm lumen output for 600x600 and 300x1200mm versions; 5400lm for 600x1200mm version
- CRI 80 and CRI90 are both available
- Higher lumen output 4800lm is available for 600*600mm size

Application

- Open plan office
- Public indoor area
- Meeting/training room

Specifications

Mounting type	Recessed	Mains Voltage	220-240V / 50/60Hz
Ceiling type	T-Bar ceiling Concealed profile ceiling	Dimming	WIA: Wireless control, compatible with Interact Pro SIA: Wireless control, compatible with SNS210 sensor

GreenPerform Panel RC099V G3

Control system input	Dali / WIA / SIA / EcoSet
Integrated sensors	SIA version with SNS210 sensor
Lumen maintenance at median useful life 50.000h	L70B50
Luminaire efficacy	140lm/w 120lm/w
Correlated color temperature - CCT	840 850 860 940 950 965



Risk Group	RG0
Mechanical impact protection	IK03
Ingress protection	IP20
UGR	22 19
Installation	Recessed
Warranty	5 years

Versions







RTP-OF-RC099X

Dimensional drawing



GreenPerform Panel RC099V G3

Dimensional drawing



Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 or 60 Hz

Mechanical and Housing

Housing Color	White RAL 9003
Ingress protection code	IP20

Approval and Application

Ambient temperature range	-20 °C to 45 °C
CE mark	Yes

Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
-------------------------	-------------

General Information

Order Code	Full Product Name	Service tag
911401533043	RC099X G3 LED52/840 LiW W60L120 OC CAU	-
911401533343	RC099X G3 LED56/840 LiW W60L120	-
911401551343	RC099X G3 LED52/940 LiW W60L120 OC	-
911401509443	RC099V G3 LED49/865 PSU W30L120	Yes
911401509543	RC099V G3 LED50/850 PSU W30L120	Yes
911401509643	RC099V G3 LED50/840 PSU W30L120	Yes
911401510243	RC099V G3 LED36/965 PSU W30L120 OC HE	Yes
911401510343	RC099V G3 LED36/950 PSU W30L120 OC HE	Yes
911401510843	RC099V G3 LED38/965 PSU W30L120 HE	Yes

Order Code	Full Product Name	Service tag
911401510943	RC099V G3 LED38/950 PSU W30L120 HE	Yes
911401512343	RC099V G3 LED34/965 PSU W30L120 OC CAUHE	Yes
911401512443	RC099V G3 LED34/950 PSU W30L120 OC CAUHE	Yes
911401512743	RC099V G3 LED29/965 PSU W30L120 OC CAUHE	Yes
911401512843	RC099V G3 LED29/950 PSU W30L120 OC CAUHE	Yes
911401512943	RC099V G3 LED29/940 PSU W30L120 OC CAUHE	Yes
911401513343	RC099V G3 LED32/965 PSU W30L120 OC CAUHE	Yes
911401513443	RC099V G3 LED32/950 PSU W30L120 OC CAUHE	Yes
911401513543	RC099V G3 LED32/940 PSU W30L120 OC CAUHE	Yes

GreenPerform Panel RC099V G3

Order Code	Full Product Name	Service tag	Order Code	Full Product Name	Service tag
911401519843	RC099V G3 LED34/965 PSD W30L120 OC CAUHE	Yes	911401551843	RC099X G3 LED40/940 L1W W60L60	-
911401519943	RC099V G3 LED34/950 PSD W30L120 OC CAUHE	Yes	911401533843	RC099X G3 LED36/840 L1W W60L60 OC HE	-
911401520243	RC099V G3 LED29/965 PSD W30L120 OC CAUHE	Yes	911401534143	RC099X G3 LED38/840 L1W W60L60 HE	-
911401520343	RC099V G3 LED29/950 PSD W30L120 OC CAUHE	Yes	911401552443	RC099X G3 LED38/940 L1W W60L60 HE	-
911401520643	RC099V G3 LED32/965 PSD W30L120 OC CAUHE	Yes	911401509143	RC099V G3 LED69/865 PSU W60L120	Yes
911401520743	RC099V G3 LED32/950 PSD W30L120 OC CAUHE	Yes	911401509243	RC099V G3 LED71/850 PSU W60L120	Yes
911401585342	RC099V G3 LED37/865 PSU W30L120 OC	Yes	911401509343	RC099V G3 LED71/840 PSU W60L120	Yes
911401585442	RC099V G3 LED37/850 PSU W30L120 OC	Yes	911401510043	RC099V G3 LED50/965 PSU W60L120 OC HE	Yes
911401585542	RC099V G3 LED37/840 PSU W30L120 OC	Yes	911401510143	RC099V G3 LED50/950 PSU W60L120 OC HE	Yes
911401586542	RC099V G3 LED39/865 PSU W30L120	Yes	911401510643	RC099V G3 LED54/965 PSU W60L120 HE	Yes
911401586642	RC099V G3 LED40/850 PSU W30L120	Yes	911401510743	RC099V G3 LED54/950 PSU W60L120 HE	Yes
911401586742	RC099V G3 LED40/840 PSU W30L120	Yes	911401512143	RC099V G3 LED50/965 PSU W60L120 OC CAUHE	Yes
911401588942	RC099V G3 LED34/865 PSU W30L120 OC CAU	Yes	911401512243	RC099V G3 LED50/950 PSU W60L120 OC CAUHE	Yes
911401589042	RC099V G3 LED34/850 PSU W30L120 OC CAU	Yes	911401519643	RC099V G3 LED50/965 PSD W60L120 OC CAUHE	Yes
911401589142	RC099V G3 LED34/840 PSU W30L120 OC CAU	Yes	911401519743	RC099V G3 LED50/950 PSD W60L120 OC CAUHE	Yes
911401589742	RC099V G3 LED29/865 PSU W30L120 OC CAU	Yes	911401584942	RC099V G3 LED51/865 PSU W60L120 OC	Yes
911401589842	RC099V G3 LED30/850 PSU W30L120 OC CAU	Yes	911401585042	RC099V G3 LED52/850 PSU W60L120 OC	Yes
911401589942	RC099V G3 LED30/840 PSU W30L120 OC CAU	Yes	911401585142	RC099V G3 LED52/840 PSU W60L120 OC	Yes
911401590542	RC099V G3 LED32/865 PSU W30L120 OC CAU	Yes	911401586142	RC099V G3 LED55/865 PSU W60L120	Yes
911401590642	RC099V G3 LED32/850 PSU W30L120 OC CAU	Yes	911401586242	RC099V G3 LED56/850 PSU W60L120	Yes
911401590742	RC099V G3 LED32/840 PSU W30L120 OC CAU	Yes	911401586342	RC099V G3 LED56/840 PSU W60L120	Yes
911401593442	RC099V G3 LED36/840 PSU W30L120 OC HE	Yes	911401588542	RC099V G3 LED51/865 PSU W60L120 OC CAU	Yes
911401593742	RC099V G3 LED38/840 PSU W30L120 HE	Yes	911401588642	RC099V G3 LED52/850 PSU W60L120 OC CAU	Yes
911401594042	RC099V G3 LED34/840 PSU W30L120 OC CAUHE	Yes	911401588742	RC099V G3 LED52/840 PSU W60L120 OC CAU	Yes
911401594342	RC099V G3 LED36/840 PSD W30L120 OC	Yes	911401593342	RC099V G3 LED50/840 PSU W60L120 OC HE	Yes
911401594642	RC099V G3 LED40/840 PSD W30L120	Yes	911401593642	RC099V G3 LED54/840 PSU W60L120 HE	Yes
911401595542	RC099V G3 LED34/865 PSD W30L120 OC CAU	Yes	911401593942	RC099V G3 LED50/840 PSU W60L120 OC CAUHE	Yes
911401595642	RC099V G3 LED34/850 PSD W30L120 OC CAU	Yes	911401594542	RC099V G3 LED56/840 PSD W60L120	Yes
911401595742	RC099V G3 LED34/840 PSD W30L120 OC CAU	Yes	911401595142	RC099V G3 LED51/865 PSD W60L120 OC CAU	Yes
911401596342	RC099V G3 LED30/865 PSD W30L120 OC CAU	Yes	911401595242	RC099V G3 LED52/850 PSD W60L120 OC CAU	Yes
911401596442	RC099V G3 LED31/850 PSD W30L120 OC CAU	Yes	911401595342	RC099V G3 LED52/840 PSD W60L120 OC CAU	Yes
911401596542	RC099V G3 LED31/840 PSD W30L120 OC CAU	Yes	911401597942	RC099V G3 LED50/840 PSD W60L120 OC HE	Yes
911401597142	RC099V G3 LED32/865 PSD W30L120 OC CAU	Yes	911401598242	RC099V G3 LED54/840 PSD W60L120 HE	Yes
911401597242	RC099V G3 LED32/850 PSD W30L120 OC CAU	Yes	911401598542	RC099V G3 LED50/840 PSD W60L120 OC CAUHE	Yes
911401597342	RC099V G3 LED32/840 PSD W30L120 OC CAU	Yes	911401533443	RC099X G3 LED40/840 L1W W30L120	-
911401598042	RC099V G3 LED36/840 PSD W30L120 OC HE	Yes	911401551443	RC099X G3 LED37/940 L1W W30L120 OC	-
911401598342	RC099V G3 LED38/840 PSD W30L120 HE	Yes	911401551743	RC099X G3 LED40/940 L1W W30L120	-
911401598642	RC099V G3 LED34/840 PSD W30L120 OC CAUHE	Yes	911401509743	RC099V G3 LED49/865 PSU W60L60	Yes
911401598842	RC099V G3 LED29/840 PSD W30L120 OC CAUHE	Yes	911401509843	RC099V G3 LED50/850 PSU W60L60	Yes
911401599042	RC099V G3 LED32/840 PSD W30L120 OC CAUHE	Yes	911401509943	RC099V G3 LED50/840 PSU W60L60	Yes
911401533643	RC099X G3 LED50/840 L1W W60L120 OC HE	-	911401510443	RC099V G3 LED36/965 PSU W60L60 OC HE	Yes
911401533943	RC099X G3 LED54/840 L1W W60L120 HE	-	911401510543	RC099V G3 LED36/950 PSU W60L60 OC HE	Yes
911401551943	RC099X G3 LED50/940 L1W W60L120 OC HE	-	911401511043	RC099V G3 LED38/965 PSU W60L60 HE	Yes
911401552243	RC099X G3 LED54/940 L1W W60L120 HE	-	911401511143	RC099V G3 LED38/950 PSU W60L60 HE	Yes
911401533143	RC099X G3 LED34/840 L1W W30L120 OC CAU	-	911401512543	RC099V G3 LED34/965 PSU W60L60 OC CAU HE	Yes
911401533743	RC099X G3 LED36/840 L1W W30L120 OC HE	-	911401512643	RC099V G3 LED34/950 PSU W60L60 OC CAU HE	Yes
911401534043	RC099X G3 LED38/840 L1W W30L120 HE	-	911401513043	RC099V G3 LED29/965 PSU W60L60 OC CAU HE	Yes
911401552043	RC099X G3 LED36/940 L1W W30L120 OC HE	-	911401513143	RC099V G3 LED29/950 PSU W60L60 OC CAU HE	Yes
911401552343	RC099X G3 LED38/940 L1W W30L120 HE	-	911401513243	RC099V G3 LED29/940 PSU W60L60 OC CAU HE	Yes
911401533243	RC099X G3 LED36/840 L1W W60L60 OC CAU	-	911401513643	RC099V G3 LED32/965 PSU W60L60 OC CAU HE	Yes
911401533543	RC099X G3 LED40/840 L1W W60L60	-	911401513743	RC099V G3 LED32/950 PSU W60L60 OC CAU HE	Yes
911401551543	RC099X G3 LED37/940 L1W W60L60 OC	-	911401513843	RC099V G3 LED32/940 PSU W60L60 OC CAU HE	Yes

GreenPerform Panel RC099V G3

Order Code	Full Product Name	Service tag
911401520043	RC099V G3 LED34/965 PSD W60L60 OC CAU HE	Yes
911401520143	RC099V G3 LED34/950 PSD W60L60 OC CAU HE	Yes
911401520443	RC099V G3 LED29/965 PSD W60L60 OC CAU HE	Yes
911401520543	RC099V G3 LED29/950 PSD W60L60 OC CAU HE	Yes
911401520843	RC099V G3 LED32/965 PSD W60L60 OC CAU HE	Yes
911401520943	RC099V G3 LED32/950 PSD W60L60 OC CAU HE	Yes
911401584642	RC099V G3 LED39/865 PSU W60L60 L	Yes
911401584742	RC099V G3 LED40/850 PSU W60L60 L	Yes
911401584842	RC099V G3 LED40/840 PSU W60L60 L	Yes
911401585742	RC099V G3 LED37/865 PSU W60L60 OC	Yes
911401585842	RC099V G3 LED37/850 PSU W60L60 OC	Yes
911401585942	RC099V G3 LED37/840 PSU W60L60 OC	Yes
911401586942	RC099V G3 LED39/865 PSU W60L60	Yes
911401587042	RC099V G3 LED40/850 PSU W60L60	Yes
911401587142	RC099V G3 LED40/840 PSU W60L60	Yes
911401589342	RC099V G3 LED34/865 PSU W60L60 OC CAU	Yes
911401589442	RC099V G3 LED35/850 PSU W60L60 OC CAU	Yes
911401589542	RC099V G3 LED35/840 PSU W60L60 OC CAU	Yes
911401590142	RC099V G3 LED29/865 PSU W60L60 OC CAU	Yes
911401590242	RC099V G3 LED30/850 PSU W60L60 OC CAU	Yes
911401590342	RC099V G3 LED30/840 PSU W60L60 OC CAU	Yes
911401590942	RC099V G3 LED32/865 PSU W60L60 OC CAU	Yes

Order Code	Full Product Name	Service tag
911401591042	RC099V G3 LED33/850 PSU W60L60 OC CAU	Yes
911401591142	RC099V G3 LED33/840 PSU W60L60 OC CAU	Yes
911401593542	RC099V G3 LED36/840 PSU W60L60 OC HE	Yes
911401593842	RC099V G3 LED38/840 PSU W60L60 HE	Yes
911401594142	RC099V G3 LED34/840 PSU W60L60 OC CAU HE	Yes
911401594242	RC099V G3 LED52/840 PSD W60L120 OC	Yes
911401594442	RC099V G3 LED36/840 PSD W60L60 OC	Yes
911401594742	RC099V G3 LED40/840 PSD W60L60	Yes
911401595942	RC099V G3 LED34/865 PSD W60L60 OC CAU	Yes
911401596042	RC099V G3 LED35/850 PSD W60L60 OC CAU	Yes
911401596142	RC099V G3 LED35/840 PSD W60L60 OC CAU	Yes
911401596742	RC099V G3 LED30/865 PSD W60L60 OC CAU	Yes
911401596842	RC099V G3 LED31/850 PSD W60L60 OC CAU	Yes
911401596942	RC099V G3 LED31/840 PSD W60L60 OC CAU	Yes
911401597542	RC099V G3 LED32/865 PSD W60L60 OC CAU	Yes
911401597642	RC099V G3 LED32/850 PSD W60L60 OC CAU	Yes
911401597742	RC099V G3 LED32/840 PSD W60L60 OC CAU	Yes
911401598142	RC099V G3 LED36/840 PSD W60L60 OC HE	Yes
911401598442	RC099V G3 LED38/840 PSD W60L60 HE	Yes
911401598742	RC099V G3 LED34/840 PSD W60L60 OC CAU HE	Yes
911401598942	RC099V G3 LED29/840 PSD W60L60 OC CAU HE	Yes
911401599142	RC099V G3 LED32/840 PSD W60L60 OC CAU HE	Yes

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401533043	RC099X G3 LED52/840 L1W W60L120 OC CAU	4000 K	80	115 lm/W	5,200 lm
911401533343	RC099X G3 LED56/840 L1W W60L120	4000 K	80	130 lm/W	5,600 lm
911401551343	RC099X G3 LED52/940 L1W W60L120 OC	4000 K	90	115 lm/W	5,200 lm
911401509443	RC099V G3 LED49/865 PSU W30L120	6500 K	>80	120 lm/W	4,800 lm
911401509543	RC099V G3 LED50/850 PSU W30L120	5000 K	>80	120 lm/W	4,800 lm
911401509643	RC099V G3 LED50/840 PSU W30L120	4000 K	>80	120 lm/W	4,800 lm
911401510243	RC099V G3 LED36/965 PSU W30L120 OC HE	6500 K	>90	125 lm/W	3,400 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401510343	RC099V G3 LED36/950 PSU W30L120 OC HE	5000 K	>90	125 lm/W	3,400 lm
911401510843	RC099V G3 LED38/965 PSU W30L120 HE	6500 K	>90	140 lm/W	3,800 lm
911401510943	RC099V G3 LED38/950 PSU W30L120 HE	5000 K	>90	140 lm/W	3,800 lm
911401512343	RC099V G3 LED34/965 PSU W30L120 OC CAUHE	6500 K	>90	125 lm/W	3,400 lm
911401512443	RC099V G3 LED34/950 PSU W30L120 OC CAUHE	5000 K	>90	125 lm/W	3,400 lm
911401512743	RC099V G3 LED29/965 PSU W30L120 OC CAUHE	6500 K	>90	125 lm/W	2,900 lm
911401512843	RC099V G3 LED29/950 PSU	5000 K	>90	125 lm/W	2,900 lm

GreenPerform Panel RC099V G3

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
	W30L120 OC CAUHE				
911401512943	RC099V G3 LED29/940 PSU W30L120 OC CAUHE	4000 K	>90	125 lm/W	2,900 lm
911401513343	RC099V G3 LED32/965 PSU W30L120 OC CAUHE	6500 K	>90	125 lm/W	3,200 lm
911401513443	RC099V G3 LED32/950 PSU W30L120 OC CAUHE	5000 K	>90	125 lm/W	3,200 lm
911401513543	RC099V G3 LED32/940 PSU W30L120 OC CAUHE	4000 K	>90	125 lm/W	3,200 lm
911401519843	RC099V G3 LED34/965 PSD W30L120 OC CAUHE	6500 K	>90	125 lm/W	3,400 lm
911401519943	RC099V G3 LED34/950 PSD W30L120 OC CAUHE	5000 K	>90	125 lm/W	3,400 lm
911401520243	RC099V G3 LED29/965 PSD W30L120 OC CAUHE	6500 K	>90	125 lm/W	2,900 lm
911401520343	RC099V G3 LED29/950 PSD W30L120 OC CAUHE	5000 K	>90	125 lm/W	2,900 lm
911401520643	RC099V G3 LED32/965 PSD W30L120 OC CAUHE	6500 K	>90	125 lm/W	3,200 lm
911401520743	RC099V G3 LED32/950 PSD W30L120 OC CAUHE	5000 K	>90	125 lm/W	3,200 lm
911401585342	RC099V G3 LED37/865 PSU W30L120 OC	6500 K	>80	110 lm/W	3,600 lm
911401585442	RC099V G3 LED37/850 PSU W30L120 OC	5000 K	>80	110 lm/W	3,600 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401585542	RC099V G3 LED37/840 PSU W30L120 OC	4000 K	>80	110 lm/W	3,600 lm
911401586542	RC099V G3 LED39/865 PSU W30L120	6500 K	>80	125 lm/W	3,800 lm
911401586642	RC099V G3 LED40/850 PSU W30L120	5000 K	>80	125 lm/W	3,800 lm
911401586742	RC099V G3 LED40/840 PSU W30L120	4000 K	>80	125 lm/W	3,800 lm
911401588942	RC099V G3 LED34/865 PSU W30L120 OC CAU	6500 K	>80	105 lm/W	3,400 lm
911401589042	RC099V G3 LED34/850 PSU W30L120 OC CAU	5000 K	>80	105 lm/W	3,400 lm
911401589142	RC099V G3 LED34/840 PSU W30L120 OC CAU	4000 K	>80	105 lm/W	3,400 lm
911401589742	RC099V G3 LED29/865 PSU W30L120 OC CAU	6500 K	>80	110 lm/W	2,900 lm
911401589842	RC099V G3 LED30/850 PSU W30L120 OC CAU	5000 K	>80	110 lm/W	2,900 lm
911401589942	RC099V G3 LED30/840 PSU W30L120 OC CAU	4000 K	>80	110 lm/W	2,900 lm
911401590542	RC099V G3 LED32/865 PSU W30L120 OC CAU	6500 K	>80	110 lm/W	3,200 lm
911401590642	RC099V G3 LED32/850 PSU W30L120 OC CAU	5000 K	>80	110 lm/W	3,200 lm
911401590742	RC099V G3 LED32/840 PSU W30L120 OC CAU	4000 K	>80	110 lm/W	3,200 lm

GreenPerform Panel RC099V G3

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401593442	RC099V G3 LED36/840 PSU W30L120 OC HE	4000 K	>80	130 lm/W	3,600 lm
911401593742	RC099V G3 LED38/840 PSU W30L120 HE	4000 K	>80	140 lm/W	3,800 lm
911401594042	RC099V G3 LED34/840 PSU W30L120 OC CAUHE	4000 K	>80	125 lm/W	3,400 lm
911401594342	RC099V G3 LED36/840 PSD W30L120 OC	4000 K	>80	130 lm/W	3,600 lm
911401594642	RC099V G3 LED40/840 PSD W30L120	4000 K	>80	125 lm/W	3,800 lm
911401595542	RC099V G3 LED34/865 PSD W30L120 OC CAU	6500 K	>80	105 lm/W	3,400 lm
911401595642	RC099V G3 LED34/850 PSD W30L120 OC CAU	5000 K	>80	105 lm/W	3,400 lm
911401595742	RC099V G3 LED34/840 PSD W30L120 OC CAU	4000 K	>80	105 lm/W	3,400 lm
911401596342	RC099V G3 LED30/865 PSD W30L120 OC CAU	6500 K	>80	110 lm/W	2,900 lm
911401596442	RC099V G3 LED31/850 PSD W30L120 OC CAU	5000 K	>80	110 lm/W	2,900 lm
911401596542	RC099V G3 LED31/840 PSD W30L120 OC CAU	4000 K	>80	110 lm/W	2,900 lm
911401597142	RC099V G3 LED32/865 PSD W30L120 OC CAU	6500 K	>80	110 lm/W	3,200 lm
911401597242	RC099V G3 LED32/850 PSD W30L120 OC CAU	5000 K	>80	110 lm/W	3,200 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401597342	RC099V G3 LED32/840 PSD W30L120 OC CAU	4000 K	>80	110 lm/W	3,200 lm
911401598042	RC099V G3 LED36/840 PSD W30L120 OC HE	4000 K	>80	130 lm/W	3,600 lm
911401598342	RC099V G3 LED38/840 PSD W30L120 HE	4000 K	>80	140 lm/W	3,800 lm
911401598642	RC099V G3 LED34/840 PSD W30L120 OC CAUHE	4000 K	>80	125 lm/W	3,400 lm
911401598842	RC099V G3 LED29/840 PSD W30L120 OC CAUHE	4000 K	>80	125 lm/W	2,900 lm
911401599042	RC099V G3 LED32/840 PSD W30L120 OC CAUHE	4000 K	>80	125 lm/W	3,200 lm
911401533643	RC099X G3 LED50/840 L1W W60L120 OC HE	4000 K	≥80	135 lm/W	5,000 lm
911401533943	RC099X G3 LED54/840 L1W W60L120 HE	4000 K	≥80	140 lm/W	5,400 lm
911401551943	RC099X G3 LED50/940 L1W W60L120 OC HE	4000 K	≥90	135 lm/W	5,000 lm
911401552243	RC099X G3 LED54/940 L1W W60L120 HE	4000 K	≥90	140 lm/W	5,400 lm
911401533143	RC099X G3 LED34/840 L1W W30L120 OC CAU	4000 K	≥80	110 lm/W	3,400 lm
911401533743	RC099X G3 LED36/840 L1W W30L120 OC HE	4000 K	≥80	130 lm/W	3,600 lm
911401534043	RC099X G3 LED38/840 L1W W30L120 HE	4000 K	≥80	140 lm/W	3,800 lm
911401552043	RC099X G3 LED36/940 L1W W30L120 OC HE	4000 K	≥90	130 lm/W	3,600 lm

GreenPerform Panel RC099V G3

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401552343	RC099X G3 LED38/940 L1W W30L120 HE	4000 K	≥90	140 lm/W	3,800 lm
911401533243	RC099X G3 LED36/840 L1W W60L60 OC CAU	4000 K	80	115 lm/W	3,600 lm
911401533543	RC099X G3 LED40/840 L1W W60L60	4000 K	80	126 lm/W	4,000 lm
911401551543	RC099X G3 LED37/940 L1W W60L60 OC	4000 K	90	115 lm/W	3,700 lm
911401551843	RC099X G3 LED40/940 L1W W60L60	4000 K	90	126 lm/W	4,000 lm
911401533843	RC099X G3 LED36/840 L1W W60L60 OC HE	4000 K	≥80	130 lm/W	3,600 lm
911401534143	RC099X G3 LED38/840 L1W W60L60 HE	4000 K	≥80	140 lm/W	3,800 lm
911401552443	RC099X G3 LED38/940 L1W W60L60 HE	4000 K	≥90	140 lm/W	3,800 lm
911401509143	RC099V G3 LED69/865 PSU W60L120	6500 K	>80	135 lm/W	6,800 lm
911401509243	RC099V G3 LED71/850 PSU W60L120	5000 K	>80	135 lm/W	6,800 lm
911401509343	RC099V G3 LED71/840 PSU W60L120	4000 K	>80	135 lm/W	6,800 lm
911401510043	RC099V G3 LED50/965 PSU W60L120 OC HE	6500 K	>90	130 lm/W	5,000 lm
911401510143	RC099V G3 LED50/950 PSU W60L120 OC HE	5000 K	>90	130 lm/W	5,000 lm
911401510643	RC099V G3 LED54/965 PSU W60L120 HE	6500 K	>90	140 lm/W	5,400 lm
911401510743	RC099V G3 LED54/950 PSU W60L120 HE	5000 K	>90	140 lm/W	5,400 lm
911401512143	RC099V G3 LED50/965 PSU	6500 K	>90	130 lm/W	5,000 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
	W60L120 OC CAUHE				
911401512243	RC099V G3 LED50/950 PSU W60L120 OC CAUHE	5000 K	>90	130 lm/W	5,000 lm
911401519643	RC099V G3 LED50/965 PSD W60L120 OC CAUHE	6500 K	>90	130 lm/W	5,000 lm
911401519743	RC099V G3 LED50/950 PSD W60L120 OC CAUHE	5000 K	>90	130 lm/W	5,000 lm
911401584942	RC099V G3 LED51/865 PSU W60L120 OC	6500 K	>80	110 lm/W	5,000 lm
911401585042	RC099V G3 LED52/850 PSU W60L120 OC	5000 K	>80	110 lm/W	5,000 lm
911401585142	RC099V G3 LED52/840 PSU W60L120 OC	4000 K	>80	110 lm/W	5,000 lm
911401586142	RC099V G3 LED55/865 PSU W60L120	6500 K	>80	125 lm/W	5,400 lm
911401586242	RC099V G3 LED56/850 PSU W60L120	5000 K	>80	125 lm/W	5,400 lm
911401586342	RC099V G3 LED56/840 PSU W60L120	4000 K	>80	125 lm/W	5,400 lm
911401588542	RC099V G3 LED51/865 PSU W60L120 OC CAU	6500 K	>80	110 lm/W	5,000 lm
911401588642	RC099V G3 LED52/850 PSU W60L120 OC CAU	5000 K	>80	110 lm/W	5,000 lm
911401588742	RC099V G3 LED52/840 PSU W60L120 OC CAU	4000 K	>80	110 lm/W	5,000 lm
911401593342	RC099V G3 LED50/840 PSU W60L120 OC HE	4000 K	>80	135 lm/W	5,000 lm

GreenPerform Panel RC099V G3

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401593642	RC099V G3 LED54/840 PSU W60L120 HE	4000 K	>80	140 lm/W	5,400 lm
911401593942	RC099V G3 LED50/840 PSU W60L120 OC CAUHE	4000 K	>80	130 lm/W	5,000 lm
911401594542	RC099V G3 LED56/840 PSD W60L120	4000 K	>80	125 lm/W	5,400 lm
911401595142	RC099V G3 LED51/865 PSD W60L120 OC CAU	6500 K	>80	110 lm/W	5,000 lm
911401595242	RC099V G3 LED52/850 PSD W60L120 OC CAU	5000 K	>80	110 lm/W	5,000 lm
911401595342	RC099V G3 LED52/840 PSD W60L120 OC CAU	4000 K	>80	110 lm/W	5,000 lm
911401597942	RC099V G3 LED50/840 PSD W60L120 OC HE	4000 K	>80	135 lm/W	5,000 lm
911401598242	RC099V G3 LED54/840 PSD W60L120 HE	4000 K	>80	140 lm/W	5,400 lm
911401598542	RC099V G3 LED50/840 PSD W60L120 OC CAUHE	4000 K	>80	130 lm/W	5,000 lm
911401533443	RC099X G3 LED40/840 LIW W30L120	4000 K	80	126 lm/W	4,000 lm
911401551443	RC099X G3 LED37/940 LIW W30L120 OC	4000 K	90	115 lm/W	3,700 lm
911401551743	RC099X G3 LED40/940 LIW W30L120	4000 K	90	126 lm/W	4,000 lm
911401509743	RC099V G3 LED49/865 PSU W60L60	6500 K	>80	120 lm/W	4,800 lm
911401509843	RC099V G3 LED50/850 PSU W60L60	5000 K	>80	120 lm/W	4,800 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
91140150994 3	RC099V G3 LED50/840 PSU W60L60	4000 K	>80	120 lm/W	4,800 lm
911401510443	RC099V G3 LED36/965 PSU W60L60 OC HE	6500 K	>90	125 lm/W	3,400 lm
911401510543	RC099V G3 LED36/950 PSU W60L60 OC HE	5000 K	>90	125 lm/W	3,400 lm
911401511043	RC099V G3 LED38/965 PSU W60L60 HE	6500 K	>90	140 lm/W	3,800 lm
911401511143	RC099V G3 LED38/950 PSU W60L60 HE	5000 K	>90	140 lm/W	3,800 lm
911401512543	RC099V G3 LED34/965 PSU W60L60 OC CAU HE	6500 K	>90	125 lm/W	3,400 lm
911401512643	RC099V G3 LED34/950 PSU W60L60 OC CAU HE	5000 K	>90	125 lm/W	3,400 lm
911401513043	RC099V G3 LED29/965 PSU W60L60 OC CAU HE	6500 K	>90	125 lm/W	2,900 lm
911401513143	RC099V G3 LED29/950 PSU W60L60 OC CAU HE	5000 K	>90	125 lm/W	2,900 lm
911401513243	RC099V G3 LED29/940 PSU W60L60 OC CAU HE	4000 K	>90	125 lm/W	2,900 lm
911401513643	RC099V G3 LED32/965 PSU W60L60 OC CAU HE	6500 K	>90	125 lm/W	3,200 lm
911401513743	RC099V G3 LED32/950 PSU W60L60 OC CAU HE	5000 K	>90	125 lm/W	3,200 lm
911401513843	RC099V G3 LED32/940 PSU W60L60 OC CAU HE	4000 K	>90	125 lm/W	3,200 lm
911401520043	RC099V G3 LED34/965 PSD	6500 K	>90	125 lm/W	3,400 lm

GreenPerform Panel RC099V G3

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
	W60L60 OC CAU HE				
911401520143	RC099V G3 LED34/950 PSD W60L60 OC CAU HE	5000 K	>90	125 lm/W	3,400 lm
911401520443	RC099V G3 LED29/965 PSD W60L60 OC CAU HE	6500 K	>90	125 lm/W	2,900 lm
911401520543	RC099V G3 LED29/950 PSD W60L60 OC CAU HE	5000 K	>90	125 lm/W	2,900 lm
911401520843	RC099V G3 LED32/965 PSD W60L60 OC CAU HE	6500 K	>90	125 lm/W	3,200 lm
911401520943	RC099V G3 LED32/950 PSD W60L60 OC CAU HE	5000 K	>90	125 lm/W	3,200 lm
911401584642	RC099V G3 LED39/865 PSU W60L60 L	6500 K	>80	113 lm/W	3,800 lm
911401584742	RC099V G3 LED40/850 PSU W60L60 L	5000 K	>80	113 lm/W	3,800 lm
911401584842	RC099V G3 LED40/840 PSU W60L60 L	4000 K	>80	113 lm/W	3,800 lm
911401585742	RC099V G3 LED37/865 PSU W60L60 OC	6500 K	>80	110 lm/W	3,600 lm
911401585842	RC099V G3 LED37/850 PSU W60L60 OC	5000 K	>80	110 lm/W	3,600 lm
911401585942	RC099V G3 LED37/840 PSU W60L60 OC	4000 K	>80	110 lm/W	3,600 lm
911401586942	RC099V G3 LED39/865 PSU W60L60	6500 K	>80	125 lm/W	3,800 lm
911401587042	RC099V G3 LED40/850 PSU W60L60	5000 K	>80	125 lm/W	3,800 lm
911401587142	RC099V G3 LED40/840 PSU W60L60	4000 K	>80	125 lm/W	3,800 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401589342	RC099V G3 LED34/865 PSU W60L60 OC CAU	6500 K	>80	105 lm/W	3,400 lm
911401589442	RC099V G3 LED35/850 PSU W60L60 OC CAU	5000 K	>80	105 lm/W	3,400 lm
911401589542	RC099V G3 LED35/840 PSU W60L60 OC CAU	4000 K	>80	105 lm/W	3,400 lm
911401590142	RC099V G3 LED29/865 PSU W60L60 OC CAU	6500 K	>80	110 lm/W	2,900 lm
911401590242	RC099V G3 LED30/850 PSU W60L60 OC CAU	5000 K	>80	110 lm/W	2,900 lm
911401590342	RC099V G3 LED30/840 PSU W60L60 OC CAU	4000 K	>80	110 lm/W	2,900 lm
911401590942	RC099V G3 LED32/865 PSU W60L60 OC CAU	6500 K	>80	110 lm/W	3,200 lm
911401591042	RC099V G3 LED33/850 PSU W60L60 OC CAU	5000 K	>80	110 lm/W	3,200 lm
911401591142	RC099V G3 LED33/840 PSU W60L60 OC CAU	4000 K	>80	110 lm/W	3,200 lm
911401593542	RC099V G3 LED36/840 PSU W60L60 OC HE	4000 K	>80	130 lm/W	3,600 lm
911401593842	RC099V G3 LED38/840 PSU W60L60 HE	4000 K	>80	140 lm/W	3,800 lm
911401594142	RC099V G3 LED34/840 PSU W60L60 OC CAU HE	4000 K	>80	125 lm/W	3,400 lm
911401594242	RC099V G3 LED52/840 PSD W60L120 OC	4000 K	>80	135 lm/W	5,000 lm

GreenPerform Panel RC099V G3

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401594442	RC099V G3 LED36/840 PSD W60L60 OC	4000 K	>80	130 lm/W	3,600 lm
911401594742	RC099V G3 LED40/840 PSD W60L60	4000 K	>80	125 lm/W	3,800 lm
911401595942	RC099V G3 LED34/865 PSD W60L60 OC CAU	6500 K	>80	105 lm/W	3,400 lm
911401596042	RC099V G3 LED35/850 PSD W60L60 OC CAU	5000 K	>80	105 lm/W	3,400 lm
911401596142	RC099V G3 LED35/840 PSD W60L60 OC CAU	4000 K	>80	105 lm/W	3,400 lm
911401596742	RC099V G3 LED30/865 PSD W60L60 OC CAU	6500 K	>80	110 lm/W	2,900 lm
911401596842	RC099V G3 LED31/850 PSD W60L60 OC CAU	5000 K	>80	110 lm/W	2,900 lm
911401596942	RC099V G3 LED31/840 PSD W60L60 OC CAU	4000 K	>80	110 lm/W	2,900 lm
911401597542	RC099V G3 LED32/865 PSD	6500 K	>80	110 lm/W	3,200 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
	W60L60 OC CAU				
911401597642	RC099V G3 LED32/850 PSD W60L60 OC CAU	5000 K	>80	110 lm/W	3,200 lm
911401597742	RC099V G3 LED32/840 PSD W60L60 OC CAU	4000 K	>80	110 lm/W	3,200 lm
911401598142	RC099V G3 LED36/840 PSD W60L60 OC HE	4000 K	>80	130 lm/W	3,600 lm
911401598442	RC099V G3 LED38/840 PSD W60L60 HE	4000 K	>80	140 lm/W	3,800 lm
911401598742	RC099V G3 LED34/840 PSD W60L60 OC CAU HE	4000 K	>80	125 lm/W	3,400 lm
911401598942	RC099V G3 LED29/840 PSD W60L60 OC CAU HE	4000 K	>80	125 lm/W	2,900 lm
911401599142	RC099V G3 LED32/840 PSD W60L60 OC CAU HE	4000 K	>80	125 lm/W	3,200 lm

Operating and Electrical

Order Code	Full Product Name	Protection class IEC	Power Consumption
911401533043	RC099X G3 LED52/840 L1W W60L120 OC CAU	Safety class II	45.5 W
911401533343	RC099X G3 LED56/840 L1W W60L120	Safety class II	43 W
911401551343	RC099X G3 LED52/940 L1W W60L120 OC	Safety class II	45.5 W
911401509443	RC099V G3 LED49/865 PSU W30L120	Safety class II	40 W
911401509543	RC099V G3 LED50/850 PSU W30L120	Safety class II	40 W
911401509643	RC099V G3 LED50/840 PSU W30L120	Safety class II	40 W

Order Code	Full Product Name	Protection class IEC	Power Consumption
911401510243	RC099V G3 LED36/965 PSU W30L120 OC HE	Safety class II	27.2 W
911401510343	RC099V G3 LED36/950 PSU W30L120 OC HE	Safety class II	27.2 W
911401510843	RC099V G3 LED38/965 PSU W30L120 HE	Safety class II	27.1 W
911401510943	RC099V G3 LED38/950 PSU W30L120 HE	Safety class II	27.1 W
911401512343	RC099V G3 LED34/965 PSU W30L120 OC CAUHE	Safety class II	27.2 W
911401512443	RC099V G3 LED34/950 PSU W30L120 OC CAUHE	Safety class II	27.2 W

GreenPerform Panel RC099V G3

Order Code	Full Product Name	Protection class IEC	Power Consumption
911401512743	RC099V G3 LED29/965 PSU W30L120 OC CAUHE	Safety class II	23.2 W
911401512843	RC099V G3 LED29/950 PSU W30L120 OC CAUHE	Safety class II	23.2 W
911401512943	RC099V G3 LED29/940 PSU W30L120 OC CAUHE	Safety class II	23.2 W
911401513343	RC099V G3 LED32/965 PSU W30L120 OC CAUHE	Safety class II	25.6 W
911401513443	RC099V G3 LED32/950 PSU W30L120 OC CAUHE	Safety class II	25.6 W
911401513543	RC099V G3 LED32/940 PSU W30L120 OC CAUHE	Safety class II	25.6 W
911401519843	RC099V G3 LED34/965 PSD W30L120 OC CAUHE	Safety class II	27.2 W
911401519943	RC099V G3 LED34/950 PSD W30L120 OC CAUHE	Safety class II	27.2 W
911401520243	RC099V G3 LED29/965 PSD W30L120 OC CAUHE	Safety class II	23.2 W
911401520343	RC099V G3 LED29/950 PSD W30L120 OC CAUHE	Safety class II	23.2 W
911401520643	RC099V G3 LED32/965 PSD W30L120 OC CAUHE	Safety class II	25.6 W
911401520743	RC099V G3 LED32/950 PSD W30L120 OC CAUHE	Safety class II	25.6 W
911401585342	RC099V G3 LED37/865 PSU W30L120 OC	Safety class II	32.7 W
911401585442	RC099V G3 LED37/850 PSU W30L120 OC	Safety class II	32.7 W
911401585542	RC099V G3 LED37/840 PSU W30L120 OC	Safety class II	32.7 W
911401586542	RC099V G3 LED39/865 PSU W30L120	Safety class II	30.4 W
911401586642	RC099V G3 LED40/850 PSU W30L120	Safety class II	30.4 W
911401586742	RC099V G3 LED40/840 PSU W30L120	Safety class II	30.4 W
911401588942	RC099V G3 LED34/865 PSU W30L120 OC CAU	Safety class II	32.7 W
911401589042	RC099V G3 LED34/850 PSU W30L120 OC CAU	Safety class II	32.7 W
911401589142	RC099V G3 LED34/840 PSU W30L120 OC CAU	Safety class II	32.7 W
911401589742	RC099V G3 LED29/865 PSU W30L120 OC CAU	Safety class II	26.4 W
911401589842	RC099V G3 LED30/850 PSU W30L120 OC CAU	Safety class II	26.4 W
911401589942	RC099V G3 LED30/840 PSU W30L120 OC CAU	Safety class II	26.4 W
911401590542	RC099V G3 LED32/865 PSU W30L120 OC CAU	Safety class II	29.1 W

Order Code	Full Product Name	Protection class IEC	Power Consumption
911401590642	RC099V G3 LED32/850 PSU W30L120 OC CAU	Safety class II	29.1 W
911401590742	RC099V G3 LED32/840 PSU W30L120 OC CAU	Safety class II	29.1 W
911401593442	RC099V G3 LED36/840 PSU W30L120 OC HE	Safety class II	27.7 W
911401593742	RC099V G3 LED38/840 PSU W30L120 HE	Safety class II	27.1 W
911401594042	RC099V G3 LED34/840 PSU W30L120 OC CAUHE	Safety class II	27.2 W
911401594342	RC099V G3 LED36/840 PSD W30L120 OC	Safety class II	27.7 W
911401594642	RC099V G3 LED40/840 PSD W30L120	Safety class II	30.4 W
911401595542	RC099V G3 LED34/865 PSD W30L120 OC CAU	Safety class II	32.7 W
911401595642	RC099V G3 LED34/850 PSD W30L120 OC CAU	Safety class II	32.7 W
911401595742	RC099V G3 LED34/840 PSD W30L120 OC CAU	Safety class II	32.7 W
911401596342	RC099V G3 LED30/865 PSD W30L120 OC CAU	Safety class II	26.4 W
911401596442	RC099V G3 LED31/850 PSD W30L120 OC CAU	Safety class II	26.4 W
911401596542	RC099V G3 LED31/840 PSD W30L120 OC CAU	Safety class II	26.4 W
911401597142	RC099V G3 LED32/865 PSD W30L120 OC CAU	Safety class II	29.1 W
911401597242	RC099V G3 LED32/850 PSD W30L120 OC CAU	Safety class II	29.1 W
911401597342	RC099V G3 LED32/840 PSD W30L120 OC CAU	Safety class II	29.1 W
911401598042	RC099V G3 LED36/840 PSD W30L120 OC HE	Safety class II	27.7 W
911401598342	RC099V G3 LED38/840 PSD W30L120 HE	Safety class II	27.1 W
911401598642	RC099V G3 LED34/840 PSD W30L120 OC CAUHE	Safety class II	27.2 W
911401598842	RC099V G3 LED29/840 PSD W30L120 OC CAUHE	Safety class II	23.2 W
911401599042	RC099V G3 LED32/840 PSD W30L120 OC CAUHE	Safety class II	25.6 W
911401533643	RC099X G3 LED50/840 L1W W60L120 OC HE	Safety class II	37.0 W
911401533943	RC099X G3 LED54/840 L1W W60L120 HE	Safety class II	38.6 W
911401551943	RC099X G3 LED50/940 L1W W60L120 OC HE	Safety class II	37.0 W
911401552243	RC099X G3 LED54/940 L1W W60L120 HE	Safety class II	38.6 W

GreenPerform Panel RC099V G3

Order Code	Full Product Name	Protection class IEC	Power Consumption
911401533143	RC099X G3 LED34/840 L1W W30L120 OC CAU	Safety class I	30.9 W
911401533743	RC099X G3 LED36/840 L1W W30L120 OC HE	Safety class I	27.7 W
911401534043	RC099X G3 LED38/840 L1W W30L120 HE	Safety class I	27.1 W
911401552043	RC099X G3 LED36/940 L1W W30L120 OC HE	Safety class I	27.7 W
911401552343	RC099X G3 LED38/940 L1W W30L120 HE	Safety class I	27.1 W
911401533243	RC099X G3 LED36/840 L1W W60L60 OC CAU	Safety class II	31.5 W
911401533543	RC099X G3 LED40/840 L1W W60L60	Safety class II	31.5 W
911401551543	RC099X G3 LED37/940 L1W W60L60 OC	Safety class II	31.5 W
911401551843	RC099X G3 LED40/940 L1W W60L60	Safety class II	31.5 W
911401533843	RC099X G3 LED36/840 L1W W60L60 OC HE	Safety class II	27.7 W
911401534143	RC099X G3 LED38/840 L1W W60L60 HE	Safety class II	27.1 W
911401552443	RC099X G3 LED38/940 L1W W60L60 HE	Safety class II	27.1 W
911401509143	RC099V G3 LED69/865 PSU W60L120	Safety class II	50.4 W
911401509243	RC099V G3 LED71/850 PSU W60L120	Safety class II	50.4 W
911401509343	RC099V G3 LED71/840 PSU W60L120	Safety class II	50.4 W
911401510043	RC099V G3 LED50/965 PSU W60L120 OC HE	Safety class II	38.5 W
911401510143	RC099V G3 LED50/950 PSU W60L120 OC HE	Safety class II	38.5 W
911401510643	RC099V G3 LED54/965 PSU W60L120 HE	Safety class II	38.6 W
911401510743	RC099V G3 LED54/950 PSU W60L120 HE	Safety class II	38.6 W
911401512143	RC099V G3 LED50/965 PSU W60L120 OC CAUHE	Safety class II	38.5 W
911401512243	RC099V G3 LED50/950 PSU W60L120 OC CAUHE	Safety class II	38.5 W
911401519643	RC099V G3 LED50/965 PSD W60L120 OC CAUHE	Safety class II	38.5 W
911401519743	RC099V G3 LED50/950 PSD W60L120 OC CAUHE	Safety class II	38.5 W
911401584942	RC099V G3 LED51/865 PSU W60L120 OC	Safety class II	45.5 W
911401585042	RC099V G3 LED52/850 PSU W60L120 OC	Safety class II	45.5 W

Order Code	Full Product Name	Protection class IEC	Power Consumption
911401585142	RC099V G3 LED52/840 PSU W60L120 OC	Safety class II	45.5 W
911401586142	RC099V G3 LED55/865 PSU W60L120	Safety class II	43.2 W
911401586242	RC099V G3 LED56/850 PSU W60L120	Safety class II	43.2 W
911401586342	RC099V G3 LED56/840 PSU W60L120	Safety class II	43.2 W
911401588542	RC099V G3 LED51/865 PSU W60L120 OC CAU	Safety class II	45.5 W
911401588642	RC099V G3 LED52/850 PSU W60L120 OC CAU	Safety class II	45.5 W
911401588742	RC099V G3 LED52/840 PSU W60L120 OC CAU	Safety class II	45.5 W
911401593342	RC099V G3 LED50/840 PSU W60L120 OC HE	Safety class II	37 W
911401593642	RC099V G3 LED54/840 PSU W60L120 HE	Safety class II	38.6 W
911401593942	RC099V G3 LED50/840 PSU W60L120 OC CAUHE	Safety class II	38.5 W
911401594542	RC099V G3 LED56/840 PSD W60L120	Safety class II	43.2 W
911401595142	RC099V G3 LED51/865 PSD W60L120 OC CAU	Safety class II	45.5 W
911401595242	RC099V G3 LED52/850 PSD W60L120 OC CAU	Safety class II	45.5 W
911401595342	RC099V G3 LED52/840 PSD W60L120 OC CAU	Safety class II	45.5 W
911401597942	RC099V G3 LED50/840 PSD W60L120 OC HE	Safety class II	37 W
911401598242	RC099V G3 LED54/840 PSD W60L120 HE	Safety class II	38.6 W
911401598542	RC099V G3 LED50/840 PSD W60L120 OC CAUHE	Safety class II	38.5 W
911401533443	RC099X G3 LED40/840 L1W W30L120	Safety class II	31.5 W
911401551443	RC099X G3 LED37/940 L1W W30L120 OC	Safety class II	31.5 W
911401551743	RC099X G3 LED40/940 L1W W30L120	Safety class II	31.5 W
911401509743	RC099V G3 LED49/865 PSU W60L60	Safety class II	40 W
911401509843	RC099V G3 LED50/850 PSU W60L60	Safety class II	40 W
91140150994	RC099V G3 LED50/840 PSU W60L60	Safety class II	40 W
911401510443	RC099V G3 LED36/965 PSU W60L60 OC HE	Safety class II	27.2 W
911401510543	RC099V G3 LED36/950 PSU W60L60 OC HE	Safety class II	27.2 W

GreenPerform Panel RC099V G3

Order Code	Full Product Name	Protection class IEC	Power Consumption
911401511043	RC099V G3 LED38/965 PSU W60L60 HE	Safety class II	27.1 W
911401511143	RC099V G3 LED38/950 PSU W60L60 HE	Safety class II	27.1 W
911401512543	RC099V G3 LED34/965 PSU W60L60 OC CAU HE	Safety class II	27.2 W
911401512643	RC099V G3 LED34/950 PSU W60L60 OC CAU HE	Safety class II	27.2 W
911401513043	RC099V G3 LED29/965 PSU W60L60 OC CAU HE	Safety class II	23.2 W
911401513143	RC099V G3 LED29/950 PSU W60L60 OC CAU HE	Safety class II	23.2 W
911401513243	RC099V G3 LED29/940 PSU W60L60 OC CAU HE	Safety class II	23.2 W
911401513643	RC099V G3 LED32/965 PSU W60L60 OC CAU HE	Safety class II	25.6 W
911401513743	RC099V G3 LED32/950 PSU W60L60 OC CAU HE	Safety class II	25.6 W
911401513843	RC099V G3 LED32/940 PSU W60L60 OC CAU HE	Safety class II	25.6 W
911401520043	RC099V G3 LED34/965 PSD W60L60 OC CAU HE	Safety class II	27.2 W
911401520143	RC099V G3 LED34/950 PSD W60L60 OC CAU HE	Safety class II	27.2 W
911401520443	RC099V G3 LED29/965 PSD W60L60 OC CAU HE	Safety class II	23.2 W
911401520543	RC099V G3 LED29/950 PSD W60L60 OC CAU HE	Safety class II	23.2 W
911401520843	RC099V G3 LED32/965 PSD W60L60 OC CAU HE	Safety class II	25.6 W
911401520943	RC099V G3 LED32/950 PSD W60L60 OC CAU HE	Safety class II	25.6 W
911401584642	RC099V G3 LED39/865 PSU W60L60 L	Safety class II	33.6 W
911401584742	RC099V G3 LED40/850 PSU W60L60 L	Safety class II	33.6 W
911401584842	RC099V G3 LED40/840 PSU W60L60 L	Safety class II	33.6 W
911401585742	RC099V G3 LED37/865 PSU W60L60 OC	Safety class II	32.7 W
911401585842	RC099V G3 LED37/850 PSU W60L60 OC	Safety class II	32.7 W
911401585942	RC099V G3 LED37/840 PSU W60L60 OC	Safety class II	32.7 W
911401586942	RC099V G3 LED39/865 PSU W60L60	Safety class II	30.4 W
911401587042	RC099V G3 LED40/850 PSU W60L60	Safety class II	30.4 W
911401587142	RC099V G3 LED40/840 PSU W60L60	Safety class II	30.4 W

Order Code	Full Product Name	Protection class IEC	Power Consumption
911401589342	RC099V G3 LED34/865 PSU W60L60 OC CAU	Safety class II	32.7 W
911401589442	RC099V G3 LED35/850 PSU W60L60 OC CAU	Safety class II	32.7 W
911401589542	RC099V G3 LED35/840 PSU W60L60 OC CAU	Safety class II	32.7 W
911401590142	RC099V G3 LED29/865 PSU W60L60 OC CAU	Safety class II	26.4 W
911401590242	RC099V G3 LED30/850 PSU W60L60 OC CAU	Safety class II	26.4 W
911401590342	RC099V G3 LED30/840 PSU W60L60 OC CAU	Safety class II	26.4 W
911401590942	RC099V G3 LED32/865 PSU W60L60 OC CAU	Safety class II	29.1 W
911401591042	RC099V G3 LED33/850 PSU W60L60 OC CAU	Safety class II	29.1 W
911401591142	RC099V G3 LED33/840 PSU W60L60 OC CAU	Safety class II	29.1 W
911401593542	RC099V G3 LED36/840 PSU W60L60 OC HE	Safety class II	27.7 W
911401593842	RC099V G3 LED38/840 PSU W60L60 HE	Safety class II	27.1 W
911401594142	RC099V G3 LED34/840 PSU W60L60 OC CAU HE	Safety class II	27.2 W
911401594242	RC099V G3 LED52/840 PSD W60L120 OC	Safety class II	37 W
911401594442	RC099V G3 LED36/840 PSD W60L60 OC	Safety class II	27.7 W
911401594742	RC099V G3 LED40/840 PSD W60L60	Safety class II	30.4 W
911401595942	RC099V G3 LED34/865 PSD W60L60 OC CAU	Safety class II	32.7 W
911401596042	RC099V G3 LED35/850 PSD W60L60 OC CAU	Safety class II	32.7 W
911401596142	RC099V G3 LED35/840 PSD W60L60 OC CAU	Safety class II	32.7 W
911401596742	RC099V G3 LED30/865 PSD W60L60 OC CAU	Safety class II	26.4 W
911401596842	RC099V G3 LED31/850 PSD W60L60 OC CAU	Safety class II	26.4 W
911401596942	RC099V G3 LED31/840 PSD W60L60 OC CAU	Safety class II	26.4 W
911401597542	RC099V G3 LED32/865 PSD W60L60 OC CAU	Safety class II	29.1 W
911401597642	RC099V G3 LED32/850 PSD W60L60 OC CAU	Safety class II	29.1 W
911401597742	RC099V G3 LED32/840 PSD W60L60 OC CAU	Safety class II	29.1 W
911401598142	RC099V G3 LED36/840 PSD W60L60 OC HE	Safety class II	27.7 W

GreenPerform Panel RC099V G3

Order Code	Full Product Name	Protection class IEC	Power Consumption
911401598442	RC099V G3 LED38/840 PSD W60L60 HE	Safety class II	27.1 W
911401598742	RC099V G3 LED34/840 PSD W60L60 OC CAU HE	Safety class II	27.2 W

Order Code	Full Product Name	Protection class IEC	Power Consumption
911401598942	RC099V G3 LED29/840 PSD W60L60 OC CAU HE	Safety class II	23.2 W
911401599142	RC099V G3 LED32/840 PSD W60L60 OC CAU HE	Safety class II	25.6 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401533043	RC099X G3 LED52/840 L1W W60L120 OC CAU	DALI
911401533343	RC099X G3 LED56/840 L1W W60L120	DALI
911401551343	RC099X G3 LED52/940 L1W W60L120 OC	DALI
911401509443	RC099V G3 LED49/865 PSU W30L120	No
911401509543	RC099V G3 LED50/850 PSU W30L120	No
911401509643	RC099V G3 LED50/840 PSU W30L120	No
911401510243	RC099V G3 LED36/965 PSU W30L120 OC HE	No
911401510343	RC099V G3 LED36/950 PSU W30L120 OC HE	No
911401510843	RC099V G3 LED38/965 PSU W30L120 HE	No
911401510943	RC099V G3 LED38/950 PSU W30L120 HE	No
911401512343	RC099V G3 LED34/965 PSU W30L120 OC CAUHE	No
911401512443	RC099V G3 LED34/950 PSU W30L120 OC CAUHE	No
911401512743	RC099V G3 LED29/965 PSU W30L120 OC CAUHE	No
911401512843	RC099V G3 LED29/950 PSU W30L120 OC CAUHE	No
911401512943	RC099V G3 LED29/940 PSU W30L120 OC CAUHE	No
911401513343	RC099V G3 LED32/965 PSU W30L120 OC CAUHE	No
911401513443	RC099V G3 LED32/950 PSU W30L120 OC CAUHE	No
911401513543	RC099V G3 LED32/940 PSU W30L120 OC CAUHE	No
911401519843	RC099V G3 LED34/965 PSD W30L120 OC CAUHE	DALI
911401519943	RC099V G3 LED34/950 PSD W30L120 OC CAUHE	DALI
911401520243	RC099V G3 LED29/965 PSD W30L120 OC CAUHE	DALI
911401520343	RC099V G3 LED29/950 PSD W30L120 OC CAUHE	DALI
911401520643	RC099V G3 LED32/965 PSD W30L120 OC CAUHE	DALI
911401520743	RC099V G3 LED32/950 PSD W30L120 OC CAUHE	DALI
911401585342	RC099V G3 LED37/865 PSU W30L120 OC	No
911401585442	RC099V G3 LED37/850 PSU W30L120 OC	No
911401585542	RC099V G3 LED37/840 PSU W30L120 OC	No
911401586542	RC099V G3 LED39/865 PSU W30L120	No
911401586642	RC099V G3 LED40/850 PSU W30L120	No
911401586742	RC099V G3 LED40/840 PSU W30L120	No
911401588942	RC099V G3 LED34/865 PSU W30L120 OC CAU	No
911401589042	RC099V G3 LED34/850 PSU W30L120 OC CAU	No
911401589142	RC099V G3 LED34/840 PSU W30L120 OC CAU	No
911401589742	RC099V G3 LED29/865 PSU W30L120 OC CAU	No
911401589842	RC099V G3 LED30/850 PSU W30L120 OC CAU	No
911401589942	RC099V G3 LED30/840 PSU W30L120 OC CAU	No
911401590542	RC099V G3 LED32/865 PSU W30L120 OC CAU	No
911401590642	RC099V G3 LED32/850 PSU W30L120 OC CAU	No
911401590742	RC099V G3 LED32/840 PSU W30L120 OC CAU	No
911401593442	RC099V G3 LED36/840 PSU W30L120 OC HE	No
911401593742	RC099V G3 LED38/840 PSU W30L120 HE	No
911401594042	RC099V G3 LED34/840 PSU W30L120 OC CAUHE	No
911401594342	RC099V G3 LED36/840 PSD W30L120 OC	DALI

Order Code	Full Product Name	Dimmable
911401594642	RC099V G3 LED40/840 PSD W30L120	DALI
911401595542	RC099V G3 LED34/865 PSD W30L120 OC CAU	DALI
911401595642	RC099V G3 LED34/850 PSD W30L120 OC CAU	DALI
911401595742	RC099V G3 LED34/840 PSD W30L120 OC CAU	DALI
911401596342	RC099V G3 LED30/865 PSD W30L120 OC CAU	DALI
911401596442	RC099V G3 LED31/850 PSD W30L120 OC CAU	DALI
911401596542	RC099V G3 LED31/840 PSD W30L120 OC CAU	DALI
911401597142	RC099V G3 LED32/865 PSD W30L120 OC CAU	DALI
911401597242	RC099V G3 LED32/850 PSD W30L120 OC CAU	DALI
911401597342	RC099V G3 LED32/840 PSD W30L120 OC CAU	DALI
911401598042	RC099V G3 LED36/840 PSD W30L120 OC HE	DALI
911401598342	RC099V G3 LED38/840 PSD W30L120 HE	DALI
911401598642	RC099V G3 LED34/840 PSD W30L120 OC CAUHE	DALI
911401598842	RC099V G3 LED29/840 PSD W30L120 OC CAUHE	DALI
911401599042	RC099V G3 LED32/840 PSD W30L120 OC CAUHE	DALI
911401533643	RC099X G3 LED50/840 L1W W60L120 OC HE	DALI
911401533943	RC099X G3 LED54/840 L1W W60L120 HE	DALI
911401551943	RC099X G3 LED50/940 L1W W60L120 OC HE	DALI
911401552243	RC099X G3 LED54/940 L1W W60L120 HE	DALI
911401533143	RC099X G3 LED34/840 L1W W30L120 OC CAU	DALI
911401533743	RC099X G3 LED36/840 L1W W30L120 OC HE	DALI
911401534043	RC099X G3 LED38/840 L1W W30L120 HE	DALI
911401552043	RC099X G3 LED36/940 L1W W30L120 OC HE	DALI
911401552343	RC099X G3 LED38/940 L1W W30L120 HE	DALI
911401533243	RC099X G3 LED36/840 L1W W60L60 OC CAU	DALI
911401533543	RC099X G3 LED40/840 L1W W60L60	DALI
911401551543	RC099X G3 LED37/940 L1W W60L60 OC	DALI
911401551843	RC099X G3 LED40/940 L1W W60L60	DALI
911401533843	RC099X G3 LED36/840 L1W W60L60 OC HE	DALI
911401534143	RC099X G3 LED38/840 L1W W60L60 HE	DALI
911401552443	RC099X G3 LED38/940 L1W W60L60 HE	DALI
911401509143	RC099V G3 LED69/865 PSU W60L120	No
911401509243	RC099V G3 LED71/850 PSU W60L120	No
911401509343	RC099V G3 LED71/840 PSU W60L120	No
911401510043	RC099V G3 LED50/965 PSU W60L120 OC HE	No
911401510143	RC099V G3 LED50/950 PSU W60L120 OC HE	No
911401510643	RC099V G3 LED54/965 PSU W60L120 HE	No
911401510743	RC099V G3 LED54/950 PSU W60L120 HE	No
911401512143	RC099V G3 LED50/965 PSU W60L120 OC CAUHE	No
911401512243	RC099V G3 LED50/950 PSU W60L120 OC CAUHE	No
911401519643	RC099V G3 LED50/965 PSD W60L120 OC CAUHE	DALI
911401519743	RC099V G3 LED50/950 PSD W60L120 OC CAUHE	DALI
911401584942	RC099V G3 LED51/865 PSU W60L120 OC	No

GreenPerform Panel RC099V G3

Order Code	Full Product Name	Dimmable
911401585042	RC099V G3 LED52/850 PSU W60L120 OC	No
911401585142	RC099V G3 LED52/840 PSU W60L120 OC	No
911401586142	RC099V G3 LED55/865 PSU W60L120	No
911401586242	RC099V G3 LED56/850 PSU W60L120	No
911401586342	RC099V G3 LED56/840 PSU W60L120	No
911401588542	RC099V G3 LED51/865 PSU W60L120 OC CAU	No
911401588642	RC099V G3 LED52/850 PSU W60L120 OC CAU	No
911401588742	RC099V G3 LED52/840 PSU W60L120 OC CAU	No
911401593342	RC099V G3 LED50/840 PSU W60L120 OC HE	No
911401593642	RC099V G3 LED54/840 PSU W60L120 HE	No
911401593942	RC099V G3 LED50/840 PSU W60L120 OC CAUHE	No
911401594542	RC099V G3 LED56/840 PSD W60L120	DALI
911401595142	RC099V G3 LED51/865 PSD W60L120 OC CAU	DALI
911401595242	RC099V G3 LED52/850 PSD W60L120 OC CAU	DALI
911401595342	RC099V G3 LED52/840 PSD W60L120 OC CAU	DALI
911401597942	RC099V G3 LED50/840 PSD W60L120 OC HE	DALI
911401598242	RC099V G3 LED54/840 PSD W60L120 HE	DALI
911401598542	RC099V G3 LED50/840 PSD W60L120 OC CAUHE	DALI
911401533443	RC099X G3 LED40/840 L1W W30L120	DALI
911401551443	RC099X G3 LED37/940 L1W W30L120 OC	DALI
911401551743	RC099X G3 LED40/940 L1W W30L120	DALI
911401509743	RC099V G3 LED49/865 PSU W60L60	No
911401509843	RC099V G3 LED50/850 PSU W60L60	No
911401509943	RC099V G3 LED50/840 PSU W60L60	No
911401510443	RC099V G3 LED36/965 PSU W60L60 OC HE	No
911401510543	RC099V G3 LED36/950 PSU W60L60 OC HE	No
911401511043	RC099V G3 LED38/965 PSU W60L60 HE	No
911401511143	RC099V G3 LED38/950 PSU W60L60 HE	No
911401512543	RC099V G3 LED34/965 PSU W60L60 OC CAU HE	No
911401512643	RC099V G3 LED34/950 PSU W60L60 OC CAU HE	No
911401513043	RC099V G3 LED29/965 PSU W60L60 OC CAU HE	No
911401513143	RC099V G3 LED29/950 PSU W60L60 OC CAU HE	No
911401513243	RC099V G3 LED29/940 PSU W60L60 OC CAU HE	No
911401513643	RC099V G3 LED32/965 PSU W60L60 OC CAU HE	No
911401513743	RC099V G3 LED32/950 PSU W60L60 OC CAU HE	No
911401513843	RC099V G3 LED32/940 PSU W60L60 OC CAU HE	No
911401520043	RC099V G3 LED34/965 PSD W60L60 OC CAU HE	DALI
911401520143	RC099V G3 LED34/950 PSD W60L60 OC CAU HE	DALI
911401520443	RC099V G3 LED29/965 PSD W60L60 OC CAU HE	DALI
911401520543	RC099V G3 LED29/950 PSD W60L60 OC CAU HE	DALI

Order Code	Full Product Name	Dimmable
911401520843	RC099V G3 LED32/965 PSD W60L60 OC CAU HE	DALI
911401520943	RC099V G3 LED32/950 PSD W60L60 OC CAU HE	DALI
911401584642	RC099V G3 LED39/865 PSU W60L60 L	No
911401584742	RC099V G3 LED40/850 PSU W60L60 L	No
911401584842	RC099V G3 LED40/840 PSU W60L60 L	No
911401585742	RC099V G3 LED37/865 PSU W60L60 OC	No
911401585842	RC099V G3 LED37/850 PSU W60L60 OC	No
911401585942	RC099V G3 LED37/840 PSU W60L60 OC	No
911401586942	RC099V G3 LED39/865 PSU W60L60	No
911401587042	RC099V G3 LED40/850 PSU W60L60	No
911401587142	RC099V G3 LED40/840 PSU W60L60	No
911401589342	RC099V G3 LED34/865 PSU W60L60 OC CAU	No
911401589442	RC099V G3 LED35/850 PSU W60L60 OC CAU	No
911401589542	RC099V G3 LED35/840 PSU W60L60 OC CAU	No
911401590142	RC099V G3 LED29/865 PSU W60L60 OC CAU	No
911401590242	RC099V G3 LED30/850 PSU W60L60 OC CAU	No
911401590342	RC099V G3 LED30/840 PSU W60L60 OC CAU	No
911401590942	RC099V G3 LED32/865 PSU W60L60 OC CAU	No
911401591042	RC099V G3 LED33/850 PSU W60L60 OC CAU	No
911401591142	RC099V G3 LED33/840 PSU W60L60 OC CAU	No
911401593542	RC099V G3 LED36/840 PSU W60L60 OC HE	No
911401593842	RC099V G3 LED38/840 PSU W60L60 HE	No
911401594142	RC099V G3 LED34/840 PSU W60L60 OC CAU HE	No
911401594242	RC099V G3 LED52/840 PSD W60L120 OC	DALI
911401594442	RC099V G3 LED36/840 PSD W60L60 OC	DALI
911401594742	RC099V G3 LED40/840 PSD W60L60	DALI
911401595942	RC099V G3 LED34/865 PSD W60L60 OC CAU	DALI
911401596042	RC099V G3 LED35/850 PSD W60L60 OC CAU	DALI
911401596142	RC099V G3 LED35/840 PSD W60L60 OC CAU	DALI
911401596742	RC099V G3 LED30/865 PSD W60L60 OC CAU	DALI
911401596842	RC099V G3 LED31/850 PSD W60L60 OC CAU	DALI
911401596942	RC099V G3 LED31/840 PSD W60L60 OC CAU	DALI
911401597542	RC099V G3 LED32/865 PSD W60L60 OC CAU	DALI
911401597642	RC099V G3 LED32/850 PSD W60L60 OC CAU	DALI
911401597742	RC099V G3 LED32/840 PSD W60L60 OC CAU	DALI
911401598142	RC099V G3 LED36/840 PSD W60L60 OC HE	DALI
911401598442	RC099V G3 LED38/840 PSD W60L60 HE	DALI
911401598742	RC099V G3 LED34/840 PSD W60L60 OC CAU HE	DALI
911401598942	RC099V G3 LED29/840 PSD W60L60 OC CAU HE	DALI
911401599142	RC099V G3 LED32/840 PSD W60L60 OC CAU HE	DALI

Mechanical and Housing

Order Code	Full Product Name	Optical cover type	Mech. impact protection code
911401533043	RC099X G3 LED52/840 L1W W60L120 OC CAU	PS	IK03
911401533343	RC099X G3 LED56/840 L1W W60L120	PS	IK02
911401551343	RC099X G3 LED52/940 L1W W60L120 OC	PS	IK03
911401509443	RC099V G3 LED49/865 PSU W30L120	Opal	IK03
911401509543	RC099V G3 LED50/850 PSU W30L120	Opal	IK03

Order Code	Full Product Name	Optical cover type	Mech. impact protection code
911401509643	RC099V G3 LED50/840 PSU W30L120	Opal	IK03
911401510243	RC099V G3 LED36/965 PSU W30L120 OC HE	Opal	IK03
911401510343	RC099V G3 LED36/950 PSU W30L120 OC HE	Opal	IK03
911401510843	RC099V G3 LED38/965 PSU W30L120 HE	Opal	IK03

GreenPerform Panel RC099V G3

Order Code	Full Product Name	Optical cover type	Mech. impact protection code
911401510943	RC099V G3 LED38/950 PSU W30L120 HE	Opal	IK03
911401512343	RC099V G3 LED34/965 PSU W30L120 OC CAUHE	Opal	IK03
911401512443	RC099V G3 LED34/950 PSU W30L120 OC CAUHE	Opal	IK03
911401512743	RC099V G3 LED29/965 PSU W30L120 OC CAUHE	Opal	IK03
911401512843	RC099V G3 LED29/950 PSU W30L120 OC CAUHE	Opal	IK03
911401512943	RC099V G3 LED29/940 PSU W30L120 OC CAUHE	Opal	IK03
911401513343	RC099V G3 LED32/965 PSU W30L120 OC CAUHE	Opal	IK03
911401513443	RC099V G3 LED32/950 PSU W30L120 OC CAUHE	Opal	IK03
911401513543	RC099V G3 LED32/940 PSU W30L120 OC CAUHE	Opal	IK03
911401519843	RC099V G3 LED34/965 PSD W30L120 OC CAUHE	Opal	IK03
911401519943	RC099V G3 LED34/950 PSD W30L120 OC CAUHE	Opal	IK03
911401520243	RC099V G3 LED29/965 PSD W30L120 OC CAUHE	Opal	IK03
911401520343	RC099V G3 LED29/950 PSD W30L120 OC CAUHE	Opal	IK03
911401520643	RC099V G3 LED32/965 PSD W30L120 OC CAUHE	Opal	IK03
911401520743	RC099V G3 LED32/950 PSD W30L120 OC CAUHE	Opal	IK03
911401585342	RC099V G3 LED37/865 PSU W30L120 OC	Opal	IK03
911401585442	RC099V G3 LED37/850 PSU W30L120 OC	Opal	IK03
911401585542	RC099V G3 LED37/840 PSU W30L120 OC	Opal	IK03
911401586542	RC099V G3 LED39/865 PSU W30L120	Opal	IK03
911401586642	RC099V G3 LED40/850 PSU W30L120	Opal	IK03
911401586742	RC099V G3 LED40/840 PSU W30L120	Opal	IK03
911401588942	RC099V G3 LED34/865 PSU W30L120 OC CAU	Opal	IK03
911401589042	RC099V G3 LED34/850 PSU W30L120 OC CAU	Opal	IK03
911401589142	RC099V G3 LED34/840 PSU W30L120 OC CAU	Opal	IK03
911401589742	RC099V G3 LED29/865 PSU W30L120 OC CAU	Opal	IK03
911401589842	RC099V G3 LED30/850 PSU W30L120 OC CAU	Opal	IK03
911401589942	RC099V G3 LED30/840 PSU W30L120 OC CAU	Opal	IK03
911401590542	RC099V G3 LED32/865 PSU W30L120 OC CAU	Opal	IK03

Order Code	Full Product Name	Optical cover type	Mech. impact protection code
911401590642	RC099V G3 LED32/850 PSU W30L120 OC CAU	Opal	IK03
911401590742	RC099V G3 LED32/840 PSU W30L120 OC CAU	Opal	IK03
911401593442	RC099V G3 LED36/840 PSU W30L120 OC HE	Opal	IK03
911401593742	RC099V G3 LED38/840 PSU W30L120 HE	Opal	IK03
911401594042	RC099V G3 LED34/840 PSU W30L120 OC CAUHE	Opal	IK03
911401594342	RC099V G3 LED36/840 PSD W30L120 OC	Opal	IK03
911401594642	RC099V G3 LED40/840 PSD W30L120	Opal	IK03
911401595542	RC099V G3 LED34/865 PSD W30L120 OC CAU	Opal	IK03
911401595642	RC099V G3 LED34/850 PSD W30L120 OC CAU	Opal	IK03
911401595742	RC099V G3 LED34/840 PSD W30L120 OC CAU	Opal	IK03
911401596342	RC099V G3 LED30/865 PSD W30L120 OC CAU	Opal	IK03
911401596442	RC099V G3 LED31/850 PSD W30L120 OC CAU	Opal	IK03
911401596542	RC099V G3 LED31/840 PSD W30L120 OC CAU	Opal	IK03
911401597142	RC099V G3 LED32/865 PSD W30L120 OC CAU	Opal	IK03
911401597242	RC099V G3 LED32/850 PSD W30L120 OC CAU	Opal	IK03
911401597342	RC099V G3 LED32/840 PSD W30L120 OC CAU	Opal	IK03
911401598042	RC099V G3 LED36/840 PSD W30L120 OC HE	Opal	IK03
911401598342	RC099V G3 LED38/840 PSD W30L120 HE	Opal	IK03
911401598642	RC099V G3 LED34/840 PSD W30L120 OC CAUHE	Opal	IK03
911401598842	RC099V G3 LED29/840 PSD W30L120 OC CAUHE	Opal	IK03
911401599042	RC099V G3 LED32/840 PSD W30L120 OC CAUHE	Opal	IK03
911401533643	RC099X G3 LED50/840 L1W W60L120 OC HE	Opal	IK03
911401533943	RC099X G3 LED54/840 L1W W60L120 HE	Opal	IK03
911401551943	RC099X G3 LED50/940 L1W W60L120 OC HE	Opal	IK03
911401552243	RC099X G3 LED54/940 L1W W60L120 HE	Opal	IK03
911401533143	RC099X G3 LED34/840 L1W W30L120 OC CAU	Opal	IK03
911401533743	RC099X G3 LED36/840 L1W W30L120 OC HE	Opal	IK03
911401534043	RC099X G3 LED38/840 L1W W30L120 HE	Opal	IK03

GreenPerform Panel RC099V G3

Order Code	Full Product Name	Optical cover type	Mech. impact protection code
911401552043	RC099X G3 LED36/940 L1W W30L120 OC HE	Opal	IK03
911401552343	RC099X G3 LED38/940 L1W W30L120 HE	Opal	IK03
911401533243	RC099X G3 LED36/840 L1W W60L60 OC CAU	PS	IK02
911401533543	RC099X G3 LED40/840 L1W W60L60	PS	IK02
911401551543	RC099X G3 LED37/940 L1W W60L60 OC	PS	IK02
911401551843	RC099X G3 LED40/940 L1W W60L60	PS	IK02
911401533843	RC099X G3 LED36/840 L1W W60L60 OC HE	Opal	IK03
911401534143	RC099X G3 LED38/840 L1W W60L60 HE	Opal	IK03
911401552443	RC099X G3 LED38/940 L1W W60L60 HE	Opal	IK03
911401509143	RC099V G3 LED69/865 PSU W60L120	Opal	IK03
911401509243	RC099V G3 LED71/850 PSU W60L120	Opal	IK03
911401509343	RC099V G3 LED71/840 PSU W60L120	Opal	IK03
911401510043	RC099V G3 LED50/965 PSU W60L120 OC HE	Opal	IK03
911401510143	RC099V G3 LED50/950 PSU W60L120 OC HE	Opal	IK03
911401510643	RC099V G3 LED54/965 PSU W60L120 HE	Opal	IK03
911401510743	RC099V G3 LED54/950 PSU W60L120 HE	Opal	IK03
911401512143	RC099V G3 LED50/965 PSU W60L120 OC CAUHE	Opal	IK03
911401512243	RC099V G3 LED50/950 PSU W60L120 OC CAUHE	Opal	IK03
911401519643	RC099V G3 LED50/965 PSD W60L120 OC CAUHE	Opal	IK03
911401519743	RC099V G3 LED50/950 PSD W60L120 OC CAUHE	Opal	IK03
911401584942	RC099V G3 LED51/865 PSU W60L120 OC	Opal	IK03
911401585042	RC099V G3 LED52/850 PSU W60L120 OC	Opal	IK03
911401585142	RC099V G3 LED52/840 PSU W60L120 OC	Opal	IK03
911401586142	RC099V G3 LED55/865 PSU W60L120	Opal	IK03
911401586242	RC099V G3 LED56/850 PSU W60L120	Opal	IK03
911401586342	RC099V G3 LED56/840 PSU W60L120	Opal	IK03
911401588542	RC099V G3 LED51/865 PSU W60L120 OC CAU	Opal	IK03
911401588642	RC099V G3 LED52/850 PSU W60L120 OC CAU	Opal	IK03
911401588742	RC099V G3 LED52/840 PSU W60L120 OC CAU	Opal	IK03
911401593342	RC099V G3 LED50/840 PSU W60L120 OC HE	Opal	IK03
911401593642	RC099V G3 LED54/840 PSU W60L120 HE	Opal	IK03
911401593942	RC099V G3 LED50/840 PSU W60L120 OC CAUHE	Opal	IK03

Order Code	Full Product Name	Optical cover type	Mech. impact protection code
911401594542	RC099V G3 LED56/840 PSD W60L120	Opal	IK03
911401595142	RC099V G3 LED51/865 PSD W60L120 OC CAU	Opal	IK03
911401595242	RC099V G3 LED52/850 PSD W60L120 OC CAU	Opal	IK03
911401595342	RC099V G3 LED52/840 PSD W60L120 OC CAU	Opal	IK03
911401597942	RC099V G3 LED50/840 PSD W60L120 OC HE	Opal	IK03
911401598242	RC099V G3 LED54/840 PSD W60L120 HE	Opal	IK03
911401598542	RC099V G3 LED50/840 PSD W60L120 OC CAUHE	Opal	IK03
911401533443	RC099X G3 LED40/840 L1W W30L120	PS	IK02
911401551443	RC099X G3 LED37/940 L1W W30L120 OC	PS	IK02
911401551743	RC099X G3 LED40/940 L1W W30L120	PS	IK02
911401509743	RC099V G3 LED49/865 PSU W60L60	Opal	IK03
911401509843	RC099V G3 LED50/850 PSU W60L60	Opal	IK03
91140150994	RC099V G3 LED50/840 PSU W60L60 3	Opal	IK03
911401510443	RC099V G3 LED36/965 PSU W60L60 OC HE	Opal	IK03
911401510543	RC099V G3 LED36/950 PSU W60L60 OC HE	Opal	IK03
911401511043	RC099V G3 LED38/965 PSU W60L60 HE	Opal	IK03
911401511143	RC099V G3 LED38/950 PSU W60L60 HE	Opal	IK03
911401512543	RC099V G3 LED34/965 PSU W60L60 OC CAU HE	Opal	IK03
911401512643	RC099V G3 LED34/950 PSU W60L60 OC CAU HE	Opal	IK03
911401513043	RC099V G3 LED29/965 PSU W60L60 OC CAU HE	Opal	IK03
911401513143	RC099V G3 LED29/950 PSU W60L60 OC CAU HE	Opal	IK03
911401513243	RC099V G3 LED29/940 PSU W60L60 OC CAU HE	Opal	IK03
911401513643	RC099V G3 LED32/965 PSU W60L60 OC CAU HE	Opal	IK03
911401513743	RC099V G3 LED32/950 PSU W60L60 OC CAU HE	Opal	IK03
911401513843	RC099V G3 LED32/940 PSU W60L60 OC CAU HE	Opal	IK03
911401520043	RC099V G3 LED34/965 PSD W60L60 OC CAU HE	Opal	IK03
911401520143	RC099V G3 LED34/950 PSD W60L60 OC CAU HE	Opal	IK03
911401520443	RC099V G3 LED29/965 PSD W60L60 OC CAU HE	Opal	IK03
911401520543	RC099V G3 LED29/950 PSD W60L60 OC CAU HE	Opal	IK03

GreenPerform Panel RC099V G3

Order Code	Full Product Name	Optical cover type	Mech. impact protection code
911401520843	RC099V G3 LED32/965 PSD W60L60 OC CAU HE	Opal	IK03
911401520943	RC099V G3 LED32/950 PSD W60L60 OC CAU HE	Opal	IK03
911401584642	RC099V G3 LED39/865 PSU W60L60 L	Opal	IK03
911401584742	RC099V G3 LED40/850 PSU W60L60 L	Opal	IK03
911401584842	RC099V G3 LED40/840 PSU W60L60 L	Opal	IK03
911401585742	RC099V G3 LED37/865 PSU W60L60 OC	Opal	IK03
911401585842	RC099V G3 LED37/850 PSU W60L60 OC	Opal	IK03
911401585942	RC099V G3 LED37/840 PSU W60L60 OC	Opal	IK03
911401586942	RC099V G3 LED39/865 PSU W60L60	Opal	IK03
911401587042	RC099V G3 LED40/850 PSU W60L60	Opal	IK03
911401587142	RC099V G3 LED40/840 PSU W60L60	Opal	IK03
911401589342	RC099V G3 LED34/865 PSU W60L60 OC CAU	Opal	IK03
911401589442	RC099V G3 LED35/850 PSU W60L60 OC CAU	Opal	IK03
911401589542	RC099V G3 LED35/840 PSU W60L60 OC CAU	Opal	IK03
911401590142	RC099V G3 LED29/865 PSU W60L60 OC CAU	Opal	IK03
911401590242	RC099V G3 LED30/850 PSU W60L60 OC CAU	Opal	IK03
911401590342	RC099V G3 LED30/840 PSU W60L60 OC CAU	Opal	IK03
911401590942	RC099V G3 LED32/865 PSU W60L60 OC CAU	Opal	IK03
911401591042	RC099V G3 LED33/850 PSU W60L60 OC CAU	Opal	IK03
911401591142	RC099V G3 LED33/840 PSU W60L60 OC CAU	Opal	IK03
911401593542	RC099V G3 LED36/840 PSU W60L60 OC HE	Opal	IK03
911401593842	RC099V G3 LED38/840 PSU W60L60 HE	Opal	IK03

Order Code	Full Product Name	Optical cover type	Mech. impact protection code
911401594142	RC099V G3 LED34/840 PSU W60L60 OC CAU HE	Opal	IK03
911401594242	RC099V G3 LED52/840 PSD W60L120 OC	Opal	IK03
911401594442	RC099V G3 LED36/840 PSD W60L60 OC	Opal	IK03
911401594742	RC099V G3 LED40/840 PSD W60L60	Opal	IK03
911401595942	RC099V G3 LED34/865 PSD W60L60 OC CAU	Opal	IK03
911401596042	RC099V G3 LED35/850 PSD W60L60 OC CAU	Opal	IK03
911401596142	RC099V G3 LED35/840 PSD W60L60 OC CAU	Opal	IK03
911401596742	RC099V G3 LED30/865 PSD W60L60 OC CAU	Opal	IK03
911401596842	RC099V G3 LED31/850 PSD W60L60 OC CAU	Opal	IK03
911401596942	RC099V G3 LED31/840 PSD W60L60 OC CAU	Opal	IK03
911401597542	RC099V G3 LED32/865 PSD W60L60 OC CAU	Opal	IK03
911401597642	RC099V G3 LED32/850 PSD W60L60 OC CAU	Opal	IK03
911401597742	RC099V G3 LED32/840 PSD W60L60 OC CAU	Opal	IK03
911401598142	RC099V G3 LED36/840 PSD W60L60 OC HE	Opal	IK03
911401598442	RC099V G3 LED38/840 PSD W60L60 HE	Opal	IK03
911401598742	RC099V G3 LED34/840 PSD W60L60 OC CAU HE	Opal	IK03
911401598942	RC099V G3 LED29/840 PSD W60L60 OC CAU HE	Opal	IK03
911401599142	RC099V G3 LED32/840 PSD W60L60 OC CAU HE	Opal	IK03

