



# When light really matters

## GreenPerform Panel RC099V G3

GreenPerform panel RC099V G3 is an affordable LED panel delivering comfortable light with excellent uniformity. It offers 3 types, 600x600, 300x1200, and 600x1200mm with max: 140lm/w. Its UGR19 brings more visual comfort in the office. Equipped with Dali, Interact and EcoSet, RC099V G2 offers easy connection to control system to bring better energy saving.

### Benefits

- Full range offer from 600x600, 300x1200 to 600x1200mm to cover key applications
- Low glare UGR19 to provide visual comfort
- Dali , Interact, EcoSet interface are available for system control

### Features

- System efficiency 140lm/W(max)
- 3800lm lumen output for 600x600 and 300x1200mm versions; 5400lm for 600x1200mm version
- CRI 80 and CRI90 are both available
- Higher lumen output 4800lm is available for 600\*600mm size

### Application

- Open plan office
- Public indoor area
- Meeting/training room

### Specifications

<b>Mounting type</b>	Recessed	<b>Mains Voltage</b>	220-240V / 50/60Hz
<b>Ceiling type</b>	T-Bar ceiling Concealed profile ceiling	<b>Dimming</b>	WIA: Wireless control, compatible with Interact Pro SIA: Wireless control, compatible with SNS210 sensor

# GreenPerform Panel RC099V G3

<b>Control system input</b>	Dali / WIA / SIA / EcoSet
<b>Integrated sensors</b>	SIA version with SNS210 sensor
<b>Lumen maintenance at median useful life 50.000h</b>	L70B50
<b>Luminaire efficacy</b>	140lm/w 120lm/w
<b>Correlated color temperature - CCT</b>	840 850 860 940 950 965

<b>Risk Group</b>	RG0
<b>Mechanical impact protection</b>	IK03
<b>Ingress protection</b>	IP20
<b>UGR</b>	22 19
<b>Installation</b>	Recessed
<b>Warranty</b>	5 years

## Versions





RTP-OF-RC099X



Philips-Greenperform-Panel-RC099-G3-22-RTP





## Dimensional drawing



# GreenPerform Panel RC099V G3

## Dimensional drawing



### Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 or 60 Hz

### Mechanical and Housing

Housing Color	White RAL 9003
Ingress protection code	IP20

### Approval and Application

Ambient temperature range	-20 °C to 45 °C
CE mark	Yes

### Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
-------------------------	-------------

## General Information

Order Code	Full Product Name	Service tag	Order Code	Full Product Name	Service tag
911401533343	RC099X G3 LED56/840 L1W W60L120	-	911401552243	RC099X G3 LED54/940 L1W W60L120 HE	-
911401551343	RC099X G3 LED52/940 L1W W60L120 OC	-	911401533743	RC099X G3 LED36/840 L1W W30L120 OC HE	-
62018999	RC099V G3 LED49/865 PSU W30L120	Yes	911401534043	RC099X G3 LED38/840 L1W W30L120 HE	-
911401509543	RC099V G3 LED50/850 PSU W30L120	Yes	911401552043	RC099X G3 LED36/940 L1W W30L120 OC HE	-
911401509643	RC099V G3 LED50/840 PSU W30L120	Yes	911401552343	RC099X G3 LED38/940 L1W W30L120 HE	-
67202799	RC099V G3 LED37/865 PSU W30L120 OC	Yes	62736299	RC099X G3 LED40/840 L1W W60L60	-
911401585442	RC099V G3 LED37/850 PSU W30L120 OC	Yes	911401551543	RC099X G3 LED37/940 L1W W60L60 OC	-
67200399	RC099V G3 LED37/840 PSU W30L120 OC	Yes	911401551843	RC099X G3 LED40/940 L1W W60L60	-
67195299	RC099V G3 LED39/865 PSU W30L120	Yes	911401533843	RC099X G3 LED36/840 L1W W60L60 OC HE	-
911401586642	RC099V G3 LED40/850 PSU W30L120	Yes	911401534143	RC099X G3 LED38/840 L1W W60L60 HE	-
67194599	RC099V G3 LED40/840 PSU W30L120	Yes	911401552443	RC099X G3 LED38/940 L1W W60L60 HE	-
911401593442	RC099V G3 LED36/840 PSU W30L120 OC HE	Yes	911401509143	RC099V G3 LED69/865 PSU W60L120	Yes
911401593742	RC099V G3 LED38/840 PSU W30L120 HE	Yes	911401509243	RC099V G3 LED71/850 PSU W60L120	Yes
911401594342	RC099V G3 LED36/840 PSD W30L120 OC	Yes	911401509343	RC099V G3 LED71/840 PSU W60L120	Yes
911401594642	RC099V G3 LED40/840 PSD W30L120	Yes	67204199	RC099V G3 LED51/865 PSU W60L120 OC	Yes
911401598042	RC099V G3 LED36/840 PSD W30L120 OC HE	Yes	911401585042	RC099V G3 LED52/850 PSU W60L120 OC	Yes
911401598342	RC099V G3 LED38/840 PSD W30L120 HE	Yes	67203499	RC099V G3 LED52/840 PSU W60L120 OC	Yes
911401533643	RC099X G3 LED50/840 L1W W60L120 OC HE	-	67197699	RC099V G3 LED55/865 PSU W60L120	Yes
911401533943	RC099X G3 LED54/840 L1W W60L120 HE	-	911401586242	RC099V G3 LED56/850 PSU W60L120	Yes
911401551943	RC099X G3 LED50/940 L1W W60L120 OC HE	-	67196999	RC099V G3 LED56/840 PSU W60L120	Yes

# GreenPerform Panel RC099V G3

Order Code	Full Product Name	Service tag
911401593342	RC099V G3 LED50/840 PSU W60L120 OC HE	Yes
911401593642	RC099V G3 LED54/840 PSU W60L120 HE	Yes
911401594542	RC099V G3 LED56/840 PSD W60L120	Yes
911401597942	RC099V G3 LED50/840 PSD W60L120 OC HE	Yes
911401598242	RC099V G3 LED54/840 PSD W60L120 HE	Yes
911401533443	RC099X G3 LED40/840 L1W W30L120	-
911401551443	RC099X G3 LED37/940 L1W W30L120 OC	-
911401551743	RC099X G3 LED40/940 L1W W30L120	-
911401509743	RC099V G3 LED49/865 PSU W60L60	Yes
911401509843	RC099V G3 LED50/850 PSU W60L60	Yes
911401509943	RC099V G3 LED50/840 PSU W60L60	Yes
911401584642	RC099V G3 LED39/865 PSU W60L60 L	Yes
911401584742	RC099V G3 LED40/850 PSU W60L60 L	Yes
911401584842	RC099V G3 LED40/840 PSU W60L60 L	Yes

Order Code	Full Product Name	Service tag
67199099	RC099V G3 LED37/865 PSU W60L60 OC	Yes
911401585842	RC099V G3 LED37/850 PSU W60L60 OC	Yes
67198399	RC099V G3 LED37/840 PSU W60L60 OC	Yes
67193899	RC099V G3 LED39/865 PSU W60L60	Yes
911401587042	RC099V G3 LED40/850 PSU W60L60	Yes
67192199	RC099V G3 LED40/840 PSU W60L60	Yes
911401593542	RC099V G3 LED36/840 PSU W60L60 OC HE	Yes
911401593842	RC099V G3 LED38/840 PSU W60L60 HE	Yes
911401594242	RC099V G3 LED52/840 PSD W60L120 OC	Yes
911401594442	RC099V G3 LED36/840 PSD W60L60 OC	Yes
911401594742	RC099V G3 LED40/840 PSD W60L60	Yes
911401598142	RC099V G3 LED36/840 PSD W60L60 OC HE	Yes
911401598442	RC099V G3 LED38/840 PSD W60L60 HE	Yes

## Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401533343	RC099X G3 LED56/840 L1W W60L120	4000 K	80	130 lm/W	5,600 lm
911401551343	RC099X G3 LED52/940 L1W W60L120 OC	4000 K	90	115 lm/W	5,200 lm
62018999	RC099V G3 LED49/865 PSU W30L120	6500 K	>80	120 lm/W	4,800 lm
911401509543	RC099V G3 LED50/850 PSU W30L120	5000 K	>80	120 lm/W	4,800 lm
911401509643	RC099V G3 LED50/840 PSU W30L120	4000 K	>80	120 lm/W	4,800 lm
67202799	RC099V G3 LED37/865 PSU W30L120 OC	6500 K	>80	110 lm/W	3,600 lm
911401585442	RC099V G3 LED37/850 PSU W30L120 OC	5000 K	>80	110 lm/W	3,600 lm
67200399	RC099V G3 LED37/840 PSU W30L120 OC	4000 K	>80	110 lm/W	3,600 lm
67195299	RC099V G3 LED39/865 PSU W30L120	6500 K	>80	125 lm/W	3,800 lm
911401586642	RC099V G3 LED40/850 PSU W30L120	5000 K	>80	125 lm/W	3,800 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
67194599	RC099V G3 LED40/840 PSU W30L120	4000 K	>80	125 lm/W	3,800 lm
911401593442	RC099V G3 LED36/840 PSU W30L120 OC HE	4000 K	>80	130 lm/W	3,600 lm
911401593742	RC099V G3 LED38/840 PSU W30L120 HE	4000 K	>80	140 lm/W	3,800 lm
911401594342	RC099V G3 LED36/840 PSD W30L120 OC	4000 K	>80	130 lm/W	3,600 lm
911401594642	RC099V G3 LED40/840 PSD W30L120	4000 K	>80	125 lm/W	3,800 lm
911401598042	RC099V G3 LED36/840 PSD W30L120 OC HE	4000 K	>80	130 lm/W	3,600 lm
911401598342	RC099V G3 LED38/840 PSD W30L120 HE	4000 K	>80	140 lm/W	3,800 lm
911401533643	RC099X G3 LED50/840 L1W W60L120 OC HE	4000 K	≥80	135 lm/W	5,000 lm
911401533943	RC099X G3 LED54/840 L1W W60L120 HE	4000 K	≥80	140 lm/W	5,400 lm
911401551943	RC099X G3 LED50/940 L1W W60L120 OC HE	4000 K	≥90	135 lm/W	5,000 lm

## GreenPerform Panel RC099V G3

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401552243	RC099X G3 LED54/940 L1W W60L120 HE	4000 K	≥90	140 lm/W	5,400 lm
911401533743	RC099X G3 LED36/840 L1W W30L120 OC HE	4000 K	≥80	130 lm/W	3,600 lm
911401534043	RC099X G3 LED38/840 L1W W30L120 HE	4000 K	≥80	140 lm/W	3,800 lm
911401552043	RC099X G3 LED36/940 L1W W30L120 OC HE	4000 K	≥90	130 lm/W	3,600 lm
911401552343	RC099X G3 LED38/940 L1W W30L120 HE	4000 K	≥90	140 lm/W	3,800 lm
62736299	RC099X G3 LED40/840 L1W W60L60	4000 K	80	126 lm/W	4,000 lm
911401551543	RC099X G3 LED37/940 L1W W60L60 OC	4000 K	90	115 lm/W	3,700 lm
911401551843	RC099X G3 LED40/940 L1W W60L60	4000 K	90	126 lm/W	4,000 lm
911401533843	RC099X G3 LED36/840 L1W W60L60 OC HE	4000 K	≥80	130 lm/W	3,600 lm
911401534143	RC099X G3 LED38/840 L1W W60L60 HE	4000 K	≥80	140 lm/W	3,800 lm
911401552443	RC099X G3 LED38/940 L1W W60L60 HE	4000 K	≥90	140 lm/W	3,800 lm
911401509143	RC099V G3 LED69/865 PSU W60L120	6500 K	>80	135 lm/W	6,800 lm
911401509243	RC099V G3 LED71/850 PSU W60L120	5000 K	>80	135 lm/W	6,800 lm
911401509343	RC099V G3 LED71/840 PSU W60L120	4000 K	>80	135 lm/W	6,800 lm
67204199	RC099V G3 LED51/865 PSU W60L120 OC	6500 K	>80	110 lm/W	5,000 lm
911401585042	RC099V G3 LED52/850 PSU W60L120 OC	5000 K	>80	110 lm/W	5,000 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
67203499	RC099V G3 LED52/840 PSU W60L120 OC	4000 K	>80	110 lm/W	5,000 lm
67197699	RC099V G3 LED55/865 PSU W60L120	6500 K	>80	125 lm/W	5,400 lm
911401586242	RC099V G3 LED56/850 PSU W60L120	5000 K	>80	125 lm/W	5,400 lm
67196999	RC099V G3 LED56/840 PSU W60L120	4000 K	>80	125 lm/W	5,400 lm
911401593342	RC099V G3 LED50/840 PSU W60L120 OC HE	4000 K	>80	135 lm/W	5,000 lm
911401593642	RC099V G3 LED54/840 PSU W60L120 HE	4000 K	>80	140 lm/W	5,400 lm
911401594542	RC099V G3 LED56/840 PSD W60L120	4000 K	>80	125 lm/W	5,400 lm
911401597942	RC099V G3 LED50/840 PSD W60L120 OC HE	4000 K	>80	135 lm/W	5,000 lm
911401598242	RC099V G3 LED54/840 PSD W60L120 HE	4000 K	>80	140 lm/W	5,400 lm
911401533443	RC099X G3 LED40/840 L1W W30L120	4000 K	80	126 lm/W	4,000 lm
911401551443	RC099X G3 LED37/940 L1W W30L120 OC	4000 K	90	115 lm/W	3,700 lm
911401551743	RC099X G3 LED40/940 L1W W30L120	4000 K	90	126 lm/W	4,000 lm
911401509743	RC099V G3 LED49/865 PSU W60L60	6500 K	>80	120 lm/W	4,800 lm
911401509843	RC099V G3 LED50/850 PSU W60L60	5000 K	>80	120 lm/W	4,800 lm
911401509943	RC099V G3 LED50/840 PSU W60L60	4000 K	>80	120 lm/W	4,800 lm
911401584642	RC099V G3 LED39/865 PSU W60L60 L	6500 K	>80	113 lm/W	3,800 lm

## GreenPerform Panel RC099V G3

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401584742	RC099V G3 LED40/850 PSU W60L60 L	5000 K	>80	113 lm/W	3,800 lm
911401584842	RC099V G3 LED40/840 PSU W60L60 L	4000 K	>80	113 lm/W	3,800 lm
67199099	RC099V G3 LED37/865 PSU W60L60 OC	6500 K	>80	110 lm/W	3,600 lm
911401585842	RC099V G3 LED37/850 PSU W60L60 OC	5000 K	>80	110 lm/W	3,600 lm
67198399	RC099V G3 LED37/840 PSU W60L60 OC	4000 K	>80	110 lm/W	3,600 lm
67193899	RC099V G3 LED39/865 PSU W60L60	6500 K	>80	125 lm/W	3,800 lm
911401587042	RC099V G3 LED40/850 PSU W60L60	5000 K	>80	125 lm/W	3,800 lm
67192199	RC099V G3 LED40/840 PSU W60L60	4000 K	>80	125 lm/W	3,800 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401593542	RC099V G3 LED36/840 PSU W60L60 OC HE	4000 K	>80	130 lm/W	3,600 lm
911401593842	RC099V G3 LED38/840 PSU W60L60 HE	4000 K	>80	140 lm/W	3,800 lm
911401594242	RC099V G3 LED52/840 PSD W60L120 OC	4000 K	>80	135 lm/W	5,000 lm
911401594442	RC099V G3 LED36/840 PSD W60L60 OC	4000 K	>80	130 lm/W	3,600 lm
911401594742	RC099V G3 LED40/840 PSD W60L60	4000 K	>80	125 lm/W	3,800 lm
911401598142	RC099V G3 LED36/840 PSD W60L60 OC HE	4000 K	>80	130 lm/W	3,600 lm
911401598442	RC099V G3 LED38/840 PSD W60L60 HE	4000 K	>80	140 lm/W	3,800 lm

### Operating and Electrical

Order Code	Full Product Name	Protection class IEC	Power Consumption
911401533343	RC099X G3 LED56/840 L1W W60L120	Safety class II	43 W
911401551343	RC099X G3 LED52/940 L1W W60L120 OC	Safety class II	45.5 W
62018999	RC099V G3 LED49/865 PSU W30L120	Safety class II	40 W
911401509543	RC099V G3 LED50/850 PSU W30L120	Safety class II	40 W
911401509643	RC099V G3 LED50/840 PSU W30L120	Safety class II	40 W
67202799	RC099V G3 LED37/865 PSU W30L120 OC	Safety class II	32.7 W
911401585442	RC099V G3 LED37/850 PSU W30L120 OC	Safety class II	32.7 W
67200399	RC099V G3 LED37/840 PSU W30L120 OC	Safety class II	32.7 W
67195299	RC099V G3 LED39/865 PSU W30L120	Safety class II	30.4 W
911401586642	RC099V G3 LED40/850 PSU W30L120	Safety class II	30.4 W

Order Code	Full Product Name	Protection class IEC	Power Consumption
67194599	RC099V G3 LED40/840 PSU W30L120	Safety class II	30.4 W
911401593442	RC099V G3 LED36/840 PSU W30L120 OC HE	Safety class II	27.7 W
911401593742	RC099V G3 LED38/840 PSU W30L120 HE	Safety class II	27.1 W
911401594342	RC099V G3 LED36/840 PSD W30L120 OC	Safety class II	27.7 W
911401594642	RC099V G3 LED40/840 PSD W30L120	Safety class II	30.4 W
911401598042	RC099V G3 LED36/840 PSD W30L120 OC HE	Safety class II	27.7 W
911401598342	RC099V G3 LED38/840 PSD W30L120 HE	Safety class II	27.1 W
911401533643	RC099X G3 LED50/840 L1W W60L120 OC HE	Safety class II	37.0 W
911401533943	RC099X G3 LED54/840 L1W W60L120 HE	Safety class II	38.6 W
911401551943	RC099X G3 LED50/940 L1W W60L120 OC HE	Safety class II	37.0 W

## GreenPerform Panel RC099V G3

Order Code	Full Product Name	Protection class IEC	Power Consumption
911401552243	RC099X G3 LED54/940 L1W W60L120 HE	Safety class II	38.6 W
911401533743	RC099X G3 LED36/840 L1W W30L120 OC HE	Safety class I	27.7 W
911401534043	RC099X G3 LED38/840 L1W W30L120 HE	Safety class I	27.1 W
911401552043	RC099X G3 LED36/940 L1W W30L120 OC HE	Safety class I	27.7 W
911401552343	RC099X G3 LED38/940 L1W W30L120 HE	Safety class I	27.1 W
62736299	RC099X G3 LED40/840 L1W W60L60	Safety class II	31.5 W
911401551543	RC099X G3 LED37/940 L1W W60L60 OC	Safety class II	31.5 W
911401551843	RC099X G3 LED40/940 L1W W60L60	Safety class II	31.5 W
911401533843	RC099X G3 LED36/840 L1W W60L60 OC HE	Safety class II	27.7 W
911401534143	RC099X G3 LED38/840 L1W W60L60 HE	Safety class II	27.1 W
911401552443	RC099X G3 LED38/940 L1W W60L60 HE	Safety class II	27.1 W
911401509143	RC099V G3 LED69/865 PSU W60L120	Safety class II	50.4 W
911401509243	RC099V G3 LED71/850 PSU W60L120	Safety class II	50.4 W
911401509343	RC099V G3 LED71/840 PSU W60L120	Safety class II	50.4 W
67204199	RC099V G3 LED51/865 PSU W60L120 OC	Safety class II	45.5 W
911401585042	RC099V G3 LED52/850 PSU W60L120 OC	Safety class II	45.5 W
67203499	RC099V G3 LED52/840 PSU W60L120 OC	Safety class II	45.5 W
67197699	RC099V G3 LED55/865 PSU W60L120	Safety class II	43.2 W
911401586242	RC099V G3 LED56/850 PSU W60L120	Safety class II	43.2 W
67196999	RC099V G3 LED56/840 PSU W60L120	Safety class II	43.2 W
911401593342	RC099V G3 LED50/840 PSU W60L120 OC HE	Safety class II	37 W
911401593642	RC099V G3 LED54/840 PSU W60L120 HE	Safety class II	38.6 W
911401594542	RC099V G3 LED56/840 PSD W60L120	Safety class II	43.2 W
911401597942	RC099V G3 LED50/840 PSD W60L120 OC HE	Safety class II	37 W

Order Code	Full Product Name	Protection class IEC	Power Consumption
911401598242	RC099V G3 LED54/840 PSD W60L120 HE	Safety class II	38.6 W
911401533443	RC099X G3 LED40/840 L1W W30L120	Safety class II	31.5 W
911401551443	RC099X G3 LED37/940 L1W W30L120 OC	Safety class II	31.5 W
911401551743	RC099X G3 LED40/940 L1W W30L120	Safety class II	31.5 W
911401509743	RC099V G3 LED49/865 PSU W60L60	Safety class II	40 W
911401509843	RC099V G3 LED50/850 PSU W60L60	Safety class II	40 W
911401509943	RC099V G3 LED50/840 PSU W60L60	Safety class II	40 W
911401584642	RC099V G3 LED39/865 PSU W60L60 L	Safety class II	33.6 W
911401584742	RC099V G3 LED40/850 PSU W60L60 L	Safety class II	33.6 W
911401584842	RC099V G3 LED40/840 PSU W60L60 L	Safety class II	33.6 W
67199099	RC099V G3 LED37/865 PSU W60L60 OC	Safety class II	32.7 W
911401585842	RC099V G3 LED37/850 PSU W60L60 OC	Safety class II	32.7 W
67198399	RC099V G3 LED37/840 PSU W60L60 OC	Safety class II	32.7 W
67193899	RC099V G3 LED39/865 PSU W60L60	Safety class II	30.4 W
911401587042	RC099V G3 LED40/850 PSU W60L60	Safety class II	30.4 W
67192199	RC099V G3 LED40/840 PSU W60L60	Safety class II	30.4 W
911401593542	RC099V G3 LED36/840 PSU W60L60 OC HE	Safety class II	27.7 W
911401593842	RC099V G3 LED38/840 PSU W60L60 HE	Safety class II	27.1 W
911401594242	RC099V G3 LED52/840 PSD W60L120 OC	Safety class II	37 W
911401594442	RC099V G3 LED36/840 PSD W60L60 OC	Safety class II	27.7 W
911401594742	RC099V G3 LED40/840 PSD W60L60	Safety class II	30.4 W
911401598142	RC099V G3 LED36/840 PSD W60L60 OC HE	Safety class II	27.7 W
911401598442	RC099V G3 LED38/840 PSD W60L60 HE	Safety class II	27.1 W

### Controls and Dimming

## GreenPerform Panel RC099V G3

Order Code	Full Product Name	Dimmable
911401533343	RC099X G3 LED56/840 L1W W60L120	DALI
911401551343	RC099X G3 LED52/940 L1W W60L120 OC	DALI
62018999	RC099V G3 LED49/865 PSU W30L120	No
911401509543	RC099V G3 LED50/850 PSU W30L120	No
911401509643	RC099V G3 LED50/840 PSU W30L120	No
67202799	RC099V G3 LED37/865 PSU W30L120 OC	No
911401585442	RC099V G3 LED37/850 PSU W30L120 OC	No
67200399	RC099V G3 LED37/840 PSU W30L120 OC	No
67195299	RC099V G3 LED39/865 PSU W30L120	No
911401586642	RC099V G3 LED40/850 PSU W30L120	No
67194599	RC099V G3 LED40/840 PSU W30L120	No
911401593442	RC099V G3 LED36/840 PSU W30L120 OC HE	No
911401593742	RC099V G3 LED38/840 PSU W30L120 HE	No
911401594342	RC099V G3 LED36/840 PSD W30L120 OC	DALI
911401594642	RC099V G3 LED40/840 PSD W30L120	DALI
911401598042	RC099V G3 LED36/840 PSD W30L120 OC HE	DALI
911401598342	RC099V G3 LED38/840 PSD W30L120 HE	DALI
911401533643	RC099X G3 LED50/840 L1W W60L120 OC HE	DALI
911401533943	RC099X G3 LED54/840 L1W W60L120 HE	DALI
911401551943	RC099X G3 LED50/940 L1W W60L120 OC HE	DALI
911401552243	RC099X G3 LED54/940 L1W W60L120 HE	DALI
911401533743	RC099X G3 LED36/840 L1W W30L120 OC HE	DALI
911401534043	RC099X G3 LED38/840 L1W W30L120 HE	DALI
911401552043	RC099X G3 LED36/940 L1W W30L120 OC HE	DALI
911401552343	RC099X G3 LED38/940 L1W W30L120 HE	DALI
62736299	RC099X G3 LED40/840 L1W W60L60	DALI
911401551543	RC099X G3 LED37/940 L1W W60L60 OC	DALI
911401551843	RC099X G3 LED40/940 L1W W60L60	DALI
911401533843	RC099X G3 LED36/840 L1W W60L60 OC HE	DALI
911401534143	RC099X G3 LED38/840 L1W W60L60 HE	DALI
911401552443	RC099X G3 LED38/940 L1W W60L60 HE	DALI
911401509143	RC099V G3 LED69/865 PSU W60L120	No
911401509243	RC099V G3 LED71/850 PSU W60L120	No
911401509343	RC099V G3 LED71/840 PSU W60L120	No

Order Code	Full Product Name	Dimmable
67204199	RC099V G3 LED51/865 PSU W60L120 OC	No
911401585042	RC099V G3 LED52/850 PSU W60L120 OC	No
67203499	RC099V G3 LED52/840 PSU W60L120 OC	No
67197699	RC099V G3 LED55/865 PSU W60L120	No
911401586242	RC099V G3 LED56/850 PSU W60L120	No
67196999	RC099V G3 LED56/840 PSU W60L120	No
911401593342	RC099V G3 LED50/840 PSU W60L120 OC HE	No
911401593642	RC099V G3 LED54/840 PSU W60L120 HE	No
911401594542	RC099V G3 LED56/840 PSD W60L120	DALI
911401597942	RC099V G3 LED50/840 PSD W60L120 OC HE	DALI
911401598242	RC099V G3 LED54/840 PSD W60L120 HE	DALI
911401533443	RC099X G3 LED40/840 L1W W30L120	DALI
911401551443	RC099X G3 LED37/940 L1W W30L120 OC	DALI
911401551743	RC099X G3 LED40/940 L1W W30L120	DALI
911401509743	RC099V G3 LED49/865 PSU W60L60	No
911401509843	RC099V G3 LED50/850 PSU W60L60	No
911401509943	RC099V G3 LED50/840 PSU W60L60	No
911401584642	RC099V G3 LED39/865 PSU W60L60 L	No
911401584742	RC099V G3 LED40/850 PSU W60L60 L	No
911401584842	RC099V G3 LED40/840 PSU W60L60 L	No
67199099	RC099V G3 LED37/865 PSU W60L60 OC	No
911401585842	RC099V G3 LED37/850 PSU W60L60 OC	No
67198399	RC099V G3 LED37/840 PSU W60L60 OC	No
67193899	RC099V G3 LED39/865 PSU W60L60	No
911401587042	RC099V G3 LED40/850 PSU W60L60	No
67192199	RC099V G3 LED40/840 PSU W60L60	No
911401593542	RC099V G3 LED36/840 PSU W60L60 OC HE	No
911401593842	RC099V G3 LED38/840 PSU W60L60 HE	No
911401594242	RC099V G3 LED52/840 PSD W60L120 OC	DALI
911401594442	RC099V G3 LED36/840 PSD W60L60 OC	DALI
911401594742	RC099V G3 LED40/840 PSD W60L60	DALI
911401598142	RC099V G3 LED36/840 PSD W60L60 OC HE	DALI
911401598442	RC099V G3 LED38/840 PSD W60L60 HE	DALI

### Mechanical and Housing

Order Code	Full Product Name	Optical cover type	Mech. impact protection code
911401533343	RC099X G3 LED56/840 L1W W60L120	PS	IK02
911401551343	RC099X G3 LED52/940 L1W W60L120 OC	PS	IK03
62018999	RC099V G3 LED49/865 PSU W30L120	Opal	IK03
911401509543	RC099V G3 LED50/850 PSU W30L120	Opal	IK03
911401509643	RC099V G3 LED50/840 PSU W30L120	Opal	IK03
67202799	RC099V G3 LED37/865 PSU W30L120 OC	Opal	IK03
911401585442	RC099V G3 LED37/850 PSU W30L120 OC	Opal	IK03
67200399	RC099V G3 LED37/840 PSU W30L120 OC	Opal	IK03

Order Code	Full Product Name	Optical cover type	Mech. impact protection code
67195299	RC099V G3 LED39/865 PSU W30L120	Opal	IK03
911401586642	RC099V G3 LED40/850 PSU W30L120	Opal	IK03
67194599	RC099V G3 LED40/840 PSU W30L120	Opal	IK03
911401593442	RC099V G3 LED36/840 PSU W30L120 OC HE	Opal	IK03
911401593742	RC099V G3 LED38/840 PSU W30L120 HE	Opal	IK03
911401594342	RC099V G3 LED36/840 PSD W30L120 OC	Opal	IK03
911401594642	RC099V G3 LED40/840 PSD W30L120	Opal	IK03
911401598042	RC099V G3 LED36/840 PSD W30L120 OC HE	Opal	IK03

## GreenPerform Panel RC099V G3

Order Code	Full Product Name	Optical cover type	Mech. impact protection code
911401598342	RC099V G3 LED38/840 PSD W30L120 HE	Opal	IK03
911401533643	RC099X G3 LED50/840 L1W W60L120 OC HE	Opal	IK03
911401533943	RC099X G3 LED54/840 L1W W60L120 HE	Opal	IK03
911401551943	RC099X G3 LED50/940 L1W W60L120 OC HE	Opal	IK03
911401552243	RC099X G3 LED54/940 L1W W60L120 HE	Opal	IK03
911401533743	RC099X G3 LED36/840 L1W W30L120 OC HE	Opal	IK03
911401534043	RC099X G3 LED38/840 L1W W30L120 HE	Opal	IK03
911401552043	RC099X G3 LED36/940 L1W W30L120 OC HE	Opal	IK03
911401552343	RC099X G3 LED38/940 L1W W30L120 HE	Opal	IK03
62736299	RC099X G3 LED40/840 L1W W60L60	PS	IK02
911401551543	RC099X G3 LED37/940 L1W W60L60 OC	PS	IK02
911401551843	RC099X G3 LED40/940 L1W W60L60	PS	IK02
911401533843	RC099X G3 LED36/840 L1W W60L60 OC HE	Opal	IK03
911401534143	RC099X G3 LED38/840 L1W W60L60 HE	Opal	IK03
911401552443	RC099X G3 LED38/940 L1W W60L60 HE	Opal	IK03
911401509143	RC099V G3 LED69/865 PSU W60L120	Opal	IK03
911401509243	RC099V G3 LED71/850 PSU W60L120	Opal	IK03
911401509343	RC099V G3 LED71/840 PSU W60L120	Opal	IK03
67204199	RC099V G3 LED51/865 PSU W60L120 OC	Opal	IK03
911401585042	RC099V G3 LED52/850 PSU W60L120 OC	Opal	IK03
67203499	RC099V G3 LED52/840 PSU W60L120 OC	Opal	IK03
67197699	RC099V G3 LED55/865 PSU W60L120	Opal	IK03
911401586242	RC099V G3 LED56/850 PSU W60L120	Opal	IK03
67196999	RC099V G3 LED56/840 PSU W60L120	Opal	IK03
911401593342	RC099V G3 LED50/840 PSU W60L120 OC HE	Opal	IK03

Order Code	Full Product Name	Optical cover type	Mech. impact protection code
911401593642	RC099V G3 LED54/840 PSU W60L120 HE	Opal	IK03
911401594542	RC099V G3 LED56/840 PSD W60L120	Opal	IK03
911401597942	RC099V G3 LED50/840 PSD W60L120 OC HE	Opal	IK03
911401598242	RC099V G3 LED54/840 PSD W60L120 HE	Opal	IK03
911401533443	RC099X G3 LED40/840 L1W W30L120	PS	IK02
911401551443	RC099X G3 LED37/940 L1W W30L120 OC	PS	IK02
911401551743	RC099X G3 LED40/940 L1W W30L120	PS	IK02
911401509743	RC099V G3 LED49/865 PSU W60L60	Opal	IK03
911401509843	RC099V G3 LED50/850 PSU W60L60	Opal	IK03
911401509943	RC099V G3 LED50/840 PSU W60L60	Opal	IK03
911401584642	RC099V G3 LED39/865 PSU W60L60 L	Opal	IK03
911401584742	RC099V G3 LED40/850 PSU W60L60 L	Opal	IK03
911401584842	RC099V G3 LED40/840 PSU W60L60 L	Opal	IK03
67199099	RC099V G3 LED37/865 PSU W60L60 OC	Opal	IK03
911401585842	RC099V G3 LED37/850 PSU W60L60 OC	Opal	IK03
67198399	RC099V G3 LED37/840 PSU W60L60 OC	Opal	IK03
67193899	RC099V G3 LED39/865 PSU W60L60	Opal	IK03
911401587042	RC099V G3 LED40/850 PSU W60L60	Opal	IK03
67192199	RC099V G3 LED40/840 PSU W60L60	Opal	IK03
911401593542	RC099V G3 LED36/840 PSU W60L60 OC HE	Opal	IK03
911401593842	RC099V G3 LED38/840 PSU W60L60 HE	Opal	IK03
911401594242	RC099V G3 LED52/840 PSD W60L120 OC	Opal	IK03
911401594442	RC099V G3 LED36/840 PSD W60L60 OC	Opal	IK03
911401594742	RC099V G3 LED40/840 PSD W60L60	Opal	IK03
911401598142	RC099V G3 LED36/840 PSD W60L60 OC HE	Opal	IK03
911401598442	RC099V G3 LED38/840 PSD W60L60 HE	Opal	IK03

## GreenPerform Panel RC099V G3

