



When light really matters

GreenPerform Panel RC099V G3

GreenPerform panel RC099V G3 is an affordable LED panel delivering comfortable light with excellent uniformity. It offers 3 types, 600x600, 300x1200, and 600x1200mm with max: 140lm/w. Its UGR19 brings more visual comfort in the office. Equipped with Dali, Interact and EcoSet, RC099V G2 offers easy connection to control system to bring better energy saving.

Benefits

- Full range offer from 600x600, 300x1200 to 600x1200mm to cover key applications
- Low glare UGR19 to provide visual comfort
- Dali , Interact, EcoSet interface are available for system control

Features

- System efficiency 140lm/W(max)
- 3800lm lumen output for 600x600 and 300x1200mm versions; 5400lm for 600x1200mm version
- CRI 80 and CRI90 are both available
- Higher lumen output 4800lm is available for 600*600mm size

Application

- Open plan office
- Public indoor area
- Meeting/training room

Specifications

Mounting type	Recessed
Ceiling type	T-Bar ceiling Concealed profile ceiling

Mains Voltage	220-240V / 50/60Hz
Dimming	WIA: Wireless control, compatible with Interact Pro SIA: Wireless control, compatible with SNS210 sensor

GreenPerform Panel RC099V G3

Control system input	Dali / WIA / SIA / EcoSet
Integrated sensors	SIA version with SNS210 sensor
Lumen maintenance at median useful life 50.000h	L70B50
Luminaire efficacy	140lm/w 120lm/w
Correlated color temperature - CCT	840 850 860 940 950 965

Risk Group	RG0
Mechanical impact protection	IK03
Ingress protection	IP20
UGR	22 19
Installation	Recessed
Warranty	5 years

Versions



RTP-OF-RC099X



Philips-Greenperform-Panel-RC099-G3-24-RTP





RTP-OF-RC099X







Philips-Greenperform-Panel-RC099-G3-22-RTP

Dimensional drawing



GreenPerform Panel RC099V G3

Dimensional drawing



Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 or 60 Hz

Mechanical and Housing

Housing Color	White RAL 9003
Ingress protection code	IP20

Approval and Application

Ambient temperature range	-20 °C to 45 °C
CE mark	Yes

Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
-------------------------	-------------

General Information

Order Code	Full Product Name	Service tag	Order Code	Full Product Name	Service tag
911401533343	RC099X G3 LED56/840 L1W W60L120	-	911401586642	RC099V G3 LED40/850 PSU W30L120	Yes
911401551343	RC099X G3 LED52/940 L1W W60L120 OC	-	911401586742	RC099V G3 LED40/840 PSU W30L120	Yes
911401509443	RC099V G3 LED49/865 PSU W30L120	Yes	911401593442	RC099V G3 LED36/840 PSU W30L120 OC HE	Yes
911401509543	RC099V G3 LED50/850 PSU W30L120	Yes	911401593742	RC099V G3 LED38/840 PSU W30L120 HE	Yes
911401509643	RC099V G3 LED50/840 PSU W30L120	Yes	911401594342	RC099V G3 LED36/840 PSD W30L120 OC	Yes
911401585342	RC099V G3 LED37/865 PSU W30L120 OC	Yes	911401594642	RC099V G3 LED40/840 PSD W30L120	Yes
911401585442	RC099V G3 LED37/850 PSU W30L120 OC	Yes	911401598042	RC099V G3 LED36/840 PSD W30L120 OC HE	Yes
911401585542	RC099V G3 LED37/840 PSU W30L120 OC	Yes	911401598342	RC099V G3 LED38/840 PSD W30L120 HE	Yes
911401586542	RC099V G3 LED39/865 PSU W30L120	Yes	911401533643	RC099X G3 LED50/840 L1W W60L120 OC HE	-

GreenPerform Panel RC099V G3

Order Code	Full Product Name	Service tag
911401533943	RC099X G3 LED54/840 L1W W60L120 HE	-
911401551943	RC099X G3 LED50/940 L1W W60L120 OC HE	-
911401552243	RC099X G3 LED54/940 L1W W60L120 HE	-
911401533743	RC099X G3 LED36/840 L1W W30L120 OC HE	-
911401534043	RC099X G3 LED38/840 L1W W30L120 HE	-
911401552043	RC099X G3 LED36/940 L1W W30L120 OC HE	-
911401552343	RC099X G3 LED38/940 L1W W30L120 HE	-
911401533543	RC099X G3 LED40/840 L1W W60L60	-
911401551543	RC099X G3 LED37/940 L1W W60L60 OC	-
911401551843	RC099X G3 LED40/940 L1W W60L60	-
911401533843	RC099X G3 LED36/840 L1W W60L60 OC HE	-
911401534143	RC099X G3 LED38/840 L1W W60L60 HE	-
911401552443	RC099X G3 LED38/940 L1W W60L60 HE	-
911401509143	RC099V G3 LED69/865 PSU W60L120	Yes
911401509243	RC099V G3 LED71/850 PSU W60L120	Yes
911401509343	RC099V G3 LED71/840 PSU W60L120	Yes
911401584942	RC099V G3 LED51/865 PSU W60L120 OC	Yes
911401585042	RC099V G3 LED52/850 PSU W60L120 OC	Yes
911401585142	RC099V G3 LED52/840 PSU W60L120 OC	Yes
911401586142	RC099V G3 LED55/865 PSU W60L120	Yes
911401586242	RC099V G3 LED56/850 PSU W60L120	Yes
911401586342	RC099V G3 LED56/840 PSU W60L120	Yes
911401593342	RC099V G3 LED50/840 PSU W60L120 OC HE	Yes
911401593642	RC099V G3 LED54/840 PSU W60L120 HE	Yes
911401594542	RC099V G3 LED56/840 PSD W60L120	Yes

Order Code	Full Product Name	Service tag
911401597942	RC099V G3 LED50/840 PSD W60L120 OC HE	Yes
911401598242	RC099V G3 LED54/840 PSD W60L120 HE	Yes
911401533443	RC099X G3 LED40/840 L1W W30L120	-
911401551443	RC099X G3 LED37/940 L1W W30L120 OC	-
911401551743	RC099X G3 LED40/940 L1W W30L120	-
911401509743	RC099V G3 LED49/865 PSU W60L60	Yes
911401509843	RC099V G3 LED50/850 PSU W60L60	Yes
911401509943	RC099V G3 LED50/840 PSU W60L60	Yes
911401584642	RC099V G3 LED39/865 PSU W60L60 L	Yes
911401584742	RC099V G3 LED40/850 PSU W60L60 L	Yes
911401584842	RC099V G3 LED40/840 PSU W60L60 L	Yes
911401585742	RC099V G3 LED37/865 PSU W60L60 OC	Yes
911401585842	RC099V G3 LED37/850 PSU W60L60 OC	Yes
911401585942	RC099V G3 LED37/840 PSU W60L60 OC	Yes
911401586942	RC099V G3 LED39/865 PSU W60L60	Yes
911401587042	RC099V G3 LED40/850 PSU W60L60	Yes
911401587142	RC099V G3 LED40/840 PSU W60L60	Yes
911401593542	RC099V G3 LED36/840 PSU W60L60 OC HE	Yes
911401593842	RC099V G3 LED38/840 PSU W60L60 HE	Yes
911401594242	RC099V G3 LED52/840 PSD W60L120 OC	Yes
911401594442	RC099V G3 LED36/840 PSD W60L60 OC	Yes
911401594742	RC099V G3 LED40/840 PSD W60L60	Yes
911401598142	RC099V G3 LED36/840 PSD W60L60 OC HE	Yes
911401598442	RC099V G3 LED38/840 PSD W60L60 HE	Yes

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401533343	RC099X G3 LED56/840 L1W W60L120	4000 K	80	130 lm/W	5,600 lm
911401551343	RC099X G3 LED52/940 L1W W60L120 OC	4000 K	90	115 lm/W	5,200 lm
911401509443	RC099V G3 LED49/865 PSU W30L120	6500 K	>80	120 lm/W	4,800 lm
911401509543	RC099V G3 LED50/850 PSU W30L120	5000 K	>80	120 lm/W	4,800 lm
911401509643	RC099V G3 LED50/840 PSU W30L120	4000 K	>80	120 lm/W	4,800 lm
911401585342	RC099V G3 LED37/865 PSU W30L120 OC	6500 K	>80	110 lm/W	3,600 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401585442	RC099V G3 LED37/850 PSU W30L120 OC	5000 K	>80	110 lm/W	3,600 lm
911401585542	RC099V G3 LED37/840 PSU W30L120 OC	4000 K	>80	110 lm/W	3,600 lm
911401586542	RC099V G3 LED39/865 PSU W30L120	6500 K	>80	125 lm/W	3,800 lm
911401586642	RC099V G3 LED40/850 PSU W30L120	5000 K	>80	125 lm/W	3,800 lm
911401586742	RC099V G3 LED40/840 PSU W30L120	4000 K	>80	125 lm/W	3,800 lm
911401593442	RC099V G3 LED36/840 PSU W30L120 OC HE	4000 K	>80	130 lm/W	3,600 lm

GreenPerform Panel RC099V G3

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401593742	RC099V G3 LED38/840 PSU W30L120 HE	4000 K	>80	140 lm/W	3,800 lm
911401594342	RC099V G3 LED36/840 PSD W30L120 OC	4000 K	>80	130 lm/W	3,600 lm
911401594642	RC099V G3 LED40/840 PSD W30L120	4000 K	>80	125 lm/W	3,800 lm
911401598042	RC099V G3 LED36/840 PSD W30L120 OC HE	4000 K	>80	130 lm/W	3,600 lm
911401598342	RC099V G3 LED38/840 PSD W30L120 HE	4000 K	>80	140 lm/W	3,800 lm
911401533643	RC099X G3 LED50/840 L1W W60L120 OC HE	4000 K	≥80	135 lm/W	5,000 lm
911401533943	RC099X G3 LED54/840 L1W W60L120 HE	4000 K	≥80	140 lm/W	5,400 lm
911401551943	RC099X G3 LED50/940 L1W W60L120 OC HE	4000 K	≥90	135 lm/W	5,000 lm
911401552243	RC099X G3 LED54/940 L1W W60L120 HE	4000 K	≥90	140 lm/W	5,400 lm
911401533743	RC099X G3 LED36/840 L1W W30L120 OC HE	4000 K	≥80	130 lm/W	3,600 lm
911401534043	RC099X G3 LED38/840 L1W W30L120 HE	4000 K	≥80	140 lm/W	3,800 lm
911401552043	RC099X G3 LED36/940 L1W W30L120 OC HE	4000 K	≥90	130 lm/W	3,600 lm
911401552343	RC099X G3 LED38/940 L1W W30L120 HE	4000 K	≥90	140 lm/W	3,800 lm
911401533543	RC099X G3 LED40/840 L1W W60L60	4000 K	80	126 lm/W	4,000 lm
911401551543	RC099X G3 LED37/940 L1W W60L60 OC	4000 K	90	115 lm/W	3,700 lm
911401551843	RC099X G3 LED40/940 L1W W60L60	4000 K	90	126 lm/W	4,000 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401533843	RC099X G3 LED36/840 L1W W60L60 OC HE	4000 K	≥80	130 lm/W	3,600 lm
911401534143	RC099X G3 LED38/840 L1W W60L60 HE	4000 K	≥80	140 lm/W	3,800 lm
911401552443	RC099X G3 LED38/940 L1W W60L60 HE	4000 K	≥90	140 lm/W	3,800 lm
911401509143	RC099V G3 LED69/865 PSU W60L120	6500 K	>80	135 lm/W	6,800 lm
911401509243	RC099V G3 LED71/850 PSU W60L120	5000 K	>80	135 lm/W	6,800 lm
911401509343	RC099V G3 LED71/840 PSU W60L120	4000 K	>80	135 lm/W	6,800 lm
911401584942	RC099V G3 LED51/865 PSU W60L120 OC	6500 K	>80	110 lm/W	5,000 lm
911401585042	RC099V G3 LED52/850 PSU W60L120 OC	5000 K	>80	110 lm/W	5,000 lm
911401585142	RC099V G3 LED52/840 PSU W60L120 OC	4000 K	>80	110 lm/W	5,000 lm
911401586142	RC099V G3 LED55/865 PSU W60L120	6500 K	>80	125 lm/W	5,400 lm
911401586242	RC099V G3 LED56/850 PSU W60L120	5000 K	>80	125 lm/W	5,400 lm
911401586342	RC099V G3 LED56/840 PSU W60L120	4000 K	>80	125 lm/W	5,400 lm
911401593342	RC099V G3 LED50/840 PSU W60L120 OC HE	4000 K	>80	135 lm/W	5,000 lm
911401593642	RC099V G3 LED54/840 PSU W60L120 HE	4000 K	>80	140 lm/W	5,400 lm
911401594542	RC099V G3 LED56/840 PSD W60L120	4000 K	>80	125 lm/W	5,400 lm
911401597942	RC099V G3 LED50/840 PSD W60L120 OC HE	4000 K	>80	135 lm/W	5,000 lm

GreenPerform Panel RC099V G3

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401598242	RC099V G3 LED54/840 PSD W60L120 HE	4000 K	>80	140 lm/W	5,400 lm
911401533443	RC099X G3 LED40/840 L1W W30L120	4000 K	80	126 lm/W	4,000 lm
911401551443	RC099X G3 LED37/940 L1W W30L120 OC	4000 K	90	115 lm/W	3,700 lm
911401551743	RC099X G3 LED40/940 L1W W30L120	4000 K	90	126 lm/W	4,000 lm
911401509743	RC099V G3 LED49/865 PSU W60L60	6500 K	>80	120 lm/W	4,800 lm
911401509843	RC099V G3 LED50/850 PSU W60L60	5000 K	>80	120 lm/W	4,800 lm
911401509943	RC099V G3 LED50/840 PSU W60L60	4000 K	>80	120 lm/W	4,800 lm
911401584642	RC099V G3 LED39/865 PSU W60L60 L	6500 K	>80	113 lm/W	3,800 lm
911401584742	RC099V G3 LED40/850 PSU W60L60 L	5000 K	>80	113 lm/W	3,800 lm
911401584842	RC099V G3 LED40/840 PSU W60L60 L	4000 K	>80	113 lm/W	3,800 lm
911401585742	RC099V G3 LED37/865 PSU W60L60 OC	6500 K	>80	110 lm/W	3,600 lm
911401585842	RC099V G3 LED37/850 PSU W60L60 OC	5000 K	>80	110 lm/W	3,600 lm
911401585942	RC099V G3 LED37/840 PSU W60L60 OC	4000 K	>80	110 lm/W	3,600 lm
911401586942	RC099V G3 LED39/865 PSU W60L60	6500 K	>80	125 lm/W	3,800 lm
911401587042	RC099V G3 LED40/850 PSU W60L60	5000 K	>80	125 lm/W	3,800 lm
911401587142	RC099V G3 LED40/840 PSU W60L60	4000 K	>80	125 lm/W	3,800 lm
911401593542	RC099V G3 LED36/840 PSU W60L60 OC HE	4000 K	>80	130 lm/W	3,600 lm
911401593842	RC099V G3 LED38/840 PSU W60L60 HE	4000 K	>80	140 lm/W	3,800 lm
911401594242	RC099V G3 LED52/840 PSD W60L120 OC	4000 K	>80	135 lm/W	5,000 lm
911401594442	RC099V G3 LED36/840 PSD W60L60 OC	4000 K	>80	130 lm/W	3,600 lm
911401594742	RC099V G3 LED40/840 PSD W60L60	4000 K	>80	125 lm/W	3,800 lm
911401598142	RC099V G3 LED36/840 PSD W60L60 OC HE	4000 K	>80	130 lm/W	3,600 lm
911401598442	RC099V G3 LED38/840 PSD W60L60 HE	4000 K	>80	140 lm/W	3,800 lm

Operating and Electrical

Order Code	Full Product Name	Protection class IEC	Power Consumption
911401533343	RC099X G3 LED56/840 L1W W60L120	Safety class II	43 W
911401551343	RC099X G3 LED52/940 L1W W60L120 OC	Safety class II	45.5 W
911401509443	RC099V G3 LED49/865 PSU W30L120	Safety class II	40 W
911401509543	RC099V G3 LED50/850 PSU W30L120	Safety class II	40 W
911401509643	RC099V G3 LED50/840 PSU W30L120	Safety class II	40 W
911401585342	RC099V G3 LED37/865 PSU W30L120 OC	Safety class II	32.7 W
911401585442	RC099V G3 LED37/850 PSU W30L120 OC	Safety class II	32.7 W
911401585542	RC099V G3 LED37/840 PSU W30L120 OC	Safety class II	32.7 W

GreenPerform Panel RC099V G3

Order Code	Full Product Name	Protection class IEC	Power Consumption
911401586542	RC099V G3 LED39/865 PSU W30L120	Safety class II	30.4 W
911401586642	RC099V G3 LED40/850 PSU W30L120	Safety class II	30.4 W
911401586742	RC099V G3 LED40/840 PSU W30L120	Safety class II	30.4 W
911401593442	RC099V G3 LED36/840 PSU W30L120 OC HE	Safety class II	27.7 W
911401593742	RC099V G3 LED38/840 PSU W30L120 HE	Safety class II	27.1 W
911401594342	RC099V G3 LED36/840 PSD W30L120 OC	Safety class II	27.7 W
911401594642	RC099V G3 LED40/840 PSD W30L120	Safety class II	30.4 W
911401598042	RC099V G3 LED36/840 PSD W30L120 OC HE	Safety class II	27.7 W
911401598342	RC099V G3 LED38/840 PSD W30L120 HE	Safety class II	27.1 W
911401533643	RC099X G3 LED50/840 L1W W60L120 OC HE	Safety class II	37.0 W
911401533943	RC099X G3 LED54/840 L1W W60L120 HE	Safety class II	38.6 W
911401551943	RC099X G3 LED50/940 L1W W60L120 OC HE	Safety class II	37.0 W
911401552243	RC099X G3 LED54/940 L1W W60L120 HE	Safety class II	38.6 W
911401533743	RC099X G3 LED36/840 L1W W30L120 OC HE	Safety class I	27.7 W
911401534043	RC099X G3 LED38/840 L1W W30L120 HE	Safety class I	27.1 W
911401552043	RC099X G3 LED36/940 L1W W30L120 OC HE	Safety class I	27.7 W
911401552343	RC099X G3 LED38/940 L1W W30L120 HE	Safety class I	27.1 W
911401533543	RC099X G3 LED40/840 L1W W60L60	Safety class II	31.5 W
911401551543	RC099X G3 LED37/940 L1W W60L60 OC	Safety class II	31.5 W
911401551843	RC099X G3 LED40/940 L1W W60L60	Safety class II	31.5 W
911401533843	RC099X G3 LED36/840 L1W W60L60 OC HE	Safety class II	27.7 W
911401534143	RC099X G3 LED38/840 L1W W60L60 HE	Safety class II	27.1 W
911401552443	RC099X G3 LED38/940 L1W W60L60 HE	Safety class II	27.1 W
911401509143	RC099V G3 LED69/865 PSU W60L120	Safety class II	50.4 W
911401509243	RC099V G3 LED71/850 PSU W60L120	Safety class II	50.4 W

Order Code	Full Product Name	Protection class IEC	Power Consumption
911401509343	RC099V G3 LED71/840 PSU W60L120	Safety class II	50.4 W
911401584942	RC099V G3 LED51/865 PSU W60L120 OC	Safety class II	45.5 W
911401585042	RC099V G3 LED52/850 PSU W60L120 OC	Safety class II	45.5 W
911401585142	RC099V G3 LED52/840 PSU W60L120 OC	Safety class II	45.5 W
911401586142	RC099V G3 LED55/865 PSU W60L120	Safety class II	43.2 W
911401586242	RC099V G3 LED56/850 PSU W60L120	Safety class II	43.2 W
911401586342	RC099V G3 LED56/840 PSU W60L120	Safety class II	43.2 W
911401593342	RC099V G3 LED50/840 PSU W60L120 OC HE	Safety class II	37 W
911401593642	RC099V G3 LED54/840 PSU W60L120 HE	Safety class II	38.6 W
911401594542	RC099V G3 LED56/840 PSD W60L120	Safety class II	43.2 W
911401597942	RC099V G3 LED50/840 PSD W60L120 OC HE	Safety class II	37 W
911401598242	RC099V G3 LED54/840 PSD W60L120 HE	Safety class II	38.6 W
911401533443	RC099X G3 LED40/840 L1W W30L120	Safety class II	31.5 W
911401551443	RC099X G3 LED37/940 L1W W30L120 OC	Safety class II	31.5 W
911401551743	RC099X G3 LED40/940 L1W W30L120	Safety class II	31.5 W
911401509743	RC099V G3 LED49/865 PSU W60L60	Safety class II	40 W
911401509843	RC099V G3 LED50/850 PSU W60L60	Safety class II	40 W
911401509943	RC099V G3 LED50/840 PSU W60L60	Safety class II	40 W
911401584642	RC099V G3 LED39/865 PSU W60L60 L	Safety class II	33.6 W
911401584742	RC099V G3 LED40/850 PSU W60L60 L	Safety class II	33.6 W
911401584842	RC099V G3 LED40/840 PSU W60L60 L	Safety class II	33.6 W
911401585742	RC099V G3 LED37/865 PSU W60L60 OC	Safety class II	32.7 W
911401585842	RC099V G3 LED37/850 PSU W60L60 OC	Safety class II	32.7 W
911401585942	RC099V G3 LED37/840 PSU W60L60 OC	Safety class II	32.7 W
911401586942	RC099V G3 LED39/865 PSU W60L60	Safety class II	30.4 W

GreenPerform Panel RC099V G3

Order Code	Full Product Name	Protection class IEC	Power Consumption
911401587042	RC099V G3 LED40/850 PSU W60L60	Safety class II	30.4 W
911401587142	RC099V G3 LED40/840 PSU W60L60	Safety class II	30.4 W
911401593542	RC099V G3 LED36/840 PSU W60L60 OC HE	Safety class II	27.7 W
911401593842	RC099V G3 LED38/840 PSU W60L60 HE	Safety class II	27.1 W
911401594242	RC099V G3 LED52/840 PSD W60L120 OC	Safety class II	37 W

Order Code	Full Product Name	Protection class IEC	Power Consumption
911401594442	RC099V G3 LED36/840 PSD W60L60 OC	Safety class II	27.7 W
911401594742	RC099V G3 LED40/840 PSD W60L60	Safety class II	30.4 W
911401598142	RC099V G3 LED36/840 PSD W60L60 OC HE	Safety class II	27.7 W
911401598442	RC099V G3 LED38/840 PSD W60L60 HE	Safety class II	27.1 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401533343	RC099X G3 LED56/840 L1W W60L120	DALI
911401551343	RC099X G3 LED52/940 L1W W60L120 OC	DALI
911401509443	RC099V G3 LED49/865 PSU W30L120	No
911401509543	RC099V G3 LED50/850 PSU W30L120	No
911401509643	RC099V G3 LED50/840 PSU W30L120	No
911401585342	RC099V G3 LED37/865 PSU W30L120 OC	No
911401585442	RC099V G3 LED37/850 PSU W30L120 OC	No
911401585542	RC099V G3 LED37/840 PSU W30L120 OC	No
911401586542	RC099V G3 LED39/865 PSU W30L120	No
911401586642	RC099V G3 LED40/850 PSU W30L120	No
911401586742	RC099V G3 LED40/840 PSU W30L120	No
911401593442	RC099V G3 LED36/840 PSU W30L120 OC HE	No
911401593742	RC099V G3 LED38/840 PSU W30L120 HE	No
911401594342	RC099V G3 LED36/840 PSD W30L120 OC	DALI
911401594642	RC099V G3 LED40/840 PSD W30L120	DALI
911401598042	RC099V G3 LED36/840 PSD W30L120 OC HE	DALI
911401598342	RC099V G3 LED38/840 PSD W30L120 HE	DALI
911401533643	RC099X G3 LED50/840 L1W W60L120 OC HE	DALI
911401533943	RC099X G3 LED54/840 L1W W60L120 HE	DALI
911401551943	RC099X G3 LED50/940 L1W W60L120 OC HE	DALI
911401552243	RC099X G3 LED54/940 L1W W60L120 HE	DALI
911401533743	RC099X G3 LED36/840 L1W W30L120 OC HE	DALI
911401534043	RC099X G3 LED38/840 L1W W30L120 HE	DALI
911401552043	RC099X G3 LED36/940 L1W W30L120 OC HE	DALI
911401552343	RC099X G3 LED38/940 L1W W30L120 HE	DALI
911401533543	RC099X G3 LED40/840 L1W W60L60	DALI
911401551543	RC099X G3 LED37/940 L1W W60L60 OC	DALI
911401551843	RC099X G3 LED40/940 L1W W60L60	DALI
911401533843	RC099X G3 LED36/840 L1W W60L60 OC HE	DALI
911401534143	RC099X G3 LED38/840 L1W W60L60 HE	DALI
911401552443	RC099X G3 LED38/940 L1W W60L60 HE	DALI
911401509143	RC099V G3 LED69/865 PSU W60L120	No
911401509243	RC099V G3 LED71/850 PSU W60L120	No
911401509343	RC099V G3 LED71/840 PSU W60L120	No

Order Code	Full Product Name	Dimmable
911401584942	RC099V G3 LED51/865 PSU W60L120 OC	No
911401585042	RC099V G3 LED52/850 PSU W60L120 OC	No
911401585142	RC099V G3 LED52/840 PSU W60L120 OC	No
911401586142	RC099V G3 LED55/865 PSU W60L120	No
911401586242	RC099V G3 LED56/850 PSU W60L120	No
911401586342	RC099V G3 LED56/840 PSU W60L120	No
911401593342	RC099V G3 LED50/840 PSU W60L120 OC HE	No
911401593642	RC099V G3 LED54/840 PSU W60L120 HE	No
911401594542	RC099V G3 LED56/840 PSD W60L120	DALI
911401597942	RC099V G3 LED50/840 PSD W60L120 OC HE	DALI
911401598242	RC099V G3 LED54/840 PSD W60L120 HE	DALI
911401533443	RC099X G3 LED40/840 L1W W30L120	DALI
911401551443	RC099X G3 LED37/940 L1W W30L120 OC	DALI
911401551743	RC099X G3 LED40/940 L1W W30L120	DALI
911401509743	RC099V G3 LED49/865 PSU W60L60	No
911401509843	RC099V G3 LED50/850 PSU W60L60	No
911401509943	RC099V G3 LED50/840 PSU W60L60	No
911401584642	RC099V G3 LED39/865 PSU W60L60 L	No
911401584742	RC099V G3 LED40/850 PSU W60L60 L	No
911401584842	RC099V G3 LED40/840 PSU W60L60 L	No
911401585742	RC099V G3 LED37/865 PSU W60L60 OC	No
911401585842	RC099V G3 LED37/850 PSU W60L60 OC	No
911401585942	RC099V G3 LED37/840 PSU W60L60 OC	No
911401586942	RC099V G3 LED39/865 PSU W60L60	No
911401587042	RC099V G3 LED40/850 PSU W60L60	No
911401587142	RC099V G3 LED40/840 PSU W60L60	No
911401593542	RC099V G3 LED36/840 PSU W60L60 OC HE	No
911401593842	RC099V G3 LED38/840 PSU W60L60 HE	No
911401594242	RC099V G3 LED52/840 PSD W60L120 OC	DALI
911401594442	RC099V G3 LED36/840 PSD W60L60 OC	DALI
911401594742	RC099V G3 LED40/840 PSD W60L60	DALI
911401598142	RC099V G3 LED36/840 PSD W60L60 OC HE	DALI
911401598442	RC099V G3 LED38/840 PSD W60L60 HE	DALI

Mechanical and Housing

GreenPerform Panel RC099V G3

Order Code	Full Product Name	Optical cover type	Mech. impact protection code
911401533343	RC099X G3 LED56/840 L1W W60L120	PS	IK02
911401551343	RC099X G3 LED52/940 L1W W60L120 OC	PS	IK03
911401509443	RC099V G3 LED49/865 PSU W30L120	Opal	IK03
911401509543	RC099V G3 LED50/850 PSU W30L120	Opal	IK03
911401509643	RC099V G3 LED50/840 PSU W30L120	Opal	IK03
911401585342	RC099V G3 LED37/865 PSU W30L120 OC	Opal	IK03
911401585442	RC099V G3 LED37/850 PSU W30L120 OC	Opal	IK03
911401585542	RC099V G3 LED37/840 PSU W30L120 OC	Opal	IK03
911401586542	RC099V G3 LED39/865 PSU W30L120	Opal	IK03
911401586642	RC099V G3 LED40/850 PSU W30L120	Opal	IK03
911401586742	RC099V G3 LED40/840 PSU W30L120	Opal	IK03
911401593442	RC099V G3 LED36/840 PSU W30L120 OC HE	Opal	IK03
911401593742	RC099V G3 LED38/840 PSU W30L120 HE	Opal	IK03
911401594342	RC099V G3 LED36/840 PSD W30L120 OC	Opal	IK03
911401594642	RC099V G3 LED40/840 PSD W30L120	Opal	IK03
911401598042	RC099V G3 LED36/840 PSD W30L120 OC HE	Opal	IK03
911401598342	RC099V G3 LED38/840 PSD W30L120 HE	Opal	IK03
911401533643	RC099X G3 LED50/840 L1W W60L120 OC HE	Opal	IK03
911401533943	RC099X G3 LED54/840 L1W W60L120 HE	Opal	IK03
911401551943	RC099X G3 LED50/940 L1W W60L120 OC HE	Opal	IK03
911401552243	RC099X G3 LED54/940 L1W W60L120 HE	Opal	IK03
911401533743	RC099X G3 LED36/840 L1W W30L120 OC HE	Opal	IK03
911401534043	RC099X G3 LED38/840 L1W W30L120 HE	Opal	IK03
911401552043	RC099X G3 LED36/940 L1W W30L120 OC HE	Opal	IK03
911401552343	RC099X G3 LED38/940 L1W W30L120 HE	Opal	IK03
911401533543	RC099X G3 LED40/840 L1W W60L60	PS	IK02
911401551543	RC099X G3 LED37/940 L1W W60L60 OC	PS	IK02
911401551843	RC099X G3 LED40/940 L1W W60L60	PS	IK02
911401533843	RC099X G3 LED36/840 L1W W60L60 OC HE	Opal	IK03
911401534143	RC099X G3 LED38/840 L1W W60L60 HE	Opal	IK03

Order Code	Full Product Name	Optical cover type	Mech. impact protection code
911401552443	RC099X G3 LED38/940 L1W W60L60 HE	Opal	IK03
911401509143	RC099V G3 LED69/865 PSU W60L120	Opal	IK03
911401509243	RC099V G3 LED71/850 PSU W60L120	Opal	IK03
911401509343	RC099V G3 LED71/840 PSU W60L120	Opal	IK03
911401584942	RC099V G3 LED51/865 PSU W60L120 OC	Opal	IK03
911401585042	RC099V G3 LED52/850 PSU W60L120 OC	Opal	IK03
911401585142	RC099V G3 LED52/840 PSU W60L120 OC	Opal	IK03
911401586142	RC099V G3 LED55/865 PSU W60L120	Opal	IK03
911401586242	RC099V G3 LED56/850 PSU W60L120	Opal	IK03
911401586342	RC099V G3 LED56/840 PSU W60L120	Opal	IK03
911401593342	RC099V G3 LED50/840 PSU W60L120 OC HE	Opal	IK03
911401593642	RC099V G3 LED54/840 PSU W60L120 HE	Opal	IK03
911401594542	RC099V G3 LED56/840 PSD W60L120	Opal	IK03
911401597942	RC099V G3 LED50/840 PSD W60L120 OC HE	Opal	IK03
911401598242	RC099V G3 LED54/840 PSD W60L120 HE	Opal	IK03
911401533443	RC099X G3 LED40/840 L1W W30L120	PS	IK02
911401551443	RC099X G3 LED37/940 L1W W30L120 OC	PS	IK02
911401551743	RC099X G3 LED40/940 L1W W30L120	PS	IK02
911401509743	RC099V G3 LED49/865 PSU W60L60	Opal	IK03
911401509843	RC099V G3 LED50/850 PSU W60L60	Opal	IK03
911401509943	RC099V G3 LED50/840 PSU W60L60	Opal	IK03
911401584642	RC099V G3 LED39/865 PSU W60L60 L	Opal	IK03
911401584742	RC099V G3 LED40/850 PSU W60L60 L	Opal	IK03
911401584842	RC099V G3 LED40/840 PSU W60L60 L	Opal	IK03
911401585742	RC099V G3 LED37/865 PSU W60L60 OC	Opal	IK03
911401585842	RC099V G3 LED37/850 PSU W60L60 OC	Opal	IK03
911401585942	RC099V G3 LED37/840 PSU W60L60 OC	Opal	IK03
911401586942	RC099V G3 LED39/865 PSU W60L60	Opal	IK03
911401587042	RC099V G3 LED40/850 PSU W60L60	Opal	IK03
911401587142	RC099V G3 LED40/840 PSU W60L60	Opal	IK03
911401593542	RC099V G3 LED36/840 PSU W60L60 OC HE	Opal	IK03
911401593842	RC099V G3 LED38/840 PSU W60L60 HE	Opal	IK03
911401594242	RC099V G3 LED52/840 PSD W60L120 OC	Opal	IK03
911401594442	RC099V G3 LED36/840 PSD W60L60 OC	Opal	IK03

GreenPerform Panel RC099V G3

Order Code	Full Product Name	Optical cover type	Mech. impact protection code
911401594742	RC099V G3 LED40/840 PSD W60L60	Opal	IK03
911401598142	RC099V G3 LED36/840 PSD W60L60	Opal	IK03
	OC HE		

Order Code	Full Product Name	Optical cover type	Mech. impact protection code
911401598442	RC099V G3 LED38/840 PSD W60L60	Opal	IK03
	HE		

