



Energy saving without compromise

GreenPerform Troffer

GreenPerform troffer improves the compact design of the last generation with performance improvement and more variants for different markets. Integrating with all available system: POE, InterAct office wireless, InterAct Office Pro, ActiLume controller, GreenPerform troffer offers additional energy saving and connected features.

Benefits

- Upgrade to smart office with more options
- Energy saving
- Slim housing
- Comfortable light
- Good light quality
- Office compliant
- Reliable performance

Features

- Compatible with all available Philips systems
- Efficacy up to 125lm/W
- Slim design with height less than 46mm
- Improved optical design without zebra effect
- CRI > 80, SDCM<4, Flicker free
- UGR 19 available
- Lifetime L70 50,000 hours

Application

- Open Office
- Public Area
- Meeting Room
- Training Room

GreenPerform Troffer

Specifications

Ceiling type	T-bar ceiling
Mains Voltage	220-240V / 50-60Hz
Dimming	PSU: non-dimmable
	PSD: Dimmable via Dali-broadcasting
	WIA: Wireless control, compatible with Interact
	SIA: Wireless control, compatible with Interact and with SNS210 sensor
Control system input	Dali





Lumen maintenance at median useful life	L70B50
50.000h	
Correlated color temperature - CCT	840
865	
UGR	19 is available through certain types
Installation	Recessed

Versions




GreenPerform Troffer RC100B 60x120

Dimensional drawing



GreenPerform Troffer

Dimensional drawing



General Information

Driver included	Yes
Number of gear units	1 unit

Operating and Electrical

Protection class IEC	Safety class I
Suitable for random switching	No

Mechanical and Housing

Housing Color	White
Mech. impact protection code	IK03
Ingress protection code	IP20

Approval and Application

Ambient temperature range	-20 to +40 °C
CE mark	Yes
ENEC mark	-

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

General Information

Order Code	Full Product Name	Light source replaceable	Service tag
911401512547	RC100B LED37S 840 W30L120 PSU G3	-	-
911401513051	RC100B LED37S 840 W30L120 PSD OC G3	No	Yes
911401513147	SM100C LED37S 840 W30L120 PSU G3	-	-
911401513247	SM100C LED37S 840 W30L120 PSU G3	-	-
911401513251	RC100B LED37S 840 W30L120 PSD G3	No	Yes
911401513351	RC100B LED37S 840 W30L120 PSU G3	No	Yes
911401513751	RC100B LED37S 865 W30L120 PSU UNV G3	No	Yes
911401513847	RC100B LED37S 840 W30L120 PSD OC G3	-	-
911401513947	RC100B LED37S 840 W30L120 PSD G3	-	-
911401514047	RC100B LED37S 840 W30L120 PSD CAU	-	-
911401514347	SM100C LED37S 840 W30L120 PSD G3	-	-
911401514747	RC100X LED37/840 W30L120 WIA	-	-
911401516547	RC100X LED37S 840 W30L120 S15 G3 OC CAU	-	-
911401519451	SM100C LED37S 840 W30L120 PSU G3	No	Yes
911401519551	SM100C LED37S 840 W30L120 PSD G3	No	Yes
911401519951	SM100C LED37S 865 W30L120 PSU UNV G3	No	Yes
911401508451	RC100B LED27S 840 W60L60 PSU G3	No	Yes
911401508651	RC100B LED27S 865 W60L60 PSU G3	No	Yes
911401509551	RC100B LED37S 840 W60L60 PSU UNV G3	No	Yes
911401509651	SM100C LED37S 840 W60L60 PSD G3	No	Yes
911401509951	SM100C LED27S 840 W60L60 PSU G3	No	Yes
911401510151	SM100C LED37S 840 W60L60 PSU G3	No	Yes
911401510751	RC100B LED37S 840 W60L60 PSU G3	No	Yes
911401510851	RC100B LED37S 840 W60L60 PSD OC G3	No	Yes
911401510951	RC100B LED37S 865 W60L60 PSU G3	No	Yes
911401511151	RC100B LED37S 840 W60L60 PSD G3	No	Yes
911401568841	RC100X LED37S 840 W60L60 IAR G3	No	Yes
911401514947	RC100X LED37S 940 W60L60 SIA S2 G3	-	-
911401515047	RC100X LED37S 840 W60L60 SIA S2 G3	-	-
911401515147	RC100X LED37S 865 W60L60 SIA S2 G3	-	-
911401515247	RC100X LED37S 840 W60L60 SIA S15 G3	-	-
911401515347	RC100X LED37S 865 W60L60 SIA S15 G3	-	-
911401515447	RC100X LED37S 940 W60L60 SIA S15 G3	-	-
911401515547	RC100X LED37S 940 W60L60 SIA S2 G3 CAU	-	-
911401515647	RC100X LED37S 840 W60L60 SIA S2 G3 CAU	-	-
911401515747	RC100X LED37S 865 W60L60 SIA S2 G3 CAU	-	-
911401515847	RC100X LED37S 840 W60L60 SIA S15 G3 CAU	-	-
911401515947	RC100X LED37S 865 W60L60 SIA S15 G3 CAU	-	-
911401516047	RC100X LED37S 940 W60L60 SIA S15 G3 CAU	-	-
911401516147	RC100X LED37S 840 W60L60 SIA S2 OC CAU	-	-
911401511847	RC100B LED27S 840 W60L60 PSU G3	-	-
911401511947	RC100B LED27S 865 W60L60 PSU G3	-	-
911401512047	RC100B LED37S 840 W60L60 PSU G3	-	-
911401512147	RC100B LED37S 865 W60L60 PSU G3	-	-
911401512347	RC100B LED37S 840 W60L60 PSU CAU	-	-
911401512447	RC100B LED37S 865 W60L60 PSU CAU	-	-
911401512847	SM100C LED27S 840 W60L60 PSU G3	-	-
911401512947	SM100C LED37S 840 W60L60 PSU G3	-	-
911401513347	RC100B LED37S 840 W60L60 PSD G3	-	-
911401513447	RC100B LED37S 865 W60L60 PSD G3	-	-
911401513647	RC100B LED37S 840 W60L60 PSD OC G3	-	-

Order Code	Full Product Name	Light source replaceable	Service tag
911401513747	RC100B LED37S 865 W60L60 PSD OC G3	-	-
911401514247	SM100C LED37S 840 W60L60 PSD G3	-	-
911401514447	RC100X LED37/840 W60L60 WIA	-	-
911401514547	RC100X LED37/865 W60L60 WIA	-	-
911401514051	RC100B LED37S 840 W60L120 PSD OC CAU	No	Yes
911401514351	RC100B LED54S 840 W60L120 PSU G3	No	Yes
911401517247	RC100B LED54S 840 W60L120 PSD OC CAU	-	-
911401517347	RC100B LED37S 840 W60L120 PSU CAU	-	-
911401517447	RC100B LED54S 840 W60L120 PSU CAU	-	-
911401517547	RC100B LED54S 840 W60L120 PSU G3	-	-

Light Technical (1/2)

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering (CRI)	Luminous Efficacy (rated) (Nom)
911401512547	RC100B LED37S 840 W30L120 PSU G3	120 degree(s)	4000 K	80	155.03875968992247 lm/W
911401513051	RC100B LED37S 840 W30L120 PSD OC G3	-	4000 K	80	121 lm/W
911401513147	SM100C LED37S 840 W30L120 PSU G3	120 degree(s)	4000 K	80	155.03875968992247 lm/W
911401513247	SM100C LED37S 840 W30L120 PSU G3	120 degree(s)	4000 K	80	155.03875968992247 lm/W
911401513251	RC100B LED37S 840 W30L120 PSD G3	-	4000 K	80	116 lm/W
911401513351	RC100B LED37S 840 W30L120 PSU G3	-	4000 K	80	116 lm/W
911401513751	RC100B LED37S 865 W30L120	-	6500 K	80	116 lm/W

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering (CRI)	Luminous Efficacy (rated) (Nom)
911401513847	RC100B LED37S 840 W30L120 PSD OC G3	120 degree(s)	4000 K	80	166.66666666666666 lm/W
911401513947	RC100B LED37S 840 W30L120 PSD G3	120 degree(s)	4000 K	80	158.73015873015873 lm/W
911401514047	RC100B LED37S 840 W30L120 PSD CAU	120 degree(s)	4000 K	80	158.73015873015873 lm/W
911401514347	SM100C LED37S 840 W30L120 PSD G3	120 degree(s)	4000 K	80	158.73015873015873 lm/W
911401514747	RC100X LED37/840 W30L120 WIA	120 degree(s)	4000 K	80	153.2567049808429 lm/W
911401516547	RC100X LED37S 840 W30L120 S15 G3 OC CAU	120 degree(s)	4000 K	80	160.91954022988506 lm/W
911401519451	SM100C LED37S 840	-	4000 K	80	116 lm/W

GreenPerform Troffer

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
	W30L120 PSU G3				
911401519551	SM100C LED37S 840 W30L120 PSD G3	-	4000 K	80	116 lm/W
911401519951	SM100C LED37S 865 W30L120 PSU UNV G3	-	6500 K	80	116 lm/W
911401508451	RC100B LED27S 840 W60L60 PSU G3	-	4000 K	80	117 lm/W
911401508651	RC100B LED27S 865 W60L60 PSU G3	-	6500 K	80	117 lm/W
911401509551	RC100B LED37S 840 W603L603 PSU UNV G3	-	4000 K	80	116 lm/W
911401509651	SM100C LED37S 840 W60L60 PSD G3	-	4000 K	80	116 lm/W
911401509951	SM100C LED27S 840 W60L60 PSU G3	-	4000 K	80	117 lm/W
911401510151	SM100C LED37S 840 W60L60 PSU G3	-	4000 K	80	116 lm/W
911401510751	RC100B LED37S 840 W60L60 PSU G3	-	4000 K	80	116 lm/W

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
911401510851	RC100B LED37S 840 W60L60 PSD OC G3	-	4000 K	80	121 lm/W
911401510951	RC100B LED37S 865 W60L60 PSU G3	-	6500 K	80	116 lm/W
911401511151	RC100B LED37S 840 W60L60 PSD G3	-	4000 K	80	116 lm/W
911401568841	RC100X LED37S 840 W60L60 IAR G3	-	4000 K	80	119 lm/W
911401514947	RC100X LED37S 940 W60L60 SIA S2 G3	120 degree(s)	4000 K	90	145.59386973180077 lm/W
911401515047	RC100X LED37S 840 W60L60 SIA S2 G3	120 degree(s)	4000 K	80	153.2567049808429 lm/W
911401515147	RC100X LED37S 865 W60L60 SIA S2 G3	120 degree(s)	6500 K	80	153.2567049808429 lm/W
911401515247	RC100X LED37S 840 W60L60 SIA S15 G3	120 degree(s)	4000 K	80	153.2567049808429 lm/W
911401515347	RC100X LED37S 865 W60L60 SIA S15 G3	120 degree(s)	6500 K	80	153.2567049808429 lm/W
911401515447	RC100X LED37S 940	120 degree(s)	4000 K	90	145.59386973180077 lm/W

GreenPerform Troffer

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
	W60L60 SIA S15 G3				
911401515547	RC100X LED37S 940 W60L60 SIA S2 G3 CAU	120 degree(s)	4000 K	90	145.59386973180077 lm/W
911401515647	RC100X LED37S 840 W60L60 SIA S2 G3 CAU	120 degree(s)	4000 K	80	153.2567049808429 lm/W
911401515747	RC100X LED37S 865 W60L60 SIA S2 G3 CAU	120 degree(s)	6500 K	80	153.2567049808429 lm/W
911401515847	RC100X LED37S 840 W60L60 SIA S15 G3 CAU	120 degree(s)	4000 K	80	153.2567049808429 lm/W
911401515947	RC100X LED37S 865 W60L60 SIA S15 G3 CAU	120 degree(s)	6500 K	80	153.2567049808429 lm/W
911401516047	RC100X LED37S 940 W60L60 SIA S15 G3 CAU	120 degree(s)	4000 K	90	145.59386973180077 lm/W
911401516147	RC100X LED37S 840 W60L60 SIA S2 OC CAU	120 degree(s)	4000 K	80	160.91954022988506 lm/W
911401511847	RC100B LED27S 840 W60L60 PSU G3	120 degree(s)	4000 K	80	154.54545454545456 lm/W

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
911401511947	RC100B LED27S 865 W60L60 PSU G3	120 degree(s)	6500 K	80	154.55 lm/W
911401512047	RC100B LED37S 840 W60L60 PSU G3	120 degree(s)	4000 K	80	155.03875968992247 lm/W
911401512147	RC100B LED37S 865 W60L60 PSU G3	120 degree(s)	6500 K	80	155.03875968992247 lm/W
911401512347	RC100B LED37S 840 W60L60 PSU CAU	120 degree(s)	4000 K	80	155.03875968992247 lm/W
911401512447	RC100B LED37S 865 W60L60 PSU CAU	120 degree(s)	6500 K	80	155.03875968992247 lm/W
911401512847	SM100C LED27S 840 W60L60 PSU G3	120 degree(s)	4000 K	80	154.54545454545456 lm/W
911401512947	SM100C LED37S 840 W60L60 PSU G3	120 degree(s)	4000 K	80	155.03875968992247 lm/W
911401513347	RC100B LED37S 840 W60L60 PSD G3	120 degree(s)	4000 K	80	158.73015873015873 lm/W
911401513447	RC100B LED37S 865 W60L60 PSD G3	120 degree(s)	6500 K	80	158.73015873015873 lm/W
911401513647	RC100B LED37S 840	120 degree(s)	4000 K	80	166.66666666666666 lm/W

GreenPerform Troffer

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
	W60L60 PSD OC G3				
911401513747	RC100B LED37S 865 W60L60 PSD OC G3	120 degree(s)	6500 K	80	166.66666666666666 lm/W
911401514247	SM100C LED37S 840 W60L60 PSD G3	120 degree(s)	4000 K	80	158.73015873015873 lm/W
911401514447	RC100X LED37/840 W60L60 WIA	120 degree(s)	4000 K	80	153.2567049808429 lm/W
911401514547	RC100X LED37/865 W60L60 WIA	120 degree(s)	6500 K	80	153.2567049808429 lm/W
911401514051	RC100B LED37S 840 W60L120	-	4000 K	80	129 lm/W

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
	PSD OC CAU				
911401514351	RC100B LED54S 840 W60L120 PSU G3	-	4000 K	80	123 lm/W
911401517247	RC100B LED54S 840 W60L120 PSD OC CAU	120 degree(s)	4000 K	80	175.7188498402556 lm/W
911401517347	RC100B LED37S 840 W60L120 PSU CAU	120 degree(s)	4000 K	80	158.1818181818182 lm/W
911401517447	RC100B LED54S 840 W60L120 PSU CAU	120 degree(s)	4000 K	80	162.5 lm/W
911401517547	RC100B LED54S 840 W60L120 PSU G3	120 degree(s)	4000 K	80	162.5 lm/W

Light Technical (2/2)

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type
911401512547	RC100B LED37S 840 W30L120 PSU G3	4,000 lm	2	Opal prismatic reflector
911401513051	RC100B LED37S 840 W30L120 PSD OC G3	3,700 lm	-	-
911401513147	SM100C LED37S 840 W30L120 PSU G3	4,000 lm	2	Opal prismatic reflector
911401513247	SM100C LED37S 840 W30L120 PSU G3	4,000 lm	2	Opal prismatic reflector
911401513251	RC100B LED37S 840 W30L120 PSD G3	3,700 lm	-	-
911401513351	RC100B LED37S 840 W30L120 PSU G3	3,700 lm	-	-
911401513751	RC100B LED37S 865 W30L120 PSU UNV G3	3,700 lm	-	-

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type
911401513847	RC100B LED37S 840 W30L120 PSD OC G3	4,200 lm	2	Opal prismatic reflector
911401513947	RC100B LED37S 840 W30L120 PSD G3	4,000 lm	2	Opal prismatic reflector
911401514047	RC100B LED37S 840 W30L120 PSD CAU	4,000 lm	2	Opal prismatic reflector
911401514347	SM100C LED37S 840 W30L120 PSD G3	4,000 lm	2	Opal prismatic reflector
911401514747	RC100X LED37/840 W30L120 WIA	4,000 lm	2	Opal prismatic reflector
911401516547	RC100X LED37S 840 W30L120 S15 G3 OC CAU	4,200 lm	2	Opal prismatic reflector
911401519451	SM100C LED37S 840 W30L120 PSU G3	3,700 lm	-	-

GreenPerform Troffer

Order Code	Full Product Name	Luminous Flux	Number of light	
			sources	Optic type
911401519551	SM100C LED37S 840 W30L120 PSD G3	3,700 lm	-	-
911401519951	SM100C LED37S 865 W30L120 PSU UNV G3	3,700 lm	-	-
911401508451	RC100B LED27S 840 W60L60 PSU G3	2,700 lm	-	-
911401508651	RC100B LED27S 865 W60L60 PSU G3	2,700 lm	-	-
911401509551	RC100B LED37S 840 W603L603 PSU UNV G3	3,700 lm	-	-
911401509651	SM100C LED37S 840 W60L60 PSD G3	3,700 lm	-	-
911401509951	SM100C LED27S 840 W60L60 PSU G3	2,700 lm	-	-
911401510151	SM100C LED37S 840 W60L60 PSU G3	3,700 lm	-	-
911401510751	RC100B LED37S 840 W60L60 PSU G3	3,700 lm	-	-
911401510851	RC100B LED37S 840 W60L60 PSD OC G3	3,700 lm	-	-
911401510951	RC100B LED37S 865 W60L60 PSU G3	3,700 lm	-	-
911401511151	RC100B LED37S 840 W60L60 PSD G3	3,700 lm	-	-
911401568841	RC100X LED37S 840 W60L60 IAR G3	3,700 lm	-	-
911401514947	RC100X LED37S 940 W60L60 SIA S2 G3	3,800 lm	2	Opal prismatic reflector
911401515047	RC100X LED37S 840 W60L60 SIA S2 G3	4,000 lm	2	Opal prismatic reflector
911401515147	RC100X LED37S 865 W60L60 SIA S2 G3	4,000 lm	2	Opal prismatic reflector
911401515247	RC100X LED37S 840 W60L60 SIA S15 G3	4,000 lm	2	Opal prismatic reflector
911401515347	RC100X LED37S 865 W60L60 SIA S15 G3	4,000 lm	2	Opal prismatic reflector
911401515447	RC100X LED37S 940 W60L60 SIA S15 G3	3,800 lm	2	Opal prismatic reflector
911401515547	RC100X LED37S 940 W60L60 SIA S2 G3 CAU	3,800 lm	2	Opal prismatic reflector
911401515647	RC100X LED37S 840 W60L60 SIA S2 G3 CAU	4,000 lm	2	Opal prismatic reflector
911401515747	RC100X LED37S 865 W60L60 SIA S2 G3 CAU	4,000 lm	2	Opal prismatic reflector
911401515847	RC100X LED37S 840 W60L60 SIA S15 G3 CAU	4,000 lm	2	Opal prismatic reflector
911401515947	RC100X LED37S 865 W60L60 SIA S15 G3 CAU	4,000 lm	2	Opal prismatic reflector

Order Code	Full Product Name	Luminous Flux	Number of light	
			sources	Optic type
911401516047	RC100X LED37S 940 W60L60 SIA S15 G3 CAU	3,800 lm	2	Opal prismatic reflector
911401516147	RC100X LED37S 840 W60L60 SIA S2 OC CAU	4,200 lm	2	Opal prismatic reflector
911401511847	RC100B LED27S 840 W60L60 PSU G3	2,890 lm	2	Opal prismatic reflector
911401511947	RC100B LED27S 865 W60L60 PSU G3	2,890 lm	2	Opal prismatic reflector
911401512047	RC100B LED37S 840 W60L60 PSU G3	4,000 lm	2	Opal prismatic reflector
911401512147	RC100B LED37S 865 W60L60 PSU G3	4,000 lm	2	Opal prismatic reflector
911401512347	RC100B LED37S 840 W60L60 PSU CAU	4,000 lm	2	Opal prismatic reflector
911401512447	RC100B LED37S 865 W60L60 PSU CAU	4,000 lm	2	Opal prismatic reflector
911401512847	SM100C LED27S 840 W60L60 PSU G3	2,890 lm	2	Opal prismatic reflector
911401512947	SM100C LED37S 840 W60L60 PSU G3	4,000 lm	2	Opal prismatic reflector
911401513347	RC100B LED37S 840 W60L60 PSD G3	4,000 lm	2	Opal prismatic reflector
911401513447	RC100B LED37S 865 W60L60 PSD G3	4,000 lm	2	Opal prismatic reflector
911401513647	RC100B LED37S 840 W60L60 PSD OC G3	4,200 lm	2	Opal prismatic reflector
911401513747	RC100B LED37S 865 W60L60 PSD OC G3	4,200 lm	2	Opal prismatic reflector
911401514247	SM100C LED37S 840 W60L60 PSD G3	4,000 lm	2	Opal prismatic reflector
911401514447	RC100X LED37/840 W60L60 WIA	4,000 lm	2	Opal prismatic reflector
911401514547	RC100X LED37/865 W60L60 WIA	4,000 lm	2	Opal prismatic reflector
911401514051	RC100B LED37S 840 W60L120 PSD OC CAU	3,700 lm	-	-
911401514351	RC100B LED54S 840 W60L120 PSU G3	5,400 lm	-	-
911401517247	RC100B LED54S 840 W60L120 PSD OC CAU	5,500 lm	4	Opal prismatic reflector
911401517347	RC100B LED37S 840 W60L120 PSU CAU	3,480 lm	4	Opal prismatic reflector
911401517447	RC100B LED54S 840 W60L120 PSU CAU	5,200 lm	4	Opal prismatic reflector
911401517547	RC100B LED54S 840 W60L120 PSU G3	5,200 lm	4	Opal prismatic reflector

Operating and Electrical

GreenPerform Troffer

Order Code	Full Product Name	Input Voltage	Line Frequency	Power	
				Consumption	
911401512547	RC100B LED37S 840 W30L120 PSU G3	220 to 240 V	50 or 60 Hz	25.8 W	
911401513051	RC100B LED37S 840 W30L120 PSD OC G3	220 to 240 V	50 to 60 Hz	32 W	
911401513147	SM100C LED37S 840 W30L120 PSU G3	220 to 240 V	50 or 60 Hz	25.8 W	
911401513247	SM100C LED37S 840 W30L120 PSU G3	220 to 240 V	50 or 60 Hz	25.8 W	
911401513251	RC100B LED37S 840 W30L120 PSD G3	220 to 240 V	50 to 60 Hz	32 W	
911401513351	RC100B LED37S 840 W30L120 PSU G3	220 to 240 V	50 to 60 Hz	32 W	
911401513751	RC100B LED37S 865 W30L120 PSU UNV G3	110 to 277 V	50 to 60 Hz	32 W	
911401513847	RC100B LED37S 840 W30L120 PSD OC G3	220 to 240 V	50 or 60 Hz	25.2 W	
911401513947	RC100B LED37S 840 W30L120 PSD G3	220 to 240 V	50 or 60 Hz	25.2 W	
911401514047	RC100B LED37S 840 W30L120 PSD CAU	220 to 240 V	50 or 60 Hz	25.2 W	
911401514347	SM100C LED37S 840 W30L120 PSD G3	220 to 240 V	50 or 60 Hz	25.2 W	
911401514747	RC100X LED37/840 W30L120 WIA	220 to 240 V	50 or 60 Hz	26.1 W	
911401516547	RC100X LED37S 840 W30L120 S15 G3 OC CAU	220 to 240 V	50 or 60 Hz	26.1 W	
911401519451	SM100C LED37S 840 W30L120 PSU G3	220 to 240 V	50 to 60 Hz	32 W	
911401519551	SM100C LED37S 840 W30L120 PSD G3	220 to 240 V	50 to 60 Hz	32 W	
911401519951	SM100C LED37S 865 W30L120 PSU UNV G3	110 to 277 V	50 to 60 Hz	32 W	
911401508451	RC100B LED27S 840 W60L60 PSU G3	220 to 240 V	50 to 60 Hz	23 W	
911401508651	RC100B LED27S 865 W60L60 PSU G3	220 to 240 V	50 to 60 Hz	23 W	
911401509551	RC100B LED37S 840 W60L60 PSU UNV G3	110 to 277 V	50 to 60 Hz	32 W	
911401509651	SM100C LED37S 840 W60L60 PSD G3	220 to 240 V	50 to 60 Hz	32 W	
911401509951	SM100C LED27S 840 W60L60 PSU G3	220 to 240 V	50 to 60 Hz	23 W	
911401510151	SM100C LED37S 840 W60L60 PSU G3	220 to 240 V	50 to 60 Hz	32 W	
911401510751	RC100B LED37S 840 W60L60 PSU G3	220 to 240 V	50 to 60 Hz	32 W	

Order Code	Full Product Name	Input Voltage	Line Frequency	Power	
				Consumption	
911401510851	RC100B LED37S 840 W60L60 PSD OC G3	220 to 240 V	50 to 60 Hz	32 W	
911401510951	RC100B LED37S 865 W60L60 PSU G3	220 to 240 V	50 to 60 Hz	32 W	
911401511151	RC100B LED37S 840 W60L60 PSD G3	220 to 240 V	50 to 60 Hz	32 W	
911401568841	RC100X LED37S 840 W60L60 IAR G3	220 to 240 V	50 to 60 Hz	31 W	
911401514947	RC100X LED37S 940 W60L60 SIA S2 G3	220 to 240 V	50 or 60 Hz	26.1 W	
911401515047	RC100X LED37S 840 W60L60 SIA S2 G3	220 to 240 V	50 or 60 Hz	26.1 W	
911401515147	RC100X LED37S 865 W60L60 SIA S2 G3	220 to 240 V	50 or 60 Hz	26.1 W	
911401515247	RC100X LED37S 840 W60L60 SIA S15 G3	220 to 240 V	50 or 60 Hz	26.1 W	
911401515347	RC100X LED37S 865 W60L60 SIA S15 G3	220 to 240 V	50 or 60 Hz	26.1 W	
911401515447	RC100X LED37S 940 W60L60 SIA S15 G3	220 to 240 V	50 or 60 Hz	26.1 W	
911401515547	RC100X LED37S 940 W60L60 SIA S2 G3 CAU	220 to 240 V	50 or 60 Hz	26.1 W	
911401515647	RC100X LED37S 840 W60L60 SIA S2 G3 CAU	220 to 240 V	50 or 60 Hz	26.1 W	
911401515747	RC100X LED37S 865 W60L60 SIA S2 G3 CAU	220 to 240 V	50 or 60 Hz	26.1 W	
911401515847	RC100X LED37S 840 W60L60 SIA S15 G3 CAU	220 to 240 V	50 or 60 Hz	26.1 W	
911401515947	RC100X LED37S 865 W60L60 SIA S15 G3 CAU	220 to 240 V	50 or 60 Hz	26.1 W	
911401516047	RC100X LED37S 940 W60L60 SIA S15 G3 CAU	220 to 240 V	50 or 60 Hz	26.1 W	
911401516147	RC100X LED37S 840 W60L60 SIA S2 OC CAU	220 to 240 V	50 or 60 Hz	26.1 W	
911401511847	RC100B LED27S 840 W60L60 PSU G3	220 to 240 V	50 or 60 Hz	18.7 W	
911401511947	RC100B LED27S 865 W60L60 PSU G3	220 to 240 V	50 or 60 Hz	18.7 W	
911401512047	RC100B LED37S 840 W60L60 PSU G3	220 to 240 V	50 or 60 Hz	25.8 W	
911401512147	RC100B LED37S 865 W60L60 PSU G3	220 to 240 V	50 or 60 Hz	25.8 W	
911401512347	RC100B LED37S 840 W60L60 PSU CAU	220 to 240 V	50 or 60 Hz	25.8 W	

GreenPerform Troffer

Order Code	Full Product Name	Input Voltage	Line Frequency	Power	
				Consumption	
911401512447	RC100B LED37S 865 W60L60 PSU CAU	220 to 240 V	50 or 60 Hz	25.8 W	
911401512847	SM100C LED27S 840 W60L60 PSU G3	220 to 240 V	50 or 60 Hz	18.7 W	
911401512947	SM100C LED37S 840 W60L60 PSU G3	220 to 240 V	50 or 60 Hz	25.8 W	
911401513347	RC100B LED37S 840 W60L60 PSD G3	220 to 240 V	50 or 60 Hz	25.2 W	
911401513447	RC100B LED37S 865 W60L60 PSD G3	220 to 240 V	50 or 60 Hz	25.2 W	
911401513647	RC100B LED37S 840 W60L60 PSD OC G3	220 to 240 V	50 or 60 Hz	25.2 W	
911401513747	RC100B LED37S 865 W60L60 PSD OC G3	220 to 240 V	50 or 60 Hz	25.2 W	
911401514247	SM100C LED37S 840 W60L60 PSD G3	220 to 240 V	50 or 60 Hz	25.2 W	
911401514447	RC100X LED37/840 W60L60 WIA	220 to 240 V	50 or 60 Hz	26.1 W	

Order Code	Full Product Name	Input Voltage	Line Frequency	Power	
				Consumption	
911401514547	RC100X LED37/865 W60L60 WIA	220 to 240 V	50 or 60 Hz	26.1 W	
911401514051	RC100B LED37S 840 W60L120 PSD OC CAU	220 to 240 V	50 to 60 Hz	32 W	
911401514351	RC100B LED54S 840 W60L120 PSU G3	220 to 240 V	50 to 60 Hz	44 W	
911401517247	RC100B LED54S 840 W60L120 PSD OC CAU	220 to 240 V	50 or 60 Hz	31.3 W	
911401517347	RC100B LED37S 840 W60L120 PSU CAU	220 to 240 V	50 or 60 Hz	22 W	
911401517447	RC100B LED54S 840 W60L120 PSU CAU	220 to 240 V	50 or 60 Hz	32 W	
911401517547	RC100B LED54S 840 W60L120 PSU G3	220 to 240 V	50 or 60 Hz	32 W	

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401512547	RC100B LED37S 840 W30L120 PSU G3	-
911401513051	RC100B LED37S 840 W30L120 PSD OC G3	Yes
911401513147	SM100C LED37S 840 W30L120 PSU G3	-
911401513247	SM100C LED37S 840 W30L120 PSU G3	-
911401513251	RC100B LED37S 840 W30L120 PSD G3	Yes
911401513351	RC100B LED37S 840 W30L120 PSU G3	No
911401513751	RC100B LED37S 865 W30L120 PSU UNV G3	No
911401513847	RC100B LED37S 840 W30L120 PSD OC G3	DALI
911401513947	RC100B LED37S 840 W30L120 PSD G3	DALI
911401514047	RC100B LED37S 840 W30L120 PSD CAU	DALI
911401514347	SM100C LED37S 840 W30L120 PSD G3	DALI
911401514747	RC100X LED37/840 W30L120 WIA	Wireless Dim
911401516547	RC100X LED37S 840 W30L120 S15 G3 OC CAU	Wireless Dim
911401519451	SM100C LED37S 840 W30L120 PSU G3	No
911401519551	SM100C LED37S 840 W30L120 PSD G3	Yes
911401519951	SM100C LED37S 865 W30L120 PSU UNV G3	No
911401508451	RC100B LED27S 840 W60L60 PSU G3	No
911401508651	RC100B LED27S 865 W60L60 PSU G3	No
911401509551	RC100B LED37S 840 W60L60 PSU UNV G3	No
911401509651	SM100C LED37S 840 W60L60 PSD G3	Yes
911401509951	SM100C LED27S 840 W60L60 PSU G3	No
911401510151	SM100C LED37S 840 W60L60 PSU G3	No
911401510751	RC100B LED37S 840 W60L60 PSU G3	No
911401510851	RC100B LED37S 840 W60L60 PSD OC G3	Yes
911401510951	RC100B LED37S 865 W60L60 PSU G3	No
911401511151	RC100B LED37S 840 W60L60 PSD G3	Yes
911401568841	RC100X LED37S 840 W60L60 IAR G3	Yes
911401514947	RC100X LED37S 940 W60L60 SIA S2 G3	Wireless Dim
911401515047	RC100X LED37S 840 W60L60 SIA S2 G3	Wireless Dim

Order Code	Full Product Name	Dimmable
911401515147	RC100X LED37S 865 W60L60 SIA S2 G3	Wireless Dim
911401515247	RC100X LED37S 840 W60L60 SIA S15 G3	Wireless Dim
911401515347	RC100X LED37S 865 W60L60 SIA S15 G3	Wireless Dim
911401515447	RC100X LED37S 940 W60L60 SIA S15 G3	Wireless Dim
911401515547	RC100X LED37S 940 W60L60 SIA S2 G3 CAU	Wireless Dim
911401515647	RC100X LED37S 840 W60L60 SIA S2 G3 CAU	Wireless Dim
911401515747	RC100X LED37S 865 W60L60 SIA S2 G3 CAU	Wireless Dim
911401515847	RC100X LED37S 840 W60L60 SIA S15 G3 CAU	Wireless Dim
911401515947	RC100X LED37S 865 W60L60 SIA S15 G3 CAU	Wireless Dim
911401516047	RC100X LED37S 940 W60L60 SIA S15 G3 CAU	Wireless Dim
911401516147	RC100X LED37S 840 W60L60 SIA S2 OC CAU	Wireless Dim
911401511847	RC100B LED27S 840 W60L60 PSU G3	-
911401511947	RC100B LED27S 865 W60L60 PSU G3	-
911401512047	RC100B LED37S 840 W60L60 PSU G3	-
911401512147	RC100B LED37S 865 W60L60 PSU G3	-
911401512347	RC100B LED37S 840 W60L60 PSU CAU	-
911401512447	RC100B LED37S 865 W60L60 PSU CAU	-
911401512847	SM100C LED27S 840 W60L60 PSU G3	-
911401512947	SM100C LED37S 840 W60L60 PSU G3	-
911401513347	RC100B LED37S 840 W60L60 PSD G3	DALI
911401513447	RC100B LED37S 865 W60L60 PSD G3	DALI
911401513647	RC100B LED37S 840 W60L60 PSD OC G3	DALI
911401513747	RC100B LED37S 865 W60L60 PSD OC G3	DALI
911401514247	SM100C LED37S 840 W60L60 PSD G3	DALI
911401514447	RC100X LED37/840 W60L60 WIA	Wireless Dim
911401514547	RC100X LED37/865 W60L60 WIA	Wireless Dim
911401514051	RC100B LED37S 840 W60L120 PSD OC CAU	Yes
911401514351	RC100B LED54S 840 W60L120 PSU G3	No
911401517247	RC100B LED54S 840 W60L120 PSD OC CAU	DALI

Order Code	Full Product Name	Dimmable
911401517347	RC100B LED37S 840 W60L120 PSU CAU	-
911401517447	RC100B LED54S 840 W60L120 PSU CAU	-

Order Code	Full Product Name	Dimmable
911401517547	RC100B LED54S 840 W60L120 PSU G3	-

Mechanical and Housing

Order Code	Full Product Name	Optical cover type
911401512547	RC100B LED37S 840 W30L120 PSU G3	Polycarbonate bowl/cover
911401513051	RC100B LED37S 840 W30L120 PSD OC G3	Variable linear-lens array in polycarbonate cover
911401513147	SM100C LED37S 840 W30L120 PSU G3	Polycarbonate bowl/cover
911401513247	SM100C LED37S 840 W30L120 PSU G3	Polycarbonate bowl/cover
911401513251	RC100B LED37S 840 W30L120 PSD G3	Variable linear-lens array in polycarbonate cover
911401513351	RC100B LED37S 840 W30L120 PSU G3	Variable linear-lens array in polycarbonate cover
911401513751	RC100B LED37S 865 W30L120 PSU UNV G3	Variable linear-lens array in polycarbonate cover
911401513847	RC100B LED37S 840 W30L120 PSD OC G3	Polycarbonate bowl/cover
911401513947	RC100B LED37S 840 W30L120 PSD G3	Polycarbonate bowl/cover
911401514047	RC100B LED37S 840 W30L120 PSD CAU	Polycarbonate bowl/cover
911401514347	SM100C LED37S 840 W30L120 PSD G3	Polycarbonate bowl/cover
911401514747	RC100X LED37/840 W30L120 WIA	Polycarbonate bowl/cover
911401516547	RC100X LED37S 840 W30L120 S15 G3 OC CAU	Polycarbonate bowl/cover
911401519451	SM100C LED37S 840 W30L120 PSU G3	Variable linear-lens array in polycarbonate cover
911401519551	SM100C LED37S 840 W30L120 PSD G3	Variable linear-lens array in polycarbonate cover
911401519951	SM100C LED37S 865 W30L120 PSU UNV G3	Variable linear-lens array in polycarbonate cover
911401508451	RC100B LED27S 840 W60L60 PSU G3	Variable linear-lens array in polycarbonate cover
911401508651	RC100B LED27S 865 W60L60 PSU G3	Variable linear-lens array in polycarbonate cover
911401509551	RC100B LED37S 840 W60L60 PSU UNV G3	Variable linear-lens array in polycarbonate cover
911401509651	SM100C LED37S 840 W60L60 PSD G3	Variable linear-lens array in polycarbonate cover
911401509951	SM100C LED27S 840 W60L60 PSU G3	Variable linear-lens array in polycarbonate cover
911401510151	SM100C LED37S 840 W60L60 PSU G3	Variable linear-lens array in polycarbonate cover
911401510751	RC100B LED37S 840 W60L60 PSU G3	Variable linear-lens array in polycarbonate cover

Order Code	Full Product Name	Optical cover type
911401510851	RC100B LED37S 840 W60L60 PSD OC G3	Variable linear-lens array in polycarbonate cover
911401510951	RC100B LED37S 865 W60L60 PSU G3	Variable linear-lens array in polycarbonate cover
911401511151	RC100B LED37S 840 W60L60 PSD G3	Variable linear-lens array in polycarbonate cover
911401568841	RC100X LED37S 840 W60L60 IAR G3	Variable linear-lens array in polycarbonate cover
911401514947	RC100X LED37S 940 W60L60 SIA S2 G3	Polycarbonate bowl/cover
911401515047	RC100X LED37S 840 W60L60 SIA S2 G3	Polycarbonate bowl/cover
911401515147	RC100X LED37S 865 W60L60 SIA S2 G3	Polycarbonate bowl/cover
911401515247	RC100X LED37S 840 W60L60 SIA S15 G3	Polycarbonate bowl/cover
911401515347	RC100X LED37S 865 W60L60 SIA S15 G3	Polycarbonate bowl/cover
911401515447	RC100X LED37S 940 W60L60 SIA S15 G3	Polycarbonate bowl/cover
911401515547	RC100X LED37S 940 W60L60 SIA S2 G3 CAU	Polycarbonate bowl/cover
911401515647	RC100X LED37S 840 W60L60 SIA S2 G3 CAU	Polycarbonate bowl/cover
911401515747	RC100X LED37S 865 W60L60 SIA S2 G3 CAU	Polycarbonate bowl/cover
911401515847	RC100X LED37S 840 W60L60 SIA S15 G3 CAU	Polycarbonate bowl/cover
911401515947	RC100X LED37S 865 W60L60 SIA S15 G3 CAU	Polycarbonate bowl/cover
911401516047	RC100X LED37S 940 W60L60 SIA S15 G3 CAU	Polycarbonate bowl/cover
911401516147	RC100X LED37S 840 W60L60 SIA S2 OC CAU	Polycarbonate bowl/cover
911401511847	RC100B LED27S 840 W60L60 PSU G3	Polycarbonate bowl/cover
911401511947	RC100B LED27S 865 W60L60 PSU G3	Polycarbonate bowl/cover
911401512047	RC100B LED37S 840 W60L60 PSU G3	Polycarbonate bowl/cover
911401512147	RC100B LED37S 865 W60L60 PSU G3	Polycarbonate bowl/cover
911401512347	RC100B LED37S 840 W60L60 PSU CAU	Polycarbonate bowl/cover
911401512447	RC100B LED37S 865 W60L60 PSU CAU	Polycarbonate bowl/cover
911401512847	SM100C LED27S 840 W60L60 PSU G3	Polycarbonate bowl/cover
911401512947	SM100C LED37S 840 W60L60 PSU G3	Polycarbonate bowl/cover
911401513347	RC100B LED37S 840 W60L60 PSD G3	Polycarbonate bowl/cover
911401513447	RC100B LED37S 865 W60L60 PSD G3	Polycarbonate bowl/cover

GreenPerform Troffer

Order Code	Full Product Name	Optical cover type
911401513647	RC100B LED37S 840 W60L60 PSD OC G3	Polycarbonate bowl/cover
911401513747	RC100B LED37S 865 W60L60 PSD OC G3	Polycarbonate bowl/cover
911401514247	SM100C LED37S 840 W60L60 PSD G3	Polycarbonate bowl/cover
911401514447	RC100X LED37/840 W60L60 WIA	Polycarbonate bowl/cover
911401514547	RC100X LED37/865 W60L60 WIA	Polycarbonate bowl/cover
911401514051	RC100B LED37S 840 W60L120 PSD OC CAU	Variable linear-lens array in polycarbonate cover
911401514351	RC100B LED54S 840 W60L120 PSU G3	Variable linear-lens array in polycarbonate cover

Order Code	Full Product Name	Optical cover type
911401517247	RC100B LED54S 840 W60L120 PSD OC CAU	Polycarbonate bowl/cover
911401517347	RC100B LED37S 840 W60L120 PSU CAU	Polycarbonate bowl/cover
911401517447	RC100B LED54S 840 W60L120 PSU CAU	Polycarbonate bowl/cover
911401517547	RC100B LED54S 840 W60L120 PSU G3	Polycarbonate bowl/cover

Approval and Application

Order Code	Full Product Name	Flammability mark	Glow-wire test
911401512547	RC100B LED37S 840 W30L120 PSU G3	-	Temperature 650 °C, duration 30 s
911401513051	RC100B LED37S 840 W30L120 PSD OC G3	For mounting on normally flammable surfaces	Temperature 600 °C, duration 30 s
911401513147	SM100C LED37S 840 W30L120 PSU G3	-	Temperature 650 °C, duration 30 s
911401513247	SM100C LED37S 840 W30L120 PSU G3	-	Temperature 650 °C, duration 30 s
911401513251	RC100B LED37S 840 W30L120 PSD G3	For mounting on normally flammable surfaces	Temperature 600 °C, duration 30 s
911401513351	RC100B LED37S 840 W30L120 PSU G3	For mounting on normally flammable surfaces	Temperature 600 °C, duration 30 s
911401513751	RC100B LED37S 865 W30L120 PSU UNV G3	For mounting on normally flammable surfaces	Temperature 600 °C, duration 30 s
911401513847	RC100B LED37S 840 W30L120 PSD OC G3	-	Temperature 650 °C, duration 30 s
911401513947	RC100B LED37S 840 W30L120 PSD G3	-	Temperature 650 °C, duration 30 s
911401514047	RC100B LED37S 840 W30L120 PSD CAU	-	Temperature 650 °C, duration 30 s
911401514347	SM100C LED37S 840 W30L120 PSD G3	-	Temperature 650 °C, duration 30 s
911401514747	RC100X LED37/840 W30L120 WIA	-	Temperature 650 °C, duration 30 s
911401516547	RC100X LED37S 840 W30L120 S15 G3 OC CAU	-	Temperature 650 °C, duration 30 s
911401519451	SM100C LED37S 840 W30L120 PSU G3	For mounting on normally	Temperature 600 °C, duration 30 s

Order Code	Full Product Name	Flammability mark	Glow-wire test
		flammable surfaces	
911401519551	SM100C LED37S 840 W30L120 PSD G3	For mounting on normally flammable surfaces	Temperature 600 °C, duration 30 s
911401519951	SM100C LED37S 865 W30L120 PSU UNV G3	For mounting on normally flammable surfaces	Temperature 600 °C, duration 30 s
911401508451	RC100B LED27S 840 W60L60 PSU G3	For mounting on normally flammable surfaces	Temperature 600 °C, duration 30 s
911401508651	RC100B LED27S 865 W60L60 PSU G3	For mounting on normally flammable surfaces	Temperature 600 °C, duration 30 s
911401509551	RC100B LED37S 840 W60L60 PSU UNV G3	For mounting on normally flammable surfaces	Temperature 600 °C, duration 30 s
911401509651	SM100C LED37S 840 W60L60 PSD G3	For mounting on normally flammable surfaces	Temperature 600 °C, duration 30 s
911401509951	SM100C LED27S 840 W60L60 PSU G3	For mounting on normally flammable surfaces	Temperature 600 °C, duration 30 s
911401510151	SM100C LED37S 840 W60L60 PSU G3	For mounting on normally flammable surfaces	Temperature 600 °C, duration 30 s
911401510751	RC100B LED37S 840 W60L60 PSU G3	For mounting on normally	Temperature 600 °C, duration 30 s

GreenPerform Troffer

Order Code	Full Product Name	Flammability mark	Glow-wire test
		flammable surfaces	
911401510851	RC100B LED37S 840 W60L60 PSD OC G3	For mounting on normally flammable surfaces	Temperature 600 °C, duration 30 s
911401510951	RC100B LED37S 865 W60L60 PSU G3	For mounting on normally flammable surfaces	Temperature 600 °C, duration 30 s
911401511151	RC100B LED37S 840 W60L60 PSD G3	For mounting on normally flammable surfaces	Temperature 600 °C, duration 30 s
911401568841	RC100X LED37S 840 W60L60 IAR G3	For mounting on normally flammable surfaces	Temperature 600 °C, duration 30 s
911401514947	RC100X LED37S 940 W60L60 SIA S2 G3	-	Temperature 650 °C, duration 30 s
911401515047	RC100X LED37S 840 W60L60 SIA S2 G3	-	Temperature 650 °C, duration 30 s
911401515147	RC100X LED37S 865 W60L60 SIA S2 G3	-	Temperature 650 °C, duration 30 s
911401515247	RC100X LED37S 840 W60L60 SIA S15 G3	-	Temperature 650 °C, duration 30 s
911401515347	RC100X LED37S 865 W60L60 SIA S15 G3	-	Temperature 650 °C, duration 30 s
911401515447	RC100X LED37S 940 W60L60 SIA S15 G3	-	Temperature 650 °C, duration 30 s
911401515547	RC100X LED37S 940 W60L60 SIA S2 G3 CAU	-	Temperature 650 °C, duration 30 s
911401515647	RC100X LED37S 840 W60L60 SIA S2 G3 CAU	-	Temperature 650 °C, duration 30 s
911401515747	RC100X LED37S 865 W60L60 SIA S2 G3 CAU	-	Temperature 650 °C, duration 30 s
911401515847	RC100X LED37S 840 W60L60 SIA S15 G3 CAU	-	Temperature 650 °C, duration 30 s
911401515947	RC100X LED37S 865 W60L60 SIA S15 G3 CAU	-	Temperature 650 °C, duration 30 s
911401516047	RC100X LED37S 940 W60L60 SIA S15 G3 CAU	-	Temperature 650 °C, duration 30 s
911401516147	RC100X LED37S 840 W60L60 SIA S2 OC CAU	-	Temperature 650 °C, duration 30 s
911401511847	RC100B LED27S 840 W60L60 PSU G3	-	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Flammability mark	Glow-wire test
911401511947	RC100B LED27S 865 W60L60 PSU G3	-	Temperature 650 °C, duration 30 s
911401512047	RC100B LED37S 840 W60L60 PSU G3	-	Temperature 650 °C, duration 30 s
911401512147	RC100B LED37S 865 W60L60 PSU G3	-	Temperature 650 °C, duration 30 s
911401512347	RC100B LED37S 840 W60L60 PSU CAU	-	Temperature 650 °C, duration 30 s
911401512447	RC100B LED37S 865 W60L60 PSU CAU	-	Temperature 650 °C, duration 30 s
911401512847	SM100C LED27S 840 W60L60 PSU G3	-	Temperature 650 °C, duration 30 s
911401512947	SM100C LED37S 840 W60L60 PSU G3	-	Temperature 650 °C, duration 30 s
911401513347	RC100B LED37S 840 W60L60 PSD G3	-	Temperature 650 °C, duration 30 s
911401513447	RC100B LED37S 865 W60L60 PSD G3	-	Temperature 650 °C, duration 30 s
911401513647	RC100B LED37S 840 W60L60 PSD OC G3	-	Temperature 650 °C, duration 30 s
911401513747	RC100B LED37S 865 W60L60 PSD OC G3	-	Temperature 650 °C, duration 30 s
911401514247	SM100C LED37S 840 W60L60 PSD G3	-	Temperature 650 °C, duration 30 s
911401514447	RC100X LED37/840 W60L60 WIA	-	Temperature 650 °C, duration 30 s
911401514547	RC100X LED37/865 W60L60 WIA	-	Temperature 650 °C, duration 30 s
911401514051	RC100B LED37S 840 W60L120 PSD OC CAU	For mounting on normally flammable surfaces	Temperature 600 °C, duration 30 s
911401514351	RC100B LED54S 840 W60L120 PSU G3	For mounting on normally flammable surfaces	Temperature 600 °C, duration 30 s
911401517247	RC100B LED54S 840 W60L120 PSD OC CAU	-	Temperature 650 °C, duration 30 s
911401517347	RC100B LED37S 840 W60L120 PSU CAU	-	Temperature 650 °C, duration 30 s
911401517447	RC100B LED54S 840 W60L120 PSU CAU	-	Temperature 650 °C, duration 30 s
911401517547	RC100B LED54S 840 W60L120 PSU G3	-	Temperature 650 °C, duration 30 s

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
911401512547	RC100B LED37S 840 W30L120 PSU G3	-
911401513051	RC100B LED37S 840 W30L120 PSD OC G3	SDCM<4

Order Code	Full Product Name	Initial chromaticity
911401513147	SM100C LED37S 840 W30L120 PSU G3	-
911401513247	SM100C LED37S 840 W30L120 PSU G3	-

GreenPerform Troffer

Order Code	Full Product Name	Initial chromaticity
911401513251	RC100B LED37S 840 W30L120 PSD G3	SDCM<4
911401513351	RC100B LED37S 840 W30L120 PSU G3	SDCM<4
911401513751	RC100B LED37S 865 W30L120 PSU UNV G3	SDCM<4
911401513847	RC100B LED37S 840 W30L120 PSD OC G3	-
911401513947	RC100B LED37S 840 W30L120 PSD G3	-
911401514047	RC100B LED37S 840 W30L120 PSD CAU	-
911401514347	SM100C LED37S 840 W30L120 PSD G3	-
911401514747	RC100X LED37/840 W30L120 WIA	-
911401516547	RC100X LED37S 840 W30L120 S15 G3 OC CAU	-
911401519451	SM100C LED37S 840 W30L120 PSU G3	SDCM<4
911401519551	SM100C LED37S 840 W30L120 PSD G3	SDCM<4
911401519951	SM100C LED37S 865 W30L120 PSU UNV G3	SDCM<4
911401508451	RC100B LED27S 840 W60L60 PSU G3	SDCM<4
911401508651	RC100B LED27S 865 W60L60 PSU G3	SDCM<4
911401509551	RC100B LED37S 840 W60L60 PSU UNV G3	SDCM<4
911401509651	SM100C LED37S 840 W60L60 PSD G3	SDCM<4
911401509951	SM100C LED27S 840 W60L60 PSU G3	SDCM<4
911401510151	SM100C LED37S 840 W60L60 PSU G3	SDCM<4
911401510751	RC100B LED37S 840 W60L60 PSU G3	SDCM<4
911401510851	RC100B LED37S 840 W60L60 PSD OC G3	SDCM<4
911401510951	RC100B LED37S 865 W60L60 PSU G3	SDCM<4
911401511151	RC100B LED37S 840 W60L60 PSD G3	SDCM<4
911401568841	RC100X LED37S 840 W60L60 IAR G3	SDCM<4
911401514947	RC100X LED37S 940 W60L60 SIA S2 G3	-
911401515047	RC100X LED37S 840 W60L60 SIA S2 G3	-
911401515147	RC100X LED37S 865 W60L60 SIA S2 G3	-
911401515247	RC100X LED37S 840 W60L60 SIA S15 G3	-
911401515347	RC100X LED37S 865 W60L60 SIA S15 G3	-
911401515447	RC100X LED37S 940 W60L60 SIA S15 G3	-

Order Code	Full Product Name	Initial chromaticity
911401515547	RC100X LED37S 940 W60L60 SIA S2 G3 CAU	-
911401515647	RC100X LED37S 840 W60L60 SIA S2 G3 CAU	-
911401515747	RC100X LED37S 865 W60L60 SIA S2 G3 CAU	-
911401515847	RC100X LED37S 840 W60L60 SIA S15 G3 CAU	-
911401515947	RC100X LED37S 865 W60L60 SIA S15 G3 CAU	-
911401516047	RC100X LED37S 940 W60L60 SIA S15 G3 CAU	-
911401516147	RC100X LED37S 840 W60L60 SIA S2 OC CAU	-
911401511847	RC100B LED27S 840 W60L60 PSU G3	-
911401511947	RC100B LED27S 865 W60L60 PSU G3	-
911401512047	RC100B LED37S 840 W60L60 PSU G3	-
911401512147	RC100B LED37S 865 W60L60 PSU G3	-
911401512347	RC100B LED37S 840 W60L60 PSU CAU	-
911401512447	RC100B LED37S 865 W60L60 PSU CAU	-
911401512847	SM100C LED27S 840 W60L60 PSU G3	-
911401512947	SM100C LED37S 840 W60L60 PSU G3	-
911401513347	RC100B LED37S 840 W60L60 PSD G3	-
911401513447	RC100B LED37S 865 W60L60 PSD G3	-
911401513647	RC100B LED37S 840 W60L60 PSD OC G3	-
911401513747	RC100B LED37S 865 W60L60 PSD OC G3	-
911401514247	SM100C LED37S 840 W60L60 PSD G3	-
911401514447	RC100X LED37/840 W60L60 WIA	-
911401514547	RC100X LED37/865 W60L60 WIA	-
911401514051	RC100B LED37S 840 W60L120 PSD OC CAU	SDCM<4
911401514351	RC100B LED54S 840 W60L120 PSU G3	SDCM<4
911401517247	RC100B LED54S 840 W60L120 PSD OC CAU	-
911401517347	RC100B LED37S 840 W60L120 PSU CAU	-
911401517447	RC100B LED54S 840 W60L120 PSU CAU	-
911401517547	RC100B LED54S 840 W60L120 PSU G3	-

