

GreenPerform Troffer

RC100B



Energy saving without compromise.

GreenPerform troffer improves the compact design of the last generation with performance improvement and more variants for different markets. Integrating with all available system: POE, InterAct office wireless, InterAct Office Pro, ActiLume controller, GreenPerform troffer offers additional energy saving and connected features.

Benefits

- Upgrade to smart office with more options
- Energy saving
- Slim housing
- Comfortable light
- Good light quality
- Office compliant
- Reliable performance

Applications

- Open Office
- Public Area

- Meeting Room
- Training Room

Features

- Compatible with all available Philips systems
- Efficacy up to 125lm/W
- Slim design with height less than 46mm
- Improved optical design without zebra effect
- CRI > 80, SDCM<4, Flicker free
- UGR 19 available
- Lifetime L70 50,000 hours

Versions



GreenPerform Troffer RC100B
30x120



GreenPerform Troffer RC100B
60x60




GreenPerform-Troffer-
product-picture




GreenPerform Troffer RC100B
60x120


Dimensional drawing




RC100B W30L120




SM100C W60L60




RC100B LED37S 840 W60L60 PSD G3




SM100C LED37S 840 W60L60 PSD G3




RC100B W60L120




RC100 W60L60



SM100C LED37S 840 W30L120 PSU G3



RC100X LED37/840 W30L120 WIA



SM100C W30L120

General Information

Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Service tag	Yes

Light Technical

Color rendering index (CRI)	80
Number of light sources	2
Beam angle of light source	120 degree(s)
Optic type	Opal prismatic reflector

Operating and Electrical

Suitable for random switching	No
Protection class IEC	Safety class I

Mechanical and Housing

Housing Color	White
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]

Approval and Application

CE mark	Yes
ENEC mark	-
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<4

Light Technical

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)
911401512547	RC100B LED37S 840 W30L120 PSU G3	4,000 lm	4000 K	155.03875968992247 lm/W
01513051	RC100B LED37S 840 W30L120 PSD OC G3	3,700 lm	4000 K	121 lm/W
911401513147	SM100C LED37S 840 W30L120 PSU G3	4,000 lm	4000 K	155.03875968992247 lm/W
911401513247	SM100C LED37S 840 W30L120 PSU G3	4,000 lm	4000 K	155.03875968992247 lm/W
01513251	RC100B LED37S 840 W30L120 PSD G3	3,700 lm	4000 K	116 lm/W
72781699	RC100B LED37S 840 W30L120 PSU G3	3,700 lm	4000 K	116 lm/W
01513751	RC100B LED37S 865 W30L120 PSU UNV G3	3,700 lm	6500 K	116 lm/W
911401513847	RC100B LED37S 840 W30L120 PSD OC G3	4,200 lm	4000 K	166.66666666666666 lm/W
911401513947	RC100B LED37S 840 W30L120 PSD G3	4,000 lm	4000 K	158.73015873015873 lm/W
911401514347	SM100C LED37S 840 W30L120 PSD G3	4,000 lm	4000 K	158.73015873015873 lm/W
911401514747	RC100X LED37/840 W30L120 WIA	4,000 lm	4000 K	153.2567049808429 lm/W
72784799	SM100C LED37S 840 W30L120 PSU G3	3,700 lm	4000 K	116 lm/W
01519551	SM100C LED37S 840 W30L120 PSD G3	3,700 lm	4000 K	116 lm/W

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)
01519951	SM100C LED37S 865 W30L120 PSU UNV G3	3,700 lm	6500 K	116 lm/W
52116299	RC100B LED27S 840 W60L60 PSU G3	2,700 lm	4000 K	117 lm/W
01508651	RC100B LED27S 865 W60L60 PSU G3	2,700 lm	6500 K	117 lm/W
01509551	RC100B LED37S 840 W603L603 PSU UNV G3	3,700 lm	4000 K	116 lm/W
01509651	SM100C LED37S 840 W60L60 PSD G3	3,700 lm	4000 K	116 lm/W
01509951	SM100C LED27S 840 W60L60 PSU G3	2,700 lm	4000 K	117 lm/W
72783099	SM100C LED37S 840 W60L60 PSU G3	3,700 lm	4000 K	116 lm/W
72782399	RC100B LED37S 840 W60L60 PSU G3	3,700 lm	4000 K	116 lm/W
01510851	RC100B LED37S 840 W60L60 PSD OC G3	3,700 lm	4000 K	121 lm/W
01510951	RC100B LED37S 865 W60L60 PSU G3	3,700 lm	6500 K	116 lm/W
51949799	RC100B LED37S 840 W60L60 PSD G3	3,700 lm	4000 K	116 lm/W
911401511847	RC100B LED27S 840 W60L60 PSU G3	2,890 lm	4000 K	154.54545454545456 lm/W
911401511947	RC100B LED27S 865 W60L60 PSU G3	2,890 lm	6500 K	154.55 lm/W
911401512047	RC100B LED37S 840 W60L60 PSU G3	4,000 lm	4000 K	155.03875968992247 lm/W
911401512147	RC100B LED37S 865 W60L60 PSU G3	4,000 lm	6500 K	155.03875968992247 lm/W
911401512847	SM100C LED27S 840 W60L60 PSU G3	2,890 lm	4000 K	154.54545454545456 lm/W
911401512947	SM100C LED37S 840 W60L60 PSU G3	4,000 lm	4000 K	155.03875968992247 lm/W
911401513347	RC100B LED37S 840 W60L60 PSD G3	4,000 lm	4000 K	158.73015873015873 lm/W
911401513447	RC100B LED37S 865 W60L60 PSD G3	4,000 lm	6500 K	158.73015873015873 lm/W
911401513647	RC100B LED37S 840 W60L60 PSD OC G3	4,200 lm	4000 K	166.66666666666666 lm/W
911401513747	RC100B LED37S 865 W60L60 PSD OC G3	4,200 lm	6500 K	166.66666666666666 lm/W
911401514247	SM100C LED37S 840 W60L60 PSD G3	4,000 lm	4000 K	158.73015873015873 lm/W
911401514447	RC100X LED37/840 W60L60 WIA	4,000 lm	4000 K	153.2567049808429 lm/W
911401514547	RC100X LED37/865 W60L60 WIA	4,000 lm	6500 K	153.2567049808429 lm/W
01514351	RC100B LED54S 840 W60L120 PSU G3	5,400 lm	4000 K	123 lm/W

Operating and Electrical

Order Code	Full Product Name	Input Voltage	Line Frequency	Power Consumption
911401512547	RC100B LED37S 840 W30L120 PSU G3	220 to 240 V	50 or 60 Hz	25.8 W
01513051	RC100B LED37S 840 W30L120 PSD OC G3	220 to 240 V	50 to 60 Hz	32 W
911401513147	SM100C LED37S 840 W30L120 PSU G3	220 to 240 V	50 or 60 Hz	25.8 W
911401513247	SM100C LED37S 840 W30L120 PSU G3	220 to 240 V	50 or 60 Hz	25.8 W
01513251	RC100B LED37S 840 W30L120 PSD G3	220 to 240 V	50 to 60 Hz	32 W
72781699	RC100B LED37S 840 W30L120 PSU G3	220 to 240 V	50 to 60 Hz	32 W
01513751	RC100B LED37S 865 W30L120 PSU UNV G3	110 to 277 V	50 to 60 Hz	32 W
911401513847	RC100B LED37S 840 W30L120 PSD OC G3	220 to 240 V	50 or 60 Hz	25.2 W
911401513947	RC100B LED37S 840 W30L120 PSD G3	220 to 240 V	50 or 60 Hz	25.2 W
911401514347	SM100C LED37S 840 W30L120 PSD G3	220 to 240 V	50 or 60 Hz	25.2 W
911401514747	RC100X LED37/840 W30L120 WIA	220 to 240 V	50 or 60 Hz	26.1 W
72784799	SM100C LED37S 840 W30L120 PSU G3	220 to 240 V	50 to 60 Hz	32 W
01519551	SM100C LED37S 840 W30L120 PSD G3	220 to 240 V	50 to 60 Hz	32 W

Order Code	Full Product Name	Input Voltage	Line Frequency	Power Consumption
01519951	SM100C LED37S 865 W30L120 PSU UNV G3	110 to 277 V	50 to 60 Hz	32 W
52116299	RC100B LED27S 840 W60L60 PSU G3	220 to 240 V	50 to 60 Hz	23 W
01508651	RC100B LED27S 865 W60L60 PSU G3	220 to 240 V	50 to 60 Hz	23 W
01509551	RC100B LED37S 840 W60L60 PSU UNV G3	110 to 277 V	50 to 60 Hz	32 W
01509651	SM100C LED37S 840 W60L60 PSD G3	220 to 240 V	50 to 60 Hz	32 W
01509951	SM100C LED27S 840 W60L60 PSU G3	220 to 240 V	50 to 60 Hz	23 W
72783099	SM100C LED37S 840 W60L60 PSU G3	220 to 240 V	50 to 60 Hz	32 W
72782399	RC100B LED37S 840 W60L60 PSU G3	220 to 240 V	50 to 60 Hz	32 W
01510851	RC100B LED37S 840 W60L60 PSD OC G3	220 to 240 V	50 to 60 Hz	32 W
01510951	RC100B LED37S 865 W60L60 PSU G3	220 to 240 V	50 to 60 Hz	32 W
51949799	RC100B LED37S 840 W60L60 PSD G3	220 to 240 V	50 to 60 Hz	32 W
911401511847	RC100B LED27S 840 W60L60 PSU G3	220 to 240 V	50 or 60 Hz	18.7 W
911401511947	RC100B LED27S 865 W60L60 PSU G3	220 to 240 V	50 or 60 Hz	18.7 W
911401512047	RC100B LED37S 840 W60L60 PSU G3	220 to 240 V	50 or 60 Hz	25.8 W
911401512147	RC100B LED37S 865 W60L60 PSU G3	220 to 240 V	50 or 60 Hz	25.8 W
911401512847	SM100C LED27S 840 W60L60 PSU G3	220 to 240 V	50 or 60 Hz	18.7 W
911401512947	SM100C LED37S 840 W60L60 PSU G3	220 to 240 V	50 or 60 Hz	25.8 W
911401513347	RC100B LED37S 840 W60L60 PSD G3	220 to 240 V	50 or 60 Hz	25.2 W
911401513447	RC100B LED37S 865 W60L60 PSD G3	220 to 240 V	50 or 60 Hz	25.2 W
911401513647	RC100B LED37S 840 W60L60 PSD OC G3	220 to 240 V	50 or 60 Hz	25.2 W
911401513747	RC100B LED37S 865 W60L60 PSD OC G3	220 to 240 V	50 or 60 Hz	25.2 W
911401514247	SM100C LED37S 840 W60L60 PSD G3	220 to 240 V	50 or 60 Hz	25.2 W
911401514447	RC100X LED37/840 W60L60 WIA	220 to 240 V	50 or 60 Hz	26.1 W
911401514547	RC100X LED37/865 W60L60 WIA	220 to 240 V	50 or 60 Hz	26.1 W
01514351	RC100B LED54S 840 W60L120 PSU G3	220 to 240 V	50 to 60 Hz	44 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401512547	RC100B LED37S 840 W30L120 PSU G3	-
01513051	RC100B LED37S 840 W30L120 PSD OC G3	Yes
911401513147	SM100C LED37S 840 W30L120 PSU G3	-
911401513247	SM100C LED37S 840 W30L120 PSU G3	-
01513251	RC100B LED37S 840 W30L120 PSD G3	Yes
72781699	RC100B LED37S 840 W30L120 PSU G3	No
01513751	RC100B LED37S 865 W30L120 PSU UNV G3	No
911401513847	RC100B LED37S 840 W30L120 PSD OC G3	DALI
911401513947	RC100B LED37S 840 W30L120 PSD G3	DALI
911401514347	SM100C LED37S 840 W30L120 PSD G3	DALI
911401514747	RC100X LED37/840 W30L120 WIA	Wireless Dim
72784799	SM100C LED37S 840 W30L120 PSU G3	No
01519551	SM100C LED37S 840 W30L120 PSD G3	Yes

Order Code	Full Product Name	Dimmable
01519951	SM100C LED37S 865 W30L120 PSU UNV G3	No
52116299	RC100B LED27S 840 W60L60 PSU G3	No
01508651	RC100B LED27S 865 W60L60 PSU G3	No
01509551	RC100B LED37S 840 W60L60 PSU UNV G3	No
01509651	SM100C LED37S 840 W60L60 PSD G3	Yes
01509951	SM100C LED27S 840 W60L60 PSU G3	No
72783099	SM100C LED37S 840 W60L60 PSU G3	No
72782399	RC100B LED37S 840 W60L60 PSU G3	No
01510851	RC100B LED37S 840 W60L60 PSD OC G3	Yes
01510951	RC100B LED37S 865 W60L60 PSU G3	No
51949799	RC100B LED37S 840 W60L60 PSD G3	Yes
911401511847	RC100B LED27S 840 W60L60 PSU G3	-
911401511947	RC100B LED27S 865 W60L60 PSU G3	-
911401512047	RC100B LED37S 840 W60L60 PSU G3	-
911401512147	RC100B LED37S 865 W60L60 PSU G3	-
911401512847	SM100C LED27S 840 W60L60 PSU G3	-
911401512947	SM100C LED37S 840 W60L60 PSU G3	-
911401513347	RC100B LED37S 840 W60L60 PSD G3	DALI
911401513447	RC100B LED37S 865 W60L60 PSD G3	DALI
911401513647	RC100B LED37S 840 W60L60 PSD OC G3	DALI
911401513747	RC100B LED37S 865 W60L60 PSD OC G3	DALI
911401514247	SM100C LED37S 840 W60L60 PSD G3	DALI
911401514447	RC100X LED37/840 W60L60 WIA	Wireless Dim
911401514547	RC100X LED37/865 W60L60 WIA	Wireless Dim
01514351	RC100B LED54S 840 W60L120 PSU G3	No

Mechanical and Housing

Order Code	Full Product Name	Optical cover type
911401512547	RC100B LED37S 840 W30L120 PSU G3	Polycarbonate bowl/cover
01513051	RC100B LED37S 840 W30L120 PSD OC G3	Variable linear-lens array in polycarbonate cover
911401513147	SM100C LED37S 840 W30L120 PSU G3	Polycarbonate bowl/cover
911401513247	SM100C LED37S 840 W30L120 PSU G3	Polycarbonate bowl/cover
01513251	RC100B LED37S 840 W30L120 PSD G3	Variable linear-lens array in polycarbonate cover
72781699	RC100B LED37S 840 W30L120 PSU G3	Variable linear-lens array in polycarbonate cover
01513751	RC100B LED37S 865 W30L120 PSU UNV G3	Variable linear-lens array in polycarbonate cover
911401513847	RC100B LED37S 840 W30L120 PSD OC G3	Polycarbonate bowl/cover
911401513947	RC100B LED37S 840 W30L120 PSD G3	Polycarbonate bowl/cover
911401514347	SM100C LED37S 840 W30L120 PSD G3	Polycarbonate bowl/cover
911401514747	RC100X LED37/840 W30L120 WIA	Polycarbonate bowl/cover
72784799	SM100C LED37S 840 W30L120 PSU G3	Variable linear-lens array in polycarbonate cover
01519551	SM100C LED37S 840 W30L120 PSD G3	Variable linear-lens array in polycarbonate cover

Order Code	Full Product Name	Optical cover type
01519951	SM100C LED37S 865 W30L120 PSU UNV G3	Variable linear-lens array in polycarbonate cover
52116299	RC100B LED27S 840 W60L60 PSU G3	Variable linear-lens array in polycarbonate cover
01508651	RC100B LED27S 865 W60L60 PSU G3	Variable linear-lens array in polycarbonate cover
01509551	RC100B LED37S 840 W603L603 PSU UNV G3	Variable linear-lens array in polycarbonate cover
01509651	SM100C LED37S 840 W60L60 PSD G3	Variable linear-lens array in polycarbonate cover
01509951	SM100C LED27S 840 W60L60 PSU G3	Variable linear-lens array in polycarbonate cover
72783099	SM100C LED37S 840 W60L60 PSU G3	Variable linear-lens array in polycarbonate cover
72782399	RC100B LED37S 840 W60L60 PSU G3	Variable linear-lens array in polycarbonate cover
01510851	RC100B LED37S 840 W60L60 PSD OC G3	Variable linear-lens array in polycarbonate cover
01510951	RC100B LED37S 865 W60L60 PSU G3	Variable linear-lens array in polycarbonate cover
51949799	RC100B LED37S 840 W60L60 PSD G3	Variable linear-lens array in polycarbonate cover
911401511847	RC100B LED27S 840 W60L60 PSU G3	Polycarbonate bowl/cover
911401511947	RC100B LED27S 865 W60L60 PSU G3	Polycarbonate bowl/cover
911401512047	RC100B LED37S 840 W60L60 PSU G3	Polycarbonate bowl/cover
911401512147	RC100B LED37S 865 W60L60 PSU G3	Polycarbonate bowl/cover
911401512847	SM100C LED27S 840 W60L60 PSU G3	Polycarbonate bowl/cover
911401512947	SM100C LED37S 840 W60L60 PSU G3	Polycarbonate bowl/cover
911401513347	RC100B LED37S 840 W60L60 PSD G3	Polycarbonate bowl/cover
911401513447	RC100B LED37S 865 W60L60 PSD G3	Polycarbonate bowl/cover
911401513647	RC100B LED37S 840 W60L60 PSD OC G3	Polycarbonate bowl/cover
911401513747	RC100B LED37S 865 W60L60 PSD OC G3	Polycarbonate bowl/cover
911401514247	SM100C LED37S 840 W60L60 PSD G3	Polycarbonate bowl/cover
911401514447	RC100X LED37/840 W60L60 WIA	Polycarbonate bowl/cover
911401514547	RC100X LED37/865 W60L60 WIA	Polycarbonate bowl/cover
01514351	RC100B LED54S 840 W60L120 PSU G3	Variable linear-lens array in polycarbonate cover

Approval and Application

Order Code	Full Product Name	Glow-wire test	Flammability mark
911401512547	RC100B LED37S 840 W30L120 PSU G3	Temperature 650 °C, duration 30 s	-
01513051	RC100B LED37S 840 W30L120 PSD OC G3	Temperature 600 °C, duration 30 s	For mounting on normally flammable surfaces
911401513147	SM100C LED37S 840 W30L120 PSU G3	Temperature 650 °C, duration 30 s	-
911401513247	SM100C LED37S 840 W30L120 PSU G3	Temperature 650 °C, duration 30 s	-
01513251	RC100B LED37S 840 W30L120 PSD G3	Temperature 600 °C, duration 30 s	For mounting on normally flammable surfaces
72781699	RC100B LED37S 840 W30L120 PSU G3	Temperature 600 °C, duration 30 s	For mounting on normally flammable surfaces
01513751	RC100B LED37S 865 W30L120 PSU UNV G3	Temperature 600 °C, duration 30 s	For mounting on normally flammable surfaces
911401513847	RC100B LED37S 840 W30L120 PSD OC G3	Temperature 650 °C, duration 30 s	-
911401513947	RC100B LED37S 840 W30L120 PSD G3	Temperature 650 °C, duration 30 s	-
911401514347	SM100C LED37S 840 W30L120 PSD G3	Temperature 650 °C, duration 30 s	-
911401514747	RC100X LED37/840 W30L120 WIA	Temperature 650 °C, duration 30 s	-
72784799	SM100C LED37S 840 W30L120 PSU G3	Temperature 600 °C, duration 30 s	For mounting on normally flammable surfaces
01519551	SM100C LED37S 840 W30L120 PSD G3	Temperature 600 °C, duration 30 s	For mounting on normally flammable surfaces

Order Code	Full Product Name	Glow-wire test	Flammability mark
01519951	SM100C LED37S 865 W30L120 PSU UNV G3	Temperature 600 °C, duration 30 s	For mounting on normally flammable surfaces
52116299	RC100B LED27S 840 W60L60 PSU G3	Temperature 600 °C, duration 30 s	For mounting on normally flammable surfaces
01508651	RC100B LED27S 865 W60L60 PSU G3	Temperature 600 °C, duration 30 s	For mounting on normally flammable surfaces
01509551	RC100B LED37S 840 W60L60 PSU UNV G3	Temperature 600 °C, duration 30 s	For mounting on normally flammable surfaces
01509651	SM100C LED37S 840 W60L60 PSD G3	Temperature 600 °C, duration 30 s	For mounting on normally flammable surfaces
01509951	SM100C LED27S 840 W60L60 PSU G3	Temperature 600 °C, duration 30 s	For mounting on normally flammable surfaces
72783099	SM100C LED37S 840 W60L60 PSU G3	Temperature 600 °C, duration 30 s	For mounting on normally flammable surfaces
72782399	RC100B LED37S 840 W60L60 PSU G3	Temperature 600 °C, duration 30 s	For mounting on normally flammable surfaces
01510851	RC100B LED37S 840 W60L60 PSD OC G3	Temperature 600 °C, duration 30 s	For mounting on normally flammable surfaces
01510951	RC100B LED37S 865 W60L60 PSU G3	Temperature 600 °C, duration 30 s	For mounting on normally flammable surfaces
51949799	RC100B LED37S 840 W60L60 PSD G3	Temperature 600 °C, duration 30 s	For mounting on normally flammable surfaces
911401511847	RC100B LED27S 840 W60L60 PSU G3	Temperature 650 °C, duration 30 s	-
911401511947	RC100B LED27S 865 W60L60 PSU G3	Temperature 650 °C, duration 30 s	-
911401512047	RC100B LED37S 840 W60L60 PSU G3	Temperature 650 °C, duration 30 s	-
911401512147	RC100B LED37S 865 W60L60 PSU G3	Temperature 650 °C, duration 30 s	-
911401512847	SM100C LED27S 840 W60L60 PSU G3	Temperature 650 °C, duration 30 s	-
911401512947	SM100C LED37S 840 W60L60 PSU G3	Temperature 650 °C, duration 30 s	-
911401513347	RC100B LED37S 840 W60L60 PSD G3	Temperature 650 °C, duration 30 s	-
911401513447	RC100B LED37S 865 W60L60 PSD G3	Temperature 650 °C, duration 30 s	-
911401513647	RC100B LED37S 840 W60L60 PSD OC G3	Temperature 650 °C, duration 30 s	-
911401513747	RC100B LED37S 865 W60L60 PSD OC G3	Temperature 650 °C, duration 30 s	-
911401514247	SM100C LED37S 840 W60L60 PSD G3	Temperature 650 °C, duration 30 s	-
911401514447	RC100X LED37/840 W60L60 WIA	Temperature 650 °C, duration 30 s	-
911401514547	RC100X LED37/865 W60L60 WIA	Temperature 650 °C, duration 30 s	-
01514351	RC100B LED54S 840 W60L120 PSU G3	Temperature 600 °C, duration 30 s	For mounting on normally flammable surfaces