



Energy saving without compromise.

GreenPerform Troffer

GreenPerform troffer improves the compact design of the last generation with performance improvement and more variants for different markets. Integrating with all available system: POE, InterAct office wireless, InterAct Office Pro, ActiLume controller, GreenPerform troffer offers additional energy saving and connected features.

Benefits

- Upgrade to smart office with more options
- Energy saving
- Slim housing
- Comfortable light
- Good light quality
- Office compliant
- Reliable performance

Features

- Compatible with all available Philips systems
- Efficacy up to 125lm/W
- Slim design with height less than 46mm
- Improved optical design without zebra effect
- CRI > 80, SDCM<4, Flicker free
- UGR 19 available
- Lifetime L70 50,000 hours

Application

- Open Office
- Public Area
- Meeting Room
- Training Room


GreenPerform Troffer

Specifications

| | |
|-----------------------------|--|
| Ceiling type | T-bar ceiling |
| Mains Voltage | 220-240V / 50-60Hz |
| Dimming | PSU: non-dimmable |
| | PSD: Dimmable via Dali-broadcasting |
| | WIA: Wireless control, compatible with Interact |
| | SIA: Wireless control, compatible with Interact and with SNS210 sensor |
| Control system input | Dali |

| | |
|--|---------------------------------------|
| Lumen maintenance at median useful life 50.000h | L70B50 |
| Correlated color temperature - CCT | 840 |
| UGR | 19 is available through certain types |
| Installation | Recessed |





Versions



GreenPerform Troffer RC100B 60x60


GreenPerform Troffer RC100B 60x120

Dimensional drawing



GreenPerform Troffer

Dimensional drawing



| General Information | |
|-------------------------------------|----------------|
| Driver included | Yes |
| Number of gear units | 1 unit |
| Light Technical | |
| Color rendering index (CRI) | 80 |
| Operating and Electrical | |
| Protection class IEC | Safety class I |
| Suitable for random switching | No |
| Mechanical and Housing | |
| Housing Color | White |
| Mech. impact protection code | IK03 |
| Ingress protection code | IP20 |
| Approval and Application | |
| Ambient temperature range | -20 to +40 °C |
| CE mark | Yes |
| ENEC mark | - |
| Initial Performance (IEC Compliant) | |
| Luminous flux tolerance | +/-10% |

General Information

| Order Code | Full Product Name | Light source replaceable | Service tag |
|--------------|--------------------------------------|--------------------------|-------------|
| 911401512547 | RC100B LED37S 840 W30L120 PSU G3 | - | - |
| 01513051 | RC100B LED37S 840 W30L120 PSD OC G3 | No | Yes |
| 911401513147 | SM100C LED37S 840 W30L120 PSU G3 | - | - |
| 911401513247 | SM100C LED37S 840 W30L120 PSU G3 | - | - |
| 01513251 | RC100B LED37S 840 W30L120 PSD G3 | No | Yes |
| 72781699 | RC100B LED37S 840 W30L120 PSU G3 | No | Yes |
| 01513751 | RC100B LED37S 865 W30L120 PSU UNV G3 | No | Yes |
| 911401513847 | RC100B LED37S 840 W30L120 PSD OC G3 | - | - |
| 911401513947 | RC100B LED37S 840 W30L120 PSD G3 | - | - |
| 911401514347 | SM100C LED37S 840 W30L120 PSD G3 | - | - |
| 911401514747 | RC100X LED37/840 W30L120 WIA | - | - |
| 72784799 | SM100C LED37S 840 W30L120 PSU G3 | No | Yes |
| 01519551 | SM100C LED37S 840 W30L120 PSD G3 | No | Yes |
| 01519951 | SM100C LED37S 865 W30L120 PSU UNV G3 | No | Yes |
| 52116299 | RC100B LED27S 840 W60L60 PSU G3 | No | Yes |
| 01508651 | RC100B LED27S 865 W60L60 PSU G3 | No | Yes |
| 01509551 | RC100B LED37S 840 W60L60 PSU UNV G3 | No | Yes |
| 01509651 | SM100C LED37S 840 W60L60 PSD G3 | No | Yes |
| 01509951 | SM100C LED27S 840 W60L60 PSU G3 | No | Yes |
| 72783099 | SM100C LED37S 840 W60L60 PSU G3 | No | Yes |
| 72782399 | RC100B LED37S 840 W60L60 PSU G3 | No | Yes |
| 01510851 | RC100B LED37S 840 W60L60 PSD OC G3 | No | Yes |
| 01510951 | RC100B LED37S 865 W60L60 PSU G3 | No | Yes |
| 51949799 | RC100B LED37S 840 W60L60 PSD G3 | No | Yes |
| 911401511847 | RC100B LED27S 840 W60L60 PSU G3 | - | - |
| 911401511947 | RC100B LED27S 865 W60L60 PSU G3 | - | - |
| 911401512047 | RC100B LED37S 840 W60L60 PSU G3 | - | - |
| 911401512147 | RC100B LED37S 865 W60L60 PSU G3 | - | - |
| 911401512847 | SM100C LED27S 840 W60L60 PSU G3 | - | - |
| 911401512947 | SM100C LED37S 840 W60L60 PSU G3 | - | - |
| 911401513347 | RC100B LED37S 840 W60L60 PSD G3 | - | - |
| 911401513447 | RC100B LED37S 865 W60L60 PSD G3 | - | - |
| 911401513647 | RC100B LED37S 840 W60L60 PSD OC G3 | - | - |
| 911401513747 | RC100B LED37S 865 W60L60 PSD OC G3 | - | - |
| 911401514247 | SM100C LED37S 840 W60L60 PSD G3 | - | - |
| 911401514447 | RC100X LED37/840 W60L60 WIA | - | - |
| 911401514547 | RC100X LED37/865 W60L60 WIA | - | - |
| 01514351 | RC100B LED54S 840 W60L120 PSU G3 | No | Yes |

Light Technical (1/2)

| Order Code | Full Product Name | Beam angle of light source | Correlated Color | | | Order Code | Full Product Name | Beam angle of light source | Correlated Color | | |
|--------------|----------------------------------|----------------------------|-------------------|---------------------------------|---------------|------------|-------------------------------------|----------------------------|-------------------|---------------------------------|---------------|
| | | | Temperature (Nom) | Luminous Efficacy (rated) (Nom) | Luminous Flux | | | | Temperature (Nom) | Luminous Efficacy (rated) (Nom) | Luminous Flux |
| 911401512547 | RC100B LED37S 840 W30L120 PSU G3 | 120 degree(s) | 4000 K | 155.03875968992247 lm/W | 4,000 lm | 01513051 | RC100B LED37S 840 W30L120 PSD OC G3 | - | 4000 K | 121 lm/W | 3,700 lm |

GreenPerform Troffer

| Order Code | Full Product Name | Beam angle of light source | Correlated Color | | |
|--------------|---|----------------------------|-------------------|---------------------------------|---------------|
| | | | Temperature (Nom) | Luminous Efficacy (rated) (Nom) | Luminous Flux |
| 911401513147 | SM100C LED37S 840 W30L120 PSU G3 | 120 degree(s) | 4000 K | 155.03875968992247 lm/W | 4,000 lm |
| 911401513247 | SM100C LED37S 840 W30L120 PSU G3 | 120 degree(s) | 4000 K | 155.03875968992247 lm/W | 4,000 lm |
| 01513251 | RC100B LED37S 840 W30L120 PSD G3 | - | 4000 K | 116 lm/W | 3,700 lm |
| 72781699 | RC100B LED37S 840 W30L120 PSU G3 | - | 4000 K | 116 lm/W | 3,700 lm |
| 01513751 | RC100B LED37S 865 W30L120 PSU UNV G3 | - | 6500 K | 116 lm/W | 3,700 lm |
| 911401513847 | RC100B LED37S 840 W30L120 PSD OC G3 | 120 degree(s) | 4000 K | 166.66666666666666 lm/W | 4,200 lm |
| 911401513947 | RC100B LED37S 840 W30L120 PSD G3 | 120 degree(s) | 4000 K | 158.73015873015873 lm/W | 4,000 lm |
| 911401514347 | SM100C LED37S 840 W30L120 PSD G3 | 120 degree(s) | 4000 K | 158.73015873015873 lm/W | 4,000 lm |
| 911401514747 | RC100X LED37/840 W30L120 WIA | 120 degree(s) | 4000 K | 153.2567049808429 lm/W | 4,000 lm |
| 72784799 | SM100C LED37S 840 | - | 4000 K | 116 lm/W | 3,700 lm |

| Order Code | Full Product Name | Beam angle of light source | Correlated Color | | |
|------------|--|----------------------------|-------------------|---------------------------------|---------------|
| | | | Temperature (Nom) | Luminous Efficacy (rated) (Nom) | Luminous Flux |
| | W30L120 PSU G3 | | | | |
| 01519551 | SM100C LED37S 840 W30L120 PSD G3 | - | 4000 K | 116 lm/W | 3,700 lm |
| 01519951 | SM100C LED37S 865 W30L120 PSU UNV G3 | - | 6500 K | 116 lm/W | 3,700 lm |
| 52116299 | RC100B LED27S 840 W60L60 PSU G3 | - | 4000 K | 117 lm/W | 2,700 lm |
| 01508651 | RC100B LED27S 865 W60L60 PSU G3 | - | 6500 K | 117 lm/W | 2,700 lm |
| 01509551 | RC100B LED37S 840 W603L603 PSU UNV G3 | - | 4000 K | 116 lm/W | 3,700 lm |
| 01509651 | SM100C LED37S 840 W60L60 PSD G3 | - | 4000 K | 116 lm/W | 3,700 lm |
| 01509951 | SM100C LED27S 840 W60L60 PSU G3 | - | 4000 K | 117 lm/W | 2,700 lm |
| 72783099 | SM100C LED37S 840 W60L60 PSU G3 | - | 4000 K | 116 lm/W | 3,700 lm |
| 72782399 | RC100B LED37S 840 W60L60 PSU G3 | - | 4000 K | 116 lm/W | 3,700 lm |

GreenPerform Troffer

| Order Code | Full Product Name | Beam angle of light source | Correlated Color | | |
|--------------|--|----------------------------|-------------------|---------------------------------|---------------|
| | | | Temperature (Nom) | Luminous Efficacy (rated) (Nom) | Luminous Flux |
| 01510851 | RC100B LED37S 840 W60L60 PSD OC G3 | - | 4000 K | 121 lm/W | 3,700 lm |
| 01510951 | RC100B LED37S 865 W60L60 PSU G3 | - | 6500 K | 116 lm/W | 3,700 lm |
| 51949799 | RC100B LED37S 840 W60L60 PSD G3 | - | 4000 K | 116 lm/W | 3,700 lm |
| 911401511847 | RC100B LED27S 840 W60L60 PSU G3 | 120 degree(s) | 4000 K | 154.54545454545456 lm/W | 2,890 lm |
| 911401511947 | RC100B LED27S 865 W60L60 PSU G3 | 120 degree(s) | 6500 K | 154.55 lm/W | 2,890 lm |
| 911401512047 | RC100B LED37S 840 W60L60 PSU G3 | 120 degree(s) | 4000 K | 155.03875968992247 lm/W | 4,000 lm |
| 911401512147 | RC100B LED37S 865 W60L60 PSU G3 | 120 degree(s) | 6500 K | 155.03875968992247 lm/W | 4,000 lm |
| 911401512847 | SM100C LED27S 840 W60L60 PSU G3 | 120 degree(s) | 4000 K | 154.54545454545456 lm/W | 2,890 lm |
| 911401512947 | SM100C LED37S 840 W60L60 PSU G3 | 120 degree(s) | 4000 K | 155.03875968992247 lm/W | 4,000 lm |

| Order Code | Full Product Name | Beam angle of light source | Correlated Color | | |
|--------------|--|----------------------------|-------------------|---------------------------------|---------------|
| | | | Temperature (Nom) | Luminous Efficacy (rated) (Nom) | Luminous Flux |
| 911401513347 | RC100B LED37S 840 W60L60 PSD G3 | 120 degree(s) | 4000 K | 158.73015873015873 lm/W | 4,000 lm |
| 911401513447 | RC100B LED37S 865 W60L60 PSD G3 | 120 degree(s) | 6500 K | 158.73015873015873 lm/W | 4,000 lm |
| 911401513647 | RC100B LED37S 840 W60L60 PSD OC G3 | 120 degree(s) | 4000 K | 166.66666666666666 lm/W | 4,200 lm |
| 911401513747 | RC100B LED37S 865 W60L60 PSD OC G3 | 120 degree(s) | 6500 K | 166.66666666666666 lm/W | 4,200 lm |
| 911401514247 | SM100C LED37S 840 W60L60 PSD G3 | 120 degree(s) | 4000 K | 158.73015873015873 lm/W | 4,000 lm |
| 911401514447 | RC100X LED37/840 W60L60 WIA | 120 degree(s) | 4000 K | 153.2567049808429 lm/W | 4,000 lm |
| 911401514547 | RC100X LED37/865 W60L60 WIA | 120 degree(s) | 6500 K | 153.2567049808429 lm/W | 4,000 lm |
| 01514351 | RC100B LED54S 840 W60L120 PSU G3 | - | 4000 K | 123 lm/W | 5,400 lm |

Light Technical (2/2)

GreenPerform Troffer

| Order Code | Full Product Name | Number of light sources | Optic type |
|--------------|--------------------------------------|-------------------------|--------------------------|
| 911401512547 | RC100B LED37S 840 W30L120 PSU G3 | 2 | Opal prismatic reflector |
| 01513051 | RC100B LED37S 840 W30L120 PSD OC G3 | - | - |
| 911401513147 | SM100C LED37S 840 W30L120 PSU G3 | 2 | Opal prismatic reflector |
| 911401513247 | SM100C LED37S 840 W30L120 PSU G3 | 2 | Opal prismatic reflector |
| 01513251 | RC100B LED37S 840 W30L120 PSD G3 | - | - |
| 72781699 | RC100B LED37S 840 W30L120 PSU G3 | - | - |
| 01513751 | RC100B LED37S 865 W30L120 PSU UNV G3 | - | - |
| 911401513847 | RC100B LED37S 840 W30L120 PSD OC G3 | 2 | Opal prismatic reflector |
| 911401513947 | RC100B LED37S 840 W30L120 PSD G3 | 2 | Opal prismatic reflector |
| 911401514347 | SM100C LED37S 840 W30L120 PSD G3 | 2 | Opal prismatic reflector |
| 911401514747 | RC100X LED37/840 W30L120 WIA | 2 | Opal prismatic reflector |
| 72784799 | SM100C LED37S 840 W30L120 PSU G3 | - | - |
| 01519551 | SM100C LED37S 840 W30L120 PSD G3 | - | - |
| 01519951 | SM100C LED37S 865 W30L120 PSU UNV G3 | - | - |
| 52116299 | RC100B LED27S 840 W60L60 PSU G3 | - | - |
| 01508651 | RC100B LED27S 865 W60L60 PSU G3 | - | - |
| 01509551 | RC100B LED37S 840 W60L60 PSU UNV G3 | - | - |
| 01509651 | SM100C LED37S 840 W60L60 PSD G3 | - | - |
| 01509951 | SM100C LED27S 840 W60L60 PSU G3 | - | - |
| 72783099 | SM100C LED37S 840 W60L60 PSU G3 | - | - |

| Order Code | Full Product Name | Number of light sources | Optic type |
|--------------|------------------------------------|-------------------------|--------------------------|
| 72782399 | RC100B LED37S 840 W60L60 PSU G3 | - | - |
| 01510851 | RC100B LED37S 840 W60L60 PSD OC G3 | - | - |
| 01510951 | RC100B LED37S 865 W60L60 PSU G3 | - | - |
| 51949799 | RC100B LED37S 840 W60L60 PSD G3 | - | - |
| 911401511847 | RC100B LED27S 840 W60L60 PSU G3 | 2 | Opal prismatic reflector |
| 911401511947 | RC100B LED27S 865 W60L60 PSU G3 | 2 | Opal prismatic reflector |
| 911401512047 | RC100B LED37S 840 W60L60 PSU G3 | 2 | Opal prismatic reflector |
| 911401512147 | RC100B LED37S 865 W60L60 PSU G3 | 2 | Opal prismatic reflector |
| 911401512847 | SM100C LED27S 840 W60L60 PSU G3 | 2 | Opal prismatic reflector |
| 911401512947 | SM100C LED37S 840 W60L60 PSU G3 | 2 | Opal prismatic reflector |
| 911401513347 | RC100B LED37S 840 W60L60 PSD G3 | 2 | Opal prismatic reflector |
| 911401513447 | RC100B LED37S 865 W60L60 PSD G3 | 2 | Opal prismatic reflector |
| 911401513647 | RC100B LED37S 840 W60L60 PSD OC G3 | 2 | Opal prismatic reflector |
| 911401513747 | RC100B LED37S 865 W60L60 PSD OC G3 | 2 | Opal prismatic reflector |
| 911401514247 | SM100C LED37S 840 W60L60 PSD G3 | 2 | Opal prismatic reflector |
| 911401514447 | RC100X LED37/840 W60L60 WIA | 2 | Opal prismatic reflector |
| 911401514547 | RC100X LED37/865 W60L60 WIA | 2 | Opal prismatic reflector |
| 01514351 | RC100B LED54S 840 W60L120 PSU G3 | - | - |

Operating and Electrical

| Order Code | Full Product Name | Input Voltage | Line Frequency | Power Consumption |
|--------------|-------------------------------------|---------------|----------------|-------------------|
| 911401512547 | RC100B LED37S 840 W30L120 PSU G3 | 220 to 240 V | 50 or 60 Hz | 25.8 W |
| 01513051 | RC100B LED37S 840 W30L120 PSD OC G3 | 220 to 240 V | 50 to 60 Hz | 32 W |
| 911401513147 | SM100C LED37S 840 W30L120 PSU G3 | 220 to 240 V | 50 or 60 Hz | 25.8 W |
| 911401513247 | SM100C LED37S 840 W30L120 PSU G3 | 220 to 240 V | 50 or 60 Hz | 25.8 W |
| 01513251 | RC100B LED37S 840 W30L120 PSD G3 | 220 to 240 V | 50 to 60 Hz | 32 W |
| 72781699 | RC100B LED37S 840 W30L120 PSU G3 | 220 to 240 V | 50 to 60 Hz | 32 W |

| Order Code | Full Product Name | Input Voltage | Line Frequency | Power Consumption |
|--------------|--------------------------------------|---------------|----------------|-------------------|
| 01513751 | RC100B LED37S 865 W30L120 PSU UNV G3 | 110 to 277 V | 50 to 60 Hz | 32 W |
| 911401513847 | RC100B LED37S 840 W30L120 PSD OC G3 | 220 to 240 V | 50 or 60 Hz | 25.2 W |
| 911401513947 | RC100B LED37S 840 W30L120 PSD G3 | 220 to 240 V | 50 or 60 Hz | 25.2 W |
| 911401514347 | SM100C LED37S 840 W30L120 PSD G3 | 220 to 240 V | 50 or 60 Hz | 25.2 W |
| 911401514747 | RC100X LED37/840 W30L120 WIA | 220 to 240 V | 50 or 60 Hz | 26.1 W |
| 72784799 | SM100C LED37S 840 W30L120 PSU G3 | 220 to 240 V | 50 to 60 Hz | 32 W |

GreenPerform Troffer

| Order Code | Full Product Name | Input Voltage | Line Frequency | Power | |
|--------------|---------------------------------------|---------------|----------------|-------------|--|
| | | | | Consumption | |
| 01519551 | SM100C LED37S 840 W30L120 PSD G3 | 220 to 240 V | 50 to 60 Hz | 32 W | |
| 01519951 | SM100C LED37S 865 W30L120 PSU UNV G3 | 110 to 277 V | 50 to 60 Hz | 32 W | |
| 52116299 | RC100B LED27S 840 W60L60 PSU G3 | 220 to 240 V | 50 to 60 Hz | 23 W | |
| 01508651 | RC100B LED27S 865 W60L60 PSU G3 | 220 to 240 V | 50 to 60 Hz | 23 W | |
| 01509551 | RC100B LED37S 840 W603L603 PSU UNV G3 | 110 to 277 V | 50 to 60 Hz | 32 W | |
| 01509651 | SM100C LED37S 840 W60L60 PSD G3 | 220 to 240 V | 50 to 60 Hz | 32 W | |
| 01509951 | SM100C LED27S 840 W60L60 PSU G3 | 220 to 240 V | 50 to 60 Hz | 23 W | |
| 72783099 | SM100C LED37S 840 W60L60 PSU G3 | 220 to 240 V | 50 to 60 Hz | 32 W | |
| 72782399 | RC100B LED37S 840 W60L60 PSU G3 | 220 to 240 V | 50 to 60 Hz | 32 W | |
| 01510851 | RC100B LED37S 840 W60L60 PSD OC G3 | 220 to 240 V | 50 to 60 Hz | 32 W | |
| 01510951 | RC100B LED37S 865 W60L60 PSU G3 | 220 to 240 V | 50 to 60 Hz | 32 W | |
| 51949799 | RC100B LED37S 840 W60L60 PSD G3 | 220 to 240 V | 50 to 60 Hz | 32 W | |
| 911401511847 | RC100B LED27S 840 W60L60 PSU G3 | 220 to 240 V | 50 or 60 Hz | 18.7 W | |

| Order Code | Full Product Name | Input Voltage | Line Frequency | Power | |
|--------------|------------------------------------|---------------|----------------|-------------|--|
| | | | | Consumption | |
| 911401511947 | RC100B LED27S 865 W60L60 PSU G3 | 220 to 240 V | 50 or 60 Hz | 18.7 W | |
| 911401512047 | RC100B LED37S 840 W60L60 PSU G3 | 220 to 240 V | 50 or 60 Hz | 25.8 W | |
| 911401512147 | RC100B LED37S 865 W60L60 PSU G3 | 220 to 240 V | 50 or 60 Hz | 25.8 W | |
| 911401512847 | SM100C LED27S 840 W60L60 PSU G3 | 220 to 240 V | 50 or 60 Hz | 18.7 W | |
| 911401512947 | SM100C LED37S 840 W60L60 PSU G3 | 220 to 240 V | 50 or 60 Hz | 25.8 W | |
| 911401513347 | RC100B LED37S 840 W60L60 PSD G3 | 220 to 240 V | 50 or 60 Hz | 25.2 W | |
| 911401513447 | RC100B LED37S 865 W60L60 PSD G3 | 220 to 240 V | 50 or 60 Hz | 25.2 W | |
| 911401513647 | RC100B LED37S 840 W60L60 PSD OC G3 | 220 to 240 V | 50 or 60 Hz | 25.2 W | |
| 911401513747 | RC100B LED37S 865 W60L60 PSD OC G3 | 220 to 240 V | 50 or 60 Hz | 25.2 W | |
| 911401514247 | SM100C LED37S 840 W60L60 PSD G3 | 220 to 240 V | 50 or 60 Hz | 25.2 W | |
| 911401514447 | RC100X LED37/840 W60L60 WIA | 220 to 240 V | 50 or 60 Hz | 26.1 W | |
| 911401514547 | RC100X LED37/865 W60L60 WIA | 220 to 240 V | 50 or 60 Hz | 26.1 W | |
| 01514351 | RC100B LED54S 840 W60L120 PSU G3 | 220 to 240 V | 50 to 60 Hz | 44 W | |

Controls and Dimming

| Order Code | Full Product Name | Dimmable |
|--------------|---------------------------------------|--------------|
| 911401512547 | RC100B LED37S 840 W30L120 PSU G3 | - |
| 01513051 | RC100B LED37S 840 W30L120 PSD OC G3 | Yes |
| 911401513147 | SM100C LED37S 840 W30L120 PSU G3 | - |
| 911401513247 | SM100C LED37S 840 W30L120 PSU G3 | - |
| 01513251 | RC100B LED37S 840 W30L120 PSD G3 | Yes |
| 72781699 | RC100B LED37S 840 W30L120 PSU G3 | No |
| 01513751 | RC100B LED37S 865 W30L120 PSU UNV G3 | No |
| 911401513847 | RC100B LED37S 840 W30L120 PSD OC G3 | DALI |
| 911401513947 | RC100B LED37S 840 W30L120 PSD G3 | DALI |
| 911401514347 | SM100C LED37S 840 W30L120 PSD G3 | DALI |
| 911401514747 | RC100X LED37/840 W30L120 WIA | Wireless Dim |
| 72784799 | SM100C LED37S 840 W30L120 PSU G3 | No |
| 01519551 | SM100C LED37S 840 W30L120 PSD G3 | Yes |
| 01519951 | SM100C LED37S 865 W30L120 PSU UNV G3 | No |
| 52116299 | RC100B LED27S 840 W60L60 PSU G3 | No |
| 01508651 | RC100B LED27S 865 W60L60 PSU G3 | No |
| 01509551 | RC100B LED37S 840 W603L603 PSU UNV G3 | No |
| 01509651 | SM100C LED37S 840 W60L60 PSD G3 | Yes |
| 01509951 | SM100C LED27S 840 W60L60 PSU G3 | No |

| Order Code | Full Product Name | Dimmable |
|--------------|------------------------------------|--------------|
| 72783099 | SM100C LED37S 840 W60L60 PSU G3 | No |
| 72782399 | RC100B LED37S 840 W60L60 PSU G3 | No |
| 01510851 | RC100B LED37S 840 W60L60 PSD OC G3 | Yes |
| 01510951 | RC100B LED37S 865 W60L60 PSU G3 | No |
| 51949799 | RC100B LED37S 840 W60L60 PSD G3 | Yes |
| 911401511847 | RC100B LED27S 840 W60L60 PSU G3 | - |
| 911401511947 | RC100B LED27S 865 W60L60 PSU G3 | - |
| 911401512047 | RC100B LED37S 840 W60L60 PSU G3 | - |
| 911401512147 | RC100B LED37S 865 W60L60 PSU G3 | - |
| 911401512847 | SM100C LED27S 840 W60L60 PSU G3 | - |
| 911401512947 | SM100C LED37S 840 W60L60 PSU G3 | - |
| 911401513347 | RC100B LED37S 840 W60L60 PSD G3 | DALI |
| 911401513447 | RC100B LED37S 865 W60L60 PSD G3 | DALI |
| 911401513647 | RC100B LED37S 840 W60L60 PSD OC G3 | DALI |
| 911401513747 | RC100B LED37S 865 W60L60 PSD OC G3 | DALI |
| 911401514247 | SM100C LED37S 840 W60L60 PSD G3 | DALI |
| 911401514447 | RC100X LED37/840 W60L60 WIA | Wireless Dim |
| 911401514547 | RC100X LED37/865 W60L60 WIA | Wireless Dim |
| 01514351 | RC100B LED54S 840 W60L120 PSU G3 | No |

Mechanical and Housing

| Order Code | Full Product Name | Optical cover type |
|--------------|--------------------------------------|---|
| 911401512547 | RC100B LED37S 840 W30L120 PSU G3 | Polycarbonate bowl/cover |
| 01513051 | RC100B LED37S 840 W30L120 PSD OC G3 | Variable linear-lens array in polycarbonate cover |
| 911401513147 | SM100C LED37S 840 W30L120 PSU G3 | Polycarbonate bowl/cover |
| 911401513247 | SM100C LED37S 840 W30L120 PSU G3 | Polycarbonate bowl/cover |
| 01513251 | RC100B LED37S 840 W30L120 PSD G3 | Variable linear-lens array in polycarbonate cover |
| 72781699 | RC100B LED37S 840 W30L120 PSU G3 | Variable linear-lens array in polycarbonate cover |
| 01513751 | RC100B LED37S 865 W30L120 PSU UNV G3 | Variable linear-lens array in polycarbonate cover |
| 911401513847 | RC100B LED37S 840 W30L120 PSD OC G3 | Polycarbonate bowl/cover |
| 911401513947 | RC100B LED37S 840 W30L120 PSD G3 | Polycarbonate bowl/cover |
| 911401514347 | SM100C LED37S 840 W30L120 PSD G3 | Polycarbonate bowl/cover |
| 911401514747 | RC100X LED37/840 W30L120 WIA | Polycarbonate bowl/cover |
| 72784799 | SM100C LED37S 840 W30L120 PSU G3 | Variable linear-lens array in polycarbonate cover |
| 01519551 | SM100C LED37S 840 W30L120 PSD G3 | Variable linear-lens array in polycarbonate cover |
| 01519951 | SM100C LED37S 865 W30L120 PSU UNV G3 | Variable linear-lens array in polycarbonate cover |
| 52116299 | RC100B LED27S 840 W60L60 PSU G3 | Variable linear-lens array in polycarbonate cover |
| 01508651 | RC100B LED27S 865 W60L60 PSU G3 | Variable linear-lens array in polycarbonate cover |
| 01509551 | RC100B LED37S 840 W60L60 PSU UNV G3 | Variable linear-lens array in polycarbonate cover |
| 01509651 | SM100C LED37S 840 W60L60 PSD G3 | Variable linear-lens array in polycarbonate cover |
| 01509951 | SM100C LED27S 840 W60L60 PSU G3 | Variable linear-lens array in polycarbonate cover |

| Order Code | Full Product Name | Optical cover type |
|--------------|------------------------------------|---|
| 72783099 | SM100C LED37S 840 W60L60 PSU G3 | Variable linear-lens array in polycarbonate cover |
| 72782399 | RC100B LED37S 840 W60L60 PSU G3 | Variable linear-lens array in polycarbonate cover |
| 01510851 | RC100B LED37S 840 W60L60 PSD OC G3 | Variable linear-lens array in polycarbonate cover |
| 01510951 | RC100B LED37S 865 W60L60 PSU G3 | Variable linear-lens array in polycarbonate cover |
| 51949799 | RC100B LED37S 840 W60L60 PSD G3 | Variable linear-lens array in polycarbonate cover |
| 911401511847 | RC100B LED27S 840 W60L60 PSU G3 | Polycarbonate bowl/cover |
| 911401511947 | RC100B LED27S 865 W60L60 PSU G3 | Polycarbonate bowl/cover |
| 911401512047 | RC100B LED37S 840 W60L60 PSU G3 | Polycarbonate bowl/cover |
| 911401512147 | RC100B LED37S 865 W60L60 PSU G3 | Polycarbonate bowl/cover |
| 911401512847 | SM100C LED27S 840 W60L60 PSU G3 | Polycarbonate bowl/cover |
| 911401512947 | SM100C LED37S 840 W60L60 PSU G3 | Polycarbonate bowl/cover |
| 911401513347 | RC100B LED37S 840 W60L60 PSD G3 | Polycarbonate bowl/cover |
| 911401513447 | RC100B LED37S 865 W60L60 PSD G3 | Polycarbonate bowl/cover |
| 911401513647 | RC100B LED37S 840 W60L60 PSD OC G3 | Polycarbonate bowl/cover |
| 911401513747 | RC100B LED37S 865 W60L60 PSD OC G3 | Polycarbonate bowl/cover |
| 911401514247 | SM100C LED37S 840 W60L60 PSD G3 | Polycarbonate bowl/cover |
| 911401514447 | RC100X LED37/840 W60L60 WIA | Polycarbonate bowl/cover |
| 911401514547 | RC100X LED37/865 W60L60 WIA | Polycarbonate bowl/cover |
| 01514351 | RC100B LED54S 840 W60L120 PSU G3 | Variable linear-lens array in polycarbonate cover |

Approval and Application

| Order Code | Full Product Name | Flammability mark | Glow-wire test |
|--------------|-------------------------------------|---|-----------------------------------|
| 911401512547 | RC100B LED37S 840 W30L120 PSU G3 | - | Temperature 650 °C, duration 30 s |
| 01513051 | RC100B LED37S 840 W30L120 PSD OC G3 | For mounting on normally flammable surfaces | Temperature 600 °C, duration 30 s |
| 911401513147 | SM100C LED37S 840 W30L120 PSU G3 | - | Temperature 650 °C, duration 30 s |
| 911401513247 | SM100C LED37S 840 W30L120 PSU G3 | - | Temperature 650 °C, duration 30 s |

| Order Code | Full Product Name | Flammability mark | Glow-wire test |
|------------|--------------------------------------|---|-----------------------------------|
| 01513251 | RC100B LED37S 840 W30L120 PSD G3 | For mounting on normally flammable surfaces | Temperature 600 °C, duration 30 s |
| 72781699 | RC100B LED37S 840 W30L120 PSU G3 | For mounting on normally flammable surfaces | Temperature 600 °C, duration 30 s |
| 01513751 | RC100B LED37S 865 W30L120 PSU UNV G3 | For mounting on normally flammable surfaces | Temperature 600 °C, duration 30 s |

GreenPerform Troffer

| Order Code | Full Product Name | Flammability mark | Glow-wire test |
|--------------|--|---|--------------------------------------|
| 911401513847 | RC100B LED37S 840 W30L120 PSD OC G3 | - | Temperature 650 °C, duration 30 s |
| 911401513947 | RC100B LED37S 840 W30L120 PSD G3 | - | Temperature 650 °C, duration 30 s |
| 911401514347 | SM100C LED37S 840 W30L120 PSD G3 | - | Temperature 650 °C, duration 30 s |
| 911401514747 | RC100X LED37/840 W30L120 WIA | - | Temperature 650 °C, duration 30 s |
| 72784799 | SM100C LED37S 840 W30L120 PSU G3 | For mounting on normally flammable surfaces | Temperature 600 °C, duration 30 s |
| 01519551 | SM100C LED37S 840 W30L120 PSD G3 | For mounting on normally flammable surfaces | Temperature 600 °C, duration 30 s |
| 01519951 | SM100C LED37S 865 W30L120 PSU UNV G3 | For mounting on normally flammable surfaces | Temperature 600 °C, duration 30 s |
| 52116299 | RC100B LED27S 840 W60L60 PSU G3 | For mounting on normally flammable surfaces | Temperature 600 °C, duration 30 s |
| 01508651 | RC100B LED27S 865 W60L60 PSU G3 | For mounting on normally flammable surfaces | Temperature 600 °C, duration 30 s |
| 01509551 | RC100B LED37S 840 W603L603 PSU UNV G3 | For mounting on normally flammable surfaces | Temperature 600 °C, duration 30 s |
| 01509651 | SM100C LED37S 840 W60L60 PSD G3 | For mounting on normally flammable surfaces | Temperature 600 °C, duration 30 s |
| 01509951 | SM100C LED27S 840 W60L60 PSU G3 | For mounting on normally flammable surfaces | Temperature 600 °C, duration 30 s |
| 72783099 | SM100C LED37S 840 W60L60 PSU G3 | For mounting on normally flammable surfaces | Temperature 600 °C, duration 30 s |
| 72782399 | RC100B LED37S 840 W60L60 PSU G3 | For mounting on normally flammable surfaces | Temperature 600 °C, duration 30 s |

| Order Code | Full Product Name | Flammability mark | Glow-wire test |
|--------------|---------------------------------------|---|--------------------------------------|
| 01510851 | RC100B LED37S 840 W60L60 PSD OC G3 | For mounting on normally flammable surfaces | Temperature 600 °C, duration 30 s |
| 01510951 | RC100B LED37S 865 W60L60 PSU G3 | For mounting on normally flammable surfaces | Temperature 600 °C, duration 30 s |
| 51949799 | RC100B LED37S 840 W60L60 PSD G3 | For mounting on normally flammable surfaces | Temperature 600 °C, duration 30 s |
| 911401511847 | RC100B LED27S 840 W60L60 PSU G3 | - | Temperature 650 °C, duration 30 s |
| 911401511947 | RC100B LED27S 865 W60L60 PSU G3 | - | Temperature 650 °C, duration 30 s |
| 911401512047 | RC100B LED37S 840 W60L60 PSU G3 | - | Temperature 650 °C, duration 30 s |
| 911401512147 | RC100B LED37S 865 W60L60 PSU G3 | - | Temperature 650 °C, duration 30 s |
| 911401512847 | SM100C LED27S 840 W60L60 PSU G3 | - | Temperature 650 °C, duration 30 s |
| 911401512947 | SM100C LED37S 840 W60L60 PSU G3 | - | Temperature 650 °C, duration 30 s |
| 911401513347 | RC100B LED37S 840 W60L60 PSD G3 | - | Temperature 650 °C, duration 30 s |
| 911401513447 | RC100B LED37S 865 W60L60 PSD G3 | - | Temperature 650 °C, duration 30 s |
| 911401513647 | RC100B LED37S 840 W60L60 PSD OC G3 | - | Temperature 650 °C, duration 30 s |
| 911401513747 | RC100B LED37S 865 W60L60 PSD OC G3 | - | Temperature 650 °C, duration 30 s |
| 911401514247 | SM100C LED37S 840 W60L60 PSD G3 | - | Temperature 650 °C, duration 30 s |
| 911401514447 | RC100X LED37/840 W60L60 WIA | - | Temperature 650 °C, duration 30 s |
| 911401514547 | RC100X LED37/865 W60L60 WIA | - | Temperature 650 °C, duration 30 s |
| 01514351 | RC100B LED54S 840 W60L120 PSU G3 | For mounting on normally flammable surfaces | Temperature 600 °C, duration 30 s |

Initial Performance (IEC Compliant)

| Order Code | Full Product Name | Initial chromaticity |
|--------------|--------------------------------------|----------------------|
| 911401512547 | RC100B LED37S 840 W30L120 PSU G3 | - |
| 01513051 | RC100B LED37S 840 W30L120 PSD OC G3 | SDCM<4 |
| 911401513147 | SM100C LED37S 840 W30L120 PSU G3 | - |
| 911401513247 | SM100C LED37S 840 W30L120 PSU G3 | - |
| 01513251 | RC100B LED37S 840 W30L120 PSD G3 | SDCM<4 |
| 72781699 | RC100B LED37S 840 W30L120 PSU G3 | SDCM<4 |
| 01513751 | RC100B LED37S 865 W30L120 PSU UNV G3 | SDCM<4 |
| 911401513847 | RC100B LED37S 840 W30L120 PSD OC G3 | - |
| 911401513947 | RC100B LED37S 840 W30L120 PSD G3 | - |
| 911401514347 | SM100C LED37S 840 W30L120 PSD G3 | - |

| Order Code | Full Product Name | Initial chromaticity |
|--------------|---------------------------------------|----------------------|
| 911401514747 | RC100X LED37/840 W30L120 WIA | - |
| 72784799 | SM100C LED37S 840 W30L120 PSU G3 | SDCM<4 |
| 01519551 | SM100C LED37S 840 W30L120 PSD G3 | SDCM<4 |
| 01519951 | SM100C LED37S 865 W30L120 PSU UNV G3 | SDCM<4 |
| 52116299 | RC100B LED27S 840 W60L60 PSU G3 | SDCM<4 |
| 01508651 | RC100B LED27S 865 W60L60 PSU G3 | SDCM<4 |
| 01509551 | RC100B LED37S 840 W603L603 PSU UNV G3 | SDCM<4 |
| 01509651 | SM100C LED37S 840 W60L60 PSD G3 | SDCM<4 |
| 01509951 | SM100C LED27S 840 W60L60 PSU G3 | SDCM<4 |
| 72783099 | SM100C LED37S 840 W60L60 PSU G3 | SDCM<4 |

GreenPerform Troffer

| Order Code | Full Product Name | Initial chromaticity |
|--------------|------------------------------------|----------------------|
| 72782399 | RC100B LED37S 840 W60L60 PSU G3 | SDCM<4 |
| 01510851 | RC100B LED37S 840 W60L60 PSD OC G3 | SDCM<4 |
| 01510951 | RC100B LED37S 865 W60L60 PSU G3 | SDCM<4 |
| 51949799 | RC100B LED37S 840 W60L60 PSD G3 | SDCM<4 |
| 911401511847 | RC100B LED27S 840 W60L60 PSU G3 | - |
| 911401511947 | RC100B LED27S 865 W60L60 PSU G3 | - |
| 911401512047 | RC100B LED37S 840 W60L60 PSU G3 | - |
| 911401512147 | RC100B LED37S 865 W60L60 PSU G3 | - |
| 911401512847 | SM100C LED27S 840 W60L60 PSU G3 | - |

| Order Code | Full Product Name | Initial chromaticity |
|--------------|------------------------------------|----------------------|
| 911401512947 | SM100C LED37S 840 W60L60 PSU G3 | - |
| 911401513347 | RC100B LED37S 840 W60L60 PSD G3 | - |
| 911401513447 | RC100B LED37S 865 W60L60 PSD G3 | - |
| 911401513647 | RC100B LED37S 840 W60L60 PSD OC G3 | - |
| 911401513747 | RC100B LED37S 865 W60L60 PSD OC G3 | - |
| 911401514247 | SM100C LED37S 840 W60L60 PSD G3 | - |
| 911401514447 | RC100X LED37/840 W60L60 WIA | - |
| 911401514547 | RC100X LED37/865 W60L60 WIA | - |
| 01514351 | RC100B LED54S 840 W60L120 PSU G3 | SDCM<4 |

