



Energy saving without compromise.

GreenPerform Troffer

GreenPerform troffer improves the compact design of the last generation with performance improvement and more variants for different markets. Integrating with all available system: POE, InterAct office wireless, InterAct Office Pro, ActiLume controller, GreenPerform troffer offers additional energy saving and connected features.

Benefits

- Upgrade to smart office with more options
- Energy saving
- Slim housing
- Comfortable light
- Good light quality
- Office compliant
- Reliable performance

Features

- Compatible with all available Philips systems
- Efficacy up to 125lm/W
- Slim design with height less than 46mm
- Improved optical design without zebra effect
- CRI > 80, SDCM<4, Flicker free
- UGR 19 available
- Lifetime L70 50,000 hours

GreenPerform Troffer

Application

- Open Office
- Open Office
- Public Area
- Public Area
- Meeting Room
- Meeting Room
- Training Room
- Training Room

Specifications


Ceiling type	T-bar ceiling	Lumen maintenance at L70B50
Mains Voltage	220-240V / 50-60Hz	median useful life
Dimming	PSU: non-dimmable	50.000h
	PSD: Dimmable via Dali-broadcasting	Correlated color 840
	WIA: Wireless control, compatible with Interact	temperature - CCT 865
	SIA: Wireless control, compatible with Interact and with SNS210 sensor	UGR 19 is available through certain types
Control system input	Dali	Installation Recessed

Versions




GreenPerform Troffer RC100B 60x120

Dimensional drawing



GreenPerform Troffer

Dimensional drawing



GreenPerform Troffer

General Information	
Driver included	Yes
Light source replaceable	No
Number of gear units	1 unit
Service tag	Yes
Light Technical	
Color rendering index (CRI)	80
Operating and Electrical	
Protection class IEC	Safety class I
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	No
Mechanical and Housing	
Optical cover type	Variable linear-lens array in polycarbonate cover
Housing Color	White
Mech. impact protection code	IK03
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	-20 to +40 °C
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 600 °C, duration 30 s
Initial Performance (IEC Compliant)	
Initial chromaticity	SDCM<4
Luminous flux tolerance	+/-10%

Light Technical

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux
		Temperature (Nom)	(rated) (Nom)	
911401513051	RC100B LED37S 840 W30L120 PSD OC G3	4000 K	121 lm/W	3,700 lm
911401513251	RC100B LED37S 840 W30L120 PSD G3	4000 K	116 lm/W	3,700 lm
911401513351	RC100B LED37S 840 W30L120 PSU G3	4000 K	116 lm/W	3,700 lm
911401519451	SM100C LED37S 840 W30L120 PSU G3	4000 K	116 lm/W	3,700 lm
911401519551	SM100C LED37S 840 W30L120 PSD G3	4000 K	116 lm/W	3,700 lm
911401508451	RC100B LED27S 840 W60L60 PSU G3	4000 K	117 lm/W	2,700 lm
911401509651	SM100C LED37S 840 W60L60 PSD G3	4000 K	116 lm/W	3,700 lm
911401509951	SM100C LED27S 840 W60L60 PSU G3	4000 K	117 lm/W	2,700 lm
911401510151	SM100C LED37S 840 W60L60 PSU G3	4000 K	116 lm/W	3,700 lm
911401510751	RC100B LED37S 840 W60L60 PSU G3	4000 K	116 lm/W	3,700 lm
911401510951	RC100B LED37S 865 W60L60 PSU G3	6500 K	116 lm/W	3,700 lm
911401511151	RC100B LED37S 840 W60L60 PSD G3	4000 K	116 lm/W	3,700 lm
911401514351	RC100B LED54S 840 W60L120 PSU G3	4000 K	123 lm/W	5,400 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401513051	RC100B LED37S 840 W30L120 PSD OC G3	32 W
911401513251	RC100B LED37S 840 W30L120 PSD G3	32 W
911401513351	RC100B LED37S 840 W30L120 PSU G3	32 W
911401519451	SM100C LED37S 840 W30L120 PSU G3	32 W
911401519551	SM100C LED37S 840 W30L120 PSD G3	32 W
911401508451	RC100B LED27S 840 W60L60 PSU G3	23 W
911401509651	SM100C LED37S 840 W60L60 PSD G3	32 W

Order Code	Full Product Name	Power Consumption
911401509951	SM100C LED27S 840 W60L60 PSU G3	23 W
911401510151	SM100C LED37S 840 W60L60 PSU G3	32 W
911401510751	RC100B LED37S 840 W60L60 PSU G3	32 W
911401510951	RC100B LED37S 865 W60L60 PSU G3	32 W
911401511151	RC100B LED37S 840 W60L60 PSD G3	32 W
911401514351	RC100B LED54S 840 W60L120 PSU G3	44 W

Controls and Dimming

GreenPerform Troffer

Order Code	Full Product Name	Dimmable
911401513051	RC100B LED37S 840 W30L120 PSD OC G3	Yes
911401513251	RC100B LED37S 840 W30L120 PSD G3	Yes
911401513351	RC100B LED37S 840 W30L120 PSU G3	No
911401519451	SM100C LED37S 840 W30L120 PSU G3	No
911401519551	SM100C LED37S 840 W30L120 PSD G3	Yes
911401508451	RC100B LED27S 840 W60L60 PSU G3	No
911401509651	SM100C LED37S 840 W60L60 PSD G3	Yes

Order Code	Full Product Name	Dimmable
911401509951	SM100C LED27S 840 W60L60 PSU G3	No
911401510151	SM100C LED37S 840 W60L60 PSU G3	No
911401510751	RC100B LED37S 840 W60L60 PSU G3	No
911401510951	RC100B LED37S 865 W60L60 PSU G3	No
911401511151	RC100B LED37S 840 W60L60 PSD G3	Yes
911401514351	RC100B LED54S 840 W60L120 PSU G3	No

