

## GreenPerform Troffer

RC100B



## Energy saving without compromise

GreenPerform troffer improves the compact design of the last generation with performance improvement and more variants for different markets. Integrating with all available system: POE, InterAct office wireless, InterAct Office Pro, ActiLume controller, GreenPerform troffer offers additional energy saving and connected features.

### Benefits

- Upgrade to smart office with more options
- Energy saving
- Slim housing
- Comfortable light
- Good light quality
- Office compliant
- Reliable performance

### Applications

- Open Office
- Public Area

- Meeting Room
- Training Room

### Features

- Compatible with all available Philips systems
- Efficacy up to 125lm/W
- Slim design with height less than 46mm
- Improved optical design without zebra effect
- CRI > 80, SDCM<4, Flicker free
- UGR 19 available
- Lifetime L70 50,000 hours

## Versions



GreenPerform Troffer RC100B  
30x120



GreenPerform Troffer RC100B  
60x60




GreenPerform-Troffer-  
product-picture




GreenPerform Troffer RC100B  
60x120


## Dimensional drawing




RC100B W30L120




SM100C W60L60




RC100B LED37S 840 W60L60 PSD G3




SM100C LED37S 840 W60L60 PSU G3




RC100B W60L120




RC100 W60L60



SM100C LED37S 840 W30L120 PSD G3



RC100B LED37S 840 W30L120 PSD G3



SM100C W30L120

### General Information

|                          |        |
|--------------------------|--------|
| Light source replaceable | No     |
| Number of gear units     | 1 unit |
| Driver included          | Yes    |
| Service tag              | Yes    |

## Light Technical

|                             |                          |
|-----------------------------|--------------------------|
| Color rendering index (CRI) | 80                       |
| Number of light sources     | 2                        |
| Beam angle of light source  | 120 degree(s)            |
| Optic type                  | Opal prismatic reflector |

## Operating and Electrical

|                               |                |
|-------------------------------|----------------|
| Suitable for random switching | No             |
| Protection class IEC          | Safety class I |

## Mechanical and Housing

|                              |                         |
|------------------------------|-------------------------|
| Housing Color                | White                   |
| Ingress protection code      | IP20 [Finger-protected] |
| Mech. impact protection code | IK03 [0.3 J]            |

## Approval and Application

|                           |               |
|---------------------------|---------------|
| CE mark                   | Yes           |
| ENEC mark                 | -             |
| Ambient temperature range | -20 to +40 °C |

## Initial Performance (IEC Compliant)

|                         |        |
|-------------------------|--------|
| Luminous flux tolerance | +/-10% |
| Initial chromaticity    | SDCM<4 |

## Light Technical

| Order Code   | Full Product Name                    | Luminous Flux | Correlated Color Temperature (Nom) | Luminous Efficacy (rated) (Nom) |
|--------------|--------------------------------------|---------------|------------------------------------|---------------------------------|
| 911401512547 | RC100B LED37S 840 W30L120 PSU G3     | 4,000 lm      | 4000 K                             | 155.03875968992247 lm/W         |
| 911401513051 | RC100B LED37S 840 W30L120 PSD OC G3  | 3,700 lm      | 4000 K                             | 121 lm/W                        |
| 911401513147 | SM100C LED37S 840 W30L120 PSU G3     | 4,000 lm      | 4000 K                             | 155.03875968992247 lm/W         |
| 911401513247 | SM100C LED37S 840 W30L120 PSU G3     | 4,000 lm      | 4000 K                             | 155.03875968992247 lm/W         |
| 911401513251 | RC100B LED37S 840 W30L120 PSD G3     | 3,700 lm      | 4000 K                             | 116 lm/W                        |
| 911401513351 | RC100B LED37S 840 W30L120 PSU G3     | 3,700 lm      | 4000 K                             | 116 lm/W                        |
| 911401513751 | RC100B LED37S 865 W30L120 PSU UNV G3 | 3,700 lm      | 6500 K                             | 116 lm/W                        |
| 911401513847 | RC100B LED37S 840 W30L120 PSD OC G3  | 4,200 lm      | 4000 K                             | 166.66666666666666 lm/W         |
| 911401513947 | RC100B LED37S 840 W30L120 PSD G3     | 4,000 lm      | 4000 K                             | 158.73015873015873 lm/W         |
| 911401514347 | SM100C LED37S 840 W30L120 PSD G3     | 4,000 lm      | 4000 K                             | 158.73015873015873 lm/W         |
| 911401514747 | RC100X LED37/840 W30L120 WIA         | 4,000 lm      | 4000 K                             | 153.2567049808429 lm/W          |
| 911401519451 | SM100C LED37S 840 W30L120 PSU G3     | 3,700 lm      | 4000 K                             | 116 lm/W                        |
| 911401519551 | SM100C LED37S 840 W30L120 PSD G3     | 3,700 lm      | 4000 K                             | 116 lm/W                        |

| Order Code   | Full Product Name                     | Luminous Flux | Correlated Color Temperature (Nom) | Luminous Efficacy (rated) (Nom) |
|--------------|---------------------------------------|---------------|------------------------------------|---------------------------------|
| 911401519951 | SM100C LED37S 865 W30L120 PSU UNV G3  | 3,700 lm      | 6500 K                             | 116 lm/W                        |
| 911401508451 | RC100B LED27S 840 W60L60 PSU G3       | 2,700 lm      | 4000 K                             | 117 lm/W                        |
| 911401508651 | RC100B LED27S 865 W60L60 PSU G3       | 2,700 lm      | 6500 K                             | 117 lm/W                        |
| 911401509551 | RC100B LED37S 840 W603L603 PSU UNV G3 | 3,700 lm      | 4000 K                             | 116 lm/W                        |
| 911401509651 | SM100C LED37S 840 W60L60 PSD G3       | 3,700 lm      | 4000 K                             | 116 lm/W                        |
| 911401509951 | SM100C LED27S 840 W60L60 PSU G3       | 2,700 lm      | 4000 K                             | 117 lm/W                        |
| 911401510151 | SM100C LED37S 840 W60L60 PSU G3       | 3,700 lm      | 4000 K                             | 116 lm/W                        |
| 911401510751 | RC100B LED37S 840 W60L60 PSU G3       | 3,700 lm      | 4000 K                             | 116 lm/W                        |
| 911401510851 | RC100B LED37S 840 W60L60 PSD OC G3    | 3,700 lm      | 4000 K                             | 121 lm/W                        |
| 911401510951 | RC100B LED37S 865 W60L60 PSU G3       | 3,700 lm      | 6500 K                             | 116 lm/W                        |
| 911401511151 | RC100B LED37S 840 W60L60 PSD G3       | 3,700 lm      | 4000 K                             | 116 lm/W                        |
| 911401511847 | RC100B LED27S 840 W60L60 PSU G3       | 2,890 lm      | 4000 K                             | 154.54545454545456 lm/W         |
| 911401511947 | RC100B LED27S 865 W60L60 PSU G3       | 2,890 lm      | 6500 K                             | 154.55 lm/W                     |
| 911401512047 | RC100B LED37S 840 W60L60 PSU G3       | 4,000 lm      | 4000 K                             | 155.03875968992247 lm/W         |
| 911401512147 | RC100B LED37S 865 W60L60 PSU G3       | 4,000 lm      | 6500 K                             | 155.03875968992247 lm/W         |
| 911401512847 | SM100C LED27S 840 W60L60 PSU G3       | 2,890 lm      | 4000 K                             | 154.54545454545456 lm/W         |
| 911401512947 | SM100C LED37S 840 W60L60 PSU G3       | 4,000 lm      | 4000 K                             | 155.03875968992247 lm/W         |
| 911401513347 | RC100B LED37S 840 W60L60 PSD G3       | 4,000 lm      | 4000 K                             | 158.73015873015873 lm/W         |
| 911401513447 | RC100B LED37S 865 W60L60 PSD G3       | 4,000 lm      | 6500 K                             | 158.73015873015873 lm/W         |
| 911401513647 | RC100B LED37S 840 W60L60 PSD OC G3    | 4,200 lm      | 4000 K                             | 166.66666666666666 lm/W         |
| 911401513747 | RC100B LED37S 865 W60L60 PSD OC G3    | 4,200 lm      | 6500 K                             | 166.66666666666666 lm/W         |
| 911401514247 | SM100C LED37S 840 W60L60 PSD G3       | 4,000 lm      | 4000 K                             | 158.73015873015873 lm/W         |
| 911401514447 | RC100X LED37/840 W60L60 WIA           | 4,000 lm      | 4000 K                             | 153.2567049808429 lm/W          |
| 911401514547 | RC100X LED37/865 W60L60 WIA           | 4,000 lm      | 6500 K                             | 153.2567049808429 lm/W          |
| 911401514351 | RC100B LED54S 840 W60L120 PSU G3      | 5,400 lm      | 4000 K                             | 123 lm/W                        |

## Operating and Electrical

| Order Code   | Full Product Name                    | Input Voltage | Line Frequency | Power Consumption |
|--------------|--------------------------------------|---------------|----------------|-------------------|
| 911401512547 | RC100B LED37S 840 W30L120 PSU G3     | 220 to 240 V  | 50 or 60 Hz    | 25.8 W            |
| 911401513051 | RC100B LED37S 840 W30L120 PSD OC G3  | 220 to 240 V  | 50 to 60 Hz    | 32 W              |
| 911401513147 | SM100C LED37S 840 W30L120 PSU G3     | 220 to 240 V  | 50 or 60 Hz    | 25.8 W            |
| 911401513247 | SM100C LED37S 840 W30L120 PSU G3     | 220 to 240 V  | 50 or 60 Hz    | 25.8 W            |
| 911401513251 | RC100B LED37S 840 W30L120 PSD G3     | 220 to 240 V  | 50 to 60 Hz    | 32 W              |
| 911401513351 | RC100B LED37S 840 W30L120 PSU G3     | 220 to 240 V  | 50 to 60 Hz    | 32 W              |
| 911401513751 | RC100B LED37S 865 W30L120 PSU UNV G3 | 110 to 277 V  | 50 to 60 Hz    | 32 W              |
| 911401513847 | RC100B LED37S 840 W30L120 PSD OC G3  | 220 to 240 V  | 50 or 60 Hz    | 25.2 W            |
| 911401513947 | RC100B LED37S 840 W30L120 PSD G3     | 220 to 240 V  | 50 or 60 Hz    | 25.2 W            |
| 911401514347 | SM100C LED37S 840 W30L120 PSD G3     | 220 to 240 V  | 50 or 60 Hz    | 25.2 W            |
| 911401514747 | RC100X LED37/840 W30L120 WIA         | 220 to 240 V  | 50 or 60 Hz    | 26.1 W            |
| 911401519451 | SM100C LED37S 840 W30L120 PSU G3     | 220 to 240 V  | 50 to 60 Hz    | 32 W              |
| 911401519551 | SM100C LED37S 840 W30L120 PSD G3     | 220 to 240 V  | 50 to 60 Hz    | 32 W              |

| Order Code   | Full Product Name                    | Input Voltage | Line Frequency | Power Consumption |
|--------------|--------------------------------------|---------------|----------------|-------------------|
| 911401519951 | SM100C LED37S 865 W30L120 PSU UNV G3 | 110 to 277 V  | 50 to 60 Hz    | 32 W              |
| 911401508451 | RC100B LED27S 840 W60L60 PSU G3      | 220 to 240 V  | 50 to 60 Hz    | 23 W              |
| 911401508651 | RC100B LED27S 865 W60L60 PSU G3      | 220 to 240 V  | 50 to 60 Hz    | 23 W              |
| 911401509551 | RC100B LED37S 840 W60L60 PSU UNV G3  | 110 to 277 V  | 50 to 60 Hz    | 32 W              |
| 911401509651 | SM100C LED37S 840 W60L60 PSD G3      | 220 to 240 V  | 50 to 60 Hz    | 32 W              |
| 911401509951 | SM100C LED27S 840 W60L60 PSU G3      | 220 to 240 V  | 50 to 60 Hz    | 23 W              |
| 911401510151 | SM100C LED37S 840 W60L60 PSU G3      | 220 to 240 V  | 50 to 60 Hz    | 32 W              |
| 911401510751 | RC100B LED37S 840 W60L60 PSU G3      | 220 to 240 V  | 50 to 60 Hz    | 32 W              |
| 911401510851 | RC100B LED37S 840 W60L60 PSD OC G3   | 220 to 240 V  | 50 to 60 Hz    | 32 W              |
| 911401510951 | RC100B LED37S 865 W60L60 PSU G3      | 220 to 240 V  | 50 to 60 Hz    | 32 W              |
| 911401511151 | RC100B LED37S 840 W60L60 PSD G3      | 220 to 240 V  | 50 to 60 Hz    | 32 W              |
| 911401511847 | RC100B LED27S 840 W60L60 PSU G3      | 220 to 240 V  | 50 or 60 Hz    | 18.7 W            |
| 911401511947 | RC100B LED27S 865 W60L60 PSU G3      | 220 to 240 V  | 50 or 60 Hz    | 18.7 W            |
| 911401512047 | RC100B LED37S 840 W60L60 PSU G3      | 220 to 240 V  | 50 or 60 Hz    | 25.8 W            |
| 911401512147 | RC100B LED37S 865 W60L60 PSU G3      | 220 to 240 V  | 50 or 60 Hz    | 25.8 W            |
| 911401512847 | SM100C LED27S 840 W60L60 PSU G3      | 220 to 240 V  | 50 or 60 Hz    | 18.7 W            |
| 911401512947 | SM100C LED37S 840 W60L60 PSU G3      | 220 to 240 V  | 50 or 60 Hz    | 25.8 W            |
| 911401513347 | RC100B LED37S 840 W60L60 PSD G3      | 220 to 240 V  | 50 or 60 Hz    | 25.2 W            |
| 911401513447 | RC100B LED37S 865 W60L60 PSD G3      | 220 to 240 V  | 50 or 60 Hz    | 25.2 W            |
| 911401513647 | RC100B LED37S 840 W60L60 PSD OC G3   | 220 to 240 V  | 50 or 60 Hz    | 25.2 W            |
| 911401513747 | RC100B LED37S 865 W60L60 PSD OC G3   | 220 to 240 V  | 50 or 60 Hz    | 25.2 W            |
| 911401514247 | SM100C LED37S 840 W60L60 PSD G3      | 220 to 240 V  | 50 or 60 Hz    | 25.2 W            |
| 911401514447 | RC100X LED37/840 W60L60 WIA          | 220 to 240 V  | 50 or 60 Hz    | 26.1 W            |
| 911401514547 | RC100X LED37/865 W60L60 WIA          | 220 to 240 V  | 50 or 60 Hz    | 26.1 W            |
| 911401514351 | RC100B LED54S 840 W60L120 PSU G3     | 220 to 240 V  | 50 to 60 Hz    | 44 W              |

## Controls and Dimming

| Order Code   | Full Product Name                    | Dimmable     |
|--------------|--------------------------------------|--------------|
| 911401512547 | RC100B LED37S 840 W30L120 PSU G3     | -            |
| 911401513051 | RC100B LED37S 840 W30L120 PSD OC G3  | Yes          |
| 911401513147 | SM100C LED37S 840 W30L120 PSU G3     | -            |
| 911401513247 | SM100C LED37S 840 W30L120 PSU G3     | -            |
| 911401513251 | RC100B LED37S 840 W30L120 PSD G3     | Yes          |
| 911401513351 | RC100B LED37S 840 W30L120 PSU G3     | No           |
| 911401513751 | RC100B LED37S 865 W30L120 PSU UNV G3 | No           |
| 911401513847 | RC100B LED37S 840 W30L120 PSD OC G3  | DALI         |
| 911401513947 | RC100B LED37S 840 W30L120 PSD G3     | DALI         |
| 911401514347 | SM100C LED37S 840 W30L120 PSD G3     | DALI         |
| 911401514747 | RC100X LED37/840 W30L120 WIA         | Wireless Dim |
| 911401519451 | SM100C LED37S 840 W30L120 PSU G3     | No           |
| 911401519551 | SM100C LED37S 840 W30L120 PSD G3     | Yes          |

| Order Code   | Full Product Name                    | Dimmable     |
|--------------|--------------------------------------|--------------|
| 911401519951 | SM100C LED37S 865 W30L120 PSU UNV G3 | No           |
| 911401508451 | RC100B LED27S 840 W60L60 PSU G3      | No           |
| 911401508651 | RC100B LED27S 865 W60L60 PSU G3      | No           |
| 911401509551 | RC100B LED37S 840 W60L603 PSU UNV G3 | No           |
| 911401509651 | SM100C LED37S 840 W60L60 PSD G3      | Yes          |
| 911401509951 | SM100C LED27S 840 W60L60 PSU G3      | No           |
| 911401510151 | SM100C LED37S 840 W60L60 PSU G3      | No           |
| 911401510751 | RC100B LED37S 840 W60L60 PSU G3      | No           |
| 911401510851 | RC100B LED37S 840 W60L60 PSD OC G3   | Yes          |
| 911401510951 | RC100B LED37S 865 W60L60 PSU G3      | No           |
| 911401511151 | RC100B LED37S 840 W60L60 PSD G3      | Yes          |
| 911401511847 | RC100B LED27S 840 W60L60 PSU G3      | -            |
| 911401511947 | RC100B LED27S 865 W60L60 PSU G3      | -            |
| 911401512047 | RC100B LED37S 840 W60L60 PSU G3      | -            |
| 911401512147 | RC100B LED37S 865 W60L60 PSU G3      | -            |
| 911401512847 | SM100C LED27S 840 W60L60 PSU G3      | -            |
| 911401512947 | SM100C LED37S 840 W60L60 PSU G3      | -            |
| 911401513347 | RC100B LED37S 840 W60L60 PSD G3      | DALI         |
| 911401513447 | RC100B LED37S 865 W60L60 PSD G3      | DALI         |
| 911401513647 | RC100B LED37S 840 W60L60 PSD OC G3   | DALI         |
| 911401513747 | RC100B LED37S 865 W60L60 PSD OC G3   | DALI         |
| 911401514247 | SM100C LED37S 840 W60L60 PSD G3      | DALI         |
| 911401514447 | RC100X LED37/840 W60L60 WIA          | Wireless Dim |
| 911401514547 | RC100X LED37/865 W60L60 WIA          | Wireless Dim |
| 911401514351 | RC100B LED54S 840 W60L120 PSU G3     | No           |

## Mechanical and Housing

| Order Code   | Full Product Name                    | Optical cover type                                |
|--------------|--------------------------------------|---------------------------------------------------|
| 911401512547 | RC100B LED37S 840 W30L120 PSU G3     | Polycarbonate bowl/cover                          |
| 911401513051 | RC100B LED37S 840 W30L120 PSD OC G3  | Variable linear-lens array in polycarbonate cover |
| 911401513147 | SM100C LED37S 840 W30L120 PSU G3     | Polycarbonate bowl/cover                          |
| 911401513247 | SM100C LED37S 840 W30L120 PSU G3     | Polycarbonate bowl/cover                          |
| 911401513251 | RC100B LED37S 840 W30L120 PSD G3     | Variable linear-lens array in polycarbonate cover |
| 911401513351 | RC100B LED37S 840 W30L120 PSU G3     | Variable linear-lens array in polycarbonate cover |
| 911401513751 | RC100B LED37S 865 W30L120 PSU UNV G3 | Variable linear-lens array in polycarbonate cover |
| 911401513847 | RC100B LED37S 840 W30L120 PSD OC G3  | Polycarbonate bowl/cover                          |
| 911401513947 | RC100B LED37S 840 W30L120 PSD G3     | Polycarbonate bowl/cover                          |
| 911401514347 | SM100C LED37S 840 W30L120 PSD G3     | Polycarbonate bowl/cover                          |
| 911401514747 | RC100X LED37/840 W30L120 WIA         | Polycarbonate bowl/cover                          |
| 911401519451 | SM100C LED37S 840 W30L120 PSU G3     | Variable linear-lens array in polycarbonate cover |
| 911401519551 | SM100C LED37S 840 W30L120 PSD G3     | Variable linear-lens array in polycarbonate cover |

| Order Code   | Full Product Name                    | Optical cover type                                |
|--------------|--------------------------------------|---------------------------------------------------|
| 911401519951 | SM100C LED37S 865 W30L120 PSU UNV G3 | Variable linear-lens array in polycarbonate cover |
| 911401508451 | RC100B LED27S 840 W60L60 PSU G3      | Variable linear-lens array in polycarbonate cover |
| 911401508651 | RC100B LED27S 865 W60L60 PSU G3      | Variable linear-lens array in polycarbonate cover |
| 911401509551 | RC100B LED37S 840 W60L60 PSU UNV G3  | Variable linear-lens array in polycarbonate cover |
| 911401509651 | SM100C LED37S 840 W60L60 PSD G3      | Variable linear-lens array in polycarbonate cover |
| 911401509951 | SM100C LED27S 840 W60L60 PSU G3      | Variable linear-lens array in polycarbonate cover |
| 911401510151 | SM100C LED37S 840 W60L60 PSU G3      | Variable linear-lens array in polycarbonate cover |
| 911401510751 | RC100B LED37S 840 W60L60 PSU G3      | Variable linear-lens array in polycarbonate cover |
| 911401510851 | RC100B LED37S 840 W60L60 PSD OC G3   | Variable linear-lens array in polycarbonate cover |
| 911401510951 | RC100B LED37S 865 W60L60 PSU G3      | Variable linear-lens array in polycarbonate cover |
| 911401511151 | RC100B LED37S 840 W60L60 PSD G3      | Variable linear-lens array in polycarbonate cover |
| 911401511847 | RC100B LED27S 840 W60L60 PSU G3      | Polycarbonate bowl/cover                          |
| 911401511947 | RC100B LED27S 865 W60L60 PSU G3      | Polycarbonate bowl/cover                          |
| 911401512047 | RC100B LED37S 840 W60L60 PSU G3      | Polycarbonate bowl/cover                          |
| 911401512147 | RC100B LED37S 865 W60L60 PSU G3      | Polycarbonate bowl/cover                          |
| 911401512847 | SM100C LED27S 840 W60L60 PSU G3      | Polycarbonate bowl/cover                          |
| 911401512947 | SM100C LED37S 840 W60L60 PSU G3      | Polycarbonate bowl/cover                          |
| 911401513347 | RC100B LED37S 840 W60L60 PSD G3      | Polycarbonate bowl/cover                          |
| 911401513447 | RC100B LED37S 865 W60L60 PSD G3      | Polycarbonate bowl/cover                          |
| 911401513647 | RC100B LED37S 840 W60L60 PSD OC G3   | Polycarbonate bowl/cover                          |
| 911401513747 | RC100B LED37S 865 W60L60 PSD OC G3   | Polycarbonate bowl/cover                          |
| 911401514247 | SM100C LED37S 840 W60L60 PSD G3      | Polycarbonate bowl/cover                          |
| 911401514447 | RC100X LED37/840 W60L60 WIA          | Polycarbonate bowl/cover                          |
| 911401514547 | RC100X LED37/865 W60L60 WIA          | Polycarbonate bowl/cover                          |
| 911401514351 | RC100B LED54S 840 W60L120 PSU G3     | Variable linear-lens array in polycarbonate cover |

## Approval and Application

| Order Code   | Full Product Name                    | Glow-wire test                    | Flammability mark                           |
|--------------|--------------------------------------|-----------------------------------|---------------------------------------------|
| 911401512547 | RC100B LED37S 840 W30L120 PSU G3     | Temperature 650 °C, duration 30 s | -                                           |
| 911401513051 | RC100B LED37S 840 W30L120 PSD OC G3  | Temperature 600 °C, duration 30 s | For mounting on normally flammable surfaces |
| 911401513147 | SM100C LED37S 840 W30L120 PSU G3     | Temperature 650 °C, duration 30 s | -                                           |
| 911401513247 | SM100C LED37S 840 W30L120 PSU G3     | Temperature 650 °C, duration 30 s | -                                           |
| 911401513251 | RC100B LED37S 840 W30L120 PSD G3     | Temperature 600 °C, duration 30 s | For mounting on normally flammable surfaces |
| 911401513351 | RC100B LED37S 840 W30L120 PSU G3     | Temperature 600 °C, duration 30 s | For mounting on normally flammable surfaces |
| 911401513751 | RC100B LED37S 865 W30L120 PSU UNV G3 | Temperature 600 °C, duration 30 s | For mounting on normally flammable surfaces |
| 911401513847 | RC100B LED37S 840 W30L120 PSD OC G3  | Temperature 650 °C, duration 30 s | -                                           |
| 911401513947 | RC100B LED37S 840 W30L120 PSD G3     | Temperature 650 °C, duration 30 s | -                                           |
| 911401514347 | SM100C LED37S 840 W30L120 PSD G3     | Temperature 650 °C, duration 30 s | -                                           |
| 911401514747 | RC100X LED37/840 W30L120 WIA         | Temperature 650 °C, duration 30 s | -                                           |
| 911401519451 | SM100C LED37S 840 W30L120 PSU G3     | Temperature 600 °C, duration 30 s | For mounting on normally flammable surfaces |
| 911401519551 | SM100C LED37S 840 W30L120 PSD G3     | Temperature 600 °C, duration 30 s | For mounting on normally flammable surfaces |



| Order Code   | Full Product Name                    | Glow-wire test                    | Flammability mark                           |
|--------------|--------------------------------------|-----------------------------------|---------------------------------------------|
| 911401519951 | SM100C LED37S 865 W30L120 PSU UNV G3 | Temperature 600 °C, duration 30 s | For mounting on normally flammable surfaces |
| 911401508451 | RC100B LED27S 840 W60L60 PSU G3      | Temperature 600 °C, duration 30 s | For mounting on normally flammable surfaces |
| 911401508651 | RC100B LED27S 865 W60L60 PSU G3      | Temperature 600 °C, duration 30 s | For mounting on normally flammable surfaces |
| 911401509551 | RC100B LED37S 840 W60L60 PSU UNV G3  | Temperature 600 °C, duration 30 s | For mounting on normally flammable surfaces |
| 911401509651 | SM100C LED37S 840 W60L60 PSD G3      | Temperature 600 °C, duration 30 s | For mounting on normally flammable surfaces |
| 911401509951 | SM100C LED27S 840 W60L60 PSU G3      | Temperature 600 °C, duration 30 s | For mounting on normally flammable surfaces |
| 911401510151 | SM100C LED37S 840 W60L60 PSU G3      | Temperature 600 °C, duration 30 s | For mounting on normally flammable surfaces |
| 911401510751 | RC100B LED37S 840 W60L60 PSU G3      | Temperature 600 °C, duration 30 s | For mounting on normally flammable surfaces |
| 911401510851 | RC100B LED37S 840 W60L60 PSD OC G3   | Temperature 600 °C, duration 30 s | For mounting on normally flammable surfaces |
| 911401510951 | RC100B LED37S 865 W60L60 PSU G3      | Temperature 600 °C, duration 30 s | For mounting on normally flammable surfaces |
| 911401511151 | RC100B LED37S 840 W60L60 PSD G3      | Temperature 600 °C, duration 30 s | For mounting on normally flammable surfaces |
| 911401511847 | RC100B LED27S 840 W60L60 PSU G3      | Temperature 650 °C, duration 30 s | -                                           |
| 911401511947 | RC100B LED27S 865 W60L60 PSU G3      | Temperature 650 °C, duration 30 s | -                                           |
| 911401512047 | RC100B LED37S 840 W60L60 PSU G3      | Temperature 650 °C, duration 30 s | -                                           |
| 911401512147 | RC100B LED37S 865 W60L60 PSU G3      | Temperature 650 °C, duration 30 s | -                                           |
| 911401512847 | SM100C LED27S 840 W60L60 PSU G3      | Temperature 650 °C, duration 30 s | -                                           |
| 911401512947 | SM100C LED37S 840 W60L60 PSU G3      | Temperature 650 °C, duration 30 s | -                                           |
| 911401513347 | RC100B LED37S 840 W60L60 PSD G3      | Temperature 650 °C, duration 30 s | -                                           |
| 911401513447 | RC100B LED37S 865 W60L60 PSD G3      | Temperature 650 °C, duration 30 s | -                                           |
| 911401513647 | RC100B LED37S 840 W60L60 PSD OC G3   | Temperature 650 °C, duration 30 s | -                                           |
| 911401513747 | RC100B LED37S 865 W60L60 PSD OC G3   | Temperature 650 °C, duration 30 s | -                                           |
| 911401514247 | SM100C LED37S 840 W60L60 PSD G3      | Temperature 650 °C, duration 30 s | -                                           |
| 911401514447 | RC100X LED37/840 W60L60 WIA          | Temperature 650 °C, duration 30 s | -                                           |
| 911401514547 | RC100X LED37/865 W60L60 WIA          | Temperature 650 °C, duration 30 s | -                                           |
| 911401514351 | RC100B LED54S 840 W60L120 PSU G3     | Temperature 600 °C, duration 30 s | For mounting on normally flammable surfaces |