



Energy saving without compromise

GreenPerform Troffer

GreenPerform troffer improves the compact design of the last generation with performance improvement and more variants for different markets. Integrating with all available system: POE, InterAct office wireless, InterAct Office Pro, ActiLume controller, GreenPerform troffer offers additional energy saving and connected features.

Benefits

- Upgrade to smart office with more options
- Energy saving
- Slim housing
- Comfortable light
- Good light quality
- Office compliant
- Reliable performance

Features

- Compatible with all available Philips systems
- Efficacy up to 125lm/W
- Slim design with height less than 46mm
- Improved optical design without zebra effect
- CRI > 80, SDCM<4, Flicker free
- UGR 19 available
- Lifetime L70 50,000 hours

Application

- Open Office
- Public Area
- Meeting Room
- Training Room


GreenPerform Troffer

Specifications

Ceiling type	T-bar ceiling
Mains Voltage	220-240V / 50-60Hz
Dimming	PSU: non-dimmable PSD: Dimmable via Dali-broadcasting WIA: Wireless control, compatible with Interact SIA: Wireless control, compatible with Interact and with SNS210 sensor
Control system input	Dali

Lumen maintenance at median useful life 50.000h	L70B50
Correlated color temperature - CCT	840 865
UGR	19 is available through certain types
Installation	Recessed





Versions



GreenPerform Troffer RC100B 30x120


GreenPerform Troffer RC100B 60x120

Dimensional drawing



GreenPerform Troffer

Dimensional drawing



General Information	
Driver included	Yes
Number of gear units	1 unit
Light Technical	
Color rendering index (CRI)	80
Operating and Electrical	
Protection class IEC	Safety class I
Suitable for random switching	No
Mechanical and Housing	
Housing Color	White
Mech. impact protection code	IK03
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	-20 to +40 °C
CE mark	Yes
ENEC mark	-
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

General Information

Order Code	Full Product Name	Light source replaceable	Service tag
911401512547	RC100B LED37S 840 W30L120 PSU G3	-	-
911401513051	RC100B LED37S 840 W30L120 PSD OC G3	No	Yes
911401513147	SM100C LED37S 840 W30L120 PSU G3	-	-
911401513247	SM100C LED37S 840 W30L120 PSU G3	-	-
911401513251	RC100B LED37S 840 W30L120 PSD G3	No	Yes
911401513351	RC100B LED37S 840 W30L120 PSU G3	No	Yes
911401513751	RC100B LED37S 865 W30L120 PSU UNV G3	No	Yes
911401513847	RC100B LED37S 840 W30L120 PSD OC G3	-	-
911401513947	RC100B LED37S 840 W30L120 PSD G3	-	-
911401514347	SM100C LED37S 840 W30L120 PSD G3	-	-
911401514747	RC100X LED37/840 W30L120 WIA	-	-
911401519451	SM100C LED37S 840 W30L120 PSU G3	No	Yes
911401519551	SM100C LED37S 840 W30L120 PSD G3	No	Yes
911401519951	SM100C LED37S 865 W30L120 PSU UNV G3	No	Yes
911401508451	RC100B LED27S 840 W60L60 PSU G3	No	Yes
911401508651	RC100B LED27S 865 W60L60 PSU G3	No	Yes
911401509551	RC100B LED37S 840 W60L60 PSU UNV G3	No	Yes
911401509651	SM100C LED37S 840 W60L60 PSD G3	No	Yes
911401509951	SM100C LED27S 840 W60L60 PSU G3	No	Yes
911401510151	SM100C LED37S 840 W60L60 PSU G3	No	Yes
911401510751	RC100B LED37S 840 W60L60 PSU G3	No	Yes
911401510851	RC100B LED37S 840 W60L60 PSD OC G3	No	Yes
911401510951	RC100B LED37S 865 W60L60 PSU G3	No	Yes
911401511151	RC100B LED37S 840 W60L60 PSD G3	No	Yes
911401511847	RC100B LED27S 840 W60L60 PSU G3	-	-
911401511947	RC100B LED27S 865 W60L60 PSU G3	-	-
911401512047	RC100B LED37S 840 W60L60 PSU G3	-	-
911401512147	RC100B LED37S 865 W60L60 PSU G3	-	-
911401512847	SM100C LED27S 840 W60L60 PSU G3	-	-
911401512947	SM100C LED37S 840 W60L60 PSU G3	-	-
911401513347	RC100B LED37S 840 W60L60 PSD G3	-	-
911401513447	RC100B LED37S 865 W60L60 PSD G3	-	-
911401513647	RC100B LED37S 840 W60L60 PSD OC G3	-	-
911401513747	RC100B LED37S 865 W60L60 PSD OC G3	-	-
911401514247	SM100C LED37S 840 W60L60 PSD G3	-	-
911401514447	RC100X LED37/840 W60L60 WIA	-	-
911401514547	RC100X LED37/865 W60L60 WIA	-	-
911401514351	RC100B LED54S 840 W60L120 PSU G3	No	Yes

Light Technical (1/2)

Order Code	Full Product Name	Beam angle of light source	Correlated Color			Order Code	Full Product Name	Beam angle of light source	Correlated Color		
			Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux				Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401512547	RC100B LED37S 840 W30L120 PSU G3	120 degree(s)	4000 K	155.03875968992247 lm/W	4,000 lm	911401513051	RC100B LED37S 840 W30L120 PSD OC G3	-	4000 K	121 lm/W	3,700 lm

GreenPerform Troffer

Order Code	Full Product Name	Beam angle of light source	Correlated Color		
			Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401513147	SM100C LED37S 840 W30L120 PSU G3	120 degree(s)	4000 K	155.03875968992247 lm/W	4,000 lm
911401513247	SM100C LED37S 840 W30L120 PSU G3	120 degree(s)	4000 K	155.03875968992247 lm/W	4,000 lm
911401513251	RC100B LED37S 840 W30L120 PSD G3	-	4000 K	116 lm/W	3,700 lm
911401513351	RC100B LED37S 840 W30L120 PSU G3	-	4000 K	116 lm/W	3,700 lm
911401513751	RC100B LED37S 865 W30L120 PSU UNV G3	-	6500 K	116 lm/W	3,700 lm
911401513847	RC100B LED37S 840 W30L120 PSD OC G3	120 degree(s)	4000 K	166.66666666666666 lm/W	4,200 lm
911401513947	RC100B LED37S 840 W30L120 PSD G3	120 degree(s)	4000 K	158.73015873015873 lm/W	4,000 lm
911401514347	SM100C LED37S 840 W30L120 PSD G3	120 degree(s)	4000 K	158.73015873015873 lm/W	4,000 lm
911401514747	RC100X LED37/840 W30L120 WIA	120 degree(s)	4000 K	153.2567049808429 lm/W	4,000 lm
911401519451	SM100C LED37S 840	-	4000 K	116 lm/W	3,700 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color		
			Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
	W30L120 PSU G3				
911401519551	SM100C LED37S 840 W30L120 PSD G3	-	4000 K	116 lm/W	3,700 lm
911401519951	SM100C LED37S 865 W30L120 PSU UNV G3	-	6500 K	116 lm/W	3,700 lm
911401508451	RC100B LED27S 840 W60L60 PSU G3	-	4000 K	117 lm/W	2,700 lm
911401508651	RC100B LED27S 865 W60L60 PSU G3	-	6500 K	117 lm/W	2,700 lm
911401509551	RC100B LED37S 840 W60L60 PSU UNV G3	-	4000 K	116 lm/W	3,700 lm
911401509651	SM100C LED37S 840 W60L60 PSD G3	-	4000 K	116 lm/W	3,700 lm
911401509951	SM100C LED27S 840 W60L60 PSU G3	-	4000 K	117 lm/W	2,700 lm
911401510151	SM100C LED37S 840 W60L60 PSU G3	-	4000 K	116 lm/W	3,700 lm
911401510751	RC100B LED37S 840 W60L60 PSU G3	-	4000 K	116 lm/W	3,700 lm

GreenPerform Troffer

Order Code	Full Product Name	Beam angle of light source	Correlated Color		
			Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401510851	RC100B LED37S 840 W60L60 PSD OC G3	-	4000 K	121 lm/W	3,700 lm
911401510951	RC100B LED37S 865 W60L60 PSU G3	-	6500 K	116 lm/W	3,700 lm
911401511151	RC100B LED37S 840 W60L60 PSD G3	-	4000 K	116 lm/W	3,700 lm
911401511847	RC100B LED27S 840 W60L60 PSU G3	120 degree(s)	4000 K	154.54545454545456 lm/W	2,890 lm
911401511947	RC100B LED27S 865 W60L60 PSU G3	120 degree(s)	6500 K	154.55 lm/W	2,890 lm
911401512047	RC100B LED37S 840 W60L60 PSU G3	120 degree(s)	4000 K	155.03875968992247 lm/W	4,000 lm
911401512147	RC100B LED37S 865 W60L60 PSU G3	120 degree(s)	6500 K	155.03875968992247 lm/W	4,000 lm
911401512847	SM100C LED27S 840 W60L60 PSU G3	120 degree(s)	4000 K	154.54545454545456 lm/W	2,890 lm
911401512947	SM100C LED37S 840 W60L60 PSU G3	120 degree(s)	4000 K	155.03875968992247 lm/W	4,000 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color		
			Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401513347	RC100B LED37S 840 W60L60 PSD G3	120 degree(s)	4000 K	158.73015873015873 lm/W	4,000 lm
911401513447	RC100B LED37S 865 W60L60 PSD G3	120 degree(s)	6500 K	158.73015873015873 lm/W	4,000 lm
911401513647	RC100B LED37S 840 W60L60 PSD OC G3	120 degree(s)	4000 K	166.66666666666666 lm/W	4,200 lm
911401513747	RC100B LED37S 865 W60L60 PSD OC G3	120 degree(s)	6500 K	166.66666666666666 lm/W	4,200 lm
911401514247	SM100C LED37S 840 W60L60 PSD G3	120 degree(s)	4000 K	158.73015873015873 lm/W	4,000 lm
911401514447	RC100X LED37/840 W60L60 WIA	120 degree(s)	4000 K	153.2567049808429 lm/W	4,000 lm
911401514547	RC100X LED37/865 W60L60 WIA	120 degree(s)	6500 K	153.2567049808429 lm/W	4,000 lm
911401514351	RC100B LED54S 840 W60L120 PSU G3	-	4000 K	123 lm/W	5,400 lm

Light Technical (2/2)

GreenPerform Troffer

Order Code	Full Product Name	Number of light sources	Optic type
911401512547	RC100B LED37S 840 W30L120 PSU G3	2	Opal prismatic reflector
911401513051	RC100B LED37S 840 W30L120 PSD OC G3	-	-
911401513147	SM100C LED37S 840 W30L120 PSU G3	2	Opal prismatic reflector
911401513247	SM100C LED37S 840 W30L120 PSU G3	2	Opal prismatic reflector
911401513251	RC100B LED37S 840 W30L120 PSD G3	-	-
911401513351	RC100B LED37S 840 W30L120 PSU G3	-	-
911401513751	RC100B LED37S 865 W30L120 PSU UNV G3	-	-
911401513847	RC100B LED37S 840 W30L120 PSD OC G3	2	Opal prismatic reflector
911401513947	RC100B LED37S 840 W30L120 PSD G3	2	Opal prismatic reflector
911401514347	SM100C LED37S 840 W30L120 PSD G3	2	Opal prismatic reflector
911401514747	RC100X LED37/840 W30L120 WIA	2	Opal prismatic reflector
911401519451	SM100C LED37S 840 W30L120 PSU G3	-	-
911401519551	SM100C LED37S 840 W30L120 PSD G3	-	-
911401519951	SM100C LED37S 865 W30L120 PSU UNV G3	-	-
911401508451	RC100B LED27S 840 W60L60 PSU G3	-	-
911401508651	RC100B LED27S 865 W60L60 PSU G3	-	-
911401509551	RC100B LED37S 840 W60L60 PSU UNV G3	-	-
911401509651	SM100C LED37S 840 W60L60 PSD G3	-	-
911401509951	SM100C LED27S 840 W60L60 PSU G3	-	-
911401510151	SM100C LED37S 840 W60L60 PSU G3	-	-

Order Code	Full Product Name	Number of light sources	Optic type
911401510751	RC100B LED37S 840 W60L60 PSU G3	-	-
911401510851	RC100B LED37S 840 W60L60 PSD OC G3	-	-
911401510951	RC100B LED37S 865 W60L60 PSU G3	-	-
911401511151	RC100B LED37S 840 W60L60 PSD G3	-	-
911401511847	RC100B LED27S 840 W60L60 PSU G3	2	Opal prismatic reflector
911401511947	RC100B LED27S 865 W60L60 PSU G3	2	Opal prismatic reflector
911401512047	RC100B LED37S 840 W60L60 PSU G3	2	Opal prismatic reflector
911401512147	RC100B LED37S 865 W60L60 PSU G3	2	Opal prismatic reflector
911401512847	SM100C LED27S 840 W60L60 PSU G3	2	Opal prismatic reflector
911401512947	SM100C LED37S 840 W60L60 PSU G3	2	Opal prismatic reflector
911401513347	RC100B LED37S 840 W60L60 PSD G3	2	Opal prismatic reflector
911401513447	RC100B LED37S 865 W60L60 PSD G3	2	Opal prismatic reflector
911401513647	RC100B LED37S 840 W60L60 PSD OC G3	2	Opal prismatic reflector
911401513747	RC100B LED37S 865 W60L60 PSD OC G3	2	Opal prismatic reflector
911401514247	SM100C LED37S 840 W60L60 PSD G3	2	Opal prismatic reflector
911401514447	RC100X LED37/840 W60L60 WIA	2	Opal prismatic reflector
911401514547	RC100X LED37/865 W60L60 WIA	2	Opal prismatic reflector
911401514351	RC100B LED54S 840 W60L120 PSU G3	-	-

Operating and Electrical

Order Code	Full Product Name	Power		
		Input Voltage	Line Frequency	Consumption
911401512547	RC100B LED37S 840 W30L120 PSU G3	220 to 240 V	50 or 60 Hz	25.8 W
911401513051	RC100B LED37S 840 W30L120 PSD OC G3	220 to 240 V	50 to 60 Hz	32 W
911401513147	SM100C LED37S 840 W30L120 PSU G3	220 to 240 V	50 or 60 Hz	25.8 W
911401513247	SM100C LED37S 840 W30L120 PSU G3	220 to 240 V	50 or 60 Hz	25.8 W
911401513251	RC100B LED37S 840 W30L120 PSD G3	220 to 240 V	50 to 60 Hz	32 W
911401513351	RC100B LED37S 840 W30L120 PSU G3	220 to 240 V	50 to 60 Hz	32 W

Order Code	Full Product Name	Power		
		Input Voltage	Line Frequency	Consumption
911401513751	RC100B LED37S 865 W30L120 PSU UNV G3	110 to 277 V	50 to 60 Hz	32 W
911401513847	RC100B LED37S 840 W30L120 PSD OC G3	220 to 240 V	50 or 60 Hz	25.2 W
911401513947	RC100B LED37S 840 W30L120 PSD G3	220 to 240 V	50 or 60 Hz	25.2 W
911401514347	SM100C LED37S 840 W30L120 PSD G3	220 to 240 V	50 or 60 Hz	25.2 W
911401514747	RC100X LED37/840 W30L120 WIA	220 to 240 V	50 or 60 Hz	26.1 W

GreenPerform Troffer

Order Code	Full Product Name	Input Voltage	Line Frequency	Power	
				Consumption	
911401519451	SM100C LED37S 840 W30L120 PSU G3	220 to 240 V	50 to 60 Hz	32 W	
911401519551	SM100C LED37S 840 W30L120 PSD G3	220 to 240 V	50 to 60 Hz	32 W	
911401519951	SM100C LED37S 865 W30L120 PSU UNV G3	110 to 277 V	50 to 60 Hz	32 W	
911401508451	RC100B LED27S 840 W60L60 PSU G3	220 to 240 V	50 to 60 Hz	23 W	
911401508651	RC100B LED27S 865 W60L60 PSU G3	220 to 240 V	50 to 60 Hz	23 W	
911401509551	RC100B LED37S 840 W603L603 PSU UNV G3	110 to 277 V	50 to 60 Hz	32 W	
911401509651	SM100C LED37S 840 W60L60 PSD G3	220 to 240 V	50 to 60 Hz	32 W	
911401509951	SM100C LED27S 840 W60L60 PSU G3	220 to 240 V	50 to 60 Hz	23 W	
911401510151	SM100C LED37S 840 W60L60 PSU G3	220 to 240 V	50 to 60 Hz	32 W	
911401510751	RC100B LED37S 840 W60L60 PSU G3	220 to 240 V	50 to 60 Hz	32 W	
911401510851	RC100B LED37S 840 W60L60 PSD OC G3	220 to 240 V	50 to 60 Hz	32 W	
911401510951	RC100B LED37S 865 W60L60 PSU G3	220 to 240 V	50 to 60 Hz	32 W	
911401511151	RC100B LED37S 840 W60L60 PSD G3	220 to 240 V	50 to 60 Hz	32 W	

Order Code	Full Product Name	Input Voltage	Line Frequency	Power	
				Consumption	
911401511847	RC100B LED27S 840 W60L60 PSU G3	220 to 240 V	50 or 60 Hz	18.7 W	
911401511947	RC100B LED27S 865 W60L60 PSU G3	220 to 240 V	50 or 60 Hz	18.7 W	
911401512047	RC100B LED37S 840 W60L60 PSU G3	220 to 240 V	50 or 60 Hz	25.8 W	
911401512147	RC100B LED37S 865 W60L60 PSU G3	220 to 240 V	50 or 60 Hz	25.8 W	
911401512847	SM100C LED27S 840 W60L60 PSU G3	220 to 240 V	50 or 60 Hz	18.7 W	
911401512947	SM100C LED37S 840 W60L60 PSU G3	220 to 240 V	50 or 60 Hz	25.8 W	
911401513347	RC100B LED37S 840 W60L60 PSD G3	220 to 240 V	50 or 60 Hz	25.2 W	
911401513447	RC100B LED37S 865 W60L60 PSD G3	220 to 240 V	50 or 60 Hz	25.2 W	
911401513647	RC100B LED37S 840 W60L60 PSD OC G3	220 to 240 V	50 or 60 Hz	25.2 W	
911401513747	RC100B LED37S 865 W60L60 PSD OC G3	220 to 240 V	50 or 60 Hz	25.2 W	
911401514247	SM100C LED37S 840 W60L60 PSD G3	220 to 240 V	50 or 60 Hz	25.2 W	
911401514447	RC100X LED37/840 W60L60 WIA	220 to 240 V	50 or 60 Hz	26.1 W	
911401514547	RC100X LED37/865 W60L60 WIA	220 to 240 V	50 or 60 Hz	26.1 W	
911401514351	RC100B LED54S 840 W60L120 PSU G3	220 to 240 V	50 to 60 Hz	44 W	

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401512547	RC100B LED37S 840 W30L120 PSU G3	-
911401513051	RC100B LED37S 840 W30L120 PSD OC G3	Yes
911401513147	SM100C LED37S 840 W30L120 PSU G3	-
911401513247	SM100C LED37S 840 W30L120 PSU G3	-
911401513251	RC100B LED37S 840 W30L120 PSD G3	Yes
911401513351	RC100B LED37S 840 W30L120 PSU G3	No
911401513751	RC100B LED37S 865 W30L120 PSU UNV G3	No
911401513847	RC100B LED37S 840 W30L120 PSD OC G3	DALI
911401513947	RC100B LED37S 840 W30L120 PSD G3	DALI
911401514347	SM100C LED37S 840 W30L120 PSD G3	DALI
911401514747	RC100X LED37/840 W30L120 WIA	Wireless Dim
911401519451	SM100C LED37S 840 W30L120 PSU G3	No
911401519551	SM100C LED37S 840 W30L120 PSD G3	Yes
911401519951	SM100C LED37S 865 W30L120 PSU UNV G3	No
911401508451	RC100B LED27S 840 W60L60 PSU G3	No
911401508651	RC100B LED27S 865 W60L60 PSU G3	No
911401509551	RC100B LED37S 840 W603L603 PSU UNV G3	No
911401509651	SM100C LED37S 840 W60L60 PSD G3	Yes
911401509951	SM100C LED27S 840 W60L60 PSU G3	No

Order Code	Full Product Name	Dimmable
911401510151	SM100C LED37S 840 W60L60 PSU G3	No
911401510751	RC100B LED37S 840 W60L60 PSU G3	No
911401510851	RC100B LED37S 840 W60L60 PSD OC G3	Yes
911401510951	RC100B LED37S 865 W60L60 PSU G3	No
911401511151	RC100B LED37S 840 W60L60 PSD G3	Yes
911401511847	RC100B LED27S 840 W60L60 PSU G3	-
911401511947	RC100B LED27S 865 W60L60 PSU G3	-
911401512047	RC100B LED37S 840 W60L60 PSU G3	-
911401512147	RC100B LED37S 865 W60L60 PSU G3	-
911401512847	SM100C LED27S 840 W60L60 PSU G3	-
911401512947	SM100C LED37S 840 W60L60 PSU G3	-
911401513347	RC100B LED37S 840 W60L60 PSD G3	DALI
911401513447	RC100B LED37S 865 W60L60 PSD G3	DALI
911401513647	RC100B LED37S 840 W60L60 PSD OC G3	DALI
911401513747	RC100B LED37S 865 W60L60 PSD OC G3	DALI
911401514247	SM100C LED37S 840 W60L60 PSD G3	DALI
911401514447	RC100X LED37/840 W60L60 WIA	Wireless Dim
911401514547	RC100X LED37/865 W60L60 WIA	Wireless Dim
911401514351	RC100B LED54S 840 W60L120 PSU G3	No

Mechanical and Housing

Order Code	Full Product Name	Optical cover type
911401512547	RC100B LED37S 840 W30L120 PSU G3	Polycarbonate bowl/cover
911401513051	RC100B LED37S 840 W30L120 PSD OC G3	Variable linear-lens array in polycarbonate cover
911401513147	SM100C LED37S 840 W30L120 PSU G3	Polycarbonate bowl/cover
911401513247	SM100C LED37S 840 W30L120 PSU G3	Polycarbonate bowl/cover
911401513251	RC100B LED37S 840 W30L120 PSD G3	Variable linear-lens array in polycarbonate cover
911401513351	RC100B LED37S 840 W30L120 PSU G3	Variable linear-lens array in polycarbonate cover
911401513751	RC100B LED37S 865 W30L120 PSU UNV G3	Variable linear-lens array in polycarbonate cover
911401513847	RC100B LED37S 840 W30L120 PSD OC G3	Polycarbonate bowl/cover
911401513947	RC100B LED37S 840 W30L120 PSD G3	Polycarbonate bowl/cover
911401514347	SM100C LED37S 840 W30L120 PSD G3	Polycarbonate bowl/cover
911401514747	RC100X LED37/840 W30L120 WIA	Polycarbonate bowl/cover
911401519451	SM100C LED37S 840 W30L120 PSU G3	Variable linear-lens array in polycarbonate cover
911401519551	SM100C LED37S 840 W30L120 PSD G3	Variable linear-lens array in polycarbonate cover
911401519951	SM100C LED37S 865 W30L120 PSU UNV G3	Variable linear-lens array in polycarbonate cover
911401508451	RC100B LED27S 840 W60L60 PSU G3	Variable linear-lens array in polycarbonate cover
911401508651	RC100B LED27S 865 W60L60 PSU G3	Variable linear-lens array in polycarbonate cover
911401509551	RC100B LED37S 840 W60L60 PSU UNV G3	Variable linear-lens array in polycarbonate cover
911401509651	SM100C LED37S 840 W60L60 PSD G3	Variable linear-lens array in polycarbonate cover
911401509951	SM100C LED27S 840 W60L60 PSU G3	Variable linear-lens array in polycarbonate cover

Order Code	Full Product Name	Optical cover type
911401510151	SM100C LED37S 840 W60L60 PSU G3	Variable linear-lens array in polycarbonate cover
911401510751	RC100B LED37S 840 W60L60 PSU G3	Variable linear-lens array in polycarbonate cover
911401510851	RC100B LED37S 840 W60L60 PSD OC G3	Variable linear-lens array in polycarbonate cover
911401510951	RC100B LED37S 865 W60L60 PSU G3	Variable linear-lens array in polycarbonate cover
911401511151	RC100B LED37S 840 W60L60 PSD G3	Variable linear-lens array in polycarbonate cover
911401511847	RC100B LED27S 840 W60L60 PSU G3	Polycarbonate bowl/cover
91140151947	RC100B LED27S 865 W60L60 PSU G3	Polycarbonate bowl/cover
911401512047	RC100B LED37S 840 W60L60 PSU G3	Polycarbonate bowl/cover
911401512147	RC100B LED37S 865 W60L60 PSU G3	Polycarbonate bowl/cover
911401512847	SM100C LED27S 840 W60L60 PSU G3	Polycarbonate bowl/cover
911401512947	SM100C LED37S 840 W60L60 PSU G3	Polycarbonate bowl/cover
911401513347	RC100B LED37S 840 W60L60 PSD G3	Polycarbonate bowl/cover
911401513447	RC100B LED37S 865 W60L60 PSD G3	Polycarbonate bowl/cover
911401513647	RC100B LED37S 840 W60L60 PSD OC G3	Polycarbonate bowl/cover
911401513747	RC100B LED37S 865 W60L60 PSD OC G3	Polycarbonate bowl/cover
911401514247	SM100C LED37S 840 W60L60 PSD G3	Polycarbonate bowl/cover
911401514447	RC100X LED37/840 W60L60 WIA	Polycarbonate bowl/cover
911401514547	RC100X LED37/865 W60L60 WIA	Polycarbonate bowl/cover
911401514351	RC100B LED54S 840 W60L120 PSU G3	Variable linear-lens array in polycarbonate cover

Approval and Application

Order Code	Full Product Name	Flammability mark	Glow-wire test
911401512547	RC100B LED37S 840 W30L120 PSU G3	-	Temperature 650 °C, duration 30 s
911401513051	RC100B LED37S 840 W30L120 PSD OC G3	For mounting on normally flammable surfaces	Temperature 600 °C, duration 30 s
911401513147	SM100C LED37S 840 W30L120 PSU G3	-	Temperature 650 °C, duration 30 s
911401513247	SM100C LED37S 840 W30L120 PSU G3	-	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Flammability mark	Glow-wire test
911401513251	RC100B LED37S 840 W30L120 PSD G3	For mounting on normally flammable surfaces	Temperature 600 °C, duration 30 s
911401513351	RC100B LED37S 840 W30L120 PSU G3	For mounting on normally flammable surfaces	Temperature 600 °C, duration 30 s
911401513751	RC100B LED37S 865 W30L120 PSU UNV G3	For mounting on normally flammable surfaces	Temperature 600 °C, duration 30 s

GreenPerform Troffer

Order Code	Full Product Name	Flammability mark	Glow-wire test
911401513847	RC100B LED37S 840 W30L120 PSD OC G3	-	Temperature 650 °C, duration 30 s
911401513947	RC100B LED37S 840 W30L120 PSD G3	-	Temperature 650 °C, duration 30 s
911401514347	SM100C LED37S 840 W30L120 PSD G3	-	Temperature 650 °C, duration 30 s
911401514747	RC100X LED37/840 W30L120 WIA	-	Temperature 650 °C, duration 30 s
911401519451	SM100C LED37S 840 W30L120 PSU G3	For mounting on normally flammable surfaces	Temperature 600 °C, duration 30 s
911401519551	SM100C LED37S 840 W30L120 PSD G3	For mounting on normally flammable surfaces	Temperature 600 °C, duration 30 s
911401519951	SM100C LED37S 865 W30L120 PSU UNV G3	For mounting on normally flammable surfaces	Temperature 600 °C, duration 30 s
911401508451	RC100B LED27S 840 W60L60 PSU G3	For mounting on normally flammable surfaces	Temperature 600 °C, duration 30 s
911401508651	RC100B LED27S 865 W60L60 PSU G3	For mounting on normally flammable surfaces	Temperature 600 °C, duration 30 s
911401509551	RC100B LED37S 840 W603L603 PSU UNV G3	For mounting on normally flammable surfaces	Temperature 600 °C, duration 30 s
911401509651	SM100C LED37S 840 W60L60 PSD G3	For mounting on normally flammable surfaces	Temperature 600 °C, duration 30 s
911401509951	SM100C LED27S 840 W60L60 PSU G3	For mounting on normally flammable surfaces	Temperature 600 °C, duration 30 s
911401510151	SM100C LED37S 840 W60L60 PSU G3	For mounting on normally flammable surfaces	Temperature 600 °C, duration 30 s
911401510751	RC100B LED37S 840 W60L60 PSU G3	For mounting on normally flammable surfaces	Temperature 600 °C, duration 30 s

Order Code	Full Product Name	Flammability mark	Glow-wire test
911401510851	RC100B LED37S 840 W60L60 PSD OC G3	For mounting on normally flammable surfaces	Temperature 600 °C, duration 30 s
911401510951	RC100B LED37S 865 W60L60 PSU G3	For mounting on normally flammable surfaces	Temperature 600 °C, duration 30 s
911401511151	RC100B LED37S 840 W60L60 PSD G3	For mounting on normally flammable surfaces	Temperature 600 °C, duration 30 s
911401511847	RC100B LED27S 840 W60L60 PSU G3	-	Temperature 650 °C, duration 30 s
911401511947	RC100B LED27S 865 W60L60 PSU G3	-	Temperature 650 °C, duration 30 s
911401512047	RC100B LED37S 840 W60L60 PSU G3	-	Temperature 650 °C, duration 30 s
911401512147	RC100B LED37S 865 W60L60 PSU G3	-	Temperature 650 °C, duration 30 s
911401512847	SM100C LED27S 840 W60L60 PSU G3	-	Temperature 650 °C, duration 30 s
911401512947	SM100C LED37S 840 W60L60 PSU G3	-	Temperature 650 °C, duration 30 s
911401513347	RC100B LED37S 840 W60L60 PSD G3	-	Temperature 650 °C, duration 30 s
911401513447	RC100B LED37S 865 W60L60 PSD G3	-	Temperature 650 °C, duration 30 s
911401513647	RC100B LED37S 840 W60L60 PSD OC G3	-	Temperature 650 °C, duration 30 s
911401513747	RC100B LED37S 865 W60L60 PSD OC G3	-	Temperature 650 °C, duration 30 s
911401514247	SM100C LED37S 840 W60L60 PSD G3	-	Temperature 650 °C, duration 30 s
911401514447	RC100X LED37/840 W60L60 WIA	-	Temperature 650 °C, duration 30 s
911401514547	RC100X LED37/865 W60L60 WIA	-	Temperature 650 °C, duration 30 s
911401514351	RC100B LED54S 840 W60L120 PSU G3	For mounting on normally flammable surfaces	Temperature 600 °C, duration 30 s

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
911401512547	RC100B LED37S 840 W30L120 PSU G3	-
911401513051	RC100B LED37S 840 W30L120 PSD OC G3	SDCM<4
911401513147	SM100C LED37S 840 W30L120 PSU G3	-
911401513247	SM100C LED37S 840 W30L120 PSU G3	-
911401513251	RC100B LED37S 840 W30L120 PSD G3	SDCM<4
911401513351	RC100B LED37S 840 W30L120 PSU G3	SDCM<4
911401513751	RC100B LED37S 865 W30L120 PSU UNV G3	SDCM<4
911401513847	RC100B LED37S 840 W30L120 PSD OC G3	-
911401513947	RC100B LED37S 840 W30L120 PSD G3	-
911401514347	SM100C LED37S 840 W30L120 PSD G3	-

Order Code	Full Product Name	Initial chromaticity
911401514747	RC100X LED37/840 W30L120 WIA	-
911401519451	SM100C LED37S 840 W30L120 PSU G3	SDCM<4
911401519551	SM100C LED37S 840 W30L120 PSD G3	SDCM<4
911401519951	SM100C LED37S 865 W30L120 PSU UNV G3	SDCM<4
911401508451	RC100B LED27S 840 W60L60 PSU G3	SDCM<4
911401508651	RC100B LED27S 865 W60L60 PSU G3	SDCM<4
911401509551	RC100B LED37S 840 W603L603 PSU UNV G3	SDCM<4
911401509651	SM100C LED37S 840 W60L60 PSD G3	SDCM<4
911401509951	SM100C LED27S 840 W60L60 PSU G3	SDCM<4
911401510151	SM100C LED37S 840 W60L60 PSU G3	SDCM<4

GreenPerform Troffer

Order Code	Full Product Name	Initial chromaticity
911401510751	RC100B LED37S 840 W60L60 PSU G3	SDCM<4
911401510851	RC100B LED37S 840 W60L60 PSD OC G3	SDCM<4
911401510951	RC100B LED37S 865 W60L60 PSU G3	SDCM<4
911401511151	RC100B LED37S 840 W60L60 PSD G3	SDCM<4
911401511847	RC100B LED27S 840 W60L60 PSU G3	-
911401511947	RC100B LED27S 865 W60L60 PSU G3	-
911401512047	RC100B LED37S 840 W60L60 PSU G3	-
911401512147	RC100B LED37S 865 W60L60 PSU G3	-
911401512847	SM100C LED27S 840 W60L60 PSU G3	-

Order Code	Full Product Name	Initial chromaticity
911401512947	SM100C LED37S 840 W60L60 PSU G3	-
911401513347	RC100B LED37S 840 W60L60 PSD G3	-
911401513447	RC100B LED37S 865 W60L60 PSD G3	-
911401513647	RC100B LED37S 840 W60L60 PSD OC G3	-
911401513747	RC100B LED37S 865 W60L60 PSD OC G3	-
911401514247	SM100C LED37S 840 W60L60 PSD G3	-
911401514447	RC100X LED37/840 W60L60 WIA	-
911401514547	RC100X LED37/865 W60L60 WIA	-
911401514351	RC100B LED54S 840 W60L120 PSU G3	SDCM<4

