



# Slim and reliable

## RC160V

GreenPerform Panel RC160V is an edge lit slim panel with high efficacy in the market. It offers 3 typical dimensions: 600x600; 300x1200 and 600x1200mm to fit most of indoor applications. Its lower UGR offers better visual comfort as well. In addition, RC160V offers easy connection to control system to bring better energy saving.

### Benefits

- High lm/w provides better energy saving
- Dali and Interact interfaces available for easy internet connection
- Lower UGR offer for WELL building certificate
- Multiple mountings to cater for various applications

### Features

- System efficiency: max 130lm/W
- CRI 80 and 90 available with SDCM 4
- UGR19 / 16 available for certain types
- IP54 front/IP20 back available for certain types









### Application

- Open plan office
- Public indoor area
- Meeting/training room

### Specifications








<b>Ingress protection</b>	IP20/IP54 front/IP20 back	<b>Installation</b>	Recessed
---------------------------	---------------------------	---------------------	----------

Dimensional drawing



# RC160V

## Dimensional drawing



## General Information

Driver included	Yes
Gear	-
Number of gear units	1 unit
Service tag	Yes

## Light Technical

Color rendering index (CRI)	80
Optic type	Beam angle 100°

## Operating and Electrical

Protection class IEC	Safety class II
Input Voltage	200 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	Not applicable

## Mechanical and Housing

Housing Color	White RAL 9003
Mech. impact protection code	IK03

## Approval and Application

Ambient temperature range	-20 to +40 °C
CE mark	Yes
ENEC mark	-
Flammability mark	-
Glow-wire test	Temperature 650 °C, duration 30 s

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

## Light Technical

Order Code	Full Product Name	Correlated Color		Number of light sources	
		Temperature (Nom)	Luminous Efficacy (rated) (Nom)		
911401505543	RC160V LED37/940 W303L1210 PSU OC UVG	4000 K	125 lm/W	3,750 lm	288
911401505643	RC160V LED37/965 W303L1210 PSU OC UVG	6500 K	125 lm/W	3,750 lm	288
911401510132	RC160V LED37/830 W30L120 PSU	3000 K	122 lm/W	3,700 lm	288
911401510232	RC160V LED39/840 W30L120 PSU	4000 K	130 lm/W	3,900 lm	288
911401510332	RC160V LED39/865 W30L120 PSU	6500 K	130 lm/W	3,900 lm	288
911401511032	RC160V LED37/830 W30L120 PSU OC	3000 K	122 lm/W	3,700 lm	288
911401511132	RC160V LED39/840 W30L120 PSU OC	4000 K	130 lm/W	3,900 lm	288
911401511232	RC160V LED39/865 W30L120 PSU OC	6500 K	130 lm/W	3,900 lm	288
911401511932	RC160V LED27/830 W30L120 PSU 16	3000 K	125 lm/W	2,740 lm	288
911401512032	RC160V LED29/840 W30L120 PSU 16	4000 K	133 lm/W	2,900 lm	288
911401512132	RC160V LED29/865 W30L120 PSU 16	6500 K	133 lm/W	2,900 lm	288
911401512832	RC160V LED37/830 W30L120 PSU 54	3000 K	122 lm/W	3,700 lm	288
911401512932	RC160V LED39/840 W30L120 PSU 54	4000 K	130 lm/W	3,900 lm	288
911401513032	RC160V LED39/865 W30L120 PSU 54	6500 K	130 lm/W	3,900 lm	288
911401513732	RC160V LED37/830 W30L120 PSU OC 54	3000 K	122 lm/W	3,700 lm	288
911401513832	RC160V LED39/840 W30L120 PSU OC 54	4000 K	130 lm/W	3,900 lm	288
911401513932	RC160V LED39/865 W30L120 PSU OC 54	6500 K	130 lm/W	3,900 lm	288
911401514632	RC160V LED27/830 W30L120 PSU 16 54	3000 K	125 lm/W	2,740 lm	288
911401514732	RC160V LED29/840 W30L120 PSU 16 54	4000 K	133 lm/W	2,900 lm	288
911401514832	RC160V LED29/865 W30L120 PSU 16 54	6500 K	133 lm/W	2,900 lm	288
911401516432	RC160V LED37/830 W30L120 PSU OC CPC	3000 K	122 lm/W	3,700 lm	288
911401516532	RC160V LED39/840 W30L120 PSU OC CPC	4000 K	130 lm/W	3,900 lm	288
911401516632	RC160V LED39/865 W30L120 PSU OC CPC	6500 K	130 lm/W	3,900 lm	288
911401519132	RC160V LED37/830 W30L120 PSU OC 54 CPC	3000 K	122 lm/W	3,700 lm	288

Order Code	Full Product Name	Correlated Color		Luminous Flux	Number of light sources
		Temperature (Nom)	Luminous Efficacy (rated) (Nom)		
911401519232	RC160V LED39/840 W30L120 PSU OC 54 CPC	4000 K	130 lm/W	3,900 lm	288
911401519332	RC160V LED39/865 W30L120 PSU OC 54 CPC	6500 K	130 lm/W	3,900 lm	288
911401520932	RC160V LED37/830 W30L120 PSD	3000 K	122 lm/W	3,700 lm	288
911401521032	RC160V LED39/840 W30L120 PSD	4000 K	130 lm/W	3,900 lm	288
911401521132	RC160V LED39/865 W30L120 PSD	6500 K	130 lm/W	3,900 lm	288
911401521832	RC160V LED37/830 W30L120 PSD OC	3000 K	122 lm/W	3,700 lm	288
911401521932	RC160V LED39/840 W30L120 PSD OC	4000 K	130 lm/W	3,900 lm	288
911401522032	RC160V LED39/865 W30L120 PSD OC	6500 K	130 lm/W	3,900 lm	288
911401522732	RC160V LED27/830 W30L120 PSD 16	3000 K	125 lm/W	2,740 lm	288
911401522832	RC160V LED29/840 W30L120 PSD 16	4000 K	133 lm/W	2,900 lm	288
911401522932	RC160V LED29/865 W30L120 PSD 16	6500 K	133 lm/W	2,900 lm	288
911401523632	RC160X LED37/830 W30L120 WIA	3000 K	122 lm/W	3,700 lm	288
911401523732	RC160X LED39/840 W30L120 WIA	4000 K	130 lm/W	3,900 lm	288
911401523832	RC160X LED39/865 W30L120 WIA	6500 K	130 lm/W	3,900 lm	288
911401524832	RC160X LED37/830 W30L120 SIA	3000 K	122 lm/W	3,700 lm	288
911401524932	RC160X LED39/840 W30L120 SIA	4000 K	130 lm/W	3,900 lm	288
911401525032	RC160X LED39/865 W30L120 SIA	6500 K	130 lm/W	3,900 lm	288
911401525532	RC160V LED38/8TW W30L120	2700 K	122 lm/W	3,800 lm	480
911401526032	RC160V LED37/830 W30L120 PSU CAU	3000 K	122 lm/W	3,700 lm	288
911401526132	RC160V LED39/840 W30L120 PSU CAU	4000 K	130 lm/W	3,900 lm	288
911401526232	RC160V LED39/865 W30L120 PSU CAU	6500 K	130 lm/W	3,900 lm	288
911401526932	RC160V LED37/830 W30L120 PSD CAU	3000 K	122 lm/W	3,700 lm	288
911401527032	RC160V LED39/840 W30L120 PSD CAU	4000 K	130 lm/W	3,900 lm	288
911401527132	RC160V LED39/865 W30L120 PSD CAU	6500 K	130 lm/W	3,900 lm	288
911401527832	RC160X LED37/830 W30L120 WIA CAU	3000 K	122 lm/W	3,700 lm	288

Order Code	Full Product Name	Correlated Color		Luminous Flux	Number of light sources
		Temperature (Nom)	Luminous Efficacy (rated) (Nom)		
911401527932	RC160X LED39/840 W30L120 WIA CAU	4000 K	130 lm/W	3,900 lm	288
911401528032	RC160X LED39/865 W30L120 WIA CAU	6500 K	130 lm/W	3,900 lm	288
911401528432	RC160X LED37/830 W30L120 SIA CAU	3000 K	122 lm/W	3,700 lm	288
911401528532	RC160X LED39/840 W30L120 SIA CAU	4000 K	130 lm/W	3,900 lm	288
911401528632	RC160X LED39/865 W30L120 SIA CAU	6500 K	130 lm/W	3,900 lm	288
911401529332	RC160V LED37/830 W30L120 PSU OC CAU	3000 K	122 lm/W	3,700 lm	288
911401529432	RC160V LED39/840 W30L120 PSU OC CAU	4000 K	130 lm/W	3,900 lm	288
911401529532	RC160V LED39/865 W30L120 PSU OC CAU	6500 K	130 lm/W	3,900 lm	288
911401530232	RC160V LED37/830 W30L120 PSD OC CAU	3000 K	122 lm/W	3,700 lm	288
911401530332	RC160V LED39/840 W30L120 PSD OC CAU	4000 K	130 lm/W	3,900 lm	288
911401530432	RC160V LED39/865 W30L120 PSD OC CAU	6500 K	130 lm/W	3,900 lm	288
911401531432	RC160V LED27/830 W30L120 PSU 16 CAU	3000 K	125 lm/W	2,740 lm	288
911401531532	RC160V LED29/840 W30L120 PSU 16 CAU	4000 K	133 lm/W	2,900 lm	288
911401531632	RC160V LED29/865 W30L120 PSU 16 CAU	6500 K	133 lm/W	2,900 lm	288
911401532332	RC160V LED27/830 W30L120 PSD 16 CAU	3000 K	125 lm/W	2,740 lm	288
911401532432	RC160V LED29/840 W30L120 PSD 16 CAU	4000 K	133 lm/W	2,900 lm	288
911401532532	RC160V LED29/865 W30L120 PSD 16 CAU	6500 K	133 lm/W	2,900 lm	288
911401533532	RC160V LED37/830 W30L120 PSU 54 CAU	3000 K	122 lm/W	3,700 lm	288
911401533632	RC160V LED39/840 W30L120 PSU 54 CAU	4000 K	130 lm/W	3,900 lm	288
911401533732	RC160V LED39/865 W30L120 PSU 54 CAU	6500 K	130 lm/W	3,900 lm	288
911401534432	RC160V LED37/830 W30L120 PSU OC 54 CAU	3000 K	122 lm/W	3,700 lm	288
911401534532	RC160V LED39/840 W30L120 PSU OC 54 CAU	4000 K	130 lm/W	3,900 lm	288
911401534632	RC160V LED39/865 W30L120 PSU OC 54 CAU	6500 K	130 lm/W	3,900 lm	288
911401535332	RC160V LED27/830 W30L120 PSU 16 54 CAU	3000 K	125 lm/W	2,740 lm	288
911401535432	RC160V LED29/840 W30L120 PSU 16 54 CAU	4000 K	133 lm/W	2,900 lm	288

Order Code	Full Product Name	Correlated Color		Number of light sources	
		Temperature (Nom)	Luminous Efficacy (rated) (Nom)		
911401535532	RC160V LED29/865 W30L120 PSU 16 54 CAU	6500 K	133 lm/W	2,900 lm	288
911401536232	RC160V LED37/830 W303L1210 PSU UVG	3000 K	122 lm/W	3,700 lm	288
911401536332	RC160V LED39/840 W303L1210 PSU UVG	4000 K	130 lm/W	3,900 lm	288
911401536432	RC160V LED39/865 W303L1210 PSU UVG	6500 K	130 lm/W	3,900 lm	288
911401536832	RC160V LED35/930 W30L120 PSU	3000 K	118 lm/W	3,500 lm	288
911401536932	RC160V LED37/940 W30L120 PSU	4000 K	126 lm/W	3,750 lm	288
911401537032	RC160V LED37/965 W30L120 PSU	6500 K	126 lm/W	3,750 lm	288
911401537732	RC160V LED35/930 W30L120 PSU 54	3000 K	118 lm/W	3,500 lm	288
911401537832	RC160V LED37/940 W30L120 PSU 54	4000 K	126 lm/W	3,750 lm	288
911401537932	RC160V LED37/965 W30L120 PSU 54	6500 K	126 lm/W	3,750 lm	288
911401538632	RC160V LED35/930 W30L120 PSD	3000 K	118 lm/W	3,500 lm	288
911401538732	RC160V LED37/940 W30L120 PSD	4000 K	126 lm/W	3,750 lm	288
911401538832	RC160V LED37/965 W30L120 PSD	6500 K	126 lm/W	3,750 lm	288
911401539532	RC160X LED35/930 W30L120 WIA	3000 K	118 lm/W	3,500 lm	288
911401539632	RC160X LED37/940 W30L120 WIA	4000 K	126 lm/W	3,750 lm	288
911401539732	RC160X LED37/965 W30L120 WIA	6500 K	126 lm/W	3,750 lm	288
911401540132	RC160X LED35/930 W30L120 SIA	3000 K	118 lm/W	3,500 lm	288
911401540232	RC160X LED37/940 W30L120 SIA	4000 K	126 lm/W	3,750 lm	288
911401540332	RC160X LED37/965 W30L120 SIA	6500 K	126 lm/W	3,750 lm	288
911401541032	RC160V LED35/930 W30L120 PSU CAU	3000 K	118 lm/W	3,500 lm	288
911401541132	RC160V LED37/940 W30L120 PSU CAU	4000 K	126 lm/W	3,750 lm	288
911401541232	RC160V LED37/965 W30L120 PSU CAU	6500 K	126 lm/W	3,750 lm	288
911401541932	RC160V LED35/930 W30L120 PSD CAU	3000 K	118 lm/W	3,500 lm	288
911401542032	RC160V LED37/940 W30L120 PSD CAU	4000 K	126 lm/W	3,750 lm	288
911401542132	RC160V LED37/965 W30L120 PSD CAU	6500 K	126 lm/W	3,750 lm	288

Order Code	Full Product Name	Correlated Color		Number of light sources	
		Temperature (Nom)	Luminous Efficacy (rated) (Nom)		
911401542832	RC160X LED35/930 W30L120 WIA CAU	3000 K	118 lm/W	3,500 lm	288
911401542932	RC160X LED37/940 W30L120 WIA CAU	4000 K	126 lm/W	3,750 lm	288
911401543032	RC160X LED37/965 W30L120 WIA CAU	6500 K	126 lm/W	3,750 lm	288
911401543432	RC160X LED35/930 W30L120 SIA CAU	3000 K	118 lm/W	3,500 lm	288
911401543532	RC160X LED37/940 W30L120 SIA CAU	4000 K	126 lm/W	3,750 lm	288
911401543632	RC160X LED37/965 W30L120 SIA CAU	6500 K	126 lm/W	3,750 lm	288
911401544332	RC160V LED35/930 W30L120 PSU 54 CAU	3000 K	118 lm/W	3,500 lm	288
911401544432	RC160V LED37/940 W30L120 PSU 54 CAU	4000 K	126 lm/W	3,750 lm	288
911401544532	RC160V LED37/965 W30L120 PSU 54 CAU	6500 K	126 lm/W	3,750 lm	288
911401545632	RC160V LED37/9TW W30L120	2700 K	123 lm/W	3,700 lm	480
911401545932	RC160V LED37/9TW W30L120 54	2700 K	123 lm/W	3,700 lm	480
911401546232	RC160V LED37/9TW W30L120 CAU	2700 K	123 lm/W	3,700 lm	480
911401546532	RC160V LED37/9TW W30L120 54 CAU	2700 K	123 lm/W	3,700 lm	480
911401578942	RC160V LED37/830 W303L1210 PSU OC UVG	3000 K	122 lm/W	3,700 lm	288
911401579042	RC160V LED39/840 W303L1210 PSU OC UVG	4000 K	130 lm/W	3,900 lm	288
911401579142	RC160V LED39/865 W303L1210 PSU OC UVG	6500 K	130 lm/W	3,900 lm	288
911401510432	RC160V LED57/830 W60L120 PSU	3000 K	123 lm/W	5,700 lm	384
911401510532	RC160V LED60/840 W60L120 PSU	4000 K	131 lm/W	6,000 lm	384
911401510632	RC160V LED60/865 W60L120 PSU	6500 K	131 lm/W	6,000 lm	384
911401511332	RC160V LED57/830 W60L120 PSU OC	3000 K	123 lm/W	5,700 lm	384
911401511432	RC160V LED60/840 W60L120 PSU OC	4000 K	131 lm/W	6,000 lm	384
911401511532	RC160V LED60/865 W60L120 PSU OC	6500 K	131 lm/W	6,000 lm	384
911401512232	RC160V LED54/830 W60L120 PSU 16	3000 K	119 lm/W	5,450 lm	384
911401512332	RC160V LED58/840 W60L120 PSU 16	4000 K	126 lm/W	5,800 lm	384
911401512432	RC160V LED58/865 W60L120 PSU 16	6500 K	126 lm/W	5,800 lm	384

Order Code	Full Product Name	Correlated Color		Luminous Flux	Number of light sources
		Temperature (Nom)	Luminous Efficacy (rated) (Nom)		
911401513132	RC160V LED57/830 W60L120 PSU 54	3000 K	123 lm/W	5,700 lm	384
911401513232	RC160V LED60/840 W60L120 PSU 54	4000 K	131 lm/W	6,000 lm	384
911401513332	RC160V LED60/865 W60L120 PSU 54	6500 K	131 lm/W	6,000 lm	384
911401514032	RC160V LED57/830 W60L120 PSU OC 54	3000 K	123 lm/W	5,700 lm	384
911401514132	RC160V LED60/840 W60L120 PSU OC 54	4000 K	131 lm/W	6,000 lm	384
911401514232	RC160V LED60/865 W60L120 PSU OC 54	6500 K	131 lm/W	6,000 lm	384
911401514932	RC160V LED54/830 W60L120 PSU 16 54	3000 K	119 lm/W	5,450 lm	384
911401515032	RC160V LED58/840 W60L120 PSU 16 54	4000 K	126 lm/W	5,800 lm	384
911401515132	RC160V LED58/865 W60L120 PSU 16 54	6500 K	126 lm/W	5,800 lm	384
911401521232	RC160V LED57/830 W60L120 PSD	3000 K	123 lm/W	5,700 lm	384
911401521332	RC160V LED60/840 W60L120 PSD	4000 K	131 lm/W	6,000 lm	384
911401521432	RC160V LED60/865 W60L120 PSD	6500 K	131 lm/W	6,000 lm	384
911401522132	RC160V LED57/830 W60L120 PSD OC	3000 K	123 lm/W	5,700 lm	384
911401522232	RC160V LED60/840 W60L120 PSD OC	4000 K	131 lm/W	6,000 lm	384
911401522332	RC160V LED60/865 W60L120 PSD OC	6500 K	131 lm/W	6,000 lm	384
911401523032	RC160V LED54/830 W60L120 PSD 16	3000 K	119 lm/W	5,450 lm	384
911401523132	RC160V LED58/840 W60L120 PSD 16	4000 K	126 lm/W	5,800 lm	384
911401523232	RC160V LED58/865 W60L120 PSD 16	6500 K	126 lm/W	5,800 lm	384
911401525132	RC160X LED57/830 W60L120 SIA	3000 K	123 lm/W	5,700 lm	384
911401525232	RC160X LED60/840 W60L120 SIA	4000 K	131 lm/W	6,000 lm	384
911401525332	RC160X LED60/865 W60L120 SIA	6500 K	131 lm/W	6,000 lm	384
911401526332	RC160V LED57/830 W60L120 PSU CAU	3000 K	123 lm/W	5,700 lm	384
911401526432	RC160V LED60/840 W60L120 PSU CAU	4000 K	131 lm/W	6,000 lm	384
911401526532	RC160V LED60/865 W60L120 PSU CAU	6500 K	131 lm/W	6,000 lm	384
911401527232	RC160V LED57/830 W60L120 PSD CAU	3000 K	123 lm/W	5,700 lm	384

Order Code	Full Product Name	Correlated Color		Luminous Flux	Number of light sources
		Temperature (Nom)	Luminous Efficacy (rated) (Nom)		
911401527332	RC160V LED60/840 W60L120 PSD CAU	4000 K	131 lm/W	6,000 lm	384
911401527432	RC160V LED60/865 W60L120 PSD CAU	6500 K	131 lm/W	6,000 lm	384
911401528732	RC160X LED57/830 W60L120 SIA CAU	3000 K	123 lm/W	5,700 lm	384
911401528832	RC160X LED60/840 W60L120 SIA CAU	4000 K	131 lm/W	6,000 lm	384
911401528932	RC160X LED60/865 W60L120 SIA CAU	6500 K	131 lm/W	6,000 lm	384
911401529632	RC160V LED57/830 W60L120 PSU OC CAU	3000 K	123 lm/W	5,700 lm	384
911401529732	RC160V LED60/840 W60L120 PSU OC CAU	4000 K	131 lm/W	6,000 lm	384
911401529832	RC160V LED60/865 W60L120 PSU OC CAU	6500 K	131 lm/W	6,000 lm	384
911401530532	RC160V LED57/830 W60L120 PSD OC CAU	3000 K	123 lm/W	5,700 lm	384
911401530632	RC160V LED60/840 W60L120 PSD OC CAU	4000 K	131 lm/W	6,000 lm	384
911401530732	RC160V LED60/865 W60L120 PSD OC CAU	6500 K	131 lm/W	6,000 lm	384
911401531732	RC160V LED54/830 W60L120 PSU 16 CAU	3000 K	119 lm/W	5,450 lm	384
911401531832	RC160V LED58/840 W60L120 PSU 16 CAU	4000 K	126 lm/W	5,800 lm	384
911401531932	RC160V LED58/865 W60L120 PSU 16 CAU	6500 K	126 lm/W	5,800 lm	384
911401532632	RC160V LED54/830 W60L120 PSD 16 CAU	3000 K	119 lm/W	5,450 lm	384
911401532732	RC160V LED58/840 W60L120 PSD 16 CAU	4000 K	126 lm/W	5,800 lm	384
911401532832	RC160V LED58/865 W60L120 PSD 16 CAU	6500 K	126 lm/W	5,800 lm	384
911401533832	RC160V LED57/830 W60L120 PSU 54 CAU	3000 K	123 lm/W	5,700 lm	384
911401533932	RC160V LED60/840 W60L120 PSU 54 CAU	4000 K	131 lm/W	6,000 lm	384
911401534032	RC160V LED60/865 W60L120 PSU 54 CAU	6500 K	131 lm/W	6,000 lm	384
911401534732	RC160V LED57/830 W60L120 PSU OC 54 CAU	3000 K	123 lm/W	5,700 lm	384
911401534832	RC160V LED60/840 W60L120 PSU OC 54 CAU	4000 K	131 lm/W	6,000 lm	384
911401534932	RC160V LED60/865 W60L120 PSU OC 54 CAU	6500 K	131 lm/W	6,000 lm	384
911401535632	RC160V LED54/830 W60L120 PSU 16 54 CAU	3000 K	119 lm/W	5,450 lm	384
911401535732	RC160V LED58/840 W60L120 PSU 16 54 CAU	4000 K	126 lm/W	5,800 lm	384

Order Code	Full Product Name	Correlated Color		Number of light sources	
		Temperature (Nom)	Luminous Efficacy (rated) (Nom)		
911401535832	RC160V LED58/865 W60L120 PSU 16 54 CAU	6500 K	126 lm/W	5,800 lm	384
911401537132	RC160V LED54/930 W60L120 PSU	3000 K	119 lm/W	5,450 lm	384
911401537232	RC160V LED58/940 W60L120 PSU	4000 K	126 lm/W	5,800 lm	384
911401537332	RC160V LED58/965 W60L120 PSU	6500 K	126 lm/W	5,800 lm	384
911401538032	RC160V LED54/930 W60L120 PSU 54	3000 K	119 lm/W	5,450 lm	384
911401538132	RC160V LED58/940 W60L120 PSU 54	4000 K	126 lm/W	5,800 lm	384
911401538232	RC160V LED58/965 W60L120 PSU 54	6500 K	126 lm/W	5,800 lm	384
911401538932	RC160V LED54/930 W60L120 PSD	3000 K	119 lm/W	5,450 lm	384
911401539032	RC160V LED58/940 W60L120 PSD	4000 K	126 lm/W	5,800 lm	384
911401539132	RC160V LED58/965 W60L120 PSD	6500 K	126 lm/W	5,800 lm	384
911401540432	RC160X LED54/930 W60L120 SIA	3000 K	119 lm/W	5,450 lm	384
911401540532	RC160X LED58/940 W60L120 SIA	4000 K	126 lm/W	5,800 lm	384
911401540632	RC160X LED58/965 W60L120 SIA	6500 K	126 lm/W	5,800 lm	384
911401541332	RC160V LED54/930 W60L120 PSU CAU	3000 K	119 lm/W	5,450 lm	384
911401541432	RC160V LED58/940 W60L120 PSU CAU	4000 K	126 lm/W	5,800 lm	384
911401541532	RC160V LED58/965 W60L120 PSU CAU	6500 K	126 lm/W	5,800 lm	384
911401542232	RC160V LED54/930 W60L120 PSD CAU	3000 K	119 lm/W	5,450 lm	384
911401542332	RC160V LED58/940 W60L120 PSD CAU	4000 K	126 lm/W	5,800 lm	384
911401542432	RC160V LED58/965 W60L120 PSD CAU	6500 K	126 lm/W	5,800 lm	384
911401543732	RC160X LED54/930 W60L120 SIA CAU	3000 K	119 lm/W	5,450 lm	384
911401543832	RC160X LED58/940 W60L120 SIA CAU	4000 K	126 lm/W	5,800 lm	384
911401543932	RC160X LED58/965 W60L120 SIA CAU	6500 K	126 lm/W	5,800 lm	384
911401544632	RC160V LED54/930 W60L120 PSU 54 CAU	3000 K	119 lm/W	5,450 lm	384
911401544732	RC160V LED58/940 W60L120 PSU 54 CAU	4000 K	126 lm/W	5,800 lm	384
911401544832	RC160V LED58/965 W60L120 PSU 54 CAU	6500 K	126 lm/W	5,800 lm	384

Order Code	Full Product Name	Correlated Color		Number of light sources	
		Temperature (Nom)	Luminous Efficacy (rated) (Nom)		
911401544932	RC160X LED48/930 W60L120 WIA	3000 K	121 lm/W	4,800 lm	384
911401545032	RC160X LED51/940 W60L120 WIA	4000 K	129 lm/W	5,100 lm	384
911401545132	RC160X LED51/965 W60L120 WIA	6500 K	129 lm/W	5,100 lm	384
911401545232	RC160X LED48/930 W60L120 WIA CAU	3000 K	121 lm/W	4,800 lm	384
911401545332	RC160X LED51/940 W60L120 WIA CAU	4000 K	129 lm/W	5,100 lm	384
911401545432	RC160X LED51/965 W60L120 WIA CAU	6500 K	129 lm/W	5,100 lm	384
911401505343	RC160V LED37/940 W603L603 PSU OC UVG	4000 K	125 lm/W	3,750 lm	240
911401505443	RC160V LED37/965 W603L603 PSU OC UVG	6500 K	125 lm/W	3,750 lm	240
91140150983 2	RC160V LED37/830 W60L60 PSU	3000 K	122 lm/W	3,700 lm	240
91140150993 2	RC160V LED39/840 W60L60 PSU	4000 K	130 lm/W	3,900 lm	240
911401510032	RC160V LED39/865 W60L60 PSU	6500 K	130 lm/W	3,900 lm	240
911401510732	RC160V LED37/830 W60L60 PSU OC	3000 K	122 lm/W	3,700 lm	240
911401510832	RC160V LED39/840 W60L60 PSU OC	4000 K	130 lm/W	3,900 lm	240
911401510932	RC160V LED39/865 W60L60 PSU OC	6500 K	130 lm/W	3,900 lm	240
911401511632	RC160V LED27/830 W60L60 PSU 16	3000 K	124 lm/W	2,740 lm	240
911401511732	RC160V LED29/840 W60L60 PSU 16	4000 K	132 lm/W	2,900 lm	240
911401511832	RC160V LED29/865 W60L60 PSU 16	6500 K	132 lm/W	2,900 lm	240
911401512532	RC160V LED37/830 W60L60 PSU 54	3000 K	122 lm/W	3,700 lm	240
911401512632	RC160V LED39/840 W60L60 PSU 54	4000 K	130 lm/W	3,900 lm	240
911401512732	RC160V LED39/865 W60L60 PSU 54	6500 K	130 lm/W	3,900 lm	240
911401513432	RC160V LED37/830 W60L60 PSU OC 54	3000 K	122 lm/W	3,700 lm	240
911401513532	RC160V LED39/840 W60L60 PSU OC 54	4000 K	130 lm/W	3,900 lm	240
911401513632	RC160V LED39/865 W60L60 PSU OC 54	6500 K	130 lm/W	3,900 lm	240
911401514332	RC160V LED27/830 W60L60 PSU 16 54	3000 K	124 lm/W	2,740 lm	240
911401514432	RC160V LED29/840 W60L60 PSU 16 54	4000 K	132 lm/W	2,900 lm	240

Order Code	Full Product Name	Correlated Color		Number of light sources	
		Temperature (Nom)	Luminous Efficacy (rated) (Nom)		
911401514532	RC160V LED29/865 W60L60 PSU 16 54	6500 K	132 lm/W	2,900 lm	240
911401516132	RC160V LED37/830 W60L60 PSU OC CPC	3000 K	122 lm/W	3,700 lm	240
911401516232	RC160V LED39/840 W60L60 PSU OC CPC	4000 K	130 lm/W	3,900 lm	240
911401516332	RC160V LED39/865 W60L60 PSU OC CPC	6500 K	130 lm/W	3,900 lm	240
911401518832	RC160V LED37/830 W60L60 PSU OC 54 CPC	3000 K	122 lm/W	3,700 lm	240
911401518932	RC160V LED39/840 W60L60 PSU OC 54 CPC	4000 K	130 lm/W	3,900 lm	240
911401519032	RC160V LED39/865 W60L60 PSU OC 54 CPC	6500 K	130 lm/W	3,900 lm	240
911401520632	RC160V LED37/830 W60L60 PSD	3000 K	122 lm/W	3,700 lm	240
911401520732	RC160V LED39/840 W60L60 PSD	4000 K	130 lm/W	3,900 lm	240
911401520832	RC160V LED39/865 W60L60 PSD	6500 K	130 lm/W	3,900 lm	240
911401521532	RC160V LED37/830 W60L60 PSD OC	3000 K	122 lm/W	3,700 lm	240
911401521632	RC160V LED39/840 W60L60 PSD OC	4000 K	130 lm/W	3,900 lm	240
911401521732	RC160V LED39/865 W60L60 PSD OC	6500 K	130 lm/W	3,900 lm	240
911401522432	RC160V LED27/830 W60L60 PSD 16	3000 K	124 lm/W	2,740 lm	240
911401522532	RC160V LED29/840 W60L60 PSD 16	4000 K	132 lm/W	2,900 lm	240
911401522632	RC160V LED29/865 W60L60 PSD 16	6500 K	132 lm/W	2,900 lm	240
911401523332	RC160X LED37/830 W60L60 WIA	3000 K	122 lm/W	3,700 lm	240
911401523432	RC160X LED39/840 W60L60 WIA	4000 K	130 lm/W	3,900 lm	240
911401523532	RC160X LED39/865 W60L60 WIA	6500 K	130 lm/W	3,900 lm	240
911401523932	RC160X LED37/830 W60L60 WIA OC	3000 K	122 lm/W	3,700 lm	240
911401524032	RC160X LED39/840 W60L60 WIA OC	4000 K	130 lm/W	3,900 lm	240
911401524132	RC160X LED39/865 W60L60 WIA OC	6500 K	130 lm/W	3,900 lm	240
911401524232	RC160X LED27/830 W60L60 WIA 16	3000 K	124 lm/W	2,740 lm	240
911401524332	RC160X LED29/840 W60L60 WIA 16	4000 K	132 lm/W	2,900 lm	240
911401524432	RC160X LED29/865 W60L60 WIA 16	6500 K	132 lm/W	2,900 lm	240

Order Code	Full Product Name	Correlated Color		Number of light sources	
		Temperature (Nom)	Luminous Efficacy (rated) (Nom)		
911401524532	RC160X LED37/830 W60L60 SIA	3000 K	122 lm/W	3,700 lm	240
911401524632	RC160X LED39/840 W60L60 SIA	4000 K	130 lm/W	3,900 lm	240
911401524732	RC160X LED39/865 W60L60 SIA	6500 K	130 lm/W	3,900 lm	240
911401525432	RC160V LED37/8TW W60L60	2700 K	112 lm/W	3,700 lm	240
911401525732	RC160V LED37/830 W60L60 PSU CAU	3000 K	122 lm/W	3,700 lm	240
911401525832	RC160V LED39/840 W60L60 PSU CAU	4000 K	130 lm/W	3,900 lm	240
911401525932	RC160V LED39/865 W60L60 PSU CAU	6500 K	130 lm/W	3,900 lm	240
911401526632	RC160V LED37/830 W60L60 PSD CAU	3000 K	122 lm/W	3,700 lm	240
911401526732	RC160V LED39/840 W60L60 PSD CAU	4000 K	130 lm/W	3,900 lm	240
911401526832	RC160V LED39/865 W60L60 PSD CAU	6500 K	130 lm/W	3,900 lm	240
911401527532	RC160X LED37/830 W60L60 WIA CAU	3000 K	122 lm/W	3,700 lm	240
911401527632	RC160X LED39/840 W60L60 WIA CAU	4000 K	130 lm/W	3,900 lm	240
911401527732	RC160X LED39/865 W60L60 WIA CAU	6500 K	130 lm/W	3,900 lm	240
911401528132	RC160X LED37/830 W60L60 SIA CAU	3000 K	122 lm/W	3,700 lm	240
911401528232	RC160X LED39/840 W60L60 SIA CAU	4000 K	130 lm/W	3,900 lm	240
911401528332	RC160X LED39/865 W60L60 SIA CAU	6500 K	130 lm/W	3,900 lm	240
911401529032	RC160V LED37/830 W60L60 PSU OC CAU	3000 K	122 lm/W	3,700 lm	240
911401529132	RC160V LED39/840 W60L60 PSU OC CAU	4000 K	130 lm/W	3,900 lm	240
911401529232	RC160V LED39/865 W60L60 PSU OC CAU	6500 K	130 lm/W	3,900 lm	240
911401529932	RC160V LED37/830 W60L60 PSD OC CAU	3000 K	122 lm/W	3,700 lm	240
91140153003 2	RC160V LED39/840 W60L60 PSD OC CAU	4000 K	130 lm/W	3,900 lm	240
911401530132	RC160V LED39/865 W60L60 PSD OC CAU	6500 K	130 lm/W	3,900 lm	240
911401530832	RC160X LED37/830 W60L60 WIA OC CAU	3000 K	122 lm/W	3,700 lm	240
911401530932	RC160X LED39/840 W60L60 WIA OC CAU	4000 K	130 lm/W	3,900 lm	240
911401531032	RC160X LED39/865 W60L60 WIA OC CAU	6500 K	130 lm/W	3,900 lm	240

Order Code	Full Product Name	Correlated Color		Number of light sources	
		Temperature (Nom)	Luminous Efficacy (rated) (Nom)		
911401531132	RC160V LED27/830 W60L60 PSU 16 CAU	3000 K	124 lm/W	2,740 lm	240
911401531232	RC160V LED29/840 W60L60 PSU 16 CAU	4000 K	132 lm/W	2,900 lm	240
911401531332	RC160V LED29/865 W60L60 PSU 16 CAU	6500 K	132 lm/W	2,900 lm	240
911401532032	RC160V LED27/830 W60L60 PSD 16 CAU	3000 K	124 lm/W	2,740 lm	240
911401532132	RC160V LED29/840 W60L60 PSD 16 CAU	4000 K	132 lm/W	2,900 lm	240
911401532232	RC160V LED29/865 W60L60 PSD 16 CAU	6500 K	132 lm/W	2,900 lm	240
911401532932	RC160X LED27/830 W60L60 WIA 16 CAU	3000 K	124 lm/W	2,740 lm	240
911401533032	RC160X LED29/840 W60L60 WIA 16 CAU	4000 K	132 lm/W	2,900 lm	240
911401533132	RC160X LED29/865 W60L60 WIA 16 CAU	6500 K	132 lm/W	2,900 lm	240
911401533232	RC160V LED37/830 W60L60 PSU 54 CAU	3000 K	122 lm/W	3,700 lm	240
911401533332	RC160V LED39/840 W60L60 PSU 54 CAU	4000 K	130 lm/W	3,900 lm	240
911401533432	RC160V LED39/865 W60L60 PSU 54 CAU	6500 K	130 lm/W	3,900 lm	240
911401534132	RC160V LED37/830 W60L60 PSU OC 54 CAU	3000 K	122 lm/W	3,700 lm	240
911401534232	RC160V LED39/840 W60L60 PSU OC 54 CAU	4000 K	130 lm/W	3,900 lm	240
911401534332	RC160V LED39/865 W60L60 PSU OC 54 CAU	6500 K	130 lm/W	3,900 lm	240
911401535032	RC160V LED27/830 W60L60 PSU 16 54 CAU	3000 K	124 lm/W	2,740 lm	240
911401535132	RC160V LED29/840 W60L60 PSU 16 54 CAU	4000 K	132 lm/W	2,900 lm	240
911401535232	RC160V LED29/865 W60L60 PSU 16 54 CAU	6500 K	132 lm/W	2,900 lm	240
911401535932	RC160V LED37/830 W603L603 PSU UVG	3000 K	122 lm/W	3,700 lm	240
911401536032	RC160V LED39/840 W603L603 PSU UVG	4000 K	130 lm/W	3,900 lm	240
911401536132	RC160V LED39/865 W603L603 PSU UVG	6500 K	130 lm/W	3,900 lm	240
911401536532	RC160V LED35/930 W60L60 PSU	3000 K	118 lm/W	3,500 lm	240
911401536632	RC160V LED37/940 W60L60 PSU	4000 K	125 lm/W	3,750 lm	240
911401536732	RC160V LED37/965 W60L60 PSU	6500 K	125 lm/W	3,750 lm	240
911401537432	RC160V LED35/930 W60L60 PSU 54	3000 K	118 lm/W	3,500 lm	240

Order Code	Full Product Name	Correlated Color		Number of light sources	
		Temperature (Nom)	Luminous Efficacy (rated) (Nom)		
911401537532	RC160V LED37/940 W60L60 PSU 54	4000 K	125 lm/W	3,750 lm	240
911401537632	RC160V LED37/965 W60L60 PSU 54	6500 K	125 lm/W	3,750 lm	240
911401538332	RC160V LED35/930 W60L60 PSD	3000 K	118 lm/W	3,500 lm	240
911401538432	RC160V LED37/940 W60L60 PSD	4000 K	125 lm/W	3,750 lm	240
911401538532	RC160V LED37/965 W60L60 PSD	6500 K	125 lm/W	3,750 lm	240
911401539232	RC160X LED35/930 W60L60 WIA	3000 K	118 lm/W	3,500 lm	240
911401539332	RC160X LED37/940 W60L60 WIA	4000 K	125 lm/W	3,750 lm	240
911401539432	RC160X LED37/965 W60L60 WIA	6500 K	125 lm/W	3,750 lm	240
911401539832	RC160X LED35/930 W60L60 SIA	3000 K	118 lm/W	3,500 lm	240
911401539932	RC160X LED37/940 W60L60 SIA	4000 K	125 lm/W	3,750 lm	240
91140154003 2	RC160X LED37/965 W60L60 SIA	6500 K	125 lm/W	3,750 lm	240
911401540732	RC160V LED35/930 W60L60 PSU CAU	3000 K	118 lm/W	3,500 lm	240
911401540832	RC160V LED37/940 W60L60 PSU CAU	4000 K	125 lm/W	3,750 lm	240
91140154093 2	RC160V LED37/965 W60L60 PSU CAU	6500 K	125 lm/W	3,750 lm	240
911401541632	RC160V LED35/930 W60L60 PSD CAU	3000 K	118 lm/W	3,500 lm	240
911401541732	RC160V LED37/940 W60L60 PSD CAU	4000 K	125 lm/W	3,750 lm	240
911401541832	RC160V LED37/965 W60L60 PSD CAU	6500 K	125 lm/W	3,750 lm	240
911401542532	RC160X LED35/930 W60L60 WIA CAU	3000 K	118 lm/W	3,500 lm	240
911401542632	RC160X LED37/940 W60L60 WIA CAU	4000 K	125 lm/W	3,750 lm	240
911401542732	RC160X LED37/965 W60L60 WIA CAU	6500 K	125 lm/W	3,750 lm	240
911401543132	RC160X LED35/930 W60L60 SIA CAU	3000 K	118 lm/W	3,500 lm	240
911401543232	RC160X LED37/940 W60L60 SIA CAU	4000 K	125 lm/W	3,750 lm	240
911401543332	RC160X LED37/965 W60L60 SIA CAU	6500 K	125 lm/W	3,750 lm	240
911401544032	RC160V LED35/930 W60L60 PSU 54 CAU	3000 K	118 lm/W	3,500 lm	240
911401544132	RC160V LED37/940 W60L60 PSU 54 CAU	4000 K	125 lm/W	3,750 lm	240

Order Code	Full Product Name	Correlated Color		Number of light sources
		Temperature (Nom)	Luminous Efficacy (rated) (Nom)	
911401544232	RC160V LED37/965 W60L60 PSU 54 CAU	6500 K	125 lm/W	3,750 lm
911401545532	RC160V LED36/9TW W60L60	2700 K	120 lm/W	3,600 lm
911401545832	RC160V LED36/9TW W60L60 54	2700 K	120 lm/W	3,600 lm
911401546132	RC160V LED36/9TW W60L60 CAU	2700 K	120 lm/W	3,600 lm
911401546432	RC160V LED36/9TW W60L60 54 CAU	2700 K	120 lm/W	3,600 lm
911401578642	RC160V LED37/830 W603L603 PSU OC UVG	3000 K	122 lm/W	3,700 lm
911401578742	RC160V LED39/840 W603L603 PSU OC UVG	4000 K	130 lm/W	3,900 lm
911401578842	RC160V LED39/865 W603L603 PSU OC UVG	6500 K	130 lm/W	3,900 lm

## Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
911401505543	RC160V LED37/940 W303L1210 PSU OC UVG	30 W	911401521932	RC160V LED39/840 W30L120 PSD OC	30 W
911401505643	RC160V LED37/965 W303L1210 PSU OC UVG	30 W	911401522032	RC160V LED39/865 W30L120 PSD OC	30 W
911401510132	RC160V LED37/830 W30L120 PSU	30 W	911401522732	RC160V LED27/830 W30L120 PSD 16	22 W
911401510232	RC160V LED39/840 W30L120 PSU	30 W	911401522832	RC160V LED29/840 W30L120 PSD 16	22 W
911401510332	RC160V LED39/865 W30L120 PSU	30 W	911401522932	RC160V LED29/865 W30L120 PSD 16	22 W
911401511032	RC160V LED37/830 W30L120 PSU OC	30 W	911401523632	RC160X LED37/830 W30L120 WIA	30 W
911401511132	RC160V LED39/840 W30L120 PSU OC	30 W	911401523732	RC160X LED39/840 W30L120 WIA	30 W
911401511232	RC160V LED39/865 W30L120 PSU OC	30 W	911401523832	RC160X LED39/865 W30L120 WIA	30 W
911401511932	RC160V LED27/830 W30L120 PSU 16	22 W	911401524832	RC160X LED37/830 W30L120 SIA	30 W
911401512032	RC160V LED29/840 W30L120 PSU 16	22 W	911401524932	RC160X LED39/840 W30L120 SIA	30 W
911401512132	RC160V LED29/865 W30L120 PSU 16	22 W	911401525032	RC160X LED39/865 W30L120 SIA	30 W
911401512832	RC160V LED37/830 W30L120 PSU 54	30 W	911401525532	RC160V LED38/8TW W30L120	30 W
911401512932	RC160V LED39/840 W30L120 PSU 54	30 W	911401526032	RC160V LED37/830 W30L120 PSU CAU	30 W
911401513032	RC160V LED39/865 W30L120 PSU 54	30 W	911401526132	RC160V LED39/840 W30L120 PSU CAU	30 W
911401513732	RC160V LED37/830 W30L120 PSU OC 54	30 W	911401526232	RC160V LED39/865 W30L120 PSU CAU	30 W
911401513832	RC160V LED39/840 W30L120 PSU OC 54	30 W	911401526932	RC160V LED37/830 W30L120 PSD CAU	30 W
911401513932	RC160V LED39/865 W30L120 PSU OC 54	30 W	911401527032	RC160V LED39/840 W30L120 PSD CAU	30 W
911401514632	RC160V LED27/830 W30L120 PSU 16 54	22 W	911401527132	RC160V LED39/865 W30L120 PSD CAU	30 W
911401514732	RC160V LED29/840 W30L120 PSU 16 54	22 W	911401527832	RC160X LED37/830 W30L120 WIA CAU	30 W
911401514832	RC160V LED29/865 W30L120 PSU 16 54	22 W	911401527932	RC160X LED39/840 W30L120 WIA CAU	30 W
911401516432	RC160V LED37/830 W30L120 PSU OC CPC	30 W	911401528032	RC160X LED39/865 W30L120 WIA CAU	30 W
911401516532	RC160V LED39/840 W30L120 PSU OC CPC	30 W	911401528432	RC160X LED37/830 W30L120 SIA CAU	30 W
911401516632	RC160V LED39/865 W30L120 PSU OC CPC	30 W	911401528532	RC160X LED39/840 W30L120 SIA CAU	30 W
911401519132	RC160V LED37/830 W30L120 PSU OC 54 CPC	30 W	911401528632	RC160X LED39/865 W30L120 SIA CAU	30 W
911401519232	RC160V LED39/840 W30L120 PSU OC 54 CPC	30 W	911401529332	RC160V LED37/830 W30L120 PSU OC CAU	30 W
911401519332	RC160V LED39/865 W30L120 PSU OC 54 CPC	30 W	911401529432	RC160V LED39/840 W30L120 PSU OC CAU	30 W
911401520932	RC160V LED37/830 W30L120 PSD	30 W	911401529532	RC160V LED39/865 W30L120 PSU OC CAU	30 W
911401521032	RC160V LED39/840 W30L120 PSD	30 W	911401530232	RC160V LED37/830 W30L120 PSD OC CAU	30 W
911401521132	RC160V LED39/865 W30L120 PSD	30 W	911401530332	RC160V LED39/840 W30L120 PSD OC CAU	30 W
911401521832	RC160V LED37/830 W30L120 PSD OC	30 W	911401530432	RC160V LED39/865 W30L120 PSD OC CAU	30 W

# RC160V

Order Code	Full Product Name	Power Consumption
911401531432	RC160V LED27/830 W30L120 PSU 16 CAU	22 W
911401531532	RC160V LED29/840 W30L120 PSU 16 CAU	22 W
911401531632	RC160V LED29/865 W30L120 PSU 16 CAU	22 W
911401532332	RC160V LED27/830 W30L120 PSD 16 CAU	22 W
911401532432	RC160V LED29/840 W30L120 PSD 16 CAU	22 W
911401532532	RC160V LED29/865 W30L120 PSD 16 CAU	22 W
911401533532	RC160V LED37/830 W30L120 PSU 54 CAU	30 W
911401533632	RC160V LED39/840 W30L120 PSU 54 CAU	30 W
911401533732	RC160V LED39/865 W30L120 PSU 54 CAU	30 W
911401534432	RC160V LED37/830 W30L120 PSU OC 54 CAU	30 W
911401534532	RC160V LED39/840 W30L120 PSU OC 54 CAU	30 W
911401534632	RC160V LED39/865 W30L120 PSU OC 54 CAU	30 W
911401535332	RC160V LED27/830 W30L120 PSU 16 54 CAU	22 W
911401535432	RC160V LED29/840 W30L120 PSU 16 54 CAU	22 W
911401535532	RC160V LED29/865 W30L120 PSU 16 54 CAU	22 W
911401536232	RC160V LED37/830 W30L1210 PSU UVG	30 W
911401536332	RC160V LED39/840 W30L1210 PSU UVG	30 W
911401536432	RC160V LED39/865 W30L1210 PSU UVG	30 W
911401536832	RC160V LED35/930 W30L120 PSU	30 W
911401536932	RC160V LED37/940 W30L120 PSU	30 W
911401537032	RC160V LED37/965 W30L120 PSU	30 W
911401537732	RC160V LED35/930 W30L120 PSU 54	30 W
911401537832	RC160V LED37/940 W30L120 PSU 54	30 W
911401537932	RC160V LED37/965 W30L120 PSU 54	30 W
911401538632	RC160V LED35/930 W30L120 PSD	30 W
911401538732	RC160V LED37/940 W30L120 PSD	30 W
911401538832	RC160V LED37/965 W30L120 PSD	30 W
911401539532	RC160X LED35/930 W30L120 WIA	30 W
911401539632	RC160X LED37/940 W30L120 WIA	30 W
911401539732	RC160X LED37/965 W30L120 WIA	30 W
911401540132	RC160X LED35/930 W30L120 SIA	30 W
911401540232	RC160X LED37/940 W30L120 SIA	30 W
911401540332	RC160X LED37/965 W30L120 SIA	30 W
911401541032	RC160V LED35/930 W30L120 PSU CAU	30 W
911401541132	RC160V LED37/940 W30L120 PSU CAU	30 W
911401541232	RC160V LED37/965 W30L120 PSU CAU	30 W
911401541932	RC160V LED35/930 W30L120 PSD CAU	30 W
911401542032	RC160V LED37/940 W30L120 PSD CAU	30 W
911401542132	RC160V LED37/965 W30L120 PSD CAU	30 W
911401542832	RC160X LED35/930 W30L120 WIA CAU	30 W
911401542932	RC160X LED37/940 W30L120 WIA CAU	30 W
911401543032	RC160X LED37/965 W30L120 WIA CAU	30 W
911401543432	RC160X LED35/930 W30L120 SIA CAU	30 W
911401543532	RC160X LED37/940 W30L120 SIA CAU	30 W
911401543632	RC160X LED37/965 W30L120 SIA CAU	30 W
911401544332	RC160V LED35/930 W30L120 PSU 54 CAU	30 W
911401544432	RC160V LED37/940 W30L120 PSU 54 CAU	30 W
911401544532	RC160V LED37/965 W30L120 PSU 54 CAU	30 W
911401545632	RC160V LED37/9TW W30L120	30 W
911401545932	RC160V LED37/9TW W30L120 54	30 W
911401546232	RC160V LED37/9TW W30L120 CAU	30 W
911401546532	RC160V LED37/9TW W30L120 54 CAU	30 W

Order Code	Full Product Name	Power Consumption
911401578942	RC160V LED37/830 W30L1210 PSU OC UVG	30 W
911401579042	RC160V LED39/840 W30L1210 PSU OC UVG	30 W
911401579142	RC160V LED39/865 W30L1210 PSU OC UVG	30 W
911401510432	RC160V LED57/830 W60L120 PSU	46 W
911401510532	RC160V LED60/840 W60L120 PSU	46 W
911401510632	RC160V LED60/865 W60L120 PSU	46 W
911401511332	RC160V LED57/830 W60L120 PSU OC	46 W
911401511432	RC160V LED60/840 W60L120 PSU OC	46 W
911401511532	RC160V LED60/865 W60L120 PSU OC	46 W
911401512232	RC160V LED54/830 W60L120 PSU 16	46 W
911401512332	RC160V LED58/840 W60L120 PSU 16	46 W
911401512432	RC160V LED58/865 W60L120 PSU 16	46 W
911401513132	RC160V LED57/830 W60L120 PSU 54	46 W
911401513232	RC160V LED60/840 W60L120 PSU 54	46 W
911401513332	RC160V LED60/865 W60L120 PSU 54	46 W
911401514032	RC160V LED57/830 W60L120 PSU OC 54	46 W
911401514132	RC160V LED60/840 W60L120 PSU OC 54	46 W
911401514232	RC160V LED60/865 W60L120 PSU OC 54	46 W
911401514932	RC160V LED54/830 W60L120 PSU 16 54	46 W
911401515032	RC160V LED58/840 W60L120 PSU 16 54	46 W
911401515132	RC160V LED58/865 W60L120 PSU 16 54	46 W
911401521232	RC160V LED57/830 W60L120 PSD	46 W
911401521332	RC160V LED60/840 W60L120 PSD	46 W
911401521432	RC160V LED60/865 W60L120 PSD	46 W
911401522132	RC160V LED57/830 W60L120 PSD OC	46 W
911401522232	RC160V LED60/840 W60L120 PSD OC	46 W
911401522332	RC160V LED60/865 W60L120 PSD OC	46 W
911401523032	RC160V LED54/830 W60L120 PSD 16	46 W
911401523132	RC160V LED58/840 W60L120 PSD 16	46 W
911401523232	RC160V LED58/865 W60L120 PSD 16	46 W
911401525132	RC160X LED57/830 W60L120 SIA	46 W
911401525232	RC160X LED60/840 W60L120 SIA	46 W
911401525332	RC160X LED60/865 W60L120 SIA	46 W
911401526332	RC160V LED57/830 W60L120 PSU CAU	46 W
911401526432	RC160V LED60/840 W60L120 PSU CAU	46 W
911401526532	RC160V LED60/865 W60L120 PSU CAU	46 W
911401527232	RC160V LED57/830 W60L120 PSD CAU	46 W
911401527332	RC160V LED60/840 W60L120 PSD CAU	46 W
911401527432	RC160V LED60/865 W60L120 PSD CAU	46 W
911401528732	RC160X LED57/830 W60L120 SIA CAU	46 W
911401528832	RC160X LED60/840 W60L120 SIA CAU	46 W
911401528932	RC160X LED60/865 W60L120 SIA CAU	46 W
911401529632	RC160V LED57/830 W60L120 PSU OC CAU	46 W
911401529732	RC160V LED60/840 W60L120 PSU OC CAU	46 W
911401529832	RC160V LED60/865 W60L120 PSU OC CAU	46 W
911401530532	RC160V LED57/830 W60L120 PSD OC CAU	46 W
911401530632	RC160V LED60/840 W60L120 PSD OC CAU	46 W
911401530732	RC160V LED60/865 W60L120 PSD OC CAU	46 W
911401531732	RC160V LED54/830 W60L120 PSU 16 CAU	46 W
911401531832	RC160V LED58/840 W60L120 PSU 16 CAU	46 W
911401531932	RC160V LED58/865 W60L120 PSU 16 CAU	46 W
911401532632	RC160V LED54/830 W60L120 PSD 16 CAU	46 W

# RC160V

Order Code	Full Product Name	Power Consumption
911401532732	RC160V LED58/840 W60L120 PSD 16 CAU	46 W
911401532832	RC160V LED58/865 W60L120 PSD 16 CAU	46 W
911401533832	RC160V LED57/830 W60L120 PSU 54 CAU	46 W
911401533932	RC160V LED60/840 W60L120 PSU 54 CAU	46 W
911401534032	RC160V LED60/865 W60L120 PSU 54 CAU	46 W
911401534732	RC160V LED57/830 W60L120 PSU OC 54 CAU	46 W
911401534832	RC160V LED60/840 W60L120 PSU OC 54 CAU	46 W
911401534932	RC160V LED60/865 W60L120 PSU OC 54 CAU	46 W
911401535632	RC160V LED54/830 W60L120 PSU 16 54 CAU	46 W
911401535732	RC160V LED58/840 W60L120 PSU 16 54 CAU	46 W
911401535832	RC160V LED58/865 W60L120 PSU 16 54 CAU	46 W
911401537132	RC160V LED54/930 W60L120 PSU	46 W
911401537232	RC160V LED58/940 W60L120 PSU	46 W
911401537332	RC160V LED58/965 W60L120 PSU	46 W
911401538032	RC160V LED54/930 W60L120 PSU 54	46 W
911401538132	RC160V LED58/940 W60L120 PSU 54	46 W
911401538232	RC160V LED58/965 W60L120 PSU 54	46 W
911401538932	RC160V LED54/930 W60L120 PSD	46 W
911401539032	RC160V LED58/940 W60L120 PSD	46 W
911401539132	RC160V LED58/965 W60L120 PSD	46 W
911401540432	RC160X LED54/930 W60L120 SIA	46 W
911401540532	RC160X LED58/940 W60L120 SIA	46 W
911401540632	RC160X LED58/965 W60L120 SIA	46 W
911401541332	RC160V LED54/930 W60L120 PSU CAU	46 W
911401541432	RC160V LED58/940 W60L120 PSU CAU	46 W
911401541532	RC160V LED58/965 W60L120 PSU CAU	46 W
911401542232	RC160V LED54/930 W60L120 PSD CAU	46 W
911401542332	RC160V LED58/940 W60L120 PSD CAU	46 W
911401542432	RC160V LED58/965 W60L120 PSD CAU	46 W
911401543732	RC160X LED54/930 W60L120 SIA CAU	46 W
911401543832	RC160X LED58/940 W60L120 SIA CAU	46 W
911401543932	RC160X LED58/965 W60L120 SIA CAU	46 W
911401544632	RC160V LED54/930 W60L120 PSU 54 CAU	46 W
911401544732	RC160V LED58/940 W60L120 PSU 54 CAU	46 W
911401544832	RC160V LED58/965 W60L120 PSU 54 CAU	46 W
911401544932	RC160X LED48/930 W60L120 WIA	40 W
911401545032	RC160X LED51/940 W60L120 WIA	40 W
911401545132	RC160X LED51/965 W60L120 WIA	40 W
911401545232	RC160X LED48/930 W60L120 WIA CAU	40 W
911401545332	RC160X LED51/940 W60L120 WIA CAU	40 W
911401545432	RC160X LED51/965 W60L120 WIA CAU	40 W
911401505343	RC160V LED37/940 W603L603 PSU OC UVG	30 W
911401505443	RC160V LED37/965 W603L603 PSU OC UVG	30 W
911401509832	RC160V LED37/830 W60L60 PSU	30 W
911401509932	RC160V LED39/840 W60L60 PSU	30 W
911401510032	RC160V LED39/865 W60L60 PSU	30 W
911401510732	RC160V LED37/830 W60L60 PSU OC	30 W
911401510832	RC160V LED39/840 W60L60 PSU OC	30 W
911401510932	RC160V LED39/865 W60L60 PSU OC	30 W
911401511632	RC160V LED27/830 W60L60 PSU 16	22 W
911401511732	RC160V LED29/840 W60L60 PSU 16	22 W
911401511832	RC160V LED29/865 W60L60 PSU 16	22 W

Order Code	Full Product Name	Power Consumption
911401512532	RC160V LED37/830 W60L60 PSU 54	30 W
911401512632	RC160V LED39/840 W60L60 PSU 54	30 W
911401512732	RC160V LED39/865 W60L60 PSU 54	30 W
911401513432	RC160V LED37/830 W60L60 PSU OC 54	30 W
911401513532	RC160V LED39/840 W60L60 PSU OC 54	30 W
911401513632	RC160V LED39/865 W60L60 PSU OC 54	30 W
911401514332	RC160V LED27/830 W60L60 PSU 16 54	22 W
911401514432	RC160V LED29/840 W60L60 PSU 16 54	22 W
911401514532	RC160V LED29/865 W60L60 PSU 16 54	22 W
911401516132	RC160V LED37/830 W60L60 PSU OC CPC	30 W
911401516232	RC160V LED39/840 W60L60 PSU OC CPC	30 W
911401516332	RC160V LED39/865 W60L60 PSU OC CPC	30 W
911401518832	RC160V LED37/830 W60L60 PSU OC 54 CPC	30 W
911401518932	RC160V LED39/840 W60L60 PSU OC 54 CPC	30 W
911401519032	RC160V LED39/865 W60L60 PSU OC 54 CPC	30 W
911401520632	RC160V LED37/830 W60L60 PSD	30 W
911401520732	RC160V LED39/840 W60L60 PSD	30 W
911401520832	RC160V LED39/865 W60L60 PSD	30 W
911401521532	RC160V LED37/830 W60L60 PSD OC	30 W
911401521632	RC160V LED39/840 W60L60 PSD OC	30 W
911401521732	RC160V LED39/865 W60L60 PSD OC	30 W
911401522432	RC160V LED27/830 W60L60 PSD 16	22 W
911401522532	RC160V LED29/840 W60L60 PSD 16	22 W
911401522632	RC160V LED29/865 W60L60 PSD 16	22 W
911401523332	RC160X LED37/830 W60L60 WIA	30 W
911401523432	RC160X LED39/840 W60L60 WIA	30 W
911401523532	RC160X LED39/865 W60L60 WIA	30 W
911401523932	RC160X LED37/830 W60L60 WIA OC	30 W
911401524032	RC160X LED39/840 W60L60 WIA OC	30 W
911401524132	RC160X LED39/865 W60L60 WIA OC	30 W
911401524232	RC160X LED27/830 W60L60 WIA 16	22 W
911401524332	RC160X LED29/840 W60L60 WIA 16	22 W
911401524432	RC160X LED29/865 W60L60 WIA 16	22 W
911401524532	RC160X LED37/830 W60L60 SIA	30 W
911401524632	RC160X LED39/840 W60L60 SIA	30 W
911401524732	RC160X LED39/865 W60L60 SIA	30 W
911401525432	RC160V LED37/8TW W60L60	30 W
911401525732	RC160V LED37/830 W60L60 PSU CAU	30 W
911401525832	RC160V LED39/840 W60L60 PSU CAU	30 W
911401525932	RC160V LED39/865 W60L60 PSU CAU	30 W
911401526632	RC160V LED37/830 W60L60 PSD CAU	30 W
911401526732	RC160V LED39/840 W60L60 PSD CAU	30 W
911401526832	RC160V LED39/865 W60L60 PSD CAU	30 W
911401527532	RC160X LED37/830 W60L60 WIA CAU	30 W
911401527632	RC160X LED39/840 W60L60 WIA CAU	30 W
911401527732	RC160X LED39/865 W60L60 WIA CAU	30 W
911401528132	RC160X LED37/830 W60L60 SIA CAU	30 W
911401528232	RC160X LED39/840 W60L60 SIA CAU	30 W
911401528332	RC160X LED39/865 W60L60 SIA CAU	30 W
911401529032	RC160V LED37/830 W60L60 PSU OC CAU	30 W
911401529132	RC160V LED39/840 W60L60 PSU OC CAU	30 W
911401529232	RC160V LED39/865 W60L60 PSU OC CAU	30 W

# RC160V

Order Code	Full Product Name	Power Consumption
911401529932	RC160V LED37/830 W60L60 PSD OC CAU	30 W
911401530032	RC160V LED39/840 W60L60 PSD OC CAU	30 W
911401530132	RC160V LED39/865 W60L60 PSD OC CAU	30 W
911401530832	RC160X LED37/830 W60L60 WIA OC CAU	30 W
911401530932	RC160X LED39/840 W60L60 WIA OC CAU	30 W
911401531032	RC160X LED39/865 W60L60 WIA OC CAU	30 W
911401531132	RC160V LED27/830 W60L60 PSU 16 CAU	22 W
911401531232	RC160V LED29/840 W60L60 PSU 16 CAU	22 W
911401531332	RC160V LED29/865 W60L60 PSU 16 CAU	22 W
911401532032	RC160V LED27/830 W60L60 PSD 16 CAU	22 W
911401532132	RC160V LED29/840 W60L60 PSD 16 CAU	22 W
911401532232	RC160V LED29/865 W60L60 PSD 16 CAU	22 W
911401532932	RC160X LED27/830 W60L60 WIA 16 CAU	22 W
911401533032	RC160X LED29/840 W60L60 WIA 16 CAU	22 W
911401533132	RC160X LED29/865 W60L60 WIA 16 CAU	22 W
911401533232	RC160V LED37/830 W60L60 PSU 54 CAU	30 W
911401533332	RC160V LED39/840 W60L60 PSU 54 CAU	30 W
911401533432	RC160V LED39/865 W60L60 PSU 54 CAU	30 W
911401534132	RC160V LED37/830 W60L60 PSU OC 54 CAU	30 W
911401534232	RC160V LED39/840 W60L60 PSU OC 54 CAU	30 W
911401534332	RC160V LED39/865 W60L60 PSU OC 54 CAU	30 W
911401535032	RC160V LED27/830 W60L60 PSU 16 54 CAU	22 W
911401535132	RC160V LED29/840 W60L60 PSU 16 54 CAU	22 W
911401535232	RC160V LED29/865 W60L60 PSU 16 54 CAU	22 W
911401535932	RC160V LED37/830 W603L603 PSU UVG	30 W
911401536032	RC160V LED39/840 W603L603 PSU UVG	30 W
911401536132	RC160V LED39/865 W603L603 PSU UVG	30 W
911401536532	RC160V LED35/930 W60L60 PSU	30 W
911401536632	RC160V LED37/940 W60L60 PSU	30 W
911401536732	RC160V LED37/965 W60L60 PSU	30 W
911401537432	RC160V LED35/930 W60L60 PSU 54	30 W
911401537532	RC160V LED37/940 W60L60 PSU 54	30 W

Order Code	Full Product Name	Power Consumption
911401537632	RC160V LED37/965 W60L60 PSU 54	30 W
911401538332	RC160V LED35/930 W60L60 PSD	30 W
911401538432	RC160V LED37/940 W60L60 PSD	30 W
911401538532	RC160V LED37/965 W60L60 PSD	30 W
911401539232	RC160X LED35/930 W60L60 WIA	30 W
911401539332	RC160X LED37/940 W60L60 WIA	30 W
911401539432	RC160X LED37/965 W60L60 WIA	30 W
911401539832	RC160X LED35/930 W60L60 SIA	30 W
911401539932	RC160X LED37/940 W60L60 SIA	30 W
911401540032	RC160X LED37/965 W60L60 SIA	30 W
911401540732	RC160V LED35/930 W60L60 PSU CAU	30 W
911401540832	RC160V LED37/940 W60L60 PSU CAU	30 W
911401540932	RC160V LED37/965 W60L60 PSU CAU	30 W
911401541632	RC160V LED35/930 W60L60 PSD CAU	30 W
911401541732	RC160V LED37/940 W60L60 PSD CAU	30 W
911401541832	RC160V LED37/965 W60L60 PSD CAU	30 W
911401542532	RC160X LED35/930 W60L60 WIA CAU	30 W
911401542632	RC160X LED37/940 W60L60 WIA CAU	30 W
911401542732	RC160X LED37/965 W60L60 WIA CAU	30 W
911401543132	RC160X LED35/930 W60L60 SIA CAU	30 W
911401543232	RC160X LED37/940 W60L60 SIA CAU	30 W
911401543332	RC160X LED37/965 W60L60 SIA CAU	30 W
911401544032	RC160V LED35/930 W60L60 PSU 54 CAU	30 W
911401544132	RC160V LED37/940 W60L60 PSU 54 CAU	30 W
911401544232	RC160V LED37/965 W60L60 PSU 54 CAU	30 W
911401545532	RC160V LED36/9TW W60L60	30 W
911401545832	RC160V LED36/9TW W60L60 54	30 W
911401546132	RC160V LED36/9TW W60L60 CAU	30 W
911401546432	RC160V LED36/9TW W60L60 54 CAU	30 W
911401578642	RC160V LED37/830 W603L603 PSU OC UVG	30 W
911401578742	RC160V LED39/840 W603L603 PSU OC UVG	30 W
911401578842	RC160V LED39/865 W603L603 PSU OC UVG	30 W

## Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
911401505543	RC160V LED37/940 W303L1210 PSU OC UVG	Fixed	0% (digital)
911401505643	RC160V LED37/965 W303L1210 PSU OC UVG	Fixed	0% (digital)
911401510132	RC160V LED37/830 W30L120 PSU	Fixed	0% (digital)
911401510232	RC160V LED39/840 W30L120 PSU	Fixed	0% (digital)
911401510332	RC160V LED39/865 W30L120 PSU	Fixed	0% (digital)
911401511032	RC160V LED37/830 W30L120 PSU OC	Fixed	0% (digital)
911401511132	RC160V LED39/840 W30L120 PSU OC	Fixed	0% (digital)
911401511232	RC160V LED39/865 W30L120 PSU OC	Fixed	0% (digital)
911401511932	RC160V LED27/830 W30L120 PSU 16	Fixed	0% (digital)
911401512032	RC160V LED29/840 W30L120 PSU 16	Fixed	0% (digital)

Order Code	Full Product Name	Dimmable	Maximum dim level
911401512132	RC160V LED29/865 W30L120 PSU 16	Fixed	0% (digital)
911401512832	RC160V LED37/830 W30L120 PSU 54	Fixed	0% (digital)
911401512932	RC160V LED39/840 W30L120 PSU 54	Fixed	0% (digital)
911401513032	RC160V LED39/865 W30L120 PSU 54	Fixed	0% (digital)
911401513732	RC160V LED37/830 W30L120 PSU OC 54	Fixed	0% (digital)
911401513832	RC160V LED39/840 W30L120 PSU OC 54	Fixed	0% (digital)
911401513932	RC160V LED39/865 W30L120 PSU OC 54	Fixed	0% (digital)
911401514632	RC160V LED27/830 W30L120 PSU 16 54	Fixed	0% (digital)

# RC160V

Order Code	Full Product Name	Dimmable	Maximum dim level
911401514732	RC160V LED29/840 W30L120 PSU 16 54	Fixed	0% (digital)
911401514832	RC160V LED29/865 W30L120 PSU 16 54	Fixed	0% (digital)
911401516432	RC160V LED37/830 W30L120 PSU OC CPC	Fixed	0% (digital)
911401516532	RC160V LED39/840 W30L120 PSU OC CPC	Fixed	0% (digital)
911401516632	RC160V LED39/865 W30L120 PSU OC CPC	Fixed	0% (digital)
911401519132	RC160V LED37/830 W30L120 PSU OC 54 CPC	Fixed	0% (digital)
911401519232	RC160V LED39/840 W30L120 PSU OC 54 CPC	Fixed	0% (digital)
911401519332	RC160V LED39/865 W30L120 PSU OC 54 CPC	Fixed	0% (digital)
911401520932	RC160V LED37/830 W30L120 PSD	DALI	Programmable
911401521032	RC160V LED39/840 W30L120 PSD	DALI	Programmable
911401521132	RC160V LED39/865 W30L120 PSD	DALI	Programmable
911401521832	RC160V LED37/830 W30L120 PSD OC	DALI	Programmable
911401521932	RC160V LED39/840 W30L120 PSD OC	DALI	Programmable
911401522032	RC160V LED39/865 W30L120 PSD OC	DALI	Programmable
911401522732	RC160V LED27/830 W30L120 PSD 16	DALI	Programmable
911401522832	RC160V LED29/840 W30L120 PSD 16	DALI	Programmable
911401522932	RC160V LED29/865 W30L120 PSD 16	DALI	Programmable
911401523632	RC160X LED37/830 W30L120 WIA	Wireless Dim	Programmable
911401523732	RC160X LED39/840 W30L120 WIA	Wireless Dim	Programmable
911401523832	RC160X LED39/865 W30L120 WIA	Wireless Dim	Programmable
911401524832	RC160X LED37/830 W30L120 SIA	Auto-Dim	0% (digital)
911401524932	RC160X LED39/840 W30L120 SIA	Auto-Dim	0% (digital)
911401525032	RC160X LED39/865 W30L120 SIA	Auto-Dim	0% (digital)
911401525532	RC160V LED38/8TW W30L120	DALI	Programmable
911401526032	RC160V LED37/830 W30L120 PSU CAU	Fixed	0% (digital)
911401526132	RC160V LED39/840 W30L120 PSU CAU	Fixed	0% (digital)
911401526232	RC160V LED39/865 W30L120 PSU CAU	Fixed	0% (digital)
911401526932	RC160V LED37/830 W30L120 PSD CAU	DALI	Programmable
911401527032	RC160V LED39/840 W30L120 PSD CAU	DALI	Programmable
911401527132	RC160V LED39/865 W30L120 PSD CAU	DALI	Programmable
911401527832	RC160X LED37/830 W30L120 WIA CAU	Wireless Dim	Programmable

Order Code	Full Product Name	Dimmable	Maximum dim level
911401527932	RC160X LED39/840 W30L120 WIA CAU	Wireless Dim	Programmable
911401528032	RC160X LED39/865 W30L120 WIA CAU	Wireless Dim	Programmable
911401528432	RC160X LED37/830 W30L120 SIA CAU	Auto-Dim	0% (digital)
911401528532	RC160X LED39/840 W30L120 SIA CAU	Auto-Dim	0% (digital)
911401528632	RC160X LED39/865 W30L120 SIA CAU	Auto-Dim	0% (digital)
911401529332	RC160V LED37/830 W30L120 PSU OC CAU	Fixed	0% (digital)
911401529432	RC160V LED39/840 W30L120 PSU OC CAU	Fixed	0% (digital)
911401529532	RC160V LED39/865 W30L120 PSU OC CAU	Fixed	0% (digital)
911401530232	RC160V LED37/830 W30L120 PSD OC CAU	DALI	Programmable
911401530332	RC160V LED39/840 W30L120 PSD OC CAU	DALI	Programmable
911401530432	RC160V LED39/865 W30L120 PSD OC CAU	DALI	Programmable
911401531432	RC160V LED27/830 W30L120 PSU 16 CAU	Fixed	0% (digital)
911401531532	RC160V LED29/840 W30L120 PSU 16 CAU	Fixed	0% (digital)
911401531632	RC160V LED29/865 W30L120 PSU 16 CAU	Fixed	0% (digital)
911401532332	RC160V LED27/830 W30L120 PSD 16 CAU	DALI	Programmable
911401532432	RC160V LED29/840 W30L120 PSD 16 CAU	DALI	Programmable
911401532532	RC160V LED29/865 W30L120 PSD 16 CAU	DALI	Programmable
911401533532	RC160V LED37/830 W30L120 PSU 54 CAU	Fixed	0% (digital)
911401533632	RC160V LED39/840 W30L120 PSU 54 CAU	Fixed	0% (digital)
911401533732	RC160V LED39/865 W30L120 PSU 54 CAU	Fixed	0% (digital)
911401534432	RC160V LED37/830 W30L120 PSU OC 54 CAU	Fixed	0% (digital)
911401534532	RC160V LED39/840 W30L120 PSU OC 54 CAU	Fixed	0% (digital)
911401534632	RC160V LED39/865 W30L120 PSU OC 54 CAU	Fixed	0% (digital)
911401535332	RC160V LED27/830 W30L120 PSU 54 CAU	Fixed	0% (digital)
911401535432	RC160V LED29/840 W30L120 PSU 16 54 CAU	Fixed	0% (digital)
911401535532	RC160V LED29/865 W30L120 PSU 16 54 CAU	Fixed	0% (digital)

# RC160V

Order Code	Full Product Name	Dimmable	Maximum dim level
911401536232	RC160V LED37/830 W303L1210 PSU UVG	Fixed	0% (digital)
911401536332	RC160V LED39/840 W303L1210 PSU UVG	Fixed	0% (digital)
911401536432	RC160V LED39/865 W303L1210 PSU UVG	Fixed	0% (digital)
911401536832	RC160V LED35/930 W30L120 PSU	Fixed	0% (digital)
911401536932	RC160V LED37/940 W30L120 PSU	Fixed	0% (digital)
911401537032	RC160V LED37/965 W30L120 PSU	Fixed	0% (digital)
911401537732	RC160V LED35/930 W30L120 PSU 54	Fixed	0% (digital)
911401537832	RC160V LED37/940 W30L120 PSU 54	Fixed	0% (digital)
911401537932	RC160V LED37/965 W30L120 PSU 54	Fixed	0% (digital)
911401538632	RC160V LED35/930 W30L120 PSD	DALI	Programmable
911401538732	RC160V LED37/940 W30L120 PSD	DALI	Programmable
911401538832	RC160V LED37/965 W30L120 PSD	DALI	Programmable
911401539532	RC160X LED35/930 W30L120 WIA	Wireless Dim	Programmable
911401539632	RC160X LED37/940 W30L120 WIA	Wireless Dim	Programmable
911401539732	RC160X LED37/965 W30L120 WIA	Wireless Dim	Programmable
911401540132	RC160X LED35/930 W30L120 SIA	Auto-Dim	0% (digital)
911401540232	RC160X LED37/940 W30L120 SIA	Auto-Dim	0% (digital)
911401540332	RC160X LED37/965 W30L120 SIA	Auto-Dim	0% (digital)
911401541032	RC160V LED35/930 W30L120 PSU CAU	Fixed	0% (digital)
911401541132	RC160V LED37/940 W30L120 PSU CAU	Fixed	0% (digital)
911401541232	RC160V LED37/965 W30L120 PSU CAU	Fixed	0% (digital)
911401541932	RC160V LED35/930 W30L120 PSD CAU	DALI	Programmable
911401542032	RC160V LED37/940 W30L120 PSD CAU	DALI	Programmable
911401542132	RC160V LED37/965 W30L120 PSD CAU	DALI	Programmable
911401542832	RC160X LED35/930 W30L120 WIA CAU	Wireless Dim	Programmable
911401542932	RC160X LED37/940 W30L120 WIA CAU	Wireless Dim	Programmable
911401543032	RC160X LED37/965 W30L120 WIA CAU	Wireless Dim	Programmable
911401543432	RC160X LED35/930 W30L120 SIA CAU	Auto-Dim	0% (digital)
911401543532	RC160X LED37/940 W30L120 SIA CAU	Auto-Dim	0% (digital)
911401543632	RC160X LED37/965 W30L120 SIA CAU	Auto-Dim	0% (digital)
911401544332	RC160V LED35/930 W30L120 PSU 54 CAU	Fixed	0% (digital)
911401544432	RC160V LED37/940 W30L120 PSU 54 CAU	Fixed	0% (digital)

Order Code	Full Product Name	Dimmable	Maximum dim level
911401544532	RC160V LED37/965 W30L120 PSU 54 CAU	Fixed	0% (digital)
911401545632	RC160V LED37/9TW W30L120	DALI	Programmable
911401545932	RC160V LED37/9TW W30L120 54	DALI	Programmable
911401546232	RC160V LED37/9TW W30L120 CAU	DALI	Programmable
911401546532	RC160V LED37/9TW W30L120 54 CAU	DALI	Programmable
911401578942	RC160V LED37/830 W303L1210 PSU OC UVG	Fixed	0% (digital)
911401579042	RC160V LED39/840 W303L1210 PSU OC UVG	Fixed	0% (digital)
911401579142	RC160V LED39/865 W303L1210 PSU OC UVG	Fixed	0% (digital)
911401510432	RC160V LED57/830 W60L120 PSU	Fixed	0% (digital)
911401510532	RC160V LED60/840 W60L120 PSU	Fixed	0% (digital)
911401510632	RC160V LED60/865 W60L120 PSU	Fixed	0% (digital)
911401511332	RC160V LED57/830 W60L120 PSU OC	Fixed	0% (digital)
911401511432	RC160V LED60/840 W60L120 PSU OC	Fixed	0% (digital)
911401511532	RC160V LED60/865 W60L120 PSU OC	Fixed	0% (digital)
911401512232	RC160V LED54/830 W60L120 PSU 16	Fixed	0% (digital)
911401512332	RC160V LED58/840 W60L120 PSU 16	Fixed	0% (digital)
911401512432	RC160V LED58/865 W60L120 PSU 16	Fixed	0% (digital)
911401513132	RC160V LED57/830 W60L120 PSU 54	Fixed	0% (digital)
911401513232	RC160V LED60/840 W60L120 PSU 54	Fixed	0% (digital)
911401513332	RC160V LED60/865 W60L120 PSU 54	Fixed	0% (digital)
911401514032	RC160V LED57/830 W60L120 PSU OC 54	Fixed	0% (digital)
911401514132	RC160V LED60/840 W60L120 PSU OC 54	Fixed	0% (digital)
911401514232	RC160V LED60/865 W60L120 PSU OC 54	Fixed	0% (digital)
911401514932	RC160V LED54/830 W60L120 PSU 16 54	Fixed	0% (digital)
911401515032	RC160V LED58/840 W60L120 PSU 16 54	Fixed	0% (digital)
911401515132	RC160V LED58/865 W60L120 PSU 16 54	Fixed	0% (digital)
911401521232	RC160V LED57/830 W60L120 PSD DALI	DALI	Programmable
911401521332	RC160V LED60/840 W60L120 PSD DALI	DALI	Programmable
911401521432	RC160V LED60/865 W60L120 PSD DALI	DALI	Programmable
911401522132	RC160V LED57/830 W60L120 PSD OC DALI	DALI	Programmable

# RC160V

Order Code	Full Product Name	Dimmable	Maximum dim level
911401522232	RC160V LED60/840 W60L120 PSD OC	DALI	Programmable
911401522332	RC160V LED60/865 W60L120 PSD OC	DALI	Programmable
911401523032	RC160V LED54/830 W60L120 PSD 16	DALI	Programmable
911401523132	RC160V LED58/840 W60L120 PSD 16	DALI	Programmable
911401523232	RC160V LED58/865 W60L120 PSD 16	DALI	Programmable
911401525132	RC160X LED57/830 W60L120 SIA	Auto-Dim	0% (digital)
911401525232	RC160X LED60/840 W60L120 SIA	Auto-Dim	0% (digital)
911401525332	RC160X LED60/865 W60L120 SIA	Auto-Dim	0% (digital)
911401526332	RC160V LED57/830 W60L120 PSU CAU	Fixed	0% (digital)
911401526432	RC160V LED60/840 W60L120 PSU CAU	Fixed	0% (digital)
911401526532	RC160V LED60/865 W60L120 PSU CAU	Fixed	0% (digital)
911401527232	RC160V LED57/830 W60L120 PSD CAU	DALI	Programmable
911401527332	RC160V LED60/840 W60L120 PSD CAU	DALI	Programmable
911401527432	RC160V LED60/865 W60L120 PSD CAU	DALI	Programmable
911401528732	RC160X LED57/830 W60L120 SIA CAU	Auto-Dim	0% (digital)
911401528832	RC160X LED60/840 W60L120 SIA CAU	Auto-Dim	0% (digital)
911401528932	RC160X LED60/865 W60L120 SIA CAU	Auto-Dim	0% (digital)
911401529632	RC160V LED57/830 W60L120 PSU OC CAU	Fixed	0% (digital)
911401529732	RC160V LED60/840 W60L120 PSU OC CAU	Fixed	0% (digital)
911401529832	RC160V LED60/865 W60L120 PSU OC CAU	Fixed	0% (digital)
911401530532	RC160V LED57/830 W60L120 PSD OC CAU	DALI	Programmable
911401530632	RC160V LED60/840 W60L120 PSD OC CAU	DALI	Programmable
911401530732	RC160V LED60/865 W60L120 PSD OC CAU	DALI	Programmable
911401531732	RC160V LED54/830 W60L120 PSU 16 CAU	Fixed	0% (digital)
911401531832	RC160V LED58/840 W60L120 PSU 16 CAU	Fixed	0% (digital)
911401531932	RC160V LED58/865 W60L120 PSU 16 CAU	Fixed	0% (digital)
911401532632	RC160V LED54/830 W60L120 PSD 16 CAU	DALI	Programmable

Order Code	Full Product Name	Dimmable	Maximum dim level
911401532732	RC160V LED58/840 W60L120 PSD 16 CAU	DALI	Programmable
911401532832	RC160V LED58/865 W60L120 PSD 16 CAU	DALI	Programmable
911401533832	RC160V LED57/830 W60L120 PSU 54 CAU	Fixed	0% (digital)
911401533932	RC160V LED60/840 W60L120 PSU 54 CAU	Fixed	0% (digital)
911401534032	RC160V LED60/865 W60L120 PSU 54 CAU	Fixed	0% (digital)
911401534732	RC160V LED57/830 W60L120 PSU OC 54 CAU	Fixed	0% (digital)
911401534832	RC160V LED60/840 W60L120 PSU OC 54 CAU	Fixed	0% (digital)
911401534932	RC160V LED60/865 W60L120 PSU OC 54 CAU	Fixed	0% (digital)
911401535632	RC160V LED54/830 W60L120 PSU 16 54 CAU	Fixed	0% (digital)
911401535732	RC160V LED58/840 W60L120 PSU 16 54 CAU	Fixed	0% (digital)
911401535832	RC160V LED58/865 W60L120 PSU 16 54 CAU	Fixed	0% (digital)
911401537132	RC160V LED54/930 W60L120 PSU	Fixed	0% (digital)
911401537232	RC160V LED58/940 W60L120 PSU	Fixed	0% (digital)
911401537332	RC160V LED58/965 W60L120 PSU	Fixed	0% (digital)
911401538032	RC160V LED54/930 W60L120 PSU 54	Fixed	0% (digital)
911401538132	RC160V LED58/940 W60L120 PSU 54	Fixed	0% (digital)
911401538232	RC160V LED58/965 W60L120 PSU 54	Fixed	0% (digital)
911401538932	RC160V LED54/930 W60L120 PSD	DALI	Programmable
911401539032	RC160V LED58/940 W60L120 PSD	DALI	Programmable
911401539132	RC160V LED58/965 W60L120 PSD	DALI	Programmable
911401540432	RC160X LED54/930 W60L120 SIA	Auto-Dim	0% (digital)
911401540532	RC160X LED58/940 W60L120 SIA	Auto-Dim	0% (digital)
911401540632	RC160X LED58/965 W60L120 SIA	Auto-Dim	0% (digital)
911401541332	RC160V LED54/930 W60L120 PSU CAU	Fixed	0% (digital)
911401541432	RC160V LED58/940 W60L120 PSU CAU	Fixed	0% (digital)
911401541532	RC160V LED58/965 W60L120 PSU CAU	Fixed	0% (digital)
911401542232	RC160V LED54/930 W60L120 PSD CAU	DALI	Programmable
911401542332	RC160V LED58/940 W60L120 PSD CAU	DALI	Programmable
911401542432	RC160V LED58/965 W60L120 PSD CAU	DALI	Programmable
911401543732	RC160X LED54/930 W60L120 SIA CAU	Auto-Dim	0% (digital)

# RC160V

Order Code	Full Product Name	Dimmable	Maximum dim level
911401543832	RC160X LED58/940 W60L120 SIA CAU	Auto-Dim	0% (digital)
911401543932	RC160X LED58/965 W60L120 SIA CAU	Auto-Dim	0% (digital)
911401544632	RC160V LED54/930 W60L120 PSU 54 CAU	Fixed	0% (digital)
911401544732	RC160V LED58/940 W60L120 PSU 54 CAU	Fixed	0% (digital)
911401544832	RC160V LED58/965 W60L120 PSU 54 CAU	Fixed	0% (digital)
911401544932	RC160X LED48/930 W60L120 WIA	Wireless Dim	Programmable
911401545032	RC160X LED51/940 W60L120 WIA	Wireless Dim	Programmable
911401545132	RC160X LED51/965 W60L120 WIA	Wireless Dim	Programmable
911401545232	RC160X LED48/930 W60L120 WIA CAU	Wireless Dim	Programmable
911401545332	RC160X LED51/940 W60L120 WIA CAU	Wireless Dim	Programmable
911401545432	RC160X LED51/965 W60L120 WIA CAU	Wireless Dim	Programmable
911401505343	RC160V LED37/940 W603L603 PSU OC UVG	Fixed	0% (digital)
911401505443	RC160V LED37/965 W603L603 PSU OC UVG	Fixed	0% (digital)
911401509832	RC160V LED37/830 W60L60 PSU 2	Fixed	0% (digital)
911401509932	RC160V LED39/840 W60L60 PSU 2	Fixed	0% (digital)
911401510032	RC160V LED39/865 W60L60 PSU	Fixed	0% (digital)
911401510732	RC160V LED37/830 W60L60 PSU OC	Fixed	0% (digital)
911401510832	RC160V LED39/840 W60L60 PSU OC	Fixed	0% (digital)
911401510932	RC160V LED39/865 W60L60 PSU OC	Fixed	0% (digital)
911401511632	RC160V LED27/830 W60L60 PSU 16	Fixed	0% (digital)
911401511732	RC160V LED29/840 W60L60 PSU 16	Fixed	0% (digital)
911401511832	RC160V LED29/865 W60L60 PSU 16	Fixed	0% (digital)
911401512532	RC160V LED37/830 W60L60 PSU 54	Fixed	0% (digital)
911401512632	RC160V LED39/840 W60L60 PSU 54	Fixed	0% (digital)
911401512732	RC160V LED39/865 W60L60 PSU 54	Fixed	0% (digital)
911401513432	RC160V LED37/830 W60L60 PSU OC 54	Fixed	0% (digital)
911401513532	RC160V LED39/840 W60L60 PSU OC 54	Fixed	0% (digital)
911401513632	RC160V LED39/865 W60L60 PSU OC 54	Fixed	0% (digital)
911401514332	RC160V LED27/830 W60L60 PSU 16 54	Fixed	0% (digital)
911401514432	RC160V LED29/840 W60L60 PSU 16 54	Fixed	0% (digital)

Order Code	Full Product Name	Dimmable	Maximum dim level
911401514532	RC160V LED29/865 W60L60 PSU 16 54	Fixed	0% (digital)
911401516132	RC160V LED37/830 W60L60 PSU OC CPC	Fixed	0% (digital)
911401516232	RC160V LED39/840 W60L60 PSU OC CPC	Fixed	0% (digital)
911401516332	RC160V LED39/865 W60L60 PSU OC CPC	Fixed	0% (digital)
911401518832	RC160V LED37/830 W60L60 PSU OC 54 CPC	Fixed	0% (digital)
911401518932	RC160V LED39/840 W60L60 PSU OC 54 CPC	Fixed	0% (digital)
911401519032	RC160V LED39/865 W60L60 PSU OC 54 CPC	Fixed	0% (digital)
911401520632	RC160V LED37/830 W60L60 PSD	DALI	Programmable
911401520732	RC160V LED39/840 W60L60 PSD	DALI	Programmable
911401520832	RC160V LED39/865 W60L60 PSD	DALI	Programmable
911401521532	RC160V LED37/830 W60L60 PSD OC	DALI	Programmable
911401521632	RC160V LED39/840 W60L60 PSD OC	DALI	Programmable
911401521732	RC160V LED39/865 W60L60 PSD OC	DALI	Programmable
911401522432	RC160V LED27/830 W60L60 PSD 16	DALI	Programmable
911401522532	RC160V LED29/840 W60L60 PSD 16	DALI	Programmable
911401522632	RC160V LED29/865 W60L60 PSD 16	DALI	Programmable
911401523332	RC160X LED37/830 W60L60 WIA	Wireless Dim	Programmable
911401523432	RC160X LED39/840 W60L60 WIA	Wireless Dim	Programmable
911401523532	RC160X LED39/865 W60L60 WIA	Wireless Dim	Programmable
911401523932	RC160X LED37/830 W60L60 WIA OC	Wireless Dim	Programmable
911401524032	RC160X LED39/840 W60L60 WIA OC	Wireless Dim	Programmable
911401524132	RC160X LED39/865 W60L60 WIA OC	Wireless Dim	Programmable
911401524232	RC160X LED27/830 W60L60 WIA 16	Wireless Dim	Programmable
911401524332	RC160X LED29/840 W60L60 WIA 16	Wireless Dim	Programmable
911401524432	RC160X LED29/865 W60L60 WIA 16	Wireless Dim	Programmable
911401524532	RC160X LED37/830 W60L60 SIA	Auto-Dim	0% (digital)
911401524632	RC160X LED39/840 W60L60 SIA	Auto-Dim	0% (digital)
911401524732	RC160X LED39/865 W60L60 SIA	Auto-Dim	0% (digital)
911401525432	RC160V LED37/8TW W60L60	DALI	Programmable
911401525732	RC160V LED37/830 W60L60 PSU CAU	Fixed	0% (digital)
911401525832	RC160V LED39/840 W60L60 PSU CAU	Fixed	0% (digital)
911401525932	RC160V LED39/865 W60L60 PSU CAU	Fixed	0% (digital)
911401526632	RC160V LED37/830 W60L60 PSD CAU	DALI	Programmable
911401526732	RC160V LED39/840 W60L60 PSD CAU	DALI	Programmable

# RC160V

Order Code	Full Product Name	Dimmable	Maximum dim level
911401526832	RC160V LED39/865 W60L60 PSD CAU	DALI	Programmable
911401527532	RC160X LED37/830 W60L60 WIA CAU	Wireless Dim	Programmable
911401527632	RC160X LED39/840 W60L60 WIA CAU	Wireless Dim	Programmable
911401527732	RC160X LED39/865 W60L60 WIA CAU	Wireless Dim	Programmable
911401528132	RC160X LED37/830 W60L60 SIA CAU	Auto-Dim	0% (digital)
911401528232	RC160X LED39/840 W60L60 SIA CAU	Auto-Dim	0% (digital)
911401528332	RC160X LED39/865 W60L60 SIA CAU	Auto-Dim	0% (digital)
911401529032	RC160V LED37/830 W60L60 PSU OC CAU	Fixed	0% (digital)
911401529132	RC160V LED39/840 W60L60 PSU OC CAU	Fixed	0% (digital)
911401529232	RC160V LED39/865 W60L60 PSU OC CAU	Fixed	0% (digital)
911401529932	RC160V LED37/830 W60L60 PSD OC CAU	DALI	Programmable
911401530032	RC160V LED39/840 W60L60 PSD OC CAU	DALI	Programmable
911401530132	RC160V LED39/865 W60L60 PSD OC CAU	DALI	Programmable
911401530832	RC160X LED37/830 W60L60 WIA OC CAU	Wireless Dim	Programmable
911401530932	RC160X LED39/840 W60L60 WIA OC CAU	Wireless Dim	Programmable
911401531032	RC160X LED39/865 W60L60 WIA OC CAU	Wireless Dim	Programmable
911401531132	RC160V LED27/830 W60L60 PSU 16 CAU	Fixed	0% (digital)
911401531232	RC160V LED29/840 W60L60 PSU 16 CAU	Fixed	0% (digital)
911401531332	RC160V LED29/865 W60L60 PSU 16 CAU	Fixed	0% (digital)
911401532032	RC160V LED27/830 W60L60 PSD 16 CAU	DALI	Programmable
911401532132	RC160V LED29/840 W60L60 PSD 16 CAU	DALI	Programmable
911401532232	RC160V LED29/865 W60L60 PSD 16 CAU	DALI	Programmable
911401532932	RC160X LED27/830 W60L60 WIA 16 CAU	Wireless Dim	Programmable
911401533032	RC160X LED29/840 W60L60 WIA 16 CAU	Wireless Dim	Programmable
911401533132	RC160X LED29/865 W60L60 WIA 16 CAU	Wireless Dim	Programmable
911401533232	RC160V LED37/830 W60L60 PSU 54 CAU	Fixed	0% (digital)

Order Code	Full Product Name	Dimmable	Maximum dim level
911401533332	RC160V LED39/840 W60L60 PSU 54 CAU	Fixed	0% (digital)
911401533432	RC160V LED39/865 W60L60 PSU 54 CAU	Fixed	0% (digital)
911401534132	RC160V LED37/830 W60L60 PSU OC 54 CAU	Fixed	0% (digital)
911401534232	RC160V LED39/840 W60L60 PSU OC 54 CAU	Fixed	0% (digital)
911401534332	RC160V LED39/865 W60L60 PSU OC 54 CAU	Fixed	0% (digital)
911401535032	RC160V LED27/830 W60L60 PSU 16 54 CAU	Fixed	0% (digital)
911401535132	RC160V LED29/840 W60L60 PSU 16 54 CAU	Fixed	0% (digital)
911401535232	RC160V LED29/865 W60L60 PSU 16 54 CAU	Fixed	0% (digital)
911401535932	RC160V LED37/830 W60L60 PSU UVG	Fixed	0% (digital)
911401536032	RC160V LED39/840 W60L60 PSU UVG	Fixed	0% (digital)
911401536132	RC160V LED39/865 W60L60 PSU UVG	Fixed	0% (digital)
911401536532	RC160V LED35/930 W60L60 PSU	Fixed	0% (digital)
911401536632	RC160V LED37/940 W60L60 PSU	Fixed	0% (digital)
911401536732	RC160V LED37/965 W60L60 PSU	Fixed	0% (digital)
911401537432	RC160V LED35/930 W60L60 PSU 54	Fixed	0% (digital)
911401537532	RC160V LED37/940 W60L60 PSU 54	Fixed	0% (digital)
911401537632	RC160V LED37/965 W60L60 PSU 54	Fixed	0% (digital)
911401538332	RC160V LED35/930 W60L60 PSD	DALI	Programmable
911401538432	RC160V LED37/940 W60L60 PSD	DALI	Programmable
911401538532	RC160V LED37/965 W60L60 PSD	DALI	Programmable
911401539232	RC160X LED35/930 W60L60 WIA	Wireless Dim	Programmable
911401539332	RC160X LED37/940 W60L60 WIA	Wireless Dim	Programmable
911401539432	RC160X LED37/965 W60L60 WIA	Wireless Dim	Programmable
911401539832	RC160X LED35/930 W60L60 SIA	Auto-Dim	0% (digital)
911401539932	RC160X LED37/940 W60L60 SIA	Auto-Dim	0% (digital)
911401540032	RC160X LED37/965 W60L60 SIA 2	Auto-Dim	0% (digital)
911401540732	RC160V LED35/930 W60L60 PSU CAU	Fixed	0% (digital)
911401540832	RC160V LED37/940 W60L60 PSU CAU	Fixed	0% (digital)
911401540932	RC160V LED37/965 W60L60 PSU CAU	Fixed	0% (digital)
911401541632	RC160V LED35/930 W60L60 PSD CAU	DALI	Programmable
911401541732	RC160V LED37/940 W60L60 PSD CAU	DALI	Programmable
911401541832	RC160V LED37/965 W60L60 PSD CAU	DALI	Programmable
911401542532	RC160X LED35/930 W60L60 WIA CAU	Wireless Dim	Programmable

# RC160V

Order Code	Full Product Name	Dimmable	Maximum dim level
911401542632	RC160X LED37/940 W60L60 WIA CAU	Wireless Dim	Programmable
911401542732	RC160X LED37/965 W60L60 WIA CAU	Wireless Dim	Programmable
911401543132	RC160X LED35/930 W60L60 SIA CAU	Auto-Dim	0% (digital)
911401543232	RC160X LED37/940 W60L60 SIA CAU	Auto-Dim	0% (digital)
911401543332	RC160X LED37/965 W60L60 SIA CAU	Auto-Dim	0% (digital)
911401544032	RC160V LED35/930 W60L60 PSU 54 CAU	Fixed	0% (digital)
911401544132	RC160V LED37/940 W60L60 PSU 54 CAU	Fixed	0% (digital)

Order Code	Full Product Name	Dimmable	Maximum dim level
911401544232	RC160V LED37/965 W60L60 PSU 54 CAU	Fixed	0% (digital)
911401545532	RC160V LED36/9TW W60L60	DALI	Programmable
911401545832	RC160V LED36/9TW W60L60 54	DALI	Programmable
911401546132	RC160V LED36/9TW W60L60 CAU	DALI	Programmable
911401546432	RC160V LED36/9TW W60L60 54 CAU	DALI	Programmable
911401578642	RC160V LED37/830 W603L603 PSU OC UVG	Fixed	0% (digital)
911401578742	RC160V LED39/840 W603L603 PSU OC UVG	Fixed	0% (digital)
911401578842	RC160V LED39/865 W603L603 PSU OC UVG	Fixed	0% (digital)

## Mechanical and Housing

Order Code	Full Product Name	Optical cover type	Ingress protection code
911401505543	RC160V LED37/940 W303L1210 PSU OC UVG	PS	IP20
911401505643	RC160V LED37/965 W303L1210 PSU OC UVG	PS	IP20
911401510132	RC160V LED37/830 W30L120 PSU	PS	IP20
911401510232	RC160V LED39/840 W30L120 PSU	PS	IP20
911401510332	RC160V LED39/865 W30L120 PSU	PS	IP20
911401511032	RC160V LED37/830 W30L120 PSU OC	PS	IP20
911401511132	RC160V LED39/840 W30L120 PSU OC	PS	IP20
911401511232	RC160V LED39/865 W30L120 PSU OC	PS	IP20
911401511932	RC160V LED27/830 W30L120 PSU 16	Polycarbonate bowl/cover	IP20
911401512032	RC160V LED29/840 W30L120 PSU 16	Polycarbonate bowl/cover	IP20
911401512132	RC160V LED29/865 W30L120 PSU 16	Polycarbonate bowl/cover	IP20
911401512832	RC160V LED37/830 W30L120 PSU 54	PS	IP54/20
911401512932	RC160V LED39/840 W30L120 PSU 54	PS	IP54/20
911401513032	RC160V LED39/865 W30L120 PSU 54	PS	IP54/20
911401513732	RC160V LED37/830 W30L120 PSU OC 54	PS	IP54/20
911401513832	RC160V LED39/840 W30L120 PSU OC 54	PS	IP54/20

Order Code	Full Product Name	Optical cover type	Ingress protection code
911401513932	RC160V LED39/865 W30L120 PSU OC 54	PS	IP54/20
911401514632	RC160V LED27/830 W30L120 PSU 16 54	Polycarbonate bowl/cover	IP54/20
911401514732	RC160V LED29/840 W30L120 PSU 16 54	Polycarbonate bowl/cover	IP54/20
911401514832	RC160V LED29/865 W30L120 PSU 16 54	Polycarbonate bowl/cover	IP54/20
911401516432	RC160V LED37/830 W30L120 PSU OC CPC	PS	IP20
911401516532	RC160V LED39/840 W30L120 PSU OC CPC	PS	IP20
911401516632	RC160V LED39/865 W30L120 PSU OC CPC	PS	IP20
911401519132	RC160V LED37/830 W30L120 PSU OC 54 CPC	PS	IP54/20
911401519232	RC160V LED39/840 W30L120 PSU OC 54 CPC	PS	IP54/20
911401519332	RC160V LED39/865 W30L120 PSU OC 54 CPC	PS	IP54/20
911401520932	RC160V LED37/830 W30L120 PSD	PS	IP20
911401521032	RC160V LED39/840 W30L120 PSD	PS	IP20
911401521132	RC160V LED39/865 W30L120 PSD	PS	IP20
911401521832	RC160V LED37/830 W30L120 PSD OC	PS	IP20
911401521932	RC160V LED39/840 W30L120 PSD OC	PS	IP20
911401522032	RC160V LED39/865 W30L120 PSD OC	PS	IP20

# RC160V

Order Code	Full Product Name	Optical cover type	Ingress protection code
911401522732	RC160V LED27/830 W30L120 PSD 16	Polycarbonate bowl/cover	IP20
911401522832	RC160V LED29/840 W30L120 PSD 16	Polycarbonate bowl/cover	IP20
911401522932	RC160V LED29/865 W30L120 PSD 16	Polycarbonate bowl/cover	IP20
911401523632	RC160X LED37/830 W30L120 WIA	PS	IP20
911401523732	RC160X LED39/840 W30L120 WIA	PS	IP20
911401523832	RC160X LED39/865 W30L120 WIA	PS	IP20
911401524832	RC160X LED37/830 W30L120 SIA	PS	IP20
911401524932	RC160X LED39/840 W30L120 SIA	PS	IP20
911401525032	RC160X LED39/865 W30L120 SIA	PS	IP20
911401525532	RC160V LED38/8TW W30L120	PS	IP20
911401526032	RC160V LED37/830 W30L120 PSU CAU	PS	IP20
911401526132	RC160V LED39/840 W30L120 PSU CAU	PS	IP20
911401526232	RC160V LED39/865 W30L120 PSU CAU	PS	IP20
911401526932	RC160V LED37/830 W30L120 PSD CAU	PS	IP20
911401527032	RC160V LED39/840 W30L120 PSD CAU	PS	IP20
911401527132	RC160V LED39/865 W30L120 PSD CAU	PS	IP20
911401527832	RC160X LED37/830 W30L120 WIA CAU	PS	IP20
911401527932	RC160X LED39/840 W30L120 WIA CAU	PS	IP20
911401528032	RC160X LED39/865 W30L120 WIA CAU	PS	IP20
911401528432	RC160X LED37/830 W30L120 SIA CAU	PS	IP20
911401528532	RC160X LED39/840 W30L120 SIA CAU	PS	IP20
911401528632	RC160X LED39/865 W30L120 SIA CAU	PS	IP20
911401529332	RC160V LED37/830 W30L120 PSU OC CAU	PS	IP20
911401529432	RC160V LED39/840 W30L120 PSU OC CAU	PS	IP20
911401529532	RC160V LED39/865 W30L120 PSU OC CAU	PS	IP20
911401530232	RC160V LED37/830 W30L120 PSD OC CAU	PS	IP20
911401530332	RC160V LED39/840 W30L120 PSD OC CAU	PS	IP20
911401530432	RC160V LED39/865 W30L120 PSD OC CAU	PS	IP20

Order Code	Full Product Name	Optical cover type	Ingress protection code
911401531432	RC160V LED27/830 W30L120 PSU 16 CAU	Polycarbonate bowl/cover	IP20
911401531532	RC160V LED29/840 W30L120 PSU 16 CAU	Polycarbonate bowl/cover	IP20
911401531632	RC160V LED29/865 W30L120 PSU 16 CAU	Polycarbonate bowl/cover	IP20
911401532332	RC160V LED27/830 W30L120 PSD 16 CAU	Polycarbonate bowl/cover	IP20
911401532432	RC160V LED29/840 W30L120 PSD 16 CAU	Polycarbonate bowl/cover	IP20
911401532532	RC160V LED29/865 W30L120 PSD 16 CAU	Polycarbonate bowl/cover	IP20
911401533532	RC160V LED37/830 W30L120 PSU 54 CAU	PS	IP54/20
911401533632	RC160V LED39/840 W30L120 PSU 54 CAU	PS	IP54/20
911401533732	RC160V LED39/865 W30L120 PSU 54 CAU	PS	IP54/20
911401534432	RC160V LED37/830 W30L120 PSU OC 54 CAU	PS	IP54/20
911401534532	RC160V LED39/840 W30L120 PSU OC 54 CAU	PS	IP54/20
911401534632	RC160V LED39/865 W30L120 PSU OC 54 CAU	PS	IP54/20
911401535332	RC160V LED27/830 W30L120 PSU 16 54 CAU	Polycarbonate bowl/cover	IP54/20
911401535432	RC160V LED29/840 W30L120 PSU 16 54 CAU	Polycarbonate bowl/cover	IP54/20
911401535532	RC160V LED29/865 W30L120 PSU 16 54 CAU	Polycarbonate bowl/cover	IP54/20
911401536232	RC160V LED37/830 W30L1210 PSU UVG	PS	IP20
911401536332	RC160V LED39/840 W30L1210 PSU UVG	PS	IP20
911401536432	RC160V LED39/865 W30L1210 PSU UVG	PS	IP20
911401536832	RC160V LED35/930 W30L120 PSU	PS	IP20
911401536932	RC160V LED37/940 W30L120 PSU	PS	IP20
911401537032	RC160V LED37/965 W30L120 PSU	PS	IP20
911401537732	RC160V LED35/930 W30L120 PSU 54	PS	IP54/20
911401537832	RC160V LED37/940 W30L120 PSU 54	PS	IP54/20
911401537932	RC160V LED37/965 W30L120 PSU 54	PS	IP54/20
911401538632	RC160V LED35/930 W30L120 PSD	PS	IP20

# RC160V

Order Code	Full Product Name	Optical cover type	Ingress protection code
911401538732	RC160V LED37/940 W30L120 PSD	PS	IP20
911401538832	RC160V LED37/965 W30L120 PSD	PS	IP20
911401539532	RC160X LED35/930 W30L120 WIA	PS	IP20
911401539632	RC160X LED37/940 W30L120 WIA	PS	IP20
911401539732	RC160X LED37/965 W30L120 WIA	PS	IP20
911401540132	RC160X LED35/930 W30L120 SIA	PS	IP20
911401540232	RC160X LED37/940 W30L120 SIA	PS	IP20
911401540332	RC160X LED37/965 W30L120 SIA	PS	IP20
911401541032	RC160V LED35/930 W30L120 PSU CAU	PS	IP20
911401541132	RC160V LED37/940 W30L120 PSU CAU	PS	IP20
911401541232	RC160V LED37/965 W30L120 PSU CAU	PS	IP20
911401541932	RC160V LED35/930 W30L120 PSD CAU	PS	IP20
911401542032	RC160V LED37/940 W30L120 PSD CAU	PS	IP20
911401542132	RC160V LED37/965 W30L120 PSD CAU	PS	IP20
911401542832	RC160X LED35/930 W30L120 WIA CAU	PS	IP20
911401542932	RC160X LED37/940 W30L120 WIA CAU	PS	IP20
911401543032	RC160X LED37/965 W30L120 WIA CAU	PS	IP20
911401543432	RC160X LED35/930 W30L120 SIA CAU	PS	IP20
911401543532	RC160X LED37/940 W30L120 SIA CAU	PS	IP20
911401543632	RC160X LED37/965 W30L120 SIA CAU	PS	IP20
911401544332	RC160V LED35/930 W30L120 PSU 54 CAU	PS	IP54/20
911401544432	RC160V LED37/940 W30L120 PSU 54 CAU	PS	IP54/20
911401544532	RC160V LED37/965 W30L120 PSU 54 CAU	PS	IP54/20
911401545632	RC160V LED37/9TW W30L120	PS	IP20
911401545932	RC160V LED37/9TW W30L120 54	PS	IP54/20
911401546232	RC160V LED37/9TW W30L120 CAU	PS	IP20
911401546532	RC160V LED37/9TW W30L120 54 CAU	PS	IP54/20
911401578942	RC160V LED37/830 W303L1210 PSU OC UVG	PS	IP20
911401579042	RC160V LED39/840 W303L1210 PSU OC UVG	PS	IP20

Order Code	Full Product Name	Optical cover type	Ingress protection code
911401579142	RC160V LED39/865 W303L1210 PSU OC UVG	PS	IP20
911401510432	RC160V LED57/830 W60L120 PSU	PS	IP20
911401510532	RC160V LED60/840 W60L120 PSU	PS	IP20
911401510632	RC160V LED60/865 W60L120 PSU	PS	IP20
911401511332	RC160V LED57/830 W60L120 PSU OC	PS	IP20
911401511432	RC160V LED60/840 W60L120 PSU OC	PS	IP20
911401511532	RC160V LED60/865 W60L120 PSU OC	PS	IP20
911401512232	RC160V LED54/830 W60L120 PSU 16	Polycarbonate bowl/cover	IP20
911401512332	RC160V LED58/840 W60L120 PSU 16	Polycarbonate bowl/cover	IP20
911401512432	RC160V LED58/865 W60L120 PSU 16	Polycarbonate bowl/cover	IP20
911401513132	RC160V LED57/830 W60L120 PSU 54	PS	IP54/20
911401513232	RC160V LED60/840 W60L120 PSU 54	PS	IP54/20
911401513332	RC160V LED60/865 W60L120 PSU 54	PS	IP54/20
911401514032	RC160V LED57/830 W60L120 PSU OC 54	PS	IP54/20
911401514132	RC160V LED60/840 W60L120 PSU OC 54	PS	IP54/20
911401514232	RC160V LED60/865 W60L120 PSU OC 54	PS	IP54/20
911401514932	RC160V LED54/830 W60L120 PSU 16 54	Polycarbonate bowl/cover	IP54/20
911401515032	RC160V LED58/840 W60L120 PSU 16 54	Polycarbonate bowl/cover	IP54/20
911401515132	RC160V LED58/865 W60L120 PSU 16 54	Polycarbonate bowl/cover	IP54/20
911401521232	RC160V LED57/830 W60L120 PSD	PS	IP20
911401521332	RC160V LED60/840 W60L120 PSD	PS	IP20
911401521432	RC160V LED60/865 W60L120 PSD	PS	IP20
911401522132	RC160V LED57/830 W60L120 PSD OC	PS	IP20
911401522232	RC160V LED60/840 W60L120 PSD OC	PS	IP20
911401522332	RC160V LED60/865 W60L120 PSD OC	PS	IP20

# RC160V

Order Code	Full Product Name	Optical cover type	Ingress protection code
911401523032	RC160V LED54/830 W60L120 PSD 16	Polycarbonate bowl/cover	IP20
911401523132	RC160V LED58/840 W60L120 PSD 16	Polycarbonate bowl/cover	IP20
911401523232	RC160V LED58/865 W60L120 PSD 16	Polycarbonate bowl/cover	IP20
911401525132	RC160X LED57/830 W60L120 SIA	PS	IP20
911401525232	RC160X LED60/840 W60L120 SIA	PS	IP20
911401525332	RC160X LED60/865 W60L120 SIA	PS	IP20
911401526332	RC160V LED57/830 W60L120 PSU CAU	PS	IP20
911401526432	RC160V LED60/840 W60L120 PSU CAU	PS	IP20
911401526532	RC160V LED60/865 W60L120 PSU CAU	PS	IP20
911401527232	RC160V LED57/830 W60L120 PSD CAU	PS	IP20
911401527332	RC160V LED60/840 W60L120 PSD CAU	PS	IP20
911401527432	RC160V LED60/865 W60L120 PSD CAU	PS	IP20
911401528732	RC160X LED57/830 W60L120 SIA CAU	PS	IP20
911401528832	RC160X LED60/840 W60L120 SIA CAU	PS	IP20
911401528932	RC160X LED60/865 W60L120 SIA CAU	PS	IP20
911401529632	RC160V LED57/830 W60L120 PSU OC CAU	PS	IP20
911401529732	RC160V LED60/840 W60L120 PSU OC CAU	PS	IP20
911401529832	RC160V LED60/865 W60L120 PSU OC CAU	PS	IP20
911401530532	RC160V LED57/830 W60L120 PSD OC CAU	PS	IP20
911401530632	RC160V LED60/840 W60L120 PSD OC CAU	PS	IP20
911401530732	RC160V LED60/865 W60L120 PSD OC CAU	PS	IP20
911401531732	RC160V LED54/830 W60L120 PSU 16 CAU	Polycarbonate bowl/cover	IP20
911401531832	RC160V LED58/840 W60L120 PSU 16 CAU	Polycarbonate bowl/cover	IP20
911401531932	RC160V LED58/865 W60L120 PSU 16 CAU	Polycarbonate bowl/cover	IP20
911401532632	RC160V LED54/830 W60L120 PSD 16 CAU	Polycarbonate bowl/cover	IP20
911401532732	RC160V LED58/840 W60L120 PSD 16 CAU	Polycarbonate bowl/cover	IP20

Order Code	Full Product Name	Optical cover type	Ingress protection code
911401532832	RC160V LED58/865 W60L120 PSD 16 CAU	Polycarbonate bowl/cover	IP20
911401533832	RC160V LED57/830 W60L120 PSU 54 CAU	PS	IP54/20
911401533932	RC160V LED60/840 W60L120 PSU 54 CAU	PS	IP54/20
911401534032	RC160V LED60/865 W60L120 PSU 54 CAU	PS	IP54/20
911401534732	RC160V LED57/830 W60L120 PSU OC 54 CAU	PS	IP54/20
911401534832	RC160V LED60/840 W60L120 PSU OC 54 CAU	PS	IP54/20
911401534932	RC160V LED60/865 W60L120 PSU OC 54 CAU	PS	IP54/20
911401535632	RC160V LED54/830 W60L120 PSU 16 54 CAU	Polycarbonate bowl/cover	IP54/20
911401535732	RC160V LED58/840 W60L120 PSU 16 54 CAU	Polycarbonate bowl/cover	IP54/20
911401535832	RC160V LED58/865 W60L120 PSU 16 54 CAU	Polycarbonate bowl/cover	IP54/20
911401537132	RC160V LED54/930 W60L120 PSU	PS	IP20
911401537232	RC160V LED58/940 W60L120 PSU	PS	IP20
911401537332	RC160V LED58/965 W60L120 PSU	PS	IP20
911401538032	RC160V LED54/930 W60L120 PSU 54	PS	IP54/20
911401538132	RC160V LED58/940 W60L120 PSU 54	PS	IP54/20
911401538232	RC160V LED58/965 W60L120 PSU 54	PS	IP54/20
911401538932	RC160V LED54/930 W60L120 PSD	PS	IP20
911401539032	RC160V LED58/940 W60L120 PSD	PS	IP20
911401539132	RC160V LED58/965 W60L120 PSD	PS	IP20
911401540432	RC160X LED54/930 W60L120 SIA	PS	IP20
911401540532	RC160X LED58/940 W60L120 SIA	PS	IP20
911401540632	RC160X LED58/965 W60L120 SIA	PS	IP20
911401541332	RC160V LED54/930 W60L120 PSU CAU	PS	IP20
911401541432	RC160V LED58/940 W60L120 PSU CAU	PS	IP20
911401541532	RC160V LED58/965 W60L120 PSU CAU	PS	IP20
911401542232	RC160V LED54/930 W60L120 PSD CAU	PS	IP20

# RC160V

Order Code	Full Product Name	Optical cover type	Ingress protection code
911401542332	RC160V LED58/940 W60L120 PSD CAU	PS	IP20
911401542432	RC160V LED58/965 W60L120 PSD CAU	PS	IP20
911401543732	RC160X LED54/930 W60L120 SIA CAU	PS	IP20
911401543832	RC160X LED58/940 W60L120 SIA CAU	PS	IP20
911401543932	RC160X LED58/965 W60L120 SIA CAU	PS	IP20
911401544632	RC160V LED54/930 W60L120 PSU 54 CAU	PS	IP54/20
911401544732	RC160V LED58/940 W60L120 PSU 54 CAU	PS	IP54/20
911401544832	RC160V LED58/965 W60L120 PSU 54 CAU	PS	IP54/20
911401544932	RC160X LED48/930 W60L120 WIA	PS	IP20
911401545032	RC160X LED51/940 W60L120 WIA	PS	IP20
911401545132	RC160X LED51/965 W60L120 WIA	PS	IP20
911401545232	RC160X LED48/930 W60L120 WIA CAU	PS	IP20
911401545332	RC160X LED51/940 W60L120 WIA CAU	PS	IP20
911401545432	RC160X LED51/965 W60L120 WIA CAU	PS	IP20
911401505343	RC160V LED37/940 W603L603 PSU OC UVG	PS	IP20
911401505443	RC160V LED37/965 W603L603 PSU OC UVG	PS	IP20
911401509832	RC160V LED37/830 W60L60 PSU 2	PS	IP20
911401509932	RC160V LED39/840 W60L60 PSU 2	PS	IP20
911401510032	RC160V LED39/865 W60L60 PSU	PS	IP20
911401510732	RC160V LED37/830 W60L60 PSU OC	PS	IP20
911401510832	RC160V LED39/840 W60L60 PSU OC	PS	IP20
911401510932	RC160V LED39/865 W60L60 PSU OC	PS	IP20
911401511632	RC160V LED27/830 W60L60 PSU 16	Polycarbonate bowl/cover	IP20
911401511732	RC160V LED29/840 W60L60 PSU 16	Polycarbonate bowl/cover	IP20
911401511832	RC160V LED29/865 W60L60 PSU 16	Polycarbonate bowl/cover	IP20
911401512532	RC160V LED37/830 W60L60 PSU 54	PS	IP54/20

Order Code	Full Product Name	Optical cover type	Ingress protection code
911401512632	RC160V LED39/840 W60L60 PSU 54	PS	IP54/20
911401512732	RC160V LED39/865 W60L60 PSU 54	PS	IP54/20
911401513432	RC160V LED37/830 W60L60 PSU OC 54	PS	IP54/20
911401513532	RC160V LED39/840 W60L60 PSU OC 54	PS	IP54/20
911401513632	RC160V LED39/865 W60L60 PSU OC 54	PS	IP54/20
911401514332	RC160V LED27/830 W60L60 PSU 16 54	Polycarbonate bowl/cover	IP54/20
911401514432	RC160V LED29/840 W60L60 PSU 16 54	Polycarbonate bowl/cover	IP54/20
911401514532	RC160V LED29/865 W60L60 PSU 16 54	Polycarbonate bowl/cover	IP54/20
911401516132	RC160V LED37/830 W60L60 PSU OC CPC	PS	IP20
911401516232	RC160V LED39/840 W60L60 PSU OC CPC	PS	IP20
911401516332	RC160V LED39/865 W60L60 PSU OC CPC	PS	IP20
911401518832	RC160V LED37/830 W60L60 PSU OC 54 CPC	PS	IP54/20
911401518932	RC160V LED39/840 W60L60 PSU OC 54 CPC	PS	IP54/20
911401519032	RC160V LED39/865 W60L60 PSU OC 54 CPC	PS	IP54/20
911401520632	RC160V LED37/830 W60L60 PSD	PS	IP20
911401520732	RC160V LED39/840 W60L60 PSD	PS	IP20
911401520832	RC160V LED39/865 W60L60 PSD	PS	IP20
911401521532	RC160V LED37/830 W60L60 PSD OC	PS	IP20
911401521632	RC160V LED39/840 W60L60 PSD OC	PS	IP20
911401521732	RC160V LED39/865 W60L60 PSD OC	PS	IP20
911401522432	RC160V LED27/830 W60L60 PSD 16	Polycarbonate bowl/cover	IP20
911401522532	RC160V LED29/840 W60L60 PSD 16	Polycarbonate bowl/cover	IP20
911401522632	RC160V LED29/865 W60L60 PSD 16	Polycarbonate bowl/cover	IP20
911401523332	RC160X LED37/830 W60L60 WIA	PS	IP20
911401523432	RC160X LED39/840 W60L60 WIA	PS	IP20
911401523532	RC160X LED39/865 W60L60 WIA	PS	IP20
911401523932	RC160X LED37/830 W60L60 WIA OC	PS	IP20
911401524032	RC160X LED39/840 W60L60 WIA OC	PS	IP20

# RC160V

Order Code	Full Product Name	Optical cover type	Ingress protection code
911401524132	RC160X LED39/865 W60L60 WIA OC	PS	IP20
911401524232	RC160X LED27/830 W60L60 WIA 16	Polycarbonate bowl/cover	IP20
911401524332	RC160X LED29/840 W60L60 WIA 16	Polycarbonate bowl/cover	IP20
911401524432	RC160X LED29/865 W60L60 WIA 16	Polycarbonate bowl/cover	IP20
911401524532	RC160X LED37/830 W60L60 SIA	PS	IP20
911401524632	RC160X LED39/840 W60L60 SIA	PS	IP20
911401524732	RC160X LED39/865 W60L60 SIA	PS	IP20
911401525432	RC160V LED37/8TW W60L60	PS	IP20
911401525732	RC160V LED37/830 W60L60 PSU CAU	PS	IP20
911401525832	RC160V LED39/840 W60L60 PSU CAU	PS	IP20
911401525932	RC160V LED39/865 W60L60 PSU CAU	PS	IP20
911401526632	RC160V LED37/830 W60L60 PSD CAU	PS	IP20
911401526732	RC160V LED39/840 W60L60 PSD CAU	PS	IP20
911401526832	RC160V LED39/865 W60L60 PSD CAU	PS	IP20
911401527532	RC160X LED37/830 W60L60 WIA CAU	PS	IP20
911401527632	RC160X LED39/840 W60L60 WIA CAU	PS	IP20
911401527732	RC160X LED39/865 W60L60 WIA CAU	PS	IP20
911401528132	RC160X LED37/830 W60L60 SIA CAU	PS	IP20
911401528232	RC160X LED39/840 W60L60 SIA CAU	PS	IP20
911401528332	RC160X LED39/865 W60L60 SIA CAU	PS	IP20
911401529032	RC160V LED37/830 W60L60 PSU OC CAU	PS	IP20
911401529132	RC160V LED39/840 W60L60 PSU OC CAU	PS	IP20
911401529232	RC160V LED39/865 W60L60 PSU OC CAU	PS	IP20
911401529932	RC160V LED37/830 W60L60 PSD OC CAU	PS	IP20
911401530032	RC160V LED39/840 W60L60 PSD OC CAU	PS	IP20
911401530132	RC160V LED39/865 W60L60 PSD OC CAU	PS	IP20
911401530832	RC160X LED37/830 W60L60 WIA OC CAU	PS	IP20

Order Code	Full Product Name	Optical cover type	Ingress protection code
911401530932	RC160X LED39/840 W60L60 WIA OC CAU	PS	IP20
911401531032	RC160X LED39/865 W60L60 WIA OC CAU	PS	IP20
911401531132	RC160V LED27/830 W60L60 PSU 16 CAU	Polycarbonate bowl/cover	IP20
911401531232	RC160V LED29/840 W60L60 PSU 16 CAU	Polycarbonate bowl/cover	IP20
911401531332	RC160V LED29/865 W60L60 PSU 16 CAU	Polycarbonate bowl/cover	IP20
911401532032	RC160V LED27/830 W60L60 PSD 16 CAU	Polycarbonate bowl/cover	IP20
911401532132	RC160V LED29/840 W60L60 PSD 16 CAU	Polycarbonate bowl/cover	IP20
911401532232	RC160V LED29/865 W60L60 PSD 16 CAU	Polycarbonate bowl/cover	IP20
911401532932	RC160X LED27/830 W60L60 WIA 16 CAU	Polycarbonate bowl/cover	IP20
911401533032	RC160X LED29/840 W60L60 WIA 16 CAU	Polycarbonate bowl/cover	IP20
911401533132	RC160X LED29/865 W60L60 WIA 16 CAU	Polycarbonate bowl/cover	IP20
911401533232	RC160V LED37/830 W60L60 PSU 54 CAU	PS	IP54/20
911401533332	RC160V LED39/840 W60L60 PSU 54 CAU	PS	IP54/20
911401533432	RC160V LED39/865 W60L60 PSU 54 CAU	PS	IP54/20
911401534132	RC160V LED37/830 W60L60 PSU OC 54 CAU	PS	IP54/20
911401534232	RC160V LED39/840 W60L60 PSU OC 54 CAU	PS	IP54/20
911401534332	RC160V LED39/865 W60L60 PSU OC 54 CAU	PS	IP54/20
911401535032	RC160V LED27/830 W60L60 PSU 16 54 CAU	Polycarbonate bowl/cover	IP54/20
911401535132	RC160V LED29/840 W60L60 PSU 16 54 CAU	Polycarbonate bowl/cover	IP54/20
911401535232	RC160V LED29/865 W60L60 PSU 16 54 CAU	Polycarbonate bowl/cover	IP54/20
911401535932	RC160V LED37/830 W603L603 PSU UVG	PS	IP20
911401536032	RC160V LED39/840 W603L603 PSU UVG	PS	IP20
911401536132	RC160V LED39/865 W603L603 PSU UVG	PS	IP20
911401536532	RC160V LED35/930 W60L60 PSU	PS	IP20
911401536632	RC160V LED37/940 W60L60 PSU	PS	IP20
911401536732	RC160V LED37/965 W60L60 PSU	PS	IP20

# RC160V

Order Code	Full Product Name	Optical cover type	Ingress protection code
911401537432	RC160V LED35/930 W60L60 PSU 54	PS	IP54/20
911401537532	RC160V LED37/940 W60L60 PSU 54	PS	IP54/20
911401537632	RC160V LED37/965 W60L60 PSU 54	PS	IP54/20
911401538332	RC160V LED35/930 W60L60 PSD	PS	IP20
911401538432	RC160V LED37/940 W60L60 PSD	PS	IP20
911401538532	RC160V LED37/965 W60L60 PSD	PS	IP20
911401539232	RC160X LED35/930 W60L60 WIA	PS	IP20
911401539332	RC160X LED37/940 W60L60 WIA	PS	IP20
911401539432	RC160X LED37/965 W60L60 WIA	PS	IP20
911401539832	RC160X LED35/930 W60L60 SIA	PS	IP20
911401539932	RC160X LED37/940 W60L60 SIA	PS	IP20
911401540032	RC160X LED37/965 W60L60 SIA 2	PS	IP20
911401540732	RC160V LED35/930 W60L60 PSU CAU	PS	IP20
911401540832	RC160V LED37/940 W60L60 PSU CAU	PS	IP20
911401540932	RC160V LED37/965 W60L60 PSU 2 CAU	PS	IP20
911401541632	RC160V LED35/930 W60L60 PSD CAU	PS	IP20
911401541732	RC160V LED37/940 W60L60 PSD CAU	PS	IP20
911401541832	RC160V LED37/965 W60L60 PSD CAU	PS	IP20
911401542532	RC160X LED35/930 W60L60 WIA CAU	PS	IP20

Order Code	Full Product Name	Optical cover type	Ingress protection code
911401542632	RC160X LED37/940 W60L60 WIA CAU	PS	IP20
911401542732	RC160X LED37/965 W60L60 WIA CAU	PS	IP20
911401543132	RC160X LED35/930 W60L60 SIA CAU	PS	IP20
911401543232	RC160X LED37/940 W60L60 SIA CAU	PS	IP20
911401543332	RC160X LED37/965 W60L60 SIA CAU	PS	IP20
911401544032	RC160V LED35/930 W60L60 PSU 54 CAU	PS	IP54/20
911401544132	RC160V LED37/940 W60L60 PSU 54 CAU	PS	IP54/20
911401544232	RC160V LED37/965 W60L60 PSU 54 CAU	PS	IP54/20
911401545532	RC160V LED36/9TW W60L60	PS	IP20
911401545832	RC160V LED36/9TW W60L60 54	PS	IP54/20
911401546132	RC160V LED36/9TW W60L60 CAU	PS	IP20
911401546432	RC160V LED36/9TW W60L60 54 CAU	PS	IP54/20
911401578642	RC160V LED37/830 W603L603 PSU OC UVG	PS	IP20
911401578742	RC160V LED39/840 W603L603 PSU OC UVG	PS	IP20
911401578842	RC160V LED39/865 W603L603 PSU OC UVG	PS	IP20

