

SlimBlend Gen2

RC330V



SlimBlend gen2: high performance, advanced control

Offices are looking for high-performance lighting that enhances performance, comfort, well-being, and sustainability. That's why 'surface of light' solutions that deliver excellent quality of light with great functionality and connectivity are in such demand. Like Philips SlimBlend Gen2 – a complete family of slim luminaires designed for enhanced well-being and circularity. SlimBlend Gen2 luminaires offer state-of-the-art efficacy and excellent light quality (CRI>90) with upgradability features and repairability that promise a long lifetime. They are also designed for recyclability, making them a truly circular, green choice. But it's the high-quality light that makes SlimBlend Gen2 luminaires really stand out. The special Micro Hexagonal Optics (MXO) provides glare-free comfort & also infuses the homogeneous light with sparkles, creating a lively surface of light that enhances interiors and offers full Office compliance. SlimBlend Gen 2 is a minimalist solution with superior lighting specifications combined with a best-in-class connectivity using Interact Pro - all with a sustainable approach to high-performance office lighting.

Benefits

- Highly efficient LED luminaire with choice of mounting options (recessed, suspended, surface mounted)
- Comfortable, glare-free Office-compliant
- Competitive solution with good lighting specifications
- Sustainable and best-in-class connected offer

Applications

- Offices
- Healthcare
- Education

Features

- Best-in-class efficacy up to 140lm/W supports green building design and energy saving subsidy criteria
- CRI90 with Tunable White option
- Office-compliant lighting using both MXO optics and Opal cover
- Long lifetime up to 50,000 hours @L90
- Quick connector or Wieland connector for simpler, faster installation
- Prepared for circularity (no glue, replaceable electronics, upgradable system, efficient and long lifetime) plus supporting Environmental Product Declaration (EPD) guide
- Connected system ready with Interact Pro scalable platform using integrated sensors and/or wireless drivers for data collection, occupancy, daylight regulation and wayfinding

Versions



SlimBlendGen2
RecessMouted RC330V
W62L62 MXO IA4 SPP



SlimBlendGen2
RecessMouted RC330V
W62L62 MXO IA5 SPP



SlimBlendGen2
RecessMouted RC330V
W30L120 MXO IA4 SPP



SlimBlendGen2
RecessMouted RC330V
W60L60 MXO IA5 SPP



SlimBlendGen2
RecessMouted RC330V
W60L60 MXO IA4 SPP




SlimBlendGen2
RecessMouted RC330V
W30L120 MXO SPP




SlimBlendGen2
RecessMouted RC330V
W62L62 MXO SPP


Dimensional drawing




RC332V 36S/940 SEIA W62L62 IA4 MXO




RC330V 36S/940 SEIA W30L120 IA4 MXO SC




RC332V 42S/930 PSD W62L62 MXO



RC330V 36S/940 PSD W60L60 MXO



RC330V 42S/940 SEIA W60L60 IA4 MXO



RC330V 42S/940 PSD W30L120 MXO SC

Product details




SlimBlendGen2 Backview
_DPP



SlimBlendGen2_IA5 Sensor
with MXO



SlimBlendGen2_IA5
Sensor_with OC



SlimBlendGen2 with CPC
accessory DPP01



SlimBlendGen2_Suspended
with sensor_W30L120



Connector- Wieland DPP01



SlimBlendGen2_Suspended
with sensor_W60L60



RC330V W60L60 sensor with
Surface mounted accessories




RC330V W30L120 with
Surface mounted accessories



RC330V W30L120 sensor with
Surface mounted accessories



RC330V W60L60 with Surface
mounted accessories



SlimBlendGen2 with CPC
accessory DPP02


PIP connector DPP02



SlimBlend Gen2
RC330Z_SMB_W30L120



Connector- Wieland DPP02



PIP connector DPP03




Safety cable




SlimBlendGen2_IA4 Sensor
with MXO



SlimBlendGen2 MXO-optics



SlimBlend Gen2
RC330Z_SMB_W60L60



SlimBlendGen2 Backview with
IA4 sensor



SlimBlendGen2_Suspended
without sensor_W60L60





SlimBlend Gen2_Backview
with EL & Sensor_DPP



SlimBlendGen2_Suspended
without sensor_W30L120

PIP connector DPP01



General Information

Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Service tag	Yes

Light Technical

Upward light output ratio	0
Color rendering index (CRI)	>90
Beam angle of light source	120 degree(s)
Optic type	-

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	No
Protection class IEC	Safety class II

Controls and Dimming

Dimmable	Yes
Maximum dim level	1%

Mechanical and Housing

Housing Color	White
Mech. impact protection code	IK03 [0.3 J]
Optical cover type	Polycarbonate

Emergency Operation

Emergency flux	270 lm
Rated duration of the emergency lighting (when fully charged)	3 hour(s)
Central Emergency	Yes

Approval and Application

Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Ambient temperature range	+10 to +35 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

General Information

Order Code	Full Product Name	Lamp family code
910505102464	RC332V 36S/930 SEIA W62L62 IA4 MXO	36S
910505102465	RC332V 36S/940 SEIA W62L62 IA4 MXO	36S
910505102466	RC332V 42S/930 SEIA W62L62 IA4 MXO	42S
910505102467	RC332V 42S/940 SEIA W62L62 IA4 MXO	42S
910505102468	RC332V 36S/940 SEIA W62L62 IA5 MXO	36S
910505102475	RC330V 36S/940 SEIA W30L120 IA4 MXO	36S
910505102477	RC330V 42S/930 SEIA W30L120 IA4 MXO	42S
910505102478	RC330V 42S/940 SEIA W30L120 IA4 MXO	42S
910505102497	RC330V 36S/940 SEIA W30L120 IA4 MXO SC	36S
910505102498	RC330V 36S/930 SEIA W30L120 IA4 MXO SC	36S
910505102451	RC330V 36S/940 SEIA W60L60 IA5 MXO	36S
910505102450	RC330V 36S/940 SEIA W60L60 IA4 MXO	36S
910505102452	RC330V 42S/930 SEIA W60L60 IA4 MXO	42S
910505102453	RC330V 42S/940 SEIA W60L60 IA4 MXO	42S
910505102454	RC330V 42S/940 SEIA W60L60 IA4 ELW3 MXO	42S
910505102488	RC330V 36S/940 SEIA W60L60 IA4 MXO SC	36S
910505102489	RC330V 36S/940 SEIA W60L60 IA5 MXO SC	36S
910505102490	RC330V 42S/930 SEIA W60L60 IA4 MXO SC	42S
910505102491	RC330V 42S/940 SEIA W60L60 IA4 MXO SC	42S
910505102492	RC330V 42S/940 SEIA W60L60 IA4 ELW3MXOSC	42S
910505102469	RC330V 36S/940 PSD W30L120 MXO	36S
910505102470	RC330V 36S/940 PSD W30L120 MXO W5	36S
910505102471	RC330V 42S/940 PSD W30L120 MXO	42S

Order Code	Full Product Name	Lamp family code
910505102472	RC330V 42S/930 PSD W30L120 MXO	42S
910505102473	RC330V 36S/940 WIA W30L120 MXO	36S
910505102474	RC330V 42S/940 WIA W30L120 MXO	42S
910505102476	RC330V 36S/940 SEIA W30L120 IA5 MXO	36S
910505102493	RC330V 36S/940 PSD W30L120 MXO SC	36S
910505102494	RC330V 36S/930 PSD W30L120 MXO SC	36S
910505102495	RC330V 42S/940 PSD W30L120 MXO SC	42S
910505102496	RC330V 42S/930 PSD W30L120 MXO SC	42S
910505102445	RC330V 36S/940 PSD W60L60 MXO	36S
910505102446	RC330V 36S/940 PSD W60L60 MXO W5	36S
910505102447	RC330V 42S/940 PSD W60L60 MXO	42S
910505102448	RC330V 42S/930 PSD W60L60 MXO	42S
910505102449	RC330V 36S/940 WIA W60L60 MXO	36S
910505102455	RC332V 36S/930 PSD W62L62 MXO	36S
910505102456	RC332V 36S/940 PSD W62L62 MXO	36S
910505102457	RC332V 42S/930 PSD W62L62 MXO	42S
910505102458	RC332V 42S/940 PSD W62L62 MXO	42S
910505102459	RC332V 36S/940 DEIA W62L62 MXO	36S
910505102460	RC332V 36S/930 WIA W62L62 MXO	36S
910505102461	RC332V 36S/940 WIA W62L62 MXO	36S
910505102462	RC332V 42S/930 WIA W62L62 MXO	42S
910505102463	RC332V 42S/940 WIA W62L62 MXO	42S
910505102484	RC330V 36S/940 PSD W60L60 MXO SC	36S
910505102485	RC330V 36S/930 PSD W60L60 MXO SC	36S
910505102486	RC330V 42S/940 PSD W60L60 MXO SC	42S
910505102487	RC330V 36S/940 WIA W60L60 MXO SC	36S

Light Technical

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)
910505102464	RC332V 36S/930 SEIA W62L62 IA4 MXO	3,400 lm	3000 K	127 lm/W
910505102465	RC332V 36S/940 SEIA W62L62 IA4 MXO	3,600 lm	4000 K	133 lm/W
910505102466	RC332V 42S/930 SEIA W62L62 IA4 MXO	4,000 lm	3000 K	127 lm/W
910505102467	RC332V 42S/940 SEIA W62L62 IA4 MXO	4,200 lm	4000 K	133 lm/W
910505102468	RC332V 36S/940 SEIA W62L62 IA5 MXO	3,600 lm	4000 K	133 lm/W
910505102475	RC330V 36S/940 SEIA W30L120 IA4 MXO	3,600 lm	4000 K	136 lm/W
910505102477	RC330V 42S/930 SEIA W30L120 IA4 MXO	4,000 lm	3000 K	129 lm/W
910505102478	RC330V 42S/940 SEIA W30L120 IA4 MXO	4,200 lm	4000 K	135 lm/W
910505102497	RC330V 36S/940 SEIA W30L120 IA4 MXO SC	3,600 lm	4000 K	136 lm/W
910505102498	RC330V 36S/930 SEIA W30L120 IA4 MXO SC	3,400 lm	3000 K	129 lm/W
910505102451	RC330V 36S/940 SEIA W60L60 IA5 MXO	3,600 lm	4000 K	133 lm/W

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)
910505102450	RC330V 36S/940 SEIA W60L60 IA4 MXO	3,600 lm	4000 K	133 lm/W
910505102452	RC330V 42S/930 SEIA W60L60 IA4 MXO	4,000 lm	3000 K	127 lm/W
910505102453	RC330V 42S/940 SEIA W60L60 IA4 MXO	4,200 lm	4000 K	133 lm/W
910505102454	RC330V 42S/940 SEIA W60L60 IA4 ELW3 MXO	3,400 lm	4000 K	127 lm/W
910505102488	RC330V 36S/940 SEIA W60L60 IA4 MXO SC	3,600 lm	4000 K	133 lm/W
910505102489	RC330V 36S/940 SEIA W60L60 IA5 MXO SC	3,600 lm	4000 K	133 lm/W
910505102490	RC330V 42S/930 SEIA W60L60 IA4 MXO SC	4,000 lm	3000 K	127 lm/W
910505102491	RC330V 42S/940 SEIA W60L60 IA4 MXO SC	4,200 lm	4000 K	133 lm/W
910505102492	RC330V 42S/940 SEIA W60L60 IA4 ELW3MXOSC	4,200 lm	4000 K	133 lm/W
910505102469	RC330V 36S/940 PSD W30L120 MXO	3,600 lm	4000 K	136 lm/W
910505102470	RC330V 36S/940 PSD W30L120 MXO W5	3,600 lm	4000 K	136 lm/W
910505102471	RC330V 42S/940 PSD W30L120 MXO	4,200 lm	4000 K	135 lm/W
910505102472	RC330V 42S/930 PSD W30L120 MXO	4,000 lm	3000 K	129 lm/W
910505102473	RC330V 36S/940 WIA W30L120 MXO	3,600 lm	4000 K	136 lm/W
910505102474	RC330V 42S/940 WIA W30L120 MXO	4,200 lm	4000 K	135 lm/W
910505102476	RC330V 36S/940 SEIA W30L120 IA5 MXO	3,600 lm	4000 K	136 lm/W
910505102493	RC330V 36S/940 PSD W30L120 MXO SC	3,600 lm	4000 K	136 lm/W
910505102494	RC330V 36S/930 PSD W30L120 MXO SC	3,400 lm	3000 K	129 lm/W
910505102495	RC330V 42S/940 PSD W30L120 MXO SC	4,200 lm	4000 K	135 lm/W
910505102496	RC330V 42S/930 PSD W30L120 MXO SC	4,000 lm	3000 K	129 lm/W
910505102445	RC330V 36S/940 PSD W60L60 MXO	3,600 lm	4000 K	133 lm/W
910505102446	RC330V 36S/940 PSD W60L60 MXO W5	3,600 lm	4000 K	133 lm/W
910505102447	RC330V 42S/940 PSD W60L60 MXO	4,200 lm	4000 K	133 lm/W
910505102448	RC330V 42S/930 PSD W60L60 MXO	4,000 lm	3000 K	127 lm/W
910505102449	RC330V 36S/940 WIA W60L60 MXO	3,600 lm	4000 K	133 lm/W
910505102455	RC332V 36S/930 PSD W62L62 MXO	3,600 lm	3000 K	133 lm/W
910505102456	RC332V 36S/940 PSD W62L62 MXO	3,600 lm	4000 K	133 lm/W
910505102457	RC332V 42S/930 PSD W62L62 MXO	4,000 lm	3000 K	127 lm/W
910505102458	RC332V 42S/940 PSD W62L62 MXO	4,200 lm	4000 K	133 lm/W
910505102459	RC332V 36S/940 DEIA W62L62 MXO	3,600 lm	4000 K	133 lm/W
910505102460	RC332V 36S/930 WIA W62L62 MXO	3,400 lm	3000 K	127 lm/W
910505102461	RC332V 36S/940 WIA W62L62 MXO	3,600 lm	4000 K	133 lm/W
910505102462	RC332V 42S/930 WIA W62L62 MXO	4,000 lm	3000 K	127 lm/W
910505102463	RC332V 42S/940 WIA W62L62 MXO	4,200 lm	4000 K	133 lm/W
910505102484	RC330V 36S/940 PSD W60L60 MXO SC	3,600 lm	4000 K	133 lm/W
910505102485	RC330V 36S/930 PSD W60L60 MXO SC	3,400 lm	3000 K	127 lm/W
910505102486	RC330V 42S/940 PSD W60L60 MXO SC	4,200 lm	4000 K	133 lm/W
910505102487	RC330V 36S/940 WIA W60L60 MXO SC	3,600 lm	4000 K	133 lm/W

Operating and Electrical

Order Code	Full Product Name	Power Consumption
910505102464	RC332V 36S/930 SEIA W62L62 IA4 MXO	27 W
910505102465	RC332V 36S/940 SEIA W62L62 IA4 MXO	27 W
910505102466	RC332V 42S/930 SEIA W62L62 IA4 MXO	31.5 W
910505102467	RC332V 42S/940 SEIA W62L62 IA4 MXO	31.5 W
910505102468	RC332V 36S/940 SEIA W62L62 IA5 MXO	27 W
910505102475	RC330V 36S/940 SEIA W30L120 IA4 MXO	26.5 W
910505102477	RC330V 42S/930 SEIA W30L120 IA4 MXO	31 W
910505102478	RC330V 42S/940 SEIA W30L120 IA4 MXO	31 W
910505102497	RC330V 36S/940 SEIA W30L120 IA4 MXO SC	26.5 W
910505102498	RC330V 36S/930 SEIA W30L120 IA4 MXO SC	26.5 W
910505102451	RC330V 36S/940 SEIA W60L60 IA5 MXO	27 W
910505102450	RC330V 36S/940 SEIA W60L60 IA4 MXO	27 W
910505102452	RC330V 42S/930 SEIA W60L60 IA4 MXO	31.5 W
910505102453	RC330V 42S/940 SEIA W60L60 IA4 MXO	31.5 W
910505102454	RC330V 42S/940 SEIA W60L60 IA4 ELW3 MXO	31.5 W
910505102488	RC330V 36S/940 SEIA W60L60 IA4 MXO SC	27 W
910505102489	RC330V 36S/940 SEIA W60L60 IA5 MXO SC	27 W
910505102490	RC330V 42S/930 SEIA W60L60 IA4 MXO SC	31.5 W
910505102491	RC330V 42S/940 SEIA W60L60 IA4 MXO SC	31.5 W
910505102492	RC330V 42S/940 SEIA W60L60 IA4 ELW3MXOSC	31.5 W
910505102469	RC330V 36S/940 PSD W30L120 MXO	26.5 W
910505102470	RC330V 36S/940 PSD W30L120 MXO W5	26.5 W
910505102471	RC330V 42S/940 PSD W30L120 MXO	31 W
910505102472	RC330V 42S/930 PSD W30L120 MXO	31 W
910505102473	RC330V 36S/940 WIA W30L120 MXO	26.5 W
910505102474	RC330V 42S/940 WIA W30L120 MXO	31 W
910505102476	RC330V 36S/940 SEIA W30L120 IA5 MXO	26.5 W
910505102493	RC330V 36S/940 PSD W30L120 MXO SC	26.5 W
910505102494	RC330V 36S/930 PSD W30L120 MXO SC	26.5 W
910505102495	RC330V 42S/940 PSD W30L120 MXO SC	31 W
910505102496	RC330V 42S/930 PSD W30L120 MXO SC	31 W
910505102445	RC330V 36S/940 PSD W60L60 MXO	27 W
910505102446	RC330V 36S/940 PSD W60L60 MXO W5	27 W
910505102447	RC330V 42S/940 PSD W60L60 MXO	31.5 W
910505102448	RC330V 42S/930 PSD W60L60 MXO	31.5 W
910505102449	RC330V 36S/940 WIA W60L60 MXO	27 W
910505102455	RC332V 36S/930 PSD W62L62 MXO	27 W
910505102456	RC332V 36S/940 PSD W62L62 MXO	27 W
910505102457	RC332V 42S/930 PSD W62L62 MXO	31.5 W
910505102458	RC332V 42S/940 PSD W62L62 MXO	31.5 W
910505102459	RC332V 36S/940 DEIA W62L62 MXO	27 W

Order Code	Full Product Name	Power Consumption
910505102460	RC332V 36S/930 WIA W62L62 MXO	27 W
910505102461	RC332V 36S/940 WIA W62L62 MXO	27 W
910505102462	RC332V 42S/930 WIA W62L62 MXO	31.5 W
910505102463	RC332V 42S/940 WIA W62L62 MXO	31.5 W
910505102484	RC330V 36S/940 PSD W60L60 MXO SC	27 W
910505102485	RC330V 36S/930 PSD W60L60 MXO SC	27 W
910505102486	RC330V 42S/940 PSD W60L60 MXO SC	31.5 W
910505102487	RC330V 36S/940 WIA W60L60 MXO SC	27 W

Controls and Dimming

Order Code	Full Product Name	Embedded control
910505102464	RC332V 36S/930 SEIA W62L62 IA4 MXO	Interact SC200 sensor
910505102465	RC332V 36S/940 SEIA W62L62 IA4 MXO	Interact SC200 sensor
910505102466	RC332V 42S/930 SEIA W62L62 IA4 MXO	Interact SC200 sensor
910505102467	RC332V 42S/940 SEIA W62L62 IA4 MXO	Interact SC200 sensor
910505102468	RC332V 36S/940 SEIA W62L62 IA5 MXO	Interact SC200 sensor
910505102475	RC330V 36S/940 SEIA W30L120 IA4 MXO	Interact SC200 sensor
910505102477	RC330V 42S/930 SEIA W30L120 IA4 MXO	Interact SC200 sensor
910505102478	RC330V 42S/940 SEIA W30L120 IA4 MXO	Interact SC200 sensor
910505102497	RC330V 36S/940 SEIA W30L120 IA4 MXO SC	Interact SC200 sensor
910505102498	RC330V 36S/930 SEIA W30L120 IA4 MXO SC	Interact SC200 sensor
910505102451	RC330V 36S/940 SEIA W60L60 IA5 MXO	Interact SC1500 Multi-sensor bundle
910505102450	RC330V 36S/940 SEIA W60L60 IA4 MXO	Interact SC200 sensor
910505102452	RC330V 42S/930 SEIA W60L60 IA4 MXO	Interact SC200 sensor
910505102453	RC330V 42S/940 SEIA W60L60 IA4 MXO	Interact SC200 sensor
910505102454	RC330V 42S/940 SEIA W60L60 IA4 ELW3 MXO	Interact SC200 sensor
910505102488	RC330V 36S/940 SEIA W60L60 IA4 MXO SC	Interact SC200 sensor
910505102489	RC330V 36S/940 SEIA W60L60 IA5 MXO SC	Interact SC1500 Multi-sensor bundle
910505102490	RC330V 42S/930 SEIA W60L60 IA4 MXO SC	Interact SC200 sensor
910505102491	RC330V 42S/940 SEIA W60L60 IA4 MXO SC	Interact SC200 sensor
910505102492	RC330V 42S/940 SEIA W60L60 IA4 ELW3MXOSC	Interact SC200 sensor
910505102469	RC330V 36S/940 PSD W30L120 MXO	-
910505102470	RC330V 36S/940 PSD W30L120 MXO W5	-
910505102471	RC330V 42S/940 PSD W30L120 MXO	-
910505102472	RC330V 42S/930 PSD W30L120 MXO	-
910505102473	RC330V 36S/940 WIA W30L120 MXO	-
910505102474	RC330V 42S/940 WIA W30L120 MXO	-
910505102476	RC330V 36S/940 SEIA W30L120 IA5 MXO	Interact SC200 sensor
910505102493	RC330V 36S/940 PSD W30L120 MXO SC	-
910505102494	RC330V 36S/930 PSD W30L120 MXO SC	-
910505102495	RC330V 42S/940 PSD W30L120 MXO SC	-
910505102496	RC330V 42S/930 PSD W30L120 MXO SC	-

Order Code	Full Product Name	Embedded control
910505102445	RC330V 36S/940 PSD W60L60 MXO	-
910505102446	RC330V 36S/940 PSD W60L60 MXO W5	-
910505102447	RC330V 42S/940 PSD W60L60 MXO	-
910505102448	RC330V 42S/930 PSD W60L60 MXO	-
910505102449	RC330V 36S/940 WIA W60L60 MXO	-
910505102455	RC332V 36S/930 PSD W62L62 MXO	-
910505102456	RC332V 36S/940 PSD W62L62 MXO	-
910505102457	RC332V 42S/930 PSD W62L62 MXO	-
910505102458	RC332V 42S/940 PSD W62L62 MXO	-
910505102459	RC332V 36S/940 DEIA W62L62 MXO	-
910505102460	RC332V 36S/930 WIA W62L62 MXO	-
910505102461	RC332V 36S/940 WIA W62L62 MXO	-
910505102462	RC332V 42S/930 WIA W62L62 MXO	-
910505102463	RC332V 42S/940 WIA W62L62 MXO	-
910505102484	RC330V 36S/940 PSD W60L60 MXO SC	-
910505102485	RC330V 36S/930 PSD W60L60 MXO SC	-
910505102486	RC330V 42S/940 PSD W60L60 MXO SC	-
910505102487	RC330V 36S/940 WIA W60L60 MXO SC	-

Mechanical and Housing

Order Code	Full Product Name	Ingress protection code
910505102464	RC332V 36S/930 SEIA W62L62 IA4 MXO	IP20
910505102465	RC332V 36S/940 SEIA W62L62 IA4 MXO	IP20
910505102466	RC332V 42S/930 SEIA W62L62 IA4 MXO	IP20
910505102467	RC332V 42S/940 SEIA W62L62 IA4 MXO	IP20
910505102468	RC332V 36S/940 SEIA W62L62 IA5 MXO	IP20
910505102475	RC330V 36S/940 SEIA W30L120 IA4 MXO	IP20
910505102477	RC330V 42S/930 SEIA W30L120 IA4 MXO	IP20
910505102478	RC330V 42S/940 SEIA W30L120 IA4 MXO	IP20
910505102497	RC330V 36S/940 SEIA W30L120 IA4 MXO SC	IP20
910505102498	RC330V 36S/930 SEIA W30L120 IA4 MXO SC	IP20
910505102451	RC330V 36S/940 SEIA W60L60 IA5 MXO	IP20
910505102450	RC330V 36S/940 SEIA W60L60 IA4 MXO	IP20
910505102452	RC330V 42S/930 SEIA W60L60 IA4 MXO	IP20
910505102453	RC330V 42S/940 SEIA W60L60 IA4 MXO	IP20
910505102454	RC330V 42S/940 SEIA W60L60 IA4 ELW3 MXO	IP20
910505102488	RC330V 36S/940 SEIA W60L60 IA4 MXO SC	IP20
910505102489	RC330V 36S/940 SEIA W60L60 IA5 MXO SC	IP20
910505102490	RC330V 42S/930 SEIA W60L60 IA4 MXO SC	IP20
910505102491	RC330V 42S/940 SEIA W60L60 IA4 MXO SC	IP20
910505102492	RC330V 42S/940 SEIA W60L60 IA4 ELW3MXOSC	IP20
910505102469	RC330V 36S/940 PSD W30L120 MXO	IP20/44

Order Code	Full Product Name	Ingress protection code
910505102470	RC330V 36S/940 PSD W30L120 MXO W5	IP20/44
910505102471	RC330V 42S/940 PSD W30L120 MXO	IP20/44
910505102472	RC330V 42S/930 PSD W30L120 MXO	IP20/44
910505102473	RC330V 36S/940 WIA W30L120 MXO	IP20/44
910505102474	RC330V 42S/940 WIA W30L120 MXO	IP20/44
910505102476	RC330V 36S/940 SEIA W30L120 IA5 MXO	IP20
910505102493	RC330V 36S/940 PSD W30L120 MXO SC	IP20/44
910505102494	RC330V 36S/930 PSD W30L120 MXO SC	IP20/44
910505102495	RC330V 42S/940 PSD W30L120 MXO SC	IP20/44
910505102496	RC330V 42S/930 PSD W30L120 MXO SC	IP20/44
910505102445	RC330V 36S/940 PSD W60L60 MXO	IP20/44
910505102446	RC330V 36S/940 PSD W60L60 MXO W5	IP20/44
910505102447	RC330V 42S/940 PSD W60L60 MXO	IP20/44
910505102448	RC330V 42S/930 PSD W60L60 MXO	IP20/44
910505102449	RC330V 36S/940 WIA W60L60 MXO	IP20/44
910505102455	RC332V 36S/930 PSD W62L62 MXO	IP20/44
910505102456	RC332V 36S/940 PSD W62L62 MXO	IP20/44
910505102457	RC332V 42S/930 PSD W62L62 MXO	IP20/44
910505102458	RC332V 42S/940 PSD W62L62 MXO	IP20/44
910505102459	RC332V 36S/940 DEIA W62L62 MXO	IP20/44
910505102460	RC332V 36S/930 WIA W62L62 MXO	IP20/44
910505102461	RC332V 36S/940 WIA W62L62 MXO	IP20/44
910505102462	RC332V 42S/930 WIA W62L62 MXO	IP20/44
910505102463	RC332V 42S/940 WIA W62L62 MXO	IP20/44
910505102484	RC330V 36S/940 PSD W60L60 MXO SC	IP20/44
910505102485	RC330V 36S/930 PSD W60L60 MXO SC	IP20/44
910505102486	RC330V 42S/940 PSD W60L60 MXO SC	IP20/44
910505102487	RC330V 36S/940 WIA W60L60 MXO SC	IP20/44

Emergency Operation

Order Code	Full Product Name	Emergency lighting
910505102464	RC332V 36S/930 SEIA W62L62 IA4 MXO	DC operated central emergency lighting
910505102465	RC332V 36S/940 SEIA W62L62 IA4 MXO	DC operated central emergency lighting
910505102466	RC332V 42S/930 SEIA W62L62 IA4 MXO	DC operated central emergency lighting
910505102467	RC332V 42S/940 SEIA W62L62 IA4 MXO	DC operated central emergency lighting
910505102468	RC332V 36S/940 SEIA W62L62 IA5 MXO	DC operated central emergency lighting
910505102475	RC330V 36S/940 SEIA W30L120 IA4 MXO	DC operated central emergency lighting
910505102477	RC330V 42S/930 SEIA W30L120 IA4 MXO	DC operated central emergency lighting
910505102478	RC330V 42S/940 SEIA W30L120 IA4 MXO	DC operated central emergency lighting
910505102497	RC330V 36S/940 SEIA W30L120 IA4 MXO SC	DC operated central emergency lighting
910505102498	RC330V 36S/930 SEIA W30L120 IA4 MXO SC	DC operated central emergency lighting
910505102451	RC330V 36S/940 SEIA W60L60 IA5 MXO	DC operated central emergency lighting

Order Code	Full Product Name	Emergency lighting
910505102450	RC330V 36S/940 SEIA W60L60 IA4 MXO	DC operated central emergency lighting
910505102452	RC330V 42S/930 SEIA W60L60 IA4 MXO	DC operated central emergency lighting
910505102453	RC330V 42S/940 SEIA W60L60 IA4 MXO	DC operated central emergency lighting
910505102454	RC330V 42S/940 SEIA W60L60 IA4 ELW3 MXO	Emergency lighting 3 hours duration with Wireless Interface DC operated central emergency lighting
910505102488	RC330V 36S/940 SEIA W60L60 IA4 MXO SC	DC operated central emergency lighting
910505102489	RC330V 36S/940 SEIA W60L60 IA5 MXO SC	DC operated central emergency lighting
910505102490	RC330V 42S/930 SEIA W60L60 IA4 MXO SC	DC operated central emergency lighting
910505102491	RC330V 42S/940 SEIA W60L60 IA4 MXO SC	DC operated central emergency lighting
910505102492	RC330V 42S/940 SEIA W60L60 IA4 ELW3MXOSC	Emergency lighting 3 hours duration with Wireless Interface DC operated central emergency lighting
910505102469	RC330V 36S/940 PSD W30L120 MXO	-
910505102470	RC330V 36S/940 PSD W30L120 MXO W5	-
910505102471	RC330V 42S/940 PSD W30L120 MXO	-
910505102472	RC330V 42S/930 PSD W30L120 MXO	-
910505102473	RC330V 36S/940 WIA W30L120 MXO	-
910505102474	RC330V 42S/940 WIA W30L120 MXO	-
910505102476	RC330V 36S/940 SEIA W30L120 IA5 MXO	DC operated central emergency lighting
910505102493	RC330V 36S/940 PSD W30L120 MXO SC	-
910505102494	RC330V 36S/930 PSD W30L120 MXO SC	-
910505102495	RC330V 42S/940 PSD W30L120 MXO SC	-
910505102496	RC330V 42S/930 PSD W30L120 MXO SC	-
910505102445	RC330V 36S/940 PSD W60L60 MXO	-
910505102446	RC330V 36S/940 PSD W60L60 MXO W5	-
910505102447	RC330V 42S/940 PSD W60L60 MXO	-
910505102448	RC330V 42S/930 PSD W60L60 MXO	-
910505102449	RC330V 36S/940 WIA W60L60 MXO	-
910505102455	RC332V 36S/930 PSD W62L62 MXO	-
910505102456	RC332V 36S/940 PSD W62L62 MXO	-
910505102457	RC332V 42S/930 PSD W62L62 MXO	-
910505102458	RC332V 42S/940 PSD W62L62 MXO	-
910505102459	RC332V 36S/940 DEIA W62L62 MXO	DC operated central emergency lighting
910505102460	RC332V 36S/930 WIA W62L62 MXO	-
910505102461	RC332V 36S/940 WIA W62L62 MXO	-
910505102462	RC332V 42S/930 WIA W62L62 MXO	-
910505102463	RC332V 42S/940 WIA W62L62 MXO	-
910505102484	RC330V 36S/940 PSD W60L60 MXO SC	-
910505102485	RC330V 36S/930 PSD W60L60 MXO SC	-
910505102486	RC330V 42S/940 PSD W60L60 MXO SC	-
910505102487	RC330V 36S/940 WIA W60L60 MXO SC	-

Approval and Application

Order Code	Full Product Name	Glow-wire test
910505102464	RC332V 36S/930 SEIA W62L62 IA4 MXO	Temperature 650 °C, duration 30 s
910505102465	RC332V 36S/940 SEIA W62L62 IA4 MXO	Temperature 650 °C, duration 30 s
910505102466	RC332V 42S/930 SEIA W62L62 IA4 MXO	Temperature 650 °C, duration 30 s
910505102467	RC332V 42S/940 SEIA W62L62 IA4 MXO	Temperature 650 °C, duration 30 s
910505102468	RC332V 36S/940 SEIA W62L62 IA5 MXO	Temperature 650 °C, duration 30 s
910505102475	RC330V 36S/940 SEIA W30L120 IA4 MXO	Temperature 650 °C, duration 30 s
910505102477	RC330V 42S/930 SEIA W30L120 IA4 MXO	Temperature 650 °C, duration 30 s
910505102478	RC330V 42S/940 SEIA W30L120 IA4 MXO	Temperature 650 °C, duration 30 s
910505102497	RC330V 36S/940 SEIA W30L120 IA4 MXO SC	Temperature 650 °C, duration 30 s
910505102498	RC330V 36S/930 SEIA W30L120 IA4 MXO SC	Temperature 650 °C, duration 30 s
910505102451	RC330V 36S/940 SEIA W60L60 IA5 MXO	Temperature 650 °C, duration 30 s
910505102450	RC330V 36S/940 SEIA W60L60 IA4 MXO	Temperature 650 °C, duration 30 s
910505102452	RC330V 42S/930 SEIA W60L60 IA4 MXO	Temperature 650 °C, duration 30 s
910505102453	RC330V 42S/940 SEIA W60L60 IA4 MXO	Temperature 650 °C, duration 30 s
910505102454	RC330V 42S/940 SEIA W60L60 IA4 ELW3 MXO	Temperature 850 °C, duration 30 s
910505102488	RC330V 36S/940 SEIA W60L60 IA4 MXO SC	Temperature 650 °C, duration 30 s
910505102489	RC330V 36S/940 SEIA W60L60 IA5 MXO SC	Temperature 650 °C, duration 30 s
910505102490	RC330V 42S/930 SEIA W60L60 IA4 MXO SC	Temperature 650 °C, duration 30 s
910505102491	RC330V 42S/940 SEIA W60L60 IA4 MXO SC	Temperature 650 °C, duration 30 s
910505102492	RC330V 42S/940 SEIA W60L60 IA4 ELW3MXOSC	Temperature 850 °C, duration 30 s
910505102469	RC330V 36S/940 PSD W30L120 MXO	Temperature 650 °C, duration 30 s
910505102470	RC330V 36S/940 PSD W30L120 MXO W5	Temperature 650 °C, duration 30 s
910505102471	RC330V 42S/940 PSD W30L120 MXO	Temperature 650 °C, duration 30 s
910505102472	RC330V 42S/930 PSD W30L120 MXO	Temperature 650 °C, duration 30 s
910505102473	RC330V 36S/940 WIA W30L120 MXO	Temperature 650 °C, duration 30 s
910505102474	RC330V 42S/940 WIA W30L120 MXO	Temperature 650 °C, duration 30 s
910505102476	RC330V 36S/940 SEIA W30L120 IA5 MXO	Temperature 650 °C, duration 30 s
910505102493	RC330V 36S/940 PSD W30L120 MXO SC	Temperature 650 °C, duration 30 s
910505102494	RC330V 36S/930 PSD W30L120 MXO SC	Temperature 650 °C, duration 30 s
910505102495	RC330V 42S/940 PSD W30L120 MXO SC	Temperature 650 °C, duration 30 s
910505102496	RC330V 42S/930 PSD W30L120 MXO SC	Temperature 650 °C, duration 30 s
910505102445	RC330V 36S/940 PSD W60L60 MXO	Temperature 650 °C, duration 30 s
910505102446	RC330V 36S/940 PSD W60L60 MXO W5	Temperature 650 °C, duration 30 s
910505102447	RC330V 42S/940 PSD W60L60 MXO	Temperature 650 °C, duration 30 s
910505102448	RC330V 42S/930 PSD W60L60 MXO	Temperature 650 °C, duration 30 s
910505102449	RC330V 36S/940 WIA W60L60 MXO	Temperature 650 °C, duration 30 s
910505102455	RC332V 36S/930 PSD W62L62 MXO	Temperature 650 °C, duration 30 s
910505102456	RC332V 36S/940 PSD W62L62 MXO	Temperature 650 °C, duration 30 s
910505102457	RC332V 42S/930 PSD W62L62 MXO	Temperature 650 °C, duration 30 s
910505102458	RC332V 42S/940 PSD W62L62 MXO	Temperature 650 °C, duration 30 s
910505102459	RC332V 36S/940 DEIA W62L62 MXO	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Glow-wire test
910505102460	RC332V 36S/930 WIA W62L62 MXO	Temperature 650 °C, duration 30 s
910505102461	RC332V 36S/940 WIA W62L62 MXO	Temperature 650 °C, duration 30 s
910505102462	RC332V 42S/930 WIA W62L62 MXO	Temperature 650 °C, duration 30 s
910505102463	RC332V 42S/940 WIA W62L62 MXO	Temperature 650 °C, duration 30 s
910505102484	RC330V 36S/940 PSD W60L60 MXO SC	Temperature 650 °C, duration 30 s
910505102485	RC330V 36S/930 PSD W60L60 MXO SC	Temperature 650 °C, duration 30 s
910505102486	RC330V 42S/940 PSD W60L60 MXO SC	Temperature 650 °C, duration 30 s
910505102487	RC330V 36S/940 WIA W60L60 MXO SC	Temperature 650 °C, duration 30 s

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910505102464	RC332V 36S/930 SEIA W62L62 IA4 MXO	(0.43, 0.40) SDCM <3
910505102465	RC332V 36S/940 SEIA W62L62 IA4 MXO	(0.38, 0.38) SDCM <3
910505102466	RC332V 42S/930 SEIA W62L62 IA4 MXO	(0.43, 0.40) SDCM <3
910505102467	RC332V 42S/940 SEIA W62L62 IA4 MXO	(0.38, 0.38) SDCM <3
910505102468	RC332V 36S/940 SEIA W62L62 IA5 MXO	(0.38, 0.38) SDCM <3
910505102475	RC330V 36S/940 SEIA W30L120 IA4 MXO	(0.38, 0.38) SDCM <3
910505102477	RC330V 42S/930 SEIA W30L120 IA4 MXO	(0.43, 0.40) SDCM <3
910505102478	RC330V 42S/940 SEIA W30L120 IA4 MXO	(0.38, 0.38) SDCM <3
910505102497	RC330V 36S/940 SEIA W30L120 IA4 MXO SC	(0.38, 0.38) SDCM <3
910505102498	RC330V 36S/930 SEIA W30L120 IA4 MXO SC	(0.43, 0.40) SDCM <3
910505102451	RC330V 36S/940 SEIA W60L60 IA5 MXO	(0.38, 0.38) SDCM <3
910505102450	RC330V 36S/940 SEIA W60L60 IA4 MXO	(0.38, 0.38) SDCM <3
910505102452	RC330V 42S/930 SEIA W60L60 IA4 MXO	(0.43, 0.40) SDCM <3
910505102453	RC330V 42S/940 SEIA W60L60 IA4 MXO	(0.38, 0.38) SDCM <3
910505102454	RC330V 42S/940 SEIA W60L60 IA4 ELW3 MXO	(0.38, 0.38) SDCM <3
910505102488	RC330V 36S/940 SEIA W60L60 IA4 MXO SC	(0.38, 0.38) SDCM <3
910505102489	RC330V 36S/940 SEIA W60L60 IA5 MXO SC	(0.38, 0.38) SDCM <3
910505102490	RC330V 42S/930 SEIA W60L60 IA4 MXO SC	(0.43, 0.40) SDCM <3
910505102491	RC330V 42S/940 SEIA W60L60 IA4 MXO SC	(0.38, 0.38) SDCM <3
910505102492	RC330V 42S/940 SEIA W60L60 IA4 ELW3MXOSC	(0.38, 0.38) SDCM <3
910505102469	RC330V 36S/940 PSD W30L120 MXO	(0.38, 0.38) SDCM <3
910505102470	RC330V 36S/940 PSD W30L120 MXO W5	(0.38, 0.38) SDCM <3
910505102471	RC330V 42S/940 PSD W30L120 MXO	(0.38, 0.38) SDCM <3
910505102472	RC330V 42S/930 PSD W30L120 MXO	(0.43, 0.40) SDCM <3
910505102473	RC330V 36S/940 WIA W30L120 MXO	(0.38, 0.38) SDCM <3
910505102474	RC330V 42S/940 WIA W30L120 MXO	(0.38, 0.38) SDCM <3
910505102476	RC330V 36S/940 SEIA W30L120 IA5 MXO	(0.38, 0.38) SDCM <3
910505102493	RC330V 36S/940 PSD W30L120 MXO SC	(0.38, 0.38) SDCM <3
910505102494	RC330V 36S/930 PSD W30L120 MXO SC	(0.43, 0.40) SDCM <3
910505102495	RC330V 42S/940 PSD W30L120 MXO SC	(0.38, 0.38) SDCM <3
910505102496	RC330V 42S/930 PSD W30L120 MXO SC	(0.43, 0.40) SDCM <3


Order Code	Full Product Name	Initial chromaticity
910505102445	RC330V 36S/940 PSD W60L60 MXO	(0.38, 0.38) SDCM <3
910505102446	RC330V 36S/940 PSD W60L60 MXO W5	(0.38, 0.38) SDCM <3
910505102447	RC330V 42S/940 PSD W60L60 MXO	(0.38, 0.38) SDCM <3
910505102448	RC330V 42S/930 PSD W60L60 MXO	(0.43, 0.40) SDCM <3
910505102449	RC330V 36S/940 WIA W60L60 MXO	(0.38, 0.38) SDCM <3
910505102455	RC332V 36S/930 PSD W62L62 MXO	(0.43, 0.40) SDCM <3
910505102456	RC332V 36S/940 PSD W62L62 MXO	(0.38, 0.38) SDCM <3
910505102457	RC332V 42S/930 PSD W62L62 MXO	(0.43, 0.40) SDCM <3
910505102458	RC332V 42S/940 PSD W62L62 MXO	(0.38, 0.38) SDCM <3
910505102459	RC332V 36S/940 DEIA W62L62 MXO	(0.38, 0.38) SDCM <3
910505102460	RC332V 36S/930 WIA W62L62 MXO	(0.43, 0.40) SDCM <3
910505102461	RC332V 36S/940 WIA W62L62 MXO	(0.38, 0.38) SDCM <3
910505102462	RC332V 42S/930 WIA W62L62 MXO	(0.43, 0.40) SDCM <3
910505102463	RC332V 42S/940 WIA W62L62 MXO	(0.38, 0.38) SDCM <3
910505102484	RC330V 36S/940 PSD W60L60 MXO SC	(0.38, 0.38) SDCM <3
910505102485	RC330V 36S/930 PSD W60L60 MXO SC	(0.43, 0.40) SDCM <3
910505102486	RC330V 42S/940 PSD W60L60 MXO SC	(0.38, 0.38) SDCM <3
910505102487	RC330V 36S/940 WIA W60L60 MXO SC	(0.38, 0.38) SDCM <3

Product Data


Order Code	Full Product Name	Product family code
910505102464	RC332V 36S/930 SEIA W62L62 IA4 MXO	RC332V
910505102465	RC332V 36S/940 SEIA W62L62 IA4 MXO	RC332V
910505102466	RC332V 42S/930 SEIA W62L62 IA4 MXO	RC332V
910505102467	RC332V 42S/940 SEIA W62L62 IA4 MXO	RC330V
910505102468	RC332V 36S/940 SEIA W62L62 IA5 MXO	RC332V
910505102475	RC330V 36S/940 SEIA W30L120 IA4 MXO	RC330V
910505102477	RC330V 42S/930 SEIA W30L120 IA4 MXO	RC330V
910505102478	RC330V 42S/940 SEIA W30L120 IA4 MXO	RC330V
910505102497	RC330V 36S/940 SEIA W30L120 IA4 MXO SC	RC330V
910505102498	RC330V 36S/930 SEIA W30L120 IA4 MXO SC	RC330V
910505102451	RC330V 36S/940 SEIA W60L60 IA5 MXO	RC330V
910505102450	RC330V 36S/940 SEIA W60L60 IA4 MXO	RC330V
910505102452	RC330V 42S/930 SEIA W60L60 IA4 MXO	RC330V
910505102453	RC330V 42S/940 SEIA W60L60 IA4 MXO	RC330V
910505102454	RC330V 42S/940 SEIA W60L60 IA4 ELW3 MXO	RC330V
910505102488	RC330V 36S/940 SEIA W60L60 IA4 MXO SC	RC330V
910505102489	RC330V 36S/940 SEIA W60L60 IA5 MXO SC	RC330V
910505102490	RC330V 42S/930 SEIA W60L60 IA4 MXO SC	RC330V
910505102491	RC330V 42S/940 SEIA W60L60 IA4 MXO SC	RC330V
910505102492	RC330V 42S/940 SEIA W60L60 IA4 ELW3MXOSC	RC330V
910505102469	RC330V 36S/940 PSD W30L120 MXO	RC330V

Order Code	Full Product Name	Product family code
910505102470	RC330V 36S/940 PSD W30L120 MXO W5	RC330V
910505102471	RC330V 42S/940 PSD W30L120 MXO	RC330V
910505102472	RC330V 42S/930 PSD W30L120 MXO	RC330V
910505102473	RC330V 36S/940 WIA W30L120 MXO	RC330V
910505102474	RC330V 42S/940 WIA W30L120 MXO	RC330V
910505102476	RC330V 36S/940 SEIA W30L120 IA5 MXO	RC330V
910505102493	RC330V 36S/940 PSD W30L120 MXO SC	RC330V
910505102494	RC330V 36S/930 PSD W30L120 MXO SC	RC330V
910505102495	RC330V 42S/940 PSD W30L120 MXO SC	RC330V
910505102496	RC330V 42S/930 PSD W30L120 MXO SC	RC330V
910505102445	RC330V 36S/940 PSD W60L60 MXO	RC330V
910505102446	RC330V 36S/940 PSD W60L60 MXO W5	RC330V
910505102447	RC330V 42S/940 PSD W60L60 MXO	RC330V
910505102448	RC330V 42S/930 PSD W60L60 MXO	RC330V
910505102449	RC330V 36S/940 WIA W60L60 MXO	RC330V
910505102455	RC332V 36S/930 PSD W62L62 MXO	RC332V
910505102456	RC332V 36S/940 PSD W62L62 MXO	RC332V
910505102457	RC332V 42S/930 PSD W62L62 MXO	RC332V
910505102458	RC332V 42S/940 PSD W62L62 MXO	RC332V
910505102459	RC332V 36S/940 DEIA W62L62 MXO	RC332V
910505102460	RC332V 36S/930 WIA W62L62 MXO	RC332V
910505102461	RC332V 36S/940 WIA W62L62 MXO	RC332V
910505102462	RC332V 42S/930 WIA W62L62 MXO	RC332V
910505102463	RC332V 42S/940 WIA W62L62 MXO	RC332V
910505102484	RC330V 36S/940 PSD W60L60 MXO SC	RC330V
910505102485	RC330V 36S/930 PSD W60L60 MXO SC	RC330V
910505102486	RC330V 42S/940 PSD W60L60 MXO SC	RC330V
910505102487	RC330V 36S/940 WIA W60L60 MXO SC	RC330V


Polar normal diagrams




RC330VI - 910505102491




RC330VI - 910505102445




RC330VI - 910505102447




RC330VI - 910505102475




RC330VI - 910505102476




RC330VI - 910505102497




RC330VI - 910505102446




RC330VI - 910505102495




RC330VI - 910505102448




RC330VI - 910505102477




RC330VI - 910505102485




RC330VI - 910505102468




RC330VI - 910505102498




RC330VI - 910505102450




RC330VI - 910505102449




RC330VI - 910505102474




RC330VI - 910505102486




RC330VI - 910505102494




RC330VI - 910505102452




RC330VI - 910505102478




RC330VI - 910505102455




RC330VI - 910505102490




RC330VI - 910505102454




RC330VI - 910505102484




RC330VI - 910505102458




RC330VI - 910505102464




RC330VI - 910505102456




RC330VI - 910505102470




RC330VI - 910505102488




RC330VI - 910505102487




RC330VI - 910505102467




RC330VI - 910505102457




RC330VI - 910505102469




RC330VI - 910505102496




RC330VI - 910505102461




RC330VI - 910505102492




RC330VI - 910505102459




RC330VI - 910505102460




RC330VI - 910505102465




RC330VI - 910505102463




RC330VI - 910505102472




RC330VI - 910505102462




RC330VI - 910505102493




RC330VI - 910505102466




RC330VI - 910505102453




RC330VI - 910505102473



RC330VI - 910505102451



RC330VI - 910505102471



RC330VI - 910505102489