




FlexBlend - Unlocking the potential of LED lighting in offices

Office owners and staff responsible for lighting operations are searching for high quality yet energy-efficient lighting that complies with norms and regulations. Designed to support these needs, Philips FlexBlend is enabling building owners to fully optimize their lighting operations, by offering office-compliant lighting with an attractive return on investment. Furthermore, FlexBlend provides the required flexibility by being easy applied on different ceiling types as well as in different office spaces like open office or meeting rooms. Though technology is changing fast, the ideal lighting solution is also expected to be ready to incorporate innovations and future advances that can help optimize operations further. For this reason, Philips FlexBlend is also ready to be connected to controls such as Actilume or used together with the Philips SpaceWise lighting system. It can also be connected to software-based lighting systems like Interact Office, which provides the luminaire with further intelligence and enables it to collect valuable data about its environment

Benefits

- High-quality office-compliant lighting
- Choice of three different exit-windows
- Fast return on investment

- Application flexibility
- Scalable and ready to be connected to controls and lighting systems

Applications

- Offices
- Education

- Healthcare
- Banks

Features

- Fully office-compliant (UGR <19)
- Homogenous and uniform light effect

- Dimensional variety, local options
- Various mounting options
- Integrated sensors
- Can be combined with Philips ActiLume and SpaceWise systems
- Ready to be connected to software based lighting systems such as Interact Office

Versions



FlexBlend Recessed RC340B
W15L120 MLO VPC




FlexBlend Recessed-RC340B
W30L120 MLO VPC



Upgradable sensor




FlexBlend Recessed



FlexBlend Recessed RC340B
W60L60 OPA VPC



FlexBlend RC340B W30L120
U4



FlexBlend Recessed RC340B
W60L60 MLO CPC



0 FlexBlend Recessed-RC340B
W30L120 MLO VPC



FlexBlend Recessed RC340B
W60L60 PCS VPC



FlexBlend Recessed



FlexBlend Recessed



FlexBlend Recessed



FlexBlend Recessed RC340B
W60L60 MLO VPC



FlexBlend Recessed RC340B
W60L60 MLO PCV



Upgradable sensor



FlexBlend Recessed



FlexBlend Recessed RC342B
W62L62 MLO VPC



FlexBlend Recessed

Technical drawing of the 'Eco' cabinet showing front, side, and top views with dimensions.

Front View: The cabinet has a total height of 685 mm and a width of 597 mm. The upper section is 672 mm high and contains two horizontal drawers. The lower section is 13 mm high.


Side View: The cabinet has a total depth of 79 mm. The upper section is 61 mm high. The lower section is 8 mm high. The depth of the drawers is 361 mm. The depth of the cabinet body is 7 mm.

Top View: The cabinet has a total width of 597 mm and a total depth of 571 mm. The depth of the drawers is 361 mm. The depth of the cabinet body is 7 mm.


Inset: A small inset drawing shows the cabinet's profile with a height of 150 mm.

Technical drawing of a rectangular plate. The main view shows a plate with a width of 120 and a height of 50. A detail view (A-A) shows a cross-section of the plate, indicating a thickness of 10 and a width of 120. The detail view also shows a fillet radius of R10 and a chamfer of 1x45°.


Data subject to change



RC340B 36S/840 DEIA W30L135 FLC2 DLO SC




RC342B 42S/940 DEIA W31L125 VPC O




RC340B 42S/930 DEIA W30L120 VPC PCS W3W2


RC340B 42S/930 DEIA W30L120 CPC MLO W3W2




FLEXBLEND RECESSED, module 625 - 940 neutral white - Power supply unit with DALI interface - Plug-in connector 3-pole Wieland/Adels compatible




RC342B 42S/940 DEIA W62L62 CPC PCS



RC340B 42S/940 DEIA W60L60 CPC MLO



FLEXBLEND RECESSED, module 625 - 940 neutral white - Power supply unit with DALI interface - Plug-in connector 3-pole Wieland/Adels compatible



RC340B 42S/940 DEIA W60L60 VPC O

Product details



Upgradable sensor



O_FlexBlend Recessed-RC342B_W62L62_MLO_VPC




FlexBlend Recessed-RC340B_MLO_DPP




FlexBlend Recessed-RC340B_W60L60_Backcover_VPC



FlexBlend Recessed-
RC340B_W60L60_CPC
brackets



FlexBlend Recessed-
RC340B_W60L60_CPC
brackets_B



FlexBlend Recessed-
RC340B_OPA_ DPP



FlexBlend Recessed-
RC340B_PCS_ DPP



0_FlexBlend Recessed-
RC340B_W60L60_PCS_VPC



FlexBlend Recessed-
RC340B_W60L60_CPC
brackets_A



FlexBlend Recessed RC340B
PIP Open



FlexBlend Recessed-
RC340B_W60L60_backcover_P
CV



0_FlexBlend Recessed-
RC340B_W60L60_MLO_VPC



0_FlexBlend Recessed-
RC340B_W60L60_MLO_CPC



FlexBlend Recessed-RC340B
PIP Closed



FlexBlend_RC340B_W30L120_
U4_DPP



FlexBlend Recessed-
RC340B_W60L60_backcover_C
PC

General Information

Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Service tag	Yes

Light Technical

Beam angle of light source	120 degree(s)
Optic type	Wide beam

Operating and Electrical

Line Frequency	50 to 60 Hz
----------------	-------------

Controls and Dimming

Maximum dim level	1%
-------------------	----

Mechanical and Housing

Housing Color	White
---------------	-------

Emergency Operation

Rated duration of the emergency lighting (when fully charged)	3 hour(s)
---	-----------

Approval and Application

Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	+10 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.01 %
-------------------------------	--------

Light Technical

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Color rendering index (CRI)
910925867015	RC340B 36S/940 PSE W15L120 VPC MLO	3,600 lm	4000 K	95 lm/W	>90
910925867016	RC340B 36S/940 DEIA W15L120 VPC MLO	3,600 lm	4000 K	95 lm/W	>90
910925867017	RC340B 42S/940 PSE W15L120 VPC MLO	4,200 lm	4000 K	93 lm/W	>90
910925867018	RC340B 42S/940 DEIA W15L120 VPC MLO	4,200 lm	4000 K	93 lm/W	>90
910925867019	RC340B 36S/940 PSU W15L120 VPC MLO ELP3	3,600 lm	4000 K	95 lm/W	>90
910925867020	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	3,600 lm	4000 K	95 lm/W	>90
910925867021	RC340B 42S/940 PSU W15L120 VPC MLO ELP3	4,200 lm	4000 K	93 lm/W	>90
910925867022	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	4,200 lm	4000 K	93 lm/W	>90
910925867024	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	3,600 lm	4000 K	95 lm/W	>90
910925867026	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	4,200 lm	4000 K	93 lm/W	>90
910925867149	RC342B 28S/940 DEIA W15L125 VPC MLO	2,800 lm	4000 K	110 lm/W	>90
910925867150	RC342B 36S/940 DEIA W15L125 VPC MLO	3,600 lm	4000 K	95 lm/W	>90
910925867153	RC342B 36S/940 DEIA W17L125 PCV MLO	3,600 lm	4000 K	95 lm/W	>90
910925867164	RC342B 28S/940 DEIA W15L125 VPC PCS	2,800 lm	4000 K	127 lm/W	>90
910925867165	RC342B 36S/940 DEIA W15L125 VPC PCS	3,600 lm	4000 K	138 lm/W	>90
910925867166	RC342B 42S/940 DEIA W15L125 VPC PCS	4,200 lm	4000 K	138 lm/W	>90
910925867169	RC342B 36S/940 DEIA W17L125 PCV PCS	3,600 lm	4000 K	144 lm/W	>90
910925867180	RC342B 28S/940 DEIA W15L125 VPC O	2,800 lm	4000 K	124 lm/W	>90
910925867181	RC342B 36S/940 DEIA W15L125 VPC O	3,600 lm	4000 K	126 lm/W	>90
910925867182	RC342B 42S/940 DEIA W15L125 VPC O	4,200 lm	4000 K	125 lm/W	>90
910925866979	RC340B 36S/940 DEIA W30L120 VPC MLO	3,600 lm	4000 K	95 lm/W	>90

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Color rendering index (CRI)
910925866982	RC342B 36S/940 PSE W31L125 VPC MLO	3,600 lm	4000 K	95 lm/W	>90
910925866983	RC342B 36S/940 DEIA W31L125 VPC MLO	3,600 lm	4000 K	95 lm/W	>90
910925867030	RC340B 42S/940 DEIA W30L120 VPC MLO W3W2	4,200 lm	4000 K	93 lm/W	>90
910925867031	RC340B 42S/940 DEIA W30L120 CPC MLO W3W2	4,200 lm	4000 K	93 lm/W	>90
910925867032	RC340B 42S/930 DEIA W30L120 VPC MLO W3W2	4,200 lm	3000 K	93 lm/W	>90
910925867033	RC340B 42S/930 DEIA W30L120 CPC MLO W3W2	4,200 lm	3000 K	93 lm/W	>90
910925867038	RC340B 42S/940 DEIA W30L120 VPC PCS W3W2	4,200 lm	4000 K	138 lm/W	>90
910925867039	RC340B 42S/940 DEIA W30L120 CPC PCS W3W2	4,200 lm	4000 K	138 lm/W	>90
910925867042	RC340B 42S/930 DEIA W30L120 VPC PCS W3W2	4,200 lm	3000 K	138 lm/W	>90
910925867147	RC342B 28S/940 DEIA W31L125 VPC MLO	2,800 lm	4000 K	110 lm/W	>90
910925867161	RC342B 28S/940 DEIA W31L125 VPC PCS	2,800 lm	4000 K	127 lm/W	>90
910925867162	RC342B 36S/940 DEIA W31L125 VPC PCS	3,600 lm	4000 K	138 lm/W	>90
910925867163	RC342B 42S/940 DEIA W31L125 VPC PCS	4,200 lm	4000 K	138 lm/W	>90
910925867177	RC342B 28S/940 DEIA W31L125 VPC O	2,800 lm	4000 K	124 lm/W	>90
910925867178	RC342B 36S/940 DEIA W31L125 VPC O	3,600 lm	4000 K	126 lm/W	>90
910925867179	RC342B 42S/940 DEIA W31L125 VPC O	4,200 lm	4000 K	125 lm/W	>90
910925868910	RC340B 36S/930 SEIA W60L60 VPC MLO U4	3,600 lm	3000 K	95 lm/W	>90
910925868911	RC340B 36S/930 SRD W60L60 VPC MLO U4	3,600 lm	3000 K	95 lm/W	>90
910925868912	RC340B 36S/930 SEIA W60L60 VPC PCS U4	3,600 lm	3000 K	138 lm/W	>90
910925868913	RC340B 36S/930 SEIA W60L60 VPC PCS U4 SC	3,600 lm	3000 K	138 lm/W	>90
910925868914	RC340B 36S/940 SEIA W60L60 VPC MLO U4	3,600 lm	4000 K	95 lm/W	>90
910925868915	RC340B 36S/940 SEIA W60L60 VPC MLO U4 SC	3,600 lm	4000 K	95 lm/W	>90
910925868916	RC340B 36S/940 SEIA W60L60 VPC PCS U4	3,600 lm	4000 K	138 lm/W	>90
910925868917	RC340B 36S/940 SEIA W60L60 VPC PCS U4 SC	3,600 lm	4000 K	138 lm/W	>90
910925868918	RC340B 36S/940 SEIA W60L60 VPC PCS U4 W3	3,600 lm	4000 K	138 lm/W	>90
910925868920	RC340B 42S/940 SEIA W60L60 VPC PCS U4 W3	4,200 lm	4000 K	140 lm/W	>90
910925868921	RC342B 28S/940 SEIA W62L62 VPC MLO U4	2,800 lm	4000 K	110 lm/W	>90
910925868922	RC342B 28S/940 SEIA W62L62 VPC PCS U4	2,800 lm	4000 K	140 lm/W	>90
910925868924	RC342B 36S/940 SEIA W62L62 VPC MLO U4	3,600 lm	4000 K	95 lm/W	>90
910925868925	RC342B 36S/940 SEIA W62L62 VPC PCS U4	3,600 lm	4000 K	138 lm/W	>90
910925868927	RC342B 42S/940 SEIA W62L62 VPC MLO U4	4,200 lm	4000 K	93 lm/W	>90
910925868928	RC342B 42S/940 SEIA W62L62 VPC PCS U4	4,200 lm	4000 K	140 lm/W	>90
910505105985	RC340B 36S/940 SEIA W60L60 VPC MXO U4	3,600 lm	4000 K	194 lm/W	>90
910925866986	RC340B 36S/940 PSU W60L60 VPC O ELP3	3,600 lm	4000 K	126 lm/W	>90
910925866987	RC340B 36S/940 DIA W60L60 VPC O ELP3	3,600 lm	4000 K	126 lm/W	>90
910925867001	RC340B 42S/940 PSE W60L60 VPC O	4,200 lm	4000 K	125 lm/W	>90
910925867002	RC340B 42S/940 DEIA W60L60 VPC O	4,200 lm	4000 K	125 lm/W	>90
910925867006	RC340B 42S/940 PSU W60L60 VPC O ELP3	4,200 lm	4000 K	125 lm/W	>90
910925867007	RC340B 42S/940 DIA W60L60 VPC O ELP3	4,200 lm	4000 K	125 lm/W	>90
910925867012	RC340B 42S/940 DIA W60L60 VPC O ELD3	4,200 lm	4000 K	125 lm/W	>90
910925867061	RC340B 36S/940 PSE W60L60 VPC O SC	3,600 lm	4000 K	126 lm/W	>90
910925867062	RC340B 36S/940 DEIA W60L60 VPC O SC	3,600 lm	4000 K	126 lm/W	>90

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Color rendering index (CRI)
910925868919	RC340B 42S/940 SEIA W30L120 VPC PCS U4W3	4,200 lm	4000 K	140 lm/W	>90
910925868923	RC342B 36S/940 SEIA W31L125 VPC PCS U4	3,600 lm	4000 K	138 lm/W	>90
910925868926	RC342B 42S/940 SEIA W31L125 VPC PCS U4	4,200 lm	4000 K	140 lm/W	>90
910925866969	RC340B 36S/940 DEIA W60L60 VPC MLO	3,600 lm	4000 K	95 lm/W	>90
910925867023	RC340B 42S/930 DEIA W60L60 CPC MLO W3W2	4,200 lm	3000 K	93 lm/W	>90
910925867028	RC340B 42S/940 DEIA W60L60 CPC MLO W3W2	4,200 lm	4000 K	93 lm/W	>90
910925867036	RC340B 42S/940 DEIA W60L60 CPC PCS W3W2	4,200 lm	4000 K	138 lm/W	>90
910925867040	RC340B 42S/930 DEIA W60L60 CPC PCS W3W2	4,200 lm	3000 K	138 lm/W	>90
910925867046	RC340B 36S/940 PSE W60L60 CPC MLO	3,600 lm	4000 K	95 lm/W	>90
910925867047	RC340B 42S/940 PSE W60L60 CPC MLO	4,200 lm	4000 K	93 lm/W	>90
910925867048	RC340B 42S/940 DEIA W60L60 CPC MLO	4,200 lm	4000 K	93 lm/W	>90
910925867167	RC342B 42S/940 DEIA W62L62 CPC PCS	4,200 lm	4000 K	138 lm/W	>90
910925867068	RC340B 42S/930 DEIA W30L120 CPC PCS W3W2	4,200 lm	3000 K	138 lm/W	>90
910925866967	RC340B 36S/940 DEIA W60L60 VPC O	3,600 lm	4000 K	126 lm/W	>90
910925866972	RC340B 36S/940 PSE W60L60 VPC PCS	3,600 lm	4000 K	138 lm/W	>90
910925866973	RC340B 36S/940 DEIA W60L60 VPC PCS	3,600 lm	4000 K	138 lm/W	>90
910925866977	RC340B 36S/940 DEIA W60L60 CPC MLO	3,600 lm	4000 K	95 lm/W	>90
910925866990	RC340B 36S/940 PSU W60L60 VPC PCS ELP3	3,600 lm	4000 K	138 lm/W	>90
910925866991	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	3,600 lm	4000 K	138 lm/W	>90
910925866997	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	3,600 lm	4000 K	138 lm/W	>90
910925867003	RC340B 42S/940 PSE W60L60 VPC PCS	4,200 lm	4000 K	138 lm/W	>90
910925867004	RC340B 42S/940 DEIA W60L60 VPC PCS	4,200 lm	4000 K	138 lm/W	>90
910925867008	RC340B 42S/940 PSU W60L60 VPC PCS ELP3	4,200 lm	4000 K	138 lm/W	>90
910925867009	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	4,200 lm	4000 K	138 lm/W	>90
910925867034	RC340B 42S/930 DEIA W60L60 VPC PCS W3W2	4,200 lm	3000 K	138 lm/W	>90
910925867035	RC340B 42S/940 DEIA W60L60 VPC PCS W3W2	4,200 lm	4000 K	138 lm/W	>90
910925867044	RC340B 36S/940 PSE W60L60 CPC PCS PIP	3,600 lm	4000 K	138 lm/W	>90
910925867045	RC340B 36S/940 DEIA W60L60 CPC PCS	3,600 lm	4000 K	138 lm/W	>90
910925867049	RC340B 42S/940 PSE W60L60 CPC PCS	4,200 lm	4000 K	138 lm/W	>90
910925867050	RC340B 42S/940 DEIA W60L60 CPC PCS	4,200 lm	4000 K	138 lm/W	>90
910925867065	RC340B 36S/940 PSE W60L60 VPC PCS SC	3,600 lm	4000 K	138 lm/W	>90
910925867066	RC340B 36S/940 DEIA W60L60 VPC PCS SC	3,600 lm	4000 K	138 lm/W	>90
910505105982	RC340B 36S/940 SEIA W60L60 VPC DLO U4	3,600 lm	4000 K	157 lm/W	>90
910505105987	RC340B 42S/840 SEIA W60L60 VPC PCS U4 SC	4,200 lm	4000 K	190 lm/W	>80
910505105990	RC340B 36S/840 SEIA W67L67 FLC4DLO U4 SC	3,600 lm	4000 K	151 lm/W	>80
910505105989	RC342B 42S/840 DEIA W62L62 VPC PCS	4,200 lm	4000 K	190 lm/W	>80
910505105984	RC342B 36S/940 DEIA W31L125 VPC DLO	3,600 lm	4000 K	157 lm/W	>90
910505105988	RC340B 42S/840 PSU W30L120 VPC PCS ELB3	4,200 lm	4000 K	190 lm/W	>80
910505105992	RC340B 36S/840 DEIA W30L135 FLC2 DLO SC	3,600 lm	4000 K	151 lm/W	>80
910925866966	RC340B 36S/940 PSE W60L60 VPC O	3,600 lm	4000 K	126 lm/W	>90
910925866980	RC342B 36S/940 PSE W62L62 VPC MLO	3,600 lm	4000 K	95 lm/W	>90
910925866988	RC340B 36S/940 PSU W60L60 VPC MLO ELP3	3,600 lm	4000 K	95 lm/W	>90

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Color rendering index (CRI)
910925866989	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	3,600 lm	4000 K	95 lm/W	>90
910925866993	RC340B 36S/940 DIA W60L60 VPC O ELD3	3,600 lm	4000 K	126 lm/W	>90
910925866995	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	3,600 lm	4000 K	95 lm/W	>90
910925866999	RC340B 42S/940 DEIA W60L60 VPC MLO	4,200 lm	4000 K	93 lm/W	>90
910925867010	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	4,200 lm	4000 K	93 lm/W	>90
910925867013	RC340B 42S/930 DEIA W60L60 VPC MLO W3W2	4,200 lm	3000 K	93 lm/W	>90
910925867027	RC340B 42S/940 DEIA W60L60 VPC MLO W3W2	4,200 lm	4000 K	93 lm/W	>90
910925867043	RC340B 42S/940 PSE W60L60 VPC MLO	4,200 lm	4000 K	93 lm/W	>90
910925867063	RC340B 36S/940 PSE W60L60 VPC MLO SC	3,600 lm	4000 K	95 lm/W	>90
910925867064	RC340B 36S/940 DEIA W60L60 VPC MLO SC	3,600 lm	4000 K	95 lm/W	>90
910925866970	RC340B 36S/940 POE W60L60 VPC MLO	3,600 lm	4000 K	95 lm/W	>90
910925867014	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	4,200 lm	4000 K	138 lm/W	>90
910925867025	RC340B 42S/930 DEIA W60L60 PCV MLO W3W2	4,200 lm	3000 K	93 lm/W	>90
910925867029	RC340B 42S/940 DEIA W60L60 PCV MLO W3W2	4,200 lm	4000 K	93 lm/W	>90
910925867037	RC340B 42S/940 DEIA W60L60 PCV PCS W3W2	4,200 lm	4000 K	138 lm/W	>90
910925867041	RC340B 42S/930 DEIA W60L60 PCV PCS W3W2	4,200 lm	3000 K	138 lm/W	>90
910925867168	RC340B 36S/940 DEIA W60L60 PCV PCS	3,600 lm	4000 K	138 lm/W	>90
910925867221	RC340B 36S/940 POE W60L60 VPC MLO U0	3,600 lm	4000 K	95 lm/W	>90
910925867224	RC340B 36S/940 POE W60L60 VPC PCS U0	3,600 lm	4000 K	144 lm/W	>90
910505105983	RC340B 42S/940 SEIA W30L120 VPC DLO U4	4,200 lm	4000 K	185 lm/W	>90
910505105991	RC340B 42S/840 SEIA W30L135 FLC4DLOU4SC	4,200 lm	4000 K	177 lm/W	>80
910925866968	RC340B 36S/940 PSE W60L60 VPC MLO PIP	3,600 lm	4000 K	95 lm/W	>90
910925866978	RC340B 36S/940 DEIA W60L60 PCV MLO	3,600 lm	4000 K	95 lm/W	>90
910925866981	RC342B 36S/940 DEIA W62L62 VPC MLO	3,600 lm	4000 K	95 lm/W	>90
910925867145	RC342B 28S/940 DEIA W62L62 VPC MLO	2,800 lm	4000 K	110 lm/W	>90
910925867158	RC342B 28S/940 DEIA W62L62 VPC PCS	2,800 lm	4000 K	127 lm/W	>90
910925867159	RC342B 36S/940 DEIA W62L62 VPC PCS	3,600 lm	4000 K	144 lm/W	>90
910925867160	RC342B 42S/940 DEIA W62L62 VPC PCS	4,200 lm	4000 K	138 lm/W	>90
910925867174	RC342B 28S/940 DEIA W62L62 VPC O	2,800 lm	4000 K	124 lm/W	>90
910925867175	RC342B 36S/940 DEIA W62L62 VPC O	3,600 lm	4000 K	126 lm/W	>90
910925867176	RC342B 42S/940 DEIA W62L62 VPC O	4,200 lm	4000 K	125 lm/W	>90
910505105986	RC342B 28S/940 DEIA W31L125 VPC MXO	2,800 lm	4000 K	149 lm/W	>90

Operating and Electrical

Order Code	Full Product Name	Input Voltage	Power Consumption	Suitable for random switching	Protection class IEC
910925867015	RC340B 36S/940 PSE W15L120 VPC MLO	220 to 240 V	38 W	Yes	Safety class I
910925867016	RC340B 36S/940 DEIA W15L120 VPC MLO	220 to 240 V	38 W	Yes	Safety class I
910925867017	RC340B 42S/940 PSE W15L120 VPC MLO	220 to 240 V	45 W	Yes	Safety class I
910925867018	RC340B 42S/940 DEIA W15L120 VPC MLO	220 to 240 V	45 W	Yes	Safety class I
910925867019	RC340B 36S/940 PSU W15L120 VPC MLO ELP3	220 to 240 V	38 W	Yes	Safety class I

Order Code	Full Product Name	Input Voltage	Power Consumption	Suitable for random switching	Protection class IEC
910925867020	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	220 to 240 V	38 W	Yes	Safety class I
910925867021	RC340B 42S/940 PSU W15L120 VPC MLO ELP3	220 to 240 V	45 W	Yes	Safety class I
910925867022	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	220 to 240 V	45 W	Yes	Safety class I
910925867024	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	220 to 240 V	38 W	Yes	Safety class I
910925867026	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	220 to 240 V	45 W	Yes	Safety class I
910925867149	RC342B 28S/940 DEIA W15L125 VPC MLO	220 to 240 V	25.5 W	Yes	Safety class I
910925867150	RC342B 36S/940 DEIA W15L125 VPC MLO	220 to 240 V	38 W	Yes	Safety class I
910925867153	RC342B 36S/940 DEIA W17L125 PCV MLO	220 to 240 V	38 W	Yes	Safety class I
910925867164	RC342B 28S/940 DEIA W15L125 VPC PCS	220 to 240 V	22 W	Yes	Safety class I
910925867165	RC342B 36S/940 DEIA W15L125 VPC PCS	220 to 240 V	26 W	Yes	Safety class I
910925867166	RC342B 42S/940 DEIA W15L125 VPC PCS	220 to 240 V	30.5 W	Yes	Safety class I
910925867169	RC342B 36S/940 DEIA W17L125 PCV PCS	220 to 240 V	25 W	Yes	Safety class I
910925867180	RC342B 28S/940 DEIA W15L125 VPC O	220 to 240 V	22.5 W	Yes	Safety class I
910925867181	RC342B 36S/940 DEIA W15L125 VPC O	220 to 240 V	28.5 W	Yes	Safety class I
910925867182	RC342B 42S/940 DEIA W15L125 VPC O	220 to 240 V	33.5 W	Yes	Safety class I
910925866979	RC340B 36S/940 DEIA W30L120 VPC MLO	220 to 240 V	38 W	Yes	Safety class I
910925866982	RC342B 36S/940 PSE W31L125 VPC MLO	220 to 240 V	37 W	Yes	Safety class I
910925866983	RC342B 36S/940 DEIA W31L125 VPC MLO	220 to 240 V	38 W	Yes	Safety class I
910925867030	RC340B 42S/940 DEIA W30L120 VPC MLO W3W2	220 to 240 V	45 W	Yes	Safety class I
910925867031	RC340B 42S/940 DEIA W30L120 CPC MLO W3W2	220 to 240 V	45 W	Yes	Safety class I
910925867032	RC340B 42S/930 DEIA W30L120 VPC MLO W3W2	220 to 240 V	45 W	Yes	Safety class I
910925867033	RC340B 42S/930 DEIA W30L120 CPC MLO W3W2	220 to 240 V	45 W	Yes	Safety class I
910925867038	RC340B 42S/940 DEIA W30L120 VPC PCS W3W2	220 to 240 V	30.5 W	Yes	Safety class I
910925867039	RC340B 42S/940 DEIA W30L120 CPC PCS W3W2	220 to 240 V	30.5 W	Yes	Safety class I
910925867042	RC340B 42S/930 DEIA W30L120 VPC PCS W3W2	220 to 240 V	30.5 W	Yes	Safety class I
910925867147	RC342B 28S/940 DEIA W31L125 VPC MLO	220 to 240 V	25.5 W	Yes	Safety class I
910925867161	RC342B 28S/940 DEIA W31L125 VPC PCS	220 to 240 V	22 W	Yes	Safety class I
910925867162	RC342B 36S/940 DEIA W31L125 VPC PCS	220 to 240 V	26 W	Yes	Safety class I
910925867163	RC342B 42S/940 DEIA W31L125 VPC PCS	220 to 240 V	30.5 W	Yes	Safety class I
910925867177	RC342B 28S/940 DEIA W31L125 VPC O	220 to 240 V	22.5 W	Yes	Safety class I
910925867178	RC342B 36S/940 DEIA W31L125 VPC O	220 to 240 V	28.5 W	Yes	Safety class I
910925867179	RC342B 42S/940 DEIA W31L125 VPC O	220 to 240 V	33.5 W	Yes	Safety class I
910925868910	RC340B 36S/930 SEIA W60L60 VPC MLO U4	220 to 240 V	38 W	No	Safety class I
910925868911	RC340B 36S/930 SRD W60L60 VPC MLO U4	220 to 240 V	38 W	No	Safety class I
910925868912	RC340B 36S/930 SEIA W60L60 VPC PCS U4	220 to 240 V	26 W	No	Safety class I
910925868913	RC340B 36S/930 SEIA W60L60 VPC PCS U4 SC	220 to 240 V	26 W	No	Safety class I
910925868914	RC340B 36S/940 SEIA W60L60 VPC MLO U4	220 to 240 V	37 W	No	Safety class I
910925868915	RC340B 36S/940 SEIA W60L60 VPC MLO U4 SC	220 to 240 V	37 W	No	Safety class I
910925868916	RC340B 36S/940 SEIA W60L60 VPC PCS U4	220 to 240 V	26 W	No	Safety class I
910925868917	RC340B 36S/940 SEIA W60L60 VPC PCS U4 SC	220 to 240 V	26 W	No	Safety class I
910925868918	RC340B 36S/940 SEIA W60L60 VPC PCS U4 W3	220 to 240 V	26 W	No	Safety class I
910925868920	RC340B 42S/940 SEIA W60L60 VPC PCS U4 W3	220 to 240 V	30 W	No	Safety class I

Order Code	Full Product Name	Input Voltage	Power Consumption	Suitable for random switching	Protection class IEC
910925868921	RC342B 28S/940 SEIA W62L62 VPC MLO U4	220 to 240 V	25.5 W	No	Safety class I
910925868922	RC342B 28S/940 SEIA W62L62 VPC PCS U4	220 to 240 V	20 W	No	Safety class I
910925868924	RC342B 36S/940 SEIA W62L62 VPC MLO U4	220 to 240 V	37 W	No	Safety class I
910925868925	RC342B 36S/940 SEIA W62L62 VPC PCS U4	220 to 240 V	26 W	No	Safety class I
910925868927	RC342B 42S/940 SEIA W62L62 VPC MLO U4	220 to 240 V	45 W	No	Safety class I
910925868928	RC342B 42S/940 SEIA W62L62 VPC PCS U4	220 to 240 V	30 W	No	Safety class I
910505105985	RC340B 36S/940 SEIA W60L60 VPC MXO U4	220-240 V	26 W	Yes	Safety class I
910925866986	RC340B 36S/940 PSU W60L60 VPC O ELP3	220 to 240 V	28.5 W	Yes	Safety class I
910925866987	RC340B 36S/940 DIA W60L60 VPC O ELP3	220 to 240 V	28.5 W	Yes	Safety class I
910925867001	RC340B 42S/940 PSE W60L60 VPC O	220 to 240 V	33.5 W	Yes	Safety class I
910925867002	RC340B 42S/940 DEIA W60L60 VPC O	220 to 240 V	33.5 W	Yes	Safety class I
910925867006	RC340B 42S/940 PSU W60L60 VPC O ELP3	220 to 240 V	33.5 W	Yes	Safety class I
910925867007	RC340B 42S/940 DIA W60L60 VPC O ELP3	220 to 240 V	33.5 W	Yes	Safety class I
910925867012	RC340B 42S/940 DIA W60L60 VPC O ELD3	220 to 240 V	33.5 W	Yes	Safety class I
910925867061	RC340B 36S/940 PSE W60L60 VPC O SC	220 to 240 V	28.5 W	Yes	Safety class I
910925867062	RC340B 36S/940 DEIA W60L60 VPC O SC	220 to 240 V	28.5 W	Yes	Safety class I
910925868919	RC340B 42S/940 SEIA W30L120 VPC PCS U4W3	220 to 240 V	30 W	No	Safety class I
910925868923	RC342B 36S/940 SEIA W31L125 VPC PCS U4	220 to 240 V	26 W	No	Safety class I
910925868926	RC342B 42S/940 SEIA W31L125 VPC PCS U4	220 to 240 V	30 W	No	Safety class I
910925866969	RC340B 36S/940 DEIA W60L60 VPC MLO	220 to 240 V	38 W	Yes	Safety class I
910925867023	RC340B 42S/930 DEIA W60L60 CPC MLO W3W2	220 to 240 V	45 W	Yes	Safety class I
910925867028	RC340B 42S/940 DEIA W60L60 CPC MLO W3W2	220 to 240 V	45 W	Yes	Safety class I
910925867036	RC340B 42S/940 DEIA W60L60 CPC PCS W3W2	220 to 240 V	30.5 W	Yes	Safety class I
910925867040	RC340B 42S/930 DEIA W60L60 CPC PCS W3W2	220 to 240 V	30.5 W	Yes	Safety class I
910925867046	RC340B 36S/940 PSE W60L60 CPC MLO	220 to 240 V	38 W	Yes	Safety class I
910925867047	RC340B 42S/940 PSE W60L60 CPC MLO	220 to 240 V	45 W	Yes	Safety class I
910925867048	RC340B 42S/940 DEIA W60L60 CPC MLO	220 to 240 V	45 W	Yes	Safety class I
910925867167	RC342B 42S/940 DEIA W62L62 CPC PCS	220 to 240 V	30.5 W	Yes	Safety class I
910925867068	RC340B 42S/930 DEIA W30L120 CPC PCS W3W2	220 to 240 V	30.5 W	Yes	Safety class I
910925866967	RC340B 36S/940 DEIA W60L60 VPC O	220 to 240 V	28.5 W	Yes	Safety class I
910925866972	RC340B 36S/940 PSE W60L60 VPC PCS	220 to 240 V	26 W	Yes	Safety class I
910925866973	RC340B 36S/940 DEIA W60L60 VPC PCS	220 to 240 V	26 W	Yes	Safety class I
910925866977	RC340B 36S/940 DEIA W60L60 CPC MLO	220 to 240 V	38 W	Yes	Safety class I
910925866990	RC340B 36S/940 PSU W60L60 VPC PCS ELP3	220 to 240 V	26 W	Yes	Safety class I
910925866991	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	220 to 240 V	26 W	Yes	Safety class I
910925866997	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	220 to 240 V	26 W	Yes	Safety class I
910925867003	RC340B 42S/940 PSE W60L60 VPC PCS	220 to 240 V	30.5 W	Yes	Safety class I
910925867004	RC340B 42S/940 DEIA W60L60 VPC PCS	220 to 240 V	30.5 W	Yes	Safety class I
910925867008	RC340B 42S/940 PSU W60L60 VPC PCS ELP3	220 to 240 V	30.5 W	Yes	Safety class I
910925867009	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	220 to 240 V	30.5 W	Yes	Safety class I
910925867034	RC340B 42S/930 DEIA W60L60 VPC PCS W3W2	220 to 240 V	30.5 W	Yes	Safety class I
910925867035	RC340B 42S/940 DEIA W60L60 VPC PCS W3W2	220 to 240 V	30.5 W	Yes	Safety class I

Order Code	Full Product Name	Input Voltage	Power Consumption	Suitable for random switching	Protection class IEC
910925867044	RC340B 36S/940 PSE W60L60 CPC PCS PIP	220 to 240 V	26 W	Yes	Safety class I
910925867045	RC340B 36S/940 DEIA W60L60 CPC PCS	220 to 240 V	26 W	Yes	Safety class I
910925867049	RC340B 42S/940 PSE W60L60 CPC PCS	220 to 240 V	30.5 W	Yes	Safety class I
910925867050	RC340B 42S/940 DEIA W60L60 CPC PCS	220 to 240 V	30.5 W	Yes	Safety class I
910925867065	RC340B 36S/940 PSE W60L60 VPC PCS SC	220 to 240 V	26 W	Yes	Safety class I
910925867066	RC340B 36S/940 DEIA W60L60 VPC PCS SC	220 to 240 V	26 W	Yes	Safety class I
910505105982	RC340B 36S/940 SEIA W60L60 VPC DLO U4	220-240 V	21 W	Yes	Safety class I
910505105987	RC340B 42S/840 SEIA W60L60 VPC PCS U4 SC	220-240 V	25.5 W	No	Safety class I
910505105990	RC340B 36S/840 SEIA W67L67 FLC4DLO U4 SC	220-240 V	20 W	Yes	Safety class I
910505105989	RC342B 42S/840 DEIA W62L62 VPC PCS	220-240 V	25.5 W	No	Safety class I
910505105984	RC342B 36S/940 DEIA W31L125 VPC DLO	220-240 V	21 W	No	Safety class I
910505105988	RC340B 42S/840 PSU W30L120 VPC PCS ELB3	220-240 V	25.5 W	No	Safety class I
910505105992	RC340B 36S/840 DEIA W30L135 FLC2 DLO SC	220-240 V	20 W	No	Safety class I
910925866966	RC340B 36S/940 PSE W60L60 VPC O	220 to 240 V	28.5 W	Yes	Safety class I
910925866980	RC342B 36S/940 PSE W62L62 VPC MLO	220 to 240 V	37 W	Yes	Safety class I
910925866988	RC340B 36S/940 PSU W60L60 VPC MLO ELP3	220 to 240 V	38 W	Yes	Safety class I
910925866989	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	220 to 240 V	38 W	Yes	Safety class I
910925866993	RC340B 36S/940 DIA W60L60 VPC O ELD3	220 to 240 V	28.5 W	Yes	Safety class I
910925866995	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	220 to 240 V	38 W	Yes	Safety class I
910925866999	RC340B 42S/940 DEIA W60L60 VPC MLO	220 to 240 V	45 W	Yes	Safety class I
910925867010	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	220 to 240 V	45 W	Yes	Safety class I
910925867013	RC340B 42S/930 DEIA W60L60 VPC MLO W3W2	220 to 240 V	45 W	Yes	Safety class I
910925867027	RC340B 42S/940 DEIA W60L60 VPC MLO W3W2	220 to 240 V	45 W	Yes	Safety class I
910925867043	RC340B 42S/940 PSE W60L60 VPC MLO	220 to 240 V	45 W	Yes	Safety class I
910925867063	RC340B 36S/940 PSE W60L60 VPC MLO SC	220 to 240 V	38 W	Yes	Safety class I
910925867064	RC340B 36S/940 DEIA W60L60 VPC MLO SC	220 to 240 V	38 W	Yes	Safety class I
910925866970	RC340B 36S/940 POE W60L60 VPC MLO	220 to 240 V	37 W	Yes	Safety class I
910925867014	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	220 to 240 V	30.5 W	Yes	Safety class I
910925867025	RC340B 42S/930 DEIA W60L60 PCV MLO W3W2	220 to 240 V	45 W	Yes	Safety class I
910925867029	RC340B 42S/940 DEIA W60L60 PCV MLO W3W2	220 to 240 V	45 W	Yes	Safety class I
910925867037	RC340B 42S/940 DEIA W60L60 PCV PCS W3W2	220 to 240 V	30.5 W	Yes	Safety class I
910925867041	RC340B 42S/930 DEIA W60L60 PCV PCS W3W2	220 to 240 V	30.5 W	Yes	Safety class I
910925867168	RC340B 36S/940 DEIA W60L60 PCV PCS	220 to 240 V	26 W	Yes	Safety class I
910925867221	RC340B 36S/940 POE W60L60 VPC MLO U0	220 to 240 V	37 W	Yes (relates to presence/ movement detection and daylight harvesting)	Safety class III
910925867224	RC340B 36S/940 POE W60L60 VPC PCS U0	220 to 240 V	25 W	Yes (relates to presence/ movement detection and daylight harvesting)	Safety class III
910505105983	RC340B 42S/940 SEIA W30L120 VPC DLO U4	220-240 V	24.5 W	Yes	Safety class I
910505105991	RC340B 42S/840 SEIA W30L135 FLC4DLOU4SC	220-240 V	23.5 W	Yes	Safety class I
910925866968	RC340B 36S/940 PSE W60L60 VPC MLO PIP	220 to 240 V	38 W	Yes	Safety class I

Order Code	Full Product Name	Input Voltage	Power Consumption	Suitable for random switching	Protection class IEC
910925866978	RC340B 36S/940 DEIA W60L60 PCV MLO	220 to 240 V	38 W	Yes	Safety class I
910925866981	RC342B 36S/940 DEIA W62L62 VPC MLO	220 to 240 V	38 W	Yes	Safety class I
910925867145	RC342B 28S/940 DEIA W62L62 VPC MLO	220 to 240 V	25.5 W	Yes	Safety class I
910925867158	RC342B 28S/940 DEIA W62L62 VPC PCS	220 to 240 V	22 W	Yes	Safety class I
910925867159	RC342B 36S/940 DEIA W62L62 VPC PCS	220 to 240 V	25 W	Yes	Safety class I
910925867160	RC342B 42S/940 DEIA W62L62 VPC PCS	220 to 240 V	30.5 W	Yes	Safety class I
910925867174	RC342B 28S/940 DEIA W62L62 VPC O	220 to 240 V	22.5 W	Yes	Safety class I
910925867175	RC342B 36S/940 DEIA W62L62 VPC O	220 to 240 V	28.5 W	Yes	Safety class I
910925867176	RC342B 42S/940 DEIA W62L62 VPC O	220 to 240 V	33.5 W	Yes	Safety class I
910505105986	RC342B 28S/940 DEIA W31L125 VPC MXO	220-240 V	20 W	No	Safety class I

Controls and Dimming

Order Code	Full Product Name	Dimmable	Embedded control
910925867015	RC340B 36S/940 PSE W15L120 VPC MLO	No	-
910925867016	RC340B 36S/940 DEIA W15L120 VPC MLO	Yes	-
910925867017	RC340B 42S/940 PSE W15L120 VPC MLO	No	-
910925867018	RC340B 42S/940 DEIA W15L120 VPC MLO	Yes	-
910925867019	RC340B 36S/940 PSU W15L120 VPC MLO ELP3	No	-
910925867020	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	Yes	-
910925867021	RC340B 42S/940 PSU W15L120 VPC MLO ELP3	No	-
910925867022	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	Yes	-
910925867024	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	Yes	-
910925867026	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	Yes	-
910925867149	RC342B 28S/940 DEIA W15L125 VPC MLO	Yes	-
910925867150	RC342B 36S/940 DEIA W15L125 VPC MLO	Yes	-
910925867153	RC342B 36S/940 DEIA W17L125 PCV MLO	Yes	-
910925867164	RC342B 28S/940 DEIA W15L125 VPC PCS	Yes	-
910925867165	RC342B 36S/940 DEIA W15L125 VPC PCS	Yes	-
910925867166	RC342B 42S/940 DEIA W15L125 VPC PCS	Yes	-
910925867169	RC342B 36S/940 DEIA W17L125 PCV PCS	Yes	-
910925867180	RC342B 28S/940 DEIA W15L125 VPC O	Yes	-
910925867181	RC342B 36S/940 DEIA W15L125 VPC O	Yes	-
910925867182	RC342B 42S/940 DEIA W15L125 VPC O	Yes	-
910925866979	RC340B 36S/940 DEIA W30L120 VPC MLO	Yes	-
910925866982	RC342B 36S/940 PSE W31L125 VPC MLO	No	-
910925866983	RC342B 36S/940 DEIA W31L125 VPC MLO	Yes	-
910925867030	RC340B 42S/940 DEIA W30L120 VPC MLO W3W2	Yes	-
910925867031	RC340B 42S/940 DEIA W30L120 CPC MLO W3W2	Yes	-
910925867032	RC340B 42S/930 DEIA W30L120 VPC MLO W3W2	Yes	-
910925867033	RC340B 42S/930 DEIA W30L120 CPC MLO W3W2	Yes	-

Order Code	Full Product Name	Dimmable	Embedded control
910925867038	RC340B 42S/940 DEIA W30L120 VPC PCS W3W2	Yes	-
910925867039	RC340B 42S/940 DEIA W30L120 CPC PCS W3W2	Yes	-
910925867042	RC340B 42S/930 DEIA W30L120 VPC PCS W3W2	Yes	-
910925867147	RC342B 28S/940 DEIA W31L125 VPC MLO	Yes	-
910925867161	RC342B 28S/940 DEIA W31L125 VPC PCS	Yes	-
910925867162	RC342B 36S/940 DEIA W31L125 VPC PCS	Yes	-
910925867163	RC342B 42S/940 DEIA W31L125 VPC PCS	Yes	-
910925867177	RC342B 28S/940 DEIA W31L125 VPC O	Yes	-
910925867178	RC342B 36S/940 DEIA W31L125 VPC O	Yes	-
910925867179	RC342B 42S/940 DEIA W31L125 VPC O	Yes	-
910925868910	RC340B 36S/930 SEIA W60L60 VPC MLO U4	No	Upgradable sensor slot with SC200 sensor
910925868911	RC340B 36S/930 SRD W60L60 VPC MLO U4	No	Upgradable sensor slot with SC200 sensor
910925868912	RC340B 36S/930 SEIA W60L60 VPC PCS U4	No	Upgradable sensor slot with SC200 sensor
910925868913	RC340B 36S/930 SEIA W60L60 VPC PCS U4 SC	No	Upgradable sensor slot with SC200 sensor
910925868914	RC340B 36S/940 SEIA W60L60 VPC MLO U4	No	Upgradable sensor slot with SC200 sensor
910925868915	RC340B 36S/940 SEIA W60L60 VPC MLO U4 SC	No	Upgradable sensor slot with SC200 sensor
910925868916	RC340B 36S/940 SEIA W60L60 VPC PCS U4	No	Upgradable sensor slot with SC200 sensor
910925868917	RC340B 36S/940 SEIA W60L60 VPC PCS U4 SC	No	Upgradable sensor slot with SC200 sensor
910925868918	RC340B 36S/940 SEIA W60L60 VPC PCS U4 W3	No	Upgradable sensor slot with SC200 sensor
910925868920	RC340B 42S/940 SEIA W60L60 VPC PCS U4 W3	No	Upgradable sensor slot with SC200 sensor
910925868921	RC342B 28S/940 SEIA W62L62 VPC MLO U4	No	Upgradable sensor slot with SC200 sensor
910925868922	RC342B 28S/940 SEIA W62L62 VPC PCS U4	No	Upgradable sensor slot with SC200 sensor
910925868924	RC342B 36S/940 SEIA W62L62 VPC MLO U4	No	Upgradable sensor slot with SC200 sensor
910925868925	RC342B 36S/940 SEIA W62L62 VPC PCS U4	No	Upgradable sensor slot with SC200 sensor
910925868927	RC342B 42S/940 SEIA W62L62 VPC MLO U4	No	Upgradable sensor slot with SC200 sensor
910925868928	RC342B 42S/940 SEIA W62L62 VPC PCS U4	No	Upgradable sensor slot with SC200 sensor
910505105985	RC340B 36S/940 SEIA W60L60 VPC MXO U4	No	Upgradable sensor slot with SC200 sensor
910925866986	RC340B 36S/940 PSU W60L60 VPC O ELP3	No	-
910925866987	RC340B 36S/940 DIA W60L60 VPC O ELP3	Yes	-
910925867001	RC340B 42S/940 PSE W60L60 VPC O	No	-
910925867002	RC340B 42S/940 DEIA W60L60 VPC O	Yes	-
910925867006	RC340B 42S/940 PSU W60L60 VPC O ELP3	No	-
910925867007	RC340B 42S/940 DIA W60L60 VPC O ELP3	Yes	-
910925867012	RC340B 42S/940 DIA W60L60 VPC O ELD3	Yes	-
910925867061	RC340B 36S/940 PSE W60L60 VPC O SC	No	-
910925867062	RC340B 36S/940 DEIA W60L60 VPC O SC	Yes	-
910925868919	RC340B 42S/940 SEIA W30L120 VPC PCS U4W3	No	Upgradable sensor slot with SC200 sensor
910925868923	RC342B 36S/940 SEIA W31L125 VPC PCS U4	No	Upgradable sensor slot with SC200 sensor
910925868926	RC342B 42S/940 SEIA W31L125 VPC PCS U4	No	Upgradable sensor slot with SC200 sensor
910925866969	RC340B 36S/940 DEIA W60L60 VPC MLO	Yes	-
910925867023	RC340B 42S/930 DEIA W60L60 CPC MLO W3W2	Yes	-
910925867028	RC340B 42S/940 DEIA W60L60 CPC MLO W3W2	Yes	-

Order Code	Full Product Name	Dimmable	Embedded control
910925867036	RC340B 42S/940 DEIA W60L60 CPC PCS W3W2	Yes	-
910925867040	RC340B 42S/930 DEIA W60L60 CPC PCS W3W2	Yes	-
910925867046	RC340B 36S/940 PSE W60L60 CPC MLO	No	-
910925867047	RC340B 42S/940 PSE W60L60 CPC MLO	No	-
910925867048	RC340B 42S/940 DEIA W60L60 CPC MLO	Yes	-
910925867167	RC342B 42S/940 DEIA W62L62 CPC PCS	Yes	-
910925867068	RC340B 42S/930 DEIA W30L120 CPC PCS W3W2	Yes	-
910925866967	RC340B 36S/940 DEIA W60L60 VPC O	Yes	-
910925866972	RC340B 36S/940 PSE W60L60 VPC PCS	No	-
910925866973	RC340B 36S/940 DEIA W60L60 VPC PCS	Yes	-
910925866977	RC340B 36S/940 DEIA W60L60 CPC MLO	Yes	-
910925866990	RC340B 36S/940 PSU W60L60 VPC PCS ELP3	No	-
910925866991	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	Yes	-
910925866997	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	Yes	-
910925867003	RC340B 42S/940 PSE W60L60 VPC PCS	No	-
910925867004	RC340B 42S/940 DEIA W60L60 VPC PCS	Yes	-
910925867008	RC340B 42S/940 PSU W60L60 VPC PCS ELP3	No	-
910925867009	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	Yes	-
910925867034	RC340B 42S/930 DEIA W60L60 VPC PCS W3W2	Yes	-
910925867035	RC340B 42S/940 DEIA W60L60 VPC PCS W3W2	Yes	-
910925867044	RC340B 36S/940 PSE W60L60 CPC PCS PIP	No	-
910925867045	RC340B 36S/940 DEIA W60L60 CPC PCS	Yes	-
910925867049	RC340B 42S/940 PSE W60L60 CPC PCS	No	-
910925867050	RC340B 42S/940 DEIA W60L60 CPC PCS	Yes	-
910925867065	RC340B 36S/940 PSE W60L60 VPC PCS SC	No	-
910925867066	RC340B 36S/940 DEIA W60L60 VPC PCS SC	Yes	-
910505105982	RC340B 36S/940 SEIA W60L60 VPC DLO U4	No	Upgradable sensor slot with SC200 sensor
910505105987	RC340B 42S/840 SEIA W60L60 VPC PCS U4 SC	No	Upgradable sensor slot with SC200 sensor
910505105990	RC340B 36S/840 SEIA W67L67 FLC4DLO U4 SC	No	Upgradable sensor slot with SC200 sensor
910505105989	RC342B 42S/840 DEIA W62L62 VPC PCS	Yes	-
910505105984	RC342B 36S/940 DEIA W31L125 VPC DLO	Yes	-
910505105988	RC340B 42S/840 PSU W30L120 VPC PCS ELB3	No	-
910505105992	RC340B 36S/840 DEIA W30L135 FLC2 DLO SC	No	-
910925866966	RC340B 36S/940 PSE W60L60 VPC O	No	-
910925866980	RC342B 36S/940 PSE W62L62 VPC MLO	No	-
910925866988	RC340B 36S/940 PSU W60L60 VPC MLO ELP3	No	-
910925866989	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	Yes	-
910925866993	RC340B 36S/940 DIA W60L60 VPC O ELD3	Yes	-
910925866995	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	Yes	-
910925866999	RC340B 42S/940 DEIA W60L60 VPC MLO	Yes	-
910925867010	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	Yes	-
910925867013	RC340B 42S/930 DEIA W60L60 VPC MLO W3W2	Yes	-

Order Code	Full Product Name	Dimmable	Embedded control
910925867027	RC340B 42S/940 DEIA W60L60 VPC MLO W3W2	Yes	-
910925867043	RC340B 42S/940 PSE W60L60 VPC MLO	No	-
910925867063	RC340B 36S/940 PSE W60L60 VPC MLO SC	No	-
910925867064	RC340B 36S/940 DEIA W60L60 VPC MLO SC	Yes	-
910925866970	RC340B 36S/940 POE W60L60 VPC MLO	No	-
910925867014	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	Yes	-
910925867025	RC340B 42S/930 DEIA W60L60 PCV MLO W3W2	Yes	-
910925867029	RC340B 42S/940 DEIA W60L60 PCV MLO W3W2	Yes	-
910925867037	RC340B 42S/940 DEIA W60L60 PCV PCS W3W2	Yes	-
910925867041	RC340B 42S/930 DEIA W60L60 PCV PCS W3W2	Yes	-
910925867168	RC340B 36S/940 DEIA W60L60 PCV PCS	Yes	-
910925867221	RC340B 36S/940 POE W60L60 VPC MLO U0	No	Upgradable sensor slot empty with cover Visible light communication
910925867224	RC340B 36S/940 POE W60L60 VPC PCS U0	No	Upgradable sensor slot empty with cover Visible light communication
910505105983	RC340B 42S/940 SEIA W30L120 VPC DLO U4	No	Upgradable sensor slot with SC200 sensor
910505105991	RC340B 42S/840 SEIA W30L135 FLC4DLOU4SC	No	Upgradable sensor slot with SC200 sensor
910925866968	RC340B 36S/940 PSE W60L60 VPC MLO PIP	No	-
910925866978	RC340B 36S/940 DEIA W60L60 PCV MLO	Yes	-
910925866981	RC342B 36S/940 DEIA W62L62 VPC MLO	Yes	-
910925867145	RC342B 28S/940 DEIA W62L62 VPC MLO	Yes	-
910925867158	RC342B 28S/940 DEIA W62L62 VPC PCS	Yes	-
910925867159	RC342B 36S/940 DEIA W62L62 VPC PCS	Yes	-
910925867160	RC342B 42S/940 DEIA W62L62 VPC PCS	Yes	-
910925867174	RC342B 28S/940 DEIA W62L62 VPC O	Yes	-
910925867175	RC342B 36S/940 DEIA W62L62 VPC O	Yes	-
910925867176	RC342B 42S/940 DEIA W62L62 VPC O	Yes	-
910505105986	RC342B 28S/940 DEIA W31L125 VPC MXO	Yes	-

Mechanical and Housing

Order Code	Full Product Name	Ingress protection code	Mech. impact protection code
910925867015	RC340B 36S/940 PSE W15L120 VPC MLO	IP20/40	IK02
910925867016	RC340B 36S/940 DEIA W15L120 VPC MLO	IP20/40	IK02
910925867017	RC340B 42S/940 PSE W15L120 VPC MLO	IP20/40	IK02
910925867018	RC340B 42S/940 DEIA W15L120 VPC MLO	IP20/40	IK02
910925867019	RC340B 36S/940 PSU W15L120 VPC MLO ELP3	IP20	IK02
910925867020	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	IP20	IK02
910925867021	RC340B 42S/940 PSU W15L120 VPC MLO ELP3	IP20	IK02
910925867022	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	IP20	IK02
910925867024	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	IP20	IK02
910925867026	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	IP20	IK02
910925867149	RC342B 28S/940 DEIA W15L125 VPC MLO	IP20/40	IK02

Order Code	Full Product Name	Ingress protection code	Mech. impact protection code
910925867150	RC342B 36S/940 DEIA W15L125 VPC MLO	IP20/40	IK02
910925867153	RC342B 36S/940 DEIA W17L125 PCV MLO	IP20/40	IK02
910925867164	RC342B 28S/940 DEIA W15L125 VPC PCS	IP20/54	IK02
910925867165	RC342B 36S/940 DEIA W15L125 VPC PCS	IP20/54	IK02
910925867166	RC342B 42S/940 DEIA W15L125 VPC PCS	IP20/54	IK02
910925867169	RC342B 36S/940 DEIA W17L125 PCV PCS	IP20/54	IK02
910925867180	RC342B 28S/940 DEIA W15L125 VPC O	IP20/54	IK02
910925867181	RC342B 36S/940 DEIA W15L125 VPC O	IP20/54	IK02
910925867182	RC342B 42S/940 DEIA W15L125 VPC O	IP20/54	IK02
910925866979	RC340B 36S/940 DEIA W30L120 VPC MLO	IP20/40	IK02
910925866982	RC342B 36S/940 PSE W31L125 VPC MLO	IP20/40	IK02
910925866983	RC342B 36S/940 DEIA W31L125 VPC MLO	IP20/40	IK02
910925867030	RC340B 42S/940 DEIA W30L120 VPC MLO W3W2	IP20/40	IK02
910925867031	RC340B 42S/940 DEIA W30L120 CPC MLO W3W2	IP20/40	IK02
910925867032	RC340B 42S/930 DEIA W30L120 VPC MLO W3W2	IP20/40	IK02
910925867033	RC340B 42S/930 DEIA W30L120 CPC MLO W3W2	IP20/40	IK02
910925867038	RC340B 42S/940 DEIA W30L120 VPC PCS W3W2	IP20/54	IK02
910925867039	RC340B 42S/940 DEIA W30L120 CPC PCS W3W2	IP20/54	IK02
910925867042	RC340B 42S/930 DEIA W30L120 VPC PCS W3W2	IP20/54	IK02
910925867147	RC342B 28S/940 DEIA W31L125 VPC MLO	IP20/40	IK02
910925867161	RC342B 28S/940 DEIA W31L125 VPC PCS	IP20/54	IK02
910925867162	RC342B 36S/940 DEIA W31L125 VPC PCS	IP20/54	IK02
910925867163	RC342B 42S/940 DEIA W31L125 VPC PCS	IP20/54	IK02
910925867177	RC342B 28S/940 DEIA W31L125 VPC O	IP20/54	IK02
910925867178	RC342B 36S/940 DEIA W31L125 VPC O	IP20/54	IK02
910925867179	RC342B 42S/940 DEIA W31L125 VPC O	IP20/54	IK02
910925868910	RC340B 36S/930 SEIA W60L60 VPC MLO U4	IP20	IK02
910925868911	RC340B 36S/930 SRD W60L60 VPC MLO U4	IP20	IK02
910925868912	RC340B 36S/930 SEIA W60L60 VPC PCS U4	IP20/54	IK02
910925868913	RC340B 36S/930 SEIA W60L60 VPC PCS U4 SC	IP20/54	IK02
910925868914	RC340B 36S/940 SEIA W60L60 VPC MLO U4	IP20	IK02
910925868915	RC340B 36S/940 SEIA W60L60 VPC MLO U4 SC	IP20	IK02
910925868916	RC340B 36S/940 SEIA W60L60 VPC PCS U4	IP20/54	IK02
910925868917	RC340B 36S/940 SEIA W60L60 VPC PCS U4 SC	IP20/54	IK02
910925868918	RC340B 36S/940 SEIA W60L60 VPC PCS U4 W3	IP20/54	IK02
910925868920	RC340B 42S/940 SEIA W60L60 VPC PCS U4 W3	IP20/54	IK02
910925868921	RC342B 28S/940 SEIA W62L62 VPC MLO U4	IP20	IK02
910925868922	RC342B 28S/940 SEIA W62L62 VPC PCS U4	IP20/54	IK02
910925868924	RC342B 36S/940 SEIA W62L62 VPC MLO U4	IP20	IK02
910925868925	RC342B 36S/940 SEIA W62L62 VPC PCS U4	IP20/54	IK02
910925868927	RC342B 42S/940 SEIA W62L62 VPC MLO U4	IP20	IK02
910925868928	RC342B 42S/940 SEIA W62L62 VPC PCS U4	IP20/54	IK02

Order Code	Full Product Name	Ingress protection code	Mech. impact protection code
910505105985	RC340B 36S/940 SEIA W60L60 VPC MXO U4	IP20	IK03
910925866986	RC340B 36S/940 PSU W60L60 VPC O ELP3	IP54	IK02
910925866987	RC340B 36S/940 DIA W60L60 VPC O ELP3	IP54	IK02
910925867001	RC340B 42S/940 PSE W60L60 VPC O	IP20/54	IK02
910925867002	RC340B 42S/940 DEIA W60L60 VPC O	IP20/54	IK02
910925867006	RC340B 42S/940 PSU W60L60 VPC O ELP3	IP20/54	IK02
910925867007	RC340B 42S/940 DIA W60L60 VPC O ELP3	IP20/54	IK02
910925867012	RC340B 42S/940 DIA W60L60 VPC O ELD3	IP54	IK02
910925867061	RC340B 36S/940 PSE W60L60 VPC O SC	IP20/54	IK02
910925867062	RC340B 36S/940 DEIA W60L60 VPC O SC	IP20/54	IK02
910925868919	RC340B 42S/940 SEIA W30L120 VPC PCS U4W3	IP20/54	IK02
910925868923	RC342B 36S/940 SEIA W31L125 VPC PCS U4	IP20/54	IK02
910925868926	RC342B 42S/940 SEIA W31L125 VPC PCS U4	IP20/54	IK02
910925866969	RC340B 36S/940 DEIA W60L60 VPC MLO	IP20/40	IK02
910925867023	RC340B 42S/930 DEIA W60L60 CPC MLO W3W2	IP20/40	IK02
910925867028	RC340B 42S/940 DEIA W60L60 CPC MLO W3W2	IP20/40	IK02
910925867036	RC340B 42S/940 DEIA W60L60 CPC PCS W3W2	IP20/54	IK02
910925867040	RC340B 42S/930 DEIA W60L60 CPC PCS W3W2	IP20/54	IK02
910925867046	RC340B 36S/940 PSE W60L60 CPC MLO	IP20/40	IK02
910925867047	RC340B 42S/940 PSE W60L60 CPC MLO	IP20/40	IK02
910925867048	RC340B 42S/940 DEIA W60L60 CPC MLO	IP20/40	IK02
910925867167	RC342B 42S/940 DEIA W62L62 CPC PCS	IP20/54	IK02
910925867068	RC340B 42S/930 DEIA W30L120 CPC PCS W3W2	IP20/54	IK02
910925866967	RC340B 36S/940 DEIA W60L60 VPC O	IP20/54	IK02
910925866972	RC340B 36S/940 PSE W60L60 VPC PCS	IP20/54	IK02
910925866973	RC340B 36S/940 DEIA W60L60 VPC PCS	IP20/54	IK02
910925866977	RC340B 36S/940 DEIA W60L60 CPC MLO	IP20/40	IK02
910925866990	RC340B 36S/940 PSU W60L60 VPC PCS ELP3	IP20/54	IK02
910925866991	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	IP20/54	IK02
910925866997	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	IP20/54	IK02
910925867003	RC340B 42S/940 PSE W60L60 VPC PCS	IP20/54	IK02
910925867004	RC340B 42S/940 DEIA W60L60 VPC PCS	IP20/54	IK02
910925867008	RC340B 42S/940 PSU W60L60 VPC PCS ELP3	IP20/54	IK02
910925867009	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	IP20/54	IK02
910925867034	RC340B 42S/930 DEIA W60L60 VPC PCS W3W2	IP20/54	IK02
910925867035	RC340B 42S/940 DEIA W60L60 VPC PCS W3W2	IP20/54	IK02
910925867044	RC340B 36S/940 PSE W60L60 CPC PCS PIP	IP20/54	IK02
910925867045	RC340B 36S/940 DEIA W60L60 CPC PCS	IP20/54	IK02
910925867049	RC340B 42S/940 PSE W60L60 CPC PCS	IP20/54	IK02
910925867050	RC340B 42S/940 DEIA W60L60 CPC PCS	IP20/54	IK02
910925867065	RC340B 36S/940 PSE W60L60 VPC PCS SC	IP20/54	IK02
910925867066	RC340B 36S/940 DEIA W60L60 VPC PCS SC	IP20/54	IK02

Order Code	Full Product Name	Ingress protection code	Mech. impact protection code
910505105982	RC340B 36S/940 SEIA W60L60 VPC DLO U4	IP20	IK03
910505105987	RC340B 42S/840 SEIA W60L60 VPC PCS U4 SC	IP20(front IP40)	IK03
910505105990	RC340B 36S/840 SEIA W67L67 FLC4DLO U4 SC	IP20	IK03
910505105989	RC342B 42S/840 DEIA W62L62 VPC PCS	IP20(front IP40)	IK03
910505105984	RC342B 36S/940 DEIA W31L125 VPC DLO	IP20	IK03
910505105988	RC340B 42S/840 PSU W30L120 VPC PCS ELB3	IP20(front IP40)	IK03
910505105992	RC340B 36S/840 DEIA W30L135 FLC2 DLO SC	IP20	IK03
910925866966	RC340B 36S/940 PSE W60L60 VPC O	IP20/54	IK02
910925866980	RC342B 36S/940 PSE W62L62 VPC MLO	IP20/40	IK02
910925866988	RC340B 36S/940 PSU W60L60 VPC MLO ELP3	IP20	IK02
910925866989	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	IP20/54	IK02
910925866993	RC340B 36S/940 DIA W60L60 VPC O ELD3	IP54	IK02
910925866995	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	IP20/54	IK02
910925866999	RC340B 42S/940 DEIA W60L60 VPC MLO	IP20/40	IK02
910925867010	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	IP20	IK02
910925867013	RC340B 42S/930 DEIA W60L60 VPC MLO W3W2	IP20/40	IK02
910925867027	RC340B 42S/940 DEIA W60L60 VPC MLO W3W2	IP20/40	IK02
910925867043	RC340B 42S/940 PSE W60L60 VPC MLO	IP20/40	IK02
910925867063	RC340B 36S/940 PSE W60L60 VPC MLO SC	IP20/40	IK02
910925867064	RC340B 36S/940 DEIA W60L60 VPC MLO SC	IP20/40	IK02
910925866970	RC340B 36S/940 POE W60L60 VPC MLO	IP20/40	IK02
910925867014	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	IP20/54	IK02
910925867025	RC340B 42S/930 DEIA W60L60 PCV MLO W3W2	IP20/40	IK02
910925867029	RC340B 42S/940 DEIA W60L60 PCV MLO W3W2	IP20/40	IK02
910925867037	RC340B 42S/940 DEIA W60L60 PCV PCS W3W2	IP20/54	IK02
910925867041	RC340B 42S/930 DEIA W60L60 PCV PCS W3W2	IP20/54	IK02
910925867168	RC340B 36S/940 DEIA W60L60 PCV PCS	IP20/54	IK02
910925867221	RC340B 36S/940 POE W60L60 VPC MLO U0	IP20	IK02
910925867224	RC340B 36S/940 POE W60L60 VPC PCS U0	IP20/54	IK02
910505105983	RC340B 42S/940 SEIA W30L120 VPC DLO U4	IP20	IK03
910505105991	RC340B 42S/840 SEIA W30L135 FLC4DLOU4SC	IP20	IK03
910925866968	RC340B 36S/940 PSE W60L60 VPC MLO PIP	IP20/40	IK02
910925866978	RC340B 36S/940 DEIA W60L60 PCV MLO	IP20/40	IK02
910925866981	RC342B 36S/940 DEIA W62L62 VPC MLO	IP20/40	IK02
910925867145	RC342B 28S/940 DEIA W62L62 VPC MLO	IP20/40	IK02
910925867158	RC342B 28S/940 DEIA W62L62 VPC PCS	IP20/54	IK02
910925867159	RC342B 36S/940 DEIA W62L62 VPC PCS	IP20/54	IK02
910925867160	RC342B 42S/940 DEIA W62L62 VPC PCS	IP20/54	IK02
910925867174	RC342B 28S/940 DEIA W62L62 VPC O	IP20/54	IK02
910925867175	RC342B 36S/940 DEIA W62L62 VPC O	IP20/54	IK02
910925867176	RC342B 42S/940 DEIA W62L62 VPC O	IP20/54	IK02
910505105986	RC342B 28S/940 DEIA W31L125 VPC MXO	IP20	IK03

Emergency Operation

Order Code	Full Product Name	Central Emergency	Emergency lighting
910925867015	RC340B 36S/940 PSE W15L120 VPC MLO	-	-
910925867016	RC340B 36S/940 DEIA W15L120 VPC MLO	Yes	DC operated central emergency lighting
910925867017	RC340B 42S/940 PSE W15L120 VPC MLO	-	-
910925867018	RC340B 42S/940 DEIA W15L120 VPC MLO	Yes	DC operated central emergency lighting
910925867019	RC340B 36S/940 PSU W15L120 VPC MLO ELP3	No	Emergency lighting 3 hours duration Pro version
910925867020	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	No	Emergency lighting 3 hours duration Pro version
910925867021	RC340B 42S/940 PSU W15L120 VPC MLO ELP3	No	Emergency lighting 3 hours duration Pro version
910925867022	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	No	Emergency lighting 3 hours duration Pro version
910925867024	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	No	Emergency lighting 3 hours duration Pro version
910925867026	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	No	Emergency lighting 3 hours duration Pro version
910925867149	RC342B 28S/940 DEIA W15L125 VPC MLO	Yes	DC operated central emergency lighting
910925867150	RC342B 36S/940 DEIA W15L125 VPC MLO	Yes	DC operated central emergency lighting
910925867153	RC342B 36S/940 DEIA W17L125 PCV MLO	Yes	DC operated central emergency lighting
910925867164	RC342B 28S/940 DEIA W15L125 VPC PCS	Yes	DC operated central emergency lighting
910925867165	RC342B 36S/940 DEIA W15L125 VPC PCS	Yes	DC operated central emergency lighting
910925867166	RC342B 42S/940 DEIA W15L125 VPC PCS	Yes	DC operated central emergency lighting
910925867169	RC342B 36S/940 DEIA W17L125 PCV PCS	Yes	DC operated central emergency lighting
910925867180	RC342B 28S/940 DEIA W15L125 VPC O	Yes	DC operated central emergency lighting
910925867181	RC342B 36S/940 DEIA W15L125 VPC O	Yes	DC operated central emergency lighting
910925867182	RC342B 42S/940 DEIA W15L125 VPC O	Yes	DC operated central emergency lighting
910925866979	RC340B 36S/940 DEIA W30L120 VPC MLO	Yes	DC operated central emergency lighting
910925866982	RC342B 36S/940 PSE W31L125 VPC MLO	-	-
910925866983	RC342B 36S/940 DEIA W31L125 VPC MLO	Yes	DC operated central emergency lighting
910925867030	RC340B 42S/940 DEIA W30L120 VPC MLO W3W2	Yes	DC operated central emergency lighting
910925867031	RC340B 42S/940 DEIA W30L120 CPC MLO W3W2	Yes	DC operated central emergency lighting
910925867032	RC340B 42S/930 DEIA W30L120 VPC MLO W3W2	Yes	DC operated central emergency lighting
910925867033	RC340B 42S/930 DEIA W30L120 CPC MLO W3W2	Yes	DC operated central emergency lighting
910925867038	RC340B 42S/940 DEIA W30L120 VPC PCS W3W2	Yes	DC operated central emergency lighting
910925867039	RC340B 42S/940 DEIA W30L120 CPC PCS W3W2	Yes	DC operated central emergency lighting
910925867042	RC340B 42S/930 DEIA W30L120 VPC PCS W3W2	Yes	DC operated central emergency lighting
910925867147	RC342B 28S/940 DEIA W31L125 VPC MLO	Yes	DC operated central emergency lighting
910925867161	RC342B 28S/940 DEIA W31L125 VPC PCS	Yes	DC operated central emergency lighting
910925867162	RC342B 36S/940 DEIA W31L125 VPC PCS	Yes	DC operated central emergency lighting
910925867163	RC342B 42S/940 DEIA W31L125 VPC PCS	Yes	DC operated central emergency lighting
910925867177	RC342B 28S/940 DEIA W31L125 VPC O	Yes	DC operated central emergency lighting
910925867178	RC342B 36S/940 DEIA W31L125 VPC O	Yes	DC operated central emergency lighting
910925867179	RC342B 42S/940 DEIA W31L125 VPC O	Yes	DC operated central emergency lighting
910925868910	RC340B 36S/930 SEIA W60L60 VPC MLO U4	Yes	DC operated central emergency lighting
910925868911	RC340B 36S/930 SRD W60L60 VPC MLO U4	-	-
910925868912	RC340B 36S/930 SEIA W60L60 VPC PCS U4	Yes	DC operated central emergency lighting
910925868913	RC340B 36S/930 SEIA W60L60 VPC PCS U4 SC	Yes	DC operated central emergency lighting

Order Code	Full Product Name	Central Emergency	Emergency lighting
910925868914	RC340B 36S/940 SEIA W60L60 VPC MLO U4	Yes	DC operated central emergency lighting
910925868915	RC340B 36S/940 SEIA W60L60 VPC MLO U4 SC	Yes	DC operated central emergency lighting
910925868916	RC340B 36S/940 SEIA W60L60 VPC PCS U4	Yes	DC operated central emergency lighting
910925868917	RC340B 36S/940 SEIA W60L60 VPC PCS U4 SC	Yes	DC operated central emergency lighting
910925868918	RC340B 36S/940 SEIA W60L60 VPC PCS U4 W3	Yes	DC operated central emergency lighting
910925868920	RC340B 42S/940 SEIA W60L60 VPC PCS U4 W3	Yes	DC operated central emergency lighting
910925868921	RC342B 28S/940 SEIA W62L62 VPC MLO U4	Yes	DC operated central emergency lighting
910925868922	RC342B 28S/940 SEIA W62L62 VPC PCS U4	Yes	DC operated central emergency lighting
910925868924	RC342B 36S/940 SEIA W62L62 VPC MLO U4	Yes	DC operated central emergency lighting
910925868925	RC342B 36S/940 SEIA W62L62 VPC PCS U4	Yes	DC operated central emergency lighting
910925868927	RC342B 42S/940 SEIA W62L62 VPC MLO U4	Yes	DC operated central emergency lighting
910925868928	RC342B 42S/940 SEIA W62L62 VPC PCS U4	Yes	DC operated central emergency lighting
910505105985	RC340B 36S/940 SEIA W60L60 VPC MXO U4	Yes	DC operated central emergency lighting
910925866986	RC340B 36S/940 PSU W60L60 VPC O ELP3	No	Emergency lighting 3 hours duration Pro version
910925866987	RC340B 36S/940 DIA W60L60 VPC O ELP3	No	Emergency lighting 3 hours duration Pro version
910925867001	RC340B 42S/940 PSE W60L60 VPC O	-	-
910925867002	RC340B 42S/940 DEIA W60L60 VPC O	Yes	DC operated central emergency lighting
910925867006	RC340B 42S/940 PSU W60L60 VPC O ELP3	No	Emergency lighting 3 hours duration Pro version
910925867007	RC340B 42S/940 DIA W60L60 VPC O ELP3	No	Emergency lighting 3 hours duration Pro version
910925867012	RC340B 42S/940 DIA W60L60 VPC O ELD3	No	Emergency lighting 3 hours duration with DALI interface
910925867061	RC340B 36S/940 PSE W60L60 VPC O SC	-	-
910925867062	RC340B 36S/940 DEIA W60L60 VPC O SC	Yes	DC operated central emergency lighting
910925868919	RC340B 42S/940 SEIA W30L120 VPC PCS U4W3	Yes	DC operated central emergency lighting
910925868923	RC342B 36S/940 SEIA W31L125 VPC PCS U4	Yes	DC operated central emergency lighting
910925868926	RC342B 42S/940 SEIA W31L125 VPC PCS U4	Yes	DC operated central emergency lighting
910925866969	RC340B 36S/940 DEIA W60L60 VPC MLO	Yes	DC operated central emergency lighting
910925867023	RC340B 42S/930 DEIA W60L60 CPC MLO W3W2	Yes	DC operated central emergency lighting
910925867028	RC340B 42S/940 DEIA W60L60 CPC MLO W3W2	Yes	DC operated central emergency lighting
910925867036	RC340B 42S/940 DEIA W60L60 CPC PCS W3W2	Yes	DC operated central emergency lighting
910925867040	RC340B 42S/930 DEIA W60L60 CPC PCS W3W2	Yes	DC operated central emergency lighting
910925867046	RC340B 36S/940 PSE W60L60 CPC MLO	-	-
910925867047	RC340B 42S/940 PSE W60L60 CPC MLO	-	-
910925867048	RC340B 42S/940 DEIA W60L60 CPC MLO	Yes	DC operated central emergency lighting
910925867167	RC342B 42S/940 DEIA W62L62 CPC PCS	Yes	DC operated central emergency lighting
910925867068	RC340B 42S/930 DEIA W30L120 CPC PCS W3W2	Yes	DC operated central emergency lighting
910925866967	RC340B 36S/940 DEIA W60L60 VPC O	Yes	DC operated central emergency lighting
910925866972	RC340B 36S/940 PSE W60L60 VPC PCS	-	-
910925866973	RC340B 36S/940 DEIA W60L60 VPC PCS	Yes	DC operated central emergency lighting
910925866977	RC340B 36S/940 DEIA W60L60 CPC MLO	Yes	DC operated central emergency lighting
910925866990	RC340B 36S/940 PSU W60L60 VPC PCS ELP3	No	Emergency lighting 3 hours duration Pro version
910925866991	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	No	Emergency lighting 3 hours duration Pro version
910925866997	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	No	Emergency lighting 3 hours duration with DALI interface

Order Code	Full Product Name	Central Emergency	Emergency lighting
910925867003	RC340B 42S/940 PSE W60L60 VPC PCS	-	-
910925867004	RC340B 42S/940 DEIA W60L60 VPC PCS	Yes	DC operated central emergency lighting
910925867008	RC340B 42S/940 PSU W60L60 VPC PCS ELP3	No	Emergency lighting 3 hours duration Pro version
910925867009	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	No	Emergency lighting 3 hours duration Pro version
910925867034	RC340B 42S/930 DEIA W60L60 VPC PCS W3W2	Yes	DC operated central emergency lighting
910925867035	RC340B 42S/940 DEIA W60L60 VPC PCS W3W2	Yes	DC operated central emergency lighting
910925867044	RC340B 36S/940 PSE W60L60 CPC PCS PIP	-	-
910925867045	RC340B 36S/940 DEIA W60L60 CPC PCS	Yes	DC operated central emergency lighting
910925867049	RC340B 42S/940 PSE W60L60 CPC PCS	-	-
910925867050	RC340B 42S/940 DEIA W60L60 CPC PCS	Yes	DC operated central emergency lighting
910925867065	RC340B 36S/940 PSE W60L60 VPC PCS SC	-	-
910925867066	RC340B 36S/940 DEIA W60L60 VPC PCS SC	Yes	DC operated central emergency lighting
910505105982	RC340B 36S/940 SEIA W60L60 VPC DLO U4	Yes	DC operated central emergency lighting
910505105987	RC340B 42S/840 SEIA W60L60 VPC PCS U4 SC	Yes	DC operated central emergency lighting
910505105990	RC340B 36S/840 SEIA W67L67 FLC4DLO U4 SC	Yes	DC operated central emergency lighting
910505105989	RC342B 42S/840 DEIA W62L62 VPC PCS	Yes	DC operated central emergency lighting
910505105984	RC342B 36S/940 DEIA W31L125 VPC DLO	Yes	DC operated central emergency lighting
910505105988	RC340B 42S/840 PSU W30L120 VPC PCS ELB3	No	Emergency lighting 3 hours duration basic version
910505105992	RC340B 36S/840 DEIA W30L135 FLC2 DLO SC	Yes	DC operated central emergency lighting
910925866966	RC340B 36S/940 PSE W60L60 VPC O	-	-
910925866980	RC342B 36S/940 PSE W62L62 VPC MLO	-	-
910925866988	RC340B 36S/940 PSU W60L60 VPC MLO ELP3	No	Emergency lighting 3 hours duration Pro version
910925866989	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	No	Emergency lighting 3 hours duration Pro version
910925866993	RC340B 36S/940 DIA W60L60 VPC O ELD3	No	Emergency lighting 3 hours duration with DALI interface
910925866995	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	No	Emergency lighting 3 hours duration with DALI interface
910925866999	RC340B 42S/940 DEIA W60L60 VPC MLO	Yes	DC operated central emergency lighting
910925867010	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	No	Emergency lighting 3 hours duration with DALI interface
910925867013	RC340B 42S/930 DEIA W60L60 VPC MLO W3W2	Yes	DC operated central emergency lighting
910925867027	RC340B 42S/940 DEIA W60L60 VPC MLO W3W2	Yes	DC operated central emergency lighting
910925867043	RC340B 42S/940 PSE W60L60 VPC MLO	-	-
910925867063	RC340B 36S/940 PSE W60L60 VPC MLO SC	-	-
910925867064	RC340B 36S/940 DEIA W60L60 VPC MLO SC	Yes	DC operated central emergency lighting
910925866970	RC340B 36S/940 POE W60L60 VPC MLO	-	-
910925867014	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	No	Emergency lighting 3 hours duration with DALI interface
910925867025	RC340B 42S/930 DEIA W60L60 PCV MLO W3W2	Yes	DC operated central emergency lighting
910925867029	RC340B 42S/940 DEIA W60L60 PCV MLO W3W2	Yes	DC operated central emergency lighting
910925867037	RC340B 42S/940 DEIA W60L60 PCV PCS W3W2	Yes	DC operated central emergency lighting
910925867041	RC340B 42S/930 DEIA W60L60 PCV PCS W3W2	Yes	DC operated central emergency lighting
910925867168	RC340B 36S/940 DEIA W60L60 PCV PCS	Yes	DC operated central emergency lighting
910925867221	RC340B 36S/940 POE W60L60 VPC MLO U0	-	-
910925867224	RC340B 36S/940 POE W60L60 VPC PCS U0	-	-
910505105983	RC340B 42S/940 SEIA W30L120 VPC DLO U4	Yes	DC operated central emergency lighting

Order Code	Full Product Name	Central Emergency	Emergency lighting
910505105991	RC340B 42S/840 SEIA W30L135 FLC4DLOU4SC	Yes	DC operated central emergency lighting
910925866968	RC340B 36S/940 PSE W60L60 VPC MLO PIP	-	-
910925866978	RC340B 36S/940 DEIA W60L60 PCV MLO	Yes	DC operated central emergency lighting
910925866981	RC342B 36S/940 DEIA W62L62 VPC MLO	Yes	DC operated central emergency lighting
910925867145	RC342B 28S/940 DEIA W62L62 VPC MLO	Yes	DC operated central emergency lighting
910925867158	RC342B 28S/940 DEIA W62L62 VPC PCS	Yes	DC operated central emergency lighting
910925867159	RC342B 36S/940 DEIA W62L62 VPC PCS	Yes	DC operated central emergency lighting
910925867160	RC342B 42S/940 DEIA W62L62 VPC PCS	Yes	DC operated central emergency lighting
910925867174	RC342B 28S/940 DEIA W62L62 VPC O	Yes	DC operated central emergency lighting
910925867175	RC342B 36S/940 DEIA W62L62 VPC O	Yes	DC operated central emergency lighting
910925867176	RC342B 42S/940 DEIA W62L62 VPC O	Yes	DC operated central emergency lighting
910505105986	RC342B 28S/940 DEIA W31L125 VPC MXO	Yes	DC operated central emergency lighting

Approval and Application

Order Code	Full Product Name	Glow-wire test
910925867015	RC340B 36S/940 PSE W15L120 VPC MLO	Temperature 650 °C, duration 30 s
910925867016	RC340B 36S/940 DEIA W15L120 VPC MLO	Temperature 650 °C, duration 30 s
910925867017	RC340B 42S/940 PSE W15L120 VPC MLO	Temperature 650 °C, duration 30 s
910925867018	RC340B 42S/940 DEIA W15L120 VPC MLO	Temperature 650 °C, duration 30 s
910925867019	RC340B 36S/940 PSU W15L120 VPC MLO ELP3	Temperature 650 °C, duration 30 s
910925867020	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	Temperature 650 °C, duration 30 s
910925867021	RC340B 42S/940 PSU W15L120 VPC MLO ELP3	Temperature 650 °C, duration 30 s
910925867022	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	Temperature 650 °C, duration 30 s
910925867024	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	Temperature 650 °C, duration 30 s
910925867026	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	Temperature 650 °C, duration 30 s
910925867149	RC342B 28S/940 DEIA W15L125 VPC MLO	Temperature 650 °C, duration 30 s
910925867150	RC342B 36S/940 DEIA W15L125 VPC MLO	Temperature 650 °C, duration 30 s
910925867153	RC342B 36S/940 DEIA W17L125 PCV MLO	Temperature 650 °C, duration 30 s
910925867164	RC342B 28S/940 DEIA W15L125 VPC PCS	Temperature 850 °C, duration 30 s
910925867165	RC342B 36S/940 DEIA W15L125 VPC PCS	Temperature 850 °C, duration 30 s
910925867166	RC342B 42S/940 DEIA W15L125 VPC PCS	Temperature 850 °C, duration 30 s
910925867169	RC342B 36S/940 DEIA W17L125 PCV PCS	Temperature 850 °C, duration 30 s
910925867180	RC342B 28S/940 DEIA W15L125 VPC O	Temperature 850 °C, duration 30 s
910925867181	RC342B 36S/940 DEIA W15L125 VPC O	Temperature 850 °C, duration 30 s
910925867182	RC342B 42S/940 DEIA W15L125 VPC O	Temperature 850 °C, duration 30 s
910925866979	RC340B 36S/940 DEIA W30L120 VPC MLO	Temperature 650 °C, duration 30 s
910925866982	RC342B 36S/940 PSE W31L125 VPC MLO	Temperature 650 °C, duration 30 s
910925866983	RC342B 36S/940 DEIA W31L125 VPC MLO	Temperature 650 °C, duration 30 s
910925867030	RC340B 42S/940 DEIA W30L120 VPC MLO W3W2	Temperature 650 °C, duration 30 s
910925867031	RC340B 42S/940 DEIA W30L120 CPC MLO W3W2	Temperature 650 °C, duration 30 s
910925867032	RC340B 42S/930 DEIA W30L120 VPC MLO W3W2	Temperature 650 °C, duration 30 s
910925867033	RC340B 42S/930 DEIA W30L120 CPC MLO W3W2	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Glow-wire test
910925867038	RC340B 42S/940 DEIA W30L120 VPC PCS W3W2	Temperature 850 °C, duration 30 s
910925867039	RC340B 42S/940 DEIA W30L120 CPC PCS W3W2	Temperature 850 °C, duration 30 s
910925867042	RC340B 42S/930 DEIA W30L120 VPC PCS W3W2	Temperature 850 °C, duration 30 s
910925867147	RC342B 28S/940 DEIA W31L125 VPC MLO	Temperature 650 °C, duration 30 s
910925867161	RC342B 28S/940 DEIA W31L125 VPC PCS	Temperature 850 °C, duration 30 s
910925867162	RC342B 36S/940 DEIA W31L125 VPC PCS	Temperature 850 °C, duration 30 s
910925867163	RC342B 42S/940 DEIA W31L125 VPC PCS	Temperature 850 °C, duration 30 s
910925867177	RC342B 28S/940 DEIA W31L125 VPC O	Temperature 850 °C, duration 30 s
910925867178	RC342B 36S/940 DEIA W31L125 VPC O	Temperature 850 °C, duration 30 s
910925867179	RC342B 42S/940 DEIA W31L125 VPC O	Temperature 850 °C, duration 30 s
910925868910	RC340B 36S/930 SEIA W60L60 VPC MLO U4	Temperature 650 °C, duration 30 s
910925868911	RC340B 36S/930 SRD W60L60 VPC MLO U4	Temperature 650 °C, duration 30 s
910925868912	RC340B 36S/930 SEIA W60L60 VPC PCS U4	Temperature 850 °C, duration 30 s
910925868913	RC340B 36S/930 SEIA W60L60 VPC PCS U4 SC	Temperature 850 °C, duration 30 s
910925868914	RC340B 36S/940 SEIA W60L60 VPC MLO U4	Temperature 650 °C, duration 30 s
910925868915	RC340B 36S/940 SEIA W60L60 VPC MLO U4 SC	Temperature 650 °C, duration 30 s
910925868916	RC340B 36S/940 SEIA W60L60 VPC PCS U4	Temperature 850 °C, duration 30 s
910925868917	RC340B 36S/940 SEIA W60L60 VPC PCS U4 SC	Temperature 850 °C, duration 30 s
910925868918	RC340B 36S/940 SEIA W60L60 VPC PCS U4 W3	Temperature 850 °C, duration 30 s
910925868920	RC340B 42S/940 SEIA W60L60 VPC PCS U4 W3	Temperature 850 °C, duration 30 s
910925868921	RC342B 28S/940 SEIA W62L62 VPC MLO U4	Temperature 650 °C, duration 30 s
910925868922	RC342B 28S/940 SEIA W62L62 VPC PCS U4	Temperature 850 °C, duration 30 s
910925868924	RC342B 36S/940 SEIA W62L62 VPC MLO U4	Temperature 650 °C, duration 30 s
910925868925	RC342B 36S/940 SEIA W62L62 VPC PCS U4	Temperature 850 °C, duration 30 s
910925868927	RC342B 42S/940 SEIA W62L62 VPC MLO U4	Temperature 650 °C, duration 30 s
910925868928	RC342B 42S/940 SEIA W62L62 VPC PCS U4	Temperature 850 °C, duration 30 s
910505105985	RC340B 36S/940 SEIA W60L60 VPC MXO U4	Temperature 650 °C, duration 30 s
910925866986	RC340B 36S/940 PSU W60L60 VPC O ELP3	Temperature 850 °C, duration 30 s
910925866987	RC340B 36S/940 DIA W60L60 VPC O ELP3	Temperature 850 °C, duration 30 s
910925867001	RC340B 42S/940 PSE W60L60 VPC O	Temperature 850 °C, duration 30 s
910925867002	RC340B 42S/940 DEIA W60L60 VPC O	Temperature 850 °C, duration 30 s
910925867006	RC340B 42S/940 PSU W60L60 VPC O ELP3	Temperature 850 °C, duration 30 s
910925867007	RC340B 42S/940 DIA W60L60 VPC O ELP3	Temperature 850 °C, duration 30 s
910925867012	RC340B 42S/940 DIA W60L60 VPC O ELD3	Temperature 850 °C, duration 30 s
910925867061	RC340B 36S/940 PSE W60L60 VPC O SC	Temperature 850 °C, duration 30 s
910925867062	RC340B 36S/940 DEIA W60L60 VPC O SC	Temperature 850 °C, duration 30 s
910925868919	RC340B 42S/940 SEIA W30L120 VPC PCS U4W3	Temperature 850 °C, duration 30 s
910925868923	RC342B 36S/940 SEIA W31L125 VPC PCS U4	Temperature 850 °C, duration 30 s
910925868926	RC342B 42S/940 SEIA W31L125 VPC PCS U4	Temperature 850 °C, duration 30 s
910925866969	RC340B 36S/940 DEIA W60L60 VPC MLO	Temperature 650 °C, duration 30 s
910925867023	RC340B 42S/930 DEIA W60L60 CPC MLO W3W2	Temperature 650 °C, duration 30 s
910925867028	RC340B 42S/940 DEIA W60L60 CPC MLO W3W2	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Glow-wire test
910925867036	RC340B 42S/940 DEIA W60L60 CPC PCS W3W2	Temperature 850 °C, duration 30 s
910925867040	RC340B 42S/930 DEIA W60L60 CPC PCS W3W2	Temperature 850 °C, duration 30 s
910925867046	RC340B 36S/940 PSE W60L60 CPC MLO	Temperature 650 °C, duration 30 s
910925867047	RC340B 42S/940 PSE W60L60 CPC MLO	Temperature 650 °C, duration 30 s
910925867048	RC340B 42S/940 DEIA W60L60 CPC MLO	Temperature 650 °C, duration 30 s
910925867167	RC342B 42S/940 DEIA W62L62 CPC PCS	Temperature 850 °C, duration 30 s
910925867068	RC340B 42S/930 DEIA W30L120 CPC PCS W3W2	Temperature 850 °C, duration 30 s
910925866967	RC340B 36S/940 DEIA W60L60 VPC O	Temperature 850 °C, duration 30 s
910925866972	RC340B 36S/940 PSE W60L60 VPC PCS	Temperature 850 °C, duration 30 s
910925866973	RC340B 36S/940 DEIA W60L60 VPC PCS	Temperature 850 °C, duration 30 s
910925866977	RC340B 36S/940 DEIA W60L60 CPC MLO	Temperature 650 °C, duration 30 s
910925866990	RC340B 36S/940 PSU W60L60 VPC PCS ELP3	Temperature 850 °C, duration 30 s
910925866991	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	Temperature 850 °C, duration 30 s
910925866997	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	Temperature 850 °C, duration 30 s
910925867003	RC340B 42S/940 PSE W60L60 VPC PCS	Temperature 850 °C, duration 30 s
910925867004	RC340B 42S/940 DEIA W60L60 VPC PCS	Temperature 850 °C, duration 30 s
910925867008	RC340B 42S/940 PSU W60L60 VPC PCS ELP3	Temperature 850 °C, duration 30 s
910925867009	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	Temperature 850 °C, duration 30 s
910925867034	RC340B 42S/930 DEIA W60L60 VPC PCS W3W2	Temperature 850 °C, duration 30 s
910925867035	RC340B 42S/940 DEIA W60L60 VPC PCS W3W2	Temperature 850 °C, duration 30 s
910925867044	RC340B 36S/940 PSE W60L60 CPC PCS PIP	Temperature 850 °C, duration 30 s
910925867045	RC340B 36S/940 DEIA W60L60 CPC PCS	Temperature 850 °C, duration 30 s
910925867049	RC340B 42S/940 PSE W60L60 CPC PCS	Temperature 850 °C, duration 30 s
910925867050	RC340B 42S/940 DEIA W60L60 CPC PCS	Temperature 850 °C, duration 30 s
910925867065	RC340B 36S/940 PSE W60L60 VPC PCS SC	Temperature 850 °C, duration 30 s
910925867066	RC340B 36S/940 DEIA W60L60 VPC PCS SC	Temperature 850 °C, duration 30 s
910505105982	RC340B 36S/940 SEIA W60L60 VPC DLO U4	Temperature 650 °C, duration 30 s
910505105987	RC340B 42S/840 SEIA W60L60 VPC PCS U4 SC	Temperature 650 °C, duration 30 s
910505105990	RC340B 36S/840 SEIA W67L67 FLC4DLO U4 SC	Temperature 650 °C, duration 30 s
910505105989	RC342B 42S/840 DEIA W62L62 VPC PCS	Temperature 650 °C, duration 30 s
910505105984	RC342B 36S/940 DEIA W31L125 VPC DLO	Temperature 650 °C, duration 30 s
910505105988	RC340B 42S/840 PSU W30L120 VPC PCS ELB3	Temperature 650 °C, duration 30 s
910505105992	RC340B 36S/840 DEIA W30L135 FLC2 DLO SC	Temperature 650 °C, duration 30 s
910925866966	RC340B 36S/940 PSE W60L60 VPC O	Temperature 850 °C, duration 30 s
910925866980	RC342B 36S/940 PSE W62L62 VPC MLO	Temperature 650 °C, duration 30 s
910925866988	RC340B 36S/940 PSU W60L60 VPC MLO ELP3	Temperature 650 °C, duration 30 s
910925866989	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	Temperature 650 °C, duration 30 s
910925866993	RC340B 36S/940 DIA W60L60 VPC O ELD3	Temperature 850 °C, duration 30 s
910925866995	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	Temperature 650 °C, duration 30 s
910925866999	RC340B 42S/940 DEIA W60L60 VPC MLO	Temperature 650 °C, duration 30 s
910925867010	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	Temperature 650 °C, duration 30 s
910925867013	RC340B 42S/930 DEIA W60L60 VPC MLO W3W2	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Glow-wire test
910925867027	RC340B 42S/940 DEIA W60L60 VPC MLO W3W2	Temperature 650 °C, duration 30 s
910925867043	RC340B 42S/940 PSE W60L60 VPC MLO	Temperature 650 °C, duration 30 s
910925867063	RC340B 36S/940 PSE W60L60 VPC MLO SC	Temperature 650 °C, duration 30 s
910925867064	RC340B 36S/940 DEIA W60L60 VPC MLO SC	Temperature 650 °C, duration 30 s
910925866970	RC340B 36S/940 POE W60L60 VPC MLO	Temperature 650 °C, duration 30 s
910925867014	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	Temperature 850 °C, duration 30 s
910925867025	RC340B 42S/930 DEIA W60L60 PCV MLO W3W2	Temperature 650 °C, duration 30 s
910925867029	RC340B 42S/940 DEIA W60L60 PCV MLO W3W2	Temperature 650 °C, duration 30 s
910925867037	RC340B 42S/940 DEIA W60L60 PCV PCS W3W2	Temperature 850 °C, duration 30 s
910925867041	RC340B 42S/930 DEIA W60L60 PCV PCS W3W2	Temperature 850 °C, duration 30 s
910925867168	RC340B 36S/940 DEIA W60L60 PCV PCS	Temperature 850 °C, duration 30 s
910925867221	RC340B 36S/940 POE W60L60 VPC MLO U0	Temperature 650 °C, duration 30 s
910925867224	RC340B 36S/940 POE W60L60 VPC PCS U0	Temperature 850 °C, duration 30 s
910505105983	RC340B 42S/940 SEIA W30L120 VPC DLO U4	Temperature 650 °C, duration 30 s
910505105991	RC340B 42S/840 SEIA W30L135 FLC4DLOU4SC	Temperature 650 °C, duration 30 s
910925866968	RC340B 36S/940 PSE W60L60 VPC MLO PIP	Temperature 650 °C, duration 30 s
910925866978	RC340B 36S/940 DEIA W60L60 PCV MLO	Temperature 650 °C, duration 30 s
910925866981	RC342B 36S/940 DEIA W62L62 VPC MLO	Temperature 650 °C, duration 30 s
910925867145	RC342B 28S/940 DEIA W62L62 VPC MLO	Temperature 650 °C, duration 30 s
910925867158	RC342B 28S/940 DEIA W62L62 VPC PCS	Temperature 850 °C, duration 30 s
910925867159	RC342B 36S/940 DEIA W62L62 VPC PCS	Temperature 850 °C, duration 30 s
910925867160	RC342B 42S/940 DEIA W62L62 VPC PCS	Temperature 850 °C, duration 30 s
910925867174	RC342B 28S/940 DEIA W62L62 VPC O	Temperature 850 °C, duration 30 s
910925867175	RC342B 36S/940 DEIA W62L62 VPC O	Temperature 850 °C, duration 30 s
910925867176	RC342B 42S/940 DEIA W62L62 VPC O	Temperature 850 °C, duration 30 s
910505105986	RC342B 28S/940 DEIA W31L125 VPC MXO	Temperature 650 °C, duration 30 s

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910925867015	RC340B 36S/940 PSE W15L120 VPC MLO	(0.38, 0.37) SDCM ≤3
910925867016	RC340B 36S/940 DEIA W15L120 VPC MLO	(0.38, 0.37) SDCM ≤3
910925867017	RC340B 42S/940 PSE W15L120 VPC MLO	(0.38, 0.37) SDCM ≤3
910925867018	RC340B 42S/940 DEIA W15L120 VPC MLO	(0.38, 0.37) SDCM ≤3
910925867019	RC340B 36S/940 PSU W15L120 VPC MLO ELP3	(0.38, 0.37) SDCM ≤3
910925867020	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	(0.38, 0.37) SDCM ≤3
910925867021	RC340B 42S/940 PSU W15L120 VPC MLO ELP3	(0.38, 0.37) SDCM ≤3
910925867022	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	(0.38, 0.37) SDCM ≤3
910925867024	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	(0.38, 0.37) SDCM ≤3
910925867026	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	(0.38, 0.37) SDCM ≤3
910925867149	RC342B 28S/940 DEIA W15L125 VPC MLO	(0.38, 0.37) SDCM ≤3
910925867150	RC342B 36S/940 DEIA W15L125 VPC MLO	(0.38, 0.37) SDCM ≤3
910925867153	RC342B 36S/940 DEIA W17L125 PCV MLO	(0.38, 0.37) SDCM ≤3

Order Code	Full Product Name	Initial chromaticity
910925867164	RC342B 28S/940 DEIA W15L125 VPC PCS	(0.38, 0.37) SDCM ≤3
910925867165	RC342B 36S/940 DEIA W15L125 VPC PCS	(0.38, 0.37) SDCM ≤3
910925867166	RC342B 42S/940 DEIA W15L125 VPC PCS	(0.38, 0.37) SDCM ≤3
910925867169	RC342B 36S/940 DEIA W17L125 PCV PCS	(0.38, 0.37) SDCM ≤3
910925867180	RC342B 28S/940 DEIA W15L125 VPC O	(0.38, 0.37) SDCM ≤3
910925867181	RC342B 36S/940 DEIA W15L125 VPC O	(0.38, 0.37) SDCM ≤3
910925867182	RC342B 42S/940 DEIA W15L125 VPC O	(0.38, 0.37) SDCM ≤3
910925866979	RC340B 36S/940 DEIA W30L120 VPC MLO	(0.38, 0.37) SDCM ≤3
910925866982	RC342B 36S/940 PSE W31L125 VPC MLO	(0.38, 0.37) SDCM ≤3
910925866983	RC342B 36S/940 DEIA W31L125 VPC MLO	(0.38, 0.37) SDCM ≤3
910925867030	RC340B 42S/940 DEIA W30L120 VPC MLO W3W2	(0.38, 0.37) SDCM ≤3
910925867031	RC340B 42S/940 DEIA W30L120 CPC MLO W3W2	(0.38, 0.37) SDCM ≤3
910925867032	RC340B 42S/930 DEIA W30L120 VPC MLO W3W2	(0.43, 0.40) SDCM <3
910925867033	RC340B 42S/930 DEIA W30L120 CPC MLO W3W2	(0.43, 0.40) SDCM <3
910925867038	RC340B 42S/940 DEIA W30L120 VPC PCS W3W2	(0.38, 0.37) SDCM ≤3
910925867039	RC340B 42S/940 DEIA W30L120 CPC PCS W3W2	(0.38, 0.37) SDCM ≤3
910925867042	RC340B 42S/930 DEIA W30L120 VPC PCS W3W2	(0.43, 0.40) SDCM <3
910925867147	RC342B 28S/940 DEIA W31L125 VPC MLO	(0.38, 0.37) SDCM ≤3
910925867161	RC342B 28S/940 DEIA W31L125 VPC PCS	(0.38, 0.37) SDCM ≤3
910925867162	RC342B 36S/940 DEIA W31L125 VPC PCS	(0.38, 0.37) SDCM ≤3
910925867163	RC342B 42S/940 DEIA W31L125 VPC PCS	(0.38, 0.37) SDCM ≤3
910925867177	RC342B 28S/940 DEIA W31L125 VPC O	(0.38, 0.37) SDCM ≤3
910925867178	RC342B 36S/940 DEIA W31L125 VPC O	(0.38, 0.37) SDCM ≤3
910925867179	RC342B 42S/940 DEIA W31L125 VPC O	(0.38, 0.37) SDCM ≤3
910925868910	RC340B 36S/930 SEIA W60L60 VPC MLO U4	(0.43, 0.40) SDCM <3
910925868911	RC340B 36S/930 SRD W60L60 VPC MLO U4	(0.38, 0.37) SDCM ≤3
910925868912	RC340B 36S/930 SEIA W60L60 VPC PCS U4	(0.43, 0.40) SDCM <3
910925868913	RC340B 36S/930 SEIA W60L60 VPC PCS U4 SC	(0.43, 0.40) SDCM <3
910925868914	RC340B 36S/940 SEIA W60L60 VPC MLO U4	(0.38, 0.37) SDCM ≤3
910925868915	RC340B 36S/940 SEIA W60L60 VPC MLO U4 SC	(0.38, 0.37) SDCM ≤3
910925868916	RC340B 36S/940 SEIA W60L60 VPC PCS U4	(0.38, 0.37) SDCM ≤3
910925868917	RC340B 36S/940 SEIA W60L60 VPC PCS U4 SC	(0.38, 0.37) SDCM ≤3
910925868918	RC340B 36S/940 SEIA W60L60 VPC PCS U4 W3	(0.38, 0.37) SDCM ≤3
910925868920	RC340B 42S/940 SEIA W60L60 VPC PCS U4 W3	(0.38, 0.37) SDCM ≤3
910925868921	RC342B 28S/940 SEIA W62L62 VPC MLO U4	(0.38, 0.37) SDCM ≤3
910925868922	RC342B 28S/940 SEIA W62L62 VPC PCS U4	(0.38, 0.37) SDCM ≤3
910925868924	RC342B 36S/940 SEIA W62L62 VPC MLO U4	(0.38, 0.37) SDCM ≤3
910925868925	RC342B 36S/940 SEIA W62L62 VPC PCS U4	(0.38, 0.37) SDCM ≤3
910925868927	RC342B 42S/940 SEIA W62L62 VPC MLO U4	(0.38, 0.37) SDCM ≤3
910925868928	RC342B 42S/940 SEIA W62L62 VPC PCS U4	(0.38, 0.37) SDCM ≤3
910505105985	RC340B 36S/940 SEIA W60L60 VPC MXO U4	(0.38, 0.38) SDCM <3
910925866986	RC340B 36S/940 PSU W60L60 VPC O ELP3	(0.38, 0.37) SDCM ≤3

Order Code	Full Product Name	Initial chromaticity
910925866987	RC340B 36S/940 DIA W60L60 VPC O ELP3	(0.38, 0.37) SDCM ≤3
910925867001	RC340B 42S/940 PSE W60L60 VPC O	(0.38, 0.37) SDCM ≤3
910925867002	RC340B 42S/940 DEIA W60L60 VPC O	(0.38, 0.37) SDCM ≤3
910925867006	RC340B 42S/940 PSU W60L60 VPC O ELP3	(0.38, 0.37) SDCM ≤3
910925867007	RC340B 42S/940 DIA W60L60 VPC O ELP3	(0.38, 0.37) SDCM ≤3
910925867012	RC340B 42S/940 DIA W60L60 VPC O ELD3	(0.38, 0.37) SDCM ≤3
910925867061	RC340B 36S/940 PSE W60L60 VPC O SC	(0.38, 0.37) SDCM ≤3
910925867062	RC340B 36S/940 DEIA W60L60 VPC O SC	(0.38, 0.37) SDCM ≤3
910925868919	RC340B 42S/940 SEIA W30L120 VPC PCS U4W3	(0.38, 0.37) SDCM ≤3
910925868923	RC342B 36S/940 SEIA W31L125 VPC PCS U4	(0.38, 0.37) SDCM ≤3
910925868926	RC342B 42S/940 SEIA W31L125 VPC PCS U4	(0.38, 0.37) SDCM ≤3
910925866969	RC340B 36S/940 DEIA W60L60 VPC MLO	(0.38, 0.37) SDCM ≤3
910925867023	RC340B 42S/930 DEIA W60L60 CPC MLO W3W2	(0.43, 0.40) SDCM <3
910925867028	RC340B 42S/940 DEIA W60L60 CPC MLO W3W2	(0.38, 0.37) SDCM ≤3
910925867036	RC340B 42S/940 DEIA W60L60 CPC PCS W3W2	(0.38, 0.37) SDCM ≤3
910925867040	RC340B 42S/930 DEIA W60L60 CPC PCS W3W2	(0.43, 0.40) SDCM <3
910925867046	RC340B 36S/940 PSE W60L60 CPC MLO	(0.38, 0.37) SDCM ≤3
910925867047	RC340B 42S/940 PSE W60L60 CPC MLO	(0.38, 0.37) SDCM ≤3
910925867048	RC340B 42S/940 DEIA W60L60 CPC MLO	(0.38, 0.37) SDCM ≤3
910925867167	RC342B 42S/940 DEIA W62L62 CPC PCS	(0.38, 0.37) SDCM ≤3
910925867068	RC340B 42S/930 DEIA W30L120 CPC PCS W3W2	(0.43, 0.40) SDCM <3
910925866967	RC340B 36S/940 DEIA W60L60 VPC O	(0.38, 0.37) SDCM ≤3
910925866972	RC340B 36S/940 PSE W60L60 VPC PCS	(0.38, 0.37) SDCM ≤3
910925866973	RC340B 36S/940 DEIA W60L60 VPC PCS	(0.38, 0.37) SDCM ≤3
910925866977	RC340B 36S/940 DEIA W60L60 CPC MLO	(0.38, 0.37) SDCM ≤3
910925866990	RC340B 36S/940 PSU W60L60 VPC PCS ELP3	(0.38, 0.37) SDCM ≤3
910925866991	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	(0.38, 0.37) SDCM ≤3
910925866997	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	(0.38, 0.37) SDCM ≤3
910925867003	RC340B 42S/940 PSE W60L60 VPC PCS	(0.38, 0.37) SDCM ≤3
910925867004	RC340B 42S/940 DEIA W60L60 VPC PCS	(0.38, 0.37) SDCM ≤3
910925867008	RC340B 42S/940 PSU W60L60 VPC PCS ELP3	(0.38, 0.37) SDCM ≤3
910925867009	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	(0.38, 0.37) SDCM ≤3
910925867034	RC340B 42S/930 DEIA W60L60 VPC PCS W3W2	(0.43, 0.40) SDCM <3
910925867035	RC340B 42S/940 DEIA W60L60 VPC PCS W3W2	(0.38, 0.37) SDCM ≤3
910925867044	RC340B 36S/940 PSE W60L60 CPC PCS PIP	(0.38, 0.37) SDCM ≤3
910925867045	RC340B 36S/940 DEIA W60L60 CPC PCS	(0.38, 0.37) SDCM ≤3
910925867049	RC340B 42S/940 PSE W60L60 CPC PCS	(0.38, 0.37) SDCM ≤3
910925867050	RC340B 42S/940 DEIA W60L60 CPC PCS	(0.38, 0.37) SDCM ≤3
910925867065	RC340B 36S/940 PSE W60L60 VPC PCS SC	(0.38, 0.37) SDCM ≤3
910925867066	RC340B 36S/940 DEIA W60L60 VPC PCS SC	(0.38, 0.37) SDCM ≤3
910505105982	RC340B 36S/940 SEIA W60L60 VPC DLO U4	(0.38, 0.38) SDCM <3
910505105987	RC340B 42S/840 SEIA W60L60 VPC PCS U4 SC	(0.38, 0.38) SDCM <3

Order Code	Full Product Name	Initial chromaticity
910505105990	RC340B 36S/840 SEIA W67L67 FLC4DLO U4 SC	(0.38, 0.38) SDCM <3
910505105989	RC342B 42S/840 DEIA W62L62 VPC PCS	(0.38, 0.38) SDCM <3
910505105984	RC342B 36S/940 DEIA W31L125 VPC DLO	(0.38, 0.38) SDCM <3
910505105988	RC340B 42S/840 PSU W30L120 VPC PCS ELB3	(0.38, 0.38) SDCM <3
910505105992	RC340B 36S/840 DEIA W30L135 FLC2 DLO SC	(0.38, 0.38) SDCM <3
910925866966	RC340B 36S/940 PSE W60L60 VPC O	(0.38, 0.37) SDCM ≤3
910925866980	RC342B 36S/940 PSE W62L62 VPC MLO	(0.38, 0.37) SDCM ≤3
910925866988	RC340B 36S/940 PSU W60L60 VPC MLO ELP3	(0.38, 0.37) SDCM ≤3
910925866989	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	(0.38, 0.37) SDCM ≤3
910925866993	RC340B 36S/940 DIA W60L60 VPC O ELD3	(0.38, 0.37) SDCM ≤3
910925866995	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	(0.38, 0.37) SDCM ≤3
910925866999	RC340B 42S/940 DEIA W60L60 VPC MLO	(0.38, 0.37) SDCM ≤3
910925867010	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	(0.38, 0.37) SDCM ≤3
910925867013	RC340B 42S/930 DEIA W60L60 VPC MLO W3W2	(0.43, 0.40) SDCM <3
910925867027	RC340B 42S/940 DEIA W60L60 VPC MLO W3W2	(0.38, 0.37) SDCM ≤3
910925867043	RC340B 42S/940 PSE W60L60 VPC MLO	(0.38, 0.37) SDCM ≤3
910925867063	RC340B 36S/940 PSE W60L60 VPC MLO SC	(0.38, 0.37) SDCM ≤3
910925867064	RC340B 36S/940 DEIA W60L60 VPC MLO SC	(0.38, 0.37) SDCM ≤3
910925866970	RC340B 36S/940 POE W60L60 VPC MLO	(0.38, 0.37) SDCM ≤3
910925867014	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	(0.38, 0.37) SDCM ≤3
910925867025	RC340B 42S/930 DEIA W60L60 PCV MLO W3W2	(0.43, 0.40) SDCM <3
910925867029	RC340B 42S/940 DEIA W60L60 PCV MLO W3W2	(0.38, 0.37) SDCM ≤3
910925867037	RC340B 42S/940 DEIA W60L60 PCV PCS W3W2	(0.38, 0.37) SDCM ≤3
910925867041	RC340B 42S/930 DEIA W60L60 PCV PCS W3W2	(0.43, 0.40) SDCM <3
910925867168	RC340B 36S/940 DEIA W60L60 PCV PCS	(0.38, 0.37) SDCM ≤3
910925867221	RC340B 36S/940 POE W60L60 VPC MLO U0	(0.38, 0.37) SDCM ≤3
910925867224	RC340B 36S/940 POE W60L60 VPC PCS U0	(0.38, 0.37) SDCM ≤3
910505105983	RC340B 42S/940 SEIA W30L120 VPC DLO U4	(0.38, 0.38) SDCM <3
910505105991	RC340B 42S/840 SEIA W30L135 FLC4DLOU4SC	(0.38, 0.38) SDCM <3
910925866968	RC340B 36S/940 PSE W60L60 VPC MLO PIP	(0.38, 0.37) SDCM ≤3
910925866978	RC340B 36S/940 DEIA W60L60 PCV MLO	(0.38, 0.37) SDCM ≤3
910925866981	RC342B 36S/940 DEIA W62L62 VPC MLO	(0.38, 0.37) SDCM ≤3
910925867145	RC342B 28S/940 DEIA W62L62 VPC MLO	(0.38, 0.37) SDCM ≤3
910925867158	RC342B 28S/940 DEIA W62L62 VPC PCS	(0.38, 0.37) SDCM ≤3
910925867159	RC342B 36S/940 DEIA W62L62 VPC PCS	(0.38, 0.37) SDCM ≤3
910925867160	RC342B 42S/940 DEIA W62L62 VPC PCS	(0.38, 0.37) SDCM ≤3
910925867174	RC342B 28S/940 DEIA W62L62 VPC O	(0.38, 0.37) SDCM ≤3
910925867175	RC342B 36S/940 DEIA W62L62 VPC O	(0.38, 0.37) SDCM ≤3
910925867176	RC342B 42S/940 DEIA W62L62 VPC O	(0.38, 0.37) SDCM ≤3
910505105986	RC342B 28S/940 DEIA W31L125 VPC MXO	(0.38, 0.38) SDCM <3

Product Data


Order Code	Full Product Name	Product family code
910925867015	RC340B 36S/940 PSE W15L120 VPC MLO	RC340B
910925867016	RC340B 36S/940 DEIA W15L120 VPC MLO	RC340B
910925867017	RC340B 42S/940 PSE W15L120 VPC MLO	RC340B
910925867018	RC340B 42S/940 DEIA W15L120 VPC MLO	RC340B
910925867019	RC340B 36S/940 PSU W15L120 VPC MLO ELP3	RC340B
910925867020	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	RC340B
910925867021	RC340B 42S/940 PSU W15L120 VPC MLO ELP3	RC340B
910925867022	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	RC340B
910925867024	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	RC340B
910925867026	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	RC340B
910925867149	RC342B 28S/940 DEIA W15L125 VPC MLO	RC342B
910925867150	RC342B 36S/940 DEIA W15L125 VPC MLO	RC342B
910925867153	RC342B 36S/940 DEIA W17L125 PCV MLO	RC342B
910925867164	RC342B 28S/940 DEIA W15L125 VPC PCS	RC342B
910925867165	RC342B 36S/940 DEIA W15L125 VPC PCS	RC342B
910925867166	RC342B 42S/940 DEIA W15L125 VPC PCS	RC342B
910925867169	RC342B 36S/940 DEIA W17L125 PCV PCS	RC342B
910925867180	RC342B 28S/940 DEIA W15L125 VPC O	RC342B
910925867181	RC342B 36S/940 DEIA W15L125 VPC O	RC342B
910925867182	RC342B 42S/940 DEIA W15L125 VPC O	RC342B
910925866979	RC340B 36S/940 DEIA W30L120 VPC MLO	RC340B
910925866982	RC342B 36S/940 PSE W31L125 VPC MLO	RC342B
910925866983	RC342B 36S/940 DEIA W31L125 VPC MLO	RC342B
910925867030	RC340B 42S/940 DEIA W30L120 VPC MLO W3W2	RC340B
910925867031	RC340B 42S/940 DEIA W30L120 CPC MLO W3W2	RC340B
910925867032	RC340B 42S/930 DEIA W30L120 VPC MLO W3W2	RC340B
910925867033	RC340B 42S/930 DEIA W30L120 CPC MLO W3W2	RC340B
910925867038	RC340B 42S/940 DEIA W30L120 VPC PCS W3W2	RC340B
910925867039	RC340B 42S/940 DEIA W30L120 CPC PCS W3W2	RC340B
910925867042	RC340B 42S/930 DEIA W30L120 VPC PCS W3W2	RC340B
910925867147	RC342B 28S/940 DEIA W31L125 VPC MLO	RC342B
910925867161	RC342B 28S/940 DEIA W31L125 VPC PCS	RC342B
910925867162	RC342B 36S/940 DEIA W31L125 VPC PCS	RC342B
910925867163	RC342B 42S/940 DEIA W31L125 VPC PCS	RC342B
910925867177	RC342B 28S/940 DEIA W31L125 VPC O	RC342B
910925867178	RC342B 36S/940 DEIA W31L125 VPC O	RC342B
910925867179	RC342B 42S/940 DEIA W31L125 VPC O	RC342B
910925868910	RC340B 36S/930 SEIA W60L60 VPC MLO U4	RC340B
910925868911	RC340B 36S/930 SRD W60L60 VPC MLO U4	RC340B
910925868912	RC340B 36S/930 SEIA W60L60 VPC PCS U4	RC340B
910925868913	RC340B 36S/930 SEIA W60L60 VPC PCS U4 SC	RC340B

Order Code	Full Product Name	Product family code
910925868914	RC340B 36S/940 SEIA W60L60 VPC MLO U4	RC340B
910925868915	RC340B 36S/940 SEIA W60L60 VPC MLO U4 SC	RC340B
910925868916	RC340B 36S/940 SEIA W60L60 VPC PCS U4	RC340B
910925868917	RC340B 36S/940 SEIA W60L60 VPC PCS U4 SC	RC340B
910925868918	RC340B 36S/940 SEIA W60L60 VPC PCS U4 W3	RC340B
910925868920	RC340B 42S/940 SEIA W60L60 VPC PCS U4 W3	RC340B
910925868921	RC342B 28S/940 SEIA W62L62 VPC MLO U4	RC342B
910925868922	RC342B 28S/940 SEIA W62L62 VPC PCS U4	RC342B
910925868924	RC342B 36S/940 SEIA W62L62 VPC MLO U4	RC342B
910925868925	RC342B 36S/940 SEIA W62L62 VPC PCS U4	RC342B
910925868927	RC342B 42S/940 SEIA W62L62 VPC MLO U4	RC342B
910925868928	RC342B 42S/940 SEIA W62L62 VPC PCS U4	RC342B
910505105985	RC340B 36S/940 SEIA W60L60 VPC MXO U4	RC340B
910925866986	RC340B 36S/940 PSU W60L60 VPC O ELP3	RC340B
910925866987	RC340B 36S/940 DIA W60L60 VPC O ELP3	RC340B
910925867001	RC340B 42S/940 PSE W60L60 VPC O	RC340B
910925867002	RC340B 42S/940 DEIA W60L60 VPC O	RC340B
910925867006	RC340B 42S/940 PSU W60L60 VPC O ELP3	RC340B
910925867007	RC340B 42S/940 DIA W60L60 VPC O ELP3	RC340B
910925867012	RC340B 42S/940 DIA W60L60 VPC O ELD3	RC340B
910925867061	RC340B 36S/940 PSE W60L60 VPC O SC	RC340B
910925867062	RC340B 36S/940 DEIA W60L60 VPC O SC	RC340B
910925868919	RC340B 42S/940 SEIA W30L120 VPC PCS U4W3	RC340B
910925868923	RC342B 36S/940 SEIA W31L125 VPC PCS U4	RC342B
910925868926	RC342B 42S/940 SEIA W31L125 VPC PCS U4	RC342B
910925866969	RC340B 36S/940 DEIA W60L60 VPC MLO	RC340B
910925867023	RC340B 42S/930 DEIA W60L60 CPC MLO W3W2	RC340B
910925867028	RC340B 42S/940 DEIA W60L60 CPC MLO W3W2	RC340B
910925867036	RC340B 42S/940 DEIA W60L60 CPC PCS W3W2	RC340B
910925867040	RC340B 42S/930 DEIA W60L60 CPC PCS W3W2	RC340B
910925867046	RC340B 36S/940 PSE W60L60 CPC MLO	RC340B
910925867047	RC340B 42S/940 PSE W60L60 CPC MLO	RC340B
910925867048	RC340B 42S/940 DEIA W60L60 CPC MLO	RC340B
910925867167	RC342B 42S/940 DEIA W62L62 CPC PCS	RC342B
910925867068	RC340B 42S/930 DEIA W30L120 CPC PCS W3W2	RC340B
910925866967	RC340B 36S/940 DEIA W60L60 VPC O	RC340B
910925866972	RC340B 36S/940 PSE W60L60 VPC PCS	RC340B
910925866973	RC340B 36S/940 DEIA W60L60 VPC PCS	RC340B
910925866977	RC340B 36S/940 DEIA W60L60 CPC MLO	RC340B
910925866990	RC340B 36S/940 PSU W60L60 VPC PCS ELP3	RC340B
910925866991	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	RC340B
910925866997	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	RC340B


Order Code	Full Product Name	Product family code
910925867003	RC340B 42S/940 PSE W60L60 VPC PCS	RC340B
910925867004	RC340B 42S/940 DEIA W60L60 VPC PCS	RC340B
910925867008	RC340B 42S/940 PSU W60L60 VPC PCS ELP3	RC340B
910925867009	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	RC340B
910925867034	RC340B 42S/930 DEIA W60L60 VPC PCS W3W2	RC340B
910925867035	RC340B 42S/940 DEIA W60L60 VPC PCS W3W2	RC340B
910925867044	RC340B 36S/940 PSE W60L60 CPC PCS PIP	RC340B
910925867045	RC340B 36S/940 DEIA W60L60 CPC PCS	RC340B
910925867049	RC340B 42S/940 PSE W60L60 CPC PCS	RC340B
910925867050	RC340B 42S/940 DEIA W60L60 CPC PCS	RC340B
910925867065	RC340B 36S/940 PSE W60L60 VPC PCS SC	RC340B
910925867066	RC340B 36S/940 DEIA W60L60 VPC PCS SC	RC340B
910505105982	RC340B 36S/940 SEIA W60L60 VPC DLO U4	RC340B
910505105987	RC340B 42S/840 SEIA W60L60 VPC PCS U4 SC	RC340B
910505105990	RC340B 36S/840 SEIA W67L67 FLC4DLO U4 SC	RC340B
910505105989	RC342B 42S/840 DEIA W62L62 VPC PCS	RC340B
910505105984	RC342B 36S/940 DEIA W31L125 VPC DLO	RC340B
910505105988	RC340B 42S/840 PSU W30L120 VPC PCS ELB3	RC340B
910505105992	RC340B 36S/840 DEIA W30L135 FLC2 DLO SC	RC340B
910925866966	RC340B 36S/940 PSE W60L60 VPC O	RC340B
910925866980	RC342B 36S/940 PSE W62L62 VPC MLO	RC342B
910925866988	RC340B 36S/940 PSU W60L60 VPC MLO ELP3	RC340B
910925866989	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	RC340B
910925866993	RC340B 36S/940 DIA W60L60 VPC O ELD3	RC340B
910925866995	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	RC340B
910925866999	RC340B 42S/940 DEIA W60L60 VPC MLO	RC340B
910925867010	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	RC340B
910925867013	RC340B 42S/930 DEIA W60L60 VPC MLO W3W2	RC340B
910925867027	RC340B 42S/940 DEIA W60L60 VPC MLO W3W2	RC340B
910925867043	RC340B 42S/940 PSE W60L60 VPC MLO	RC340B
910925867063	RC340B 36S/940 PSE W60L60 VPC MLO SC	RC340B
910925867064	RC340B 36S/940 DEIA W60L60 VPC MLO SC	RC340B
910925866970	RC340B 36S/940 POE W60L60 VPC MLO	RC340B
910925867014	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	RC340B
910925867025	RC340B 42S/930 DEIA W60L60 PCV MLO W3W2	RC340B
910925867029	RC340B 42S/940 DEIA W60L60 PCV MLO W3W2	RC340B
910925867037	RC340B 42S/940 DEIA W60L60 PCV PCS W3W2	RC340B
910925867041	RC340B 42S/930 DEIA W60L60 PCV PCS W3W2	RC340B
910925867168	RC340B 36S/940 DEIA W60L60 PCV PCS	RC340B
910925867221	RC340B 36S/940 POE W60L60 VPC MLO U0	RC340B
910925867224	RC340B 36S/940 POE W60L60 VPC PCS U0	RC340B
910505105983	RC340B 42S/940 SEIA W30L120 VPC DLO U4	RC340B

Order Code	Full Product Name	Product family code
910505105991	RC340B 42S/840 SEIA W30L135 FLC4DLOU4SC	RC340B
910925866968	RC340B 36S/940 PSE W60L60 VPC MLO PIP	RC340B
910925866978	RC340B 36S/940 DEIA W60L60 PCV MLO	RC340B
910925866981	RC342B 36S/940 DEIA W62L62 VPC MLO	RC342B
910925867145	RC342B 28S/940 DEIA W62L62 VPC MLO	RC342B
910925867158	RC342B 28S/940 DEIA W62L62 VPC PCS	RC342B
910925867159	RC342B 36S/940 DEIA W62L62 VPC PCS	RC342B
910925867160	RC342B 42S/940 DEIA W62L62 VPC PCS	RC342B
910925867174	RC342B 28S/940 DEIA W62L62 VPC O	RC342B
910925867175	RC342B 36S/940 DEIA W62L62 VPC O	RC342B
910925867176	RC342B 42S/940 DEIA W62L62 VPC O	RC342B
910505105986	RC342B 28S/940 DEIA W31L125 VPC MXO	RC340B


Polar normal diagrams




RC340BI - 910925866978




RC340BI - 910925866989




RC340BI - 910925867030




RC340BI - 910925867031




RC340BI - 910925866987




RC340BI - 910925868912




RC340BI - 910925868924




RC340BI - 910925868915




RC340BI - 910925868917




RC340BI - 910925868928




RC340BI - 910925868910




RC340BI - 910925868927




RC340BI - 910925868921




RC340BI - 910925868926




RC340BI - 910925868914




RC340BI - 910925868923




RC340BI - 910925868911




RC340BI - 910925868922




RC340BI - 910925868925




RC340BI - 910925868920




RC340BI - 910925866969




RC340BI - 910925866968




RC340BI - 910925866970




RC340BI - 910925866979




RC340BI - 910925866981




RC340BI - 910925867038




RC340BI - 910925867040




RC340BI - 910925867050




RC340BI - 910925866973




RC340BI - 910925866991




RC340BI - 910925866993




RC340BI - 910925867002




RC340BI - 910925867003




RC340BI - 910925866977




RC340BI - 910925866995




RC340BI - 910925867012




RC340BI - 910925867017




RC340BI - 910925867019




RC340BI - 910925867033




RC340BI - 910925867024




RC340BI - 910925867043




RC340BI - 910925867049




RC340BI - 910925866967




RC340BI - 910925867010




RC340BI - 910925867013




RC340BI - 910925867022




RC340BI - 910925867034




RC340BI - 910925867039




RC340BI - 910925867032




RC340BI - 910925867064




RC340BI - 910925866980




RC340BI - 910925866982




RC340BI - 910925866983




RC340BI - 910925866988




RC340BI - 910925866997




RC340BI - 910925867006




RC340BI - 910925867009




RC340BI - 910925867047




RC340BI - 910925867062




RC340BI - 910925867063




RC340BI - 910925866966




RC340BI - 910925867008




RC340BI - 910925867018




RC340BI - 910925867016




RC340BI - 910925867021




RC340BI - 910925867025




RC340BI - 910925867028




RC340BI - 910925867014




RC340BI - 910925867145




RC340BI - 910925867147




RC340BI - 910925867020




RC340BI - 910925867026




RC340BI - 910925867035




RC340BI - 910925867036




RC340BI - 910925867044




RC340BI - 910925867045




RC340BI - 910925867048




RC340BI - 910925867065




RC340BI - 910925867149




RC340BI - 910925867159




RC340BI - 910925867158




RC340BI - 910925867165




RC340BI - 910925867166




RC340BI - 910925867167




RC340BI - 910925867177




RC340BI - 910925867178




RC340BI - 910925867221




RC340BI - 910925867041




RC340BI - 910925867066




RC340BI - 910925867162




RC340BI - 910925867160




RC340BI - 910925867153




RC340BI - 910925867175




RC340BI - 910925867179




RC340BI - 910925867182




RC340BI - 910925867163




RC340BI - 910925867174




RC340BI - 910925867176




RC340BI - 910925866972




RC340BI - 910925866986




RC340BI - 910925866990




RC340BI - 910925866999




RC340BI - 910925867001




RC340BI - 910925867004




RC340BI - 910925867007




RC340BI - 910925867015




RC340BI - 910925867023




RC340BI - 910925867027




RC340BI - 910925867029




RC340BI - 910925867037




RC340BI - 910925867046




RC340BI - 910925867042




RC340BI - 910925867061




RC340BI - 910925867068




RC340BI - 910925867150




RC340BI - 910925867161




RC340BI - 910925867164




RC340BI - 910925867168




RC340BI - 910925867169




RC340BI - 910925867181




RC340BI - 910925867180




RC340BI - 910925867224




RC340BI - 910925868913




RC340BI - 910925868916




RC340BI - 910925868918




RC340BI - 910925868919




910505105984




910505105990




910505105982




910505105985




910505105987




910505105992




910505105989




910505105986



910505105988



910505105991



910505105983