



FlexBlend - Unlocking the potential of LED lighting in offices

FlexBlend Recessed

Office owners and staff responsible for lighting operations are searching for high quality yet energy-efficient lighting that complies with norms and regulations. Designed to support these needs, Philips FlexBlend is enabling building owners to fully optimize their lighting operations, by offering office-compliant lighting with an attractive return on investment. Furthermore, FlexBlend provides the required flexibility by being easy applied on different ceiling types as well as in different office spaces like open office or meeting rooms. Though technology is changing fast, the ideal lighting solution is also expected to be ready to incorporate innovations and future advances that can help optimize operations further. For this reason, Philips FlexBlend is also ready to be connected to controls such as Actilume or used together with the Philips SpaceWise lighting system. It can also be connected to software-based lighting systems like Interact Office, which provides the luminaire with further intelligence and enables it to collect valuable data about its environment

Benefits

- High-quality office-compliant lighting
- Choice of three different exit-windows
- Fast return on investment
- Application flexibility
- Scalable and ready to be connected to controls and lighting systems

FlexBlend Recessed


Features

- Fully office-compliant (UGR <19)
- Homogenous and uniform light effect
- Dimensional variety, local options
- Various mounting options
- Integrated sensors
- Can be combined with Philips ActiLume and SpaceWise systems
- Ready to be connected to software based lighting systems such as Interact Office

Application

- Offices
- Education
- Healthcare
- Banks

Versions




FlexBlend Recessed

Versions

FlexBlend Recessed


















Dimensional drawing



FlexBlend Recessed

Dimensional drawing




FlexBlend Recessed

Product details



Upgradable sensor

O_FlexBlend Recessed-
RC342B_W62L62_MLO_VPC




FlexBlend Recessed-
RC340B_MLO_DPP

FlexBlend Recessed-
RC340B_W60L60_Backcover_VP
C



FlexBlend Recessed-
RC340B_W60L60_CPC brackets

FlexBlend Recessed-
RC340B_W60L60_CPC
brackets_B



FlexBlend Recessed-
RC340B_OPA_DPP

FlexBlend Recessed-
RC340B_PCS_DPP



FlexBlend Recessed

Product details

O_FlexBlend Recessed-
RC340B_W60L60_PCS_VPC



FlexBlend Recessed-
RC340B_W60L60_CPC
brackets_A



FlexBlend Recessed RC340B PIP
Open



FlexBlend Recessed-
RC340B_W60L60_backcover_PC
V



O_FlexBlend Recessed-
RC340B_W60L60_MLO_VPC



O_FlexBlend Recessed-
RC340B_W60L60_MLO_CPC



FlexBlend Recessed-RC340B PIP
Closed



FlexBlend_RC340B_W30L120_U4
_DPP



FlexBlend Recessed

Product details

FlexBlend Recessed-
RC340B_W60L60_backcover_CP
C



General Information

Driver included	Yes
Number of gear units	1 unit

Light Technical

Beam angle of light source	120 degree(s)
Optic type	Wide beam

Operating and Electrical

Line Frequency	50 to 60 Hz
----------------	-------------

Mechanical and Housing

Housing Color	White
---------------	-------

Approval and Application

Ambient temperature range	+10 to +40 °C
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

General Information

Order Code	Full Product Name	Light source replaceable	Service tag
910925867015	RC340B 36S/940 PSE W15L120 VPC MLO	No	Yes
910925867016	RC340B 36S/940 DEIA W15L120 VPC MLO	No	Yes
910925867017	RC340B 42S/940 PSE W15L120 VPC MLO	No	Yes
910925867018	RC340B 42S/940 DEIA W15L120 VPC MLO	No	Yes
910925867019	RC340B 36S/940 PSU W15L120 VPC MLO ELP3	No	Yes
910925867020	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	No	Yes
910925867021	RC340B 42S/940 PSU W15L120 VPC MLO ELP3	No	Yes
910925867022	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	No	Yes
910925867024	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	No	Yes
910925867026	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	No	Yes
910925867149	RC342B 28S/940 DEIA W15L125 VPC MLO	No	Yes
910925867150	RC342B 36S/940 DEIA W15L125 VPC MLO	No	Yes
910925867153	RC342B 36S/940 DEIA W17L125 PCV MLO	No	Yes
910925867164	RC342B 28S/940 DEIA W15L125 VPC PCS	No	Yes
910925867165	RC342B 36S/940 DEIA W15L125 VPC PCS	No	Yes
910925867166	RC342B 42S/940 DEIA W15L125 VPC PCS	No	Yes
910925867169	RC342B 36S/940 DEIA W17L125 PCV PCS	No	Yes
910925867180	RC342B 28S/940 DEIA W15L125 VPC O	No	Yes
910925867181	RC342B 36S/940 DEIA W15L125 VPC O	No	Yes
910925867182	RC342B 42S/940 DEIA W15L125 VPC O	No	Yes
910925866979	RC340B 36S/940 DEIA W30L120 VPC MLO	No	Yes
910925866982	RC342B 36S/940 PSE W31L125 VPC MLO	No	Yes
910925866983	RC342B 36S/940 DEIA W31L125 VPC MLO	No	Yes
910925867030	RC340B 42S/940 DEIA W30L120 VPC MLO W3W2	No	Yes
910925867031	RC340B 42S/940 DEIA W30L120 CPC MLO W3W2	No	Yes
910925867032	RC340B 42S/930 DEIA W30L120 VPC MLO W3W2	No	Yes
910925867033	RC340B 42S/930 DEIA W30L120 CPC MLO W3W2	No	Yes
910925867038	RC340B 42S/940 DEIA W30L120 VPC PCS W3W2	No	Yes
910925867039	RC340B 42S/940 DEIA W30L120 CPC PCS W3W2	No	Yes
910925867042	RC340B 42S/930 DEIA W30L120 VPC PCS W3W2	No	Yes
910925867147	RC342B 28S/940 DEIA W31L125 VPC MLO	No	Yes
910925867161	RC342B 28S/940 DEIA W31L125 VPC PCS	No	Yes
910925867162	RC342B 36S/940 DEIA W31L125 VPC PCS	No	Yes
910925867163	RC342B 42S/940 DEIA W31L125 VPC PCS	No	Yes
910925867177	RC342B 28S/940 DEIA W31L125 VPC O	No	Yes
910925867178	RC342B 36S/940 DEIA W31L125 VPC O	No	Yes
910925867179	RC342B 42S/940 DEIA W31L125 VPC O	No	Yes

Order Code	Full Product Name	Light source replaceable	Service tag
910925868910	RC340B 36S/930 SRD W60L60 VPC MLO U4	No	Yes
910925868911	RC340B 36S/930 SRD W60L60 VPC MLO U4	No	Yes
910925868912	RC340B 36S/930 SEIA W60L60 VPC PCS U4	No	Yes
910925868913	RC340B 36S/930 SEIA W60L60 VPC PCS U4 SC	No	Yes
910925868914	RC340B 36S/940 SEIA W60L60 VPC MLO U4	No	Yes
910925868915	RC340B 36S/940 SEIA W60L60 VPC MLO U4 SC	No	Yes
910925868916	RC340B 36S/940 SEIA W60L60 VPC PCS U4	No	Yes
910925868917	RC340B 36S/940 SEIA W60L60 VPC PCS U4 SC	No	Yes
910925868918	RC340B 36S/940 SEIA W60L60 VPC PCS U4 W3	No	Yes
910925868920	RC340B 42S/940 SEIA W60L60 VPC PCS U4 W3	No	Yes
910925868921	RC342B 28S/940 SEIA W62L62 VPC MLO U4	No	Yes
910925868922	RC342B 28S/940 SEIA W62L62 VPC PCS U4	No	Yes
910925868924	RC342B 36S/940 SEIA W62L62 VPC MLO U4	No	Yes
910925868925	RC342B 36S/940 SEIA W62L62 VPC PCS U4	No	Yes
910925868927	RC342B 42S/940 SEIA W62L62 VPC MLO U4	No	Yes
910925868928	RC342B 42S/940 SEIA W62L62 VPC PCS U4	No	Yes
910505105985	RC340B 36S/940 SEIA W60L60 VPC MXO U4	-	-
910925866986	RC340B 36S/940 PSU W60L60 VPC O ELP3	No	Yes
910925866987	RC340B 36S/940 DIA W60L60 VPC O ELP3	No	Yes
910925867001	RC340B 42S/940 PSE W60L60 VPC O	No	Yes
910925867002	RC340B 42S/940 DEIA W60L60 VPC O	No	Yes
910925867006	RC340B 42S/940 PSU W60L60 VPC O ELP3	No	Yes
910925867007	RC340B 42S/940 DIA W60L60 VPC O ELP3	No	Yes
910925867012	RC340B 42S/940 DIA W60L60 VPC O ELD3	No	Yes
910925867061	RC340B 36S/940 PSE W60L60 VPC O SC	No	Yes
910925867062	RC340B 36S/940 DEIA W60L60 VPC O SC	No	Yes
910925868919	RC340B 42S/940 SEIA W30L120 VPC PCS U4W3	No	Yes
910925868923	RC342B 36S/940 SEIA W31L125 VPC PCS U4	No	Yes
910925868926	RC342B 42S/940 SEIA W31L125 VPC PCS U4	No	Yes
910925866969	RC340B 36S/940 DEIA W60L60 VPC MLO	No	Yes
910925867023	RC340B 42S/930 DEIA W60L60 CPC MLO W3W2	No	Yes
910925867028	RC340B 42S/940 DEIA W60L60 CPC MLO W3W2	No	Yes
910925867036	RC340B 42S/940 DEIA W60L60 CPC PCS W3W2	No	Yes
910925867040	RC340B 42S/930 DEIA W60L60 CPC PCS W3W2	No	Yes
910925867046	RC340B 36S/940 PSE W60L60 CPC MLO	No	Yes
910925867047	RC340B 42S/940 PSE W60L60 CPC MLO	No	Yes
910925867048	RC340B 42S/940 DEIA W60L60 CPC MLO	No	Yes
910925867167	RC342B 42S/940 DEIA W62L62 CPC PCS	No	Yes
910925867068	RC340B 42S/930 DEIA W30L120 CPC PCS W3W2	No	Yes
910925866967	RC340B 36S/940 DEIA W60L60 VPC O	No	Yes
910925866972	RC340B 36S/940 PSE W60L60 VPC PCS	No	Yes
910925866973	RC340B 36S/940 DEIA W60L60 VPC PCS	No	Yes
910925866977	RC340B 36S/940 DEIA W60L60 CPC MLO	No	Yes
910925866990	RC340B 36S/940 PSU W60L60 VPC PCS ELP3	No	Yes
910925866991	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	No	Yes
910925866997	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	No	Yes
910925867003	RC340B 42S/940 PSE W60L60 VPC PCS	No	Yes
910925867004	RC340B 42S/940 DEIA W60L60 VPC PCS	No	Yes
910925867008	RC340B 42S/940 PSU W60L60 VPC PCS ELP3	No	Yes
910925867009	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	No	Yes
910925867034	RC340B 42S/930 DEIA W60L60 VPC PCS W3W2	No	Yes
910925867035	RC340B 42S/940 DEIA W60L60 VPC PCS W3W2	No	Yes

FlexBlend Recessed

Order Code	Full Product Name	Light source replaceable	Service tag
910925867044	RC340B 36S/940 PSE W60L60 CPC PCS PIP	No	Yes
910925867045	RC340B 36S/940 DEIA W60L60 CPC PCS	No	Yes
910925867049	RC340B 42S/940 PSE W60L60 CPC PCS	No	Yes
910925867050	RC340B 42S/940 DEIA W60L60 CPC PCS	No	Yes
910925867065	RC340B 36S/940 PSE W60L60 VPC PCS SC	No	Yes
910925867066	RC340B 36S/940 DEIA W60L60 VPC PCS SC	No	Yes
910505105982	RC340B 36S/940 SEIA W60L60 VPC DLO U4	-	-
910505105987	RC340B 42S/840 SEIA W60L60 VPC PCS U4 SC	-	-
910505105990	RC340B 36S/840 SEIA W67L67 FLC4DLO U4 SC	-	-
910505105989	RC342B 42S/840 DEIA W62L62 VPC PCS	-	-
910505105984	RC342B 36S/940 DEIA W31L125 VPC DLO	-	-
910505105988	RC340B 42S/840 PSU W30L120 VPC PCS ELB3	-	-
910505105992	RC340B 36S/840 DEIA W30L135 FLC2 DLO SC	-	-
910925866966	RC340B 36S/940 PSE W60L60 VPC O	No	Yes
910925866980	RC342B 36S/940 PSE W62L62 VPC MLO	No	Yes
910925866988	RC340B 36S/940 PSU W60L60 VPC MLO ELP3	No	Yes
910925866989	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	No	Yes
910925866993	RC340B 36S/940 DIA W60L60 VPC O ELD3	No	Yes
910925866995	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	No	Yes
910925866999	RC340B 42S/940 DEIA W60L60 VPC MLO	No	Yes
910925867010	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	No	Yes
910925867013	RC340B 42S/930 DEIA W60L60 VPC MLO W3W2	No	Yes
910925867027	RC340B 42S/940 DEIA W60L60 VPC MLO W3W2	No	Yes
910925867043	RC340B 42S/940 PSE W60L60 VPC MLO	No	Yes
910925867063	RC340B 36S/940 PSE W60L60 VPC MLO SC	No	Yes
910925867064	RC340B 36S/940 DEIA W60L60 VPC MLO SC	No	Yes
910925866970	RC340B 36S/940 POE W60L60 VPC MLO	No	Yes
910925867014	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	No	Yes
910925867025	RC340B 42S/930 DEIA W60L60 PCV MLO W3W2	No	Yes
910925867029	RC340B 42S/940 DEIA W60L60 PCV MLO W3W2	No	Yes
910925867037	RC340B 42S/940 DEIA W60L60 PCV PCS W3W2	No	Yes
910925867041	RC340B 42S/930 DEIA W60L60 PCV PCS W3W2	No	Yes
910925867168	RC340B 36S/940 DEIA W60L60 PCV PCS	No	Yes
910925867221	RC340B 36S/940 POE W60L60 VPC MLO U0	No	Yes
910925867224	RC340B 36S/940 POE W60L60 VPC PCS U0	No	Yes
910505105983	RC340B 42S/940 SEIA W30L120 VPC DLO U4	-	-
910505105991	RC340B 42S/840 SEIA W30L135 FLC4DLOU4SC	-	-
910925866968	RC340B 36S/940 PSE W60L60 VPC MLO PIP	No	Yes
910925866978	RC340B 36S/940 DEIA W60L60 PCV MLO	No	Yes
910925866981	RC342B 36S/940 DEIA W62L62 VPC MLO	No	Yes
910925867145	RC342B 28S/940 DEIA W62L62 VPC MLO	No	Yes
910925867158	RC342B 28S/940 DEIA W62L62 VPC PCS	No	Yes
910925867159	RC342B 36S/940 DEIA W62L62 VPC PCS	No	Yes
910925867160	RC342B 42S/940 DEIA W62L62 VPC PCS	No	Yes
910925867174	RC342B 28S/940 DEIA W62L62 VPC O	No	Yes
910925867175	RC342B 36S/940 DEIA W62L62 VPC O	No	Yes
910925867176	RC342B 42S/940 DEIA W62L62 VPC O	No	Yes
910505105986	RC342B 28S/940 DEIA W31L125 VPC MXO	-	-

Light Technical

FlexBlend Recessed

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910925867015	RC340B 36S/940 PSE W15L120 VPC MLO	4000 K	>90	95 lm/W	3,600 lm
910925867016	RC340B 36S/940 DEIA W15L120 VPC MLO	4000 K	>90	95 lm/W	3,600 lm
910925867017	RC340B 42S/940 PSE W15L120 VPC MLO	4000 K	>90	93 lm/W	4,200 lm
910925867018	RC340B 42S/940 DEIA W15L120 VPC MLO	4000 K	>90	93 lm/W	4,200 lm
910925867019	RC340B 36S/940 PSU W15L120 VPC MLO ELP3	4000 K	>90	95 lm/W	3,600 lm
910925867020	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	4000 K	>90	95 lm/W	3,600 lm
910925867021	RC340B 42S/940 PSU W15L120 VPC MLO ELP3	4000 K	>90	93 lm/W	4,200 lm
910925867022	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	4000 K	>90	93 lm/W	4,200 lm
910925867024	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	4000 K	>90	95 lm/W	3,600 lm
910925867026	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	4000 K	>90	93 lm/W	4,200 lm
910925867149	RC342B 28S/940 DEIA W15L125 VPC MLO	4000 K	>90	110 lm/W	2,800 lm
910925867150	RC342B 36S/940 DEIA W15L125 VPC MLO	4000 K	>90	95 lm/W	3,600 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910925867153	RC342B 36S/940 DEIA W17L125 PCV MLO	4000 K	>90	95 lm/W	3,600 lm
910925867164	RC342B 28S/940 DEIA W15L125 VPC PCS	4000 K	>90	127 lm/W	2,800 lm
910925867165	RC342B 36S/940 DEIA W15L125 VPC PCS	4000 K	>90	138 lm/W	3,600 lm
910925867166	RC342B 42S/940 DEIA W15L125 VPC PCS	4000 K	>90	138 lm/W	4,200 lm
910925867169	RC342B 36S/940 DEIA W17L125 PCV PCS	4000 K	>90	144 lm/W	3,600 lm
910925867180	RC342B 28S/940 DEIA W15L125 VPC O	4000 K	>90	124 lm/W	2,800 lm
910925867181	RC342B 36S/940 DEIA W15L125 VPC O	4000 K	>90	126 lm/W	3,600 lm
910925867182	RC342B 42S/940 DEIA W15L125 VPC O	4000 K	>90	125 lm/W	4,200 lm
910925866979	RC340B 36S/940 DEIA W30L120 VPC MLO	4000 K	>90	95 lm/W	3,600 lm
910925866982	RC342B 36S/940 PSE W31L125 VPC MLO	4000 K	>90	95 lm/W	3,600 lm
910925866983	RC342B 36S/940 DEIA W31L125 VPC MLO	4000 K	>90	95 lm/W	3,600 lm
910925867030	RC340B 42S/940 DEIA W30L120 VPC MLO W3W2	4000 K	>90	93 lm/W	4,200 lm
910925867031	RC340B 42S/940 DEIA W30L120 CPC MLO W3W2	4000 K	>90	93 lm/W	4,200 lm

FlexBlend Recessed

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910925867032	RC340B 42S/930 DEIA W30L120 VPC MLO W3W2	3000 K	>90	93 lm/W	4,200 lm
910925867033	RC340B 42S/930 DEIA W30L120 CPC MLO W3W2	3000 K	>90	93 lm/W	4,200 lm
910925867038	RC340B 42S/940 DEIA W30L120 VPC PCS W3W2	4000 K	>90	138 lm/W	4,200 lm
910925867039	RC340B 42S/940 DEIA W30L120 CPC PCS W3W2	4000 K	>90	138 lm/W	4,200 lm
910925867042	RC340B 42S/930 DEIA W30L120 VPC PCS W3W2	3000 K	>90	138 lm/W	4,200 lm
910925867147	RC342B 28S/940 DEIA W31L125 VPC MLO	4000 K	>90	110 lm/W	2,800 lm
910925867161	RC342B 28S/940 DEIA W31L125 VPC PCS	4000 K	>90	127 lm/W	2,800 lm
910925867162	RC342B 36S/940 DEIA W31L125 VPC PCS	4000 K	>90	138 lm/W	3,600 lm
910925867163	RC342B 42S/940 DEIA W31L125 VPC PCS	4000 K	>90	138 lm/W	4,200 lm
910925867177	RC342B 28S/940 DEIA W31L125 VPC O	4000 K	>90	124 lm/W	2,800 lm
910925867178	RC342B 36S/940 DEIA W31L125 VPC O	4000 K	>90	126 lm/W	3,600 lm
910925867179	RC342B 42S/940 DEIA W31L125 VPC O	4000 K	>90	125 lm/W	4,200 lm
910925868910	RC340B 36S/930 SRD W60L60 VPC MLO U4	3000 K	>90	95 lm/W	3,600 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910925868911	RC340B 36S/930 SRD W60L60 VPC MLO U4	3000 K	>90	95 lm/W	3,600 lm
910925868912	RC340B 36S/930 SEIA W60L60 VPC PCS U4	3000 K	>90	138 lm/W	3,600 lm
910925868913	RC340B 36S/930 SEIA W60L60 VPC PCS U4 SC	3000 K	>90	138 lm/W	3,600 lm
910925868914	RC340B 36S/940 SEIA W60L60 VPC MLO U4	4000 K	>90	95 lm/W	3,600 lm
910925868915	RC340B 36S/940 SEIA W60L60 VPC MLO U4 SC	4000 K	>90	95 lm/W	3,600 lm
910925868916	RC340B 36S/940 SEIA W60L60 VPC PCS U4	4000 K	>90	138 lm/W	3,600 lm
910925868917	RC340B 36S/940 SEIA W60L60 VPC PCS U4 SC	4000 K	>90	138 lm/W	3,600 lm
910925868918	RC340B 36S/940 SEIA W60L60 VPC PCS U4 W3	4000 K	>90	138 lm/W	3,600 lm
910925868920	RC340B 42S/940 SEIA W60L60 VPC PCS U4 W3	4000 K	>90	140 lm/W	4,200 lm
910925868921	RC342B 28S/940 SEIA W62L62 VPC MLO U4	4000 K	>90	110 lm/W	2,800 lm
910925868922	RC342B 28S/940 SEIA W62L62 VPC PCS U4	4000 K	>90	140 lm/W	2,800 lm
910925868924	RC342B 36S/940 SEIA W62L62 VPC MLO U4	4000 K	>90	95 lm/W	3,600 lm

FlexBlend Recessed

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910925868925	RC342B 36S/940 SEIA W62L62 VPC PCS U4	4000 K	>90	138 lm/W	3,600 lm
910925868927	RC342B 42S/940 SEIA W62L62 VPC MLO U4	4000 K	>90	93 lm/W	4,200 lm
910925868928	RC342B 42S/940 SEIA W62L62 VPC PCS U4	4000 K	>90	140 lm/W	4,200 lm
910505105985	RC340B 36S/940 SEIA W60L60 VPC MXO U4	4000 K	≥80	194 lm/W	3,600 lm
910925866986	RC340B 36S/940 PSU W60L60 VPC O ELP3	4000 K	>90	126 lm/W	3,600 lm
910925866987	RC340B 36S/940 DIA W60L60 VPC O ELP3	4000 K	>90	126 lm/W	3,600 lm
910925867001	RC340B 42S/940 PSE W60L60 VPC O	4000 K	>90	125 lm/W	4,200 lm
910925867002	RC340B 42S/940 DEIA W60L60 VPC O	4000 K	>90	125 lm/W	4,200 lm
910925867006	RC340B 42S/940 PSU W60L60 VPC O ELP3	4000 K	>90	125 lm/W	4,200 lm
910925867007	RC340B 42S/940 DIA W60L60 VPC O ELP3	4000 K	>90	125 lm/W	4,200 lm
910925867012	RC340B 42S/940 DIA W60L60 VPC O ELD3	4000 K	>90	125 lm/W	4,200 lm
910925867061	RC340B 36S/940 PSE W60L60 VPC O SC	4000 K	>90	126 lm/W	3,600 lm
910925867062	RC340B 36S/940 DEIA	4000 K	>90	126 lm/W	3,600 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
	W60L60 VPC O SC				
910925868919	RC340B 42S/940 SEIA W30L120 VPC PCS U4W3	4000 K	>90	140 lm/W	4,200 lm
910925868923	RC342B 36S/940 SEIA W31L125 VPC PCS U4	4000 K	>90	138 lm/W	3,600 lm
910925868926	RC342B 42S/940 SEIA W31L125 VPC PCS U4	4000 K	>90	140 lm/W	4,200 lm
910925866969	RC340B 36S/940 DEIA W60L60 VPC MLO	4000 K	>90	95 lm/W	3,600 lm
910925867023	RC340B 42S/930 DEIA W60L60 CPC MLO W3W2	3000 K	>90	93 lm/W	4,200 lm
910925867028	RC340B 42S/940 DEIA W60L60 CPC MLO W3W2	4000 K	>90	93 lm/W	4,200 lm
910925867036	RC340B 42S/940 DEIA W60L60 CPC PCS W3W2	4000 K	>90	138 lm/W	4,200 lm
910925867040	RC340B 42S/930 DEIA W60L60 CPC PCS W3W2	3000 K	>90	138 lm/W	4,200 lm
910925867046	RC340B 36S/940 PSE W60L60 CPC MLO	4000 K	>90	95 lm/W	3,600 lm
910925867047	RC340B 42S/940 PSE W60L60 CPC MLO	4000 K	>90	93 lm/W	4,200 lm
910925867048	RC340B 42S/940 DEIA W60L60 CPC MLO	4000 K	>90	93 lm/W	4,200 lm
910925867167	RC342B 42S/940 DEIA	4000 K	>90	138 lm/W	4,200 lm

FlexBlend Recessed

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
	W62L62 CPC PCS				
910925867068	RC340B 42S/930 DEIA W30L120 CPC PCS W3W2	3000 K	>90	138 lm/W	4,200 lm
910925866967	RC340B 36S/940 DEIA W60L60 VPC O	4000 K	>90	126 lm/W	3,600 lm
910925866972	RC340B 36S/940 PSE W60L60 VPC PCS	4000 K	>90	138 lm/W	3,600 lm
910925866973	RC340B 36S/940 DEIA W60L60 VPC PCS	4000 K	>90	138 lm/W	3,600 lm
910925866977	RC340B 36S/940 DEIA W60L60 CPC MLO	4000 K	>90	95 lm/W	3,600 lm
910925866990	RC340B 36S/940 PSU W60L60 VPC PCS ELP3	4000 K	>90	138 lm/W	3,600 lm
910925866991	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	4000 K	>90	138 lm/W	3,600 lm
910925866997	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	4000 K	>90	138 lm/W	3,600 lm
910925867003	RC340B 42S/940 PSE W60L60 VPC PCS	4000 K	>90	138 lm/W	4,200 lm
910925867004	RC340B 42S/940 DEIA W60L60 VPC PCS	4000 K	>90	138 lm/W	4,200 lm
910925867008	RC340B 42S/940 PSU W60L60 VPC PCS ELP3	4000 K	>90	138 lm/W	4,200 lm
910925867009	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	4000 K	>90	138 lm/W	4,200 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910925867034	RC340B 42S/930 DEIA W60L60 VPC PCS W3W2	3000 K	>90	138 lm/W	4,200 lm
910925867035	RC340B 42S/940 DEIA W60L60 VPC PCS W3W2	4000 K	>90	138 lm/W	4,200 lm
910925867044	RC340B 36S/940 PSE W60L60 CPC PCS PIP	4000 K	>90	138 lm/W	3,600 lm
910925867045	RC340B 36S/940 DEIA W60L60 CPC PCS	4000 K	>90	138 lm/W	3,600 lm
910925867049	RC340B 42S/940 PSE W60L60 CPC PCS	4000 K	>90	138 lm/W	4,200 lm
910925867050	RC340B 42S/940 DEIA W60L60 CPC PCS	4000 K	>90	138 lm/W	4,200 lm
910925867065	RC340B 36S/940 PSE W60L60 VPC PCS SC	4000 K	>90	138 lm/W	3,600 lm
910925867066	RC340B 36S/940 DEIA W60L60 VPC PCS SC	4000 K	>90	138 lm/W	3,600 lm
910505105982	RC340B 36S/940 SEIA W60L60 VPC DLO U4	4000 K	≥80	157 lm/W	3,600 lm
910505105987	RC340B 42S/840 SEIA W60L60 VPC PCS U4 SC	4000 K	≥90	190 lm/W	4,200 lm
910505105990	RC340B 36S/840 SEIA W67L67 FLC4DLO U4 SC	4000 K	≥90	151 lm/W	3,600 lm
910505105989	RC342B 42S/840 DEIA W62L62 VPC PCS	4000 K	≥90	190 lm/W	4,200 lm

FlexBlend Recessed

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505105984	RC342B 36S/940 DEIA W31L125 VPC DLO	4000 K	≥80	157 lm/W	3,600 lm
910505105988	RC340B 42S/840 PSU W30L120 VPC PCS ELB3	4000 K	≥90	190 lm/W	4,200 lm
910505105992	RC340B 36S/840 DEIA W30L135 FLC2 DLO SC	4000 K	≥90	151 lm/W	3,600 lm
910925866966	RC340B 36S/940 PSE W60L60 VPC O	4000 K	>90	126 lm/W	3,600 lm
910925866980	RC342B 36S/940 PSE W62L62 VPC MLO	4000 K	>90	95 lm/W	3,600 lm
910925866988	RC340B 36S/940 PSU W60L60 VPC MLO ELP3	4000 K	>90	95 lm/W	3,600 lm
910925866989	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	4000 K	>90	95 lm/W	3,600 lm
910925866993	RC340B 36S/940 DIA W60L60 VPC O ELD3	4000 K	>90	126 lm/W	3,600 lm
910925866995	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	4000 K	>90	95 lm/W	3,600 lm
910925866999	RC340B 42S/940 DEIA W60L60 VPC MLO	4000 K	>90	93 lm/W	4,200 lm
910925867010	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	4000 K	>90	93 lm/W	4,200 lm
910925867013	RC340B 42S/930 DEIA W60L60 VPC MLO W3W2	3000 K	>90	93 lm/W	4,200 lm
910925867027	RC340B 42S/940 DEIA	4000 K	>90	93 lm/W	4,200 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
	W60L60 VPC MLO W3W2				
910925867043	RC340B 42S/940 PSE W60L60 VPC MLO	4000 K	>90	93 lm/W	4,200 lm
910925867063	RC340B 36S/940 PSE W60L60 VPC MLO SC	4000 K	>90	95 lm/W	3,600 lm
910925867064	RC340B 36S/940 DEIA W60L60 VPC MLO SC	4000 K	>90	95 lm/W	3,600 lm
910925866970	RC340B 36S/940 POE W60L60 VPC MLO	4000 K	>90	95 lm/W	3,600 lm
910925867014	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	4000 K	>90	138 lm/W	4,200 lm
910925867025	RC340B 42S/930 DEIA W60L60 PCV MLO W3W2	3000 K	>90	93 lm/W	4,200 lm
910925867029	RC340B 42S/940 DEIA W60L60 PCV MLO W3W2	4000 K	>90	93 lm/W	4,200 lm
910925867037	RC340B 42S/940 DEIA W60L60 PCV PCS W3W2	4000 K	>90	138 lm/W	4,200 lm
910925867041	RC340B 42S/930 DEIA W60L60 PCV PCS W3W2	3000 K	>90	138 lm/W	4,200 lm
910925867168	RC340B 36S/940 DEIA W60L60 PCV PCS	4000 K	>90	138 lm/W	3,600 lm
910925867221	RC340B 36S/940 POE W60L60 VPC MLO U0	4000 K	>90	95 lm/W	3,600 lm
910925867224	RC340B 36S/940 POE	4000 K	>90	144 lm/W	3,600 lm

FlexBlend Recessed

Order Code	Full Product Name	Correlated Color	Color rendering index	Luminous Efficacy (rated)	Luminous Flux
		Temperature (Nom)	(CRI)	(Nom)	
	W60L60 VPC PCS U0				
910505105983	RC340B 42S/940 SEIA W30L120 VPC DLO U4	4000 K	≥80	185 lm/W	4,200 lm
910505105991	RC340B 42S/840 SEIA W30L135 FLC4DLOU45C	4000 K	≥90	177 lm/W	4,200 lm
910925866968	RC340B 36S/940 PSE W60L60 VPC MLO PIP	4000 K	>90	95 lm/W	3,600 lm
910925866978	RC340B 36S/940 DEIA W60L60 PCV MLO	4000 K	>90	95 lm/W	3,600 lm
910925866981	RC342B 36S/940 DEIA W62L62 VPC MLO	4000 K	>90	95 lm/W	3,600 lm
910925867145	RC342B 28S/940 DEIA	4000 K	>90	110 lm/W	2,800 lm

Order Code	Full Product Name	Correlated Color	Color rendering index	Luminous Efficacy (rated)	Luminous Flux
		Temperature (Nom)	(CRI)	(Nom)	
	W62L62 VPC MLO				
910925867158	RC342B 28S/940 DEIA W62L62 VPC PCS	4000 K	>90	127 lm/W	2,800 lm
910925867159	RC342B 36S/940 DEIA W62L62 VPC PCS	4000 K	>90	144 lm/W	3,600 lm
910925867160	RC342B 42S/940 DEIA W62L62 VPC PCS	4000 K	>90	138 lm/W	4,200 lm
910925867174	RC342B 28S/940 DEIA W62L62 VPC O	4000 K	>90	124 lm/W	2,800 lm
910925867175	RC342B 36S/940 DEIA W62L62 VPC O	4000 K	>90	126 lm/W	3,600 lm
910925867176	RC342B 42S/940 DEIA W62L62 VPC O	4000 K	>90	125 lm/W	4,200 lm
910505105986	RC342B 28S/940 DEIA W31L125 VPC MXO	4000 K	≥80	149 lm/W	2,800 lm

Operating and Electrical

Order Code	Full Product Name	Protection class IEC	Input Voltage	Power Consumption	Suitable for
					random switching
910925867015	RC340B 36S/940 PSE W15L120 VPC MLO	Safety class I	220 to 240 V	38 W	Yes
910925867016	RC340B 36S/940 DEIA W15L120 VPC MLO	Safety class I	220 to 240 V	38 W	Yes
910925867017	RC340B 42S/940 PSE W15L120 VPC MLO	Safety class I	220 to 240 V	45 W	Yes
910925867018	RC340B 42S/940 DEIA	Safety class I	220 to 240 V	45 W	Yes

Order Code	Full Product Name	Protection class IEC	Input Voltage	Power Consumption	Suitable for
					random switching
	W15L120 VPC MLO				
910925867019	RC340B 36S/940 PSU W15L120 VPC MLO ELP3	Safety class I	220 to 240 V	38 W	Yes
910925867020	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	Safety class I	220 to 240 V	38 W	Yes
910925867021	RC340B 42S/940 PSU W15L120 VPC MLO ELP3	Safety class I	220 to 240 V	45 W	Yes

FlexBlend Recessed

Order Code	Full Product Name	Protection class IEC	Input Voltage	Power Consumption	Suitable for random switching
910925867022	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	Safety class I	220 to 240 V	45 W	Yes
910925867024	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	Safety class I	220 to 240 V	38 W	Yes
910925867026	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	Safety class I	220 to 240 V	45 W	Yes
910925867149	RC342B 28S/940 DEIA W15L125 VPC MLO	Safety class I	220 to 240 V	25.5 W	Yes
910925867150	RC342B 36S/940 DEIA W15L125 VPC MLO	Safety class I	220 to 240 V	38 W	Yes
910925867153	RC342B 36S/940 DEIA W17L125 PCV MLO	Safety class I	220 to 240 V	38 W	Yes
910925867164	RC342B 28S/940 DEIA W15L125 VPC PCS	Safety class I	220 to 240 V	22 W	Yes
910925867165	RC342B 36S/940 DEIA W15L125 VPC PCS	Safety class I	220 to 240 V	26 W	Yes
910925867166	RC342B 42S/940 DEIA W15L125 VPC PCS	Safety class I	220 to 240 V	30.5 W	Yes
910925867169	RC342B 36S/940 DEIA W17L125 PCV PCS	Safety class I	220 to 240 V	25 W	Yes
910925867180	RC342B 28S/940 DEIA W15L125 VPC O	Safety class I	220 to 240 V	22.5 W	Yes
910925867181	RC342B 36S/940 DEIA W15L125 VPC O	Safety class I	220 to 240 V	28.5 W	Yes

Order Code	Full Product Name	Protection class IEC	Input Voltage	Power Consumption	Suitable for random switching
910925867182	RC342B 42S/940 DEIA W15L125 VPC O	Safety class I	220 to 240 V	33.5 W	Yes
910925866979	RC340B 36S/940 DEIA W30L120 VPC MLO	Safety class I	220 to 240 V	38 W	Yes
910925866982	RC342B 36S/940 PSE W31L125 VPC MLO	Safety class I	220 to 240 V	37 W	Yes
910925866983	RC342B 36S/940 DEIA W31L125 VPC MLO	Safety class I	220 to 240 V	38 W	Yes
910925867030	RC340B 42S/940 DEIA W30L120 VPC MLO W3W2	Safety class I	220 to 240 V	45 W	Yes
910925867031	RC340B 42S/940 DEIA W30L120 CPC MLO W3W2	Safety class I	220 to 240 V	45 W	Yes
910925867032	RC340B 42S/930 DEIA W30L120 VPC MLO W3W2	Safety class I	220 to 240 V	45 W	Yes
910925867033	RC340B 42S/930 DEIA W30L120 CPC MLO W3W2	Safety class I	220 to 240 V	45 W	Yes
910925867038	RC340B 42S/940 DEIA W30L120 VPC PCS W3W2	Safety class I	220 to 240 V	30.5 W	Yes
910925867039	RC340B 42S/940 DEIA W30L120 CPC PCS W3W2	Safety class I	220 to 240 V	30.5 W	Yes
910925867042	RC340B 42S/930 DEIA W30L120 VPC PCS W3W2	Safety class I	220 to 240 V	30.5 W	Yes
910925867147	RC342B 28S/940 DEIA W31L125 VPC MLO	Safety class I	220 to 240 V	25.5 W	Yes

FlexBlend Recessed

Order Code	Full Product Name	Protection class IEC	Input Voltage	Power Consumption	Suitable for random switching
910925867161	RC342B 28S/940 DEIA W31L125 VPC PCS	Safety class I	220 to 240 V	22 W	Yes
910925867162	RC342B 36S/940 DEIA W31L125 VPC PCS	Safety class I	220 to 240 V	26 W	Yes
910925867163	RC342B 42S/940 DEIA W31L125 VPC PCS	Safety class I	220 to 240 V	30.5 W	Yes
910925867177	RC342B 28S/940 DEIA W31L125 VPC O	Safety class I	220 to 240 V	22.5 W	Yes
910925867178	RC342B 36S/940 DEIA W31L125 VPC O	Safety class I	220 to 240 V	28.5 W	Yes
910925867179	RC342B 42S/940 DEIA W31L125 VPC O	Safety class I	220 to 240 V	33.5 W	Yes
910925868910	RC340B 36S/930 SRD W60L60 VPC MLO U4	Safety class I	220 to 240 V	38 W	No
910925868911	RC340B 36S/930 SRD W60L60 VPC MLO U4	Safety class I	220 to 240 V	38 W	No
910925868912	RC340B 36S/930 SEIA W60L60 VPC PCS U4	Safety class I	220 to 240 V	26 W	No
910925868913	RC340B 36S/930 SEIA W60L60 VPC PCS U4 SC	Safety class I	220 to 240 V	26 W	No
910925868914	RC340B 36S/940 SEIA W60L60 VPC MLO U4	Safety class I	220 to 240 V	37 W	No
910925868915	RC340B 36S/940 SEIA W60L60 VPC MLO U4 SC	Safety class I	220 to 240 V	37 W	No

Order Code	Full Product Name	Protection class IEC	Input Voltage	Power Consumption	Suitable for random switching
910925868916	RC340B 36S/940 SEIA W60L60 VPC PCS U4	Safety class I	220 to 240 V	26 W	No
910925868917	RC340B 36S/940 SEIA W60L60 VPC PCS U4 SC	Safety class I	220 to 240 V	26 W	No
910925868918	RC340B 36S/940 SEIA W60L60 VPC PCS U4 W3	Safety class I	220 to 240 V	26 W	No
910925868920	RC340B 42S/940 SEIA W60L60 VPC PCS U4 W3	Safety class I	220 to 240 V	30 W	No
910925868921	RC342B 28S/940 SEIA W62L62 VPC MLO U4	Safety class I	220 to 240 V	25.5 W	No
910925868922	RC342B 28S/940 SEIA W62L62 VPC PCS U4	Safety class I	220 to 240 V	20 W	No
910925868924	RC342B 36S/940 SEIA W62L62 VPC MLO U4	Safety class I	220 to 240 V	37 W	No
910925868925	RC342B 36S/940 SEIA W62L62 VPC PCS U4	Safety class I	220 to 240 V	25 W	No
910925868927	RC342B 42S/940 SEIA W62L62 VPC MLO U4	Safety class I	220 to 240 V	45 W	No
910925868928	RC342B 42S/940 SEIA W62L62 VPC PCS U4	Safety class I	220 to 240 V	30 W	No
910505105985	RC340B 36S/940 SEIA W60L60 VPC MXO U4	Safety class I	220-240 V	26 W	Yes
910925866986	RC340B 36S/940 PSU W60L60 VPC O ELP3	Safety class I	220 to 240 V	28.5 W	Yes

FlexBlend Recessed

Order Code	Full Product Name	Protection class IEC	Input Voltage	Power Consumption	Suitable for random switching
910925866987	RC340B 36S/940 DIA W60L60 VPC O ELP3	Safety class I	220 to 240 V	28.5 W	Yes
910925867001	RC340B 42S/940 PSE W60L60 VPC O	Safety class I	220 to 240 V	33.5 W	Yes
910925867002	RC340B 42S/940 DEIA W60L60 VPC O	Safety class I	220 to 240 V	33.5 W	Yes
910925867006	RC340B 42S/940 PSU W60L60 VPC O ELP3	Safety class I	220 to 240 V	33.5 W	Yes
910925867007	RC340B 42S/940 DIA W60L60 VPC O ELP3	Safety class I	220 to 240 V	33.5 W	Yes
910925867012	RC340B 42S/940 DIA W60L60 VPC O ELD3	Safety class I	220 to 240 V	33.5 W	Yes
910925867061	RC340B 36S/940 PSE W60L60 VPC O SC	Safety class I	220 to 240 V	28.5 W	Yes
910925867062	RC340B 36S/940 DEIA W60L60 VPC O SC	Safety class I	220 to 240 V	28.5 W	Yes
910925868919	RC340B 42S/940 SEIA W30L120 VPC PCS U4W3	Safety class I	220 to 240 V	30 W	No
910925868923	RC342B 36S/940 SEIA W31L125 VPC PCS U4	Safety class I	220 to 240 V	24 W	No
910925868926	RC342B 42S/940 SEIA W31L125 VPC PCS U4	Safety class I	220 to 240 V	30 W	No
910925866969	RC340B 36S/940 DEIA W60L60 VPC MLO	Safety class I	220 to 240 V	38 W	Yes

Order Code	Full Product Name	Protection class IEC	Input Voltage	Power Consumption	Suitable for random switching
910925867023	RC340B 42S/930 DEIA W60L60 CPC MLO W3W2	Safety class I	220 to 240 V	45 W	Yes
910925867028	RC340B 42S/940 DEIA W60L60 CPC MLO W3W2	Safety class I	220 to 240 V	45 W	Yes
910925867036	RC340B 42S/940 DEIA W60L60 CPC PCS W3W2	Safety class I	220 to 240 V	30.5 W	Yes
910925867040	RC340B 42S/930 DEIA W60L60 CPC PCS W3W2	Safety class I	220 to 240 V	30.5 W	Yes
910925867046	RC340B 36S/940 PSE W60L60 CPC MLO	Safety class I	220 to 240 V	38 W	Yes
910925867047	RC340B 42S/940 PSE W60L60 CPC MLO	Safety class I	220 to 240 V	45 W	Yes
910925867048	RC340B 42S/940 DEIA W60L60 CPC MLO	Safety class I	220 to 240 V	45 W	Yes
910925867167	RC342B 42S/940 DEIA W62L62 CPC PCS	Safety class I	220 to 240 V	30.5 W	Yes
910925867068	RC340B 42S/930 DEIA W30L120 CPC PCS W3W2	Safety class I	220 to 240 V	30.5 W	Yes
910925866967	RC340B 36S/940 DEIA W60L60 VPC O	Safety class I	220 to 240 V	28.5 W	Yes
910925866972	RC340B 36S/940 PSE W60L60 VPC PCS	Safety class I	220 to 240 V	26 W	Yes
910925866973	RC340B 36S/940 DEIA W60L60 VPC PCS	Safety class I	220 to 240 V	26 W	Yes

FlexBlend Recessed

Order Code	Full Product Name	Protection class IEC	Input Voltage	Power Consumption	Suitable for random switching
910925866977	RC340B 36S/940 DEIA W60L60 CPC MLO	Safety class I	220 to 240 V	38 W	Yes
910925866990	RC340B 36S/940 PSU W60L60 VPC PCS ELP3	Safety class I	220 to 240 V	26 W	Yes
910925866991	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	Safety class I	220 to 240 V	26 W	Yes
910925866997	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	Safety class I	220 to 240 V	26 W	Yes
910925867003	RC340B 42S/940 PSE W60L60 VPC PCS	Safety class I	220 to 240 V	30.5 W	Yes
910925867004	RC340B 42S/940 DEIA W60L60 VPC PCS	Safety class I	220 to 240 V	30.5 W	Yes
910925867008	RC340B 42S/940 PSU W60L60 VPC PCS ELP3	Safety class I	220 to 240 V	30.5 W	Yes
910925867009	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	Safety class I	220 to 240 V	30.5 W	Yes
910925867034	RC340B 42S/930 DEIA W60L60 VPC PCS W3W2	Safety class I	220 to 240 V	30.5 W	Yes
910925867035	RC340B 42S/940 DEIA W60L60 VPC PCS W3W2	Safety class I	220 to 240 V	30.5 W	Yes
910925867044	RC340B 36S/940 PSE W60L60 CPC PCS PIP	Safety class I	220 to 240 V	26 W	Yes
910925867045	RC340B 36S/940 DEIA W60L60 CPC PCS	Safety class I	220 to 240 V	26 W	Yes

Order Code	Full Product Name	Protection class IEC	Input Voltage	Power Consumption	Suitable for random switching
910925867049	RC340B 42S/940 PSE W60L60 CPC PCS	Safety class I	220 to 240 V	30.5 W	Yes
910925867050	RC340B 42S/940 DEIA W60L60 CPC PCS	Safety class I	220 to 240 V	30.5 W	Yes
910925867065	RC340B 36S/940 PSE W60L60 VPC PCS SC	Safety class I	220 to 240 V	26 W	Yes
910925867066	RC340B 36S/940 DEIA W60L60 VPC PCS SC	Safety class I	220 to 240 V	26 W	Yes
910505105982	RC340B 36S/940 SEIA W60L60 VPC DLO U4	Safety class I	220-240 V	21 W	Yes
910505105987	RC340B 42S/840 SEIA W60L60 VPC PCS U4 SC	Safety class I	220-240 V	25.5 W	No
910505105990	RC340B 36S/840 SEIA W67L67 FLC4DLO U4 SC	Safety class I	220-240 V	20 W	Yes
910505105989	RC342B 42S/840 DEIA W62L62 VPC PCS	Safety class I	220-240 V	25.5 W	No
910505105984	RC342B 36S/940 DEIA W31L125 VPC DLO	Safety class I	220-240 V	21 W	No
910505105988	RC340B 42S/840 PSU W30L120 VPC PCS ELB3	Safety class I	220-240 V	25.5 W	No
910505105992	RC340B 36S/840 DEIA W30L135 FLC2 DLO SC	Safety class I	220-240 V	20 W	No
910925866966	RC340B 36S/940 PSE W60L60 VPC O	Safety class I	220 to 240 V	28.5 W	Yes

FlexBlend Recessed

Order Code	Full Product Name	Protection class IEC	Input Voltage	Power Consumption	Suitable for random switching
910925866980	RC342B 36S/940 PSE W62L62 VPC MLO	Safety class I	220 to 240 V	37 W	Yes
910925866988	RC340B 36S/940 PSU W60L60 VPC MLO ELP3	Safety class I	220 to 240 V	38 W	Yes
910925866989	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	Safety class I	220 to 240 V	38 W	Yes
910925866993	RC340B 36S/940 DIA W60L60 VPC O ELD3	Safety class I	220 to 240 V	28.5 W	Yes
910925866995	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	Safety class I	220 to 240 V	38 W	Yes
910925866999	RC340B 42S/940 DEIA W60L60 VPC MLO	Safety class I	220 to 240 V	45 W	Yes
910925867010	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	Safety class I	220 to 240 V	45 W	Yes
910925867013	RC340B 42S/930 DEIA W60L60 VPC MLO W3W2	Safety class I	220 to 240 V	45 W	Yes
910925867027	RC340B 42S/940 DEIA W60L60 VPC MLO W3W2	Safety class I	220 to 240 V	45 W	Yes
910925867043	RC340B 42S/940 PSE W60L60 VPC MLO	Safety class I	220 to 240 V	45 W	Yes
910925867063	RC340B 36S/940 PSE W60L60 VPC MLO SC	Safety class I	220 to 240 V	38 W	Yes
910925867064	RC340B 36S/940 DEIA W60L60 VPC MLO SC	Safety class I	220 to 240 V	38 W	Yes

Order Code	Full Product Name	Protection class IEC	Input Voltage	Power Consumption	Suitable for random switching
910925866970	RC340B 36S/940 POE W60L60 VPC MLO	Safety class I	220 to 240 V	37 W	Yes
910925867014	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	Safety class I	220 to 240 V	30.5 W	Yes
910925867025	RC340B 42S/930 DEIA W60L60 PCV MLO W3W2	Safety class I	220 to 240 V	45 W	Yes
910925867029	RC340B 42S/940 DEIA W60L60 PCV MLO W3W2	Safety class I	220 to 240 V	45 W	Yes
910925867037	RC340B 42S/940 DEIA W60L60 PCV PCS W3W2	Safety class I	220 to 240 V	30.5 W	Yes
910925867041	RC340B 42S/930 DEIA W60L60 PCV PCS W3W2	Safety class I	220 to 240 V	30.5 W	Yes
910925867168	RC340B 36S/940 DEIA W60L60 PCV PCS	Safety class I	220 to 240 V	26 W	Yes
910925867221	RC340B 36S/940 POE W60L60 VPC MLO U0	Safety class III	220 to 240 V	37 W	Yes (relates to presence/movement detection and daylight harvesting)
910925867224	RC340B 36S/940 POE W60L60 VPC PCS U0	Safety class III	220 to 240 V	25 W	Yes (relates to presence/movement detection and daylight harvesting)

FlexBlend Recessed

Order Code	Full Product Name	Protection class IEC	Input Voltage	Power Consumption	Suitable for random switching
910505105983	RC340B 42S/940 SEIA W30L120 VPC DLO U4	Safety class I	220-240 V	24.5 W	Yes
910505105991	RC340B 42S/840 SEIA W30L135 FLC4DLOU4SC	Safety class I	220-240 V	23.5 W	Yes
910925866968	RC340B 36S/940 PSE W60L60 VPC MLO PIP	Safety class I	220 to 240 V	38 W	Yes
910925866978	RC340B 36S/940 DEIA W60L60 PCV MLO	Safety class I	220 to 240 V	38 W	Yes
910925866981	RC342B 36S/940 DEIA W62L62 VPC MLO	Safety class I	220 to 240 V	38 W	Yes
910925867145	RC342B 28S/940 DEIA W62L62 VPC MLO	Safety class I	220 to 240 V	25.5 W	Yes
910925867158	RC342B 28S/940 DEIA W62L62 VPC PCS	Safety class I	220 to 240 V	22 W	Yes

Order Code	Full Product Name	Protection class IEC	Input Voltage	Power Consumption	Suitable for random switching
910925867159	RC342B 36S/940 DEIA W62L62 VPC PCS	Safety class I	220 to 240 V	25 W	Yes
910925867160	RC342B 42S/940 DEIA W62L62 VPC PCS	Safety class I	220 to 240 V	30.5 W	Yes
910925867174	RC342B 28S/940 DEIA W62L62 VPC O	Safety class I	220 to 240 V	22.5 W	Yes
910925867175	RC342B 36S/940 DEIA W62L62 VPC O	Safety class I	220 to 240 V	28.5 W	Yes
910925867176	RC342B 42S/940 DEIA W62L62 VPC O	Safety class I	220 to 240 V	33.5 W	Yes
910505105986	RC342B 28S/940 DEIA W31L125 VPC MXO	Safety class I	220-240 V	20 W	No

Controls and Dimming

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910925867015	RC340B 36S/940 PSE W15L120 VPC MLO	No	-	1%
910925867016	RC340B 36S/940 DEIA W15L120 VPC MLO	Yes	-	1%
910925867017	RC340B 42S/940 PSE W15L120 VPC MLO	No	-	1%
910925867018	RC340B 42S/940 DEIA W15L120 VPC MLO	Yes	-	1%
910925867019	RC340B 36S/940 PSU W15L120 VPC MLO ELP3	No	-	1%
910925867020	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	Yes	-	1%
910925867021	RC340B 42S/940 PSU W15L120 VPC MLO ELP3	No	-	1%
910925867022	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	Yes	-	1%

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910925867024	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	Yes	-	1%
910925867026	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	Yes	-	1%
910925867149	RC342B 28S/940 DEIA W15L125 VPC MLO	Yes	-	1%
910925867150	RC342B 36S/940 DEIA W15L125 VPC MLO	Yes	-	1%
910925867153	RC342B 36S/940 DEIA W17L125 PCV MLO	Yes	-	1%
910925867164	RC342B 28S/940 DEIA W15L125 VPC PCS	Yes	-	1%
910925867165	RC342B 36S/940 DEIA W15L125 VPC PCS	Yes	-	1%
910925867166	RC342B 42S/940 DEIA W15L125 VPC PCS	Yes	-	1%

FlexBlend Recessed

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910925867169	RC342B 36S/940 DEIA W17L125 PCV PCS	Yes	-	1%
910925867180	RC342B 28S/940 DEIA W15L125 VPC O	Yes	-	1%
910925867181	RC342B 36S/940 DEIA W15L125 VPC O	Yes	-	1%
910925867182	RC342B 42S/940 DEIA W15L125 VPC O	Yes	-	1%
910925866979	RC340B 36S/940 DEIA W30L120 VPC MLO	Yes	-	1%
910925866982	RC342B 36S/940 PSE W31L125 VPC MLO	No	-	1%
910925866983	RC342B 36S/940 DEIA W31L125 VPC MLO	Yes	-	1%
910925867030	RC340B 42S/940 DEIA W30L120 VPC MLO W3W2	Yes	-	1%
910925867031	RC340B 42S/940 DEIA W30L120 CPC MLO W3W2	Yes	-	1%
910925867032	RC340B 42S/930 DEIA W30L120 VPC MLO W3W2	Yes	-	1%
910925867033	RC340B 42S/930 DEIA W30L120 CPC MLO W3W2	Yes	-	1%
910925867038	RC340B 42S/940 DEIA W30L120 VPC PCS W3W2	Yes	-	1%
910925867039	RC340B 42S/940 DEIA W30L120 CPC PCS W3W2	Yes	-	1%
910925867042	RC340B 42S/930 DEIA W30L120 VPC PCS W3W2	Yes	-	1%
910925867147	RC342B 28S/940 DEIA W31L125 VPC MLO	Yes	-	1%
910925867161	RC342B 28S/940 DEIA W31L125 VPC PCS	Yes	-	1%
910925867162	RC342B 36S/940 DEIA W31L125 VPC PCS	Yes	-	1%
910925867163	RC342B 42S/940 DEIA W31L125 VPC PCS	Yes	-	1%
910925867177	RC342B 28S/940 DEIA W31L125 VPC O	Yes	-	1%
910925867178	RC342B 36S/940 DEIA W31L125 VPC O	Yes	-	1%
910925867179	RC342B 42S/940 DEIA W31L125 VPC O	Yes	-	1%
910925868910	RC340B 36S/930 SRD W60L60 VPC MLO U4	No	Upgradable sensor slot with SNS210 sensor	1%
910925868911	RC340B 36S/930 SRD W60L60 VPC MLO U4	No	Upgradable sensor slot with SNS210 sensor	1%
910925868912	RC340B 36S/930 SEIA W60L60 VPC PCS U4	No	Upgradable sensor slot with SNS210 sensor	1%

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910925868913	RC340B 36S/930 SEIA W60L60 VPC PCS U4 SC	No	Upgradable sensor slot with SNS210 sensor	1%
910925868914	RC340B 36S/940 SEIA W60L60 VPC MLO U4	No	Upgradable sensor slot with SNS210 sensor	1%
910925868915	RC340B 36S/940 SEIA W60L60 VPC MLO U4 SC	No	Upgradable sensor slot with SNS210 sensor	1%
910925868916	RC340B 36S/940 SEIA W60L60 VPC PCS U4	No	Upgradable sensor slot with SNS210 sensor	1%
910925868917	RC340B 36S/940 SEIA W60L60 VPC PCS U4 SC	No	Upgradable sensor slot with SNS210 sensor	1%
910925868918	RC340B 36S/940 SEIA W60L60 VPC PCS U4 W3	No	Upgradable sensor slot with SNS210 sensor	1%
910925868920	RC340B 42S/940 SEIA W60L60 VPC PCS U4 W3	No	Upgradable sensor slot with SNS210 sensor	1%
910925868921	RC342B 28S/940 SEIA W62L62 VPC MLO U4	No	Upgradable sensor slot with SNS210 sensor	1%
910925868922	RC342B 28S/940 SEIA W62L62 VPC PCS U4	No	Upgradable sensor slot with SNS210 sensor	1%
910925868924	RC342B 36S/940 SEIA W62L62 VPC MLO U4	No	Upgradable sensor slot with SNS210 sensor	1%
910925868925	RC342B 36S/940 SEIA W62L62 VPC PCS U4	No	Upgradable sensor slot with SNS210 sensor	1%
910925868927	RC342B 42S/940 SEIA W62L62 VPC MLO U4	No	Upgradable sensor slot with SNS210 sensor	1%
910925868928	RC342B 42S/940 SEIA W62L62 VPC PCS U4	No	Upgradable sensor slot with SNS210 sensor	1%
910505105985	RC340B 36S/940 SEIA W60L60 VPC MXO U4	No	Interact SC200 sensor	-
910925866986	RC340B 36S/940 PSU W60L60 VPC O ELP3	No	-	1%
910925866987	RC340B 36S/940 DIA W60L60 VPC O ELP3	Yes	-	1%
910925867001	RC340B 42S/940 PSE W60L60 VPC O	No	-	1%
910925867002	RC340B 42S/940 DEIA W60L60 VPC O	Yes	-	1%
910925867006	RC340B 42S/940 PSU W60L60 VPC O ELP3	No	-	1%

FlexBlend Recessed

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910925867007	RC340B 42S/940 DIA W60L60 VPC O ELP3	Yes	-	1%
910925867012	RC340B 42S/940 DIA W60L60 VPC O ELD3	Yes	-	1%
910925867061	RC340B 36S/940 PSE W60L60 VPC O SC	No	-	1%
910925867062	RC340B 36S/940 DEIA W60L60 VPC O SC	Yes	-	1%
910925868919	RC340B 42S/940 SEIA W30L120 VPC PCS U4W3	No	Upgradable sensor slot with SNS210 sensor	1%
910925868923	RC342B 36S/940 SEIA W31L125 VPC PCS U4	No	Upgradable sensor slot with SNS210 sensor	1%
910925868926	RC342B 42S/940 SEIA W31L125 VPC PCS U4	No	Upgradable sensor slot with SNS210 sensor	1%
910925866969	RC340B 36S/940 DEIA W60L60 VPC MLO	Yes	-	1%
910925867023	RC340B 42S/930 DEIA W60L60 CPC MLO W3W2	Yes	-	1%
910925867028	RC340B 42S/940 DEIA W60L60 CPC MLO W3W2	Yes	-	1%
910925867036	RC340B 42S/940 DEIA W60L60 CPC PCS W3W2	Yes	-	1%
910925867040	RC340B 42S/930 DEIA W60L60 CPC PCS W3W2	Yes	-	1%
910925867046	RC340B 36S/940 PSE W60L60 CPC MLO	No	-	1%
910925867047	RC340B 42S/940 PSE W60L60 CPC MLO	No	-	1%
910925867048	RC340B 42S/940 DEIA W60L60 CPC MLO	Yes	-	1%
910925867167	RC342B 42S/940 DEIA W62L62 CPC PCS	Yes	-	1%
910925867068	RC340B 42S/930 DEIA W30L120 CPC PCS W3W2	Yes	-	1%
910925866967	RC340B 36S/940 DEIA W60L60 VPC O	Yes	-	1%
910925866972	RC340B 36S/940 PSE W60L60 VPC PCS	No	-	1%
910925866973	RC340B 36S/940 DEIA W60L60 VPC PCS	Yes	-	1%
910925866977	RC340B 36S/940 DEIA W60L60 CPC MLO	Yes	-	1%
910925866990	RC340B 36S/940 PSU W60L60 VPC PCS ELP3	No	-	1%
910925866991	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	Yes	-	1%
910925866997	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	Yes	-	1%

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910925867003	RC340B 42S/940 PSE W60L60 VPC PCS	No	-	1%
910925867004	RC340B 42S/940 DEIA W60L60 VPC PCS	Yes	-	1%
910925867008	RC340B 42S/940 PSU W60L60 VPC PCS ELP3	No	-	1%
910925867009	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	Yes	-	1%
910925867034	RC340B 42S/930 DEIA W60L60 VPC PCS W3W2	Yes	-	1%
910925867035	RC340B 42S/940 DEIA W60L60 VPC PCS W3W2	Yes	-	1%
910925867044	RC340B 36S/940 PSE W60L60 CPC PCS PIP	No	-	1%
910925867045	RC340B 36S/940 DEIA W60L60 CPC PCS	Yes	-	1%
910925867049	RC340B 42S/940 PSE W60L60 CPC PCS	No	-	1%
910925867050	RC340B 42S/940 DEIA W60L60 CPC PCS	Yes	-	1%
910925867065	RC340B 36S/940 PSE W60L60 VPC PCS SC	No	-	1%
910925867066	RC340B 36S/940 DEIA W60L60 VPC PCS SC	Yes	-	1%
910505105982	RC340B 36S/940 SEIA W60L60 VPC DLO U4	No	Interact SC200 sensor	-
910505105987	RC340B 42S/840 SEIA W60L60 VPC PCS U4 SC	No	Interact SC200 sensor	-
910505105990	RC340B 36S/840 SEIA W67L67 FLC4DLO U4 SC	No	Interact SC200 sensor	-
910505105989	RC342B 42S/840 DEIA W62L62 VPC PCS	Yes	-	-
910505105984	RC342B 36S/940 DEIA W31L125 VPC DLO	Yes	-	-
910505105988	RC340B 42S/840 PSU W30L120 VPC PCS ELB3	No	-	-
910505105992	RC340B 36S/840 DEIA W30L135 FLC2 DLO SC	No	-	-
910925866966	RC340B 36S/940 PSE W60L60 VPC O	No	-	1%
910925866980	RC342B 36S/940 PSE W62L62 VPC MLO	No	-	1%
910925866988	RC340B 36S/940 PSU W60L60 VPC MLO ELP3	No	-	1%
910925866989	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	Yes	-	1%
910925866993	RC340B 36S/940 DIA W60L60 VPC O ELD3	Yes	-	1%
910925866995	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	Yes	-	1%

FlexBlend Recessed

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910925866999	RC340B 42S/940 DEIA W60L60 VPC MLO	Yes	-	1%
910925867010	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	Yes	-	1%
910925867013	RC340B 42S/930 DEIA W60L60 VPC MLO W3W2	Yes	-	1%
910925867027	RC340B 42S/940 DEIA W60L60 VPC MLO W3W2	Yes	-	1%
910925867043	RC340B 42S/940 PSE W60L60 VPC MLO	No	-	1%
910925867063	RC340B 36S/940 PSE W60L60 VPC MLO SC	No	-	1%
910925867064	RC340B 36S/940 DEIA W60L60 VPC MLO SC	Yes	-	1%
910925866970	RC340B 36S/940 POE W60L60 VPC MLO	No	-	1%
910925867014	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	Yes	-	1%
910925867025	RC340B 42S/930 DEIA W60L60 PCV MLO W3W2	Yes	-	1%
910925867029	RC340B 42S/940 DEIA W60L60 PCV MLO W3W2	Yes	-	1%
910925867037	RC340B 42S/940 DEIA W60L60 PCV PCS W3W2	Yes	-	1%
910925867041	RC340B 42S/930 DEIA W60L60 PCV PCS W3W2	Yes	-	1%
910925867168	RC340B 36S/940 DEIA W60L60 PCV PCS	Yes	-	1%
910925867221	RC340B 36S/940 POE W60L60 VPC MLO U0	No	Upgradable sensor slot	1%

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
			empty with cover	
910925867224	RC340B 36S/940 POE W60L60 VPC PCS U0	No	Upgradable sensor slot	1%
			empty with cover	
910505105983	RC340B 42S/940 SEIA W30L120 VPC DLO U4	No	Interact SC200 sensor	-
910505105991	RC340B 42S/840 SEIA W30L135 FLC4DLOU4SC	No	Interact SC200 sensor	-
910925866968	RC340B 36S/940 PSE W60L60 VPC MLO PIP	No	-	1%
910925866978	RC340B 36S/940 DEIA W60L60 PCV MLO	Yes	-	1%
910925866981	RC342B 36S/940 DEIA W62L62 VPC MLO	Yes	-	1%
910925867145	RC342B 28S/940 DEIA W62L62 VPC MLO	Yes	-	1%
910925867158	RC342B 28S/940 DEIA W62L62 VPC PCS	Yes	-	1%
910925867159	RC342B 36S/940 DEIA W62L62 VPC PCS	Yes	-	1%
910925867160	RC342B 42S/940 DEIA W62L62 VPC PCS	Yes	-	1%
910925867174	RC342B 28S/940 DEIA W62L62 VPC O	Yes	-	1%
910925867175	RC342B 36S/940 DEIA W62L62 VPC O	Yes	-	1%
910925867176	RC342B 42S/940 DEIA W62L62 VPC O	Yes	-	1%
910505105986	RC342B 28S/940 DEIA W31L125 VPC MXO	Yes	-	-

Mechanical and Housing

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
910925867015	RC340B 36S/940 PSE W15L120 VPC MLO	IK02	IP20/40
910925867016	RC340B 36S/940 DEIA W15L120 VPC MLO	IK02	IP20/40
910925867017	RC340B 42S/940 PSE W15L120 VPC MLO	IK02	IP20/40
910925867018	RC340B 42S/940 DEIA W15L120 VPC MLO	IK02	IP20/40
910925867019	RC340B 36S/940 PSU W15L120 VPC MLO ELP3	IK02	IP20
910925867020	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	IK02	IP20

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
910925867021	RC340B 42S/940 PSU W15L120 VPC MLO ELP3	IK02	IP20
910925867022	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	IK02	IP20
910925867024	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	IK02	IP20
910925867026	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	IK02	IP20
910925867149	RC342B 28S/940 DEIA W15L125 VPC MLO	IK02	IP20/40
910925867150	RC342B 36S/940 DEIA W15L125 VPC MLO	IK02	IP20/40

FlexBlend Recessed

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
910925867153	RC342B 36S/940 DEIA W17L125 PCV MLO	IK02	IP20/40
910925867164	RC342B 28S/940 DEIA W15L125 VPC PCS	IK02	IP20/54
910925867165	RC342B 36S/940 DEIA W15L125 VPC PCS	IK02	IP20/54
910925867166	RC342B 42S/940 DEIA W15L125 VPC PCS	IK02	IP20/54
910925867169	RC342B 36S/940 DEIA W17L125 PCV PCS	IK02	IP20/54
910925867180	RC342B 28S/940 DEIA W15L125 VPC O	IK02	IP20/54
910925867181	RC342B 36S/940 DEIA W15L125 VPC O	IK02	IP20/54
910925867182	RC342B 42S/940 DEIA W15L125 VPC O	IK02	IP20/54
910925866979	RC340B 36S/940 DEIA W30L120 VPC MLO	IK02	IP20/40
910925866982	RC342B 36S/940 PSE W31L125 VPC MLO	IK02	IP20/40
910925866983	RC342B 36S/940 DEIA W31L125 VPC MLO	IK02	IP20/40
910925867030	RC340B 42S/940 DEIA W30L120 VPC MLO W3W2	IK02	IP20/40
910925867031	RC340B 42S/940 DEIA W30L120 CPC MLO W3W2	IK02	IP20/40
910925867032	RC340B 42S/930 DEIA W30L120 VPC MLO W3W2	IK02	IP20/40
910925867033	RC340B 42S/930 DEIA W30L120 CPC MLO W3W2	IK02	IP20/40
910925867038	RC340B 42S/940 DEIA W30L120 VPC PCS W3W2	IK02	IP20/54
910925867039	RC340B 42S/940 DEIA W30L120 CPC PCS W3W2	IK02	IP20/54
910925867042	RC340B 42S/930 DEIA W30L120 VPC PCS W3W2	IK02	IP20/54
910925867147	RC342B 28S/940 DEIA W31L125 VPC MLO	IK02	IP20/40
910925867161	RC342B 28S/940 DEIA W31L125 VPC PCS	IK02	IP20/54
910925867162	RC342B 36S/940 DEIA W31L125 VPC PCS	IK02	IP20/54
910925867163	RC342B 42S/940 DEIA W31L125 VPC PCS	IK02	IP20/54
910925867177	RC342B 28S/940 DEIA W31L125 VPC O	IK02	IP20/54
910925867178	RC342B 36S/940 DEIA W31L125 VPC O	IK02	IP20/54
910925867179	RC342B 42S/940 DEIA W31L125 VPC O	IK02	IP20/54
910925868910	RC340B 36S/930 SRD W60L60 VPC MLO U4	IK02	IP20
910925868911	RC340B 36S/930 SRD W60L60 VPC MLO U4	IK02	IP20
910925868912	RC340B 36S/930 SEIA W60L60 VPC PCS U4	IK02	IP20/54

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
910925868913	RC340B 36S/930 SEIA W60L60 VPC PCS U4 SC	IK02	IP20/54
910925868914	RC340B 36S/940 SEIA W60L60 VPC MLO U4	IK02	IP20
910925868915	RC340B 36S/940 SEIA W60L60 VPC MLO U4 SC	IK02	IP20
910925868916	RC340B 36S/940 SEIA W60L60 VPC PCS U4	IK02	IP20/54
910925868917	RC340B 36S/940 SEIA W60L60 VPC PCS U4 SC	IK02	IP20/54
910925868918	RC340B 36S/940 SEIA W60L60 VPC PCS U4 W3	IK02	IP20/54
910925868920	RC340B 42S/940 SEIA W60L60 VPC PCS U4 W3	IK02	IP20/54
910925868921	RC342B 28S/940 SEIA W62L62 VPC MLO U4	IK02	IP20
910925868922	RC342B 28S/940 SEIA W62L62 VPC PCS U4	IK02	IP20/54
910925868924	RC342B 36S/940 SEIA W62L62 VPC MLO U4	IK02	IP20
910925868925	RC342B 36S/940 SEIA W62L62 VPC PCS U4	IK02	IP20/54
910925868927	RC342B 42S/940 SEIA W62L62 VPC MLO U4	IK02	IP20
910925868928	RC342B 42S/940 SEIA W62L62 VPC PCS U4	IK02	IP20/54
910505105985	RC340B 36S/940 SEIA W60L60 VPC MXO U4	IK03	IP20
910925866986	RC340B 36S/940 PSU W60L60 VPC O ELP3	IK02	IP54
910925866987	RC340B 36S/940 DIA W60L60 VPC O ELP3	IK02	IP54
910925867001	RC340B 42S/940 PSE W60L60 VPC O	IK02	IP20/54
910925867002	RC340B 42S/940 DEIA W60L60 VPC O	IK02	IP20/54
910925867006	RC340B 42S/940 PSU W60L60 VPC O ELP3	IK02	IP20/54
910925867007	RC340B 42S/940 DIA W60L60 VPC O ELP3	IK02	IP20/54
910925867012	RC340B 42S/940 DIA W60L60 VPC O ELD3	IK02	IP54
910925867061	RC340B 36S/940 PSE W60L60 VPC O SC	IK02	IP20/54
910925867062	RC340B 36S/940 DEIA W60L60 VPC O SC	IK02	IP20/54
910925868919	RC340B 42S/940 SEIA W30L120 VPC PCS U4W3	IK02	IP20/54
910925868923	RC342B 36S/940 SEIA W31L125 VPC PCS U4	IK02	IP20/54

FlexBlend Recessed

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
910925868926	RC342B 42S/940 SEIA W31L125 VPC PCS U4	IK02	IP20/54
910925866969	RC340B 36S/940 DEIA W60L60 VPC MLO	IK02	IP20/40
910925867023	RC340B 42S/930 DEIA W60L60 CPC MLO W3W2	IK02	IP20/40
910925867028	RC340B 42S/940 DEIA W60L60 CPC MLO W3W2	IK02	IP20/40
910925867036	RC340B 42S/940 DEIA W60L60 CPC PCS W3W2	IK02	IP20/54
910925867040	RC340B 42S/930 DEIA W60L60 CPC PCS W3W2	IK02	IP20/54
910925867046	RC340B 36S/940 PSE W60L60 CPC MLO	IK02	IP20/40
910925867047	RC340B 42S/940 PSE W60L60 CPC MLO	IK02	IP20/40
910925867048	RC340B 42S/940 DEIA W60L60 CPC MLO	IK02	IP20/40
910925867167	RC342B 42S/940 DEIA W62L62 CPC PCS	IK02	IP20/54
910925867068	RC340B 42S/930 DEIA W30L120 CPC PCS W3W2	IK02	IP20/54
910925866967	RC340B 36S/940 DEIA W60L60 VPC O	IK02	IP20/54
910925866972	RC340B 36S/940 PSE W60L60 VPC PCS	IK02	IP20/54
910925866973	RC340B 36S/940 DEIA W60L60 VPC PCS	IK02	IP20/54
910925866977	RC340B 36S/940 DEIA W60L60 CPC MLO	IK02	IP20/40
910925866990	RC340B 36S/940 PSU W60L60 VPC PCS ELP3	IK02	IP20/54
910925866991	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	IK02	IP20/54
910925866997	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	IK02	IP20/54
910925867003	RC340B 42S/940 PSE W60L60 VPC PCS	IK02	IP20/54
910925867004	RC340B 42S/940 DEIA W60L60 VPC PCS	IK02	IP20/54
910925867008	RC340B 42S/940 PSU W60L60 VPC PCS ELP3	IK02	IP20/54
910925867009	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	IK02	IP20/54
910925867034	RC340B 42S/930 DEIA W60L60 VPC PCS W3W2	IK02	IP20/54
910925867035	RC340B 42S/940 DEIA W60L60 VPC PCS W3W2	IK02	IP20/54
910925867044	RC340B 36S/940 PSE W60L60 CPC PCS PIP	IK02	IP20/54

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
910925867045	RC340B 36S/940 DEIA W60L60 CPC PCS	IK02	IP20/54
910925867049	RC340B 42S/940 PSE W60L60 CPC PCS	IK02	IP20/54
910925867050	RC340B 42S/940 DEIA W60L60 CPC PCS	IK02	IP20/54
910925867065	RC340B 36S/940 PSE W60L60 VPC PCS SC	IK02	IP20/54
910925867066	RC340B 36S/940 DEIA W60L60 VPC PCS SC	IK02	IP20/54
910505105982	RC340B 36S/940 SEIA W60L60 VPC DLO U4	IK03	IP20
910505105987	RC340B 42S/840 SEIA W60L60 VPC PCS U4 SC	IK03	IP20(front IP40)
910505105990	RC340B 36S/840 SEIA W67L67 FLC4DLO U4 SC	IK03	IP20
910505105989	RC342B 42S/840 DEIA W62L62 VPC PCS	IK03	IP20(front IP40)
910505105984	RC342B 36S/940 DEIA W31L125 VPC DLO	IK03	IP20
910505105988	RC340B 42S/840 PSU W30L120 VPC PCS ELB3	IK03	IP20(front IP40)
910505105992	RC340B 36S/840 DEIA W30L135 FLC2 DLO SC	IK03	IP20
910925866966	RC340B 36S/940 PSE W60L60 VPC O	IK02	IP20/54
910925866980	RC342B 36S/940 PSE W62L62 VPC MLO	IK02	IP20/40
910925866988	RC340B 36S/940 PSU W60L60 VPC MLO ELP3	IK02	IP20
910925866989	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	IK02	IP20/54
910925866993	RC340B 36S/940 DIA W60L60 VPC O ELD3	IK02	IP54
910925866995	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	IK02	IP20/54
910925866999	RC340B 42S/940 DEIA W60L60 VPC MLO	IK02	IP20/40
910925867010	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	IK02	IP20
910925867013	RC340B 42S/930 DEIA W60L60 VPC MLO W3W2	IK02	IP20/40
910925867027	RC340B 42S/940 DEIA W60L60 VPC MLO W3W2	IK02	IP20/40
910925867043	RC340B 42S/940 PSE W60L60 VPC MLO	IK02	IP20/40
910925867063	RC340B 36S/940 PSE W60L60 VPC MLO SC	IK02	IP20/40
910925867064	RC340B 36S/940 DEIA W60L60 VPC MLO SC	IK02	IP20/40

FlexBlend Recessed

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
910925866970	RC340B 36S/940 POE W60L60 VPC MLO	IK02	IP20/40
910925867014	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	IK02	IP20/54
910925867025	RC340B 42S/930 DEIA W60L60 PCV MLO W3W2	IK02	IP20/40
910925867029	RC340B 42S/940 DEIA W60L60 PCV MLO W3W2	IK02	IP20/40
910925867037	RC340B 42S/940 DEIA W60L60 PCV PCS W3W2	IK02	IP20/54
910925867041	RC340B 42S/930 DEIA W60L60 PCV PCS W3W2	IK02	IP20/54
910925867168	RC340B 36S/940 DEIA W60L60 PCV PCS	IK02	IP20/54
910925867221	RC340B 36S/940 POE W60L60 VPC MLO U0	IK02	IP20
910925867224	RC340B 36S/940 POE W60L60 VPC PCS U0	IK02	IP20/54
910505105983	RC340B 42S/940 SEIA W30L120 VPC DLO U4	IK03	IP20
910505105991	RC340B 42S/840 SEIA W30L135 FLC4DLOU4SC	IK03	IP20

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
910925866968	RC340B 36S/940 PSE W60L60 VPC MLO PIP	IK02	IP20/40
910925866978	RC340B 36S/940 DEIA W60L60 PCV MLO	IK02	IP20/40
910925866981	RC342B 36S/940 DEIA W62L62 VPC MLO	IK02	IP20/40
910925867145	RC342B 28S/940 DEIA W62L62 VPC MLO	IK02	IP20/40
910925867158	RC342B 28S/940 DEIA W62L62 VPC PCS	IK02	IP20/54
910925867159	RC342B 36S/940 DEIA W62L62 VPC PCS	IK02	IP20/54
910925867160	RC342B 42S/940 DEIA W62L62 VPC PCS	IK02	IP20/54
910925867174	RC342B 28S/940 DEIA W62L62 VPC O	IK02	IP20/54
910925867175	RC342B 36S/940 DEIA W62L62 VPC O	IK02	IP20/54
910925867176	RC342B 42S/940 DEIA W62L62 VPC O	IK02	IP20/54
910505105986	RC342B 28S/940 DEIA W31L125 VPC MXO	IK03	IP20

Emergency Operation

Order Code	Full Product Name	Central Emergency	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910925867015	RC340B 36S/940 PSE W15L120 VPC MLO	-	-	-
910925867016	RC340B 36S/940 DEIA W15L120 VPC MLO	Yes	DC operated central emergency lighting	-
910925867017	RC340B 42S/940 PSE W15L120 VPC MLO	-	-	-
910925867018	RC340B 42S/940 DEIA W15L120 VPC MLO	Yes	DC operated central emergency lighting	-
910925867019	RC340B 36S/940 PSU W15L120 VPC MLO ELP3	No	Emergency lighting 3 hours duration Pro version	3 hour(s)

Order Code	Full Product Name	Central Emergency	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910925867020	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	No	Emergency lighting 3 hours duration Pro version	3 hour(s)
910925867021	RC340B 42S/940 PSU W15L120 VPC MLO ELP3	No	Emergency lighting 3 hours duration Pro version	3 hour(s)
910925867022	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	No	Emergency lighting 3 hours duration Pro version	3 hour(s)
910925867024	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	No	Emergency lighting 3 hours duration Pro version	3 hour(s)

FlexBlend Recessed

Order Code	Full Product Name	Central Emergency	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910925867026	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	No	Emergency lighting 3 hours duration Pro version	3 hour(s)
910925867149	RC342B 28S/940 DEIA W15L125 VPC MLO	Yes	DC operated central emergency lighting	-
910925867150	RC342B 36S/940 DEIA W15L125 VPC MLO	Yes	DC operated central emergency lighting	-
910925867153	RC342B 36S/940 DEIA W17L125 PCV MLO	Yes	DC operated central emergency lighting	-
910925867164	RC342B 28S/940 DEIA W15L125 VPC PCS	Yes	DC operated central emergency lighting	-
910925867165	RC342B 36S/940 DEIA W15L125 VPC PCS	Yes	DC operated central emergency lighting	-
910925867166	RC342B 42S/940 DEIA W15L125 VPC PCS	Yes	DC operated central emergency lighting	-
910925867169	RC342B 36S/940 DEIA W17L125 PCV PCS	Yes	DC operated central emergency lighting	-
910925867180	RC342B 28S/940 DEIA W15L125 VPC O	Yes	DC operated central emergency lighting	-
910925867181	RC342B 36S/940 DEIA W15L125 VPC O	Yes	DC operated central emergency lighting	-
910925867182	RC342B 42S/940 DEIA W15L125 VPC O	Yes	DC operated central emergency lighting	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910925866979	RC340B 36S/940 DEIA W30L120 VPC MLO	Yes	DC operated central emergency lighting	-
910925866982	RC342B 36S/940 PSE W31L125 VPC MLO	-	-	-
910925866983	RC342B 36S/940 DEIA W31L125 VPC MLO	Yes	DC operated central emergency lighting	-
910925867030	RC340B 42S/940 DEIA W30L120 VPC MLO W3W2	Yes	DC operated central emergency lighting	-
910925867031	RC340B 42S/940 DEIA W30L120 CPC MLO W3W2	Yes	DC operated central emergency lighting	-
910925867032	RC340B 42S/930 DEIA W30L120 VPC MLO W3W2	Yes	DC operated central emergency lighting	-
910925867033	RC340B 42S/930 DEIA W30L120 CPC MLO W3W2	Yes	DC operated central emergency lighting	-
910925867038	RC340B 42S/940 DEIA W30L120 VPC PCS W3W2	Yes	DC operated central emergency lighting	-
910925867039	RC340B 42S/940 DEIA W30L120 CPC PCS W3W2	Yes	DC operated central emergency lighting	-
910925867042	RC340B 42S/930 DEIA W30L120 VPC PCS W3W2	Yes	DC operated central emergency lighting	-
910925867147	RC342B 28S/940 DEIA W31L125 VPC MLO	Yes	DC operated central emergency lighting	-
910925867161	RC342B 28S/940 DEIA W31L125 VPC PCS	Yes	DC operated central emergency lighting	-

FlexBlend Recessed

Order Code	Full Product Name	Central Emergency	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910925867162	RC342B 36S/940 DEIA W31L125 VPC PCS	Yes	DC operated central emergency lighting	-
910925867163	RC342B 42S/940 DEIA W31L125 VPC PCS	Yes	DC operated central emergency lighting	-
910925867177	RC342B 28S/940 DEIA W31L125 VPC O	Yes	DC operated central emergency lighting	-
910925867178	RC342B 36S/940 DEIA W31L125 VPC O	Yes	DC operated central emergency lighting	-
910925867179	RC342B 42S/940 DEIA W31L125 VPC O	Yes	DC operated central emergency lighting	-
910925868910	RC340B 36S/930 SRD W60L60 VPC MLO U4	-	-	-
910925868911	RC340B 36S/930 SRD W60L60 VPC MLO U4	-	-	-
910925868912	RC340B 36S/930 SEIA W60L60 VPC PCS U4	-	-	-
910925868913	RC340B 36S/930 SEIA W60L60 VPC PCS U4 SC	-	-	-
910925868914	RC340B 36S/940 SEIA W60L60 VPC MLO U4	-	-	-
910925868915	RC340B 36S/940 SEIA W60L60 VPC MLO U4 SC	-	-	-
910925868916	RC340B 36S/940 SEIA W60L60 VPC PCS U4	-	-	-
910925868917	RC340B 36S/940 SEIA W60L60 VPC PCS U4 SC	-	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910925868918	RC340B 36S/940 SEIA W60L60 VPC PCS U4 W3	-	-	-
910925868920	RC340B 42S/940 SEIA W60L60 VPC PCS U4 W3	-	-	-
910925868921	RC342B 28S/940 SEIA W62L62 VPC MLO U4	-	-	-
910925868922	RC342B 28S/940 SEIA W62L62 VPC PCS U4	-	-	-
910925868924	RC342B 36S/940 SEIA W62L62 VPC MLO U4	-	-	-
910925868925	RC342B 36S/940 SEIA W62L62 VPC PCS U4	-	-	-
910925868927	RC342B 42S/940 SEIA W62L62 VPC MLO U4	-	-	-
910925868928	RC342B 42S/940 SEIA W62L62 VPC PCS U4	-	-	-
910505105985	RC340B 36S/940 SEIA W60L60 VPC MXO U4	Yes	DC operated central emergency lighting	-
910925866986	RC340B 36S/940 PSU W60L60 VPC O ELP3	No	Emergency lighting 3 hours duration Pro version	3 hour(s)
910925866987	RC340B 36S/940 DIA W60L60 VPC O ELP3	No	Emergency lighting 3 hours duration Pro version	3 hour(s)
910925867001	RC340B 42S/940 PSE W60L60 VPC O	-	-	-
910925867002	RC340B 42S/940 DEIA W60L60 VPC O	Yes	DC operated central emergency lighting	-
910925867006	RC340B 42S/940 PSU W60L60 VPC O ELP3	No	Emergency lighting 3 hours duration Pro version	3 hour(s)

FlexBlend Recessed

Order Code	Full Product Name	Central Emergency	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910925867007	RC340B 42S/940 DIA W60L60 VPC O ELP3	No	Emergency lighting 3 hours duration Pro version	3 hour(s)
910925867012	RC340B 42S/940 DIA W60L60 VPC O ELD3	No	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
910925867061	RC340B 36S/940 PSE W60L60 VPC O SC	-	-	-
910925867062	RC340B 36S/940 DEIA W60L60 VPC O SC	Yes	DC operated central emergency lighting	-
910925868919	RC340B 42S/940 SEIA W30L120 VPC PCS U4W3	-	-	-
910925868923	RC342B 36S/940 SEIA W31L125 VPC PCS U4	-	-	-
910925868926	RC342B 42S/940 SEIA W31L125 VPC PCS U4	-	-	-
910925866969	RC340B 36S/940 DEIA W60L60 VPC MLO	Yes	DC operated central emergency lighting	-
910925867023	RC340B 42S/930 DEIA W60L60 CPC MLO W3W2	Yes	DC operated central emergency lighting	-
910925867028	RC340B 42S/940 DEIA W60L60 CPC MLO W3W2	Yes	DC operated central emergency lighting	-
910925867036	RC340B 42S/940 DEIA W60L60 CPC PCS W3W2	Yes	DC operated central emergency lighting	-
910925867040	RC340B 42S/930 DEIA W60L60 CPC PCS W3W2	Yes	DC operated central emergency lighting	-
910925867046	RC340B 36S/940 PSE W60L60 CPC MLO	-	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910925867047	RC340B 42S/940 PSE W60L60 CPC MLO	-	-	-
910925867048	RC340B 42S/940 DEIA W60L60 CPC MLO	Yes	DC operated central emergency lighting	-
910925867167	RC342B 42S/940 DEIA W62L62 CPC PCS	Yes	DC operated central emergency lighting	-
910925867068	RC340B 42S/930 DEIA W30L120 CPC PCS W3W2	Yes	DC operated central emergency lighting	-
910925866967	RC340B 36S/940 DEIA W60L60 VPC O	Yes	DC operated central emergency lighting	-
910925866972	RC340B 36S/940 PSE W60L60 VPC PCS	-	-	-
910925866973	RC340B 36S/940 DEIA W60L60 VPC PCS	Yes	DC operated central emergency lighting	-
910925866977	RC340B 36S/940 DEIA W60L60 CPC MLO	Yes	DC operated central emergency lighting	-
910925866990	RC340B 36S/940 PSU W60L60 VPC PCS ELP3	No	Emergency lighting 3 hours duration Pro version	3 hour(s)
910925866991	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	No	Emergency lighting 3 hours duration Pro version	3 hour(s)
910925866997	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	No	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
910925867003	RC340B 42S/940 PSE W60L60 VPC PCS	-	-	-
910925867004	RC340B 42S/940 DEIA W60L60 VPC PCS	Yes	DC operated central emergency lighting	-

FlexBlend Recessed

Order Code	Full Product Name	Central Emergency	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910925867008	RC340B 42S/940 PSU W60L60 VPC PCS ELP3	No	Emergency lighting 3 hours duration Pro version	3 hour(s)
910925867009	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	No	Emergency lighting 3 hours duration Pro version	3 hour(s)
910925867034	RC340B 42S/930 DEIA W60L60 VPC PCS W3W2	Yes	DC operated central emergency lighting	-
910925867035	RC340B 42S/940 DEIA W60L60 VPC PCS W3W2	Yes	DC operated central emergency lighting	-
910925867044	RC340B 36S/940 PSE W60L60 CPC PCS PIP	-	-	-
910925867045	RC340B 36S/940 DEIA W60L60 CPC PCS	Yes	DC operated central emergency lighting	-
910925867049	RC340B 42S/940 PSE W60L60 CPC PCS	-	-	-
910925867050	RC340B 42S/940 DEIA W60L60 CPC PCS	Yes	DC operated central emergency lighting	-
910925867065	RC340B 36S/940 PSE W60L60 VPC PCS SC	-	-	-
910925867066	RC340B 36S/940 DEIA W60L60 VPC PCS SC	Yes	DC operated central emergency lighting	-
910505105982	RC340B 36S/940 SEIA W60L60 VPC DLO U4	Yes	DC operated central emergency lighting	-
910505105987	RC340B 42S/840 SEIA W60L60 VPC PCS U4 SC	Yes	DC operated central emergency lighting	-
910505105990	RC340B 36S/840 SEIA W67L67 FLC4DLO U4 SC	Yes	DC operated central emergency lighting	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910505105989	RC342B 42S/840 DEIA W62L62 VPC PCS	Yes	DC operated central emergency lighting	-
910505105984	RC342B 36S/940 DEIA W31L125 VPC DLO	Yes	DC operated central emergency lighting	-
910505105988	RC340B 42S/840 PSU W30L120 VPC PCS ELB3	No	Emergency lighting 3 hours duration basic version	-
910505105992	RC340B 36S/840 DEIA W30L135 FLC2 DLO SC	Yes	DC operated central emergency lighting	-
910925866966	RC340B 36S/940 PSE W60L60 VPC O	-	-	-
910925866980	RC342B 36S/940 PSE W62L62 VPC MLO	-	-	-
910925866988	RC340B 36S/940 PSU W60L60 VPC MLO ELP3	No	Emergency lighting 3 hours duration Pro version	3 hour(s)
910925866989	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	No	Emergency lighting 3 hours duration Pro version	3 hour(s)
910925866993	RC340B 36S/940 DIA W60L60 VPC O ELD3	No	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
910925866995	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	No	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
910925866999	RC340B 42S/940 DEIA W60L60 VPC MLO	Yes	DC operated central emergency lighting	-
910925867010	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	No	Emergency lighting 3 hours duration with DALI interface	3 hour(s)

FlexBlend Recessed

Order Code	Full Product Name	Central Emergency	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910925867013	RC340B 42S/930 DEIA W60L60 VPC MLO W3W2	Yes	DC operated central emergency lighting	-
910925867027	RC340B 42S/940 DEIA W60L60 VPC MLO W3W2	Yes	DC operated central emergency lighting	-
910925867043	RC340B 42S/940 PSE W60L60 VPC MLO	-	-	-
910925867063	RC340B 36S/940 PSE W60L60 VPC MLO SC	-	-	-
910925867064	RC340B 36S/940 DEIA W60L60 VPC MLO SC	Yes	DC operated central emergency lighting	-
910925866970	RC340B 36S/940 POE W60L60 VPC MLO	-	-	-
910925867014	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	No	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
910925867025	RC340B 42S/930 DEIA W60L60 PCV MLO W3W2	Yes	DC operated central emergency lighting	-
910925867029	RC340B 42S/940 DEIA W60L60 PCV MLO W3W2	Yes	DC operated central emergency lighting	-
910925867037	RC340B 42S/940 DEIA W60L60 PCV PCS W3W2	Yes	DC operated central emergency lighting	-
910925867041	RC340B 42S/930 DEIA W60L60 PCV PCS W3W2	Yes	DC operated central emergency lighting	-
910925867168	RC340B 36S/940 DEIA W60L60 PCV PCS	Yes	DC operated central emergency lighting	-
910925867221	RC340B 36S/940 POE W60L60 VPC MLO UO	-	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910925867224	RC340B 36S/940 POE W60L60 VPC PCS UO	-	-	-
910505105983	RC340B 42S/940 SEIA W30L120 VPC DLO U4	Yes	DC operated central emergency lighting	-
910505105991	RC340B 42S/840 SEIA W30L135 FLC4DLOU4SC	Yes	DC operated central emergency lighting	-
910925866968	RC340B 36S/940 PSE W60L60 VPC MLO PIP	-	-	-
910925866978	RC340B 36S/940 DEIA W60L60 PCV MLO	Yes	DC operated central emergency lighting	-
910925866981	RC342B 36S/940 DEIA W62L62 VPC MLO	Yes	DC operated central emergency lighting	-
910925867145	RC342B 28S/940 DEIA W62L62 VPC MLO	Yes	DC operated central emergency lighting	-
910925867158	RC342B 28S/940 DEIA W62L62 VPC PCS	Yes	DC operated central emergency lighting	-
910925867159	RC342B 36S/940 DEIA W62L62 VPC PCS	Yes	DC operated central emergency lighting	-
910925867160	RC342B 42S/940 DEIA W62L62 VPC PCS	Yes	DC operated central emergency lighting	-
910925867174	RC342B 28S/940 DEIA W62L62 VPC O	Yes	DC operated central emergency lighting	-
910925867175	RC342B 36S/940 DEIA W62L62 VPC O	Yes	DC operated central emergency lighting	-

FlexBlend Recessed

Order Code	Full Product Name	Central Emergency	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910925867176	RC342B 42S/940 DEIA W62L62 VPC O	Yes	DC operated central emergency lighting	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910505105986	RC342B 28S/940 DEIA W31L125 VPC MXO	Yes	DC operated central emergency lighting	-

Approval and Application

Order Code	Full Product Name	Glow-wire test	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
910925867015	RC340B 36S/940 PSE W15L120 VPC MLO	Temperature 650 °C, duration 30 s	1	0.4
910925867016	RC340B 36S/940 DEIA W15L120 VPC MLO	Temperature 650 °C, duration 30 s	1	0.4
910925867017	RC340B 42S/940 PSE W15L120 VPC MLO	Temperature 650 °C, duration 30 s	1	0.4
910925867018	RC340B 42S/940 DEIA W15L120 VPC MLO	Temperature 650 °C, duration 30 s	1	0.4
910925867019	RC340B 36S/940 PSU W15L120 VPC MLO ELP3	Temperature 650 °C, duration 30 s	1	0.4
910925867020	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	Temperature 650 °C, duration 30 s	1	0.4
910925867021	RC340B 42S/940 PSU W15L120 VPC MLO ELP3	Temperature 650 °C, duration 30 s	1	0.4
910925867022	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	Temperature 650 °C, duration 30 s	1	0.4
910925867024	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	Temperature 650 °C, duration 30 s	1	0.4
910925867026	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	Temperature 650 °C, duration 30 s	1	0.4

Order Code	Full Product Name	Glow-wire test	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
910925867149	RC342B 28S/940 DEIA W15L125 VPC MLO	Temperature 650 °C, duration 30 s	1	0.4
910925867150	RC342B 36S/940 DEIA W15L125 VPC MLO	Temperature 650 °C, duration 30 s	1	0.4
910925867153	RC342B 36S/940 DEIA W17L125 PCV MLO	Temperature 650 °C, duration 30 s	1	0.4
910925867164	RC342B 28S/940 DEIA W15L125 VPC PCS	Temperature 850 °C, duration 30 s	1	0.4
910925867165	RC342B 36S/940 DEIA W15L125 VPC PCS	Temperature 850 °C, duration 30 s	1	0.4
910925867166	RC342B 42S/940 DEIA W15L125 VPC PCS	Temperature 850 °C, duration 30 s	1	0.4
910925867169	RC342B 36S/940 DEIA W17L125 PCV PCS	Temperature 850 °C, duration 30 s	1	0.4
910925867180	RC342B 28S/940 DEIA W15L125 VPC O	Temperature 850 °C, duration 30 s	1	0.4
910925867181	RC342B 36S/940 DEIA W15L125 VPC O	Temperature 850 °C, duration 30 s	1	0.4
910925867182	RC342B 42S/940 DEIA W15L125 VPC O	Temperature 850 °C, duration 30 s	1	0.4

FlexBlend Recessed

Order Code	Full Product Name	Glow-wire test	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	
			Stroboscopic effect visibility measure (SVM)	
910925866979	RC340B 36S/940 DEIA W30L120 VPC MLO	Temperature 650 °C, duration 30 s	1	0.4
910925866982	RC342B 36S/940 PSE W31L125 VPC MLO	Temperature 650 °C, duration 30 s	1	0.4
910925866983	RC342B 36S/940 DEIA W31L125 VPC MLO	Temperature 650 °C, duration 30 s	1	0.4
910925867030	RC340B 42S/940 DEIA W30L120 VPC MLO W3W2	Temperature 650 °C, duration 30 s	1	0.4
910925867031	RC340B 42S/940 DEIA W30L120 CPC MLO W3W2	Temperature 650 °C, duration 30 s	1	0.4
910925867032	RC340B 42S/930 DEIA W30L120 VPC MLO W3W2	Temperature 650 °C, duration 30 s	1	0.4
910925867033	RC340B 42S/930 DEIA W30L120 CPC MLO W3W2	Temperature 650 °C, duration 30 s	1	0.4
910925867038	RC340B 42S/940 DEIA W30L120 VPC PCS W3W2	Temperature 850 °C, duration 30 s	1	0.4
910925867039	RC340B 42S/940 DEIA W30L120 CPC PCS W3W2	Temperature 850 °C, duration 30 s	1	0.4
910925867042	RC340B 42S/930 DEIA W30L120 VPC PCS W3W2	Temperature 850 °C, duration 30 s	1	0.4
910925867147	RC342B 28S/940 DEIA W31L125 VPC MLO	Temperature 650 °C, duration 30 s	1	0.4
910925867161	RC342B 28S/940 DEIA W31L125 VPC PCS	Temperature 850 °C, duration 30 s	1	0.4
910925867162	RC342B 36S/940 DEIA W31L125 VPC PCS	Temperature 850 °C, duration 30 s	1	0.4
910925867163	RC342B 42S/940 DEIA W31L125 VPC PCS	Temperature 850 °C, duration 30 s	1	0.4
910925867177	RC342B 28S/940 DEIA W31L125 VPC O	Temperature 850 °C, duration 30 s	1	0.4

Order Code	Full Product Name	Glow-wire test	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	
			Stroboscopic effect visibility measure (SVM)	
910925867178	RC342B 36S/940 DEIA W31L125 VPC O	Temperature 850 °C, duration 30 s	1	0.4
910925867179	RC342B 42S/940 DEIA W31L125 VPC O	Temperature 850 °C, duration 30 s	1	0.4
910925868910	RC340B 36S/930 SRD W60L60 VPC MLO U4	Temperature 650 °C, duration 30 s	1	0.4
910925868911	RC340B 36S/930 SRD W60L60 VPC MLO U4	Temperature 650 °C, duration 30 s	1	0.4
910925868912	RC340B 36S/930 SEIA W60L60 VPC PCS U4	Temperature 850 °C, duration 30 s	1	0.4
910925868913	RC340B 36S/930 SEIA W60L60 VPC PCS U4 SC	Temperature 850 °C, duration 30 s	1	0.4
910925868914	RC340B 36S/940 SEIA W60L60 VPC MLO U4	Temperature 650 °C, duration 30 s	1	0.4
910925868915	RC340B 36S/940 SEIA W60L60 VPC MLO U4 SC	Temperature 650 °C, duration 30 s	1	0.4
910925868916	RC340B 36S/940 SEIA W60L60 VPC PCS U4	Temperature 850 °C, duration 30 s	1	0.4
910925868917	RC340B 36S/940 SEIA W60L60 VPC PCS U4 SC	Temperature 850 °C, duration 30 s	1	0.4
910925868918	RC340B 36S/940 SEIA W60L60 VPC PCS U4 W3	Temperature 850 °C, duration 30 s	1	0.4
910925868920	RC340B 42S/940 SEIA W60L60 VPC PCS U4 W3	Temperature 850 °C, duration 30 s	1	0.4
910925868921	RC342B 28S/940 SEIA W62L62 VPC MLO U4	Temperature 650 °C, duration 30 s	1	0.4
910925868922	RC342B 28S/940 SEIA W62L62 VPC PCS U4	Temperature 850 °C, duration 30 s	1	0.4
910925868924	RC342B 36S/940 SEIA W62L62 VPC MLO U4	Temperature 650 °C, duration 30 s	1	0.4

FlexBlend Recessed

Order Code	Full Product Name	Glow-wire test	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	
			Stroboscopic effect visibility measure (SVM)	
910925868925	RC342B 36S/940 SEIA W62L62 VPC PCS U4	Temperature 850 °C, duration 30 s	1	0.4
910925868927	RC342B 42S/940 SEIA W62L62 VPC MLO U4	Temperature 650 °C, duration 30 s	1	0.4
910925868928	RC342B 42S/940 SEIA W62L62 VPC PCS U4	Temperature 850 °C, duration 30 s	1	0.4
910505105985	RC340B 36S/940 SEIA W60L60 VPC MXO U4	Temperature 650 °C, duration 30 s	-	-
910925866986	RC340B 36S/940 PSU W60L60 VPC O ELP3	Temperature 850 °C, duration 30 s	1	0.4
910925866987	RC340B 36S/940 DIA W60L60 VPC O ELP3	Temperature 850 °C, duration 30 s	1	0.4
910925867001	RC340B 42S/940 PSE W60L60 VPC O	Temperature 850 °C, duration 30 s	1	0.4
910925867002	RC340B 42S/940 DEIA W60L60 VPC O	Temperature 850 °C, duration 30 s	1	0.4
910925867006	RC340B 42S/940 PSU W60L60 VPC O ELP3	Temperature 850 °C, duration 30 s	1	0.4
910925867007	RC340B 42S/940 DIA W60L60 VPC O ELP3	Temperature 850 °C, duration 30 s	1	0.4
910925867012	RC340B 42S/940 DIA W60L60 VPC O ELD3	Temperature 850 °C, duration 30 s	1	0.4
910925867061	RC340B 36S/940 PSE W60L60 VPC O SC	Temperature 850 °C, duration 30 s	1	0.4
910925867062	RC340B 36S/940 DEIA W60L60 VPC O SC	Temperature 850 °C, duration 30 s	1	0.4
910925868919	RC340B 42S/940 SEIA W30L120 VPC PCS U4W3	Temperature 850 °C, duration 30 s	1	0.4
910925868923	RC342B 36S/940 SEIA W31L125 VPC PCS U4	Temperature 850 °C, duration 30 s	1	0.4

Order Code	Full Product Name	Glow-wire test	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	
			Stroboscopic effect visibility measure (SVM)	
910925868926	RC342B 42S/940 SEIA W31L125 VPC PCS U4	Temperature 850 °C, duration 30 s	1	0.4
910925866969	RC340B 36S/940 DEIA W60L60 VPC MLO	Temperature 650 °C, duration 30 s	1	0.4
910925867023	RC340B 42S/930 DEIA W60L60 CPC MLO W3W2	Temperature 650 °C, duration 30 s	1	0.4
910925867028	RC340B 42S/940 DEIA W60L60 CPC MLO W3W2	Temperature 650 °C, duration 30 s	1	0.4
910925867036	RC340B 42S/940 DEIA W60L60 CPC PCS W3W2	Temperature 850 °C, duration 30 s	1	0.4
910925867040	RC340B 42S/930 DEIA W60L60 CPC PCS W3W2	Temperature 850 °C, duration 30 s	1	0.4
910925867046	RC340B 36S/940 PSE W60L60 CPC MLO	Temperature 650 °C, duration 30 s	1	0.4
910925867047	RC340B 42S/940 PSE W60L60 CPC MLO	Temperature 650 °C, duration 30 s	1	0.4
910925867048	RC340B 42S/940 DEIA W60L60 CPC MLO	Temperature 650 °C, duration 30 s	1	0.4
910925867167	RC342B 42S/940 DEIA W62L62 CPC PCS	Temperature 850 °C, duration 30 s	1	0.4
910925867068	RC340B 42S/930 DEIA W30L120 CPC PCS W3W2	Temperature 850 °C, duration 30 s	1	0.4
910925866967	RC340B 36S/940 DEIA W60L60 VPC O	Temperature 850 °C, duration 30 s	1	0.4
910925866972	RC340B 36S/940 PSE W60L60 VPC PCS	Temperature 850 °C, duration 30 s	1	0.4
910925866973	RC340B 36S/940 DEIA W60L60 VPC PCS	Temperature 850 °C, duration 30 s	1	0.4
910925866977	RC340B 36S/940 DEIA W60L60 CPC MLO	Temperature 650 °C, duration 30 s	1	0.4

FlexBlend Recessed

Order Code	Full Product Name	Glow-wire test	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	
			Stroboscopic effect visibility measure (SVM)	
910925866990	RC340B 36S/940 PSU W60L60 VPC PCS ELP3	Temperature 850 °C, duration 30 s	1	0.4
910925866991	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	Temperature 850 °C, duration 30 s	1	0.4
910925866997	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	Temperature 850 °C, duration 30 s	1	0.4
910925867003	RC340B 42S/940 PSE W60L60 VPC PCS	Temperature 850 °C, duration 30 s	1	0.4
910925867004	RC340B 42S/940 DEIA W60L60 VPC PCS	Temperature 850 °C, duration 30 s	1	0.4
910925867008	RC340B 42S/940 PSU W60L60 VPC PCS ELP3	Temperature 850 °C, duration 30 s	1	0.4
910925867009	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	Temperature 850 °C, duration 30 s	1	0.4
910925867034	RC340B 42S/930 DEIA W60L60 VPC PCS W3W2	Temperature 850 °C, duration 30 s	1	0.4
910925867035	RC340B 42S/940 DEIA W60L60 VPC PCS W3W2	Temperature 850 °C, duration 30 s	1	0.4
910925867044	RC340B 36S/940 PSE W60L60 CPC PCS PIP	Temperature 850 °C, duration 30 s	1	0.4
910925867045	RC340B 36S/940 DEIA W60L60 CPC PCS	Temperature 850 °C, duration 30 s	1	0.4
910925867049	RC340B 42S/940 PSE W60L60 CPC PCS	Temperature 850 °C, duration 30 s	1	0.4
910925867050	RC340B 42S/940 DEIA W60L60 CPC PCS	Temperature 850 °C, duration 30 s	1	0.4
910925867065	RC340B 36S/940 PSE W60L60 VPC PCS SC	Temperature 850 °C, duration 30 s	1	0.4
910925867066	RC340B 36S/940 DEIA W60L60 VPC PCS SC	Temperature 850 °C, duration 30 s	1	0.4

Order Code	Full Product Name	Glow-wire test	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	
			Stroboscopic effect visibility measure (SVM)	
910505105982	RC340B 36S/940 SEIA W60L60 VPC DLO U4	Temperature 650 °C, duration 30 s	-	-
910505105987	RC340B 42S/840 SEIA W60L60 VPC PCS U4 SC	Temperature 650 °C, duration 30 s	-	-
910505105990	RC340B 36S/840 SEIA W67L67 FLC4DLO U4 SC	Temperature 650 °C, duration 30 s	-	-
910505105989	RC342B 42S/840 DEIA W62L62 VPC PCS	Temperature 650 °C, duration 30 s	-	-
910505105984	RC342B 36S/940 DEIA W31L125 VPC DLO	Temperature 650 °C, duration 30 s	-	-
910505105988	RC340B 42S/840 PSU W30L120 VPC PCS ELB3	Temperature 650 °C, duration 30 s	-	-
910505105992	RC340B 36S/840 DEIA W30L135 FLC2 DLO SC	Temperature 650 °C, duration 30 s	-	-
910925866966	RC340B 36S/940 PSE W60L60 VPC O	Temperature 850 °C, duration 30 s	1	0.4
910925866980	RC342B 36S/940 PSE W62L62 VPC MLO	Temperature 650 °C, duration 30 s	1	0.4
910925866988	RC340B 36S/940 PSU W60L60 VPC MLO ELP3	Temperature 650 °C, duration 30 s	1	0.4
910925866989	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	Temperature 650 °C, duration 30 s	1	0.4
910925866993	RC340B 36S/940 DIA W60L60 VPC O ELD3	Temperature 850 °C, duration 30 s	1	0.4
910925866995	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	Temperature 650 °C, duration 30 s	1	0.4
910925866999	RC340B 42S/940 DEIA W60L60 VPC MLO	Temperature 650 °C, duration 30 s	1	0.4
910925867010	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	Temperature 650 °C, duration 30 s	1	0.4

FlexBlend Recessed

Order Code	Full Product Name	Glow-wire test	Flickering value (PstLM) - Flickering value as per EN 61000-3-3		Stroboscopic effect visibility measure (SVM)
			1	0.4	
910925867013	RC340B 42S/930 DEIA W60L60 VPC MLO W3W2	Temperature 650 °C, duration 30 s	1	0.4	0.4
910925867027	RC340B 42S/940 DEIA W60L60 VPC MLO W3W2	Temperature 650 °C, duration 30 s	1	0.4	0.4
910925867043	RC340B 42S/940 PSE W60L60 VPC MLO	Temperature 650 °C, duration 30 s	1	0.4	0.4
910925867063	RC340B 36S/940 PSE W60L60 VPC MLO SC	Temperature 650 °C, duration 30 s	1	0.4	0.4
910925867064	RC340B 36S/940 DEIA W60L60 VPC MLO SC	Temperature 650 °C, duration 30 s	1	0.4	0.4
910925866970	RC340B 36S/940 POE W60L60 VPC MLO	Temperature 650 °C, duration 30 s	1	0.4	0.4
910925867014	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	Temperature 850 °C, duration 30 s	1	0.4	0.4
910925867025	RC340B 42S/930 DEIA W60L60 PCV MLO W3W2	Temperature 650 °C, duration 30 s	1	0.4	0.4
910925867029	RC340B 42S/940 DEIA W60L60 PCV MLO W3W2	Temperature 650 °C, duration 30 s	1	0.4	0.4
910925867037	RC340B 42S/940 DEIA W60L60 PCV PCS W3W2	Temperature 850 °C, duration 30 s	1	0.4	0.4
910925867041	RC340B 42S/930 DEIA W60L60 PCV PCS W3W2	Temperature 850 °C, duration 30 s	1	0.4	0.4
910925867168	RC340B 36S/940 DEIA W60L60 PCV PCS	Temperature 850 °C, duration 30 s	1	0.4	0.4
910925867221	RC340B 36S/940 POE W60L60 VPC MLO UO	Temperature 650 °C, duration 30 s	1	0.4	0.4
910925867224	RC340B 36S/940 POE W60L60 VPC PCS UO	Temperature 850 °C, duration 30 s	1	0.4	0.4

Order Code	Full Product Name	Glow-wire test	Flickering value (PstLM) - Flickering value as per EN 61000-3-3		Stroboscopic effect visibility measure (SVM)
			1	0.4	
910505105983	RC340B 42S/940 SEIA W30L120 VPC DLO U4	Temperature 650 °C, duration 30 s	-	-	-
910505105991	RC340B 42S/840 SEIA W30L135 FLC4DLOU4SC	Temperature 650 °C, duration 30 s	-	-	-
910925866968	RC340B 36S/940 PSE W60L60 VPC MLO PIP	Temperature 650 °C, duration 30 s	1	0.4	0.4
910925866978	RC340B 36S/940 DEIA W60L60 PCV MLO	Temperature 650 °C, duration 30 s	1	0.4	0.4
910925866981	RC342B 36S/940 DEIA W62L62 VPC MLO	Temperature 650 °C, duration 30 s	1	0.4	0.4
910925867145	RC342B 28S/940 DEIA W62L62 VPC MLO	Temperature 650 °C, duration 30 s	1	0.4	0.4
910925867158	RC342B 28S/940 DEIA W62L62 VPC PCS	Temperature 850 °C, duration 30 s	1	0.4	0.4
910925867159	RC342B 36S/940 DEIA W62L62 VPC PCS	Temperature 850 °C, duration 30 s	1	0.4	0.4
910925867160	RC342B 42S/940 DEIA W62L62 VPC PCS	Temperature 850 °C, duration 30 s	1	0.4	0.4
910925867174	RC342B 28S/940 DEIA W62L62 VPC O	Temperature 850 °C, duration 30 s	1	0.4	0.4
910925867175	RC342B 36S/940 DEIA W62L62 VPC O	Temperature 850 °C, duration 30 s	1	0.4	0.4
910925867176	RC342B 42S/940 DEIA W62L62 VPC O	Temperature 850 °C, duration 30 s	1	0.4	0.4
910505105986	RC342B 28S/940 DEIA W31L125 VPC MXO	Temperature 650 °C, duration 30 s	-	-	-

Initial Performance (IEC Compliant)

FlexBlend Recessed

Order Code	Full Product Name	Initial chromaticity
910925867015	RC340B 36S/940 PSE W15L120 VPC MLO	(0.38, 0.37) SDCM ≤3
910925867016	RC340B 36S/940 DEIA W15L120 VPC MLO	(0.38, 0.37) SDCM ≤3
910925867017	RC340B 42S/940 PSE W15L120 VPC MLO	(0.38, 0.37) SDCM ≤3
910925867018	RC340B 42S/940 DEIA W15L120 VPC MLO	(0.38, 0.37) SDCM ≤3
910925867019	RC340B 36S/940 PSU W15L120 VPC MLO ELP3	(0.38, 0.37) SDCM ≤3
910925867020	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	(0.38, 0.37) SDCM ≤3
910925867021	RC340B 42S/940 PSU W15L120 VPC MLO ELP3	(0.38, 0.37) SDCM ≤3
910925867022	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	(0.38, 0.37) SDCM ≤3
910925867024	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	(0.38, 0.37) SDCM ≤3
910925867026	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	(0.38, 0.37) SDCM ≤3
910925867149	RC342B 28S/940 DEIA W15L125 VPC MLO	(0.38, 0.37) SDCM ≤3
910925867150	RC342B 36S/940 DEIA W15L125 VPC MLO	(0.38, 0.37) SDCM ≤3
910925867153	RC342B 36S/940 DEIA W17L125 PCV MLO	(0.38, 0.37) SDCM ≤3
910925867164	RC342B 28S/940 DEIA W15L125 VPC PCS	(0.38, 0.37) SDCM ≤3
910925867165	RC342B 36S/940 DEIA W15L125 VPC PCS	(0.38, 0.37) SDCM ≤3
910925867166	RC342B 42S/940 DEIA W15L125 VPC PCS	(0.38, 0.37) SDCM ≤3
910925867169	RC342B 36S/940 DEIA W17L125 PCV PCS	(0.38, 0.37) SDCM ≤3
910925867180	RC342B 28S/940 DEIA W15L125 VPC O	(0.38, 0.37) SDCM ≤3
910925867181	RC342B 36S/940 DEIA W15L125 VPC O	(0.38, 0.37) SDCM ≤3
910925867182	RC342B 42S/940 DEIA W15L125 VPC O	(0.38, 0.37) SDCM ≤3
910925866979	RC340B 36S/940 DEIA W30L120 VPC MLO	(0.38, 0.37) SDCM ≤3
910925866982	RC342B 36S/940 PSE W31L125 VPC MLO	(0.38, 0.37) SDCM ≤3
910925866983	RC342B 36S/940 DEIA W31L125 VPC MLO	(0.38, 0.37) SDCM ≤3
910925867030	RC340B 42S/940 DEIA W30L120 VPC MLO W3W2	(0.38, 0.37) SDCM ≤3
910925867031	RC340B 42S/940 DEIA W30L120 CPC MLO W3W2	(0.38, 0.37) SDCM ≤3
910925867032	RC340B 42S/930 DEIA W30L120 VPC MLO W3W2	(0.38, 0.37) SDCM ≤3
910925867033	RC340B 42S/930 DEIA W30L120 CPC MLO W3W2	(0.38, 0.37) SDCM ≤3
910925867038	RC340B 42S/940 DEIA W30L120 VPC PCS W3W2	(0.38, 0.37) SDCM ≤3
910925867039	RC340B 42S/940 DEIA W30L120 CPC PCS W3W2	(0.38, 0.37) SDCM ≤3
910925867042	RC340B 42S/930 DEIA W30L120 VPC PCS W3W2	(0.38, 0.37) SDCM ≤3
910925867147	RC342B 28S/940 DEIA W31L125 VPC MLO	(0.38, 0.37) SDCM ≤3
910925867161	RC342B 28S/940 DEIA W31L125 VPC PCS	(0.38, 0.37) SDCM ≤3
910925867162	RC342B 36S/940 DEIA W31L125 VPC PCS	(0.38, 0.37) SDCM ≤3
910925867163	RC342B 42S/940 DEIA W31L125 VPC PCS	(0.38, 0.37) SDCM ≤3
910925867177	RC342B 28S/940 DEIA W31L125 VPC O	(0.38, 0.37) SDCM ≤3
910925867178	RC342B 36S/940 DEIA W31L125 VPC O	(0.38, 0.37) SDCM ≤3
910925867179	RC342B 42S/940 DEIA W31L125 VPC O	(0.38, 0.37) SDCM ≤3
910925868910	RC340B 36S/930 SRD W60L60 VPC MLO U4	(0.38, 0.37) SDCM ≤3
910925868911	RC340B 36S/930 SRD W60L60 VPC MLO U4	(0.38, 0.37) SDCM ≤3
910925868912	RC340B 36S/930 SEIA W60L60 VPC PCS U4	(0.38, 0.37) SDCM ≤3
910925868913	RC340B 36S/930 SEIA W60L60 VPC PCS U4 SC	(0.38, 0.37) SDCM ≤3
910925868914	RC340B 36S/940 SEIA W60L60 VPC MLO U4	(0.38, 0.37) SDCM ≤3
910925868915	RC340B 36S/940 SEIA W60L60 VPC MLO U4 SC	(0.38, 0.37) SDCM ≤3
910925868916	RC340B 36S/940 SEIA W60L60 VPC PCS U4	(0.38, 0.37) SDCM ≤3

Order Code	Full Product Name	Initial chromaticity
910925868917	RC340B 36S/940 SEIA W60L60 VPC PCS U4 SC	(0.38, 0.37) SDCM ≤3
910925868918	RC340B 36S/940 SEIA W60L60 VPC PCS U4 W3	(0.38, 0.37) SDCM ≤3
910925868920	RC340B 42S/940 SEIA W60L60 VPC PCS U4 W3	(0.38, 0.37) SDCM ≤3
910925868921	RC342B 28S/940 SEIA W62L62 VPC MLO U4	(0.38, 0.37) SDCM ≤3
910925868922	RC342B 28S/940 SEIA W62L62 VPC PCS U4	(0.38, 0.37) SDCM ≤3
910925868924	RC342B 36S/940 SEIA W62L62 VPC MLO U4	(0.38, 0.37) SDCM ≤3
910925868925	RC342B 36S/940 SEIA W62L62 VPC PCS U4	(0.38, 0.37) SDCM ≤3
910925868927	RC342B 42S/940 SEIA W62L62 VPC MLO U4	(0.38, 0.37) SDCM ≤3
910925868928	RC342B 42S/940 SEIA W62L62 VPC PCS U4	(0.38, 0.37) SDCM ≤3
910505105985	RC340B 36S/940 SEIA W60L60 VPC MXO U4	(0.43, 0.40) SDCM <3
910925866986	RC340B 36S/940 PSU W60L60 VPC O ELP3	(0.38, 0.37) SDCM ≤3
910925866987	RC340B 36S/940 DIA W60L60 VPC O ELP3	(0.38, 0.37) SDCM ≤3
910925867001	RC340B 42S/940 PSE W60L60 VPC O	(0.38, 0.37) SDCM ≤3
910925867002	RC340B 42S/940 DEIA W60L60 VPC O	(0.38, 0.37) SDCM ≤3
910925867006	RC340B 42S/940 PSU W60L60 VPC O ELP3	(0.38, 0.37) SDCM ≤3
910925867007	RC340B 42S/940 DIA W60L60 VPC O ELP3	(0.38, 0.37) SDCM ≤3
910925867012	RC340B 42S/940 DIA W60L60 VPC O ELD3	(0.38, 0.37) SDCM ≤3
910925867061	RC340B 36S/940 PSE W60L60 VPC O SC	(0.38, 0.37) SDCM ≤3
910925867062	RC340B 36S/940 DEIA W60L60 VPC O SC	(0.38, 0.37) SDCM ≤3
910925868919	RC340B 42S/940 SEIA W30L120 VPC PCS U4W3	(0.38, 0.37) SDCM ≤3
910925868923	RC342B 36S/940 SEIA W31L125 VPC PCS U4	(0.38, 0.37) SDCM ≤3
910925868926	RC342B 42S/940 SEIA W31L125 VPC PCS U4	(0.38, 0.37) SDCM ≤3
910925866969	RC340B 36S/940 DEIA W60L60 VPC MLO	(0.38, 0.37) SDCM ≤3
910925867023	RC340B 42S/930 DEIA W60L60 CPC MLO W3W2	(0.38, 0.37) SDCM ≤3
910925867028	RC340B 42S/940 DEIA W60L60 CPC MLO W3W2	(0.38, 0.37) SDCM ≤3
910925867036	RC340B 42S/940 DEIA W60L60 CPC PCS W3W2	(0.38, 0.37) SDCM ≤3
910925867040	RC340B 42S/930 DEIA W60L60 CPC PCS W3W2	(0.38, 0.37) SDCM ≤3
910925867046	RC340B 36S/940 PSE W60L60 CPC MLO	(0.38, 0.37) SDCM ≤3
910925867047	RC340B 42S/940 PSE W60L60 CPC MLO	(0.38, 0.37) SDCM ≤3
910925867048	RC340B 42S/940 DEIA W60L60 CPC MLO	(0.38, 0.37) SDCM ≤3
910925867167	RC342B 42S/940 DEIA W62L62 CPC PCS	(0.38, 0.37) SDCM ≤3
910925867068	RC340B 42S/930 DEIA W30L120 CPC PCS W3W2	(0.38, 0.37) SDCM ≤3
910925866967	RC340B 36S/940 DEIA W60L60 VPC O	(0.38, 0.37) SDCM ≤3
910925866972	RC340B 36S/940 PSE W60L60 VPC PCS	(0.38, 0.37) SDCM ≤3
910925866973	RC340B 36S/940 DEIA W60L60 VPC PCS	(0.38, 0.37) SDCM ≤3
910925866977	RC340B 36S/940 DEIA W60L60 CPC MLO	(0.38, 0.37) SDCM ≤3
910925866990	RC340B 36S/940 PSU W60L60 VPC PCS ELP3	(0.38, 0.37) SDCM ≤3
910925866991	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	(0.38, 0.37) SDCM ≤3
910925866997	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	(0.38, 0.37) SDCM ≤3
910925867003	RC340B 42S/940 PSE W60L60 VPC PCS	(0.38, 0.37) SDCM ≤3
910925867004	RC340B 42S/940 DEIA W60L60 VPC PCS	(0.38, 0.37) SDCM ≤3
910925867008	RC340B 42S/940 PSU W60L60 VPC PCS ELP3	(0.38, 0.37) SDCM ≤3
910925867009	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	(0.38, 0.37) SDCM ≤3
910925867034	RC340B 42S/930 DEIA W60L60 VPC PCS W3W2	(0.38, 0.37) SDCM ≤3

FlexBlend Recessed

Order Code	Full Product Name	Initial chromaticity
910925867035	RC340B 42S/940 DEIA W60L60 VPC PCS W3W2	(0.38, 0.37) SDCM ≤3
910925867044	RC340B 36S/940 PSE W60L60 CPC PCS PIP	(0.38, 0.37) SDCM ≤3
910925867045	RC340B 36S/940 DEIA W60L60 CPC PCS	(0.38, 0.37) SDCM ≤3
910925867049	RC340B 42S/940 PSE W60L60 CPC PCS	(0.38, 0.37) SDCM ≤3
910925867050	RC340B 42S/940 DEIA W60L60 CPC PCS	(0.38, 0.37) SDCM ≤3
910925867065	RC340B 36S/940 PSE W60L60 VPC PCS SC	(0.38, 0.37) SDCM ≤3
910925867066	RC340B 36S/940 DEIA W60L60 VPC PCS SC	(0.38, 0.37) SDCM ≤3
910505105982	RC340B 36S/940 SEIA W60L60 VPC DLO U4	(0.43, 0.40) SDCM <3
910505105987	RC340B 42S/840 SEIA W60L60 VPC PCS U4 SC	(0.43, 0.40) SDCM <3
910505105990	RC340B 36S/840 SEIA W67L67 FLC4DLO U4 SC	(0.43, 0.40) SDCM <3
910505105989	RC342B 42S/840 DEIA W62L62 VPC PCS	(0.43, 0.40) SDCM <3
910505105984	RC342B 36S/940 DEIA W31L125 VPC DLO	(0.43, 0.40) SDCM <3
910505105988	RC340B 42S/840 PSU W30L120 VPC PCS ELB3	(0.43, 0.40) SDCM <3
910505105992	RC340B 36S/840 DEIA W30L135 FLC2 DLO SC	(0.43, 0.40) SDCM <3
910925866966	RC340B 36S/940 PSE W60L60 VPC O	(0.38, 0.37) SDCM ≤3
910925866980	RC342B 36S/940 PSE W62L62 VPC MLO	(0.38, 0.37) SDCM ≤3
910925866988	RC340B 36S/940 PSU W60L60 VPC MLO ELP3	(0.38, 0.37) SDCM ≤3
910925866989	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	(0.38, 0.37) SDCM ≤3
910925866993	RC340B 36S/940 DIA W60L60 VPC O ELD3	(0.38, 0.37) SDCM ≤3
910925866995	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	(0.38, 0.37) SDCM ≤3
910925866999	RC340B 42S/940 DEIA W60L60 VPC MLO	(0.38, 0.37) SDCM ≤3
910925867010	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	(0.38, 0.37) SDCM ≤3
910925867013	RC340B 42S/930 DEIA W60L60 VPC MLO W3W2	(0.38, 0.37) SDCM ≤3
910925867027	RC340B 42S/940 DEIA W60L60 VPC MLO W3W2	(0.38, 0.37) SDCM ≤3
910925867043	RC340B 42S/940 PSE W60L60 VPC MLO	(0.38, 0.37) SDCM ≤3

Order Code	Full Product Name	Initial chromaticity
910925867063	RC340B 36S/940 PSE W60L60 VPC MLO SC	(0.38, 0.37) SDCM ≤3
910925867064	RC340B 36S/940 DEIA W60L60 VPC MLO SC	(0.38, 0.37) SDCM ≤3
910925866970	RC340B 36S/940 POE W60L60 VPC MLO	(0.38, 0.37) SDCM ≤3
910925867014	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	(0.38, 0.37) SDCM ≤3
910925867025	RC340B 42S/930 DEIA W60L60 PCV MLO W3W2	(0.38, 0.37) SDCM ≤3
910925867029	RC340B 42S/940 DEIA W60L60 PCV MLO W3W2	(0.38, 0.37) SDCM ≤3
910925867037	RC340B 42S/940 DEIA W60L60 PCV PCS W3W2	(0.38, 0.37) SDCM ≤3
910925867041	RC340B 42S/930 DEIA W60L60 PCV PCS W3W2	(0.38, 0.37) SDCM ≤3
910925867168	RC340B 36S/940 DEIA W60L60 PCV PCS	(0.38, 0.37) SDCM ≤3
910925867221	RC340B 36S/940 POE W60L60 VPC MLO U0	(0.38, 0.37) SDCM ≤3
910925867224	RC340B 36S/940 POE W60L60 VPC PCS U0	(0.38, 0.37) SDCM ≤3
910505105983	RC340B 42S/940 SEIA W30L120 VPC DLO U4	(0.43, 0.40) SDCM <3
910505105991	RC340B 42S/840 SEIA W30L135 FLC4DLOU4SC	(0.43, 0.40) SDCM <3
910925866968	RC340B 36S/940 PSE W60L60 VPC MLO PIP	(0.38, 0.37) SDCM ≤3
910925866978	RC340B 36S/940 DEIA W60L60 PCV MLO	(0.38, 0.37) SDCM ≤3
910925866981	RC342B 36S/940 DEIA W62L62 VPC MLO	(0.38, 0.37) SDCM ≤3
910925867145	RC342B 28S/940 DEIA W62L62 VPC MLO	(0.38, 0.37) SDCM ≤3
910925867158	RC342B 28S/940 DEIA W62L62 VPC PCS	(0.38, 0.37) SDCM ≤3
910925867159	RC342B 36S/940 DEIA W62L62 VPC PCS	(0.38, 0.37) SDCM ≤3
910925867160	RC342B 42S/940 DEIA W62L62 VPC PCS	(0.38, 0.37) SDCM ≤3
910925867174	RC342B 28S/940 DEIA W62L62 VPC O	(0.38, 0.37) SDCM ≤3
910925867175	RC342B 36S/940 DEIA W62L62 VPC O	(0.38, 0.37) SDCM ≤3
910925867176	RC342B 42S/940 DEIA W62L62 VPC O	(0.38, 0.37) SDCM ≤3
910505105986	RC342B 28S/940 DEIA W31L125 VPC MXO	(0.43, 0.40) SDCM <3

Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Driver failure rate at 5000 h
910925867015	RC340B 36S/940 PSE W15L120 VPC MLO	0.01 %
910925867016	RC340B 36S/940 DEIA W15L120 VPC MLO	0.01 %
910925867017	RC340B 42S/940 PSE W15L120 VPC MLO	0.01 %
910925867018	RC340B 42S/940 DEIA W15L120 VPC MLO	0.01 %
910925867019	RC340B 36S/940 PSU W15L120 VPC MLO ELP3	0.01 %
910925867020	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	0.01 %
910925867021	RC340B 42S/940 PSU W15L120 VPC MLO ELP3	0.01 %
910925867022	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	0.01 %
910925867024	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	0.01 %
910925867026	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	0.01 %
910925867149	RC342B 28S/940 DEIA W15L125 VPC MLO	-
910925867150	RC342B 36S/940 DEIA W15L125 VPC MLO	-
910925867153	RC342B 36S/940 DEIA W17L125 PCV MLO	-
910925867164	RC342B 28S/940 DEIA W15L125 VPC PCS	-
910925867165	RC342B 36S/940 DEIA W15L125 VPC PCS	-
910925867166	RC342B 42S/940 DEIA W15L125 VPC PCS	-
910925867169	RC342B 36S/940 DEIA W17L125 PCV PCS	-
910925867180	RC342B 28S/940 DEIA W15L125 VPC O	-
910925867181	RC342B 36S/940 DEIA W15L125 VPC O	-

Order Code	Full Product Name	Driver failure rate at 5000 h
910925867182	RC342B 42S/940 DEIA W15L125 VPC O	-
910925866979	RC340B 36S/940 DEIA W30L120 VPC MLO	0.01 %
910925866982	RC342B 36S/940 PSE W31L125 VPC MLO	0.01 %
910925866983	RC342B 36S/940 DEIA W31L125 VPC MLO	0.01 %
910925867030	RC340B 42S/940 DEIA W30L120 VPC MLO W3W2	0.01 %
910925867031	RC340B 42S/940 DEIA W30L120 CPC MLO W3W2	0.01 %
910925867032	RC340B 42S/930 DEIA W30L120 VPC MLO W3W2	0.01 %
910925867033	RC340B 42S/930 DEIA W30L120 CPC MLO W3W2	0.01 %
910925867038	RC340B 42S/940 DEIA W30L120 VPC PCS W3W2	0.01 %
910925867039	RC340B 42S/940 DEIA W30L120 CPC PCS W3W2	0.01 %
910925867042	RC340B 42S/930 DEIA W30L120 VPC PCS W3W2	0.01 %
910925867147	RC342B 28S/940 DEIA W31L125 VPC MLO	-
910925867161	RC342B 28S/940 DEIA W31L125 VPC PCS	-
910925867162	RC342B 36S/940 DEIA W31L125 VPC PCS	-
910925867163	RC342B 42S/940 DEIA W31L125 VPC PCS	-
910925867177	RC342B 28S/940 DEIA W31L125 VPC O	-
910925867178	RC342B 36S/940 DEIA W31L125 VPC O	-
910925867179	RC342B 42S/940 DEIA W31L125 VPC O	-
910925868910	RC340B 36S/930 SRD W60L60 VPC MLO U4	-

FlexBlend Recessed

Order Code	Full Product Name	Driver failure rate at 5000 h
910925868911	RC340B 36S/930 SRD W60L60 VPC MLO U4	-
910925868912	RC340B 36S/930 SEIA W60L60 VPC PCS U4	-
910925868913	RC340B 36S/930 SEIA W60L60 VPC PCS U4 SC	-
910925868914	RC340B 36S/940 SEIA W60L60 VPC MLO U4	-
910925868915	RC340B 36S/940 SEIA W60L60 VPC MLO U4 SC	-
910925868916	RC340B 36S/940 SEIA W60L60 VPC PCS U4	-
910925868917	RC340B 36S/940 SEIA W60L60 VPC PCS U4 SC	-
910925868918	RC340B 36S/940 SEIA W60L60 VPC PCS U4 W3	-
910925868920	RC340B 42S/940 SEIA W60L60 VPC PCS U4 W3	-
910925868921	RC342B 28S/940 SEIA W62L62 VPC MLO U4	-
910925868922	RC342B 28S/940 SEIA W62L62 VPC PCS U4	-
910925868924	RC342B 36S/940 SEIA W62L62 VPC MLO U4	-
910925868925	RC342B 36S/940 SEIA W62L62 VPC PCS U4	-
910925868927	RC342B 42S/940 SEIA W62L62 VPC MLO U4	-
910925868928	RC342B 42S/940 SEIA W62L62 VPC PCS U4	-
910505105985	RC340B 36S/940 SEIA W60L60 VPC MXO U4	-
910925866986	RC340B 36S/940 PSU W60L60 VPC O ELP3	0.01 %
910925866987	RC340B 36S/940 DIA W60L60 VPC O ELP3	0.01 %
910925867001	RC340B 42S/940 PSE W60L60 VPC O	0.01 %
910925867002	RC340B 42S/940 DEIA W60L60 VPC O	0.01 %
910925867006	RC340B 42S/940 PSU W60L60 VPC O ELP3	0.01 %
910925867007	RC340B 42S/940 DIA W60L60 VPC O ELP3	0.01 %
910925867012	RC340B 42S/940 DIA W60L60 VPC O ELD3	0.01 %
910925867061	RC340B 36S/940 PSE W60L60 VPC O SC	0.01 %
910925867062	RC340B 36S/940 DEIA W60L60 VPC O SC	0.01 %
910925868919	RC340B 42S/940 SEIA W30L120 VPC PCS U4W3	-
910925868923	RC342B 36S/940 SEIA W31L125 VPC PCS U4	-
910925868926	RC342B 42S/940 SEIA W31L125 VPC PCS U4	-
910925866969	RC340B 36S/940 DEIA W60L60 VPC MLO	0.01 %
910925867023	RC340B 42S/930 DEIA W60L60 CPC MLO W3W2	0.01 %
910925867028	RC340B 42S/940 DEIA W60L60 CPC MLO W3W2	0.01 %
910925867036	RC340B 42S/940 DEIA W60L60 CPC PCS W3W2	0.01 %
910925867040	RC340B 42S/930 DEIA W60L60 CPC PCS W3W2	0.01 %
910925867046	RC340B 36S/940 PSE W60L60 CPC MLO	0.01 %
910925867047	RC340B 42S/940 PSE W60L60 CPC MLO	0.01 %
910925867048	RC340B 42S/940 DEIA W60L60 CPC MLO	0.01 %
910925867167	RC342B 42S/940 DEIA W62L62 CPC PCS	-
910925867068	RC340B 42S/930 DEIA W30L120 CPC PCS W3W2	0.01 %
910925866967	RC340B 36S/940 DEIA W60L60 VPC O	0.01 %
910925866972	RC340B 36S/940 PSE W60L60 VPC PCS	0.01 %
910925866973	RC340B 36S/940 DEIA W60L60 VPC PCS	0.01 %
910925866977	RC340B 36S/940 DEIA W60L60 CPC MLO	0.01 %
910925866990	RC340B 36S/940 PSU W60L60 VPC PCS ELP3	0.01 %
910925866991	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	0.01 %
910925866997	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	0.01 %
910925867003	RC340B 42S/940 PSE W60L60 VPC PCS	0.01 %
910925867004	RC340B 42S/940 DEIA W60L60 VPC PCS	0.01 %
910925867008	RC340B 42S/940 PSU W60L60 VPC PCS ELP3	0.01 %
910925867009	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	0.01 %
910925867034	RC340B 42S/930 DEIA W60L60 VPC PCS W3W2	0.01 %

Order Code	Full Product Name	Driver failure rate at 5000 h
910925867035	RC340B 42S/940 DEIA W60L60 VPC PCS W3W2	0.01 %
910925867044	RC340B 36S/940 PSE W60L60 CPC PCS PIP	0.01 %
910925867045	RC340B 36S/940 DEIA W60L60 CPC PCS	0.01 %
910925867049	RC340B 42S/940 PSE W60L60 CPC PCS	0.01 %
910925867050	RC340B 42S/940 DEIA W60L60 CPC PCS	0.01 %
910925867065	RC340B 36S/940 PSE W60L60 VPC PCS SC	0.01 %
910925867066	RC340B 36S/940 DEIA W60L60 VPC PCS SC	0.01 %
910505105982	RC340B 36S/940 SEIA W60L60 VPC DLO U4	-
910505105987	RC340B 42S/840 SEIA W60L60 VPC PCS U4 SC	-
910505105990	RC340B 36S/840 SEIA W67L67 FLC4DLO U4 SC	-
910505105989	RC342B 42S/840 DEIA W62L62 VPC PCS	-
910505105984	RC342B 36S/940 DEIA W31L125 VPC DLO	-
910505105988	RC340B 42S/840 PSU W30L120 VPC PCS ELB3	-
910505105992	RC340B 36S/840 DEIA W30L135 FLC2 DLO SC	-
910925866966	RC340B 36S/940 PSE W60L60 VPC O	0.01 %
910925866980	RC342B 36S/940 PSE W62L62 VPC MLO	0.01 %
910925866988	RC340B 36S/940 PSU W60L60 VPC MLO ELP3	0.01 %
910925866989	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	0.01 %
910925866993	RC340B 36S/940 DIA W60L60 VPC O ELD3	0.01 %
910925866995	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	0.01 %
910925866999	RC340B 42S/940 DEIA W60L60 VPC MLO	0.01 %
910925867010	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	0.01 %
910925867013	RC340B 42S/930 DEIA W60L60 VPC MLO W3W2	0.01 %
910925867027	RC340B 42S/940 DEIA W60L60 VPC MLO W3W2	0.01 %
910925867043	RC340B 42S/940 PSE W60L60 VPC MLO	0.01 %
910925867063	RC340B 36S/940 PSE W60L60 VPC MLO SC	0.01 %
910925867064	RC340B 36S/940 DEIA W60L60 VPC MLO SC	0.01 %
910925866970	RC340B 36S/940 POE W60L60 VPC MLO	0.01 %
910925867014	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	0.01 %
910925867025	RC340B 42S/930 DEIA W60L60 PCV MLO W3W2	0.01 %
910925867029	RC340B 42S/940 DEIA W60L60 PCV MLO W3W2	0.01 %
910925867037	RC340B 42S/940 DEIA W60L60 PCV PCS W3W2	0.01 %
910925867041	RC340B 42S/930 DEIA W60L60 PCV PCS W3W2	0.01 %
910925867168	RC340B 36S/940 DEIA W60L60 PCV PCS	-
910925867221	RC340B 36S/940 POE W60L60 VPC MLO U0	-
910925867224	RC340B 36S/940 POE W60L60 VPC PCS U0	-
910505105983	RC340B 42S/940 SEIA W30L120 VPC DLO U4	-
910505105991	RC340B 42S/840 SEIA W30L135 FLC4DLOU4SC	-
910925866968	RC340B 36S/940 PSE W60L60 VPC MLO PIP	0.01 %
910925866978	RC340B 36S/940 DEIA W60L60 PCV MLO	0.01 %
910925866981	RC342B 36S/940 DEIA W62L62 VPC MLO	0.01 %
910925867145	RC342B 28S/940 DEIA W62L62 VPC MLO	-
910925867158	RC342B 28S/940 DEIA W62L62 VPC PCS	-
910925867159	RC342B 36S/940 DEIA W62L62 VPC PCS	-
910925867160	RC342B 42S/940 DEIA W62L62 VPC PCS	-
910925867174	RC342B 28S/940 DEIA W62L62 VPC O	-
910925867175	RC342B 36S/940 DEIA W62L62 VPC O	-
910925867176	RC342B 42S/940 DEIA W62L62 VPC O	-
910505105986	RC342B 28S/940 DEIA W31L125 VPC MXO	-

Product Data

FlexBlend Recessed

Order Code	Full Product Name	Product family code
910925867015	RC340B 36S/940 PSE W15L120 VPC MLO	RC340B
910925867016	RC340B 36S/940 DEIA W15L120 VPC MLO	RC340B
910925867017	RC340B 42S/940 PSE W15L120 VPC MLO	RC340B
910925867018	RC340B 42S/940 DEIA W15L120 VPC MLO	RC340B
910925867019	RC340B 36S/940 PSU W15L120 VPC MLO ELP3	RC340B
910925867020	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	RC340B
910925867021	RC340B 42S/940 PSU W15L120 VPC MLO ELP3	RC340B
910925867022	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	RC340B
910925867024	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	RC340B
910925867026	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	RC340B
910925867149	RC342B 28S/940 DEIA W15L125 VPC MLO	RC342B
910925867150	RC342B 36S/940 DEIA W15L125 VPC MLO	RC342B
910925867153	RC342B 36S/940 DEIA W17L125 PCV MLO	RC342B
910925867164	RC342B 28S/940 DEIA W15L125 VPC PCS	RC342B
910925867165	RC342B 36S/940 DEIA W15L125 VPC PCS	RC342B
910925867166	RC342B 42S/940 DEIA W15L125 VPC PCS	RC342B
910925867169	RC342B 36S/940 DEIA W17L125 PCV PCS	RC342B
910925867180	RC342B 28S/940 DEIA W15L125 VPC O	RC342B
910925867181	RC342B 36S/940 DEIA W15L125 VPC O	RC342B
910925867182	RC342B 42S/940 DEIA W15L125 VPC O	RC342B
910925866979	RC340B 36S/940 DEIA W30L120 VPC MLO	RC340B
910925866982	RC342B 36S/940 PSE W31L125 VPC MLO	RC342B
910925866983	RC342B 36S/940 DEIA W31L125 VPC MLO	RC342B
910925867030	RC340B 42S/940 DEIA W30L120 VPC MLO W3W2	RC340B
910925867031	RC340B 42S/940 DEIA W30L120 CPC MLO W3W2	RC340B
910925867032	RC340B 42S/930 DEIA W30L120 VPC MLO W3W2	RC340B
910925867033	RC340B 42S/930 DEIA W30L120 CPC MLO W3W2	RC340B
910925867038	RC340B 42S/940 DEIA W30L120 VPC PCS W3W2	RC340B
910925867039	RC340B 42S/940 DEIA W30L120 CPC PCS W3W2	RC340B
910925867042	RC340B 42S/930 DEIA W30L120 VPC PCS W3W2	RC340B
910925867147	RC342B 28S/940 DEIA W31L125 VPC MLO	RC342B
910925867161	RC342B 28S/940 DEIA W31L125 VPC PCS	RC342B
910925867162	RC342B 36S/940 DEIA W31L125 VPC PCS	RC342B
910925867163	RC342B 42S/940 DEIA W31L125 VPC PCS	RC342B
910925867177	RC342B 28S/940 DEIA W31L125 VPC O	RC342B
910925867178	RC342B 36S/940 DEIA W31L125 VPC O	RC342B
910925867179	RC342B 42S/940 DEIA W31L125 VPC O	RC342B
910925868910	RC340B 36S/930 SRD W60L60 VPC MLO U4	RC340B
910925868911	RC340B 36S/930 SRD W60L60 VPC MLO U4	RC340B
910925868912	RC340B 36S/930 SEIA W60L60 VPC PCS U4	RC340B
910925868913	RC340B 36S/930 SEIA W60L60 VPC PCS U4 SC	RC340B
910925868914	RC340B 36S/940 SEIA W60L60 VPC MLO U4	RC340B
910925868915	RC340B 36S/940 SEIA W60L60 VPC MLO U4 SC	RC340B
910925868916	RC340B 36S/940 SEIA W60L60 VPC PCS U4	RC340B
910925868917	RC340B 36S/940 SEIA W60L60 VPC PCS U4 SC	RC340B
910925868918	RC340B 36S/940 SEIA W60L60 VPC PCS U4 W3	RC340B
910925868920	RC340B 42S/940 SEIA W60L60 VPC PCS U4 W3	RC340B
910925868921	RC342B 28S/940 SEIA W62L62 VPC MLO U4	RC342B
910925868922	RC342B 28S/940 SEIA W62L62 VPC PCS U4	RC342B
910925868924	RC342B 36S/940 SEIA W62L62 VPC MLO U4	RC342B
910925868925	RC342B 36S/940 SEIA W62L62 VPC PCS U4	RC342B


Order Code	Full Product Name	Product family code
910925868927	RC342B 42S/940 SEIA W62L62 VPC MLO U4	RC342B
910925868928	RC342B 42S/940 SEIA W62L62 VPC PCS U4	RC342B
910505105985	RC340B 36S/940 SEIA W60L60 VPC MXO U4	RC340B
910925866986	RC340B 36S/940 PSU W60L60 VPC O ELP3	RC340B
910925866987	RC340B 36S/940 DIA W60L60 VPC O ELP3	RC340B
910925867001	RC340B 42S/940 PSE W60L60 VPC O	RC340B
910925867002	RC340B 42S/940 DEIA W60L60 VPC O	RC340B
910925867006	RC340B 42S/940 PSU W60L60 VPC O ELP3	RC340B
910925867007	RC340B 42S/940 DIA W60L60 VPC O ELP3	RC340B
910925867012	RC340B 42S/940 DIA W60L60 VPC O ELD3	RC340B
910925867061	RC340B 36S/940 PSE W60L60 VPC O SC	RC340B
910925867062	RC340B 36S/940 DEIA W60L60 VPC O SC	RC340B
910925868919	RC340B 42S/940 SEIA W30L120 VPC PCS U4W3	RC340B
910925868923	RC342B 36S/940 SEIA W31L125 VPC PCS U4	RC342B
910925868926	RC342B 42S/940 SEIA W31L125 VPC PCS U4	RC342B
910925866969	RC340B 36S/940 DEIA W60L60 VPC MLO	RC340B
910925867023	RC340B 42S/930 DEIA W60L60 CPC MLO W3W2	RC340B
910925867028	RC340B 42S/940 DEIA W60L60 CPC MLO W3W2	RC340B
910925867036	RC340B 42S/940 DEIA W60L60 CPC PCS W3W2	RC340B
910925867040	RC340B 42S/930 DEIA W60L60 CPC PCS W3W2	RC340B
910925867046	RC340B 36S/940 PSE W60L60 CPC MLO	RC340B
910925867047	RC340B 42S/940 PSE W60L60 CPC MLO	RC340B
910925867048	RC340B 42S/940 DEIA W60L60 CPC MLO	RC340B
910925867167	RC342B 42S/940 DEIA W62L62 CPC PCS	RC342B
910925867068	RC340B 42S/930 DEIA W30L120 CPC PCS W3W2	RC340B
910925866967	RC340B 36S/940 DEIA W60L60 VPC O	RC340B
910925866972	RC340B 36S/940 PSE W60L60 VPC PCS	RC340B
910925866973	RC340B 36S/940 DEIA W60L60 VPC PCS	RC340B
910925866977	RC340B 36S/940 DEIA W60L60 CPC MLO	RC340B
910925866990	RC340B 36S/940 PSU W60L60 VPC PCS ELP3	RC340B
910925866991	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	RC340B
910925866997	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	RC340B
910925867003	RC340B 42S/940 PSE W60L60 VPC PCS	RC340B
910925867004	RC340B 42S/940 DEIA W60L60 VPC PCS	RC340B
910925867008	RC340B 42S/940 PSU W60L60 VPC PCS ELP3	RC340B
910925867009	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	RC340B
910925867034	RC340B 42S/930 DEIA W60L60 VPC PCS W3W2	RC340B
910925867035	RC340B 42S/940 DEIA W60L60 VPC PCS W3W2	RC340B
910925867044	RC340B 36S/940 PSE W60L60 CPC PCS PIP	RC340B
910925867045	RC340B 36S/940 DEIA W60L60 CPC PCS	RC340B
910925867049	RC340B 42S/940 PSE W60L60 CPC PCS	RC340B
910925867050	RC340B 42S/940 DEIA W60L60 CPC PCS	RC340B
910925867065	RC340B 36S/940 PSE W60L60 VPC PCS SC	RC340B
910925867066	RC340B 36S/940 DEIA W60L60 VPC PCS SC	RC340B
910505105982	RC340B 36S/940 SEIA W60L60 VPC DLO U4	RC340B
910505105987	RC340B 42S/840 SEIA W60L60 VPC PCS U4 SC	RC340B
910505105990	RC340B 36S/840 SEIA W67L67 FLC4DLO U4 SC	RC340B
910505105989	RC342B 42S/840 DEIA W62L62 VPC PCS	RC340B
910505105984	RC342B 36S/940 DEIA W31L125 VPC DLO	RC340B
910505105988	RC340B 42S/840 PSU W30L120 VPC PCS ELB3	RC340B
910505105992	RC340B 36S/840 DEIA W30L135 FLC2 DLO SC	RC340B

FlexBlend Recessed


Order Code	Full Product Name	Product family code
910925866966	RC340B 36S/940 PSE W60L60 VPC O	RC340B
910925866980	RC342B 36S/940 PSE W62L62 VPC MLO	RC342B
910925866988	RC340B 36S/940 PSU W60L60 VPC MLO ELP3	RC340B
910925866989	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	RC340B
910925866993	RC340B 36S/940 DIA W60L60 VPC O ELD3	RC340B
910925866995	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	RC340B
910925866999	RC340B 42S/940 DEIA W60L60 VPC MLO	RC340B
910925867010	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	RC340B
910925867013	RC340B 42S/930 DEIA W60L60 VPC MLO W3W2	RC340B
910925867027	RC340B 42S/940 DEIA W60L60 VPC MLO W3W2	RC340B
910925867043	RC340B 42S/940 PSE W60L60 VPC MLO	RC340B
910925867063	RC340B 36S/940 PSE W60L60 VPC MLO SC	RC340B
910925867064	RC340B 36S/940 DEIA W60L60 VPC MLO SC	RC340B
910925866970	RC340B 36S/940 POE W60L60 VPC MLO	RC340B
910925867014	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	RC340B
910925867025	RC340B 42S/930 DEIA W60L60 PCV MLO W3W2	RC340B
910925867029	RC340B 42S/940 DEIA W60L60 PCV MLO W3W2	RC340B
910925867037	RC340B 42S/940 DEIA W60L60 PCV PCS W3W2	RC340B

Order Code	Full Product Name	Product family code
910925867041	RC340B 42S/930 DEIA W60L60 PCV PCS W3W2	RC340B
910925867168	RC340B 36S/940 DEIA W60L60 PCV PCS	RC340B
910925867221	RC340B 36S/940 POE W60L60 VPC MLO U0	RC340B
910925867224	RC340B 36S/940 POE W60L60 VPC PCS U0	RC340B
910505105983	RC340B 42S/940 SEIA W30L120 VPC DLO U4	RC340B
910505105991	RC340B 42S/840 SEIA W30L135 FLC4DLOU4SC	RC340B
910925866968	RC340B 36S/940 PSE W60L60 VPC MLO PIP	RC340B
910925866978	RC340B 36S/940 DEIA W60L60 PCV MLO	RC340B
910925866981	RC342B 36S/940 DEIA W62L62 VPC MLO	RC342B
910925867145	RC342B 28S/940 DEIA W62L62 VPC MLO	RC342B
910925867158	RC342B 28S/940 DEIA W62L62 VPC PCS	RC342B
910925867159	RC342B 36S/940 DEIA W62L62 VPC PCS	RC342B
910925867160	RC342B 42S/940 DEIA W62L62 VPC PCS	RC342B
910925867174	RC342B 28S/940 DEIA W62L62 VPC O	RC342B
910925867175	RC342B 36S/940 DEIA W62L62 VPC O	RC342B
910925867176	RC342B 42S/940 DEIA W62L62 VPC O	RC342B
910505105986	RC342B 28S/940 DEIA W31L125 VPC MXO	RC340B


Polar Wide Diagrams




Polar Normal (separate) - RC340BI -
910925866978




Polar Normal (separate) - RC340BI -
910925866989




Polar Normal (separate) - RC340BI -
910925867030



Polar Normal (separate) - RC340BI -
910925867031




Polar Normal (separate) - RC340BI -
910925866987




Polar Normal (separate) - RC340BI -
910925868912

FlexBlend Recessed


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925868924




Polar Normal (separate) - RC340BI - 910925868915




Polar Normal (separate) - RC340BI - 910925868917




Polar Normal (separate) - RC340BI - 910925868928




Polar Normal (separate) - RC340BI - 910925868910




Polar Normal (separate) - RC340BI - 910925868927



Polar Normal (separate) - RC340BI - 910925868921




Polar Normal (separate) - RC340BI - 910925868926




Polar Normal (separate) - RC340BI - 910925868914

FlexBlend Recessed


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925868923




Polar Normal (separate) - RC340BI - 910925868911




Polar Normal (separate) - RC340BI - 910925868922




Polar Normal (separate) - RC340BI - 910925868925




Polar Normal (separate) - RC340BI - 910925868920




Polar Normal (separate) - RC340BI - 910925866969



Polar Normal (separate) - RC340BI - 910925866968




Polar Normal (separate) - RC340BI - 910925866970




Polar Normal (separate) - RC340BI - 910925866979

FlexBlend Recessed


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925866981




Polar Normal (separate) - RC340BI - 910925867038




Polar Normal (separate) - RC340BI - 910925867040




Polar Normal (separate) - RC340BI - 910925867050




Polar Normal (separate) - RC340BI - 910925866973




Polar Normal (separate) - RC340BI - 910925866991



Polar Normal (separate) - RC340BI - 910925866993




Polar Normal (separate) - RC340BI - 910925867002




Polar Normal (separate) - RC340BI - 910925867003

FlexBlend Recessed


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925866977




Polar Normal (separate) - RC340BI - 910925866995




Polar Normal (separate) - RC340BI - 910925867012




Polar Normal (separate) - RC340BI - 910925867017




Polar Normal (separate) - RC340BI - 910925867019




Polar Normal (separate) - RC340BI - 910925867033



Polar Normal (separate) - RC340BI - 910925867024




Polar Normal (separate) - RC340BI - 910925867043




Polar Normal (separate) - RC340BI - 910925867049

FlexBlend Recessed


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925866967




Polar Normal (separate) - RC340BI - 910925867010




Polar Normal (separate) - RC340BI - 910925867013




Polar Normal (separate) - RC340BI - 910925867022




Polar Normal (separate) - RC340BI - 910925867034




Polar Normal (separate) - RC340BI - 910925867039



Polar Normal (separate) - RC340BI - 910925867032




Polar Normal (separate) - RC340BI - 910925867064




Polar Normal (separate) - RC340BI - 910925866980

FlexBlend Recessed


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925866982




Polar Normal (separate) - RC340BI - 910925866983




Polar Normal (separate) - RC340BI - 910925866988




Polar Normal (separate) - RC340BI - 910925866997




Polar Normal (separate) - RC340BI - 910925867006




Polar Normal (separate) - RC340BI - 910925867009



Polar Normal (separate) - RC340BI - 910925867047




Polar Normal (separate) - RC340BI - 910925867062




Polar Normal (separate) - RC340BI - 910925867063

FlexBlend Recessed


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925866966




Polar Normal (separate) - RC340BI - 910925867008




Polar Normal (separate) - RC340BI - 910925867018




Polar Normal (separate) - RC340BI - 910925867016




Polar Normal (separate) - RC340BI - 910925867021




Polar Normal (separate) - RC340BI - 910925867025



Polar Normal (separate) - RC340BI - 910925867028




Polar Normal (separate) - RC340BI - 910925867014




Polar Normal (separate) - RC340BI - 910925867145

FlexBlend Recessed


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925867147




Polar Normal (separate) - RC340BI - 910925867020




Polar Normal (separate) - RC340BI - 910925867026




Polar Normal (separate) - RC340BI - 910925867035




Polar Normal (separate) - RC340BI - 910925867036




Polar Normal (separate) - RC340BI - 910925867044



Polar Normal (separate) - RC340BI - 910925867045




Polar Normal (separate) - RC340BI - 910925867048




Polar Normal (separate) - RC340BI - 910925867065

FlexBlend Recessed


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925867041




Polar Normal (separate) - RC340BI - 910925867066




Polar Normal (separate) - RC340BI - 910925867162




Polar Normal (separate) - RC340BI - 910925867160




Polar Normal (separate) - RC340BI - 910925867153




Polar Normal (separate) - RC340BI - 910925867175



Polar Normal (separate) - RC340BI - 910925867179




Polar Normal (separate) - RC340BI - 910925867182




Polar Normal (separate) - RC340BI - 910925867163

FlexBlend Recessed


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925867174




Polar Normal (separate) - RC340BI - 910925867176




Polar Normal (separate) - RC340BI - 910925866972




Polar Normal (separate) - RC340BI - 910925866986




Polar Normal (separate) - RC340BI - 910925866990




Polar Normal (separate) - RC340BI - 910925866999



Polar Normal (separate) - RC340BI - 910925867001




Polar Normal (separate) - RC340BI - 910925867004




Polar Normal (separate) - RC340BI - 910925867007

FlexBlend Recessed


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925867015




Polar Normal (separate) - RC340BI - 910925867023




Polar Normal (separate) - RC340BI - 910925867027




Polar Normal (separate) - RC340BI - 910925867029




Polar Normal (separate) - RC340BI - 910925867037




Polar Normal (separate) - RC340BI - 910925867046



Polar Normal (separate) - RC340BI - 910925867042




Polar Normal (separate) - RC340BI - 910925867061




Polar Normal (separate) - RC340BI - 910925867068

FlexBlend Recessed


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925867150




Polar Normal (separate) - RC340BI - 910925867161




Polar Normal (separate) - RC340BI - 910925867166




Polar Normal (separate) - RC340BI - 910925867168




Polar Normal (separate) - RC340BI - 910925867169




Polar Normal (separate) - RC340BI - 910925867181



Polar Normal (separate) - RC340BI - 910925867180




Polar Normal (separate) - RC340BI - 910925867224




Polar Normal (separate) - RC340BI - 910925868913

FlexBlend Recessed

Polar Wide Diagrams



Polar Normal (separate) - null - 910505105991



Polar Normal (separate) - null - 910505105983

