




FlexBlend - Unlocking the potential of LED lighting in offices

Office owners and staff responsible for lighting operations are searching for high-quality yet energy-efficient lighting that complies with norms and regulations. Designed to support these needs, Philips FlexBlend is enabling building owners to fully optimise their lighting operations, by offering office-compliant lighting with an attractive return on investment. Furthermore, FlexBlend provides the required flexibility by being easy to use with different ceiling lights, as well as in different office spaces like open office or meeting rooms. Though technology is changing fast, the ideal lighting solution is also expected to be ready to incorporate innovations and future advances that can help optimise operations further. For this reason, Philips FlexBlend is also ready to be connected to controls such as Actilume or used together with the Philips SpaceWise lighting system. It can also be connected to software-based lighting systems like Interact Office, which provides the luminaire with further intelligence and enables it to collect valuable data about its environment

Benefits

- High-quality office-compliant lighting
- Choice of three different exit-windows
- Fast return on investment

- Application flexibility
- Scalable and ready to be connected to controls and lighting systems

Applications

- Offices
- Education

- Healthcare
- Banks

Features

- Fully office-compliant (UGR <19)
- Homogenous and uniform light effect

- Dimensional variety, local options
- Various mounting options
- Integrated sensors
- Can be combined with Philips ActiLume and SpaceWise systems
- Ready to be connected to software based lighting systems such as Interact Office


Versions




FlexBlend Recessed RC340B
W15L120 MLO VPC




FlexBlend Recessed-RC340B
W30L120 MLO VPC




FlexBlend Recessed RC340B
W60L60 OPA VPC



FlexBlend Recessed RC340B
W60L60 MLO CPC



FlexBlend Recessed RC340B
W60L60 PCS VPC



FlexBlend Recessed RC340B
W60L60 MLO VPC




FlexBlend Recessed RC340B
W60L60 MLO PCV




FlexBlend Recessed RC342B
W62L62 MLO VPC


Dimensional drawing




RC342B 42S/940 DEIA W62L62 VPC PCS




RC342B 42S/940 DEIA W31L125 VPC PCS




RC340B 36S/940 DEIA W30L120 VPC MLO




RC340B 42S/940 DIA W15L120 VPC MLO ELP3




FLEXBLEND RECESSED, module 625 - 940 neutral white - Power supply unit with DALI interface - Plug-in connector 3-pole Wieland/Adels compatible




RC342B 42S/940 DEIA W62L62 CPC PCS



RC340B 42S/940 PSE W60L60 CPC MLO



FLEXBLEND RECESSED, module 625 - 940 neutral white - Power supply unit with DALI interface - Plug-in connector 3-pole Wieland/Adels compatible



RC340B 42S/940 DEIA W60L60 VPC MLO

Product details

0_FlexBlend Recessed-
RC342B_W62L62_MLO_VPC



FlexBlend Recessed-
RC340B_MLO_DPP




FlexBlend Recessed-
RC340B_W60L60_Backcover_V
PC




FlexBlend Recessed-
RC340B_W60L60_CPC
brackets





FlexBlend Recessed-RC340B_W60L60_CPC brackets_B



FlexBlend Recessed-RC340B_OPA_DPP



FlexBlend Recessed-RC340B_PCS_DPP



0_FlexBlend Recessed-RC340B_W60L60_PCS_VPC



FlexBlend Recessed-RC340B_W60L60_CPC brackets_A



FlexBlend Recessed RC340B PIP Open



FlexBlend Recessed-RC340B_W60L60_backcover_P CV



0_FlexBlend Recessed-RC340B_W60L60_MLO_VPC



0_FlexBlend Recessed-RC340B_W60L60_MLO_CPC



FlexBlend Recessed-RC340B PIP Closed



FlexBlend Recessed-
RC340B_W60L60_backcover_C
PC

General Information

Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Service tag	Yes

Light Technical

Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	>90
Beam angle of light source	120 degree(s)
Optic type	Wide beam

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	Yes
Protection class IEC	Safety class I

Controls and Dimming

Maximum dim level	1%
-------------------	----

Mechanical and Housing

Housing Color	White
Mech. impact protection code	IK02 [0.2 J standard]

Emergency Operation

Rated duration of the emergency lighting (when fully charged)	3 hour(s)
---	-----------

Approval and Application

Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	+10 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.37) SDCM ≤3

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.01 %
-------------------------------	--------

Light Technical

Order Code	Full Product Name	Luminous Flux	Luminous Efficacy (rated) (Nom)
10277400	RC340B 36S/940 PSE W15L120 VPC MLO	3,600 lm	95 lm/W
10278100	RC340B 36S/940 DEIA W15L120 VPC MLO	3,600 lm	95 lm/W
10279800	RC340B 42S/940 PSE W15L120 VPC MLO	4,200 lm	93 lm/W
10280400	RC340B 42S/940 DEIA W15L120 VPC MLO	4,200 lm	93 lm/W
10282800	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	3,600 lm	95 lm/W
10284200	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	4,200 lm	93 lm/W
10286600	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	3,600 lm	95 lm/W
10288000	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	4,200 lm	93 lm/W
10410500	RC342B 28S/940 DEIA W15L125 VPC MLO	2,800 lm	110 lm/W
10411200	RC342B 36S/940 DEIA W15L125 VPC MLO	3,600 lm	95 lm/W
10414300	RC342B 36S/940 DEIA W17L125 PCV MLO	3,600 lm	95 lm/W
10425900	RC342B 28S/940 DEIA W15L125 VPC PCS	2,800 lm	127 lm/W
10426600	RC342B 36S/940 DEIA W15L125 VPC PCS	3,600 lm	138 lm/W
10427300	RC342B 42S/940 DEIA W15L125 VPC PCS	4,200 lm	138 lm/W
10430300	RC342B 36S/940 DEIA W17L125 PCV PCS	3,600 lm	144 lm/W
10441900	RC342B 28S/940 DEIA W15L125 VPC O	2,800 lm	124 lm/W
10442600	RC342B 36S/940 DEIA W15L125 VPC O	3,600 lm	126 lm/W
10443300	RC342B 42S/940 DEIA W15L125 VPC O	4,200 lm	125 lm/W
10242200	RC340B 36S/940 DEIA W30L120 VPC MLO	3,600 lm	95 lm/W
10245300	RC342B 36S/940 PSE W31L125 VPC MLO	3,600 lm	95 lm/W
10246000	RC342B 36S/940 DEIA W31L125 VPC MLO	3,600 lm	95 lm/W

Order Code	Full Product Name	Luminous Flux	Luminous Efficacy (rated) (Nom)
10408200	RC342B 28S/940 DEIA W31L125 VPC MLO	2,800 lm	110 lm/W
10422800	RC342B 28S/940 DEIA W31L125 VPC PCS	2,800 lm	127 lm/W
10423500	RC342B 36S/940 DEIA W31L125 VPC PCS	3,600 lm	138 lm/W
10424200	RC342B 42S/940 DEIA W31L125 VPC PCS	4,200 lm	138 lm/W
10438900	RC342B 28S/940 DEIA W31L125 VPC O	2,800 lm	124 lm/W
10439600	RC342B 36S/940 DEIA W31L125 VPC O	3,600 lm	126 lm/W
10440200	RC342B 42S/940 DEIA W31L125 VPC O	4,200 lm	125 lm/W
10250700	RC340B 36S/940 DIA W60L60 VPC O ELP3	3,600 lm	126 lm/W
10263700	RC340B 42S/940 PSE W60L60 VPC O	4,200 lm	125 lm/W
10264400	RC340B 42S/940 DEIA W60L60 VPC O	4,200 lm	125 lm/W
10269900	RC340B 42S/940 DIA W60L60 VPC O ELP3	4,200 lm	125 lm/W
10274300	RC340B 42S/940 DIA W60L60 VPC O ELD3	4,200 lm	125 lm/W
10323800	RC340B 36S/940 PSE W60L60 VPC O SC	3,600 lm	126 lm/W
10324500	RC340B 36S/940 DEIA W60L60 VPC O SC	3,600 lm	126 lm/W
10232300	RC340B 36S/940 DEIA W60L60 VPC MLO	3,600 lm	95 lm/W
10308500	RC340B 36S/940 PSE W60L60 CPC MLO	3,600 lm	95 lm/W
10309200	RC340B 42S/940 PSE W60L60 CPC MLO	4,200 lm	93 lm/W
10310800	RC340B 42S/940 DEIA W60L60 CPC MLO	4,200 lm	93 lm/W
10428000	RC342B 42S/940 DEIA W62L62 CPC PCS	4,200 lm	138 lm/W
10230900	RC340B 36S/940 DEIA W60L60 VPC O	3,600 lm	126 lm/W
10235400	RC340B 36S/940 PSE W60L60 VPC PCS	3,600 lm	138 lm/W
10236100	RC340B 36S/940 DEIA W60L60 VPC PCS	3,600 lm	138 lm/W
10240800	RC340B 36S/940 DEIA W60L60 CPC MLO	3,600 lm	95 lm/W
10254500	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	3,600 lm	138 lm/W
10260600	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	3,600 lm	138 lm/W
10265100	RC340B 42S/940 PSE W60L60 VPC PCS	4,200 lm	138 lm/W
10266800	RC340B 42S/940 DEIA W60L60 VPC PCS	4,200 lm	138 lm/W
10271200	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	4,200 lm	138 lm/W
10306100	RC340B 36S/940 PSE W60L60 CPC PCS PIP	3,600 lm	138 lm/W
10307800	RC340B 36S/940 DEIA W60L60 CPC PCS	3,600 lm	138 lm/W
10311500	RC340B 42S/940 PSE W60L60 CPC PCS	4,200 lm	138 lm/W
10312200	RC340B 42S/940 DEIA W60L60 CPC PCS	4,200 lm	138 lm/W
10327600	RC340B 36S/940 PSE W60L60 VPC PCS SC	3,600 lm	138 lm/W
10328300	RC340B 36S/940 DEIA W60L60 VPC PCS SC	3,600 lm	138 lm/W
10229300	RC340B 36S/940 PSE W60L60 VPC O	3,600 lm	126 lm/W
10243900	RC342B 36S/940 PSE W62L62 VPC MLO	3,600 lm	95 lm/W
10252100	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	3,600 lm	95 lm/W
10256900	RC340B 36S/940 DIA W60L60 VPC O ELD3	3,600 lm	126 lm/W
10258300	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	3,600 lm	95 lm/W
10262000	RC340B 42S/940 DEIA W60L60 VPC MLO	4,200 lm	93 lm/W
10272900	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	4,200 lm	93 lm/W
10305400	RC340B 42S/940 PSE W60L60 VPC MLO	4,200 lm	93 lm/W

Order Code	Full Product Name	Luminous Flux	Luminous Efficacy (rated) (Nom)
10325200	RC340B 36S/940 PSE W60L60 VPC MLO SC	3,600 lm	95 lm/W
10326900	RC340B 36S/940 DEIA W60L60 VPC MLO SC	3,600 lm	95 lm/W
10276700	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	4,200 lm	138 lm/W
10231600	RC340B 36S/940 PSE W60L60 VPC MLO PIP	3,600 lm	95 lm/W
10241500	RC340B 36S/940 DEIA W60L60 PCV MLO	3,600 lm	95 lm/W
10244600	RC342B 36S/940 DEIA W62L62 VPC MLO	3,600 lm	95 lm/W
10406800	RC342B 28S/940 DEIA W62L62 VPC MLO	2,800 lm	110 lm/W
10419800	RC342B 28S/940 DEIA W62L62 VPC PCS	2,800 lm	127 lm/W
10420400	RC342B 36S/940 DEIA W62L62 VPC PCS	3,600 lm	144 lm/W
10421100	RC342B 42S/940 DEIA W62L62 VPC PCS	4,200 lm	138 lm/W
10435800	RC342B 28S/940 DEIA W62L62 VPC O	2,800 lm	124 lm/W
10436500	RC342B 36S/940 DEIA W62L62 VPC O	3,600 lm	126 lm/W
10437200	RC342B 42S/940 DEIA W62L62 VPC O	4,200 lm	125 lm/W

Operating and Electrical

Order Code	Full Product Name	Power Consumption
10277400	RC340B 36S/940 PSE W15L120 VPC MLO	38 W
10278100	RC340B 36S/940 DEIA W15L120 VPC MLO	38 W
10279800	RC340B 42S/940 PSE W15L120 VPC MLO	45 W
10280400	RC340B 42S/940 DEIA W15L120 VPC MLO	45 W
10282800	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	38 W
10284200	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	45 W
10286600	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	38 W
10288000	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	45 W
10410500	RC342B 28S/940 DEIA W15L125 VPC MLO	25.5 W
10411200	RC342B 36S/940 DEIA W15L125 VPC MLO	38 W
10414300	RC342B 36S/940 DEIA W17L125 PCV MLO	38 W
10425900	RC342B 28S/940 DEIA W15L125 VPC PCS	22 W
10426600	RC342B 36S/940 DEIA W15L125 VPC PCS	26 W
10427300	RC342B 42S/940 DEIA W15L125 VPC PCS	30.5 W
10430300	RC342B 36S/940 DEIA W17L125 PCV PCS	25 W
10441900	RC342B 28S/940 DEIA W15L125 VPC O	22.5 W
10442600	RC342B 36S/940 DEIA W15L125 VPC O	28.5 W
10443300	RC342B 42S/940 DEIA W15L125 VPC O	33.5 W
10242200	RC340B 36S/940 DEIA W30L120 VPC MLO	38 W
10245300	RC342B 36S/940 PSE W31L125 VPC MLO	37 W
10246000	RC342B 36S/940 DEIA W31L125 VPC MLO	38 W
10408200	RC342B 28S/940 DEIA W31L125 VPC MLO	25.5 W
10422800	RC342B 28S/940 DEIA W31L125 VPC PCS	22 W
10423500	RC342B 36S/940 DEIA W31L125 VPC PCS	26 W
10424200	RC342B 42S/940 DEIA W31L125 VPC PCS	30.5 W

Order Code	Full Product Name	Power Consumption
10438900	RC342B 28S/940 DEIA W31L125 VPC O	22.5 W
10439600	RC342B 36S/940 DEIA W31L125 VPC O	28.5 W
10440200	RC342B 42S/940 DEIA W31L125 VPC O	33.5 W
10250700	RC340B 36S/940 DIA W60L60 VPC O ELP3	28.5 W
10263700	RC340B 42S/940 PSE W60L60 VPC O	33.5 W
10264400	RC340B 42S/940 DEIA W60L60 VPC O	33.5 W
10269900	RC340B 42S/940 DIA W60L60 VPC O ELP3	33.5 W
10274300	RC340B 42S/940 DIA W60L60 VPC O ELD3	33.5 W
10323800	RC340B 36S/940 PSE W60L60 VPC O SC	28.5 W
10324500	RC340B 36S/940 DEIA W60L60 VPC O SC	28.5 W
10232300	RC340B 36S/940 DEIA W60L60 VPC MLO	38 W
10308500	RC340B 36S/940 PSE W60L60 CPC MLO	38 W
10309200	RC340B 42S/940 PSE W60L60 CPC MLO	45 W
10310800	RC340B 42S/940 DEIA W60L60 CPC MLO	45 W
10428000	RC342B 42S/940 DEIA W62L62 CPC PCS	30.5 W
10230900	RC340B 36S/940 DEIA W60L60 VPC O	28.5 W
10235400	RC340B 36S/940 PSE W60L60 VPC PCS	26 W
10236100	RC340B 36S/940 DEIA W60L60 VPC PCS	26 W
10240800	RC340B 36S/940 DEIA W60L60 CPC MLO	38 W
10254500	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	26 W
10260600	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	26 W
10265100	RC340B 42S/940 PSE W60L60 VPC PCS	30.5 W
10266800	RC340B 42S/940 DEIA W60L60 VPC PCS	30.5 W
10271200	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	30.5 W
10306100	RC340B 36S/940 PSE W60L60 CPC PCS PIP	26 W
10307800	RC340B 36S/940 DEIA W60L60 CPC PCS	26 W
10311500	RC340B 42S/940 PSE W60L60 CPC PCS	30.5 W
10312200	RC340B 42S/940 DEIA W60L60 CPC PCS	30.5 W
10327600	RC340B 36S/940 PSE W60L60 VPC PCS SC	26 W
10328300	RC340B 36S/940 DEIA W60L60 VPC PCS SC	26 W
10229300	RC340B 36S/940 PSE W60L60 VPC O	28.5 W
10243900	RC342B 36S/940 PSE W62L62 VPC MLO	37 W
10252100	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	38 W
10256900	RC340B 36S/940 DIA W60L60 VPC O ELD3	28.5 W
10258300	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	38 W
10262000	RC340B 42S/940 DEIA W60L60 VPC MLO	45 W
10272900	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	45 W
10305400	RC340B 42S/940 PSE W60L60 VPC MLO	45 W
10325200	RC340B 36S/940 PSE W60L60 VPC MLO SC	38 W
10326900	RC340B 36S/940 DEIA W60L60 VPC MLO SC	38 W
10276700	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	30.5 W
10231600	RC340B 36S/940 PSE W60L60 VPC MLO PIP	38 W

Order Code	Full Product Name	Power Consumption
10241500	RC340B 36S/940 DEIA W60L60 PCV MLO	38 W
10244600	RC342B 36S/940 DEIA W62L62 VPC MLO	38 W
10406800	RC342B 28S/940 DEIA W62L62 VPC MLO	25.5 W
10419800	RC342B 28S/940 DEIA W62L62 VPC PCS	22 W
10420400	RC342B 36S/940 DEIA W62L62 VPC PCS	25 W
10421100	RC342B 42S/940 DEIA W62L62 VPC PCS	30.5 W
10435800	RC342B 28S/940 DEIA W62L62 VPC O	22.5 W
10436500	RC342B 36S/940 DEIA W62L62 VPC O	28.5 W
10437200	RC342B 42S/940 DEIA W62L62 VPC O	33.5 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
10277400	RC340B 36S/940 PSE W15L120 VPC MLO	No
10278100	RC340B 36S/940 DEIA W15L120 VPC MLO	Yes
10279800	RC340B 42S/940 PSE W15L120 VPC MLO	No
10280400	RC340B 42S/940 DEIA W15L120 VPC MLO	Yes
10282800	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	Yes
10284200	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	Yes
10286600	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	Yes
10288000	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	Yes
10410500	RC342B 28S/940 DEIA W15L125 VPC MLO	Yes
10411200	RC342B 36S/940 DEIA W15L125 VPC MLO	Yes
10414300	RC342B 36S/940 DEIA W17L125 PCV MLO	Yes
10425900	RC342B 28S/940 DEIA W15L125 VPC PCS	Yes
10426600	RC342B 36S/940 DEIA W15L125 VPC PCS	Yes
10427300	RC342B 42S/940 DEIA W15L125 VPC PCS	Yes
10430300	RC342B 36S/940 DEIA W17L125 PCV PCS	Yes
10441900	RC342B 28S/940 DEIA W15L125 VPC O	Yes
10442600	RC342B 36S/940 DEIA W15L125 VPC O	Yes
10443300	RC342B 42S/940 DEIA W15L125 VPC O	Yes
10242200	RC340B 36S/940 DEIA W30L120 VPC MLO	Yes
10245300	RC342B 36S/940 PSE W31L125 VPC MLO	No
10246000	RC342B 36S/940 DEIA W31L125 VPC MLO	Yes
10408200	RC342B 28S/940 DEIA W31L125 VPC MLO	Yes
10422800	RC342B 28S/940 DEIA W31L125 VPC PCS	Yes
10423500	RC342B 36S/940 DEIA W31L125 VPC PCS	Yes
10424200	RC342B 42S/940 DEIA W31L125 VPC PCS	Yes
10438900	RC342B 28S/940 DEIA W31L125 VPC O	Yes
10439600	RC342B 36S/940 DEIA W31L125 VPC O	Yes
10440200	RC342B 42S/940 DEIA W31L125 VPC O	Yes
10250700	RC340B 36S/940 DIA W60L60 VPC O ELP3	Yes

Order Code	Full Product Name	Dimmable
10263700	RC340B 42S/940 PSE W60L60 VPC O	No
10264400	RC340B 42S/940 DEIA W60L60 VPC O	Yes
10269900	RC340B 42S/940 DIA W60L60 VPC O ELP3	Yes
10274300	RC340B 42S/940 DIA W60L60 VPC O ELD3	Yes
10323800	RC340B 36S/940 PSE W60L60 VPC O SC	No
10324500	RC340B 36S/940 DEIA W60L60 VPC O SC	Yes
10232300	RC340B 36S/940 DEIA W60L60 VPC MLO	Yes
10308500	RC340B 36S/940 PSE W60L60 CPC MLO	No
10309200	RC340B 42S/940 PSE W60L60 CPC MLO	No
10310800	RC340B 42S/940 DEIA W60L60 CPC MLO	Yes
10428000	RC342B 42S/940 DEIA W62L62 CPC PCS	Yes
10230900	RC340B 36S/940 DEIA W60L60 VPC O	Yes
10235400	RC340B 36S/940 PSE W60L60 VPC PCS	No
10236100	RC340B 36S/940 DEIA W60L60 VPC PCS	Yes
10240800	RC340B 36S/940 DEIA W60L60 CPC MLO	Yes
10254500	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	Yes
10260600	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	Yes
10265100	RC340B 42S/940 PSE W60L60 VPC PCS	No
10266800	RC340B 42S/940 DEIA W60L60 VPC PCS	Yes
10271200	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	Yes
10306100	RC340B 36S/940 PSE W60L60 CPC PCS PIP	No
10307800	RC340B 36S/940 DEIA W60L60 CPC PCS	Yes
10311500	RC340B 42S/940 PSE W60L60 CPC PCS	No
10312200	RC340B 42S/940 DEIA W60L60 CPC PCS	Yes
10327600	RC340B 36S/940 PSE W60L60 VPC PCS SC	No
10328300	RC340B 36S/940 DEIA W60L60 VPC PCS SC	Yes
10229300	RC340B 36S/940 PSE W60L60 VPC O	No
10243900	RC342B 36S/940 PSE W62L62 VPC MLO	No
10252100	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	Yes
10256900	RC340B 36S/940 DIA W60L60 VPC O ELD3	Yes
10258300	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	Yes
10262000	RC340B 42S/940 DEIA W60L60 VPC MLO	Yes
10272900	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	Yes
10305400	RC340B 42S/940 PSE W60L60 VPC MLO	No
10325200	RC340B 36S/940 PSE W60L60 VPC MLO SC	No
10326900	RC340B 36S/940 DEIA W60L60 VPC MLO SC	Yes
10276700	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	Yes
10231600	RC340B 36S/940 PSE W60L60 VPC MLO PIP	No
10241500	RC340B 36S/940 DEIA W60L60 PCV MLO	Yes
10244600	RC342B 36S/940 DEIA W62L62 VPC MLO	Yes
10406800	RC342B 28S/940 DEIA W62L62 VPC MLO	Yes
10419800	RC342B 28S/940 DEIA W62L62 VPC PCS	Yes

Order Code	Full Product Name	Dimmable
10420400	RC342B 36S/940 DEIA W62L62 VPC PCS	Yes
10421100	RC342B 42S/940 DEIA W62L62 VPC PCS	Yes
10435800	RC342B 28S/940 DEIA W62L62 VPC O	Yes
10436500	RC342B 36S/940 DEIA W62L62 VPC O	Yes
10437200	RC342B 42S/940 DEIA W62L62 VPC O	Yes

Mechanical and Housing

Order Code	Full Product Name	Ingress protection code
10277400	RC340B 36S/940 PSE W15L120 VPC MLO	IP20/40
10278100	RC340B 36S/940 DEIA W15L120 VPC MLO	IP20/40
10279800	RC340B 42S/940 PSE W15L120 VPC MLO	IP20/40
10280400	RC340B 42S/940 DEIA W15L120 VPC MLO	IP20/40
10282800	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	IP20
10284200	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	IP20
10286600	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	IP20
10288000	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	IP20
10410500	RC342B 28S/940 DEIA W15L125 VPC MLO	IP20/40
10411200	RC342B 36S/940 DEIA W15L125 VPC MLO	IP20/40
10414300	RC342B 36S/940 DEIA W17L125 PCV MLO	IP20/40
10425900	RC342B 28S/940 DEIA W15L125 VPC PCS	IP20/54
10426600	RC342B 36S/940 DEIA W15L125 VPC PCS	IP20/54
10427300	RC342B 42S/940 DEIA W15L125 VPC PCS	IP20/54
10430300	RC342B 36S/940 DEIA W17L125 PCV PCS	IP20/54
10441900	RC342B 28S/940 DEIA W15L125 VPC O	IP20/54
10442600	RC342B 36S/940 DEIA W15L125 VPC O	IP20/54
10443300	RC342B 42S/940 DEIA W15L125 VPC O	IP20/54
10242200	RC340B 36S/940 DEIA W30L120 VPC MLO	IP20/40
10245300	RC342B 36S/940 PSE W31L125 VPC MLO	IP20/40
10246000	RC342B 36S/940 DEIA W31L125 VPC MLO	IP20/40
10408200	RC342B 28S/940 DEIA W31L125 VPC MLO	IP20/40
10422800	RC342B 28S/940 DEIA W31L125 VPC PCS	IP20/54
10423500	RC342B 36S/940 DEIA W31L125 VPC PCS	IP20/54
10424200	RC342B 42S/940 DEIA W31L125 VPC PCS	IP20/54
10438900	RC342B 28S/940 DEIA W31L125 VPC O	IP20/54
10439600	RC342B 36S/940 DEIA W31L125 VPC O	IP20/54
10440200	RC342B 42S/940 DEIA W31L125 VPC O	IP20/54
10250700	RC340B 36S/940 DIA W60L60 VPC O ELP3	IP54
10263700	RC340B 42S/940 PSE W60L60 VPC O	IP20/54
10264400	RC340B 42S/940 DEIA W60L60 VPC O	IP20/54
10269900	RC340B 42S/940 DIA W60L60 VPC O ELP3	IP20/54
10274300	RC340B 42S/940 DIA W60L60 VPC O ELD3	IP54

Order Code	Full Product Name	Ingress protection code
10323800	RC340B 36S/940 PSE W60L60 VPC O SC	IP20/54
10324500	RC340B 36S/940 DEIA W60L60 VPC O SC	IP20/54
10232300	RC340B 36S/940 DEIA W60L60 VPC MLO	IP20/40
10308500	RC340B 36S/940 PSE W60L60 CPC MLO	IP20/40
10309200	RC340B 42S/940 PSE W60L60 CPC MLO	IP20/40
10310800	RC340B 42S/940 DEIA W60L60 CPC MLO	IP20/40
10428000	RC342B 42S/940 DEIA W62L62 CPC PCS	IP20/54
10230900	RC340B 36S/940 DEIA W60L60 VPC O	IP20/54
10235400	RC340B 36S/940 PSE W60L60 VPC PCS	IP20/54
10236100	RC340B 36S/940 DEIA W60L60 VPC PCS	IP20/54
10240800	RC340B 36S/940 DEIA W60L60 CPC MLO	IP20/40
10254500	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	IP20/54
10260600	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	IP20/54
10265100	RC340B 42S/940 PSE W60L60 VPC PCS	IP20/54
10266800	RC340B 42S/940 DEIA W60L60 VPC PCS	IP20/54
10271200	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	IP20/54
10306100	RC340B 36S/940 PSE W60L60 CPC PCS PIP	IP20/54
10307800	RC340B 36S/940 DEIA W60L60 CPC PCS	IP20/54
10311500	RC340B 42S/940 PSE W60L60 CPC PCS	IP20/54
10312200	RC340B 42S/940 DEIA W60L60 CPC PCS	IP20/54
10327600	RC340B 36S/940 PSE W60L60 VPC PCS SC	IP20/54
10328300	RC340B 36S/940 DEIA W60L60 VPC PCS SC	IP20/54
10229300	RC340B 36S/940 PSE W60L60 VPC O	IP20/54
10243900	RC342B 36S/940 PSE W62L62 VPC MLO	IP20/40
10252100	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	IP20/54
10256900	RC340B 36S/940 DIA W60L60 VPC O ELD3	IP54
10258300	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	IP20/54
10262000	RC340B 42S/940 DEIA W60L60 VPC MLO	IP20/40
10272900	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	IP20
10305400	RC340B 42S/940 PSE W60L60 VPC MLO	IP20/40
10325200	RC340B 36S/940 PSE W60L60 VPC MLO SC	IP20/40
10326900	RC340B 36S/940 DEIA W60L60 VPC MLO SC	IP20/40
10276700	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	IP20/54
10231600	RC340B 36S/940 PSE W60L60 VPC MLO PIP	IP20/40
10241500	RC340B 36S/940 DEIA W60L60 PCV MLO	IP20/40
10244600	RC342B 36S/940 DEIA W62L62 VPC MLO	IP20/40
10406800	RC342B 28S/940 DEIA W62L62 VPC MLO	IP20/40
10419800	RC342B 28S/940 DEIA W62L62 VPC PCS	IP20/54
10420400	RC342B 36S/940 DEIA W62L62 VPC PCS	IP20/54
10421100	RC342B 42S/940 DEIA W62L62 VPC PCS	IP20/54
10435800	RC342B 28S/940 DEIA W62L62 VPC O	IP20/54
10436500	RC342B 36S/940 DEIA W62L62 VPC O	IP20/54
10437200	RC342B 42S/940 DEIA W62L62 VPC O	IP20/54

Emergency Operation

Order Code	Full Product Name	Central Emergency	Emergency lighting
10277400	RC340B 36S/940 PSE W15L120 VPC MLO	-	-
10278100	RC340B 36S/940 DEIA W15L120 VPC MLO	Yes	DC operated central emergency lighting
10279800	RC340B 42S/940 PSE W15L120 VPC MLO	-	-
10280400	RC340B 42S/940 DEIA W15L120 VPC MLO	Yes	DC operated central emergency lighting
10282800	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	No	Emergency lighting 3 hours duration Pro version
10284200	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	No	Emergency lighting 3 hours duration Pro version
10286600	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	No	Emergency lighting 3 hours duration Pro version
10288000	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	No	Emergency lighting 3 hours duration Pro version
10410500	RC342B 28S/940 DEIA W15L125 VPC MLO	Yes	DC operated central emergency lighting
10411200	RC342B 36S/940 DEIA W15L125 VPC MLO	Yes	DC operated central emergency lighting
10414300	RC342B 36S/940 DEIA W17L125 PCV MLO	Yes	DC operated central emergency lighting
10425900	RC342B 28S/940 DEIA W15L125 VPC PCS	Yes	DC operated central emergency lighting
10426600	RC342B 36S/940 DEIA W15L125 VPC PCS	Yes	DC operated central emergency lighting
10427300	RC342B 42S/940 DEIA W15L125 VPC PCS	Yes	DC operated central emergency lighting
10430300	RC342B 36S/940 DEIA W17L125 PCV PCS	Yes	DC operated central emergency lighting
10441900	RC342B 28S/940 DEIA W15L125 VPC O	Yes	DC operated central emergency lighting
10442600	RC342B 36S/940 DEIA W15L125 VPC O	Yes	DC operated central emergency lighting
10443300	RC342B 42S/940 DEIA W15L125 VPC O	Yes	DC operated central emergency lighting
10242200	RC340B 36S/940 DEIA W30L120 VPC MLO	Yes	DC operated central emergency lighting
10245300	RC342B 36S/940 PSE W31L125 VPC MLO	-	-
10246000	RC342B 36S/940 DEIA W31L125 VPC MLO	Yes	DC operated central emergency lighting
10408200	RC342B 28S/940 DEIA W31L125 VPC MLO	Yes	DC operated central emergency lighting
10422800	RC342B 28S/940 DEIA W31L125 VPC PCS	Yes	DC operated central emergency lighting
10423500	RC342B 36S/940 DEIA W31L125 VPC PCS	Yes	DC operated central emergency lighting
10424200	RC342B 42S/940 DEIA W31L125 VPC PCS	Yes	DC operated central emergency lighting
10438900	RC342B 28S/940 DEIA W31L125 VPC O	Yes	DC operated central emergency lighting
10439600	RC342B 36S/940 DEIA W31L125 VPC O	Yes	DC operated central emergency lighting
10440200	RC342B 42S/940 DEIA W31L125 VPC O	Yes	DC operated central emergency lighting
10250700	RC340B 36S/940 DIA W60L60 VPC O ELP3	No	Emergency lighting 3 hours duration Pro version
10263700	RC340B 42S/940 PSE W60L60 VPC O	-	-
10264400	RC340B 42S/940 DEIA W60L60 VPC O	Yes	DC operated central emergency lighting
10269900	RC340B 42S/940 DIA W60L60 VPC O ELP3	No	Emergency lighting 3 hours duration Pro version
10274300	RC340B 42S/940 DIA W60L60 VPC O ELD3	No	Emergency lighting 3 hours duration with DALI interface
10323800	RC340B 36S/940 PSE W60L60 VPC O SC	-	-
10324500	RC340B 36S/940 DEIA W60L60 VPC O SC	Yes	DC operated central emergency lighting
10232300	RC340B 36S/940 DEIA W60L60 VPC MLO	Yes	DC operated central emergency lighting
10308500	RC340B 36S/940 PSE W60L60 CPC MLO	-	-
10309200	RC340B 42S/940 PSE W60L60 CPC MLO	-	-
10310800	RC340B 42S/940 DEIA W60L60 CPC MLO	Yes	DC operated central emergency lighting
10428000	RC342B 42S/940 DEIA W62L62 CPC PCS	Yes	DC operated central emergency lighting
10230900	RC340B 36S/940 DEIA W60L60 VPC O	Yes	DC operated central emergency lighting

Order Code	Full Product Name	Central Emergency	Emergency lighting
10235400	RC340B 36S/940 PSE W60L60 VPC PCS	-	-
10236100	RC340B 36S/940 DEIA W60L60 VPC PCS	Yes	DC operated central emergency lighting
10240800	RC340B 36S/940 DEIA W60L60 CPC MLO	Yes	DC operated central emergency lighting
10254500	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	No	Emergency lighting 3 hours duration Pro version
10260600	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	No	Emergency lighting 3 hours duration with DALI interface
10265100	RC340B 42S/940 PSE W60L60 VPC PCS	-	-
10266800	RC340B 42S/940 DEIA W60L60 VPC PCS	Yes	DC operated central emergency lighting
10271200	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	No	Emergency lighting 3 hours duration Pro version
10306100	RC340B 36S/940 PSE W60L60 CPC PCS PIP	-	-
10307800	RC340B 36S/940 DEIA W60L60 CPC PCS	Yes	DC operated central emergency lighting
10311500	RC340B 42S/940 PSE W60L60 CPC PCS	-	-
10312200	RC340B 42S/940 DEIA W60L60 CPC PCS	Yes	DC operated central emergency lighting
10327600	RC340B 36S/940 PSE W60L60 VPC PCS SC	-	-
10328300	RC340B 36S/940 DEIA W60L60 VPC PCS SC	Yes	DC operated central emergency lighting
10229300	RC340B 36S/940 PSE W60L60 VPC O	-	-
10243900	RC342B 36S/940 PSE W62L62 VPC MLO	-	-
10252100	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	No	Emergency lighting 3 hours duration Pro version
10256900	RC340B 36S/940 DIA W60L60 VPC O ELD3	No	Emergency lighting 3 hours duration with DALI interface
10258300	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	No	Emergency lighting 3 hours duration with DALI interface
10262000	RC340B 42S/940 DEIA W60L60 VPC MLO	Yes	DC operated central emergency lighting
10272900	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	No	Emergency lighting 3 hours duration with DALI interface
10305400	RC340B 42S/940 PSE W60L60 VPC MLO	-	-
10325200	RC340B 36S/940 PSE W60L60 VPC MLO SC	-	-
10326900	RC340B 36S/940 DEIA W60L60 VPC MLO SC	Yes	DC operated central emergency lighting
10276700	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	No	Emergency lighting 3 hours duration with DALI interface
10231600	RC340B 36S/940 PSE W60L60 VPC MLO PIP	-	-
10241500	RC340B 36S/940 DEIA W60L60 PCV MLO	Yes	DC operated central emergency lighting
10244600	RC342B 36S/940 DEIA W62L62 VPC MLO	Yes	DC operated central emergency lighting
10406800	RC342B 28S/940 DEIA W62L62 VPC MLO	Yes	DC operated central emergency lighting
10419800	RC342B 28S/940 DEIA W62L62 VPC PCS	Yes	DC operated central emergency lighting
10420400	RC342B 36S/940 DEIA W62L62 VPC PCS	Yes	DC operated central emergency lighting
10421100	RC342B 42S/940 DEIA W62L62 VPC PCS	Yes	DC operated central emergency lighting
10435800	RC342B 28S/940 DEIA W62L62 VPC O	Yes	DC operated central emergency lighting
10436500	RC342B 36S/940 DEIA W62L62 VPC O	Yes	DC operated central emergency lighting
10437200	RC342B 42S/940 DEIA W62L62 VPC O	Yes	DC operated central emergency lighting

Approval and Application

Order Code	Full Product Name	Glow-wire test
10277400	RC340B 36S/940 PSE W15L120 VPC MLO	Temperature 650 °C, duration 30 s
10278100	RC340B 36S/940 DEIA W15L120 VPC MLO	Temperature 650 °C, duration 30 s
10279800	RC340B 42S/940 PSE W15L120 VPC MLO	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Glow-wire test
10280400	RC340B 42S/940 DEIA W15L120 VPC MLO	Temperature 650 °C, duration 30 s
10282800	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	Temperature 650 °C, duration 30 s
10284200	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	Temperature 650 °C, duration 30 s
10286600	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	Temperature 650 °C, duration 30 s
10288000	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	Temperature 650 °C, duration 30 s
10410500	RC342B 28S/940 DEIA W15L125 VPC MLO	Temperature 650 °C, duration 30 s
10411200	RC342B 36S/940 DEIA W15L125 VPC MLO	Temperature 650 °C, duration 30 s
10414300	RC342B 36S/940 DEIA W17L125 PCV MLO	Temperature 650 °C, duration 30 s
10425900	RC342B 28S/940 DEIA W15L125 VPC PCS	Temperature 850 °C, duration 30 s
10426600	RC342B 36S/940 DEIA W15L125 VPC PCS	Temperature 850 °C, duration 30 s
10427300	RC342B 42S/940 DEIA W15L125 VPC PCS	Temperature 850 °C, duration 30 s
10430300	RC342B 36S/940 DEIA W17L125 PCV PCS	Temperature 850 °C, duration 30 s
10441900	RC342B 28S/940 DEIA W15L125 VPC O	Temperature 850 °C, duration 30 s
10442600	RC342B 36S/940 DEIA W15L125 VPC O	Temperature 850 °C, duration 30 s
10443300	RC342B 42S/940 DEIA W15L125 VPC O	Temperature 850 °C, duration 30 s
10242200	RC340B 36S/940 DEIA W30L120 VPC MLO	Temperature 650 °C, duration 30 s
10245300	RC342B 36S/940 PSE W31L125 VPC MLO	Temperature 650 °C, duration 30 s
10246000	RC342B 36S/940 DEIA W31L125 VPC MLO	Temperature 650 °C, duration 30 s
10408200	RC342B 28S/940 DEIA W31L125 VPC MLO	Temperature 650 °C, duration 30 s
10422800	RC342B 28S/940 DEIA W31L125 VPC PCS	Temperature 850 °C, duration 30 s
10423500	RC342B 36S/940 DEIA W31L125 VPC PCS	Temperature 850 °C, duration 30 s
10424200	RC342B 42S/940 DEIA W31L125 VPC PCS	Temperature 850 °C, duration 30 s
10438900	RC342B 28S/940 DEIA W31L125 VPC O	Temperature 850 °C, duration 30 s
10439600	RC342B 36S/940 DEIA W31L125 VPC O	Temperature 850 °C, duration 30 s
10440200	RC342B 42S/940 DEIA W31L125 VPC O	Temperature 850 °C, duration 30 s
10250700	RC340B 36S/940 DIA W60L60 VPC O ELP3	Temperature 850 °C, duration 30 s
10263700	RC340B 42S/940 PSE W60L60 VPC O	Temperature 850 °C, duration 30 s
10264400	RC340B 42S/940 DEIA W60L60 VPC O	Temperature 850 °C, duration 30 s
10269900	RC340B 42S/940 DIA W60L60 VPC O ELP3	Temperature 850 °C, duration 30 s
10274300	RC340B 42S/940 DIA W60L60 VPC O ELD3	Temperature 850 °C, duration 30 s
10323800	RC340B 36S/940 PSE W60L60 VPC O SC	Temperature 850 °C, duration 30 s
10324500	RC340B 36S/940 DEIA W60L60 VPC O SC	Temperature 850 °C, duration 30 s
10232300	RC340B 36S/940 DEIA W60L60 VPC MLO	Temperature 650 °C, duration 30 s
10308500	RC340B 36S/940 PSE W60L60 CPC MLO	Temperature 650 °C, duration 30 s
10309200	RC340B 42S/940 PSE W60L60 CPC MLO	Temperature 650 °C, duration 30 s
10310800	RC340B 42S/940 DEIA W60L60 CPC MLO	Temperature 650 °C, duration 30 s
10428000	RC342B 42S/940 DEIA W62L62 CPC PCS	Temperature 850 °C, duration 30 s
10230900	RC340B 36S/940 DEIA W60L60 VPC O	Temperature 850 °C, duration 30 s
10235400	RC340B 36S/940 PSE W60L60 VPC PCS	Temperature 850 °C, duration 30 s
10236100	RC340B 36S/940 DEIA W60L60 VPC PCS	Temperature 850 °C, duration 30 s
10240800	RC340B 36S/940 DEIA W60L60 CPC MLO	Temperature 650 °C, duration 30 s
10254500	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	Temperature 850 °C, duration 30 s

Order Code	Full Product Name	Glow-wire test
10260600	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	Temperature 850 °C, duration 30 s
10265100	RC340B 42S/940 PSE W60L60 VPC PCS	Temperature 850 °C, duration 30 s
10266800	RC340B 42S/940 DEIA W60L60 VPC PCS	Temperature 850 °C, duration 30 s
10271200	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	Temperature 850 °C, duration 30 s
10306100	RC340B 36S/940 PSE W60L60 CPC PCS PIP	Temperature 850 °C, duration 30 s
10307800	RC340B 36S/940 DEIA W60L60 CPC PCS	Temperature 850 °C, duration 30 s
10311500	RC340B 42S/940 PSE W60L60 CPC PCS	Temperature 850 °C, duration 30 s
10312200	RC340B 42S/940 DEIA W60L60 CPC PCS	Temperature 850 °C, duration 30 s
10327600	RC340B 36S/940 PSE W60L60 VPC PCS SC	Temperature 850 °C, duration 30 s
10328300	RC340B 36S/940 DEIA W60L60 VPC PCS SC	Temperature 850 °C, duration 30 s
10229300	RC340B 36S/940 PSE W60L60 VPC O	Temperature 850 °C, duration 30 s
10243900	RC342B 36S/940 PSE W62L62 VPC MLO	Temperature 650 °C, duration 30 s
10252100	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	Temperature 650 °C, duration 30 s
10256900	RC340B 36S/940 DIA W60L60 VPC O ELD3	Temperature 850 °C, duration 30 s
10258300	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	Temperature 650 °C, duration 30 s
10262000	RC340B 42S/940 DEIA W60L60 VPC MLO	Temperature 650 °C, duration 30 s
10272900	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	Temperature 650 °C, duration 30 s
10305400	RC340B 42S/940 PSE W60L60 VPC MLO	Temperature 650 °C, duration 30 s
10325200	RC340B 36S/940 PSE W60L60 VPC MLO SC	Temperature 650 °C, duration 30 s
10326900	RC340B 36S/940 DEIA W60L60 VPC MLO SC	Temperature 650 °C, duration 30 s
10276700	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	Temperature 850 °C, duration 30 s
10231600	RC340B 36S/940 PSE W60L60 VPC MLO PIP	Temperature 650 °C, duration 30 s
10241500	RC340B 36S/940 DEIA W60L60 PCV MLO	Temperature 650 °C, duration 30 s
10244600	RC342B 36S/940 DEIA W62L62 VPC MLO	Temperature 650 °C, duration 30 s
10406800	RC342B 28S/940 DEIA W62L62 VPC MLO	Temperature 650 °C, duration 30 s
10419800	RC342B 28S/940 DEIA W62L62 VPC PCS	Temperature 850 °C, duration 30 s
10420400	RC342B 36S/940 DEIA W62L62 VPC PCS	Temperature 850 °C, duration 30 s
10421100	RC342B 42S/940 DEIA W62L62 VPC PCS	Temperature 850 °C, duration 30 s
10435800	RC342B 28S/940 DEIA W62L62 VPC O	Temperature 850 °C, duration 30 s
10436500	RC342B 36S/940 DEIA W62L62 VPC O	Temperature 850 °C, duration 30 s
10437200	RC342B 42S/940 DEIA W62L62 VPC O	Temperature 850 °C, duration 30 s


Product Data

Order Code	Full Product Name	Product family code
10277400	RC340B 36S/940 PSE W15L120 VPC MLO	RC340B
10278100	RC340B 36S/940 DEIA W15L120 VPC MLO	RC340B
10279800	RC340B 42S/940 PSE W15L120 VPC MLO	RC340B
10280400	RC340B 42S/940 DEIA W15L120 VPC MLO	RC340B
10282800	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	RC340B
10284200	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	RC340B
10286600	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	RC340B


Order Code	Full Product Name	Product family code
10288000	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	RC340B
10410500	RC342B 28S/940 DEIA W15L125 VPC MLO	RC342B
10411200	RC342B 36S/940 DEIA W15L125 VPC MLO	RC342B
10414300	RC342B 36S/940 DEIA W17L125 PCV MLO	RC342B
10425900	RC342B 28S/940 DEIA W15L125 VPC PCS	RC342B
10426600	RC342B 36S/940 DEIA W15L125 VPC PCS	RC342B
10427300	RC342B 42S/940 DEIA W15L125 VPC PCS	RC342B
10430300	RC342B 36S/940 DEIA W17L125 PCV PCS	RC342B
10441900	RC342B 28S/940 DEIA W15L125 VPC O	RC342B
10442600	RC342B 36S/940 DEIA W15L125 VPC O	RC342B
10443300	RC342B 42S/940 DEIA W15L125 VPC O	RC342B
10242200	RC340B 36S/940 DEIA W30L120 VPC MLO	RC340B
10245300	RC342B 36S/940 PSE W31L125 VPC MLO	RC342B
10246000	RC342B 36S/940 DEIA W31L125 VPC MLO	RC342B
10408200	RC342B 28S/940 DEIA W31L125 VPC MLO	RC342B
10422800	RC342B 28S/940 DEIA W31L125 VPC PCS	RC342B
10423500	RC342B 36S/940 DEIA W31L125 VPC PCS	RC342B
10424200	RC342B 42S/940 DEIA W31L125 VPC PCS	RC342B
10438900	RC342B 28S/940 DEIA W31L125 VPC O	RC342B
10439600	RC342B 36S/940 DEIA W31L125 VPC O	RC342B
10440200	RC342B 42S/940 DEIA W31L125 VPC O	RC342B
10250700	RC340B 36S/940 DIA W60L60 VPC O ELP3	RC340B
10263700	RC340B 42S/940 PSE W60L60 VPC O	RC340B
10264400	RC340B 42S/940 DEIA W60L60 VPC O	RC340B
10269900	RC340B 42S/940 DIA W60L60 VPC O ELP3	RC340B
10274300	RC340B 42S/940 DIA W60L60 VPC O ELD3	RC340B
10323800	RC340B 36S/940 PSE W60L60 VPC O SC	RC340B
10324500	RC340B 36S/940 DEIA W60L60 VPC O SC	RC340B
10232300	RC340B 36S/940 DEIA W60L60 VPC MLO	RC340B
10308500	RC340B 36S/940 PSE W60L60 CPC MLO	RC340B
10309200	RC340B 42S/940 PSE W60L60 CPC MLO	RC340B
10310800	RC340B 42S/940 DEIA W60L60 CPC MLO	RC340B
10428000	RC342B 42S/940 DEIA W62L62 CPC PCS	RC342B
10230900	RC340B 36S/940 DEIA W60L60 VPC O	RC340B
10235400	RC340B 36S/940 PSE W60L60 VPC PCS	RC340B
10236100	RC340B 36S/940 DEIA W60L60 VPC PCS	RC340B
10240800	RC340B 36S/940 DEIA W60L60 CPC MLO	RC340B
10254500	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	RC340B
10260600	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	RC340B
10265100	RC340B 42S/940 PSE W60L60 VPC PCS	RC340B
10266800	RC340B 42S/940 DEIA W60L60 VPC PCS	RC340B
10271200	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	RC340B

Order Code	Full Product Name	Product family code
10306100	RC340B 36S/940 PSE W60L60 CPC PCS PIP	RC340B
10307800	RC340B 36S/940 DEIA W60L60 CPC PCS	RC340B
10311500	RC340B 42S/940 PSE W60L60 CPC PCS	RC340B
10312200	RC340B 42S/940 DEIA W60L60 CPC PCS	RC340B
10327600	RC340B 36S/940 PSE W60L60 VPC PCS SC	RC340B
10328300	RC340B 36S/940 DEIA W60L60 VPC PCS SC	RC340B
10229300	RC340B 36S/940 PSE W60L60 VPC O	RC340B
10243900	RC342B 36S/940 PSE W62L62 VPC MLO	RC342B
10252100	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	RC340B
10256900	RC340B 36S/940 DIA W60L60 VPC O ELD3	RC340B
10258300	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	RC340B
10262000	RC340B 42S/940 DEIA W60L60 VPC MLO	RC340B
10272900	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	RC340B
10305400	RC340B 42S/940 PSE W60L60 VPC MLO	RC340B
10325200	RC340B 36S/940 PSE W60L60 VPC MLO SC	RC340B
10326900	RC340B 36S/940 DEIA W60L60 VPC MLO SC	RC340B
10276700	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	RC340B
10231600	RC340B 36S/940 PSE W60L60 VPC MLO PIP	RC340B
10241500	RC340B 36S/940 DEIA W60L60 PCV MLO	RC340B
10244600	RC342B 36S/940 DEIA W62L62 VPC MLO	RC342B
10406800	RC342B 28S/940 DEIA W62L62 VPC MLO	RC342B
10419800	RC342B 28S/940 DEIA W62L62 VPC PCS	RC342B
10420400	RC342B 36S/940 DEIA W62L62 VPC PCS	RC342B
10421100	RC342B 42S/940 DEIA W62L62 VPC PCS	RC342B
10435800	RC342B 28S/940 DEIA W62L62 VPC O	RC342B
10436500	RC342B 36S/940 DEIA W62L62 VPC O	RC342B
10437200	RC342B 42S/940 DEIA W62L62 VPC O	RC342B


Polar normal diagrams




RC340BI - 910925866978




RC340BI - 910925866989




RC340BI - 910925866987




RC340BI - 910925866969




RC340BI - 910925866968




RC340BI - 910925866979




RC340BI - 910925866981




RC340BI - 910925867050




RC340BI - 910925866973




RC340BI - 910925866991




RC340BI - 910925866993




RC340BI - 910925867002




RC340BI - 910925867003




RC340BI - 910925866977




RC340BI - 910925866995




RC340BI - 910925867012




RC340BI - 910925867017




RC340BI - 910925867024




RC340BI - 910925867043




RC340BI - 910925867049




RC340BI - 910925866967




RC340BI - 910925867010




RC340BI - 910925867022




RC340BI - 910925867064




RC340BI - 910925866980




RC340BI - 910925866982




RC340BI - 910925866983




RC340BI - 910925866997




RC340BI - 910925867009




RC340BI - 910925867047




RC340BI - 910925867062




RC340BI - 910925867063




RC340BI - 910925866966




RC340BI - 910925867018




RC340BI - 910925867016




RC340BI - 910925867014




RC340BI - 910925867145




RC340BI - 910925867147




RC340BI - 910925867020




RC340BI - 910925867026




RC340BI - 910925867044




RC340BI - 910925867045




RC340BI - 910925867048




RC340BI - 910925867065




RC340BI - 910925867149




RC340BI - 910925867159




RC340BI - 910925867158




RC340BI - 910925867165




RC340BI - 910925867166




RC340BI - 910925867167




RC340BI - 910925867177




RC340BI - 910925867178




RC340BI - 910925867066




RC340BI - 910925867162




RC340BI - 910925867160




RC340BI - 910925867153




RC340BI - 910925867175




RC340BI - 910925867179




RC340BI - 910925867182




RC340BI - 910925867163




RC340BI - 910925867174




RC340BI - 910925867176




RC340BI - 910925866972




RC340BI - 910925866999




RC340BI - 910925867001




RC340BI - 910925867004




RC340BI - 910925867007




RC340BI - 910925867015




RC340BI - 910925867046




RC340BI - 910925867061




RC340BI - 910925867150




RC340BI - 910925867161




RC340BI - 910925867164



RC340BI - 910925867169



RC340BI - 910925867181



RC340BI - 910925867180