




FlexBlend - Unlocking the potential of LED lighting in offices

Office owners and staff responsible for lighting operations are searching for high quality yet energy-efficient lighting that complies with norms and regulations. Designed to support these needs, Philips FlexBlend is enabling building owners to fully optimize their lighting operations, by offering office-compliant lighting with an attractive return on investment. Furthermore, FlexBlend provides the required flexibility by being easy applied on different ceiling types as well as in different office spaces like open office or meeting rooms. Though technology is changing fast, the ideal lighting solution is also expected to be ready to incorporate innovations and future advances that can help optimize operations further. For this reason, Philips FlexBlend is also ready to be connected to controls such as Actilume or used together with the Philips SpaceWise lighting system. It can also be connected to software-based lighting systems like Interact Office, which provides the luminaire with further intelligence and enables it to collect valuable data about its environment

Benefits

- High-quality office-compliant lighting
- Choice of three different exit-windows
- Fast return on investment

- Application flexibility
- Scalable and ready to be connected to controls and lighting systems

Applications

- Offices
- Education

- Healthcare
- Banks

Features

- Fully office-compliant (UGR <19)
- Homogenous and uniform light effect

Versions

- Dimensional variety, local options
- Various mounting options
- Integrated sensors
- Can be combined with Philips ActiLume and SpaceWise systems
- Ready to be connected to software based lighting systems such as Interact Office




FlexBlend Recessed RC340B
W15L120 MLO VPC




FlexBlend Recessed-RC340B
W30L120 MLO VPC



Upgradable sensor




FlexBlend Recessed RC340B
W60L60 OPA VPC




FlexBlend Recessed RC340B
W60L60 MLO CPC




0 FlexBlend Recessed-RC340B
W30L120 MLO VPC




FlexBlend Recessed RC340B
W60L60 PCS VPC



FlexBlend Recessed RC340B
W60L60 MLO VPC




FlexBlend Recessed RC340B
W60L60 MLO PCV




FlexBlend Recessed RC342B
W62L62 MLO VPC


Dimensional drawing



FLEXBLEND RECESSED, module 600 - 940 neutral white - Power supply unit with DALI interface - Plug-in connector 3-pole Wieland/Adels compatible





RC342B 36S/940 PSE W62L62 VPC MLO





RC340B 36S/940 DIA W15L120 VPC MLO ELP3


RC340B 42S/930 DEIA W30L120 CPC PCS W3W2




RC342B 36S/940 PSE W31L125 VPC MLO



RC340B 42S/930 DEIA W30L120 VPC MLO W3W2



RC340B 42S/940 DEIA W60L60 CPC PCS



RC340B 42S/940 DIA W60L60 VPC PCS ELD3

Product details

0_FlexBlend Recessed-
RC342B_W62L62_MLO_VPC



FlexBlend Recessed-
RC340B_MLO_DPP




FlexBlend Recessed-
RC340B_W60L60_Backcover_V
PC



FlexBlend Recessed-
RC340B_W60L60_CPC
brackets





FlexBlend Recessed-RC340B_W60L60_CPC brackets_B



FlexBlend Recessed-RC340B_OPA_DPP



FlexBlend Recessed-RC340B_PCS_DPP



0_FlexBlend Recessed-RC340B_W60L60_PCS_VPC



FlexBlend Recessed-RC340B_W60L60_CPC brackets_A



FlexBlend Recessed RC340B PIP Open



FlexBlend Recessed-RC340B_W60L60_backcover_P CV



0_FlexBlend Recessed-RC340B_W60L60_MLO_VPC



0_FlexBlend Recessed-RC340B_W60L60_MLO_CPC



FlexBlend Recessed-RC340B PIP Closed



FlexBlend Recessed-
RC340B_W60L60_backcover_C
PC

General Information

Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Service tag	Yes

Light Technical

Color rendering index (CRI)	>90
Beam angle of light source	120 degree(s)
Optic type	Wide beam

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Protection class IEC	Safety class I

Controls and Dimming

Maximum dim level	1%
Embedded control	Upgradable sensor slot with SC200 sensor

Mechanical and Housing

Housing Color	White
Mech. impact protection code	IK02 [0.2 J standard]

Emergency Operation

Rated duration of the emergency lighting (when fully charged)	3 hour(s)
---	-----------

Approval and Application

Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	+10 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.01 %
-------------------------------	--------

Light Technical

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)
10277400	RC340B 36S/940 PSE W15L120 VPC MLO	3,600 lm	4000 K	95 lm/W
10278100	RC340B 36S/940 DEIA W15L120 VPC MLO	3,600 lm	4000 K	95 lm/W
10279800	RC340B 42S/940 PSE W15L120 VPC MLO	4,200 lm	4000 K	93 lm/W
10280400	RC340B 42S/940 DEIA W15L120 VPC MLO	4,200 lm	4000 K	93 lm/W
10282800	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	3,600 lm	4000 K	95 lm/W
10284200	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	4,200 lm	4000 K	93 lm/W
10286600	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	3,600 lm	4000 K	95 lm/W
10288000	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	4,200 lm	4000 K	93 lm/W
10242200	RC340B 36S/940 DEIA W30L120 VPC MLO	3,600 lm	4000 K	95 lm/W
10245300	RC342B 36S/940 PSE W31L125 VPC MLO	3,600 lm	4000 K	95 lm/W
10246000	RC342B 36S/940 DEIA W31L125 VPC MLO	3,600 lm	4000 K	95 lm/W
10292700	RC340B 42S/940 DEIA W30L120 VPC MLO W3W2	4,200 lm	4000 K	93 lm/W
10293400	RC340B 42S/940 DEIA W30L120 CPC MLO W3W2	4,200 lm	4000 K	93 lm/W
10294100	RC340B 42S/930 DEIA W30L120 VPC MLO W3W2	4,200 lm	3000 K	93 lm/W
10295800	RC340B 42S/930 DEIA W30L120 CPC MLO W3W2	4,200 lm	3000 K	93 lm/W
10300900	RC340B 42S/940 DEIA W30L120 VPC PCS W3W2	4,200 lm	4000 K	138 lm/W
10301600	RC340B 42S/940 DEIA W30L120 CPC PCS W3W2	4,200 lm	4000 K	138 lm/W
10304700	RC340B 42S/930 DEIA W30L120 VPC PCS W3W2	4,200 lm	3000 K	138 lm/W
70832700	RC340B 42S/940 SEIA W60L60 VPC PCS U4 W3	4,200 lm	4000 K	140 lm/W
10250700	RC340B 36S/940 DIA W60L60 VPC O ELP3	3,600 lm	4000 K	126 lm/W
10263700	RC340B 42S/940 PSE W60L60 VPC O	4,200 lm	4000 K	125 lm/W

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)
10264400	RC340B 42S/940 DEIA W60L60 VPC O	4,200 lm	4000 K	125 lm/W
10269900	RC340B 42S/940 DIA W60L60 VPC O ELP3	4,200 lm	4000 K	125 lm/W
10274300	RC340B 42S/940 DIA W60L60 VPC O ELD3	4,200 lm	4000 K	125 lm/W
10323800	RC340B 36S/940 PSE W60L60 VPC O SC	3,600 lm	4000 K	126 lm/W
10324500	RC340B 36S/940 DEIA W60L60 VPC O SC	3,600 lm	4000 K	126 lm/W
10232300	RC340B 36S/940 DEIA W60L60 VPC MLO	3,600 lm	4000 K	95 lm/W
10285900	RC340B 42S/930 DEIA W60L60 CPC MLO W3W2	4,200 lm	3000 K	93 lm/W
10290300	RC340B 42S/940 DEIA W60L60 CPC MLO W3W2	4,200 lm	4000 K	93 lm/W
10298900	RC340B 42S/940 DEIA W60L60 CPC PCS W3W2	4,200 lm	4000 K	138 lm/W
10302300	RC340B 42S/930 DEIA W60L60 CPC PCS W3W2	4,200 lm	3000 K	138 lm/W
10308500	RC340B 36S/940 PSE W60L60 CPC MLO	3,600 lm	4000 K	95 lm/W
10309200	RC340B 42S/940 PSE W60L60 CPC MLO	4,200 lm	4000 K	93 lm/W
10310800	RC340B 42S/940 DEIA W60L60 CPC MLO	4,200 lm	4000 K	93 lm/W
10330600	RC340B 42S/930 DEIA W30L120 CPC PCS W3W2	4,200 lm	3000 K	138 lm/W
10230900	RC340B 36S/940 DEIA W60L60 VPC O	3,600 lm	4000 K	126 lm/W
10235400	RC340B 36S/940 PSE W60L60 VPC PCS	3,600 lm	4000 K	138 lm/W
10236100	RC340B 36S/940 DEIA W60L60 VPC PCS	3,600 lm	4000 K	138 lm/W
10240800	RC340B 36S/940 DEIA W60L60 CPC MLO	3,600 lm	4000 K	95 lm/W
10254500	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	3,600 lm	4000 K	138 lm/W
10260600	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	3,600 lm	4000 K	138 lm/W
10265100	RC340B 42S/940 PSE W60L60 VPC PCS	4,200 lm	4000 K	138 lm/W
10266800	RC340B 42S/940 DEIA W60L60 VPC PCS	4,200 lm	4000 K	138 lm/W
10271200	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	4,200 lm	4000 K	138 lm/W
10296500	RC340B 42S/930 DEIA W60L60 VPC PCS W3W2	4,200 lm	3000 K	138 lm/W
10297200	RC340B 42S/940 DEIA W60L60 VPC PCS W3W2	4,200 lm	4000 K	138 lm/W
10306100	RC340B 36S/940 PSE W60L60 CPC PCS PIP	3,600 lm	4000 K	138 lm/W
10307800	RC340B 36S/940 DEIA W60L60 CPC PCS	3,600 lm	4000 K	138 lm/W
10311500	RC340B 42S/940 PSE W60L60 CPC PCS	4,200 lm	4000 K	138 lm/W
10312200	RC340B 42S/940 DEIA W60L60 CPC PCS	4,200 lm	4000 K	138 lm/W
10327600	RC340B 36S/940 PSE W60L60 VPC PCS SC	3,600 lm	4000 K	138 lm/W
10328300	RC340B 36S/940 DEIA W60L60 VPC PCS SC	3,600 lm	4000 K	138 lm/W
10229300	RC340B 36S/940 PSE W60L60 VPC O	3,600 lm	4000 K	126 lm/W
10243900	RC342B 36S/940 PSE W62L62 VPC MLO	3,600 lm	4000 K	95 lm/W
10252100	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	3,600 lm	4000 K	95 lm/W
10256900	RC340B 36S/940 DIA W60L60 VPC O ELD3	3,600 lm	4000 K	126 lm/W
10258300	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	3,600 lm	4000 K	95 lm/W
10262000	RC340B 42S/940 DEIA W60L60 VPC MLO	4,200 lm	4000 K	93 lm/W
10272900	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	4,200 lm	4000 K	93 lm/W
10275000	RC340B 42S/930 DEIA W60L60 VPC MLO W3W2	4,200 lm	3000 K	93 lm/W
10289700	RC340B 42S/940 DEIA W60L60 VPC MLO W3W2	4,200 lm	4000 K	93 lm/W
10305400	RC340B 42S/940 PSE W60L60 VPC MLO	4,200 lm	4000 K	93 lm/W
10325200	RC340B 36S/940 PSE W60L60 VPC MLO SC	3,600 lm	4000 K	95 lm/W

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)
10326900	RC340B 36S/940 DEIA W60L60 VPC MLO SC	3,600 lm	4000 K	95 lm/W
10276700	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	4,200 lm	4000 K	138 lm/W
10287300	RC340B 42S/930 DEIA W60L60 PCV MLO W3W2	4,200 lm	3000 K	93 lm/W
10291000	RC340B 42S/940 DEIA W60L60 PCV MLO W3W2	4,200 lm	4000 K	93 lm/W
10299600	RC340B 42S/940 DEIA W60L60 PCV PCS W3W2	4,200 lm	4000 K	138 lm/W
10303000	RC340B 42S/930 DEIA W60L60 PCV PCS W3W2	4,200 lm	3000 K	138 lm/W
10429700	RC340B 36S/940 DEIA W60L60 PCV PCS	3,600 lm	4000 K	138 lm/W
10231600	RC340B 36S/940 PSE W60L60 VPC MLO PIP	3,600 lm	4000 K	95 lm/W
10241500	RC340B 36S/940 DEIA W60L60 PCV MLO	3,600 lm	4000 K	95 lm/W
10244600	RC342B 36S/940 DEIA W62L62 VPC MLO	3,600 lm	4000 K	95 lm/W
10420400	RC342B 36S/940 DEIA W62L62 VPC PCS	3,600 lm	4000 K	144 lm/W

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Suitable for random switching
10277400	RC340B 36S/940 PSE W15L120 VPC MLO	38 W	Yes
10278100	RC340B 36S/940 DEIA W15L120 VPC MLO	38 W	Yes
10279800	RC340B 42S/940 PSE W15L120 VPC MLO	45 W	Yes
10280400	RC340B 42S/940 DEIA W15L120 VPC MLO	45 W	Yes
10282800	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	38 W	Yes
10284200	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	45 W	Yes
10286600	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	38 W	Yes
10288000	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	45 W	Yes
10242200	RC340B 36S/940 DEIA W30L120 VPC MLO	38 W	Yes
10245300	RC342B 36S/940 PSE W31L125 VPC MLO	37 W	Yes
10246000	RC342B 36S/940 DEIA W31L125 VPC MLO	38 W	Yes
10292700	RC340B 42S/940 DEIA W30L120 VPC MLO W3W2	45 W	Yes
10293400	RC340B 42S/940 DEIA W30L120 CPC MLO W3W2	45 W	Yes
10294100	RC340B 42S/930 DEIA W30L120 VPC MLO W3W2	45 W	Yes
10295800	RC340B 42S/930 DEIA W30L120 CPC MLO W3W2	45 W	Yes
10300900	RC340B 42S/940 DEIA W30L120 VPC PCS W3W2	30.5 W	Yes
10301600	RC340B 42S/940 DEIA W30L120 CPC PCS W3W2	30.5 W	Yes
10304700	RC340B 42S/930 DEIA W30L120 VPC PCS W3W2	30.5 W	Yes
70832700	RC340B 42S/940 SEIA W60L60 VPC PCS U4 W3	30 W	No
10250700	RC340B 36S/940 DIA W60L60 VPC O ELP3	28.5 W	Yes
10263700	RC340B 42S/940 PSE W60L60 VPC O	33.5 W	Yes
10264400	RC340B 42S/940 DEIA W60L60 VPC O	33.5 W	Yes
10269900	RC340B 42S/940 DIA W60L60 VPC O ELP3	33.5 W	Yes
10274300	RC340B 42S/940 DIA W60L60 VPC O ELD3	33.5 W	Yes
10323800	RC340B 36S/940 PSE W60L60 VPC O SC	28.5 W	Yes
10324500	RC340B 36S/940 DEIA W60L60 VPC O SC	28.5 W	Yes
10232300	RC340B 36S/940 DEIA W60L60 VPC MLO	38 W	Yes

Order Code	Full Product Name	Power Consumption	Suitable for random switching
10285900	RC340B 42S/930 DEIA W60L60 CPC MLO W3W2	45 W	Yes
10290300	RC340B 42S/940 DEIA W60L60 CPC MLO W3W2	45 W	Yes
10298900	RC340B 42S/940 DEIA W60L60 CPC PCS W3W2	30.5 W	Yes
10302300	RC340B 42S/930 DEIA W60L60 CPC PCS W3W2	30.5 W	Yes
10308500	RC340B 36S/940 PSE W60L60 CPC MLO	38 W	Yes
10309200	RC340B 42S/940 PSE W60L60 CPC MLO	45 W	Yes
10310800	RC340B 42S/940 DEIA W60L60 CPC MLO	45 W	Yes
10330600	RC340B 42S/930 DEIA W30L120 CPC PCS W3W2	30.5 W	Yes
10230900	RC340B 36S/940 DEIA W60L60 VPC O	28.5 W	Yes
10235400	RC340B 36S/940 PSE W60L60 VPC PCS	26 W	Yes
10236100	RC340B 36S/940 DEIA W60L60 VPC PCS	26 W	Yes
10240800	RC340B 36S/940 DEIA W60L60 CPC MLO	38 W	Yes
10254500	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	26 W	Yes
10260600	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	26 W	Yes
10265100	RC340B 42S/940 PSE W60L60 VPC PCS	30.5 W	Yes
10266800	RC340B 42S/940 DEIA W60L60 VPC PCS	30.5 W	Yes
10271200	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	30.5 W	Yes
10296500	RC340B 42S/930 DEIA W60L60 VPC PCS W3W2	30.5 W	Yes
10297200	RC340B 42S/940 DEIA W60L60 VPC PCS W3W2	30.5 W	Yes
10306100	RC340B 36S/940 PSE W60L60 CPC PCS PIP	26 W	Yes
10307800	RC340B 36S/940 DEIA W60L60 CPC PCS	26 W	Yes
10311500	RC340B 42S/940 PSE W60L60 CPC PCS	30.5 W	Yes
10312200	RC340B 42S/940 DEIA W60L60 CPC PCS	30.5 W	Yes
10327600	RC340B 36S/940 PSE W60L60 VPC PCS SC	26 W	Yes
10328300	RC340B 36S/940 DEIA W60L60 VPC PCS SC	26 W	Yes
10229300	RC340B 36S/940 PSE W60L60 VPC O	28.5 W	Yes
10243900	RC342B 36S/940 PSE W62L62 VPC MLO	37 W	Yes
10252100	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	38 W	Yes
10256900	RC340B 36S/940 DIA W60L60 VPC O ELD3	28.5 W	Yes
10258300	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	38 W	Yes
10262000	RC340B 42S/940 DEIA W60L60 VPC MLO	45 W	Yes
10272900	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	45 W	Yes
10275000	RC340B 42S/930 DEIA W60L60 VPC MLO W3W2	45 W	Yes
10289700	RC340B 42S/940 DEIA W60L60 VPC MLO W3W2	45 W	Yes
10305400	RC340B 42S/940 PSE W60L60 VPC MLO	45 W	Yes
10325200	RC340B 36S/940 PSE W60L60 VPC MLO SC	38 W	Yes
10326900	RC340B 36S/940 DEIA W60L60 VPC MLO SC	38 W	Yes
10276700	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	30.5 W	Yes
10287300	RC340B 42S/930 DEIA W60L60 PCV MLO W3W2	45 W	Yes
10291000	RC340B 42S/940 DEIA W60L60 PCV MLO W3W2	45 W	Yes
10299600	RC340B 42S/940 DEIA W60L60 PCV PCS W3W2	30.5 W	Yes
10303000	RC340B 42S/930 DEIA W60L60 PCV PCS W3W2	30.5 W	Yes

Order Code	Full Product Name	Power Consumption	Suitable for random switching
10429700	RC340B 36S/940 DEIA W60L60 PCV PCS	26 W	Yes
10231600	RC340B 36S/940 PSE W60L60 VPC MLO PIP	38 W	Yes
10241500	RC340B 36S/940 DEIA W60L60 PCV MLO	38 W	Yes
10244600	RC342B 36S/940 DEIA W62L62 VPC MLO	38 W	Yes
10420400	RC342B 36S/940 DEIA W62L62 VPC PCS	25 W	Yes

Controls and Dimming

Order Code	Full Product Name	Dimmable
10277400	RC340B 36S/940 PSE W15L120 VPC MLO	No
10278100	RC340B 36S/940 DEIA W15L120 VPC MLO	Yes
10279800	RC340B 42S/940 PSE W15L120 VPC MLO	No
10280400	RC340B 42S/940 DEIA W15L120 VPC MLO	Yes
10282800	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	Yes
10284200	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	Yes
10286600	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	Yes
10288000	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	Yes
10242200	RC340B 36S/940 DEIA W30L120 VPC MLO	Yes
10245300	RC342B 36S/940 PSE W31L125 VPC MLO	No
10246000	RC342B 36S/940 DEIA W31L125 VPC MLO	Yes
10292700	RC340B 42S/940 DEIA W30L120 VPC MLO W3W2	Yes
10293400	RC340B 42S/940 DEIA W30L120 CPC MLO W3W2	Yes
10294100	RC340B 42S/930 DEIA W30L120 VPC MLO W3W2	Yes
10295800	RC340B 42S/930 DEIA W30L120 CPC MLO W3W2	Yes
10300900	RC340B 42S/940 DEIA W30L120 VPC PCS W3W2	Yes
10301600	RC340B 42S/940 DEIA W30L120 CPC PCS W3W2	Yes
10304700	RC340B 42S/930 DEIA W30L120 VPC PCS W3W2	Yes
70832700	RC340B 42S/940 SEIA W60L60 VPC PCS U4 W3	No
10250700	RC340B 36S/940 DIA W60L60 VPC O ELP3	Yes
10263700	RC340B 42S/940 PSE W60L60 VPC O	No
10264400	RC340B 42S/940 DEIA W60L60 VPC O	Yes
10269900	RC340B 42S/940 DIA W60L60 VPC O ELP3	Yes
10274300	RC340B 42S/940 DIA W60L60 VPC O ELD3	Yes
10323800	RC340B 36S/940 PSE W60L60 VPC O SC	No
10324500	RC340B 36S/940 DEIA W60L60 VPC O SC	Yes
10232300	RC340B 36S/940 DEIA W60L60 VPC MLO	Yes
10285900	RC340B 42S/930 DEIA W60L60 CPC MLO W3W2	Yes
10290300	RC340B 42S/940 DEIA W60L60 CPC MLO W3W2	Yes
10298900	RC340B 42S/940 DEIA W60L60 CPC PCS W3W2	Yes
10302300	RC340B 42S/930 DEIA W60L60 CPC PCS W3W2	Yes
10308500	RC340B 36S/940 PSE W60L60 CPC MLO	No
10309200	RC340B 42S/940 PSE W60L60 CPC MLO	No

Order Code	Full Product Name	Dimmable
10310800	RC340B 42S/940 DEIA W60L60 CPC MLO	Yes
10330600	RC340B 42S/930 DEIA W30L120 CPC PCS W3W2	Yes
10230900	RC340B 36S/940 DEIA W60L60 VPC O	Yes
10235400	RC340B 36S/940 PSE W60L60 VPC PCS	No
10236100	RC340B 36S/940 DEIA W60L60 VPC PCS	Yes
10240800	RC340B 36S/940 DEIA W60L60 CPC MLO	Yes
10254500	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	Yes
10260600	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	Yes
10265100	RC340B 42S/940 PSE W60L60 VPC PCS	No
10266800	RC340B 42S/940 DEIA W60L60 VPC PCS	Yes
10271200	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	Yes
10296500	RC340B 42S/930 DEIA W60L60 VPC PCS W3W2	Yes
10297200	RC340B 42S/940 DEIA W60L60 VPC PCS W3W2	Yes
10306100	RC340B 36S/940 PSE W60L60 CPC PCS PIP	No
10307800	RC340B 36S/940 DEIA W60L60 CPC PCS	Yes
10311500	RC340B 42S/940 PSE W60L60 CPC PCS	No
10312200	RC340B 42S/940 DEIA W60L60 CPC PCS	Yes
10327600	RC340B 36S/940 PSE W60L60 VPC PCS SC	No
10328300	RC340B 36S/940 DEIA W60L60 VPC PCS SC	Yes
10229300	RC340B 36S/940 PSE W60L60 VPC O	No
10243900	RC342B 36S/940 PSE W62L62 VPC MLO	No
10252100	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	Yes
10256900	RC340B 36S/940 DIA W60L60 VPC O ELD3	Yes
10258300	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	Yes
10262000	RC340B 42S/940 DEIA W60L60 VPC MLO	Yes
10272900	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	Yes
10275000	RC340B 42S/930 DEIA W60L60 VPC MLO W3W2	Yes
10289700	RC340B 42S/940 DEIA W60L60 VPC MLO W3W2	Yes
10305400	RC340B 42S/940 PSE W60L60 VPC MLO	No
10325200	RC340B 36S/940 PSE W60L60 VPC MLO SC	No
10326900	RC340B 36S/940 DEIA W60L60 VPC MLO SC	Yes
10276700	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	Yes
10287300	RC340B 42S/930 DEIA W60L60 PCV MLO W3W2	Yes
10291000	RC340B 42S/940 DEIA W60L60 PCV MLO W3W2	Yes
10299600	RC340B 42S/940 DEIA W60L60 PCV PCS W3W2	Yes
10303000	RC340B 42S/930 DEIA W60L60 PCV PCS W3W2	Yes
10429700	RC340B 36S/940 DEIA W60L60 PCV PCS	Yes
10231600	RC340B 36S/940 PSE W60L60 VPC MLO PIP	No
10241500	RC340B 36S/940 DEIA W60L60 PCV MLO	Yes
10244600	RC342B 36S/940 DEIA W62L62 VPC MLO	Yes
10420400	RC342B 36S/940 DEIA W62L62 VPC PCS	Yes

Mechanical and Housing

Order Code	Full Product Name	Ingress protection code
10277400	RC340B 36S/940 PSE W15L120 VPC MLO	IP20/40
10278100	RC340B 36S/940 DEIA W15L120 VPC MLO	IP20/40
10279800	RC340B 42S/940 PSE W15L120 VPC MLO	IP20/40
10280400	RC340B 42S/940 DEIA W15L120 VPC MLO	IP20/40
10282800	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	IP20
10284200	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	IP20
10286600	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	IP20
10288000	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	IP20
10242200	RC340B 36S/940 DEIA W30L120 VPC MLO	IP20/40
10245300	RC342B 36S/940 PSE W31L125 VPC MLO	IP20/40
10246000	RC342B 36S/940 DEIA W31L125 VPC MLO	IP20/40
10292700	RC340B 42S/940 DEIA W30L120 VPC MLO W3W2	IP20/40
10293400	RC340B 42S/940 DEIA W30L120 CPC MLO W3W2	IP20/40
10294100	RC340B 42S/930 DEIA W30L120 VPC MLO W3W2	IP20/40
10295800	RC340B 42S/930 DEIA W30L120 CPC MLO W3W2	IP20/40
10300900	RC340B 42S/940 DEIA W30L120 VPC PCS W3W2	IP20/54
10301600	RC340B 42S/940 DEIA W30L120 CPC PCS W3W2	IP20/54
10304700	RC340B 42S/930 DEIA W30L120 VPC PCS W3W2	IP20/54
70832700	RC340B 42S/940 SEIA W60L60 VPC PCS U4 W3	IP20/54
10250700	RC340B 36S/940 DIA W60L60 VPC O ELP3	IP54
10263700	RC340B 42S/940 PSE W60L60 VPC O	IP20/54
10264400	RC340B 42S/940 DEIA W60L60 VPC O	IP20/54
10269900	RC340B 42S/940 DIA W60L60 VPC O ELP3	IP20/54
10274300	RC340B 42S/940 DIA W60L60 VPC O ELD3	IP54
10323800	RC340B 36S/940 PSE W60L60 VPC O SC	IP20/54
10324500	RC340B 36S/940 DEIA W60L60 VPC O SC	IP20/54
10232300	RC340B 36S/940 DEIA W60L60 VPC MLO	IP20/40
10285900	RC340B 42S/930 DEIA W60L60 CPC MLO W3W2	IP20/40
10290300	RC340B 42S/940 DEIA W60L60 CPC MLO W3W2	IP20/40
10298900	RC340B 42S/940 DEIA W60L60 CPC PCS W3W2	IP20/54
10302300	RC340B 42S/930 DEIA W60L60 CPC PCS W3W2	IP20/54
10308500	RC340B 36S/940 PSE W60L60 CPC MLO	IP20/40
10309200	RC340B 42S/940 PSE W60L60 CPC MLO	IP20/40
10310800	RC340B 42S/940 DEIA W60L60 CPC MLO	IP20/40
10330600	RC340B 42S/930 DEIA W30L120 CPC PCS W3W2	IP20/54
10230900	RC340B 36S/940 DEIA W60L60 VPC O	IP20/54
10235400	RC340B 36S/940 PSE W60L60 VPC PCS	IP20/54
10236100	RC340B 36S/940 DEIA W60L60 VPC PCS	IP20/54
10240800	RC340B 36S/940 DEIA W60L60 CPC MLO	IP20/40
10254500	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	IP20/54
10260600	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	IP20/54

Order Code	Full Product Name	Ingress protection code
10265100	RC340B 42S/940 PSE W60L60 VPC PCS	IP20/54
10266800	RC340B 42S/940 DEIA W60L60 VPC PCS	IP20/54
10271200	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	IP20/54
10296500	RC340B 42S/930 DEIA W60L60 VPC PCS W3W2	IP20/54
10297200	RC340B 42S/940 DEIA W60L60 VPC PCS W3W2	IP20/54
10306100	RC340B 36S/940 PSE W60L60 CPC PCS PIP	IP20/54
10307800	RC340B 36S/940 DEIA W60L60 CPC PCS	IP20/54
10311500	RC340B 42S/940 PSE W60L60 CPC PCS	IP20/54
10312200	RC340B 42S/940 DEIA W60L60 CPC PCS	IP20/54
10327600	RC340B 36S/940 PSE W60L60 VPC PCS SC	IP20/54
10328300	RC340B 36S/940 DEIA W60L60 VPC PCS SC	IP20/54
10229300	RC340B 36S/940 PSE W60L60 VPC O	IP20/54
10243900	RC342B 36S/940 PSE W62L62 VPC MLO	IP20/40
10252100	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	IP20/54
10256900	RC340B 36S/940 DIA W60L60 VPC O ELD3	IP54
10258300	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	IP20/54
10262000	RC340B 42S/940 DEIA W60L60 VPC MLO	IP20/40
10272900	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	IP20
10275000	RC340B 42S/930 DEIA W60L60 VPC MLO W3W2	IP20/40
10289700	RC340B 42S/940 DEIA W60L60 VPC MLO W3W2	IP20/40
10305400	RC340B 42S/940 PSE W60L60 VPC MLO	IP20/40
10325200	RC340B 36S/940 PSE W60L60 VPC MLO SC	IP20/40
10326900	RC340B 36S/940 DEIA W60L60 VPC MLO SC	IP20/40
10276700	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	IP20/54
10287300	RC340B 42S/930 DEIA W60L60 PCV MLO W3W2	IP20/40
10291000	RC340B 42S/940 DEIA W60L60 PCV MLO W3W2	IP20/40
10299600	RC340B 42S/940 DEIA W60L60 PCV PCS W3W2	IP20/54
10303000	RC340B 42S/930 DEIA W60L60 PCV PCS W3W2	IP20/54
10429700	RC340B 36S/940 DEIA W60L60 PCV PCS	IP20/54
10231600	RC340B 36S/940 PSE W60L60 VPC MLO PIP	IP20/40
10241500	RC340B 36S/940 DEIA W60L60 PCV MLO	IP20/40
10244600	RC342B 36S/940 DEIA W62L62 VPC MLO	IP20/40
10420400	RC342B 36S/940 DEIA W62L62 VPC PCS	IP20/54

Emergency Operation

Order Code	Full Product Name	Central Emergency	Emergency lighting
10277400	RC340B 36S/940 PSE W15L120 VPC MLO	-	-
10278100	RC340B 36S/940 DEIA W15L120 VPC MLO	Yes	DC operated central emergency lighting
10279800	RC340B 42S/940 PSE W15L120 VPC MLO	-	-
10280400	RC340B 42S/940 DEIA W15L120 VPC MLO	Yes	DC operated central emergency lighting
10282800	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	No	Emergency lighting 3 hours duration Pro version

Order Code	Full Product Name	Central Emergency	Emergency lighting
10284200	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	No	Emergency lighting 3 hours duration Pro version
10286600	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	No	Emergency lighting 3 hours duration Pro version
10288000	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	No	Emergency lighting 3 hours duration Pro version
10242200	RC340B 36S/940 DEIA W30L120 VPC MLO	Yes	DC operated central emergency lighting
10245300	RC342B 36S/940 PSE W31L125 VPC MLO	-	-
10246000	RC342B 36S/940 DEIA W31L125 VPC MLO	Yes	DC operated central emergency lighting
10292700	RC340B 42S/940 DEIA W30L120 VPC MLO W3W2	Yes	DC operated central emergency lighting
10293400	RC340B 42S/940 DEIA W30L120 CPC MLO W3W2	Yes	DC operated central emergency lighting
10294100	RC340B 42S/930 DEIA W30L120 VPC MLO W3W2	Yes	DC operated central emergency lighting
10295800	RC340B 42S/930 DEIA W30L120 CPC MLO W3W2	Yes	DC operated central emergency lighting
10300900	RC340B 42S/940 DEIA W30L120 VPC PCS W3W2	Yes	DC operated central emergency lighting
10301600	RC340B 42S/940 DEIA W30L120 CPC PCS W3W2	Yes	DC operated central emergency lighting
10304700	RC340B 42S/930 DEIA W30L120 VPC PCS W3W2	Yes	DC operated central emergency lighting
70832700	RC340B 42S/940 SEIA W60L60 VPC PCS U4 W3	Yes	DC operated central emergency lighting
10250700	RC340B 36S/940 DIA W60L60 VPC O ELP3	No	Emergency lighting 3 hours duration Pro version
10263700	RC340B 42S/940 PSE W60L60 VPC O	-	-
10264400	RC340B 42S/940 DEIA W60L60 VPC O	Yes	DC operated central emergency lighting
10269900	RC340B 42S/940 DIA W60L60 VPC O ELP3	No	Emergency lighting 3 hours duration Pro version
10274300	RC340B 42S/940 DIA W60L60 VPC O ELD3	No	Emergency lighting 3 hours duration with DALI interface
10323800	RC340B 36S/940 PSE W60L60 VPC O SC	-	-
10324500	RC340B 36S/940 DEIA W60L60 VPC O SC	Yes	DC operated central emergency lighting
10232300	RC340B 36S/940 DEIA W60L60 VPC MLO	Yes	DC operated central emergency lighting
10285900	RC340B 42S/930 DEIA W60L60 CPC MLO W3W2	Yes	DC operated central emergency lighting
10290300	RC340B 42S/940 DEIA W60L60 CPC MLO W3W2	Yes	DC operated central emergency lighting
10298900	RC340B 42S/940 DEIA W60L60 CPC PCS W3W2	Yes	DC operated central emergency lighting
10302300	RC340B 42S/930 DEIA W60L60 CPC PCS W3W2	Yes	DC operated central emergency lighting
10308500	RC340B 36S/940 PSE W60L60 CPC MLO	-	-
10309200	RC340B 42S/940 PSE W60L60 CPC MLO	-	-
10310800	RC340B 42S/940 DEIA W60L60 CPC MLO	Yes	DC operated central emergency lighting
10330600	RC340B 42S/930 DEIA W30L120 CPC PCS W3W2	Yes	DC operated central emergency lighting
10230900	RC340B 36S/940 DEIA W60L60 VPC O	Yes	DC operated central emergency lighting
10235400	RC340B 36S/940 PSE W60L60 VPC PCS	-	-
10236100	RC340B 36S/940 DEIA W60L60 VPC PCS	Yes	DC operated central emergency lighting
10240800	RC340B 36S/940 DEIA W60L60 CPC MLO	Yes	DC operated central emergency lighting
10254500	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	No	Emergency lighting 3 hours duration Pro version
10260600	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	No	Emergency lighting 3 hours duration with DALI interface
10265100	RC340B 42S/940 PSE W60L60 VPC PCS	-	-
10266800	RC340B 42S/940 DEIA W60L60 VPC PCS	Yes	DC operated central emergency lighting
10271200	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	No	Emergency lighting 3 hours duration Pro version
10296500	RC340B 42S/930 DEIA W60L60 VPC PCS W3W2	Yes	DC operated central emergency lighting
10297200	RC340B 42S/940 DEIA W60L60 VPC PCS W3W2	Yes	DC operated central emergency lighting
10306100	RC340B 36S/940 PSE W60L60 CPC PCS PIP	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting
10307800	RC340B 36S/940 DEIA W60L60 CPC PCS	Yes	DC operated central emergency lighting
10311500	RC340B 42S/940 PSE W60L60 CPC PCS	-	-
10312200	RC340B 42S/940 DEIA W60L60 CPC PCS	Yes	DC operated central emergency lighting
10327600	RC340B 36S/940 PSE W60L60 VPC PCS SC	-	-
10328300	RC340B 36S/940 DEIA W60L60 VPC PCS SC	Yes	DC operated central emergency lighting
10229300	RC340B 36S/940 PSE W60L60 VPC O	-	-
10243900	RC342B 36S/940 PSE W62L62 VPC MLO	-	-
10252100	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	No	Emergency lighting 3 hours duration Pro version
10256900	RC340B 36S/940 DIA W60L60 VPC O ELD3	No	Emergency lighting 3 hours duration with DALI interface
10258300	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	No	Emergency lighting 3 hours duration with DALI interface
10262000	RC340B 42S/940 DEIA W60L60 VPC MLO	Yes	DC operated central emergency lighting
10272900	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	No	Emergency lighting 3 hours duration with DALI interface
10275000	RC340B 42S/930 DEIA W60L60 VPC MLO W3W2	Yes	DC operated central emergency lighting
10289700	RC340B 42S/940 DEIA W60L60 VPC MLO W3W2	Yes	DC operated central emergency lighting
10305400	RC340B 42S/940 PSE W60L60 VPC MLO	-	-
10325200	RC340B 36S/940 PSE W60L60 VPC MLO SC	-	-
10326900	RC340B 36S/940 DEIA W60L60 VPC MLO SC	Yes	DC operated central emergency lighting
10276700	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	No	Emergency lighting 3 hours duration with DALI interface
10287300	RC340B 42S/930 DEIA W60L60 PCV MLO W3W2	Yes	DC operated central emergency lighting
10291000	RC340B 42S/940 DEIA W60L60 PCV MLO W3W2	Yes	DC operated central emergency lighting
10299600	RC340B 42S/940 DEIA W60L60 PCV PCS W3W2	Yes	DC operated central emergency lighting
10303000	RC340B 42S/930 DEIA W60L60 PCV PCS W3W2	Yes	DC operated central emergency lighting
10429700	RC340B 36S/940 DEIA W60L60 PCV PCS	Yes	DC operated central emergency lighting
10231600	RC340B 36S/940 PSE W60L60 VPC MLO PIP	-	-
10241500	RC340B 36S/940 DEIA W60L60 PCV MLO	Yes	DC operated central emergency lighting
10244600	RC342B 36S/940 DEIA W62L62 VPC MLO	Yes	DC operated central emergency lighting
10420400	RC342B 36S/940 DEIA W62L62 VPC PCS	Yes	DC operated central emergency lighting

Approval and Application

Order Code	Full Product Name	Glow-wire test
10277400	RC340B 36S/940 PSE W15L120 VPC MLO	Temperature 650 °C, duration 30 s
10278100	RC340B 36S/940 DEIA W15L120 VPC MLO	Temperature 650 °C, duration 30 s
10279800	RC340B 42S/940 PSE W15L120 VPC MLO	Temperature 650 °C, duration 30 s
10280400	RC340B 42S/940 DEIA W15L120 VPC MLO	Temperature 650 °C, duration 30 s
10282800	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	Temperature 650 °C, duration 30 s
10284200	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	Temperature 650 °C, duration 30 s
10286600	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	Temperature 650 °C, duration 30 s
10288000	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	Temperature 650 °C, duration 30 s
10242200	RC340B 36S/940 DEIA W30L120 VPC MLO	Temperature 650 °C, duration 30 s
10245300	RC342B 36S/940 PSE W31L125 VPC MLO	Temperature 650 °C, duration 30 s
10246000	RC342B 36S/940 DEIA W31L125 VPC MLO	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Glow-wire test
10292700	RC340B 42S/940 DEIA W30L120 VPC MLO W3W2	Temperature 650 °C, duration 30 s
10293400	RC340B 42S/940 DEIA W30L120 CPC MLO W3W2	Temperature 650 °C, duration 30 s
10294100	RC340B 42S/930 DEIA W30L120 VPC MLO W3W2	Temperature 650 °C, duration 30 s
10295800	RC340B 42S/930 DEIA W30L120 CPC MLO W3W2	Temperature 650 °C, duration 30 s
10300900	RC340B 42S/940 DEIA W30L120 VPC PCS W3W2	Temperature 850 °C, duration 30 s
10301600	RC340B 42S/940 DEIA W30L120 CPC PCS W3W2	Temperature 850 °C, duration 30 s
10304700	RC340B 42S/930 DEIA W30L120 VPC PCS W3W2	Temperature 850 °C, duration 30 s
70832700	RC340B 42S/940 SEIA W60L60 VPC PCS U4 W3	Temperature 850 °C, duration 30 s
10250700	RC340B 36S/940 DIA W60L60 VPC O ELP3	Temperature 850 °C, duration 30 s
10263700	RC340B 42S/940 PSE W60L60 VPC O	Temperature 850 °C, duration 30 s
10264400	RC340B 42S/940 DEIA W60L60 VPC O	Temperature 850 °C, duration 30 s
10269900	RC340B 42S/940 DIA W60L60 VPC O ELP3	Temperature 850 °C, duration 30 s
10274300	RC340B 42S/940 DIA W60L60 VPC O ELD3	Temperature 850 °C, duration 30 s
10323800	RC340B 36S/940 PSE W60L60 VPC O SC	Temperature 850 °C, duration 30 s
10324500	RC340B 36S/940 DEIA W60L60 VPC O SC	Temperature 850 °C, duration 30 s
10232300	RC340B 36S/940 DEIA W60L60 VPC MLO	Temperature 650 °C, duration 30 s
10285900	RC340B 42S/930 DEIA W60L60 CPC MLO W3W2	Temperature 650 °C, duration 30 s
10290300	RC340B 42S/940 DEIA W60L60 CPC MLO W3W2	Temperature 650 °C, duration 30 s
10298900	RC340B 42S/940 DEIA W60L60 CPC PCS W3W2	Temperature 850 °C, duration 30 s
10302300	RC340B 42S/930 DEIA W60L60 CPC PCS W3W2	Temperature 850 °C, duration 30 s
10308500	RC340B 36S/940 PSE W60L60 CPC MLO	Temperature 650 °C, duration 30 s
10309200	RC340B 42S/940 PSE W60L60 CPC MLO	Temperature 650 °C, duration 30 s
10310800	RC340B 42S/940 DEIA W60L60 CPC MLO	Temperature 650 °C, duration 30 s
10330600	RC340B 42S/930 DEIA W30L120 CPC PCS W3W2	Temperature 850 °C, duration 30 s
10230900	RC340B 36S/940 DEIA W60L60 VPC O	Temperature 850 °C, duration 30 s
10235400	RC340B 36S/940 PSE W60L60 VPC PCS	Temperature 850 °C, duration 30 s
10236100	RC340B 36S/940 DEIA W60L60 VPC PCS	Temperature 850 °C, duration 30 s
10240800	RC340B 36S/940 DEIA W60L60 CPC MLO	Temperature 650 °C, duration 30 s
10254500	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	Temperature 850 °C, duration 30 s
10260600	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	Temperature 850 °C, duration 30 s
10265100	RC340B 42S/940 PSE W60L60 VPC PCS	Temperature 850 °C, duration 30 s
10266800	RC340B 42S/940 DEIA W60L60 VPC PCS	Temperature 850 °C, duration 30 s
10271200	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	Temperature 850 °C, duration 30 s
10296500	RC340B 42S/930 DEIA W60L60 VPC PCS W3W2	Temperature 850 °C, duration 30 s
10297200	RC340B 42S/940 DEIA W60L60 VPC PCS W3W2	Temperature 850 °C, duration 30 s
10306100	RC340B 36S/940 PSE W60L60 CPC PCS PIP	Temperature 850 °C, duration 30 s
10307800	RC340B 36S/940 DEIA W60L60 CPC PCS	Temperature 850 °C, duration 30 s
10311500	RC340B 42S/940 PSE W60L60 CPC PCS	Temperature 850 °C, duration 30 s
10312200	RC340B 42S/940 DEIA W60L60 CPC PCS	Temperature 850 °C, duration 30 s
10327600	RC340B 36S/940 PSE W60L60 VPC PCS SC	Temperature 850 °C, duration 30 s
10328300	RC340B 36S/940 DEIA W60L60 VPC PCS SC	Temperature 850 °C, duration 30 s
10229300	RC340B 36S/940 PSE W60L60 VPC O	Temperature 850 °C, duration 30 s

Order Code	Full Product Name	Glow-wire test
10243900	RC342B 36S/940 PSE W62L62 VPC MLO	Temperature 650 °C, duration 30 s
10252100	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	Temperature 650 °C, duration 30 s
10256900	RC340B 36S/940 DIA W60L60 VPC O ELD3	Temperature 850 °C, duration 30 s
10258300	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	Temperature 650 °C, duration 30 s
10262000	RC340B 42S/940 DEIA W60L60 VPC MLO	Temperature 650 °C, duration 30 s
10272900	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	Temperature 650 °C, duration 30 s
10275000	RC340B 42S/930 DEIA W60L60 VPC MLO W3W2	Temperature 650 °C, duration 30 s
10289700	RC340B 42S/940 DEIA W60L60 VPC MLO W3W2	Temperature 650 °C, duration 30 s
10305400	RC340B 42S/940 PSE W60L60 VPC MLO	Temperature 650 °C, duration 30 s
10325200	RC340B 36S/940 PSE W60L60 VPC MLO SC	Temperature 650 °C, duration 30 s
10326900	RC340B 36S/940 DEIA W60L60 VPC MLO SC	Temperature 650 °C, duration 30 s
10276700	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	Temperature 850 °C, duration 30 s
10287300	RC340B 42S/930 DEIA W60L60 PCV MLO W3W2	Temperature 650 °C, duration 30 s
10291000	RC340B 42S/940 DEIA W60L60 PCV MLO W3W2	Temperature 650 °C, duration 30 s
10299600	RC340B 42S/940 DEIA W60L60 PCV PCS W3W2	Temperature 850 °C, duration 30 s
10303000	RC340B 42S/930 DEIA W60L60 PCV PCS W3W2	Temperature 850 °C, duration 30 s
10429700	RC340B 36S/940 DEIA W60L60 PCV PCS	Temperature 850 °C, duration 30 s
10231600	RC340B 36S/940 PSE W60L60 VPC MLO PIP	Temperature 650 °C, duration 30 s
10241500	RC340B 36S/940 DEIA W60L60 PCV MLO	Temperature 650 °C, duration 30 s
10244600	RC342B 36S/940 DEIA W62L62 VPC MLO	Temperature 650 °C, duration 30 s
10420400	RC342B 36S/940 DEIA W62L62 VPC PCS	Temperature 850 °C, duration 30 s

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
10277400	RC340B 36S/940 PSE W15L120 VPC MLO	(0.38, 0.37) SDCM ≤3
10278100	RC340B 36S/940 DEIA W15L120 VPC MLO	(0.38, 0.37) SDCM ≤3
10279800	RC340B 42S/940 PSE W15L120 VPC MLO	(0.38, 0.37) SDCM ≤3
10280400	RC340B 42S/940 DEIA W15L120 VPC MLO	(0.38, 0.37) SDCM ≤3
10282800	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	(0.38, 0.37) SDCM ≤3
10284200	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	(0.38, 0.37) SDCM ≤3
10286600	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	(0.38, 0.37) SDCM ≤3
10288000	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	(0.38, 0.37) SDCM ≤3
10242200	RC340B 36S/940 DEIA W30L120 VPC MLO	(0.38, 0.37) SDCM ≤3
10245300	RC342B 36S/940 PSE W31L125 VPC MLO	(0.38, 0.37) SDCM ≤3
10246000	RC342B 36S/940 DEIA W31L125 VPC MLO	(0.38, 0.37) SDCM ≤3
10292700	RC340B 42S/940 DEIA W30L120 VPC MLO W3W2	(0.38, 0.37) SDCM ≤3
10293400	RC340B 42S/940 DEIA W30L120 CPC MLO W3W2	(0.38, 0.37) SDCM ≤3
10294100	RC340B 42S/930 DEIA W30L120 VPC MLO W3W2	(0.43, 0.40) SDCM <3
10295800	RC340B 42S/930 DEIA W30L120 CPC MLO W3W2	(0.43, 0.40) SDCM <3
10300900	RC340B 42S/940 DEIA W30L120 VPC PCS W3W2	(0.38, 0.37) SDCM ≤3
10301600	RC340B 42S/940 DEIA W30L120 CPC PCS W3W2	(0.38, 0.37) SDCM ≤3

Order Code	Full Product Name	Initial chromaticity
10304700	RC340B 42S/930 DEIA W30L120 VPC PCS W3W2	(0.43, 0.40) SDCM <3
70832700	RC340B 42S/940 SEIA W60L60 VPC PCS U4 W3	(0.38, 0.37) SDCM ≤3
10250700	RC340B 36S/940 DIA W60L60 VPC O ELP3	(0.38, 0.37) SDCM ≤3
10263700	RC340B 42S/940 PSE W60L60 VPC O	(0.38, 0.37) SDCM ≤3
10264400	RC340B 42S/940 DEIA W60L60 VPC O	(0.38, 0.37) SDCM ≤3
10269900	RC340B 42S/940 DIA W60L60 VPC O ELP3	(0.38, 0.37) SDCM ≤3
10274300	RC340B 42S/940 DIA W60L60 VPC O ELD3	(0.38, 0.37) SDCM ≤3
10323800	RC340B 36S/940 PSE W60L60 VPC O SC	(0.38, 0.37) SDCM ≤3
10324500	RC340B 36S/940 DEIA W60L60 VPC O SC	(0.38, 0.37) SDCM ≤3
10232300	RC340B 36S/940 DEIA W60L60 VPC MLO	(0.38, 0.37) SDCM ≤3
10285900	RC340B 42S/930 DEIA W60L60 CPC MLO W3W2	(0.43, 0.40) SDCM <3
10290300	RC340B 42S/940 DEIA W60L60 CPC MLO W3W2	(0.38, 0.37) SDCM ≤3
10298900	RC340B 42S/940 DEIA W60L60 CPC PCS W3W2	(0.38, 0.37) SDCM ≤3
10302300	RC340B 42S/930 DEIA W60L60 CPC PCS W3W2	(0.43, 0.40) SDCM <3
10308500	RC340B 36S/940 PSE W60L60 CPC MLO	(0.38, 0.37) SDCM ≤3
10309200	RC340B 42S/940 PSE W60L60 CPC MLO	(0.38, 0.37) SDCM ≤3
10310800	RC340B 42S/940 DEIA W60L60 CPC MLO	(0.38, 0.37) SDCM ≤3
10330600	RC340B 42S/930 DEIA W30L120 CPC PCS W3W2	(0.43, 0.40) SDCM <3
10230900	RC340B 36S/940 DEIA W60L60 VPC O	(0.38, 0.37) SDCM ≤3
10235400	RC340B 36S/940 PSE W60L60 VPC PCS	(0.38, 0.37) SDCM ≤3
10236100	RC340B 36S/940 DEIA W60L60 VPC PCS	(0.38, 0.37) SDCM ≤3
10240800	RC340B 36S/940 DEIA W60L60 CPC MLO	(0.38, 0.37) SDCM ≤3
10254500	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	(0.38, 0.37) SDCM ≤3
10260600	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	(0.38, 0.37) SDCM ≤3
10265100	RC340B 42S/940 PSE W60L60 VPC PCS	(0.38, 0.37) SDCM ≤3
10266800	RC340B 42S/940 DEIA W60L60 VPC PCS	(0.38, 0.37) SDCM ≤3
10271200	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	(0.38, 0.37) SDCM ≤3
10296500	RC340B 42S/930 DEIA W60L60 VPC PCS W3W2	(0.43, 0.40) SDCM <3
10297200	RC340B 42S/940 DEIA W60L60 VPC PCS W3W2	(0.38, 0.37) SDCM ≤3
10306100	RC340B 36S/940 PSE W60L60 CPC PCS PIP	(0.38, 0.37) SDCM ≤3
10307800	RC340B 36S/940 DEIA W60L60 CPC PCS	(0.38, 0.37) SDCM ≤3
10311500	RC340B 42S/940 PSE W60L60 CPC PCS	(0.38, 0.37) SDCM ≤3
10312200	RC340B 42S/940 DEIA W60L60 CPC PCS	(0.38, 0.37) SDCM ≤3
10327600	RC340B 36S/940 PSE W60L60 VPC PCS SC	(0.38, 0.37) SDCM ≤3
10328300	RC340B 36S/940 DEIA W60L60 VPC PCS SC	(0.38, 0.37) SDCM ≤3
10229300	RC340B 36S/940 PSE W60L60 VPC O	(0.38, 0.37) SDCM ≤3
10243900	RC342B 36S/940 PSE W62L62 VPC MLO	(0.38, 0.37) SDCM ≤3
10252100	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	(0.38, 0.37) SDCM ≤3
10256900	RC340B 36S/940 DIA W60L60 VPC O ELD3	(0.38, 0.37) SDCM ≤3
10258300	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	(0.38, 0.37) SDCM ≤3
10262000	RC340B 42S/940 DEIA W60L60 VPC MLO	(0.38, 0.37) SDCM ≤3
10272900	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	(0.38, 0.37) SDCM ≤3

Order Code	Full Product Name	Initial chromaticity
10275000	RC340B 42S/930 DEIA W60L60 VPC MLO W3W2	(0.43, 0.40) SDCM <3
10289700	RC340B 42S/940 DEIA W60L60 VPC MLO W3W2	(0.38, 0.37) SDCM ≤3
10305400	RC340B 42S/940 PSE W60L60 VPC MLO	(0.38, 0.37) SDCM ≤3
10325200	RC340B 36S/940 PSE W60L60 VPC MLO SC	(0.38, 0.37) SDCM ≤3
10326900	RC340B 36S/940 DEIA W60L60 VPC MLO SC	(0.38, 0.37) SDCM ≤3
10276700	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	(0.38, 0.37) SDCM ≤3
10287300	RC340B 42S/930 DEIA W60L60 PCV MLO W3W2	(0.43, 0.40) SDCM <3
10291000	RC340B 42S/940 DEIA W60L60 PCV MLO W3W2	(0.38, 0.37) SDCM ≤3
10299600	RC340B 42S/940 DEIA W60L60 PCV PCS W3W2	(0.38, 0.37) SDCM ≤3
10303000	RC340B 42S/930 DEIA W60L60 PCV PCS W3W2	(0.43, 0.40) SDCM <3
10429700	RC340B 36S/940 DEIA W60L60 PCV PCS	(0.38, 0.37) SDCM ≤3
10231600	RC340B 36S/940 PSE W60L60 VPC MLO PIP	(0.38, 0.37) SDCM ≤3
10241500	RC340B 36S/940 DEIA W60L60 PCV MLO	(0.38, 0.37) SDCM ≤3
10244600	RC342B 36S/940 DEIA W62L62 VPC MLO	(0.38, 0.37) SDCM ≤3
10420400	RC342B 36S/940 DEIA W62L62 VPC PCS	(0.38, 0.37) SDCM ≤3


Product Data

Order Code	Full Product Name	Product family code
10277400	RC340B 36S/940 PSE W15L120 VPC MLO	RC340B
10278100	RC340B 36S/940 DEIA W15L120 VPC MLO	RC340B
10279800	RC340B 42S/940 PSE W15L120 VPC MLO	RC340B
10280400	RC340B 42S/940 DEIA W15L120 VPC MLO	RC340B
10282800	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	RC340B
10284200	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	RC340B
10286600	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	RC340B
10288000	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	RC340B
10242200	RC340B 36S/940 DEIA W30L120 VPC MLO	RC340B
10245300	RC342B 36S/940 PSE W31L125 VPC MLO	RC342B
10246000	RC342B 36S/940 DEIA W31L125 VPC MLO	RC342B
10292700	RC340B 42S/940 DEIA W30L120 VPC MLO W3W2	RC340B
10293400	RC340B 42S/940 DEIA W30L120 CPC MLO W3W2	RC340B
10294100	RC340B 42S/930 DEIA W30L120 VPC MLO W3W2	RC340B
10295800	RC340B 42S/930 DEIA W30L120 CPC MLO W3W2	RC340B
10300900	RC340B 42S/940 DEIA W30L120 VPC PCS W3W2	RC340B
10301600	RC340B 42S/940 DEIA W30L120 CPC PCS W3W2	RC340B
10304700	RC340B 42S/930 DEIA W30L120 VPC PCS W3W2	RC340B
70832700	RC340B 42S/940 SEIA W60L60 VPC PCS U4 W3	RC340B
10250700	RC340B 36S/940 DIA W60L60 VPC O ELP3	RC340B
10263700	RC340B 42S/940 PSE W60L60 VPC O	RC340B
10264400	RC340B 42S/940 DEIA W60L60 VPC O	RC340B
10269900	RC340B 42S/940 DIA W60L60 VPC O ELP3	RC340B


Order Code	Full Product Name	Product family code
10274300	RC340B 42S/940 DIA W60L60 VPC O ELD3	RC340B
10323800	RC340B 36S/940 PSE W60L60 VPC O SC	RC340B
10324500	RC340B 36S/940 DEIA W60L60 VPC O SC	RC340B
10232300	RC340B 36S/940 DEIA W60L60 VPC MLO	RC340B
10285900	RC340B 42S/930 DEIA W60L60 CPC MLO W3W2	RC340B
10290300	RC340B 42S/940 DEIA W60L60 CPC MLO W3W2	RC340B
10298900	RC340B 42S/940 DEIA W60L60 CPC PCS W3W2	RC340B
10302300	RC340B 42S/930 DEIA W60L60 CPC PCS W3W2	RC340B
10308500	RC340B 36S/940 PSE W60L60 CPC MLO	RC340B
10309200	RC340B 42S/940 PSE W60L60 CPC MLO	RC340B
10310800	RC340B 42S/940 DEIA W60L60 CPC MLO	RC340B
10330600	RC340B 42S/930 DEIA W30L120 CPC PCS W3W2	RC340B
10230900	RC340B 36S/940 DEIA W60L60 VPC O	RC340B
10235400	RC340B 36S/940 PSE W60L60 VPC PCS	RC340B
10236100	RC340B 36S/940 DEIA W60L60 VPC PCS	RC340B
10240800	RC340B 36S/940 DEIA W60L60 CPC MLO	RC340B
10254500	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	RC340B
10260600	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	RC340B
10265100	RC340B 42S/940 PSE W60L60 VPC PCS	RC340B
10266800	RC340B 42S/940 DEIA W60L60 VPC PCS	RC340B
10271200	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	RC340B
10296500	RC340B 42S/930 DEIA W60L60 VPC PCS W3W2	RC340B
10297200	RC340B 42S/940 DEIA W60L60 VPC PCS W3W2	RC340B
10306100	RC340B 36S/940 PSE W60L60 CPC PCS PIP	RC340B
10307800	RC340B 36S/940 DEIA W60L60 CPC PCS	RC340B
10311500	RC340B 42S/940 PSE W60L60 CPC PCS	RC340B
10312200	RC340B 42S/940 DEIA W60L60 CPC PCS	RC340B
10327600	RC340B 36S/940 PSE W60L60 VPC PCS SC	RC340B
10328300	RC340B 36S/940 DEIA W60L60 VPC PCS SC	RC340B
10229300	RC340B 36S/940 PSE W60L60 VPC O	RC340B
10243900	RC342B 36S/940 PSE W62L62 VPC MLO	RC342B
10252100	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	RC340B
10256900	RC340B 36S/940 DIA W60L60 VPC O ELD3	RC340B
10258300	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	RC340B
10262000	RC340B 42S/940 DEIA W60L60 VPC MLO	RC340B
10272900	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	RC340B
10275000	RC340B 42S/930 DEIA W60L60 VPC MLO W3W2	RC340B
10289700	RC340B 42S/940 DEIA W60L60 VPC MLO W3W2	RC340B
10305400	RC340B 42S/940 PSE W60L60 VPC MLO	RC340B
10325200	RC340B 36S/940 PSE W60L60 VPC MLO SC	RC340B
10326900	RC340B 36S/940 DEIA W60L60 VPC MLO SC	RC340B
10276700	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	RC340B

Order Code	Full Product Name	Product family code
10287300	RC340B 42S/930 DEIA W60L60 PCV MLO W3W2	RC340B
10291000	RC340B 42S/940 DEIA W60L60 PCV MLO W3W2	RC340B
10299600	RC340B 42S/940 DEIA W60L60 PCV PCS W3W2	RC340B
10303000	RC340B 42S/930 DEIA W60L60 PCV PCS W3W2	RC340B
10429700	RC340B 36S/940 DEIA W60L60 PCV PCS	RC340B
10231600	RC340B 36S/940 PSE W60L60 VPC MLO PIP	RC340B
10241500	RC340B 36S/940 DEIA W60L60 PCV MLO	RC340B
10244600	RC342B 36S/940 DEIA W62L62 VPC MLO	RC342B
10420400	RC342B 36S/940 DEIA W62L62 VPC PCS	RC342B


Polar normal diagrams




RC340BI - 910925866978




RC340BI - 910925866989




RC340BI - 910925867030




RC340BI - 910925867031




RC340BI - 910925866987




RC340BI - 910925868920




RC340BI - 910925866969




RC340BI - 910925866968




RC340BI - 910925866979




RC340BI - 910925866981




RC340BI - 910925867038




RC340BI - 910925867040




RC340BI - 910925867050




RC340BI - 910925866973




RC340BI - 910925866991




RC340BI - 910925866993




RC340BI - 910925867002




RC340BI - 910925867003




RC340BI - 910925866977




RC340BI - 910925866995




RC340BI - 910925867012




RC340BI - 910925867017




RC340BI - 910925867033




RC340BI - 910925867024




RC340BI - 910925867043




RC340BI - 910925867049




RC340BI - 910925866967




RC340BI - 910925867010




RC340BI - 910925867013




RC340BI - 910925867022




RC340BI - 910925867034




RC340BI - 910925867039




RC340BI - 910925867032




RC340BI - 910925867064




RC340BI - 910925866980




RC340BI - 910925866982




RC340BI - 910925866983




RC340BI - 910925866997




RC340BI - 910925867009




RC340BI - 910925867047




RC340BI - 910925867062




RC340BI - 910925867063




RC340BI - 910925866966




RC340BI - 910925867018




RC340BI - 910925867016




RC340BI - 910925867025




RC340BI - 910925867028




RC340BI - 910925867014




RC340BI - 910925867020




RC340BI - 910925867026




RC340BI - 910925867035




RC340BI - 910925867036




RC340BI - 910925867044




RC340BI - 910925867045




RC340BI - 910925867048




RC340BI - 910925867065




RC340BI - 910925867159




RC340BI - 910925867041




RC340BI - 910925867066




RC340BI - 910925866972




RC340BI - 910925866999




RC340BI - 910925867001




RC340BI - 910925867004




RC340BI - 910925867007




RC340BI - 910925867015




RC340BI - 910925867023




RC340BI - 910925867027




RC340BI - 910925867029




RC340BI - 910925867037




RC340BI - 910925867046




RC340BI - 910925867042



RC340BI - 910925867061



RC340BI - 910925867068



RC340BI - 910925867168