




FlexBlend - Unlocking the potential of LED lighting in offices

Office owners and staff responsible for lighting operations are searching for high quality yet energy-efficient lighting that complies with norms and regulations. Designed to support these needs, Philips FlexBlend is enabling building owners to fully optimize their lighting operations, by offering office-compliant lighting with an attractive return on investment. Furthermore, FlexBlend provides the required flexibility by being easy applied on different ceiling types as well as in different office spaces like open office or meeting rooms. Though technology is changing fast, the ideal lighting solution is also expected to be ready to incorporate innovations and future advances that can help optimize operations further. For this reason, Philips FlexBlend is also ready to be connected to controls such as Actilume or used together with the Philips SpaceWise lighting system. It can also be connected to software-based lighting systems like Interact Office, which provides the luminaire with further intelligence and enables it to collect valuable data about its environment

Benefits

- High-quality office-compliant lighting
- Choice of three different exit-windows
- Fast return on investment

- Application flexibility
- Scalable and ready to be connected to controls and lighting systems

Applications

- Offices
- Education

- Healthcare
- Banks

Features

- Fully office-compliant (UGR <19)
- Homogenous and uniform light effect

- Dimensional variety, local options
- Various mounting options
- Integrated sensors
- Can be combined with Philips ActiLume and SpaceWise systems
- Ready to be connected to software based lighting systems such as Interact Office


Versions




FlexBlend Recessed RC340B
W15L120 MLO VPC




FlexBlend Recessed-RC340B
W30L120 MLO VPC




FlexBlend Recessed RC340B
W60L60 OPA VPC




FlexBlend Recessed RC340B
W60L60 MLO CPC




FlexBlend Recessed RC340B
W60L60 PCS VPC



FlexBlend Recessed RC340B
W60L60 MLO VPC




FlexBlend Recessed RC340B
W60L60 MLO PCV




FlexBlend Recessed RC342B
W62L62 MLO VPC


Dimensional drawing




RC342B 42S/940 DEIA W62L62 VPC O




RC342B 28S/940 DEIA W31L125 VPC O




RC340B 36S/940 DEIA W30L120 VPC MLO




RC340B 36S/940 DEIA W15L120 VPC MLO




FLEXBLEND RECESSED, module 625 - 940 neutral white - Power supply unit with DALI interface - Plug-in connector 3-pole Wieland/Adels compatible




RC342B 42S/940 DEIA W62L62 CPC PCS



RC340B 36S/940 PSE W60L60 CPC MLO



FLEXBLEND RECESSED, module 625 - 940 neutral white - Power supply unit with DALI interface - Plug-in connector 3-pole Wieland/Adels compatible



RC340B 42S/940 DIA W60L60 VPC O ELP3

Product details

0_FlexBlend Recessed-
RC342B_W62L62_MLO_VPC



FlexBlend Recessed-
RC340B_MLO_DPP




FlexBlend Recessed-
RC340B_W60L60_Backcover_V
PC



FlexBlend Recessed-
RC340B_W60L60_CPC
brackets





FlexBlend Recessed-RC340B_W60L60_CPC brackets_B



FlexBlend Recessed-RC340B_OPA_DPP



FlexBlend Recessed-RC340B_PCS_DPP



0_FlexBlend Recessed-RC340B_W60L60_PCS_VPC



FlexBlend Recessed-RC340B_W60L60_CPC brackets_A



FlexBlend Recessed RC340B PIP Open



FlexBlend Recessed-RC340B_W60L60_backcover_P CV



0_FlexBlend Recessed-RC340B_W60L60_MLO_VPC



0_FlexBlend Recessed-RC340B_W60L60_MLO_CPC



FlexBlend Recessed-RC340B PIP Closed



FlexBlend Recessed-
RC340B_W60L60_backcover_C
PC

General Information

Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Service tag	Yes

Light Technical

Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	>90
Beam angle of light source	120 degree(s)
Optic type	Wide beam

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	Yes
Protection class IEC	Safety class I

Controls and Dimming

Maximum dim level	1%
-------------------	----

Mechanical and Housing

Housing Color	White
Mech. impact protection code	IK02 [0.2 J standard]

Emergency Operation

Rated duration of the emergency lighting (when fully charged)	3 hour(s)
---	-----------

Approval and Application

Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	+10 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.37) SDCM ≤3

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.01 %
-------------------------------	--------

Light Technical

Order Code	Full Product Name	Luminous Flux	Luminous Efficacy (rated) (Nom)
910925867015	RC340B 36S/940 PSE W15L120 VPC MLO	3,600 lm	95 lm/W
910925867016	RC340B 36S/940 DEIA W15L120 VPC MLO	3,600 lm	95 lm/W
910925867017	RC340B 42S/940 PSE W15L120 VPC MLO	4,200 lm	93 lm/W
910925867018	RC340B 42S/940 DEIA W15L120 VPC MLO	4,200 lm	93 lm/W
910925867020	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	3,600 lm	95 lm/W
910925867022	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	4,200 lm	93 lm/W
910925867024	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	3,600 lm	95 lm/W
910925867026	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	4,200 lm	93 lm/W
910925867149	RC342B 28S/940 DEIA W15L125 VPC MLO	2,800 lm	110 lm/W
910925867150	RC342B 36S/940 DEIA W15L125 VPC MLO	3,600 lm	95 lm/W
910925867153	RC342B 36S/940 DEIA W17L125 PCV MLO	3,600 lm	95 lm/W
910925867164	RC342B 28S/940 DEIA W15L125 VPC PCS	2,800 lm	127 lm/W
910925867165	RC342B 36S/940 DEIA W15L125 VPC PCS	3,600 lm	138 lm/W
910925867166	RC342B 42S/940 DEIA W15L125 VPC PCS	4,200 lm	138 lm/W
910925867169	RC342B 36S/940 DEIA W17L125 PCV PCS	3,600 lm	144 lm/W
910925867180	RC342B 28S/940 DEIA W15L125 VPC O	2,800 lm	124 lm/W
910925867181	RC342B 36S/940 DEIA W15L125 VPC O	3,600 lm	126 lm/W
910925867182	RC342B 42S/940 DEIA W15L125 VPC O	4,200 lm	125 lm/W
910925866979	RC340B 36S/940 DEIA W30L120 VPC MLO	3,600 lm	95 lm/W
910925866982	RC342B 36S/940 PSE W31L125 VPC MLO	3,600 lm	95 lm/W
910925866983	RC342B 36S/940 DEIA W31L125 VPC MLO	3,600 lm	95 lm/W

Order Code	Full Product Name	Luminous Flux	Luminous Efficacy (rated) (Nom)
910925867147	RC342B 28S/940 DEIA W31L125 VPC MLO	2,800 lm	110 lm/W
910925867161	RC342B 28S/940 DEIA W31L125 VPC PCS	2,800 lm	127 lm/W
910925867162	RC342B 36S/940 DEIA W31L125 VPC PCS	3,600 lm	138 lm/W
910925867163	RC342B 42S/940 DEIA W31L125 VPC PCS	4,200 lm	138 lm/W
910925867177	RC342B 28S/940 DEIA W31L125 VPC O	2,800 lm	124 lm/W
910925867178	RC342B 36S/940 DEIA W31L125 VPC O	3,600 lm	126 lm/W
910925867179	RC342B 42S/940 DEIA W31L125 VPC O	4,200 lm	125 lm/W
910925866987	RC340B 36S/940 DIA W60L60 VPC O ELP3	3,600 lm	126 lm/W
910925867001	RC340B 42S/940 PSE W60L60 VPC O	4,200 lm	125 lm/W
910925867002	RC340B 42S/940 DEIA W60L60 VPC O	4,200 lm	125 lm/W
910925867007	RC340B 42S/940 DIA W60L60 VPC O ELP3	4,200 lm	125 lm/W
910925867012	RC340B 42S/940 DIA W60L60 VPC O ELD3	4,200 lm	125 lm/W
910925867061	RC340B 36S/940 PSE W60L60 VPC O SC	3,600 lm	126 lm/W
910925867062	RC340B 36S/940 DEIA W60L60 VPC O SC	3,600 lm	126 lm/W
910925866969	RC340B 36S/940 DEIA W60L60 VPC MLO	3,600 lm	95 lm/W
910925867046	RC340B 36S/940 PSE W60L60 CPC MLO	3,600 lm	95 lm/W
910925867047	RC340B 42S/940 PSE W60L60 CPC MLO	4,200 lm	93 lm/W
910925867048	RC340B 42S/940 DEIA W60L60 CPC MLO	4,200 lm	93 lm/W
910925867167	RC342B 42S/940 DEIA W62L62 CPC PCS	4,200 lm	138 lm/W
910925866967	RC340B 36S/940 DEIA W60L60 VPC O	3,600 lm	126 lm/W
910925866972	RC340B 36S/940 PSE W60L60 VPC PCS	3,600 lm	138 lm/W
910925866973	RC340B 36S/940 DEIA W60L60 VPC PCS	3,600 lm	138 lm/W
910925866977	RC340B 36S/940 DEIA W60L60 CPC MLO	3,600 lm	95 lm/W
910925866991	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	3,600 lm	138 lm/W
910925866997	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	3,600 lm	138 lm/W
910925867003	RC340B 42S/940 PSE W60L60 VPC PCS	4,200 lm	138 lm/W
910925867004	RC340B 42S/940 DEIA W60L60 VPC PCS	4,200 lm	138 lm/W
910925867009	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	4,200 lm	138 lm/W
910925867044	RC340B 36S/940 PSE W60L60 CPC PCS PIP	3,600 lm	138 lm/W
910925867045	RC340B 36S/940 DEIA W60L60 CPC PCS	3,600 lm	138 lm/W
910925867049	RC340B 42S/940 PSE W60L60 CPC PCS	4,200 lm	138 lm/W
910925867050	RC340B 42S/940 DEIA W60L60 CPC PCS	4,200 lm	138 lm/W
910925867065	RC340B 36S/940 PSE W60L60 VPC PCS SC	3,600 lm	138 lm/W
910925867066	RC340B 36S/940 DEIA W60L60 VPC PCS SC	3,600 lm	138 lm/W
910925866966	RC340B 36S/940 PSE W60L60 VPC O	3,600 lm	126 lm/W
910925866980	RC342B 36S/940 PSE W62L62 VPC MLO	3,600 lm	95 lm/W
910925866989	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	3,600 lm	95 lm/W
910925866993	RC340B 36S/940 DIA W60L60 VPC O ELD3	3,600 lm	126 lm/W
910925866995	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	3,600 lm	95 lm/W
910925866999	RC340B 42S/940 DEIA W60L60 VPC MLO	4,200 lm	93 lm/W
910925867010	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	4,200 lm	93 lm/W
910925867043	RC340B 42S/940 PSE W60L60 VPC MLO	4,200 lm	93 lm/W

Order Code	Full Product Name	Luminous Flux	Luminous Efficacy (rated) (Nom)
910925867063	RC340B 36S/940 PSE W60L60 VPC MLO SC	3,600 lm	95 lm/W
910925867064	RC340B 36S/940 DEIA W60L60 VPC MLO SC	3,600 lm	95 lm/W
910925867014	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	4,200 lm	138 lm/W
910925866968	RC340B 36S/940 PSE W60L60 VPC MLO PIP	3,600 lm	95 lm/W
910925866978	RC340B 36S/940 DEIA W60L60 PCV MLO	3,600 lm	95 lm/W
910925866981	RC342B 36S/940 DEIA W62L62 VPC MLO	3,600 lm	95 lm/W
910925867145	RC342B 28S/940 DEIA W62L62 VPC MLO	2,800 lm	110 lm/W
910925867158	RC342B 28S/940 DEIA W62L62 VPC PCS	2,800 lm	127 lm/W
910925867159	RC342B 36S/940 DEIA W62L62 VPC PCS	3,600 lm	144 lm/W
910925867160	RC342B 42S/940 DEIA W62L62 VPC PCS	4,200 lm	138 lm/W
910925867174	RC342B 28S/940 DEIA W62L62 VPC O	2,800 lm	124 lm/W
910925867175	RC342B 36S/940 DEIA W62L62 VPC O	3,600 lm	126 lm/W
910925867176	RC342B 42S/940 DEIA W62L62 VPC O	4,200 lm	125 lm/W

Operating and Electrical

Order Code	Full Product Name	Power Consumption
910925867015	RC340B 36S/940 PSE W15L120 VPC MLO	38 W
910925867016	RC340B 36S/940 DEIA W15L120 VPC MLO	38 W
910925867017	RC340B 42S/940 PSE W15L120 VPC MLO	45 W
910925867018	RC340B 42S/940 DEIA W15L120 VPC MLO	45 W
910925867020	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	38 W
910925867022	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	45 W
910925867024	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	38 W
910925867026	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	45 W
910925867149	RC342B 28S/940 DEIA W15L125 VPC MLO	25.5 W
910925867150	RC342B 36S/940 DEIA W15L125 VPC MLO	38 W
910925867153	RC342B 36S/940 DEIA W17L125 PCV MLO	38 W
910925867164	RC342B 28S/940 DEIA W15L125 VPC PCS	22 W
910925867165	RC342B 36S/940 DEIA W15L125 VPC PCS	26 W
910925867166	RC342B 42S/940 DEIA W15L125 VPC PCS	30.5 W
910925867169	RC342B 36S/940 DEIA W17L125 PCV PCS	25 W
910925867180	RC342B 28S/940 DEIA W15L125 VPC O	22.5 W
910925867181	RC342B 36S/940 DEIA W15L125 VPC O	28.5 W
910925867182	RC342B 42S/940 DEIA W15L125 VPC O	33.5 W
910925866979	RC340B 36S/940 DEIA W30L120 VPC MLO	38 W
910925866982	RC342B 36S/940 PSE W31L125 VPC MLO	37 W
910925866983	RC342B 36S/940 DEIA W31L125 VPC MLO	38 W
910925867147	RC342B 28S/940 DEIA W31L125 VPC MLO	25.5 W
910925867161	RC342B 28S/940 DEIA W31L125 VPC PCS	22 W
910925867162	RC342B 36S/940 DEIA W31L125 VPC PCS	26 W
910925867163	RC342B 42S/940 DEIA W31L125 VPC PCS	30.5 W

Order Code	Full Product Name	Power Consumption
910925867177	RC342B 28S/940 DEIA W31L125 VPC O	22.5 W
910925867178	RC342B 36S/940 DEIA W31L125 VPC O	28.5 W
910925867179	RC342B 42S/940 DEIA W31L125 VPC O	33.5 W
910925866987	RC340B 36S/940 DIA W60L60 VPC O ELP3	28.5 W
910925867001	RC340B 42S/940 PSE W60L60 VPC O	33.5 W
910925867002	RC340B 42S/940 DEIA W60L60 VPC O	33.5 W
910925867007	RC340B 42S/940 DIA W60L60 VPC O ELP3	33.5 W
910925867012	RC340B 42S/940 DIA W60L60 VPC O ELD3	33.5 W
910925867061	RC340B 36S/940 PSE W60L60 VPC O SC	28.5 W
910925867062	RC340B 36S/940 DEIA W60L60 VPC O SC	28.5 W
910925866969	RC340B 36S/940 DEIA W60L60 VPC MLO	38 W
910925867046	RC340B 36S/940 PSE W60L60 CPC MLO	38 W
910925867047	RC340B 42S/940 PSE W60L60 CPC MLO	45 W
910925867048	RC340B 42S/940 DEIA W60L60 CPC MLO	45 W
910925867167	RC342B 42S/940 DEIA W62L62 CPC PCS	30.5 W
910925866967	RC340B 36S/940 DEIA W60L60 VPC O	28.5 W
910925866972	RC340B 36S/940 PSE W60L60 VPC PCS	26 W
910925866973	RC340B 36S/940 DEIA W60L60 VPC PCS	26 W
910925866977	RC340B 36S/940 DEIA W60L60 CPC MLO	38 W
910925866991	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	26 W
910925866997	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	26 W
910925867003	RC340B 42S/940 PSE W60L60 VPC PCS	30.5 W
910925867004	RC340B 42S/940 DEIA W60L60 VPC PCS	30.5 W
910925867009	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	30.5 W
910925867044	RC340B 36S/940 PSE W60L60 CPC PCS PIP	26 W
910925867045	RC340B 36S/940 DEIA W60L60 CPC PCS	26 W
910925867049	RC340B 42S/940 PSE W60L60 CPC PCS	30.5 W
910925867050	RC340B 42S/940 DEIA W60L60 CPC PCS	30.5 W
910925867065	RC340B 36S/940 PSE W60L60 VPC PCS SC	26 W
910925867066	RC340B 36S/940 DEIA W60L60 VPC PCS SC	26 W
910925866966	RC340B 36S/940 PSE W60L60 VPC O	28.5 W
910925866980	RC342B 36S/940 PSE W62L62 VPC MLO	37 W
910925866989	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	38 W
910925866993	RC340B 36S/940 DIA W60L60 VPC O ELD3	28.5 W
910925866995	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	38 W
910925866999	RC340B 42S/940 DEIA W60L60 VPC MLO	45 W
910925867010	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	45 W
910925867043	RC340B 42S/940 PSE W60L60 VPC MLO	45 W
910925867063	RC340B 36S/940 PSE W60L60 VPC MLO SC	38 W
910925867064	RC340B 36S/940 DEIA W60L60 VPC MLO SC	38 W
910925867014	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	30.5 W
910925866968	RC340B 36S/940 PSE W60L60 VPC MLO PIP	38 W

Order Code	Full Product Name	Power Consumption
910925866978	RC340B 36S/940 DEIA W60L60 PCV MLO	38 W
910925866981	RC342B 36S/940 DEIA W62L62 VPC MLO	38 W
910925867145	RC342B 28S/940 DEIA W62L62 VPC MLO	25.5 W
910925867158	RC342B 28S/940 DEIA W62L62 VPC PCS	22 W
910925867159	RC342B 36S/940 DEIA W62L62 VPC PCS	25 W
910925867160	RC342B 42S/940 DEIA W62L62 VPC PCS	30.5 W
910925867174	RC342B 28S/940 DEIA W62L62 VPC O	22.5 W
910925867175	RC342B 36S/940 DEIA W62L62 VPC O	28.5 W
910925867176	RC342B 42S/940 DEIA W62L62 VPC O	33.5 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
910925867015	RC340B 36S/940 PSE W15L120 VPC MLO	No
910925867016	RC340B 36S/940 DEIA W15L120 VPC MLO	Yes
910925867017	RC340B 42S/940 PSE W15L120 VPC MLO	No
910925867018	RC340B 42S/940 DEIA W15L120 VPC MLO	Yes
910925867020	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	Yes
910925867022	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	Yes
910925867024	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	Yes
910925867026	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	Yes
910925867149	RC342B 28S/940 DEIA W15L125 VPC MLO	Yes
910925867150	RC342B 36S/940 DEIA W15L125 VPC MLO	Yes
910925867153	RC342B 36S/940 DEIA W17L125 PCV MLO	Yes
910925867164	RC342B 28S/940 DEIA W15L125 VPC PCS	Yes
910925867165	RC342B 36S/940 DEIA W15L125 VPC PCS	Yes
910925867166	RC342B 42S/940 DEIA W15L125 VPC PCS	Yes
910925867169	RC342B 36S/940 DEIA W17L125 PCV PCS	Yes
910925867180	RC342B 28S/940 DEIA W15L125 VPC O	Yes
910925867181	RC342B 36S/940 DEIA W15L125 VPC O	Yes
910925867182	RC342B 42S/940 DEIA W15L125 VPC O	Yes
910925866979	RC340B 36S/940 DEIA W30L120 VPC MLO	Yes
910925866982	RC342B 36S/940 PSE W31L125 VPC MLO	No
910925866983	RC342B 36S/940 DEIA W31L125 VPC MLO	Yes
910925867147	RC342B 28S/940 DEIA W31L125 VPC MLO	Yes
910925867161	RC342B 28S/940 DEIA W31L125 VPC PCS	Yes
910925867162	RC342B 36S/940 DEIA W31L125 VPC PCS	Yes
910925867163	RC342B 42S/940 DEIA W31L125 VPC PCS	Yes
910925867177	RC342B 28S/940 DEIA W31L125 VPC O	Yes
910925867178	RC342B 36S/940 DEIA W31L125 VPC O	Yes
910925867179	RC342B 42S/940 DEIA W31L125 VPC O	Yes
910925866987	RC340B 36S/940 DIA W60L60 VPC O ELP3	Yes

Order Code	Full Product Name	Dimmable
910925867001	RC340B 42S/940 PSE W60L60 VPC O	No
910925867002	RC340B 42S/940 DEIA W60L60 VPC O	Yes
910925867007	RC340B 42S/940 DIA W60L60 VPC O ELP3	Yes
910925867012	RC340B 42S/940 DIA W60L60 VPC O ELD3	Yes
910925867061	RC340B 36S/940 PSE W60L60 VPC O SC	No
910925867062	RC340B 36S/940 DEIA W60L60 VPC O SC	Yes
910925866969	RC340B 36S/940 DEIA W60L60 VPC MLO	Yes
910925867046	RC340B 36S/940 PSE W60L60 CPC MLO	No
910925867047	RC340B 42S/940 PSE W60L60 CPC MLO	No
910925867048	RC340B 42S/940 DEIA W60L60 CPC MLO	Yes
910925867167	RC342B 42S/940 DEIA W62L62 CPC PCS	Yes
910925866967	RC340B 36S/940 DEIA W60L60 VPC O	Yes
910925866972	RC340B 36S/940 PSE W60L60 VPC PCS	No
910925866973	RC340B 36S/940 DEIA W60L60 VPC PCS	Yes
910925866977	RC340B 36S/940 DEIA W60L60 CPC MLO	Yes
910925866991	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	Yes
910925866997	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	Yes
910925867003	RC340B 42S/940 PSE W60L60 VPC PCS	No
910925867004	RC340B 42S/940 DEIA W60L60 VPC PCS	Yes
910925867009	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	Yes
910925867044	RC340B 36S/940 PSE W60L60 CPC PCS PIP	No
910925867045	RC340B 36S/940 DEIA W60L60 CPC PCS	Yes
910925867049	RC340B 42S/940 PSE W60L60 CPC PCS	No
910925867050	RC340B 42S/940 DEIA W60L60 CPC PCS	Yes
910925867065	RC340B 36S/940 PSE W60L60 VPC PCS SC	No
910925867066	RC340B 36S/940 DEIA W60L60 VPC PCS SC	Yes
910925866966	RC340B 36S/940 PSE W60L60 VPC O	No
910925866980	RC342B 36S/940 PSE W62L62 VPC MLO	No
910925866989	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	Yes
910925866993	RC340B 36S/940 DIA W60L60 VPC O ELD3	Yes
910925866995	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	Yes
910925866999	RC340B 42S/940 DEIA W60L60 VPC MLO	Yes
910925867010	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	Yes
910925867043	RC340B 42S/940 PSE W60L60 VPC MLO	No
910925867063	RC340B 36S/940 PSE W60L60 VPC MLO SC	No
910925867064	RC340B 36S/940 DEIA W60L60 VPC MLO SC	Yes
910925867014	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	Yes
910925866968	RC340B 36S/940 PSE W60L60 VPC MLO PIP	No
910925866978	RC340B 36S/940 DEIA W60L60 PCV MLO	Yes
910925866981	RC342B 36S/940 DEIA W62L62 VPC MLO	Yes
910925867145	RC342B 28S/940 DEIA W62L62 VPC MLO	Yes
910925867158	RC342B 28S/940 DEIA W62L62 VPC PCS	Yes

Order Code	Full Product Name	Dimmable
910925867159	RC342B 36S/940 DEIA W62L62 VPC PCS	Yes
910925867160	RC342B 42S/940 DEIA W62L62 VPC PCS	Yes
910925867174	RC342B 28S/940 DEIA W62L62 VPC O	Yes
910925867175	RC342B 36S/940 DEIA W62L62 VPC O	Yes
910925867176	RC342B 42S/940 DEIA W62L62 VPC O	Yes

Mechanical and Housing

Order Code	Full Product Name	Ingress protection code
910925867015	RC340B 36S/940 PSE W15L120 VPC MLO	IP20/40
910925867016	RC340B 36S/940 DEIA W15L120 VPC MLO	IP20/40
910925867017	RC340B 42S/940 PSE W15L120 VPC MLO	IP20/40
910925867018	RC340B 42S/940 DEIA W15L120 VPC MLO	IP20/40
910925867020	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	IP20
910925867022	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	IP20
910925867024	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	IP20
910925867026	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	IP20
910925867149	RC342B 28S/940 DEIA W15L125 VPC MLO	IP20/40
910925867150	RC342B 36S/940 DEIA W15L125 VPC MLO	IP20/40
910925867153	RC342B 36S/940 DEIA W17L125 PCV MLO	IP20/40
910925867164	RC342B 28S/940 DEIA W15L125 VPC PCS	IP20/54
910925867165	RC342B 36S/940 DEIA W15L125 VPC PCS	IP20/54
910925867166	RC342B 42S/940 DEIA W15L125 VPC PCS	IP20/54
910925867169	RC342B 36S/940 DEIA W17L125 PCV PCS	IP20/54
910925867180	RC342B 28S/940 DEIA W15L125 VPC O	IP20/54
910925867181	RC342B 36S/940 DEIA W15L125 VPC O	IP20/54
910925867182	RC342B 42S/940 DEIA W15L125 VPC O	IP20/54
910925866979	RC340B 36S/940 DEIA W30L120 VPC MLO	IP20/40
910925866982	RC342B 36S/940 PSE W31L125 VPC MLO	IP20/40
910925866983	RC342B 36S/940 DEIA W31L125 VPC MLO	IP20/40
910925867147	RC342B 28S/940 DEIA W31L125 VPC MLO	IP20/40
910925867161	RC342B 28S/940 DEIA W31L125 VPC PCS	IP20/54
910925867162	RC342B 36S/940 DEIA W31L125 VPC PCS	IP20/54
910925867163	RC342B 42S/940 DEIA W31L125 VPC PCS	IP20/54
910925867177	RC342B 28S/940 DEIA W31L125 VPC O	IP20/54
910925867178	RC342B 36S/940 DEIA W31L125 VPC O	IP20/54
910925867179	RC342B 42S/940 DEIA W31L125 VPC O	IP20/54
910925866987	RC340B 36S/940 DIA W60L60 VPC O ELP3	IP54
910925867001	RC340B 42S/940 PSE W60L60 VPC O	IP20/54
910925867002	RC340B 42S/940 DEIA W60L60 VPC O	IP20/54
910925867007	RC340B 42S/940 DIA W60L60 VPC O ELP3	IP20/54
910925867012	RC340B 42S/940 DIA W60L60 VPC O ELD3	IP54

Order Code	Full Product Name	Ingress protection code
910925867061	RC340B 36S/940 PSE W60L60 VPC O SC	IP20/54
910925867062	RC340B 36S/940 DEIA W60L60 VPC O SC	IP20/54
910925866969	RC340B 36S/940 DEIA W60L60 VPC MLO	IP20/40
910925867046	RC340B 36S/940 PSE W60L60 CPC MLO	IP20/40
910925867047	RC340B 42S/940 PSE W60L60 CPC MLO	IP20/40
910925867048	RC340B 42S/940 DEIA W60L60 CPC MLO	IP20/40
910925867167	RC342B 42S/940 DEIA W62L62 CPC PCS	IP20/54
910925866967	RC340B 36S/940 DEIA W60L60 VPC O	IP20/54
910925866972	RC340B 36S/940 PSE W60L60 VPC PCS	IP20/54
910925866973	RC340B 36S/940 DEIA W60L60 VPC PCS	IP20/54
910925866977	RC340B 36S/940 DEIA W60L60 CPC MLO	IP20/40
910925866991	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	IP20/54
910925866997	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	IP20/54
910925867003	RC340B 42S/940 PSE W60L60 VPC PCS	IP20/54
910925867004	RC340B 42S/940 DEIA W60L60 VPC PCS	IP20/54
910925867009	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	IP20/54
910925867044	RC340B 36S/940 PSE W60L60 CPC PCS PIP	IP20/54
910925867045	RC340B 36S/940 DEIA W60L60 CPC PCS	IP20/54
910925867049	RC340B 42S/940 PSE W60L60 CPC PCS	IP20/54
910925867050	RC340B 42S/940 DEIA W60L60 CPC PCS	IP20/54
910925867065	RC340B 36S/940 PSE W60L60 VPC PCS SC	IP20/54
910925867066	RC340B 36S/940 DEIA W60L60 VPC PCS SC	IP20/54
910925866966	RC340B 36S/940 PSE W60L60 VPC O	IP20/54
910925866980	RC342B 36S/940 PSE W62L62 VPC MLO	IP20/40
910925866989	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	IP20/54
910925866993	RC340B 36S/940 DIA W60L60 VPC O ELD3	IP54
910925866995	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	IP20/54
910925866999	RC340B 42S/940 DEIA W60L60 VPC MLO	IP20/40
910925867010	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	IP20
910925867043	RC340B 42S/940 PSE W60L60 VPC MLO	IP20/40
910925867063	RC340B 36S/940 PSE W60L60 VPC MLO SC	IP20/40
910925867064	RC340B 36S/940 DEIA W60L60 VPC MLO SC	IP20/40
910925867014	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	IP20/54
910925866968	RC340B 36S/940 PSE W60L60 VPC MLO PIP	IP20/40
910925866978	RC340B 36S/940 DEIA W60L60 PCV MLO	IP20/40
910925866981	RC342B 36S/940 DEIA W62L62 VPC MLO	IP20/40
910925867145	RC342B 28S/940 DEIA W62L62 VPC MLO	IP20/40
910925867158	RC342B 28S/940 DEIA W62L62 VPC PCS	IP20/54
910925867159	RC342B 36S/940 DEIA W62L62 VPC PCS	IP20/54
910925867160	RC342B 42S/940 DEIA W62L62 VPC PCS	IP20/54
910925867174	RC342B 28S/940 DEIA W62L62 VPC O	IP20/54
910925867175	RC342B 36S/940 DEIA W62L62 VPC O	IP20/54
910925867176	RC342B 42S/940 DEIA W62L62 VPC O	IP20/54

Emergency Operation

Order Code	Full Product Name	Central Emergency	Emergency lighting
910925867015	RC340B 36S/940 PSE W15L120 VPC MLO	-	-
910925867016	RC340B 36S/940 DEIA W15L120 VPC MLO	Yes	DC operated central emergency lighting
910925867017	RC340B 42S/940 PSE W15L120 VPC MLO	-	-
910925867018	RC340B 42S/940 DEIA W15L120 VPC MLO	Yes	DC operated central emergency lighting
910925867020	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	No	Emergency lighting 3 hours duration Pro version
910925867022	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	No	Emergency lighting 3 hours duration Pro version
910925867024	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	No	Emergency lighting 3 hours duration Pro version
910925867026	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	No	Emergency lighting 3 hours duration Pro version
910925867149	RC342B 28S/940 DEIA W15L125 VPC MLO	Yes	DC operated central emergency lighting
910925867150	RC342B 36S/940 DEIA W15L125 VPC MLO	Yes	DC operated central emergency lighting
910925867153	RC342B 36S/940 DEIA W17L125 PCV MLO	Yes	DC operated central emergency lighting
910925867164	RC342B 28S/940 DEIA W15L125 VPC PCS	Yes	DC operated central emergency lighting
910925867165	RC342B 36S/940 DEIA W15L125 VPC PCS	Yes	DC operated central emergency lighting
910925867166	RC342B 42S/940 DEIA W15L125 VPC PCS	Yes	DC operated central emergency lighting
910925867169	RC342B 36S/940 DEIA W17L125 PCV PCS	Yes	DC operated central emergency lighting
910925867180	RC342B 28S/940 DEIA W15L125 VPC O	Yes	DC operated central emergency lighting
910925867181	RC342B 36S/940 DEIA W15L125 VPC O	Yes	DC operated central emergency lighting
910925867182	RC342B 42S/940 DEIA W15L125 VPC O	Yes	DC operated central emergency lighting
910925866979	RC340B 36S/940 DEIA W30L120 VPC MLO	Yes	DC operated central emergency lighting
910925866982	RC342B 36S/940 PSE W31L125 VPC MLO	-	-
910925866983	RC342B 36S/940 DEIA W31L125 VPC MLO	Yes	DC operated central emergency lighting
910925867147	RC342B 28S/940 DEIA W31L125 VPC MLO	Yes	DC operated central emergency lighting
910925867161	RC342B 28S/940 DEIA W31L125 VPC PCS	Yes	DC operated central emergency lighting
910925867162	RC342B 36S/940 DEIA W31L125 VPC PCS	Yes	DC operated central emergency lighting
910925867163	RC342B 42S/940 DEIA W31L125 VPC PCS	Yes	DC operated central emergency lighting
910925867177	RC342B 28S/940 DEIA W31L125 VPC O	Yes	DC operated central emergency lighting
910925867178	RC342B 36S/940 DEIA W31L125 VPC O	Yes	DC operated central emergency lighting
910925867179	RC342B 42S/940 DEIA W31L125 VPC O	Yes	DC operated central emergency lighting
910925866987	RC340B 36S/940 DIA W60L60 VPC O ELP3	No	Emergency lighting 3 hours duration Pro version
910925867001	RC340B 42S/940 PSE W60L60 VPC O	-	-
910925867002	RC340B 42S/940 DEIA W60L60 VPC O	Yes	DC operated central emergency lighting
910925867007	RC340B 42S/940 DIA W60L60 VPC O ELP3	No	Emergency lighting 3 hours duration Pro version
910925867012	RC340B 42S/940 DIA W60L60 VPC O ELD3	No	Emergency lighting 3 hours duration with DALI interface
910925867061	RC340B 36S/940 PSE W60L60 VPC O SC	-	-
910925867062	RC340B 36S/940 DEIA W60L60 VPC O SC	Yes	DC operated central emergency lighting
910925866969	RC340B 36S/940 DEIA W60L60 VPC MLO	Yes	DC operated central emergency lighting
910925867046	RC340B 36S/940 PSE W60L60 CPC MLO	-	-
910925867047	RC340B 42S/940 PSE W60L60 CPC MLO	-	-
910925867048	RC340B 42S/940 DEIA W60L60 CPC MLO	Yes	DC operated central emergency lighting
910925867167	RC342B 42S/940 DEIA W62L62 CPC PCS	Yes	DC operated central emergency lighting
910925866967	RC340B 36S/940 DEIA W60L60 VPC O	Yes	DC operated central emergency lighting

Order Code	Full Product Name	Central Emergency	Emergency lighting
910925866972	RC340B 36S/940 PSE W60L60 VPC PCS	-	-
910925866973	RC340B 36S/940 DEIA W60L60 VPC PCS	Yes	DC operated central emergency lighting
910925866977	RC340B 36S/940 DEIA W60L60 CPC MLO	Yes	DC operated central emergency lighting
910925866991	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	No	Emergency lighting 3 hours duration Pro version
910925866997	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	No	Emergency lighting 3 hours duration with DALI interface
910925867003	RC340B 42S/940 PSE W60L60 VPC PCS	-	-
910925867004	RC340B 42S/940 DEIA W60L60 VPC PCS	Yes	DC operated central emergency lighting
910925867009	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	No	Emergency lighting 3 hours duration Pro version
910925867044	RC340B 36S/940 PSE W60L60 CPC PCS PIP	-	-
910925867045	RC340B 36S/940 DEIA W60L60 CPC PCS	Yes	DC operated central emergency lighting
910925867049	RC340B 42S/940 PSE W60L60 CPC PCS	-	-
910925867050	RC340B 42S/940 DEIA W60L60 CPC PCS	Yes	DC operated central emergency lighting
910925867065	RC340B 36S/940 PSE W60L60 VPC PCS SC	-	-
910925867066	RC340B 36S/940 DEIA W60L60 VPC PCS SC	Yes	DC operated central emergency lighting
910925866966	RC340B 36S/940 PSE W60L60 VPC O	-	-
910925866980	RC342B 36S/940 PSE W62L62 VPC MLO	-	-
910925866989	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	No	Emergency lighting 3 hours duration Pro version
910925866993	RC340B 36S/940 DIA W60L60 VPC O ELD3	No	Emergency lighting 3 hours duration with DALI interface
910925866995	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	No	Emergency lighting 3 hours duration with DALI interface
910925866999	RC340B 42S/940 DEIA W60L60 VPC MLO	Yes	DC operated central emergency lighting
910925867010	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	No	Emergency lighting 3 hours duration with DALI interface
910925867043	RC340B 42S/940 PSE W60L60 VPC MLO	-	-
910925867063	RC340B 36S/940 PSE W60L60 VPC MLO SC	-	-
910925867064	RC340B 36S/940 DEIA W60L60 VPC MLO SC	Yes	DC operated central emergency lighting
910925867014	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	No	Emergency lighting 3 hours duration with DALI interface
910925866968	RC340B 36S/940 PSE W60L60 VPC MLO PIP	-	-
910925866978	RC340B 36S/940 DEIA W60L60 PCV MLO	Yes	DC operated central emergency lighting
910925866981	RC342B 36S/940 DEIA W62L62 VPC MLO	Yes	DC operated central emergency lighting
910925867145	RC342B 28S/940 DEIA W62L62 VPC MLO	Yes	DC operated central emergency lighting
910925867158	RC342B 28S/940 DEIA W62L62 VPC PCS	Yes	DC operated central emergency lighting
910925867159	RC342B 36S/940 DEIA W62L62 VPC PCS	Yes	DC operated central emergency lighting
910925867160	RC342B 42S/940 DEIA W62L62 VPC PCS	Yes	DC operated central emergency lighting
910925867174	RC342B 28S/940 DEIA W62L62 VPC O	Yes	DC operated central emergency lighting
910925867175	RC342B 36S/940 DEIA W62L62 VPC O	Yes	DC operated central emergency lighting
910925867176	RC342B 42S/940 DEIA W62L62 VPC O	Yes	DC operated central emergency lighting

Approval and Application

Order Code	Full Product Name	Glow-wire test
910925867015	RC340B 36S/940 PSE W15L120 VPC MLO	Temperature 650 °C, duration 30 s
910925867016	RC340B 36S/940 DEIA W15L120 VPC MLO	Temperature 650 °C, duration 30 s
910925867017	RC340B 42S/940 PSE W15L120 VPC MLO	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Glow-wire test
910925867018	RC340B 42S/940 DEIA W15L120 VPC MLO	Temperature 650 °C, duration 30 s
910925867020	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	Temperature 650 °C, duration 30 s
910925867022	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	Temperature 650 °C, duration 30 s
910925867024	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	Temperature 650 °C, duration 30 s
910925867026	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	Temperature 650 °C, duration 30 s
910925867149	RC342B 28S/940 DEIA W15L125 VPC MLO	Temperature 650 °C, duration 30 s
910925867150	RC342B 36S/940 DEIA W15L125 VPC MLO	Temperature 650 °C, duration 30 s
910925867153	RC342B 36S/940 DEIA W17L125 PCV MLO	Temperature 650 °C, duration 30 s
910925867164	RC342B 28S/940 DEIA W15L125 VPC PCS	Temperature 850 °C, duration 30 s
910925867165	RC342B 36S/940 DEIA W15L125 VPC PCS	Temperature 850 °C, duration 30 s
910925867166	RC342B 42S/940 DEIA W15L125 VPC PCS	Temperature 850 °C, duration 30 s
910925867169	RC342B 36S/940 DEIA W17L125 PCV PCS	Temperature 850 °C, duration 30 s
910925867180	RC342B 28S/940 DEIA W15L125 VPC O	Temperature 850 °C, duration 30 s
910925867181	RC342B 36S/940 DEIA W15L125 VPC O	Temperature 850 °C, duration 30 s
910925867182	RC342B 42S/940 DEIA W15L125 VPC O	Temperature 850 °C, duration 30 s
910925866979	RC340B 36S/940 DEIA W30L120 VPC MLO	Temperature 650 °C, duration 30 s
910925866982	RC342B 36S/940 PSE W31L125 VPC MLO	Temperature 650 °C, duration 30 s
910925866983	RC342B 36S/940 DEIA W31L125 VPC MLO	Temperature 650 °C, duration 30 s
910925867147	RC342B 28S/940 DEIA W31L125 VPC MLO	Temperature 650 °C, duration 30 s
910925867161	RC342B 28S/940 DEIA W31L125 VPC PCS	Temperature 850 °C, duration 30 s
910925867162	RC342B 36S/940 DEIA W31L125 VPC PCS	Temperature 850 °C, duration 30 s
910925867163	RC342B 42S/940 DEIA W31L125 VPC PCS	Temperature 850 °C, duration 30 s
910925867177	RC342B 28S/940 DEIA W31L125 VPC O	Temperature 850 °C, duration 30 s
910925867178	RC342B 36S/940 DEIA W31L125 VPC O	Temperature 850 °C, duration 30 s
910925867179	RC342B 42S/940 DEIA W31L125 VPC O	Temperature 850 °C, duration 30 s
910925866987	RC340B 36S/940 DIA W60L60 VPC O ELP3	Temperature 850 °C, duration 30 s
910925867001	RC340B 42S/940 PSE W60L60 VPC O	Temperature 850 °C, duration 30 s
910925867002	RC340B 42S/940 DEIA W60L60 VPC O	Temperature 850 °C, duration 30 s
910925867007	RC340B 42S/940 DIA W60L60 VPC O ELP3	Temperature 850 °C, duration 30 s
910925867012	RC340B 42S/940 DIA W60L60 VPC O ELD3	Temperature 850 °C, duration 30 s
910925867061	RC340B 36S/940 PSE W60L60 VPC O SC	Temperature 850 °C, duration 30 s
910925867062	RC340B 36S/940 DEIA W60L60 VPC O SC	Temperature 850 °C, duration 30 s
910925866969	RC340B 36S/940 DEIA W60L60 VPC MLO	Temperature 650 °C, duration 30 s
910925867046	RC340B 36S/940 PSE W60L60 CPC MLO	Temperature 650 °C, duration 30 s
910925867047	RC340B 42S/940 PSE W60L60 CPC MLO	Temperature 650 °C, duration 30 s
910925867048	RC340B 42S/940 DEIA W60L60 CPC MLO	Temperature 650 °C, duration 30 s
910925867167	RC342B 42S/940 DEIA W62L62 CPC PCS	Temperature 850 °C, duration 30 s
910925866967	RC340B 36S/940 DEIA W60L60 VPC O	Temperature 850 °C, duration 30 s
910925866972	RC340B 36S/940 PSE W60L60 VPC PCS	Temperature 850 °C, duration 30 s
910925866973	RC340B 36S/940 DEIA W60L60 VPC PCS	Temperature 850 °C, duration 30 s
910925866977	RC340B 36S/940 DEIA W60L60 CPC MLO	Temperature 650 °C, duration 30 s
910925866991	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	Temperature 850 °C, duration 30 s

Order Code	Full Product Name	Glow-wire test
910925866997	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	Temperature 850 °C, duration 30 s
910925867003	RC340B 42S/940 PSE W60L60 VPC PCS	Temperature 850 °C, duration 30 s
910925867004	RC340B 42S/940 DEIA W60L60 VPC PCS	Temperature 850 °C, duration 30 s
910925867009	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	Temperature 850 °C, duration 30 s
910925867044	RC340B 36S/940 PSE W60L60 CPC PCS PIP	Temperature 850 °C, duration 30 s
910925867045	RC340B 36S/940 DEIA W60L60 CPC PCS	Temperature 850 °C, duration 30 s
910925867049	RC340B 42S/940 PSE W60L60 CPC PCS	Temperature 850 °C, duration 30 s
910925867050	RC340B 42S/940 DEIA W60L60 CPC PCS	Temperature 850 °C, duration 30 s
910925867065	RC340B 36S/940 PSE W60L60 VPC PCS SC	Temperature 850 °C, duration 30 s
910925867066	RC340B 36S/940 DEIA W60L60 VPC PCS SC	Temperature 850 °C, duration 30 s
910925866966	RC340B 36S/940 PSE W60L60 VPC O	Temperature 850 °C, duration 30 s
910925866980	RC342B 36S/940 PSE W62L62 VPC MLO	Temperature 650 °C, duration 30 s
910925866989	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	Temperature 650 °C, duration 30 s
910925866993	RC340B 36S/940 DIA W60L60 VPC O ELD3	Temperature 850 °C, duration 30 s
910925866995	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	Temperature 650 °C, duration 30 s
910925866999	RC340B 42S/940 DEIA W60L60 VPC MLO	Temperature 650 °C, duration 30 s
910925867010	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	Temperature 650 °C, duration 30 s
910925867043	RC340B 42S/940 PSE W60L60 VPC MLO	Temperature 650 °C, duration 30 s
910925867063	RC340B 36S/940 PSE W60L60 VPC MLO SC	Temperature 650 °C, duration 30 s
910925867064	RC340B 36S/940 DEIA W60L60 VPC MLO SC	Temperature 650 °C, duration 30 s
910925867014	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	Temperature 850 °C, duration 30 s
910925866968	RC340B 36S/940 PSE W60L60 VPC MLO PIP	Temperature 650 °C, duration 30 s
910925866978	RC340B 36S/940 DEIA W60L60 PCV MLO	Temperature 650 °C, duration 30 s
910925866981	RC342B 36S/940 DEIA W62L62 VPC MLO	Temperature 650 °C, duration 30 s
910925867145	RC342B 28S/940 DEIA W62L62 VPC MLO	Temperature 650 °C, duration 30 s
910925867158	RC342B 28S/940 DEIA W62L62 VPC PCS	Temperature 850 °C, duration 30 s
910925867159	RC342B 36S/940 DEIA W62L62 VPC PCS	Temperature 850 °C, duration 30 s
910925867160	RC342B 42S/940 DEIA W62L62 VPC PCS	Temperature 850 °C, duration 30 s
910925867174	RC342B 28S/940 DEIA W62L62 VPC O	Temperature 850 °C, duration 30 s
910925867175	RC342B 36S/940 DEIA W62L62 VPC O	Temperature 850 °C, duration 30 s
910925867176	RC342B 42S/940 DEIA W62L62 VPC O	Temperature 850 °C, duration 30 s


Product Data

Order Code	Full Product Name	Product family code
910925867015	RC340B 36S/940 PSE W15L120 VPC MLO	RC340B
910925867016	RC340B 36S/940 DEIA W15L120 VPC MLO	RC340B
910925867017	RC340B 42S/940 PSE W15L120 VPC MLO	RC340B
910925867018	RC340B 42S/940 DEIA W15L120 VPC MLO	RC340B
910925867020	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	RC340B
910925867022	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	RC340B
910925867024	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	RC340B


Order Code	Full Product Name	Product family code
910925867026	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	RC340B
910925867149	RC342B 28S/940 DEIA W15L125 VPC MLO	RC342B
910925867150	RC342B 36S/940 DEIA W15L125 VPC MLO	RC342B
910925867153	RC342B 36S/940 DEIA W17L125 PCV MLO	RC342B
910925867164	RC342B 28S/940 DEIA W15L125 VPC PCS	RC342B
910925867165	RC342B 36S/940 DEIA W15L125 VPC PCS	RC342B
910925867166	RC342B 42S/940 DEIA W15L125 VPC PCS	RC342B
910925867169	RC342B 36S/940 DEIA W17L125 PCV PCS	RC342B
910925867180	RC342B 28S/940 DEIA W15L125 VPC O	RC342B
910925867181	RC342B 36S/940 DEIA W15L125 VPC O	RC342B
910925867182	RC342B 42S/940 DEIA W15L125 VPC O	RC342B
910925866979	RC340B 36S/940 DEIA W30L120 VPC MLO	RC340B
910925866982	RC342B 36S/940 PSE W31L125 VPC MLO	RC342B
910925866983	RC342B 36S/940 DEIA W31L125 VPC MLO	RC342B
910925867147	RC342B 28S/940 DEIA W31L125 VPC MLO	RC342B
910925867161	RC342B 28S/940 DEIA W31L125 VPC PCS	RC342B
910925867162	RC342B 36S/940 DEIA W31L125 VPC PCS	RC342B
910925867163	RC342B 42S/940 DEIA W31L125 VPC PCS	RC342B
910925867177	RC342B 28S/940 DEIA W31L125 VPC O	RC342B
910925867178	RC342B 36S/940 DEIA W31L125 VPC O	RC342B
910925867179	RC342B 42S/940 DEIA W31L125 VPC O	RC342B
910925866987	RC340B 36S/940 DIA W60L60 VPC O ELP3	RC340B
910925867001	RC340B 42S/940 PSE W60L60 VPC O	RC340B
910925867002	RC340B 42S/940 DEIA W60L60 VPC O	RC340B
910925867007	RC340B 42S/940 DIA W60L60 VPC O ELP3	RC340B
910925867012	RC340B 42S/940 DIA W60L60 VPC O ELD3	RC340B
910925867061	RC340B 36S/940 PSE W60L60 VPC O SC	RC340B
910925867062	RC340B 36S/940 DEIA W60L60 VPC O SC	RC340B
910925866969	RC340B 36S/940 DEIA W60L60 VPC MLO	RC340B
910925867046	RC340B 36S/940 PSE W60L60 CPC MLO	RC340B
910925867047	RC340B 42S/940 PSE W60L60 CPC MLO	RC340B
910925867048	RC340B 42S/940 DEIA W60L60 CPC MLO	RC340B
910925867167	RC342B 42S/940 DEIA W62L62 CPC PCS	RC342B
910925866967	RC340B 36S/940 DEIA W60L60 VPC O	RC340B
910925866972	RC340B 36S/940 PSE W60L60 VPC PCS	RC340B
910925866973	RC340B 36S/940 DEIA W60L60 VPC PCS	RC340B
910925866977	RC340B 36S/940 DEIA W60L60 CPC MLO	RC340B
910925866991	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	RC340B
910925866997	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	RC340B
910925867003	RC340B 42S/940 PSE W60L60 VPC PCS	RC340B
910925867004	RC340B 42S/940 DEIA W60L60 VPC PCS	RC340B
910925867009	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	RC340B

Order Code	Full Product Name	Product family code
910925867044	RC340B 36S/940 PSE W60L60 CPC PCS PIP	RC340B
910925867045	RC340B 36S/940 DEIA W60L60 CPC PCS	RC340B
910925867049	RC340B 42S/940 PSE W60L60 CPC PCS	RC340B
910925867050	RC340B 42S/940 DEIA W60L60 CPC PCS	RC340B
910925867065	RC340B 36S/940 PSE W60L60 VPC PCS SC	RC340B
910925867066	RC340B 36S/940 DEIA W60L60 VPC PCS SC	RC340B
910925866966	RC340B 36S/940 PSE W60L60 VPC O	RC340B
910925866980	RC342B 36S/940 PSE W62L62 VPC MLO	RC342B
910925866989	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	RC340B
910925866993	RC340B 36S/940 DIA W60L60 VPC O ELD3	RC340B
910925866995	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	RC340B
910925866999	RC340B 42S/940 DEIA W60L60 VPC MLO	RC340B
910925867010	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	RC340B
910925867043	RC340B 42S/940 PSE W60L60 VPC MLO	RC340B
910925867063	RC340B 36S/940 PSE W60L60 VPC MLO SC	RC340B
910925867064	RC340B 36S/940 DEIA W60L60 VPC MLO SC	RC340B
910925867014	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	RC340B
910925866968	RC340B 36S/940 PSE W60L60 VPC MLO PIP	RC340B
910925866978	RC340B 36S/940 DEIA W60L60 PCV MLO	RC340B
910925866981	RC342B 36S/940 DEIA W62L62 VPC MLO	RC342B
910925867145	RC342B 28S/940 DEIA W62L62 VPC MLO	RC342B
910925867158	RC342B 28S/940 DEIA W62L62 VPC PCS	RC342B
910925867159	RC342B 36S/940 DEIA W62L62 VPC PCS	RC342B
910925867160	RC342B 42S/940 DEIA W62L62 VPC PCS	RC342B
910925867174	RC342B 28S/940 DEIA W62L62 VPC O	RC342B
910925867175	RC342B 36S/940 DEIA W62L62 VPC O	RC342B
910925867176	RC342B 42S/940 DEIA W62L62 VPC O	RC342B


Polar normal diagrams




RC340BI - 910925866978




RC340BI - 910925866989




RC340BI - 910925866987




RC340BI - 910925866969




RC340BI - 910925866968




RC340BI - 910925866979




RC340BI - 910925866981




RC340BI - 910925867050




RC340BI - 910925866973




RC340BI - 910925866991




RC340BI - 910925866993




RC340BI - 910925867002




RC340BI - 910925867003




RC340BI - 910925866977




RC340BI - 910925866995




RC340BI - 910925867012




RC340BI - 910925867017




RC340BI - 910925867024




RC340BI - 910925867043




RC340BI - 910925867049




RC340BI - 910925866967




RC340BI - 910925867010




RC340BI - 910925867022




RC340BI - 910925867064




RC340BI - 910925866980




RC340BI - 910925866982




RC340BI - 910925866983




RC340BI - 910925866997




RC340BI - 910925867009




RC340BI - 910925867047




RC340BI - 910925867062




RC340BI - 910925867063




RC340BI - 910925866966




RC340BI - 910925867018




RC340BI - 910925867016




RC340BI - 910925867014




RC340BI - 910925867145




RC340BI - 910925867147




RC340BI - 910925867020




RC340BI - 910925867026




RC340BI - 910925867044




RC340BI - 910925867045




RC340BI - 910925867048




RC340BI - 910925867065




RC340BI - 910925867149




RC340BI - 910925867159




RC340BI - 910925867158




RC340BI - 910925867165




RC340BI - 910925867166




RC340BI - 910925867167




RC340BI - 910925867177




RC340BI - 910925867178




RC340BI - 910925867066




RC340BI - 910925867162




RC340BI - 910925867160




RC340BI - 910925867153




RC340BI - 910925867175




RC340BI - 910925867179




RC340BI - 910925867182




RC340BI - 910925867163




RC340BI - 910925867174




RC340BI - 910925867176




RC340BI - 910925866972




RC340BI - 910925866999




RC340BI - 910925867001




RC340BI - 910925867004




RC340BI - 910925867007




RC340BI - 910925867015




RC340BI - 910925867046




RC340BI - 910925867061




RC340BI - 910925867150




RC340BI - 910925867161




RC340BI - 910925867164



RC340BI - 910925867169



RC340BI - 910925867181



RC340BI - 910925867180