

FlexBlend - Unlocking the potential of LED lighting in offices

FlexBlend Recessed

Office owners and staff responsible for lighting operations are searching for high quality yet energy-efficient lighting that complies with norms and regulations. Designed to support these needs, Philips FlexBlend is enabling building owners to fully optimize their lighting operations, by offering office-compliant lighting with an attractive return on investment. Furthermore, FlexBlend provides the required flexibility by being easy applied on different ceiling types as well as in different office spaces like open office or meeting rooms. Though technology is changing fast, the ideal lighting solution is also expected to be ready to incorporate innovations and future advances that can help optimize operations further. For this reason, Philips FlexBlend is also ready to be connected to controls such as Actilume or used together with the Philips SpaceWise lighting system. It can also be connected to software-based lighting systems like Interact Office, which provides the luminaire with further intelligence and enables it to collect valuable data about its environment

Benefits

- High-quality office-compliant lighting
- Choice of three different exit-windows
- Fast return on investment
- Application flexibility
- Scalable and ready to be connected to controls and lighting systems

FlexBlend Recessed

Features

- Fully office-compliant (UGR <19)
- Homogenous and uniform light effect
- Dimensional variety, local options
- Various mounting options
- Integrated sensors
- Can be combined with Philips ActiLume and SpaceWise systems
- Ready to be connected to software based lighting systems such as Interact Office

Application


- Offices
- Education
- Healthcare
- Banks

Versions




FlexBlend Recessed RC340B
W60L60 MLO PCV

Dimensional drawing



FlexBlend Recessed

Dimensional drawing



FlexBlend Recessed

Product details

O_FlexBlend Recessed-
RC342B_W62L62_MLO_VPC




FlexBlend Recessed-
RC340B_MLO_DPP



FlexBlend Recessed-
RC340B_W60L60_Backcover_VP
C




FlexBlend Recessed-
RC340B_W60L60_CPC brackets



FlexBlend Recessed-
RC340B_W60L60_CPC
brackets_B



FlexBlend Recessed-
RC340B_OPA_DPP



FlexBlend Recessed-
RC340B_PCS_DPP



O_FlexBlend Recessed-
RC340B_W60L60_PCS_VPC



FlexBlend Recessed


Product details



FlexBlend Recessed-
RC340B_W60L60_CPC
brackets_A



FlexBlend Recessed RC340B PIP
Open



FlexBlend Recessed-
RC340B_W60L60_backcover_PC
V



O_FlexBlend Recessed-
RC340B_W60L60_MLO_VPC



O_FlexBlend Recessed-
RC340B_W60L60_MLO_CPC



FlexBlend Recessed-RC340B PIP
Closed



FlexBlend Recessed-
RC340B_W60L60_backcover_CP
C

FlexBlend Recessed

General Information	
Driver included	Yes
Light source replaceable	No
Number of gear units	1 unit
Service tag	Yes
Light Technical	
Beam angle of light source	120 degree(s)
Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	>90
Optic type	Wide beam
Operating and Electrical	
Protection class IEC	Safety class I
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	Yes
Controls and Dimming	
Maximum dim level	1%
Mechanical and Housing	
Housing Color	White
Mech. impact protection code	IK02
Approval and Application	
Ambient temperature range	+10 to +40 °C
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Initial Performance (IEC Compliant)	
Initial chromaticity	(0.38, 0.37) SDCM ≤3
Luminous flux tolerance	+/-10%

Light Technical

Order Code	Full Product Name	Luminous Efficacy (rated)	
		(Nom)	Luminous Flux
910925867015	RC340B 36S/940 PSE W15L120 VPC MLO	95 lm/W	3,600 lm
910925867016	RC340B 36S/940 DEIA W15L120 VPC MLO	95 lm/W	3,600 lm
910925867017	RC340B 42S/940 PSE W15L120 VPC MLO	93 lm/W	4,200 lm
910925867018	RC340B 42S/940 DEIA W15L120 VPC MLO	93 lm/W	4,200 lm
910925867020	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	95 lm/W	3,600 lm
910925867022	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	93 lm/W	4,200 lm
910925867024	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	95 lm/W	3,600 lm
910925867026	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	93 lm/W	4,200 lm
910925867149	RC342B 28S/940 DEIA W15L125 VPC MLO	110 lm/W	2,800 lm
910925867150	RC342B 36S/940 DEIA W15L125 VPC MLO	95 lm/W	3,600 lm
910925867153	RC342B 36S/940 DEIA W17L125 PCV MLO	95 lm/W	3,600 lm
910925867164	RC342B 28S/940 DEIA W15L125 VPC PCS	127 lm/W	2,800 lm
910925867165	RC342B 36S/940 DEIA W15L125 VPC PCS	138 lm/W	3,600 lm
910925867166	RC342B 42S/940 DEIA W15L125 VPC PCS	138 lm/W	4,200 lm
910925867169	RC342B 36S/940 DEIA W17L125 PCV PCS	144 lm/W	3,600 lm
910925867180	RC342B 28S/940 DEIA W15L125 VPC O	124 lm/W	2,800 lm
910925867181	RC342B 36S/940 DEIA W15L125 VPC O	126 lm/W	3,600 lm
910925867182	RC342B 42S/940 DEIA W15L125 VPC O	125 lm/W	4,200 lm
910925866979	RC340B 36S/940 DEIA W30L120 VPC MLO	95 lm/W	3,600 lm
910925866982	RC342B 36S/940 PSE W31L125 VPC MLO	95 lm/W	3,600 lm
910925866983	RC342B 36S/940 DEIA W31L125 VPC MLO	95 lm/W	3,600 lm
910925867147	RC342B 28S/940 DEIA W31L125 VPC MLO	110 lm/W	2,800 lm
910925867161	RC342B 28S/940 DEIA W31L125 VPC PCS	127 lm/W	2,800 lm
910925867162	RC342B 36S/940 DEIA W31L125 VPC PCS	138 lm/W	3,600 lm
910925867163	RC342B 42S/940 DEIA W31L125 VPC PCS	138 lm/W	4,200 lm
910925867177	RC342B 28S/940 DEIA W31L125 VPC O	124 lm/W	2,800 lm
910925867178	RC342B 36S/940 DEIA W31L125 VPC O	126 lm/W	3,600 lm
910925867179	RC342B 42S/940 DEIA W31L125 VPC O	125 lm/W	4,200 lm
910925866987	RC340B 36S/940 DIA W60L60 VPC O ELP3	126 lm/W	3,600 lm
910925867001	RC340B 42S/940 PSE W60L60 VPC O	125 lm/W	4,200 lm
910925867002	RC340B 42S/940 DEIA W60L60 VPC O	125 lm/W	4,200 lm
910925867007	RC340B 42S/940 DIA W60L60 VPC O ELP3	125 lm/W	4,200 lm
910925867012	RC340B 42S/940 DIA W60L60 VPC O ELD3	125 lm/W	4,200 lm
910925867061	RC340B 36S/940 PSE W60L60 VPC O SC	126 lm/W	3,600 lm
910925867062	RC340B 36S/940 DEIA W60L60 VPC O SC	126 lm/W	3,600 lm
910925866969	RC340B 36S/940 DEIA W60L60 VPC MLO	95 lm/W	3,600 lm
910925867046	RC340B 36S/940 PSE W60L60 CPC MLO	95 lm/W	3,600 lm
910925867047	RC340B 42S/940 PSE W60L60 CPC MLO	93 lm/W	4,200 lm
910925867048	RC340B 42S/940 DEIA W60L60 CPC MLO	93 lm/W	4,200 lm
910925867167	RC342B 42S/940 DEIA W62L62 CPC PCS	138 lm/W	4,200 lm
910925866967	RC340B 36S/940 DEIA W60L60 VPC O	126 lm/W	3,600 lm
910925866972	RC340B 36S/940 PSE W60L60 VPC PCS	138 lm/W	3,600 lm
910925866973	RC340B 36S/940 DEIA W60L60 VPC PCS	138 lm/W	3,600 lm
910925866977	RC340B 36S/940 DEIA W60L60 CPC MLO	95 lm/W	3,600 lm
910925866991	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	138 lm/W	3,600 lm
910925866997	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	138 lm/W	3,600 lm
910925867003	RC340B 42S/940 PSE W60L60 VPC PCS	138 lm/W	4,200 lm
910925867004	RC340B 42S/940 DEIA W60L60 VPC PCS	138 lm/W	4,200 lm
910925867009	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	138 lm/W	4,200 lm
910925867044	RC340B 36S/940 PSE W60L60 CPC PCS PIP	138 lm/W	3,600 lm

FlexBlend Recessed

Order Code	Full Product Name	Luminous Efficacy (rated)	
		(Nom)	Luminous Flux
910925867045	RC340B 36S/940 DEIA W60L60 CPC PCS	138 lm/W	3,600 lm
910925867049	RC340B 42S/940 PSE W60L60 CPC PCS	138 lm/W	4,200 lm
910925867050	RC340B 42S/940 DEIA W60L60 CPC PCS	138 lm/W	4,200 lm
910925867065	RC340B 36S/940 PSE W60L60 VPC PCS SC	138 lm/W	3,600 lm
910925867066	RC340B 36S/940 DEIA W60L60 VPC PCS SC	138 lm/W	3,600 lm
910925866966	RC340B 36S/940 PSE W60L60 VPC O	126 lm/W	3,600 lm
910925866980	RC342B 36S/940 PSE W62L62 VPC MLO	95 lm/W	3,600 lm
910925866989	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	95 lm/W	3,600 lm
910925866993	RC340B 36S/940 DIA W60L60 VPC O ELD3	126 lm/W	3,600 lm
910925866995	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	95 lm/W	3,600 lm
910925866999	RC340B 42S/940 DEIA W60L60 VPC MLO	93 lm/W	4,200 lm
910925867010	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	93 lm/W	4,200 lm
910925867043	RC340B 42S/940 PSE W60L60 VPC MLO	93 lm/W	4,200 lm
910925867063	RC340B 36S/940 PSE W60L60 VPC MLO SC	95 lm/W	3,600 lm
910925867064	RC340B 36S/940 DEIA W60L60 VPC MLO SC	95 lm/W	3,600 lm
910925867014	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	138 lm/W	4,200 lm
910925866968	RC340B 36S/940 PSE W60L60 VPC MLO PIP	95 lm/W	3,600 lm
910925866978	RC340B 36S/940 DEIA W60L60 PCV MLO	95 lm/W	3,600 lm
910925866981	RC342B 36S/940 DEIA W62L62 VPC MLO	95 lm/W	3,600 lm
910925867145	RC342B 28S/940 DEIA W62L62 VPC MLO	110 lm/W	2,800 lm
910925867158	RC342B 28S/940 DEIA W62L62 VPC PCS	127 lm/W	2,800 lm
910925867159	RC342B 36S/940 DEIA W62L62 VPC PCS	144 lm/W	3,600 lm
910925867160	RC342B 42S/940 DEIA W62L62 VPC PCS	138 lm/W	4,200 lm
910925867174	RC342B 28S/940 DEIA W62L62 VPC O	124 lm/W	2,800 lm
910925867175	RC342B 36S/940 DEIA W62L62 VPC O	126 lm/W	3,600 lm
910925867176	RC342B 42S/940 DEIA W62L62 VPC O	125 lm/W	4,200 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
910925867015	RC340B 36S/940 PSE W15L120 VPC MLO	38 W	910925867147	RC342B 28S/940 DEIA W31L125 VPC MLO	25.5 W
910925867016	RC340B 36S/940 DEIA W15L120 VPC MLO	38 W	910925867161	RC342B 28S/940 DEIA W31L125 VPC PCS	22 W
910925867017	RC340B 42S/940 PSE W15L120 VPC MLO	45 W	910925867162	RC342B 36S/940 DEIA W31L125 VPC PCS	26 W
910925867018	RC340B 42S/940 DEIA W15L120 VPC MLO	45 W	910925867163	RC342B 42S/940 DEIA W31L125 VPC PCS	30.5 W
910925867020	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	38 W	910925867177	RC342B 28S/940 DEIA W31L125 VPC O	22.5 W
910925867022	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	45 W	910925867178	RC342B 36S/940 DEIA W31L125 VPC O	28.5 W
910925867024	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	38 W	910925867179	RC342B 42S/940 DEIA W31L125 VPC O	33.5 W
910925867026	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	45 W	910925866987	RC340B 36S/940 DIA W60L60 VPC O ELP3	28.5 W
910925867149	RC342B 28S/940 DEIA W15L125 VPC MLO	25.5 W	910925867001	RC340B 42S/940 PSE W60L60 VPC O	33.5 W
910925867150	RC342B 36S/940 DEIA W15L125 VPC MLO	38 W	910925867002	RC340B 42S/940 DEIA W60L60 VPC O	33.5 W
910925867153	RC342B 36S/940 DEIA W17L125 PCV MLO	38 W	910925867007	RC340B 42S/940 DIA W60L60 VPC O ELP3	33.5 W
910925867164	RC342B 28S/940 DEIA W15L125 VPC PCS	22 W	910925867012	RC340B 42S/940 DIA W60L60 VPC O ELD3	33.5 W
910925867165	RC342B 36S/940 DEIA W15L125 VPC PCS	26 W	910925867061	RC340B 36S/940 PSE W60L60 VPC O SC	28.5 W
910925867166	RC342B 42S/940 DEIA W15L125 VPC PCS	30.5 W	910925867062	RC340B 36S/940 DEIA W60L60 VPC O SC	28.5 W
910925867169	RC342B 36S/940 DEIA W17L125 PCV PCS	25 W	910925866969	RC340B 36S/940 DEIA W60L60 VPC MLO	38 W
910925867180	RC342B 28S/940 DEIA W15L125 VPC O	22.5 W	910925867046	RC340B 36S/940 PSE W60L60 CPC MLO	38 W
910925867181	RC342B 36S/940 DEIA W15L125 VPC O	28.5 W	910925867047	RC340B 42S/940 PSE W60L60 CPC MLO	45 W
910925867182	RC342B 42S/940 DEIA W15L125 VPC O	33.5 W	910925867048	RC340B 42S/940 DEIA W60L60 CPC MLO	45 W
910925866979	RC340B 36S/940 DEIA W30L120 VPC MLO	38 W	910925867167	RC342B 42S/940 DEIA W62L62 CPC PCS	30.5 W
910925866982	RC342B 36S/940 PSE W31L125 VPC MLO	37 W	910925866967	RC340B 36S/940 DEIA W60L60 VPC O	28.5 W
910925866983	RC342B 36S/940 DEIA W31L125 VPC MLO	38 W	910925866972	RC340B 36S/940 PSE W60L60 VPC PCS	26 W

FlexBlend Recessed

Order Code	Full Product Name	Power Consumption
910925866973	RC340B 36S/940 DEIA W60L60 VPC PCS	26 W
910925866977	RC340B 36S/940 DEIA W60L60 CPC MLO	38 W
910925866991	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	26 W
910925866997	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	26 W
910925867003	RC340B 42S/940 PSE W60L60 VPC PCS	30.5 W
910925867004	RC340B 42S/940 DEIA W60L60 VPC PCS	30.5 W
910925867009	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	30.5 W
910925867044	RC340B 36S/940 PSE W60L60 CPC PCS PIP	26 W
910925867045	RC340B 36S/940 DEIA W60L60 CPC PCS	26 W
910925867049	RC340B 42S/940 PSE W60L60 CPC PCS	30.5 W
910925867050	RC340B 42S/940 DEIA W60L60 CPC PCS	30.5 W
910925867065	RC340B 36S/940 PSE W60L60 VPC PCS SC	26 W
910925867066	RC340B 36S/940 DEIA W60L60 VPC PCS SC	26 W
910925866966	RC340B 36S/940 PSE W60L60 VPC O	28.5 W
910925866980	RC342B 36S/940 PSE W62L62 VPC MLO	37 W
910925866989	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	38 W
910925866993	RC340B 36S/940 DIA W60L60 VPC O ELD3	28.5 W

Order Code	Full Product Name	Power Consumption
910925866995	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	38 W
910925866999	RC340B 42S/940 DEIA W60L60 VPC MLO	45 W
910925867010	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	45 W
910925867043	RC340B 42S/940 PSE W60L60 VPC MLO	45 W
910925867063	RC340B 36S/940 PSE W60L60 VPC MLO SC	38 W
910925867064	RC340B 36S/940 DEIA W60L60 VPC MLO SC	38 W
910925867014	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	30.5 W
910925866968	RC340B 36S/940 PSE W60L60 VPC MLO PIP	38 W
910925866978	RC340B 36S/940 DEIA W60L60 PCV MLO	38 W
910925866981	RC342B 36S/940 DEIA W62L62 VPC MLO	38 W
910925867145	RC342B 28S/940 DEIA W62L62 VPC MLO	25.5 W
910925867158	RC342B 28S/940 DEIA W62L62 VPC PCS	22 W
910925867159	RC342B 36S/940 DEIA W62L62 VPC PCS	25 W
910925867160	RC342B 42S/940 DEIA W62L62 VPC PCS	30.5 W
910925867174	RC342B 28S/940 DEIA W62L62 VPC O	22.5 W
910925867175	RC342B 36S/940 DEIA W62L62 VPC O	28.5 W
910925867176	RC342B 42S/940 DEIA W62L62 VPC O	33.5 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
910925867015	RC340B 36S/940 PSE W15L120 VPC MLO	No
910925867016	RC340B 36S/940 DEIA W15L120 VPC MLO	Yes
910925867017	RC340B 42S/940 PSE W15L120 VPC MLO	No
910925867018	RC340B 42S/940 DEIA W15L120 VPC MLO	Yes
910925867020	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	Yes
910925867022	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	Yes
910925867024	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	Yes
910925867026	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	Yes
910925867149	RC342B 28S/940 DEIA W15L125 VPC MLO	Yes
910925867150	RC342B 36S/940 DEIA W15L125 VPC MLO	Yes
910925867153	RC342B 36S/940 DEIA W17L125 PCV MLO	Yes
910925867164	RC342B 28S/940 DEIA W15L125 VPC PCS	Yes
910925867165	RC342B 36S/940 DEIA W15L125 VPC PCS	Yes
910925867166	RC342B 42S/940 DEIA W15L125 VPC PCS	Yes
910925867169	RC342B 36S/940 DEIA W17L125 PCV PCS	Yes
910925867180	RC342B 28S/940 DEIA W15L125 VPC O	Yes
910925867181	RC342B 36S/940 DEIA W15L125 VPC O	Yes
910925867182	RC342B 42S/940 DEIA W15L125 VPC O	Yes
910925866979	RC340B 36S/940 DEIA W30L120 VPC MLO	Yes
910925866982	RC342B 36S/940 PSE W31L125 VPC MLO	No
910925866983	RC342B 36S/940 DEIA W31L125 VPC MLO	Yes
910925867147	RC342B 28S/940 DEIA W31L125 VPC MLO	Yes
910925867161	RC342B 28S/940 DEIA W31L125 VPC PCS	Yes
910925867162	RC342B 36S/940 DEIA W31L125 VPC PCS	Yes
910925867163	RC342B 42S/940 DEIA W31L125 VPC PCS	Yes
910925867177	RC342B 28S/940 DEIA W31L125 VPC O	Yes
910925867178	RC342B 36S/940 DEIA W31L125 VPC O	Yes
910925867179	RC342B 42S/940 DEIA W31L125 VPC O	Yes
910925866987	RC340B 36S/940 DIA W60L60 VPC O ELP3	Yes
910925867001	RC340B 42S/940 PSE W60L60 VPC O	No
910925867002	RC340B 42S/940 DEIA W60L60 VPC O	Yes

Order Code	Full Product Name	Dimmable
910925867007	RC340B 42S/940 DIA W60L60 VPC O ELP3	Yes
910925867012	RC340B 42S/940 DIA W60L60 VPC O ELD3	Yes
910925867061	RC340B 36S/940 PSE W60L60 VPC O SC	No
910925867062	RC340B 36S/940 DEIA W60L60 VPC O SC	Yes
910925866969	RC340B 36S/940 DEIA W60L60 VPC MLO	Yes
910925867046	RC340B 36S/940 PSE W60L60 CPC MLO	No
910925867047	RC340B 42S/940 PSE W60L60 CPC MLO	No
910925867048	RC340B 42S/940 DEIA W60L60 CPC MLO	Yes
910925867167	RC342B 42S/940 DEIA W62L62 CPC PCS	Yes
910925866967	RC340B 36S/940 DEIA W60L60 VPC O	Yes
910925866972	RC340B 36S/940 PSE W60L60 VPC PCS	No
910925866973	RC340B 36S/940 DEIA W60L60 VPC PCS	Yes
910925866977	RC340B 36S/940 DEIA W60L60 CPC MLO	Yes
910925866991	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	Yes
910925866997	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	Yes
910925867003	RC340B 42S/940 PSE W60L60 VPC PCS	No
910925867004	RC340B 42S/940 DEIA W60L60 VPC PCS	Yes
910925867009	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	Yes
910925867044	RC340B 36S/940 PSE W60L60 CPC PCS PIP	No
910925867045	RC340B 36S/940 DEIA W60L60 CPC PCS	Yes
910925867049	RC340B 42S/940 PSE W60L60 CPC PCS	No
910925867050	RC340B 42S/940 DEIA W60L60 CPC PCS	Yes
910925867065	RC340B 36S/940 PSE W60L60 VPC PCS SC	No
910925867066	RC340B 36S/940 DEIA W60L60 VPC PCS SC	Yes
910925866966	RC340B 36S/940 PSE W60L60 VPC O	No
910925866980	RC342B 36S/940 PSE W62L62 VPC MLO	No
910925866989	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	Yes
910925866993	RC340B 36S/940 DIA W60L60 VPC O ELD3	Yes
910925866995	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	Yes
910925866999	RC340B 42S/940 DEIA W60L60 VPC MLO	Yes
910925867010	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	Yes

FlexBlend Recessed

Order Code	Full Product Name	Dimmable
910925867043	RC340B 42S/940 PSE W60L60 VPC MLO	No
910925867063	RC340B 36S/940 PSE W60L60 VPC MLO SC	No
910925867064	RC340B 36S/940 DEIA W60L60 VPC MLO SC	Yes
910925867014	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	Yes
910925866968	RC340B 36S/940 PSE W60L60 VPC MLO PIP	No
910925866978	RC340B 36S/940 DEIA W60L60 PCV MLO	Yes
910925866981	RC342B 36S/940 DEIA W62L62 VPC MLO	Yes

Order Code	Full Product Name	Dimmable
910925867145	RC342B 28S/940 DEIA W62L62 VPC MLO	Yes
910925867158	RC342B 28S/940 DEIA W62L62 VPC PCS	Yes
910925867159	RC342B 36S/940 DEIA W62L62 VPC PCS	Yes
910925867160	RC342B 42S/940 DEIA W62L62 VPC PCS	Yes
910925867174	RC342B 28S/940 DEIA W62L62 VPC O	Yes
910925867175	RC342B 36S/940 DEIA W62L62 VPC O	Yes
910925867176	RC342B 42S/940 DEIA W62L62 VPC O	Yes

Mechanical and Housing

Order Code	Full Product Name	Ingress protection code
910925867015	RC340B 36S/940 PSE W15L120 VPC MLO	IP20/40
910925867016	RC340B 36S/940 DEIA W15L120 VPC MLO	IP20/40
910925867017	RC340B 42S/940 PSE W15L120 VPC MLO	IP20/40
910925867018	RC340B 42S/940 DEIA W15L120 VPC MLO	IP20/40
910925867020	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	IP20
910925867022	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	IP20
910925867024	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	IP20
910925867026	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	IP20
910925867149	RC342B 28S/940 DEIA W15L125 VPC MLO	IP20/40
910925867150	RC342B 36S/940 DEIA W15L125 VPC MLO	IP20/40
910925867153	RC342B 36S/940 DEIA W17L125 PCV MLO	IP20/40
910925867164	RC342B 28S/940 DEIA W15L125 VPC PCS	IP20/54
910925867165	RC342B 36S/940 DEIA W15L125 VPC PCS	IP20/54
910925867166	RC342B 42S/940 DEIA W15L125 VPC PCS	IP20/54
910925867169	RC342B 36S/940 DEIA W17L125 PCV PCS	IP20/54
910925867180	RC342B 28S/940 DEIA W15L125 VPC O	IP20/54
910925867181	RC342B 36S/940 DEIA W15L125 VPC O	IP20/54
910925867182	RC342B 42S/940 DEIA W15L125 VPC O	IP20/54
910925866979	RC340B 36S/940 DEIA W30L120 VPC MLO	IP20/40
910925866982	RC342B 36S/940 PSE W31L125 VPC MLO	IP20/40
910925866983	RC342B 36S/940 DEIA W31L125 VPC MLO	IP20/40
910925867147	RC342B 28S/940 DEIA W31L125 VPC MLO	IP20/40
910925867161	RC342B 28S/940 DEIA W31L125 VPC PCS	IP20/54
910925867162	RC342B 36S/940 DEIA W31L125 VPC PCS	IP20/54
910925867163	RC342B 42S/940 DEIA W31L125 VPC PCS	IP20/54
910925867177	RC342B 28S/940 DEIA W31L125 VPC O	IP20/54
910925867178	RC342B 36S/940 DEIA W31L125 VPC O	IP20/54
910925867179	RC342B 42S/940 DEIA W31L125 VPC O	IP20/54
910925866987	RC340B 36S/940 DIA W60L60 VPC O ELP3	IP54
910925867001	RC340B 42S/940 PSE W60L60 VPC O	IP20/54
910925867002	RC340B 42S/940 DEIA W60L60 VPC O	IP20/54
910925867007	RC340B 42S/940 DIA W60L60 VPC O ELP3	IP20/54
910925867012	RC340B 42S/940 DIA W60L60 VPC O ELD3	IP54
910925867061	RC340B 36S/940 PSE W60L60 VPC O SC	IP20/54
910925867062	RC340B 36S/940 DEIA W60L60 VPC O SC	IP20/54
910925866969	RC340B 36S/940 DEIA W60L60 VPC MLO	IP20/40
910925867046	RC340B 36S/940 PSE W60L60 CPC MLO	IP20/40
910925867047	RC340B 42S/940 PSE W60L60 CPC MLO	IP20/40

Order Code	Full Product Name	Ingress protection code
910925867048	RC340B 42S/940 DEIA W60L60 CPC MLO	IP20/40
910925867167	RC342B 42S/940 DEIA W62L62 CPC PCS	IP20/54
910925866967	RC340B 36S/940 DEIA W60L60 VPC O	IP20/54
910925866972	RC340B 36S/940 PSE W60L60 VPC PCS	IP20/54
910925866973	RC340B 36S/940 DEIA W60L60 VPC PCS	IP20/54
910925866977	RC340B 36S/940 DEIA W60L60 CPC MLO	IP20/40
910925866991	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	IP20/54
910925866997	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	IP20/54
910925867003	RC340B 42S/940 PSE W60L60 VPC PCS	IP20/54
910925867004	RC340B 42S/940 DEIA W60L60 VPC PCS	IP20/54
910925867009	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	IP20/54
910925867044	RC340B 36S/940 PSE W60L60 CPC PCS PIP	IP20/54
910925867045	RC340B 36S/940 DEIA W60L60 CPC PCS	IP20/54
910925867049	RC340B 42S/940 PSE W60L60 CPC PCS	IP20/54
910925867050	RC340B 42S/940 DEIA W60L60 CPC PCS	IP20/54
910925867065	RC340B 36S/940 PSE W60L60 VPC PCS SC	IP20/54
910925867066	RC340B 36S/940 DEIA W60L60 VPC PCS SC	IP20/54
910925866966	RC340B 36S/940 PSE W60L60 VPC O	IP20/54
910925866980	RC342B 36S/940 PSE W62L62 VPC MLO	IP20/40
910925866989	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	IP20/54
910925866993	RC340B 36S/940 DIA W60L60 VPC O ELD3	IP54
910925866995	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	IP20/54
910925866999	RC340B 42S/940 DEIA W60L60 VPC MLO	IP20/40
910925867010	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	IP20
910925867043	RC340B 42S/940 PSE W60L60 VPC MLO	IP20/40
910925867063	RC340B 36S/940 PSE W60L60 VPC MLO SC	IP20/40
910925867064	RC340B 36S/940 DEIA W60L60 VPC MLO SC	IP20/40
910925867014	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	IP20/54
910925866968	RC340B 36S/940 PSE W60L60 VPC MLO PIP	IP20/40
910925866978	RC340B 36S/940 DEIA W60L60 PCV MLO	IP20/40
910925866981	RC342B 36S/940 DEIA W62L62 VPC MLO	IP20/40
910925867145	RC342B 28S/940 DEIA W62L62 VPC MLO	IP20/40
910925867158	RC342B 28S/940 DEIA W62L62 VPC PCS	IP20/54
910925867159	RC342B 36S/940 DEIA W62L62 VPC PCS	IP20/54
910925867160	RC342B 42S/940 DEIA W62L62 VPC PCS	IP20/54
910925867174	RC342B 28S/940 DEIA W62L62 VPC O	IP20/54
910925867175	RC342B 36S/940 DEIA W62L62 VPC O	IP20/54
910925867176	RC342B 42S/940 DEIA W62L62 VPC O	IP20/54

Emergency Operation

FlexBlend Recessed

Order Code	Full Product Name	Central Emergency	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910925867015	RC340B 36S/940 PSE W15L120 VPC MLO	-	-	-
910925867016	RC340B 36S/940 DEIA W15L120 VPC MLO	Yes	DC operated central emergency lighting	-
910925867017	RC340B 42S/940 PSE W15L120 VPC MLO	-	-	-
910925867018	RC340B 42S/940 DEIA W15L120 VPC MLO	Yes	DC operated central emergency lighting	-
910925867020	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	No	Emergency lighting 3 hours duration Pro version	3 hour(s)
910925867022	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	No	Emergency lighting 3 hours duration Pro version	3 hour(s)
910925867024	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	No	Emergency lighting 3 hours duration Pro version	3 hour(s)
910925867026	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	No	Emergency lighting 3 hours duration Pro version	3 hour(s)
910925867149	RC342B 28S/940 DEIA W15L125 VPC MLO	Yes	DC operated central emergency lighting	-
910925867150	RC342B 36S/940 DEIA W15L125 VPC MLO	Yes	DC operated central emergency lighting	-
910925867153	RC342B 36S/940 DEIA W17L125 PCV MLO	Yes	DC operated central emergency lighting	-
910925867164	RC342B 28S/940 DEIA W15L125 VPC PCS	Yes	DC operated central emergency lighting	-
910925867165	RC342B 36S/940 DEIA W15L125 VPC PCS	Yes	DC operated central emergency lighting	-
910925867166	RC342B 42S/940 DEIA W15L125 VPC PCS	Yes	DC operated central emergency lighting	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910925867169	RC342B 36S/940 DEIA W17L125 PCV PCS	Yes	DC operated central emergency lighting	-
910925867180	RC342B 28S/940 DEIA W15L125 VPC O	Yes	DC operated central emergency lighting	-
910925867181	RC342B 36S/940 DEIA W15L125 VPC O	Yes	DC operated central emergency lighting	-
910925867182	RC342B 42S/940 DEIA W15L125 VPC O	Yes	DC operated central emergency lighting	-
910925866979	RC340B 36S/940 DEIA W30L120 VPC MLO	Yes	DC operated central emergency lighting	-
910925866982	RC342B 36S/940 PSE W31L125 VPC MLO	-	-	-
910925866983	RC342B 36S/940 DEIA W31L125 VPC MLO	Yes	DC operated central emergency lighting	-
910925867147	RC342B 28S/940 DEIA W31L125 VPC MLO	Yes	DC operated central emergency lighting	-
910925867161	RC342B 28S/940 DEIA W31L125 VPC PCS	Yes	DC operated central emergency lighting	-
910925867162	RC342B 36S/940 DEIA W31L125 VPC PCS	Yes	DC operated central emergency lighting	-
910925867163	RC342B 42S/940 DEIA W31L125 VPC PCS	Yes	DC operated central emergency lighting	-
910925867177	RC342B 28S/940 DEIA W31L125 VPC O	Yes	DC operated central emergency lighting	-
910925867178	RC342B 36S/940 DEIA W31L125 VPC O	Yes	DC operated central emergency lighting	-
910925867179	RC342B 42S/940 DEIA W31L125 VPC O	Yes	DC operated central emergency lighting	-
910925866987	RC340B 36S/940 DIA W60L60 VPC O ELP3	No	Emergency lighting 3 hours duration Pro version	3 hour(s)

FlexBlend Recessed

Order Code	Full Product Name	Central Emergency	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910925867001	RC340B 42S/940 PSE W60L60 VPC O	-	-	-
910925867002	RC340B 42S/940 DEIA W60L60 VPC O	Yes	DC operated central emergency lighting	-
910925867007	RC340B 42S/940 DIA W60L60 VPC O ELP3	No	Emergency lighting 3 hours duration Pro version	3 hour(s)
910925867012	RC340B 42S/940 DIA W60L60 VPC O ELD3	No	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
910925867061	RC340B 36S/940 PSE W60L60 VPC O SC	-	-	-
910925867062	RC340B 36S/940 DEIA W60L60 VPC O SC	Yes	DC operated central emergency lighting	-
910925866969	RC340B 36S/940 DEIA W60L60 VPC MLO	Yes	DC operated central emergency lighting	-
910925867046	RC340B 36S/940 PSE W60L60 CPC MLO	-	-	-
910925867047	RC340B 42S/940 PSE W60L60 CPC MLO	-	-	-
910925867048	RC340B 42S/940 DEIA W60L60 CPC MLO	Yes	DC operated central emergency lighting	-
910925867167	RC342B 42S/940 DEIA W62L62 CPC PCS	Yes	DC operated central emergency lighting	-
910925866967	RC340B 36S/940 DEIA W60L60 VPC O	Yes	DC operated central emergency lighting	-
910925866972	RC340B 36S/940 PSE W60L60 VPC PCS	-	-	-
910925866973	RC340B 36S/940 DEIA W60L60 VPC PCS	Yes	DC operated central emergency lighting	-
910925866977	RC340B 36S/940 DEIA W60L60 CPC MLO	Yes	DC operated central emergency lighting	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910925866991	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	No	Emergency lighting 3 hours duration Pro version	3 hour(s)
910925866997	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	No	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
910925867003	RC340B 42S/940 PSE W60L60 VPC PCS	-	-	-
910925867004	RC340B 42S/940 DEIA W60L60 VPC PCS	Yes	DC operated central emergency lighting	-
910925867009	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	No	Emergency lighting 3 hours duration Pro version	3 hour(s)
910925867044	RC340B 36S/940 PSE W60L60 CPC PCS PIP	-	-	-
910925867045	RC340B 36S/940 DEIA W60L60 CPC PCS	Yes	DC operated central emergency lighting	-
910925867049	RC340B 42S/940 PSE W60L60 CPC PCS	-	-	-
910925867050	RC340B 42S/940 DEIA W60L60 CPC PCS	Yes	DC operated central emergency lighting	-
910925867065	RC340B 36S/940 PSE W60L60 VPC PCS SC	-	-	-
910925867066	RC340B 36S/940 DEIA W60L60 VPC PCS SC	Yes	DC operated central emergency lighting	-
910925866966	RC340B 36S/940 PSE W60L60 VPC O	-	-	-
910925866980	RC342B 36S/940 PSE W62L62 VPC MLO	-	-	-
910925866989	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	No	Emergency lighting 3 hours duration Pro version	3 hour(s)

FlexBlend Recessed

Order Code	Full Product Name	Central Emergency	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910925866993	RC340B 36S/940 DIA W60L60 VPC O ELD3	No	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
910925866995	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	No	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
910925866999	RC340B 42S/940 DEIA W60L60 VPC MLO	Yes	DC operated central emergency lighting	-
910925867010	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	No	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
910925867043	RC340B 42S/940 PSE W60L60 VPC MLO	-	-	-
910925867063	RC340B 36S/940 PSE W60L60 VPC MLO SC	-	-	-
910925867064	RC340B 36S/940 DEIA W60L60 VPC MLO SC	Yes	DC operated central emergency lighting	-
910925867014	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	No	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
910925866968	RC340B 36S/940 PSE W60L60 VPC MLO PIP	-	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910925866978	RC340B 36S/940 DEIA W60L60 PCV MLO	Yes	DC operated central emergency lighting	-
910925866981	RC342B 36S/940 DEIA W62L62 VPC MLO	Yes	DC operated central emergency lighting	-
910925867145	RC342B 28S/940 DEIA W62L62 VPC MLO	Yes	DC operated central emergency lighting	-
910925867158	RC342B 28S/940 DEIA W62L62 VPC PCS	Yes	DC operated central emergency lighting	-
910925867159	RC342B 36S/940 DEIA W62L62 VPC PCS	Yes	DC operated central emergency lighting	-
910925867160	RC342B 42S/940 DEIA W62L62 VPC PCS	Yes	DC operated central emergency lighting	-
910925867174	RC342B 28S/940 DEIA W62L62 VPC O	Yes	DC operated central emergency lighting	-
910925867175	RC342B 36S/940 DEIA W62L62 VPC O	Yes	DC operated central emergency lighting	-
910925867176	RC342B 42S/940 DEIA W62L62 VPC O	Yes	DC operated central emergency lighting	-

Approval and Application

Order Code	Full Product Name	Glow-wire test
910925867015	RC340B 36S/940 PSE W15L120 VPC MLO	Temperature 650 °C, duration 30 s
910925867016	RC340B 36S/940 DEIA W15L120 VPC MLO	Temperature 650 °C, duration 30 s
910925867017	RC340B 42S/940 PSE W15L120 VPC MLO	Temperature 650 °C, duration 30 s
910925867018	RC340B 42S/940 DEIA W15L120 VPC MLO	Temperature 650 °C, duration 30 s
910925867020	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Glow-wire test
910925867022	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	Temperature 650 °C, duration 30 s
910925867024	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	Temperature 650 °C, duration 30 s
910925867026	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	Temperature 650 °C, duration 30 s
910925867149	RC342B 28S/940 DEIA W15L125 VPC MLO	Temperature 650 °C, duration 30 s
910925867150	RC342B 36S/940 DEIA W15L125 VPC MLO	Temperature 650 °C, duration 30 s

FlexBlend Recessed

Order Code	Full Product Name	Glow-wire test	Order Code	Full Product Name	Glow-wire test
910925867153	RC342B 36S/940 DEIA W17L125 PCV MLO	Temperature 650 °C, duration 30 s	910925867046	RC340B 36S/940 PSE W60L60 CPC MLO	Temperature 650 °C, duration 30 s
910925867164	RC342B 28S/940 DEIA W15L125 VPC PCS	Temperature 850 °C, duration 30 s	910925867047	RC340B 42S/940 PSE W60L60 CPC MLO	Temperature 650 °C, duration 30 s
910925867165	RC342B 36S/940 DEIA W15L125 VPC PCS	Temperature 850 °C, duration 30 s	910925867048	RC340B 42S/940 DEIA W60L60 CPC MLO	Temperature 650 °C, duration 30 s
910925867166	RC342B 42S/940 DEIA W15L125 VPC PCS	Temperature 850 °C, duration 30 s	910925867167	RC342B 42S/940 DEIA W62L62 CPC PCS	Temperature 850 °C, duration 30 s
910925867169	RC342B 36S/940 DEIA W17L125 PCV PCS	Temperature 850 °C, duration 30 s	910925866967	RC340B 36S/940 DEIA W60L60 VPC O	Temperature 850 °C, duration 30 s
910925867180	RC342B 28S/940 DEIA W15L125 VPC O	Temperature 850 °C, duration 30 s	910925866972	RC340B 36S/940 PSE W60L60 VPC PCS	Temperature 850 °C, duration 30 s
910925867181	RC342B 36S/940 DEIA W15L125 VPC O	Temperature 850 °C, duration 30 s	910925866973	RC340B 36S/940 DEIA W60L60 VPC PCS	Temperature 850 °C, duration 30 s
910925867182	RC342B 42S/940 DEIA W15L125 VPC O	Temperature 850 °C, duration 30 s	910925866977	RC340B 36S/940 DEIA W60L60 CPC MLO	Temperature 650 °C, duration 30 s
910925866979	RC340B 36S/940 DEIA W30L120 VPC MLO	Temperature 650 °C, duration 30 s	910925866991	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	Temperature 850 °C, duration 30 s
910925866982	RC342B 36S/940 PSE W31L125 VPC MLO	Temperature 650 °C, duration 30 s	910925866997	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	Temperature 850 °C, duration 30 s
910925866983	RC342B 36S/940 DEIA W31L125 VPC MLO	Temperature 650 °C, duration 30 s	910925867003	RC340B 42S/940 PSE W60L60 VPC PCS	Temperature 850 °C, duration 30 s
910925867147	RC342B 28S/940 DEIA W31L125 VPC MLO	Temperature 650 °C, duration 30 s	910925867004	RC340B 42S/940 DEIA W60L60 VPC PCS	Temperature 850 °C, duration 30 s
910925867161	RC342B 28S/940 DEIA W31L125 VPC PCS	Temperature 850 °C, duration 30 s	910925867009	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	Temperature 850 °C, duration 30 s
910925867162	RC342B 36S/940 DEIA W31L125 VPC PCS	Temperature 850 °C, duration 30 s	910925867044	RC340B 36S/940 PSE W60L60 CPC PCS PIP	Temperature 850 °C, duration 30 s
910925867163	RC342B 42S/940 DEIA W31L125 VPC PCS	Temperature 850 °C, duration 30 s	910925867045	RC340B 36S/940 DEIA W60L60 CPC PCS	Temperature 850 °C, duration 30 s
910925867177	RC342B 28S/940 DEIA W31L125 VPC O	Temperature 850 °C, duration 30 s	910925867049	RC340B 42S/940 PSE W60L60 CPC PCS	Temperature 850 °C, duration 30 s
910925867178	RC342B 36S/940 DEIA W31L125 VPC O	Temperature 850 °C, duration 30 s	910925867050	RC340B 42S/940 DEIA W60L60 CPC PCS	Temperature 850 °C, duration 30 s
910925867179	RC342B 42S/940 DEIA W31L125 VPC O	Temperature 850 °C, duration 30 s	910925867065	RC340B 36S/940 PSE W60L60 VPC PCS SC	Temperature 850 °C, duration 30 s
910925866987	RC340B 36S/940 DIA W60L60 VPC O ELP3	Temperature 850 °C, duration 30 s	910925867066	RC340B 36S/940 DEIA W60L60 VPC PCS SC	Temperature 850 °C, duration 30 s
910925867001	RC340B 42S/940 PSE W60L60 VPC O	Temperature 850 °C, duration 30 s	910925866966	RC340B 36S/940 PSE W60L60 VPC O	Temperature 850 °C, duration 30 s
910925867002	RC340B 42S/940 DEIA W60L60 VPC O	Temperature 850 °C, duration 30 s	910925866980	RC342B 36S/940 PSE W62L62 VPC MLO	Temperature 650 °C, duration 30 s
910925867007	RC340B 42S/940 DIA W60L60 VPC O ELP3	Temperature 850 °C, duration 30 s	910925866989	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	Temperature 650 °C, duration 30 s
910925867012	RC340B 42S/940 DIA W60L60 VPC O ELD3	Temperature 850 °C, duration 30 s	910925866993	RC340B 36S/940 DIA W60L60 VPC O ELD3	Temperature 850 °C, duration 30 s
910925867061	RC340B 36S/940 PSE W60L60 VPC O SC	Temperature 850 °C, duration 30 s	910925866995	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	Temperature 650 °C, duration 30 s
910925867062	RC340B 36S/940 DEIA W60L60 VPC O SC	Temperature 850 °C, duration 30 s	910925866999	RC340B 42S/940 DEIA W60L60 VPC MLO	Temperature 650 °C, duration 30 s
910925866969	RC340B 36S/940 DEIA W60L60 VPC MLO	Temperature 650 °C, duration 30 s	910925867010	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	Temperature 650 °C, duration 30 s

FlexBlend Recessed

Order Code	Full Product Name	Glow-wire test
910925867043	RC340B 42S/940 PSE W60L60 VPC MLO	Temperature 650 °C, duration 30 s
910925867063	RC340B 36S/940 PSE W60L60 VPC MLO SC	Temperature 650 °C, duration 30 s
910925867064	RC340B 36S/940 DEIA W60L60 VPC MLO SC	Temperature 650 °C, duration 30 s
910925867014	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	Temperature 850 °C, duration 30 s
910925866968	RC340B 36S/940 PSE W60L60 VPC MLO PIP	Temperature 650 °C, duration 30 s
910925866978	RC340B 36S/940 DEIA W60L60 PCV MLO	Temperature 650 °C, duration 30 s
910925866981	RC342B 36S/940 DEIA W62L62 VPC MLO	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Glow-wire test
910925867145	RC342B 28S/940 DEIA W62L62 VPC MLO	Temperature 650 °C, duration 30 s
910925867158	RC342B 28S/940 DEIA W62L62 VPC PCS	Temperature 850 °C, duration 30 s
910925867159	RC342B 36S/940 DEIA W62L62 VPC PCS	Temperature 850 °C, duration 30 s
910925867160	RC342B 42S/940 DEIA W62L62 VPC PCS	Temperature 850 °C, duration 30 s
910925867174	RC342B 28S/940 DEIA W62L62 VPC O	Temperature 850 °C, duration 30 s
910925867175	RC342B 36S/940 DEIA W62L62 VPC O	Temperature 850 °C, duration 30 s
910925867176	RC342B 42S/940 DEIA W62L62 VPC O	Temperature 850 °C, duration 30 s

Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Driver failure rate at 5000 h
910925867015	RC340B 36S/940 PSE W15L120 VPC MLO	0.01 %
910925867016	RC340B 36S/940 DEIA W15L120 VPC MLO	0.01 %
910925867017	RC340B 42S/940 PSE W15L120 VPC MLO	0.01 %
910925867018	RC340B 42S/940 DEIA W15L120 VPC MLO	0.01 %
910925867020	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	0.01 %
910925867022	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	0.01 %
910925867024	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	0.01 %
910925867026	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	0.01 %
910925867149	RC342B 28S/940 DEIA W15L125 VPC MLO	-
910925867150	RC342B 36S/940 DEIA W15L125 VPC MLO	-
910925867153	RC342B 36S/940 DEIA W17L125 PCV MLO	-
910925867164	RC342B 28S/940 DEIA W15L125 VPC PCS	-
910925867165	RC342B 36S/940 DEIA W15L125 VPC PCS	-
910925867166	RC342B 42S/940 DEIA W15L125 VPC PCS	-
910925867169	RC342B 36S/940 DEIA W17L125 PCV PCS	-
910925867180	RC342B 28S/940 DEIA W15L125 VPC O	-
910925867181	RC342B 36S/940 DEIA W15L125 VPC O	-
910925867182	RC342B 42S/940 DEIA W15L125 VPC O	-
910925866979	RC340B 36S/940 DEIA W30L120 VPC MLO	0.01 %
910925866982	RC342B 36S/940 PSE W31L125 VPC MLO	0.01 %
910925866983	RC342B 36S/940 DEIA W31L125 VPC MLO	0.01 %
910925867147	RC342B 28S/940 DEIA W31L125 VPC MLO	-
910925867161	RC342B 28S/940 DEIA W31L125 VPC PCS	-
910925867162	RC342B 36S/940 DEIA W31L125 VPC PCS	-
910925867163	RC342B 42S/940 DEIA W31L125 VPC PCS	-
910925867177	RC342B 28S/940 DEIA W31L125 VPC O	-
910925867178	RC342B 36S/940 DEIA W31L125 VPC O	-
910925867179	RC342B 42S/940 DEIA W31L125 VPC O	-
910925866987	RC340B 36S/940 DIA W60L60 VPC O ELP3	0.01 %
910925867001	RC340B 42S/940 PSE W60L60 VPC O	0.01 %
910925867002	RC340B 42S/940 DEIA W60L60 VPC O	0.01 %
910925867007	RC340B 42S/940 DIA W60L60 VPC O ELP3	0.01 %
910925867012	RC340B 42S/940 DIA W60L60 VPC O ELD3	0.01 %

Order Code	Full Product Name	Driver failure rate at 5000 h
910925867061	RC340B 36S/940 PSE W60L60 VPC O SC	0.01 %
910925867062	RC340B 36S/940 DEIA W60L60 VPC O SC	0.01 %
910925866969	RC340B 36S/940 DEIA W60L60 VPC MLO	0.01 %
910925867046	RC340B 36S/940 PSE W60L60 CPC MLO	0.01 %
910925867047	RC340B 42S/940 PSE W60L60 CPC MLO	0.01 %
910925867048	RC340B 42S/940 DEIA W60L60 CPC MLO	0.01 %
910925867167	RC342B 42S/940 DEIA W62L62 CPC PCS	-
910925866967	RC340B 36S/940 DEIA W60L60 VPC O	0.01 %
910925866972	RC340B 36S/940 PSE W60L60 VPC PCS	0.01 %
910925866973	RC340B 36S/940 DEIA W60L60 VPC PCS	0.01 %
910925866977	RC340B 36S/940 DEIA W60L60 CPC MLO	0.01 %
910925866991	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	0.01 %
910925866997	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	0.01 %
910925867003	RC340B 42S/940 PSE W60L60 VPC PCS	0.01 %
910925867004	RC340B 42S/940 DEIA W60L60 VPC PCS	0.01 %
910925867009	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	0.01 %
910925867044	RC340B 36S/940 PSE W60L60 CPC PCS PIP	0.01 %
910925867045	RC340B 36S/940 DEIA W60L60 CPC PCS	0.01 %
910925867049	RC340B 42S/940 PSE W60L60 CPC PCS	0.01 %
910925867050	RC340B 42S/940 DEIA W60L60 CPC PCS	0.01 %
910925867065	RC340B 36S/940 PSE W60L60 VPC PCS SC	0.01 %
910925867066	RC340B 36S/940 DEIA W60L60 VPC PCS SC	0.01 %
910925866966	RC340B 36S/940 PSE W60L60 VPC O	0.01 %
910925866980	RC342B 36S/940 PSE W62L62 VPC MLO	0.01 %
910925866989	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	0.01 %
910925866993	RC340B 36S/940 DIA W60L60 VPC O ELD3	0.01 %
910925866995	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	0.01 %
910925866999	RC340B 42S/940 DEIA W60L60 VPC MLO	0.01 %
910925867010	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	0.01 %
910925867043	RC340B 42S/940 PSE W60L60 VPC MLO	0.01 %
910925867063	RC340B 36S/940 PSE W60L60 VPC MLO SC	0.01 %
910925867064	RC340B 36S/940 DEIA W60L60 VPC MLO SC	0.01 %
910925867014	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	0.01 %

FlexBlend Recessed

Order Code	Full Product Name	Driver failure rate at 5000 h
910925866968	RC340B 36S/940 PSE W60L60 VPC MLO PIP	0.01 %
910925866978	RC340B 36S/940 DEIA W60L60 PCV MLO	0.01 %
910925866981	RC342B 36S/940 DEIA W62L62 VPC MLO	0.01 %
910925867145	RC342B 28S/940 DEIA W62L62 VPC MLO	-
910925867158	RC342B 28S/940 DEIA W62L62 VPC PCS	-

Order Code	Full Product Name	Driver failure rate at 5000 h
910925867159	RC342B 36S/940 DEIA W62L62 VPC PCS	-
910925867160	RC342B 42S/940 DEIA W62L62 VPC PCS	-
910925867174	RC342B 28S/940 DEIA W62L62 VPC O	-
910925867175	RC342B 36S/940 DEIA W62L62 VPC O	-
910925867176	RC342B 42S/940 DEIA W62L62 VPC O	-


Product Data

Order Code	Full Product Name	Product family code
910925867015	RC340B 36S/940 PSE W15L120 VPC MLO	RC340B
910925867016	RC340B 36S/940 DEIA W15L120 VPC MLO	RC340B
910925867017	RC340B 42S/940 PSE W15L120 VPC MLO	RC340B
910925867018	RC340B 42S/940 DEIA W15L120 VPC MLO	RC340B
910925867020	RC340B 36S/940 DIA W15L120 VPC MLO ELP3	RC340B
910925867022	RC340B 42S/940 DIA W15L120 VPC MLO ELP3	RC340B
910925867024	RC340B 36S/940 DIA W15L120 VPC MLO ELD3	RC340B
910925867026	RC340B 42S/940 DIA W15L120 VPC MLO ELD3	RC340B
910925867149	RC342B 28S/940 DEIA W15L125 VPC MLO	RC342B
910925867150	RC342B 36S/940 DEIA W15L125 VPC MLO	RC342B
910925867153	RC342B 36S/940 DEIA W17L125 PCV MLO	RC342B
910925867164	RC342B 28S/940 DEIA W15L125 VPC PCS	RC342B
910925867165	RC342B 36S/940 DEIA W15L125 VPC PCS	RC342B
910925867166	RC342B 42S/940 DEIA W15L125 VPC PCS	RC342B
910925867169	RC342B 36S/940 DEIA W17L125 PCV PCS	RC342B
910925867180	RC342B 28S/940 DEIA W15L125 VPC O	RC342B
910925867181	RC342B 36S/940 DEIA W15L125 VPC O	RC342B
910925867182	RC342B 42S/940 DEIA W15L125 VPC O	RC342B
910925866979	RC340B 36S/940 DEIA W30L120 VPC MLO	RC340B
910925866982	RC342B 36S/940 PSE W31L125 VPC MLO	RC342B
910925866983	RC342B 36S/940 DEIA W31L125 VPC MLO	RC342B
910925867147	RC342B 28S/940 DEIA W31L125 VPC MLO	RC342B
910925867161	RC342B 28S/940 DEIA W31L125 VPC PCS	RC342B
910925867162	RC342B 36S/940 DEIA W31L125 VPC PCS	RC342B
910925867163	RC342B 42S/940 DEIA W31L125 VPC PCS	RC342B
910925867177	RC342B 28S/940 DEIA W31L125 VPC O	RC342B
910925867178	RC342B 36S/940 DEIA W31L125 VPC O	RC342B
910925867179	RC342B 42S/940 DEIA W31L125 VPC O	RC342B
910925866987	RC340B 36S/940 DIA W60L60 VPC O ELP3	RC340B
910925867001	RC340B 42S/940 PSE W60L60 VPC O	RC340B
910925867002	RC340B 42S/940 DEIA W60L60 VPC O	RC340B
910925867007	RC340B 42S/940 DIA W60L60 VPC O ELP3	RC340B
910925867012	RC340B 42S/940 DIA W60L60 VPC O ELD3	RC340B
910925867061	RC340B 36S/940 PSE W60L60 VPC O SC	RC340B
910925867062	RC340B 36S/940 DEIA W60L60 VPC O SC	RC340B
910925866969	RC340B 36S/940 DEIA W60L60 VPC MLO	RC340B
910925867046	RC340B 36S/940 PSE W60L60 CPC MLO	RC340B
910925867047	RC340B 42S/940 PSE W60L60 CPC MLO	RC340B


Order Code	Full Product Name	Product family code
910925867048	RC340B 42S/940 DEIA W60L60 CPC MLO	RC340B
910925867167	RC342B 42S/940 DEIA W62L62 CPC PCS	RC342B
910925866967	RC340B 36S/940 DEIA W60L60 VPC O	RC340B
910925866972	RC340B 36S/940 PSE W60L60 VPC PCS	RC340B
910925866973	RC340B 36S/940 DEIA W60L60 VPC PCS	RC340B
910925866977	RC340B 36S/940 DEIA W60L60 CPC MLO	RC340B
910925866991	RC340B 36S/940 DIA W60L60 VPC PCS ELP3	RC340B
910925866997	RC340B 36S/940 DIA W60L60 VPC PCS ELD3	RC340B
910925867003	RC340B 42S/940 PSE W60L60 VPC PCS	RC340B
910925867004	RC340B 42S/940 DEIA W60L60 VPC PCS	RC340B
910925867009	RC340B 42S/940 DIA W60L60 VPC PCS ELP3	RC340B
910925867044	RC340B 36S/940 PSE W60L60 CPC PCS PIP	RC340B
910925867045	RC340B 36S/940 DEIA W60L60 CPC PCS	RC340B
910925867049	RC340B 42S/940 PSE W60L60 CPC PCS	RC340B
910925867050	RC340B 42S/940 DEIA W60L60 CPC PCS	RC340B
910925867065	RC340B 36S/940 PSE W60L60 VPC PCS SC	RC340B
910925867066	RC340B 36S/940 DEIA W60L60 VPC PCS SC	RC340B
910925866966	RC340B 36S/940 PSE W60L60 VPC O	RC340B
910925866980	RC342B 36S/940 PSE W62L62 VPC MLO	RC342B
910925866989	RC340B 36S/940 DIA W60L60 VPC MLO ELP3	RC340B
910925866993	RC340B 36S/940 DIA W60L60 VPC O ELD3	RC340B
910925866995	RC340B 36S/940 DIA W60L60 VPC MLO ELD3	RC340B
910925866999	RC340B 42S/940 DEIA W60L60 VPC MLO	RC340B
910925867010	RC340B 42S/940 DIA W60L60 VPC MLO ELD3	RC340B
910925867043	RC340B 42S/940 PSE W60L60 VPC MLO	RC340B
910925867063	RC340B 36S/940 PSE W60L60 VPC MLO SC	RC340B
910925867064	RC340B 36S/940 DEIA W60L60 VPC MLO SC	RC340B
910925867014	RC340B 42S/940 DIA W60L60 VPC PCS ELD3	RC340B
910925866968	RC340B 36S/940 PSE W60L60 VPC MLO PIP	RC340B
910925866978	RC340B 36S/940 DEIA W60L60 PCV MLO	RC340B
910925866981	RC342B 36S/940 DEIA W62L62 VPC MLO	RC342B
910925867145	RC342B 28S/940 DEIA W62L62 VPC MLO	RC342B
910925867158	RC342B 28S/940 DEIA W62L62 VPC PCS	RC342B
910925867159	RC342B 36S/940 DEIA W62L62 VPC PCS	RC342B
910925867160	RC342B 42S/940 DEIA W62L62 VPC PCS	RC342B
910925867174	RC342B 28S/940 DEIA W62L62 VPC O	RC342B
910925867175	RC342B 36S/940 DEIA W62L62 VPC O	RC342B
910925867176	RC342B 42S/940 DEIA W62L62 VPC O	RC342B

FlexBlend Recessed


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925866978




Polar Normal (separate) - RC340BI - 910925866989




Polar Normal (separate) - RC340BI - 910925866987




Polar Normal (separate) - RC340BI - 910925866969




Polar Normal (separate) - RC340BI - 910925866968




Polar Normal (separate) - RC340BI - 910925866979



Polar Normal (separate) - RC340BI - 910925866981




Polar Normal (separate) - RC340BI - 910925867050




Polar Normal (separate) - RC340BI - 910925866973

FlexBlend Recessed


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925866991




Polar Normal (separate) - RC340BI - 910925866993




Polar Normal (separate) - RC340BI - 910925867002




Polar Normal (separate) - RC340BI - 910925867003




Polar Normal (separate) - RC340BI - 910925866977




Polar Normal (separate) - RC340BI - 910925866995



Polar Normal (separate) - RC340BI - 910925867012




Polar Normal (separate) - RC340BI - 910925867017




Polar Normal (separate) - RC340BI - 910925867024

FlexBlend Recessed


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925867043




Polar Normal (separate) - RC340BI - 910925867049




Polar Normal (separate) - RC340BI - 910925866967




Polar Normal (separate) - RC340BI - 910925867010




Polar Normal (separate) - RC340BI - 910925867022




Polar Normal (separate) - RC340BI - 910925867064



Polar Normal (separate) - RC340BI - 910925866980




Polar Normal (separate) - RC340BI - 910925866982




Polar Normal (separate) - RC340BI - 910925866983

FlexBlend Recessed


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925866997




Polar Normal (separate) - RC340BI - 910925867009




Polar Normal (separate) - RC340BI - 910925867047




Polar Normal (separate) - RC340BI - 910925867062




Polar Normal (separate) - RC340BI - 910925867063




Polar Normal (separate) - RC340BI - 910925866966



Polar Normal (separate) - RC340BI - 910925867018




Polar Normal (separate) - RC340BI - 910925867016




Polar Normal (separate) - RC340BI - 910925867014

FlexBlend Recessed


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925867145




Polar Normal (separate) - RC340BI - 910925867147




Polar Normal (separate) - RC340BI - 910925867020




Polar Normal (separate) - RC340BI - 910925867026




Polar Normal (separate) - RC340BI - 910925867044




Polar Normal (separate) - RC340BI - 910925867045



Polar Normal (separate) - RC340BI - 910925867048




Polar Normal (separate) - RC340BI - 910925867065




Polar Normal (separate) - RC340BI - 910925867149

FlexBlend Recessed


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925867159




Polar Normal (separate) - RC340BI - 910925867158




Polar Normal (separate) - RC340BI - 910925867165




Polar Normal (separate) - RC340BI - 910925867166




Polar Normal (separate) - RC340BI - 910925867167




Polar Normal (separate) - RC340BI - 910925867177



Polar Normal (separate) - RC340BI - 910925867178




Polar Normal (separate) - RC340BI - 910925867066




Polar Normal (separate) - RC340BI - 910925867162

FlexBlend Recessed


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925867160




Polar Normal (separate) - RC340BI - 910925867153




Polar Normal (separate) - RC340BI - 910925867175




Polar Normal (separate) - RC340BI - 910925867179




Polar Normal (separate) - RC340BI - 910925867182




Polar Normal (separate) - RC340BI - 910925867163



Polar Normal (separate) - RC340BI - 910925867174




Polar Normal (separate) - RC340BI - 910925867176




Polar Normal (separate) - RC340BI - 910925866972

FlexBlend Recessed


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925866999




Polar Normal (separate) - RC340BI - 910925867001




Polar Normal (separate) - RC340BI - 910925867004




Polar Normal (separate) - RC340BI - 910925867007




Polar Normal (separate) - RC340BI - 910925867015




Polar Normal (separate) - RC340BI - 910925867046



Polar Normal (separate) - RC340BI - 910925867061




Polar Normal (separate) - RC340BI - 910925867150




Polar Normal (separate) - RC340BI - 910925867161

FlexBlend Recessed


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925867164



Polar Normal (separate) - RC340BI - 910925867169



Polar Normal (separate) - RC340BI - 910925867181



Polar Normal (separate) - RC340BI - 910925867180

