



A troffer beyond visual comfort

Aura

As an innovative troffer, CoreView Pro RC430V uses indirect and direct light output to reach UGR19 without using heavy and big glare control plates. The central module can be easily replaceable for future maintenance. The light from the central light module can be controlled separately to fit multiple applications. BioUp technology provides better well being for the people in indoor environment.

Benefits

- Slim and nice look and feel
- Easy maintenance on site
- Fit multiple applications for office, healthcare
- Support better well being for people in indoor




Features

- Unique light module design with indirect and direct light to reach UGR19
- Replaceable light module
- Adjustable up and downward light output ratio
- BioUp technology enabled

Application

- Office
- Meeting room
- Healthcare

Dimensional drawing



General Information	
Driver included	Yes
Gear	-
Number of gear units	1 unit
Light Technical	
Beam angle of light source	115 degree(s)
Optic type	Beam angle 90°
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Suitable for random switching	Yes
Mechanical and Housing	
Optical cover type	Prismatic bowl/ cover linear horizontal
Housing Color	White RAL 9003
Mech. impact protection code	IK03
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	-20 to +40 °C
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Initial Performance (IEC Compliant)	
Luminous flux tolerance	-10% / +10%

Light Technical (1/2)

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401578645	RC430X LED38/840 W60L60 SC2 OC	4000 K	80	120 lm/W	3,800 lm
911401578945	RC430X LED36/940 W60L60 SC2 OC	4000 K	90	114 lm/W	3,600 lm
911401579245	RC430X LED38/840 W60L60 SC2 OC CAU	4000 K	80	120 lm/W	3,800 lm
911401579545	RC430X LED36/940 W60L60 SC2 OC CAU	4000 K	90	114 lm/W	3,600 lm
911401579845	RC430X LED38/840 W60L60 SC15 OC	4000 K	80	120 lm/W	3,800 lm
911401580145	RC430X LED36/940 W60L60 SC15 OC	4000 K	90	114 lm/W	3,600 lm
911401580445	RC430X LED38/840 W60L60 SC15 OC CAU	4000 K	80	120 lm/W	3,800 lm
911401580745	RC430X LED36/940 W60L60 SC15 OC CAU	4000 K	90	114 lm/W	3,600 lm
911401582745	RC430X LED35/9TW W60L60 SC2 OC	Tunable white 2700-6500 K	90	118 lm/W	3,500 lm
911401583045	RC430X LED35/9TW W60L60 SC2 OC CAU	Tunable white 2700-6500 K	90	118 lm/W	3,500 lm
911401583345	RC430X LED35/9TW W60L60 SC15 OC	Tunable white 2700-6500 K	90	118 lm/W	3,500 lm
911401583645	RC430X LED35/9TW W60L60 SC15 OC CAU	Tunable white 2700-6500 K	90	118 lm/W	3,500 lm
911401584345	RC430X LED37/BioUPD W60L60 SC2 OC	4000 K	80	106 lm/W	3,700 lm
911401584445	RC430X LED37/BioUPD W60L60 SC2 OC CAU	4000 K	80	106 lm/W	3,700 lm
911401584545	RC430X LED37/BioUPD W60L60 SC15 OC	4000 K	80	106 lm/W	3,700 lm
911401584645	RC430X LED37/BioUPD W60L60 SC15 OC CAU	4000 K	80	106 lm/W	3,700 lm
911401585545	RC430X LED37/840 W60L60 SC2 OC U/D	4000 K	80	114 lm/W	3,700 lm
911401585845	RC430X LED35/940 W60L60 SC2 OC U/D	4000 K	90	108 lm/W	3,500 lm
911401586145	RC430X LED37/840 W60L60 SC15 OC U/D	4000 K	80	114 lm/W	3,700 lm
911401586445	RC430X LED35/940 W60L60 SC15 OC U/D	4000 K	90	108 lm/W	3,500 lm
911401587345	RC430X LED37/840 W60L60 SC2 OC U/D CAU	4000 K	80	114 lm/W	3,700 lm
911401587645	RC430X LED35/940 W60L60 SC2 OC U/D CAU	4000 K	90	108 lm/W	3,500 lm
911401587945	RC430X LED37/840 W60L60 SC15 OC U/D CAU	4000 K	80	114 lm/W	3,700 lm
911401588245	RC430X LED35/940 W60L60 SC15 OC U/D CAU	4000 K	90	108 lm/W	3,500 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401578445	RC430X LED55/840 W60L120 SC2 OC	4000 K	80	123 lm/W	5,500 lm
911401578745	RC430X LED52/940 W60L120 SC2 OC	4000 K	90	116 lm/W	5,200 lm
911401579045	RC430X LED55/840 W60L120 SC2 OC CAU	4000 K	80	123 lm/W	5,500 lm
911401579345	RC430X LED52/940 W60L120 SC2 OC CAU	4000 K	90	116 lm/W	5,200 lm
911401579645	RC430X LED55/840 W60L120 SC15 OC	4000 K	80	126 lm/W	5,500 lm
911401579945	RC430X LED52/940 W60L120 SC15 OC	4000 K	90	116 lm/W	5,200 lm
911401580245	RC430X LED55/840 W60L120 SC15 OC CAU	4000 K	80	123 lm/W	5,500 lm
911401580545	RC430X LED52/940 W60L120 SC15 OC CAU	4000 K	90	116 lm/W	5,200 lm
911401580845	RC430V LED54/840 W60L120 PSU OC SG	4000 K	80	129 lm/W	5,400 lm
911401581945	RC430V LED51/9TW W60L120 PSD OC	Tunable white 2700-6500 K	90	120 lm/W	5,100 lm
911401582245	RC430V LED51/9TW W60L120 PSD OC CAU	Tunable white 2700-6500 K	90	120 lm/W	5,100 lm
911401582545	RC430X LED51/9TW W60L120 SC2 OC	Tunable white 2700-6500 K	90	120 lm/W	5,100 lm
911401582845	RC430X LED51/9TW W60L120 SC2 OC CAU	Tunable white 2700-6500 K	90	120 lm/W	5,100 lm
911401583145	RC430X LED51/9TW W60L120 SC15 OC	Tunable white 2700-6500 K	90	120 lm/W	5,100 lm
911401583445	RC430X LED51/9TW W60L120 SC15 OC CAU	Tunable white 2700-6500 K	90	120 lm/W	5,100 lm
911401583745	RC430V LED52/BioUPD W60L120 PSD OC	4000 K	80	108 lm/W	5,200 lm
911401584045	RC430V LED52/BioUPD W60L120 PSD OC CAU	4000 K	80	108 lm/W	5,200 lm
911401584745	RC430V LED54/840 W60L120 PSD OC U/D	4000 K	80	113 lm/W	5,400 lm
911401585045	RC430V LED51/940 W60L120 PSD OC U/D	4000 K	90	108 lm/W	5,100 lm
911401585345	RC430X LED54/840 W60L120 SC2 OC U/D	4000 K	80	113 lm/W	5,400 lm
911401585645	RC430X LED51/940 W60L120 SC2 OC U/D	4000 K	90	108 lm/W	5,100 lm
911401585945	RC430X LED54/840 W60L120 SC15 OC U/D	4000 K	80	113 lm/W	5,400 lm
911401586245	RC430X LED51/940 W60L120 SC15 OC U/D	4000 K	90	108 lm/W	5,100 lm
911401586545	RC430V LED54/840 W60L120 PSD OC U/D CAU	4000 K	80	113 lm/W	5,400 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401586845	RC430V LED51/940 W60L120 PSD OC U/D CAU	4000 K	90	108 lm/W	5,100 lm
911401587145	RC430X LED54/840 W60L120 SC2 OC U/D CAU	4000 K	80	113 lm/W	5,400 lm
911401587445	RC430X LED51/940 W60L120 SC2 OC U/D CAU	4000 K	90	108 lm/W	5,100 lm
911401587745	RC430X LED54/840 W60L120 SC15 OC U/D CAU	4000 K	80	113 lm/W	5,400 lm
911401588045	RC430X LED51/940 W60L120 SC15 OC U/D CAU	4000 K	90	108 lm/W	5,100 lm
911401578545	RC430X LED40/840 W30L120 SC2 OC	4000 K	80	131 lm/W	4,000 lm
911401578845	RC430X LED38/940 W30L120 SC2 OC	4000 K	90	124 lm/W	3,800 lm
911401579145	RC430X LED40/840 W30L120 SC2 OC CAU	4000 K	80	131 lm/W	4,000 lm
911401579445	RC430X LED38/940 W30L120 SC2 OC CAU	4000 K	90	124 lm/W	3,800 lm
911401579745	RC430X LED40/840 W30L120 SC15 OC	4000 K	80	131 lm/W	4,000 lm
911401580045	RC430X LED38/940 W30L120 SC15 OC	4000 K	90	124 lm/W	3,800 lm
911401580345	RC430X LED40/840 W30L120 SC15 OC CAU	4000 K	80	131 lm/W	4,000 lm
911401580645	RC430X LED38/940 W30L120 SC15 OC CAU	4000 K	90	124 lm/W	3,800 lm
911401582645	RC430X LED36/9TW W30L120 SC2 OC	Tunable white 2700-6500 K	90	124 lm/W	3,600 lm
911401582945	RC430X LED36/9TW W30L120 SC2 OC CAU	Tunable white 2700-6500 K	90	124 lm/W	3,600 lm
911401583245	RC430X LED36/9TW W30L120 SC15 OC	Tunable white 2700-6500 K	90	124 lm/W	3,600 lm
911401583545	RC430X LED36/9TW W30L120 SC15 OC CAU	Tunable white 2700-6500 K	90	124 lm/W	3,600 lm
911401585445	RC430X LED38/840 W30L120 SC2 OC U/D	4000 K	80	131 lm/W	3,800 lm
911401585745	RC430X LED36/940 W30L120 SC2 OC U/D	4000 K	90	124 lm/W	3,600 lm
911401586045	RC430X LED38/840 W30L120 SC15 OC U/D	4000 K	80	131 lm/W	3,800 lm
911401586345	RC430X LED36/940 W30L120 SC15 OC U/D	4000 K	90	124 lm/W	3,600 lm
911401587245	RC430X LED38/840 W30L120 SC2 OC U/D CAU	4000 K	80	131 lm/W	3,800 lm
911401587545	RC430X LED36/940 W30L120 SC2 OC U/D CAU	4000 K	90	124 lm/W	3,600 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401587845	RC430X LED38/840 W30L120 SC15 OC U/D CAU	4000 K	80	131 lm/W	3,800 lm
911401588145	RC430X LED36/940 W30L120 SC15 OC U/D CAU	4000 K	90	124 lm/W	3,600 lm
911401522845	RC430V LED38/840 W60L60 PSU OC	4000 K	80	123 lm/W	3,800 lm
911401523145	RC430V LED38/840 W60L60 PSD OC	4000 K	80	117 lm/W	3,800 lm
911401523445	RC430X LED38/840 W60L60 WIA OC	4000 K	80	122 lm/W	3,800 lm
911401523745	RC430V LED38/840 W60L60 PSU OC CAU	4000 K	80	123 lm/W	3,800 lm
911401524045	RC430V LED38/840 W60L60 PSD OC CAU	4000 K	80	117 lm/W	3,800 lm
911401524345	RC430X LED38/840 W60L60 WIA OC CAU	4000 K	80	122 lm/W	3,800 lm
911401524645	RC430V LED36/940 W60L60 PSU OC	4000 K	90	117 lm/W	3,600 lm
911401524945	RC430V LED36/940 W60L60 PSD OC	4000 K	90	112 lm/W	3,600 lm
911401525245	RC430X LED36/940 W60L60 WIA OC	4000 K	90	115 lm/W	3,600 lm
911401525545	RC430V LED36/940 W60L60 PSU OC CAU	4000 K	90	117 lm/W	3,600 lm
911401525845	RC430V LED36/940 W60L60 PSD OC CAU	4000 K	90	112 lm/W	3,600 lm
911401526145	RC430X LED36/940 W60L60 WIA OC CAU	4000 K	90	115 lm/W	3,600 lm
911401522645	RC430V LED55/840 W60L120 PSU OC	4000 K	80	128 lm/W	5,500 lm
911401522945	RC430V LED55/840 W60L120 PSD OC	4000 K	80	121 lm/W	5,500 lm
911401523245	RC430X LED49/840 W60L120 WIA OC	4000 K	80	129 lm/W	4,900 lm
911401523545	RC430V LED55/840 W60L120 PSU OC CAU	4000 K	80	128 lm/W	5,500 lm
911401523845	RC430V LED55/840 W60L120 PSD OC CAU	4000 K	80	121 lm/W	5,500 lm
911401524145	RC430X LED49/840 W60L120 WIA OC CAU	4000 K	80	129 lm/W	4,900 lm
911401524445	RC430V LED52/940 W60L120 PSU OC	4000 K	90	122 lm/W	5,200 lm
911401524745	RC430V LED52/940 W60L120 PSD OC	4000 K	90	115 lm/W	5,200 lm
911401525045	RC430X LED46/940 W60L120 WIA OC	4000 K	90	122 lm/W	4,600 lm
911401525345	RC430V LED52/940 W60L120 PSU OC CAU	4000 K	90	122 lm/W	5,200 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401525645	RC430V LED52/940 W60L120 PSD OC CAU	4000 K	90	115 lm/W	5,200 lm
911401525945	RC430X LED46/940 W60L120 WIA OC CAU	4000 K	90	122 lm/W	4,600 lm
911401580945	RC430V LED40/840 W30L120 PSU OC SG	4000 K	80	134 lm/W	4,000 lm
911401581145	RC430V LED37/865 W303L1210 PSU OC UVG	6500 K	80	131 lm/W	3,700 lm
911401581245	RC430V LED37/850 W303L1210 PSU OC UVG	5000 K	80	131 lm/W	3,700 lm
911401581345	RC430V LED37/840 W303L1210 PSU OC UVG	4000 K	80	131 lm/W	3,700 lm
911401581445	RC430V LED35/830 W303L1210 PSU OC UVG	3000 K	80	121 lm/W	3,500 lm
911401582045	RC430V LED36/9TW W30L120 PSD OC	Tunable white 2700-6500 K	90	124 lm/W	3,600 lm
911401582345	RC430V LED36/9TW W30L120 PSD OC CAU	Tunable white 2700-6500 K	90	124 lm/W	3,600 lm
911401583845	RC430V LED39/BioUPD W30L120 PSD OC	4000 K	80	116 lm/W	3,900 lm
911401584145	RC430V LED39/BioUPD W30L120 PSD OC CAU	4000 K	80	116 lm/W	3,900 lm
911401584845	RC430V LED38/840 W30L120 PSD OC U/D	4000 K	80	131 lm/W	3,800 lm
911401585145	RC430V LED36/940 W30L120 PSD OC U/D	4000 K	90	124 lm/W	3,600 lm
911401586645	RC430V LED38/840 W30L120 PSD OC U/D CAU	4000 K	80	131 lm/W	3,800 lm
911401586945	RC430V LED36/940 W30L120 PSD OC U/D CAU	4000 K	90	124 lm/W	3,600 lm
911401593345	RC430V LED40/865 W303L1210 PSU OC	6500 K	80	134 lm/W	4,000 lm
911401593445	RC430V LED40/850 W303L1210 PSU OC	5000 K	80	134 lm/W	4,000 lm
911401593545	RC430V LED40/840 W303L1210 PSU OC	4000 K	80	134 lm/W	4,000 lm
911401593645	RC430V LED37/830 W303L1210 PSU OC	3000 K	80	124 lm/W	3,700 lm
911401594145	RC430V LED40/865 W303L1210 PSD OC	6500 K	80	126 lm/W	4,000 lm
911401594245	RC430V LED40/850 W303L1210 PSD OC	5000 K	80	126 lm/W	4,000 lm
911401594345	RC430V LED40/840 W303L1210 PSD OC	4000 K	80	126 lm/W	4,000 lm
911401594445	RC430V LED37/830 W303L1210 PSD OC	3000 K	80	117 lm/W	3,700 lm
911401581045	RC430V LED40/840 W60L60 PSU OC SG	4000 K	80	132 lm/W	4,000 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401581545	RC430V LED35/865 W603L603 PSU OC UVG	6500 K	80	120 lm/W	3,500 lm
911401581645	RC430V LED35/850 W603L603 PSU OC UVG	5000 K	80	120 lm/W	3,500 lm
911401581745	RC430V LED35/840 W603L603 PSU OC UVG	4000 K	80	120 lm/W	3,500 lm
911401581845	RC430V LED33/830 W603L603 PSU OC UVG	3000 K	80	112 lm/W	3,300 lm
911401582145	RC430V LED35/9TW W60L60 PSD OC	Tunable white 2700-6500 K	90	118 lm/W	3,500 lm
911401582445	RC430V LED35/9TW W60L60 PSD OC CAU	Tunable white 2700-6500 K	90	118 lm/W	3,500 lm
911401583945	RC430V LED37/BioUPD W60L60 PSD OC	4000 K	80	106 lm/W	3,700 lm
911401584245	RC430V LED37/BioUPD W60L60 PSD OC CAU	4000 K	80	106 lm/W	3,700 lm
911401584945	RC430V LED37/840 W60L60 PSD OC U/D	4000 K	80	114 lm/W	3,700 lm
911401585245	RC430V LED35/940 W60L60 PSD OC U/D	4000 K	90	108 lm/W	3,500 lm
911401586745	RC430V LED37/840 W60L60 PSD OC U/D CAU	4000 K	80	114 lm/W	3,700 lm
911401587045	RC430V LED35/940 W60L60 PSD OC U/D CAU	4000 K	90	108 lm/W	3,500 lm
911401593745	RC430V LED38/865 W603L603 PSU OC	6500 K	80	123 lm/W	3,800 lm
911401593845	RC430V LED38/850 W603L603 PSU OC	5000 K	80	123 lm/W	3,800 lm
911401593945	RC430V LED38/840 W603L603 PSU OC	4000 K	80	123 lm/W	3,800 lm
911401594045	RC430V LED36/830 W603L603 PSU OC	3000 K	80	114 lm/W	3,600 lm
911401594545	RC430V LED38/865 W603L603 PSD OC	6500 K	80	117 lm/W	3,800 lm
911401594645	RC430V LED38/850 W603L603 PSD OC	5000 K	80	117 lm/W	3,800 lm
911401594745	RC430V LED38/840 W603L603 PSD OC	4000 K	80	117 lm/W	3,800 lm
911401594845	RC430V LED36/830 W603L603 PSD OC	3000 K	80	109 lm/W	3,600 lm
911401522745	RC430V LED40/840 W30L120 PSU OC	4000 K	80	134 lm/W	4,000 lm
911401523045	RC430V LED40/840 W30L120 PSD OC	4000 K	80	126 lm/W	4,000 lm
911401523345	RC430X LED40/840 W30L120 WIA OC	4000 K	80	132 lm/W	4,000 lm
911401523645	RC430V LED40/840 W30L120 PSU OC CAU	4000 K	80	134 lm/W	4,000 lm
911401523945	RC430V LED40/840 W30L120 PSD OC CAU	4000 K	80	126 lm/W	4,000 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401524245	RC430X LED40/840 W30L120 WIA OC CAU	4000 K	80	132 lm/W	4,000 lm
911401524545	RC430V LED38/940 W30L120 PSU OC	4000 K	90	127 lm/W	3,800 lm
911401524845	RC430V LED38/940 W30L120 PSD OC	4000 K	90	120 lm/W	3,800 lm
911401525145	RC430X LED38/940 W30L120 WIA OC	4000 K	90	126 lm/W	3,800 lm
911401525445	RC430V LED38/940 W30L120 PSU OC CAU	4000 K	90	127 lm/W	3,800 lm
911401525745	RC430V LED38/940 W30L120 PSD OC CAU	4000 K	90	120 lm/W	3,800 lm
911401526045	RC430X LED38/940 W30L120 WIA OC CAU	4000 K	90	126 lm/W	3,800 lm

Light Technical (2/2)

Order Code	Full Product Name	Number of light sources
911401578645	RC430X LED38/840 W60L60 SC2 OC	1
911401578945	RC430X LED36/940 W60L60 SC2 OC	1
911401579245	RC430X LED38/840 W60L60 SC2 OC CAU	1
911401579545	RC430X LED36/940 W60L60 SC2 OC CAU	1
911401579845	RC430X LED38/840 W60L60 SC15 OC	1
911401580145	RC430X LED36/940 W60L60 SC15 OC	1
911401580445	RC430X LED38/840 W60L60 SC15 OC CAU	1
911401580745	RC430X LED36/940 W60L60 SC15 OC CAU	1
911401582745	RC430X LED35/9TW W60L60 SC2 OC	1
911401583045	RC430X LED35/9TW W60L60 SC2 OC CAU	1
911401583345	RC430X LED35/9TW W60L60 SC15 OC	1
911401583645	RC430X LED35/9TW W60L60 SC15 OC CAU	1
911401584345	RC430X LED37/BioUPD W60L60 SC2 OC	1
911401584445	RC430X LED37/BioUPD W60L60 SC2 OC CAU	1
911401584545	RC430X LED37/BioUPD W60L60 SC15 OC	1
911401584645	RC430X LED37/BioUPD W60L60 SC15 OC CAU	1
911401585545	RC430X LED37/840 W60L60 SC2 OC U/D	1
911401585845	RC430X LED35/940 W60L60 SC2 OC U/D	1
911401586145	RC430X LED37/840 W60L60 SC15 OC U/D	1
911401586445	RC430X LED35/940 W60L60 SC15 OC U/D	1
911401587345	RC430X LED37/840 W60L60 SC2 OC U/D CAU	1
911401587645	RC430X LED35/940 W60L60 SC2 OC U/D CAU	1
911401587945	RC430X LED37/840 W60L60 SC15 OC U/D CAU	1
911401588245	RC430X LED35/940 W60L60 SC15 OC U/D CAU	1
911401578445	RC430X LED55/840 W60L120 SC2 OC	1
911401578745	RC430X LED52/940 W60L120 SC2 OC	1
911401579045	RC430X LED55/840 W60L120 SC2 OC CAU	1
911401579345	RC430X LED52/940 W60L120 SC2 OC CAU	1
911401579645	RC430X LED55/840 W60L120 SC15 OC	1
911401579945	RC430X LED52/940 W60L120 SC15 OC	1
911401580245	RC430X LED55/840 W60L120 SC15 OC CAU	1

Order Code	Full Product Name	Number of light sources
911401580545	RC430X LED52/940 W60L120 SC15 OC CAU	1
911401580845	RC430V LED54/840 W60L120 PSU OC SG	1
911401581945	RC430V LED51/9TW W60L120 PSD OC	1
911401582245	RC430V LED51/9TW W60L120 PSD OC CAU	1
911401582545	RC430X LED51/9TW W60L120 SC2 OC	1
911401582845	RC430X LED51/9TW W60L120 SC2 OC CAU	1
911401583145	RC430X LED51/9TW W60L120 SC15 OC	1
911401583445	RC430X LED51/9TW W60L120 SC15 OC CAU	1
911401583745	RC430V LED52/BioUPD W60L120 PSD OC	1
911401584045	RC430V LED52/BioUPD W60L120 PSD OC CAU	1
911401584745	RC430V LED54/840 W60L120 PSD OC U/D	1
911401585045	RC430V LED51/940 W60L120 PSD OC U/D	1
911401585345	RC430X LED54/840 W60L120 SC2 OC U/D	1
911401585645	RC430X LED51/940 W60L120 SC2 OC U/D	1
911401585945	RC430X LED54/840 W60L120 SC15 OC U/D	1
911401586245	RC430X LED51/940 W60L120 SC15 OC U/D	1
911401586545	RC430V LED54/840 W60L120 PSD OC U/D CAU	1
911401586845	RC430V LED51/940 W60L120 PSD OC U/D CAU	1
911401587145	RC430X LED54/840 W60L120 SC2 OC U/D CAU	1
911401587445	RC430X LED51/940 W60L120 SC2 OC U/D CAU	1
911401587745	RC430X LED54/840 W60L120 SC15 OC U/D CAU	1
911401588045	RC430X LED51/940 W60L120 SC15 OC U/D CAU	1
911401578545	RC430X LED40/840 W30L120 SC2 OC	1
911401578845	RC430X LED38/940 W30L120 SC2 OC	1
911401579145	RC430X LED40/840 W30L120 SC2 OC CAU	1
911401579445	RC430X LED38/940 W30L120 SC2 OC CAU	1
911401579745	RC430X LED40/840 W30L120 SC15 OC	1
911401580045	RC430X LED38/940 W30L120 SC15 OC	1
911401580345	RC430X LED40/840 W30L120 SC15 OC CAU	1
911401580645	RC430X LED38/940 W30L120 SC15 OC CAU	1
911401582645	RC430X LED36/9TW W30L120 SC2 OC	1

Order Code	Full Product Name	Number of light sources
911401582945	RC430X LED36/9TW W30L120 SC2 OC CAU	1
911401583245	RC430X LED36/9TW W30L120 SC15 OC	1
911401583545	RC430X LED36/9TW W30L120 SC15 OC CAU	1
911401585445	RC430X LED38/840 W30L120 SC2 OC U/D	1
911401585745	RC430X LED36/940 W30L120 SC2 OC U/D	1
911401586045	RC430X LED38/840 W30L120 SC15 OC U/D	1
911401586345	RC430X LED36/940 W30L120 SC15 OC U/D	1
911401587245	RC430X LED38/840 W30L120 SC2 OC U/D CAU	1
911401587545	RC430X LED36/940 W30L120 SC2 OC U/D CAU	1
911401587845	RC430X LED38/840 W30L120 SC15 OC U/D CAU	1
911401588145	RC430X LED36/940 W30L120 SC15 OC U/D CAU	1
911401522845	RC430V LED38/840 W60L60 PSU OC	144
911401523145	RC430V LED38/840 W60L60 PSD OC	144
911401523445	RC430X LED38/840 W60L60 WIA OC	144
911401523745	RC430V LED38/840 W60L60 PSU OC CAU	144
911401524045	RC430V LED38/840 W60L60 PSD OC CAU	144
911401524345	RC430X LED38/840 W60L60 WIA OC CAU	144
911401524645	RC430V LED36/940 W60L60 PSU OC	144
911401524945	RC430V LED36/940 W60L60 PSD OC	144
911401525245	RC430X LED36/940 W60L60 WIA OC	144
911401525545	RC430V LED36/940 W60L60 PSU OC CAU	144
911401525845	RC430V LED36/940 W60L60 PSD OC CAU	144
911401526145	RC430X LED36/940 W60L60 WIA OC CAU	144
911401522645	RC430V LED55/840 W60L120 PSU OC	228
911401522945	RC430V LED55/840 W60L120 PSD OC	228
911401523245	RC430X LED49/840 W60L120 WIA OC	228
911401523545	RC430V LED55/840 W60L120 PSU OC CAU	228
911401523845	RC430V LED55/840 W60L120 PSD OC CAU	228
911401524145	RC430X LED49/840 W60L120 WIA OC CAU	228
911401524445	RC430V LED52/940 W60L120 PSU OC	228
911401524745	RC430V LED52/940 W60L120 PSD OC	228
911401525045	RC430X LED46/940 W60L120 WIA OC	228
911401525345	RC430V LED52/940 W60L120 PSU OC CAU	228
911401525645	RC430V LED52/940 W60L120 PSD OC CAU	228
911401525945	RC430X LED46/940 W60L120 WIA OC CAU	228
911401580945	RC430V LED40/840 W30L120 PSU OC SG	1
911401581145	RC430V LED37/865 W303L1210 PSU OC UVG	1
911401581245	RC430V LED37/850 W303L1210 PSU OC UVG	1
911401581345	RC430V LED37/840 W303L1210 PSU OC UVG	1
911401581445	RC430V LED35/830 W303L1210 PSU OC UVG	1
911401582045	RC430V LED36/9TW W30L120 PSD OC	1
911401582345	RC430V LED36/9TW W30L120 PSD OC CAU	1
911401583845	RC430V LED39/BioUPD W30L120 PSD OC	1
911401584145	RC430V LED39/BioUPD W30L120 PSD OC CAU	1
911401584845	RC430V LED38/840 W30L120 PSD OC U/D	1

Order Code	Full Product Name	Number of light sources
911401585145	RC430V LED36/940 W30L120 PSD OC U/D	1
911401586645	RC430V LED38/840 W30L120 PSD OC U/D CAU	1
911401586945	RC430V LED36/940 W30L120 PSD OC U/D CAU	1
911401593345	RC430V LED40/865 W303L1210 PSU OC	1
911401593445	RC430V LED40/850 W303L1210 PSU OC	1
911401593545	RC430V LED40/840 W303L1210 PSU OC	1
911401593645	RC430V LED37/830 W303L1210 PSU OC	1
911401594145	RC430V LED40/865 W303L1210 PSD OC	1
911401594245	RC430V LED40/850 W303L1210 PSD OC	1
911401594345	RC430V LED40/840 W303L1210 PSD OC	1
911401594445	RC430V LED37/830 W303L1210 PSD OC	1
911401581045	RC430V LED40/840 W60L60 PSU OC SG	1
911401581545	RC430V LED35/865 W603L603 PSU OC UVG	1
911401581645	RC430V LED35/850 W603L603 PSU OC UVG	1
911401581745	RC430V LED35/840 W603L603 PSU OC UVG	1
911401581845	RC430V LED33/830 W603L603 PSU OC UVG	1
911401582145	RC430V LED35/9TW W60L60 PSD OC	1
911401582445	RC430V LED35/9TW W60L60 PSD OC CAU	1
911401583945	RC430V LED37/BioUPD W60L60 PSD OC	1
911401584245	RC430V LED37/BioUPD W60L60 PSD OC CAU	1
911401584945	RC430V LED37/840 W60L60 PSD OC U/D	1
911401585245	RC430V LED35/940 W60L60 PSD OC U/D	1
911401586745	RC430V LED37/840 W60L60 PSD OC U/D CAU	1
911401587045	RC430V LED35/940 W60L60 PSD OC U/D CAU	1
911401593745	RC430V LED38/865 W603L603 PSU OC	1
911401593845	RC430V LED38/850 W603L603 PSU OC	1
911401593945	RC430V LED38/840 W603L603 PSU OC	1
911401594045	RC430V LED36/830 W603L603 PSU OC	1
911401594545	RC430V LED38/865 W603L603 PSD OC	1
911401594645	RC430V LED38/850 W603L603 PSD OC	1
911401594745	RC430V LED38/840 W603L603 PSD OC	1
911401594845	RC430V LED36/830 W603L603 PSD OC	1
911401522745	RC430V LED40/840 W30L120 PSU OC	378
911401523045	RC430V LED40/840 W30L120 PSD OC	378
911401523345	RC430X LED40/840 W30L120 WIA OC	378
911401523645	RC430V LED40/840 W30L120 PSU OC CAU	378
911401523945	RC430V LED40/840 W30L120 PSD OC CAU	378
911401524245	RC430X LED40/840 W30L120 WIA OC CAU	378
911401524545	RC430V LED38/940 W30L120 PSU OC	378
911401524845	RC430V LED38/940 W30L120 PSD OC	378
911401525145	RC430X LED38/940 W30L120 WIA OC	378
911401525445	RC430V LED38/940 W30L120 PSU OC CAU	378
911401525745	RC430V LED38/940 W30L120 PSD OC CAU	378
911401526045	RC430X LED38/940 W30L120 WIA OC CAU	378

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401578645	RC430X LED38/840 W60L60 SC2 OC	32 W
911401578945	RC430X LED36/940 W60L60 SC2 OC	32 W

Order Code	Full Product Name	Power Consumption
911401579245	RC430X LED38/840 W60L60 SC2 OC CAU	32 W
911401579545	RC430X LED36/940 W60L60 SC2 OC CAU	32 W

Order Code	Full Product Name	Power Consumption
911401579845	RC430X LED38/840 W60L60 SC15 OC	32 W
911401580145	RC430X LED36/940 W60L60 SC15 OC	32 W
911401580445	RC430X LED38/840 W60L60 SC15 OC CAU	32 W
911401580745	RC430X LED36/940 W60L60 SC15 OC CAU	32 W
911401582745	RC430X LED35/9TW W60L60 SC2 OC	29 W
911401583045	RC430X LED35/9TW W60L60 SC2 OC CAU	29 W
911401583345	RC430X LED35/9TW W60L60 SC15 OC	29 W
911401583645	RC430X LED35/9TW W60L60 SC15 OC CAU	29 W
911401584345	RC430X LED37/BioUPD W60L60 SC2 OC	35 W
911401584445	RC430X LED37/BioUPD W60L60 SC2 OC CAU	35 W
911401584545	RC430X LED37/BioUPD W60L60 SC15 OC	35 W
911401584645	RC430X LED37/BioUPD W60L60 SC15 OC CAU	35 W
911401585545	RC430X LED37/840 W60L60 SC2 OC U/D	32 W
911401585845	RC430X LED35/940 W60L60 SC2 OC U/D	32 W
911401586145	RC430X LED37/840 W60L60 SC15 OC U/D	32 W
911401586445	RC430X LED35/940 W60L60 SC15 OC U/D	32 W
911401587345	RC430X LED37/840 W60L60 SC2 OC U/D CAU	32 W
911401587645	RC430X LED35/940 W60L60 SC2 OC U/D CAU	32 W
911401587945	RC430X LED37/840 W60L60 SC15 OC U/D CAU	32 W
911401588245	RC430X LED35/940 W60L60 SC15 OC U/D CAU	32 W
911401578445	RC430X LED55/840 W60L120 SC2 OC	45 W
911401578745	RC430X LED52/940 W60L120 SC2 OC	45 W
911401579045	RC430X LED55/840 W60L120 SC2 OC CAU	45 W
911401579345	RC430X LED52/940 W60L120 SC2 OC CAU	45 W
911401579645	RC430X LED55/840 W60L120 SC15 OC	45 W
911401579945	RC430X LED52/940 W60L120 SC15 OC	45 W
911401580245	RC430X LED55/840 W60L120 SC15 OC CAU	45 W
911401580545	RC430X LED52/940 W60L120 SC15 OC CAU	45 W
911401580845	RC430V LED54/840 W60L120 PSU OC SG	42 W
911401581945	RC430V LED51/9TW W60L120 PSD OC	43 W
911401582245	RC430V LED51/9TW W60L120 PSD OC CAU	43 W
911401582545	RC430X LED51/9TW W60L120 SC2 OC	43 W
911401582845	RC430X LED51/9TW W60L120 SC2 OC CAU	43 W
911401583145	RC430X LED51/9TW W60L120 SC15 OC	43 W
911401583445	RC430X LED51/9TW W60L120 SC15 OC CAU	43 W
911401583745	RC430V LED52/BioUPD W60L120 PSD OC	47 W
911401584045	RC430V LED52/BioUPD W60L120 PSD OC CAU	47 W
911401584745	RC430V LED54/840 W60L120 PSD OC U/D	44 W
911401585045	RC430V LED51/940 W60L120 PSD OC U/D	44 W
911401585345	RC430X LED54/840 W60L120 SC2 OC U/D	44 W
911401585645	RC430X LED51/940 W60L120 SC2 OC U/D	44 W
911401585945	RC430X LED54/840 W60L120 SC15 OC U/D	44 W
911401586245	RC430X LED51/940 W60L120 SC15 OC U/D	44 W
911401586545	RC430V LED54/840 W60L120 PSD OC U/D CAU	44 W
911401586845	RC430V LED51/940 W60L120 PSD OC U/D CAU	44 W
911401587145	RC430X LED54/840 W60L120 SC2 OC U/D CAU	44 W
911401587445	RC430X LED51/940 W60L120 SC2 OC U/D CAU	44 W
911401587745	RC430X LED54/840 W60L120 SC15 OC U/D CAU	44 W
911401588045	RC430X LED51/940 W60L120 SC15 OC U/D CAU	44 W
911401578545	RC430X LED40/840 W30L120 SC2 OC	30 W
911401578845	RC430X LED38/940 W30L120 SC2 OC	30 W
911401579145	RC430X LED40/840 W30L120 SC2 OC CAU	30 W

Order Code	Full Product Name	Power Consumption
911401579445	RC430X LED38/940 W30L120 SC2 OC CAU	30 W
911401579745	RC430X LED40/840 W30L120 SC15 OC	30 W
911401580045	RC430X LED38/940 W30L120 SC15 OC	30 W
911401580345	RC430X LED40/840 W30L120 SC15 OC CAU	30 W
911401580645	RC430X LED38/940 W30L120 SC15 OC CAU	30 W
911401582645	RC430X LED36/9TW W30L120 SC2 OC	29 W
911401582945	RC430X LED36/9TW W30L120 SC2 OC CAU	29 W
911401583245	RC430X LED36/9TW W30L120 SC15 OC	29 W
911401583545	RC430X LED36/9TW W30L120 SC15 OC CAU	29 W
911401585445	RC430X LED38/840 W30L120 SC2 OC U/D	29 W
911401585745	RC430X LED36/940 W30L120 SC2 OC U/D	29 W
911401586045	RC430X LED38/840 W30L120 SC15 OC U/D	29 W
911401586345	RC430X LED36/940 W30L120 SC15 OC U/D	29 W
911401587245	RC430X LED38/840 W30L120 SC2 OC U/D CAU	29 W
911401587545	RC430X LED36/940 W30L120 SC2 OC U/D CAU	29 W
911401587845	RC430X LED38/840 W30L120 SC15 OC U/D CAU	29 W
911401588145	RC430X LED36/940 W30L120 SC15 OC U/D CAU	29 W
911401522845	RC430V LED38/840 W60L60 PSU OC	31 W
911401523145	RC430V LED38/840 W60L60 PSD OC	33 W
911401523445	RC430X LED38/840 W60L60 WIA OC	31 W
911401523745	RC430V LED38/840 W60L60 PSU OC CAU	31 W
911401524045	RC430V LED38/840 W60L60 PSD OC CAU	33 W
911401524345	RC430X LED38/840 W60L60 WIA OC CAU	31 W
911401524645	RC430V LED36/940 W60L60 PSU OC	31 W
911401524945	RC430V LED36/940 W60L60 PSD OC	33 W
911401525245	RC430X LED36/940 W60L60 WIA OC	31 W
911401525545	RC430V LED36/940 W60L60 PSU OC CAU	31 W
911401525845	RC430V LED36/940 W60L60 PSD OC CAU	33 W
911401526145	RC430X LED36/940 W60L60 WIA OC CAU	31 W
911401522645	RC430V LED55/840 W60L120 PSU OC	43 W
911401522945	RC430V LED55/840 W60L120 PSD OC	46 W
911401523245	RC430X LED49/840 W60L120 WIA OC	38 W
911401523545	RC430V LED55/840 W60L120 PSU OC CAU	43 W
911401523845	RC430V LED55/840 W60L120 PSD OC CAU	46 W
911401524145	RC430X LED49/840 W60L120 WIA OC CAU	38 W
911401524445	RC430V LED52/940 W60L120 PSU OC	43 W
911401524745	RC430V LED52/940 W60L120 PSD OC	46 W
911401525045	RC430X LED46/940 W60L120 WIA OC	38 W
911401525345	RC430V LED52/940 W60L120 PSU OC CAU	43 W
911401525645	RC430V LED52/940 W60L120 PSD OC CAU	46 W
911401525945	RC430X LED46/940 W60L120 WIA OC CAU	38 W
911401580945	RC430V LED40/840 W30L120 PSU OC SG	29 W
911401581145	RC430V LED37/865 W303L1210 PSU OC UVG	29 W
911401581245	RC430V LED37/850 W303L1210 PSU OC UVG	29 W
911401581345	RC430V LED37/840 W303L1210 PSU OC UVG	29 W
911401581445	RC430V LED35/830 W303L1210 PSU OC UVG	29 W
911401582045	RC430V LED36/9TW W30L120 PSD OC	29 W
911401582345	RC430V LED36/9TW W30L120 PSD OC CAU	29 W
911401583845	RC430V LED39/BioUPD W30L120 PSD OC	33 W
911401584145	RC430V LED39/BioUPD W30L120 PSD OC CAU	33 W
911401584845	RC430V LED38/840 W30L120 PSD OC U/D	29 W
911401585145	RC430V LED36/940 W30L120 PSD OC U/D	29 W

Order Code	Full Product Name	Power Consumption
911401586645	RC430V LED38/840 W30L120 PSD OC U/D CAU	29 W
911401586945	RC430V LED36/940 W30L120 PSD OC U/D CAU	29 W
911401593345	RC430V LED40/865 W303L1210 PSU OC	30 W
911401593445	RC430V LED40/850 W303L1210 PSU OC	30 W
911401593545	RC430V LED40/840 W303L1210 PSU OC	30 W
911401593645	RC430V LED37/830 W303L1210 PSU OC	30 W
911401594145	RC430V LED40/865 W303L1210 PSD OC	32 W
911401594245	RC430V LED40/850 W303L1210 PSD OC	32 W
911401594345	RC430V LED40/840 W303L1210 PSD OC	32 W
911401594445	RC430V LED37/830 W303L1210 PSD OC	32 W
911401581045	RC430V LED40/840 W60L60 PSU OC SG	31 W
911401581545	RC430V LED35/865 W603L603 PSU OC UVG	30 W
911401581645	RC430V LED35/850 W603L603 PSU OC UVG	30 W
911401581745	RC430V LED35/840 W603L603 PSU OC UVG	30 W
911401581845	RC430V LED33/830 W603L603 PSU OC UVG	30 W
911401582145	RC430V LED35/9TW W60L60 PSD OC	29 W
911401582445	RC430V LED35/9TW W60L60 PSD OC CAU	29 W
911401583945	RC430V LED37/BioUPD W60L60 PSD OC	35 W
911401584245	RC430V LED37/BioUPD W60L60 PSD OC CAU	35 W
911401584945	RC430V LED37/840 W60L60 PSD OC U/D	32 W
911401585245	RC430V LED35/940 W60L60 PSD OC U/D	32 W
911401586745	RC430V LED37/840 W60L60 PSD OC U/D CAU	32 W

Order Code	Full Product Name	Power Consumption
911401587045	RC430V LED35/940 W60L60 PSD OC U/D CAU	32 W
911401593745	RC430V LED38/865 W603L603 PSU OC	31 W
911401593845	RC430V LED38/850 W603L603 PSU OC	31 W
911401593945	RC430V LED38/840 W603L603 PSU OC	31 W
911401594045	RC430V LED36/830 W603L603 PSU OC	31 W
911401594545	RC430V LED38/865 W603L603 PSD OC	33 W
911401594645	RC430V LED38/850 W603L603 PSD OC	33 W
911401594745	RC430V LED38/840 W603L603 PSD OC	33 W
911401594845	RC430V LED36/830 W603L603 PSD OC	33 W
911401522745	RC430V LED40/840 W30L120 PSU OC	30 W
911401523045	RC430V LED40/840 W30L120 PSD OC	32 W
911401523345	RC430X LED40/840 W30L120 WIA OC	30 W
911401523645	RC430V LED40/840 W30L120 PSU OC CAU	30 W
911401523945	RC430V LED40/840 W30L120 PSD OC CAU	32 W
911401524245	RC430X LED40/840 W30L120 WIA OC CAU	30 W
911401524545	RC430V LED38/940 W30L120 PSU OC	30 W
911401524845	RC430V LED38/940 W30L120 PSD OC	32 W
911401525145	RC430X LED38/940 W30L120 WIA OC	30 W
911401525445	RC430V LED38/940 W30L120 PSU OC CAU	30 W
911401525745	RC430V LED38/940 W30L120 PSD OC CAU	32 W
911401526045	RC430X LED38/940 W30L120 WIA OC CAU	30 W

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
911401578645	RC430X LED38/840 W60L60 SC2 OC	Wireless Dim	1%
911401578945	RC430X LED36/940 W60L60 SC2 OC	Wireless Dim	1%
911401579245	RC430X LED38/840 W60L60 SC2 OC CAU	Wireless Dim	1%
911401579545	RC430X LED36/940 W60L60 SC2 OC CAU	Wireless Dim	1%
911401579845	RC430X LED38/840 W60L60 SC15 OC	Wireless Dim	1%
911401580145	RC430X LED36/940 W60L60 SC15 OC	Wireless Dim	1%
911401580445	RC430X LED38/840 W60L60 SC15 OC CAU	Wireless Dim	1%
911401580745	RC430X LED36/940 W60L60 SC15 OC CAU	Wireless Dim	1%
911401582745	RC430X LED35/9TW W60L60 SC2 OC	Wireless Dim	1%
911401583045	RC430X LED35/9TW W60L60 SC2 OC CAU	Wireless Dim	1%
911401583345	RC430X LED35/9TW W60L60 SC15 OC	Wireless Dim	1%
911401583645	RC430X LED35/9TW W60L60 SC15 OC CAU	Wireless Dim	1%
911401584345	RC430X LED37/BioUPD W60L60 SC2 OC	Wireless Dim	1%
911401584445	RC430X LED37/BioUPD W60L60 SC2 OC CAU	Wireless Dim	1%
911401584545	RC430X LED37/BioUPD W60L60 SC15 OC	Wireless Dim	1%

Order Code	Full Product Name	Dimmable	Maximum dim level
911401584645	RC430X LED37/BioUPD W60L60 SC15 OC CAU	Wireless Dim	1%
911401585545	RC430X LED37/840 W60L60 SC2 OC U/D	Wireless Dim	1%
911401585845	RC430X LED35/940 W60L60 SC2 OC U/D	Wireless Dim	1%
911401586145	RC430X LED37/840 W60L60 SC15 OC U/D	Wireless Dim	1%
911401586445	RC430X LED35/940 W60L60 SC15 OC U/D	Wireless Dim	1%
911401587345	RC430X LED37/840 W60L60 SC2 OC U/D CAU	Wireless Dim	1%
911401587645	RC430X LED35/940 W60L60 SC2 OC U/D CAU	Wireless Dim	1%
911401587945	RC430X LED37/840 W60L60 SC15 OC U/D CAU	Wireless Dim	1%
911401588245	RC430X LED35/940 W60L60 SC15 OC U/D CAU	Wireless Dim	1%
911401578445	RC430X LED55/840 W60L120 SC2 OC	Wireless Dim	1%
911401578745	RC430X LED52/940 W60L120 SC2 OC	Wireless Dim	1%
911401579045	RC430X LED55/840 W60L120 SC2 OC CAU	Wireless Dim	1%
911401579345	RC430X LED52/940 W60L120 SC2 OC CAU	Wireless Dim	1%
911401579645	RC430X LED55/840 W60L120 SC15 OC	Wireless Dim	1%

Order Code	Full Product Name	Dimmable	Maximum dim level
911401579945	RC430X LED52/940 W60L120 SC15 OC	Wireless Dim	1%
911401580245	RC430X LED55/840 W60L120 SC15 OC CAU	Wireless Dim	1%
911401580545	RC430X LED52/940 W60L120 SC15 OC CAU	Wireless Dim	1%
911401580845	RC430V LED54/840 W60L120 PSU OC SG	-	Not applicable
911401581945	RC430V LED51/9TW W60L120 PSD OC	DALI	1%
911401582245	RC430V LED51/9TW W60L120 PSD OC CAU	DALI	1%
911401582545	RC430X LED51/9TW W60L120 SC2 OC	Wireless Dim	1%
911401582845	RC430X LED51/9TW W60L120 SC2 OC CAU	Wireless Dim	1%
911401583145	RC430X LED51/9TW W60L120 SC15 OC	Wireless Dim	1%
911401583445	RC430X LED51/9TW W60L120 SC15 OC CAU	Wireless Dim	1%
911401583745	RC430V LED52/BioUPD W60L120 PSD OC	DALI	1%
911401584045	RC430V LED52/BioUPD W60L120 PSD OC CAU	DALI	1%
911401584745	RC430V LED54/840 W60L120 PSD OC U/D	DALI	1%
911401585045	RC430V LED51/940 W60L120 PSD OC U/D	DALI	1%
911401585345	RC430X LED54/840 W60L120 SC2 OC U/D	Wireless Dim	1%
911401585645	RC430X LED51/940 W60L120 SC2 OC U/D	Wireless Dim	1%
911401585945	RC430X LED54/840 W60L120 SC15 OC U/D	Wireless Dim	1%
911401586245	RC430X LED51/940 W60L120 SC15 OC U/D	Wireless Dim	1%
911401586545	RC430V LED54/840 W60L120 PSD OC U/D CAU	DALI	1%
911401586845	RC430V LED51/940 W60L120 PSD OC U/D CAU	DALI	1%
911401587145	RC430X LED54/840 W60L120 SC2 OC U/D CAU	Wireless Dim	1%
911401587445	RC430X LED51/940 W60L120 SC2 OC U/D CAU	Wireless Dim	1%
911401587745	RC430X LED54/840 W60L120 SC15 OC U/D CAU	Wireless Dim	1%
911401588045	RC430X LED51/940 W60L120 SC15 OC U/D CAU	Wireless Dim	1%
911401578545	RC430X LED40/840 W30L120 SC2 OC	Wireless Dim	1%
911401578845	RC430X LED38/940 W30L120 SC2 OC	Wireless Dim	1%
911401579145	RC430X LED40/840 W30L120 SC2 OC CAU	Wireless Dim	1%
911401579445	RC430X LED38/940 W30L120 SC2 OC CAU	Wireless Dim	1%
911401579745	RC430X LED40/840 W30L120 SC15 OC	Wireless Dim	1%

Order Code	Full Product Name	Dimmable	Maximum dim level
911401580045	RC430X LED38/940 W30L120 SC15 OC	Wireless Dim	1%
911401580345	RC430X LED40/840 W30L120 SC15 OC CAU	Wireless Dim	1%
911401580645	RC430X LED38/940 W30L120 SC15 OC CAU	Wireless Dim	1%
911401582645	RC430X LED36/9TW W30L120 SC2 OC	Wireless Dim	1%
911401582945	RC430X LED36/9TW W30L120 SC2 OC CAU	Wireless Dim	1%
911401583245	RC430X LED36/9TW W30L120 SC15 OC	Wireless Dim	1%
911401583545	RC430X LED36/9TW W30L120 SC15 OC CAU	Wireless Dim	1%
911401585445	RC430X LED38/840 W30L120 SC2 OC U/D	Wireless Dim	1%
911401585745	RC430X LED36/940 W30L120 SC2 OC U/D	Wireless Dim	1%
911401586045	RC430X LED38/840 W30L120 SC15 OC U/D	Wireless Dim	1%
911401586345	RC430X LED36/940 W30L120 SC15 OC U/D	Wireless Dim	1%
911401587245	RC430X LED38/840 W30L120 SC2 OC U/D CAU	Wireless Dim	1%
911401587545	RC430X LED36/940 W30L120 SC2 OC U/D CAU	Wireless Dim	1%
911401587845	RC430X LED38/840 W30L120 SC15 OC U/D CAU	Wireless Dim	1%
911401588145	RC430X LED36/940 W30L120 SC15 OC U/D CAU	Wireless Dim	1%
911401522845	RC430V LED38/840 W60L60 PSU OC	Fixed	Not applicable
911401523145	RC430V LED38/840 W60L60 PSD OC	DALI	1%
911401523445	RC430X LED38/840 W60L60 WIA OC	Wireless Dim	1%
911401523745	RC430V LED38/840 W60L60 PSU OC CAU	Fixed	Not applicable
911401524045	RC430V LED38/840 W60L60 PSD OC CAU	DALI	1%
911401524345	RC430X LED38/840 W60L60 WIA OC CAU	Wireless Dim	1%
911401524645	RC430V LED36/940 W60L60 PSU OC	Fixed	Not applicable
911401524945	RC430V LED36/940 W60L60 PSD OC	DALI	1%
911401525245	RC430X LED36/940 W60L60 WIA OC	Wireless Dim	1%
911401525545	RC430V LED36/940 W60L60 PSU OC CAU	Fixed	Not applicable
911401525845	RC430V LED36/940 W60L60 PSD OC CAU	DALI	1%
911401526145	RC430X LED36/940 W60L60 WIA OC CAU	Wireless Dim	1%
911401522645	RC430V LED55/840 W60L120 PSU OC	Fixed	Not applicable
911401522945	RC430V LED55/840 W60L120 PSD OC	DALI	3%
911401523245	RC430X LED49/840 W60L120 WIA OC	Wireless Dim	1%
911401523545	RC430V LED55/840 W60L120 PSU OC CAU	Fixed	Not applicable

Order Code	Full Product Name	Dimmable	Maximum dim level
911401523845	RC430V LED55/840 W60L120 PSD OC CAU	DALI	3%
911401524145	RC430X LED49/840 W60L120 WIA OC CAU	Wireless Dim	1%
911401524445	RC430V LED52/940 W60L120 PSU OC	Fixed	Not applicable
911401524745	RC430V LED52/940 W60L120 PSD OC	DALI	3%
911401525045	RC430X LED46/940 W60L120 WIA OC	Wireless Dim	1%
911401525345	RC430V LED52/940 W60L120 PSU OC CAU	Fixed	Not applicable
911401525645	RC430V LED52/940 W60L120 PSD OC CAU	DALI	3%
911401525945	RC430X LED46/940 W60L120 WIA OC CAU	Wireless Dim	1%
911401580945	RC430V LED40/840 W30L120 PSU OC SG	-	Not applicable
911401581145	RC430V LED37/865 W303L1210 PSU OC UVG	-	Not applicable
911401581245	RC430V LED37/850 W303L1210 PSU OC UVG	-	Not applicable
911401581345	RC430V LED37/840 W303L1210 PSU OC UVG	-	Not applicable
911401581445	RC430V LED35/830 W303L1210 PSU OC UVG	-	Not applicable
911401582045	RC430V LED36/9TW W30L120 PSD OC	DALI	1%
911401582345	RC430V LED36/9TW W30L120 PSD OC CAU	DALI	1%
911401583845	RC430V LED39/BioUPD W30L120 PSD OC	DALI	1%
911401584145	RC430V LED39/BioUPD W30L120 PSD OC CAU	DALI	1%
911401584845	RC430V LED38/840 W30L120 PSD OC U/D	DALI	1%
911401585145	RC430V LED36/940 W30L120 PSD OC U/D	DALI	1%
911401586645	RC430V LED38/840 W30L120 PSD OC U/D CAU	DALI	1%
911401586945	RC430V LED36/940 W30L120 PSD OC U/D CAU	DALI	1%
911401593345	RC430V LED40/865 W303L1210 PSU OC	-	Not applicable
911401593445	RC430V LED40/850 W303L1210 PSU OC	-	Not applicable
911401593545	RC430V LED40/840 W303L1210 PSU OC	-	Not applicable
911401593645	RC430V LED37/830 W303L1210 PSU OC	-	Not applicable
911401594145	RC430V LED40/865 W303L1210 PSD OC	DALI	1%
911401594245	RC430V LED40/850 W303L1210 PSD OC	DALI	1%
911401594345	RC430V LED40/840 W303L1210 PSD OC	DALI	1%
911401594445	RC430V LED37/830 W303L1210 PSD OC	DALI	1%
911401581045	RC430V LED40/840 W60L60 PSU OC SG	-	Not applicable
911401581545	RC430V LED35/865 W603L603 PSU OC UVG	-	Not applicable

Order Code	Full Product Name	Dimmable	Maximum dim level
911401581645	RC430V LED35/850 W603L603 PSU OC UVG	-	Not applicable
911401581745	RC430V LED35/840 W603L603 PSU OC UVG	-	Not applicable
911401581845	RC430V LED33/830 W603L603 PSU OC UVG	-	Not applicable
911401582145	RC430V LED35/9TW W60L60 PSD OC	DALI	1%
911401582445	RC430V LED35/9TW W60L60 PSD OC CAU	DALI	1%
911401583945	RC430V LED37/BioUPD W60L60 PSD OC	DALI	1%
911401584245	RC430V LED37/BioUPD W60L60 PSD OC CAU	DALI	1%
911401584945	RC430V LED37/840 W60L60 PSD OC U/D	DALI	1%
911401585245	RC430V LED35/940 W60L60 PSD OC U/D	DALI	1%
911401586745	RC430V LED37/840 W60L60 PSD OC U/D CAU	DALI	1%
911401587045	RC430V LED35/940 W60L60 PSD OC U/D CAU	DALI	1%
911401593745	RC430V LED38/865 W603L603 PSU OC	-	Not applicable
911401593845	RC430V LED38/850 W603L603 PSU OC	-	Not applicable
911401593945	RC430V LED38/840 W603L603 PSU OC	-	Not applicable
911401594045	RC430V LED36/830 W603L603 PSU OC	-	Not applicable
911401594545	RC430V LED38/865 W603L603 PSD OC	DALI	1%
911401594645	RC430V LED38/850 W603L603 PSD OC	DALI	1%
911401594745	RC430V LED38/840 W603L603 PSD OC	DALI	1%
911401594845	RC430V LED36/830 W603L603 PSD OC	DALI	1%
911401522745	RC430V LED40/840 W30L120 PSU OC	Fixed	Not applicable
911401523045	RC430V LED40/840 W30L120 PSD OC	DALI	1%
911401523345	RC430X LED40/840 W30L120 WIA OC	Wireless Dim	1%
911401523645	RC430V LED40/840 W30L120 PSU OC CAU	Fixed	Not applicable
911401523945	RC430V LED40/840 W30L120 PSD OC CAU	DALI	1%
911401524245	RC430X LED40/840 W30L120 WIA OC CAU	Wireless Dim	1%
911401524545	RC430V LED38/940 W30L120 PSU OC	Fixed	Not applicable
911401524845	RC430V LED38/940 W30L120 PSD OC	DALI	1%
911401525145	RC430X LED38/940 W30L120 WIA OC	Wireless Dim	1%
911401525445	RC430V LED38/940 W30L120 PSU OC CAU	Fixed	Not applicable
911401525745	RC430V LED38/940 W30L120 PSD OC CAU	DALI	1%
911401526045	RC430X LED38/940 W30L120 WIA OC CAU	Wireless Dim	1%

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
911401578645	RC430X LED38/840 W60L60 SC2 OC	3
911401578945	RC430X LED36/940 W60L60 SC2 OC	3
911401579245	RC430X LED38/840 W60L60 SC2 OC CAU	3
911401579545	RC430X LED36/940 W60L60 SC2 OC CAU	3
911401579845	RC430X LED38/840 W60L60 SC15 OC	3
911401580145	RC430X LED36/940 W60L60 SC15 OC	3
911401580445	RC430X LED38/840 W60L60 SC15 OC CAU	3
911401580745	RC430X LED36/940 W60L60 SC15 OC CAU	3
911401582745	RC430X LED35/9TW W60L60 SC2 OC	3
911401583045	RC430X LED35/9TW W60L60 SC2 OC CAU	3
911401583345	RC430X LED35/9TW W60L60 SC15 OC	3
911401583645	RC430X LED35/9TW W60L60 SC15 OC CAU	3
911401584345	RC430X LED37/BioUPD W60L60 SC2 OC	3
911401584445	RC430X LED37/BioUPD W60L60 SC2 OC CAU	3
911401584545	RC430X LED37/BioUPD W60L60 SC15 OC	3
911401584645	RC430X LED37/BioUPD W60L60 SC15 OC CAU	3
911401585545	RC430X LED37/840 W60L60 SC2 OC U/D	3
911401585845	RC430X LED35/940 W60L60 SC2 OC U/D	3
911401586145	RC430X LED37/840 W60L60 SC15 OC U/D	3
911401586445	RC430X LED35/940 W60L60 SC15 OC U/D	3
911401587345	RC430X LED37/840 W60L60 SC2 OC U/D CAU	3
911401587645	RC430X LED35/940 W60L60 SC2 OC U/D CAU	3
911401587945	RC430X LED37/840 W60L60 SC15 OC U/D CAU	3
911401588245	RC430X LED35/940 W60L60 SC15 OC U/D CAU	3
911401578445	RC430X LED55/840 W60L120 SC2 OC	3
911401578745	RC430X LED52/940 W60L120 SC2 OC	3
911401579045	RC430X LED55/840 W60L120 SC2 OC CAU	3
911401579345	RC430X LED52/940 W60L120 SC2 OC CAU	3
911401579645	RC430X LED55/840 W60L120 SC15 OC	3
911401579945	RC430X LED52/940 W60L120 SC15 OC	3
911401580245	RC430X LED55/840 W60L120 SC15 OC CAU	3
911401580545	RC430X LED52/940 W60L120 SC15 OC CAU	3
911401580845	RC430V LED54/840 W60L120 PSU OC SG	3
911401581945	RC430V LED51/9TW W60L120 PSD OC	3
911401582245	RC430V LED51/9TW W60L120 PSD OC CAU	3
911401582545	RC430X LED51/9TW W60L120 SC2 OC	3
911401582845	RC430X LED51/9TW W60L120 SC2 OC CAU	3
911401583145	RC430X LED51/9TW W60L120 SC15 OC	3
911401583445	RC430X LED51/9TW W60L120 SC15 OC CAU	3
911401583745	RC430V LED52/BioUPD W60L120 PSD OC	3
911401584045	RC430V LED52/BioUPD W60L120 PSD OC CAU	3
911401584745	RC430V LED54/840 W60L120 PSD OC U/D	3
911401585045	RC430V LED51/940 W60L120 PSD OC U/D	3
911401585345	RC430X LED54/840 W60L120 SC2 OC U/D	3
911401585645	RC430X LED51/940 W60L120 SC2 OC U/D	3
911401585945	RC430X LED54/840 W60L120 SC15 OC U/D	3

Order Code	Full Product Name	Initial chromaticity
911401586245	RC430X LED51/940 W60L120 SC15 OC U/D	3
911401586545	RC430V LED54/840 W60L120 PSD OC U/D CAU	3
911401586845	RC430V LED51/940 W60L120 PSD OC U/D CAU	3
911401587145	RC430X LED54/840 W60L120 SC2 OC U/D CAU	3
911401587445	RC430X LED51/940 W60L120 SC2 OC U/D CAU	3
911401587745	RC430X LED54/840 W60L120 SC15 OC U/D CAU	3
911401588045	RC430X LED51/940 W60L120 SC15 OC U/D CAU	3
911401578545	RC430X LED40/840 W30L120 SC2 OC	3
911401578845	RC430X LED38/940 W30L120 SC2 OC	3
911401579145	RC430X LED40/840 W30L120 SC2 OC CAU	3
911401579445	RC430X LED38/940 W30L120 SC2 OC CAU	3
911401579745	RC430X LED40/840 W30L120 SC15 OC	3
911401580045	RC430X LED38/940 W30L120 SC15 OC	3
911401580345	RC430X LED40/840 W30L120 SC15 OC CAU	3
911401580645	RC430X LED38/940 W30L120 SC15 OC CAU	3
911401582645	RC430X LED36/9TW W30L120 SC2 OC	3
911401582945	RC430X LED36/9TW W30L120 SC2 OC CAU	3
911401583245	RC430X LED36/9TW W30L120 SC15 OC	3
911401583545	RC430X LED36/9TW W30L120 SC15 OC CAU	3
911401585445	RC430X LED38/840 W30L120 SC2 OC U/D	3
911401585745	RC430X LED36/940 W30L120 SC2 OC U/D	3
911401586045	RC430X LED38/840 W30L120 SC15 OC U/D	3
911401586345	RC430X LED36/940 W30L120 SC15 OC U/D	3
911401587245	RC430X LED38/840 W30L120 SC2 OC U/D CAU	3
911401587545	RC430X LED36/940 W30L120 SC2 OC U/D CAU	3
911401587845	RC430X LED38/840 W30L120 SC15 OC U/D CAU	3
911401588145	RC430X LED36/940 W30L120 SC15 OC U/D CAU	3
911401522845	RC430V LED38/840 W60L60 PSU OC	(0.382,0.3792)SDCM<3
911401523145	RC430V LED38/840 W60L60 PSD OC	(0.382,0.3792)SDCM<3
911401523445	RC430X LED38/840 W60L60 WIA OC	(0.382,0.3792)SDCM<3
911401523745	RC430V LED38/840 W60L60 PSU OC CAU	(0.382,0.3792)SDCM<3
911401524045	RC430V LED38/840 W60L60 PSD OC CAU	(0.382,0.3792)SDCM<3
911401524345	RC430X LED38/840 W60L60 WIA OC CAU	(0.382,0.3792)SDCM<3
911401524645	RC430V LED36/940 W60L60 PSU OC	(0.3825,0.3795)SDCM<3
911401524945	RC430V LED36/940 W60L60 PSD OC	(0.3825,0.3795)SDCM<3
911401525245	RC430X LED36/940 W60L60 WIA OC	(0.3825,0.3795)SDCM<3
911401525545	RC430V LED36/940 W60L60 PSU OC CAU	(0.3825,0.3795)SDCM<3
911401525845	RC430V LED36/940 W60L60 PSD OC CAU	(0.3825,0.3795)SDCM<3
911401526145	RC430X LED36/940 W60L60 WIA OC CAU	(0.3825,0.3795)SDCM<3
911401522645	RC430V LED55/840 W60L120 PSU OC	(0.3847,0.3813)SDCM<3
911401522945	RC430V LED55/840 W60L120 PSD OC	(0.3847,0.3813)SDCM<3
911401523245	RC430X LED49/840 W60L120 WIA OC	(0.3847,0.3813)SDCM<3

Order Code	Full Product Name	Initial chromaticity
911401523545	RC430V LED55/840 W60L120 PSU OC CAU	(0.3847,0.3813)SDCM<3
911401523845	RC430V LED55/840 W60L120 PSD OC CAU	(0.3847,0.3813)SDCM<3
911401524145	RC430X LED49/840 W60L120 WIA OC CAU	(0.3847,0.3813)SDCM<3
911401524445	RC430V LED52/940 W60L120 PSU OC	(0.3825,0.3795)SDCM<3
911401524745	RC430V LED52/940 W60L120 PSD OC	(0.3825,0.3795)SDCM<3
911401525045	RC430X LED46/940 W60L120 WIA OC	(0.3825,0.3795)SDCM<3
911401525345	RC430V LED52/940 W60L120 PSU OC CAU	(0.3825,0.3795)SDCM<3
911401525645	RC430V LED52/940 W60L120 PSD OC CAU	(0.3825,0.3795)SDCM<3
911401525945	RC430X LED46/940 W60L120 WIA OC CAU	(0.3825,0.3795)SDCM<3
911401580945	RC430V LED40/840 W30L120 PSU OC SG	3
911401581145	RC430V LED37/865 W303L1210 PSU OC UVG	3
911401581245	RC430V LED37/850 W303L1210 PSU OC UVG	3
911401581345	RC430V LED37/840 W303L1210 PSU OC UVG	3
911401581445	RC430V LED35/830 W303L1210 PSU OC UVG	3
911401582045	RC430V LED36/9TW W30L120 PSD OC	3
911401582345	RC430V LED36/9TW W30L120 PSD OC CAU	3
911401583845	RC430V LED39/BioUPD W30L120 PSD OC	3
911401584145	RC430V LED39/BioUPD W30L120 PSD OC CAU	3
911401584845	RC430V LED38/840 W30L120 PSD OC U/D	3
911401585145	RC430V LED36/940 W30L120 PSD OC U/D	3
911401586645	RC430V LED38/840 W30L120 PSD OC U/D CAU	3
911401586945	RC430V LED36/940 W30L120 PSD OC U/D CAU	3
911401593345	RC430V LED40/865 W303L1210 PSU OC	3
911401593445	RC430V LED40/850 W303L1210 PSU OC	3
911401593545	RC430V LED40/840 W303L1210 PSU OC	3
911401593645	RC430V LED37/830 W303L1210 PSU OC	3
911401594145	RC430V LED40/865 W303L1210 PSD OC	3
911401594245	RC430V LED40/850 W303L1210 PSD OC	3
911401594345	RC430V LED40/840 W303L1210 PSD OC	3
911401594445	RC430V LED37/830 W303L1210 PSD OC	3
911401581045	RC430V LED40/840 W60L60 PSU OC SG	3

Order Code	Full Product Name	Initial chromaticity
911401581545	RC430V LED35/865 W603L603 PSU OC UVG	3
911401581645	RC430V LED35/850 W603L603 PSU OC UVG	3
911401581745	RC430V LED35/840 W603L603 PSU OC UVG	3
911401581845	RC430V LED33/830 W603L603 PSU OC UVG	3
911401582145	RC430V LED35/9TW W60L60 PSD OC	3
911401582445	RC430V LED35/9TW W60L60 PSD OC CAU	3
911401583945	RC430V LED37/BioUPD W60L60 PSD OC	3
911401584245	RC430V LED37/BioUPD W60L60 PSD OC CAU	3
911401584945	RC430V LED37/840 W60L60 PSD OC U/D	3
911401585245	RC430V LED35/940 W60L60 PSD OC U/D	3
911401586745	RC430V LED37/840 W60L60 PSD OC U/D CAU	3
911401587045	RC430V LED35/940 W60L60 PSD OC U/D CAU	3
911401593745	RC430V LED38/865 W603L603 PSU OC	3
911401593845	RC430V LED38/850 W603L603 PSU OC	3
911401593945	RC430V LED38/840 W603L603 PSU OC	3
911401594045	RC430V LED36/830 W603L603 PSU OC	3
911401594545	RC430V LED38/865 W603L603 PSD OC	3
911401594645	RC430V LED38/850 W603L603 PSD OC	3
911401594745	RC430V LED38/840 W603L603 PSD OC	3
911401594845	RC430V LED36/830 W603L603 PSD OC	3
911401522745	RC430V LED40/840 W30L120 PSU OC	(0.381,0.3774)SDCM<3
911401523045	RC430V LED40/840 W30L120 PSD OC	(0.381,0.3774)SDCM<3
911401523345	RC430X LED40/840 W30L120 WIA OC	(0.381,0.3774)SDCM<3
911401523645	RC430V LED40/840 W30L120 PSU OC CAU	(0.381,0.3774)SDCM<3
911401523945	RC430V LED40/840 W30L120 PSD OC CAU	(0.381,0.3774)SDCM<3
911401524245	RC430X LED40/840 W30L120 WIA OC CAU	(0.381,0.3774)SDCM<3
911401524545	RC430V LED38/940 W30L120 PSU OC	(0.3841,0.3804)SDCM<3
911401524845	RC430V LED38/940 W30L120 PSD OC	(0.3841,0.3804)SDCM<3
911401525145	RC430X LED38/940 W30L120 WIA OC	(0.3841,0.3804)SDCM<3
911401525445	RC430V LED38/940 W30L120 PSU OC CAU	(0.3841,0.3804)SDCM<3
911401525745	RC430V LED38/940 W30L120 PSD OC CAU	(0.3841,0.3804)SDCM<3
911401526045	RC430X LED38/940 W30L120 WIA OC CAU	(0.3841,0.3804)SDCM<3

