



A troffer beyond visual comfort

Aura

As an innovative troffer, CoreView Pro RC430V uses indirect and direct light output to reach UGR19 without using heavy and big glare control plates. The central module can be easily replaceable for future maintenance. The light from the central light module can be controlled separately to fit multiple applications. BioUp technology provides better well being for the people in indoor environment.

Benefits

- Slim and nice look and feel
- Easy maintenance on site
- Fit multiple applications for office, healthcare
- Support better well being for people in indoor

Features

- Unique light module design with indirect and direct light to reach UGR19
- Replaceable light module
- Adjustable up and downward light output ratio
- BioUp technology enabled

Application

- Office
- Meeting room
- Healthcare

Versions









Aura RC430

Aura RC430



CoreView Pro

Aura RC430

Dimensional drawing



Dimensional drawing



General Information	
Driver included	Yes
Gear	-
Number of gear units	1 unit
Light Technical	
Beam angle of light source	115 degree(s)
Optic type	Beam angle 90°
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Suitable for random switching	Yes
Mechanical and Housing	
Optical cover type	Prismatic bowl/ cover linear horizontal
Housing Color	White RAL 9003
Mech. impact protection code	IK03
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	-20 to +40 °C
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Initial Performance (IEC Compliant)	
Luminous flux tolerance	-10% / +10%

Light Technical (1/2)

Order Code	Full Product Name	Correlated Color	Color	Luminous	Luminous Flux
		Temperature	rendering	Efficacy (rated)	
		(Nom)	index (CRI)	(Nom)	
911401583345	RC430X LED35/9TW W60L60 SC15 OC	Tunable white 2700-6500 K	90	118 lm/W	3,500 lm
911401584545	RC430X LED37/BioUPD W60L60 SC15 OC	4000 K	80	106 lm/W	3,700 lm
911401583745	RC430V LED52/BioUPD W60L120 PSD OC	4000 K	80	108 lm/W	5,200 lm
911401522845	RC430V LED38/840 W60L60 PSU OC	4000 K	80	123 lm/W	3,800 lm
911401523145	RC430V LED38/840 W60L60 PSD OC	4000 K	80	117 lm/W	3,800 lm
911401523445	RC430X LED38/840 W60L60 WIA OC	4000 K	80	122 lm/W	3,800 lm
911401523745	RC430V LED38/840 W60L60 PSU OC CAU	4000 K	80	123 lm/W	3,800 lm
911401524045	RC430V LED38/840 W60L60 PSD OC CAU	4000 K	80	117 lm/W	3,800 lm
911401524345	RC430X LED38/840 W60L60 WIA OC CAU	4000 K	80	122 lm/W	3,800 lm
911401524645	RC430V LED36/940 W60L60 PSU OC	4000 K	90	117 lm/W	3,600 lm
911401524945	RC430V LED36/940 W60L60 PSD OC	4000 K	90	112 lm/W	3,600 lm
911401525245	RC430X LED36/940 W60L60 WIA OC	4000 K	90	115 lm/W	3,600 lm
911401522645	RC430V LED55/840 W60L120 PSU OC	4000 K	80	128 lm/W	5,500 lm
911401522945	RC430V LED55/840 W60L120 PSD OC	4000 K	80	121 lm/W	5,500 lm
911401523245	RC430X LED49/840 W60L120 WIA OC	4000 K	80	129 lm/W	4,900 lm
911401523545	RC430V LED55/840 W60L120 PSU OC CAU	4000 K	80	128 lm/W	5,500 lm
911401523845	RC430V LED55/840 W60L120 PSD OC CAU	4000 K	80	121 lm/W	5,500 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401524145	RC430X LED49/840 W60L120 WIA OC CAU	4000 K	80	129 lm/W	4,900 lm
911401524445	RC430V LED52/940 W60L120 PSU OC	4000 K	90	122 lm/W	5,200 lm
911401524745	RC430V LED52/940 W60L120 PSD OC	4000 K	90	115 lm/W	5,200 lm
911401525045	RC430X LED46/940 W60L120 WIA OC	4000 K	90	122 lm/W	4,600 lm
911401593645	RC430V LED37/830 W303L1210 PSU OC	3000 K	80	124 lm/W	3,700 lm
911401594445	RC430V LED37/830 W303L1210 PSD OC	3000 K	80	117 lm/W	3,700 lm
911401582145	RC430V LED35/9TW W60L60 PSD OC	Tunable white 2700–6500 K	90	118 lm/W	3,500 lm
911401583945	RC430V LED37/BioUPD W60L60 PSD OC	4000 K	80	106 lm/W	3,700 lm
911401594045	RC430V LED36/830 W603L603 PSU OC	3000 K	80	114 lm/W	3,600 lm
911401594845	RC430V LED36/830 W603L603 PSD OC	3000 K	80	109 lm/W	3,600 lm
911401522745	RC430V LED40/840 W30L120 PSU OC	4000 K	80	134 lm/W	4,000 lm
911401523045	RC430V LED40/840 W30L120 PSD OC	4000 K	80	126 lm/W	4,000 lm
911401523345	RC430X LED40/840 W30L120 WIA OC	4000 K	80	132 lm/W	4,000 lm
911401523645	RC430V LED40/840 W30L120 PSU OC CAU	4000 K	80	134 lm/W	4,000 lm
911401523945	RC430V LED40/840 W30L120 PSD OC CAU	4000 K	80	126 lm/W	4,000 lm
911401524245	RC430X LED40/840 W30L120 WIA OC CAU	4000 K	80	132 lm/W	4,000 lm
911401524545	RC430V LED38/940 W30L120 PSU OC	4000 K	90	127 lm/W	3,800 lm
911401524845	RC430V LED38/940 W30L120 PSD OC	4000 K	90	120 lm/W	3,800 lm
911401525145	RC430X LED38/940 W30L120 WIA OC	4000 K	90	126 lm/W	3,800 lm

Light Technical (2/2)

Order Code	Full Product Name	Number of light sources	Order Code	Full Product Name	Number of light sources
911401583345	RC430X LED35/9TW W60L60 SC15 OC	1	911401524345	RC430X LED38/840 W60L60 WIA OC CAU	144
911401584545	RC430X LED37/BioUPD W60L60 SC15 OC	1	911401524645	RC430V LED36/940 W60L60 PSU OC	144
911401583745	RC430V LED52/BioUPD W60L120 PSD OC	1	911401524945	RC430V LED36/940 W60L60 PSD OC	144
911401522845	RC430V LED38/840 W60L60 PSU OC	144	911401525245	RC430X LED36/940 W60L60 WIA OC	144
911401523145	RC430V LED38/840 W60L60 PSD OC	144	911401522645	RC430V LED55/840 W60L120 PSU OC	228
911401523445	RC430X LED38/840 W60L60 WIA OC	144	911401522945	RC430V LED55/840 W60L120 PSD OC	228
911401523745	RC430V LED38/840 W60L60 PSU OC CAU	144	911401523245	RC430X LED49/840 W60L120 WIA OC	228
911401524045	RC430V LED38/840 W60L60 PSD OC CAU	144	911401523545	RC430V LED55/840 W60L120 PSU OC CAU	228

Order Code	Full Product Name	Number of light sources
911401523845	RC430V LED55/840 W60L120 PSD OC CAU	228
911401524145	RC430X LED49/840 W60L120 WIA OC CAU	228
911401524445	RC430V LED52/940 W60L120 PSU OC	228
911401524745	RC430V LED52/940 W60L120 PSD OC	228
911401525045	RC430X LED46/940 W60L120 WIA OC	228
911401593645	RC430V LED37/830 W303L1210 PSU OC	1
911401594445	RC430V LED37/830 W303L1210 PSD OC	1
911401582145	RC430V LED35/9TW W60L60 PSD OC	1
911401583945	RC430V LED37/BioUPD W60L60 PSD OC	1
911401594045	RC430V LED36/830 W603L603 PSU OC	1

Order Code	Full Product Name	Number of light sources
911401594845	RC430V LED36/830 W603L603 PSD OC	1
911401522745	RC430V LED40/840 W30L120 PSU OC	378
911401523045	RC430V LED40/840 W30L120 PSD OC	378
911401523345	RC430X LED40/840 W30L120 WIA OC	378
911401523645	RC430V LED40/840 W30L120 PSU OC CAU	378
911401523945	RC430V LED40/840 W30L120 PSD OC CAU	378
911401524245	RC430X LED40/840 W30L120 WIA OC CAU	378
911401524545	RC430V LED38/940 W30L120 PSU OC	378
911401524845	RC430V LED38/940 W30L120 PSD OC	378
911401525145	RC430X LED38/940 W30L120 WIA OC	378

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401583345	RC430X LED35/9TW W60L60 SC15 OC	29 W
911401584545	RC430X LED37/BioUPD W60L60 SC15 OC	35 W
911401583745	RC430V LED52/BioUPD W60L120 PSD OC	47 W
911401522845	RC430V LED38/840 W60L60 PSU OC	31 W
911401523145	RC430V LED38/840 W60L60 PSD OC	33 W
911401523445	RC430X LED38/840 W60L60 WIA OC	31 W
911401523745	RC430V LED38/840 W60L60 PSU OC CAU	31 W
911401524045	RC430V LED38/840 W60L60 PSD OC CAU	33 W
911401524345	RC430X LED38/840 W60L60 WIA OC CAU	31 W
911401524645	RC430V LED36/940 W60L60 PSU OC	31 W
911401524945	RC430V LED36/940 W60L60 PSD OC	33 W
911401525245	RC430X LED36/940 W60L60 WIA OC	31 W
911401522645	RC430V LED55/840 W60L120 PSU OC	43 W
911401522945	RC430V LED55/840 W60L120 PSD OC	46 W
911401523245	RC430X LED49/840 W60L120 WIA OC	38 W
911401523545	RC430V LED55/840 W60L120 PSU OC CAU	43 W
911401523845	RC430V LED55/840 W60L120 PSD OC CAU	46 W
911401524145	RC430X LED49/840 W60L120 WIA OC CAU	38 W

Order Code	Full Product Name	Power Consumption
911401524445	RC430V LED52/940 W60L120 PSU OC	43 W
911401524745	RC430V LED52/940 W60L120 PSD OC	46 W
911401525045	RC430X LED46/940 W60L120 WIA OC	38 W
911401593645	RC430V LED37/830 W303L1210 PSU OC	30 W
911401594445	RC430V LED37/830 W303L1210 PSD OC	32 W
911401582145	RC430V LED35/9TW W60L60 PSD OC	29 W
911401583945	RC430V LED37/BioUPD W60L60 PSD OC	35 W
911401594045	RC430V LED36/830 W603L603 PSU OC	31 W
911401594845	RC430V LED36/830 W603L603 PSD OC	33 W
911401522745	RC430V LED40/840 W30L120 PSU OC	30 W
911401523045	RC430V LED40/840 W30L120 PSD OC	32 W
911401523345	RC430X LED40/840 W30L120 WIA OC	30 W
911401523645	RC430V LED40/840 W30L120 PSU OC CAU	30 W
911401523945	RC430V LED40/840 W30L120 PSD OC CAU	32 W
911401524245	RC430X LED40/840 W30L120 WIA OC CAU	30 W
911401524545	RC430V LED38/940 W30L120 PSU OC	30 W
911401524845	RC430V LED38/940 W30L120 PSD OC	32 W
911401525145	RC430X LED38/940 W30L120 WIA OC	30 W

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
911401583345	RC430X LED35/9TW W60L60 SC15 OC	Wireless Dim	1%
911401584545	RC430X LED37/BioUPD W60L60 SC15 OC	Wireless Dim	1%
911401583745	RC430V LED52/BioUPD W60L120 PSD OC	DALI	1%
911401522845	RC430V LED38/840 W60L60 PSU OC	Fixed	Not applicable
911401523145	RC430V LED38/840 W60L60 PSD OC	DALI	1%
911401523445	RC430X LED38/840 W60L60 WIA OC	Wireless Dim	1%
911401523745	RC430V LED38/840 W60L60 PSU OC CAU	Fixed	Not applicable
911401524045	RC430V LED38/840 W60L60 PSD OC CAU	DALI	1%
911401524345	RC430X LED38/840 W60L60 WIA OC CAU	Wireless Dim	1%

Order Code	Full Product Name	Dimmable	Maximum dim level
911401524645	RC430V LED36/940 W60L60 PSU OC	Fixed	Not applicable
911401524945	RC430V LED36/940 W60L60 PSD OC	DALI	1%
911401525245	RC430X LED36/940 W60L60 WIA OC	Wireless Dim	1%
911401522645	RC430V LED55/840 W60L120 PSU OC	Fixed	Not applicable
911401522945	RC430V LED55/840 W60L120 PSD OC	DALI	3%
911401523245	RC430X LED49/840 W60L120 WIA OC	Wireless Dim	1%
911401523545	RC430V LED55/840 W60L120 PSU OC CAU	Fixed	Not applicable
911401523845	RC430V LED55/840 W60L120 PSD OC CAU	DALI	3%
911401524145	RC430X LED49/840 W60L120 WIA OC CAU	Wireless Dim	1%
911401524445	RC430V LED52/940 W60L120 PSU OC	Fixed	Not applicable
911401524745	RC430V LED52/940 W60L120 PSD OC	DALI	3%

Order Code	Full Product Name	Dimmable	Maximum dim level
911401525045	RC430X LED46/940 W60L120 WIA OC	Wireless Dim	1%
911401593645	RC430V LED37/830 W303L1210 PSU OC	-	Not applicable
911401594445	RC430V LED37/830 W303L1210 PSD OC	DALI	1%
911401582145	RC430V LED35/9TW W60L60 PSD OC	DALI	1%
911401583945	RC430V LED37/BioUPD W60L60 PSD OC	DALI	1%
911401594045	RC430V LED36/830 W603L603 PSU OC	-	Not applicable
911401594845	RC430V LED36/830 W603L603 PSD OC	DALI	1%

Order Code	Full Product Name	Dimmable	Maximum dim level
911401522745	RC430V LED40/840 W30L120 PSU OC	Fixed	Not applicable
911401523045	RC430V LED40/840 W30L120 PSD OC	DALI	1%
911401523345	RC430X LED40/840 W30L120 WIA OC	Wireless Dim	1%
911401523645	RC430V LED40/840 W30L120 PSU OC CAU	Fixed	Not applicable
911401523945	RC430V LED40/840 W30L120 PSD OC CAU	DALI	1%
911401524245	RC430X LED40/840 W30L120 WIA OC CAU	Wireless Dim	1%
911401524545	RC430V LED38/940 W30L120 PSU OC	Fixed	Not applicable
911401524845	RC430V LED38/940 W30L120 PSD OC	DALI	1%
911401525145	RC430X LED38/940 W30L120 WIA OC	Wireless Dim	1%

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
911401583345	RC430X LED35/9TW W60L60 SC15 OC	3
911401584545	RC430X LED37/BioUPD W60L60 SC15 OC	3
911401583745	RC430V LED52/BioUPD W60L120 PSD OC	3
911401522845	RC430V LED38/840 W60L60 PSU OC	(0.382,0.3792)SDCM<3
911401523145	RC430V LED38/840 W60L60 PSD OC	(0.382,0.3792)SDCM<3
911401523445	RC430X LED38/840 W60L60 WIA OC	(0.382,0.3792)SDCM<3
911401523745	RC430V LED38/840 W60L60 PSU OC CAU	(0.382,0.3792)SDCM<3
911401524045	RC430V LED38/840 W60L60 PSD OC CAU	(0.382,0.3792)SDCM<3
911401524345	RC430X LED38/840 W60L60 WIA OC CAU	(0.382,0.3792)SDCM<3
911401524645	RC430V LED36/940 W60L60 PSU OC	(0.3825,0.3795)SDCM<3
911401524945	RC430V LED36/940 W60L60 PSD OC	(0.3825,0.3795)SDCM<3
911401525245	RC430X LED36/940 W60L60 WIA OC	(0.3825,0.3795)SDCM<3
911401522645	RC430V LED55/840 W60L120 PSU OC	(0.3847,0.3813)SDCM<3
911401522945	RC430V LED55/840 W60L120 PSD OC	(0.3847,0.3813)SDCM<3
911401523245	RC430X LED49/840 W60L120 WIA OC	(0.3847,0.3813)SDCM<3
911401523545	RC430V LED55/840 W60L120 PSU OC CAU	(0.3847,0.3813)SDCM<3
911401523845	RC430V LED55/840 W60L120 PSD OC CAU	(0.3847,0.3813)SDCM<3
911401524145	RC430X LED49/840 W60L120 WIA OC CAU	(0.3847,0.3813)SDCM<3

Order Code	Full Product Name	Initial chromaticity
911401524445	RC430V LED52/940 W60L120 PSU OC	(0.3825,0.3795)SDCM<3
911401524745	RC430V LED52/940 W60L120 PSD OC	(0.3825,0.3795)SDCM<3
911401525045	RC430X LED46/940 W60L120 WIA OC	(0.3825,0.3795)SDCM<3
911401593645	RC430V LED37/830 W303L1210 PSU OC	3
911401594445	RC430V LED37/830 W303L1210 PSD OC	3
911401582145	RC430V LED35/9TW W60L60 PSD OC	3
911401583945	RC430V LED37/BioUPD W60L60 PSD OC	3
911401594045	RC430V LED36/830 W603L603 PSU OC	3
911401594845	RC430V LED36/830 W603L603 PSD OC	3
911401522745	RC430V LED40/840 W30L120 PSU OC	(0.381,0.3774)SDCM<3
911401523045	RC430V LED40/840 W30L120 PSD OC	(0.381,0.3774)SDCM<3
911401523345	RC430X LED40/840 W30L120 WIA OC	(0.381,0.3774)SDCM<3
911401523645	RC430V LED40/840 W30L120 PSU OC CAU	(0.381,0.3774)SDCM<3
911401523945	RC430V LED40/840 W30L120 PSD OC CAU	(0.381,0.3774)SDCM<3
911401524245	RC430X LED40/840 W30L120 WIA OC CAU	(0.381,0.3774)SDCM<3
911401524545	RC430V LED38/940 W30L120 PSU OC	(0.3841,0.3804)SDCM<3
911401524845	RC430V LED38/940 W30L120 PSD OC	(0.3841,0.3804)SDCM<3
911401525145	RC430X LED38/940 W30L120 WIA OC	(0.3841,0.3804)SDCM<3

