

TrueBlend Recessed

RC450BI



TrueBlend: Proposition build around flexibility, choice, and performance.

When specifying lighting for premium office applications, technical specifiers need to deal with a wide variety of requirements and constraints linked to ceiling types and customer/ architect preferences. Philips TrueBlend is a flexible luminaire portfolio offering choice in look & feel for the architect, and mechanical fit to many different ceiling types, and a palette of optics to choose from. Philips TrueBlend is built around flexibility and choice; our new recessed office range is a perfect fit for your non-standard ceiling or renovation project where luminaires need to fit the hole of existing luminaires. A wide variety of optics, best-in-class efficacy, combined with our wellbeing led spectra, and Interact connectivity, offers choice in performance and look & feel. TrueBlend helps save energy & provide the right level of light. Not only is it compliant with the WELL Building Standard for Light, but also is rated UGR<19, which is compliant with all office norms (OC). This luminaire family is available in different lengths, light outputs, optics, housing colors, various bracket height, connectors.

This offers the ultimate design flexibility and unlimited possibilities. TrueBlend luminaires offer state-of-the-art efficacy and excellent light quality (CRI>90) with upgradability features and repairability that promises a long lifetime. They are also designed for recyclability, making them a truly circular, green choice. So, TrueBlend is an all-in-one solution with superior lighting specifications combined with sustainable approach to high-performance office lighting.

Benefits

- Designed for enhanced well-being of people with high quality of light.
- Best-in-class efficacy with superior lighting specifications & long lifetime
- Sustainable, future-ready, scalable smart office capabilities with best-in-class Interact proposition.
- Significantly reduces operational costs for an attractive payback time.

Applications

- Offices
- Education
- Retail

Features

- Best-in-class efficacy up to 170lm/W supports green building design and energy saving subsidy criteria.
- Office-compliant lighting with wide optics choices like DLO, MLO & mini cups.

Versions

- Highly uniform lighting with excellent glare control (UGR<19, L65<3000cd/m2)
- 3000K, 4000K, Tunable White & tunable white bio-up versions, all CRI>90
- Long lifetime upto L90@50,000 hours
- Wide connector choice for simpler & faster installation
- Connected system ready with Interact Pro scalable platform using integrated sensors and/or wireless drivers for data collection, occupancy, daylight regulation and wayfinding.
- Prepared for circularity (no glue, replaceable electronics, upgradable system, efficient and long lifetime) plus supporting Environmental Product Declaration (EPD) guide.
- Recessed mounting options, including all accessories.
- The product is IP20 and, as such, is not protected against water ingress. Therefore, we strongly recommend that the environment in which the luminaire is to be installed is suitably checked.
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure and the product warranty will become void.



TrueBlend Recessed RC455B
MXO U4 4FT



TrueBlend MLO/MXO SPP



TrueBlend Recessed RC455B
MLO U4



TrueBlend Recessed RC453B
DLO U4 EL



TrueBlend Recessed RC455B
MXO



TrueBlend Recessed RC455B
minicups WH U4 4FT



TrueBlend Recessed RC453B
MXO



TrueBlend Recessed RC455B
MXO 4FT



TrueBlend Recessed RC455B
DLO U4



TrueBlend Recessed RC455B
DLO 4Ft



TrueBlend Recessed RC455B
MINI CUPS WH U4



TrueBlend Recessed RC455X
DLO



TrueBlend Recessed RC455X
DLO U4



TrueBlend Recessed RC455B
DLO U4



TrueBlend Recessed RC453X
DLO U4



TrueBlend Recessed RC455B
MCB U4



TrueBlend Recessed RC455B
MLO U4 4FT



TrueBlend Recessed RC455X
DLO



TrueBlend Recessed RC455B
MINI CUPS BK U4 4FT



TrueBlend Recessed RC455B
DLO



TrueBlend Recessed RC455X
DLO



TrueBlend Recessed RC453B
DLO U4



TrueBlend Recessed RC453X
MXO



TrueBlend Recessed RC453B
MXO



TrueBlend Recessed RC455B
MLO U4 4FT



TrueBlend Recessed RC453B
DLO



TrueBlend Recessed RC455B
MINI CUPS WH C



TrueBlend Recessed RC455B
MINI CUPS WH U4




TrueBlend Recessed RC455X
DLO U4




TrueBlend Recessed RC453B
DLO U5


Dimensional drawing




RC453B 28S/840 DLO L1200 W300 B30




RC453B 28S/840 DLO 9010 ELP3L1200W300B30




RC455B 36S/940 MLO L1200 W150 B40




RC455B 36S/940 MXO L1200 W100 B40




RC453B42S/940DLO9010U4ELW3W4L1200W300B30




RC455X 40S/940 DLO W3W2 L1722 W150 B30




RC453B 28S/UE840 MXO9010ELP3L1200W150B30




RC453B 40S/TW9 DLO U4 L1200 W300 B30




RC453B 28S/UE840MXO9010ELP3 L1200W300B30




RC455B 36S/940 MLO L1200 W125 B40




RC455X 40S/940 DLO W3W2 L1497W150B30 SC




RC455B 36S/UE840 DLO W3W2 L1722 W185 B30




RC455X 40S/940 DLO W3W2 L1497 W185 B30




RC455X 36S/UE840 DLO U4 W3 L1722W200B40




RC455B 40S/940 MXO ELP3 W6L1722W150B40WT




RC455B 40S/940 MXO L1200 W100 B40




RC455X 36S/940 DLOU5 9016W3 L1722W185B40




RC453X 28S/UE840MXO9010 U4W3L1200W150B30




RC455B 40S/940 DLO U4 W3 L1722 W100 B30




RC453B 36S/940 DLO9010U4ELW3L1200W300B30




RC455X 36S/930 DLO U4 W3 L1495 W100 B30




RC453B 28S/840 DLO L1195 W298 B30




RC453X 28S/840 DLO L1195 W298 B30




RC455X 36S/940 DLO W5 L1700 W150 B30 WT




RC455B 40S/940 MCB-M W3W2 L1722 W150 B30




RC455X 36S/940 DLO U4 W3 L1722 W100 B30




RC455B 36S/940 MXO L1200 W150 B40




RC455B 40S/940 DLO W3W2 L1722 W150 B30




RC455B 48S/940 MXO L1495 W100 B40




RC455X 36S/940 MCB-M U4 W3 L1722 W100B30




RC455B 40S/940MCW-M U4W3 L1722 W150 B40




RC453B 28S/UE840 MXO L1200 W150 B30




RC455B 28S/TW9 MLO U4 L1200 W100 B40




RC455X 36S/940 MLO W5 L1722 W185 B30 WT




RC455B 36S/940 DLO 9010U4W3 L1722W150B30




RC455X 36S/940 DLO W5 L1722 W185 B30 WT




RC453B 42S/940 DLO9010U4 L1200W300B30 SC



RC455B 36S/940 MCB-M U4 L1200 W100 B40



RC455B 40S/940 MCW-M L1200 W100 B40



RC455X 40S/940 DLO W3W2 L1700 W100 B30

Product details



TrueBlend Recessed DLO-optics DPP



TrueBlend Recessed U5 sensor



TrueBlend Recessed MXO-optics DPP



TrueBlend Recessed Mini cups- Black optics DPP



TrueBlend Recessed T profile



TrueBlend Recessed U4 sensor



TrueBlend Recessed U4 & EL indicator DPP



TrueBlend Recessed C profile



TrueBlend Recessed Mini cups- White optics DPP



TrueBlend Recessed EL indicator

General Information

Number of gear units	1 unit
Driver included	Yes
Service tag	Yes

Light Technical

Upward light output ratio	0
Beam angle of light source	72 degree(s)

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Protection class IEC	Safety class I

Controls and Dimming

Dimmable	Yes
Maximum dim level	1%

Mechanical and Housing

Housing Color	White
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]

Emergency Operation

Power consumption during Central DC emergency mode	6 W
Rated duration of the emergency lighting (when fully charged)	3 hour(s)
Central Emergency	Yes

Approval and Application

Glow-wire test	Temperature 850 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Ambient temperature range	+10 to +35 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

General Information

Order Code	Full Product Name	Lamp family code
910505103952	RC455B 36S/940 MXO U4 L1200 W100 B40	36S
910505103958	RC455B 40S/TW9 MXO U4 L1200 W100 B40	40S
910505103960	RC455B 40S/940 MXO ELP3 W6L1722W150B40WT	40S
910505103949	RC455B 28S/TW9 MLO U4 L1720 W124 B40	40S
910505103950	RC455B 36S/940 MLO U4 W3 L1722 W100 B40	36S
910505103974	RC453B42S/940DLO9010U4ELW3W4L1200W300B30	42S
910505103976	RC453B 36S/940 DLO9010U4ELW3L1200W300B30	34S
910505103957	RC455B 48S/940 MXO L1495 W100 B40	48S
910505103959	RC455B 28S/TWBU MCW-M U4 L1200 W100 B40	40S
910505103965	RC455B 36S/940 MCW-M U4 L1200 W100 B40	36S
910505103978	RC453B 28S/UE840 MXO 9010 L1200 W300 B30	28S
910505103979	RC453B 28S/UE840MXO9010ELP3 L1200W300B30	28S
910505103951	RC455B 36S/940 MXO L1200 W100 B40	36S
910505103953	RC455B 40S/940 MXO L1200 W100 B40	40S
910505103954	RC455B 36S/940 MXO L1200 W125 B40	36S
910505103955	RC455B 36S/940 MXO L1200 W150 B40	36S
910505103956	RC455B 28S/940 MXO L1200 W150 B40	28S
910505105905	RC455B 40S/940 MXO L1200 W100 B40 SC	-
910505103937	RC455B 40S/940 DLO U4 W3 L1722 W100 B30	40S
910505103940	RC455B 36S/940 DLO L1200 W100 B30	36S
910505103934	RC455X 36S/940 MCW-M U4 W3 L1722 W100B30	36S
910505105902	RC455B 36S/940 MCW-M U4W3L1722W100B30SC	-
910505103926	RC455X 40S/940 DLO W3W2 L1700 W100 B30	40S
910505103927	RC455X 40S/940 DLO W3W2 L1497 W150 B30	40S
910505105901	RC455X 40S/940 DLO W3W2 L1497W150B30 SC	-
910505105913	RC455B 40S/UE 840 DLO L1200 W100 B30	-
910505103924	RC455X 36S/940 DLO U4 W3 L1722 W200 B40	36S
910505105911	RC455X 36S/UE840 DLO U4 W3 L1722W200B40	-
910505103936	RC455B 36S/940 DLO 9010U4W3 L1722W150B30	36S
910505103985	RC453X 28S/UE840MXO9010 U4W3L1200W150B30	28S
910505103921	RC455X 28S/TWBU MCB-M U4 W3 L1722W100B30	36S
910505103935	RC455X 36S/940 MCB-M U4 W3 L1722 W100B30	36S
910505103967	RC455B 40S/940 MCB-M W3W2 L1722 W150 B30	40S
910505103948	RC455B 28S/TW9 MLO U4 L1200 W100 B40	36S
910505103918	RC455X 36S/940 DLO W5 L1722 W185 B30 WT	36S
910505103930	RC455X 40S/940 DLO W3W2 L1497 W185 B30	40S
910505103932	RC455X 36S/940 MLO W5 L1722 W185 B30 WT	36S
910505105912	RC455B 36S/UE840 DLO W3W2 L1722 W185 B30	-
910505103962	RC455B 36S/940 MCB-M L1200 W100 B40	36S
910505103964	RC455B 40S/940 MCB-M L1200 W100 B40	40S
910505103966	RC455B 36S/940 MCB-M U4 L1200 W100 B40	36S

Order Code	Full Product Name	Lamp family code
910505103938	RC455B 40S/940 DLO W3W2 L1722 W150 B30	40S
910505103939	RC455B 36S/940 DLO W3W2 L1722 W185 B30	36S
910505103917	RC455X 40S/940 DLO W3W2 L1722 W150 B30	40S
910505103919	RC455X 40S/940 DLO W3W2 L1722 W150 B40	40S
910505103922	RC455X 40S/930 DLO W3W2 L1722 W150 B30	40S
910505103925	RC455X 36S/940 DLO W5 L1700 W150 B30 WT	36S
910505105910	RC455X 40S/UE840 DLO W3W2 L1722 W150 B40	-
910505105918	RC455X 40S/BU840 DLO W3W2 L1722 W150 B30	-
910505103973	RC453B 42S/940 DLO 9010 U4 L1200 W300B30	42S
910505103981	RC453B 40S/TW9 DLO U4 L1200 W300 B30	28S
910505105909	RC453B 42S/940 DLO9010U4 L1200W300B30 SC	-
910505105915	RC453B 42S/UE840 DLO9010 U4 L1200W300B30	-
910505103984	RC453X 28S/840 DLO L1195 W298 B30	28S
910505103980	RC453B 28S/UE840 MXO9010ELP3L1200W150B30	28S
910505103982	RC453B 28S/UE840 MXO L1200 W150 B30	28S
910505103941	RC455B 28S/940 MLO L1200 W100 B40	28S
910505103942	RC455B 36S/940 MLO L1200 W100 B40	36S
910505103943	RC455B 36S/940 MLO L1200 W125 B40	36S
910505103944	RC455B 36S/940 MLO L1200 W150 B40	36S
910505103945	RC455B 40S/940 MLO L1200 W100 B40	40S
910505103946	RC455B 48S/940 MLO L1495 W100 B40	48S
910505103947	RC455B 28S/TW9 MLO L1200 W100 B40	40S
910505105903	RC455B 28S/940 MLO L1200 W100 B40 SC	-
910505105904	RC455B 40S/940 MLO L1200 W100 B40 SC	-
910505105917	RC455B 40S/BU840 MLO L1200 W100 B40	-
910505103971	RC453B 28S/840 DLO L1200 W300 B30	28S
910505103972	RC453B 28S/840 DLO 9010 ELP3L1200W300B30	28S
910505103977	RC453B 28S/840 DLO L1195 W298 B30	28S
910505105907	RC453B 28S/840 DLO L1200W300B30 SC	-
910505105908	RC453B 40S/UE840 DLO L1200W300B30 SC	-
910505105914	RC453B 28S/UE840 DLO L1200 W300 B30	-
910505105916	RC453B 28S/BU840 DLO L1200W300B30	-
910505103961	RC455B 36S/940 MCW-M L1200 W100 B40	36S
910505103963	RC455B 40S/940 MCW-M L1200 W100 B40	40S
910505105906	RC455B 36S/940 MCW-M L1200W100B40 SC	-
910505103968	RC455B 40S/940MCW-M U4W3 L1722 W150 B40	40S
910505103916	RC455X 36S/940 DLO U4 W3 L1722 W100 B30	36S
910505103920	RC455X 40S/TW9 DLO U4 W3 L1722 W100 B30	40S
910505103923	RC455X 36S/940 DLOU5 9016W3 L1722W185B40	36S
910505103931	RC455X 36S/930 DLO U4 W3 L1495 W100 B30	36S
910505103975	RC453B 36S/940 DLO U5 L1200 W300 B30	34S

Light Technical

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Color rendering index (CRI)	Optic type
910505103952	RC455B 36S/940 MXO U4 L1200 W100 B40	3,600 lm	4000 K	122 lm/W	>90	Wide beam
910505103958	RC455B 40S/TW9 MXO U4 L1200 W100 B40	4,000 lm	Tunable white 2700-6500 K	90 lm/W	>90	Wide beam
910505103960	RC455B 40S/940 MXO ELP3 W6L1722W150B40WT	4,000 lm	4000 K	108 lm/W	>90	Wide beam
910505103949	RC455B 28S/TW9 MLO U4 L1720 W124 B40	2,800 lm	Tunable white 2700-6500 K	85 lm/W	>90	Wide beam office compliant
910505103950	RC455B 36S/940 MLO U4 W3 L1722 W100 B40	3,600 lm	4000 K	95 lm/W	>90	Wide beam office compliant
910505103974	RC453B42S/940DLO9010U4ELW3W4L1200W300B30	4,200 lm	4000 K	131 lm/W	>90	Wide beam office compliant
910505103976	RC453B 36S/940 DLO9010U4ELW3L1200W300B30	3,600 lm	4000 K	126 lm/W	>90	Wide beam office compliant
910505103957	RC455B 48S/940 MXO L1495 W100 B40	4,800 lm	4000 K	119 lm/W	>90	Wide beam
910505103959	RC455B 28S/TWBU MCW-M U4 L1200 W100 B40	2,800 lm	Tunable white 2700-6500 K	75 lm/W	>90	Reflector
910505103965	RC455B 36S/940 MCW-M U4 L1200 W100 B40	3,600 lm	4000 K	122 lm/W	>90	Reflector
910505103978	RC453B 28S/UE840 MXO 9010 L1200 W300 B30	2,800 lm	4000 K	144 lm/W	>80	Wide beam
910505103979	RC453B 28S/UE840MXO9010ELP3 L1200W300B30	2,800 lm	4000 K	110 lm/W	>80	Wide beam
910505103951	RC455B 36S/940 MXO L1200 W100 B40	3,600 lm	4000 K	120 lm/W	>90	Wide beam
910505103953	RC455B 40S/940 MXO L1200 W100 B40	4,000 lm	4000 K	118 lm/W	>90	Wide beam
910505103954	RC455B 36S/940 MXO L1200 W125 B40	3,600 lm	4000 K	124 lm/W	>90	Wide beam
910505103955	RC455B 36S/940 MXO L1200 W150 B40	3,600 lm	4000 K	129 lm/W	>90	Wide beam
910505103956	RC455B 28S/940 MXO L1200 W150 B40	2,800 lm	4000 K	127 lm/W	>90	Wide beam
910505105905	RC455B 40S/940 MXO L1200 W100 B40 SC	4,000 lm	4000 K	114 lm/W	>90	Wide beam
910505103937	RC455B 40S/940 DLO U4 W3 L1722 W100 B30	4,000 lm	4000 K	154 lm/W	>90	Wide beam office compliant
910505103940	RC455B 36S/940 DLO L1200 W100 B30	3,600 lm	4000 K	150 lm/W	>90	Wide beam office compliant
910505103934	RC455X 36S/940 MCW-M U4 W3 L1722 W100B30	3,600 lm	4000 K	122 lm/W	>90	Reflector
910505105902	RC455B 36S/940 MCW-M U4W3L1722W100B30SC	3,600 lm	4000 K	122 lm/W	>90	Reflector
910505103926	RC455X 40S/940 DLO W3W2 L1700 W100 B30	4,000 lm	4000 K	140 lm/W	>90	Wide beam office compliant
910505103927	RC455X 40S/940 DLO W3W2 L1497 W150 B30	4,000 lm	4000 K	151 lm/W	>90	Wide beam office compliant
910505105901	RC455X 40S/940 DLO W3W2 L1497W150B30 SC	4,000 lm	4000 K	151 lm/W	>90	Wide beam office compliant
910505105913	RC455B 40S/UE 840 DLO L1200 W100 B30	4,000 lm	4000 K	182 lm/W	>80	Wide beam office compliant
910505103924	RC455X 36S/940 DLO U4 W3 L1722 W200 B40	3,600 lm	4000 K	153 lm/W	>90	Wide beam office compliant
910505105911	RC455X 36S/UE840 DLO U4 W3 L1722W200B40	3,600 lm	4000 K	182 lm/W	>80	Wide beam office compliant
910505103936	RC455B 36S/940 DLO 9010U4W3 L1722W150B30	3,600 lm	4000 K	153 lm/W	>90	Wide beam office compliant

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Color rendering index (CRI)	Optic type
910505103985	RC453X 28S/UE840MXO9010 U4W3L1200W150B30	2,800 lm	4000 K	112 lm/W	>80	Wide beam
910505103921	RC455X 28S/TWBU MCB-M U4 W3 L1722W100B30	2,800 lm	Tunable white 2700-6500 K	73 lm/W	>90	Reflector
910505103935	RC455X 36S/940 MCB-M U4 W3 L1722 W100B30	3,600 lm	4000 K	107 lm/W	>90	Reflector
910505103967	RC455B 40S/940 MCB-M W3W2 L1722 W150 B30	4,000 lm	4000 K	105 lm/W	>90	Reflector
910505103948	RC455B 28S/TW9 MLO U4 L1200 W100 B40	2,800 lm	Tunable white 2700-6500 K	85 lm/W	>90	Wide beam office compliant
910505103918	RC455X 36S/940 DLO W5 L1722 W185 B30 WT	3,600 lm	4000 K	150 lm/W	>90	Wide beam office compliant
910505103930	RC455X 40S/940 DLO W3W2 L1497 W185 B30	4,000 lm	4000 K	151 lm/W	>90	Wide beam office compliant
910505103932	RC455X 36S/940 MLO W5 L1722 W185 B30 WT	3,600 lm	4000 K	100 lm/W	>90	Wide beam office compliant
910505105912	RC455B 36S/UE840 DLO W3W2 L1722 W185 B30	3,600 lm	4000 K	182 lm/W	>80	Wide beam office compliant
910505103962	RC455B 36S/940 MCB-M L1200 W100 B40	3,600 lm	4000 K	105 lm/W	>90	Reflector
910505103964	RC455B 40S/940 MCB-M L1200 W100 B40	4,000 lm	4000 K	104 lm/W	>90	Reflector
910505103966	RC455B 36S/940 MCB-M U4 L1200 W100 B40	3,600 lm	4000 K	107 lm/W	>90	Reflector
910505103938	RC455B 40S/940 DLO W3W2 L1722 W150 B30	4,000 lm	4000 K	151 lm/W	>90	Wide beam office compliant
910505103939	RC455B 36S/940 DLO W3W2 L1722 W185 B30	3,600 lm	4000 K	150 lm/W	>90	Wide beam office compliant
910505103917	RC455X 40S/940 DLO W3W2 L1722 W150 B30	4,000 lm	4000 K	151 lm/W	>90	Wide beam office compliant
910505103919	RC455X 40S/940 DLO W3W2 L1722 W150 B40	4,000 lm	4000 K	151 lm/W	>90	Wide beam office compliant
910505103922	RC455X 40S/930 DLO W3W2 L1722 W150 B30	4,000 lm	3000 K	151 lm/W	>90	Wide beam office compliant
910505103925	RC455X 36S/940 DLO W5 L1700 W150 B30 WT	3,600 lm	4000 K	150 lm/W	>90	Wide beam office compliant
910505105910	RC455X 40S/UE840 DLO W3W2 L1722 W150 B40	4,000 lm	4000 K	182 lm/W	>80	Wide beam office compliant
910505105918	RC455X 40S/BU840 DLO W3W2 L1722 W150 B30	4,000 lm	4000 K	143 lm/W	>80	Wide beam office compliant
910505103973	RC453B 42S/940 DLO 9010 U4 L1200 W300B30	4,200 lm	4000 K	162 lm/W	>90	Wide beam office compliant
910505103981	RC453B 40S/TW9 DLO U4 L1200 W300 B30	4,000 lm	Tunable white 2700-6500 K	118 lm/W	>90	Wide beam office compliant
910505105909	RC453B 42S/940 DLO9010U4 L1200W300B30 SC	4,200 lm	4000 K	162 lm/W	>90	Wide beam office compliant
910505105915	RC453B 42S/UE840 DLO9010 U4 L1200W300B30	4,200 lm	4000 K	183 lm/W	>80	Wide beam office compliant
910505103984	RC453X 28S/840 DLO L1195 W298 B30	2,800 lm	4000 K	161 lm/W	>80	Wide beam office compliant
910505103980	RC453B 28S/UE840 MXO9010ELP3L1200W150B30	2,800 lm	4000 K	110 lm/W	>80	Wide beam
910505103982	RC453B 28S/UE840 MXO L1200 W150 B30	2,800 lm	4000 K	144 lm/W	>80	Wide beam
910505103941	RC455B 28S/940 MLO L1200 W100 B40	2,800 lm	4000 K	97 lm/W	>90	Wide beam office compliant

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Color rendering index (CRI)	Optic type
910505103942	RC455B 36S/940 MLO L1200 W100 B40	3,600 lm	4000 K	95 lm/W	>90	Wide beam office compliant
910505103943	RC455B 36S/940 MLO L1200 W125 B40	3,600 lm	4000 K	100 lm/W	>90	Wide beam office compliant
910505103944	RC455B 36S/940 MLO L1200 W150 B40	3,600 lm	4000 K	100 lm/W	>90	Wide beam office compliant
910505103945	RC455B 40S/940 MLO L1200 W100 B40	4,000 lm	4000 K	94 lm/W	>90	Wide beam office compliant
910505103946	RC455B 48S/940 MLO L1495 W100 B40	4,800 lm	4000 K	96 lm/W	>90	Wide beam office compliant
910505103947	RC455B 28S/TW9 MLO L1200 W100 B40	2,800 lm	Tunable white 2700-6500 K	85 lm/W	>90	Wide beam office compliant
910505105903	RC455B 28S/940 MLO L1200 W100 B40 SC	2,800 lm	4000 K	97 lm/W	>90	Wide beam office compliant
910505105904	RC455B 40S/940 MLO L1200 W100 B40 SC	4,000 lm	4000 K	94 lm/W	>90	Wide beam office compliant
910505105917	RC455B 40S/BU840 MLO L1200 W100 B40	4,000 lm	4000 K	100 lm/W	>80	Wide beam office compliant
910505103971	RC453B 28S/840 DLO L1200 W300 B30	2,800 lm	4000 K	161 lm/W	>80	Wide beam office compliant
910505103972	RC453B 28S/840 DLO 9010 ELP3L1200W300B30	2,800 lm	4000 K	119 lm/W	>80	Wide beam office compliant
910505103977	RC453B 28S/840 DLO L1195 W298 B30	2,800 lm	4000 K	124 lm/W	>80	Wide beam office compliant
910505105907	RC453B 28S/840 DLO L1200W300B30 SC	2,800 lm	4000 K	152.2 lm/W	>80	Wide beam office compliant
910505105908	RC453B 40S/UE840 DLO L1200W300B30 SC	4,000 lm	4000 K	182 lm/W	>80	Wide beam office compliant
910505105914	RC453B 28S/UE840 DLO L1200 W300 B30	2,800 lm	4000 K	180 lm/W	>80	Wide beam office compliant
910505105916	RC453B 28S/BU840 DLO L1200W300B30	2,800 lm	4000 K	143 lm/W	>80	Wide beam office compliant
910505103961	RC455B 36S/940 MCW-M L1200 W100 B40	3,600 lm	4000 K	120 lm/W	>90	Reflector
910505103963	RC455B 40S/940 MCW-M L1200 W100 B40	4,000 lm	4000 K	119 lm/W	>90	Reflector
910505105906	RC455B 36S/940 MCW-M L1200W100B40 SC	3,600 lm	4000 K	120 lm/W	>90	Reflector
910505103968	RC455B 40S/940MCW-M U4W3 L1722 W150 B40	4,000 lm	4000 K	121 lm/W	>90	Reflector
910505103916	RC455X 36S/940 DLO U4 W3 L1722 W100 B30	3,600 lm	4000 K	147 lm/W	>90	Wide beam office compliant
910505103920	RC455X 40S/TW9 DLO U4 W3 L1722 W100 B30	4,000 lm	Tunable white 2700-6500 K	119 lm/W	>90	Wide beam office compliant
910505103923	RC455X 36S/940 DLOU5 9016W3 L1722W185B40	3,600 lm	4000 K	153 lm/W	>90	Wide beam office compliant
910505103931	RC455X 36S/930 DLO U4 W3 L1495 W100 B30	3,600 lm	3000 K	150 lm/W	>90	Wide beam office compliant
910505103975	RC453B 36S/940 DLO U5 L1200 W300 B30	3,600 lm	4000 K	160 lm/W	>90	Wide beam office compliant

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Suitable for random switching
910505103952	RC455B 36S/940 MXO U4 L1200 W100 B40	29.5 W	Yes
910505103958	RC455B 40S/TW9 MXO U4 L1200 W100 B40	44.5 W	Yes
910505103960	RC455B 40S/940 MXO ELP3 W6L1722W150B40WT	37 W	No
910505103949	RC455B 28S/TW9 MLO U4 L1720 W124 B40	33 W	Yes
910505103950	RC455B 36S/940 MLO U4 W3 L1722 W100 B40	38 W	Yes
910505103974	RC453B42S/940DLO9010U4ELW3W4L1200W300B30	32 W	Yes
910505103976	RC453B 36S/940 DLO9010U4ELW3L1200W300B30	28.5 W	Yes
910505103957	RC455B 48S/940 MXO L1495 W100 B40	40.5 W	No
910505103959	RC455B 28S/TWBU MCW-M U4 L1200 W100 B40	37.5 W	Yes
910505103965	RC455B 36S/940 MCW-M U4 L1200 W100 B40	29.5 W	Yes
910505103978	RC453B 28S/UE840 MXO 9010 L1200 W300 B30	19.4 W	No
910505103979	RC453B 28S/UE840MXO9010ELP3 L1200W300B30	25.5 W	No
910505103951	RC455B 36S/940 MXO L1200 W100 B40	30 W	No
910505103953	RC455B 40S/940 MXO L1200 W100 B40	34 W	No
910505103954	RC455B 36S/940 MXO L1200 W125 B40	29 W	No
910505103955	RC455B 36S/940 MXO L1200 W150 B40	28 W	No
910505103956	RC455B 28S/940 MXO L1200 W150 B40	22 W	No
910505105905	RC455B 40S/940 MXO L1200 W100 B40 SC	35 W	No
910505103937	RC455B 40S/940 DLO U4 W3 L1722 W100 B30	26 W	Yes
910505103940	RC455B 36S/940 DLO L1200 W100 B30	24 W	No
910505103934	RC455X 36S/940 MCW-M U4 W3 L1722 W100B30	29.5 W	Yes
910505105902	RC455B 36S/940 MCW-M U4W3L1722W100B30SC	29.5 W	Yes
910505103926	RC455X 40S/940 DLO W3W2 L1700 W100 B30	28.5 W	No
910505103927	RC455X 40S/940 DLO W3W2 L1497 W150 B30	26.5 W	No
910505105901	RC455X 40S/940 DLO W3W2 L1497W150B30 SC	26.6 W	No
910505105913	RC455B 40S/UE 840 DLO L1200 W100 B30	22 W	No
910505103924	RC455X 36S/940 DLO U4 W3 L1722 W200 B40	23.5 W	Yes
910505105911	RC455X 36S/UE840 DLO U4 W3 L1722W200B40	19.8 W	Yes
910505103936	RC455B 36S/940 DLO 9010U4W3 L1722W150B30	23.5 W	Yes
910505103985	RC453X 28S/UE840MXO9010 U4W3L1200W150B30	25 W	Yes
910505103921	RC455X 28S/TWBU MCB-M U4 W3 L1722W100B30	38.5 W	Yes
910505103935	RC455X 36S/940 MCB-M U4 W3 L1722 W100B30	33.5 W	Yes
910505103967	RC455B 40S/940 MCB-M W3W2 L1722 W150 B30	38 W	No
910505103948	RC455B 28S/TW9 MLO U4 L1200 W100 B40	33 W	Yes
910505103918	RC455X 36S/940 DLO W5 L1722 W185 B30 WT	24 W	No
910505103930	RC455X 40S/940 DLO W3W2 L1497 W185 B30	26.5 W	No
910505103932	RC455X 36S/940 MLO W5 L1722 W185 B30 WT	36 W	No
910505105912	RC455B 36S/UE840 DLO W3W2 L1722 W185 B30	19.8 W	No
910505103962	RC455B 36S/940 MCB-M L1200 W100 B40	34 W	No
910505103964	RC455B 40S/940 MCB-M L1200 W100 B40	38.5 W	No
910505103966	RC455B 36S/940 MCB-M U4 L1200 W100 B40	33.5 W	Yes

Order Code	Full Product Name	Power Consumption	Suitable for random switching
910505103938	RC455B 40S/940 DLO W3W2 L1722 W150 B30	26.5 W	No
910505103939	RC455B 36S/940 DLO W3W2 L1722 W185 B30	24 W	No
910505103917	RC455X 40S/940 DLO W3W2 L1722 W150 B30	26.5 W	No
910505103919	RC455X 40S/940 DLO W3W2 L1722 W150 B40	26.5 W	No
910505103922	RC455X 40S/930 DLO W3W2 L1722 W150 B30	26.5 W	No
910505103925	RC455X 36S/940 DLO W5 L1700 W150 B30 WT	24 W	No
910505105910	RC455X 40S/UE840 DLO W3W2 L1722 W150 B40	22 W	No
910505105918	RC455X 40S/BU840 DLO W3W2 L1722 W150 B30	28 W	No
910505103973	RC453B 42S/940 DLO 9010 U4 L1200 W300B30	26 W	Yes
910505103981	RC453B 40S/TW9 DLO U4 L1200 W300 B30	36.5 W	Yes
910505105909	RC453B 42S/940 DLO9010U4 L1200W300B30 SC	26 W	Yes
910505105915	RC453B 42S/UE840 DLO9010 U4 L1200W300B30	23.1 W	Yes
910505103984	RC453X 28S/840 DLO L1195 W298 B30	17.4 W	No
910505103980	RC453B 28S/UE840 MXO9010ELP3L1200W150B30	25.5 W	No
910505103982	RC453B 28S/UE840 MXO L1200 W150 B30	19.4 W	No
910505103941	RC455B 28S/940 MLO L1200 W100 B40	29 W	No
910505103942	RC455B 36S/940 MLO L1200 W100 B40	38 W	No
910505103943	RC455B 36S/940 MLO L1200 W125 B40	36 W	No
910505103944	RC455B 36S/940 MLO L1200 W150 B40	36 W	No
910505103945	RC455B 40S/940 MLO L1200 W100 B40	42.5 W	No
910505103946	RC455B 48S/940 MLO L1495 W100 B40	50 W	No
910505103947	RC455B 28S/TW9 MLO L1200 W100 B40	33 W	No
910505105903	RC455B 28S/940 MLO L1200 W100 B40 SC	29 W	No
910505105904	RC455B 40S/940 MLO L1200 W100 B40 SC	42.5 W	No
910505105917	RC455B 40S/BU840 MLO L1200 W100 B40	39.9 W	No
910505103971	RC453B 28S/840 DLO L1200 W300 B30	17.4 W	No
910505103972	RC453B 28S/840 DLO 9010 ELP3L1200W300B30	23.5 W	No
910505103977	RC453B 28S/840 DLO L1195 W298 B30	22.5 W	No
910505105907	RC453B 28S/840 DLO L1200W300B30 SC	18.4 W	No
910505105908	RC453B 40S/UE840 DLO L1200W300B30 SC	22 W	No
910505105914	RC453B 28S/UE840 DLO L1200 W300 B30	15.4 W	No
910505105916	RC453B 28S/BU840 DLO L1200W300B30	19.6 W	No
910505103961	RC455B 36S/940 MCW-M L1200 W100 B40	30 W	No
910505103963	RC455B 40S/940 MCW-M L1200 W100 B40	33.5 W	No
910505105906	RC455B 36S/940 MCW-M L1200W100B40 SC	30 W	No
910505103968	RC455B 40S/940MCW-M U4W3 L1722 W150 B40	33 W	Yes
910505103916	RC455X 36S/940 DLO U4 W3 L1722 W100 B30	24.5 W	Yes
910505103920	RC455X 40S/TW9 DLO U4 W3 L1722 W100 B30	33.5 W	Yes
910505103923	RC455X 36S/940 DLOU5 9016W3 L1722W185B40	23.5 W	Yes
910505103931	RC455X 36S/930 DLO U4 W3 L1495 W100 B30	24 W	Yes
910505103975	RC453B 36S/940 DLO U5 L1200 W300 B30	22.5 W	Yes

Controls and Dimming

Order Code	Full Product Name	Embedded control
910505103952	RC455B 36S/940 MXO U4 L1200 W100 B40	Upgradable sensor slot with SC200 sensor
910505103958	RC455B 40S/TW9 MXO U4 L1200 W100 B40	Upgradable sensor slot with SC200 sensor
910505103960	RC455B 40S/940 MXO ELP3 W6L1722W150B40WT	-
910505103949	RC455B 28S/TW9 MLO U4 L1720 W124 B40	Upgradable sensor slot with SC200 sensor
910505103950	RC455B 36S/940 MLO U4 W3 L1722 W100 B40	Upgradable sensor slot with SC200 sensor
910505103974	RC453B42S/940DLO9010U4ELW3W4L1200W300B30	Upgradable sensor slot with SC200 sensor
910505103976	RC453B 36S/940 DLO9010U4ELW3L1200W300B30	Upgradable sensor slot with SC200 sensor
910505103957	RC455B 48S/940 MXO L1495 W100 B40	-
910505103959	RC455B 28S/TWBW MCW-M U4 L1200 W100 B40	Upgradable sensor slot with SC200 sensor
910505103965	RC455B 36S/940 MCW-M U4 L1200 W100 B40	Upgradable sensor slot with SC200 sensor
910505103978	RC453B 28S/UE840 MXO 9010 L1200 W300 B30	-
910505103979	RC453B 28S/UE840MXO9010ELP3 L1200W300B30	-
910505103951	RC455B 36S/940 MXO L1200 W100 B40	-
910505103953	RC455B 40S/940 MXO L1200 W100 B40	-
910505103954	RC455B 36S/940 MXO L1200 W125 B40	-
910505103955	RC455B 36S/940 MXO L1200 W150 B40	-
910505103956	RC455B 28S/940 MXO L1200 W150 B40	-
910505105905	RC455B 40S/940 MXO L1200 W100 B40 SC	-
910505103937	RC455B 40S/940 DLO U4 W3 L1722 W100 B30	Upgradable sensor slot with SC200 sensor
910505103940	RC455B 36S/940 DLO L1200 W100 B30	-
910505103934	RC455X 36S/940 MCW-M U4 W3 L1722 W100B30	Upgradable sensor slot with SC200 sensor
910505105902	RC455B 36S/940 MCW-M U4W3L1722W100B30SC	Upgradable sensor slot with SC200 sensor
910505103926	RC455X 40S/940 DLO W3W2 L1700 W100 B30	-
910505103927	RC455X 40S/940 DLO W3W2 L1497 W150 B30	-
910505105901	RC455X 40S/940 DLO W3W2 L1497W150B30 SC	-
910505105913	RC455B 40S/UE 840 DLO L1200 W100 B30	-
910505103924	RC455X 36S/940 DLO U4 W3 L1722 W200 B40	Upgradable sensor slot with SC200 sensor
910505105911	RC455X 36S/UE840 DLO U4 W3 L1722W200B40	Upgradable sensor slot with SC200 sensor
910505103936	RC455B 36S/940 DLO 9010U4W3 L1722W150B30	Upgradable sensor slot with SC200 sensor
910505103985	RC453X 28S/UE840MXO9010 U4W3L1200W150B30	Upgradable sensor slot with SC200 sensor
910505103921	RC455X 28S/TWBW MCB-M U4 W3 L1722W100B30	Upgradable sensor slot with SC200 sensor
910505103935	RC455X 36S/940 MCB-M U4 W3 L1722 W100B30	Upgradable sensor slot with SC200 sensor
910505103967	RC455B 40S/940 MCB-M W3W2 L1722 W150 B30	-
910505103948	RC455B 28S/TW9 MLO U4 L1200 W100 B40	Upgradable sensor slot with SC200 sensor
910505103918	RC455X 36S/940 DLO W5 L1722 W185 B30 WT	-
910505103930	RC455X 40S/940 DLO W3W2 L1497 W185 B30	-
910505103932	RC455X 36S/940 MLO W5 L1722 W185 B30 WT	-
910505105912	RC455B 36S/UE840 DLO W3W2 L1722 W185 B30	-
910505103962	RC455B 36S/940 MCB-M L1200 W100 B40	-
910505103964	RC455B 40S/940 MCB-M L1200 W100 B40	-
910505103966	RC455B 36S/940 MCB-M U4 L1200 W100 B40	Upgradable sensor slot with SC200 sensor

Order Code	Full Product Name	Embedded control
910505103938	RC455B 40S/940 DLO W3W2 L1722 W150 B30	-
910505103939	RC455B 36S/940 DLO W3W2 L1722 W185 B30	-
910505103917	RC455X 40S/940 DLO W3W2 L1722 W150 B30	-
910505103919	RC455X 40S/940 DLO W3W2 L1722 W150 B40	-
910505103922	RC455X 40S/930 DLO W3W2 L1722 W150 B30	-
910505103925	RC455X 36S/940 DLO W5 L1700 W150 B30 WT	-
910505105910	RC455X 40S/UE840 DLO W3W2 L1722 W150 B40	-
910505105918	RC455X 40S/BU840 DLO W3W2 L1722 W150 B30	-
910505103973	RC453B 42S/940 DLO 9010 U4 L1200 W300B30	Upgradable sensor slot with SC200 sensor
910505103981	RC453B 40S/TW9 DLO U4 L1200 W300 B30	Upgradable sensor slot with SC200 sensor
910505105909	RC453B 42S/940 DLO9010U4 L1200W300B30 SC	Upgradable sensor slot with SC200 sensor
910505105915	RC453B 42S/UE840 DLO9010 U4 L1200W300B30	Upgradable sensor slot with SC200 sensor
910505103984	RC453X 28S/840 DLO L1195 W298 B30	-
910505103980	RC453B 28S/UE840 MXO9010ELP3L1200W150B30	-
910505103982	RC453B 28S/UE840 MXO L1200 W150 B30	-
910505103941	RC455B 28S/940 MLO L1200 W100 B40	-
910505103942	RC455B 36S/940 MLO L1200 W100 B40	-
910505103943	RC455B 36S/940 MLO L1200 W125 B40	-
910505103944	RC455B 36S/940 MLO L1200 W150 B40	-
910505103945	RC455B 40S/940 MLO L1200 W100 B40	-
910505103946	RC455B 48S/940 MLO L1495 W100 B40	-
910505103947	RC455B 28S/TW9 MLO L1200 W100 B40	-
910505105903	RC455B 28S/940 MLO L1200 W100 B40 SC	-
910505105904	RC455B 40S/940 MLO L1200 W100 B40 SC	-
910505105917	RC455B 40S/BU840 MLO L1200 W100 B40	-
910505103971	RC453B 28S/840 DLO L1200 W300 B30	-
910505103972	RC453B 28S/840 DLO 9010 ELP3L1200W300B30	-
910505103977	RC453B 28S/840 DLO L1195 W298 B30	-
910505105907	RC453B 28S/840 DLO L1200W300B30 SC	-
910505105908	RC453B 40S/UE840 DLO L1200W300B30 SC	-
910505105914	RC453B 28S/UE840 DLO L1200 W300 B30	-
910505105916	RC453B 28S/BU840 DLO L1200W300B30	-
910505103961	RC455B 36S/940 MCW-M L1200 W100 B40	-
910505103963	RC455B 40S/940 MCW-M L1200 W100 B40	-
910505105906	RC455B 36S/940 MCW-M L1200W100B40 SC	-
910505103968	RC455B 40S/940MCW-M U4W3 L1722 W150 B40	Upgradable sensor slot with SC200 sensor
910505103916	RC455X 36S/940 DLO U4 W3 L1722 W100 B30	Upgradable sensor slot with SC200 sensor
910505103920	RC455X 40S/TW9 DLO U4 W3 L1722 W100 B30	Upgradable sensor slot with SC200 sensor
910505103923	RC455X 36S/940 DLOU5 9016W3 L1722W185B40	Interact SC1500 Multi-sensor bundle
910505103931	RC455X 36S/930 DLO U4 W3 L1495 W100 B30	Upgradable sensor slot with SC200 sensor
910505103975	RC453B 36S/940 DLO U5 L1200 W300 B30	Interact SC1500 Multi-sensor bundle

Mechanical and Housing

Order Code	Full Product Name	Optical cover type
910505103952	RC455B 36S/940 MXO U4 L1200 W100 B40	Micro Hexagonal Optic
910505103958	RC455B 40S/TW9 MXO U4 L1200 W100 B40	Micro Hexagonal Optic
910505103960	RC455B 40S/940 MXO ELP3 W6L1722W150B40WT	Micro Hexagonal Optic
910505103949	RC455B 28S/TW9 MLO U4 L1720 W124 B40	Micro-lens optic
910505103950	RC455B 36S/940 MLO U4 W3 L1722 W100 B40	Micro-lens optic
910505103974	RC453B42S/940DLO9010U4ELW3W4L1200W300B30	Acrylic bowl/cover frosted
910505103976	RC453B 36S/940 DLO9010U4ELW3L1200W300B30	Acrylic bowl/cover frosted
910505103957	RC455B 48S/940 MXO L1495 W100 B40	Micro Hexagonal Optic
910505103959	RC455B 28S/TWBU MCW-M U4 L1200 W100 B40	Micro Hexagonal Optic
910505103965	RC455B 36S/940 MCW-M U4 L1200 W100 B40	-
910505103978	RC453B 28S/UE840 MXO 9010 L1200 W300 B30	Micro Hexagonal Optic
910505103979	RC453B 28S/UE840MXO9010ELP3 L1200W300B30	Micro Hexagonal Optic
910505103951	RC455B 36S/940 MXO L1200 W100 B40	Micro Hexagonal Optic
910505103953	RC455B 40S/940 MXO L1200 W100 B40	Micro Hexagonal Optic
910505103954	RC455B 36S/940 MXO L1200 W125 B40	Micro Hexagonal Optic
910505103955	RC455B 36S/940 MXO L1200 W150 B40	Micro Hexagonal Optic
910505103956	RC455B 28S/940 MXO L1200 W150 B40	Micro Hexagonal Optic
910505105905	RC455B 40S/940 MXO L1200 W100 B40 SC	-
910505103937	RC455B 40S/940 DLO U4 W3 L1722 W100 B30	Acrylic bowl/cover frosted
910505103940	RC455B 36S/940 DLO L1200 W100 B30	Acrylic bowl/cover frosted
910505103934	RC455X 36S/940 MCW-M U4 W3 L1722 W100B30	-
910505105902	RC455B 36S/940 MCW-M U4W3L1722W100B30SC	-
910505103926	RC455X 40S/940 DLO W3W2 L1700 W100 B30	Acrylic bowl/cover frosted
910505103927	RC455X 40S/940 DLO W3W2 L1497 W150 B30	Acrylic bowl/cover frosted
910505105901	RC455X 40S/940 DLO W3W2 L1497W150B30 SC	-
910505105913	RC455B 40S/UE 840 DLO L1200 W100 B30	-
910505103924	RC455X 36S/940 DLO U4 W3 L1722 W200 B40	Acrylic bowl/cover frosted
910505105911	RC455X 36S/UE840 DLO U4 W3 L1722W200B40	-
910505103936	RC455B 36S/940 DLO 9010U4W3 L1722W150B30	Acrylic bowl/cover frosted
910505103985	RC453X 28S/UE840MXO9010 U4W3L1200W150B30	Micro Hexagonal Optic
910505103921	RC455X 28S/TWBU MCB-M U4 W3 L1722W100B30	Acrylic bowl/cover frosted
910505103935	RC455X 36S/940 MCB-M U4 W3 L1722 W100B30	-
910505103967	RC455B 40S/940 MCB-M W3W2 L1722 W150 B30	-
910505103948	RC455B 28S/TW9 MLO U4 L1200 W100 B40	Micro-lens optic
910505103918	RC455X 36S/940 DLO W5 L1722 W185 B30 WT	Acrylic bowl/cover frosted
910505103930	RC455X 40S/940 DLO W3W2 L1497 W185 B30	Acrylic bowl/cover frosted
910505103932	RC455X 36S/940 MLO W5 L1722 W185 B30 WT	Micro Hexagonal Optic
910505105912	RC455B 36S/UE840 DLO W3W2 L1722 W185 B30	-
910505103962	RC455B 36S/940 MCB-M L1200 W100 B40	-
910505103964	RC455B 40S/940 MCB-M L1200 W100 B40	-
910505103966	RC455B 36S/940 MCB-M U4 L1200 W100 B40	-

Order Code	Full Product Name	Optical cover type
910505103938	RC455B 40S/940 DLO W3W2 L1722 W150 B30	Acrylic bowl/cover frosted
910505103939	RC455B 36S/940 DLO W3W2 L1722 W185 B30	Acrylic bowl/cover frosted
910505103917	RC455X 40S/940 DLO W3W2 L1722 W150 B30	Acrylic bowl/cover frosted
910505103919	RC455X 40S/940 DLO W3W2 L1722 W150 B40	Acrylic bowl/cover frosted
910505103922	RC455X 40S/930 DLO W3W2 L1722 W150 B30	Acrylic bowl/cover frosted
910505103925	RC455X 36S/940 DLO W5 L1700 W150 B30 WT	Acrylic bowl/cover frosted
910505105910	RC455X 40S/UE840 DLO W3W2 L1722 W150 B40	-
910505105918	RC455X 40S/BU840 DLO W3W2 L1722 W150 B30	-
910505103973	RC453B 42S/940 DLO 9010 U4 L1200 W300B30	Acrylic bowl/cover frosted
910505103981	RC453B 40S/TW9 DLO U4 L1200 W300 B30	Micro Hexagonal Optic
910505105909	RC453B 42S/940 DLO9010U4 L1200W300B30 SC	-
910505105915	RC453B 42S/UE840 DLO9010 U4 L1200W300B30	-
910505103984	RC453X 28S/840 DLO L1195 W298 B30	Acrylic bowl/cover frosted
910505103980	RC453B 28S/UE840 MXO9010ELP3L1200W150B30	Micro Hexagonal Optic
910505103982	RC453B 28S/UE840 MXO L1200 W150 B30	Micro Hexagonal Optic
910505103941	RC455B 28S/940 MLO L1200 W100 B40	Micro-lens optic
910505103942	RC455B 36S/940 MLO L1200 W100 B40	Micro-lens optic
910505103943	RC455B 36S/940 MLO L1200 W125 B40	Micro-lens optic
910505103944	RC455B 36S/940 MLO L1200 W150 B40	Micro-lens optic
910505103945	RC455B 40S/940 MLO L1200 W100 B40	Micro-lens optic
910505103946	RC455B 48S/940 MLO L1495 W100 B40	Micro-lens optic
910505103947	RC455B 28S/TW9 MLO L1200 W100 B40	Micro-lens optic
910505105903	RC455B 28S/940 MLO L1200 W100 B40 SC	-
910505105904	RC455B 40S/940 MLO L1200 W100 B40 SC	-
910505105917	RC455B 40S/BU840 MLO L1200 W100 B40	-
910505103971	RC453B 28S/840 DLO L1200 W300 B30	Acrylic bowl/cover frosted
910505103972	RC453B 28S/840 DLO 9010 ELP3L1200W300B30	Acrylic bowl/cover frosted
910505103977	RC453B 28S/840 DLO L1195 W298 B30	Acrylic bowl/cover frosted
910505105907	RC453B 28S/840 DLO L1200W300B30 SC	-
910505105908	RC453B 40S/UE840 DLO L1200W300B30 SC	-
910505105914	RC453B 28S/UE840 DLO L1200 W300 B30	-
910505105916	RC453B 28S/BU840 DLO L1200W300B30	-
910505103961	RC455B 36S/940 MCW-M L1200 W100 B40	-
910505103963	RC455B 40S/940 MCW-M L1200 W100 B40	-
910505105906	RC455B 36S/940 MCW-M L1200W100B40 SC	-
910505103968	RC455B 40S/940MCW-M U4W3 L1722 W150 B40	-
910505103916	RC455X 36S/940 DLO U4 W3 L1722 W100 B30	Acrylic bowl/cover frosted
910505103920	RC455X 40S/TW9 DLO U4 W3 L1722 W100 B30	Acrylic bowl/cover frosted
910505103923	RC455X 36S/940 DLOU5 9016W3 L1722W185B40	Acrylic bowl/cover frosted
910505103931	RC455X 36S/930 DLO U4 W3 L1495 W100 B30	Acrylic bowl/cover frosted
910505103975	RC453B 36S/940 DLO U5 L1200 W300 B30	Acrylic bowl/cover frosted

Emergency Operation

Order Code	Full Product Name	Emergency flux	Emergency lighting
910505103952	RC455B 36S/940 MXO U4 L1200 W100 B40	-	DC operated central emergency lighting
910505103958	RC455B 40S/TW9 MXO U4 L1200 W100 B40	-	DC operated central emergency lighting
910505103960	RC455B 40S/940 MXO ELP3 W6L1722W150B40WT	405 lm	Emergency lighting 3 hours duration Pro version DC operated central emergency lighting
910505103949	RC455B 28S/TW9 MLO U4 L1720 W124 B40	-	DC operated central emergency lighting
910505103950	RC455B 36S/940 MLO U4 W3 L1722 W100 B40	-	DC operated central emergency lighting
910505103974	RC453B42S/940DLO9010U4ELW3W4L1200W300B30	520 lm	DC operated central emergency lighting Emergency lighting 3 hours duration with Wireless Interface
910505103976	RC453B 36S/940 DLO9010U4ELW3L1200W300B30	520 lm	DC operated central emergency lighting Emergency lighting 3 hours duration with Wireless Interface
910505103957	RC455B 48S/940 MXO L1495 W100 B40	-	DC operated central emergency lighting
910505103959	RC455B 28S/TWBU MCW-M U4 L1200 W100 B40	-	DC operated central emergency lighting
910505103965	RC455B 36S/940 MCW-M U4 L1200 W100 B40	-	DC operated central emergency lighting
910505103978	RC453B 28S/UE840 MXO 9010 L1200 W300 B30	-	DC operated central emergency lighting
910505103979	RC453B 28S/UE840MXO9010ELP3 L1200W300B30	405 lm	Emergency lighting 3 hours duration Pro version DC operated central emergency lighting
910505103951	RC455B 36S/940 MXO L1200 W100 B40	-	DC operated central emergency lighting
910505103953	RC455B 40S/940 MXO L1200 W100 B40	-	DC operated central emergency lighting
910505103954	RC455B 36S/940 MXO L1200 W125 B40	-	DC operated central emergency lighting
910505103955	RC455B 36S/940 MXO L1200 W150 B40	-	DC operated central emergency lighting
910505103956	RC455B 28S/940 MXO L1200 W150 B40	-	DC operated central emergency lighting
910505105905	RC455B 40S/940 MXO L1200 W100 B40 SC	-	DC operated central emergency lighting
910505103937	RC455B 40S/940 DLO U4 W3 L1722 W100 B30	-	DC operated central emergency lighting
910505103940	RC455B 36S/940 DLO L1200 W100 B30	-	DC operated central emergency lighting
910505103934	RC455X 36S/940 MCW-M U4 W3 L1722 W100B30	-	DC operated central emergency lighting
910505105902	RC455B 36S/940 MCW-M U4W3L1722W100B30SC	-	DC operated central emergency lighting Emergency lighting 3 hours duration basic version
910505103926	RC455X 40S/940 DLO W3W2 L1700 W100 B30	-	DC operated central emergency lighting
910505103927	RC455X 40S/940 DLO W3W2 L1497 W150 B30	-	DC operated central emergency lighting
910505105901	RC455X 40S/940 DLO W3W2 L1497W150B30 SC	-	DC operated central emergency lighting
910505105913	RC455B 40S/UE 840 DLO L1200 W100 B30	-	DC operated central emergency lighting
910505103924	RC455X 36S/940 DLO U4 W3 L1722 W200 B40	-	DC operated central emergency lighting
910505105911	RC455X 36S/UE840 DLO U4 W3 L1722W200B40	-	DC operated central emergency lighting
910505103936	RC455B 36S/940 DLO 9010U4W3 L1722W150B30	-	DC operated central emergency lighting
910505103985	RC453X 28S/UE840MXO9010 U4W3L1200W150B30	-	DC operated central emergency lighting
910505103921	RC455X 28S/TWBU MCB-M U4 W3 L1722W100B30	-	DC operated central emergency lighting
910505103935	RC455X 36S/940 MCB-M U4 W3 L1722 W100B30	-	DC operated central emergency lighting
910505103967	RC455B 40S/940 MCB-M W3W2 L1722 W150 B30	-	DC operated central emergency lighting
910505103948	RC455B 28S/TW9 MLO U4 L1200 W100 B40	-	DC operated central emergency lighting
910505103918	RC455X 36S/940 DLO W5 L1722 W185 B30 WT	-	DC operated central emergency lighting
910505103930	RC455X 40S/940 DLO W3W2 L1497 W185 B30	-	DC operated central emergency lighting
910505103932	RC455X 36S/940 MLO W5 L1722 W185 B30 WT	-	DC operated central emergency lighting

Order Code	Full Product Name	Emergency flux	Emergency lighting
910505105912	RC455B 36S/UE840 DLO W3W2 L1722 W185 B30	-	DC operated central emergency lighting
910505103962	RC455B 36S/940 MCB-M L1200 W100 B40	-	DC operated central emergency lighting
910505103964	RC455B 40S/940 MCB-M L1200 W100 B40	-	DC operated central emergency lighting
910505103966	RC455B 36S/940 MCB-M U4 L1200 W100 B40	-	DC operated central emergency lighting
910505103938	RC455B 40S/940 DLO W3W2 L1722 W150 B30	-	DC operated central emergency lighting
910505103939	RC455B 36S/940 DLO W3W2 L1722 W185 B30	-	DC operated central emergency lighting
910505103917	RC455X 40S/940 DLO W3W2 L1722 W150 B30	-	DC operated central emergency lighting
910505103919	RC455X 40S/940 DLO W3W2 L1722 W150 B40	-	DC operated central emergency lighting
910505103922	RC455X 40S/930 DLO W3W2 L1722 W150 B30	-	DC operated central emergency lighting
910505103925	RC455X 36S/940 DLO W5 L1700 W150 B30 WT	-	DC operated central emergency lighting
910505105910	RC455X 40S/UE840 DLO W3W2 L1722 W150 B40	-	DC operated central emergency lighting
910505105918	RC455X 40S/BU840 DLO W3W2 L1722 W150 B30	-	DC operated central emergency lighting
910505103973	RC453B 42S/940 DLO 9010 U4 L1200 W300B30	-	DC operated central emergency lighting
910505103981	RC453B 40S/TW9 DLO U4 L1200 W300 B30	-	DC operated central emergency lighting
910505105909	RC453B 42S/940 DLO9010U4 L1200W300B30 SC	-	DC operated central emergency lighting
910505105915	RC453B 42S/UE840 DLO9010 U4 L1200W300B30	-	DC operated central emergency lighting
910505103984	RC453X 28S/840 DLO L1195 W298 B30	-	DC operated central emergency lighting
910505103980	RC453B 28S/UE840 MXO9010ELP3L1200W150B30	405 lm	Emergency lighting 3 hours duration with DALI interface DC operated central emergency lighting
910505103982	RC453B 28S/UE840 MXO L1200 W150 B30	-	DC operated central emergency lighting
910505103941	RC455B 28S/940 MLO L1200 W100 B40	-	DC operated central emergency lighting
910505103942	RC455B 36S/940 MLO L1200 W100 B40	-	DC operated central emergency lighting
910505103943	RC455B 36S/940 MLO L1200 W125 B40	-	DC operated central emergency lighting
910505103944	RC455B 36S/940 MLO L1200 W150 B40	-	DC operated central emergency lighting
910505103945	RC455B 40S/940 MLO L1200 W100 B40	-	DC operated central emergency lighting
910505103946	RC455B 48S/940 MLO L1495 W100 B40	-	DC operated central emergency lighting
910505103947	RC455B 28S/TW9 MLO L1200 W100 B40	-	DC operated central emergency lighting
910505105903	RC455B 28S/940 MLO L1200 W100 B40 SC	-	DC operated central emergency lighting
910505105904	RC455B 40S/940 MLO L1200 W100 B40 SC	-	DC operated central emergency lighting
910505105917	RC455B 40S/BU840 MLO L1200 W100 B40	-	DC operated central emergency lighting
910505103971	RC453B 28S/840 DLO L1200 W300 B30	-	DC operated central emergency lighting
910505103972	RC453B 28S/840 DLO 9010 ELP3L1200W300B30	520 lm	Emergency lighting 3 hours duration Pro version DC operated central emergency lighting
910505103977	RC453B 28S/840 DLO L1195 W298 B30	-	DC operated central emergency lighting
910505105907	RC453B 28S/840 DLO L1200W300B30 SC	-	DC operated central emergency lighting
910505105908	RC453B 40S/UE840 DLO L1200W300B30 SC	-	DC operated central emergency lighting
910505105914	RC453B 28S/UE840 DLO L1200 W300 B30	-	DC operated central emergency lighting
910505105916	RC453B 28S/BU840 DLO L1200W300B30	-	DC operated central emergency lighting
910505103961	RC455B 36S/940 MCW-M L1200 W100 B40	-	DC operated central emergency lighting
910505103963	RC455B 40S/940 MCW-M L1200 W100 B40	-	DC operated central emergency lighting
910505105906	RC455B 36S/940 MCW-M L1200W100B40 SC	-	DC operated central emergency lighting
910505103968	RC455B 40S/940MCW-M U4W3 L1722 W150 B40	-	DC operated central emergency lighting
910505103916	RC455X 36S/940 DLO U4 W3 L1722 W100 B30	-	DC operated central emergency lighting
910505103920	RC455X 40S/TW9 DLO U4 W3 L1722 W100 B30	-	DC operated central emergency lighting

Order Code	Full Product Name	Emergency flux	Emergency lighting
910505103923	RC455X 36S/940 DLOU5 9016W3 L1722W185B40	-	DC operated central emergency lighting
910505103931	RC455X 36S/930 DLO U4 W3 L1495 W100 B30	-	DC operated central emergency lighting
910505103975	RC453B 36S/940 DLO U5 L1200 W300 B30	-	DC operated central emergency lighting

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910505103952	RC455B 36S/940 MXO U4 L1200 W100 B40	(0.38, 0.38) SDCM ≤3.0
910505103958	RC455B 40S/TW9 MXO U4 L1200 W100 B40	Tunable, SDCM ≤3.0
910505103960	RC455B 40S/940 MXO ELP3 W6L1722W150B40WT	(0.38, 0.38) SDCM ≤3.0
910505103949	RC455B 28S/TW9 MLO U4 L1720 W124 B40	Tunable, SDCM ≤3.0
910505103950	RC455B 36S/940 MLO U4 W3 L1722 W100 B40	(0.38, 0.38) SDCM ≤3.0
910505103974	RC453B42S/940DLO9010U4ELW3W4L1200W300B30	(0.38, 0.38) SDCM ≤3.0
910505103976	RC453B 36S/940 DLO9010U4ELW3L1200W300B30	(0.38, 0.38) SDCM ≤3.0
910505103957	RC455B 48S/940 MXO L1495 W100 B40	(0.38, 0.38) SDCM ≤3.0
910505103959	RC455B 28S/TWBU MCW-M U4 L1200 W100 B40	Tunable, SDCM ≤3.0
910505103965	RC455B 36S/940 MCW-M U4 L1200 W100 B40	(0.38, 0.38) SDCM ≤3.0
910505103978	RC453B 28S/UE840 MXO 9010 L1200 W300 B30	(0.38, 0.38) SDCM ≤3.0
910505103979	RC453B 28S/UE840MXO9010ELP3 L1200W300B30	(0.38, 0.38) SDCM ≤3.0
910505103951	RC455B 36S/940 MXO L1200 W100 B40	(0.38, 0.38) SDCM ≤3.0
910505103953	RC455B 40S/940 MXO L1200 W100 B40	(0.38, 0.38) SDCM ≤3.0
910505103954	RC455B 36S/940 MXO L1200 W125 B40	(0.38, 0.38) SDCM ≤3.0
910505103955	RC455B 36S/940 MXO L1200 W150 B40	(0.38, 0.38) SDCM ≤3.0
910505103956	RC455B 28S/940 MXO L1200 W150 B40	(0.38, 0.38) SDCM ≤3.0
910505105905	RC455B 40S/940 MXO L1200 W100 B40 SC	(0.38, 0.38) SDCM ≤3.0
910505103937	RC455B 40S/940 DLO U4 W3 L1722 W100 B30	(0.38, 0.38) SDCM ≤3.0
910505103940	RC455B 36S/940 DLO L1200 W100 B30	(0.38, 0.38) SDCM ≤3.0
910505103934	RC455X 36S/940 MCW-M U4 W3 L1722 W100B30	(0.38, 0.38) SDCM ≤3.0
910505105902	RC455B 36S/940 MCW-M U4W3L1722W100B30SC	(0.38, 0.38) SDCM ≤3.0
910505103926	RC455X 40S/940 DLO W3W2 L1700 W100 B30	(0.38, 0.38) SDCM ≤3.0
910505103927	RC455X 40S/940 DLO W3W2 L1497 W150 B30	(0.38, 0.38) SDCM ≤3.0
910505105901	RC455X 40S/940 DLO W3W2 L1497W150B30 SC	(0.38, 0.38) SDCM ≤3.0
910505105913	RC455B 40S/UE 840 DLO L1200 W100 B30	(0.38, 0.38) SDCM ≤3.0
910505103924	RC455X 36S/940 DLO U4 W3 L1722 W200 B40	(0.38, 0.38) SDCM ≤3.0
910505105911	RC455X 36S/UE840 DLO U4 W3 L1722W200B40	(0.38, 0.38) SDCM ≤3.0
910505103936	RC455B 36S/940 DLO 9010U4W3 L1722W150B30	(0.38, 0.38) SDCM ≤3.0
910505103985	RC453X 28S/UE840MXO9010 U4W3L1200W150B30	(0.38, 0.38) SDCM ≤3.0
910505103921	RC455X 28S/TWBU MCB-M U4 W3 L1722W100B30	Tunable, SDCM ≤3.0
910505103935	RC455X 36S/940 MCB-M U4 W3 L1722 W100B30	(0.38, 0.38) SDCM ≤3.0
910505103967	RC455B 40S/940 MCB-M W3W2 L1722 W150 B30	(0.38, 0.38) SDCM ≤3.0
910505103948	RC455B 28S/TW9 MLO U4 L1200 W100 B40	Tunable, SDCM ≤3.0
910505103918	RC455X 36S/940 DLO W5 L1722 W185 B30 WT	(0.38, 0.38) SDCM ≤3.0

Order Code	Full Product Name	Initial chromaticity
910505103930	RC455X 40S/940 DLO W3W2 L1497 W185 B30	(0.38, 0.38) SDCM ≤3.0
910505103932	RC455X 36S/940 MLO W5 L1722 W185 B30 WT	(0.38, 0.38) SDCM ≤3.0
910505105912	RC455B 36S/UE840 DLO W3W2 L1722 W185 B30	(0.38, 0.38) SDCM ≤3.0
910505103962	RC455B 36S/940 MCB-M L1200 W100 B40	(0.38, 0.38) SDCM ≤3.0
910505103964	RC455B 40S/940 MCB-M L1200 W100 B40	(0.38, 0.38) SDCM ≤3.0
910505103966	RC455B 36S/940 MCB-M U4 L1200 W100 B40	(0.38, 0.38) SDCM ≤3.0
910505103938	RC455B 40S/940 DLO W3W2 L1722 W150 B30	(0.38, 0.38) SDCM ≤3.0
910505103939	RC455B 36S/940 DLO W3W2 L1722 W185 B30	(0.38, 0.38) SDCM ≤3.0
910505103917	RC455X 40S/940 DLO W3W2 L1722 W150 B30	(0.38, 0.38) SDCM ≤3.0
910505103919	RC455X 40S/940 DLO W3W2 L1722 W150 B40	(0.38, 0.38) SDCM ≤3.0
910505103922	RC455X 40S/930 DLO W3W2 L1722 W150 B30	(0.43, 0.40) SDCM ≤3.0
910505103925	RC455X 36S/940 DLO W5 L1700 W150 B30 WT	(0.38, 0.38) SDCM ≤3.0
910505105910	RC455X 40S/UE840 DLO W3W2 L1722 W150 B40	(0.38, 0.38) SDCM ≤3.0
910505105918	RC455X 40S/BU840 DLO W3W2 L1722 W150 B30	(0.38, 0.38) SDCM ≤3.0
910505103973	RC453B 42S/940 DLO 9010 U4 L1200 W300B30	(0.38, 0.38) SDCM ≤3.0
910505103981	RC453B 40S/TW9 DLO U4 L1200 W300 B30	Tunable, SDCM ≤3.0
910505105909	RC453B 42S/940 DLO9010U4 L1200W300B30 SC	(0.38, 0.38) SDCM ≤3.0
910505105915	RC453B 42S/UE840 DLO9010 U4 L1200W300B30	(0.38, 0.38) SDCM ≤3.0
910505103984	RC453X 28S/840 DLO L1195 W298 B30	(0.38, 0.38) SDCM ≤3.0
910505103980	RC453B 28S/UE840 MXO9010ELP3L1200W150B30	(0.38, 0.38) SDCM ≤3.0
910505103982	RC453B 28S/UE840 MXO L1200 W150 B30	(0.38, 0.38) SDCM ≤3.0
910505103941	RC455B 28S/940 MLO L1200 W100 B40	(0.38, 0.38) SDCM ≤3.0
910505103942	RC455B 36S/940 MLO L1200 W100 B40	(0.38, 0.38) SDCM ≤3.0
910505103943	RC455B 36S/940 MLO L1200 W125 B40	(0.38, 0.38) SDCM ≤3.0
910505103944	RC455B 36S/940 MLO L1200 W150 B40	(0.38, 0.38) SDCM ≤3.0
910505103945	RC455B 40S/940 MLO L1200 W100 B40	(0.38, 0.38) SDCM ≤3.0
910505103946	RC455B 48S/940 MLO L1495 W100 B40	(0.38, 0.38) SDCM ≤3.0
910505103947	RC455B 28S/TW9 MLO L1200 W100 B40	Tunable, SDCM ≤3.0
910505105903	RC455B 28S/940 MLO L1200 W100 B40 SC	(0.38, 0.38) SDCM ≤3.0
910505105904	RC455B 40S/940 MLO L1200 W100 B40 SC	(0.38, 0.38) SDCM ≤3.0
910505105917	RC455B 40S/BU840 MLO L1200 W100 B40	(0.38, 0.38) SDCM ≤3.0
910505103971	RC453B 28S/840 DLO L1200 W300 B30	(0.38, 0.38) SDCM ≤3.0
910505103972	RC453B 28S/840 DLO 9010 ELP3L1200W300B30	(0.38, 0.38) SDCM ≤3.0
910505103977	RC453B 28S/840 DLO L1195 W298 B30	(0.38, 0.38) SDCM ≤3.0
910505105907	RC453B 28S/840 DLO L1200W300B30 SC	(0.38, 0.38) SDCM ≤3.0
910505105908	RC453B 40S/UE840 DLO L1200W300B30 SC	(0.38, 0.38) SDCM ≤3.0
910505105914	RC453B 28S/UE840 DLO L1200 W300 B30	(0.38, 0.38) SDCM ≤3.0
910505105916	RC453B 28S/BU840 DLO L1200W300B30	(0.38, 0.38) SDCM ≤3.0
910505103961	RC455B 36S/940 MCW-M L1200 W100 B40	(0.38, 0.38) SDCM ≤3.0
910505103963	RC455B 40S/940 MCW-M L1200 W100 B40	(0.38, 0.38) SDCM ≤3.0
910505105906	RC455B 36S/940 MCW-M L1200W100B40 SC	(0.38, 0.38) SDCM ≤3.0
910505103968	RC455B 40S/940MCW-M U4W3 L1722 W150 B40	(0.38, 0.38) SDCM ≤3.0

Order Code	Full Product Name	Initial chromaticity
910505103916	RC455X 36S/940 DLO U4 W3 L1722 W100 B30	(0.38, 0.38) SDCM ≤3.0
910505103920	RC455X 40S/TW9 DLO U4 W3 L1722 W100 B30	Tunable, SDCM ≤3.0
910505103923	RC455X 36S/940 DLOU5 9016W3 L1722W185B40	(0.38, 0.38) SDCM ≤3.0
910505103931	RC455X 36S/930 DLO U4 W3 L1495 W100 B30	(0.43, 0.40) SDCM ≤3.0
910505103975	RC453B 36S/940 DLO U5 L1200 W300 B30	(0.38, 0.38) SDCM ≤3.0


Product Data

Order Code	Full Product Name	Product family code
910505103952	RC455B 36S/940 MXO U4 L1200 W100 B40	RC455B
910505103958	RC455B 40S/TW9 MXO U4 L1200 W100 B40	RC455B
910505103960	RC455B 40S/940 MXO ELP3 W6L1722W150B40WT	RC455B
910505103949	RC455B 28S/TW9 MLO U4 L1720 W124 B40	RC455B
910505103950	RC455B 36S/940 MLO U4 W3 L1722 W100 B40	RC455B
910505103974	RC453B42S/940DLO9010U4ELW3W4L1200W300B30	RC455B
910505103976	RC453B 36S/940 DLO9010U4ELW3L1200W300B30	RC455B
910505103957	RC455B 48S/940 MXO L1495 W100 B40	RC455B
910505103959	RC455B 28S/TWBU MCW-M U4 L1200 W100 B40	RC455B
910505103965	RC455B 36S/940 MCW-M U4 L1200 W100 B40	RC455B
910505103978	RC453B 28S/UE840 MXO 9010 L1200 W300 B30	RC455B
910505103979	RC453B 28S/UE840MXO9010ELP3 L1200W300B30	RC455B
910505103951	RC455B 36S/940 MXO L1200 W100 B40	RC455B
910505103953	RC455B 40S/940 MXO L1200 W100 B40	RC455B
910505103954	RC455B 36S/940 MXO L1200 W125 B40	RC455B
910505103955	RC455B 36S/940 MXO L1200 W150 B40	RC455B
910505103956	RC455B 28S/940 MXO L1200 W150 B40	RC455B
910505105905	RC455B 40S/940 MXO L1200 W100 B40 SC	RC455B
910505103937	RC455B 40S/940 DLO U4 W3 L1722 W100 B30	RC455B
910505103940	RC455B 36S/940 DLO L1200 W100 B30	RC455B
910505103934	RC455X 36S/940 MCW-M U4 W3 L1722 W100B30	RC455B
910505105902	RC455B 36S/940 MCW-M U4W3L1722W100B30SC	RC455X
910505103926	RC455X 40S/940 DLO W3W2 L1700 W100 B30	RC455B
910505103927	RC455X 40S/940 DLO W3W2 L1497 W150 B30	RC455B
910505105901	RC455X 40S/940 DLO W3W2 L1497W150B30 SC	RC455X
910505105913	RC455B 40S/UE 840 DLO L1200 W100 B30	RC455B
910505103924	RC455X 36S/940 DLO U4 W3 L1722 W200 B40	RC455B
910505105911	RC455X 36S/UE840 DLO U4 W3 L1722W200B40	RC455X
910505103936	RC455B 36S/940 DLO 9010U4W3 L1722W150B30	RC455B
910505103985	RC453X 28S/UE840MXO9010 U4W3L1200W150B30	RC455B
910505103921	RC455X 28S/TWBU MCB-M U4 W3 L1722W100B30	RC455B
910505103935	RC455X 36S/940 MCB-M U4 W3 L1722 W100B30	RC455B
910505103967	RC455B 40S/940 MCB-M W3W2 L1722 W150 B30	RC455B

Order Code	Full Product Name	Product family code
910505103948	RC455B 28S/TW9 MLO U4 L1200 W100 B40	RC455B
910505103918	RC455X 36S/940 DLO W5 L1722 W185 B30 WT	RC455B
910505103930	RC455X 40S/940 DLO W3W2 L1497 W185 B30	RC455B
910505103932	RC455X 36S/940 MLO W5 L1722 W185 B30 WT	RC455B
910505105912	RC455B 36S/UE840 DLO W3W2 L1722 W185 B30	RC455B
910505103962	RC455B 36S/940 MCB-M L1200 W100 B40	RC455B
910505103964	RC455B 40S/940 MCB-M L1200 W100 B40	RC455B
910505103966	RC455B 36S/940 MCB-M U4 L1200 W100 B40	RC455B
910505103938	RC455B 40S/940 DLO W3W2 L1722 W150 B30	RC455B
910505103939	RC455B 36S/940 DLO W3W2 L1722 W185 B30	RC455B
910505103917	RC455X 40S/940 DLO W3W2 L1722 W150 B30	RC455B
910505103919	RC455X 40S/940 DLO W3W2 L1722 W150 B40	RC455B
910505103922	RC455X 40S/930 DLO W3W2 L1722 W150 B30	RC455B
910505103925	RC455X 36S/940 DLO W5 L1700 W150 B30 WT	RC455B
910505105910	RC455X 40S/UE840 DLO W3W2 L1722 W150 B40	RC455X
910505105918	RC455X 40S/BU840 DLO W3W2 L1722 W150 B30	RC455X
910505103973	RC453B 42S/940 DLO 9010 U4 L1200 W300B30	RC455B
910505103981	RC453B 40S/TW9 DLO U4 L1200 W300 B30	RC455B
910505105909	RC453B 42S/940 DLO9010U4 L1200W300B30 SC	RC453B
910505105915	RC453B 42S/UE840 DLO9010 U4 L1200W300B30	RC453B
910505103984	RC453X 28S/840 DLO L1195 W298 B30	RC455B
910505103980	RC453B 28S/UE840 MXO9010ELP3L1200W150B30	RC455B
910505103982	RC453B 28S/UE840 MXO L1200 W150 B30	RC455B
910505103941	RC455B 28S/940 MLO L1200 W100 B40	RC455B
910505103942	RC455B 36S/940 MLO L1200 W100 B40	RC455B
910505103943	RC455B 36S/940 MLO L1200 W125 B40	RC455B
910505103944	RC455B 36S/940 MLO L1200 W150 B40	RC455B
910505103945	RC455B 40S/940 MLO L1200 W100 B40	RC455B
910505103946	RC455B 48S/940 MLO L1495 W100 B40	RC455B
910505103947	RC455B 28S/TW9 MLO L1200 W100 B40	RC455B
910505105903	RC455B 28S/940 MLO L1200 W100 B40 SC	RC455B
910505105904	RC455B 40S/940 MLO L1200 W100 B40 SC	RC455B
910505105917	RC455B 40S/BU840 MLO L1200 W100 B40	RC455B
910505103971	RC453B 28S/840 DLO L1200 W300 B30	RC455B
910505103972	RC453B 28S/840 DLO 9010 ELP3L1200W300B30	RC455B
910505103977	RC453B 28S/840 DLO L1195 W298 B30	RC455B
910505105907	RC453B 28S/840 DLO L1200W300B30 SC	RC453B
910505105908	RC453B 40S/UE840 DLO L1200W300B30 SC	RC453B
910505105914	RC453B 28S/UE840 DLO L1200 W300 B30	RC453B
910505105916	RC453B 28S/BU840 DLO L1200W300B30	RC453B
910505103961	RC455B 36S/940 MCW-M L1200 W100 B40	RC455B
910505103963	RC455B 40S/940 MCW-M L1200 W100 B40	RC455B

Order Code	Full Product Name	Product family code
910505105906	RC455B 36S/940 MCW-M L1200W100B40 SC	RC455B
910505103968	RC455B 40S/940MCW-M U4W3 L1722 W150 B40	RC455B
910505103916	RC455X 36S/940 DLO U4 W3 L1722 W100 B30	RC455B
910505103920	RC455X 40S/TW9 DLO U4 W3 L1722 W100 B30	RC455B
910505103923	RC455X 36S/940 DLOU5 9016W3 L1722W185B40	RC455B
910505103931	RC455X 36S/930 DLO U4 W3 L1495 W100 B30	RC455B
910505103975	RC453B 36S/940 DLO U5 L1200 W300 B30	RC455B


Polar normal diagrams



RC450BI - 910505103949

RC450BI - 910505103973


RC450BI - 910505103943




RC450BI - 910505103948

RC450BI - 910505103918


RC450BI - 910505103941




RC450BI - 910505103946




RC450BI - 910505103921




RC450BI - 910505103960




RC450BI - 910505103980




RC450BI - 910505103985




RC450BI - 910505103917




RC450BI - 910505103942




RC450BI - 910505103955




RC450BI - 910505103919




RC450BI - 910505103974




RC450BI - 910505103932




RC450BI - 910505103981




RC450BI - 910505103931




RC450BI - 910505103916




RC450BI - 910505103926




RC450BI - 910505103954




RC450BI - 910505103920




RC450BI - 910505103978




RC450BI - 910505103944




RC450BI - 910505103958




RC450BI - 910505103967




RC450BI - 910505103953




RC450BI - 910505103947




RC450BI - 910505103964




RC450BI - 910505103945




RC450BI - 910505103957




RC450BI - 910505103950




RC450BI - 910505103952




RC450BI - 910505103956




RC450BI - 910505103979




RC450BI - 910505103951




RC450BI - 910505103982




RC450BI - 910505103961




RC450BI - 910505103962




RC450BI - 910505103927




RC450BI - 910505103940




RC450BI - 910505103971




RC450BI - 910505103972




RC450BI - 910505103977




RC450BI - 910505103984




RC450BI - 910505103976




RC450BI - 910505103975




RC450BI - 910505103966




RC450BI - 910505103922




RC450BI - 910505103934




RC450BI - 910505103924




RC450BI - 910505103968




RC450BI - 910505103925




RC450BI - 910505103937




RC450BI - 910505103923




RC450BI - 910505103936




RC450BI - 910505103938




RC450BI - 910505103930




RC450BI - 910505103935




RC450BI - 910505103965




RC450BI - 910505103963




RC450BI - 910505103939




RC450BI - 910505103959




RC450BI - 910505105901




RC450BI - 910505105902




RC450BI - 910505105904




RC450BI - 910505105903




RC450BI - 910505105909




RC450BI - 910505105905




RC450BI - 910505105907




RC450BI - 910505105906




910505105908




910505105910




910505105915




910505105917




910505105911




910505105913




910505105912



910505105914



910505105916



910505105918