

Deep recessed & Anti-dazzle, Wide Dimming Range, High Color Rendering

Smartbright Dimmable Spot

The SmartBright Dimmable Spot comes offering reliable lighting performance with smooth dimming control, suitable for diversified applications. Deep recessed design, 0-10V dimming driver and high color rendering can attract you more with its elegant design.

Benefits

- Deep recessed & Anti-dazzle
- Smooth dimming control (0-10V)
- High color rendering
- Narrow-edge ring design

Features


- Power: 7W, 9W, 12W and 15W
- 4 CCT: 2700K, 3000K, 3500K (only for 9W) and 4000K
- Input voltage is 220-240V
- CRI90
- 0-10V dimming
- Power factor: >0.9
- Working temperature: -20℃ to +40℃

Smartbright Dimmable Spot

Application

- Residential
- Hospitality
- Retail
- Architectural light
- High-end restaurants
- High-end clubs
- Hotels

Dimensional drawing



Light Technical	
Color rendering index (CRI)	>90
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Optical cover type	Lens
Approval and Application	
Ambient temperature range	-20 to +40 °C
CE mark	No
Flammability mark	For mounting on normally flammable surfaces
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

Light Technical (1/2)

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401803285	RS051B LED4 24D/927 D55 DIM GM	-	2700 K	65 lm/W	455 lm
911401803385	RS051B LED4 24D/930 D55 DIM GM	-	3000 K	70 lm/W	490 lm
911401803485	RS051B LED4 24D/940 D55 DIM GM	-	4000 K	75 lm/W	525 lm
911401803585	RS051B LED4 36D/927 D55 DIM GM	-	2700 K	65 lm/W	455 lm
911401803685	RS051B LED4 36D/930 D55 DIM GM	-	3000 K	70 lm/W	490 lm
911401803785	RS051B LED4 36D/940 D55 DIM GM	-	4000 K	75 lm/W	525 lm
911401803885	RS051B LED4 50D/930 D55 DIM GM	-	3000 K	70 lm/W	490 lm
911401803985	RS051B LED4 50D/940 D55 DIM GM	-	4000 K	75 lm/W	525 lm
911401804085	RS051B LED6 24D/927 D75 DIM GM	-	2700 K	70 lm/W	630 lm
911401804185	RS051B LED6 24D/930 D75 DIM GM	-	3000 K	75 lm/W	675 lm
911401804285	RS051B LED6 24D/935 D75 DIM GM	-	3500 K	77 lm/W	695 lm
911401804385	RS051B LED6 24D/940 D75 DIM GM	-	4000 K	80 lm/W	720 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401804485	RS051B LED6 36D/927 D75 DIM GM	-	2700 K	70 lm/W	630 lm
911401804585	RS051B LED6 36D/930 D75 DIM GM	-	3000 K	75 lm/W	675 lm
911401804685	RS051B LED6 36D/940 D75 DIM GM	-	4000 K	80 lm/W	720 lm
911401804785	RS051B LED6 50D/930 D75 DIM GM	-	3000 K	70 lm/W	630 lm
911401804885	RS051B LED6 50D/935 D75 DIM GM	-	3500 K	72 lm/W	650 lm
911401804985	RS051B LED6 50D/940 D75 DIM GM	-	4000 K	73 lm/W	660 lm
911401805085	RS051B LED8 24D/930 D75 DIM GM	-	3000 K	75 lm/W	900 lm
911401805185	RS051B LED8 24D/940 D75 DIM GM	120 degree(s)	4000 K	100 lm/W	650 lm
911401805285	RS051B LED8 36D/930 D75 DIM GM	-	3000 K	75 lm/W	900 lm
911401805385	RS051B LED8 36D/940 D75 DIM GM	-	4000 K	80 lm/W	960 lm
911401805485	RS051B LED8 50D/930 D75 DIM GM	-	3000 K	70 lm/W	840 lm
911401805585	RS051B LED8 50D/940 D75 DIM GM	-	4000 K	73 lm/W	875 lm
911401805685	RS051B LED10 24D/930 D95 DIM GM	-	3000 K	70 lm/W	1,050 lm
911401805785	RS051B LED10 24D/940 D95 DIM GM	-	4000 K	73 lm/W	1,095 lm
911401805885	RS051B LED10 36D/930 D95 DIM GM	-	3000 K	70 lm/W	1,050 lm
911401805985	RS051B LED10 36D/940 D95 DIM GM	-	4000 K	73 lm/W	1,095 lm
911401806085	RS051B LED10 50D/930 D95 DIM GM	-	3000 K	70 lm/W	1,050 lm
911401806185	RS051B LED10 50D/940 D95 DIM GM	-	4000 K	75 lm/W	1,125 lm

Light Technical (2/2)

Order Code	Full Product Name	Optic type
911401803285	RS051B LED4 24D/927 D55 DIM GM	-
911401803385	RS051B LED4 24D/930 D55 DIM GM	-
911401803485	RS051B LED4 24D/940 D55 DIM GM	-
911401803585	RS051B LED4 36D/927 D55 DIM GM	-
911401803685	RS051B LED4 36D/930 D55 DIM GM	-
911401803785	RS051B LED4 36D/940 D55 DIM GM	-
911401803885	RS051B LED4 50D/930 D55 DIM GM	-
911401803985	RS051B LED4 50D/940 D55 DIM GM	-
911401804085	RS051B LED6 24D/927 D75 DIM GM	-
911401804185	RS051B LED6 24D/930 D75 DIM GM	-

Order Code	Full Product Name	Optic type
911401804285	RS051B LED6 24D/935 D75 DIM GM	-
911401804385	RS051B LED6 24D/940 D75 DIM GM	-
911401804485	RS051B LED6 36D/927 D75 DIM GM	-
911401804585	RS051B LED6 36D/930 D75 DIM GM	-
911401804685	RS051B LED6 36D/940 D75 DIM GM	-
911401804785	RS051B LED6 50D/930 D75 DIM GM	-
911401804885	RS051B LED6 50D/935 D75 DIM GM	-
911401804985	RS051B LED6 50D/940 D75 DIM GM	-
911401805085	RS051B LED8 24D/930 D75 DIM GM	-
911401805185	RS051B LED8 24D/940 D75 DIM GM	Beam angle 90°

Smartbright Dimmable Spot

Order Code	Full Product Name	Optic type
911401805285	RS051B LED8 36D/930 D75 DIM GM	-
911401805385	RS051B LED8 36D/940 D75 DIM GM	-
911401805485	RS051B LED8 50D/930 D75 DIM GM	-
911401805585	RS051B LED8 50D/940 D75 DIM GM	-
911401805685	RS051B LED10 24D/930 D95 DIM GM	-

Order Code	Full Product Name	Optic type
911401805785	RS051B LED10 24D/940 D95 DIM GM	-
911401805885	RS051B LED10 36D/930 D95 DIM GM	-
911401805985	RS051B LED10 36D/940 D95 DIM GM	-
911401806085	RS051B LED10 50D/930 D95 DIM GM	-
911401806185	RS051B LED10 50D/940 D95 DIM GM	-

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401803285	RS051B LED4 24D/927 D55 DIM GM	7 W
911401803385	RS051B LED4 24D/930 D55 DIM GM	7 W
911401803485	RS051B LED4 24D/940 D55 DIM GM	7 W
911401803585	RS051B LED4 36D/927 D55 DIM GM	7 W
911401803685	RS051B LED4 36D/930 D55 DIM GM	7 W
911401803785	RS051B LED4 36D/940 D55 DIM GM	7 W
911401803885	RS051B LED4 50D/930 D55 DIM GM	7 W
911401803985	RS051B LED4 50D/940 D55 DIM GM	7 W
911401804085	RS051B LED6 24D/927 D75 DIM GM	9 W
911401804185	RS051B LED6 24D/930 D75 DIM GM	9 W
911401804285	RS051B LED6 24D/935 D75 DIM GM	9 W
911401804385	RS051B LED6 24D/940 D75 DIM GM	9 W
911401804485	RS051B LED6 36D/927 D75 DIM GM	9 W
911401804585	RS051B LED6 36D/930 D75 DIM GM	9 W
911401804685	RS051B LED6 36D/940 D75 DIM GM	9 W

Order Code	Full Product Name	Power Consumption
911401804785	RS051B LED6 50D/930 D75 DIM GM	9 W
911401804885	RS051B LED6 50D/935 D75 DIM GM	9 W
911401804985	RS051B LED6 50D/940 D75 DIM GM	9 W
911401805085	RS051B LED8 24D/930 D75 DIM GM	12 W
911401805185	RS051B LED8 24D/940 D75 DIM GM	6.5 W
911401805285	RS051B LED8 36D/930 D75 DIM GM	12 W
911401805385	RS051B LED8 36D/940 D75 DIM GM	12 W
911401805485	RS051B LED8 50D/930 D75 DIM GM	12 W
911401805585	RS051B LED8 50D/940 D75 DIM GM	12 W
911401805685	RS051B LED10 24D/930 D95 DIM GM	15 W
911401805785	RS051B LED10 24D/940 D95 DIM GM	15 W
911401805885	RS051B LED10 36D/930 D95 DIM GM	15 W
911401805985	RS051B LED10 36D/940 D95 DIM GM	15 W
911401806085	RS051B LED10 50D/930 D95 DIM GM	15 W
911401806185	RS051B LED10 50D/940 D95 DIM GM	15 W

Mechanical and Housing

Order Code	Full Product Name	Housing Color	Mech. impact protection code	Ingress protection code
911401803285	RS051B LED4 24D/927 D55 DIM GM	Black	IK03	IP20
911401803385	RS051B LED4 24D/930 D55 DIM GM	Black	IK03	IP20
911401803485	RS051B LED4 24D/940 D55 DIM GM	Black	IK03	IP20
911401803585	RS051B LED4 36D/927 D55 DIM GM	Black	IK03	IP20
911401803685	RS051B LED4 36D/930 D55 DIM GM	Black	IK03	IP20
911401803785	RS051B LED4 36D/940 D55 DIM GM	Black	IK03	IP20
911401803885	RS051B LED4 50D/930 D55 DIM GM	Black	IK03	IP20
911401803985	RS051B LED4 50D/940 D55 DIM GM	Black	IK03	IP20
911401804085	RS051B LED6 24D/927 D75 DIM GM	Black	IK03	IP20
911401804185	RS051B LED6 24D/930 D75 DIM GM	Black	IK03	IP20

Order Code	Full Product Name	Housing Color	Mech. impact protection code	Ingress protection code
911401804285	RS051B LED6 24D/935 D75 DIM GM	Black	IK03	IP20
911401804385	RS051B LED6 24D/940 D75 DIM GM	Black	IK03	IP20
911401804485	RS051B LED6 36D/927 D75 DIM GM	Black	IK03	IP20
911401804585	RS051B LED6 36D/930 D75 DIM GM	Black	IK03	IP20
911401804685	RS051B LED6 36D/940 D75 DIM GM	Black	IK03	IP20
911401804785	RS051B LED6 50D/930 D75 DIM GM	Black	IK03	IP20
911401804885	RS051B LED6 50D/935 D75 DIM GM	Black	IK03	IP20
911401804985	RS051B LED6 50D/940 D75 DIM GM	Black	IK03	IP20
911401805085	RS051B LED8 24D/930 D75 DIM GM	Black	IK03	IP20
911401805185	RS051B LED8 24D/940 D75 DIM GM	White	IK02	IP20/44

Smartbright Dimmable Spot

Order Code	Full Product Name	Housing Color	Mech. impact protection code	Ingress protection code
911401805285	RS051B LED8 36D/930 D75 DIM GM	Black	IK03	IP20
911401805385	RS051B LED8 36D/940 D75 DIM GM	Black	IK03	IP20
911401805485	RS051B LED8 50D/930 D75 DIM GM	Black	IK03	IP20
911401805585	RS051B LED8 50D/940 D75 DIM GM	Black	IK03	IP20
911401805685	RS051B LED10 24D/930 D95 DIM GM	Black	IK03	IP20

Order Code	Full Product Name	Housing Color	Mech. impact protection code	Ingress protection code
911401805785	RS051B LED10 24D/940 D95 DIM GM	Black	IK03	IP20
911401805885	RS051B LED10 36D/930 D95 DIM GM	Black	IK03	IP20
911401805985	RS051B LED10 36D/940 D95 DIM GM	Black	IK03	IP20
911401806085	RS051B LED10 50D/930 D95 DIM GM	Black	IK03	IP20
911401806185	RS051B LED10 50D/940 D95 DIM GM	Black	IK03	IP20

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
911401803285	RS051B LED4 24D/927 D55 DIM GM	(0.46, 0.41) SDCM <5
911401803385	RS051B LED4 24D/930 D55 DIM GM	(0.43, 0.40) SDCM <5
911401803485	RS051B LED4 24D/940 D55 DIM GM	(0.38, 0.38) SDCM <5
911401803585	RS051B LED4 36D/927 D55 DIM GM	(0.46, 0.41) SDCM <5
911401803685	RS051B LED4 36D/930 D55 DIM GM	(0.43, 0.40) SDCM <5
911401803785	RS051B LED4 36D/940 D55 DIM GM	(0.38, 0.38) SDCM <5
911401803885	RS051B LED4 50D/930 D55 DIM GM	(0.43, 0.40) SDCM <5
911401803985	RS051B LED4 50D/940 D55 DIM GM	(0.38, 0.38) SDCM <5
911401804085	RS051B LED6 24D/927 D75 DIM GM	(0.46, 0.41) SDCM <5
911401804185	RS051B LED6 24D/930 D75 DIM GM	(0.43, 0.40) SDCM <5
911401804285	RS051B LED6 24D/935 D75 DIM GM	(0.41, 0.40) SDCM <5
911401804385	RS051B LED6 24D/940 D75 DIM GM	(0.38, 0.38) SDCM <5
911401804485	RS051B LED6 36D/927 D75 DIM GM	(0.46, 0.41) SDCM <5
911401804585	RS051B LED6 36D/930 D75 DIM GM	(0.43, 0.40) SDCM <5
911401804685	RS051B LED6 36D/940 D75 DIM GM	(0.38, 0.38) SDCM <5

Order Code	Full Product Name	Initial chromaticity
911401804785	RS051B LED6 50D/930 D75 DIM GM	(0.43, 0.40) SDCM <5
911401804885	RS051B LED6 50D/935 D75 DIM GM	(0.41, 0.40) SDCM <5
911401804985	RS051B LED6 50D/940 D75 DIM GM	(0.38, 0.38) SDCM <5
911401805085	RS051B LED8 24D/930 D75 DIM GM	(0.43, 0.40) SDCM <5
911401805185	RS051B LED8 24D/940 D75 DIM GM	(0.38212,0.38031) SDCM<3
911401805285	RS051B LED8 36D/930 D75 DIM GM	(0.43, 0.40) SDCM <5
911401805385	RS051B LED8 36D/940 D75 DIM GM	(0.38, 0.38) SDCM <5
911401805485	RS051B LED8 50D/930 D75 DIM GM	(0.43, 0.40) SDCM <5
911401805585	RS051B LED8 50D/940 D75 DIM GM	(0.38, 0.38) SDCM <5
911401805685	RS051B LED10 24D/930 D95 DIM GM	(0.43, 0.40) SDCM <5
911401805785	RS051B LED10 24D/940 D95 DIM GM	(0.38, 0.38) SDCM <5
911401805885	RS051B LED10 36D/930 D95 DIM GM	(0.43, 0.40) SDCM <5
911401805985	RS051B LED10 36D/940 D95 DIM GM	(0.38, 0.38) SDCM <5
911401806085	RS051B LED10 50D/930 D95 DIM GM	(0.43, 0.40) SDCM <5
911401806185	RS051B LED10 50D/940 D95 DIM GM	(0.38, 0.38) SDCM <5

© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.