



Small but comprehensive

GreenUp hospitality spot

GreenUp hospitality spot is a small cut out spot but with comprehensive offers. It offers flexible wattages for different indoor applications, such as retail and hospitality. This family delivers high CRI90 and 3 different beam angles to perfectly fit the light requirement of indoor retail and hospitality applications.

Benefits

- High color rendering index helps better visual comfort in hospitality retail applications
- 3 different beams facilitate the lighting designers for wide lighting applications
- Tilttable angle for easier installation options
- Multiple lumen output and wattages to provide more choices for the designers

Features

- CRI 90 high color rendering index available
- Narrow/medium/wide beams options
- 30 degree tilt angle
- 5/7/9/12w options are available

Application

- Retail and Hospitality




GreenUp hospitality spot

Versions



GreenUp Hospitality

Dimensional drawing



Product details

GreenUp hospitality accent



GreenUp hospitality spot

Light Technical

Color rendering index (CRI)	>90
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220 to 240 V
Line Frequency	0/50/60 Hz
Mechanical and Housing	
Optical cover type	-
Housing Color	Aluminum and gray
Mech. impact protection code	IK03
Ingress protection code	IP20
Approval and Application	
CE mark	No
Flammability mark	-
Initial Performance (IEC Compliant)	
Initial chromaticity	-
Luminous flux tolerance	+/-10%

Light Technical

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux
		Temperature (Nom)	(rated) (Nom)	
911401536902	RS318B P5 927 PSU-E NB S	2700 K	96 lm/W	70 lm
911401537002	RS318B P5 927 PSU-E MB S	2700 K	96 lm/W	75 lm
911401537102	RS318B P5 927 PSU-E WB S	2700 K	96 lm/W	80 lm
911401537302	RS318B P5 930 PSU-E MB S	3000 K	101 lm/W	80 lm
911401537402	RS318B P5 930 PSU-E WB S	3000 K	101 lm/W	80 lm
911401537502	RS318B P7 927 PSU-E NB S	2700 K	96 lm/W	65 lm
911401537602	RS318B P7 927 PSU-E MB S	2700 K	96 lm/W	80 lm
911401537902	RS318B P7 930 PSU-E MB S	3000 K	101 lm/W	80 lm
911401538002	RS318B P7 930 PSU-E WB S	3000 K	101 lm/W	80 lm
911401538202	RS318B P9 927 PSU-E MB S	2700 K	96 lm/W	75 lm
911401538502	RS318B P9 930 PSU-E MB S	3000 K	101 lm/W	75 lm
911401538602	RS318B P9 930 PSU-E WB S	3000 K	101 lm/W	75 lm
911401538702	RS318B P12 927 PSU-E NB S	2700 K	96 lm/W	60 lm
911401538802	RS318B P12 927 PSU-E MB S	2700 K	96 lm/W	70 lm
911401538902	RS318B P12 927 PSU-E WB S	2700 K	96 lm/W	70 lm
911401593422	RS318B P9 930 PSR-E MB S	3000 K	101 lm/W	70 lm
911401593522	RS318B P9 930 PSR-E WB S	3000 K	101 lm/W	70 lm
911401504832	RS318B P12 927 PSU-E WB D	2700 K	96 lm/W	720 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401536902	RS318B P5 927 PSU-E NB S	5 W
911401537002	RS318B P5 927 PSU-E MB S	5 W
911401537102	RS318B P5 927 PSU-E WB S	5 W
911401537302	RS318B P5 930 PSU-E MB S	5 W
911401537402	RS318B P5 930 PSU-E WB S	5 W
911401537502	RS318B P7 927 PSU-E NB S	7 W
911401537602	RS318B P7 927 PSU-E MB S	7 W
911401537902	RS318B P7 930 PSU-E MB S	7 W
911401538002	RS318B P7 930 PSU-E WB S	7 W

Order Code	Full Product Name	Power Consumption
911401538202	RS318B P9 927 PSU-E MB S	9 W
911401538502	RS318B P9 930 PSU-E MB S	9 W
911401538602	RS318B P9 930 PSU-E WB S	9 W
911401538702	RS318B P12 927 PSU-E NB S	12 W
911401538802	RS318B P12 927 PSU-E MB S	12 W
911401538902	RS318B P12 927 PSU-E WB S	12 W
911401593422	RS318B P9 930 PSR-E MB S	9 W
911401593522	RS318B P9 930 PSR-E WB S	9 W
911401504832	RS318B P12 927 PSU-E WB D	12 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401536902	RS318B P5 927 PSU-E NB S	No
911401537002	RS318B P5 927 PSU-E MB S	No
911401537102	RS318B P5 927 PSU-E WB S	No
911401537302	RS318B P5 930 PSU-E MB S	No
911401537402	RS318B P5 930 PSU-E WB S	No
911401537502	RS318B P7 927 PSU-E NB S	No
911401537602	RS318B P7 927 PSU-E MB S	No
911401537902	RS318B P7 930 PSU-E MB S	No
911401538002	RS318B P7 930 PSU-E WB S	No

Order Code	Full Product Name	Dimmable
911401538202	RS318B P9 927 PSU-E MB S	No
911401538502	RS318B P9 930 PSU-E MB S	No
911401538602	RS318B P9 930 PSU-E WB S	No
911401538702	RS318B P12 927 PSU-E NB S	No
911401538802	RS318B P12 927 PSU-E MB S	No
911401538902	RS318B P12 927 PSU-E WB S	No
911401593422	RS318B P9 930 PSR-E MB S	Yes
911401593522	RS318B P9 930 PSR-E WB S	Yes
911401504832	RS318B P12 927 PSU-E WB D	No

Approval and Application

GreenUp hospitality spot

Order Code	Full Product Name	Ambient temperature range
911401536902	RS318B P5 927 PSU-E NB S	+20 to +40 °C
911401537002	RS318B P5 927 PSU-E MB S	+20 to +40 °C
911401537102	RS318B P5 927 PSU-E WB S	+20 to +40 °C
911401537302	RS318B P5 930 PSU-E MB S	+20 to +40 °C
911401537402	RS318B P5 930 PSU-E WB S	+20 to +40 °C
911401537502	RS318B P7 927 PSU-E NB S	+20 to +40 °C
911401537602	RS318B P7 927 PSU-E MB S	+20 to +40 °C
911401537902	RS318B P7 930 PSU-E MB S	+20 to +40 °C
911401538002	RS318B P7 930 PSU-E WB S	+20 to +40 °C

Order Code	Full Product Name	Ambient temperature range
911401538202	RS318B P9 927 PSU-E MB S	+20 to +40 °C
911401538502	RS318B P9 930 PSU-E MB S	+20 to +40 °C
911401538602	RS318B P9 930 PSU-E WB S	+20 to +40 °C
911401538702	RS318B P12 927 PSU-E NB S	+20 to +40 °C
911401538802	RS318B P12 927 PSU-E MB S	+20 to +40 °C
911401538902	RS318B P12 927 PSU-E WB S	+20 to +40 °C
911401593422	RS318B P9 930 PSR-E MB S	+20 to +40 °C
911401593522	RS318B P9 930 PSR-E WB S	+20 to +40 °C
911401504832	RS318B P12 927 PSU-E WB D	-20 to +40 °C

