



# Small but comprehensive

## GreenUp hospitality spot

GreenUp hospitality spot is a small cut out spot but with comprehensive offers. It offers flexible wattages for different indoor applications, such as retail and hospitality. This family delivers high CRI90 and 3 different beam angles to perfectly fit the light requirement of indoor retail and hospitality applications.

### Benefits

- High color rendering index helps better visual comfort in hospitality retail applications
- 3 different beams facilitate the lighting designers for wide lighting applications
- Tilttable angle for easier installation options
- Multiple lumen output and wattages to provide more choices for the designers

### Features

- CRI 90 high color rendering index available
- Narrow/medium/wide beams options
- 30 degree tilt angle
- 5/7/9/12w options are available

### Application

- Retail and Hospitality




# GreenUp hospitality spot

## Versions



GreenUp Hospitality

## Dimensional drawing



## Product details

GreenUp hospitality accent



| Light Technical                     |                   |
|-------------------------------------|-------------------|
| Color rendering index (CRI)         | >90               |
| Operating and Electrical            |                   |
| Protection class IEC                | Safety class II   |
| Input Voltage                       | 220 to 240 V      |
| Line Frequency                      | 0/50/60 Hz        |
| Mechanical and Housing              |                   |
| Optical cover type                  | -                 |
| Housing Color                       | Aluminum and gray |
| Mech. impact protection code        | IK03              |
| Ingress protection code             | IP20              |
| Approval and Application            |                   |
| CE mark                             | No                |
| Flammability mark                   | -                 |
| Initial Performance (IEC Compliant) |                   |
| Initial chromaticity                | -                 |
| Luminous flux tolerance             | +/-10%            |

Light Technical

| Order Code | Full Product Name         | Correlated Color  | Luminous Efficacy (rated) |               |
|------------|---------------------------|-------------------|---------------------------|---------------|
|            |                           | Temperature (Nom) | (Nom)                     | Luminous Flux |
| 53314199   | RS318B P5 927 PSU-E NB S  | 2700 K            | 96 lm/W                   | 70 lm         |
| 53375299   | RS318B P5 927 PSU-E MB S  | 2700 K            | 96 lm/W                   | 75 lm         |
| 53361599   | RS318B P5 927 PSU-E WB S  | 2700 K            | 96 lm/W                   | 80 lm         |
| 53320299   | RS318B P5 930 PSU-E MB S  | 3000 K            | 101 lm/W                  | 80 lm         |
| 53315899   | RS318B P5 930 PSU-E WB S  | 3000 K            | 101 lm/W                  | 80 lm         |
| 53346299   | RS318B P7 927 PSU-E NB S  | 2700 K            | 96 lm/W                   | 65 lm         |
| 53281699   | RS318B P7 927 PSU-E MB S  | 2700 K            | 96 lm/W                   | 80 lm         |
| 53362299   | RS318B P7 930 PSU-E MB S  | 3000 K            | 101 lm/W                  | 80 lm         |
| 53347999   | RS318B P7 930 PSU-E WB S  | 3000 K            | 101 lm/W                  | 80 lm         |
| 53328899   | RS318B P9 927 PSU-E MB S  | 2700 K            | 96 lm/W                   | 75 lm         |
| 53303599   | RS318B P9 930 PSU-E MB S  | 3000 K            | 101 lm/W                  | 75 lm         |
| 53298499   | RS318B P9 930 PSU-E WB S  | 3000 K            | 101 lm/W                  | 75 lm         |
| 53316599   | RS318B P12 927 PSU-E NB S | 2700 K            | 96 lm/W                   | 60 lm         |
| 53348699   | RS318B P12 927 PSU-E MB S | 2700 K            | 96 lm/W                   | 70 lm         |
| 53283099   | RS318B P12 927 PSU-E WB S | 2700 K            | 96 lm/W                   | 70 lm         |
| 53381399   | RS318B P9 930 PSR-E MB S  | 3000 K            | 101 lm/W                  | 70 lm         |
| 53366099   | RS318B P9 930 PSR-E WB S  | 3000 K            | 101 lm/W                  | 70 lm         |
| 53341799   | RS318B P12 927 PSU-E WB D | 2700 K            | 96 lm/W                   | 720 lm        |

Operating and Electrical

| Order Code | Full Product Name        | Power Consumption |
|------------|--------------------------|-------------------|
| 53314199   | RS318B P5 927 PSU-E NB S | 5 W               |
| 53375299   | RS318B P5 927 PSU-E MB S | 5 W               |
| 53361599   | RS318B P5 927 PSU-E WB S | 5 W               |
| 53320299   | RS318B P5 930 PSU-E MB S | 5 W               |
| 53315899   | RS318B P5 930 PSU-E WB S | 5 W               |
| 53346299   | RS318B P7 927 PSU-E NB S | 7 W               |
| 53281699   | RS318B P7 927 PSU-E MB S | 7 W               |
| 53362299   | RS318B P7 930 PSU-E MB S | 7 W               |
| 53347999   | RS318B P7 930 PSU-E WB S | 7 W               |

| Order Code | Full Product Name         | Power Consumption |
|------------|---------------------------|-------------------|
| 53328899   | RS318B P9 927 PSU-E MB S  | 9 W               |
| 53303599   | RS318B P9 930 PSU-E MB S  | 9 W               |
| 53298499   | RS318B P9 930 PSU-E WB S  | 9 W               |
| 53316599   | RS318B P12 927 PSU-E NB S | 12 W              |
| 53348699   | RS318B P12 927 PSU-E MB S | 12 W              |
| 53283099   | RS318B P12 927 PSU-E WB S | 12 W              |
| 53381399   | RS318B P9 930 PSR-E MB S  | 9 W               |
| 53366099   | RS318B P9 930 PSR-E WB S  | 9 W               |
| 53341799   | RS318B P12 927 PSU-E WB D | 12 W              |

Controls and Dimming

| Order Code | Full Product Name        | Dimmable |
|------------|--------------------------|----------|
| 53314199   | RS318B P5 927 PSU-E NB S | No       |
| 53375299   | RS318B P5 927 PSU-E MB S | No       |
| 53361599   | RS318B P5 927 PSU-E WB S | No       |
| 53320299   | RS318B P5 930 PSU-E MB S | No       |
| 53315899   | RS318B P5 930 PSU-E WB S | No       |
| 53346299   | RS318B P7 927 PSU-E NB S | No       |
| 53281699   | RS318B P7 927 PSU-E MB S | No       |
| 53362299   | RS318B P7 930 PSU-E MB S | No       |
| 53347999   | RS318B P7 930 PSU-E WB S | No       |

| Order Code | Full Product Name         | Dimmable |
|------------|---------------------------|----------|
| 53328899   | RS318B P9 927 PSU-E MB S  | No       |
| 53303599   | RS318B P9 930 PSU-E MB S  | No       |
| 53298499   | RS318B P9 930 PSU-E WB S  | No       |
| 53316599   | RS318B P12 927 PSU-E NB S | No       |
| 53348699   | RS318B P12 927 PSU-E MB S | No       |
| 53283099   | RS318B P12 927 PSU-E WB S | No       |
| 53381399   | RS318B P9 930 PSR-E MB S  | Yes      |
| 53366099   | RS318B P9 930 PSR-E WB S  | Yes      |
| 53341799   | RS318B P12 927 PSU-E WB D | No       |

Approval and Application

GreenUp hospitality spot

| Order Code | Full Product Name        | Ambient temperature range |
|------------|--------------------------|---------------------------|
| 53314199   | RS318B P5 927 PSU-E NB S | +20 to +40 °C             |
| 53375299   | RS318B P5 927 PSU-E MB S | +20 to +40 °C             |
| 53361599   | RS318B P5 927 PSU-E WB S | +20 to +40 °C             |
| 53320299   | RS318B P5 930 PSU-E MB S | +20 to +40 °C             |
| 53315899   | RS318B P5 930 PSU-E WB S | +20 to +40 °C             |
| 53346299   | RS318B P7 927 PSU-E NB S | +20 to +40 °C             |
| 53281699   | RS318B P7 927 PSU-E MB S | +20 to +40 °C             |
| 53362299   | RS318B P7 930 PSU-E MB S | +20 to +40 °C             |
| 53347999   | RS318B P7 930 PSU-E WB S | +20 to +40 °C             |

| Order Code | Full Product Name         | Ambient temperature range |
|------------|---------------------------|---------------------------|
| 53328899   | RS318B P9 927 PSU-E MB S  | +20 to +40 °C             |
| 53303599   | RS318B P9 930 PSU-E MB S  | +20 to +40 °C             |
| 53298499   | RS318B P9 930 PSU-E WB S  | +20 to +40 °C             |
| 53316599   | RS318B P12 927 PSU-E NB S | +20 to +40 °C             |
| 53348699   | RS318B P12 927 PSU-E MB S | +20 to +40 °C             |
| 53283099   | RS318B P12 927 PSU-E WB S | +20 to +40 °C             |
| 53381399   | RS318B P9 930 PSR-E MB S  | +20 to +40 °C             |
| 53366099   | RS318B P9 930 PSR-E WB S  | +20 to +40 °C             |
| 53341799   | RS318B P12 927 PSU-E WB D | -20 to +40 °C             |

