



It delivers super flexibility, a complete product range and seamless system integration for hospitality customers..

Greenspace Flex

GreenSpace Flex is performance portfolio dedicated to Hospitality segment for GC/GM countries. With modular design concept, the light engines and different trims could have multiply of combination to satisfy diversified customer's requirement.

Benefits

- Complete portfolio covering from 400lm to 3000lm, 3CCT and 3 beam angles.
- Super flexibility with modular design, and different trims to suit different application.
- Smart connectivity to seamlessly integration with Interact Hospitality.
- Deep recess for visual comfort
- Easy installation and maintenance

Features

- 6w ~42w (400lm~3200lm)
- CRI 90, SDCM <3
- Beam Angle: NB, MB, WB
- CCT: 2700K, 3000K, 4000K
- High reliability, 50Khrs (L80B50@25°C)

Application

- Guest room
- Bath room
- Corridor
- Lobby

Specifications

Mounting type	Recessed
Operating Temperature range	-20 to +45 °C
Light Source	COB
Mains Voltage	220-240V AC/ 50-60Hz
Optical Accessories	available through ETO
Dimming	PSU: non-dimmable PSD: dimmable via Dali protocol PSR: trailing dimmable PSR 1-10V: 1-10v dimmable DMX: dimmable via DMX protocol
Control system input	DALI / 1-10V / DMX / trailing edge
Material	Heat sink: die-cast aluminum
Main color of the luminaire	Housing: dark Grey Reflector: color available through ETO
Lumen maintenance at median useful life 50.000h	L80
Luminous flux	468-3990lm
Power consumption	6W-42W

Correlated color temperature - CCT	2700K, 3000K, 4000K
Color Rendering index - CRI	90
Beam angle	NB (Narrow Beam): 15-18° MB (Medium Beam): 20-24° WB (Wide Beam): 30-40° VWB (Very Wide Beam): 50°
Protection Class IEC61140	Class II & Class III for MR16 version
Mechanical impact protection	IK04
Ingress protection	IP20 / IP54(Front side) for selected SKU only
Light source replaceable	No
Driver replaceable	yes
Overall diameter	D55-D150
Installation	recessed Fixation by means of spring fasteners





Versions





RS378B P11 M55

Greenspace Flex, Prof GCGM

Dimensional drawing



Modular Type	D, mm	H, mm
RS378B P6/P11 M55	55	49
RS378B P15 M55	55	49
RS378B P24 M70	70	90
RS378B P33 M87	87	107
RS378B P42 M102	102	116



Light Technical	
Color rendering index (CRI)	>90
Optic type	-
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Mechanical and Housing	
Optical cover type	PMMA
Housing Color	Grey
Mech. impact protection code	IK04
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	-20 to +45 °C
CE mark	Yes
ENEC mark	-
Flammability mark	-
Initial Performance (IEC Compliant)	
Luminous flux tolerance	-10% / +10%

General Information

Order Code	Full Product Name	Driver included	Number of gear units
01535871	RS378B P11 927 PSD-E NB M55	-	-
65337899	RS378B P11 927 PSD-E MB M55	-	-
01536071	RS378B P11 927 PSD-E WB M55	-	-
01536271	RS378B P11 930 PSD-E MB M55	-	-
65100899	RS378B P11 930 PSD-E WB M55	-	-
01536471	RS378B P11 940 PSD-E NB M55	-	-
01536571	RS378B P11 940 PSD-E MB M55	-	-
01536671	RS378B P11 940 PSD-E WB M55	-	-
01720892	RS378B P6 927 PSU-E NB M55	Yes	1 unit
01720902	RS378B P6 930 PSU-E NB M55	Yes	1 unit
01720912	RS378B P6 940 PSU-E NB M55	Yes	1 unit
01720922	RS378B P6 927 PSU-E MB M55	Yes	1 unit
01720932	RS378B P6 930 PSU-E MB M55	Yes	1 unit
64994499	RS378B P6 940 PSU-E MB M55	Yes	1 unit
64989099	RS378B P6 927 PSU-E WB M55	Yes	1 unit
64992099	RS378B P6 930 PSU-E WB M55	Yes	1 unit
64995199	RS378B P6 940 PSU-E WB M55	Yes	1 unit
64996899	RS378B P11 927 PSU-E NB M55	Yes	1 unit
64999999	RS378B P11 930 PSU-E NB M55	Yes	1 unit
01721002	RS378B P11 940 PSU-E NB M55	Yes	1 unit
01721012	RS378B P11 927 PSU-E MB M55	Yes	1 unit
01721022	RS378B P11 930 PSU-E MB M55	Yes	1 unit
65003299	RS378B P11 940 PSU-E MB M55	Yes	1 unit
64998299	RS378B P11 927 PSU-E WB M55	Yes	1 unit
65001899	RS378B P11 930 PSU-E WB M55	Yes	1 unit
65004999	RS378B P11 940 PSU-E WB M55	Yes	1 unit
01721072	RS378B P6 927 PSR-E NB M55	Yes	1 unit
01721112	RS378B P6 930 PSR-E MB M55	Yes	1 unit
01721172	RS378B P11 930 PSR-E NB M55	Yes	1 unit
01721192	RS378B P11 927 PSR-E MB M55	Yes	1 unit
65061299	RS378B P11 927 PSR-E WB M55	Yes	1 unit
65064399	RS378B P11 930 PSR-E WB M55	Yes	1 unit
01721622	RS378B P42 930 PSU-E NB M102	Yes	1 unit
01721632	RS378B P42 940 PSU-E NB M102	Yes	1 unit
01721642	RS378B P42 927 PSU-E MB M102	Yes	1 unit
01721652	RS378B P42 930 PSU-E MB M102	Yes	1 unit
01721662	RS378B P42 940 PSU-E MB M102	Yes	1 unit
01721682	RS378B P42 930 PSU-E WB M102	Yes	1 unit
01721692	RS378B P42 940 PSU-E WB M102	Yes	1 unit
01534971	RS378B P6 927 PSD-E NB M55	-	-
01535071	RS378B P6 927 PSD-E MB M55	-	-
65329399	RS378B P6 927 PSD-E WB M55	-	-
01535371	RS378B P6 930 PSD-E MB M55	-	-
01535471	RS378B P6 930 PSD-E WB M55	-	-
01535571	RS378B P6 940 PSD-E NB M55	-	-
01537771	RS378B P24 927 PSD-E MB M70	-	-
65358399	RS378B P24 930 PSD-E MB M70	-	-
65359099	RS378B P24 930 PSD-E WB M70	-	-
01538271	RS378B P24 940 PSD-E NB M70	-	-
01538371	RS378B P24 940 PSD-E MB M70	-	-
01538471	RS378B P24 940 PSD-E WB M70	-	-

Order Code	Full Product Name	Driver included	Number of gear units
01721432	RS378B P24 927 PSU-E NB M70	Yes	1 unit
65017999	RS378B P24 930 PSU-E NB M70	Yes	1 unit
01721452	RS378B P24 940 PSU-E NB M70	Yes	1 unit
01721472	RS378B P24 930 PSU-E MB M70	Yes	1 unit
01721482	RS378B P24 940 PSU-E MB M70	Yes	1 unit
01721492	RS378B P24 927 PSU-E WB M70	Yes	1 unit
65019399	RS378B P24 930 PSU-E WB M70	Yes	1 unit
01721512	RS378B P24 940 PSU-E WB M70	Yes	1 unit
01538571	RS378B P33 927 PSD-E NB M87	-	-
01538671	RS378B P33 927 PSD-E MB M87	-	-
01538871	RS378B P33 930 PSD-E NB M87	-	-
01539171	RS378B P33 940 PSD-E NB M87	-	-
65023099	RS378B P33 927 PSU-E NB M87	Yes	1 unit
65026199	RS378B P33 930 PSU-E NB M87	Yes	1 unit
65029299	RS378B P33 940 PSU-E NB M87	Yes	1 unit
65027899	RS378B P33 930 PSU-E MB M87	Yes	1 unit
65030899	RS378B P33 940 PSU-E MB M87	Yes	1 unit
65028599	RS378B P33 930 PSU-E WB M87	Yes	1 unit
65031599	RS378B P33 940 PSU-E WB M87	Yes	1 unit
01539871	RS378B P42 930 PSD-E MB M102	-	-
01539971	RS378B P42 930 PSD-E WB M102	-	-
01540271	RS378B P42 940 PSD-E WB M102	-	-
01545571	RS378B P11 930 PSU-E WW S	-	-
01545671	RS378B P11 940 PSU-E WW S	-	-
01546571	RS378B P11 940 PSD-E WW S	-	-
01545971	RS378B P15 940 PSU-E WW S	-	-
01546771	RS378B P15 930 PSD-E WW S	-	-
01536771	RS378B P15 927 PSD-E NB M55	-	-
01536871	RS378B P15 927 PSD-E MB M55	-	-
01536971	RS378B P15 927 PSD-E WB M55	-	-
01537171	RS378B P15 930 PSD-E MB M55	-	-
01537271	RS378B P15 930 PSD-E WB M55	-	-
01537371	RS378B P15 940 PSD-E NB M55	-	-
01537471	RS378B P15 940 PSD-E MB M55	-	-
01537571	RS378B P15 940 PSD-E WB M55	-	-
01540471	RS378B P15 927 PSR-E 1-10V MB M55	-	-
01540771	RS378B P15 930 PSR-E 1-10V MB M55	-	-
01540871	RS378B P15 930 PSR-E 1-10V WB M55	-	-
01541171	RS378B P15 940 PSR-E 1-10V WB M55	-	-
01532371	RS378B P6 927 PSU-E MB M43	-	-
01532471	RS378B P6 927 PSU-E WB M43	-	-
01532571	RS378B P6 930 PSU-E NB M43	-	-
01532671	RS378B P6 930 PSU-E MB M43	-	-
01532771	RS378B P6 930 PSU-E WB M43	-	-
01532871	RS378B P6 940 PSU-E NB M43	-	-
01532971	RS378B P6 940 PSU-E MB M43	-	-
01533071	RS378B P6 940 PSU-E WB M43	-	-
01533271	RS378B P6 927 PSR-E MB M43	-	-
01533571	RS378B P6 930 PSR-E MB M43	-	-
01533671	RS378B P6 930 PSR-E WB M43	-	-
01533771	RS378B P6 940 PSR-E NB M43	-	-
01534471	RS378B P6 930 PSD-E MB M43	-	-

Order Code	Full Product Name	Driver included	Number of gear units
01534571	RS378B P6 930 PSD-E WB M43	-	-
01534771	RS378B P6 940 PSD-E MB M43	-	-
01721252	RS378B P15 927 PSU-E NB M55	Yes	1 unit
01721262	RS378B P15 930 PSU-E NB M55	Yes	1 unit
01721272	RS378B P15 940 PSU-E NB M55	Yes	1 unit
65006399	RS378B P15 927 PSU-E MB M55	Yes	1 unit
01721292	RS378B P15 930 PSU-E MB M55	Yes	1 unit
01721302	RS378B P15 940 PSU-E MB M55	Yes	1 unit
65007099	RS378B P15 927 PSU-E WB M55	Yes	1 unit
65010099	RS378B P15 930 PSU-E WB M55	Yes	1 unit
65013199	RS378B P15 940 PSU-E WB M55	Yes	1 unit
65069899	RS378B P15 927 PSR-E MB M55	Yes	1 unit
65073599	RS378B P15 930 PSR-E WB M55	Yes	1 unit
65076699	RS378B P15 940 PSR-E WB M55	Yes	1 unit

Light Technical

Full Product		Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
Order Code	Name				
01535871	RS378B P11 927 PSD-E NB M55	-	2700 K	97 lm/W	580 lm
65337899	RS378B P11 927 PSD-E MB M55	-	2700 K	110 lm/W	660 lm
01536071	RS378B P11 927 PSD-E WB M55	-	2700 K	110 lm/W	660 lm
01536271	RS378B P11 930 PSD-E MB M55	-	3000 K	87 lm/W	957 lm
65100899	RS378B P11 930 PSD-E WB M55	-	3000 K	87 lm/W	957 lm
01536471	RS378B P11 940 PSD-E NB M55	-	4000 K	78 lm/W	858 lm
01536571	RS378B P11 940 PSD-E MB M55	-	4000 K	92 lm/W	1,012 lm
01536671	RS378B P11 940 PSD-E WB M55	-	4000 K	92 lm/W	1,012 lm
01720892	RS378B P6 927 PSU-E NB M55	- degree(s)	2700 K	92 lm/W	3,864 lm
01720902	RS378B P6 930 PSU-E NB M55	- degree(s)	3000 K	87 lm/W	1,305 lm
01720912	RS378B P6 940 PSU-E NB M55	- degree(s)	4000 K	80 lm/W	1,200 lm
01720922	RS378B P6 927 PSU-E MB M55	- degree(s)	2700 K	77 lm/W	2,540 lm
01720932	RS378B P6 930 PSU-E MB M55	- degree(s)	3000 K	97 lm/W	4,074 lm
64994499	RS378B P6 940 PSU-E MB M55	- degree(s)	4000 K	82 lm/W	900 lm
64989099	RS378B P6 927 PSU-E WB M55	- degree(s)	2700 K	92 lm/W	3,864 lm

Full Product		Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
Order Code	Name				
64992099	RS378B P6 930 PSU-E WB M55	- degree(s)	3000 K	100 lm/W	1,500 lm
64995199	RS378B P6 940 PSU-E WB M55	- degree(s)	4000 K	93 lm/W	1,400 lm
64996899	RS378B P11 927 PSU-E NB M55	-	2700 K	76 lm/W	836 lm
64999999	RS378B P11 930 PSU-E NB M55	-	3000 K	85 lm/W	510 lm
01721002	RS378B P11 940 PSU-E NB M55	-	4000 K	95 lm/W	570 lm
01721012	RS378B P11 927 PSU-E MB M55	-	2700 K	87 lm/W	957 lm
01721022	RS378B P11 930 PSU-E MB M55	-	3000 K	85 lm/W	510 lm
65003299	RS378B P11 940 PSU-E MB M55	-	4000 K	90 lm/W	540 lm
64998299	RS378B P11 927 PSU-E WB M55	-	2700 K	87 lm/W	957 lm
65001899	RS378B P11 930 PSU-E WB M55	-	3000 K	90 lm/W	540 lm
65004999	RS378B P11 940 PSU-E WB M55	-	4000 K	95 lm/W	570 lm
01721072	RS378B P6 927 PSR-E NB M55	-	2700 K	65 lm/W	390 lm
01721112	RS378B P6 930 PSR-E MB M55	-	3000 K	75 lm/W	450 lm
01721172	RS378B P11 930 PSR-E NB M55	-	3000 K	76 lm/W	836 lm
01721192	RS378B P11 927 PSR-E MB M55	-	2700 K	85 lm/W	510 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
65061299	RS378B P11 927 PSR-E WB M55	-	2700 K	85 lm/W	510 lm
65064399	RS378B P11 930 PSR-E WB M55	-	3000 K	87 lm/W	957 lm
01721622	RS378B P42 930 PSU-E NB M102	-	3000 K	71 lm/W	2,350 lm
01721632	RS378B P42 940 PSU-E NB M102	-	4000 K	73 lm/W	2,400 lm
01721642	RS378B P42 927 PSU-E MB M102	-	2700 K	106 lm/W	2,540 lm
01721652	RS378B P42 930 PSU-E MB M102	- degree(s)	3000 K	71 lm/W	2,350 lm
01721662	RS378B P42 940 PSU-E MB M102	- degree(s)	4000 K	73 lm/W	2,400 lm
01721682	RS378B P42 930 PSU-E WB M102	- degree(s)	3000 K	71 lm/W	2,350 lm
01721692	RS378B P42 940 PSU-E WB M102	- degree(s)	4000 K	73 lm/W	2,400 lm
01534971	RS378B P6 927 PSD-E NB M55	-	2700 K	95 lm/W	570 lm
01535071	RS378B P6 927 PSD-E MB M55	-	2700 K	100 lm/W	600 lm
65329399	RS378B P6 927 PSD-E WB M55	-	2700 K	100 lm/W	600 lm
01535371	RS378B P6 930 PSD-E MB M55	-	3000 K	100 lm/W	600 lm
01535471	RS378B P6 930 PSD-E WB M55	-	3000 K	100 lm/W	600 lm
01535571	RS378B P6 940 PSD-E NB M55	-	4000 K	88 lm/W	530 lm
01537771	RS378B P24 927 PSD-E MB M70	-	2700 K	100 lm/W	1,500 lm
65358399	RS378B P24 930 PSD-E MB M70	-	3000 K	98 lm/W	2,350 lm
65359099	RS378B P24 930 PSD-E WB M70	-	3000 K	98 lm/W	2,350 lm
01538271	RS378B P24 940 PSD-E NB M70	-	4000 K	100 lm/W	2,400 lm
01538371	RS378B P24 940 PSD-E MB M70	-	4000 K	100 lm/W	2,400 lm
01538471	RS378B P24 940 PSD-E WB M70	-	4000 K	100 lm/W	2,400 lm
01721432	RS378B P24 927 PSU-E NB M70	-	2700 K	92 lm/W	1,012 lm
65017999	RS378B P24 930 PSU-E NB M70	-	3000 K	100 lm/W	1,100 lm
01721452	RS378B P24 940 PSU-E NB M70	-	4000 K	78 lm/W	1,170 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
01721472	RS378B P24 930 PSU-E MB M70	-	3000 K	100 lm/W	1,100 lm
01721482	RS378B P24 940 PSU-E MB M70	-	4000 K	90 lm/W	1,350 lm
01721492	RS378B P24 927 PSU-E WB M70	-	2700 K	92 lm/W	1,012 lm
65019399	RS378B P24 930 PSU-E WB M70	-	3000 K	76 lm/W	1,140 lm
01721512	RS378B P24 940 PSU-E WB M70	-	4000 K	94 lm/W	1,410 lm
01538571	RS378B P33 927 PSD-E NB M87	-	2700 K	106 lm/W	2,540 lm
01538671	RS378B P33 927 PSD-E MB M87	-	2700 K	106 lm/W	2,540 lm
01538871	RS378B P33 930 PSD-E NB M87	-	3000 K	71 lm/W	2,350 lm
01539171	RS378B P33 940 PSD-E NB M87	-	4000 K	73 lm/W	2,400 lm
65023099	RS378B P33 927 PSU-E NB M87	-	2700 K	100 lm/W	1,500 lm
65026199	RS378B P33 930 PSU-E NB M87	-	3000 K	98 lm/W	2,350 lm
65029299	RS378B P33 940 PSU-E NB M87	-	4000 K	100 lm/W	2,400 lm
65027899	RS378B P33 930 PSU-E MB M87	-	3000 K	98 lm/W	2,350 lm
65030899	RS378B P33 940 PSU-E MB M87	-	4000 K	100 lm/W	2,400 lm
65028599	RS378B P33 930 PSU-E WB M87	-	3000 K	98 lm/W	2,350 lm
65031599	RS378B P33 940 PSU-E WB M87	-	4000 K	100 lm/W	2,400 lm
01539871	RS378B P42 930 PSD-E MB M102	-	3000 K	92 lm/W	3,864 lm
01539971	RS378B P42 930 PSD-E WB M102	-	3000 K	92 lm/W	3,864 lm
01540271	RS378B P42 940 PSD-E WB M102	-	4000 K	97 lm/W	4,074 lm
01545571	RS378B P11 930 PSU-E WW S	-	3000 K	90 lm/W	540 lm
01545671	RS378B P11 940 PSU-E WW S	-	4000 K	95 lm/W	570 lm
01546571	RS378B P11 940 PSD-E WW S	-	4000 K	90 lm/W	2,150 lm
01545971	RS378B P15 940 PSU-E WW S	-	4000 K	87 lm/W	957 lm
01546771	RS378B P15 930 PSD-E WW S	-	3000 K	82 lm/W	900 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
01536771	RS378B P15 927 PSD-E NB M55	-	2700 K	87 lm/W	957 lm
01536871	RS378B P15 927 PSD-E MB M55	-	2700 K	100 lm/W	1,100 lm
01536971	RS378B P15 927 PSD-E WB M55	-	2700 K	100 lm/W	1,100 lm
01537171	RS378B P15 930 PSD-E MB M55	-	3000 K	90 lm/W	1,350 lm
01537271	RS378B P15 930 PSD-E WB M55	-	3000 K	90 lm/W	1,350 lm
01537371	RS378B P15 940 PSD-E NB M55	-	4000 K	78 lm/W	1,170 lm
01537471	RS378B P15 940 PSD-E MB M55	-	4000 K	94 lm/W	1,410 lm
01537571	RS378B P15 940 PSD-E WB M55	-	4000 K	94 lm/W	1,410 lm
01540471	RS378B P15 927 PSR-E 1-10V MB M55	-	2700 K	104 lm/W	4,386 lm
01540771	RS378B P15 930 PSR-E 1-10V MB M55	-	3000 K	90 lm/W	1,350 lm
01540871	RS378B P15 930 PSR-E 1-10V WB M55	-	3000 K	90 lm/W	1,350 lm
01541171	RS378B P15 940 PSR-E 1-10V WB M55	-	4000 K	94 lm/W	1,410 lm
01532371	RS378B P6 927 PSU-E MB M43	-	2700 K	77 lm/W	2,540 lm
01532471	RS378B P6 927 PSU-E WB M43	-	2700 K	92 lm/W	3,864 lm
01532571	RS378B P6 930 PSU-E NB M43	-	3000 K	97 lm/W	4,074 lm
01532671	RS378B P6 930 PSU-E MB M43	-	3000 K	97 lm/W	4,074 lm
01532771	RS378B P6 930 PSU-E WB M43	-	3000 K	100 lm/W	1,500 lm
01532871	RS378B P6 940 PSU-E NB M43	-	4000 K	89 lm/W	980 lm
01532971	RS378B P6 940 PSU-E MB M43	-	4000 K	73 lm/W	800 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
01533071	RS378B P6 940 PSU-E WB M43	-	4000 K	87 lm/W	1,300 lm
01533271	RS378B P6 927 PSR-E MB M43	-	2700 K	104 lm/W	4,386 lm
01533571	RS378B P6 930 PSR-E MB M43	-	3000 K	58 lm/W	348 lm
01533671	RS378B P6 930 PSR-E WB M43	-	3000 K	58 lm/W	348 lm
01533771	RS378B P6 940 PSR-E NB M43	-	4000 K	60 lm/W	360 lm
01534471	RS378B P6 930 PSD-E MB M43	-	3000 K	89 lm/W	535 lm
01534571	RS378B P6 930 PSD-E WB M43	-	3000 K	89 lm/W	535 lm
01534771	RS378B P6 940 PSD-E MB M43	-	4000 K	93 lm/W	560 lm
01721252	RS378B P15 927 PSU-E NB M55	-	2700 K	85 lm/W	510 lm
01721262	RS378B P15 930 PSU-E NB M55	-	3000 K	97 lm/W	580 lm
01721272	RS378B P15 940 PSU-E NB M55	-	4000 K	76 lm/W	836 lm
65006399	RS378B P15 927 PSU-E MB M55	-	2700 K	83 lm/W	500 lm
01721292	RS378B P15 930 PSU-E MB M55	-	3000 K	91 lm/W	545 lm
01721302	RS378B P15 940 PSU-E MB M55	-	4000 K	105 lm/W	630 lm
65007099	RS378B P15 927 PSU-E WB M55	-	2700 K	90 lm/W	540 lm
65010099	RS378B P15 930 PSU-E WB M55	-	3000 K	97 lm/W	580 lm
65013199	RS378B P15 940 PSU-E WB M55	-	4000 K	87 lm/W	957 lm
65069899	RS378B P15 927 PSR-E MB M55	-	2700 K	100 lm/W	1,100 lm
65073599	RS378B P15 930 PSR-E WB M55	-	3000 K	90 lm/W	1,350 lm
65076699	RS378B P15 940 PSR-E WB M55	-	4000 K	94 lm/W	1,410 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Suitable for random switching
01535871	RS378B P11 927 PSD-E NB M55	11 W	-

Order Code	Full Product Name	Power Consumption	Suitable for random switching
65337899	RS378B P11 927 PSD-E MB M55	11 W	-

Order Code	Full Product Name	Power Consumption	Suitable for random switching
01536071	RS378B P11 927 PSD-E WB M55	11 W	-
01536271	RS378B P11 930 PSD-E MB M55	11 W	-
65100899	RS378B P11 930 PSD-E WB M55	11 W	-
01536471	RS378B P11 940 PSD-E NB M55	11 W	-
01536571	RS378B P11 940 PSD-E MB M55	11 W	-
01536671	RS378B P11 940 PSD-E WB M55	11 W	-
01720892	RS378B P6 927 PSU-E NB M55	6 W	No
01720902	RS378B P6 930 PSU-E NB M55	6 W	No
01720912	RS378B P6 940 PSU-E NB M55	6 W	No
01720922	RS378B P6 927 PSU-E MB M55	6 W	No
01720932	RS378B P6 930 PSU-E MB M55	6 W	No
64994499	RS378B P6 940 PSU-E MB M55	6 W	No
64989099	RS378B P6 927 PSU-E WB M55	6 W	No
64992099	RS378B P6 930 PSU-E WB M55	6 W	No
64995199	RS378B P6 940 PSU-E WB M55	6 W	No
64996899	RS378B P11 927 PSU-E NB M55	11 W	No
64999999	RS378B P11 930 PSU-E NB M55	11 W	No
01721002	RS378B P11 940 PSU-E NB M55	11 W	No
01721012	RS378B P11 927 PSU-E MB M55	11 W	No
01721022	RS378B P11 930 PSU-E MB M55	11 W	No
65003299	RS378B P11 940 PSU-E MB M55	11 W	No
64998299	RS378B P11 927 PSU-E WB M55	11 W	No
65001899	RS378B P11 930 PSU-E WB M55	11 W	No
65004999	RS378B P11 940 PSU-E WB M55	11 W	No
01721072	RS378B P6 927 PSR-E NB M55	6 W	No
01721112	RS378B P6 930 PSR-E MB M55	6 W	No
01721172	RS378B P11 930 PSR-E NB M55	11 W	No
01721192	RS378B P11 927 PSR-E MB M55	11 W	No
65061299	RS378B P11 927 PSR-E WB M55	11 W	No
65064399	RS378B P11 930 PSR-E WB M55	11 W	No
01721622	RS378B P42 930 PSU-E NB M102	42 W	No
01721632	RS378B P42 940 PSU-E NB M102	42 W	No
01721642	RS378B P42 927 PSU-E MB M102	42 W	No
01721652	RS378B P42 930 PSU-E MB M102	42 W	No
01721662	RS378B P42 940 PSU-E MB M102	42 W	No
01721682	RS378B P42 930 PSU-E WB M102	42 W	No
01721692	RS378B P42 940 PSU-E WB M102	42 W	No
01534971	RS378B P6 927 PSD-E NB M55	6 W	-
01535071	RS378B P6 927 PSD-E MB M55	6 W	-
65329399	RS378B P6 927 PSD-E WB M55	6 W	-
01535371	RS378B P6 930 PSD-E MB M55	6 W	-
01535471	RS378B P6 930 PSD-E WB M55	6 W	-
01535571	RS378B P6 940 PSD-E NB M55	6 W	-
01537771	RS378B P24 927 PSD-E MB M70	24 W	-
65358399	RS378B P24 930 PSD-E MB M70	24 W	-
65359099	RS378B P24 930 PSD-E WB M70	24 W	-
01538271	RS378B P24 940 PSD-E NB M70	24 W	-
01538371	RS378B P24 940 PSD-E MB M70	24 W	-
01538471	RS378B P24 940 PSD-E WB M70	24 W	-
01721432	RS378B P24 927 PSU-E NB M70	24 W	No

Order Code	Full Product Name	Power Consumption	Suitable for random switching
65017999	RS378B P24 930 PSU-E NB M70	24 W	No
01721452	RS378B P24 940 PSU-E NB M70	24 W	No
01721472	RS378B P24 930 PSU-E MB M70	24 W	No
01721482	RS378B P24 940 PSU-E MB M70	24 W	No
01721492	RS378B P24 927 PSU-E WB M70	24 W	No
65019399	RS378B P24 930 PSU-E WB M70	24 W	No
01721512	RS378B P24 940 PSU-E WB M70	24 W	No
01538571	RS378B P33 927 PSD-E NB M87	33 W	-
01538671	RS378B P33 927 PSD-E MB M87	33 W	-
01538871	RS378B P33 930 PSD-E NB M87	33 W	-
01539171	RS378B P33 940 PSD-E NB M87	33 W	-
65023099	RS378B P33 927 PSU-E NB M87	33 W	No
65026199	RS378B P33 930 PSU-E NB M87	33 W	No
65029299	RS378B P33 940 PSU-E NB M87	33 W	No
65027899	RS378B P33 930 PSU-E MB M87	33 W	No
65030899	RS378B P33 940 PSU-E MB M87	33 W	No
65028599	RS378B P33 930 PSU-E WB M87	33 W	No
65031599	RS378B P33 940 PSU-E WB M87	33 W	No
01539871	RS378B P42 930 PSD-E MB M102	42 W	-
01539971	RS378B P42 930 PSD-E WB M102	42 W	-
01540271	RS378B P42 940 PSD-E WB M102	42 W	-
01545571	RS378B P11 930 PSU-E WW S	11 W	-
01545671	RS378B P11 940 PSU-E WW S	11 W	-
01546571	RS378B P11 940 PSD-E WW S	11 W	-
01545971	RS378B P15 940 PSU-E WW S	15 W	-
01546771	RS378B P15 930 PSD-E WW S	15 W	-
01536771	RS378B P15 927 PSD-E NB M55	15 W	-
01536871	RS378B P15 927 PSD-E MB M55	15 W	-
01536971	RS378B P15 927 PSD-E WB M55	15 W	-
01537171	RS378B P15 930 PSD-E MB M55	15 W	-
01537271	RS378B P15 930 PSD-E WB M55	15 W	-
01537371	RS378B P15 940 PSD-E NB M55	15 W	-
01537471	RS378B P15 940 PSD-E MB M55	15 W	-
01537571	RS378B P15 940 PSD-E WB M55	15 W	-
01540471	RS378B P15 927 PSR-E 1-10V MB M55	15 W	-
01540771	RS378B P15 930 PSR-E 1-10V MB M55	15 W	-
01540871	RS378B P15 930 PSR-E 1-10V WB M55	15 W	-
01541171	RS378B P15 940 PSR-E 1-10V WB M55	15 W	-
01532371	RS378B P6 927 PSU-E MB M43	6 W	-
01532471	RS378B P6 927 PSU-E WB M43	6 W	-
01532571	RS378B P6 930 PSU-E NB M43	6 W	-
01532671	RS378B P6 930 PSU-E MB M43	6 W	-
01532771	RS378B P6 930 PSU-E WB M43	6 W	-
01532871	RS378B P6 940 PSU-E NB M43	6 W	-
01532971	RS378B P6 940 PSU-E MB M43	6 W	-
01533071	RS378B P6 940 PSU-E WB M43	6 W	-

Order Code	Full Product Name	Power Consumption	Suitable for random switching
01533271	RS378B P6 927 PSR-E MB M43	6 W	-
01533571	RS378B P6 930 PSR-E MB M43	6 W	-
01533671	RS378B P6 930 PSR-E WB M43	6 W	-
01533771	RS378B P6 940 PSR-E NB M43	6 W	-
01534471	RS378B P6 930 PSD-E MB M43	6 W	-
01534571	RS378B P6 930 PSD-E WB M43	6 W	-
01534771	RS378B P6 940 PSD-E MB M43	6 W	-
01721252	RS378B P15 927 PSU-E NB M55	15 W	No
01721262	RS378B P15 930 PSU-E NB M55	15 W	No
01721272	RS378B P15 940 PSU-E NB M55	15 W	No

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
01535871	RS378B P11 927 PSD-E NB M55	DALI	-
65337899	RS378B P11 927 PSD-E MB M55	DALI	-
01536071	RS378B P11 927 PSD-E WB M55	DALI	-
01536271	RS378B P11 930 PSD-E MB M55	DALI	-
65100899	RS378B P11 930 PSD-E WB M55	DALI	-
01536471	RS378B P11 940 PSD-E NB M55	DALI	-
01536571	RS378B P11 940 PSD-E MB M55	DALI	-
01536671	RS378B P11 940 PSD-E WB M55	DALI	-
01720892	RS378B P6 927 PSU-E NB M55	No	Not applicable
01720902	RS378B P6 930 PSU-E NB M55	No	Not applicable
01720912	RS378B P6 940 PSU-E NB M55	No	Not applicable
01720922	RS378B P6 927 PSU-E MB M55	No	Not applicable
01720932	RS378B P6 930 PSU-E MB M55	No	Not applicable
64994499	RS378B P6 940 PSU-E MB M55	No	Not applicable
64989099	RS378B P6 927 PSU-E WB M55	No	Not applicable
64992099	RS378B P6 930 PSU-E WB M55	No	Not applicable
64995199	RS378B P6 940 PSU-E WB M55	No	Not applicable
64996899	RS378B P11 927 PSU-E NB M55	No	Not applicable
64999999	RS378B P11 930 PSU-E NB M55	No	Not applicable
01721002	RS378B P11 940 PSU-E NB M55	No	Not applicable
01721012	RS378B P11 927 PSU-E MB M55	No	Not applicable
01721022	RS378B P11 930 PSU-E MB M55	No	Not applicable
65003299	RS378B P11 940 PSU-E MB M55	No	Not applicable
64998299	RS378B P11 927 PSU-E WB M55	No	Not applicable
65001899	RS378B P11 930 PSU-E WB M55	No	Not applicable
65004999	RS378B P11 940 PSU-E WB M55	No	Not applicable
01721072	RS378B P6 927 PSR-E NB M55	TRIAC	10%
01721112	RS378B P6 930 PSR-E MB M55	TRIAC	10%
01721172	RS378B P11 930 PSR-E NB M55	TRIAC	10%
01721192	RS378B P11 927 PSR-E MB M55	TRIAC	10%
65061299	RS378B P11 927 PSR-E WB M55	TRIAC	10%
65064399	RS378B P11 930 PSR-E WB M55	TRIAC	10%
01721622	RS378B P42 930 PSU-E NB M102	No	Not applicable
01721632	RS378B P42 940 PSU-E NB M102	No	Not applicable
01721642	RS378B P42 927 PSU-E MB M102	No	Not applicable
01721652	RS378B P42 930 PSU-E MB M102	No	Not applicable

Order Code	Full Product Name	Power Consumption	Suitable for random switching
65006399	RS378B P15 927 PSU-E MB M55	15 W	No
01721292	RS378B P15 930 PSU-E MB M55	15 W	No
01721302	RS378B P15 940 PSU-E MB M55	15 W	No
65007099	RS378B P15 927 PSU-E WB M55	15 W	No
65010099	RS378B P15 930 PSU-E WB M55	15 W	No
65013199	RS378B P15 940 PSU-E WB M55	15 W	No
65069899	RS378B P15 927 PSR-E MB M55	15 W	No
65073599	RS378B P15 930 PSR-E WB M55	15 W	No
65076699	RS378B P15 940 PSR-E WB M55	15 W	No

Order Code	Full Product Name	Dimmable	Maximum dim level
01721662	RS378B P42 940 PSU-E MB M102	No	Not applicable
01721682	RS378B P42 930 PSU-E WB M102	No	Not applicable
01721692	RS378B P42 940 PSU-E WB M102	No	Not applicable
01534971	RS378B P6 927 PSD-E NB M55	DALI	-
01535071	RS378B P6 927 PSD-E MB M55	DALI	-
65329399	RS378B P6 927 PSD-E WB M55	DALI	-
01535371	RS378B P6 930 PSD-E MB M55	DALI	-
01535471	RS378B P6 930 PSD-E WB M55	DALI	-
01535571	RS378B P6 940 PSD-E NB M55	DALI	-
01537771	RS378B P24 927 PSD-E MB M70	DALI	-
65358399	RS378B P24 930 PSD-E MB M70	DALI	-
65359099	RS378B P24 930 PSD-E WB M70	DALI	-
01538271	RS378B P24 940 PSD-E NB M70	DALI	-
01538371	RS378B P24 940 PSD-E MB M70	DALI	-
01538471	RS378B P24 940 PSD-E WB M70	DALI	-
01721432	RS378B P24 927 PSU-E NB M70	No	Not applicable
65017999	RS378B P24 930 PSU-E NB M70	No	Not applicable
01721452	RS378B P24 940 PSU-E NB M70	No	Not applicable
01721472	RS378B P24 930 PSU-E MB M70	No	Not applicable
01721482	RS378B P24 940 PSU-E MB M70	No	Not applicable
01721492	RS378B P24 927 PSU-E WB M70	No	Not applicable
65019399	RS378B P24 930 PSU-E WB M70	No	Not applicable
01721512	RS378B P24 940 PSU-E WB M70	No	Not applicable
01538571	RS378B P33 927 PSD-E NB M87	DALI	-
01538671	RS378B P33 927 PSD-E MB M87	DALI	-
01538871	RS378B P33 930 PSD-E NB M87	DALI	-
01539171	RS378B P33 940 PSD-E NB M87	DALI	-
65023099	RS378B P33 927 PSU-E NB M87	No	Not applicable
65026199	RS378B P33 930 PSU-E NB M87	No	Not applicable
65029299	RS378B P33 940 PSU-E NB M87	No	Not applicable
65027899	RS378B P33 930 PSU-E MB M87	No	Not applicable
65030899	RS378B P33 940 PSU-E MB M87	No	Not applicable
65028599	RS378B P33 930 PSU-E WB M87	No	Not applicable
65031599	RS378B P33 940 PSU-E WB M87	No	Not applicable
01539871	RS378B P42 930 PSD-E MB M102	DALI	-
01539971	RS378B P42 930 PSD-E WB M102	DALI	-

Order Code	Full Product Name	Dimmable	Maximum dim level
01540271	RS378B P42 940 PSD-E WB M102	DALI	-
01545571	RS378B P11 930 PSU-E WW S	No	-
01545671	RS378B P11 940 PSU-E WW S	No	-
01546571	RS378B P11 940 PSD-E WW S	DALI	-
01545971	RS378B P15 940 PSU-E WW S	No	-
01546771	RS378B P15 930 PSD-E WW S	DALI	-
01536771	RS378B P15 927 PSD-E NB M55	DALI	-
01536871	RS378B P15 927 PSD-E MB M55	DALI	-
01536971	RS378B P15 927 PSD-E WB M55	DALI	-
01537171	RS378B P15 930 PSD-E MB M55	DALI	-
01537271	RS378B P15 930 PSD-E WB M55	DALI	-
01537371	RS378B P15 940 PSD-E NB M55	DALI	-
01537471	RS378B P15 940 PSD-E MB M55	DALI	-
01537571	RS378B P15 940 PSD-E WB M55	DALI	-
01540471	RS378B P15 927 PSR-E 1-10V MB M55	1-10V	-
01540771	RS378B P15 930 PSR-E 1-10V MB M55	1-10V	-
01540871	RS378B P15 930 PSR-E 1-10V WB M55	1-10V	-
01541171	RS378B P15 940 PSR-E 1-10V WB M55	1-10V	-
01532371	RS378B P6 927 PSU-E MB M43	No	-
01532471	RS378B P6 927 PSU-E WB M43	No	-
01532571	RS378B P6 930 PSU-E NB M43	No	-
01532671	RS378B P6 930 PSU-E MB M43	No	-
01532771	RS378B P6 930 PSU-E WB M43	No	-

Order Code	Full Product Name	Dimmable	Maximum dim level
01532871	RS378B P6 940 PSU-E NB M43	No	-
01532971	RS378B P6 940 PSU-E MB M43	No	-
01533071	RS378B P6 940 PSU-E WB M43	No	-
01533271	RS378B P6 927 PSR-E MB M43	TRIAC	-
01533571	RS378B P6 930 PSR-E MB M43	TRIAC	-
01533671	RS378B P6 930 PSR-E WB M43	TRIAC	-
01533771	RS378B P6 940 PSR-E NB M43	TRIAC	-
01534471	RS378B P6 930 PSD-E MB M43	DALI	-
01534571	RS378B P6 930 PSD-E WB M43	DALI	-
01534771	RS378B P6 940 PSD-E MB M43	DALI	-
01721252	RS378B P15 927 PSU-E NB M55	No	Not applicable
01721262	RS378B P15 930 PSU-E NB M55	No	Not applicable
01721272	RS378B P15 940 PSU-E NB M55	No	Not applicable
65006399	RS378B P15 927 PSU-E MB M55	No	Not applicable
01721292	RS378B P15 930 PSU-E MB M55	No	Not applicable
01721302	RS378B P15 940 PSU-E MB M55	No	Not applicable
65007099	RS378B P15 927 PSU-E WB M55	No	Not applicable
65010099	RS378B P15 930 PSU-E WB M55	No	Not applicable
65013199	RS378B P15 940 PSU-E WB M55	No	Not applicable
65069899	RS378B P15 927 PSR-E MB M55	TRIAC	10%
65073599	RS378B P15 930 PSR-E WB M55	TRIAC	10%
65076699	RS378B P15 940 PSR-E WB M55	TRIAC	10%

Approval and Application

Order Code	Full Product Name	Glow-wire test
01535871	RS378B P11 927 PSD-E NB M55	-
65337899	RS378B P11 927 PSD-E MB M55	-
01536071	RS378B P11 927 PSD-E WB M55	-
01536271	RS378B P11 930 PSD-E MB M55	-
65100899	RS378B P11 930 PSD-E WB M55	-
01536471	RS378B P11 940 PSD-E NB M55	-
01536571	RS378B P11 940 PSD-E MB M55	-
01536671	RS378B P11 940 PSD-E WB M55	-
01720892	RS378B P6 927 PSU-E NB M55	Temperature 600 °C, duration 30 s
01720902	RS378B P6 930 PSU-E NB M55	Temperature 600 °C, duration 30 s
01720912	RS378B P6 940 PSU-E NB M55	Temperature 600 °C, duration 30 s
01720922	RS378B P6 927 PSU-E MB M55	Temperature 600 °C, duration 30 s
01720932	RS378B P6 930 PSU-E MB M55	Temperature 600 °C, duration 30 s
64994499	RS378B P6 940 PSU-E MB M55	Temperature 600 °C, duration 30 s
64989099	RS378B P6 927 PSU-E WB M55	Temperature 600 °C, duration 30 s
64992099	RS378B P6 930 PSU-E WB M55	Temperature 600 °C, duration 30 s
64995199	RS378B P6 940 PSU-E WB M55	Temperature 600 °C, duration 30 s
64996899	RS378B P11 927 PSU-E NB M55	Temperature 600 °C, duration 30 s
64999999	RS378B P11 930 PSU-E NB M55	Temperature 600 °C, duration 30 s
01721002	RS378B P11 940 PSU-E NB M55	Temperature 600 °C, duration 30 s
01721012	RS378B P11 927 PSU-E MB M55	Temperature 600 °C, duration 30 s
01721022	RS378B P11 930 PSU-E MB M55	Temperature 600 °C, duration 30 s
65003299	RS378B P11 940 PSU-E MB M55	Temperature 600 °C, duration 30 s
64998299	RS378B P11 927 PSU-E WB M55	Temperature 600 °C, duration 30 s
65001899	RS378B P11 930 PSU-E WB M55	Temperature 600 °C, duration 30 s

Order Code	Full Product Name	Glow-wire test
65004999	RS378B P11 940 PSU-E WB M55	Temperature 600 °C, duration 30 s
01721072	RS378B P6 927 PSR-E NB M55	Temperature 600 °C, duration 30 s
01721112	RS378B P6 930 PSR-E MB M55	Temperature 600 °C, duration 30 s
01721172	RS378B P11 930 PSR-E NB M55	Temperature 600 °C, duration 30 s
01721192	RS378B P11 927 PSR-E MB M55	Temperature 600 °C, duration 30 s
65061299	RS378B P11 927 PSR-E WB M55	Temperature 600 °C, duration 30 s
65064399	RS378B P11 930 PSR-E WB M55	Temperature 600 °C, duration 30 s
01721622	RS378B P42 930 PSU-E NB M102	Temperature 600 °C, duration 30 s
01721632	RS378B P42 940 PSU-E NB M102	Temperature 600 °C, duration 30 s
01721642	RS378B P42 927 PSU-E MB M102	Temperature 600 °C, duration 30 s
01721652	RS378B P42 930 PSU-E MB M102	Temperature 600 °C, duration 30 s
01721662	RS378B P42 940 PSU-E MB M102	Temperature 600 °C, duration 30 s
01721682	RS378B P42 930 PSU-E WB M102	Temperature 600 °C, duration 30 s
01721692	RS378B P42 940 PSU-E WB M102	Temperature 600 °C, duration 30 s
01534971	RS378B P6 927 PSD-E NB M55	-
01535071	RS378B P6 927 PSD-E MB M55	-
65329399	RS378B P6 927 PSD-E WB M55	-
01535371	RS378B P6 930 PSD-E MB M55	-
01535471	RS378B P6 930 PSD-E WB M55	-
01535571	RS378B P6 940 PSD-E NB M55	-
01537771	RS378B P24 927 PSD-E MB M70	-
65358399	RS378B P24 930 PSD-E MB M70	-
65359099	RS378B P24 930 PSD-E WB M70	-
01538271	RS378B P24 940 PSD-E NB M70	-
01538371	RS378B P24 940 PSD-E MB M70	-

Order Code	Full Product Name	Glow-wire test
01538471	RS378B P24 940 PSD-E WB M70	-
01721432	RS378B P24 927 PSU-E NB M70	Temperature 600 °C, duration 30 s
65017999	RS378B P24 930 PSU-E NB M70	Temperature 600 °C, duration 30 s
01721452	RS378B P24 940 PSU-E NB M70	Temperature 600 °C, duration 30 s
01721472	RS378B P24 930 PSU-E MB M70	Temperature 600 °C, duration 30 s
01721482	RS378B P24 940 PSU-E MB M70	Temperature 600 °C, duration 30 s
01721492	RS378B P24 927 PSU-E WB M70	Temperature 600 °C, duration 30 s
65019399	RS378B P24 930 PSU-E WB M70	Temperature 600 °C, duration 30 s
01721512	RS378B P24 940 PSU-E WB M70	Temperature 600 °C, duration 30 s
01538571	RS378B P33 927 PSD-E NB M87	-
01538671	RS378B P33 927 PSD-E MB M87	-
01538871	RS378B P33 930 PSD-E NB M87	-
01539171	RS378B P33 940 PSD-E NB M87	-
65023099	RS378B P33 927 PSU-E NB M87	Temperature 600 °C, duration 30 s
65026199	RS378B P33 930 PSU-E NB M87	Temperature 600 °C, duration 30 s
65029299	RS378B P33 940 PSU-E NB M87	Temperature 600 °C, duration 30 s
65027899	RS378B P33 930 PSU-E MB M87	Temperature 600 °C, duration 30 s
65030899	RS378B P33 940 PSU-E MB M87	Temperature 600 °C, duration 30 s
65028599	RS378B P33 930 PSU-E WB M87	Temperature 600 °C, duration 30 s
65031599	RS378B P33 940 PSU-E WB M87	Temperature 600 °C, duration 30 s
01539871	RS378B P42 930 PSD-E MB M102	-
01539971	RS378B P42 930 PSD-E WB M102	-
01540271	RS378B P42 940 PSD-E WB M102	-
01545571	RS378B P11 930 PSU-E WW S	-
01545671	RS378B P11 940 PSU-E WW S	-
01546571	RS378B P11 940 PSD-E WW S	-
01545971	RS378B P15 940 PSU-E WW S	-
01546771	RS378B P15 930 PSD-E WW S	-
01536771	RS378B P15 927 PSD-E NB M55	-
01536871	RS378B P15 927 PSD-E MB M55	-
01536971	RS378B P15 927 PSD-E WB M55	-
01537171	RS378B P15 930 PSD-E MB M55	-
01537271	RS378B P15 930 PSD-E WB M55	-
01537371	RS378B P15 940 PSD-E NB M55	-

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
01535871	RS378B P11 927 PSD-E NB M55	-
65337899	RS378B P11 927 PSD-E MB M55	-
01536071	RS378B P11 927 PSD-E WB M55	-
01536271	RS378B P11 930 PSD-E MB M55	-
65100899	RS378B P11 930 PSD-E WB M55	-
01536471	RS378B P11 940 PSD-E NB M55	-
01536571	RS378B P11 940 PSD-E MB M55	-
01536671	RS378B P11 940 PSD-E WB M55	-
01720892	RS378B P6 927 PSU-E NB M55	SDCM<3
01720902	RS378B P6 930 PSU-E NB M55	SDCM<3
01720912	RS378B P6 940 PSU-E NB M55	SDCM<3
01720922	RS378B P6 927 PSU-E MB M55	SDCM<3
01720932	RS378B P6 930 PSU-E MB M55	SDCM<3
64994499	RS378B P6 940 PSU-E MB M55	SDCM<3

Order Code	Full Product Name	Glow-wire test
01537471	RS378B P15 940 PSD-E MB M55	-
01537571	RS378B P15 940 PSD-E WB M55	-
01540471	RS378B P15 927 PSR-E 1-10V MB M55	-
01540771	RS378B P15 930 PSR-E 1-10V MB M55	-
01540871	RS378B P15 930 PSR-E 1-10V WB M55	-
01541171	RS378B P15 940 PSR-E 1-10V WB M55	-
01532371	RS378B P6 927 PSU-E MB M43	-
01532471	RS378B P6 927 PSU-E WB M43	-
01532571	RS378B P6 930 PSU-E NB M43	-
01532671	RS378B P6 930 PSU-E MB M43	-
01532771	RS378B P6 930 PSU-E WB M43	-
01532871	RS378B P6 940 PSU-E NB M43	-
01532971	RS378B P6 940 PSU-E MB M43	-
01533071	RS378B P6 940 PSU-E WB M43	-
01533271	RS378B P6 927 PSR-E MB M43	-
01533571	RS378B P6 930 PSR-E MB M43	-
01533671	RS378B P6 930 PSR-E WB M43	-
01533771	RS378B P6 940 PSR-E NB M43	-
01534471	RS378B P6 930 PSD-E MB M43	-
01534571	RS378B P6 930 PSD-E WB M43	-
01534771	RS378B P6 940 PSD-E MB M43	-
01721252	RS378B P15 927 PSU-E NB M55	Temperature 600 °C, duration 30 s
01721262	RS378B P15 930 PSU-E NB M55	Temperature 600 °C, duration 30 s
01721272	RS378B P15 940 PSU-E NB M55	Temperature 600 °C, duration 30 s
65006399	RS378B P15 927 PSU-E MB M55	Temperature 600 °C, duration 30 s
01721292	RS378B P15 930 PSU-E MB M55	Temperature 600 °C, duration 30 s
01721302	RS378B P15 940 PSU-E MB M55	Temperature 600 °C, duration 30 s
65007099	RS378B P15 927 PSU-E WB M55	Temperature 600 °C, duration 30 s
65010099	RS378B P15 930 PSU-E WB M55	Temperature 600 °C, duration 30 s
65013199	RS378B P15 940 PSU-E WB M55	Temperature 600 °C, duration 30 s
65069899	RS378B P15 927 PSR-E MB M55	Temperature 600 °C, duration 30 s
65073599	RS378B P15 930 PSR-E WB M55	Temperature 600 °C, duration 30 s
65076699	RS378B P15 940 PSR-E WB M55	Temperature 600 °C, duration 30 s

Order Code	Full Product Name	Initial chromaticity
64989099	RS378B P6 927 PSU-E WB M55	SDCM<3
64992099	RS378B P6 930 PSU-E WB M55	SDCM<3
64995199	RS378B P6 940 PSU-E WB M55	SDCM<3
64996899	RS378B P11 927 PSU-E NB M55	SDCM<3
64999999	RS378B P11 930 PSU-E NB M55	SDCM<3
01721002	RS378B P11 940 PSU-E NB M55	SDCM<3
01721012	RS378B P11 927 PSU-E MB M55	SDCM<3
01721022	RS378B P11 930 PSU-E MB M55	SDCM<3
65003299	RS378B P11 940 PSU-E MB M55	SDCM<3
64998299	RS378B P11 927 PSU-E WB M55	SDCM<3
65001899	RS378B P11 930 PSU-E WB M55	SDCM<3
65004999	RS378B P11 940 PSU-E WB M55	SDCM<3
01721072	RS378B P6 927 PSR-E NB M55	SDCM<3
01721112	RS378B P6 930 PSR-E MB M55	SDCM<3

Order Code	Full Product Name	Initial chromaticity
01721172	RS378B P11 930 PSR-E NB M55	SDCM<3
01721192	RS378B P11 927 PSR-E MB M55	SDCM<3
65061299	RS378B P11 927 PSR-E WB M55	SDCM<3
65064399	RS378B P11 930 PSR-E WB M55	SDCM<3
01721622	RS378B P42 930 PSU-E NB M102	SDCM<3
01721632	RS378B P42 940 PSU-E NB M102	SDCM<3
01721642	RS378B P42 927 PSU-E MB M102	SDCM<3
01721652	RS378B P42 930 PSU-E MB M102	SDCM<3
01721662	RS378B P42 940 PSU-E MB M102	SDCM<3
01721682	RS378B P42 930 PSU-E WB M102	SDCM<3
01721692	RS378B P42 940 PSU-E WB M102	SDCM<3
01534971	RS378B P6 927 PSD-E NB M55	-
01535071	RS378B P6 927 PSD-E MB M55	-
65329399	RS378B P6 927 PSD-E WB M55	-
01535371	RS378B P6 930 PSD-E MB M55	-
01535471	RS378B P6 930 PSD-E WB M55	-
01535571	RS378B P6 940 PSD-E NB M55	-
01537771	RS378B P24 927 PSD-E MB M70	-
65358399	RS378B P24 930 PSD-E MB M70	-
65359099	RS378B P24 930 PSD-E WB M70	-
01538271	RS378B P24 940 PSD-E NB M70	-
01538371	RS378B P24 940 PSD-E MB M70	-
01538471	RS378B P24 940 PSD-E WB M70	-
01721432	RS378B P24 927 PSU-E NB M70	SDCM<3
65017999	RS378B P24 930 PSU-E NB M70	SDCM<3
01721452	RS378B P24 940 PSU-E NB M70	SDCM<3
01721472	RS378B P24 930 PSU-E MB M70	SDCM<3
01721482	RS378B P24 940 PSU-E MB M70	SDCM<3
01721492	RS378B P24 927 PSU-E WB M70	SDCM<3
65019399	RS378B P24 930 PSU-E WB M70	SDCM<3
01721512	RS378B P24 940 PSU-E WB M70	SDCM<3
01538571	RS378B P33 927 PSD-E NB M87	-
01538671	RS378B P33 927 PSD-E MB M87	-
01538871	RS378B P33 930 PSD-E NB M87	-
01539171	RS378B P33 940 PSD-E NB M87	-
65023099	RS378B P33 927 PSU-E NB M87	SDCM<3
65026199	RS378B P33 930 PSU-E NB M87	SDCM<3
65029299	RS378B P33 940 PSU-E NB M87	SDCM<3
65027899	RS378B P33 930 PSU-E MB M87	SDCM<3
65030899	RS378B P33 940 PSU-E MB M87	SDCM<3
65028599	RS378B P33 930 PSU-E WB M87	SDCM<3
65031599	RS378B P33 940 PSU-E WB M87	SDCM<3
01539871	RS378B P42 930 PSD-E MB M102	-
01539971	RS378B P42 930 PSD-E WB M102	-
01540271	RS378B P42 940 PSD-E WB M102	-

Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Median useful life L80B50
01535871	RS378B P11 927 PSD-E NB M55	-
65337899	RS378B P11 927 PSD-E MB M55	-
01536071	RS378B P11 927 PSD-E WB M55	-

Order Code	Full Product Name	Initial chromaticity
01545571	RS378B P11 930 PSU-E WW S	-
01545671	RS378B P11 940 PSU-E WW S	-
01546571	RS378B P11 940 PSD-E WW S	-
01545971	RS378B P15 940 PSU-E WW S	-
01546771	RS378B P15 930 PSD-E WW S	-
01536771	RS378B P15 927 PSD-E NB M55	-
01536871	RS378B P15 927 PSD-E MB M55	-
01536971	RS378B P15 927 PSD-E WB M55	-
01537171	RS378B P15 930 PSD-E MB M55	-
01537271	RS378B P15 930 PSD-E WB M55	-
01537371	RS378B P15 940 PSD-E NB M55	-
01537471	RS378B P15 940 PSD-E MB M55	-
01537571	RS378B P15 940 PSD-E WB M55	-
01540471	RS378B P15 927 PSR-E 1-10V MB M55	-
01540771	RS378B P15 930 PSR-E 1-10V MB M55	-
01540871	RS378B P15 930 PSR-E 1-10V WB M55	-
01541171	RS378B P15 940 PSR-E 1-10V WB M55	-
01532371	RS378B P6 927 PSU-E MB M43	-
01532471	RS378B P6 927 PSU-E WB M43	-
01532571	RS378B P6 930 PSU-E NB M43	-
01532671	RS378B P6 930 PSU-E MB M43	-
01532771	RS378B P6 930 PSU-E WB M43	-
01532871	RS378B P6 940 PSU-E NB M43	-
01532971	RS378B P6 940 PSU-E MB M43	-
01533071	RS378B P6 940 PSU-E WB M43	-
01533271	RS378B P6 927 PSR-E MB M43	-
01533571	RS378B P6 930 PSR-E MB M43	-
01533671	RS378B P6 930 PSR-E WB M43	-
01533771	RS378B P6 940 PSR-E NB M43	-
01534471	RS378B P6 930 PSD-E MB M43	-
01534571	RS378B P6 930 PSD-E WB M43	-
01534771	RS378B P6 940 PSD-E MB M43	-
01721252	RS378B P15 927 PSU-E NB M55	SDCM<3
01721262	RS378B P15 930 PSU-E NB M55	SDCM<3
01721272	RS378B P15 940 PSU-E NB M55	SDCM<3
65006399	RS378B P15 927 PSU-E MB M55	SDCM<3
01721292	RS378B P15 930 PSU-E MB M55	SDCM<3
01721302	RS378B P15 940 PSU-E MB M55	SDCM<3
65007099	RS378B P15 927 PSU-E WB M55	SDCM<3
65010099	RS378B P15 930 PSU-E WB M55	SDCM<3
65013199	RS378B P15 940 PSU-E WB M55	SDCM<3
65069899	RS378B P15 927 PSR-E MB M55	SDCM<3
65073599	RS378B P15 930 PSR-E WB M55	SDCM<3
65076699	RS378B P15 940 PSR-E WB M55	SDCM<3

Order Code	Full Product Name	Median useful life L80B50
01536271	RS378B P11 930 PSD-E MB M55	-
65100899	RS378B P11 930 PSD-E WB M55	-
01536471	RS378B P11 940 PSD-E NB M55	-

Order Code	Full Product Name	Median useful life L80B50
01536571	RS378B P11 940 PSD-E MB M55	-
01536671	RS378B P11 940 PSD-E WB M55	-
01720892	RS378B P6 927 PSU-E NB M55	50,000 hour(s)
01720902	RS378B P6 930 PSU-E NB M55	50,000 hour(s)
01720912	RS378B P6 940 PSU-E NB M55	50,000 hour(s)
01720922	RS378B P6 927 PSU-E MB M55	50,000 hour(s)
01720932	RS378B P6 930 PSU-E MB M55	50,000 hour(s)
64994499	RS378B P6 940 PSU-E MB M55	50,000 hour(s)
64989099	RS378B P6 927 PSU-E WB M55	50,000 hour(s)
64992099	RS378B P6 930 PSU-E WB M55	50,000 hour(s)
64995199	RS378B P6 940 PSU-E WB M55	50,000 hour(s)
64996899	RS378B P11 927 PSU-E NB M55	50,000 hour(s)
64999999	RS378B P11 930 PSU-E NB M55	50,000 hour(s)
01721002	RS378B P11 940 PSU-E NB M55	50,000 hour(s)
01721012	RS378B P11 927 PSU-E MB M55	50,000 hour(s)
01721022	RS378B P11 930 PSU-E MB M55	50,000 hour(s)
65003299	RS378B P11 940 PSU-E MB M55	50,000 hour(s)
64998299	RS378B P11 927 PSU-E WB M55	50,000 hour(s)
65001899	RS378B P11 930 PSU-E WB M55	50,000 hour(s)
65004999	RS378B P11 940 PSU-E WB M55	50,000 hour(s)
01721072	RS378B P6 927 PSR-E NB M55	50,000 hour(s)
01721112	RS378B P6 930 PSR-E MB M55	50,000 hour(s)
01721172	RS378B P11 930 PSR-E NB M55	50,000 hour(s)
01721192	RS378B P11 927 PSR-E MB M55	50,000 hour(s)
65061299	RS378B P11 927 PSR-E WB M55	50,000 hour(s)
65064399	RS378B P11 930 PSR-E WB M55	50,000 hour(s)
01721622	RS378B P42 930 PSU-E NB M102	50,000 hour(s)
01721632	RS378B P42 940 PSU-E NB M102	50,000 hour(s)
01721642	RS378B P42 927 PSU-E MB M102	50,000 hour(s)
01721652	RS378B P42 930 PSU-E MB M102	50,000 hour(s)
01721662	RS378B P42 940 PSU-E MB M102	50,000 hour(s)
01721682	RS378B P42 930 PSU-E WB M102	50,000 hour(s)
01721692	RS378B P42 940 PSU-E WB M102	50,000 hour(s)
01534971	RS378B P6 927 PSD-E NB M55	-
01535071	RS378B P6 927 PSD-E MB M55	-
65329399	RS378B P6 927 PSD-E WB M55	-
01535371	RS378B P6 930 PSD-E MB M55	-
01535471	RS378B P6 930 PSD-E WB M55	-
01535571	RS378B P6 940 PSD-E NB M55	-
01537771	RS378B P24 927 PSD-E MB M70	-
65358399	RS378B P24 930 PSD-E MB M70	-
65359099	RS378B P24 930 PSD-E WB M70	-
01538271	RS378B P24 940 PSD-E NB M70	-
01538371	RS378B P24 940 PSD-E MB M70	-
01538471	RS378B P24 940 PSD-E WB M70	-
01721432	RS378B P24 927 PSU-E NB M70	50,000 hour(s)
65017999	RS378B P24 930 PSU-E NB M70	50,000 hour(s)
01721452	RS378B P24 940 PSU-E NB M70	50,000 hour(s)
01721472	RS378B P24 930 PSU-E MB M70	50,000 hour(s)
01721482	RS378B P24 940 PSU-E MB M70	50,000 hour(s)
01721492	RS378B P24 927 PSU-E WB M70	50,000 hour(s)
65019399	RS378B P24 930 PSU-E WB M70	50,000 hour(s)

Order Code	Full Product Name	Median useful life L80B50
01721512	RS378B P24 940 PSU-E WB M70	50,000 hour(s)
01538571	RS378B P33 927 PSD-E NB M87	-
01538671	RS378B P33 927 PSD-E MB M87	-
01538871	RS378B P33 930 PSD-E NB M87	-
01539171	RS378B P33 940 PSD-E NB M87	-
65023099	RS378B P33 927 PSU-E NB M87	50,000 hour(s)
65026199	RS378B P33 930 PSU-E NB M87	50,000 hour(s)
65029299	RS378B P33 940 PSU-E NB M87	50,000 hour(s)
65027899	RS378B P33 930 PSU-E MB M87	50,000 hour(s)
65030899	RS378B P33 940 PSU-E MB M87	50,000 hour(s)
65028599	RS378B P33 930 PSU-E WB M87	50,000 hour(s)
65031599	RS378B P33 940 PSU-E WB M87	50,000 hour(s)
01539871	RS378B P42 930 PSD-E MB M102	-
01539971	RS378B P42 930 PSD-E WB M102	-
01540271	RS378B P42 940 PSD-E WB M102	-
01545571	RS378B P11 930 PSU-E WW S	-
01545671	RS378B P11 940 PSU-E WW S	-
01546571	RS378B P11 940 PSD-E WW S	-
01545971	RS378B P15 940 PSU-E WW S	-
01546771	RS378B P15 930 PSD-E WW S	-
01536771	RS378B P15 927 PSD-E NB M55	-
01536871	RS378B P15 927 PSD-E MB M55	-
01536971	RS378B P15 927 PSD-E WB M55	-
01537171	RS378B P15 930 PSD-E MB M55	-
01537271	RS378B P15 930 PSD-E WB M55	-
01537371	RS378B P15 940 PSD-E NB M55	-
01537471	RS378B P15 940 PSD-E MB M55	-
01537571	RS378B P15 940 PSD-E WB M55	-
01540471	RS378B P15 927 PSR-E 1-10V MB M55	-
01540771	RS378B P15 930 PSR-E 1-10V MB M55	-
01540871	RS378B P15 930 PSR-E 1-10V WB M55	-
01541171	RS378B P15 940 PSR-E 1-10V WB M55	-
01532371	RS378B P6 927 PSU-E MB M43	-
01532471	RS378B P6 927 PSU-E WB M43	-
01532571	RS378B P6 930 PSU-E NB M43	-
01532671	RS378B P6 930 PSU-E MB M43	-
01532771	RS378B P6 930 PSU-E WB M43	-
01532871	RS378B P6 940 PSU-E NB M43	-
01532971	RS378B P6 940 PSU-E MB M43	-
01533071	RS378B P6 940 PSU-E WB M43	-
01533271	RS378B P6 927 PSR-E MB M43	-
01533571	RS378B P6 930 PSR-E MB M43	-
01533671	RS378B P6 930 PSR-E WB M43	-
01533771	RS378B P6 940 PSR-E NB M43	-
01534471	RS378B P6 930 PSD-E MB M43	-
01534571	RS378B P6 930 PSD-E WB M43	-
01534771	RS378B P6 940 PSD-E MB M43	-
01721252	RS378B P15 927 PSU-E NB M55	50,000 hour(s)
01721262	RS378B P15 930 PSU-E NB M55	50,000 hour(s)
01721272	RS378B P15 940 PSU-E NB M55	50,000 hour(s)
65006399	RS378B P15 927 PSU-E MB M55	50,000 hour(s)
01721292	RS378B P15 930 PSU-E MB M55	50,000 hour(s)

Order Code	Full Product Name	Median useful life L80B50
01721302	RS378B P15 940 PSU-E MB M55	50,000 hour(s)
65007099	RS378B P15 927 PSU-E WB M55	50,000 hour(s)
65010099	RS378B P15 930 PSU-E WB M55	50,000 hour(s)
65013199	RS378B P15 940 PSU-E WB M55	50,000 hour(s)

Order Code	Full Product Name	Median useful life L80B50
65069899	RS378B P15 927 PSR-E MB M55	50,000 hour(s)
65073599	RS378B P15 930 PSR-E WB M55	50,000 hour(s)
65076699	RS378B P15 940 PSR-E WB M55	50,000 hour(s)

