



**It delivers super flexibility, a complete product range and seamless system integration for hospitality customers..**

## **Greenspace Flex**

GreenSpace Flex is performance portfolio dedicated to Hospitality segment for GC/GM countries. With modular design concept, the light engines and different trims could have multiply of combination to satisfy diversified customer's requirement.

### **Benefits**

- Complete portfolio covering from 400lm to 3000lm, 3CCT and 3 beam angles.
- Super flexibility with modular design, and different trims to suit different application.
- Smart connectivity to seamlessly integration with Interact Hospitality.
- Deep recess for visual comfort
- Easy installation and maintenance

# Greenspace Flex

## Features

- 6w ~42w (400lm~3200lm)
- CRI 90, SDCM <3
- Beam Angle: NB, MB, WB
- CCT: 2700K, 3000K, 4000K
- High reliability, 50Khrs (L80B50@25°C)

## Application

- Guest room
- Bath room
- Corridor
- Lobby

## Specifications

|                                                 |                                                                                                                                               |
|-------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------|
| Mounting type                                   | Recessed                                                                                                                                      |
| Operating Temperature range                     | -20 to +45 °C                                                                                                                                 |
| Light Source                                    | COB                                                                                                                                           |
| Mains Voltage                                   | 220-240V AC/ 50-60Hz                                                                                                                          |
| Optical Accessories                             | available through ETO                                                                                                                         |
| Dimming                                         | PSU: non-dimmable<br>PSD: dimmable via Dali protocol<br>PSR: trailing dimmable<br>PSR 1-10V: 1-10v dimmable<br>DMX: dimmable via DMX protocol |
| Control system input                            | DALI / 1-10V / DMX / trailing edge                                                                                                            |
| Material                                        | Heat sink: die-cast aluminum                                                                                                                  |
| Main color of the luminaire                     | Housing: dark Grey<br>Reflector: color available through ETO                                                                                  |
| Lumen maintenance at median useful life 50.000h | L80                                                                                                                                           |
| Luminous flux                                   | 468-3990lm                                                                                                                                    |
| Power consumption                               | 6W-42W                                                                                                                                        |





|                                    |                                                                                                             |
|------------------------------------|-------------------------------------------------------------------------------------------------------------|
| Correlated color temperature - CCT | 2700K, 3000K, 4000K                                                                                         |
| Color Rendering index - CRI        | 90                                                                                                          |
| Beam angle                         | NB (Narrow Beam): 15-18°<br>MB (Medium Beam): 20-24°<br>WB (Wide Beam): 30-40°<br>VWB (Very Wide Beam): 50° |
| Protection Class IEC61140          | Class II & Class III for MR16 version                                                                       |
| Mechanical impact protection       | IK04                                                                                                        |
| Ingress protection                 | IP20 / IP54(Front side) for selected SKU only                                                               |
| Light source replaceable           | No                                                                                                          |
| Driver replaceable                 | yes                                                                                                         |
| Overall diameter                   | D55-D150                                                                                                    |
| Installation                       | recessed<br>Fixation by means of spring fasteners                                                           |

## Versions





Greenspace Flex, Prof GCGM

Dimensional drawing



| Modular Type      | D, mm | H, mm |
|-------------------|-------|-------|
| RS378B P6/P11 M55 | 55    | 49    |
| RS378B P15 M55    | 55    | 49    |
| RS378B P24 M70    | 70    | 90    |
| RS378B P33 M87    | 87    | 107   |
| RS378B P42 M102   | 102   | 116   |



## Light Technical

|                             |     |
|-----------------------------|-----|
| Color rendering index (CRI) | >90 |
| Optic type                  | -   |

## Operating and Electrical

|                      |                 |
|----------------------|-----------------|
| Protection class IEC | Safety class II |
| Input Voltage        | 220-240 V       |
| Line Frequency       | 50 or 60 Hz     |

## Mechanical and Housing

|                              |      |
|------------------------------|------|
| Optical cover type           | PMMA |
| Housing Color                | Grey |
| Mech. impact protection code | IK04 |
| Ingress protection code      | IP20 |

## Approval and Application

|                           |               |
|---------------------------|---------------|
| Ambient temperature range | -20 to +45 °C |
| CE mark                   | Yes           |
| ENEC mark                 | -             |
| Flammability mark         | -             |

## Initial Performance (IEC Compliant)

|                         |             |
|-------------------------|-------------|
| Luminous flux tolerance | -10% / +10% |
|-------------------------|-------------|

## General Information

| Order Code   | Full Product Name            | Driver included | Number of gear units |
|--------------|------------------------------|-----------------|----------------------|
| 911401535871 | RS378B P11 927 PSD-E NB M55  | -               | -                    |
| 911401536071 | RS378B P11 927 PSD-E WB M55  | -               | -                    |
| 911401536271 | RS378B P11 930 PSD-E MB M55  | -               | -                    |
| 911401536371 | RS378B P11 930 PSD-E WB M55  | -               | -                    |
| 911401536471 | RS378B P11 940 PSD-E NB M55  | -               | -                    |
| 911401536571 | RS378B P11 940 PSD-E MB M55  | -               | -                    |
| 911401536671 | RS378B P11 940 PSD-E WB M55  | -               | -                    |
| 911401720892 | RS378B P6 927 PSU-E NB M55   | Yes             | 1 unit               |
| 911401720902 | RS378B P6 930 PSU-E NB M55   | Yes             | 1 unit               |
| 911401720912 | RS378B P6 940 PSU-E NB M55   | Yes             | 1 unit               |
| 911401720932 | RS378B P6 930 PSU-E MB M55   | Yes             | 1 unit               |
| 911401720942 | RS378B P6 940 PSU-E MB M55   | Yes             | 1 unit               |
| 911401720952 | RS378B P6 927 PSU-E WB M55   | Yes             | 1 unit               |
| 911401720962 | RS378B P6 930 PSU-E WB M55   | Yes             | 1 unit               |
| 911401720972 | RS378B P6 940 PSU-E WB M55   | Yes             | 1 unit               |
| 911401720992 | RS378B P11 930 PSU-E NB M55  | Yes             | 1 unit               |
| 911401721002 | RS378B P11 940 PSU-E NB M55  | Yes             | 1 unit               |
| 911401721012 | RS378B P11 927 PSU-E MB M55  | Yes             | 1 unit               |
| 911401721022 | RS378B P11 930 PSU-E MB M55  | Yes             | 1 unit               |
| 911401721032 | RS378B P11 940 PSU-E MB M55  | Yes             | 1 unit               |
| 911401721042 | RS378B P11 927 PSU-E WB M55  | Yes             | 1 unit               |
| 911401721052 | RS378B P11 930 PSU-E WB M55  | Yes             | 1 unit               |
| 911401721062 | RS378B P11 940 PSU-E WB M55  | Yes             | 1 unit               |
| 911401721112 | RS378B P6 930 PSR-E MB M55   | Yes             | 1 unit               |
| 911401721192 | RS378B P11 927 PSR-E MB M55  | Yes             | 1 unit               |
| 911401721222 | RS378B P11 927 PSR-E WB M55  | Yes             | 1 unit               |
| 911401721232 | RS378B P11 930 PSR-E WB M55  | Yes             | 1 unit               |
| 911401721622 | RS378B P42 930 PSU-E NB M102 | Yes             | 1 unit               |
| 911401721632 | RS378B P42 940 PSU-E NB M102 | Yes             | 1 unit               |
| 911401721642 | RS378B P42 927 PSU-E MB M102 | Yes             | 1 unit               |
| 911401721652 | RS378B P42 930 PSU-E MB M102 | Yes             | 1 unit               |
| 911401721662 | RS378B P42 940 PSU-E MB M102 | Yes             | 1 unit               |
| 911401721682 | RS378B P42 930 PSU-E WB M102 | Yes             | 1 unit               |
| 911401721692 | RS378B P42 940 PSU-E WB M102 | Yes             | 1 unit               |
| 911401534971 | RS378B P6 927 PSD-E NB M55   | -               | -                    |
| 911401535071 | RS378B P6 927 PSD-E MB M55   | -               | -                    |
| 911401535171 | RS378B P6 927 PSD-E WB M55   | -               | -                    |
| 911401535371 | RS378B P6 930 PSD-E MB M55   | -               | -                    |
| 911401535471 | RS378B P6 930 PSD-E WB M55   | -               | -                    |
| 911401535571 | RS378B P6 940 PSD-E NB M55   | -               | -                    |
| 911401537771 | RS378B P24 927 PSD-E MB M70  | -               | -                    |
| 911401538071 | RS378B P24 930 PSD-E MB M70  | -               | -                    |
| 911401538171 | RS378B P24 930 PSD-E WB M70  | -               | -                    |
| 911401538271 | RS378B P24 940 PSD-E NB M70  | -               | -                    |
| 911401538371 | RS378B P24 940 PSD-E MB M70  | -               | -                    |
| 911401538471 | RS378B P24 940 PSD-E WB M70  | -               | -                    |
| 911401721432 | RS378B P24 927 PSU-E NB M70  | Yes             | 1 unit               |
| 911401721442 | RS378B P24 930 PSU-E NB M70  | Yes             | 1 unit               |
| 911401721452 | RS378B P24 940 PSU-E NB M70  | Yes             | 1 unit               |
| 911401721472 | RS378B P24 930 PSU-E MB M70  | Yes             | 1 unit               |
| 911401721482 | RS378B P24 940 PSU-E MB M70  | Yes             | 1 unit               |

| Order Code   | Full Product Name                 | Driver included | Number of gear units |
|--------------|-----------------------------------|-----------------|----------------------|
| 911401721492 | RS378B P24 927 PSU-E WB M70       | Yes             | 1 unit               |
| 911401721502 | RS378B P24 930 PSU-E WB M70       | Yes             | 1 unit               |
| 911401721512 | RS378B P24 940 PSU-E WB M70       | Yes             | 1 unit               |
| 911401538571 | RS378B P33 927 PSD-E NB M87       | -               | -                    |
| 911401538671 | RS378B P33 927 PSD-E MB M87       | -               | -                    |
| 911401538871 | RS378B P33 930 PSD-E NB M87       | -               | -                    |
| 911401539171 | RS378B P33 940 PSD-E NB M87       | -               | -                    |
| 911401721522 | RS378B P33 927 PSU-E NB M87       | Yes             | 1 unit               |
| 911401721532 | RS378B P33 930 PSU-E NB M87       | Yes             | 1 unit               |
| 911401721542 | RS378B P33 940 PSU-E NB M87       | Yes             | 1 unit               |
| 911401721562 | RS378B P33 930 PSU-E MB M87       | Yes             | 1 unit               |
| 911401721572 | RS378B P33 940 PSU-E MB M87       | Yes             | 1 unit               |
| 911401721592 | RS378B P33 930 PSU-E WB M87       | Yes             | 1 unit               |
| 911401721602 | RS378B P33 940 PSU-E WB M87       | Yes             | 1 unit               |
| 911401539571 | RS378B P42 927 PSD-E MB M102      | -               | -                    |
| 911401539871 | RS378B P42 930 PSD-E MB M102      | -               | -                    |
| 911401539971 | RS378B P42 930 PSD-E WB M102      | -               | -                    |
| 911401540271 | RS378B P42 940 PSD-E WB M102      | -               | -                    |
| 911401545571 | RS378B P11 930 PSU-E WW S         | -               | -                    |
| 911401545671 | RS378B P11 940 PSU-E WW S         | -               | -                    |
| 911401546571 | RS378B P11 940 PSD-E WW S         | -               | -                    |
| 911401545971 | RS378B P15 940 PSU-E WW S         | -               | -                    |
| 911401546771 | RS378B P15 930 PSD-E WW S         | -               | -                    |
| 911401536771 | RS378B P15 927 PSD-E NB M55       | -               | -                    |
| 911401536871 | RS378B P15 927 PSD-E MB M55       | -               | -                    |
| 911401537171 | RS378B P15 930 PSD-E MB M55       | -               | -                    |
| 911401537271 | RS378B P15 930 PSD-E WB M55       | -               | -                    |
| 911401537371 | RS378B P15 940 PSD-E NB M55       | -               | -                    |
| 911401537471 | RS378B P15 940 PSD-E MB M55       | -               | -                    |
| 911401537571 | RS378B P15 940 PSD-E WB M55       | -               | -                    |
| 911401540471 | RS378B P15 927 PSR-E 1-10V MB M55 | -               | -                    |
| 911401540771 | RS378B P15 930 PSR-E 1-10V MB M55 | -               | -                    |
| 911401540871 | RS378B P15 930 PSR-E 1-10V WB M55 | -               | -                    |
| 911401541171 | RS378B P15 940 PSR-E 1-10V WB M55 | -               | -                    |
| 911401532371 | RS378B P6 927 PSU-E MB M43        | -               | -                    |
| 911401532471 | RS378B P6 927 PSU-E WB M43        | -               | -                    |
| 911401532571 | RS378B P6 930 PSU-E NB M43        | -               | -                    |
| 911401532671 | RS378B P6 930 PSU-E MB M43        | -               | -                    |
| 911401532771 | RS378B P6 930 PSU-E WB M43        | -               | -                    |
| 911401532871 | RS378B P6 940 PSU-E NB M43        | -               | -                    |
| 911401532971 | RS378B P6 940 PSU-E MB M43        | -               | -                    |
| 911401533071 | RS378B P6 940 PSU-E WB M43        | -               | -                    |
| 911401533271 | RS378B P6 927 PSR-E MB M43        | -               | -                    |
| 911401533571 | RS378B P6 930 PSR-E MB M43        | -               | -                    |
| 911401533671 | RS378B P6 930 PSR-E WB M43        | -               | -                    |
| 911401533771 | RS378B P6 940 PSR-E NB M43        | -               | -                    |
| 911401534471 | RS378B P6 930 PSD-E MB M43        | -               | -                    |
| 911401534571 | RS378B P6 930 PSD-E WB M43        | -               | -                    |
| 911401534771 | RS378B P6 940 PSD-E MB M43        | -               | -                    |
| 911401721252 | RS378B P15 927 PSU-E NB M55       | Yes             | 1 unit               |
| 911401721262 | RS378B P15 930 PSU-E NB M55       | Yes             | 1 unit               |
| 911401721272 | RS378B P15 940 PSU-E NB M55       | Yes             | 1 unit               |

| Order Code   | Full Product Name           | Driver included | Number of gear units |
|--------------|-----------------------------|-----------------|----------------------|
| 911401721292 | RS378B P15 930 PSU-E MB M55 | Yes             | 1 unit               |
| 911401721302 | RS378B P15 940 PSU-E MB M55 | Yes             | 1 unit               |
| 911401721312 | RS378B P15 927 PSU-E WB M55 | Yes             | 1 unit               |
| 911401721322 | RS378B P15 930 PSU-E WB M55 | Yes             | 1 unit               |
| 911401721332 | RS378B P15 940 PSU-E WB M55 | Yes             | 1 unit               |
| 911401721372 | RS378B P15 927 PSR-E MB M55 | Yes             | 1 unit               |
| 911401721412 | RS378B P15 930 PSR-E WB M55 | Yes             | 1 unit               |
| 911401721422 | RS378B P15 940 PSR-E WB M55 | Yes             | 1 unit               |

Light Technical

| Order Code   | Full Product Name           | Beam angle of light source | Correlated Color Temperature (Nom) | Luminous Efficacy (rated) (Nom) | Luminous Flux |
|--------------|-----------------------------|----------------------------|------------------------------------|---------------------------------|---------------|
| 911401535871 | RS378B P11 927 PSD-E NB M55 | -                          | 2700 K                             | 97 lm/W                         | 580 lm        |
| 911401536071 | RS378B P11 927 PSD-E WB M55 | -                          | 2700 K                             | 110 lm/W                        | 660 lm        |
| 911401536271 | RS378B P11 930 PSD-E MB M55 | -                          | 3000 K                             | 87 lm/W                         | 957 lm        |
| 911401536371 | RS378B P11 930 PSD-E WB M55 | -                          | 3000 K                             | 87 lm/W                         | 957 lm        |
| 911401536471 | RS378B P11 940 PSD-E NB M55 | -                          | 4000 K                             | 78 lm/W                         | 858 lm        |
| 911401536571 | RS378B P11 940 PSD-E MB M55 | -                          | 4000 K                             | 92 lm/W                         | 1,012 lm      |
| 911401536671 | RS378B P11 940 PSD-E WB M55 | -                          | 4000 K                             | 92 lm/W                         | 1,012 lm      |
| 911401720892 | RS378B P6 927 PSU-E NB M55  | - degree(s)                | 2700 K                             | 92 lm/W                         | 3,864 lm      |
| 911401720902 | RS378B P6 930 PSU-E NB M55  | - degree(s)                | 3000 K                             | 87 lm/W                         | 1,305 lm      |
| 911401720912 | RS378B P6 940 PSU-E NB M55  | - degree(s)                | 4000 K                             | 80 lm/W                         | 1,200 lm      |
| 911401720932 | RS378B P6 930 PSU-E MB M55  | - degree(s)                | 3000 K                             | 97 lm/W                         | 4,074 lm      |
| 911401720942 | RS378B P6 940 PSU-E MB M55  | - degree(s)                | 4000 K                             | 82 lm/W                         | 900 lm        |
| 911401720952 | RS378B P6 927 PSU-E WB M55  | - degree(s)                | 2700 K                             | 92 lm/W                         | 3,864 lm      |
| 911401720962 | RS378B P6 930 PSU-E WB M55  | - degree(s)                | 3000 K                             | 100 lm/W                        | 1,500 lm      |
| 911401720972 | RS378B P6 940 PSU-E WB M55  | - degree(s)                | 4000 K                             | 93 lm/W                         | 1,400 lm      |

| Order Code   | Full Product Name            | Beam angle of light source | Correlated Color Temperature (Nom) | Luminous Efficacy (rated) (Nom) | Luminous Flux |
|--------------|------------------------------|----------------------------|------------------------------------|---------------------------------|---------------|
| 911401720992 | RS378B P11 930 PSU-E NB M55  | -                          | 3000 K                             | 85 lm/W                         | 510 lm        |
| 911401721002 | RS378B P11 940 PSU-E NB M55  | -                          | 4000 K                             | 95 lm/W                         | 570 lm        |
| 911401721012 | RS378B P11 927 PSU-E MB M55  | -                          | 2700 K                             | 87 lm/W                         | 957 lm        |
| 911401721022 | RS378B P11 930 PSU-E MB M55  | -                          | 3000 K                             | 85 lm/W                         | 510 lm        |
| 911401721032 | RS378B P11 940 PSU-E MB M55  | -                          | 4000 K                             | 90 lm/W                         | 540 lm        |
| 911401721042 | RS378B P11 927 PSU-E WB M55  | -                          | 2700 K                             | 87 lm/W                         | 957 lm        |
| 911401721052 | RS378B P11 930 PSU-E WB M55  | -                          | 3000 K                             | 90 lm/W                         | 540 lm        |
| 911401721062 | RS378B P11 940 PSU-E WB M55  | -                          | 4000 K                             | 95 lm/W                         | 570 lm        |
| 911401721112 | RS378B P6 930 PSR-E MB M55   | -                          | 3000 K                             | 75 lm/W                         | 450 lm        |
| 911401721192 | RS378B P11 927 PSR-E MB M55  | -                          | 2700 K                             | 85 lm/W                         | 510 lm        |
| 911401721222 | RS378B P11 927 PSR-E WB M55  | -                          | 2700 K                             | 85 lm/W                         | 510 lm        |
| 911401721232 | RS378B P11 930 PSR-E WB M55  | -                          | 3000 K                             | 87 lm/W                         | 957 lm        |
| 911401721622 | RS378B P42 930 PSU-E NB M102 | -                          | 3000 K                             | 71 lm/W                         | 2,350 lm      |
| 911401721632 | RS378B P42 940 PSU-E NB M102 | -                          | 4000 K                             | 73 lm/W                         | 2,400 lm      |

## Greenspace Flex

| Order Code   | Full Product Name                  | Beam angle of light source | Correlated Color Temperature (Nom) | Luminous Efficacy (rated) (Nom) | Luminous Flux |
|--------------|------------------------------------|----------------------------|------------------------------------|---------------------------------|---------------|
| 911401721642 | RS378B P42<br>927 PSU-E MB<br>M102 | -                          | 2700 K                             | 106 lm/W                        | 2,540 lm      |
| 911401721652 | RS378B P42<br>930 PSU-E MB<br>M102 | - degree(s)                | 3000 K                             | 71 lm/W                         | 2,350 lm      |
| 911401721662 | RS378B P42<br>940 PSU-E MB<br>M102 | - degree(s)                | 4000 K                             | 73 lm/W                         | 2,400 lm      |
| 911401721682 | RS378B P42<br>930 PSU-E WB<br>M102 | - degree(s)                | 3000 K                             | 71 lm/W                         | 2,350 lm      |
| 911401721692 | RS378B P42<br>940 PSU-E WB<br>M102 | - degree(s)                | 4000 K                             | 73 lm/W                         | 2,400 lm      |
| 911401534971 | RS378B P6 927<br>PSD-E NB M55      | -                          | 2700 K                             | 95 lm/W                         | 570 lm        |
| 911401535071 | RS378B P6 927<br>PSD-E MB M55      | -                          | 2700 K                             | 100 lm/W                        | 600 lm        |
| 911401535171 | RS378B P6 927<br>PSD-E WB M55      | -                          | 2700 K                             | 100 lm/W                        | 600 lm        |
| 911401535371 | RS378B P6 930<br>PSD-E MB M55      | -                          | 3000 K                             | 100 lm/W                        | 600 lm        |
| 911401535471 | RS378B P6 930<br>PSD-E WB M55      | -                          | 3000 K                             | 100 lm/W                        | 600 lm        |
| 911401535571 | RS378B P6 940<br>PSD-E NB M55      | -                          | 4000 K                             | 88 lm/W                         | 530 lm        |
| 911401537771 | RS378B P24<br>927 PSD-E MB<br>M70  | -                          | 2700 K                             | 100 lm/W                        | 1,500 lm      |
| 911401538071 | RS378B P24<br>930 PSD-E MB<br>M70  | -                          | 3000 K                             | 98 lm/W                         | 2,350 lm      |
| 911401538171 | RS378B P24<br>930 PSD-E WB<br>M70  | -                          | 3000 K                             | 98 lm/W                         | 2,350 lm      |
| 911401538271 | RS378B P24<br>940 PSD-E NB<br>M70  | -                          | 4000 K                             | 100 lm/W                        | 2,400 lm      |
| 911401538371 | RS378B P24<br>940 PSD-E MB<br>M70  | -                          | 4000 K                             | 100 lm/W                        | 2,400 lm      |
| 911401538471 | RS378B P24<br>940 PSD-E WB<br>M70  | -                          | 4000 K                             | 100 lm/W                        | 2,400 lm      |
| 911401721432 | RS378B P24<br>927 PSU-E NB<br>M70  | -                          | 2700 K                             | 92 lm/W                         | 1,012 lm      |

| Order Code   | Full Product Name                 | Beam angle of light source | Correlated Color Temperature (Nom) | Luminous Efficacy (rated) (Nom) | Luminous Flux |
|--------------|-----------------------------------|----------------------------|------------------------------------|---------------------------------|---------------|
| 911401721442 | RS378B P24<br>930 PSU-E NB<br>M70 | -                          | 3000 K                             | 100 lm/W                        | 1,100 lm      |
| 911401721452 | RS378B P24<br>940 PSU-E NB<br>M70 | -                          | 4000 K                             | 78 lm/W                         | 1,170 lm      |
| 911401721472 | RS378B P24<br>930 PSU-E MB<br>M70 | -                          | 3000 K                             | 100 lm/W                        | 1,100 lm      |
| 911401721482 | RS378B P24<br>940 PSU-E MB<br>M70 | -                          | 4000 K                             | 90 lm/W                         | 1,350 lm      |
| 911401721492 | RS378B P24<br>927 PSU-E WB<br>M70 | -                          | 2700 K                             | 92 lm/W                         | 1,012 lm      |
| 911401721502 | RS378B P24<br>930 PSU-E WB<br>M70 | -                          | 3000 K                             | 76 lm/W                         | 1,140 lm      |
| 911401721512 | RS378B P24<br>940 PSU-E WB<br>M70 | -                          | 4000 K                             | 94 lm/W                         | 1,410 lm      |
| 911401538571 | RS378B P33<br>927 PSD-E NB<br>M87 | -                          | 2700 K                             | 106 lm/W                        | 2,540 lm      |
| 911401538671 | RS378B P33<br>927 PSD-E MB<br>M87 | -                          | 2700 K                             | 106 lm/W                        | 2,540 lm      |
| 911401538871 | RS378B P33<br>930 PSD-E NB<br>M87 | -                          | 3000 K                             | 71 lm/W                         | 2,350 lm      |
| 911401539171 | RS378B P33<br>940 PSD-E NB<br>M87 | -                          | 4000 K                             | 73 lm/W                         | 2,400 lm      |
| 911401721522 | RS378B P33<br>927 PSU-E NB<br>M87 | -                          | 2700 K                             | 100 lm/W                        | 1,500 lm      |
| 911401721532 | RS378B P33<br>930 PSU-E NB<br>M87 | -                          | 3000 K                             | 98 lm/W                         | 2,350 lm      |
| 911401721542 | RS378B P33<br>940 PSU-E NB<br>M87 | -                          | 4000 K                             | 100 lm/W                        | 2,400 lm      |
| 911401721562 | RS378B P33<br>930 PSU-E MB<br>M87 | -                          | 3000 K                             | 98 lm/W                         | 2,350 lm      |
| 911401721572 | RS378B P33<br>940 PSU-E MB<br>M87 | -                          | 4000 K                             | 100 lm/W                        | 2,400 lm      |

| Order Code   | Full Product Name                  | Beam angle of light source | Correlated Color Temperature (Nom) | Luminous Efficacy (rated) (Nom) | Luminous Flux |
|--------------|------------------------------------|----------------------------|------------------------------------|---------------------------------|---------------|
| 911401721592 | RS378B P33<br>930 PSU-E WB<br>M87  | -                          | 3000 K                             | 98 lm/W                         | 2,350 lm      |
| 911401721602 | RS378B P33<br>940 PSU-E WB<br>M87  | -                          | 4000 K                             | 100 lm/W                        | 2,400 lm      |
| 911401539571 | RS378B P42<br>927 PSD-E MB<br>M102 | -                          | 2700 K                             | 77 lm/W                         | 2,540 lm      |
| 911401539871 | RS378B P42<br>930 PSD-E MB<br>M102 | -                          | 3000 K                             | 92 lm/W                         | 3,864 lm      |
| 911401539971 | RS378B P42<br>930 PSD-E WB<br>M102 | -                          | 3000 K                             | 92 lm/W                         | 3,864 lm      |
| 911401540271 | RS378B P42<br>940 PSD-E WB<br>M102 | -                          | 4000 K                             | 97 lm/W                         | 4,074 lm      |
| 911401545571 | RS378B P11<br>930 PSU-E<br>WW S    | -                          | 3000 K                             | 90 lm/W                         | 540 lm        |
| 911401545671 | RS378B P11<br>940 PSU-E<br>WW S    | -                          | 4000 K                             | 95 lm/W                         | 570 lm        |
| 911401546571 | RS378B P11<br>940 PSD-E<br>WW S    | -                          | 4000 K                             | 90 lm/W                         | 2,150 lm      |
| 911401545971 | RS378B P15<br>940 PSU-E<br>WW S    | -                          | 4000 K                             | 87 lm/W                         | 957 lm        |
| 911401546771 | RS378B P15<br>930 PSD-E<br>WW S    | -                          | 3000 K                             | 82 lm/W                         | 900 lm        |
| 911401536771 | RS378B P15<br>927 PSD-E NB<br>M55  | -                          | 2700 K                             | 87 lm/W                         | 957 lm        |
| 911401536871 | RS378B P15<br>927 PSD-E MB<br>M55  | -                          | 2700 K                             | 100 lm/W                        | 1,100 lm      |
| 911401537171 | RS378B P15<br>930 PSD-E MB<br>M55  | -                          | 3000 K                             | 90 lm/W                         | 1,350 lm      |
| 911401537271 | RS378B P15<br>930 PSD-E WB<br>M55  | -                          | 3000 K                             | 90 lm/W                         | 1,350 lm      |
| 911401537371 | RS378B P15<br>940 PSD-E NB<br>M55  | -                          | 4000 K                             | 78 lm/W                         | 1,170 lm      |

| Order Code   | Full Product Name                       | Beam angle of light source | Correlated Color Temperature (Nom) | Luminous Efficacy (rated) (Nom) | Luminous Flux |
|--------------|-----------------------------------------|----------------------------|------------------------------------|---------------------------------|---------------|
| 911401537471 | RS378B P15<br>940 PSD-E MB<br>M55       | -                          | 4000 K                             | 94 lm/W                         | 1,410 lm      |
| 911401537571 | RS378B P15<br>940 PSD-E WB<br>M55       | -                          | 4000 K                             | 94 lm/W                         | 1,410 lm      |
| 911401540471 | RS378B P15<br>927 PSR-E<br>1-10V MB M55 | -                          | 2700 K                             | 104 lm/W                        | 4,386 lm      |
| 911401540771 | RS378B P15<br>930 PSR-E<br>1-10V MB M55 | -                          | 3000 K                             | 90 lm/W                         | 1,350 lm      |
| 911401540871 | RS378B P15<br>930 PSR-E<br>1-10V WB M55 | -                          | 3000 K                             | 90 lm/W                         | 1,350 lm      |
| 911401541171 | RS378B P15<br>940 PSR-E<br>1-10V WB M55 | -                          | 4000 K                             | 94 lm/W                         | 1,410 lm      |
| 911401532371 | RS378B P6 927<br>PSU-E MB M43           | -                          | 2700 K                             | 77 lm/W                         | 2,540 lm      |
| 911401532471 | RS378B P6 927<br>PSU-E WB M43           | -                          | 2700 K                             | 92 lm/W                         | 3,864 lm      |
| 911401532571 | RS378B P6 930<br>PSU-E NB M43           | -                          | 3000 K                             | 97 lm/W                         | 4,074 lm      |
| 911401532671 | RS378B P6 930<br>PSU-E MB M43           | -                          | 3000 K                             | 97 lm/W                         | 4,074 lm      |
| 911401532771 | RS378B P6 930<br>PSU-E WB M43           | -                          | 3000 K                             | 100 lm/W                        | 1,500 lm      |
| 911401532871 | RS378B P6 940<br>PSU-E NB M43           | -                          | 4000 K                             | 89 lm/W                         | 980 lm        |
| 911401532971 | RS378B P6 940<br>PSU-E MB M43           | -                          | 4000 K                             | 73 lm/W                         | 800 lm        |
| 911401533071 | RS378B P6 940<br>PSU-E WB M43           | -                          | 4000 K                             | 87 lm/W                         | 1,300 lm      |
| 911401533271 | RS378B P6 927<br>PSR-E MB M43           | -                          | 2700 K                             | 104 lm/W                        | 4,386 lm      |
| 911401533571 | RS378B P6 930<br>PSR-E MB M43           | -                          | 3000 K                             | 58 lm/W                         | 348 lm        |
| 911401533671 | RS378B P6 930<br>PSR-E WB M43           | -                          | 3000 K                             | 58 lm/W                         | 348 lm        |
| 911401533771 | RS378B P6 940<br>PSR-E NB M43           | -                          | 4000 K                             | 60 lm/W                         | 360 lm        |
| 911401534471 | RS378B P6 930<br>PSD-E MB M43           | -                          | 3000 K                             | 89 lm/W                         | 535 lm        |
| 911401534571 | RS378B P6 930<br>PSD-E WB M43           | -                          | 3000 K                             | 89 lm/W                         | 535 lm        |
| 911401534771 | RS378B P6 940<br>PSD-E MB M43           | -                          | 4000 K                             | 93 lm/W                         | 560 lm        |

| Order Code   | Full Product Name           | Beam angle of light source | Correlated Color Temperature (Nom) | Luminous Efficacy (rated) (Nom) | Luminous Flux |
|--------------|-----------------------------|----------------------------|------------------------------------|---------------------------------|---------------|
| 911401721252 | RS378B P15 927 PSU-E NB M55 | -                          | 2700 K                             | 85 lm/W                         | 510 lm        |
| 911401721262 | RS378B P15 930 PSU-E NB M55 | -                          | 3000 K                             | 97 lm/W                         | 580 lm        |
| 911401721272 | RS378B P15 940 PSU-E NB M55 | -                          | 4000 K                             | 76 lm/W                         | 836 lm        |
| 911401721292 | RS378B P15 930 PSU-E MB M55 | -                          | 3000 K                             | 91 lm/W                         | 545 lm        |
| 911401721302 | RS378B P15 940 PSU-E MB M55 | -                          | 4000 K                             | 105 lm/W                        | 630 lm        |
| 911401721312 | RS378B P15 927 PSU-E WB M55 | -                          | 2700 K                             | 90 lm/W                         | 540 lm        |

| Order Code   | Full Product Name           | Beam angle of light source | Correlated Color Temperature (Nom) | Luminous Efficacy (rated) (Nom) | Luminous Flux |
|--------------|-----------------------------|----------------------------|------------------------------------|---------------------------------|---------------|
| 911401721322 | RS378B P15 930 PSU-E WB M55 | -                          | 3000 K                             | 97 lm/W                         | 580 lm        |
| 911401721332 | RS378B P15 940 PSU-E WB M55 | -                          | 4000 K                             | 87 lm/W                         | 957 lm        |
| 911401721372 | RS378B P15 927 PSR-E MB M55 | -                          | 2700 K                             | 100 lm/W                        | 1,100 lm      |
| 911401721412 | RS378B P15 930 PSR-E WB M55 | -                          | 3000 K                             | 90 lm/W                         | 1,350 lm      |
| 911401721422 | RS378B P15 940 PSR-E WB M55 | -                          | 4000 K                             | 94 lm/W                         | 1,410 lm      |

Operating and Electrical

| Order Code   | Full Product Name           | Power Consumption | Suitable for random switching |
|--------------|-----------------------------|-------------------|-------------------------------|
| 911401535871 | RS378B P11 927 PSD-E NB M55 | 11 W              | -                             |
| 911401536071 | RS378B P11 927 PSD-E WB M55 | 11 W              | -                             |
| 911401536271 | RS378B P11 930 PSD-E MB M55 | 11 W              | -                             |
| 911401536371 | RS378B P11 930 PSD-E WB M55 | 11 W              | -                             |
| 911401536471 | RS378B P11 940 PSD-E NB M55 | 11 W              | -                             |
| 911401536571 | RS378B P11 940 PSD-E MB M55 | 11 W              | -                             |
| 911401536671 | RS378B P11 940 PSD-E WB M55 | 11 W              | -                             |
| 911401720892 | RS378B P6 927 PSU-E NB M55  | 6 W               | No                            |
| 911401720902 | RS378B P6 930 PSU-E NB M55  | 6 W               | No                            |
| 911401720912 | RS378B P6 940 PSU-E NB M55  | 6 W               | No                            |
| 911401720932 | RS378B P6 930 PSU-E MB M55  | 6 W               | No                            |
| 911401720942 | RS378B P6 940 PSU-E MB M55  | 6 W               | No                            |
| 911401720952 | RS378B P6 927 PSU-E WB M55  | 6 W               | No                            |
| 911401720962 | RS378B P6 930 PSU-E WB M55  | 6 W               | No                            |
| 911401720972 | RS378B P6 940 PSU-E WB M55  | 6 W               | No                            |
| 911401720992 | RS378B P11 930 PSU-E NB M55 | 11 W              | No                            |
| 911401721002 | RS378B P11 940 PSU-E NB M55 | 11 W              | No                            |
| 911401721012 | RS378B P11 927 PSU-E MB M55 | 11 W              | No                            |
| 911401721022 | RS378B P11 930 PSU-E MB M55 | 11 W              | No                            |
| 911401721032 | RS378B P11 940 PSU-E MB M55 | 11 W              | No                            |
| 911401721042 | RS378B P11 927 PSU-E WB M55 | 11 W              | No                            |
| 911401721052 | RS378B P11 930 PSU-E WB M55 | 11 W              | No                            |
| 911401721062 | RS378B P11 940 PSU-E WB M55 | 11 W              | No                            |
| 911401721112 | RS378B P6 930 PSR-E MB M55  | 6 W               | No                            |
| 911401721192 | RS378B P11 927 PSR-E MB M55 | 11 W              | No                            |

| Order Code   | Full Product Name            | Power Consumption | Suitable for random switching |
|--------------|------------------------------|-------------------|-------------------------------|
| 911401721222 | RS378B P11 927 PSR-E WB M55  | 11 W              | No                            |
| 911401721232 | RS378B P11 930 PSR-E WB M55  | 11 W              | No                            |
| 911401721622 | RS378B P42 930 PSU-E NB M102 | 42 W              | No                            |
| 911401721632 | RS378B P42 940 PSU-E NB M102 | 42 W              | No                            |
| 911401721642 | RS378B P42 927 PSU-E MB M102 | 42 W              | No                            |
| 911401721652 | RS378B P42 930 PSU-E MB M102 | 42 W              | No                            |
| 911401721662 | RS378B P42 940 PSU-E MB M102 | 42 W              | No                            |
| 911401721682 | RS378B P42 930 PSU-E WB M102 | 42 W              | No                            |
| 911401721692 | RS378B P42 940 PSU-E WB M102 | 42 W              | No                            |
| 911401534971 | RS378B P6 927 PSD-E NB M55   | 6 W               | -                             |
| 911401535071 | RS378B P6 927 PSD-E MB M55   | 6 W               | -                             |
| 911401535171 | RS378B P6 927 PSD-E WB M55   | 6 W               | -                             |
| 911401535371 | RS378B P6 930 PSD-E MB M55   | 6 W               | -                             |
| 911401535471 | RS378B P6 930 PSD-E WB M55   | 6 W               | -                             |
| 911401535571 | RS378B P6 940 PSD-E NB M55   | 6 W               | -                             |
| 911401537771 | RS378B P24 927 PSD-E MB M70  | 24 W              | -                             |
| 911401538071 | RS378B P24 930 PSD-E MB M70  | 24 W              | -                             |
| 911401538171 | RS378B P24 930 PSD-E WB M70  | 24 W              | -                             |
| 911401538271 | RS378B P24 940 PSD-E NB M70  | 24 W              | -                             |
| 911401538371 | RS378B P24 940 PSD-E MB M70  | 24 W              | -                             |
| 911401538471 | RS378B P24 940 PSD-E WB M70  | 24 W              | -                             |
| 911401721432 | RS378B P24 927 PSU-E NB M70  | 24 W              | No                            |
| 911401721442 | RS378B P24 930 PSU-E NB M70  | 24 W              | No                            |
| 911401721452 | RS378B P24 940 PSU-E NB M70  | 24 W              | No                            |
| 911401721472 | RS378B P24 930 PSU-E MB M70  | 24 W              | No                            |

| Order Code   | Full Product Name                 | Power Consumption | Suitable for random switching |
|--------------|-----------------------------------|-------------------|-------------------------------|
| 911401721482 | RS378B P24 940 PSU-E MB M70       | 24 W              | No                            |
| 911401721492 | RS378B P24 927 PSU-E WB M70       | 24 W              | No                            |
| 911401721502 | RS378B P24 930 PSU-E WB M70       | 24 W              | No                            |
| 911401721512 | RS378B P24 940 PSU-E WB M70       | 24 W              | No                            |
| 911401538571 | RS378B P33 927 PSD-E NB M87       | 33 W              | -                             |
| 911401538671 | RS378B P33 927 PSD-E MB M87       | 33 W              | -                             |
| 911401538871 | RS378B P33 930 PSD-E NB M87       | 33 W              | -                             |
| 911401539171 | RS378B P33 940 PSD-E NB M87       | 33 W              | -                             |
| 911401721522 | RS378B P33 927 PSU-E NB M87       | 33 W              | No                            |
| 911401721532 | RS378B P33 930 PSU-E NB M87       | 33 W              | No                            |
| 911401721542 | RS378B P33 940 PSU-E NB M87       | 33 W              | No                            |
| 911401721562 | RS378B P33 930 PSU-E MB M87       | 33 W              | No                            |
| 911401721572 | RS378B P33 940 PSU-E MB M87       | 33 W              | No                            |
| 911401721592 | RS378B P33 930 PSU-E WB M87       | 33 W              | No                            |
| 911401721602 | RS378B P33 940 PSU-E WB M87       | 33 W              | No                            |
| 911401539571 | RS378B P42 927 PSD-E MB M102      | 42 W              | -                             |
| 911401539871 | RS378B P42 930 PSD-E MB M102      | 42 W              | -                             |
| 911401539971 | RS378B P42 930 PSD-E WB M102      | 42 W              | -                             |
| 911401540271 | RS378B P42 940 PSD-E WB M102      | 42 W              | -                             |
| 911401545571 | RS378B P11 930 PSU-E WW S         | 11 W              | -                             |
| 911401545671 | RS378B P11 940 PSU-E WW S         | 11 W              | -                             |
| 911401546571 | RS378B P11 940 PSD-E WW S         | 11 W              | -                             |
| 911401545971 | RS378B P15 940 PSU-E WW S         | 15 W              | -                             |
| 911401546771 | RS378B P15 930 PSD-E WW S         | 15 W              | -                             |
| 911401536771 | RS378B P15 927 PSD-E NB M55       | 15 W              | -                             |
| 911401536871 | RS378B P15 927 PSD-E MB M55       | 15 W              | -                             |
| 911401537171 | RS378B P15 930 PSD-E MB M55       | 15 W              | -                             |
| 911401537271 | RS378B P15 930 PSD-E WB M55       | 15 W              | -                             |
| 911401537371 | RS378B P15 940 PSD-E NB M55       | 15 W              | -                             |
| 911401537471 | RS378B P15 940 PSD-E MB M55       | 15 W              | -                             |
| 911401537571 | RS378B P15 940 PSD-E WB M55       | 15 W              | -                             |
| 911401540471 | RS378B P15 927 PSR-E 1-10V MB M55 | 15 W              | -                             |

| Order Code   | Full Product Name                 | Power Consumption | Suitable for random switching |
|--------------|-----------------------------------|-------------------|-------------------------------|
| 911401540771 | RS378B P15 930 PSR-E 1-10V MB M55 | 15 W              | -                             |
| 911401540871 | RS378B P15 930 PSR-E 1-10V WB M55 | 15 W              | -                             |
| 911401541171 | RS378B P15 940 PSR-E 1-10V WB M55 | 15 W              | -                             |
| 911401532371 | RS378B P6 927 PSU-E MB M43        | 6 W               | -                             |
| 911401532471 | RS378B P6 927 PSU-E WB M43        | 6 W               | -                             |
| 911401532571 | RS378B P6 930 PSU-E NB M43        | 6 W               | -                             |
| 911401532671 | RS378B P6 930 PSU-E MB M43        | 6 W               | -                             |
| 911401532771 | RS378B P6 930 PSU-E WB M43        | 6 W               | -                             |
| 911401532871 | RS378B P6 940 PSU-E NB M43        | 6 W               | -                             |
| 911401532971 | RS378B P6 940 PSU-E MB M43        | 6 W               | -                             |
| 911401533071 | RS378B P6 940 PSU-E WB M43        | 6 W               | -                             |
| 911401533271 | RS378B P6 927 PSR-E MB M43        | 6 W               | -                             |
| 911401533571 | RS378B P6 930 PSR-E MB M43        | 6 W               | -                             |
| 911401533671 | RS378B P6 930 PSR-E WB M43        | 6 W               | -                             |
| 911401533771 | RS378B P6 940 PSR-E NB M43        | 6 W               | -                             |
| 911401534471 | RS378B P6 930 PSD-E MB M43        | 6 W               | -                             |
| 911401534571 | RS378B P6 930 PSD-E WB M43        | 6 W               | -                             |
| 911401534771 | RS378B P6 940 PSD-E MB M43        | 6 W               | -                             |
| 911401721252 | RS378B P15 927 PSU-E NB M55       | 15 W              | No                            |
| 911401721262 | RS378B P15 930 PSU-E NB M55       | 15 W              | No                            |
| 911401721272 | RS378B P15 940 PSU-E NB M55       | 15 W              | No                            |
| 911401721292 | RS378B P15 930 PSU-E MB M55       | 15 W              | No                            |
| 911401721302 | RS378B P15 940 PSU-E MB M55       | 15 W              | No                            |
| 911401721312 | RS378B P15 927 PSU-E WB M55       | 15 W              | No                            |
| 911401721322 | RS378B P15 930 PSU-E WB M55       | 15 W              | No                            |
| 911401721332 | RS378B P15 940 PSU-E WB M55       | 15 W              | No                            |
| 911401721372 | RS378B P15 927 PSR-E MB M55       | 15 W              | No                            |
| 911401721412 | RS378B P15 930 PSR-E WB M55       | 15 W              | No                            |
| 911401721422 | RS378B P15 940 PSR-E WB M55       | 15 W              | No                            |

Controls and Dimming

| Order Code   | Full Product Name           | Dimmable | Maximum dim level |
|--------------|-----------------------------|----------|-------------------|
| 911401535871 | RS378B P11 927 PSD-E NB M55 | DALI     | -                 |
| 911401536071 | RS378B P11 927 PSD-E WB M55 | DALI     | -                 |
| 911401536271 | RS378B P11 930 PSD-E MB M55 | DALI     | -                 |
| 911401536371 | RS378B P11 930 PSD-E WB M55 | DALI     | -                 |
| 911401536471 | RS378B P11 940 PSD-E NB M55 | DALI     | -                 |
| 911401536571 | RS378B P11 940 PSD-E MB M55 | DALI     | -                 |
| 911401536671 | RS378B P11 940 PSD-E WB M55 | DALI     | -                 |
| 911401720892 | RS378B P6 927 PSU-E NB M55  | No       | Not applicable    |
| 911401720902 | RS378B P6 930 PSU-E NB M55  | No       | Not applicable    |
| 911401720912 | RS378B P6 940 PSU-E NB M55  | No       | Not applicable    |
| 911401720932 | RS378B P6 930 PSU-E MB M55  | No       | Not applicable    |
| 911401720942 | RS378B P6 940 PSU-E MB M55  | No       | Not applicable    |
| 911401720952 | RS378B P6 927 PSU-E WB M55  | No       | Not applicable    |

| Order Code   | Full Product Name           | Dimmable | Maximum dim level |
|--------------|-----------------------------|----------|-------------------|
| 911401720962 | RS378B P6 930 PSU-E WB M55  | No       | Not applicable    |
| 911401720972 | RS378B P6 940 PSU-E WB M55  | No       | Not applicable    |
| 911401720992 | RS378B P11 930 PSU-E NB M55 | No       | Not applicable    |
| 911401721002 | RS378B P11 940 PSU-E NB M55 | No       | Not applicable    |
| 911401721012 | RS378B P11 927 PSU-E MB M55 | No       | Not applicable    |
| 911401721022 | RS378B P11 930 PSU-E MB M55 | No       | Not applicable    |
| 911401721032 | RS378B P11 940 PSU-E MB M55 | No       | Not applicable    |
| 911401721042 | RS378B P11 927 PSU-E WB M55 | No       | Not applicable    |
| 911401721052 | RS378B P11 930 PSU-E WB M55 | No       | Not applicable    |
| 911401721062 | RS378B P11 940 PSU-E WB M55 | No       | Not applicable    |
| 911401721112 | RS378B P6 930 PSR-E MB M55  | TRIAC    | 10%               |
| 911401721192 | RS378B P11 927 PSR-E MB M55 | TRIAC    | 10%               |
| 911401721222 | RS378B P11 927 PSR-E WB M55 | TRIAC    | 10%               |

| Order Code   | Full Product Name            | Dimmable | Maximum dim level |
|--------------|------------------------------|----------|-------------------|
| 911401721232 | RS378B P11 930 PSR-E WB M55  | TRIAC    | 10%               |
| 911401721622 | RS378B P42 930 PSU-E NB M102 | No       | Not applicable    |
| 911401721632 | RS378B P42 940 PSU-E NB M102 | No       | Not applicable    |
| 911401721642 | RS378B P42 927 PSU-E MB M102 | No       | Not applicable    |
| 911401721652 | RS378B P42 930 PSU-E MB M102 | No       | Not applicable    |
| 911401721662 | RS378B P42 940 PSU-E MB M102 | No       | Not applicable    |
| 911401721682 | RS378B P42 930 PSU-E WB M102 | No       | Not applicable    |
| 911401721692 | RS378B P42 940 PSU-E WB M102 | No       | Not applicable    |
| 911401534971 | RS378B P6 927 PSD-E NB M55   | DALI     | -                 |
| 911401535071 | RS378B P6 927 PSD-E MB M55   | DALI     | -                 |
| 911401535171 | RS378B P6 927 PSD-E WB M55   | DALI     | -                 |
| 911401535371 | RS378B P6 930 PSD-E MB M55   | DALI     | -                 |
| 911401535471 | RS378B P6 930 PSD-E WB M55   | DALI     | -                 |
| 911401535571 | RS378B P6 940 PSD-E NB M55   | DALI     | -                 |
| 911401537771 | RS378B P24 927 PSD-E MB M70  | DALI     | -                 |
| 911401538071 | RS378B P24 930 PSD-E MB M70  | DALI     | -                 |
| 911401538171 | RS378B P24 930 PSD-E WB M70  | DALI     | -                 |
| 911401538271 | RS378B P24 940 PSD-E NB M70  | DALI     | -                 |
| 911401538371 | RS378B P24 940 PSD-E MB M70  | DALI     | -                 |
| 911401538471 | RS378B P24 940 PSD-E WB M70  | DALI     | -                 |
| 911401721432 | RS378B P24 927 PSU-E NB M70  | No       | Not applicable    |
| 911401721442 | RS378B P24 930 PSU-E NB M70  | No       | Not applicable    |
| 911401721452 | RS378B P24 940 PSU-E NB M70  | No       | Not applicable    |
| 911401721472 | RS378B P24 930 PSU-E MB M70  | No       | Not applicable    |
| 911401721482 | RS378B P24 940 PSU-E MB M70  | No       | Not applicable    |
| 911401721492 | RS378B P24 927 PSU-E WB M70  | No       | Not applicable    |
| 911401721502 | RS378B P24 930 PSU-E WB M70  | No       | Not applicable    |
| 911401721512 | RS378B P24 940 PSU-E WB M70  | No       | Not applicable    |
| 911401538571 | RS378B P33 927 PSD-E NB M87  | DALI     | -                 |
| 911401538671 | RS378B P33 927 PSD-E MB M87  | DALI     | -                 |
| 911401538871 | RS378B P33 930 PSD-E NB M87  | DALI     | -                 |
| 911401539171 | RS378B P33 940 PSD-E NB M87  | DALI     | -                 |
| 911401721522 | RS378B P33 927 PSU-E NB M87  | No       | Not applicable    |
| 911401721532 | RS378B P33 930 PSU-E NB M87  | No       | Not applicable    |
| 911401721542 | RS378B P33 940 PSU-E NB M87  | No       | Not applicable    |
| 911401721562 | RS378B P33 930 PSU-E MB M87  | No       | Not applicable    |
| 911401721572 | RS378B P33 940 PSU-E MB M87  | No       | Not applicable    |
| 911401721592 | RS378B P33 930 PSU-E WB M87  | No       | Not applicable    |
| 911401721602 | RS378B P33 940 PSU-E WB M87  | No       | Not applicable    |
| 911401539571 | RS378B P42 927 PSD-E MB M102 | DALI     | -                 |
| 911401539871 | RS378B P42 930 PSD-E MB M102 | DALI     | -                 |
| 911401539971 | RS378B P42 930 PSD-E WB M102 | DALI     | -                 |
| 911401540271 | RS378B P42 940 PSD-E WB M102 | DALI     | -                 |

Approval and Application

| Order Code   | Full Product Name           | Glow-wire test |
|--------------|-----------------------------|----------------|
| 911401535871 | RS378B P11 927 PSD-E NB M55 | -              |
| 911401536071 | RS378B P11 927 PSD-E WB M55 | -              |
| 911401536271 | RS378B P11 930 PSD-E MB M55 | -              |
| 911401536371 | RS378B P11 930 PSD-E WB M55 | -              |
| 911401536471 | RS378B P11 940 PSD-E NB M55 | -              |

| Order Code   | Full Product Name                 | Dimmable | Maximum dim level |
|--------------|-----------------------------------|----------|-------------------|
| 911401545571 | RS378B P11 930 PSU-E WW S         | No       | -                 |
| 911401545671 | RS378B P11 940 PSU-E WW S         | No       | -                 |
| 911401546571 | RS378B P11 940 PSD-E WW S         | DALI     | -                 |
| 911401545971 | RS378B P15 940 PSU-E WW S         | No       | -                 |
| 911401546771 | RS378B P15 930 PSD-E WW S         | DALI     | -                 |
| 911401536771 | RS378B P15 927 PSD-E NB M55       | DALI     | -                 |
| 911401536871 | RS378B P15 927 PSD-E MB M55       | DALI     | -                 |
| 911401537171 | RS378B P15 930 PSD-E MB M55       | DALI     | -                 |
| 911401537271 | RS378B P15 930 PSD-E WB M55       | DALI     | -                 |
| 911401537371 | RS378B P15 940 PSD-E NB M55       | DALI     | -                 |
| 911401537471 | RS378B P15 940 PSD-E MB M55       | DALI     | -                 |
| 911401537571 | RS378B P15 940 PSD-E WB M55       | DALI     | -                 |
| 911401540471 | RS378B P15 927 PSR-E 1-10V MB M55 | 1-10V    | -                 |
| 911401540771 | RS378B P15 930 PSR-E 1-10V MB M55 | 1-10V    | -                 |
| 911401540871 | RS378B P15 930 PSR-E 1-10V WB M55 | 1-10V    | -                 |
| 911401541171 | RS378B P15 940 PSR-E 1-10V WB M55 | 1-10V    | -                 |
| 911401532371 | RS378B P6 927 PSU-E MB M43        | No       | -                 |
| 911401532471 | RS378B P6 927 PSU-E WB M43        | No       | -                 |
| 911401532571 | RS378B P6 930 PSU-E NB M43        | No       | -                 |
| 911401532671 | RS378B P6 930 PSU-E MB M43        | No       | -                 |
| 911401532771 | RS378B P6 930 PSU-E WB M43        | No       | -                 |
| 911401532871 | RS378B P6 940 PSU-E NB M43        | No       | -                 |
| 911401532971 | RS378B P6 940 PSU-E MB M43        | No       | -                 |
| 911401533071 | RS378B P6 940 PSU-E WB M43        | No       | -                 |
| 911401533271 | RS378B P6 927 PSR-E MB M43        | TRIAC    | -                 |
| 911401533571 | RS378B P6 930 PSR-E MB M43        | TRIAC    | -                 |
| 911401533671 | RS378B P6 930 PSR-E WB M43        | TRIAC    | -                 |
| 911401533771 | RS378B P6 940 PSR-E NB M43        | TRIAC    | -                 |
| 911401534471 | RS378B P6 930 PSD-E MB M43        | DALI     | -                 |
| 911401534571 | RS378B P6 930 PSD-E WB M43        | DALI     | -                 |
| 911401534771 | RS378B P6 940 PSD-E MB M43        | DALI     | -                 |
| 911401721252 | RS378B P15 927 PSU-E NB M55       | No       | Not applicable    |
| 911401721262 | RS378B P15 930 PSU-E NB M55       | No       | Not applicable    |
| 911401721272 | RS378B P15 940 PSU-E NB M55       | No       | Not applicable    |
| 911401721292 | RS378B P15 930 PSU-E MB M55       | No       | Not applicable    |
| 911401721302 | RS378B P15 940 PSU-E MB M55       | No       | Not applicable    |
| 911401721312 | RS378B P15 927 PSU-E WB M55       | No       | Not applicable    |
| 911401721322 | RS378B P15 930 PSU-E WB M55       | No       | Not applicable    |
| 911401721332 | RS378B P15 940 PSU-E WB M55       | No       | Not applicable    |
| 911401721372 | RS378B P15 927 PSR-E MB M55       | TRIAC    | 10%               |
| 911401721412 | RS378B P15 930 PSR-E WB M55       | TRIAC    | 10%               |
| 911401721422 | RS378B P15 940 PSR-E WB M55       | TRIAC    | 10%               |

| Order Code   | Full Product Name           | Glow-wire test                    |
|--------------|-----------------------------|-----------------------------------|
| 911401536571 | RS378B P11 940 PSD-E MB M55 | -                                 |
| 911401536671 | RS378B P11 940 PSD-E WB M55 | -                                 |
| 911401720892 | RS378B P6 927 PSU-E NB M55  | Temperature 600 °C, duration 30 s |

| Order Code   | Full Product Name            | Glow-wire test                    |
|--------------|------------------------------|-----------------------------------|
| 911401720902 | RS378B P6 930 PSU-E NB M55   | Temperature 600 °C, duration 30 s |
| 911401720912 | RS378B P6 940 PSU-E NB M55   | Temperature 600 °C, duration 30 s |
| 911401720932 | RS378B P6 930 PSU-E MB M55   | Temperature 600 °C, duration 30 s |
| 911401720942 | RS378B P6 940 PSU-E MB M55   | Temperature 600 °C, duration 30 s |
| 911401720952 | RS378B P6 927 PSU-E WB M55   | Temperature 600 °C, duration 30 s |
| 911401720962 | RS378B P6 930 PSU-E WB M55   | Temperature 600 °C, duration 30 s |
| 911401720972 | RS378B P6 940 PSU-E WB M55   | Temperature 600 °C, duration 30 s |
| 911401720992 | RS378B P11 930 PSU-E NB M55  | Temperature 600 °C, duration 30 s |
| 911401721002 | RS378B P11 940 PSU-E NB M55  | Temperature 600 °C, duration 30 s |
| 911401721012 | RS378B P11 927 PSU-E MB M55  | Temperature 600 °C, duration 30 s |
| 911401721022 | RS378B P11 930 PSU-E MB M55  | Temperature 600 °C, duration 30 s |
| 911401721032 | RS378B P11 940 PSU-E MB M55  | Temperature 600 °C, duration 30 s |
| 911401721042 | RS378B P11 927 PSU-E WB M55  | Temperature 600 °C, duration 30 s |
| 911401721052 | RS378B P11 930 PSU-E WB M55  | Temperature 600 °C, duration 30 s |
| 911401721062 | RS378B P11 940 PSU-E WB M55  | Temperature 600 °C, duration 30 s |
| 911401721112 | RS378B P6 930 PSR-E MB M55   | Temperature 600 °C, duration 30 s |
| 911401721192 | RS378B P11 927 PSR-E MB M55  | Temperature 600 °C, duration 30 s |
| 911401721222 | RS378B P11 927 PSR-E WB M55  | Temperature 600 °C, duration 30 s |
| 911401721232 | RS378B P11 930 PSR-E WB M55  | Temperature 600 °C, duration 30 s |
| 911401721622 | RS378B P42 930 PSU-E NB M102 | Temperature 600 °C, duration 30 s |
| 911401721632 | RS378B P42 940 PSU-E NB M102 | Temperature 600 °C, duration 30 s |
| 911401721642 | RS378B P42 927 PSU-E MB M102 | Temperature 600 °C, duration 30 s |
| 911401721652 | RS378B P42 930 PSU-E MB M102 | Temperature 600 °C, duration 30 s |
| 911401721662 | RS378B P42 940 PSU-E MB M102 | Temperature 600 °C, duration 30 s |
| 911401721682 | RS378B P42 930 PSU-E WB M102 | Temperature 600 °C, duration 30 s |
| 911401721692 | RS378B P42 940 PSU-E WB M102 | Temperature 600 °C, duration 30 s |

| Order Code   | Full Product Name            | Glow-wire test                    |
|--------------|------------------------------|-----------------------------------|
| 911401534971 | RS378B P6 927 PSD-E NB M55   | -                                 |
| 911401535071 | RS378B P6 927 PSD-E MB M55   | -                                 |
| 911401535171 | RS378B P6 927 PSD-E WB M55   | -                                 |
| 911401535371 | RS378B P6 930 PSD-E MB M55   | -                                 |
| 911401535471 | RS378B P6 930 PSD-E WB M55   | -                                 |
| 911401535571 | RS378B P6 940 PSD-E NB M55   | -                                 |
| 911401537771 | RS378B P24 927 PSD-E MB M70  | -                                 |
| 911401538071 | RS378B P24 930 PSD-E MB M70  | -                                 |
| 911401538171 | RS378B P24 930 PSD-E WB M70  | -                                 |
| 911401538271 | RS378B P24 940 PSD-E NB M70  | -                                 |
| 911401538371 | RS378B P24 940 PSD-E MB M70  | -                                 |
| 911401538471 | RS378B P24 940 PSD-E WB M70  | -                                 |
| 911401721432 | RS378B P24 927 PSU-E NB M70  | Temperature 600 °C, duration 30 s |
| 911401721442 | RS378B P24 930 PSU-E NB M70  | Temperature 600 °C, duration 30 s |
| 911401721452 | RS378B P24 940 PSU-E NB M70  | Temperature 600 °C, duration 30 s |
| 911401721472 | RS378B P24 930 PSU-E MB M70  | Temperature 600 °C, duration 30 s |
| 911401721482 | RS378B P24 940 PSU-E MB M70  | Temperature 600 °C, duration 30 s |
| 911401721492 | RS378B P24 927 PSU-E WB M70  | Temperature 600 °C, duration 30 s |
| 911401721502 | RS378B P24 930 PSU-E WB M70  | Temperature 600 °C, duration 30 s |
| 911401721512 | RS378B P24 940 PSU-E WB M70  | Temperature 600 °C, duration 30 s |
| 911401538571 | RS378B P33 927 PSD-E NB M87  | -                                 |
| 911401538671 | RS378B P33 927 PSD-E MB M87  | -                                 |
| 911401538871 | RS378B P33 930 PSD-E NB M87  | -                                 |
| 911401539171 | RS378B P33 940 PSD-E NB M87  | -                                 |
| 911401721522 | RS378B P33 927 PSU-E NB M87  | Temperature 600 °C, duration 30 s |
| 911401721532 | RS378B P33 930 PSU-E NB M87  | Temperature 600 °C, duration 30 s |
| 911401721542 | RS378B P33 940 PSU-E NB M87  | Temperature 600 °C, duration 30 s |
| 911401721562 | RS378B P33 930 PSU-E MB M87  | Temperature 600 °C, duration 30 s |
| 911401721572 | RS378B P33 940 PSU-E MB M87  | Temperature 600 °C, duration 30 s |
| 911401721592 | RS378B P33 930 PSU-E WB M87  | Temperature 600 °C, duration 30 s |
| 911401721602 | RS378B P33 940 PSU-E WB M87  | Temperature 600 °C, duration 30 s |
| 911401539571 | RS378B P42 927 PSD-E MB M102 | -                                 |
| 911401539871 | RS378B P42 930 PSD-E MB M102 | -                                 |
| 911401539971 | RS378B P42 930 PSD-E WB M102 | -                                 |
| 911401540271 | RS378B P42 940 PSD-E WB M102 | -                                 |
| 911401545571 | RS378B P11 930 PSU-E WW S    | -                                 |
| 911401545671 | RS378B P11 940 PSU-E WW S    | -                                 |

| Order Code   | Full Product Name                 | Glow-wire test |
|--------------|-----------------------------------|----------------|
| 911401546571 | RS378B P11 940 PSD-E WW S         | -              |
| 911401545971 | RS378B P15 940 PSU-E WW S         | -              |
| 911401546771 | RS378B P15 930 PSD-E WW S         | -              |
| 911401536771 | RS378B P15 927 PSD-E NB M55       | -              |
| 911401536871 | RS378B P15 927 PSD-E MB M55       | -              |
| 911401537171 | RS378B P15 930 PSD-E MB M55       | -              |
| 911401537271 | RS378B P15 930 PSD-E WB M55       | -              |
| 911401537371 | RS378B P15 940 PSD-E NB M55       | -              |
| 911401537471 | RS378B P15 940 PSD-E MB M55       | -              |
| 911401537571 | RS378B P15 940 PSD-E WB M55       | -              |
| 911401540471 | RS378B P15 927 PSR-E 1-10V MB M55 | -              |
| 911401540771 | RS378B P15 930 PSR-E 1-10V MB M55 | -              |
| 911401540871 | RS378B P15 930 PSR-E 1-10V WB M55 | -              |
| 911401541171 | RS378B P15 940 PSR-E 1-10V WB M55 | -              |
| 911401532371 | RS378B P6 927 PSU-E MB M43        | -              |
| 911401532471 | RS378B P6 927 PSU-E WB M43        | -              |
| 911401532571 | RS378B P6 930 PSU-E NB M43        | -              |
| 911401532671 | RS378B P6 930 PSU-E MB M43        | -              |
| 911401532771 | RS378B P6 930 PSU-E WB M43        | -              |
| 911401532871 | RS378B P6 940 PSU-E NB M43        | -              |
| 911401532971 | RS378B P6 940 PSU-E MB M43        | -              |
| 911401533071 | RS378B P6 940 PSU-E WB M43        | -              |
| 911401533271 | RS378B P6 927 PSR-E MB M43        | -              |
| 911401533571 | RS378B P6 930 PSR-E MB M43        | -              |
| 911401533671 | RS378B P6 930 PSR-E WB M43        | -              |
| 911401533771 | RS378B P6 940 PSR-E NB M43        | -              |

| Order Code   | Full Product Name           | Glow-wire test                    |
|--------------|-----------------------------|-----------------------------------|
| 911401534471 | RS378B P6 930 PSD-E MB M43  | -                                 |
| 911401534571 | RS378B P6 930 PSD-E WB M43  | -                                 |
| 911401534771 | RS378B P6 940 PSD-E MB M43  | -                                 |
| 911401721252 | RS378B P15 927 PSU-E NB M55 | Temperature 600 °C, duration 30 s |
| 911401721262 | RS378B P15 930 PSU-E NB M55 | Temperature 600 °C, duration 30 s |
| 911401721272 | RS378B P15 940 PSU-E NB M55 | Temperature 600 °C, duration 30 s |
| 911401721292 | RS378B P15 930 PSU-E MB M55 | Temperature 600 °C, duration 30 s |
| 911401721302 | RS378B P15 940 PSU-E MB M55 | Temperature 600 °C, duration 30 s |
| 911401721312 | RS378B P15 927 PSU-E WB M55 | Temperature 600 °C, duration 30 s |
| 911401721322 | RS378B P15 930 PSU-E WB M55 | Temperature 600 °C, duration 30 s |
| 911401721332 | RS378B P15 940 PSU-E WB M55 | Temperature 600 °C, duration 30 s |
| 911401721372 | RS378B P15 927 PSR-E MB M55 | Temperature 600 °C, duration 30 s |
| 911401721412 | RS378B P15 930 PSR-E WB M55 | Temperature 600 °C, duration 30 s |
| 911401721422 | RS378B P15 940 PSR-E WB M55 | Temperature 600 °C, duration 30 s |

Initial Performance (IEC Compliant)

| Order Code   | Full Product Name           | Initial chromaticity |
|--------------|-----------------------------|----------------------|
| 911401535871 | RS378B P11 927 PSD-E NB M55 | -                    |
| 911401536071 | RS378B P11 927 PSD-E WB M55 | -                    |
| 911401536271 | RS378B P11 930 PSD-E MB M55 | -                    |
| 911401536371 | RS378B P11 930 PSD-E WB M55 | -                    |
| 911401536471 | RS378B P11 940 PSD-E NB M55 | -                    |
| 911401536571 | RS378B P11 940 PSD-E MB M55 | -                    |
| 911401536671 | RS378B P11 940 PSD-E WB M55 | -                    |
| 911401720892 | RS378B P6 927 PSU-E NB M55  | SDCM<3               |
| 911401720902 | RS378B P6 930 PSU-E NB M55  | SDCM<3               |
| 911401720912 | RS378B P6 940 PSU-E NB M55  | SDCM<3               |
| 911401720932 | RS378B P6 930 PSU-E MB M55  | SDCM<3               |
| 911401720942 | RS378B P6 940 PSU-E MB M55  | SDCM<3               |
| 911401720952 | RS378B P6 927 PSU-E WB M55  | SDCM<3               |
| 911401720962 | RS378B P6 930 PSU-E WB M55  | SDCM<3               |
| 911401720972 | RS378B P6 940 PSU-E WB M55  | SDCM<3               |
| 911401720992 | RS378B P11 930 PSU-E NB M55 | SDCM<3               |
| 911401721002 | RS378B P11 940 PSU-E NB M55 | SDCM<3               |
| 911401721012 | RS378B P11 927 PSU-E MB M55 | SDCM<3               |
| 911401721022 | RS378B P11 930 PSU-E MB M55 | SDCM<3               |
| 911401721032 | RS378B P11 940 PSU-E MB M55 | SDCM<3               |
| 911401721042 | RS378B P11 927 PSU-E WB M55 | SDCM<3               |
| 911401721052 | RS378B P11 930 PSU-E WB M55 | SDCM<3               |

| Order Code   | Full Product Name            | Initial chromaticity |
|--------------|------------------------------|----------------------|
| 911401721062 | RS378B P11 940 PSU-E WB M55  | SDCM<3               |
| 911401721112 | RS378B P6 930 PSR-E MB M55   | SDCM<3               |
| 911401721192 | RS378B P11 927 PSR-E MB M55  | SDCM<3               |
| 911401721222 | RS378B P11 927 PSR-E WB M55  | SDCM<3               |
| 911401721232 | RS378B P11 930 PSR-E WB M55  | SDCM<3               |
| 911401721622 | RS378B P42 930 PSU-E NB M102 | SDCM<3               |
| 911401721632 | RS378B P42 940 PSU-E NB M102 | SDCM<3               |
| 911401721642 | RS378B P42 927 PSU-E MB M102 | SDCM<3               |
| 911401721652 | RS378B P42 930 PSU-E MB M102 | SDCM<3               |
| 911401721662 | RS378B P42 940 PSU-E MB M102 | SDCM<3               |
| 911401721682 | RS378B P42 930 PSU-E WB M102 | SDCM<3               |
| 911401721692 | RS378B P42 940 PSU-E WB M102 | SDCM<3               |
| 911401534971 | RS378B P6 927 PSD-E NB M55   | -                    |
| 911401535071 | RS378B P6 927 PSD-E MB M55   | -                    |
| 911401535171 | RS378B P6 927 PSD-E WB M55   | -                    |
| 911401535371 | RS378B P6 930 PSD-E MB M55   | -                    |
| 911401535471 | RS378B P6 930 PSD-E WB M55   | -                    |
| 911401535571 | RS378B P6 940 PSD-E NB M55   | -                    |
| 911401537771 | RS378B P24 927 PSD-E MB M70  | -                    |
| 911401538071 | RS378B P24 930 PSD-E MB M70  | -                    |
| 911401538171 | RS378B P24 930 PSD-E WB M70  | -                    |
| 911401538271 | RS378B P24 940 PSD-E NB M70  | -                    |

| Order Code   | Full Product Name            | Initial chromaticity |
|--------------|------------------------------|----------------------|
| 911401538371 | RS378B P24 940 PSD-E MB M70  | -                    |
| 911401538471 | RS378B P24 940 PSD-E WB M70  | -                    |
| 911401721432 | RS378B P24 927 PSU-E NB M70  | SDCM<3               |
| 911401721442 | RS378B P24 930 PSU-E NB M70  | SDCM<3               |
| 911401721452 | RS378B P24 940 PSU-E NB M70  | SDCM<3               |
| 911401721472 | RS378B P24 930 PSU-E MB M70  | SDCM<3               |
| 911401721482 | RS378B P24 940 PSU-E MB M70  | SDCM<3               |
| 911401721492 | RS378B P24 927 PSU-E WB M70  | SDCM<3               |
| 911401721502 | RS378B P24 930 PSU-E WB M70  | SDCM<3               |
| 911401721512 | RS378B P24 940 PSU-E WB M70  | SDCM<3               |
| 911401538571 | RS378B P33 927 PSD-E NB M87  | -                    |
| 911401538671 | RS378B P33 927 PSD-E MB M87  | -                    |
| 911401538871 | RS378B P33 930 PSD-E NB M87  | -                    |
| 911401539171 | RS378B P33 940 PSD-E NB M87  | -                    |
| 911401721522 | RS378B P33 927 PSU-E NB M87  | SDCM<3               |
| 911401721532 | RS378B P33 930 PSU-E NB M87  | SDCM<3               |
| 911401721542 | RS378B P33 940 PSU-E NB M87  | SDCM<3               |
| 911401721562 | RS378B P33 930 PSU-E MB M87  | SDCM<3               |
| 911401721572 | RS378B P33 940 PSU-E MB M87  | SDCM<3               |
| 911401721592 | RS378B P33 930 PSU-E WB M87  | SDCM<3               |
| 911401721602 | RS378B P33 940 PSU-E WB M87  | SDCM<3               |
| 911401539571 | RS378B P42 927 PSD-E MB M102 | -                    |
| 911401539871 | RS378B P42 930 PSD-E MB M102 | -                    |
| 911401539971 | RS378B P42 930 PSD-E WB M102 | -                    |
| 911401540271 | RS378B P42 940 PSD-E WB M102 | -                    |
| 911401545571 | RS378B P11 930 PSU-E WW S    | -                    |
| 911401545671 | RS378B P11 940 PSU-E WW S    | -                    |
| 911401546571 | RS378B P11 940 PSD-E WW S    | -                    |
| 911401545971 | RS378B P15 940 PSU-E WW S    | -                    |
| 911401546771 | RS378B P15 930 PSD-E WW S    | -                    |
| 911401536771 | RS378B P15 927 PSD-E NB M55  | -                    |
| 911401536871 | RS378B P15 927 PSD-E MB M55  | -                    |
| 911401537171 | RS378B P15 930 PSD-E MB M55  | -                    |
| 911401537271 | RS378B P15 930 PSD-E WB M55  | -                    |

| Order Code   | Full Product Name                 | Initial chromaticity |
|--------------|-----------------------------------|----------------------|
| 911401537371 | RS378B P15 940 PSD-E NB M55       | -                    |
| 911401537471 | RS378B P15 940 PSD-E MB M55       | -                    |
| 911401537571 | RS378B P15 940 PSD-E WB M55       | -                    |
| 911401540471 | RS378B P15 927 PSR-E 1-10V MB M55 | -                    |
| 911401540771 | RS378B P15 930 PSR-E 1-10V MB M55 | -                    |
| 911401540871 | RS378B P15 930 PSR-E 1-10V WB M55 | -                    |
| 911401541171 | RS378B P15 940 PSR-E 1-10V WB M55 | -                    |
| 911401532371 | RS378B P6 927 PSU-E MB M43        | -                    |
| 911401532471 | RS378B P6 927 PSU-E WB M43        | -                    |
| 911401532571 | RS378B P6 930 PSU-E NB M43        | -                    |
| 911401532671 | RS378B P6 930 PSU-E MB M43        | -                    |
| 911401532771 | RS378B P6 930 PSU-E WB M43        | -                    |
| 911401532871 | RS378B P6 940 PSU-E NB M43        | -                    |
| 911401532971 | RS378B P6 940 PSU-E MB M43        | -                    |
| 911401533071 | RS378B P6 940 PSU-E WB M43        | -                    |
| 911401533271 | RS378B P6 927 PSR-E MB M43        | -                    |
| 911401533571 | RS378B P6 930 PSR-E MB M43        | -                    |
| 911401533671 | RS378B P6 930 PSR-E WB M43        | -                    |
| 911401533771 | RS378B P6 940 PSR-E NB M43        | -                    |
| 911401534471 | RS378B P6 930 PSD-E MB M43        | -                    |
| 911401534571 | RS378B P6 930 PSD-E WB M43        | -                    |
| 911401534771 | RS378B P6 940 PSD-E MB M43        | -                    |
| 911401721252 | RS378B P15 927 PSU-E NB M55       | SDCM<3               |
| 911401721262 | RS378B P15 930 PSU-E NB M55       | SDCM<3               |
| 911401721272 | RS378B P15 940 PSU-E NB M55       | SDCM<3               |
| 911401721292 | RS378B P15 930 PSU-E MB M55       | SDCM<3               |
| 911401721302 | RS378B P15 940 PSU-E MB M55       | SDCM<3               |
| 911401721312 | RS378B P15 927 PSU-E WB M55       | SDCM<3               |
| 911401721322 | RS378B P15 930 PSU-E WB M55       | SDCM<3               |
| 911401721332 | RS378B P15 940 PSU-E WB M55       | SDCM<3               |
| 911401721372 | RS378B P15 927 PSR-E MB M55       | SDCM<3               |
| 911401721412 | RS378B P15 930 PSR-E WB M55       | SDCM<3               |
| 911401721422 | RS378B P15 940 PSR-E WB M55       | SDCM<3               |

Over Time Performance (IEC Compliant)

| Order Code   | Full Product Name           | Median useful life L80B50 |
|--------------|-----------------------------|---------------------------|
| 911401535871 | RS378B P11 927 PSD-E NB M55 | -                         |
| 911401536071 | RS378B P11 927 PSD-E WB M55 | -                         |
| 911401536271 | RS378B P11 930 PSD-E MB M55 | -                         |
| 911401536371 | RS378B P11 930 PSD-E WB M55 | -                         |
| 911401536471 | RS378B P11 940 PSD-E NB M55 | -                         |
| 911401536571 | RS378B P11 940 PSD-E MB M55 | -                         |
| 911401536671 | RS378B P11 940 PSD-E WB M55 | -                         |
| 911401720892 | RS378B P6 927 PSU-E NB M55  | 50,000 hour(s)            |
| 911401720902 | RS378B P6 930 PSU-E NB M55  | 50,000 hour(s)            |
| 911401720912 | RS378B P6 940 PSU-E NB M55  | 50,000 hour(s)            |
| 911401720932 | RS378B P6 930 PSU-E MB M55  | 50,000 hour(s)            |
| 911401720942 | RS378B P6 940 PSU-E MB M55  | 50,000 hour(s)            |
| 911401720952 | RS378B P6 927 PSU-E WB M55  | 50,000 hour(s)            |
| 911401720962 | RS378B P6 930 PSU-E WB M55  | 50,000 hour(s)            |

| Order Code   | Full Product Name            | Median useful life L80B50 |
|--------------|------------------------------|---------------------------|
| 911401720972 | RS378B P6 940 PSU-E WB M55   | 50,000 hour(s)            |
| 911401720992 | RS378B P11 930 PSU-E NB M55  | 50,000 hour(s)            |
| 911401721002 | RS378B P11 940 PSU-E NB M55  | 50,000 hour(s)            |
| 911401721012 | RS378B P11 927 PSU-E MB M55  | 50,000 hour(s)            |
| 911401721022 | RS378B P11 930 PSU-E MB M55  | 50,000 hour(s)            |
| 911401721032 | RS378B P11 940 PSU-E MB M55  | 50,000 hour(s)            |
| 911401721042 | RS378B P11 927 PSU-E WB M55  | 50,000 hour(s)            |
| 911401721052 | RS378B P11 930 PSU-E WB M55  | 50,000 hour(s)            |
| 911401721062 | RS378B P11 940 PSU-E WB M55  | 50,000 hour(s)            |
| 911401721112 | RS378B P6 930 PSR-E MB M55   | 50,000 hour(s)            |
| 911401721192 | RS378B P11 927 PSR-E MB M55  | 50,000 hour(s)            |
| 911401721222 | RS378B P11 927 PSR-E WB M55  | 50,000 hour(s)            |
| 911401721232 | RS378B P11 930 PSR-E WB M55  | 50,000 hour(s)            |
| 911401721622 | RS378B P42 930 PSU-E NB M102 | 50,000 hour(s)            |

| Order Code   | Full Product Name            | Median useful life L80B50 |
|--------------|------------------------------|---------------------------|
| 911401721632 | RS378B P42 940 PSU-E NB M102 | 50,000 hour(s)            |
| 911401721642 | RS378B P42 927 PSU-E MB M102 | 50,000 hour(s)            |
| 911401721652 | RS378B P42 930 PSU-E MB M102 | 50,000 hour(s)            |
| 911401721662 | RS378B P42 940 PSU-E MB M102 | 50,000 hour(s)            |
| 911401721682 | RS378B P42 930 PSU-E WB M102 | 50,000 hour(s)            |
| 911401721692 | RS378B P42 940 PSU-E WB M102 | 50,000 hour(s)            |
| 911401534971 | RS378B P6 927 PSD-E NB M55   | -                         |
| 911401535071 | RS378B P6 927 PSD-E MB M55   | -                         |
| 911401535171 | RS378B P6 927 PSD-E WB M55   | -                         |
| 911401535371 | RS378B P6 930 PSD-E MB M55   | -                         |
| 911401535471 | RS378B P6 930 PSD-E WB M55   | -                         |
| 911401535571 | RS378B P6 940 PSD-E NB M55   | -                         |
| 911401537771 | RS378B P24 927 PSD-E MB M70  | -                         |
| 911401538071 | RS378B P24 930 PSD-E MB M70  | -                         |
| 911401538171 | RS378B P24 930 PSD-E WB M70  | -                         |
| 911401538271 | RS378B P24 940 PSD-E NB M70  | -                         |
| 911401538371 | RS378B P24 940 PSD-E MB M70  | -                         |
| 911401538471 | RS378B P24 940 PSD-E WB M70  | -                         |
| 911401721432 | RS378B P24 927 PSU-E NB M70  | 50,000 hour(s)            |
| 911401721442 | RS378B P24 930 PSU-E NB M70  | 50,000 hour(s)            |
| 911401721452 | RS378B P24 940 PSU-E NB M70  | 50,000 hour(s)            |
| 911401721472 | RS378B P24 930 PSU-E MB M70  | 50,000 hour(s)            |
| 911401721482 | RS378B P24 940 PSU-E MB M70  | 50,000 hour(s)            |
| 911401721492 | RS378B P24 927 PSU-E WB M70  | 50,000 hour(s)            |
| 911401721502 | RS378B P24 930 PSU-E WB M70  | 50,000 hour(s)            |
| 911401721512 | RS378B P24 940 PSU-E WB M70  | 50,000 hour(s)            |
| 911401538571 | RS378B P33 927 PSD-E NB M87  | -                         |
| 911401538671 | RS378B P33 927 PSD-E MB M87  | -                         |
| 911401538871 | RS378B P33 930 PSD-E NB M87  | -                         |
| 911401539171 | RS378B P33 940 PSD-E NB M87  | -                         |
| 911401721522 | RS378B P33 927 PSU-E NB M87  | 50,000 hour(s)            |
| 911401721532 | RS378B P33 930 PSU-E NB M87  | 50,000 hour(s)            |
| 911401721542 | RS378B P33 940 PSU-E NB M87  | 50,000 hour(s)            |
| 911401721562 | RS378B P33 930 PSU-E MB M87  | 50,000 hour(s)            |
| 911401721572 | RS378B P33 940 PSU-E MB M87  | 50,000 hour(s)            |
| 911401721592 | RS378B P33 930 PSU-E WB M87  | 50,000 hour(s)            |
| 911401721602 | RS378B P33 940 PSU-E WB M87  | 50,000 hour(s)            |
| 911401539571 | RS378B P42 927 PSD-E MB M102 | -                         |
| 911401539871 | RS378B P42 930 PSD-E MB M102 | -                         |
| 911401539971 | RS378B P42 930 PSD-E WB M102 | -                         |
| 911401540271 | RS378B P42 940 PSD-E WB M102 | -                         |
| 911401545571 | RS378B P11 930 PSU-E WW S    | -                         |

| Order Code   | Full Product Name                 | Median useful life L80B50 |
|--------------|-----------------------------------|---------------------------|
| 911401545671 | RS378B P11 940 PSU-E WW S         | -                         |
| 911401546571 | RS378B P11 940 PSD-E WW S         | -                         |
| 911401545971 | RS378B P15 940 PSU-E WW S         | -                         |
| 911401546771 | RS378B P15 930 PSD-E WW S         | -                         |
| 911401536771 | RS378B P15 927 PSD-E NB M55       | -                         |
| 911401536871 | RS378B P15 927 PSD-E MB M55       | -                         |
| 911401537171 | RS378B P15 930 PSD-E MB M55       | -                         |
| 911401537271 | RS378B P15 930 PSD-E WB M55       | -                         |
| 911401537371 | RS378B P15 940 PSD-E NB M55       | -                         |
| 911401537471 | RS378B P15 940 PSD-E MB M55       | -                         |
| 911401537571 | RS378B P15 940 PSD-E WB M55       | -                         |
| 911401540471 | RS378B P15 927 PSR-E 1-10V MB M55 | -                         |
| 911401540771 | RS378B P15 930 PSR-E 1-10V MB M55 | -                         |
| 911401540871 | RS378B P15 930 PSR-E 1-10V WB M55 | -                         |
| 911401541171 | RS378B P15 940 PSR-E 1-10V WB M55 | -                         |
| 911401532371 | RS378B P6 927 PSU-E MB M43        | -                         |
| 911401532471 | RS378B P6 927 PSU-E WB M43        | -                         |
| 911401532571 | RS378B P6 930 PSU-E NB M43        | -                         |
| 911401532671 | RS378B P6 930 PSU-E MB M43        | -                         |
| 911401532771 | RS378B P6 930 PSU-E WB M43        | -                         |
| 911401532871 | RS378B P6 940 PSU-E NB M43        | -                         |
| 911401532971 | RS378B P6 940 PSU-E MB M43        | -                         |
| 911401533071 | RS378B P6 940 PSU-E WB M43        | -                         |
| 911401533271 | RS378B P6 927 PSR-E MB M43        | -                         |
| 911401533571 | RS378B P6 930 PSR-E MB M43        | -                         |
| 911401533671 | RS378B P6 930 PSR-E WB M43        | -                         |
| 911401533771 | RS378B P6 940 PSR-E NB M43        | -                         |
| 911401534471 | RS378B P6 930 PSD-E MB M43        | -                         |
| 911401534571 | RS378B P6 930 PSD-E WB M43        | -                         |
| 911401534771 | RS378B P6 940 PSD-E MB M43        | -                         |
| 911401721252 | RS378B P15 927 PSU-E NB M55       | 50,000 hour(s)            |
| 911401721262 | RS378B P15 930 PSU-E NB M55       | 50,000 hour(s)            |
| 911401721272 | RS378B P15 940 PSU-E NB M55       | 50,000 hour(s)            |
| 911401721292 | RS378B P15 930 PSU-E MB M55       | 50,000 hour(s)            |
| 911401721302 | RS378B P15 940 PSU-E MB M55       | 50,000 hour(s)            |
| 911401721312 | RS378B P15 927 PSU-E WB M55       | 50,000 hour(s)            |
| 911401721322 | RS378B P15 930 PSU-E WB M55       | 50,000 hour(s)            |
| 911401721332 | RS378B P15 940 PSU-E WB M55       | 50,000 hour(s)            |
| 911401721372 | RS378B P15 927 PSR-E MB M55       | 50,000 hour(s)            |
| 911401721412 | RS378B P15 930 PSR-E WB M55       | 50,000 hour(s)            |
| 911401721422 | RS378B P15 940 PSR-E WB M55       | 50,000 hour(s)            |

