



It delivers super flexibility, complete product range and seamlessly system integration to Hospitality customers..

Greenspace Flex

GreenSpace Flex is performance portfolio dedicated to Hospitality segment for GC/GM countries. With modular design concept, the light engines and different trims could have multiply of combination to satisfy diversified customer's requirement.

Benefits

- Complete portfolio covering from 400lm to 3000lm, 3CCT and 3 beam angles.
- Super flexibility with modular design, and different trims to suit different application.
- Smart connectivity to seamlessly integration with Interact Hospitality.
- Deep recess for visual comfort
- Easy installation and maintenance

Features

- 6w ~42w (400lm~3200lm)
- CRI 90, SDCM <3
- Beam Angle: NB, MB, WB
- CCT: 2700K, 3000K, 4000K
- High reliability, 50Khrs (L80B50@25°C)

Application

- Guest room
- Bath room
- Corridor
- Lobby

Specifications

Mounting type	Recessed
Operating Temperature range	-20 to +45 °C
Light Source	COB
Mains Voltage	220-240V AC/ 50-60Hz
Optical Accessories	available through ETO
Dimming	PSU: non-dimmable PSD: dimmable via Dali protocol PSR: trailing dimmable PSR 1-10V: 1-10v dimmable DMX: dimmable via DMX protocol
Control system input	DALI / 1-10V / DMX / trailing edge
Material	Heat sink: die-cast aluminum
Main color of the luminaire	Housing: dark Grey Reflector: color available through ETO
Lumen maintenance at median useful life 50.000h	L80
Luminous flux	468-3990lm
Power consumption	6W-42W





Correlated color temperature - CCT	2700K, 3000K, 4000K
Color Rendering index - CRI	90
Beam angle	NB (Narrow Beam): 15-18° MB (Medium Beam): 20-24° WB (Wide Beam): 30-40° VWB (Very Wide Beam): 50°
Protection Class IEC61140	Class II & Class III for MR16 version
Mechanical impact protection	IK04
Ingress protection	IP20 / IP54(Front side) for selected SKU only
Light source replaceable	No
Driver replaceable	yes
Overall diameter	D55-D150
Installation	recessed Fixation by means of spring fasteners

Versions




RS378B P6 M55

Dimensional drawing



Modular Type	D, mm	H, mm
RS378B P6/P11 M55	55	49
RS378B P15 M55	55	49
RS378B P24 M70	70	90
RS378B P33 M87	87	107
RS378B P42 M102	102	116



Light Technical

Color rendering index (CRI)	>90
Optic type	-

Operating and Electrical

Protection class IEC	Safety class II
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz

Mechanical and Housing

Optical cover type	PMMA
Housing Color	Grey
Mech. impact protection code	IK04
Ingress protection code	IP20

Approval and Application

Ambient temperature range	-20 to +45 °C
CE mark	Yes
ENEC mark	-
Flammability mark	-

Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
-------------------------	-------------

General Information

Order Code	Full Product Name	Driver included	Number of gear units
911401535871	RS378B P11 927 PSD-E NB M55	-	-
911401535971	RS378B P11 927 PSD-E MB M55	-	-
911401536071	RS378B P11 927 PSD-E WB M55	-	-
911401536271	RS378B P11 930 PSD-E MB M55	-	-
911401536371	RS378B P11 930 PSD-E WB M55	-	-
911401536471	RS378B P11 940 PSD-E NB M55	-	-
911401536571	RS378B P11 940 PSD-E MB M55	-	-
911401536671	RS378B P11 940 PSD-E WB M55	-	-
911401720892	RS378B P6 927 PSU-E NB M55	Yes	1 unit
911401720902	RS378B P6 930 PSU-E NB M55	Yes	1 unit
911401720912	RS378B P6 940 PSU-E NB M55	Yes	1 unit
911401720922	RS378B P6 927 PSU-E MB M55	Yes	1 unit
911401720932	RS378B P6 930 PSU-E MB M55	Yes	1 unit
911401720942	RS378B P6 940 PSU-E MB M55	Yes	1 unit
911401720952	RS378B P6 927 PSU-E WB M55	Yes	1 unit
911401720962	RS378B P6 930 PSU-E WB M55	Yes	1 unit
911401720972	RS378B P6 940 PSU-E WB M55	Yes	1 unit
911401720982	RS378B P11 927 PSU-E NB M55	Yes	1 unit
911401720992	RS378B P11 930 PSU-E NB M55	Yes	1 unit
911401721002	RS378B P11 940 PSU-E NB M55	Yes	1 unit
911401721012	RS378B P11 927 PSU-E MB M55	Yes	1 unit
911401721022	RS378B P11 930 PSU-E MB M55	Yes	1 unit
911401721032	RS378B P11 940 PSU-E MB M55	Yes	1 unit
911401721042	RS378B P11 927 PSU-E WB M55	Yes	1 unit
911401721052	RS378B P11 930 PSU-E WB M55	Yes	1 unit
911401721062	RS378B P11 940 PSU-E WB M55	Yes	1 unit
911401721072	RS378B P6 927 PSR-E NB M55	Yes	1 unit
911401721112	RS378B P6 930 PSR-E MB M55	Yes	1 unit
911401721172	RS378B P11 930 PSR-E NB M55	Yes	1 unit
911401721192	RS378B P11 927 PSR-E MB M55	Yes	1 unit
911401721222	RS378B P11 927 PSR-E WB M55	Yes	1 unit
911401721232	RS378B P11 930 PSR-E WB M55	Yes	1 unit
911401721622	RS378B P42 930 PSU-E NB M102	Yes	1 unit
911401721632	RS378B P42 940 PSU-E NB M102	Yes	1 unit
911401721642	RS378B P42 927 PSU-E MB M102	Yes	1 unit
911401721652	RS378B P42 930 PSU-E MB M102	Yes	1 unit
911401721662	RS378B P42 940 PSU-E MB M102	Yes	1 unit
911401721682	RS378B P42 930 PSU-E WB M102	Yes	1 unit
911401721692	RS378B P42 940 PSU-E WB M102	Yes	1 unit
911401534971	RS378B P6 927 PSD-E NB M55	-	-
911401535071	RS378B P6 927 PSD-E MB M55	-	-
911401535171	RS378B P6 927 PSD-E WB M55	-	-
911401535371	RS378B P6 930 PSD-E MB M55	-	-
911401535471	RS378B P6 930 PSD-E WB M55	-	-
911401535571	RS378B P6 940 PSD-E NB M55	-	-
911401537771	RS378B P24 927 PSD-E MB M70	-	-
911401538071	RS378B P24 930 PSD-E MB M70	-	-
911401538171	RS378B P24 930 PSD-E WB M70	-	-
911401538271	RS378B P24 940 PSD-E NB M70	-	-
911401538371	RS378B P24 940 PSD-E MB M70	-	-
911401538471	RS378B P24 940 PSD-E WB M70	-	-

Order Code	Full Product Name	Driver included	Number of gear units
911401721432	RS378B P24 927 PSU-E NB M70	Yes	1 unit
911401721442	RS378B P24 930 PSU-E NB M70	Yes	1 unit
911401721452	RS378B P24 940 PSU-E NB M70	Yes	1 unit
911401721472	RS378B P24 930 PSU-E MB M70	Yes	1 unit
911401721482	RS378B P24 940 PSU-E MB M70	Yes	1 unit
911401721492	RS378B P24 927 PSU-E WB M70	Yes	1 unit
911401721502	RS378B P24 930 PSU-E WB M70	Yes	1 unit
911401721512	RS378B P24 940 PSU-E WB M70	Yes	1 unit
911401538571	RS378B P33 927 PSD-E NB M87	-	-
911401538671	RS378B P33 927 PSD-E MB M87	-	-
911401538871	RS378B P33 930 PSD-E NB M87	-	-
911401539171	RS378B P33 940 PSD-E NB M87	-	-
911401721522	RS378B P33 927 PSU-E NB M87	Yes	1 unit
911401721532	RS378B P33 930 PSU-E NB M87	Yes	1 unit
911401721542	RS378B P33 940 PSU-E NB M87	Yes	1 unit
911401721562	RS378B P33 930 PSU-E MB M87	Yes	1 unit
911401721572	RS378B P33 940 PSU-E MB M87	Yes	1 unit
911401721592	RS378B P33 930 PSU-E WB M87	Yes	1 unit
911401721602	RS378B P33 940 PSU-E WB M87	Yes	1 unit
911401539871	RS378B P42 930 PSD-E MB M102	-	-
911401539971	RS378B P42 930 PSD-E WB M102	-	-
911401540271	RS378B P42 940 PSD-E WB M102	-	-
911401545571	RS378B P11 930 PSU-E WW S	-	-
911401545671	RS378B P11 940 PSU-E WW S	-	-
911401546571	RS378B P11 940 PSD-E WW S	-	-
911401545971	RS378B P15 940 PSU-E WW S	-	-
911401546771	RS378B P15 930 PSD-E WW S	-	-
911401536771	RS378B P15 927 PSD-E NB M55	-	-
911401536871	RS378B P15 927 PSD-E MB M55	-	-
911401536971	RS378B P15 927 PSD-E WB M55	-	-
911401537171	RS378B P15 930 PSD-E MB M55	-	-
911401537271	RS378B P15 930 PSD-E WB M55	-	-
911401537371	RS378B P15 940 PSD-E NB M55	-	-
911401537471	RS378B P15 940 PSD-E MB M55	-	-
911401537571	RS378B P15 940 PSD-E WB M55	-	-
911401540471	RS378B P15 927 PSR-E 1-10V MB M55	-	-
911401540771	RS378B P15 930 PSR-E 1-10V MB M55	-	-
911401540871	RS378B P15 930 PSR-E 1-10V WB M55	-	-
911401541171	RS378B P15 940 PSR-E 1-10V WB M55	-	-
911401532371	RS378B P6 927 PSU-E MB M43	-	-
911401532471	RS378B P6 927 PSU-E WB M43	-	-
911401532571	RS378B P6 930 PSU-E NB M43	-	-
911401532671	RS378B P6 930 PSU-E MB M43	-	-
911401532771	RS378B P6 930 PSU-E WB M43	-	-
911401532871	RS378B P6 940 PSU-E NB M43	-	-
911401532971	RS378B P6 940 PSU-E MB M43	-	-
911401533071	RS378B P6 940 PSU-E WB M43	-	-
911401533271	RS378B P6 927 PSR-E MB M43	-	-
911401533571	RS378B P6 930 PSR-E MB M43	-	-
911401533671	RS378B P6 930 PSR-E WB M43	-	-
911401533771	RS378B P6 940 PSR-E NB M43	-	-
911401534471	RS378B P6 930 PSD-E MB M43	-	-

Order Code	Full Product Name	Driver included	Number of gear units
911401534571	RS378B P6 930 PSD-E WB M43	-	-
911401534771	RS378B P6 940 PSD-E MB M43	-	-
911401721252	RS378B P15 927 PSU-E NB M55	Yes	1 unit
911401721262	RS378B P15 930 PSU-E NB M55	Yes	1 unit
911401721272	RS378B P15 940 PSU-E NB M55	Yes	1 unit
911401721282	RS378B P15 927 PSU-E MB M55	Yes	1 unit
911401721292	RS378B P15 930 PSU-E MB M55	Yes	1 unit
911401721302	RS378B P15 940 PSU-E MB M55	Yes	1 unit
911401721312	RS378B P15 927 PSU-E WB M55	Yes	1 unit
911401721322	RS378B P15 930 PSU-E WB M55	Yes	1 unit
911401721332	RS378B P15 940 PSU-E WB M55	Yes	1 unit
911401721372	RS378B P15 927 PSR-E MB M55	Yes	1 unit
911401721412	RS378B P15 930 PSR-E WB M55	Yes	1 unit
911401721422	RS378B P15 940 PSR-E WB M55	Yes	1 unit

Light Technical

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401535871	RS378B P11 927 PSD-E NB M55	-	2700 K	97 lm/W	580 lm
911401535971	RS378B P11 927 PSD-E MB M55	-	2700 K	110 lm/W	660 lm
911401536071	RS378B P11 927 PSD-E WB M55	-	2700 K	110 lm/W	660 lm
911401536271	RS378B P11 930 PSD-E MB M55	-	3000 K	87 lm/W	957 lm
911401536371	RS378B P11 930 PSD-E WB M55	-	3000 K	87 lm/W	957 lm
911401536471	RS378B P11 940 PSD-E NB M55	-	4000 K	78 lm/W	858 lm
911401536571	RS378B P11 940 PSD-E MB M55	-	4000 K	92 lm/W	1,012 lm
911401536671	RS378B P11 940 PSD-E WB M55	-	4000 K	92 lm/W	1,012 lm
911401720892	RS378B P6 927 PSU-E NB M55	- degree(s)	2700 K	92 lm/W	3,864 lm
911401720902	RS378B P6 930 PSU-E NB M55	- degree(s)	3000 K	87 lm/W	1,305 lm
911401720912	RS378B P6 940 PSU-E NB M55	- degree(s)	4000 K	80 lm/W	1,200 lm
911401720922	RS378B P6 927 PSU-E MB M55	- degree(s)	2700 K	77 lm/W	2,540 lm
911401720932	RS378B P6 930 PSU-E MB M55	- degree(s)	3000 K	97 lm/W	4,074 lm
911401720942	RS378B P6 940 PSU-E MB M55	- degree(s)	4000 K	82 lm/W	900 lm
911401720952	RS378B P6 927 PSU-E WB M55	- degree(s)	2700 K	92 lm/W	3,864 lm
911401720962	RS378B P6 930 PSU-E WB M55	- degree(s)	3000 K	100 lm/W	1,500 lm
911401720972	RS378B P6 940 PSU-E WB M55	- degree(s)	4000 K	93 lm/W	1,400 lm
911401720982	RS378B P11 927 PSU-E NB M55	-	2700 K	76 lm/W	836 lm
911401720992	RS378B P11 930 PSU-E NB M55	-	3000 K	85 lm/W	510 lm
911401721002	RS378B P11 940 PSU-E NB M55	-	4000 K	95 lm/W	570 lm
911401721012	RS378B P11 927 PSU-E MB M55	-	2700 K	87 lm/W	957 lm
911401721022	RS378B P11 930 PSU-E MB M55	-	3000 K	85 lm/W	510 lm
911401721032	RS378B P11 940 PSU-E MB M55	-	4000 K	90 lm/W	540 lm
911401721042	RS378B P11 927 PSU-E WB M55	-	2700 K	87 lm/W	957 lm
911401721052	RS378B P11 930 PSU-E WB M55	-	3000 K	90 lm/W	540 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401721062	RS378B P11 940 PSU-E WB M55	-	4000 K	95 lm/W	570 lm
911401721072	RS378B P6 927 PSR-E NB M55	-	2700 K	65 lm/W	390 lm
911401721112	RS378B P6 930 PSR-E MB M55	-	3000 K	75 lm/W	450 lm
911401721172	RS378B P11 930 PSR-E NB M55	-	3000 K	76 lm/W	836 lm
911401721192	RS378B P11 927 PSR-E MB M55	-	2700 K	85 lm/W	510 lm
911401721222	RS378B P11 927 PSR-E WB M55	-	2700 K	85 lm/W	510 lm
911401721232	RS378B P11 930 PSR-E WB M55	-	3000 K	87 lm/W	957 lm
911401721622	RS378B P42 930 PSU-E NB M102	-	3000 K	71 lm/W	2,350 lm
911401721632	RS378B P42 940 PSU-E NB M102	-	4000 K	73 lm/W	2,400 lm
911401721642	RS378B P42 927 PSU-E MB M102	-	2700 K	106 lm/W	2,540 lm
911401721652	RS378B P42 930 PSU-E MB M102	- degree(s)	3000 K	71 lm/W	2,350 lm
911401721662	RS378B P42 940 PSU-E MB M102	- degree(s)	4000 K	73 lm/W	2,400 lm
911401721682	RS378B P42 930 PSU-E WB M102	- degree(s)	3000 K	71 lm/W	2,350 lm
911401721692	RS378B P42 940 PSU-E WB M102	- degree(s)	4000 K	73 lm/W	2,400 lm
911401534971	RS378B P6 927 PSD-E NB M55	-	2700 K	95 lm/W	570 lm
911401535071	RS378B P6 927 PSD-E MB M55	-	2700 K	100 lm/W	600 lm
911401535171	RS378B P6 927 PSD-E WB M55	-	2700 K	100 lm/W	600 lm
911401535371	RS378B P6 930 PSD-E MB M55	-	3000 K	100 lm/W	600 lm
911401535471	RS378B P6 930 PSD-E WB M55	-	3000 K	100 lm/W	600 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401535571	RS378B P6 940 PSD-E NB M55	-	4000 K	88 lm/W	530 lm
911401537771	RS378B P24 927 PSD-E MB M70	-	2700 K	100 lm/W	1,500 lm
911401538071	RS378B P24 930 PSD-E MB M70	-	3000 K	98 lm/W	2,350 lm
911401538171	RS378B P24 930 PSD-E WB M70	-	3000 K	98 lm/W	2,350 lm
911401538271	RS378B P24 940 PSD-E NB M70	-	4000 K	100 lm/W	2,400 lm
911401538371	RS378B P24 940 PSD-E MB M70	-	4000 K	100 lm/W	2,400 lm
911401538471	RS378B P24 940 PSD-E WB M70	-	4000 K	100 lm/W	2,400 lm
911401721432	RS378B P24 927 PSU-E NB M70	-	2700 K	92 lm/W	1,012 lm
911401721442	RS378B P24 930 PSU-E NB M70	-	3000 K	100 lm/W	1,100 lm
911401721452	RS378B P24 940 PSU-E NB M70	-	4000 K	78 lm/W	1,170 lm
911401721472	RS378B P24 930 PSU-E MB M70	-	3000 K	100 lm/W	1,100 lm
911401721482	RS378B P24 940 PSU-E MB M70	-	4000 K	90 lm/W	1,350 lm
911401721492	RS378B P24 927 PSU-E WB M70	-	2700 K	92 lm/W	1,012 lm
911401721502	RS378B P24 930 PSU-E WB M70	-	3000 K	76 lm/W	1,140 lm
911401721512	RS378B P24 940 PSU-E WB M70	-	4000 K	94 lm/W	1,410 lm
911401538571	RS378B P33 927 PSD-E NB M87	-	2700 K	106 lm/W	2,540 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401538671	RS378B P33 927 PSD-E MB M87	-	2700 K	106 lm/W	2,540 lm
911401538871	RS378B P33 930 PSD-E NB M87	-	3000 K	71 lm/W	2,350 lm
911401539171	RS378B P33 940 PSD-E NB M87	-	4000 K	73 lm/W	2,400 lm
911401721522	RS378B P33 927 PSU-E NB M87	-	2700 K	100 lm/W	1,500 lm
911401721532	RS378B P33 930 PSU-E NB M87	-	3000 K	98 lm/W	2,350 lm
911401721542	RS378B P33 940 PSU-E NB M87	-	4000 K	100 lm/W	2,400 lm
911401721562	RS378B P33 930 PSU-E MB M87	-	3000 K	98 lm/W	2,350 lm
911401721572	RS378B P33 940 PSU-E MB M87	-	4000 K	100 lm/W	2,400 lm
911401721592	RS378B P33 930 PSU-E WB M87	-	3000 K	98 lm/W	2,350 lm
911401721602	RS378B P33 940 PSU-E WB M87	-	4000 K	100 lm/W	2,400 lm
911401539871	RS378B P42 930 PSD-E MB M102	-	3000 K	92 lm/W	3,864 lm
911401539971	RS378B P42 930 PSD-E WB M102	-	3000 K	92 lm/W	3,864 lm
911401540271	RS378B P42 940 PSD-E WB M102	-	4000 K	97 lm/W	4,074 lm
911401545571	RS378B P11 930 PSU-E WW S	-	3000 K	90 lm/W	540 lm
911401545671	RS378B P11 940 PSU-E WW S	-	4000 K	95 lm/W	570 lm
911401546571	RS378B P11 940 PSD-E WW S	-	4000 K	90 lm/W	2,150 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401545971	RS378B P15 940 PSU-E WW S	-	4000 K	87 lm/W	957 lm
911401546771	RS378B P15 930 PSD-E WW S	-	3000 K	82 lm/W	900 lm
911401536771	RS378B P15 927 PSD-E NB M55	-	2700 K	87 lm/W	957 lm
911401536871	RS378B P15 927 PSD-E MB M55	-	2700 K	100 lm/W	1,100 lm
911401536971	RS378B P15 927 PSD-E WB M55	-	2700 K	100 lm/W	1,100 lm
911401537171	RS378B P15 930 PSD-E MB M55	-	3000 K	90 lm/W	1,350 lm
911401537271	RS378B P15 930 PSD-E WB M55	-	3000 K	90 lm/W	1,350 lm
911401537371	RS378B P15 940 PSD-E NB M55	-	4000 K	78 lm/W	1,170 lm
911401537471	RS378B P15 940 PSD-E MB M55	-	4000 K	94 lm/W	1,410 lm
911401537571	RS378B P15 940 PSD-E WB M55	-	4000 K	94 lm/W	1,410 lm
911401540471	RS378B P15 927 PSR-E 1-10V MB M55	-	2700 K	104 lm/W	4,386 lm
911401540771	RS378B P15 930 PSR-E 1-10V MB M55	-	3000 K	90 lm/W	1,350 lm
911401540871	RS378B P15 930 PSR-E 1-10V WB M55	-	3000 K	90 lm/W	1,350 lm
911401541171	RS378B P15 940 PSR-E 1-10V WB M55	-	4000 K	94 lm/W	1,410 lm
911401532371	RS378B P6 927 PSU-E MB M43	-	2700 K	77 lm/W	2,540 lm
911401532471	RS378B P6 927 PSU-E WB M43	-	2700 K	92 lm/W	3,864 lm
911401532571	RS378B P6 930 PSU-E NB M43	-	3000 K	97 lm/W	4,074 lm

Greenspace Flex

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401532671	RS378B P6 930 PSU-E MB M43	-	3000 K	97 lm/W	4,074 lm
911401532771	RS378B P6 930 PSU-E WB M43	-	3000 K	100 lm/W	1,500 lm
911401532871	RS378B P6 940 PSU-E NB M43	-	4000 K	89 lm/W	980 lm
911401532971	RS378B P6 940 PSU-E MB M43	-	4000 K	73 lm/W	800 lm
911401533071	RS378B P6 940 PSU-E WB M43	-	4000 K	87 lm/W	1,300 lm
911401533271	RS378B P6 927 PSR-E MB M43	-	2700 K	104 lm/W	4,386 lm
911401533571	RS378B P6 930 PSR-E MB M43	-	3000 K	58 lm/W	348 lm
911401533671	RS378B P6 930 PSR-E WB M43	-	3000 K	58 lm/W	348 lm
911401533771	RS378B P6 940 PSR-E NB M43	-	4000 K	60 lm/W	360 lm
911401534471	RS378B P6 930 PSD-E MB M43	-	3000 K	89 lm/W	535 lm
911401534571	RS378B P6 930 PSD-E WB M43	-	3000 K	89 lm/W	535 lm
911401534771	RS378B P6 940 PSD-E MB M43	-	4000 K	93 lm/W	560 lm
911401721252	RS378B P15 927 PSU-E NB M55	-	2700 K	85 lm/W	510 lm
911401721262	RS378B P15 930 PSU-E NB M55	-	3000 K	97 lm/W	580 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401721272	RS378B P15 940 PSU-E NB M55	-	4000 K	76 lm/W	836 lm
911401721282	RS378B P15 927 PSU-E MB M55	-	2700 K	83 lm/W	500 lm
911401721292	RS378B P15 930 PSU-E MB M55	-	3000 K	91 lm/W	545 lm
911401721302	RS378B P15 940 PSU-E MB M55	-	4000 K	105 lm/W	630 lm
911401721312	RS378B P15 927 PSU-E WB M55	-	2700 K	90 lm/W	540 lm
911401721322	RS378B P15 930 PSU-E WB M55	-	3000 K	97 lm/W	580 lm
911401721332	RS378B P15 940 PSU-E WB M55	-	4000 K	87 lm/W	957 lm
911401721372	RS378B P15 927 PSR-E MB M55	-	2700 K	100 lm/W	1,100 lm
911401721412	RS378B P15 930 PSR-E WB M55	-	3000 K	90 lm/W	1,350 lm
911401721422	RS378B P15 940 PSR-E WB M55	-	4000 K	94 lm/W	1,410 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Suitable for random switching
911401535871	RS378B P11 927 PSD-E NB M55	11 W	-
911401535971	RS378B P11 927 PSD-E MB M55	11 W	-
911401536071	RS378B P11 927 PSD-E WB M55	11 W	-
911401536271	RS378B P11 930 PSD-E MB M55	11 W	-
911401536371	RS378B P11 930 PSD-E WB M55	11 W	-
911401536471	RS378B P11 940 PSD-E NB M55	11 W	-
911401536571	RS378B P11 940 PSD-E MB M55	11 W	-
911401536671	RS378B P11 940 PSD-E WB M55	11 W	-
911401720892	RS378B P6 927 PSU-E NB M55	6 W	No
911401720902	RS378B P6 930 PSU-E NB M55	6 W	No
911401720912	RS378B P6 940 PSU-E NB M55	6 W	No
911401720922	RS378B P6 927 PSU-E MB M55	6 W	No
911401720932	RS378B P6 930 PSU-E MB M55	6 W	No

Order Code	Full Product Name	Power Consumption	Suitable for random switching
911401720942	RS378B P6 940 PSU-E MB M55	6 W	No
911401720952	RS378B P6 927 PSU-E WB M55	6 W	No
911401720962	RS378B P6 930 PSU-E WB M55	6 W	No
911401720972	RS378B P6 940 PSU-E WB M55	6 W	No
911401720982	RS378B P11 927 PSU-E NB M55	11 W	No
911401720992	RS378B P11 930 PSU-E NB M55	11 W	No
911401721002	RS378B P11 940 PSU-E NB M55	11 W	No
911401721012	RS378B P11 927 PSU-E MB M55	11 W	No
911401721022	RS378B P11 930 PSU-E MB M55	11 W	No
911401721032	RS378B P11 940 PSU-E MB M55	11 W	No
911401721042	RS378B P11 927 PSU-E WB M55	11 W	No
911401721052	RS378B P11 930 PSU-E WB M55	11 W	No
911401721062	RS378B P11 940 PSU-E WB M55	11 W	No

Order Code	Full Product Name	Power Consumption	Suitable for random switching
911401721072	RS378B P6 927 PSR-E NB M55	6 W	No
911401721112	RS378B P6 930 PSR-E MB M55	6 W	No
911401721172	RS378B P11 930 PSR-E NB M55	11 W	No
911401721192	RS378B P11 927 PSR-E MB M55	11 W	No
911401721222	RS378B P11 927 PSR-E WB M55	11 W	No
911401721232	RS378B P11 930 PSR-E WB M55	11 W	No
911401721622	RS378B P42 930 PSU-E NB M102	42 W	No
911401721632	RS378B P42 940 PSU-E NB M102	42 W	No
911401721642	RS378B P42 927 PSU-E MB M102	42 W	No
911401721652	RS378B P42 930 PSU-E MB M102	42 W	No
911401721662	RS378B P42 940 PSU-E MB M102	42 W	No
911401721682	RS378B P42 930 PSU-E WB M102	42 W	No
911401721692	RS378B P42 940 PSU-E WB M102	42 W	No
911401534971	RS378B P6 927 PSD-E NB M55	6 W	-
911401535071	RS378B P6 927 PSD-E MB M55	6 W	-
911401535171	RS378B P6 927 PSD-E WB M55	6 W	-
911401535371	RS378B P6 930 PSD-E MB M55	6 W	-
911401535471	RS378B P6 930 PSD-E WB M55	6 W	-
911401535571	RS378B P6 940 PSD-E NB M55	6 W	-
911401537771	RS378B P24 927 PSD-E MB M70	24 W	-
911401538071	RS378B P24 930 PSD-E MB M70	24 W	-
911401538171	RS378B P24 930 PSD-E WB M70	24 W	-
911401538271	RS378B P24 940 PSD-E NB M70	24 W	-
911401538371	RS378B P24 940 PSD-E MB M70	24 W	-
911401538471	RS378B P24 940 PSD-E WB M70	24 W	-
911401721432	RS378B P24 927 PSU-E NB M70	24 W	No
911401721442	RS378B P24 930 PSU-E NB M70	24 W	No
911401721452	RS378B P24 940 PSU-E NB M70	24 W	No
911401721472	RS378B P24 930 PSU-E MB M70	24 W	No
911401721482	RS378B P24 940 PSU-E MB M70	24 W	No
911401721492	RS378B P24 927 PSU-E WB M70	24 W	No
911401721502	RS378B P24 930 PSU-E WB M70	24 W	No
911401721512	RS378B P24 940 PSU-E WB M70	24 W	No
911401538571	RS378B P33 927 PSD-E NB M87	33 W	-
911401538671	RS378B P33 927 PSD-E MB M87	33 W	-
911401538871	RS378B P33 930 PSD-E NB M87	33 W	-
911401539171	RS378B P33 940 PSD-E NB M87	33 W	-
911401721522	RS378B P33 927 PSU-E NB M87	33 W	No
911401721532	RS378B P33 930 PSU-E NB M87	33 W	No
911401721542	RS378B P33 940 PSU-E NB M87	33 W	No
911401721562	RS378B P33 930 PSU-E MB M87	33 W	No
911401721572	RS378B P33 940 PSU-E MB M87	33 W	No
911401721592	RS378B P33 930 PSU-E WB M87	33 W	No
911401721602	RS378B P33 940 PSU-E WB M87	33 W	No
911401539871	RS378B P42 930 PSD-E MB M102	42 W	-
911401539971	RS378B P42 930 PSD-E WB M102	42 W	-
911401540271	RS378B P42 940 PSD-E WB M102	42 W	-
911401545571	RS378B P11 930 PSU-E WW S	11 W	-

Order Code	Full Product Name	Power Consumption	Suitable for random switching
911401545671	RS378B P11 940 PSU-E WW S	11 W	-
911401546571	RS378B P11 940 PSD-E WW S	11 W	-
911401545971	RS378B P15 940 PSU-E WW S	15 W	-
911401546771	RS378B P15 930 PSD-E WW S	15 W	-
911401536771	RS378B P15 927 PSD-E NB M55	15 W	-
911401536871	RS378B P15 927 PSD-E MB M55	15 W	-
911401536971	RS378B P15 927 PSD-E WB M55	15 W	-
911401537171	RS378B P15 930 PSD-E MB M55	15 W	-
911401537271	RS378B P15 930 PSD-E WB M55	15 W	-
911401537371	RS378B P15 940 PSD-E NB M55	15 W	-
911401537471	RS378B P15 940 PSD-E MB M55	15 W	-
911401537571	RS378B P15 940 PSD-E WB M55	15 W	-
911401540471	RS378B P15 927 PSR-E 1-10V MB M55	15 W	-
911401540771	RS378B P15 930 PSR-E 1-10V MB M55	15 W	-
911401540871	RS378B P15 930 PSR-E 1-10V WB M55	15 W	-
911401541171	RS378B P15 940 PSR-E 1-10V WB M55	15 W	-
911401532371	RS378B P6 927 PSU-E MB M43	6 W	-
911401532471	RS378B P6 927 PSU-E WB M43	6 W	-
911401532571	RS378B P6 930 PSU-E NB M43	6 W	-
911401532671	RS378B P6 930 PSU-E MB M43	6 W	-
911401532771	RS378B P6 930 PSU-E WB M43	6 W	-
911401532871	RS378B P6 940 PSU-E NB M43	6 W	-
911401532971	RS378B P6 940 PSU-E MB M43	6 W	-
911401533071	RS378B P6 940 PSU-E WB M43	6 W	-
911401533271	RS378B P6 927 PSR-E MB M43	6 W	-
911401533571	RS378B P6 930 PSR-E MB M43	6 W	-
911401533671	RS378B P6 930 PSR-E WB M43	6 W	-
911401533771	RS378B P6 940 PSR-E NB M43	6 W	-
911401534471	RS378B P6 930 PSD-E MB M43	6 W	-
911401534571	RS378B P6 930 PSD-E WB M43	6 W	-
911401534771	RS378B P6 940 PSD-E MB M43	6 W	-
911401721252	RS378B P15 927 PSU-E NB M55	15 W	No
911401721262	RS378B P15 930 PSU-E NB M55	15 W	No
911401721272	RS378B P15 940 PSU-E NB M55	15 W	No
911401721282	RS378B P15 927 PSU-E MB M55	15 W	No
911401721292	RS378B P15 930 PSU-E MB M55	15 W	No
911401721302	RS378B P15 940 PSU-E MB M55	15 W	No
911401721312	RS378B P15 927 PSU-E WB M55	15 W	No
911401721322	RS378B P15 930 PSU-E WB M55	15 W	No
911401721332	RS378B P15 940 PSU-E WB M55	15 W	No
911401721372	RS378B P15 927 PSR-E MB M55	15 W	No
911401721412	RS378B P15 930 PSR-E WB M55	15 W	No
911401721422	RS378B P15 940 PSR-E WB M55	15 W	No

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
911401535871	RS378B P11 927 PSD-E NB M55	DALI	-
911401535971	RS378B P11 927 PSD-E MB M55	DALI	-
911401536071	RS378B P11 927 PSD-E WB M55	DALI	-
911401536271	RS378B P11 930 PSD-E MB M55	DALI	-
911401536371	RS378B P11 930 PSD-E WB M55	DALI	-
911401536471	RS378B P11 940 PSD-E NB M55	DALI	-
911401536571	RS378B P11 940 PSD-E MB M55	DALI	-
911401536671	RS378B P11 940 PSD-E WB M55	DALI	-
911401720892	RS378B P6 927 PSU-E NB M55	No	Not applicable
911401720902	RS378B P6 930 PSU-E NB M55	No	Not applicable
911401720912	RS378B P6 940 PSU-E NB M55	No	Not applicable
911401720922	RS378B P6 927 PSU-E MB M55	No	Not applicable
911401720932	RS378B P6 930 PSU-E MB M55	No	Not applicable
911401720942	RS378B P6 940 PSU-E MB M55	No	Not applicable
911401720952	RS378B P6 927 PSU-E WB M55	No	Not applicable
911401720962	RS378B P6 930 PSU-E WB M55	No	Not applicable
911401720972	RS378B P6 940 PSU-E WB M55	No	Not applicable
911401720982	RS378B P11 927 PSU-E NB M55	No	Not applicable
911401720992	RS378B P11 930 PSU-E NB M55	No	Not applicable
911401721002	RS378B P11 940 PSU-E NB M55	No	Not applicable
911401721012	RS378B P11 927 PSU-E MB M55	No	Not applicable
911401721022	RS378B P11 930 PSU-E MB M55	No	Not applicable
911401721032	RS378B P11 940 PSU-E MB M55	No	Not applicable
911401721042	RS378B P11 927 PSU-E WB M55	No	Not applicable
911401721052	RS378B P11 930 PSU-E WB M55	No	Not applicable
911401721062	RS378B P11 940 PSU-E WB M55	No	Not applicable
911401721072	RS378B P6 927 PSR-E NB M55	TRIAC	10%
911401721112	RS378B P6 930 PSR-E MB M55	TRIAC	10%
911401721172	RS378B P11 930 PSR-E NB M55	TRIAC	10%
911401721192	RS378B P11 927 PSR-E MB M55	TRIAC	10%
911401721222	RS378B P11 927 PSR-E WB M55	TRIAC	10%
911401721232	RS378B P11 930 PSR-E WB M55	TRIAC	10%
911401721622	RS378B P42 930 PSU-E NB M102	No	Not applicable
911401721632	RS378B P42 940 PSU-E NB M102	No	Not applicable
911401721642	RS378B P42 927 PSU-E MB M102	No	Not applicable
911401721652	RS378B P42 930 PSU-E MB M102	No	Not applicable
911401721662	RS378B P42 940 PSU-E MB M102	No	Not applicable
911401721682	RS378B P42 930 PSU-E WB M102	No	Not applicable
911401721692	RS378B P42 940 PSU-E WB M102	No	Not applicable
911401534971	RS378B P6 927 PSD-E NB M55	DALI	-
911401535071	RS378B P6 927 PSD-E MB M55	DALI	-
911401535171	RS378B P6 927 PSD-E WB M55	DALI	-
911401535371	RS378B P6 930 PSD-E MB M55	DALI	-
911401535471	RS378B P6 930 PSD-E WB M55	DALI	-
911401535571	RS378B P6 940 PSD-E NB M55	DALI	-
911401537771	RS378B P24 927 PSD-E MB M70	DALI	-
911401538071	RS378B P24 930 PSD-E MB M70	DALI	-
911401538171	RS378B P24 930 PSD-E WB M70	DALI	-
911401538271	RS378B P24 940 PSD-E NB M70	DALI	-
911401538371	RS378B P24 940 PSD-E MB M70	DALI	-
911401538471	RS378B P24 940 PSD-E WB M70	DALI	-
911401721432	RS378B P24 927 PSU-E NB M70	No	Not applicable

Order Code	Full Product Name	Dimmable	Maximum dim level
911401721442	RS378B P24 930 PSU-E NB M70	No	Not applicable
911401721452	RS378B P24 940 PSU-E NB M70	No	Not applicable
911401721472	RS378B P24 930 PSU-E MB M70	No	Not applicable
911401721482	RS378B P24 940 PSU-E MB M70	No	Not applicable
911401721492	RS378B P24 927 PSU-E WB M70	No	Not applicable
911401721502	RS378B P24 930 PSU-E WB M70	No	Not applicable
911401721512	RS378B P24 940 PSU-E WB M70	No	Not applicable
911401538571	RS378B P33 927 PSD-E NB M87	DALI	-
911401538671	RS378B P33 927 PSD-E MB M87	DALI	-
911401538871	RS378B P33 930 PSD-E NB M87	DALI	-
911401539171	RS378B P33 940 PSD-E NB M87	DALI	-
911401721522	RS378B P33 927 PSU-E NB M87	No	Not applicable
911401721532	RS378B P33 930 PSU-E NB M87	No	Not applicable
911401721542	RS378B P33 940 PSU-E NB M87	No	Not applicable
911401721562	RS378B P33 930 PSU-E MB M87	No	Not applicable
911401721572	RS378B P33 940 PSU-E MB M87	No	Not applicable
911401721592	RS378B P33 930 PSU-E WB M87	No	Not applicable
911401721602	RS378B P33 940 PSU-E WB M87	No	Not applicable
911401539871	RS378B P42 930 PSD-E MB M102	DALI	-
911401539971	RS378B P42 930 PSD-E WB M102	DALI	-
911401540271	RS378B P42 940 PSD-E WB M102	DALI	-
911401545571	RS378B P11 930 PSU-E WW S	No	-
911401545671	RS378B P11 940 PSU-E WW S	No	-
911401546571	RS378B P11 940 PSD-E WW S	DALI	-
911401545971	RS378B P15 940 PSU-E WW S	No	-
911401546771	RS378B P15 930 PSD-E WW S	DALI	-
911401536771	RS378B P15 927 PSD-E NB M55	DALI	-
911401536871	RS378B P15 927 PSD-E MB M55	DALI	-
911401536971	RS378B P15 927 PSD-E WB M55	DALI	-
911401537171	RS378B P15 930 PSD-E MB M55	DALI	-
911401537271	RS378B P15 930 PSD-E WB M55	DALI	-
911401537371	RS378B P15 940 PSD-E NB M55	DALI	-
911401537471	RS378B P15 940 PSD-E MB M55	DALI	-
911401537571	RS378B P15 940 PSD-E WB M55	DALI	-
911401540471	RS378B P15 927 PSR-E 1-10V MB M55	1-10V	-
911401540771	RS378B P15 930 PSR-E 1-10V MB M55	1-10V	-
911401540871	RS378B P15 930 PSR-E 1-10V WB M55	1-10V	-
911401541171	RS378B P15 940 PSR-E 1-10V WB M55	1-10V	-
911401532371	RS378B P6 927 PSU-E MB M43	No	-
911401532471	RS378B P6 927 PSU-E WB M43	No	-
911401532571	RS378B P6 930 PSU-E NB M43	No	-
911401532671	RS378B P6 930 PSU-E MB M43	No	-
911401532771	RS378B P6 930 PSU-E WB M43	No	-
911401532871	RS378B P6 940 PSU-E NB M43	No	-
911401532971	RS378B P6 940 PSU-E MB M43	No	-
911401533071	RS378B P6 940 PSU-E WB M43	No	-
911401533271	RS378B P6 927 PSR-E MB M43	TRIAC	-
911401533571	RS378B P6 930 PSR-E MB M43	TRIAC	-
911401533671	RS378B P6 930 PSR-E WB M43	TRIAC	-
911401533771	RS378B P6 940 PSR-E NB M43	TRIAC	-
911401534471	RS378B P6 930 PSD-E MB M43	DALI	-
911401534571	RS378B P6 930 PSD-E WB M43	DALI	-

Order Code	Full Product Name	Dimmable	Maximum dim level
911401534771	RS378B P6 940 PSD-E MB M43	DALI	-
911401721252	RS378B P15 927 PSU-E NB M55	No	Not applicable
911401721262	RS378B P15 930 PSU-E NB M55	No	Not applicable
911401721272	RS378B P15 940 PSU-E NB M55	No	Not applicable
911401721282	RS378B P15 927 PSU-E MB M55	No	Not applicable
911401721292	RS378B P15 930 PSU-E MB M55	No	Not applicable
911401721302	RS378B P15 940 PSU-E MB M55	No	Not applicable

Approval and Application

Order Code	Full Product Name	Glow-wire test
911401535871	RS378B P11 927 PSD-E NB M55	-
911401535971	RS378B P11 927 PSD-E MB M55	-
911401536071	RS378B P11 927 PSD-E WB M55	-
911401536271	RS378B P11 930 PSD-E MB M55	-
911401536371	RS378B P11 930 PSD-E WB M55	-
911401536471	RS378B P11 940 PSD-E NB M55	-
911401536571	RS378B P11 940 PSD-E MB M55	-
911401536671	RS378B P11 940 PSD-E WB M55	-
911401720892	RS378B P6 927 PSU-E NB M55	Temperature 600 °C, duration 30 s
911401720902	RS378B P6 930 PSU-E NB M55	Temperature 600 °C, duration 30 s
911401720912	RS378B P6 940 PSU-E NB M55	Temperature 600 °C, duration 30 s
911401720922	RS378B P6 927 PSU-E MB M55	Temperature 600 °C, duration 30 s
911401720932	RS378B P6 930 PSU-E MB M55	Temperature 600 °C, duration 30 s
911401720942	RS378B P6 940 PSU-E MB M55	Temperature 600 °C, duration 30 s
911401720952	RS378B P6 927 PSU-E WB M55	Temperature 600 °C, duration 30 s
911401720962	RS378B P6 930 PSU-E WB M55	Temperature 600 °C, duration 30 s
911401720972	RS378B P6 940 PSU-E WB M55	Temperature 600 °C, duration 30 s
911401720982	RS378B P11 927 PSU-E NB M55	Temperature 600 °C, duration 30 s
911401720992	RS378B P11 930 PSU-E NB M55	Temperature 600 °C, duration 30 s
911401721002	RS378B P11 940 PSU-E NB M55	Temperature 600 °C, duration 30 s
911401721012	RS378B P11 927 PSU-E MB M55	Temperature 600 °C, duration 30 s
911401721022	RS378B P11 930 PSU-E MB M55	Temperature 600 °C, duration 30 s
911401721032	RS378B P11 940 PSU-E MB M55	Temperature 600 °C, duration 30 s
911401721042	RS378B P11 927 PSU-E WB M55	Temperature 600 °C, duration 30 s

Order Code	Full Product Name	Dimmable	Maximum dim level
911401721312	RS378B P15 927 PSU-E WB M55	No	Not applicable
911401721322	RS378B P15 930 PSU-E WB M55	No	Not applicable
911401721332	RS378B P15 940 PSU-E WB M55	No	Not applicable
911401721372	RS378B P15 927 PSR-E MB M55	TRIAC	10%
911401721412	RS378B P15 930 PSR-E WB M55	TRIAC	10%
911401721422	RS378B P15 940 PSR-E WB M55	TRIAC	10%

Order Code	Full Product Name	Glow-wire test
911401721052	RS378B P11 930 PSU-E WB M55	Temperature 600 °C, duration 30 s
911401721062	RS378B P11 940 PSU-E WB M55	Temperature 600 °C, duration 30 s
911401721072	RS378B P6 927 PSR-E NB M55	Temperature 600 °C, duration 30 s
911401721112	RS378B P6 930 PSR-E MB M55	Temperature 600 °C, duration 30 s
911401721172	RS378B P11 930 PSR-E NB M55	Temperature 600 °C, duration 30 s
911401721192	RS378B P11 927 PSR-E MB M55	Temperature 600 °C, duration 30 s
911401721222	RS378B P11 927 PSR-E WB M55	Temperature 600 °C, duration 30 s
911401721232	RS378B P11 930 PSR-E WB M55	Temperature 600 °C, duration 30 s
911401721622	RS378B P42 930 PSU-E NB M102	Temperature 600 °C, duration 30 s
911401721632	RS378B P42 940 PSU-E NB M102	Temperature 600 °C, duration 30 s
911401721642	RS378B P42 927 PSU-E MB M102	Temperature 600 °C, duration 30 s
911401721652	RS378B P42 930 PSU-E MB M102	Temperature 600 °C, duration 30 s
911401721662	RS378B P42 940 PSU-E MB M102	Temperature 600 °C, duration 30 s
911401721682	RS378B P42 930 PSU-E WB M102	Temperature 600 °C, duration 30 s
911401721692	RS378B P42 940 PSU-E WB M102	Temperature 600 °C, duration 30 s
911401534971	RS378B P6 927 PSD-E NB M55	-
911401535071	RS378B P6 927 PSD-E MB M55	-
911401535171	RS378B P6 927 PSD-E WB M55	-
911401535371	RS378B P6 930 PSD-E MB M55	-
911401535471	RS378B P6 930 PSD-E WB M55	-
911401535571	RS378B P6 940 PSD-E NB M55	-
911401537771	RS378B P24 927 PSD-E MB M70	-
911401538071	RS378B P24 930 PSD-E MB M70	-
911401538171	RS378B P24 930 PSD-E WB M70	-
911401538271	RS378B P24 940 PSD-E NB M70	-
911401538371	RS378B P24 940 PSD-E MB M70	-

Order Code	Full Product Name	Glow-wire test
911401538471	RS378B P24 940 PSD-E WB M70	-
911401721432	RS378B P24 927 PSU-E NB M70	Temperature 600 °C, duration 30 s
911401721442	RS378B P24 930 PSU-E NB M70	Temperature 600 °C, duration 30 s
911401721452	RS378B P24 940 PSU-E NB M70	Temperature 600 °C, duration 30 s
911401721472	RS378B P24 930 PSU-E MB M70	Temperature 600 °C, duration 30 s
911401721482	RS378B P24 940 PSU-E MB M70	Temperature 600 °C, duration 30 s
911401721492	RS378B P24 927 PSU-E WB M70	Temperature 600 °C, duration 30 s
911401721502	RS378B P24 930 PSU-E WB M70	Temperature 600 °C, duration 30 s
911401721512	RS378B P24 940 PSU-E WB M70	Temperature 600 °C, duration 30 s
911401538571	RS378B P33 927 PSD-E NB M87	-
911401538671	RS378B P33 927 PSD-E MB M87	-
911401538871	RS378B P33 930 PSD-E NB M87	-
911401539171	RS378B P33 940 PSD-E NB M87	-
911401721522	RS378B P33 927 PSU-E NB M87	Temperature 600 °C, duration 30 s
911401721532	RS378B P33 930 PSU-E NB M87	Temperature 600 °C, duration 30 s
911401721542	RS378B P33 940 PSU-E NB M87	Temperature 600 °C, duration 30 s
911401721562	RS378B P33 930 PSU-E MB M87	Temperature 600 °C, duration 30 s
911401721572	RS378B P33 940 PSU-E MB M87	Temperature 600 °C, duration 30 s
911401721592	RS378B P33 930 PSU-E WB M87	Temperature 600 °C, duration 30 s
911401721602	RS378B P33 940 PSU-E WB M87	Temperature 600 °C, duration 30 s
911401539871	RS378B P42 930 PSD-E MB M102	-
911401539971	RS378B P42 930 PSD-E WB M102	-
911401540271	RS378B P42 940 PSD-E WB M102	-
911401545571	RS378B P11 930 PSU-E WW S	-
911401545671	RS378B P11 940 PSU-E WW S	-
911401546571	RS378B P11 940 PSD-E WW S	-
911401545971	RS378B P15 940 PSU-E WW S	-
911401546771	RS378B P15 930 PSD-E WW S	-
911401536771	RS378B P15 927 PSD-E NB M55	-
911401536871	RS378B P15 927 PSD-E MB M55	-
911401536971	RS378B P15 927 PSD-E WB M55	-
911401537171	RS378B P15 930 PSD-E MB M55	-

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
911401535871	RS378B P11 927 PSD-E NB M55	-

Order Code	Full Product Name	Glow-wire test
911401537271	RS378B P15 930 PSD-E WB M55	-
911401537371	RS378B P15 940 PSD-E NB M55	-
911401537471	RS378B P15 940 PSD-E MB M55	-
911401537571	RS378B P15 940 PSD-E WB M55	-
911401540471	RS378B P15 927 PSR-E 1-10V MB M55	-
911401540771	RS378B P15 930 PSR-E 1-10V MB M55	-
911401540871	RS378B P15 930 PSR-E 1-10V WB M55	-
911401541171	RS378B P15 940 PSR-E 1-10V WB M55	-
911401532371	RS378B P6 927 PSU-E MB M43	-
911401532471	RS378B P6 927 PSU-E WB M43	-
911401532571	RS378B P6 930 PSU-E NB M43	-
911401532671	RS378B P6 930 PSU-E MB M43	-
911401532771	RS378B P6 930 PSU-E WB M43	-
911401532871	RS378B P6 940 PSU-E NB M43	-
911401532971	RS378B P6 940 PSU-E MB M43	-
911401533071	RS378B P6 940 PSU-E WB M43	-
911401533271	RS378B P6 927 PSR-E MB M43	-
911401533571	RS378B P6 930 PSR-E MB M43	-
911401533671	RS378B P6 930 PSR-E WB M43	-
911401533771	RS378B P6 940 PSR-E NB M43	-
911401534471	RS378B P6 930 PSD-E MB M43	-
911401534571	RS378B P6 930 PSD-E WB M43	-
911401534771	RS378B P6 940 PSD-E MB M43	-
911401721252	RS378B P15 927 PSU-E NB M55	Temperature 600 °C, duration 30 s
911401721262	RS378B P15 930 PSU-E NB M55	Temperature 600 °C, duration 30 s
911401721272	RS378B P15 940 PSU-E NB M55	Temperature 600 °C, duration 30 s
911401721282	RS378B P15 927 PSU-E MB M55	Temperature 600 °C, duration 30 s
911401721292	RS378B P15 930 PSU-E MB M55	Temperature 600 °C, duration 30 s
911401721302	RS378B P15 940 PSU-E MB M55	Temperature 600 °C, duration 30 s
911401721312	RS378B P15 927 PSU-E WB M55	Temperature 600 °C, duration 30 s
911401721322	RS378B P15 930 PSU-E WB M55	Temperature 600 °C, duration 30 s
911401721332	RS378B P15 940 PSU-E WB M55	Temperature 600 °C, duration 30 s
911401721372	RS378B P15 927 PSR-E MB M55	Temperature 600 °C, duration 30 s
911401721412	RS378B P15 930 PSR-E WB M55	Temperature 600 °C, duration 30 s
911401721422	RS378B P15 940 PSR-E WB M55	Temperature 600 °C, duration 30 s

Order Code	Full Product Name	Initial chromaticity
911401535971	RS378B P11 927 PSD-E MB M55	-

Order Code	Full Product Name	Initial chromaticity
911401536071	RS378B P11 927 PSD-E WB M55	-
911401536271	RS378B P11 930 PSD-E MB M55	-
911401536371	RS378B P11 930 PSD-E WB M55	-
911401536471	RS378B P11 940 PSD-E NB M55	-
911401536571	RS378B P11 940 PSD-E MB M55	-
911401536671	RS378B P11 940 PSD-E WB M55	-
911401720892	RS378B P6 927 PSU-E NB M55	SDCM<3
911401720902	RS378B P6 930 PSU-E NB M55	SDCM<3
911401720912	RS378B P6 940 PSU-E NB M55	SDCM<3
911401720922	RS378B P6 927 PSU-E MB M55	SDCM<3
911401720932	RS378B P6 930 PSU-E MB M55	SDCM<3
911401720942	RS378B P6 940 PSU-E MB M55	SDCM<3
911401720952	RS378B P6 927 PSU-E WB M55	SDCM<3
911401720962	RS378B P6 930 PSU-E WB M55	SDCM<3
911401720972	RS378B P6 940 PSU-E WB M55	SDCM<3
911401720982	RS378B P11 927 PSU-E NB M55	SDCM<3
911401720992	RS378B P11 930 PSU-E NB M55	SDCM<3
911401721002	RS378B P11 940 PSU-E NB M55	SDCM<3
911401721012	RS378B P11 927 PSU-E MB M55	SDCM<3
911401721022	RS378B P11 930 PSU-E MB M55	SDCM<3
911401721032	RS378B P11 940 PSU-E MB M55	SDCM<3
911401721042	RS378B P11 927 PSU-E WB M55	SDCM<3
911401721052	RS378B P11 930 PSU-E WB M55	SDCM<3
911401721062	RS378B P11 940 PSU-E WB M55	SDCM<3
911401721072	RS378B P6 927 PSR-E NB M55	SDCM<3
911401721112	RS378B P6 930 PSR-E MB M55	SDCM<3
911401721172	RS378B P11 930 PSR-E NB M55	SDCM<3
911401721192	RS378B P11 927 PSR-E MB M55	SDCM<3
911401721222	RS378B P11 927 PSR-E WB M55	SDCM<3
911401721232	RS378B P11 930 PSR-E WB M55	SDCM<3
911401721622	RS378B P42 930 PSU-E NB M102	SDCM<3
911401721632	RS378B P42 940 PSU-E NB M102	SDCM<3
911401721642	RS378B P42 927 PSU-E MB M102	SDCM<3
911401721652	RS378B P42 930 PSU-E MB M102	SDCM<3
911401721662	RS378B P42 940 PSU-E MB M102	SDCM<3
911401721682	RS378B P42 930 PSU-E WB M102	SDCM<3
911401721692	RS378B P42 940 PSU-E WB M102	SDCM<3
911401534971	RS378B P6 927 PSD-E NB M55	-
911401535071	RS378B P6 927 PSD-E MB M55	-
911401535171	RS378B P6 927 PSD-E WB M55	-
911401535371	RS378B P6 930 PSD-E MB M55	-
911401535471	RS378B P6 930 PSD-E WB M55	-
911401535571	RS378B P6 940 PSD-E NB M55	-
911401537771	RS378B P24 927 PSD-E MB M70	-
911401538071	RS378B P24 930 PSD-E MB M70	-
911401538171	RS378B P24 930 PSD-E WB M70	-
911401538271	RS378B P24 940 PSD-E NB M70	-
911401538371	RS378B P24 940 PSD-E MB M70	-
911401538471	RS378B P24 940 PSD-E WB M70	-
911401721432	RS378B P24 927 PSU-E NB M70	SDCM<3
911401721442	RS378B P24 930 PSU-E NB M70	SDCM<3
911401721452	RS378B P24 940 PSU-E NB M70	SDCM<3

Order Code	Full Product Name	Initial chromaticity
911401721472	RS378B P24 930 PSU-E MB M70	SDCM<3
911401721482	RS378B P24 940 PSU-E MB M70	SDCM<3
911401721492	RS378B P24 927 PSU-E WB M70	SDCM<3
911401721502	RS378B P24 930 PSU-E WB M70	SDCM<3
911401721512	RS378B P24 940 PSU-E WB M70	SDCM<3
911401538571	RS378B P33 927 PSD-E NB M87	-
911401538671	RS378B P33 927 PSD-E MB M87	-
911401538871	RS378B P33 930 PSD-E NB M87	-
911401539171	RS378B P33 940 PSD-E NB M87	-
911401721522	RS378B P33 927 PSU-E NB M87	SDCM<3
911401721532	RS378B P33 930 PSU-E NB M87	SDCM<3
911401721542	RS378B P33 940 PSU-E NB M87	SDCM<3
911401721562	RS378B P33 930 PSU-E MB M87	SDCM<3
911401721572	RS378B P33 940 PSU-E MB M87	SDCM<3
911401721592	RS378B P33 930 PSU-E WB M87	SDCM<3
911401721602	RS378B P33 940 PSU-E WB M87	SDCM<3
911401539871	RS378B P42 930 PSD-E MB M102	-
911401539971	RS378B P42 930 PSD-E WB M102	-
911401540271	RS378B P42 940 PSD-E WB M102	-
911401545571	RS378B P11 930 PSU-E WW S	-
911401545671	RS378B P11 940 PSU-E WW S	-
911401546571	RS378B P11 940 PSD-E WW S	-
911401545971	RS378B P15 940 PSU-E WW S	-
911401546771	RS378B P15 930 PSD-E WW S	-
911401536771	RS378B P15 927 PSD-E NB M55	-
911401536871	RS378B P15 927 PSD-E MB M55	-
911401536971	RS378B P15 927 PSD-E WB M55	-
911401537171	RS378B P15 930 PSD-E MB M55	-
911401537271	RS378B P15 930 PSD-E WB M55	-
911401537371	RS378B P15 940 PSD-E NB M55	-
911401537471	RS378B P15 940 PSD-E MB M55	-
911401537571	RS378B P15 940 PSD-E WB M55	-
911401540471	RS378B P15 927 PSR-E 1-10V MB M55	-
911401540771	RS378B P15 930 PSR-E 1-10V MB M55	-
911401540871	RS378B P15 930 PSR-E 1-10V WB M55	-
911401541171	RS378B P15 940 PSR-E 1-10V WB M55	-
911401532371	RS378B P6 927 PSU-E MB M43	-
911401532471	RS378B P6 927 PSU-E WB M43	-
911401532571	RS378B P6 930 PSU-E NB M43	-
911401532671	RS378B P6 930 PSU-E MB M43	-
911401532771	RS378B P6 930 PSU-E WB M43	-
911401532871	RS378B P6 940 PSU-E NB M43	-
911401532971	RS378B P6 940 PSU-E MB M43	-
911401533071	RS378B P6 940 PSU-E WB M43	-
911401533271	RS378B P6 927 PSR-E MB M43	-
911401533571	RS378B P6 930 PSR-E MB M43	-
911401533671	RS378B P6 930 PSR-E WB M43	-
911401533771	RS378B P6 940 PSR-E NB M43	-
911401534471	RS378B P6 930 PSD-E MB M43	-
911401534571	RS378B P6 930 PSD-E WB M43	-
911401534771	RS378B P6 940 PSD-E MB M43	-
911401721252	RS378B P15 927 PSU-E NB M55	SDCM<3

Order Code	Full Product Name	Initial chromaticity
911401721262	RS378B P15 930 PSU-E NB M55	SDCM<3
911401721272	RS378B P15 940 PSU-E NB M55	SDCM<3
911401721282	RS378B P15 927 PSU-E MB M55	SDCM<3
911401721292	RS378B P15 930 PSU-E MB M55	SDCM<3
911401721302	RS378B P15 940 PSU-E MB M55	SDCM<3
911401721312	RS378B P15 927 PSU-E WB M55	SDCM<3

Order Code	Full Product Name	Initial chromaticity
911401721322	RS378B P15 930 PSU-E WB M55	SDCM<3
911401721332	RS378B P15 940 PSU-E WB M55	SDCM<3
911401721372	RS378B P15 927 PSR-E MB M55	SDCM<3
911401721412	RS378B P15 930 PSR-E WB M55	SDCM<3
911401721422	RS378B P15 940 PSR-E WB M55	SDCM<3

Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Median useful life L80B50
911401535871	RS378B P11 927 PSD-E NB M55	-
911401535971	RS378B P11 927 PSD-E MB M55	-
911401536071	RS378B P11 927 PSD-E WB M55	-
911401536271	RS378B P11 930 PSD-E MB M55	-
911401536371	RS378B P11 930 PSD-E WB M55	-
911401536471	RS378B P11 940 PSD-E NB M55	-
911401536571	RS378B P11 940 PSD-E MB M55	-
911401536671	RS378B P11 940 PSD-E WB M55	-
911401720892	RS378B P6 927 PSU-E NB M55	50,000 hour(s)
911401720902	RS378B P6 930 PSU-E NB M55	50,000 hour(s)
911401720912	RS378B P6 940 PSU-E NB M55	50,000 hour(s)
911401720922	RS378B P6 927 PSU-E MB M55	50,000 hour(s)
911401720932	RS378B P6 930 PSU-E MB M55	50,000 hour(s)
911401720942	RS378B P6 940 PSU-E MB M55	50,000 hour(s)
911401720952	RS378B P6 927 PSU-E WB M55	50,000 hour(s)
911401720962	RS378B P6 930 PSU-E WB M55	50,000 hour(s)
911401720972	RS378B P6 940 PSU-E WB M55	50,000 hour(s)
911401720982	RS378B P11 927 PSU-E NB M55	50,000 hour(s)
911401720992	RS378B P11 930 PSU-E NB M55	50,000 hour(s)
911401721002	RS378B P11 940 PSU-E NB M55	50,000 hour(s)
911401721012	RS378B P11 927 PSU-E MB M55	50,000 hour(s)
911401721022	RS378B P11 930 PSU-E MB M55	50,000 hour(s)
911401721032	RS378B P11 940 PSU-E MB M55	50,000 hour(s)
911401721042	RS378B P11 927 PSU-E WB M55	50,000 hour(s)
911401721052	RS378B P11 930 PSU-E WB M55	50,000 hour(s)
911401721062	RS378B P11 940 PSU-E WB M55	50,000 hour(s)
911401721072	RS378B P6 927 PSR-E NB M55	50,000 hour(s)
911401721112	RS378B P6 930 PSR-E MB M55	50,000 hour(s)
911401721172	RS378B P11 930 PSR-E NB M55	50,000 hour(s)
911401721192	RS378B P11 927 PSR-E MB M55	50,000 hour(s)
911401721222	RS378B P11 927 PSR-E WB M55	50,000 hour(s)
911401721232	RS378B P11 930 PSR-E WB M55	50,000 hour(s)
911401721622	RS378B P42 930 PSU-E NB M102	50,000 hour(s)
911401721632	RS378B P42 940 PSU-E NB M102	50,000 hour(s)
911401721642	RS378B P42 927 PSU-E MB M102	50,000 hour(s)
911401721652	RS378B P42 930 PSU-E MB M102	50,000 hour(s)
911401721662	RS378B P42 940 PSU-E MB M102	50,000 hour(s)
911401721682	RS378B P42 930 PSU-E WB M102	50,000 hour(s)
911401721692	RS378B P42 940 PSU-E WB M102	50,000 hour(s)
911401534971	RS378B P6 927 PSD-E NB M55	-
911401535071	RS378B P6 927 PSD-E MB M55	-
911401535171	RS378B P6 927 PSD-E WB M55	-

Order Code	Full Product Name	Median useful life L80B50
911401535371	RS378B P6 930 PSD-E MB M55	-
911401535471	RS378B P6 930 PSD-E WB M55	-
911401535571	RS378B P6 940 PSD-E NB M55	-
911401537771	RS378B P24 927 PSD-E MB M70	-
911401538071	RS378B P24 930 PSD-E MB M70	-
911401538171	RS378B P24 930 PSD-E WB M70	-
911401538271	RS378B P24 940 PSD-E NB M70	-
911401538371	RS378B P24 940 PSD-E MB M70	-
911401538471	RS378B P24 940 PSD-E WB M70	-
911401721432	RS378B P24 927 PSU-E NB M70	50,000 hour(s)
911401721442	RS378B P24 930 PSU-E NB M70	50,000 hour(s)
911401721452	RS378B P24 940 PSU-E NB M70	50,000 hour(s)
911401721472	RS378B P24 930 PSU-E MB M70	50,000 hour(s)
911401721482	RS378B P24 940 PSU-E MB M70	50,000 hour(s)
911401721492	RS378B P24 927 PSU-E WB M70	50,000 hour(s)
911401721502	RS378B P24 930 PSU-E WB M70	50,000 hour(s)
911401721512	RS378B P24 940 PSU-E WB M70	50,000 hour(s)
911401538571	RS378B P33 927 PSD-E NB M87	-
911401538671	RS378B P33 927 PSD-E MB M87	-
911401538871	RS378B P33 930 PSD-E NB M87	-
911401539171	RS378B P33 940 PSD-E NB M87	-
911401721522	RS378B P33 927 PSU-E NB M87	50,000 hour(s)
911401721532	RS378B P33 930 PSU-E NB M87	50,000 hour(s)
911401721542	RS378B P33 940 PSU-E NB M87	50,000 hour(s)
911401721562	RS378B P33 930 PSU-E MB M87	50,000 hour(s)
911401721572	RS378B P33 940 PSU-E MB M87	50,000 hour(s)
911401721592	RS378B P33 930 PSU-E WB M87	50,000 hour(s)
911401721602	RS378B P33 940 PSU-E WB M87	50,000 hour(s)
911401539871	RS378B P42 930 PSD-E MB M102	-
911401539971	RS378B P42 930 PSD-E WB M102	-
911401540271	RS378B P42 940 PSD-E WB M102	-
911401545571	RS378B P11 930 PSU-E WW S	-
911401545671	RS378B P11 940 PSU-E WW S	-
911401546571	RS378B P11 940 PSD-E WW S	-
911401545971	RS378B P15 940 PSU-E WW S	-
911401546771	RS378B P15 930 PSD-E WW S	-
911401536771	RS378B P15 927 PSD-E NB M55	-
911401536871	RS378B P15 927 PSD-E MB M55	-
911401536971	RS378B P15 927 PSD-E WB M55	-
911401537171	RS378B P15 930 PSD-E MB M55	-
911401537271	RS378B P15 930 PSD-E WB M55	-
911401537371	RS378B P15 940 PSD-E NB M55	-

Order Code	Full Product Name	Median useful life L80B50
911401537471	RS378B P15 940 PSD-E MB M55	-
911401537571	RS378B P15 940 PSD-E WB M55	-
911401540471	RS378B P15 927 PSR-E 1-10V MB M55	-
911401540771	RS378B P15 930 PSR-E 1-10V MB M55	-
911401540871	RS378B P15 930 PSR-E 1-10V WB M55	-
911401541171	RS378B P15 940 PSR-E 1-10V WB M55	-
911401532371	RS378B P6 927 PSU-E MB M43	-
911401532471	RS378B P6 927 PSU-E WB M43	-
911401532571	RS378B P6 930 PSU-E NB M43	-
911401532671	RS378B P6 930 PSU-E MB M43	-
911401532771	RS378B P6 930 PSU-E WB M43	-
911401532871	RS378B P6 940 PSU-E NB M43	-
911401532971	RS378B P6 940 PSU-E MB M43	-
911401533071	RS378B P6 940 PSU-E WB M43	-
911401533271	RS378B P6 927 PSR-E MB M43	-
911401533571	RS378B P6 930 PSR-E MB M43	-
911401533671	RS378B P6 930 PSR-E WB M43	-

Order Code	Full Product Name	Median useful life L80B50
911401533771	RS378B P6 940 PSR-E NB M43	-
911401534471	RS378B P6 930 PSD-E MB M43	-
911401534571	RS378B P6 930 PSD-E WB M43	-
911401534771	RS378B P6 940 PSD-E MB M43	-
911401721252	RS378B P15 927 PSU-E NB M55	50,000 hour(s)
911401721262	RS378B P15 930 PSU-E NB M55	50,000 hour(s)
911401721272	RS378B P15 940 PSU-E NB M55	50,000 hour(s)
911401721282	RS378B P15 927 PSU-E MB M55	50,000 hour(s)
911401721292	RS378B P15 930 PSU-E MB M55	50,000 hour(s)
911401721302	RS378B P15 940 PSU-E MB M55	50,000 hour(s)
911401721312	RS378B P15 927 PSU-E WB M55	50,000 hour(s)
911401721322	RS378B P15 930 PSU-E WB M55	50,000 hour(s)
911401721332	RS378B P15 940 PSU-E WB M55	50,000 hour(s)
911401721372	RS378B P15 927 PSR-E MB M55	50,000 hour(s)
911401721412	RS378B P15 930 PSR-E WB M55	50,000 hour(s)
911401721422	RS378B P15 940 PSR-E WB M55	50,000 hour(s)

