



GreenSpace Flex Luna – Bringing moonlight inside.

GreenSpace Flex Luna

Ever-changing yet dependable, the moon reflects the very essence of hospitality lighting, which is adaptable, elegant, and always in tune with its surroundings. GreenSpace Flex Luna is designed to evoke a unique sensation. Like the moon, Luna does not overpower but enhances its surroundings, casting a glow that feels both intimate and grand. It is not just a light. It is an intimate experience.

Benefits

- Sustainable, more light with less energy consumption, up to 120lm/W.
- Silent brilliance with superior visual comfort.
- Deliver light that speaks luxury, supported by superior color consistency and beam control.
- Comprehensive family offering, maintain effortlessly with ceiling proof design.

Features

- Leading lm/W, up to 120lm/W on luminaire level.
- 40° cut off angle and UGR19 for major variants.
- Leading color performance, with CRI92, R9>50.
- Super color consistency, SDCM 3 on luminaire level and SDCM 2 on COB level.
- Modular design concept, supporting strong customization and flexibility on family level, covering cut out(D35 to D100), optics (12° to 55°), controls (PSU, PSD, 1-10V, WIA) and customized reflector and front ring color options.

Application

- Hospitality
- Retail
- Offices
- General indoor space


GreenSpace Flex Luna

Versions



GreenSpace Flex Luna

Dimensional drawing



General Information	
Driver included	Yes
Light Technical	
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	92
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Controls and Dimming	
Dimmable	DALI
Mechanical and Housing	
Optical cover type	Lens
Housing Color	Black
Mech. impact protection code	IK03
Approval and Application	
Ambient temperature range	-20 to +45 °C
CE mark	No
ENEC mark	-
Initial Performance (IEC Compliant)	
Luminous flux tolerance	-10% / +10%

Light Technical

Order Code	Full Product Name	Luminous Efficacy (rated)	
		(Nom)	Luminous Flux
911401581747	RS378B P9 930 PSD VWB D75 G-TT PROCAU	94 lm/W	895 lm
911401581847	RS378B P9 930 PSD VWB WP D75 G-TT PROCAU	94 lm/W	895 lm
911401582147	RS378B P9 930 PSD MB D75 G-TT PROCAU	97 lm/W	920 lm
911401582247	RS378B P9 930 PSD MB WP D75 G-TT PROCAU	97 lm/W	920 lm
911401582747	RS378B P12 930 PSD VWB WP D100M-WHPROCAU	118 lm/W	1,510 lm
911401582847	RS378B P12 930 PSD VWB D100 M-WH PROCAU	118 lm/W	1,510 lm
911401583147	RS378B P12 930 PSD MB WP D100M-WHPROCAU	118 lm/W	1,510 lm
911401583247	RS378B P12 930 PSD MB D100 M-WH PROCAU	118 lm/W	1,510 lm
911401580947	RS378B P7 930 PSD VWB D55 G-TT PROCAU	77 lm/W	570 lm
911401581047	RS378B P7 930 PSD VWB WP D55 G-TT PROCAU	77 lm/W	570 lm
911401581347	RS378B P7 930 PSD MB D55 G-TT PROCAU	74 lm/W	545 lm
911401581447	RS378B P7 930 PSD MB WP D55 G-TT PROCAU	74 lm/W	545 lm
911401581147	RS378B P7 930 PSD VWB WP D55 M-WH PROCAU	77 lm/W	570 lm
911401581247	RS378B P7 930 PSD VWB D55 M-WH PROCAU	77 lm/W	570 lm
911401581547	RS378B P7 930 PSD MB WP D55 M-WH PROCAU	74 lm/W	545 lm
911401581647	RS378B P7 930 PSD MB D55 M-WH PROCAU	74 lm/W	545 lm
911401582547	RS378B P12 930 PSD VWB D100 G-TT PROCAU	118 lm/W	1,510 lm
911401582647	RS378B P12 930 PSD VWB WP D100G-TTPROCAU	118 lm/W	1,510 lm
911401582947	RS378B P12 930 PSD MB D100 G-TT PROCAU	118 lm/W	1,510 lm
911401583047	RS378B P12 930 PSD MB WP D100G-TTPROCAU	118 lm/W	1,510 lm
911401581947	RS378B P9 930 PSD VWB WP D75 M-WH PROCAU	94 lm/W	895 lm
911401582047	RS378B P9 930 PSD VWB D75 M-WH PROCAU	94 lm/W	895 lm
911401582347	RS378B P9 930 PSD MB WP D75 M-WH PROCAU	97 lm/W	920 lm
911401582447	RS378B P9 930 PSD MB D75 M-WH PROCAU	97 lm/W	920 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401581747	RS378B P9 930 PSD VWB D75 G-TT PROCAU	9.5 W
911401581847	RS378B P9 930 PSD VWB WP D75 G-TT PROCAU	9.5 W
911401582147	RS378B P9 930 PSD MB D75 G-TT PROCAU	9.5 W
911401582247	RS378B P9 930 PSD MB WP D75 G-TT PROCAU	9.5 W
911401582747	RS378B P12 930 PSD VWB WP D100M-WHPROCAU	12.8 W
911401582847	RS378B P12 930 PSD VWB D100 M-WH PROCAU	12.8 W
911401583147	RS378B P12 930 PSD MB WP D100M-WHPROCAU	12.8 W
911401583247	RS378B P12 930 PSD MB D100 M-WH PROCAU	12.8 W
911401580947	RS378B P7 930 PSD VWB D55 G-TT PROCAU	7.4 W
911401581047	RS378B P7 930 PSD VWB WP D55 G-TT PROCAU	7.4 W
911401581347	RS378B P7 930 PSD MB D55 G-TT PROCAU	7.4 W
911401581447	RS378B P7 930 PSD MB WP D55 G-TT PROCAU	7.4 W
911401581147	RS378B P7 930 PSD VWB WP D55 M-WH PROCAU	7.4 W

Order Code	Full Product Name	Power Consumption
911401581247	RS378B P7 930 PSD VWB D55 M-WH PROCAU	7.4 W
911401581547	RS378B P7 930 PSD MB WP D55 M-WH PROCAU	7.4 W
911401581647	RS378B P7 930 PSD MB D55 M-WH PROCAU	7.4 W
911401582547	RS378B P12 930 PSD VWB D100 G-TT PROCAU	12.8 W
911401582647	RS378B P12 930 PSD VWB WP D100G-TTPROCAU	12.8 W
911401582947	RS378B P12 930 PSD MB D100 G-TT PROCAU	12.8 W
911401583047	RS378B P12 930 PSD MB WP D100G-TTPROCAU	12.8 W
911401581947	RS378B P9 930 PSD VWB WP D75 M-WH PROCAU	9.5 W
911401582047	RS378B P9 930 PSD VWB D75 M-WH PROCAU	9.5 W
911401582347	RS378B P9 930 PSD MB WP D75 M-WH PROCAU	9.5 W
911401582447	RS378B P9 930 PSD MB D75 M-WH PROCAU	9.5 W

Mechanical and Housing

Order Code	Full Product Name	Ingress protection code
911401581747	RS378B P9 930 PSD VWB D75 G-TT PROCAU	IP20

Order Code	Full Product Name	Ingress protection code
911401581847	RS378B P9 930 PSD VWB WP D75 G-TT PROCAU	IP20/54

GreenSpace Flex Luna

Order Code	Full Product Name	Ingress protection code
911401582147	RS378B P9 930 PSD MB D75 G-TT PROCAU	IP20
911401582247	RS378B P9 930 PSD MB WP D75 G-TT PROCAU	IP20/54
911401582747	RS378B P12 930 PSD VWB WP D100M-WHPROCAU	IP20/54
911401582847	RS378B P12 930 PSD VWB D100 M-WH PROCAU	IP20
911401583147	RS378B P12 930 PSD MB WP D100M-WHPROCAU	IP20/54
911401583247	RS378B P12 930 PSD MB D100 M-WH PROCAU	IP20
911401580947	RS378B P7 930 PSD VWB D55 G-TT PROCAU	IP20
911401581047	RS378B P7 930 PSD VWB WP D55 G-TT PROCAU	IP20/54
911401581347	RS378B P7 930 PSD MB D55 G-TT PROCAU	IP20
911401581447	RS378B P7 930 PSD MB WP D55 G-TT PROCAU	IP20/54
911401581147	RS378B P7 930 PSD VWB WP D55 M-WH PROCAU	IP20/54

Order Code	Full Product Name	Ingress protection code
911401581247	RS378B P7 930 PSD VWB D55 M-WH PROCAU	IP20
911401581547	RS378B P7 930 PSD MB WP D55 M-WH PROCAU	IP20/54
911401581647	RS378B P7 930 PSD MB D55 M-WH PROCAU	IP20
911401582547	RS378B P12 930 PSD VWB D100 G-TT PROCAU	IP20
911401582647	RS378B P12 930 PSD VWB WP D100G-TTPROCAU	IP20/54
911401582947	RS378B P12 930 PSD MB D100 G-TT PROCAU	IP20
911401583047	RS378B P12 930 PSD MB WP D100G-TTPROCAU	IP20/54
911401581947	RS378B P9 930 PSD VWB WP D75 M-WH PROCAU	IP20/54
911401582047	RS378B P9 930 PSD VWB D75 M-WH PROCAU	IP20
911401582347	RS378B P9 930 PSD MB WP D75 M-WH PROCAU	IP20/54
911401582447	RS378B P9 930 PSD MB D75 M-WH PROCAU	IP20

