



# GreenSpace Flex Luna – Bringing moonlight inside.

## GreenSpace Flex Luna

Ever-changing yet dependable, the moon reflects the very essence of hospitality lighting, which is adaptable, elegant, and always in tune with its surroundings. GreenSpace Flex Luna is designed to evoke a unique sensation. Like the moon, Luna does not overpower but enhances its surroundings, casting a glow that feels both intimate and grand. It is not just a light. It is an intimate experience.

### Benefits

- Sustainable, more light with less energy consumption, up to 120lm/W.
- Silent brilliance with superior visual comfort.
- Deliver light that speaks luxury, supported by superior color consistency and beam control.
- Comprehensive family offering, maintain effortlessly with ceiling proof design.

### Features

- Leading lm/W, up to 120lm/W on luminaire level.
- 40° cut off angle and UGR19 for major variants.
- Leading color performance, with CRI92, R9>50.
- Super color consistency, SDCM 3 on luminaire level and SDCM 2 on COB level.
- Modular design concept, supporting strong customization and flexibility on family level, covering cut out(D35 to D100), optics (12° to 55°), controls (PSU, PSD, 1-10V, WIA) and customized reflector and front ring color options.

### Application

- Hospitality
- Retail
- Offices
- General indoor space

# GreenSpace Flex Luna













## Versions




GreenSpace Flex Luna

GreenSpace Flex Luna

## Dimensional drawing



## Dimensional drawing



### Operating and Electrical

Protection class IEC	Safety class II
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz

### Mechanical and Housing

Optical cover type	Lens
Housing Color	Black
Mech. impact protection code	IK03

### Approval and Application

Ambient temperature range	-20 to +45 °C
---------------------------	---------------

### Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
-------------------------	-------------

### Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401528746	SM378B R P14 940 PSD-E WB D100 G-TT PRO	4000 K	92	111 lm/W	1,615 lm
911401528846	SM378X R P8 930 WIA MB D100 G-TT PRO	3000 K	92	118 lm/W	965 lm
911401528946	SM378X R P8 930 WIA WB D100 G-TT PRO	3000 K	92	113 lm/W	930 lm
911401500046	RS378B P7 930 PSD-E WB M43 PRO	3000 K	92	81 lm/W	600 lm
911401500146	RS378B P7 940 PSD-E WB M43 PRO	4000 K	92	89 lm/W	660 lm
911401500246	RS378B P6 930 PSU-E MB M43 WP PRO	3000 K	92	92 lm/W	540 lm
911401500346	RS378B P6 930 PSU-E WB M43 WP PRO	3000 K	92	92 lm/W	545 lm
911401500446	RS378B P8 930 PSU-E MB M43 WP PRO	3000 K	92	86 lm/W	685 lm
911401500546	RS378B P8 930 PSU-E WB M43 WP PRO	3000 K	92	88 lm/W	705 lm
911401520146	RS378B P7 PSD-TNW NB M43 PRO	Tunable White	90	71 lm/W	530 lm
911401520246	RS378B P7 PSD-TNW MB M43 PRO	Tunable White	90	71 lm/W	530 lm
911401520346	RS378B P7 PSD-TNW WB M43 PRO	Tunable White	90	77 lm/W	580 lm
911401596945	RS378B P6 927 PSU-E SNB M43 PRO	2700 K	92	73 lm/W	475 lm
911401597045	RS378B P6 930 PSU-E SNB M43 PRO	3000 K	92	78 lm/W	510 lm
911401597145	RS378B P6 940 PSU-E SNB M43 PRO	4000 K	92	83 lm/W	540 lm
911401597245	RS378B P6 927 PSU-E NB M43 PRO	2700 K	92	85 lm/W	500 lm
911401597345	RS378B P6 930 PSU-E NB M43 PRO	3000 K	92	90 lm/W	530 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401597445	RS378B P6 940 PSU-E NB M43 PRO	4000 K	92	93 lm/W	550 lm
911401597545	RS378B P6 927 PSU-E MB M43 PRO	2700 K	92	86 lm/W	510 lm
911401597645	RS378B P6 930 PSU-E MB M43 PRO	3000 K	92	92 lm/W	540 lm
911401597745	RS378B P6 940 PSU-E MB M43 PRO	4000 K	92	99 lm/W	585 lm
911401597845	RS378B P6 927 PSU-E WB M43 PRO	2700 K	92	89 lm/W	525 lm
911401597945	RS378B P6 930 PSU-E WB M43 PRO	3000 K	92	92 lm/W	545 lm
911401598045	RS378B P6 940 PSU-E WB M43 PRO	4000 K	92	102 lm/W	600 lm
911401598145	RS378B P8 927 PSU-E NB M43 PRO	2700 K	92	78 lm/W	625 lm
911401598245	RS378B P8 930 PSU-E NB M43 PRO	3000 K	92	83 lm/W	665 lm
911401598345	RS378B P8 940 PSU-E NB M43 PRO	4000 K	92	88 lm/W	705 lm
911401598445	RS378B P8 927 PSU-E MB M43 PRO	2700 K	92	81 lm/W	645 lm
911401598545	RS378B P8 930 PSU-E MB M43 PRO	3000 K	92	86 lm/W	685 lm
911401598645	RS378B P8 940 PSU-E MB M43 PRO	4000 K	92	91 lm/W	725 lm
911401598745	RS378B P8 927 PSU-E WB M43 PRO	2700 K	92	83 lm/W	665 lm
911401598845	RS378B P8 930 PSU-E WB M43 PRO	3000 K	92	88 lm/W	705 lm
911401598945	RS378B P8 940 PSU-E WB M43 PRO	4000 K	92	94 lm/W	750 lm
911401599045	RS378B P7 927 PSD-E SNB M43 PRO	2700 K	92	70 lm/W	525 lm
911401599145	RS378B P7 930 PSD-E SNB M43 PRO	3000 K	92	74 lm/W	555 lm
911401599245	RS378B P7 940 PSD-E SNB M43 PRO	4000 K	92	79 lm/W	595 lm
911401599345	RS378B P7 927 PSD-E NB M43 PRO	2700 K	92	74 lm/W	550 lm
911401599445	RS378B P7 930 PSD-E NB M43 PRO	3000 K	92	79 lm/W	585 lm
911401599545	RS378B P7 940 PSD-E NB M43 PRO	4000 K	92	82 lm/W	605 lm
911401599645	RS378B P7 927 PSD-E MB M43 PRO	2700 K	92	76 lm/W	560 lm
911401599745	RS378B P7 930 PSD-E MB M43 PRO	3000 K	92	80 lm/W	595 lm
911401599845	RS378B P7 940 PSD-E MB M43 PRO	4000 K	92	87 lm/W	645 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401599945	RS378B P7 927 PSD-E WB M43 PRO	2700 K	92	78 lm/W	575 lm
911401500646	RS378B P7 927 PSU-E SNB M55 PRO	2700 K	92	86 lm/W	620 lm
911401500746	RS378B P7 930 PSU-E SNB M55 PRO	3000 K	92	92 lm/W	660 lm
911401500846	RS378B P7 940 PSU-E SNB M55 PRO	4000 K	92	97 lm/W	700 lm
911401500946	RS378B P7 927 PSU-E NB M55 PRO	2700 K	92	105 lm/W	745 lm
911401501046	RS378B P7 930 PSU-E NB M55 PRO	3000 K	92	112 lm/W	795 lm
911401501146	RS378B P7 940 PSU-E NB M55 PRO	4000 K	92	115 lm/W	820 lm
911401501246	RS378B P7 927 PSU-E MB M55 PRO	2700 K	92	108 lm/W	765 lm
911401501346	RS378B P7 930 PSU-E MB M55 PRO	3000 K	92	114 lm/W	810 lm
911401501446	RS378B P7 940 PSU-E MB M55 PRO	4000 K	92	118 lm/W	835 lm
911401501546	RS378B P7 927 PSU-E WB M55 PRO	2700 K	92	111 lm/W	785 lm
911401501646	RS378B P7 930 PSU-E WB M55 PRO	3000 K	92	116 lm/W	825 lm
911401501746	RS378B P7 940 PSU-E WB M55 PRO	4000 K	92	121 lm/W	860 lm
911401501846	RS378B P8 927 PSU-E SNB M55 PRO	2700 K	92	83 lm/W	665 lm
911401501946	RS378B P8 930 PSU-E SNB M55 PRO	3000 K	92	88 lm/W	705 lm
911401502046	RS378B P8 940 PSU-E SNB M55 PRO	4000 K	92	93 lm/W	745 lm
911401502146	RS378B P9 927 PSU-E NB M55 PRO	2700 K	92	99 lm/W	890 lm
911401502246	RS378B P9 930 PSU-E NB M55 PRO	3000 K	92	106 lm/W	950 lm
911401502346	RS378B P9 940 PSU-E NB M55 PRO	4000 K	92	109 lm/W	980 lm
911401502446	RS378B P9 927 PSU-E MB M55 PRO	2700 K	92	102 lm/W	920 lm
911401502546	RS378B P9 930 PSU-E MB M55 PRO	3000 K	92	109 lm/W	980 lm
911401502646	RS378B P9 940 PSU-E MB M55 PRO	4000 K	92	111 lm/W	1,000 lm
911401502746	RS378B P9 927 PSU-E WB M55 PRO	2700 K	92	106 lm/W	950 lm
911401502846	RS378B P9 930 PSU-E WB M55 PRO	3000 K	92	111 lm/W	1,000 lm
911401502946	RS378B P9 940 PSU-E WB M55 PRO	4000 K	92	114 lm/W	1,030 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401504846	RS378B P7 927 PSD-E SNB M55 PRO	2700 K	92	77 lm/W	580 lm
911401504946	RS378B P7 930 PSD-E SNB M55 PRO	3000 K	92	84 lm/W	630 lm
911401505046	RS378B P7 940 PSD-E SNB M55 PRO	4000 K	92	87 lm/W	655 lm
911401505146	RS378B P7 927 PSD-E NB M55 PRO	2700 K	92	96 lm/W	700 lm
911401505246	RS378B P7 930 PSD-E NB M55 PRO	3000 K	92	102 lm/W	745 lm
911401505346	RS378B P7 940 PSD-E NB M55 PRO	4000 K	92	105 lm/W	770 lm
911401505446	RS378B P7 927 PSD-E MB M55 PRO	2700 K	92	98 lm/W	715 lm
911401505546	RS378B P7 930 PSD-E MB M55 PRO	3000 K	92	104 lm/W	760 lm
911401505646	RS378B P7 940 PSD-E MB M55 PRO	4000 K	92	107 lm/W	780 lm
911401505746	RS378B P7 927 PSD-E WB M55 PRO	2700 K	92	101 lm/W	735 lm
911401505846	RS378B P7 930 PSD-E WB M55 PRO	3000 K	92	105 lm/W	770 lm
911401505946	RS378B P7 940 PSD-E WB M55 PRO	4000 K	92	110 lm/W	805 lm
911401506046	RS378B P9 927 PSD-E NB M55 PRO	2700 K	92	94 lm/W	890 lm
911401506146	RS378B P9 930 PSD-E NB M55 PRO	3000 K	92	100 lm/W	950 lm
911401506246	RS378B P9 940 PSD-E NB M55 PRO	4000 K	92	103 lm/W	980 lm
911401506346	RS378B P9 927 PSD-E MB M55 PRO	2700 K	92	97 lm/W	920 lm
911401506446	RS378B P9 930 PSD-E MB M55 PRO	3000 K	92	103 lm/W	980 lm
911401506546	RS378B P9 940 PSD-E MB M55 PRO	4000 K	92	105 lm/W	1,000 lm
911401506646	RS378B P9 927 PSD-E WB M55 PRO	2700 K	92	100 lm/W	950 lm
911401506746	RS378B P9 930 PSD-E WB M55 PRO	3000 K	92	105 lm/W	1,000 lm
911401506846	RS378B P9 940 PSD-E WB M55 PRO	4000 K	92	108 lm/W	1,030 lm
911401509346	RS378B P7 930 PSU-E MB M55 WP PRO	3000 K	92	114 lm/W	810 lm
911401509446	RS378B P7 930 PSU-E WB M55 WP PRO	3000 K	92	116 lm/W	825 lm
911401509546	RS378B P9 930 PSU-E MB M55 WP PRO	3000 K	92	109 lm/W	980 lm
911401509646	RS378B P9 930 PSU-E WB M55 WP PRO	3000 K	92	111 lm/W	1,000 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401518946	RS378B P7 PSD-TNW NB M55 PRO	Tunable White	90	73 lm/W	520 lm
911401519046	RS378B P7 PSD-TNW MB M55 PRO	Tunable White	90	75 lm/W	530 lm
911401519146	RS378B P7 PSD-TNW WB M55 PRO	Tunable White	90	77 lm/W	550 lm
911401519246	RS378B P9 PSD-TNW NB M55 PRO	Tunable White	90	72 lm/W	650 lm
911401519346	RS378B P9 PSD-TNW MB M55 PRO	Tunable White	90	74 lm/W	670 lm
911401519446	RS378B P9 PSD-TNW WB M55 PRO	Tunable White	90	77 lm/W	690 lm
911401595145	RS378B P3 927 PSU-E MB D35 G-TT PRO	2700 K	92	74 lm/W	230 lm
911401595245	RS378B P3 930 PSU-E MB D35 G-TT PRO	3000 K	92	79 lm/W	245 lm
911401595345	RS378B P3 940 PSU-E MB D35 G-TT PRO	4000 K	92	84 lm/W	260 lm
911401595445	RS378B P3 927 PSU-E WB D35 G-TT PRO	2700 K	92	71 lm/W	220 lm
911401595545	RS378B P3 930 PSU-E WB D35 G-TT PRO	3000 K	92	79 lm/W	245 lm
911401595645	RS378B P3 940 PSU-E WB D35 G-TT PRO	4000 K	92	81 lm/W	250 lm
911401595745	RS378B P5 927 PSU-E MB D35 G-TT PRO	2700 K	92	73 lm/W	345 lm
911401595845	RS378B P5 930 PSU-E MB D35 G-TT PRO	3000 K	92	79 lm/W	370 lm
911401595945	RS378B P5 940 PSU-E MB D35 G-TT PRO	4000 K	92	83 lm/W	390 lm
911401596045	RS378B P5 927 PSU-E WB D35 G-TT PRO	2700 K	92	72 lm/W	340 lm
911401596145	RS378B P5 930 PSU-E WB D35 G-TT PRO	3000 K	92	78 lm/W	365 lm
911401596245	RS378B P5 940 PSU-E WB D35 G-TT PRO	4000 K	92	83 lm/W	390 lm
911401596345	RS378B P5 927 PSD-E MB D35 G-TT PRO	2700 K	92	59 lm/W	315 lm
911401596445	RS378B P5 930 PSD-E MB D35 G-TT PRO	3000 K	92	63 lm/W	335 lm
911401596545	RS378B P5 940 PSD-E MB D35 G-TT PRO	4000 K	92	67 lm/W	355 lm
911401596645	RS378B P5 927 PSD-E WB D35 G-TT PRO	2700 K	92	58 lm/W	310 lm
911401596745	RS378B P5 930 PSD-E WB D35 G-TT PRO	3000 K	92	62 lm/W	330 lm
911401596845	RS378B P5 940 PSD-E WB D35 G-TT PRO	4000 K	92	67 lm/W	355 lm
911401510146	RS378B P12 927 PSU-E NB M70 PRO	2700 K	92	123 lm/W	1,475 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401510246	RS378B P12 930 PSU-E NB M70 PRO	3000 K	92	132 lm/W	1,585 lm
911401510346	RS378B P12 940 PSU-E NB M70 PRO	4000 K	92	131 lm/W	1,575 lm
911401510446	RS378B P12 927 PSU-E MB M70 PRO	2700 K	92	121 lm/W	1,455 lm
911401510546	RS378B P12 930 PSU-E MB M70 PRO	3000 K	92	135 lm/W	1,625 lm
911401510646	RS378B P12 940 PSU-E MB M70 PRO	4000 K	92	138 lm/W	1,650 lm
911401510746	RS378B P12 927 PSU-E WB M70 PRO	2700 K	92	130 lm/W	1,560 lm
911401510846	RS378B P12 930 PSU-E WB M70 PRO	3000 K	92	138 lm/W	1,655 lm
911401510946	RS378B P12 940 PSU-E WB M70 PRO	4000 K	92	143 lm/W	1,710 lm
911401511046	RS378B P17 927 PSU-E NB M70 PRO	2700 K	92	120 lm/W	2,095 lm
911401511146	RS378B P17 930 PSU-E NB M70 PRO	3000 K	92	128 lm/W	2,245 lm
911401511246	RS378B P17 940 PSU-E NB M70 PRO	4000 K	92	133 lm/W	2,330 lm
911401511346	RS378B P17 927 PSU-E MB M70 PRO	2700 K	92	118 lm/W	2,065 lm
911401511446	RS378B P17 930 PSU-E MB M70 PRO	3000 K	92	131 lm/W	2,295 lm
911401511546	RS378B P17 940 PSU-E MB M70 PRO	4000 K	92	135 lm/W	2,365 lm
911401511646	RS378B P17 927 PSU-E WB M70 PRO	2700 K	92	128 lm/W	2,240 lm
911401511746	RS378B P17 930 PSU-E WB M70 PRO	3000 K	92	136 lm/W	2,385 lm
911401511846	RS378B P17 940 PSU-E WB M70 PRO	4000 K	92	137 lm/W	2,390 lm
911401511946	RS378B P19 927 PSU-E NB M70 PRO	2700 K	92	116 lm/W	2,270 lm
911401512046	RS378B P19 930 PSU-E NB M70 PRO	3000 K	92	123 lm/W	2,390 lm
911401512146	RS378B P19 940 PSU-E NB M70 PRO	4000 K	92	129 lm/W	2,510 lm
911401512246	RS378B P19 927 PSU-E MB M70 PRO	2700 K	92	116 lm/W	2,265 lm
911401512346	RS378B P19 930 PSU-E MB M70 PRO	3000 K	92	128 lm/W	2,505 lm
911401512446	RS378B P19 940 PSU-E MB M70 PRO	4000 K	92	133 lm/W	2,585 lm
911401512546	RS378B P19 927 PSU-E WB M70 PRO	2700 K	92	125 lm/W	2,435 lm
911401512646	RS378B P19 930 PSU-E WB M70 PRO	3000 K	92	133 lm/W	2,585 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401512746	RS378B P19 940 PSU-E WB M70 PRO	4000 K	92	134 lm/W	2,605 lm
911401513746	RS378B P12 927 PSD-E NB M70 PRO	2700 K	92	115 lm/W	1,475 lm
911401513846	RS378B P12 930 PSD-E NB M70 PRO	3000 K	92	124 lm/W	1,585 lm
911401513946	RS378B P12 940 PSD-E NB M70 PRO	4000 K	92	123 lm/W	1,575 lm
911401514046	RS378B P12 927 PSD-E MB M70 PRO	2700 K	92	114 lm/W	1,455 lm
911401514146	RS378B P12 930 PSD-E MB M70 PRO	3000 K	92	127 lm/W	1,625 lm
911401514246	RS378B P12 940 PSD-E MB M70 PRO	4000 K	92	129 lm/W	1,650 lm
911401514346	RS378B P12 927 PSD-E WB M70 PRO	2700 K	92	122 lm/W	1,560 lm
911401514446	RS378B P12 930 PSD-E WB M70 PRO	3000 K	92	129 lm/W	1,655 lm
911401514546	RS378B P12 940 PSD-E WB M70 PRO	4000 K	92	134 lm/W	1,710 lm
911401514646	RS378B P18 927 PSD-E NB M70 PRO	2700 K	92	113 lm/W	2,095 lm
911401514746	RS378B P18 930 PSD-E NB M70 PRO	3000 K	92	121 lm/W	2,245 lm
911401514846	RS378B P18 940 PSD-E NB M70 PRO	4000 K	92	126 lm/W	2,330 lm
911401514946	RS378B P18 927 PSD-E MB M70 PRO	2700 K	92	112 lm/W	2,065 lm
911401515046	RS378B P18 930 PSD-E MB M70 PRO	3000 K	92	124 lm/W	2,295 lm
911401515146	RS378B P18 940 PSD-E MB M70 PRO	4000 K	92	128 lm/W	2,365 lm
911401515246	RS378B P18 927 PSD-E WB M70 PRO	2700 K	92	121 lm/W	2,240 lm
911401515346	RS378B P18 930 PSD-E WB M70 PRO	3000 K	92	129 lm/W	2,385 lm
911401515446	RS378B P18 940 PSD-E WB M70 PRO	4000 K	92	129 lm/W	2,390 lm
911401515546	RS378B P20 927 PSD-E NB M70 PRO	2700 K	92	111 lm/W	2,270 lm
911401515646	RS378B P20 930 PSD-E NB M70 PRO	3000 K	92	117 lm/W	2,390 lm
911401515746	RS378B P20 940 PSD-E NB M70 PRO	4000 K	92	122 lm/W	2,510 lm
911401515846	RS378B P20 927 PSD-E MB M70 PRO	2700 K	92	110 lm/W	2,265 lm
911401515946	RS378B P20 930 PSD-E MB M70 PRO	3000 K	92	122 lm/W	2,505 lm
911401516046	RS378B P20 940 PSD-E MB M70 PRO	4000 K	92	126 lm/W	2,585 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401516146	RS378B P20 927 PSD-E WB M70 PRO	2700 K	92	119 lm/W	2,435 lm
911401516246	RS378B P20 930 PSD-E WB M70 PRO	3000 K	92	126 lm/W	2,585 lm
911401516346	RS378B P20 940 PSD-E WB M70 PRO	4000 K	92	127 lm/W	2,605 lm
911401518146	RS378B P12 930 PSU-E MB M70 WP PRO	3000 K	92	135 lm/W	1,625 lm
911401518246	RS378B P12 930 PSU-E WB M70 WP PRO	3000 K	92	138 lm/W	1,655 lm
911401518346	RS378B P17 930 PSU-E MB M70 WP PRO	3000 K	92	131 lm/W	2,295 lm
911401518446	RS378B P17 930 PSU-E WB M70 WP PRO	3000 K	92	136 lm/W	2,385 lm
911401518546	RS378B P19 930 PSU-E MB M70 WP PRO	3000 K	92	128 lm/W	2,505 lm
911401518646	RS378B P19 930 PSU-E WB M70 WP PRO	3000 K	92	133 lm/W	2,585 lm
911401520446	RS378B P13 PSD-TNW NB M70 PRO	Tunable White	90	83 lm/W	1,120 lm
911401520546	RS378B P13 PSD-TNW MB M70 PRO	Tunable White	90	82 lm/W	1,110 lm
911401520646	RS378B P13 PSD-TNW WB M70 PRO	Tunable White	90	82 lm/W	1,110 lm
911401520746	RS378B P19 PSD-TNW NB M70 PRO	Tunable White	90	81 lm/W	1,620 lm
911401520846	RS378B P19 PSD-TNW MB M70 PRO	Tunable White	90	80 lm/W	1,600 lm
911401520946	RS378B P19 PSD-TNW WB M70 PRO	Tunable White	90	80 lm/W	1,600 lm
911401521046	RS378B P22 PSD-TNW NB M70 PRO	Tunable White	90	81 lm/W	1,780 lm
911401521146	RS378B P22 PSD-TNW MB M70 PRO	Tunable White	90	80 lm/W	1,760 lm
911401521246	RS378B P22 PSD-TNW WB M70 PRO	Tunable White	90	80 lm/W	1,760 lm
911401512846	RS378B P27 927 PSU-E NB M70 PRO	2700 K	92	106 lm/W	2,905 lm
911401512946	RS378B P27 930 PSU-E NB M70 PRO	3000 K	92	112 lm/W	3,090 lm
911401513046	RS378B P27 940 PSU-E NB M70 PRO	4000 K	92	116 lm/W	3,185 lm
911401513146	RS378B P27 927 PSU-E MB M70 PRO	2700 K	92	109 lm/W	2,995 lm
911401513246	RS378B P27 930 PSU-E MB M70 PRO	3000 K	92	116 lm/W	3,185 lm
911401513346	RS378B P27 940 PSU-E MB M70 PRO	4000 K	92	119 lm/W	3,280 lm
911401513446	RS378B P27 927 PSU-E WB M70 PRO	2700 K	92	112 lm/W	3,090 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401513546	RS378B P27 930 PSU-E WB M70 PRO	3000 K	92	119 lm/W	3,285 lm
911401513646	RS378B P27 940 PSU-E WB M70 PRO	4000 K	92	123 lm/W	3,385 lm
911401516446	RS378B P27 927 PSD-E NB M70 PRO	2700 K	92	102 lm/W	2,750 lm
911401516546	RS378B P27 930 PSD-E NB M70 PRO	3000 K	92	108 lm/W	2,925 lm
911401516646	RS378B P27 940 PSD-E NB M70 PRO	4000 K	92	112 lm/W	3,015 lm
911401516746	RS378B P27 927 PSD-E MB M70 PRO	2700 K	92	105 lm/W	2,835 lm
911401516846	RS378B P27 930 PSD-E MB M70 PRO	3000 K	92	112 lm/W	3,015 lm
911401516946	RS378B P27 940 PSD-E MB M70 PRO	4000 K	92	115 lm/W	3,105 lm
911401517046	RS378B P27 927 PSD-E WB M70 PRO	2700 K	92	108 lm/W	2,925 lm
911401517146	RS378B P27 930 PSD-E WB M70 PRO	3000 K	92	115 lm/W	3,110 lm
911401517246	RS378B P27 940 PSD-E WB M70 PRO	4000 K	92	119 lm/W	3,205 lm
911401518746	RS378B P27 930 PSU-E MB M70 WP PRO	3000 K	92	116 lm/W	3,185 lm
911401518846	RS378B P27 930 PSU-E WB M70 WP PRO	3000 K	92	119 lm/W	3,285 lm
911401521346	RS378B P29 PSD-TNW NB M70 PRO	Tunable White	90	80 lm/W	2,240 lm
911401521446	RS378B P29 PSD-TNW MB M70 PRO	Tunable White	90	79 lm/W	2,210 lm
911401521546	RS378B P29 PSD-TNW WB M70 PRO	Tunable White	90	79 lm/W	2,210 lm
911401531546	SM378B S P8 930 PSU-E WB D100 G-TT PRO	3000 K	92	119 lm/W	930 lm
911401540046	SM378B S P22 PSD-TNW WB D100 G-TT PRO	Tunable White	90	79 lm/W	1,740 lm
911401503046	RS378B P12 927 PSU-E NB M55 PRO	2700 K	92	101 lm/W	1,270 lm
911401503146	RS378B P12 930 PSU-E NB M55 PRO	3000 K	92	106 lm/W	1,330 lm
911401503246	RS378B P12 940 PSU-E NB M55 PRO	4000 K	92	110 lm/W	1,390 lm
911401503346	RS378B P12 927 PSU-E MB M55 PRO	2700 K	92	105 lm/W	1,325 lm
911401503446	RS378B P12 930 PSU-E MB M55 PRO	3000 K	92	110 lm/W	1,390 lm
911401503546	RS378B P12 940 PSU-E MB M55 PRO	4000 K	92	116 lm/W	1,460 lm
911401503646	RS378B P12 927 PSU-E WB M55 PRO	2700 K	92	107 lm/W	1,350 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401503746	RS378B P12 930 PSU-E WB M55 PRO	3000 K	92	115 lm/W	1,450 lm
911401503846	RS378B P12 940 PSU-E WB M55 PRO	4000 K	92	118 lm/W	1,490 lm
911401503946	RS378B P14 927 PSU-E NB M55 PRO	2700 K	92	96 lm/W	1,390 lm
911401504046	RS378B P14 930 PSU-E NB M55 PRO	3000 K	92	102 lm/W	1,480 lm
911401504146	RS378B P14 940 PSU-E NB M55 PRO	4000 K	92	105 lm/W	1,525 lm
911401504246	RS378B P14 927 PSU-E MB M55 PRO	2700 K	92	103 lm/W	1,490 lm
911401504346	RS378B P14 930 PSU-E MB M55 PRO	3000 K	92	109 lm/W	1,585 lm
911401504446	RS378B P14 940 PSU-E MB M55 PRO	4000 K	92	113 lm/W	1,635 lm
911401504546	RS378B P14 927 PSU-E WB M55 PRO	2700 K	92	104 lm/W	1,505 lm
911401504646	RS378B P14 930 PSU-E WB M55 PRO	3000 K	92	110 lm/W	1,600 lm
911401504746	RS378B P14 940 PSU-E WB M55 PRO	4000 K	92	114 lm/W	1,650 lm
911401506946	RS378B P13 927 PSD-E NB M55 PRO	2700 K	92	94 lm/W	1,270 lm
911401507046	RS378B P13 930 PSD-E NB M55 PRO	3000 K	92	99 lm/W	1,330 lm
911401507146	RS378B P13 940 PSD-E NB M55 PRO	4000 K	92	103 lm/W	1,390 lm
911401507246	RS378B P13 927 PSD-E MB M55 PRO	2700 K	92	98 lm/W	1,325 lm
911401507346	RS378B P13 930 PSD-E MB M55 PRO	3000 K	92	103 lm/W	1,390 lm
911401507446	RS378B P13 940 PSD-E MB M55 PRO	4000 K	92	108 lm/W	1,460 lm
911401507546	RS378B P13 927 PSD-E WB M55 PRO	2700 K	92	100 lm/W	1,350 lm
911401507646	RS378B P13 930 PSD-E WB M55 PRO	3000 K	92	107 lm/W	1,450 lm
911401507746	RS378B P13 940 PSD-E WB M55 PRO	4000 K	92	110 lm/W	1,490 lm
911401507846	RS378B P15 927 PSD-E NB M55 PRO	2700 K	92	90 lm/W	1,390 lm
911401507946	RS378B P15 930 PSD-E NB M55 PRO	3000 K	92	95 lm/W	1,480 lm
911401508046	RS378B P15 940 PSD-E NB M55 PRO	4000 K	92	98 lm/W	1,525 lm
911401508146	RS378B P15 927 PSD-E MB M55 PRO	2700 K	92	96 lm/W	1,490 lm
911401508246	RS378B P15 930 PSD-E MB M55 PRO	3000 K	92	102 lm/W	1,585 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401508346	RS378B P15 940 PSD-E MB M55 PRO	4000 K	92	105 lm/W	1,635 lm
911401508446	RS378B P15 927 PSD-E WB M55 PRO	2700 K	92	97 lm/W	1,505 lm
911401508546	RS378B P15 930 PSD-E WB M55 PRO	3000 K	92	103 lm/W	1,600 lm
911401508646	RS378B P15 940 PSD-E WB M55 PRO	4000 K	92	106 lm/W	1,650 lm
911401509746	RS378B P12 930 PSU-E MB M55 WP PRO	3000 K	92	110 lm/W	1,390 lm
911401509846	RS378B P12 930 PSU-E WB M55 WP PRO	3000 K	92	115 lm/W	1,450 lm
911401509946	RS378B P14 930 PSU-E MB M55 WP PRO	3000 K	92	109 lm/W	1,585 lm
911401510046	RS378B P14 930 PSU-E WB M55 WP PRO	3000 K	92	110 lm/W	1,600 lm
911401519546	RS378B P13 PSD-TNW NB M55 PRO	Tunable White	90	71 lm/W	960 lm
911401519646	RS378B P13 PSD-TNW MB M55 PRO	Tunable White	90	73 lm/W	990 lm
911401519746	RS378B P13 PSD-TNW WB M55 PRO	Tunable White	90	76 lm/W	1,030 lm
911401519846	RS378B P15 PSD-TNW NB M55 PRO	Tunable White	90	71 lm/W	1,070 lm
911401519946	RS378B P15 PSD-TNW MB M55 PRO	Tunable White	90	73 lm/W	1,100 lm
911401520046	RS378B P15 PSD-TNW WB M55 PRO	Tunable White	90	76 lm/W	1,140 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
911401528746	SM378B R P14 940 PSD-E WB D100 G-TT PRO	14.5 W	911401597545	RS378B P6 927 PSU-E MB M43 PRO	5.9 W
911401528846	SM378X R P8 930 WIA MB D100 G-TT PRO	8.2 W	911401597645	RS378B P6 930 PSU-E MB M43 PRO	5.9 W
911401528946	SM378X R P8 930 WIA WB D100 G-TT PRO	8.2 W	911401597745	RS378B P6 940 PSU-E MB M43 PRO	5.9 W
911401500046	RS378B P7 930 PSD-E WB M43 PRO	7.4 W	911401597845	RS378B P6 927 PSU-E WB M43 PRO	5.9 W
911401500146	RS378B P7 940 PSD-E WB M43 PRO	7.4 W	911401597945	RS378B P6 930 PSU-E WB M43 PRO	5.9 W
911401500246	RS378B P6 930 PSU-E MB M43 WP PRO	5.9 W	911401598045	RS378B P6 940 PSU-E WB M43 PRO	5.9 W
911401500346	RS378B P6 930 PSU-E WB M43 WP PRO	5.9 W	911401598145	RS378B P8 927 PSU-E NB M43 PRO	8 W
911401500446	RS378B P8 930 PSU-E MB M43 WP PRO	8 W	911401598245	RS378B P8 930 PSU-E NB M43 PRO	8 W
911401500546	RS378B P8 930 PSU-E WB M43 WP PRO	8 W	911401598345	RS378B P8 940 PSU-E NB M43 PRO	8 W
911401520146	RS378B P7 PSD-TNW NB M43 PRO	7.5 W	911401598445	RS378B P8 927 PSU-E MB M43 PRO	8 W
911401520246	RS378B P7 PSD-TNW MB M43 PRO	7.5 W	911401598545	RS378B P8 930 PSU-E MB M43 PRO	8 W
911401520346	RS378B P7 PSD-TNW WB M43 PRO	7.5 W	911401598645	RS378B P8 940 PSU-E MB M43 PRO	8 W
911401596945	RS378B P6 927 PSU-E SNB M43 PRO	6.5 W	911401598745	RS378B P8 927 PSU-E WB M43 PRO	8 W
911401597045	RS378B P6 930 PSU-E SNB M43 PRO	6.5 W	911401598845	RS378B P8 930 PSU-E WB M43 PRO	8 W
911401597145	RS378B P6 940 PSU-E SNB M43 PRO	6.5 W	911401598945	RS378B P8 940 PSU-E WB M43 PRO	8 W
911401597245	RS378B P6 927 PSU-E NB M43 PRO	5.9 W	911401599045	RS378B P7 927 PSD-E SNB M43 PRO	7.5 W
911401597345	RS378B P6 930 PSU-E NB M43 PRO	5.9 W	911401599145	RS378B P7 930 PSD-E SNB M43 PRO	7.5 W
911401597445	RS378B P6 940 PSU-E NB M43 PRO	5.9 W	911401599245	RS378B P7 940 PSD-E SNB M43 PRO	7.5 W

# GreenSpace Flex Luna

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
911401599345	RS378B P7 927 PSD-E NB M43 PRO	7.4 W	911401509346	RS378B P7 930 PSU-E MB M55 WP PRO	7.1 W
911401599445	RS378B P7 930 PSD-E NB M43 PRO	7.4 W	911401509446	RS378B P7 930 PSU-E WB M55 WP PRO	7.1 W
911401599545	RS378B P7 940 PSD-E NB M43 PRO	7.4 W	911401509546	RS378B P9 930 PSU-E MB M55 WP PRO	9 W
911401599645	RS378B P7 927 PSD-E MB M43 PRO	7.4 W	911401509646	RS378B P9 930 PSU-E WB M55 WP PRO	9 W
911401599745	RS378B P7 930 PSD-E MB M43 PRO	7.4 W	911401518946	RS378B P7 PSD-TNW NB M55 PRO	7.1 W
911401599845	RS378B P7 940 PSD-E MB M43 PRO	7.4 W	911401519046	RS378B P7 PSD-TNW MB M55 PRO	7.1 W
911401599945	RS378B P7 927 PSD-E WB M43 PRO	7.4 W	911401519146	RS378B P7 PSD-TNW WB M55 PRO	7.1 W
911401500646	RS378B P7 927 PSU-E SNB M55 PRO	7.2 W	911401519246	RS378B P9 PSD-TNW NB M55 PRO	9 W
911401500746	RS378B P7 930 PSU-E SNB M55 PRO	7.2 W	911401519346	RS378B P9 PSD-TNW MB M55 PRO	9 W
911401500846	RS378B P7 940 PSU-E SNB M55 PRO	7.2 W	911401519446	RS378B P9 PSD-TNW WB M55 PRO	9 W
911401500946	RS378B P7 927 PSU-E NB M55 PRO	7.1 W	911401595145	RS378B P3 927 PSU-E MB D35 G-TT PRO	3.1 W
911401501046	RS378B P7 930 PSU-E NB M55 PRO	7.1 W	911401595245	RS378B P3 930 PSU-E MB D35 G-TT PRO	3.1 W
911401501146	RS378B P7 940 PSU-E NB M55 PRO	7.1 W	911401595345	RS378B P3 940 PSU-E MB D35 G-TT PRO	3.1 W
911401501246	RS378B P7 927 PSU-E MB M55 PRO	7.1 W	911401595445	RS378B P3 927 PSU-E WB D35 G-TT PRO	3.1 W
911401501346	RS378B P7 930 PSU-E MB M55 PRO	7.1 W	911401595545	RS378B P3 930 PSU-E WB D35 G-TT PRO	3.1 W
911401501446	RS378B P7 940 PSU-E MB M55 PRO	7.1 W	911401595645	RS378B P3 940 PSU-E WB D35 G-TT PRO	3.1 W
911401501546	RS378B P7 927 PSU-E WB M55 PRO	7.1 W	911401595745	RS378B P5 927 PSU-E MB D35 G-TT PRO	4.7 W
911401501646	RS378B P7 930 PSU-E WB M55 PRO	7.1 W	911401595845	RS378B P5 930 PSU-E MB D35 G-TT PRO	4.7 W
911401501746	RS378B P7 940 PSU-E WB M55 PRO	7.1 W	911401595945	RS378B P5 940 PSU-E MB D35 G-TT PRO	4.7 W
911401501846	RS378B P8 927 PSU-E SNB M55 PRO	8 W	911401596045	RS378B P5 927 PSU-E WB D35 G-TT PRO	4.7 W
911401501946	RS378B P8 930 PSU-E SNB M55 PRO	8 W	911401596145	RS378B P5 930 PSU-E WB D35 G-TT PRO	4.7 W
911401502046	RS378B P8 940 PSU-E SNB M55 PRO	8 W	911401596245	RS378B P5 940 PSU-E WB D35 G-TT PRO	4.7 W
911401502146	RS378B P9 927 PSU-E NB M55 PRO	9 W	911401596345	RS378B P5 927 PSD-E MB D35 G-TT PRO	5.9 W
911401502246	RS378B P9 930 PSU-E NB M55 PRO	9 W	911401596445	RS378B P5 930 PSD-E MB D35 G-TT PRO	5.3 W
911401502346	RS378B P9 940 PSU-E NB M55 PRO	9 W	911401596545	RS378B P5 940 PSD-E MB D35 G-TT PRO	5.3 W
911401502446	RS378B P9 927 PSU-E MB M55 PRO	9 W	911401596645	RS378B P5 927 PSD-E WB D35 G-TT PRO	5.3 W
911401502546	RS378B P9 930 PSU-E MB M55 PRO	9 W	911401596745	RS378B P5 930 PSD-E WB D35 G-TT PRO	5.3 W
911401502646	RS378B P9 940 PSU-E MB M55 PRO	9 W	911401596845	RS378B P5 940 PSD-E WB D35 G-TT PRO	5.3 W
911401502746	RS378B P9 927 PSU-E WB M55 PRO	9 W	911401510146	RS378B P12 927 PSU-E NB M70 PRO	12 W
911401502846	RS378B P9 930 PSU-E WB M55 PRO	9 W	911401510246	RS378B P12 930 PSU-E NB M70 PRO	12 W
911401502946	RS378B P9 940 PSU-E WB M55 PRO	9 W	911401510346	RS378B P12 940 PSU-E NB M70 PRO	12 W
911401504846	RS378B P7 927 PSD-E SNB M55 PRO	7.5 W	911401510446	RS378B P12 927 PSU-E MB M70 PRO	12 W
911401504946	RS378B P7 930 PSD-E SNB M55 PRO	7.5 W	911401510546	RS378B P12 930 PSU-E MB M70 PRO	12 W
911401505046	RS378B P7 940 PSD-E SNB M55 PRO	7.5 W	911401510646	RS378B P12 940 PSU-E MB M70 PRO	12 W
911401505146	RS378B P7 927 PSD-E NB M55 PRO	7.3 W	911401510746	RS378B P12 927 PSU-E WB M70 PRO	12 W
911401505246	RS378B P7 930 PSD-E NB M55 PRO	7.3 W	911401510846	RS378B P12 930 PSU-E WB M70 PRO	12 W
911401505346	RS378B P7 940 PSD-E NB M55 PRO	7.3 W	911401510946	RS378B P12 940 PSU-E WB M70 PRO	12 W
911401505446	RS378B P7 927 PSD-E MB M55 PRO	7.3 W	911401511046	RS378B P17 927 PSU-E NB M70 PRO	17.5 W
911401505546	RS378B P7 930 PSD-E MB M55 PRO	7.3 W	911401511146	RS378B P17 930 PSU-E NB M70 PRO	17.5 W
911401505646	RS378B P7 940 PSD-E MB M55 PRO	7.3 W	911401511246	RS378B P17 940 PSU-E NB M70 PRO	17.5 W
911401505746	RS378B P7 927 PSD-E WB M55 PRO	7.3 W	911401511346	RS378B P17 927 PSU-E MB M70 PRO	17.5 W
911401505846	RS378B P7 930 PSD-E WB M55 PRO	7.3 W	911401511446	RS378B P17 930 PSU-E MB M70 PRO	17.5 W
911401505946	RS378B P7 940 PSD-E WB M55 PRO	7.3 W	911401511546	RS378B P17 940 PSU-E MB M70 PRO	17.5 W
911401506046	RS378B P9 927 PSD-E NB M55 PRO	9.5 W	911401511646	RS378B P17 927 PSU-E WB M70 PRO	17.5 W
911401506146	RS378B P9 930 PSD-E NB M55 PRO	9.5 W	911401511746	RS378B P17 930 PSU-E WB M70 PRO	17.5 W
911401506246	RS378B P9 940 PSD-E NB M55 PRO	9.5 W	911401511846	RS378B P17 940 PSU-E WB M70 PRO	17.5 W
911401506346	RS378B P9 927 PSD-E MB M55 PRO	9.5 W	911401511946	RS378B P19 927 PSU-E NB M70 PRO	19.5 W
911401506446	RS378B P9 930 PSD-E MB M55 PRO	9.5 W	911401512046	RS378B P19 930 PSU-E NB M70 PRO	19.5 W
911401506546	RS378B P9 940 PSD-E MB M55 PRO	9.5 W	911401512146	RS378B P19 940 PSU-E NB M70 PRO	19.5 W
911401506646	RS378B P9 927 PSD-E WB M55 PRO	9.5 W	911401512246	RS378B P19 927 PSU-E MB M70 PRO	19.5 W
911401506746	RS378B P9 930 PSD-E WB M55 PRO	9.5 W	911401512346	RS378B P19 930 PSU-E MB M70 PRO	19.5 W
911401506846	RS378B P9 940 PSD-E WB M55 PRO	9.5 W	911401512446	RS378B P19 940 PSU-E MB M70 PRO	19.5 W

# GreenSpace Flex Luna

Order Code	Full Product Name	Power Consumption
911401512546	RS378B P19 927 PSU-E WB M70 PRO	19.5 W
911401512646	RS378B P19 930 PSU-E WB M70 PRO	19.5 W
911401512746	RS378B P19 940 PSU-E WB M70 PRO	19.5 W
911401513746	RS378B P12 927 PSD-E NB M70 PRO	12.8 W
911401513846	RS378B P12 930 PSD-E NB M70 PRO	12.8 W
911401513946	RS378B P12 940 PSD-E NB M70 PRO	12.8 W
911401514046	RS378B P12 927 PSD-E MB M70 PRO	12.8 W
911401514146	RS378B P12 930 PSD-E MB M70 PRO	12.8 W
911401514246	RS378B P12 940 PSD-E MB M70 PRO	12.8 W
911401514346	RS378B P12 927 PSD-E WB M70 PRO	12.8 W
911401514446	RS378B P12 930 PSD-E WB M70 PRO	12.8 W
911401514546	RS378B P12 940 PSD-E WB M70 PRO	12.8 W
911401514646	RS378B P18 927 PSD-E NB M70 PRO	18.5 W
911401514746	RS378B P18 930 PSD-E NB M70 PRO	18.5 W
911401514846	RS378B P18 940 PSD-E NB M70 PRO	18.5 W
911401514946	RS378B P18 927 PSD-E MB M70 PRO	18.5 W
911401515046	RS378B P18 930 PSD-E MB M70 PRO	18.5 W
911401515146	RS378B P18 940 PSD-E MB M70 PRO	18.5 W
911401515246	RS378B P18 927 PSD-E WB M70 PRO	18.5 W
911401515346	RS378B P18 930 PSD-E WB M70 PRO	18.5 W
911401515446	RS378B P18 940 PSD-E WB M70 PRO	18.5 W
911401515546	RS378B P20 927 PSD-E NB M70 PRO	20.5 W
911401515646	RS378B P20 930 PSD-E NB M70 PRO	20.5 W
911401515746	RS378B P20 940 PSD-E NB M70 PRO	20.5 W
911401515846	RS378B P20 927 PSD-E MB M70 PRO	20.5 W
911401515946	RS378B P20 930 PSD-E MB M70 PRO	20.5 W
911401516046	RS378B P20 940 PSD-E MB M70 PRO	20.5 W
911401516146	RS378B P20 927 PSD-E WB M70 PRO	20.5 W
911401516246	RS378B P20 930 PSD-E WB M70 PRO	20.5 W
911401516346	RS378B P20 940 PSD-E WB M70 PRO	20.5 W
911401518146	RS378B P12 930 PSU-E MB M70 WP PRO	12 W
911401518246	RS378B P12 930 PSU-E WB M70 WP PRO	12 W
911401518346	RS378B P17 930 PSU-E MB M70 WP PRO	17.5 W
911401518446	RS378B P17 930 PSU-E WB M70 WP PRO	17.5 W
911401518546	RS378B P19 930 PSU-E MB M70 WP PRO	19.5 W
911401518646	RS378B P19 930 PSU-E WB M70 WP PRO	19.5 W
911401520446	RS378B P13 PSD-TNW NB M70 PRO	13.5 W
911401520546	RS378B P13 PSD-TNW MB M70 PRO	13.5 W
911401520646	RS378B P13 PSD-TNW WB M70 PRO	13.5 W
911401520746	RS378B P19 PSD-TNW NB M70 PRO	20 W
911401520846	RS378B P19 PSD-TNW MB M70 PRO	20 W
911401520946	RS378B P19 PSD-TNW WB M70 PRO	20 W
911401521046	RS378B P22 PSD-TNW NB M70 PRO	22 W
911401521146	RS378B P22 PSD-TNW MB M70 PRO	22 W
911401521246	RS378B P22 PSD-TNW WB M70 PRO	22 W
911401512846	RS378B P27 927 PSU-E NB M70 PRO	27.5 W
911401512946	RS378B P27 930 PSU-E NB M70 PRO	27.5 W
911401513046	RS378B P27 940 PSU-E NB M70 PRO	27.5 W
911401513146	RS378B P27 927 PSU-E MB M70 PRO	27.5 W
911401513246	RS378B P27 930 PSU-E MB M70 PRO	27.5 W
911401513346	RS378B P27 940 PSU-E MB M70 PRO	27.5 W
911401513446	RS378B P27 927 PSU-E WB M70 PRO	27.5 W

Order Code	Full Product Name	Power Consumption
911401513546	RS378B P27 930 PSU-E WB M70 PRO	27.5 W
911401513646	RS378B P27 940 PSU-E WB M70 PRO	27.5 W
911401516446	RS378B P27 927 PSD-E NB M70 PRO	27 W
911401516546	RS378B P27 930 PSD-E NB M70 PRO	27 W
911401516646	RS378B P27 940 PSD-E NB M70 PRO	27 W
911401516746	RS378B P27 927 PSD-E MB M70 PRO	27 W
911401516846	RS378B P27 930 PSD-E MB M70 PRO	27 W
911401516946	RS378B P27 940 PSD-E MB M70 PRO	27 W
911401517046	RS378B P27 927 PSD-E WB M70 PRO	27 W
911401517146	RS378B P27 930 PSD-E WB M70 PRO	27 W
911401517246	RS378B P27 940 PSD-E WB M70 PRO	27 W
911401518746	RS378B P27 930 PSU-E MB M70 WP PRO	27.5 W
911401518846	RS378B P27 930 PSU-E WB M70 WP PRO	27.5 W
911401521346	RS378B P29 PSD-TNW NB M70 PRO	28 W
911401521446	RS378B P29 PSD-TNW MB M70 PRO	28 W
911401521546	RS378B P29 PSD-TNW WB M70 PRO	28 W
911401531546	SM378B S P8 930 PSU-E WB D100 G-TT PRO	7.8 W
911401540046	SM378B S P22 PSD-TNW WB D100 G-TT PRO	22 W
911401503046	RS378B P12 927 PSU-E NB M55 PRO	12.6 W
911401503146	RS378B P12 930 PSU-E NB M55 PRO	12.6 W
911401503246	RS378B P12 940 PSU-E NB M55 PRO	12.6 W
911401503346	RS378B P12 927 PSU-E MB M55 PRO	12.6 W
911401503446	RS378B P12 930 PSU-E MB M55 PRO	12.6 W
911401503546	RS378B P12 940 PSU-E MB M55 PRO	12.6 W
911401503646	RS378B P12 927 PSU-E WB M55 PRO	12.6 W
911401503746	RS378B P12 930 PSU-E WB M55 PRO	12.6 W
911401503846	RS378B P12 940 PSU-E WB M55 PRO	12.6 W
911401503946	RS378B P14 927 PSU-E NB M55 PRO	14.5 W
911401504046	RS378B P14 930 PSU-E NB M55 PRO	14.5 W
911401504146	RS378B P14 940 PSU-E NB M55 PRO	14.5 W
911401504246	RS378B P14 927 PSU-E MB M55 PRO	14.5 W
911401504346	RS378B P14 930 PSU-E MB M55 PRO	14.5 W
911401504446	RS378B P14 940 PSU-E MB M55 PRO	14.5 W
911401504546	RS378B P14 927 PSU-E WB M55 PRO	14.5 W
911401504646	RS378B P14 930 PSU-E WB M55 PRO	14.5 W
911401504746	RS378B P14 940 PSU-E WB M55 PRO	14.5 W
911401506946	RS378B P13 927 PSD-E NB M55 PRO	13.5 W
911401507046	RS378B P13 930 PSD-E NB M55 PRO	13.5 W
911401507146	RS378B P13 940 PSD-E NB M55 PRO	13.5 W
911401507246	RS378B P13 927 PSD-E MB M55 PRO	13.5 W
911401507346	RS378B P13 930 PSD-E MB M55 PRO	13.5 W
911401507446	RS378B P13 940 PSD-E MB M55 PRO	13.5 W
911401507546	RS378B P13 927 PSD-E WB M55 PRO	13.5 W
911401507646	RS378B P13 930 PSD-E WB M55 PRO	13.5 W
911401507746	RS378B P13 940 PSD-E WB M55 PRO	13.5 W
911401507846	RS378B P15 927 PSD-E NB M55 PRO	15.5 W
911401507946	RS378B P15 930 PSD-E NB M55 PRO	15.5 W
911401508046	RS378B P15 940 PSD-E NB M55 PRO	15.5 W
911401508146	RS378B P15 927 PSD-E MB M55 PRO	15.5 W
911401508246	RS378B P15 930 PSD-E MB M55 PRO	15.5 W
911401508346	RS378B P15 940 PSD-E MB M55 PRO	15.5 W
911401508446	RS378B P15 927 PSD-E WB M55 PRO	15.5 W

# GreenSpace Flex Luna

Order Code	Full Product Name	Power Consumption
911401508546	RS378B P15 930 PSD-E WB M55 PRO	15.5 W
911401508646	RS378B P15 940 PSD-E WB M55 PRO	15.5 W
911401509746	RS378B P12 930 PSU-E MB M55 WP PRO	12.6 W
911401509846	RS378B P12 930 PSU-E WB M55 WP PRO	12.6 W
911401509946	RS378B P14 930 PSU-E MB M55 WP PRO	14.5 W
911401510046	RS378B P14 930 PSU-E WB M55 WP PRO	14.5 W

Order Code	Full Product Name	Power Consumption
911401519546	RS378B P13 PSD-TNW NB M55 PRO	13.5 W
911401519646	RS378B P13 PSD-TNW MB M55 PRO	13.5 W
911401519746	RS378B P13 PSD-TNW WB M55 PRO	13.5 W
911401519846	RS378B P15 PSD-TNW NB M55 PRO	15 W
911401519946	RS378B P15 PSD-TNW MB M55 PRO	15 W
911401520046	RS378B P15 PSD-TNW WB M55 PRO	15 W

## Controls and Dimming

Order Code	Full Product Name	Dimmable
911401528746	SM378B R P14 940 PSD-E WB D100 G-TT PRO	DALI
911401528846	SM378X R P8 930 WIA MB D100 G-TT PRO	Wireless Dim
911401528946	SM378X R P8 930 WIA WB D100 G-TT PRO	Wireless Dim
911401500046	RS378B P7 930 PSD-E WB M43 PRO	DALI
911401500146	RS378B P7 940 PSD-E WB M43 PRO	DALI
911401500246	RS378B P6 930 PSU-E MB M43 WP PRO	-
911401500346	RS378B P6 930 PSU-E WB M43 WP PRO	-
911401500446	RS378B P8 930 PSU-E MB M43 WP PRO	-
911401500546	RS378B P8 930 PSU-E WB M43 WP PRO	-
911401520146	RS378B P7 PSD-TNW NB M43 PRO	DALI
911401520246	RS378B P7 PSD-TNW MB M43 PRO	DALI
911401520346	RS378B P7 PSD-TNW WB M43 PRO	DALI
911401596945	RS378B P6 927 PSU-E SNB M43 PRO	-
911401597045	RS378B P6 930 PSU-E SNB M43 PRO	-
911401597145	RS378B P6 940 PSU-E SNB M43 PRO	-
911401597245	RS378B P6 927 PSU-E NB M43 PRO	-
911401597345	RS378B P6 930 PSU-E NB M43 PRO	-
911401597445	RS378B P6 940 PSU-E NB M43 PRO	-
911401597545	RS378B P6 927 PSU-E MB M43 PRO	-
911401597645	RS378B P6 930 PSU-E MB M43 PRO	-
911401597745	RS378B P6 940 PSU-E MB M43 PRO	-
911401597845	RS378B P6 927 PSU-E WB M43 PRO	-
911401597945	RS378B P6 930 PSU-E WB M43 PRO	-
911401598045	RS378B P6 940 PSU-E WB M43 PRO	-
911401598145	RS378B P8 927 PSU-E NB M43 PRO	-
911401598245	RS378B P8 930 PSU-E NB M43 PRO	-
911401598345	RS378B P8 940 PSU-E NB M43 PRO	-
911401598445	RS378B P8 927 PSU-E MB M43 PRO	-
911401598545	RS378B P8 930 PSU-E MB M43 PRO	-
911401598645	RS378B P8 940 PSU-E MB M43 PRO	-
911401598745	RS378B P8 927 PSU-E WB M43 PRO	-
911401598845	RS378B P8 930 PSU-E WB M43 PRO	-
911401598945	RS378B P8 940 PSU-E WB M43 PRO	-
911401599045	RS378B P7 927 PSD-E SNB M43 PRO	DALI
911401599145	RS378B P7 930 PSD-E SNB M43 PRO	DALI
911401599245	RS378B P7 940 PSD-E SNB M43 PRO	DALI
911401599345	RS378B P7 927 PSD-E NB M43 PRO	DALI
911401599445	RS378B P7 930 PSD-E NB M43 PRO	DALI
911401599545	RS378B P7 940 PSD-E NB M43 PRO	DALI
911401599645	RS378B P7 927 PSD-E MB M43 PRO	DALI
911401599745	RS378B P7 930 PSD-E MB M43 PRO	DALI
911401599845	RS378B P7 940 PSD-E MB M43 PRO	DALI

Order Code	Full Product Name	Dimmable
911401599945	RS378B P7 927 PSD-E WB M43 PRO	DALI
911401500646	RS378B P7 927 PSU-E SNB M55 PRO	-
911401500746	RS378B P7 930 PSU-E SNB M55 PRO	-
911401500846	RS378B P7 940 PSU-E SNB M55 PRO	-
911401500946	RS378B P7 927 PSU-E NB M55 PRO	-
911401501046	RS378B P7 930 PSU-E NB M55 PRO	-
911401501146	RS378B P7 940 PSU-E NB M55 PRO	-
911401501246	RS378B P7 927 PSU-E MB M55 PRO	-
911401501346	RS378B P7 930 PSU-E MB M55 PRO	-
911401501446	RS378B P7 940 PSU-E MB M55 PRO	-
911401501546	RS378B P7 927 PSU-E WB M55 PRO	-
911401501646	RS378B P7 930 PSU-E WB M55 PRO	-
911401501746	RS378B P7 940 PSU-E WB M55 PRO	-
911401501846	RS378B P8 927 PSU-E SNB M55 PRO	-
911401501946	RS378B P8 930 PSU-E SNB M55 PRO	-
911401502046	RS378B P8 940 PSU-E SNB M55 PRO	-
911401502146	RS378B P9 927 PSU-E NB M55 PRO	-
911401502246	RS378B P9 930 PSU-E NB M55 PRO	-
911401502346	RS378B P9 940 PSU-E NB M55 PRO	-
911401502446	RS378B P9 927 PSU-E MB M55 PRO	-
911401502546	RS378B P9 930 PSU-E MB M55 PRO	-
911401502646	RS378B P9 940 PSU-E MB M55 PRO	-
911401502746	RS378B P9 927 PSU-E WB M55 PRO	-
911401502846	RS378B P9 930 PSU-E WB M55 PRO	-
911401502946	RS378B P9 940 PSU-E WB M55 PRO	-
911401504846	RS378B P7 927 PSD-E SNB M55 PRO	DALI
911401504946	RS378B P7 930 PSD-E SNB M55 PRO	DALI
911401505046	RS378B P7 940 PSD-E SNB M55 PRO	DALI
911401505146	RS378B P7 927 PSD-E NB M55 PRO	DALI
911401505246	RS378B P7 930 PSD-E NB M55 PRO	DALI
911401505346	RS378B P7 940 PSD-E NB M55 PRO	DALI
911401505446	RS378B P7 927 PSD-E MB M55 PRO	DALI
911401505546	RS378B P7 930 PSD-E MB M55 PRO	DALI
911401505646	RS378B P7 940 PSD-E MB M55 PRO	DALI
911401505746	RS378B P7 927 PSD-E WB M55 PRO	DALI
911401505846	RS378B P7 930 PSD-E WB M55 PRO	DALI
911401505946	RS378B P7 940 PSD-E WB M55 PRO	DALI
911401506046	RS378B P9 927 PSD-E NB M55 PRO	DALI
911401506146	RS378B P9 930 PSD-E NB M55 PRO	DALI
911401506246	RS378B P9 940 PSD-E NB M55 PRO	DALI
911401506346	RS378B P9 927 PSD-E MB M55 PRO	DALI
911401506446	RS378B P9 930 PSD-E MB M55 PRO	DALI

# GreenSpace Flex Luna

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
911401506546	RS378B P9 940 PSD-E MB M55 PRO	DALI	911401512146	RS378B P19 940 PSU-E NB M70 PRO	-
911401506646	RS378B P9 927 PSD-E WB M55 PRO	DALI	911401512246	RS378B P19 927 PSU-E MB M70 PRO	-
911401506746	RS378B P9 930 PSD-E WB M55 PRO	DALI	911401512346	RS378B P19 930 PSU-E MB M70 PRO	-
911401506846	RS378B P9 940 PSD-E WB M55 PRO	DALI	911401512446	RS378B P19 940 PSU-E MB M70 PRO	-
911401509346	RS378B P7 930 PSU-E MB M55 WP PRO	-	911401512546	RS378B P19 927 PSU-E WB M70 PRO	-
911401509446	RS378B P7 930 PSU-E WB M55 WP PRO	-	911401512646	RS378B P19 930 PSU-E WB M70 PRO	-
911401509546	RS378B P9 930 PSU-E MB M55 WP PRO	-	911401512746	RS378B P19 940 PSU-E WB M70 PRO	-
911401509646	RS378B P9 930 PSU-E WB M55 WP PRO	-	911401513746	RS378B P12 927 PSD-E NB M70 PRO	DALI
911401518946	RS378B P7 PSD-TNW NB M55 PRO	DALI	911401513846	RS378B P12 930 PSD-E NB M70 PRO	DALI
911401519046	RS378B P7 PSD-TNW MB M55 PRO	DALI	911401513946	RS378B P12 940 PSD-E NB M70 PRO	DALI
911401519146	RS378B P7 PSD-TNW WB M55 PRO	DALI	911401514046	RS378B P12 927 PSD-E MB M70 PRO	DALI
911401519246	RS378B P9 PSD-TNW NB M55 PRO	DALI	911401514146	RS378B P12 930 PSD-E MB M70 PRO	DALI
911401519346	RS378B P9 PSD-TNW MB M55 PRO	DALI	911401514246	RS378B P12 940 PSD-E MB M70 PRO	DALI
911401519446	RS378B P9 PSD-TNW WB M55 PRO	DALI	911401514346	RS378B P12 927 PSD-E WB M70 PRO	DALI
911401595145	RS378B P3 927 PSU-E MB D35 G-TT PRO	-	911401514446	RS378B P12 930 PSD-E WB M70 PRO	DALI
911401595245	RS378B P3 930 PSU-E MB D35 G-TT PRO	-	911401514546	RS378B P12 940 PSD-E WB M70 PRO	DALI
911401595345	RS378B P3 940 PSU-E MB D35 G-TT PRO	-	911401514646	RS378B P18 927 PSD-E NB M70 PRO	DALI
911401595445	RS378B P3 927 PSU-E WB D35 G-TT PRO	-	911401514746	RS378B P18 930 PSD-E NB M70 PRO	DALI
911401595545	RS378B P3 930 PSU-E WB D35 G-TT PRO	-	911401514846	RS378B P18 940 PSD-E NB M70 PRO	DALI
911401595645	RS378B P3 940 PSU-E WB D35 G-TT PRO	-	911401514946	RS378B P18 927 PSD-E MB M70 PRO	DALI
911401595745	RS378B P5 927 PSU-E MB D35 G-TT PRO	-	911401515046	RS378B P18 930 PSD-E MB M70 PRO	DALI
911401595845	RS378B P5 930 PSU-E MB D35 G-TT PRO	-	911401515146	RS378B P18 940 PSD-E MB M70 PRO	DALI
911401595945	RS378B P5 940 PSU-E MB D35 G-TT PRO	-	911401515246	RS378B P18 927 PSD-E WB M70 PRO	DALI
911401596045	RS378B P5 927 PSU-E WB D35 G-TT PRO	-	911401515346	RS378B P18 930 PSD-E WB M70 PRO	DALI
911401596145	RS378B P5 930 PSU-E WB D35 G-TT PRO	-	911401515446	RS378B P18 940 PSD-E WB M70 PRO	DALI
911401596245	RS378B P5 940 PSU-E WB D35 G-TT PRO	-	911401515546	RS378B P20 927 PSD-E NB M70 PRO	DALI
911401596345	RS378B P5 927 PSD-E MB D35 G-TT PRO	DALI	911401515646	RS378B P20 930 PSD-E NB M70 PRO	DALI
911401596445	RS378B P5 930 PSD-E MB D35 G-TT PRO	DALI	911401515746	RS378B P20 940 PSD-E NB M70 PRO	DALI
911401596545	RS378B P5 940 PSD-E MB D35 G-TT PRO	DALI	911401515846	RS378B P20 927 PSD-E MB M70 PRO	DALI
911401596645	RS378B P5 927 PSD-E WB D35 G-TT PRO	DALI	911401515946	RS378B P20 930 PSD-E MB M70 PRO	DALI
911401596745	RS378B P5 930 PSD-E WB D35 G-TT PRO	DALI	911401516046	RS378B P20 940 PSD-E MB M70 PRO	DALI
911401596845	RS378B P5 940 PSD-E WB D35 G-TT PRO	DALI	911401516146	RS378B P20 927 PSD-E WB M70 PRO	DALI
911401510146	RS378B P12 927 PSU-E NB M70 PRO	-	911401516246	RS378B P20 930 PSD-E WB M70 PRO	DALI
911401510246	RS378B P12 930 PSU-E NB M70 PRO	-	911401516346	RS378B P20 940 PSD-E WB M70 PRO	DALI
911401510346	RS378B P12 940 PSU-E NB M70 PRO	-	911401518146	RS378B P12 930 PSU-E MB M70 WP PRO	-
911401510446	RS378B P12 927 PSU-E MB M70 PRO	-	911401518246	RS378B P12 930 PSU-E WB M70 WP PRO	-
911401510546	RS378B P12 930 PSU-E MB M70 PRO	-	911401518346	RS378B P17 930 PSU-E MB M70 WP PRO	-
911401510646	RS378B P12 940 PSU-E MB M70 PRO	-	911401518446	RS378B P17 930 PSU-E WB M70 WP PRO	-
911401510746	RS378B P12 927 PSU-E WB M70 PRO	-	911401518546	RS378B P19 930 PSU-E MB M70 WP PRO	-
911401510846	RS378B P12 930 PSU-E WB M70 PRO	-	911401518646	RS378B P19 930 PSU-E WB M70 WP PRO	-
911401510946	RS378B P12 940 PSU-E WB M70 PRO	-	911401520446	RS378B P13 PSD-TNW NB M70 PRO	DALI
911401511046	RS378B P17 927 PSU-E NB M70 PRO	-	911401520546	RS378B P13 PSD-TNW MB M70 PRO	DALI
911401511146	RS378B P17 930 PSU-E NB M70 PRO	-	911401520646	RS378B P13 PSD-TNW WB M70 PRO	DALI
911401511246	RS378B P17 940 PSU-E NB M70 PRO	-	911401520746	RS378B P19 PSD-TNW NB M70 PRO	DALI
911401511346	RS378B P17 927 PSU-E MB M70 PRO	-	911401520846	RS378B P19 PSD-TNW MB M70 PRO	DALI
911401511446	RS378B P17 930 PSU-E MB M70 PRO	-	911401520946	RS378B P19 PSD-TNW WB M70 PRO	DALI
911401511546	RS378B P17 940 PSU-E MB M70 PRO	-	911401521046	RS378B P22 PSD-TNW NB M70 PRO	DALI
911401511646	RS378B P17 927 PSU-E WB M70 PRO	-	911401521146	RS378B P22 PSD-TNW MB M70 PRO	DALI
911401511746	RS378B P17 930 PSU-E WB M70 PRO	-	911401521246	RS378B P22 PSD-TNW WB M70 PRO	DALI
911401511846	RS378B P17 940 PSU-E WB M70 PRO	-	911401512846	RS378B P27 927 PSU-E NB M70 PRO	-
911401511946	RS378B P19 927 PSU-E NB M70 PRO	-	911401512946	RS378B P27 930 PSU-E NB M70 PRO	-
911401512046	RS378B P19 930 PSU-E NB M70 PRO	-	911401513046	RS378B P27 940 PSU-E NB M70 PRO	-

# GreenSpace Flex Luna

Order Code	Full Product Name	Dimmable
911401513146	RS378B P27 927 PSU-E MB M70 PRO	-
911401513246	RS378B P27 930 PSU-E MB M70 PRO	-
911401513346	RS378B P27 940 PSU-E MB M70 PRO	-
911401513446	RS378B P27 927 PSU-E WB M70 PRO	-
911401513546	RS378B P27 930 PSU-E WB M70 PRO	-
911401513646	RS378B P27 940 PSU-E WB M70 PRO	-
911401516446	RS378B P27 927 PSD-E NB M70 PRO	DALI
911401516546	RS378B P27 930 PSD-E NB M70 PRO	DALI
911401516646	RS378B P27 940 PSD-E NB M70 PRO	DALI
911401516746	RS378B P27 927 PSD-E MB M70 PRO	DALI
911401516846	RS378B P27 930 PSD-E MB M70 PRO	DALI
911401516946	RS378B P27 940 PSD-E MB M70 PRO	DALI
911401517046	RS378B P27 927 PSD-E WB M70 PRO	DALI
911401517146	RS378B P27 930 PSD-E WB M70 PRO	DALI
911401517246	RS378B P27 940 PSD-E WB M70 PRO	DALI
911401518746	RS378B P27 930 PSU-E MB M70 WP PRO	-
911401518846	RS378B P27 930 PSU-E WB M70 WP PRO	-
911401521346	RS378B P29 PSD-TNW NB M70 PRO	DALI
911401521446	RS378B P29 PSD-TNW MB M70 PRO	DALI
911401521546	RS378B P29 PSD-TNW WB M70 PRO	DALI
911401531546	SM378B S P8 930 PSU-E WB D100 G-TT PRO	-
911401540046	SM378B S P22 PSD-TNW WB D100 G-TT PRO	DALI
911401503046	RS378B P12 927 PSU-E NB M55 PRO	-
911401503146	RS378B P12 930 PSU-E NB M55 PRO	-
911401503246	RS378B P12 940 PSU-E NB M55 PRO	-
911401503346	RS378B P12 927 PSU-E MB M55 PRO	-
911401503446	RS378B P12 930 PSU-E MB M55 PRO	-
911401503546	RS378B P12 940 PSU-E MB M55 PRO	-
911401503646	RS378B P12 927 PSU-E WB M55 PRO	-
911401503746	RS378B P12 930 PSU-E WB M55 PRO	-
911401503846	RS378B P12 940 PSU-E WB M55 PRO	-
911401503946	RS378B P14 927 PSU-E NB M55 PRO	-
911401504046	RS378B P14 930 PSU-E NB M55 PRO	-
911401504146	RS378B P14 940 PSU-E NB M55 PRO	-

Order Code	Full Product Name	Dimmable
911401504246	RS378B P14 927 PSU-E MB M55 PRO	-
911401504346	RS378B P14 930 PSU-E MB M55 PRO	-
911401504446	RS378B P14 940 PSU-E MB M55 PRO	-
911401504546	RS378B P14 927 PSU-E WB M55 PRO	-
911401504646	RS378B P14 930 PSU-E WB M55 PRO	-
911401504746	RS378B P14 940 PSU-E WB M55 PRO	-
911401506946	RS378B P13 927 PSD-E NB M55 PRO	DALI
911401507046	RS378B P13 930 PSD-E NB M55 PRO	DALI
911401507146	RS378B P13 940 PSD-E NB M55 PRO	DALI
911401507246	RS378B P13 927 PSD-E MB M55 PRO	DALI
911401507346	RS378B P13 930 PSD-E MB M55 PRO	DALI
911401507446	RS378B P13 940 PSD-E MB M55 PRO	DALI
911401507546	RS378B P13 927 PSD-E WB M55 PRO	DALI
911401507646	RS378B P13 930 PSD-E WB M55 PRO	DALI
911401507746	RS378B P13 940 PSD-E WB M55 PRO	DALI
911401507846	RS378B P15 927 PSD-E NB M55 PRO	DALI
911401507946	RS378B P15 930 PSD-E NB M55 PRO	DALI
911401508046	RS378B P15 940 PSD-E NB M55 PRO	DALI
911401508146	RS378B P15 927 PSD-E MB M55 PRO	DALI
911401508246	RS378B P15 930 PSD-E MB M55 PRO	DALI
911401508346	RS378B P15 940 PSD-E MB M55 PRO	DALI
911401508446	RS378B P15 927 PSD-E WB M55 PRO	DALI
911401508546	RS378B P15 930 PSD-E WB M55 PRO	DALI
911401508646	RS378B P15 940 PSD-E WB M55 PRO	DALI
911401509746	RS378B P12 930 PSU-E MB M55 WP PRO	-
911401509846	RS378B P12 930 PSU-E WB M55 WP PRO	-
911401509946	RS378B P14 930 PSU-E MB M55 WP PRO	-
911401510046	RS378B P14 930 PSU-E WB M55 WP PRO	-
911401519546	RS378B P13 PSD-TNW NB M55 PRO	DALI
911401519646	RS378B P13 PSD-TNW MB M55 PRO	DALI
911401519746	RS378B P13 PSD-TNW WB M55 PRO	DALI
911401519846	RS378B P15 PSD-TNW NB M55 PRO	DALI
911401519946	RS378B P15 PSD-TNW MB M55 PRO	DALI
911401520046	RS378B P15 PSD-TNW WB M55 PRO	DALI

## Mechanical and Housing

Order Code	Full Product Name	Ingress protection code
911401528746	SM378B R P14 940 PSD-E WB D100 G-TT PRO	IP20
911401528846	SM378X R P8 930 WIA MB D100 G-TT PRO	IP20
911401528946	SM378X R P8 930 WIA WB D100 G-TT PRO	IP20
911401500046	RS378B P7 930 PSD-E WB M43 PRO	IP20
911401500146	RS378B P7 940 PSD-E WB M43 PRO	IP20
911401500246	RS378B P6 930 PSU-E MB M43 WP PRO	IP20/54
911401500346	RS378B P6 930 PSU-E WB M43 WP PRO	IP20/54
911401500446	RS378B P8 930 PSU-E MB M43 WP PRO	IP20/54
911401500546	RS378B P8 930 PSU-E WB M43 WP PRO	IP20/54
911401520146	RS378B P7 PSD-TNW NB M43 PRO	IP20
911401520246	RS378B P7 PSD-TNW MB M43 PRO	IP20
911401520346	RS378B P7 PSD-TNW WB M43 PRO	IP20
911401596945	RS378B P6 927 PSU-E SNB M43 PRO	IP20
911401597045	RS378B P6 930 PSU-E SNB M43 PRO	IP20

Order Code	Full Product Name	Ingress protection code
911401597145	RS378B P6 940 PSU-E SNB M43 PRO	IP20
911401597245	RS378B P6 927 PSU-E NB M43 PRO	IP20
911401597345	RS378B P6 930 PSU-E NB M43 PRO	IP20
911401597445	RS378B P6 940 PSU-E NB M43 PRO	IP20
911401597545	RS378B P6 927 PSU-E MB M43 PRO	IP20
911401597645	RS378B P6 930 PSU-E MB M43 PRO	IP20
911401597745	RS378B P6 940 PSU-E MB M43 PRO	IP20
911401597845	RS378B P6 927 PSU-E WB M43 PRO	IP20
911401597945	RS378B P6 930 PSU-E WB M43 PRO	IP20
911401598045	RS378B P6 940 PSU-E WB M43 PRO	IP20
911401598145	RS378B P8 927 PSU-E NB M43 PRO	IP20
911401598245	RS378B P8 930 PSU-E NB M43 PRO	IP20
911401598345	RS378B P8 940 PSU-E NB M43 PRO	IP20
911401598445	RS378B P8 927 PSU-E MB M43 PRO	IP20

# GreenSpace Flex Luna

Order Code	Full Product Name	Ingress protection code	Order Code	Full Product Name	Ingress protection code
911401598545	RS378B P8 930 PSU-E MB M43 PRO	IP20	911401506146	RS378B P9 930 PSD-E NB M55 PRO	IP20
911401598645	RS378B P8 940 PSU-E MB M43 PRO	IP20	911401506246	RS378B P9 940 PSD-E NB M55 PRO	IP20
911401598745	RS378B P8 927 PSU-E WB M43 PRO	IP20	911401506346	RS378B P9 927 PSD-E MB M55 PRO	IP20
911401598845	RS378B P8 930 PSU-E WB M43 PRO	IP20	911401506446	RS378B P9 930 PSD-E MB M55 PRO	IP20
911401598945	RS378B P8 940 PSU-E WB M43 PRO	IP20	911401506546	RS378B P9 940 PSD-E MB M55 PRO	IP20
911401599045	RS378B P7 927 PSD-E SNB M43 PRO	IP20	911401506646	RS378B P9 927 PSD-E WB M55 PRO	IP20
911401599145	RS378B P7 930 PSD-E SNB M43 PRO	IP20	911401506746	RS378B P9 930 PSD-E WB M55 PRO	IP20
911401599245	RS378B P7 940 PSD-E SNB M43 PRO	IP20	911401506846	RS378B P9 940 PSD-E WB M55 PRO	IP20
911401599345	RS378B P7 927 PSD-E NB M43 PRO	IP20	911401509346	RS378B P7 930 PSU-E MB M55 WP PRO	IP20/54
911401599445	RS378B P7 930 PSD-E NB M43 PRO	IP20	911401509446	RS378B P7 930 PSU-E WB M55 WP PRO	IP20/54
911401599545	RS378B P7 940 PSD-E NB M43 PRO	IP20	911401509546	RS378B P9 930 PSU-E MB M55 WP PRO	IP20/54
911401599645	RS378B P7 927 PSD-E MB M43 PRO	IP20	911401509646	RS378B P9 930 PSU-E WB M55 WP PRO	IP20/54
911401599745	RS378B P7 930 PSD-E MB M43 PRO	IP20	911401518946	RS378B P7 PSD-TNW NB M55 PRO	IP20
911401599845	RS378B P7 940 PSD-E MB M43 PRO	IP20	911401519046	RS378B P7 PSD-TNW MB M55 PRO	IP20
911401599945	RS378B P7 927 PSD-E WB M43 PRO	IP20	911401519146	RS378B P7 PSD-TNW WB M55 PRO	IP20
911401500646	RS378B P7 927 PSU-E SNB M55 PRO	IP20	911401519246	RS378B P9 PSD-TNW NB M55 PRO	IP20
911401500746	RS378B P7 930 PSU-E SNB M55 PRO	IP20	911401519346	RS378B P9 PSD-TNW MB M55 PRO	IP20
911401500846	RS378B P7 940 PSU-E SNB M55 PRO	IP20	911401519446	RS378B P9 PSD-TNW WB M55 PRO	IP20
911401500946	RS378B P7 927 PSU-E NB M55 PRO	IP20	911401595145	RS378B P3 927 PSU-E MB D35 G-TT PRO	IP20
911401501046	RS378B P7 930 PSU-E NB M55 PRO	IP20	911401595245	RS378B P3 930 PSU-E MB D35 G-TT PRO	IP20
911401501146	RS378B P7 940 PSU-E NB M55 PRO	IP20	911401595345	RS378B P3 940 PSU-E MB D35 G-TT PRO	IP20
911401501246	RS378B P7 927 PSU-E MB M55 PRO	IP20	911401595445	RS378B P3 927 PSU-E WB D35 G-TT PRO	IP20
911401501346	RS378B P7 930 PSU-E MB M55 PRO	IP20	911401595545	RS378B P3 930 PSU-E WB D35 G-TT PRO	IP20
911401501446	RS378B P7 940 PSU-E MB M55 PRO	IP20	911401595645	RS378B P3 940 PSU-E WB D35 G-TT PRO	IP20
911401501546	RS378B P7 927 PSU-E WB M55 PRO	IP20	911401595745	RS378B P5 927 PSU-E MB D35 G-TT PRO	IP20
911401501646	RS378B P7 930 PSU-E WB M55 PRO	IP20	911401595845	RS378B P5 930 PSU-E MB D35 G-TT PRO	IP20
911401501746	RS378B P7 940 PSU-E WB M55 PRO	IP20	911401595945	RS378B P5 940 PSU-E MB D35 G-TT PRO	IP20
911401501846	RS378B P8 927 PSU-E SNB M55 PRO	IP20	911401596045	RS378B P5 927 PSU-E WB D35 G-TT PRO	IP20
911401501946	RS378B P8 930 PSU-E SNB M55 PRO	IP20	911401596145	RS378B P5 930 PSU-E WB D35 G-TT PRO	IP20
911401502046	RS378B P8 940 PSU-E SNB M55 PRO	IP20	911401596245	RS378B P5 940 PSU-E WB D35 G-TT PRO	IP20
911401502146	RS378B P9 927 PSU-E NB M55 PRO	IP20	911401596345	RS378B P5 927 PSD-E MB D35 G-TT PRO	IP20
911401502246	RS378B P9 930 PSU-E NB M55 PRO	IP20	911401596445	RS378B P5 930 PSD-E MB D35 G-TT PRO	IP20
911401502346	RS378B P9 940 PSU-E NB M55 PRO	IP20	911401596545	RS378B P5 940 PSD-E MB D35 G-TT PRO	IP20
911401502446	RS378B P9 927 PSU-E MB M55 PRO	IP20	911401596645	RS378B P5 927 PSD-E WB D35 G-TT PRO	IP20
911401502546	RS378B P9 930 PSU-E MB M55 PRO	IP20	911401596745	RS378B P5 930 PSD-E WB D35 G-TT PRO	IP20
911401502646	RS378B P9 940 PSU-E MB M55 PRO	IP20	911401596845	RS378B P5 940 PSD-E WB D35 G-TT PRO	IP20
911401502746	RS378B P9 927 PSU-E WB M55 PRO	IP20	911401510146	RS378B P12 927 PSU-E NB M70 PRO	IP20
911401502846	RS378B P9 930 PSU-E WB M55 PRO	IP20	911401510246	RS378B P12 930 PSU-E NB M70 PRO	IP20
911401502946	RS378B P9 940 PSU-E WB M55 PRO	IP20	911401510346	RS378B P12 940 PSU-E NB M70 PRO	IP20
911401504846	RS378B P7 927 PSD-E SNB M55 PRO	IP20	911401510446	RS378B P12 927 PSU-E MB M70 PRO	IP20
911401504946	RS378B P7 930 PSD-E SNB M55 PRO	IP20	911401510546	RS378B P12 930 PSU-E MB M70 PRO	IP20
911401505046	RS378B P7 940 PSD-E SNB M55 PRO	IP20	911401510646	RS378B P12 940 PSU-E MB M70 PRO	IP20
911401505146	RS378B P7 927 PSD-E NB M55 PRO	IP20	911401510746	RS378B P12 927 PSU-E WB M70 PRO	IP20
911401505246	RS378B P7 930 PSD-E NB M55 PRO	IP20	911401510846	RS378B P12 930 PSU-E WB M70 PRO	IP20
911401505346	RS378B P7 940 PSD-E NB M55 PRO	IP20	911401510946	RS378B P12 940 PSU-E WB M70 PRO	IP20
911401505446	RS378B P7 927 PSD-E MB M55 PRO	IP20	911401511046	RS378B P17 927 PSU-E NB M70 PRO	IP20
911401505546	RS378B P7 930 PSD-E MB M55 PRO	IP20	911401511146	RS378B P17 930 PSU-E NB M70 PRO	IP20
911401505646	RS378B P7 940 PSD-E MB M55 PRO	IP20	911401511246	RS378B P17 940 PSU-E NB M70 PRO	IP20
911401505746	RS378B P7 927 PSD-E WB M55 PRO	IP20	911401511346	RS378B P17 927 PSU-E MB M70 PRO	IP20
911401505846	RS378B P7 930 PSD-E WB M55 PRO	IP20	911401511446	RS378B P17 930 PSU-E MB M70 PRO	IP20
911401505946	RS378B P7 940 PSD-E WB M55 PRO	IP20	911401511546	RS378B P17 940 PSU-E MB M70 PRO	IP20
911401506046	RS378B P9 927 PSD-E NB M55 PRO	IP20	911401511646	RS378B P17 927 PSU-E WB M70 PRO	IP20

# GreenSpace Flex Luna

Order Code	Full Product Name	Ingress protection code	Order Code	Full Product Name	Ingress protection code
911401511746	RS378B P17 930 PSU-E WB M70 PRO	IP20	911401521246	RS378B P22 PSD-TNW WB M70 PRO	IP20
911401511846	RS378B P17 940 PSU-E WB M70 PRO	IP20	911401512846	RS378B P27 927 PSU-E NB M70 PRO	IP20
911401511946	RS378B P19 927 PSU-E NB M70 PRO	IP20	911401512946	RS378B P27 930 PSU-E NB M70 PRO	IP20
911401512046	RS378B P19 930 PSU-E NB M70 PRO	IP20	911401513046	RS378B P27 940 PSU-E NB M70 PRO	IP20
911401512146	RS378B P19 940 PSU-E NB M70 PRO	IP20	911401513146	RS378B P27 927 PSU-E MB M70 PRO	IP20
911401512246	RS378B P19 927 PSU-E MB M70 PRO	IP20	911401513246	RS378B P27 930 PSU-E MB M70 PRO	IP20
911401512346	RS378B P19 930 PSU-E MB M70 PRO	IP20	911401513346	RS378B P27 940 PSU-E MB M70 PRO	IP20
911401512446	RS378B P19 940 PSU-E MB M70 PRO	IP20	911401513446	RS378B P27 927 PSU-E WB M70 PRO	IP20
911401512546	RS378B P19 927 PSU-E WB M70 PRO	IP20	911401513546	RS378B P27 930 PSU-E WB M70 PRO	IP20
911401512646	RS378B P19 930 PSU-E WB M70 PRO	IP20	911401513646	RS378B P27 940 PSU-E WB M70 PRO	IP20
911401512746	RS378B P19 940 PSU-E WB M70 PRO	IP20	911401516446	RS378B P27 927 PSD-E NB M70 PRO	IP20
911401513746	RS378B P12 927 PSD-E NB M70 PRO	IP20	911401516546	RS378B P27 930 PSD-E NB M70 PRO	IP20
911401513846	RS378B P12 930 PSD-E NB M70 PRO	IP20	911401516646	RS378B P27 940 PSD-E NB M70 PRO	IP20
911401513946	RS378B P12 940 PSD-E NB M70 PRO	IP20	911401516746	RS378B P27 927 PSD-E MB M70 PRO	IP20
911401514046	RS378B P12 927 PSD-E MB M70 PRO	IP20	911401516846	RS378B P27 930 PSD-E MB M70 PRO	IP20
911401514146	RS378B P12 930 PSD-E MB M70 PRO	IP20	911401516946	RS378B P27 940 PSD-E MB M70 PRO	IP20
911401514246	RS378B P12 940 PSD-E MB M70 PRO	IP20	911401517046	RS378B P27 927 PSD-E WB M70 PRO	IP20
911401514346	RS378B P12 927 PSD-E WB M70 PRO	IP20	911401517146	RS378B P27 930 PSD-E WB M70 PRO	IP20
911401514446	RS378B P12 930 PSD-E WB M70 PRO	IP20	911401517246	RS378B P27 940 PSD-E WB M70 PRO	IP20
911401514546	RS378B P12 940 PSD-E WB M70 PRO	IP20	911401518746	RS378B P27 930 PSU-E MB M70 WP PRO	IP20/54
911401514646	RS378B P18 927 PSD-E NB M70 PRO	IP20	911401518846	RS378B P27 930 PSU-E WB M70 WP PRO	IP20/54
911401514746	RS378B P18 930 PSD-E NB M70 PRO	IP20	911401521346	RS378B P29 PSD-TNW NB M70 PRO	IP20
911401514846	RS378B P18 940 PSD-E NB M70 PRO	IP20	911401521446	RS378B P29 PSD-TNW MB M70 PRO	IP20
911401514946	RS378B P18 927 PSD-E MB M70 PRO	IP20	911401521546	RS378B P29 PSD-TNW WB M70 PRO	IP20
911401515046	RS378B P18 930 PSD-E MB M70 PRO	IP20	911401531546	SM378B S P8 930 PSU-E WB D100 G-TT PRO	IP20
911401515146	RS378B P18 940 PSD-E MB M70 PRO	IP20	911401540046	SM378B S P22 PSD-TNW WB D100 G-TT PRO	IP20
911401515246	RS378B P18 927 PSD-E WB M70 PRO	IP20	911401503046	RS378B P12 927 PSU-E NB M55 PRO	IP20
911401515346	RS378B P18 930 PSD-E WB M70 PRO	IP20	911401503146	RS378B P12 930 PSU-E NB M55 PRO	IP20
911401515446	RS378B P18 940 PSD-E WB M70 PRO	IP20	911401503246	RS378B P12 940 PSU-E NB M55 PRO	IP20
911401515546	RS378B P20 927 PSD-E NB M70 PRO	IP20	911401503346	RS378B P12 927 PSU-E MB M55 PRO	IP20
911401515646	RS378B P20 930 PSD-E NB M70 PRO	IP20	911401503446	RS378B P12 930 PSU-E MB M55 PRO	IP20
911401515746	RS378B P20 940 PSD-E NB M70 PRO	IP20	911401503546	RS378B P12 940 PSU-E MB M55 PRO	IP20
911401515846	RS378B P20 927 PSD-E MB M70 PRO	IP20	911401503646	RS378B P12 927 PSU-E WB M55 PRO	IP20
911401515946	RS378B P20 930 PSD-E MB M70 PRO	IP20	911401503746	RS378B P12 930 PSU-E WB M55 PRO	IP20
911401516046	RS378B P20 940 PSD-E MB M70 PRO	IP20	911401503846	RS378B P12 940 PSU-E WB M55 PRO	IP20
911401516146	RS378B P20 927 PSD-E WB M70 PRO	IP20	911401503946	RS378B P14 927 PSU-E NB M55 PRO	IP20
911401516246	RS378B P20 930 PSD-E WB M70 PRO	IP20	911401504046	RS378B P14 930 PSU-E NB M55 PRO	IP20
911401516346	RS378B P20 940 PSD-E WB M70 PRO	IP20	911401504146	RS378B P14 940 PSU-E NB M55 PRO	IP20
911401518146	RS378B P12 930 PSU-E MB M70 WP PRO	IP20/54	911401504246	RS378B P14 927 PSU-E MB M55 PRO	IP20
911401518246	RS378B P12 930 PSU-E WB M70 WP PRO	IP20/54	911401504346	RS378B P14 930 PSU-E MB M55 PRO	IP20
911401518346	RS378B P17 930 PSU-E MB M70 WP PRO	IP20/54	911401504446	RS378B P14 940 PSU-E MB M55 PRO	IP20
911401518446	RS378B P17 930 PSU-E WB M70 WP PRO	IP20/54	911401504546	RS378B P14 927 PSU-E WB M55 PRO	IP20
911401518546	RS378B P19 930 PSU-E MB M70 WP PRO	IP20/54	911401504646	RS378B P14 930 PSU-E WB M55 PRO	IP20
911401518646	RS378B P19 930 PSU-E WB M70 WP PRO	IP20/54	911401504746	RS378B P14 940 PSU-E WB M55 PRO	IP20
911401520446	RS378B P13 PSD-TNW NB M70 PRO	IP20	911401506946	RS378B P13 927 PSD-E NB M55 PRO	IP20
911401520546	RS378B P13 PSD-TNW MB M70 PRO	IP20	911401507046	RS378B P13 930 PSD-E NB M55 PRO	IP20
911401520646	RS378B P13 PSD-TNW WB M70 PRO	IP20	911401507146	RS378B P13 940 PSD-E NB M55 PRO	IP20
911401520746	RS378B P19 PSD-TNW NB M70 PRO	IP20	911401507246	RS378B P13 927 PSD-E MB M55 PRO	IP20
911401520846	RS378B P19 PSD-TNW MB M70 PRO	IP20	911401507346	RS378B P13 930 PSD-E MB M55 PRO	IP20
911401520946	RS378B P19 PSD-TNW WB M70 PRO	IP20	911401507446	RS378B P13 940 PSD-E MB M55 PRO	IP20
911401521046	RS378B P22 PSD-TNW NB M70 PRO	IP20	911401507546	RS378B P13 927 PSD-E WB M55 PRO	IP20
911401521146	RS378B P22 PSD-TNW MB M70 PRO	IP20	911401507646	RS378B P13 930 PSD-E WB M55 PRO	IP20

Order Code	Full Product Name	Ingress protection code
911401507746	RS378B P13 940 PSD-E WB M55 PRO	IP20
911401507846	RS378B P15 927 PSD-E NB M55 PRO	IP20
911401507946	RS378B P15 930 PSD-E NB M55 PRO	IP20
911401508046	RS378B P15 940 PSD-E NB M55 PRO	IP20
911401508146	RS378B P15 927 PSD-E MB M55 PRO	IP20
911401508246	RS378B P15 930 PSD-E MB M55 PRO	IP20
911401508346	RS378B P15 940 PSD-E MB M55 PRO	IP20
911401508446	RS378B P15 927 PSD-E WB M55 PRO	IP20
911401508546	RS378B P15 930 PSD-E WB M55 PRO	IP20
911401508646	RS378B P15 940 PSD-E WB M55 PRO	IP20

Order Code	Full Product Name	Ingress protection code
911401509746	RS378B P12 930 PSU-E MB M55 WP PRO	IP20/54
911401509846	RS378B P12 930 PSU-E WB M55 WP PRO	IP20/54
911401509946	RS378B P14 930 PSU-E MB M55 WP PRO	IP20/54
911401510046	RS378B P14 930 PSU-E WB M55 WP PRO	IP20/54
911401519546	RS378B P13 PSD-TNW NB M55 PRO	IP20
911401519646	RS378B P13 PSD-TNW MB M55 PRO	IP20
911401519746	RS378B P13 PSD-TNW WB M55 PRO	IP20
911401519846	RS378B P15 PSD-TNW NB M55 PRO	IP20
911401519946	RS378B P15 PSD-TNW MB M55 PRO	IP20
911401520046	RS378B P15 PSD-TNW WB M55 PRO	IP20

## Approval and Application

Order Code	Full Product Name	CE mark
911401528746	SM378B R P14 940 PSD-E WB D100 G-TT PRO	Yes
911401528846	SM378X R P8 930 WIA MB D100 G-TT PRO	Yes
911401528946	SM378X R P8 930 WIA WB D100 G-TT PRO	Yes
911401500046	RS378B P7 930 PSD-E WB M43 PRO	Yes
911401500146	RS378B P7 940 PSD-E WB M43 PRO	Yes
911401500246	RS378B P6 930 PSU-E MB M43 WP PRO	Yes
911401500346	RS378B P6 930 PSU-E WB M43 WP PRO	Yes
911401500446	RS378B P8 930 PSU-E MB M43 WP PRO	Yes
911401500546	RS378B P8 930 PSU-E WB M43 WP PRO	Yes
911401520146	RS378B P7 PSD-TNW NB M43 PRO	No
911401520246	RS378B P7 PSD-TNW MB M43 PRO	No
911401520346	RS378B P7 PSD-TNW WB M43 PRO	No
911401596945	RS378B P6 927 PSU-E SNB M43 PRO	Yes
911401597045	RS378B P6 930 PSU-E SNB M43 PRO	Yes
911401597145	RS378B P6 940 PSU-E SNB M43 PRO	Yes
911401597245	RS378B P6 927 PSU-E NB M43 PRO	Yes
911401597345	RS378B P6 930 PSU-E NB M43 PRO	Yes
911401597445	RS378B P6 940 PSU-E NB M43 PRO	Yes
911401597545	RS378B P6 927 PSU-E MB M43 PRO	Yes
911401597645	RS378B P6 930 PSU-E MB M43 PRO	Yes
911401597745	RS378B P6 940 PSU-E MB M43 PRO	Yes
911401597845	RS378B P6 927 PSU-E WB M43 PRO	Yes
911401597945	RS378B P6 930 PSU-E WB M43 PRO	Yes
911401598045	RS378B P6 940 PSU-E WB M43 PRO	Yes
911401598145	RS378B P8 927 PSU-E NB M43 PRO	Yes
911401598245	RS378B P8 930 PSU-E NB M43 PRO	Yes
911401598345	RS378B P8 940 PSU-E NB M43 PRO	Yes
911401598445	RS378B P8 927 PSU-E MB M43 PRO	Yes
911401598545	RS378B P8 930 PSU-E MB M43 PRO	Yes
911401598645	RS378B P8 940 PSU-E MB M43 PRO	Yes
911401598745	RS378B P8 927 PSU-E WB M43 PRO	Yes
911401598845	RS378B P8 930 PSU-E WB M43 PRO	Yes
911401598945	RS378B P8 940 PSU-E WB M43 PRO	Yes
911401599045	RS378B P7 927 PSD-E SNB M43 PRO	Yes
911401599145	RS378B P7 930 PSD-E SNB M43 PRO	Yes
911401599245	RS378B P7 940 PSD-E SNB M43 PRO	Yes
911401599345	RS378B P7 927 PSD-E NB M43 PRO	Yes
911401599445	RS378B P7 930 PSD-E NB M43 PRO	Yes

Order Code	Full Product Name	CE mark
911401599545	RS378B P7 940 PSD-E NB M43 PRO	Yes
911401599645	RS378B P7 927 PSD-E MB M43 PRO	Yes
911401599745	RS378B P7 930 PSD-E MB M43 PRO	Yes
911401599845	RS378B P7 940 PSD-E MB M43 PRO	Yes
911401599945	RS378B P7 927 PSD-E WB M43 PRO	Yes
911401500646	RS378B P7 927 PSU-E SNB M55 PRO	Yes
911401500746	RS378B P7 930 PSU-E SNB M55 PRO	Yes
911401500846	RS378B P7 940 PSU-E SNB M55 PRO	Yes
911401500946	RS378B P7 927 PSU-E NB M55 PRO	Yes
911401501046	RS378B P7 930 PSU-E NB M55 PRO	Yes
911401501146	RS378B P7 940 PSU-E NB M55 PRO	Yes
911401501246	RS378B P7 927 PSU-E MB M55 PRO	Yes
911401501346	RS378B P7 930 PSU-E MB M55 PRO	Yes
911401501446	RS378B P7 940 PSU-E MB M55 PRO	Yes
911401501546	RS378B P7 927 PSU-E WB M55 PRO	Yes
911401501646	RS378B P7 930 PSU-E WB M55 PRO	Yes
911401501746	RS378B P7 940 PSU-E WB M55 PRO	Yes
911401501846	RS378B P8 927 PSU-E SNB M55 PRO	Yes
911401501946	RS378B P8 930 PSU-E SNB M55 PRO	Yes
911401502046	RS378B P8 940 PSU-E SNB M55 PRO	Yes
911401502146	RS378B P9 927 PSU-E NB M55 PRO	Yes
911401502246	RS378B P9 930 PSU-E NB M55 PRO	Yes
911401502346	RS378B P9 940 PSU-E NB M55 PRO	Yes
911401502446	RS378B P9 927 PSU-E MB M55 PRO	Yes
911401502546	RS378B P9 930 PSU-E MB M55 PRO	Yes
911401502646	RS378B P9 940 PSU-E MB M55 PRO	Yes
911401502746	RS378B P9 927 PSU-E WB M55 PRO	Yes
911401502846	RS378B P9 930 PSU-E WB M55 PRO	Yes
911401502946	RS378B P9 940 PSU-E WB M55 PRO	Yes
911401504846	RS378B P7 927 PSD-E SNB M55 PRO	Yes
911401504946	RS378B P7 930 PSD-E SNB M55 PRO	Yes
911401505046	RS378B P7 940 PSD-E SNB M55 PRO	Yes
911401505146	RS378B P7 927 PSD-E NB M55 PRO	Yes
911401505246	RS378B P7 930 PSD-E NB M55 PRO	Yes
911401505346	RS378B P7 940 PSD-E NB M55 PRO	Yes
911401505446	RS378B P7 927 PSD-E MB M55 PRO	Yes
911401505546	RS378B P7 930 PSD-E MB M55 PRO	Yes
911401505646	RS378B P7 940 PSD-E MB M55 PRO	Yes

# GreenSpace Flex Luna

Order Code	Full Product Name	CE mark	Order Code	Full Product Name	CE mark
911401505746	RS378B P7 927 PSD-E WB M55 PRO	Yes	911401511346	RS378B P17 927 PSU-E MB M70 PRO	Yes
911401505846	RS378B P7 930 PSD-E WB M55 PRO	Yes	911401511446	RS378B P17 930 PSU-E MB M70 PRO	Yes
911401505946	RS378B P7 940 PSD-E WB M55 PRO	Yes	911401511546	RS378B P17 940 PSU-E MB M70 PRO	Yes
911401506046	RS378B P9 927 PSD-E NB M55 PRO	Yes	911401511646	RS378B P17 927 PSU-E WB M70 PRO	Yes
911401506146	RS378B P9 930 PSD-E NB M55 PRO	Yes	911401511746	RS378B P17 930 PSU-E WB M70 PRO	Yes
911401506246	RS378B P9 940 PSD-E NB M55 PRO	Yes	911401511846	RS378B P17 940 PSU-E WB M70 PRO	Yes
911401506346	RS378B P9 927 PSD-E MB M55 PRO	Yes	911401511946	RS378B P19 927 PSU-E NB M70 PRO	Yes
911401506446	RS378B P9 930 PSD-E MB M55 PRO	Yes	911401512046	RS378B P19 930 PSU-E NB M70 PRO	Yes
911401506546	RS378B P9 940 PSD-E MB M55 PRO	Yes	911401512146	RS378B P19 940 PSU-E NB M70 PRO	Yes
911401506646	RS378B P9 927 PSD-E WB M55 PRO	Yes	911401512246	RS378B P19 927 PSU-E MB M70 PRO	Yes
911401506746	RS378B P9 930 PSD-E WB M55 PRO	Yes	911401512346	RS378B P19 930 PSU-E MB M70 PRO	Yes
911401506846	RS378B P9 940 PSD-E WB M55 PRO	Yes	911401512446	RS378B P19 940 PSU-E MB M70 PRO	Yes
911401509346	RS378B P7 930 PSU-E MB M55 WP PRO	Yes	911401512546	RS378B P19 927 PSU-E WB M70 PRO	Yes
911401509446	RS378B P7 930 PSU-E WB M55 WP PRO	Yes	911401512646	RS378B P19 930 PSU-E WB M70 PRO	Yes
911401509546	RS378B P9 930 PSU-E MB M55 WP PRO	Yes	911401512746	RS378B P19 940 PSU-E WB M70 PRO	Yes
911401509646	RS378B P9 930 PSU-E WB M55 WP PRO	Yes	911401513746	RS378B P12 927 PSD-E NB M70 PRO	Yes
911401518946	RS378B P7 PSD-TNW NB M55 PRO	No	911401513846	RS378B P12 930 PSD-E NB M70 PRO	Yes
911401519046	RS378B P7 PSD-TNW MB M55 PRO	No	911401513946	RS378B P12 940 PSD-E NB M70 PRO	Yes
911401519146	RS378B P7 PSD-TNW WB M55 PRO	No	911401514046	RS378B P12 927 PSD-E MB M70 PRO	Yes
911401519246	RS378B P9 PSD-TNW NB M55 PRO	No	911401514146	RS378B P12 930 PSD-E MB M70 PRO	Yes
911401519346	RS378B P9 PSD-TNW MB M55 PRO	No	911401514246	RS378B P12 940 PSD-E MB M70 PRO	Yes
911401519446	RS378B P9 PSD-TNW WB M55 PRO	No	911401514346	RS378B P12 927 PSD-E WB M70 PRO	Yes
911401595145	RS378B P3 927 PSU-E MB D35 G-TT PRO	Yes	911401514446	RS378B P12 930 PSD-E WB M70 PRO	Yes
911401595245	RS378B P3 930 PSU-E MB D35 G-TT PRO	Yes	911401514546	RS378B P12 940 PSD-E WB M70 PRO	Yes
911401595345	RS378B P3 940 PSU-E MB D35 G-TT PRO	Yes	911401514646	RS378B P18 927 PSD-E NB M70 PRO	Yes
911401595445	RS378B P3 927 PSU-E WB D35 G-TT PRO	Yes	911401514746	RS378B P18 930 PSD-E NB M70 PRO	Yes
911401595545	RS378B P3 930 PSU-E WB D35 G-TT PRO	Yes	911401514846	RS378B P18 940 PSD-E NB M70 PRO	Yes
911401595645	RS378B P3 940 PSU-E WB D35 G-TT PRO	Yes	911401514946	RS378B P18 927 PSD-E MB M70 PRO	Yes
911401595745	RS378B P5 927 PSU-E MB D35 G-TT PRO	Yes	911401515046	RS378B P18 930 PSD-E MB M70 PRO	Yes
911401595845	RS378B P5 930 PSU-E MB D35 G-TT PRO	Yes	911401515146	RS378B P18 940 PSD-E MB M70 PRO	Yes
911401595945	RS378B P5 940 PSU-E MB D35 G-TT PRO	Yes	911401515246	RS378B P18 927 PSD-E WB M70 PRO	Yes
911401596045	RS378B P5 927 PSU-E WB D35 G-TT PRO	Yes	911401515346	RS378B P18 930 PSD-E WB M70 PRO	Yes
911401596145	RS378B P5 930 PSU-E WB D35 G-TT PRO	Yes	911401515446	RS378B P18 940 PSD-E WB M70 PRO	Yes
911401596245	RS378B P5 940 PSU-E WB D35 G-TT PRO	Yes	911401515546	RS378B P20 927 PSD-E NB M70 PRO	Yes
911401596345	RS378B P5 927 PSD-E MB D35 G-TT PRO	Yes	911401515646	RS378B P20 930 PSD-E NB M70 PRO	Yes
911401596445	RS378B P5 930 PSD-E MB D35 G-TT PRO	Yes	911401515746	RS378B P20 940 PSD-E NB M70 PRO	Yes
911401596545	RS378B P5 940 PSD-E MB D35 G-TT PRO	Yes	911401515846	RS378B P20 927 PSD-E MB M70 PRO	Yes
911401596645	RS378B P5 927 PSD-E WB D35 G-TT PRO	Yes	911401515946	RS378B P20 930 PSD-E MB M70 PRO	Yes
911401596745	RS378B P5 930 PSD-E WB D35 G-TT PRO	Yes	911401516046	RS378B P20 940 PSD-E MB M70 PRO	Yes
911401596845	RS378B P5 940 PSD-E WB D35 G-TT PRO	Yes	911401516146	RS378B P20 927 PSD-E WB M70 PRO	Yes
911401510146	RS378B P12 927 PSU-E NB M70 PRO	Yes	911401516246	RS378B P20 930 PSD-E WB M70 PRO	Yes
911401510246	RS378B P12 930 PSU-E NB M70 PRO	Yes	911401516346	RS378B P20 940 PSD-E WB M70 PRO	Yes
911401510346	RS378B P12 940 PSU-E NB M70 PRO	Yes	911401518146	RS378B P12 930 PSU-E MB M70 WP PRO	Yes
911401510446	RS378B P12 927 PSU-E MB M70 PRO	Yes	911401518246	RS378B P12 930 PSU-E WB M70 WP PRO	Yes
911401510546	RS378B P12 930 PSU-E MB M70 PRO	Yes	911401518346	RS378B P17 930 PSU-E MB M70 WP PRO	Yes
911401510646	RS378B P12 940 PSU-E MB M70 PRO	Yes	911401518446	RS378B P17 930 PSU-E WB M70 WP PRO	Yes
911401510746	RS378B P12 927 PSU-E WB M70 PRO	Yes	911401518546	RS378B P19 930 PSU-E MB M70 WP PRO	Yes
911401510846	RS378B P12 930 PSU-E WB M70 PRO	Yes	911401518646	RS378B P19 930 PSU-E WB M70 WP PRO	Yes
911401510946	RS378B P12 940 PSU-E WB M70 PRO	Yes	911401520446	RS378B P13 PSD-TNW NB M70 PRO	No
911401511046	RS378B P17 927 PSU-E NB M70 PRO	Yes	911401520546	RS378B P13 PSD-TNW MB M70 PRO	No
911401511146	RS378B P17 930 PSU-E NB M70 PRO	Yes	911401520646	RS378B P13 PSD-TNW WB M70 PRO	No
911401511246	RS378B P17 940 PSU-E NB M70 PRO	Yes	911401520746	RS378B P19 PSD-TNW NB M70 PRO	No

# GreenSpace Flex Luna

Order Code	Full Product Name	CE mark	Order Code	Full Product Name	CE mark
911401520846	RS378B P19 PSD-TNW MB M70 PRO	No	911401503846	RS378B P12 940 PSU-E WB M55 PRO	Yes
911401520946	RS378B P19 PSD-TNW WB M70 PRO	No	911401503946	RS378B P14 927 PSU-E NB M55 PRO	Yes
911401521046	RS378B P22 PSD-TNW NB M70 PRO	No	911401504046	RS378B P14 930 PSU-E NB M55 PRO	Yes
911401521146	RS378B P22 PSD-TNW MB M70 PRO	No	911401504146	RS378B P14 940 PSU-E NB M55 PRO	Yes
911401521246	RS378B P22 PSD-TNW WB M70 PRO	No	911401504246	RS378B P14 927 PSU-E MB M55 PRO	Yes
911401512846	RS378B P27 927 PSU-E NB M70 PRO	Yes	911401504346	RS378B P14 930 PSU-E MB M55 PRO	Yes
911401512946	RS378B P27 930 PSU-E NB M70 PRO	Yes	911401504446	RS378B P14 940 PSU-E MB M55 PRO	Yes
911401513046	RS378B P27 940 PSU-E NB M70 PRO	Yes	911401504546	RS378B P14 927 PSU-E WB M55 PRO	Yes
911401513146	RS378B P27 927 PSU-E MB M70 PRO	Yes	911401504646	RS378B P14 930 PSU-E WB M55 PRO	Yes
911401513246	RS378B P27 930 PSU-E MB M70 PRO	Yes	911401504746	RS378B P14 940 PSU-E WB M55 PRO	Yes
911401513346	RS378B P27 940 PSU-E MB M70 PRO	Yes	911401506946	RS378B P13 927 PSD-E NB M55 PRO	Yes
911401513446	RS378B P27 927 PSU-E WB M70 PRO	Yes	911401507046	RS378B P13 930 PSD-E NB M55 PRO	Yes
911401513546	RS378B P27 930 PSU-E WB M70 PRO	Yes	911401507146	RS378B P13 940 PSD-E NB M55 PRO	Yes
911401513646	RS378B P27 940 PSU-E WB M70 PRO	Yes	911401507246	RS378B P13 927 PSD-E MB M55 PRO	Yes
911401516446	RS378B P27 927 PSD-E NB M70 PRO	Yes	911401507346	RS378B P13 930 PSD-E MB M55 PRO	Yes
911401516546	RS378B P27 930 PSD-E NB M70 PRO	Yes	911401507446	RS378B P13 940 PSD-E MB M55 PRO	Yes
911401516646	RS378B P27 940 PSD-E NB M70 PRO	Yes	911401507546	RS378B P13 927 PSD-E WB M55 PRO	Yes
911401516746	RS378B P27 927 PSD-E MB M70 PRO	Yes	911401507646	RS378B P13 930 PSD-E WB M55 PRO	Yes
911401516846	RS378B P27 930 PSD-E MB M70 PRO	Yes	911401507746	RS378B P13 940 PSD-E WB M55 PRO	Yes
911401516946	RS378B P27 940 PSD-E MB M70 PRO	Yes	911401507846	RS378B P15 927 PSD-E NB M55 PRO	Yes
911401517046	RS378B P27 927 PSD-E WB M70 PRO	Yes	911401507946	RS378B P15 930 PSD-E NB M55 PRO	Yes
911401517146	RS378B P27 930 PSD-E WB M70 PRO	Yes	911401508046	RS378B P15 940 PSD-E NB M55 PRO	Yes
911401517246	RS378B P27 940 PSD-E WB M70 PRO	Yes	911401508146	RS378B P15 927 PSD-E MB M55 PRO	Yes
911401518746	RS378B P27 930 PSU-E MB M70 WP PRO	Yes	911401508246	RS378B P15 930 PSD-E MB M55 PRO	Yes
911401518846	RS378B P27 930 PSU-E WB M70 WP PRO	Yes	911401508346	RS378B P15 940 PSD-E MB M55 PRO	Yes
911401521346	RS378B P29 PSD-TNW NB M70 PRO	No	911401508446	RS378B P15 927 PSD-E WB M55 PRO	Yes
911401521446	RS378B P29 PSD-TNW MB M70 PRO	No	911401508546	RS378B P15 930 PSD-E WB M55 PRO	Yes
911401521546	RS378B P29 PSD-TNW WB M70 PRO	No	911401508646	RS378B P15 940 PSD-E WB M55 PRO	Yes
911401531546	SM378B S P8 930 PSU-E WB D100 G-TT PRO	Yes	911401509746	RS378B P12 930 PSU-E MB M55 WP PRO	Yes
911401540046	SM378B S P22 PSD-TNW WB D100 G-TT PRO	No	911401509846	RS378B P12 930 PSU-E WB M55 WP PRO	Yes
911401503046	RS378B P12 927 PSU-E NB M55 PRO	Yes	911401509946	RS378B P14 930 PSU-E MB M55 WP PRO	Yes
911401503146	RS378B P12 930 PSU-E NB M55 PRO	Yes	911401510046	RS378B P14 930 PSU-E WB M55 WP PRO	Yes
911401503246	RS378B P12 940 PSU-E NB M55 PRO	Yes	911401519546	RS378B P13 PSD-TNW NB M55 PRO	No
911401503346	RS378B P12 927 PSU-E MB M55 PRO	Yes	911401519646	RS378B P13 PSD-TNW MB M55 PRO	No
911401503446	RS378B P12 930 PSU-E MB M55 PRO	Yes	911401519746	RS378B P13 PSD-TNW WB M55 PRO	No
911401503546	RS378B P12 940 PSU-E MB M55 PRO	Yes	911401519846	RS378B P15 PSD-TNW NB M55 PRO	No
911401503646	RS378B P12 927 PSU-E WB M55 PRO	Yes	911401519946	RS378B P15 PSD-TNW MB M55 PRO	No
911401503746	RS378B P12 930 PSU-E WB M55 PRO	Yes	911401520046	RS378B P15 PSD-TNW WB M55 PRO	No

