



A powerful discreet spots with an accent on sustainability

LuxSpace Accent Compact Adjustable

With LuxSpace Accent Compact Adjustable, retailers and building operators can enjoy the superior quality of light and market-leading energy efficiency of PerfectAccent optics in a refined and neutral spot design. Powerful and discreet, LuxSpace Accent combines a high luminous flux in a compact form factor. Design-in and installation are easy due to its small built-in dimensions. Maintenance and upgrades of the optics is fast and requires no tools. Furthermore, LuxSpace Compact Adjustable spots are certified as circular lighting products and offer multiple system integration and dimming options, including wired as well as wireless. LuxSpace Accent Compact Adjustable allows spot head rotation and two-directional tilting for maximum aiming flexibility. For prolonged shelf life and better visual representation of food, reducing food waste and increasing sales, fresh food LED lighting recipes are available. Check out our Fashion and Food catalog pages to find out more about PremiumWhite, PremiumColor, Fresh Meat, Rosé, Frost and Champagne.

Benefits

- More sparkle and enhanced shopper eye comfort with PerfectAccent optics
- Best-in-class efficacy to reduce carbon footprint and save on energy use
- Certified as circular lighting with PerfectAccent high-efficacy reflectors
- Easy maintenance and upgrades with tool-less access to driver and optics
- The clean and refined product design helps the spots blend in with ceilings

LuxSpace Accent Compact Adjustable

Features

- RS771B offers high maximum flux (4900lm) in a very compact housing with limited built-in dimensions
- Available with PerfectAccent high-efficacy reflectors
- Optional front glass (advised in dusty environments)
- Two-directional tilt for great light control
- Available with fresh food LED lighting recipes and LED flavors
- Wired (DALI) and wireless connectivity options

Application

- Convenience stores
- Supermarkets & hypermarkets
- Offices and hospitality areas

Warnings and Safety

- All photometrical data is calculated without optional front glass. Flux should be reduced by 3.5% when using a front glass
- Cleaning of the optic should only be done with pressurized air. Touching the LED or reflector is forbidden. For food preparation areas and areas with high levels of dust, the use of the optional front glass is strongly advised, as it can be cleaned with a (dry) microfiber cloth
- During maintenance, the product must be switched off and cooled down
- The product must be installed out of arm's reach. Manipulating the product when hot is only possible with an insulated glove

Versions





RS771B LuxSpace Accent Compact Adjustable Black



RS771B LuxSpace Accent Compact Adjustable Silver

Dimensional drawing



LuxSpace Accent Compact Adjustable

Product details

LuxSpace Accent Adjustable luminaires offer 2-way tilting for easy aiming in any installation



Step5 (optional): Add or remove the front glass



Step4: Replace the reflector



RS771B LuxSpace Accent Compact Adjustable Back View



Step1; Press the button to unlock the front face



Step2: Remove the optical assembly from the luminaire



Step3: Pull the clip of the frontface to release the reflector



LuxSpace Accent Compact Adjustable

Product details



PerfectAccent reflector and front glass maintenance and upgrading is easy with an integrated button

General Information

Driver included	Yes
Light source replaceable	No
Number of gear units	1 unit
Service tag	Yes

Light Technical

Beam angle of light source	120 degree(s)
----------------------------	---------------

Operating and Electrical

Protection class IEC	Safety class II
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	No

Mechanical and Housing

Mech. impact protection code	IK02
Ingress protection code	IP20

Approval and Application

Ambient temperature range	+10 to +35 °C
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.5

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Product Data

Product family code	RS771B
---------------------	--------

Light Technical (1/2)

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505101566	RS771B 17S/930 PSU-E HWB WH	3000 K	>90	134 lm/W	1,650 lm
910505101570	RS771B 19S/ROSE PSU-E HWB FG WH	2200 K	>80	103 lm/W	2,000 lm
910505101571	RS771B 19S/FMT PSU-E HWB FG WH	3000 K	>90	81 lm/W	2,000 lm
910505101572	RS771B 20S/830 PSU-E NB WH	3000 K	>80	120 lm/W	2,000 lm
910505101573	RS771B 27S/827 PSU-E WB WH	2700 K	>80	131 lm/W	2,600 lm
910505101574	RS771B 27S/830 PSU-E MB WH	3000 K	>80	136 lm/W	2,700 lm
910505101575	RS771B 27S/830 DIA-VLC-E HMB WH	3000 K	>80	133 lm/W	2,800 lm
910505101576	RS771B 27S/830 WIA-E MB WH	3000 K	>80	131 lm/W	2,700 lm
910505101577	RS771B 27S/840 PSU-E WB WH	4000 K	>80	142 lm/W	2,800 lm
910505101579	RS771B 27S/PW930 PSU-E HMB WH	3000 K	>90	138 lm/W	2,700 lm
910505101580	RS771B 27S/PC930 PSU-E HWB WH	3000 K	>90	118 lm/W	2,900 lm
910505101581	RS771B 27S/ROSE PSU-E HWB FG WH	2200 K	>80	93 lm/W	2,900 lm
910505101582	RS771B 27S/FMT PSU-E HWB FG WH	3000 K	>90	81 lm/W	2,800 lm
910505101583	RS771B 27S/CH PSU-E HWB FG WH	2700 K	>80	135 lm/W	2,700 lm
910505101584	RS771B 27S/FR PSU-E HWB FG WH	5000 K	>90	119 lm/W	2,700 lm
910505101586	RS771B 39S/830 PSU-E VVB WH	3000 K	>80	142 lm/W	4,100 lm
910505101587	RS771B 39S/840 PSU-E WB WH	4000 K	>80	147 lm/W	4,200 lm

LuxSpace Accent Compact Adjustable

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505101588	RS771B 39S/930 PSU-E WB WH	3000 K	>90	127 lm/W	3,900 lm
910505101589	RS771B 39S/PW930 PSU-E WB WH	3000 K	>90	130 lm/W	4,000 lm
910505101590	RS771B 49S/827 PSU-E HWB WH	2700 K	>80	133 lm/W	5,000 lm
910505101591	RS771B 49S/830 PSU-E HWB WH	3000 K	>80	139 lm/W	5,200 lm
910505101592	RS771B 49S/840 PSU-E HWB WH	4000 K	>80	144 lm/W	5,400 lm
910505101593	RS771B 49S/930 PSU-E HWB WH	3000 K	>90	137 lm/W	5,200 lm
910505101594	RS771B 49S/PW930 PSU-E HWB WH	3000 K	>90	137 lm/W	5,200 lm
910505101578	RS771B 27S/930 PSU-E WB BK	3000 K	>90	132 lm/W	2,600 lm
910505101585	RS771B 39S/827 PSU-E WB SI	2700 K	>80	132 lm/W	4,100 lm

Light Technical (2/2)

Order Code	Full Product Name	Optic type	Order Code	Full Product Name	Optic type
910505101566	RS771B 17S/930 PSU-E HWB WH	High-reflective metal reflector Wide beam 40 to 80 degrees	910505101583	RS771B 27S/CH PSU-E HWB FG WH	High-reflective metal reflector Wide beam 40 to 80 degrees
910505101570	RS771B 19S/ROSE PSU-E HWB FG WH	High-reflective metal reflector Wide beam 40 to 80 degrees	910505101584	RS771B 27S/FR PSU-E HWB FG WH	High-reflective metal reflector Wide beam 40 to 80 degrees
910505101571	RS771B 19S/FMT PSU-E HWB FG WH	High-reflective metal reflector Wide beam 40 to 80 degrees	910505101586	RS771B 39S/830 PSU-E VWB WH	Very wide beam
910505101572	RS771B 20S/830 PSU-E NB WH	Narrow beam	910505101587	RS771B 39S/840 PSU-E WB WH	Wide beam
910505101573	RS771B 27S/827 PSU-E WB WH	Wide beam	910505101588	RS771B 39S/930 PSU-E WB WH	Wide beam
910505101574	RS771B 27S/830 PSU-E MB WH	Medium beam	910505101589	RS771B 39S/PW930 PSU-E WB WH	Wide beam
910505101575	RS771B 27S/830 DIA-VLC-E HMB WH	High-reflective metal reflector Medium beam 20 to 40 degrees	910505101590	RS771B 49S/827 PSU-E HWB WH	High-reflective metal reflector Wide beam 40 to 80 degrees
910505101576	RS771B 27S/830 WIA-E MB WH	Medium beam	910505101591	RS771B 49S/830 PSU-E HWB WH	High-reflective metal reflector Wide beam 40 to 80 degrees
910505101577	RS771B 27S/840 PSU-E WB WH	Wide beam	910505101592	RS771B 49S/840 PSU-E HWB WH	High-reflective metal reflector Wide beam 40 to 80 degrees
910505101579	RS771B 27S/PW930 PSU-E HWB WH	High-reflective metal reflector Wide beam 40 to 80 degrees	910505101593	RS771B 49S/930 PSU-E HWB WH	High-reflective metal reflector Wide beam 40 to 80 degrees
910505101580	RS771B 27S/PC930 PSU-E HWB WH	High-reflective metal reflector Wide beam 40 to 80 degrees	910505101594	RS771B 49S/PW930 PSU-E HWB WH	High-reflective metal reflector Wide beam 40 to 80 degrees
910505101581	RS771B 27S/ROSE PSU-E HWB FG WH	High-reflective metal reflector Wide beam 40 to 80 degrees	910505101578	RS771B 27S/930 PSU-E WB BK	Wide beam
910505101582	RS771B 27S/FMT PSU-E HWB FG WH	High-reflective metal reflector Wide beam 40 to 80 degrees	910505101585	RS771B 39S/827 PSU-E WB SI	Wide beam

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
910505101566	RS771B 17S/930 PSU-E HWB WH	11.8 W	910505101571	RS771B 19S/FMT PSU-E HWB FG WH	25 W
910505101570	RS771B 19S/ROSE PSU-E HWB FG WH	19.2 W	910505101572	RS771B 20S/830 PSU-E NB WH	16.6 W

LuxSpace Accent Compact Adjustable

Order Code	Full Product Name	Power Consumption
910505101573	RS771B 27S/827 PSU-E WB WH	19.6 W
910505101574	RS771B 27S/830 PSU-E MB WH	19.6 W
910505101575	RS771B 27S/830 DIA-VLC-E HMB WH	20.5 W
910505101576	RS771B 27S/830 WIA-E MB WH	20.5 W
910505101577	RS771B 27S/840 PSU-E WB WH	19.6 W
910505101579	RS771B 27S/PW930 PSU-E HWB WH	19.8 W
910505101580	RS771B 27S/PC930 PSU-E HWB WH	24.5 W
910505101581	RS771B 27S/ROSE PSU-E HWB FG WH	5 W
910505101582	RS771B 27S/FMT PSU-E HWB FG WH	35 W
910505101583	RS771B 27S/CH PSU-E HWB FG WH	19.8 W
910505101584	RS771B 27S/FR PSU-E HWB FG WH	23 W

Order Code	Full Product Name	Power Consumption
910505101586	RS771B 39S/830 PSU-E VWB WH	29 W
910505101587	RS771B 39S/840 PSU-E WB WH	29 W
910505101588	RS771B 39S/930 PSU-E WB WH	31 W
910505101589	RS771B 39S/PW930 PSU-E WB WH	31 W
910505101590	RS771B 49S/827 PSU-E HWB WH	37.5 W
910505101591	RS771B 49S/830 PSU-E HWB WH	37.5 W
910505101592	RS771B 49S/840 PSU-E HWB WH	37.5 W
910505101593	RS771B 49S/930 PSU-E HWB WH	38 W
910505101594	RS771B 49S/PW930 PSU-E HWB WH	38 W
910505101578	RS771B 27S/930 PSU-E WB BK	19.8 W
910505101585	RS771B 39S/827 PSU-E WB SI	31 W

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
910505101566	RS771B 17S/930 PSU-E HWB WH	No	Not applicable
910505101570	RS771B 19S/ROSE PSU-E HWB FG WH	No	Not applicable
910505101571	RS771B 19S/FMT PSU-E HWB FG WH	No	Not applicable
910505101572	RS771B 20S/830 PSU-E NB WH	No	Not applicable
910505101573	RS771B 27S/827 PSU-E WB WH	No	Not applicable
910505101574	RS771B 27S/830 PSU-E MB WH	No	Not applicable
910505101575	RS771B 27S/830 DIA-VLC-E HMB WH	Yes	1%
910505101576	RS771B 27S/830 WIA-E MB WH	Yes	Not applicable
910505101577	RS771B 27S/840 PSU-E WB WH	No	Not applicable
910505101579	RS771B 27S/PW930 PSU-E HWB WH	No	Not applicable
910505101580	RS771B 27S/PC930 PSU-E HWB WH	No	Not applicable
910505101581	RS771B 27S/ROSE PSU-E HWB FG WH	No	Not applicable
910505101582	RS771B 27S/FMT PSU-E HWB FG WH	No	Not applicable

Order Code	Full Product Name	Dimmable	Maximum dim level
910505101583	RS771B 27S/CH PSU-E HWB FG WH	No	Not applicable
910505101584	RS771B 27S/FR PSU-E HWB FG WH	No	Not applicable
910505101586	RS771B 39S/830 PSU-E VWB WH	No	Not applicable
910505101587	RS771B 39S/840 PSU-E WB WH	No	Not applicable
910505101588	RS771B 39S/930 PSU-E WB WH	No	Not applicable
910505101589	RS771B 39S/PW930 PSU-E WB WH	No	Not applicable
910505101590	RS771B 49S/827 PSU-E HWB WH	No	Not applicable
910505101591	RS771B 49S/830 PSU-E HWB WH	No	Not applicable
910505101592	RS771B 49S/840 PSU-E HWB WH	No	Not applicable
910505101593	RS771B 49S/930 PSU-E HWB WH	No	Not applicable
910505101594	RS771B 49S/PW930 PSU-E HWB WH	No	Not applicable
910505101578	RS771B 27S/930 PSU-E WB BK	No	Not applicable
910505101585	RS771B 39S/827 PSU-E WB SI	No	Not applicable

Mechanical and Housing

Order Code	Full Product Name	Housing Color
910505101566	RS771B 17S/930 PSU-E HWB WH	White
910505101570	RS771B 19S/ROSE PSU-E HWB FG WH	White
910505101571	RS771B 19S/FMT PSU-E HWB FG WH	White
910505101572	RS771B 20S/830 PSU-E NB WH	White
910505101573	RS771B 27S/827 PSU-E WB WH	White
910505101574	RS771B 27S/830 PSU-E MB WH	White
910505101575	RS771B 27S/830 DIA-VLC-E HMB WH	White
910505101576	RS771B 27S/830 WIA-E MB WH	White
910505101577	RS771B 27S/840 PSU-E WB WH	White
910505101579	RS771B 27S/PW930 PSU-E HWB WH	White
910505101580	RS771B 27S/PC930 PSU-E HWB WH	White
910505101581	RS771B 27S/ROSE PSU-E HWB FG WH	White
910505101582	RS771B 27S/FMT PSU-E HWB FG WH	White

Order Code	Full Product Name	Housing Color
910505101583	RS771B 27S/CH PSU-E HWB FG WH	White
910505101584	RS771B 27S/FR PSU-E HWB FG WH	White
910505101586	RS771B 39S/830 PSU-E VWB WH	White
910505101587	RS771B 39S/840 PSU-E WB WH	White
910505101588	RS771B 39S/930 PSU-E WB WH	White
910505101589	RS771B 39S/PW930 PSU-E WB WH	White
910505101590	RS771B 49S/827 PSU-E HWB WH	White
910505101591	RS771B 49S/830 PSU-E HWB WH	White
910505101592	RS771B 49S/840 PSU-E HWB WH	White
910505101593	RS771B 49S/930 PSU-E HWB WH	White
910505101594	RS771B 49S/PW930 PSU-E HWB WH	White
910505101578	RS771B 27S/930 PSU-E WB BK	Black
910505101585	RS771B 39S/827 PSU-E WB SI	Silver

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910505101566	RS771B 17S/930 PSU-E HWB WH	(0.434,0.403)<2
910505101570	RS771B 19S/ROSE PSU-E HWB FG WH	(0.478,0.382)<2




Order Code	Full Product Name	Initial chromaticity
910505101571	RS771B 19S/FMT PSU-E HWB FG WH	(0.457,0.385)<3
910505101572	RS771B 20S/830 PSU-E NB WH	(0.434,0.403)<3

LuxSpace Accent Compact Adjustable


Order Code	Full Product Name	Initial chromaticity
910505101573	RS771B 27S/827 PSU-E WB WH	(0.458,0.410)<3
910505101574	RS771B 27S/830 PSU-E MB WH	(0.434,0.403)<3
910505101575	RS771B 27S/830 DIA-VLC-E HMB WH	(0.434,0.403)<3
910505101576	RS771B 27S/830 WIA-E MB WH	(0.434,0.403)<3
910505101577	RS771B 27S/840 PSU-E WB WH	(0.382,0.380)<3
910505101579	RS771B 27S/PW930 PSU-E HWB WH	(0.422,0.386)<2
910505101580	RS771B 27S/PC930 PSU-E HWB WH	(0.422,0.386)<2
910505101581	RS771B 27S/ROSE PSU-E HWB FG WH	(0.478,0.382)<2
910505101582	RS771B 27S/FMT PSU-E HWB FG WH	(0.457,0.385)<3
910505101583	RS771B 27S/CH PSU-E HWB FG WH	(0.458,0.410)<3
910505101584	RS771B 27S/FR PSU-E HWB FG WH	(0.343,0.331)<3

Order Code	Full Product Name	Initial chromaticity
910505101586	RS771B 39S/830 PSU-E VWB WH	(0.434,0.403)<3
910505101587	RS771B 39S/840 PSU-E WB WH	(0.382,0.380)<3
910505101588	RS771B 39S/930 PSU-E WB WH	(0.434,0.403)<2
910505101589	RS771B 39S/PW930 PSU-E WB WH	(0.422,0.386)<2
910505101590	RS771B 49S/827 PSU-E HWB WH	(0.458,0.410)<3
910505101591	RS771B 49S/830 PSU-E HWB WH	(0.434,0.403)<3
910505101592	RS771B 49S/840 PSU-E HWB WH	(0.382,0.380)<3
910505101593	RS771B 49S/930 PSU-E HWB WH	(0.434,0.403)<2
910505101594	RS771B 49S/PW930 PSU-E HWB WH	(0.422,0.386)<2
910505101578	RS771B 27S/930 PSU-E WB BK	(0.434,0.403)<2
910505101585	RS771B 39S/827 PSU-E WB SI	(0.458,0.410)<3


Polar Wide Diagrams




Polar Normal (separate) - RS770BI - 910505101575



Polar Normal (separate) - RS770BI - 910505101576



Polar Normal (separate) - RS770BI - 910505101577



Polar Normal (separate) - RS770BI - 910505101581



Polar Normal (separate) - RS770BI - 910505101582




Polar Normal (separate) - RS770BI - 910505101572




LuxSpace Accent Compact Adjustable


Polar Wide Diagrams




Polar Normal (separate) - RS770BI - 910505101585




Polar Normal (separate) - RS770BI - 910505101586




Polar Normal (separate) - RS770BI - 910505101584




Polar Normal (separate) - RS770BI - 910505101579




Polar Normal (separate) - RS770BI - 910505101589




Polar Normal (separate) - RS770BI - 910505101593



Polar Normal (separate) - RS770BI - 910505101591




Polar Normal (separate) - RS770BI - 910505101580




Polar Normal (separate) - RS770BI - 910505101573

LuxSpace Accent Compact Adjustable


Polar Wide Diagrams




Polar Normal (separate) - RS770BI - 910505101587




Polar Normal (separate) - RS770BI - 910505101583




Polar Normal (separate) - RS770BI - 910505101592




Polar Normal (separate) - RS770BI - 910505101578




Polar Normal (separate) - RS770BI - 910505101566




Polar Normal (separate) - RS770BI - 910505101571



Polar Normal (separate) - RS770BI - 910505101588




Polar Normal (separate) - RS770BI - 910505101594




Polar Normal (separate) - RS770BI - 910505101574

LuxSpace Accent Compact Adjustable

Polar Wide Diagrams



**Polar Normal (separate) - RS770BI -
910505101570**



**Polar Normal (separate) - RS770BI -
910505101590**

