



Elegant, Comprehensive and Affordable

GreenSpace Surface Mount

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenSpace Surface Mount is the entry level downlight family dedicated with suspension and surface mount versions, which offers a complete range of options for optical solutions, lumen outputs and color temperatures with multiple form factors available.

Benefits

- Elegant look & feel.
- Complete family with multiple installations and form factors.
- Good glare control with color rendering performance.
- Ensured quality and reliability.

Features








- Both round and square version available.
- Both suspension and surface mount version available.
- UGR19 & CRI90, SDCM \leq 3
- Wide range of lumen packages, beam angles and color temperatures available.

Application

- Retail
- Hospitality
- Fashion

GreenSpace Surface Mount

Dimensional drawing



GreenSpace Surface Mount

Light Technical

Color rendering index (CRI)	>90
Operating and Electrical	
Protection class IEC	Safety class II
Line Frequency	50 to 60 Hz
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Optical cover type	Acrylate
Housing Color	White
Mech. impact protection code	IK03
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	-20 to +40 °C
CE mark	No
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

Light Technical

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux
		Temperature (Nom)	(rated) (Nom)	
911401592012	SP303P P6 940 PSU NB	4000 K	80 lm/W	480 lm
911401592112	SP303P P6 940 PSU MB	4000 K	89 lm/W	530 lm
911401592212	SP303P P6 940 PSU WB	4000 K	94 lm/W	560 lm
911401592312	SP303P P6 940 PSU VWB	4000 K	91 lm/W	550 lm
911401592412	SP303P P6 950 PSU NB	5000 K	81 lm/W	490 lm
911401592512	SP303P P6 950 PSU MB	5000 K	90 lm/W	540 lm
911401592612	SP303P P6 950 PSU WB	5000 K	97 lm/W	580 lm
911401592712	SP303P P6 950 PSU VWB	5000 K	93 lm/W	560 lm
911401594812	SP303P P9 927 PSU NB	2700 K	72 lm/W	650 lm
911401594912	SP303P P9 927 PSU MB	2700 K	80 lm/W	720 lm
911401595012	SP303P P9 927 PSU WB	2700 K	85 lm/W	770 lm
911401595112	SP303P P9 927 PSU VWB	2700 K	81 lm/W	730 lm
911401595212	SP303P P9 930 PSU NB	3000 K	75 lm/W	680 lm
911401595312	SP303P P9 930 PSU MB	3000 K	83 lm/W	750 lm
911401595412	SP303P P9 930 PSU WB	3000 K	87 lm/W	780 lm
911401595512	SP303P P9 930 PSU VWB	3000 K	84 lm/W	760 lm
911401596012	SP303P P9 940 PSU NB	4000 K	77 lm/W	690 lm
911401596112	SP303P P9 940 PSU MB	4000 K	85 lm/W	770 lm
911401596212	SP303P P9 940 PSU WB	4000 K	90 lm/W	810 lm
911401596312	SP303P P9 940 PSU VWB	4000 K	87 lm/W	780 lm
911401596412	SP303P P9 950 PSU NB	5000 K	78 lm/W	700 lm
911401596512	SP303P P9 950 PSU MB	5000 K	87 lm/W	780 lm
911401596612	SP303P P9 950 PSU WB	5000 K	93 lm/W	840 lm
911401596712	SP303P P9 950 PSU VWB	5000 K	89 lm/W	800 lm
911401598812	SP303P P6S 927 PSU NB	2700 K	76 lm/W	460 lm
911401598912	SP303P P6S 927 PSU MB	2700 K	84 lm/W	500 lm
911401599012	SP303P P6S 927 PSU WB	2700 K	89 lm/W	530 lm
911401599112	SP303P P6S 927 PSU VWB	2700 K	84 lm/W	500 lm
911401599212	SP303P P6S 930 PSU NB	3000 K	77 lm/W	460 lm
911401599312	SP303P P6S 930 PSU MB	3000 K	86 lm/W	520 lm
911401599412	SP303P P6S 930 PSU WB	3000 K	91 lm/W	550 lm
911401599512	SP303P P6S 930 PSU VWB	3000 K	87 lm/W	520 lm
911401500022	SP303P P6S 940 PSU NB	4000 K	80 lm/W	480 lm
911401500122	SP303P P6S 940 PSU MB	4000 K	89 lm/W	530 lm
911401500222	SP303P P6S 940 PSU WB	4000 K	94 lm/W	560 lm
911401500322	SP303P P6S 940 PSU VWB	4000 K	91 lm/W	550 lm
911401500422	SP303P P6S 950 PSU NB	5000 K	81 lm/W	490 lm
911401500522	SP303P P6S 950 PSU MB	5000 K	90 lm/W	540 lm
911401500622	SP303P P6S 950 PSU WB	5000 K	97 lm/W	580 lm
911401500722	SP303P P6S 950 PSU VWB	5000 K	93 lm/W	560 lm
911401502822	SP303P P9S 927 PSU NB	2700 K	72 lm/W	650 lm
911401502922	SP303P P9S 927 PSU MB	2700 K	80 lm/W	720 lm
911401503022	SP303P P9S 927 PSU WB	2700 K	85 lm/W	770 lm
911401503122	SP303P P9S 927 PSU VWB	2700 K	81 lm/W	730 lm
911401503222	SP303P P9S 930 PSU NB	3000 K	75 lm/W	680 lm
911401503322	SP303P P9S 930 PSU MB	3000 K	83 lm/W	750 lm
911401503422	SP303P P9S 930 PSU WB	3000 K	87 lm/W	780 lm
911401503522	SP303P P9S 930 PSU VWB	3000 K	84 lm/W	760 lm
911401504022	SP303P P9S 940 PSU NB	4000 K	77 lm/W	690 lm
911401504122	SP303P P9S 940 PSU MB	4000 K	85 lm/W	770 lm

GreenSpace Surface Mount

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	
		Temperature (Nom)	(rated) (Nom)	Luminous Flux
911401504222	SP303P P9S 940 PSU WB	4000 K	90 lm/W	810 lm
911401504322	SP303P P9S 940 PSU VWB	4000 K	87 lm/W	780 lm
911401504422	SP303P P9S 950 PSU NB	5000 K	78 lm/W	700 lm
911401504522	SP303P P9S 950 PSU MB	5000 K	87 lm/W	780 lm
911401504622	SP303P P9S 950 PSU WB	5000 K	93 lm/W	840 lm
911401504722	SP303P P9S 950 PSU VWB	5000 K	89 lm/W	800 lm
911401590812	SP303P P6 927 PSU NB	2700 K	76 lm/W	460 lm
911401590912	SP303P P6 927 PSU MB	2700 K	84 lm/W	500 lm
911401591012	SP303P P6 927 PSU WB	2700 K	89 lm/W	530 lm
911401591112	SP303P P6 927 PSU VWB	2700 K	84 lm/W	500 lm
911401591212	SP303P P6 930 PSU NB	3000 K	77 lm/W	460 lm
911401591312	SP303P P6 930 PSU MB	3000 K	86 lm/W	520 lm
911401591412	SP303P P6 930 PSU WB	3000 K	91 lm/W	550 lm
911401591512	SP303P P6 930 PSU VWB	3000 K	87 lm/W	520 lm
911401510822	SM303C P24 927 PSU NB	2700 K	86 lm/W	2,060 lm
911401510922	SM303C P24 927 PSU MB	2700 K	87 lm/W	2,090 lm
911401511022	SM303C P24 927 PSU WB	2700 K	88 lm/W	2,110 lm
911401511122	SM303C P24 927 PSU VWB	2700 K	87 lm/W	2,090 lm
911401511222	SM303C P24 930 PSU NB	3000 K	94 lm/W	2,260 lm
911401511322	SM303C P24 930 PSU MB	3000 K	93 lm/W	2,230 lm
911401511422	SM303C P24 930 PSU WB	3000 K	94 lm/W	2,260 lm
911401511522	SM303C P24 930 PSU VWB	3000 K	94 lm/W	2,260 lm
911401512022	SM303C P24 940 PSU NB	4000 K	100 lm/W	2,400 lm
911401512122	SM303C P24 940 PSU MB	4000 K	101 lm/W	2,420 lm
911401512222	SM303C P24 940 PSU WB	4000 K	102 lm/W	2,450 lm
911401512422	SM303C P24 950 PSU NB	5000 K	98 lm/W	2,350 lm
911401512522	SM303C P24 950 PSU MB	5000 K	99 lm/W	2,380 lm
911401512622	SM303C P24 950 PSU WB	5000 K	100 lm/W	2,400 lm
911401512722	SM303C P24 950 PSU VWB	5000 K	99 lm/W	2,380 lm
911401514822	SM303C P28 927 PSU NB	2700 K	83 lm/W	2,320 lm
911401514922	SM303C P28 927 PSU MB	2700 K	83 lm/W	2,320 lm
911401515022	SM303C P28 927 PSU WB	2700 K	84 lm/W	2,350 lm
911401515122	SM303C P28 927 PSU VWB	2700 K	83 lm/W	2,320 lm
911401515222	SM303C P28 930 PSU NB	3000 K	89 lm/W	2,490 lm
911401515322	SM303C P28 930 PSU MB	3000 K	88 lm/W	2,460 lm
911401515422	SM303C P28 930 PSU WB	3000 K	89 lm/W	2,490 lm
911401515522	SM303C P28 930 PSU VWB	3000 K	88 lm/W	2,460 lm
911401516022	SM303C P28 940 PSU NB	4000 K	97 lm/W	2,720 lm
911401516122	SM303C P28 940 PSU MB	4000 K	96 lm/W	2,690 lm
911401516222	SM303C P28 940 PSU WB	4000 K	98 lm/W	2,740 lm
911401516322	SM303C P28 940 PSU VWB	4000 K	96 lm/W	2,690 lm
911401516422	SM303C P28 950 PSU NB	5000 K	95 lm/W	2,660 lm
911401516522	SM303C P28 950 PSU MB	5000 K	94 lm/W	2,630 lm
911401516622	SM303C P28 950 PSU WB	5000 K	96 lm/W	2,690 lm
911401516722	SM303C P28 950 PSU VWB	5000 K	96 lm/W	2,690 lm
911401547932	SM303C P24 940 PSU VWB	4000 K	95 lm/W	2,280 lm
911401517822	SM304C P10 927 PSU MB	2700 K	71 lm/W	730 lm
911401517922	SM304C P10 927 PSU WB	2700 K	75 lm/W	770 lm
911401518022	SM304C P10 930 PSU MB	3000 K	76 lm/W	770 lm
911401518122	SM304C P10 930 PSU WB	3000 K	78 lm/W	810 lm
911401518422	SM304C P10 940 PSU MB	4000 K	80 lm/W	810 lm

GreenSpace Surface Mount

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux
		Temperature (Nom)	(rated) (Nom)	
911401518522	SM304C P10 940 PSU WB	4000 K	83 lm/W	860 lm
911401518622	SM304C P10 950 PSU MB	5000 K	86 lm/W	870 lm
911401518722	SM304C P10 950 PSU WB	5000 K	88 lm/W	890 lm
911401519822	SM304C P12 927 PSU MB	2700 K	70 lm/W	860 lm
911401519922	SM304C P12 927 PSU WB	2700 K	73 lm/W	890 lm
911401520022	SM304C P12 930 PSU MB	3000 K	75 lm/W	910 lm
911401520122	SM304C P12 930 PSU WB	3000 K	77 lm/W	940 lm
911401520422	SM304C P12 940 PSU MB	4000 K	78 lm/W	950 lm
911401520522	SM304C P12 940 PSU WB	4000 K	81 lm/W	990 lm
911401520622	SM304C P12 950 PSU MB	5000 K	84 lm/W	1,010 lm
911401520722	SM304C P12 950 PSU WB	5000 K	86 lm/W	1,050 lm
911401521822	SM304C P15 927 PSU MB	2700 K	70 lm/W	1,050 lm
911401521922	SM304C P15 927 PSU WB	2700 K	73 lm/W	1,100 lm
911401522022	SM304C P15 930 PSU MB	3000 K	75 lm/W	1,130 lm
911401522122	SM304C P15 930 PSU WB	3000 K	78 lm/W	1,170 lm
911401522422	SM304C P15 940 PSU MB	4000 K	78 lm/W	1,170 lm
911401522522	SM304C P15 940 PSU WB	4000 K	82 lm/W	1,230 lm
911401522622	SM304C P15 950 PSU MB	5000 K	84 lm/W	1,260 lm
911401522722	SM304C P15 950 PSU WB	5000 K	88 lm/W	1,320 lm
911401582812	SM303C P6S 927 PSU NB	2700 K	76 lm/W	460 lm
911401582912	SM303C P6S 927 PSU MB	2700 K	84 lm/W	500 lm
911401583012	SM303C P6S 927 PSU WB	2700 K	89 lm/W	530 lm
911401583112	SM303C P6S 927 PSU VWB	2700 K	84 lm/W	500 lm
911401583212	SM303C P6S 930 PSU NB	3000 K	77 lm/W	460 lm
911401583312	SM303C P6S 930 PSU MB	3000 K	86 lm/W	520 lm
911401583412	SM303C P6S 930 PSU WB	3000 K	91 lm/W	550 lm
911401583512	SM303C P6S 930 PSU VWB	3000 K	87 lm/W	520 lm
911401584012	SM303C P6S 940 PSU NB	4000 K	80 lm/W	480 lm
911401584112	SM303C P6S 940 PSU MB	4000 K	89 lm/W	530 lm
911401584212	SM303C P6S 940 PSU WB	4000 K	94 lm/W	560 lm
911401584312	SM303C P6S 940 PSU VWB	4000 K	91 lm/W	550 lm
911401584412	SM303C P6S 950 PSU NB	5000 K	81 lm/W	490 lm
911401584512	SM303C P6S 950 PSU MB	5000 K	90 lm/W	540 lm
911401584612	SM303C P6S 950 PSU WB	5000 K	97 lm/W	580 lm
911401584712	SM303C P6S 950 PSU VWB	5000 K	93 lm/W	560 lm
911401586812	SM303C P9S 927 PSU NB	2700 K	72 lm/W	650 lm
911401586912	SM303C P9S 927 PSU MB	2700 K	80 lm/W	720 lm
911401587012	SM303C P9S 927 PSU WB	2700 K	85 lm/W	770 lm
911401587112	SM303C P9S 927 PSU VWB	2700 K	81 lm/W	730 lm
911401587212	SM303C P9S 930 PSU NB	3000 K	75 lm/W	680 lm
911401587312	SM303C P9S 930 PSU MB	3000 K	83 lm/W	750 lm
911401587412	SM303C P9S 930 PSU WB	3000 K	87 lm/W	780 lm
911401587512	SM303C P9S 930 PSU VWB	3000 K	84 lm/W	760 lm
911401588012	SM303C P9S 940 PSU NB	4000 K	77 lm/W	690 lm
911401588112	SM303C P9S 940 PSU MB	4000 K	85 lm/W	770 lm
911401588212	SM303C P9S 940 PSU WB	4000 K	90 lm/W	810 lm

GreenSpace Surface Mount

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux
		Temperature (Nom)	(rated) (Nom)	
911401588312	SM303C P9S 940 PSU VWB	4000 K	87 lm/W	780 lm
911401588412	SM303C P9S 950 PSU NB	5000 K	78 lm/W	700 lm
911401588512	SM303C P9S 950 PSU MB	5000 K	87 lm/W	780 lm
911401588612	SM303C P9S 950 PSU WB	5000 K	93 lm/W	840 lm
911401588712	SM303C P9S 950 PSU VWB	5000 K	89 lm/W	800 lm
911401506822	SM303C P20 927 PSU NB	2700 K	80 lm/W	1,600 lm
911401506922	SM303C P20 927 PSU MB	2700 K	80 lm/W	1,600 lm
911401507022	SM303C P20 927 PSU WB	2700 K	81 lm/W	1,620 lm
911401507122	SM303C P20 927 PSU VWB	2700 K	81 lm/W	1,620 lm
911401507222	SM303C P20 930 PSU NB	3000 K	88 lm/W	1,760 lm
911401507322	SM303C P20 930 PSU MB	3000 K	88 lm/W	1,760 lm
911401507422	SM303C P20 930 PSU WB	3000 K	90 lm/W	1,800 lm
911401507522	SM303C P20 930 PSU VWB	3000 K	89 lm/W	1,780 lm
911401508022	SM303C P20 940 PSU NB	4000 K	99 lm/W	1,980 lm
911401508122	SM303C P20 940 PSU MB	4000 K	99 lm/W	1,980 lm
911401508222	SM303C P20 940 PSU WB	4000 K	100 lm/W	2,000 lm
911401508322	SM303C P20 940 PSU VWB	4000 K	100 lm/W	2,000 lm
911401508422	SM303C P20 950 PSU NB	5000 K	102 lm/W	2,040 lm
911401508522	SM303C P20 950 PSU MB	5000 K	102 lm/W	2,040 lm
911401547832	SM303C P20 950 PSU WB	5000 K	90 lm/W	1,800 lm
911401574812	SM303C P6 927 PSU NB	2700 K	76 lm/W	460 lm
911401574912	SM303C P6 927 PSU MB	2700 K	84 lm/W	500 lm
911401575012	SM303C P6 927 PSU WB	2700 K	89 lm/W	530 lm
911401575112	SM303C P6 927 PSU VWB	2700 K	84 lm/W	500 lm
911401575212	SM303C P6 930 PSU NB	3000 K	77 lm/W	460 lm
911401575312	SM303C P6 930 PSU MB	3000 K	86 lm/W	520 lm
911401575412	SM303C P6 930 PSU WB	3000 K	91 lm/W	550 lm
911401575512	SM303C P6 930 PSU VWB	3000 K	87 lm/W	520 lm
911401576012	SM303C P6 940 PSU NB	4000 K	80 lm/W	480 lm
911401576112	SM303C P6 940 PSU MB	4000 K	89 lm/W	530 lm
911401576212	SM303C P6 940 PSU WB	4000 K	94 lm/W	560 lm
911401576312	SM303C P6 940 PSU VWB	4000 K	91 lm/W	550 lm
911401576412	SM303C P6 950 PSU NB	5000 K	81 lm/W	490 lm
911401576512	SM303C P6 950 PSU MB	5000 K	90 lm/W	540 lm
911401576612	SM303C P6 950 PSU WB	5000 K	97 lm/W	580 lm
911401576712	SM303C P6 950 PSU VWB	5000 K	93 lm/W	560 lm
911401578812	SM303C P9 927 PSU NB	2700 K	72 lm/W	650 lm
911401578912	SM303C P9 927 PSU MB	2700 K	80 lm/W	720 lm
911401579012	SM303C P9 927 PSU WB	2700 K	85 lm/W	770 lm
911401579112	SM303C P9 927 PSU VWB	2700 K	81 lm/W	730 lm
911401579212	SM303C P9 930 PSU NB	3000 K	75 lm/W	680 lm
911401579312	SM303C P9 930 PSU MB	3000 K	83 lm/W	750 lm
911401579412	SM303C P9 930 PSU WB	3000 K	87 lm/W	780 lm
911401579512	SM303C P9 930 PSU VWB	3000 K	84 lm/W	760 lm
911401580012	SM303C P9 940 PSU NB	4000 K	77 lm/W	690 lm
911401580112	SM303C P9 940 PSU MB	4000 K	85 lm/W	770 lm
911401580212	SM303C P9 940 PSU WB	4000 K	90 lm/W	810 lm

GreenSpace Surface Mount

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux
		Temperature (Nom)	(rated) (Nom)	
911401580312	SM303C P9 940 PSU VWB	4000 K	87 lm/W	780 lm
911401580412	SM303C P9 950 PSU NB	5000 K	78 lm/W	700 lm
911401580512	SM303C P9 950 PSU MB	5000 K	87 lm/W	780 lm
911401580612	SM303C P9 950 PSU WB	5000 K	93 lm/W	840 lm
911401580712	SM303C P9 950 PSU VWB	5000 K	89 lm/W	800 lm

Operating and Electrical

Order Code	Full Product Name	Input Voltage	Power Consumption	Order Code	Full Product Name	Input Voltage	Power Consumption
911401592012	SP303P P6 940 PSU NB	200 to 240 V	5.4 W	911401503022	SP303P P9S 927 PSU WB	200 to 240 V	8.1 W
911401592112	SP303P P6 940 PSU MB	200 to 240 V	5.4 W	911401503122	SP303P P9S 927 PSU VWB	200 to 240 V	8.1 W
911401592212	SP303P P6 940 PSU WB	200 to 240 V	5.4 W	911401503222	SP303P P9S 930 PSU NB	200 to 240 V	8.1 W
911401592312	SP303P P6 940 PSU VWB	200 to 240 V	5.4 W	911401503322	SP303P P9S 930 PSU MB	200 to 240 V	8.1 W
911401592412	SP303P P6 950 PSU NB	200 to 240 V	5.4 W	911401503422	SP303P P9S 930 PSU WB	200 to 240 V	8.1 W
911401592512	SP303P P6 950 PSU MB	200 to 240 V	5.4 W	911401503522	SP303P P9S 930 PSU VWB	200 to 240 V	8.1 W
911401592612	SP303P P6 950 PSU WB	200 to 240 V	5.4 W	911401504022	SP303P P9S 940 PSU NB	200 to 240 V	8.1 W
911401592712	SP303P P6 950 PSU VWB	200 to 240 V	5.4 W	911401504122	SP303P P9S 940 PSU MB	200 to 240 V	8.1 W
911401594812	SP303P P9 927 PSU NB	200 to 240 V	8.1 W	911401504222	SP303P P9S 940 PSU WB	200 to 240 V	8.1 W
911401594912	SP303P P9 927 PSU MB	200 to 240 V	8.1 W	911401504322	SP303P P9S 940 PSU VWB	200 to 240 V	8.1 W
911401595012	SP303P P9 927 PSU WB	200 to 240 V	8.1 W	911401504422	SP303P P9S 950 PSU NB	200 to 240 V	8.1 W
911401595112	SP303P P9 927 PSU VWB	200 to 240 V	8.1 W	911401504522	SP303P P9S 950 PSU MB	200 to 240 V	8.1 W
911401595212	SP303P P9 930 PSU NB	200 to 240 V	8.1 W	911401504622	SP303P P9S 950 PSU WB	200 to 240 V	8.1 W
911401595312	SP303P P9 930 PSU MB	200 to 240 V	8.1 W	911401504722	SP303P P9S 950 PSU VWB	200 to 240 V	8.1 W
911401595412	SP303P P9 930 PSU WB	200 to 240 V	8.1 W	911401590812	SP303P P6 927 PSU NB	200 to 240 V	5.4 W
911401595512	SP303P P9 930 PSU VWB	200 to 240 V	8.1 W	911401590912	SP303P P6 927 PSU MB	200 to 240 V	5.4 W
911401596012	SP303P P9 940 PSU NB	200 to 240 V	8.1 W	911401591012	SP303P P6 927 PSU WB	200 to 240 V	5.4 W
911401596112	SP303P P9 940 PSU MB	200 to 240 V	8.1 W	911401591112	SP303P P6 927 PSU VWB	200 to 240 V	5.4 W
911401596212	SP303P P9 940 PSU WB	200 to 240 V	8.1 W	911401591212	SP303P P6 930 PSU NB	200 to 240 V	5.4 W
911401596312	SP303P P9 940 PSU VWB	200 to 240 V	8.1 W	911401591312	SP303P P6 930 PSU MB	200 to 240 V	5.4 W
911401596412	SP303P P9 950 PSU NB	200 to 240 V	8.1 W	911401591412	SP303P P6 930 PSU WB	200 to 240 V	5.4 W
911401596512	SP303P P9 950 PSU MB	200 to 240 V	8.1 W	911401591512	SP303P P6 930 PSU VWB	200 to 240 V	5.4 W
911401596612	SP303P P9 950 PSU WB	200 to 240 V	8.1 W	911401510822	SM303C P24 927 PSU NB	200 to 240 V	21.6 W
911401596712	SP303P P9 950 PSU VWB	200 to 240 V	8.1 W	911401510922	SM303C P24 927 PSU MB	200 to 240 V	21.6 W
911401598812	SP303P P6S 927 PSU NB	200 to 240 V	5.4 W	911401511022	SM303C P24 927 PSU WB	200 to 240 V	21.6 W
911401598912	SP303P P6S 927 PSU MB	200 to 240 V	5.4 W	911401511122	SM303C P24 927 PSU VWB	200 to 240 V	21.6 W
911401599012	SP303P P6S 927 PSU WB	200 to 240 V	5.4 W	911401511222	SM303C P24 930 PSU NB	200 to 240 V	21.6 W
911401599112	SP303P P6S 927 PSU VWB	200 to 240 V	5.4 W	911401511322	SM303C P24 930 PSU MB	200 to 240 V	21.6 W
911401599212	SP303P P6S 930 PSU NB	200 to 240 V	5.4 W	911401511422	SM303C P24 930 PSU WB	200 to 240 V	21.6 W
911401599312	SP303P P6S 930 PSU MB	200 to 240 V	5.4 W	911401511522	SM303C P24 930 PSU VWB	200 to 240 V	21.6 W
911401599412	SP303P P6S 930 PSU WB	200 to 240 V	5.4 W	911401512022	SM303C P24 940 PSU NB	200 to 240 V	21.6 W
911401599512	SP303P P6S 930 PSU VWB	200 to 240 V	5.4 W	911401512122	SM303C P24 940 PSU MB	200 to 240 V	21.6 W
911401500022	SP303P P6S 940 PSU NB	200 to 240 V	5.4 W	911401512222	SM303C P24 940 PSU WB	200 to 240 V	21.6 W
911401500122	SP303P P6S 940 PSU MB	200 to 240 V	5.4 W	911401512422	SM303C P24 950 PSU NB	200 to 240 V	21.6 W
911401500222	SP303P P6S 940 PSU WB	200 to 240 V	5.4 W	911401512522	SM303C P24 950 PSU MB	200 to 240 V	21.6 W
911401500322	SP303P P6S 940 PSU VWB	200 to 240 V	5.4 W	911401512622	SM303C P24 950 PSU WB	200 to 240 V	21.6 W
911401500422	SP303P P6S 950 PSU NB	200 to 240 V	5.4 W	911401512722	SM303C P24 950 PSU VWB	200 to 240 V	21.6 W
911401500522	SP303P P6S 950 PSU MB	200 to 240 V	5.4 W	911401514822	SM303C P28 927 PSU NB	200 to 240 V	25.2 W
911401500622	SP303P P6S 950 PSU WB	200 to 240 V	5.4 W	911401514922	SM303C P28 927 PSU MB	200 to 240 V	25.2 W
911401500722	SP303P P6S 950 PSU VWB	200 to 240 V	5.4 W	911401515022	SM303C P28 927 PSU WB	200 to 240 V	25.2 W
911401502822	SP303P P9S 927 PSU NB	200 to 240 V	8.1 W	911401515122	SM303C P28 927 PSU VWB	200 to 240 V	25.2 W
911401502922	SP303P P9S 927 PSU MB	200 to 240 V	8.1 W	911401515222	SM303C P28 930 PSU NB	200 to 240 V	25.2 W

GreenSpace Surface Mount

Order Code	Full Product Name	Input Voltage	Power Consumption	Order Code	Full Product Name	Input Voltage	Power Consumption
911401515322	SM303C P28 930 PSU MB	200 to 240 V	25.2 W	911401586812	SM303C P9S 927 PSU NB	200 to 240 V	8.1 W
911401515422	SM303C P28 930 PSU WB	200 to 240 V	25.2 W	911401586912	SM303C P9S 927 PSU MB	200 to 240 V	8.1 W
911401515522	SM303C P28 930 PSU VWB	200 to 240 V	25.2 W	911401587012	SM303C P9S 927 PSU WB	200 to 240 V	8.1 W
911401516022	SM303C P28 940 PSU NB	200 to 240 V	25.2 W	911401587112	SM303C P9S 927 PSU VWB	200 to 240 V	8.1 W
911401516122	SM303C P28 940 PSU MB	200 to 240 V	25.2 W	911401587212	SM303C P9S 930 PSU NB	200 to 240 V	8.1 W
911401516222	SM303C P28 940 PSU WB	200 to 240 V	25.2 W	911401587312	SM303C P9S 930 PSU MB	200 to 240 V	8.1 W
911401516322	SM303C P28 940 PSU VWB	200 to 240 V	25.2 W	911401587412	SM303C P9S 930 PSU WB	200 to 240 V	8.1 W
911401516422	SM303C P28 950 PSU NB	200 to 240 V	25.2 W	911401587512	SM303C P9S 930 PSU VWB	200 to 240 V	8.1 W
911401516522	SM303C P28 950 PSU MB	200 to 240 V	25.2 W	911401588012	SM303C P9S 940 PSU NB	200 to 240 V	8.1 W
911401516622	SM303C P28 950 PSU WB	200 to 240 V	25.2 W	911401588112	SM303C P9S 940 PSU MB	200 to 240 V	8.1 W
911401516722	SM303C P28 950 PSU VWB	200 to 240 V	25.2 W	911401588212	SM303C P9S 940 PSU WB	200 to 240 V	8.1 W
911401547932	SM303C P24 940 PSU VWB	220-240 V	24 W	911401588312	SM303C P9S 940 PSU VWB	200 to 240 V	8.1 W
911401517822	SM304C P10 927 PSU MB	200 to 240 V	11 W	911401588412	SM303C P9S 950 PSU NB	200 to 240 V	8.1 W
911401517922	SM304C P10 927 PSU WB	200 to 240 V	11 W	911401588512	SM303C P9S 950 PSU MB	200 to 240 V	8.1 W
911401518022	SM304C P10 930 PSU MB	200 to 240 V	11 W	911401588612	SM303C P9S 950 PSU WB	200 to 240 V	8.1 W
911401518122	SM304C P10 930 PSU WB	200 to 240 V	11 W	911401588712	SM303C P9S 950 PSU VWB	200 to 240 V	8.1 W
911401518422	SM304C P10 940 PSU MB	200 to 240 V	11 W	911401506822	SM303C P20 927 PSU NB	200 to 240 V	18 W
911401518522	SM304C P10 940 PSU WB	200 to 240 V	11 W	911401506922	SM303C P20 927 PSU MB	200 to 240 V	18 W
911401518622	SM304C P10 950 PSU MB	200 to 240 V	11 W	911401507022	SM303C P20 927 PSU WB	200 to 240 V	18 W
911401518722	SM304C P10 950 PSU WB	200 to 240 V	11 W	911401507122	SM303C P20 927 PSU VWB	200 to 240 V	18 W
911401519822	SM304C P12 927 PSU MB	200 to 240 V	10.8 W	911401507222	SM303C P20 930 PSU NB	200 to 240 V	18 W
911401519922	SM304C P12 927 PSU WB	200 to 240 V	10.8 W	911401507322	SM303C P20 930 PSU MB	200 to 240 V	18 W
911401520022	SM304C P12 930 PSU MB	200 to 240 V	10.8 W	911401507422	SM303C P20 930 PSU WB	200 to 240 V	18 W
911401520122	SM304C P12 930 PSU WB	200 to 240 V	10.8 W	911401507522	SM303C P20 930 PSU VWB	200 to 240 V	18 W
911401520422	SM304C P12 940 PSU MB	200 to 240 V	10.8 W	911401508022	SM303C P20 940 PSU NB	200 to 240 V	18 W
911401520522	SM304C P12 940 PSU WB	200 to 240 V	10.8 W	911401508122	SM303C P20 940 PSU MB	200 to 240 V	18 W
911401520622	SM304C P12 950 PSU MB	200 to 240 V	10.8 W	911401508222	SM303C P20 940 PSU WB	200 to 240 V	18 W
911401520722	SM304C P12 950 PSU WB	200 to 240 V	10.8 W	911401508322	SM303C P20 940 PSU VWB	200 to 240 V	18 W
911401521822	SM304C P15 927 PSU MB	200 to 240 V	13.5 W	911401508422	SM303C P20 950 PSU NB	200 to 240 V	18 W
911401521922	SM304C P15 927 PSU WB	200 to 240 V	13.5 W	911401508522	SM303C P20 950 PSU MB	200 to 240 V	18 W
911401522022	SM304C P15 930 PSU MB	200 to 240 V	13.5 W	911401547832	SM303C P20 950 PSU WB	220-240 V	20 W
911401522122	SM304C P15 930 PSU WB	200 to 240 V	13.5 W	911401574812	SM303C P6 927 PSU NB	200 to 240 V	5.4 W
911401522422	SM304C P15 940 PSU MB	200 to 240 V	13.5 W	911401574912	SM303C P6 927 PSU MB	200 to 240 V	5.4 W
911401522522	SM304C P15 940 PSU WB	200 to 240 V	13.5 W	911401575012	SM303C P6 927 PSU WB	200 to 240 V	5.4 W
911401522622	SM304C P15 950 PSU MB	200 to 240 V	13.5 W	911401575112	SM303C P6 927 PSU VWB	200 to 240 V	5.4 W
911401522722	SM304C P15 950 PSU WB	200 to 240 V	13.5 W	911401575212	SM303C P6 930 PSU NB	200 to 240 V	5.4 W
911401582812	SM303C P6S 927 PSU NB	200 to 240 V	5.4 W	911401575312	SM303C P6 930 PSU MB	200 to 240 V	5.4 W
911401582912	SM303C P6S 927 PSU MB	200 to 240 V	5.4 W	911401575412	SM303C P6 930 PSU WB	200 to 240 V	5.4 W
911401583012	SM303C P6S 927 PSU WB	200 to 240 V	5.4 W	911401575512	SM303C P6 930 PSU VWB	200 to 240 V	5.4 W
911401583112	SM303C P6S 927 PSU VWB	200 to 240 V	5.4 W	911401576012	SM303C P6 940 PSU NB	200 to 240 V	5.4 W
911401583212	SM303C P6S 930 PSU NB	200 to 240 V	5.4 W	911401576112	SM303C P6 940 PSU MB	200 to 240 V	5.4 W
911401583312	SM303C P6S 930 PSU MB	200 to 240 V	5.4 W	911401576212	SM303C P6 940 PSU WB	200 to 240 V	5.4 W
911401583412	SM303C P6S 930 PSU WB	200 to 240 V	5.4 W	911401576312	SM303C P6 940 PSU VWB	200 to 240 V	5.4 W
911401583512	SM303C P6S 930 PSU VWB	200 to 240 V	5.4 W	911401576412	SM303C P6 950 PSU NB	200 to 240 V	5.4 W
911401584012	SM303C P6S 940 PSU NB	200 to 240 V	5.4 W	911401576512	SM303C P6 950 PSU MB	200 to 240 V	5.4 W
911401584112	SM303C P6S 940 PSU MB	200 to 240 V	5.4 W	911401576612	SM303C P6 950 PSU WB	200 to 240 V	5.4 W
911401584212	SM303C P6S 940 PSU WB	200 to 240 V	5.4 W	911401576712	SM303C P6 950 PSU VWB	200 to 240 V	5.4 W
911401584312	SM303C P6S 940 PSU VWB	200 to 240 V	5.4 W	911401578812	SM303C P9 927 PSU NB	200 to 240 V	8.1 W
911401584412	SM303C P6S 950 PSU NB	200 to 240 V	5.4 W	911401578912	SM303C P9 927 PSU MB	200 to 240 V	8.1 W
911401584512	SM303C P6S 950 PSU MB	200 to 240 V	5.4 W	911401579012	SM303C P9 927 PSU WB	200 to 240 V	8.1 W
911401584612	SM303C P6S 950 PSU WB	200 to 240 V	5.4 W	911401579112	SM303C P9 927 PSU VWB	200 to 240 V	8.1 W
911401584712	SM303C P6S 950 PSU VWB	200 to 240 V	5.4 W	911401579212	SM303C P9 930 PSU NB	200 to 240 V	8.1 W

GreenSpace Surface Mount

Order Code	Full Product Name	Input Voltage	Power Consumption
911401579312	SM303C P9 930 PSU MB	200 to 240 V	8.1 W
911401579412	SM303C P9 930 PSU WB	200 to 240 V	8.1 W
911401579512	SM303C P9 930 PSU VWB	200 to 240 V	8.1 W
911401580012	SM303C P9 940 PSU NB	200 to 240 V	8.1 W
911401580112	SM303C P9 940 PSU MB	200 to 240 V	8.1 W
911401580212	SM303C P9 940 PSU WB	200 to 240 V	8.1 W

Order Code	Full Product Name	Input Voltage	Power Consumption
911401580312	SM303C P9 940 PSU VWB	200 to 240 V	8.1 W
911401580412	SM303C P9 950 PSU NB	200 to 240 V	8.1 W
911401580512	SM303C P9 950 PSU MB	200 to 240 V	8.1 W
911401580612	SM303C P9 950 PSU WB	200 to 240 V	8.1 W
911401580712	SM303C P9 950 PSU VWB	200 to 240 V	8.1 W

