



Elegant, Comprehensive and Affordable

GreenSpace Surface Mount

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenSpace Surface Mount is the entry level downlight family dedicated with suspension and surface mount versions, which offers a complete range of options for optical solutions, lumen outputs and color temperatures with multiple form factors available.

Benefits

- Elegant look & feel.
- Complete family with multiple installations and form factors.
- Good glare control with color rendering performance.
- Ensured quality and reliability.








Features

- Both round and square version available.
- Both suspension and surface mount version available.
- UGR19 & CRI90, SDCM $\leq$ 3
- Wide range of lumen packages, beam angles and color temperatures available.

Application

- Retail
- Hospitality
- Fashion

Dimensional drawing



Light Technical	
Color rendering index (CRI)	>90
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	200 to 240 V
Line Frequency	50 to 60 Hz
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Optical cover type	Acrylate
Housing Color	White
Mech. impact protection code	IK03
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	-20 to +40 °C
CE mark	No
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

Light Technical

Order Code	Full Product Name	Correlated Color	Luminous Efficacy (rated)	
		Temperature (Nom)	(Nom)	Luminous Flux
52546799	SP303P P6 940 PSU NB	4000 K	80 lm/W	480 lm
52458399	SP303P P6 940 PSU MB	4000 K	89 lm/W	530 lm
52388399	SP303P P6 940 PSU WB	4000 K	94 lm/W	560 lm
52896399	SP303P P6 940 PSU VWB	4000 K	91 lm/W	550 lm
52373999	SP303P P6 950 PSU NB	5000 K	81 lm/W	490 lm
52788199	SP303P P6 950 PSU MB	5000 K	90 lm/W	540 lm
53181999	SP303P P6 950 PSU WB	5000 K	97 lm/W	580 lm
53053999	SP303P P6 950 PSU VWB	5000 K	93 lm/W	560 lm
52392099	SP303P P9 927 PSU NB	2700 K	72 lm/W	650 lm
52902199	SP303P P9 927 PSU MB	2700 K	80 lm/W	720 lm
53060799	SP303P P9 927 PSU WB	2700 K	85 lm/W	770 lm
52552899	SP303P P9 927 PSU VWB	2700 K	81 lm/W	730 lm
52908399	SP303P P9 930 PSU NB	3000 K	75 lm/W	680 lm
52394499	SP303P P9 930 PSU MB	3000 K	83 lm/W	750 lm
52904599	SP303P P9 930 PSU WB	3000 K	87 lm/W	780 lm
52380799	SP303P P9 930 PSU VWB	3000 K	84 lm/W	760 lm
52691499	SP303P P9 940 PSU NB	4000 K	77 lm/W	690 lm
52797399	SP303P P9 940 PSU MB	4000 K	85 lm/W	770 lm
53190199	SP303P P9 940 PSU WB	4000 K	90 lm/W	810 lm
53064599	SP303P P9 940 PSU VWB	4000 K	87 lm/W	780 lm
52555999	SP303P P9 950 PSU NB	5000 K	78 lm/W	700 lm
52913799	SP303P P9 950 PSU MB	5000 K	87 lm/W	780 lm
52398299	SP303P P9 950 PSU WB	5000 K	93 lm/W	840 lm
52808699	SP303P P9 950 PSU VWB	5000 K	89 lm/W	800 lm
53193299	SP303P P6S 927 PSU NB	2700 K	76 lm/W	460 lm
53068399	SP303P P6S 927 PSU MB	2700 K	84 lm/W	500 lm
52813099	SP303P P6S 927 PSU WB	2700 K	89 lm/W	530 lm
52697699	SP303P P6S 927 PSU VWB	2700 K	84 lm/W	500 lm
52800099	SP303P P6S 930 PSU NB	3000 K	77 lm/W	460 lm
53195699	SP303P P6S 930 PSU MB	3000 K	86 lm/W	520 lm
53069099	SP303P P6S 930 PSU WB	3000 K	91 lm/W	550 lm
52625999	SP303P P6S 930 PSU VWB	3000 K	87 lm/W	520 lm
52389099	SP303P P6S 940 PSU NB	4000 K	80 lm/W	480 lm
52897099	SP303P P6S 940 PSU MB	4000 K	89 lm/W	530 lm
52374699	SP303P P6S 940 PSU WB	4000 K	94 lm/W	560 lm
52789899	SP303P P6S 940 PSU VWB	4000 K	91 lm/W	550 lm
53182699	SP303P P6S 950 PSU NB	5000 K	81 lm/W	490 lm
53054699	SP303P P6S 950 PSU MB	5000 K	90 lm/W	540 lm
52548199	SP303P P6S 950 PSU WB	5000 K	97 lm/W	580 lm
52906999	SP303P P6S 950 PSU VWB	5000 K	93 lm/W	560 lm
52377799	SP303P P9S 927 PSU NB	2700 K	72 lm/W	650 lm
52793599	SP303P P9S 927 PSU MB	2700 K	80 lm/W	720 lm
52909099	SP303P P9S 927 PSU WB	2700 K	85 lm/W	770 lm
52395199	SP303P P9S 927 PSU VWB	2700 K	81 lm/W	730 lm
52905299	SP303P P9S 930 PSU NB	3000 K	75 lm/W	680 lm
52381499	SP303P P9S 930 PSU MB	3000 K	83 lm/W	750 lm
52796699	SP303P P9S 930 PSU WB	3000 K	87 lm/W	780 lm
53189599	SP303P P9S 930 PSU VWB	3000 K	84 lm/W	760 lm
53191899	SP303P P9S 940 PSU NB	4000 K	77 lm/W	690 lm
53065299	SP303P P9S 940 PSU MB	4000 K	85 lm/W	770 lm

Order Code	Full Product Name	Correlated Color	Luminous Efficacy (rated)	
		Temperature (Nom)	(Nom)	Luminous Flux
52556699	SP303P P9S 940 PSU WB	4000 K	90 lm/W	810 lm
52914499	SP303P P9S 940 PSU VWB	4000 K	87 lm/W	780 lm
52399999	SP303P P9S 950 PSU NB	5000 K	78 lm/W	700 lm
52809399	SP303P P9S 950 PSU MB	5000 K	87 lm/W	780 lm
52693899	SP303P P9S 950 PSU WB	5000 K	93 lm/W	840 lm
52798099	SP303P P9S 950 PSU VWB	5000 K	89 lm/W	800 lm
53175899	SP303P P6 927 PSU NB	2700 K	76 lm/W	460 lm
53047899	SP303P P6 927 PSU MB	2700 K	84 lm/W	500 lm
52892599	SP303P P6 927 PSU WB	2700 K	89 lm/W	530 lm
52370899	SP303P P6 927 PSU VWB	2700 K	84 lm/W	500 lm
52784399	SP303P P6 930 PSU NB	3000 K	77 lm/W	460 lm
53177299	SP303P P6 930 PSU MB	3000 K	86 lm/W	520 lm
53049299	SP303P P6 930 PSU WB	3000 K	91 lm/W	550 lm
52545099	SP303P P6 930 PSU VWB	3000 K	87 lm/W	520 lm
52421799	SM303C P24 927 PSU NB	2700 K	86 lm/W	2,060 lm
52293099	SM303C P24 927 PSU MB	2700 K	87 lm/W	2,090 lm
52469999	SM303C P24 927 PSU WB	2700 K	88 lm/W	2,110 lm
52640299	SM303C P24 927 PSU VWB	2700 K	87 lm/W	2,090 lm
52934299	SM303C P24 930 PSU NB	3000 K	94 lm/W	2,260 lm
52426299	SM303C P24 930 PSU MB	3000 K	93 lm/W	2,230 lm
52296199	SM303C P24 930 PSU WB	3000 K	94 lm/W	2,260 lm
52711999	SM303C P24 930 PSU VWB	3000 K	94 lm/W	2,260 lm
52713399	SM303C P24 940 PSU NB	4000 K	100 lm/W	2,400 lm
53092899	SM303C P24 940 PSU MB	4000 K	101 lm/W	2,420 lm
52968799	SM303C P24 940 PSU WB	4000 K	102 lm/W	2,450 lm
52643399	SM303C P24 950 PSU NB	5000 K	98 lm/W	2,350 lm
52938099	SM303C P24 950 PSU MB	5000 K	99 lm/W	2,380 lm
52431699	SM303C P24 950 PSU WB	5000 K	100 lm/W	2,400 lm
52302999	SM303C P24 950 PSU VWB	5000 K	99 lm/W	2,380 lm
52970099	SM303C P28 927 PSU NB	2700 K	83 lm/W	2,320 lm
52475099	SM303C P28 927 PSU MB	2700 K	83 lm/W	2,320 lm
52303699	SM303C P28 927 PSU WB	2700 K	84 lm/W	2,350 lm
52716499	SM303C P28 927 PSU VWB	2700 K	83 lm/W	2,320 lm
53094299	SM303C P28 930 PSU NB	3000 K	89 lm/W	2,490 lm
52971799	SM303C P28 930 PSU MB	3000 K	88 lm/W	2,460 lm
52476799	SM303C P28 930 PSU WB	3000 K	89 lm/W	2,490 lm
52644099	SM303C P28 930 PSU VWB	3000 K	88 lm/W	2,460 lm
52647199	SM303C P28 940 PSU NB	4000 K	97 lm/W	2,720 lm
52941099	SM303C P28 940 PSU MB	4000 K	96 lm/W	2,690 lm
52433099	SM303C P28 940 PSU WB	4000 K	98 lm/W	2,740 lm
52305099	SM303C P28 940 PSU VWB	4000 K	96 lm/W	2,690 lm
52718899	SM303C P28 950 PSU NB	5000 K	95 lm/W	2,660 lm
53096699	SM303C P28 950 PSU MB	5000 K	94 lm/W	2,630 lm
52973199	SM303C P28 950 PSU WB	5000 K	96 lm/W	2,690 lm
52479899	SM303C P28 950 PSU VWB	5000 K	96 lm/W	2,690 lm
53098099	SM304C P10 927 PSU MB	2700 K	71 lm/W	730 lm
52974899	SM304C P10 927 PSU WB	2700 K	75 lm/W	770 lm
52819299	SM304C P10 930 PSU MB	3000 K	76 lm/W	770 lm
52307499	SM304C P10 930 PSU WB	3000 K	78 lm/W	810 lm
52976299	SM304C P10 940 PSU MB	4000 K	80 lm/W	810 lm
52482899	SM304C P10 940 PSU WB	4000 K	83 lm/W	860 lm

Order Code	Full Product Name	Correlated Color	Luminous Efficacy (rated)	
		Temperature (Nom)	(Nom)	Luminous Flux
52650199	SM304C P10 950 PSU MB	5000 K	86 lm/W	870 lm
52945899	SM304C P10 950 PSU WB	5000 K	88 lm/W	890 lm
52485999	SM304C P12 927 PSU MB	2700 K	70 lm/W	860 lm
52652599	SM304C P12 927 PSU WB	2700 K	73 lm/W	890 lm
52313599	SM304C P12 930 PSU MB	3000 K	75 lm/W	910 lm
52726399	SM304C P12 930 PSU WB	3000 K	77 lm/W	940 lm
52489799	SM304C P12 940 PSU MB	4000 K	78 lm/W	950 lm
52657099	SM304C P12 940 PSU WB	4000 K	81 lm/W	990 lm
52561099	SM304C P12 950 PSU MB	5000 K	84 lm/W	1,010 lm
52830799	SM304C P12 950 PSU WB	5000 K	86 lm/W	1,050 lm
52660099	SM304C P15 927 PSU MB	2700 K	70 lm/W	1,050 lm
52563499	SM304C P15 927 PSU WB	2700 K	73 lm/W	1,100 lm
53111699	SM304C P15 930 PSU MB	3000 K	75 lm/W	1,130 lm
52990899	SM304C P15 930 PSU WB	3000 K	78 lm/W	1,170 lm
52564199	SM304C P15 940 PSU MB	4000 K	78 lm/W	1,170 lm
52832199	SM304C P15 940 PSU WB	4000 K	82 lm/W	1,230 lm
52317399	SM304C P15 950 PSU MB	5000 K	84 lm/W	1,260 lm
52731799	SM304C P15 950 PSU WB	5000 K	88 lm/W	1,320 lm
53023299	SM303C P6S 927 PSU NB	2700 K	76 lm/W	460 lm
52519199	SM303C P6S 927 PSU MB	2700 K	84 lm/W	500 lm
52347099	SM303C P6S 927 PSU WB	2700 K	89 lm/W	530 lm
52763899	SM303C P6S 927 PSU VWB	2700 K	84 lm/W	500 lm
53151299	SM303C P6S 930 PSU NB	3000 K	77 lm/W	460 lm
53025699	SM303C P6S 930 PSU MB	3000 K	86 lm/W	520 lm
52522199	SM303C P6S 930 PSU WB	3000 K	91 lm/W	550 lm
52437899	SM303C P6S 930 PSU VWB	3000 K	87 lm/W	520 lm
52439299	SM303C P6S 940 PSU NB	4000 K	80 lm/W	480 lm
52604499	SM303C P6S 940 PSU MB	4000 K	89 lm/W	530 lm
52867399	SM303C P6S 940 PSU WB	4000 K	94 lm/W	560 lm
52349499	SM303C P6S 940 PSU VWB	4000 K	91 lm/W	550 lm
52766999	SM303C P6S 950 PSU NB	5000 K	81 lm/W	490 lm
53155099	SM303C P6S 950 PSU MB	5000 K	90 lm/W	540 lm
53029499	SM303C P6S 950 PSU WB	5000 K	97 lm/W	580 lm
52525299	SM303C P6S 950 PSU VWB	5000 K	93 lm/W	560 lm
52873499	SM303C P9S 927 PSU NB	2700 K	72 lm/W	650 lm
52354899	SM303C P9S 927 PSU MB	2700 K	80 lm/W	720 lm
52529099	SM303C P9S 927 PSU WB	2700 K	85 lm/W	770 lm
52444699	SM303C P9S 927 PSU VWB	2700 K	81 lm/W	730 lm
52608299	SM303C P9S 930 PSU NB	3000 K	75 lm/W	680 lm
52875899	SM303C P9S 930 PSU MB	3000 K	83 lm/W	750 lm
52356299	SM303C P9S 930 PSU WB	3000 K	87 lm/W	780 lm
52772099	SM303C P9S 930 PSU VWB	3000 K	84 lm/W	760 lm
52775199	SM303C P9S 940 PSU NB	4000 K	77 lm/W	690 lm
53165999	SM303C P9S 940 PSU MB	4000 K	85 lm/W	770 lm
53038699	SM303C P9S 940 PSU WB	4000 K	90 lm/W	810 lm
52535199	SM303C P9S 940 PSU VWB	4000 K	87 lm/W	780 lm

Order Code	Full Product Name	Correlated Color	Luminous Efficacy (rated)	
		Temperature (Nom)	(Nom)	Luminous Flux
52449199	SM303C P9S 950 PSU NB	5000 K	78 lm/W	700 lm
52614399	SM303C P9S 950 PSU MB	5000 K	87 lm/W	780 lm
52880299	SM303C P9S 950 PSU WB	5000 K	93 lm/W	840 lm
52360999	SM303C P9S 950 PSU VWB	5000 K	89 lm/W	800 lm
52623599	SM303C P20 927 PSU NB	2700 K	80 lm/W	1,600 lm
52916899	SM303C P20 927 PSU MB	2700 K	80 lm/W	1,600 lm
52801799	SM303C P20 927 PSU WB	2700 K	81 lm/W	1,620 lm
53196399	SM303C P20 927 PSU VWB	2700 K	81 lm/W	1,620 lm
53070699	SM303C P20 930 PSU NB	3000 K	88 lm/W	1,760 lm
52626699	SM303C P20 930 PSU MB	3000 K	88 lm/W	1,760 lm
52918299	SM303C P20 930 PSU WB	3000 K	90 lm/W	1,800 lm
52405799	SM303C P20 930 PSU VWB	3000 K	89 lm/W	1,780 lm
52408899	SM303C P20 940 PSU NB	4000 K	99 lm/W	1,980 lm
52818599	SM303C P20 940 PSU MB	4000 K	99 lm/W	1,980 lm
52702799	SM303C P20 940 PSU WB	4000 K	100 lm/W	2,000 lm
53077599	SM303C P20 940 PSU VWB	4000 K	100 lm/W	2,000 lm
53201499	SM303C P20 950 PSU NB	5000 K	102 lm/W	2,040 lm
53075199	SM303C P20 950 PSU MB	5000 K	102 lm/W	2,040 lm
52502399	SM303C P6 927 PSU NB	2700 K	76 lm/W	460 lm
52674799	SM303C P6 927 PSU MB	2700 K	84 lm/W	500 lm
52743099	SM303C P6 927 PSU WB	2700 K	89 lm/W	530 lm
53129199	SM303C P6 927 PSU VWB	2700 K	84 lm/W	500 lm
53005899	SM303C P6 930 PSU NB	3000 K	77 lm/W	460 lm
52504799	SM303C P6 930 PSU MB	3000 K	86 lm/W	520 lm
52676199	SM303C P6 930 PSU WB	3000 K	91 lm/W	550 lm
52582599	SM303C P6 930 PSU VWB	3000 K	87 lm/W	520 lm
52583299	SM303C P6 940 PSU NB	4000 K	80 lm/W	480 lm
52849999	SM303C P6 940 PSU MB	4000 K	89 lm/W	530 lm
52331999	SM303C P6 940 PSU WB	4000 K	94 lm/W	560 lm
52746199	SM303C P6 940 PSU VWB	4000 K	91 lm/W	550 lm
53131499	SM303C P6 950 PSU NB	5000 K	81 lm/W	490 lm
53008999	SM303C P6 950 PSU MB	5000 K	90 lm/W	540 lm
52507899	SM303C P6 950 PSU WB	5000 K	97 lm/W	580 lm
52678599	SM303C P6 950 PSU VWB	5000 K	93 lm/W	560 lm
52334099	SM303C P9 927 PSU NB	2700 K	72 lm/W	650 lm
52750899	SM303C P9 927 PSU MB	2700 K	80 lm/W	720 lm
52681599	SM303C P9 927 PSU WB	2700 K	85 lm/W	770 lm
52588799	SM303C P9 927 PSU VWB	2700 K	81 lm/W	730 lm
52854399	SM303C P9 930 PSU NB	3000 K	75 lm/W	680 lm
52337199	SM303C P9 930 PSU MB	3000 K	83 lm/W	750 lm
52753999	SM303C P9 930 PSU WB	3000 K	87 lm/W	780 lm
53137699	SM303C P9 930 PSU VWB	3000 K	84 lm/W	760 lm
52759199	SM303C P9 940 PSU NB	4000 K	77 lm/W	690 lm
53144499	SM303C P9 940 PSU MB	4000 K	85 lm/W	770 lm
53017199	SM303C P9 940 PSU WB	4000 K	90 lm/W	810 lm
52515399	SM303C P9 940 PSU VWB	4000 K	87 lm/W	780 lm
52687799	SM303C P9 950 PSU NB	5000 K	78 lm/W	700 lm
52595599	SM303C P9 950 PSU MB	5000 K	87 lm/W	780 lm

Order Code	Full Product Name	Correlated Color	Luminous Efficacy (rated)	
		Temperature (Nom)	(Nom)	Luminous Flux
52859899	SM303C P9 950 PSU WB	5000 K	93 lm/W	840 lm
52343299	SM303C P9 950 PSU VWB	5000 K	89 lm/W	800 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
52546799	SP303P P6 940 PSU NB	5.4 W	52381499	SP303P P9S 930 PSU MB	8.1 W
52458399	SP303P P6 940 PSU MB	5.4 W	52796699	SP303P P9S 930 PSU WB	8.1 W
52388399	SP303P P6 940 PSU WB	5.4 W	53189599	SP303P P9S 930 PSU VWB	8.1 W
52896399	SP303P P6 940 PSU VWB	5.4 W	53191899	SP303P P9S 940 PSU NB	8.1 W
52373999	SP303P P6 950 PSU NB	5.4 W	53065299	SP303P P9S 940 PSU MB	8.1 W
52788199	SP303P P6 950 PSU MB	5.4 W	52556699	SP303P P9S 940 PSU WB	8.1 W
53181999	SP303P P6 950 PSU WB	5.4 W	52914499	SP303P P9S 940 PSU VWB	8.1 W
53053999	SP303P P6 950 PSU VWB	5.4 W	52399999	SP303P P9S 950 PSU NB	8.1 W
52392099	SP303P P9 927 PSU NB	8.1 W	52809399	SP303P P9S 950 PSU MB	8.1 W
52902199	SP303P P9 927 PSU MB	8.1 W	52693899	SP303P P9S 950 PSU WB	8.1 W
53060799	SP303P P9 927 PSU WB	8.1 W	52798099	SP303P P9S 950 PSU VWB	8.1 W
52552899	SP303P P9 927 PSU VWB	8.1 W	53175899	SP303P P6 927 PSU NB	5.4 W
52908399	SP303P P9 930 PSU NB	8.1 W	53047899	SP303P P6 927 PSU MB	5.4 W
52394499	SP303P P9 930 PSU MB	8.1 W	52892599	SP303P P6 927 PSU WB	5.4 W
52904599	SP303P P9 930 PSU WB	8.1 W	52370899	SP303P P6 927 PSU VWB	5.4 W
52380799	SP303P P9 930 PSU VWB	8.1 W	52784399	SP303P P6 930 PSU NB	5.4 W
52691499	SP303P P9 940 PSU NB	8.1 W	53177299	SP303P P6 930 PSU MB	5.4 W
52797399	SP303P P9 940 PSU MB	8.1 W	53049299	SP303P P6 930 PSU WB	5.4 W
53190199	SP303P P9 940 PSU WB	8.1 W	52545099	SP303P P6 930 PSU VWB	5.4 W
53064599	SP303P P9 940 PSU VWB	8.1 W	52421799	SM303C P24 927 PSU NB	21.6 W
52555999	SP303P P9 950 PSU NB	8.1 W	52293099	SM303C P24 927 PSU MB	21.6 W
52913799	SP303P P9 950 PSU MB	8.1 W	52469999	SM303C P24 927 PSU WB	21.6 W
52398299	SP303P P9 950 PSU WB	8.1 W	52640299	SM303C P24 927 PSU VWB	21.6 W
52808699	SP303P P9 950 PSU VWB	8.1 W	52934299	SM303C P24 930 PSU NB	21.6 W
53193299	SP303P P6S 927 PSU NB	5.4 W	52426299	SM303C P24 930 PSU MB	21.6 W
53068399	SP303P P6S 927 PSU MB	5.4 W	52296199	SM303C P24 930 PSU WB	21.6 W
52813099	SP303P P6S 927 PSU WB	5.4 W	52711999	SM303C P24 930 PSU VWB	21.6 W
52697699	SP303P P6S 927 PSU VWB	5.4 W	52713399	SM303C P24 940 PSU NB	21.6 W
52800099	SP303P P6S 930 PSU NB	5.4 W	53092899	SM303C P24 940 PSU MB	21.6 W
53195699	SP303P P6S 930 PSU MB	5.4 W	52968799	SM303C P24 940 PSU WB	21.6 W
53069099	SP303P P6S 930 PSU WB	5.4 W	52643399	SM303C P24 950 PSU NB	21.6 W
52625999	SP303P P6S 930 PSU VWB	5.4 W	52938099	SM303C P24 950 PSU MB	21.6 W
52389099	SP303P P6S 940 PSU NB	5.4 W	52431699	SM303C P24 950 PSU WB	21.6 W
52897099	SP303P P6S 940 PSU MB	5.4 W	52302999	SM303C P24 950 PSU VWB	21.6 W
52374699	SP303P P6S 940 PSU WB	5.4 W	52970099	SM303C P28 927 PSU NB	25.2 W
52789899	SP303P P6S 940 PSU VWB	5.4 W	52475099	SM303C P28 927 PSU MB	25.2 W
53182699	SP303P P6S 950 PSU NB	5.4 W	52303699	SM303C P28 927 PSU WB	25.2 W
53054699	SP303P P6S 950 PSU MB	5.4 W	52716499	SM303C P28 927 PSU VWB	25.2 W
52548199	SP303P P6S 950 PSU WB	5.4 W	53094299	SM303C P28 930 PSU NB	25.2 W
52906999	SP303P P6S 950 PSU VWB	5.4 W	52971799	SM303C P28 930 PSU MB	25.2 W
52377799	SP303P P9S 927 PSU NB	8.1 W	52476799	SM303C P28 930 PSU WB	25.2 W
52793599	SP303P P9S 927 PSU MB	8.1 W	52644099	SM303C P28 930 PSU VWB	25.2 W
52909099	SP303P P9S 927 PSU WB	8.1 W	52647199	SM303C P28 940 PSU NB	25.2 W
52395199	SP303P P9S 927 PSU VWB	8.1 W	52941099	SM303C P28 940 PSU MB	25.2 W
52905299	SP303P P9S 930 PSU NB	8.1 W	52433099	SM303C P28 940 PSU WB	25.2 W

GreenSpace Surface Mount

Order Code	Full Product Name	Power Consumption
52305099	SM303C P28 940 PSU VWB	25.2 W
52718899	SM303C P28 950 PSU NB	25.2 W
53096699	SM303C P28 950 PSU MB	25.2 W
52973199	SM303C P28 950 PSU WB	25.2 W
52479899	SM303C P28 950 PSU VWB	25.2 W
53098099	SM304C P10 927 PSU MB	11 W
52974899	SM304C P10 927 PSU WB	11 W
52819299	SM304C P10 930 PSU MB	11 W
52307499	SM304C P10 930 PSU WB	11 W
52976299	SM304C P10 940 PSU MB	11 W
52482899	SM304C P10 940 PSU WB	11 W
52650199	SM304C P10 950 PSU MB	11 W
52945899	SM304C P10 950 PSU WB	11 W
52485999	SM304C P12 927 PSU MB	10.8 W
52652599	SM304C P12 927 PSU WB	10.8 W
52313599	SM304C P12 930 PSU MB	10.8 W
52726399	SM304C P12 930 PSU WB	10.8 W
52489799	SM304C P12 940 PSU MB	10.8 W
52657099	SM304C P12 940 PSU WB	10.8 W
52561099	SM304C P12 950 PSU MB	10.8 W
52830799	SM304C P12 950 PSU WB	10.8 W
52660099	SM304C P15 927 PSU MB	13.5 W
52563499	SM304C P15 927 PSU WB	13.5 W
53111699	SM304C P15 930 PSU MB	13.5 W
52990899	SM304C P15 930 PSU WB	13.5 W
52564199	SM304C P15 940 PSU MB	13.5 W
52832199	SM304C P15 940 PSU WB	13.5 W
52317399	SM304C P15 950 PSU MB	13.5 W
52731799	SM304C P15 950 PSU WB	13.5 W
53023299	SM303C P6S 927 PSU NB	5.4 W
52519199	SM303C P6S 927 PSU MB	5.4 W
52347099	SM303C P6S 927 PSU WB	5.4 W
52763899	SM303C P6S 927 PSU VWB	5.4 W
53151299	SM303C P6S 930 PSU NB	5.4 W
53025699	SM303C P6S 930 PSU MB	5.4 W
52522199	SM303C P6S 930 PSU WB	5.4 W
52437899	SM303C P6S 930 PSU VWB	5.4 W
52439299	SM303C P6S 940 PSU NB	5.4 W
52604499	SM303C P6S 940 PSU MB	5.4 W
52867399	SM303C P6S 940 PSU WB	5.4 W
52349499	SM303C P6S 940 PSU VWB	5.4 W
52766999	SM303C P6S 950 PSU NB	5.4 W
53155099	SM303C P6S 950 PSU MB	5.4 W
53029499	SM303C P6S 950 PSU WB	5.4 W
52525299	SM303C P6S 950 PSU VWB	5.4 W
52873499	SM303C P9S 927 PSU NB	8.1 W
52354899	SM303C P9S 927 PSU MB	8.1 W
52529099	SM303C P9S 927 PSU WB	8.1 W
52444699	SM303C P9S 927 PSU VWB	8.1 W
52608299	SM303C P9S 930 PSU NB	8.1 W
52875899	SM303C P9S 930 PSU MB	8.1 W
52356299	SM303C P9S 930 PSU WB	8.1 W

Order Code	Full Product Name	Power Consumption
52772099	SM303C P9S 930 PSU VWB	8.1 W
52775199	SM303C P9S 940 PSU NB	8.1 W
53165999	SM303C P9S 940 PSU MB	8.1 W
53038699	SM303C P9S 940 PSU WB	8.1 W
52535199	SM303C P9S 940 PSU VWB	8.1 W
52449199	SM303C P9S 950 PSU NB	8.1 W
52614399	SM303C P9S 950 PSU MB	8.1 W
52880299	SM303C P9S 950 PSU WB	8.1 W
52360999	SM303C P9S 950 PSU VWB	8.1 W
52623599	SM303C P20 927 PSU NB	18 W
52916899	SM303C P20 927 PSU MB	18 W
52801799	SM303C P20 927 PSU WB	18 W
53196399	SM303C P20 927 PSU VWB	18 W
53070699	SM303C P20 930 PSU NB	18 W
52626699	SM303C P20 930 PSU MB	18 W
52918299	SM303C P20 930 PSU WB	18 W
52405799	SM303C P20 930 PSU VWB	18 W
52408899	SM303C P20 940 PSU NB	18 W
52818599	SM303C P20 940 PSU MB	18 W
52702799	SM303C P20 940 PSU WB	18 W
53077599	SM303C P20 940 PSU VWB	18 W
53201499	SM303C P20 950 PSU NB	18 W
53075199	SM303C P20 950 PSU MB	18 W
52502399	SM303C P6 927 PSU NB	5.4 W
52674799	SM303C P6 927 PSU MB	5.4 W
52743099	SM303C P6 927 PSU WB	5.4 W
53129199	SM303C P6 927 PSU VWB	5.4 W
53005899	SM303C P6 930 PSU NB	5.4 W
52504799	SM303C P6 930 PSU MB	5.4 W
52676199	SM303C P6 930 PSU WB	5.4 W
52582599	SM303C P6 930 PSU VWB	5.4 W
52583299	SM303C P6 940 PSU NB	5.4 W
52849999	SM303C P6 940 PSU MB	5.4 W
52331999	SM303C P6 940 PSU WB	5.4 W
52746199	SM303C P6 940 PSU VWB	5.4 W
53131499	SM303C P6 950 PSU NB	5.4 W
53008999	SM303C P6 950 PSU MB	5.4 W
52507899	SM303C P6 950 PSU WB	5.4 W
52678599	SM303C P6 950 PSU VWB	5.4 W
52334099	SM303C P9 927 PSU NB	8.1 W
52750899	SM303C P9 927 PSU MB	8.1 W
52681599	SM303C P9 927 PSU WB	8.1 W
52588799	SM303C P9 927 PSU VWB	8.1 W
52854399	SM303C P9 930 PSU NB	8.1 W
52337199	SM303C P9 930 PSU MB	8.1 W
52753999	SM303C P9 930 PSU WB	8.1 W
53137699	SM303C P9 930 PSU VWB	8.1 W
52759199	SM303C P9 940 PSU NB	8.1 W
53144499	SM303C P9 940 PSU MB	8.1 W
53017199	SM303C P9 940 PSU WB	8.1 W
52515399	SM303C P9 940 PSU VWB	8.1 W
52687799	SM303C P9 950 PSU NB	8.1 W

GreenSpace Surface Mount

Order Code	Full Product Name	Power Consumption
52595599	SM303C P9 950 PSU MB	8.1 W
52859899	SM303C P9 950 PSU WB	8.1 W

Order Code	Full Product Name	Power Consumption
52343299	SM303C P9 950 PSU VWB	8.1 W

