



Elegant, Comprehensive and Affordable

GreenSpace Surface Mount

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenSpace Surface Mount is the entry level downlight family dedicated with suspension and surface mount versions, which offers a complete range of options for optical solutions, lumen outputs and color temperatures with multiple form factors available.

Benefits

- Elegant look & feel.
- Complete family with multiple installations and form factors.
- Good glare control with color rendering performance.
- Ensured quality and reliability.








Features

- Both round and square version available.
- Both suspension and surface mount version available.
- UGR19 & CRI90, SDCM≤3
- Wide range of lumen packages, beam angles and color temperatures available.

Application

- Retail
- Hospitality
- Fashion

Dimensional drawing



GreenSpace Surface Mount

Operating and Electrical	
Protection class IEC	Safety class II
Line Frequency	50 to 60 Hz
Mechanical and Housing	
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	-20 to +40 °C
ENEC mark	-

General Information

Order Code	Full Product Name	Driver included	Order Code	Full Product Name	Driver included
911401513348	SP303P P8 927 PSU MB PLUS	Yes	911401596712	SP303P P9 950 PSU VWB	-
911401513448	SP303P P8 927 PSU NB PLUS	Yes	911401598812	SP303P P6S 927 PSU NB	-
911401513548	SP303P P8 927 PSU VWB PLUS	Yes	911401598912	SP303P P6S 927 PSU MB	-
911401513648	SP303P P8 927 PSU WB PLUS	Yes	911401599012	SP303P P6S 927 PSU WB	-
911401513748	SP303P P8 930 PSU MB PLUS	Yes	911401599112	SP303P P6S 927 PSU VWB	-
911401513848	SP303P P8 930 PSU NB PLUS	Yes	911401599212	SP303P P6S 930 PSU NB	-
911401513948	SP303P P8 930 PSU VWB PLUS	Yes	911401599312	SP303P P6S 930 PSU MB	-
911401514048	SP303P P8 930 PSU WB PLUS	Yes	911401599412	SP303P P6S 930 PSU WB	-
911401514148	SP303P P8 940 PSU MB PLUS	Yes	911401599512	SP303P P6S 930 PSU VWB	-
911401514248	SP303P P8 940 PSU NB PLUS	Yes	911401500022	SP303P P6S 940 PSU NB	-
911401514348	SP303P P8 940 PSU VWB PLUS	Yes	911401500122	SP303P P6S 940 PSU MB	-
911401514448	SP303P P8 940 PSU WB PLUS	Yes	911401500222	SP303P P6S 940 PSU WB	-
911401514548	SP303P P8 950 PSU MB PLUS	Yes	911401500322	SP303P P6S 940 PSU VWB	-
911401514648	SP303P P8 950 PSU NB PLUS	Yes	911401500422	SP303P P6S 950 PSU NB	-
911401514748	SP303P P8 950 PSU VWB PLUS	Yes	911401500522	SP303P P6S 950 PSU MB	-
911401514848	SP303P P8 950 PSU WB PLUS	Yes	911401500622	SP303P P6S 950 PSU WB	-
911401592012	SP303P P6 940 PSU NB	-	911401500722	SP303P P6S 950 PSU VWB	-
911401592112	SP303P P6 940 PSU MB	-	911401502822	SP303P P9S 927 PSU NB	-
911401592212	SP303P P6 940 PSU WB	-	911401502922	SP303P P9S 927 PSU MB	-
911401592312	SP303P P6 940 PSU VWB	-	911401503022	SP303P P9S 927 PSU WB	-
911401592412	SP303P P6 950 PSU NB	-	911401503122	SP303P P9S 927 PSU VWB	-
911401592512	SP303P P6 950 PSU MB	-	911401503222	SP303P P9S 930 PSU NB	-
911401592612	SP303P P6 950 PSU WB	-	911401503322	SP303P P9S 930 PSU MB	-
911401592712	SP303P P6 950 PSU VWB	-	911401503422	SP303P P9S 930 PSU WB	-
911401594812	SP303P P9 927 PSU NB	-	911401503522	SP303P P9S 930 PSU VWB	-
911401594912	SP303P P9 927 PSU MB	-	911401504022	SP303P P9S 940 PSU NB	-
911401595012	SP303P P9 927 PSU WB	-	911401504122	SP303P P9S 940 PSU MB	-
911401595112	SP303P P9 927 PSU VWB	-	911401504222	SP303P P9S 940 PSU WB	-
911401595212	SP303P P9 930 PSU NB	-	911401504322	SP303P P9S 940 PSU VWB	-
911401595312	SP303P P9 930 PSU MB	-	911401504422	SP303P P9S 950 PSU NB	-
911401595412	SP303P P9 930 PSU WB	-	911401504522	SP303P P9S 950 PSU MB	-
911401595512	SP303P P9 930 PSU VWB	-	911401504622	SP303P P9S 950 PSU WB	-
911401596012	SP303P P9 940 PSU NB	-	911401504722	SP303P P9S 950 PSU VWB	-
911401596112	SP303P P9 940 PSU MB	-	911401514948	SP303P P8S 927 PSU MB PLUS	Yes
911401596212	SP303P P9 940 PSU WB	-	911401515048	SP303P P8S 927 PSU NB PLUS	Yes
911401596312	SP303P P9 940 PSU VWB	-	911401515148	SP303P P8S 927 PSU VWB PLUS	Yes
911401596412	SP303P P9 950 PSU NB	-	911401515248	SP303P P8S 927 PSU WB PLUS	Yes
911401596512	SP303P P9 950 PSU MB	-	911401515348	SP303P P8S 930 PSU MB PLUS	Yes
911401596612	SP303P P9 950 PSU WB	-	911401515448	SP303P P8S 930 PSU NB PLUS	Yes

GreenSpace Surface Mount

Order Code	Full Product Name	Driver included
911401515548	SP303P P8S 930 PSU VWB PLUS	Yes
911401515648	SP303P P8S 930 PSU WB PLUS	Yes
911401515748	SP303P P8S 940 PSU MB PLUS	Yes
911401515848	SP303P P8S 940 PSU NB PLUS	Yes
911401515948	SP303P P8S 940 PSU VWB PLUS	Yes
911401516048	SP303P P8S 940 PSU WB PLUS	Yes
911401516148	SP303P P8S 950 PSU MB PLUS	Yes
911401516248	SP303P P8S 950 PSU NB PLUS	Yes
911401516348	SP303P P8S 950 PSU VWB PLUS	Yes
911401516448	SP303P P8S 950 PSU WB PLUS	Yes
911401590812	SP303P P6 927 PSU NB	-
911401590912	SP303P P6 927 PSU MB	-
911401591012	SP303P P6 927 PSU WB	-
911401591112	SP303P P6 927 PSU VWB	-
911401591212	SP303P P6 930 PSU NB	-
911401591312	SP303P P6 930 PSU MB	-
911401591412	SP303P P6 930 PSU WB	-
911401591512	SP303P P6 930 PSU VWB	-
911401510248	SM303C P24 927 PSU MB PLUS	Yes
911401510348	SM303C P24 927 PSU NB PLUS	Yes
911401510448	SM303C P24 927 PSU VWB PLUS	Yes
911401510548	SM303C P24 927 PSU WB PLUS	Yes
911401510648	SM303C P24 930 PSU MB PLUS	Yes
911401510748	SM303C P24 930 PSU NB PLUS	Yes
911401510822	SM303C P24 927 PSU NB	-
911401510848	SM303C P24 930 PSU VWB PLUS	Yes
911401510922	SM303C P24 927 PSU MB	-
911401510948	SM303C P24 930 PSU WB PLUS	Yes
911401511022	SM303C P24 927 PSU WB	-
911401511048	SM303C P24 940 PSU MB PLUS	Yes
911401511122	SM303C P24 927 PSU VWB	-
911401511148	SM303C P24 940 PSU NB PLUS	Yes
911401511222	SM303C P24 930 PSU NB	-
911401511248	SM303C P24 940 PSU WB PLUS	Yes
911401511322	SM303C P24 930 PSU MB	-
911401511348	SM303C P24 950 PSU MB PLUS	Yes
911401511422	SM303C P24 930 PSU WB	-
911401511448	SM303C P24 950 PSU NB PLUS	Yes
911401511522	SM303C P24 930 PSU VWB	-
911401511548	SM303C P24 950 PSU VWB PLUS	Yes
911401511648	SM303C P24 950 PSU WB PLUS	Yes
911401511748	SM303C P28 927 PSU MB PLUS	Yes
911401511848	SM303C P28 927 PSU NB PLUS	Yes
911401511948	SM303C P28 927 PSU VWB PLUS	Yes
911401512022	SM303C P24 940 PSU NB	-
911401512048	SM303C P28 927 PSU WB PLUS	Yes
911401512122	SM303C P24 940 PSU MB	-
911401512148	SM303C P28 930 PSU MB PLUS	Yes
911401512222	SM303C P24 940 PSU WB	-
911401512248	SM303C P28 930 PSU NB PLUS	Yes
911401512348	SM303C P28 930 PSU VWB PLUS	Yes
911401512422	SM303C P24 950 PSU NB	-

Order Code	Full Product Name	Driver included
911401512448	SM303C P28 930 PSU WB PLUS	Yes
911401512522	SM303C P24 950 PSU MB	-
911401512548	SM303C P28 940 PSU MB PLUS	Yes
911401512622	SM303C P24 950 PSU WB	-
911401512648	SM303C P28 940 PSU NB PLUS	Yes
911401512722	SM303C P24 950 PSU VWB	-
911401512748	SM303C P28 940 PSU VWB PLUS	Yes
911401512848	SM303C P28 940 PSU WB PLUS	Yes
911401512948	SM303C P28 950 PSU MB PLUS	Yes
911401513048	SM303C P28 950 PSU NB PLUS	Yes
911401513148	SM303C P28 950 PSU VWB PLUS	Yes
911401513248	SM303C P28 950 PSU WB PLUS	Yes
911401514822	SM303C P28 927 PSU NB	-
911401514922	SM303C P28 927 PSU MB	-
911401515022	SM303C P28 927 PSU WB	-
911401515122	SM303C P28 927 PSU VWB	-
911401515222	SM303C P28 930 PSU NB	-
911401515322	SM303C P28 930 PSU MB	-
911401515422	SM303C P28 930 PSU WB	-
911401515522	SM303C P28 930 PSU VWB	-
911401516022	SM303C P28 940 PSU NB	-
911401516122	SM303C P28 940 PSU MB	-
911401516222	SM303C P28 940 PSU WB	-
911401516322	SM303C P28 940 PSU VWB	-
911401516422	SM303C P28 950 PSU NB	-
911401516522	SM303C P28 950 PSU MB	-
911401516622	SM303C P28 950 PSU WB	-
911401516722	SM303C P28 950 PSU VWB	-
911401517822	SM304C P10 927 PSU MB	-
911401517922	SM304C P10 927 PSU WB	-
911401518022	SM304C P10 930 PSU MB	-
911401518122	SM304C P10 930 PSU WB	-
911401518422	SM304C P10 940 PSU MB	-
911401518522	SM304C P10 940 PSU WB	-
911401518622	SM304C P10 950 PSU MB	-
911401518722	SM304C P10 950 PSU WB	-
911401519822	SM304C P12 927 PSU MB	-
911401519922	SM304C P12 927 PSU WB	-
911401520022	SM304C P12 930 PSU MB	-
911401520122	SM304C P12 930 PSU WB	-
911401520422	SM304C P12 940 PSU MB	-
911401520522	SM304C P12 940 PSU WB	-
911401520622	SM304C P12 950 PSU MB	-
911401520722	SM304C P12 950 PSU WB	-
911401521822	SM304C P15 927 PSU MB	-
911401521922	SM304C P15 927 PSU WB	-
911401522022	SM304C P15 930 PSU MB	-
911401522122	SM304C P15 930 PSU WB	-
911401522422	SM304C P15 940 PSU MB	-
911401522522	SM304C P15 940 PSU WB	-
911401522622	SM304C P15 950 PSU MB	-
911401522722	SM304C P15 950 PSU WB	-

GreenSpace Surface Mount

Order Code	Full Product Name	Driver included
911401541248	SM303C P8S 927 PSU MB PLUS	Yes
911401541348	SM303C P8S 927 PSU NB PLUS	Yes
911401541448	SM303C P8S 927 PSU VWB PLUS	Yes
911401541548	SM303C P8S 927 PSU WB PLUS	Yes
911401541648	SM303C P8S 930 PSU MB PLUS	Yes
911401541748	SM303C P8S 930 PSU NB PLUS	Yes
911401541848	SM303C P8S 930 PSU VWB PLUS	Yes
911401541948	SM303C P8S 930 PSU WB PLUS	Yes
911401542048	SM303C P8S 940 PSU MB PLUS	Yes
911401542148	SM303C P8S 940 PSU NB PLUS	Yes
911401542248	SM303C P8S 940 PSU VWB PLUS	Yes
911401542348	SM303C P8S 940 PSU WB PLUS	Yes
911401542448	SM303C P8S 950 PSU MB PLUS	Yes
911401542548	SM303C P8S 950 PSU NB PLUS	Yes
911401542648	SM303C P8S 950 PSU VWB PLUS	Yes
911401542748	SM303C P8S 950 PSU WB PLUS	Yes
911401582812	SM303C P6S 927 PSU NB	-
911401582912	SM303C P6S 927 PSU MB	-
911401583012	SM303C P6S 927 PSU WB	-
911401583112	SM303C P6S 927 PSU VWB	-
911401583212	SM303C P6S 930 PSU NB	-
911401583312	SM303C P6S 930 PSU MB	-
911401583412	SM303C P6S 930 PSU WB	-
911401583512	SM303C P6S 930 PSU VWB	-
911401584012	SM303C P6S 940 PSU NB	-
911401584112	SM303C P6S 940 PSU MB	-
911401584212	SM303C P6S 940 PSU WB	-
911401584312	SM303C P6S 940 PSU VWB	-
911401584412	SM303C P6S 950 PSU NB	-
911401584512	SM303C P6S 950 PSU MB	-
911401584612	SM303C P6S 950 PSU WB	-
911401584712	SM303C P6S 950 PSU VWB	-
911401586812	SM303C P9S 927 PSU NB	-
911401586912	SM303C P9S 927 PSU MB	-
911401587012	SM303C P9S 927 PSU WB	-
911401587112	SM303C P9S 927 PSU VWB	-
911401587212	SM303C P9S 930 PSU NB	-
911401587312	SM303C P9S 930 PSU MB	-
911401587412	SM303C P9S 930 PSU WB	-
911401587512	SM303C P9S 930 PSU VWB	-
911401588012	SM303C P9S 940 PSU NB	-
911401588112	SM303C P9S 940 PSU MB	-
911401588212	SM303C P9S 940 PSU WB	-
911401588312	SM303C P9S 940 PSU VWB	-
911401588412	SM303C P9S 950 PSU NB	-
911401588512	SM303C P9S 950 PSU MB	-
911401588612	SM303C P9S 950 PSU WB	-
911401588712	SM303C P9S 950 PSU VWB	-
911401506822	SM303C P20 927 PSU NB	-
911401506922	SM303C P20 927 PSU MB	-
911401507022	SM303C P20 927 PSU WB	-
911401507122	SM303C P20 927 PSU VWB	-

Order Code	Full Product Name	Driver included
911401507222	SM303C P20 930 PSU NB	-
911401507322	SM303C P20 930 PSU MB	-
911401507422	SM303C P20 930 PSU WB	-
911401507522	SM303C P20 930 PSU VWB	-
911401508022	SM303C P20 940 PSU NB	-
911401508122	SM303C P20 940 PSU MB	-
911401508222	SM303C P20 940 PSU WB	-
911401508322	SM303C P20 940 PSU VWB	-
911401508422	SM303C P20 950 PSU NB	-
911401508522	SM303C P20 950 PSU MB	-
911401508848	SM303C P20 927 PSU MB PLUS	Yes
911401508948	SM303C P20 927 PSU NB PLUS	Yes
911401509048	SM303C P20 927 PSU VWB PLUS	Yes
911401509148	SM303C P20 927 PSU WB PLUS	Yes
911401509248	SM303C P20 930 PSU MB PLUS	Yes
911401509348	SM303C P20 930 PSU NB PLUS	Yes
911401509448	SM303C P20 930 PSU VWB PLUS	Yes
911401509548	SM303C P20 930 PSU WB PLUS	Yes
911401509648	SM303C P20 940 PSU MB PLUS	Yes
911401509748	SM303C P20 940 PSU NB PLUS	Yes
911401509848	SM303C P20 940 PSU VWB PLUS	Yes
911401509948	SM303C P20 940 PSU WB PLUS	Yes
911401510048	SM303C P20 950 PSU MB PLUS	Yes
911401510148	SM303C P20 950 PSU NB PLUS	Yes
911401539648	SM303C P8 927 PSU MB PLUS	Yes
911401539748	SM303C P8 927 PSU NB PLUS	Yes
911401539848	SM303C P8 927 PSU VWB PLUS	Yes
911401539948	SM303C P8 927 PSU WB PLUS	Yes
911401540048	SM303C P8 930 PSU MB PLUS	Yes
911401540148	SM303C P8 930 PSU NB PLUS	Yes
911401540248	SM303C P8 930 PSU VWB PLUS	Yes
911401540348	SM303C P8 930 PSU WB PLUS	Yes
911401540448	SM303C P8 940 PSU MB PLUS	Yes
911401540548	SM303C P8 940 PSU NB PLUS	Yes
911401540648	SM303C P8 940 PSU VWB PLUS	Yes
911401540748	SM303C P8 940 PSU WB PLUS	Yes
911401540848	SM303C P8 950 PSU MB PLUS	Yes
911401540948	SM303C P8 950 PSU NB PLUS	Yes
911401541048	SM303C P8 950 PSU VWB PLUS	Yes
911401541148	SM303C P8 950 PSU WB PLUS	Yes
911401574812	SM303C P6 927 PSU NB	-
911401574912	SM303C P6 927 PSU MB	-
911401575012	SM303C P6 927 PSU WB	-
911401575112	SM303C P6 927 PSU VWB	-
911401575212	SM303C P6 930 PSU NB	-
911401575312	SM303C P6 930 PSU MB	-
911401575412	SM303C P6 930 PSU WB	-
911401575512	SM303C P6 930 PSU VWB	-
911401576012	SM303C P6 940 PSU NB	-
911401576112	SM303C P6 940 PSU MB	-
911401576212	SM303C P6 940 PSU WB	-
911401576312	SM303C P6 940 PSU VWB	-

GreenSpace Surface Mount

Order Code	Full Product Name	Driver included
911401576412	SM303C P6 950 PSU NB	-
911401576512	SM303C P6 950 PSU MB	-
911401576612	SM303C P6 950 PSU WB	-
911401576712	SM303C P6 950 PSU VWB	-
911401578812	SM303C P9 927 PSU NB	-
911401578912	SM303C P9 927 PSU MB	-
911401579012	SM303C P9 927 PSU WB	-
911401579112	SM303C P9 927 PSU VWB	-
911401579212	SM303C P9 930 PSU NB	-
911401579312	SM303C P9 930 PSU MB	-

Order Code	Full Product Name	Driver included
911401579412	SM303C P9 930 PSU WB	-
911401579512	SM303C P9 930 PSU VWB	-
911401580012	SM303C P9 940 PSU NB	-
911401580112	SM303C P9 940 PSU MB	-
911401580212	SM303C P9 940 PSU WB	-
911401580312	SM303C P9 940 PSU VWB	-
911401580412	SM303C P9 950 PSU NB	-
911401580512	SM303C P9 950 PSU MB	-
911401580612	SM303C P9 950 PSU WB	-
911401580712	SM303C P9 950 PSU VWB	-

Light Technical

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401513348	SP303P P8 927 PSU MB PLUS	24 degree(s)	2700 K	90	97 lm/W	775 lm
911401513448	SP303P P8 927 PSU NB PLUS	15 x 15 degree(s)	2700 K	90	90 lm/W	720 lm
911401513548	SP303P P8 927 PSU VWB PLUS	55 degree(s)	2700 K	90	96 lm/W	770 lm
911401513648	SP303P P8 927 PSU WB PLUS	38 degree(s)	2700 K	90	102 lm/W	815 lm
911401513748	SP303P P8 930 PSU MB PLUS	24 degree(s)	3000 K	90	97 lm/W	775 lm
911401513848	SP303P P8 930 PSU NB PLUS	15 x 15 degree(s)	3000 K	90	90 lm/W	720 lm
911401513948	SP303P P8 930 PSU VWB PLUS	55 degree(s)	3000 K	90	96 lm/W	770 lm
911401514048	SP303P P8 930 PSU WB PLUS	38 degree(s)	3000 K	90	103 lm/W	825 lm
911401514148	SP303P P8 940 PSU MB PLUS	24 degree(s)	4000 K	90	106 lm/W	850 lm
911401514248	SP303P P8 940 PSU NB PLUS	15 x 15 degree(s)	4000 K	90	98 lm/W	785 lm
911401514348	SP303P P8 940 PSU VWB PLUS	55 degree(s)	4000 K	90	105 lm/W	840 lm
911401514448	SP303P P8 940 PSU WB PLUS	38 degree(s)	4000 K	90	110 lm/W	880 lm
911401514548	SP303P P8 950 PSU MB PLUS	24 degree(s)	5000 K	90	101.25 lm/W	810 lm
911401514648	SP303P P8 950 PSU NB PLUS	15 x 15 degree(s)	5000 K	90	94.375 lm/W	755 lm
911401514748	SP303P P8 950 PSU VWB PLUS	55 degree(s)	5000 K	90	100.625 lm/W	805 lm
911401514848	SP303P P8 950 PSU WB PLUS	38 degree(s)	5000 K	90	108.125 lm/W	865 lm
911401592012	SP303P P6 940 PSU NB	-	4000 K	>90	80 lm/W	480 lm
911401592112	SP303P P6 940 PSU MB	-	4000 K	>90	89 lm/W	530 lm
911401592212	SP303P P6 940 PSU WB	-	4000 K	>90	94 lm/W	560 lm
911401592312	SP303P P6 940 PSU VWB	-	4000 K	>90	91 lm/W	550 lm
911401592412	SP303P P6 950 PSU NB	-	5000 K	>90	81 lm/W	490 lm
911401592512	SP303P P6 950 PSU MB	-	5000 K	>90	90 lm/W	540 lm
911401592612	SP303P P6 950 PSU WB	-	5000 K	>90	97 lm/W	580 lm
911401592712	SP303P P6 950 PSU VWB	-	5000 K	>90	93 lm/W	560 lm
911401594812	SP303P P9 927 PSU NB	-	2700 K	>90	72 lm/W	650 lm
911401594912	SP303P P9 927 PSU MB	-	2700 K	>90	80 lm/W	720 lm
911401595012	SP303P P9 927 PSU WB	-	2700 K	>90	85 lm/W	770 lm
911401595112	SP303P P9 927 PSU VWB	-	2700 K	>90	81 lm/W	730 lm
911401595212	SP303P P9 930 PSU NB	-	3000 K	>90	75 lm/W	680 lm
911401595312	SP303P P9 930 PSU MB	-	3000 K	>90	83 lm/W	750 lm
911401595412	SP303P P9 930 PSU WB	-	3000 K	>90	87 lm/W	780 lm
911401595512	SP303P P9 930 PSU VWB	-	3000 K	>90	84 lm/W	760 lm
911401596012	SP303P P9 940 PSU NB	-	4000 K	>90	77 lm/W	690 lm
911401596112	SP303P P9 940 PSU MB	-	4000 K	>90	85 lm/W	770 lm
911401596212	SP303P P9 940 PSU WB	-	4000 K	>90	90 lm/W	810 lm
911401596312	SP303P P9 940 PSU VWB	-	4000 K	>90	87 lm/W	780 lm
911401596412	SP303P P9 950 PSU NB	-	5000 K	>90	78 lm/W	700 lm

GreenSpace Surface Mount

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401596512	SP303P P9 950 PSU MB	-	5000 K	>90	87 lm/W	780 lm
911401596612	SP303P P9 950 PSU WB	-	5000 K	>90	93 lm/W	840 lm
911401596712	SP303P P9 950 PSU VWB	-	5000 K	>90	89 lm/W	800 lm
911401598812	SP303P P6S 927 PSU NB	-	2700 K	>90	76 lm/W	460 lm
911401598912	SP303P P6S 927 PSU MB	-	2700 K	>90	84 lm/W	500 lm
911401599012	SP303P P6S 927 PSU WB	-	2700 K	>90	89 lm/W	530 lm
911401599112	SP303P P6S 927 PSU VWB	-	2700 K	>90	84 lm/W	500 lm
911401599212	SP303P P6S 930 PSU NB	-	3000 K	>90	77 lm/W	460 lm
911401599312	SP303P P6S 930 PSU MB	-	3000 K	>90	86 lm/W	520 lm
911401599412	SP303P P6S 930 PSU WB	-	3000 K	>90	91 lm/W	550 lm
911401599512	SP303P P6S 930 PSU VWB	-	3000 K	>90	87 lm/W	520 lm
911401500022	SP303P P6S 940 PSU NB	-	4000 K	>90	80 lm/W	480 lm
911401500122	SP303P P6S 940 PSU MB	-	4000 K	>90	89 lm/W	530 lm
911401500222	SP303P P6S 940 PSU WB	-	4000 K	>90	94 lm/W	560 lm
911401500322	SP303P P6S 940 PSU VWB	-	4000 K	>90	91 lm/W	550 lm
911401500422	SP303P P6S 950 PSU NB	-	5000 K	>90	81 lm/W	490 lm
911401500522	SP303P P6S 950 PSU MB	-	5000 K	>90	90 lm/W	540 lm
911401500622	SP303P P6S 950 PSU WB	-	5000 K	>90	97 lm/W	580 lm
911401500722	SP303P P6S 950 PSU VWB	-	5000 K	>90	93 lm/W	560 lm
911401502822	SP303P P9S 927 PSU NB	-	2700 K	>90	72 lm/W	650 lm
911401502922	SP303P P9S 927 PSU MB	-	2700 K	>90	80 lm/W	720 lm
911401503022	SP303P P9S 927 PSU WB	-	2700 K	>90	85 lm/W	770 lm
911401503122	SP303P P9S 927 PSU VWB	-	2700 K	>90	81 lm/W	730 lm
911401503222	SP303P P9S 930 PSU NB	-	3000 K	>90	75 lm/W	680 lm
911401503322	SP303P P9S 930 PSU MB	-	3000 K	>90	83 lm/W	750 lm
911401503422	SP303P P9S 930 PSU WB	-	3000 K	>90	87 lm/W	780 lm
911401503522	SP303P P9S 930 PSU VWB	-	3000 K	>90	84 lm/W	760 lm
911401504022	SP303P P9S 940 PSU NB	-	4000 K	>90	77 lm/W	690 lm
911401504122	SP303P P9S 940 PSU MB	-	4000 K	>90	85 lm/W	770 lm
911401504222	SP303P P9S 940 PSU WB	-	4000 K	>90	90 lm/W	810 lm
911401504322	SP303P P9S 940 PSU VWB	-	4000 K	>90	87 lm/W	780 lm
911401504422	SP303P P9S 950 PSU NB	-	5000 K	>90	78 lm/W	700 lm
911401504522	SP303P P9S 950 PSU MB	-	5000 K	>90	87 lm/W	780 lm
911401504622	SP303P P9S 950 PSU WB	-	5000 K	>90	93 lm/W	840 lm
911401504722	SP303P P9S 950 PSU VWB	-	5000 K	>90	89 lm/W	800 lm
911401514948	SP303P P8S 927 PSU MB PLUS	24 degree(s)	2700 K	90	97 lm/W	775 lm
911401515048	SP303P P8S 927 PSU NB PLUS	15 x 15 degree(s)	2700 K	90	90 lm/W	720 lm
911401515148	SP303P P8S 927 PSU VWB PLUS	55 degree(s)	2700 K	90	96 lm/W	770 lm
911401515248	SP303P P8S 927 PSU WB PLUS	38 degree(s)	2700 K	90	102 lm/W	815 lm
911401515348	SP303P P8S 930 PSU MB PLUS	24 degree(s)	3000 K	90	97 lm/W	775 lm
911401515448	SP303P P8S 930 PSU NB PLUS	15 x 15 degree(s)	3000 K	90	90 lm/W	720 lm
911401515548	SP303P P8S 930 PSU VWB PLUS	55 degree(s)	3000 K	90	96 lm/W	770 lm
911401515648	SP303P P8S 930 PSU WB PLUS	38 degree(s)	3000 K	90	103 lm/W	825 lm
911401515748	SP303P P8S 940 PSU MB PLUS	24 degree(s)	4000 K	90	106 lm/W	850 lm
911401515848	SP303P P8S 940 PSU NB PLUS	15 x 15 degree(s)	4000 K	90	98 lm/W	785 lm
911401515948	SP303P P8S 940 PSU VWB PLUS	55 degree(s)	4000 K	90	105 lm/W	840 lm
911401516048	SP303P P8S 940 PSU WB PLUS	38 degree(s)	4000 K	90	110 lm/W	880 lm
911401516148	SP303P P8S 950 PSU MB PLUS	24 degree(s)	5000 K	90	101.25 lm/W	810 lm
911401516248	SP303P P8S 950 PSU NB PLUS	15 x 15 degree(s)	5000 K	90	94.375 lm/W	755 lm
911401516348	SP303P P8S 950 PSU VWB PLUS	55 degree(s)	5000 K	90	100.625 lm/W	805 lm
911401516448	SP303P P8S 950 PSU WB PLUS	38 degree(s)	5000 K	90	108.125 lm/W	865 lm

GreenSpace Surface Mount

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401590812	SP303P P6 927 PSU NB	-	2700 K	>90	76 lm/W	460 lm
911401590912	SP303P P6 927 PSU MB	-	2700 K	>90	84 lm/W	500 lm
911401591012	SP303P P6 927 PSU WB	-	2700 K	>90	89 lm/W	530 lm
911401591112	SP303P P6 927 PSU VWB	-	2700 K	>90	84 lm/W	500 lm
911401591212	SP303P P6 930 PSU NB	-	3000 K	>90	77 lm/W	460 lm
911401591312	SP303P P6 930 PSU MB	-	3000 K	>90	86 lm/W	520 lm
911401591412	SP303P P6 930 PSU WB	-	3000 K	>90	91 lm/W	550 lm
911401591512	SP303P P6 930 PSU VWB	-	3000 K	>90	87 lm/W	520 lm
911401510248	SM303C P24 927 PSU MB PLUS	24 degree(s)	2700 K	90	101.66666666666667 lm/W	2,440 lm
911401510348	SM303C P24 927 PSU NB PLUS	15 x 15 degree(s)	2700 K	90	101.875 lm/W	2,445 lm
911401510448	SM303C P24 927 PSU VWB PLUS	55 degree(s)	2700 K	90	99.58333333333333 lm/W	2,390 lm
911401510548	SM303C P24 927 PSU WB PLUS	38 degree(s)	2700 K	90	103.75 lm/W	2,490 lm
911401510648	SM303C P24 930 PSU MB PLUS	24 degree(s)	3000 K	90	110.20833333333333 lm/W	2,645 lm
911401510748	SM303C P24 930 PSU NB PLUS	15 x 15 degree(s)	3000 K	90	111.25 lm/W	2,670 lm
911401510822	SM303C P24 927 PSU NB	-	2700 K	>90	86 lm/W	2,060 lm
911401510848	SM303C P24 930 PSU VWB PLUS	55 degree(s)	3000 K	90	104.16666666666667 lm/W	2,500 lm
911401510922	SM303C P24 927 PSU MB	-	2700 K	>90	87 lm/W	2,090 lm
911401510948	SM303C P24 930 PSU WB PLUS	38 degree(s)	3000 K	90	108.95833333333333 lm/W	2,615 lm
911401511022	SM303C P24 927 PSU WB	-	2700 K	>90	88 lm/W	2,110 lm
911401511048	SM303C P24 940 PSU MB PLUS	24 degree(s)	4000 K	90	113.54166666666667 lm/W	2,725 lm
911401511122	SM303C P24 927 PSU VWB	-	2700 K	>90	87 lm/W	2,090 lm
911401511148	SM303C P24 940 PSU NB PLUS	15 x 15 degree(s)	4000 K	90	113.95833333333333 lm/W	2,735 lm
911401511222	SM303C P24 930 PSU NB	-	3000 K	>90	94 lm/W	2,260 lm
911401511248	SM303C P24 940 PSU WB PLUS	38 degree(s)	4000 K	90	114.16666666666667 lm/W	2,740 lm
911401511322	SM303C P24 930 PSU MB	-	3000 K	>90	93 lm/W	2,230 lm
911401511348	SM303C P24 950 PSU MB PLUS	24 degree(s)	5000 K	90	115.625 lm/W	2,775 lm
911401511422	SM303C P24 930 PSU WB	-	3000 K	>90	94 lm/W	2,260 lm
911401511448	SM303C P24 950 PSU NB PLUS	15 x 15 degree(s)	5000 K	90	116.66666666666667 lm/W	2,800 lm
911401511522	SM303C P24 930 PSU VWB	-	3000 K	>90	94 lm/W	2,260 lm
911401511548	SM303C P24 950 PSU VWB PLUS	55 degree(s)	5000 K	90	109.375 lm/W	2,625 lm
911401511648	SM303C P24 950 PSU WB PLUS	38 degree(s)	5000 K	90	114.375 lm/W	2,745 lm
911401511748	SM303C P28 927 PSU MB PLUS	24 degree(s)	2700 K	90	98.57142857142857 lm/W	2,760 lm
911401511848	SM303C P28 927 PSU NB PLUS	15 x 15 degree(s)	2700 K	90	99.64285714285714 lm/W	2,790 lm
911401511948	SM303C P28 927 PSU VWB PLUS	55 degree(s)	2700 K	90	96.78571428571429 lm/W	2,710 lm
911401512022	SM303C P24 940 PSU NB	-	4000 K	>90	100 lm/W	2,400 lm
911401512048	SM303C P28 927 PSU WB PLUS	38 degree(s)	2700 K	90	100.89285714285714 lm/W	2,825 lm
911401512122	SM303C P24 940 PSU MB	-	4000 K	>90	101 lm/W	2,420 lm
911401512148	SM303C P28 930 PSU MB PLUS	24 degree(s)	3000 K	90	106.25 lm/W	2,975 lm
911401512222	SM303C P24 940 PSU WB	-	4000 K	>90	102 lm/W	2,450 lm
911401512248	SM303C P28 930 PSU NB PLUS	15 x 15 degree(s)	3000 K	90	106.07142857142857 lm/W	2,970 lm
911401512348	SM303C P28 930 PSU VWB PLUS	55 degree(s)	3000 K	90	102.32142857142857 lm/W	2,865 lm
911401512422	SM303C P24 950 PSU NB	-	5000 K	>90	98 lm/W	2,350 lm
911401512448	SM303C P28 930 PSU WB PLUS	38 degree(s)	3000 K	90	106.07142857142857 lm/W	2,970 lm
911401512522	SM303C P24 950 PSU MB	-	5000 K	>90	99 lm/W	2,380 lm
911401512548	SM303C P28 940 PSU MB PLUS	24 degree(s)	4000 K	90	109.82142857142857 lm/W	3,075 lm
911401512622	SM303C P24 950 PSU WB	-	5000 K	>90	100 lm/W	2,400 lm
911401512648	SM303C P28 940 PSU NB PLUS	15 x 15 degree(s)	4000 K	90	111.42857142857143 lm/W	3,120 lm
911401512722	SM303C P24 950 PSU VWB	-	5000 K	>90	99 lm/W	2,380 lm

GreenSpace Surface Mount

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401512748	SM303C P28 940 PSU VWB PLUS	55 degree(s)	4000 K	90	106.96428571428571 lm/W	2,995 lm
911401512848	SM303C P28 940 PSU WB PLUS	38 degree(s)	4000 K	90	111.07142857142857 lm/W	3,110 lm
911401512948	SM303C P28 950 PSU MB PLUS	24 degree(s)	5000 K	90	111.60714285714286 lm/W	3,125 lm
911401513048	SM303C P28 950 PSU NB PLUS	15 x 15 degree(s)	5000 K	90	111.42857142857143 lm/W	3,120 lm
911401513148	SM303C P28 950 PSU VWB PLUS	55 degree(s)	5000 K	90	107.5 lm/W	3,010 lm
911401513248	SM303C P28 950 PSU WB PLUS	38 degree(s)	5000 K	90	111.42857142857143 lm/W	3,120 lm
911401514822	SM303C P28 927 PSU NB	-	2700 K	>90	83 lm/W	2,320 lm
911401514922	SM303C P28 927 PSU MB	-	2700 K	>90	83 lm/W	2,320 lm
911401515022	SM303C P28 927 PSU WB	-	2700 K	>90	84 lm/W	2,350 lm
911401515122	SM303C P28 927 PSU VWB	-	2700 K	>90	83 lm/W	2,320 lm
911401515222	SM303C P28 930 PSU NB	-	3000 K	>90	89 lm/W	2,490 lm
911401515322	SM303C P28 930 PSU MB	-	3000 K	>90	88 lm/W	2,460 lm
911401515422	SM303C P28 930 PSU WB	-	3000 K	>90	89 lm/W	2,490 lm
911401515522	SM303C P28 930 PSU VWB	-	3000 K	>90	88 lm/W	2,460 lm
911401516022	SM303C P28 940 PSU NB	-	4000 K	>90	97 lm/W	2,720 lm
911401516122	SM303C P28 940 PSU MB	-	4000 K	>90	96 lm/W	2,690 lm
911401516222	SM303C P28 940 PSU WB	-	4000 K	>90	98 lm/W	2,740 lm
911401516322	SM303C P28 940 PSU VWB	-	4000 K	>90	96 lm/W	2,690 lm
911401516422	SM303C P28 950 PSU NB	-	5000 K	>90	95 lm/W	2,660 lm
911401516522	SM303C P28 950 PSU MB	-	5000 K	>90	94 lm/W	2,630 lm
911401516622	SM303C P28 950 PSU WB	-	5000 K	>90	96 lm/W	2,690 lm
911401516722	SM303C P28 950 PSU VWB	-	5000 K	>90	96 lm/W	2,690 lm
911401517822	SM304C P10 927 PSU MB	-	2700 K	>90	71 lm/W	730 lm
911401517922	SM304C P10 927 PSU WB	-	2700 K	>90	75 lm/W	770 lm
911401518022	SM304C P10 930 PSU MB	-	3000 K	>90	76 lm/W	770 lm
911401518122	SM304C P10 930 PSU WB	-	3000 K	>90	78 lm/W	810 lm
911401518422	SM304C P10 940 PSU MB	-	4000 K	>90	80 lm/W	810 lm
911401518522	SM304C P10 940 PSU WB	-	4000 K	>90	83 lm/W	860 lm
911401518622	SM304C P10 950 PSU MB	-	5000 K	>90	86 lm/W	870 lm
911401518722	SM304C P10 950 PSU WB	-	5000 K	>90	88 lm/W	890 lm
911401519822	SM304C P12 927 PSU MB	-	2700 K	>90	70 lm/W	860 lm
911401519922	SM304C P12 927 PSU WB	-	2700 K	>90	73 lm/W	890 lm
911401520022	SM304C P12 930 PSU MB	-	3000 K	>90	75 lm/W	910 lm
911401520122	SM304C P12 930 PSU WB	-	3000 K	>90	77 lm/W	940 lm
911401520422	SM304C P12 940 PSU MB	-	4000 K	>90	78 lm/W	950 lm
911401520522	SM304C P12 940 PSU WB	-	4000 K	>90	81 lm/W	990 lm
911401520622	SM304C P12 950 PSU MB	-	5000 K	>90	84 lm/W	1,010 lm
911401520722	SM304C P12 950 PSU WB	-	5000 K	>90	86 lm/W	1,050 lm
911401521822	SM304C P15 927 PSU MB	-	2700 K	>90	70 lm/W	1,050 lm
911401521922	SM304C P15 927 PSU WB	-	2700 K	>90	73 lm/W	1,100 lm
911401522022	SM304C P15 930 PSU MB	-	3000 K	>90	75 lm/W	1,130 lm
911401522122	SM304C P15 930 PSU WB	-	3000 K	>90	78 lm/W	1,170 lm
911401522422	SM304C P15 940 PSU MB	-	4000 K	>90	78 lm/W	1,170 lm
911401522522	SM304C P15 940 PSU WB	-	4000 K	>90	82 lm/W	1,230 lm
911401522622	SM304C P15 950 PSU MB	-	5000 K	>90	84 lm/W	1,260 lm
911401522722	SM304C P15 950 PSU WB	-	5000 K	>90	88 lm/W	1,320 lm
911401541248	SM303C P8S 927 PSU MB PLUS	24 degree(s)	2700 K	90	97 lm/W	882 lm
911401541348	SM303C P8S 927 PSU NB PLUS	15 x 15 degree(s)	2700 K	90	90 lm/W	883 lm

GreenSpace Surface Mount

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401541448	SM303C P8S 927 PSU VWB PLUS	55 degree(s)	2700 K	90	96 lm/W	884 lm
911401541548	SM303C P8S 927 PSU WB PLUS	38 degree(s)	2700 K	90	102 lm/W	885 lm
911401541648	SM303C P8S 930 PSU MB PLUS	24 degree(s)	3000 K	90	97 lm/W	886 lm
911401541748	SM303C P8S 930 PSU NB PLUS	15 x 15 degree(s)	3000 K	90	90 lm/W	887 lm
911401541848	SM303C P8S 930 PSU VWB PLUS	55 degree(s)	3000 K	90	96 lm/W	888 lm
911401541948	SM303C P8S 930 PSU WB PLUS	38 degree(s)	3000 K	90	103 lm/W	889 lm
911401542048	SM303C P8S 940 PSU MB PLUS	24 degree(s)	4000 K	90	106 lm/W	890 lm
911401542148	SM303C P8S 940 PSU NB PLUS	15 x 15 degree(s)	4000 K	90	98 lm/W	891 lm
911401542248	SM303C P8S 940 PSU VWB PLUS	55 degree(s)	4000 K	90	105 lm/W	892 lm
911401542348	SM303C P8S 940 PSU WB PLUS	38 degree(s)	4000 K	90	110 lm/W	893 lm
911401542448	SM303C P8S 950 PSU MB PLUS	24 degree(s)	5000 K	90	101 lm/W	894 lm
911401542548	SM303C P8S 950 PSU NB PLUS	15 x 15 degree(s)	5000 K	90	94 lm/W	895 lm
911401542648	SM303C P8S 950 PSU VWB PLUS	55 degree(s)	5000 K	90	101 lm/W	896 lm
911401542748	SM303C P8S 950 PSU WB PLUS	38 degree(s)	5000 K	90	108 lm/W	897 lm
911401582812	SM303C P6S 927 PSU NB	-	2700 K	>90	76 lm/W	460 lm
911401582912	SM303C P6S 927 PSU MB	-	2700 K	>90	84 lm/W	500 lm
911401583012	SM303C P6S 927 PSU WB	-	2700 K	>90	89 lm/W	530 lm
911401583112	SM303C P6S 927 PSU VWB	-	2700 K	>90	84 lm/W	500 lm
911401583212	SM303C P6S 930 PSU NB	-	3000 K	>90	77 lm/W	460 lm
911401583312	SM303C P6S 930 PSU MB	-	3000 K	>90	86 lm/W	520 lm
911401583412	SM303C P6S 930 PSU WB	-	3000 K	>90	91 lm/W	550 lm
911401583512	SM303C P6S 930 PSU VWB	-	3000 K	>90	87 lm/W	520 lm
911401584012	SM303C P6S 940 PSU NB	-	4000 K	>90	80 lm/W	480 lm
911401584112	SM303C P6S 940 PSU MB	-	4000 K	>90	89 lm/W	530 lm
911401584212	SM303C P6S 940 PSU WB	-	4000 K	>90	94 lm/W	560 lm
911401584312	SM303C P6S 940 PSU VWB	-	4000 K	>90	91 lm/W	550 lm
911401584412	SM303C P6S 950 PSU NB	-	5000 K	>90	81 lm/W	490 lm
911401584512	SM303C P6S 950 PSU MB	-	5000 K	>90	90 lm/W	540 lm
911401584612	SM303C P6S 950 PSU WB	-	5000 K	>90	97 lm/W	580 lm
911401584712	SM303C P6S 950 PSU VWB	-	5000 K	>90	93 lm/W	560 lm
911401586812	SM303C P9S 927 PSU NB	-	2700 K	>90	72 lm/W	650 lm
911401586912	SM303C P9S 927 PSU MB	-	2700 K	>90	80 lm/W	720 lm
911401587012	SM303C P9S 927 PSU WB	-	2700 K	>90	85 lm/W	770 lm
911401587112	SM303C P9S 927 PSU VWB	-	2700 K	>90	81 lm/W	730 lm
911401587212	SM303C P9S 930 PSU NB	-	3000 K	>90	75 lm/W	680 lm
911401587312	SM303C P9S 930 PSU MB	-	3000 K	>90	83 lm/W	750 lm
911401587412	SM303C P9S 930 PSU WB	-	3000 K	>90	87 lm/W	780 lm
911401587512	SM303C P9S 930 PSU VWB	-	3000 K	>90	84 lm/W	760 lm
911401588012	SM303C P9S 940 PSU NB	-	4000 K	>90	77 lm/W	690 lm
911401588112	SM303C P9S 940 PSU MB	-	4000 K	>90	85 lm/W	770 lm
911401588212	SM303C P9S 940 PSU WB	-	4000 K	>90	90 lm/W	810 lm
911401588312	SM303C P9S 940 PSU VWB	-	4000 K	>90	87 lm/W	780 lm
911401588412	SM303C P9S 950 PSU NB	-	5000 K	>90	78 lm/W	700 lm
911401588512	SM303C P9S 950 PSU MB	-	5000 K	>90	87 lm/W	780 lm
911401588612	SM303C P9S 950 PSU WB	-	5000 K	>90	93 lm/W	840 lm
911401588712	SM303C P9S 950 PSU VWB	-	5000 K	>90	89 lm/W	800 lm
911401506822	SM303C P20 927 PSU NB	-	2700 K	>90	80 lm/W	1,600 lm

GreenSpace Surface Mount

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401506922	SM303C P20 927 PSU MB	-	2700 K	>90	80 lm/W	1,600 lm
911401507022	SM303C P20 927 PSU WB	-	2700 K	>90	81 lm/W	1,620 lm
911401507122	SM303C P20 927 PSU VWB	-	2700 K	>90	81 lm/W	1,620 lm
911401507222	SM303C P20 930 PSU NB	-	3000 K	>90	88 lm/W	1,760 lm
911401507322	SM303C P20 930 PSU MB	-	3000 K	>90	88 lm/W	1,760 lm
911401507422	SM303C P20 930 PSU WB	-	3000 K	>90	90 lm/W	1,800 lm
911401507522	SM303C P20 930 PSU VWB	-	3000 K	>90	89 lm/W	1,780 lm
911401508022	SM303C P20 940 PSU NB	-	4000 K	>90	99 lm/W	1,980 lm
911401508122	SM303C P20 940 PSU MB	-	4000 K	>90	99 lm/W	1,980 lm
911401508222	SM303C P20 940 PSU WB	-	4000 K	>90	100 lm/W	2,000 lm
911401508322	SM303C P20 940 PSU VWB	-	4000 K	>90	100 lm/W	2,000 lm
911401508422	SM303C P20 950 PSU NB	-	5000 K	>90	102 lm/W	2,040 lm
911401508522	SM303C P20 950 PSU MB	-	5000 K	>90	102 lm/W	2,040 lm
911401508848	SM303C P20 927 PSU MB PLUS	24 degree(s)	2700 K	90	98.25 lm/W	1,965 lm
911401508948	SM303C P20 927 PSU NB PLUS	15 x 15 degree(s)	2700 K	90	96 lm/W	1,920 lm
911401509048	SM303C P20 927 PSU VWB PLUS	55 degree(s)	2700 K	90	97.5 lm/W	1,950 lm
911401509148	SM303C P20 927 PSU WB PLUS	38 degree(s)	2700 K	90	99 lm/W	1,980 lm
911401509248	SM303C P20 930 PSU MB PLUS	24 degree(s)	3000 K	90	105.5 lm/W	2,110 lm
911401509348	SM303C P20 930 PSU NB PLUS	15 x 15 degree(s)	3000 K	90	103 lm/W	2,060 lm
911401509448	SM303C P20 930 PSU VWB PLUS	55 degree(s)	3000 K	90	104 lm/W	2,080 lm
911401509548	SM303C P20 930 PSU WB PLUS	38 degree(s)	3000 K	90	104.75 lm/W	2,095 lm
911401509648	SM303C P20 940 PSU MB PLUS	24 degree(s)	4000 K	90	110 lm/W	2,200 lm
911401509748	SM303C P20 940 PSU NB PLUS	15 x 15 degree(s)	4000 K	90	108.75 lm/W	2,175 lm
911401509848	SM303C P20 940 PSU VWB PLUS	55 degree(s)	4000 K	90	111.5 lm/W	2,230 lm
911401509948	SM303C P20 940 PSU WB PLUS	38 degree(s)	4000 K	90	110.75 lm/W	2,215 lm
911401510048	SM303C P20 950 PSU MB PLUS	24 degree(s)	5000 K	90	110.75 lm/W	2,215 lm
911401510148	SM303C P20 950 PSU NB PLUS	15 x 15 degree(s)	5000 K	90	108 lm/W	2,160 lm
911401539648	SM303C P8 927 PSU MB PLUS	24 degree(s)	2700 K	90	97 lm/W	866 lm
911401539748	SM303C P8 927 PSU NB PLUS	15 x 15 degree(s)	2700 K	90	90 lm/W	867 lm
911401539848	SM303C P8 927 PSU VWB PLUS	55 degree(s)	2700 K	90	96 lm/W	868 lm
911401539948	SM303C P8 927 PSU WB PLUS	38 degree(s)	2700 K	90	102 lm/W	869 lm
911401540048	SM303C P8 930 PSU MB PLUS	24 degree(s)	3000 K	90	97 lm/W	870 lm
911401540148	SM303C P8 930 PSU NB PLUS	15 x 15 degree(s)	3000 K	90	90 lm/W	871 lm
911401540248	SM303C P8 930 PSU VWB PLUS	55 degree(s)	3000 K	90	96 lm/W	872 lm
911401540348	SM303C P8 930 PSU WB PLUS	38 degree(s)	3000 K	90	103 lm/W	873 lm
911401540448	SM303C P8 940 PSU MB PLUS	24 degree(s)	4000 K	90	106 lm/W	874 lm
911401540548	SM303C P8 940 PSU NB PLUS	15 x 15 degree(s)	4000 K	90	98 lm/W	875 lm
911401540648	SM303C P8 940 PSU VWB PLUS	55 degree(s)	4000 K	90	105 lm/W	876 lm
911401540748	SM303C P8 940 PSU WB PLUS	38 degree(s)	4000 K	90	110 lm/W	877 lm
911401540848	SM303C P8 950 PSU MB PLUS	24 degree(s)	5000 K	90	101 lm/W	878 lm
911401540948	SM303C P8 950 PSU NB PLUS	15 x 15 degree(s)	5000 K	90	94 lm/W	879 lm
911401541048	SM303C P8 950 PSU VWB PLUS	55 degree(s)	5000 K	90	101 lm/W	880 lm
911401541148	SM303C P8 950 PSU WB PLUS	38 degree(s)	5000 K	90	108 lm/W	881 lm
911401574812	SM303C P6 927 PSU NB	-	2700 K	>90	76 lm/W	460 lm
911401574912	SM303C P6 927 PSU MB	-	2700 K	>90	84 lm/W	500 lm

GreenSpace Surface Mount

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401575012	SM303C P6 927 PSU WB	-	2700 K	>90	89 lm/W	530 lm
911401575112	SM303C P6 927 PSU VWB	-	2700 K	>90	84 lm/W	500 lm
911401575212	SM303C P6 930 PSU NB	-	3000 K	>90	77 lm/W	460 lm
911401575312	SM303C P6 930 PSU MB	-	3000 K	>90	86 lm/W	520 lm
911401575412	SM303C P6 930 PSU WB	-	3000 K	>90	91 lm/W	550 lm
911401575512	SM303C P6 930 PSU VWB	-	3000 K	>90	87 lm/W	520 lm
911401576012	SM303C P6 940 PSU NB	-	4000 K	>90	80 lm/W	480 lm
911401576112	SM303C P6 940 PSU MB	-	4000 K	>90	89 lm/W	530 lm
911401576212	SM303C P6 940 PSU WB	-	4000 K	>90	94 lm/W	560 lm
911401576312	SM303C P6 940 PSU VWB	-	4000 K	>90	91 lm/W	550 lm
911401576412	SM303C P6 950 PSU NB	-	5000 K	>90	81 lm/W	490 lm
911401576512	SM303C P6 950 PSU MB	-	5000 K	>90	90 lm/W	540 lm
911401576612	SM303C P6 950 PSU WB	-	5000 K	>90	97 lm/W	580 lm
911401576712	SM303C P6 950 PSU VWB	-	5000 K	>90	93 lm/W	560 lm
911401578812	SM303C P9 927 PSU NB	-	2700 K	>90	72 lm/W	650 lm
911401578912	SM303C P9 927 PSU MB	-	2700 K	>90	80 lm/W	720 lm
911401579012	SM303C P9 927 PSU WB	-	2700 K	>90	85 lm/W	770 lm
911401579112	SM303C P9 927 PSU VWB	-	2700 K	>90	81 lm/W	730 lm
911401579212	SM303C P9 930 PSU NB	-	3000 K	>90	75 lm/W	680 lm
911401579312	SM303C P9 930 PSU MB	-	3000 K	>90	83 lm/W	750 lm
911401579412	SM303C P9 930 PSU WB	-	3000 K	>90	87 lm/W	780 lm
911401579512	SM303C P9 930 PSU VWB	-	3000 K	>90	84 lm/W	760 lm
911401580012	SM303C P9 940 PSU NB	-	4000 K	>90	77 lm/W	690 lm
911401580112	SM303C P9 940 PSU MB	-	4000 K	>90	85 lm/W	770 lm
911401580212	SM303C P9 940 PSU WB	-	4000 K	>90	90 lm/W	810 lm
911401580312	SM303C P9 940 PSU VWB	-	4000 K	>90	87 lm/W	780 lm
911401580412	SM303C P9 950 PSU NB	-	5000 K	>90	78 lm/W	700 lm
911401580512	SM303C P9 950 PSU MB	-	5000 K	>90	87 lm/W	780 lm
911401580612	SM303C P9 950 PSU WB	-	5000 K	>90	93 lm/W	840 lm
911401580712	SM303C P9 950 PSU VWB	-	5000 K	>90	89 lm/W	800 lm

Operating and Electrical

Order Code	Full Product Name	Input Voltage	Power Consumption	Order Code	Full Product Name	Input Voltage	Power Consumption
911401513348	SP303P P8 927 PSU MB PLUS	100-242 V	8 W	911401592112	SP303P P6 940 PSU MB	200 to 240 V	5.4 W
911401513448	SP303P P8 927 PSU NB PLUS	100-242 V	8 W	911401592212	SP303P P6 940 PSU WB	200 to 240 V	5.4 W
911401513548	SP303P P8 927 PSU VWB PLUS	100-242 V	8 W	911401592312	SP303P P6 940 PSU VWB	200 to 240 V	5.4 W
911401513648	SP303P P8 927 PSU WB PLUS	100-242 V	8 W	911401592412	SP303P P6 950 PSU NB	200 to 240 V	5.4 W
911401513748	SP303P P8 930 PSU MB PLUS	100-242 V	8 W	911401592512	SP303P P6 950 PSU MB	200 to 240 V	5.4 W
911401513848	SP303P P8 930 PSU NB PLUS	100-242 V	8 W	911401592612	SP303P P6 950 PSU WB	200 to 240 V	5.4 W
911401513948	SP303P P8 930 PSU VWB PLUS	100-242 V	8 W	911401592712	SP303P P6 950 PSU VWB	200 to 240 V	5.4 W
911401514048	SP303P P8 930 PSU WB PLUS	100-242 V	8 W	911401594812	SP303P P9 927 PSU NB	200 to 240 V	8.1 W
911401514148	SP303P P8 940 PSU MB PLUS	100-242 V	8 W	911401594912	SP303P P9 927 PSU MB	200 to 240 V	8.1 W
911401514248	SP303P P8 940 PSU NB PLUS	100-242 V	8 W	911401595012	SP303P P9 927 PSU WB	200 to 240 V	8.1 W
911401514348	SP303P P8 940 PSU VWB PLUS	100-242 V	8 W	911401595112	SP303P P9 927 PSU VWB	200 to 240 V	8.1 W
911401514448	SP303P P8 940 PSU WB PLUS	100-242 V	8 W	911401595212	SP303P P9 930 PSU NB	200 to 240 V	8.1 W
911401514548	SP303P P8 950 PSU MB PLUS	100-242 V	8 W	911401595312	SP303P P9 930 PSU MB	200 to 240 V	8.1 W
911401514648	SP303P P8 950 PSU NB PLUS	100-242 V	8 W	911401595412	SP303P P9 930 PSU WB	200 to 240 V	8.1 W
911401514748	SP303P P8 950 PSU VWB PLUS	100-242 V	8 W	911401595512	SP303P P9 930 PSU VWB	200 to 240 V	8.1 W
911401514848	SP303P P8 950 PSU WB PLUS	100-242 V	8 W	911401596012	SP303P P9 940 PSU NB	200 to 240 V	8.1 W
911401592012	SP303P P6 940 PSU NB	200 to 240 V	5.4 W	911401596112	SP303P P9 940 PSU MB	200 to 240 V	8.1 W

GreenSpace Surface Mount

Order Code	Full Product Name	Input Voltage	Power Consumption
911401596212	SP303P P9 940 PSU WB	200 to 240 V	8.1 W
911401596312	SP303P P9 940 PSU VWB	200 to 240 V	8.1 W
911401596412	SP303P P9 950 PSU NB	200 to 240 V	8.1 W
911401596512	SP303P P9 950 PSU MB	200 to 240 V	8.1 W
911401596612	SP303P P9 950 PSU WB	200 to 240 V	8.1 W
911401596712	SP303P P9 950 PSU VWB	200 to 240 V	8.1 W
911401598812	SP303P P6S 927 PSU NB	200 to 240 V	5.4 W
911401598912	SP303P P6S 927 PSU MB	200 to 240 V	5.4 W
911401599012	SP303P P6S 927 PSU WB	200 to 240 V	5.4 W
911401599112	SP303P P6S 927 PSU VWB	200 to 240 V	5.4 W
911401599212	SP303P P6S 930 PSU NB	200 to 240 V	5.4 W
911401599312	SP303P P6S 930 PSU MB	200 to 240 V	5.4 W
911401599412	SP303P P6S 930 PSU WB	200 to 240 V	5.4 W
911401599512	SP303P P6S 930 PSU VWB	200 to 240 V	5.4 W
911401500022	SP303P P6S 940 PSU NB	200 to 240 V	5.4 W
911401500122	SP303P P6S 940 PSU MB	200 to 240 V	5.4 W
911401500222	SP303P P6S 940 PSU WB	200 to 240 V	5.4 W
911401500322	SP303P P6S 940 PSU VWB	200 to 240 V	5.4 W
911401500422	SP303P P6S 950 PSU NB	200 to 240 V	5.4 W
911401500522	SP303P P6S 950 PSU MB	200 to 240 V	5.4 W
911401500622	SP303P P6S 950 PSU WB	200 to 240 V	5.4 W
911401500722	SP303P P6S 950 PSU VWB	200 to 240 V	5.4 W
911401502822	SP303P P9S 927 PSU NB	200 to 240 V	8.1 W
911401502922	SP303P P9S 927 PSU MB	200 to 240 V	8.1 W
911401503022	SP303P P9S 927 PSU WB	200 to 240 V	8.1 W
911401503122	SP303P P9S 927 PSU VWB	200 to 240 V	8.1 W
911401503222	SP303P P9S 930 PSU NB	200 to 240 V	8.1 W
911401503322	SP303P P9S 930 PSU MB	200 to 240 V	8.1 W
911401503422	SP303P P9S 930 PSU WB	200 to 240 V	8.1 W
911401503522	SP303P P9S 930 PSU VWB	200 to 240 V	8.1 W
911401504022	SP303P P9S 940 PSU NB	200 to 240 V	8.1 W
911401504122	SP303P P9S 940 PSU MB	200 to 240 V	8.1 W
911401504222	SP303P P9S 940 PSU WB	200 to 240 V	8.1 W
911401504322	SP303P P9S 940 PSU VWB	200 to 240 V	8.1 W
911401504422	SP303P P9S 950 PSU NB	200 to 240 V	8.1 W
911401504522	SP303P P9S 950 PSU MB	200 to 240 V	8.1 W
911401504622	SP303P P9S 950 PSU WB	200 to 240 V	8.1 W
911401504722	SP303P P9S 950 PSU VWB	200 to 240 V	8.1 W
911401514948	SP303P P8S 927 PSU MB PLUS	100–242 V	8 W
911401515048	SP303P P8S 927 PSU NB PLUS	100–242 V	8 W
911401515148	SP303P P8S 927 PSU VWB PLUS	100–242 V	8 W
911401515248	SP303P P8S 927 PSU WB PLUS	100–242 V	8 W
911401515348	SP303P P8S 930 PSU MB PLUS	100–242 V	8 W
911401515448	SP303P P8S 930 PSU NB PLUS	100–242 V	8 W
911401515548	SP303P P8S 930 PSU VWB PLUS	100–242 V	8 W
911401515648	SP303P P8S 930 PSU WB PLUS	100–242 V	8 W
911401515748	SP303P P8S 940 PSU MB PLUS	100–242 V	8 W
911401515848	SP303P P8S 940 PSU NB PLUS	100–242 V	8 W
911401515948	SP303P P8S 940 PSU VWB PLUS	100–242 V	8 W
911401516048	SP303P P8S 940 PSU WB PLUS	100–242 V	8 W
911401516148	SP303P P8S 950 PSU MB PLUS	100–242 V	8 W
911401516248	SP303P P8S 950 PSU NB PLUS	100–242 V	8 W

Order Code	Full Product Name	Input Voltage	Power Consumption
911401516348	SP303P P8S 950 PSU VWB PLUS	100–242 V	8 W
911401516448	SP303P P8S 950 PSU WB PLUS	100–242 V	8 W
911401590812	SP303P P6 927 PSU NB	200 to 240 V	5.4 W
911401590912	SP303P P6 927 PSU MB	200 to 240 V	5.4 W
911401591012	SP303P P6 927 PSU WB	200 to 240 V	5.4 W
911401591112	SP303P P6 927 PSU VWB	200 to 240 V	5.4 W
911401591212	SP303P P6 930 PSU NB	200 to 240 V	5.4 W
911401591312	SP303P P6 930 PSU MB	200 to 240 V	5.4 W
911401591412	SP303P P6 930 PSU WB	200 to 240 V	5.4 W
911401591512	SP303P P6 930 PSU VWB	200 to 240 V	5.4 W
911401510248	SM303C P24 927 PSU MB PLUS	100–242 V	24 W
911401510348	SM303C P24 927 PSU NB PLUS	100–242 V	24 W
911401510448	SM303C P24 927 PSU VWB PLUS	100–242 V	24 W
911401510548	SM303C P24 927 PSU WB PLUS	100–242 V	24 W
911401510648	SM303C P24 930 PSU MB PLUS	100–242 V	24 W
911401510748	SM303C P24 930 PSU NB PLUS	100–242 V	24 W
911401510822	SM303C P24 927 PSU NB	200 to 240 V	21.6 W
911401510848	SM303C P24 930 PSU VWB PLUS	100–242 V	24 W
911401510922	SM303C P24 927 PSU MB	200 to 240 V	21.6 W
911401510948	SM303C P24 930 PSU WB PLUS	100–242 V	24 W
911401511022	SM303C P24 927 PSU WB	200 to 240 V	21.6 W
911401511048	SM303C P24 940 PSU MB PLUS	100–242 V	24 W
911401511122	SM303C P24 927 PSU VWB	200 to 240 V	21.6 W
911401511148	SM303C P24 940 PSU NB PLUS	100–242 V	24 W
911401511222	SM303C P24 930 PSU NB	200 to 240 V	21.6 W
911401511248	SM303C P24 940 PSU WB PLUS	100–242 V	24 W
911401511322	SM303C P24 930 PSU MB	200 to 240 V	21.6 W
911401511348	SM303C P24 950 PSU MB PLUS	100–242 V	24 W
911401511422	SM303C P24 930 PSU WB	200 to 240 V	21.6 W
911401511448	SM303C P24 950 PSU NB PLUS	100–242 V	24 W
911401511522	SM303C P24 930 PSU VWB	200 to 240 V	21.6 W
911401511548	SM303C P24 950 PSU VWB PLUS	100–242 V	24 W
911401511648	SM303C P24 950 PSU WB PLUS	100–242 V	24 W
911401511748	SM303C P28 927 PSU MB PLUS	100–242 V	28 W
911401511848	SM303C P28 927 PSU NB PLUS	100–242 V	28 W
911401511948	SM303C P28 927 PSU VWB PLUS	100–242 V	28 W
911401512022	SM303C P24 940 PSU NB	200 to 240 V	21.6 W
911401512048	SM303C P28 927 PSU WB PLUS	100–242 V	28 W
911401512122	SM303C P24 940 PSU MB	200 to 240 V	21.6 W
911401512148	SM303C P28 930 PSU MB PLUS	100–242 V	28 W
911401512222	SM303C P24 940 PSU WB	200 to 240 V	21.6 W
911401512248	SM303C P28 930 PSU NB PLUS	100–242 V	28 W
911401512348	SM303C P28 930 PSU VWB PLUS	100–242 V	28 W
911401512422	SM303C P24 950 PSU NB	200 to 240 V	21.6 W
911401512448	SM303C P28 930 PSU WB PLUS	100–242 V	28 W
911401512522	SM303C P24 950 PSU MB	200 to 240 V	21.6 W
911401512548	SM303C P28 940 PSU MB PLUS	100–242 V	28 W
911401512622	SM303C P24 950 PSU WB	200 to 240 V	21.6 W
911401512648	SM303C P28 940 PSU NB PLUS	100–242 V	28 W
911401512722	SM303C P24 950 PSU VWB	200 to 240 V	21.6 W
911401512748	SM303C P28 940 PSU VWB PLUS	100–242 V	28 W
911401512848	SM303C P28 940 PSU WB PLUS	100–242 V	28 W

GreenSpace Surface Mount

Order Code	Full Product Name	Input Voltage	Power Consumption
911401512948	SM303C P28 950 PSU MB PLUS	100–242 V	28 W
911401513048	SM303C P28 950 PSU NB PLUS	100–242 V	28 W
911401513148	SM303C P28 950 PSU VWB PLUS	100–242 V	28 W
911401513248	SM303C P28 950 PSU WB PLUS	100–242 V	28 W
911401514822	SM303C P28 927 PSU NB	200 to 240 V	25.2 W
911401514922	SM303C P28 927 PSU MB	200 to 240 V	25.2 W
911401515022	SM303C P28 927 PSU WB	200 to 240 V	25.2 W
911401515122	SM303C P28 927 PSU VWB	200 to 240 V	25.2 W
911401515222	SM303C P28 930 PSU NB	200 to 240 V	25.2 W
911401515322	SM303C P28 930 PSU MB	200 to 240 V	25.2 W
911401515422	SM303C P28 930 PSU WB	200 to 240 V	25.2 W
911401515522	SM303C P28 930 PSU VWB	200 to 240 V	25.2 W
911401516022	SM303C P28 940 PSU NB	200 to 240 V	25.2 W
911401516122	SM303C P28 940 PSU MB	200 to 240 V	25.2 W
911401516222	SM303C P28 940 PSU WB	200 to 240 V	25.2 W
911401516322	SM303C P28 940 PSU VWB	200 to 240 V	25.2 W
911401516422	SM303C P28 950 PSU NB	200 to 240 V	25.2 W
911401516522	SM303C P28 950 PSU MB	200 to 240 V	25.2 W
911401516622	SM303C P28 950 PSU WB	200 to 240 V	25.2 W
911401516722	SM303C P28 950 PSU VWB	200 to 240 V	25.2 W
911401517822	SM304C P10 927 PSU MB	200 to 240 V	11 W
911401517922	SM304C P10 927 PSU WB	200 to 240 V	11 W
911401518022	SM304C P10 930 PSU MB	200 to 240 V	11 W
911401518122	SM304C P10 930 PSU WB	200 to 240 V	11 W
911401518422	SM304C P10 940 PSU MB	200 to 240 V	11 W
911401518522	SM304C P10 940 PSU WB	200 to 240 V	11 W
911401518622	SM304C P10 950 PSU MB	200 to 240 V	11 W
911401518722	SM304C P10 950 PSU WB	200 to 240 V	11 W
911401519822	SM304C P12 927 PSU MB	200 to 240 V	10.8 W
911401519922	SM304C P12 927 PSU WB	200 to 240 V	10.8 W
911401520022	SM304C P12 930 PSU MB	200 to 240 V	10.8 W
911401520122	SM304C P12 930 PSU WB	200 to 240 V	10.8 W
911401520422	SM304C P12 940 PSU MB	200 to 240 V	10.8 W
911401520522	SM304C P12 940 PSU WB	200 to 240 V	10.8 W
911401520622	SM304C P12 950 PSU MB	200 to 240 V	10.8 W
911401520722	SM304C P12 950 PSU WB	200 to 240 V	10.8 W
911401521822	SM304C P15 927 PSU MB	200 to 240 V	13.5 W
911401521922	SM304C P15 927 PSU WB	200 to 240 V	13.5 W
911401522022	SM304C P15 930 PSU MB	200 to 240 V	13.5 W
911401522122	SM304C P15 930 PSU WB	200 to 240 V	13.5 W
911401522422	SM304C P15 940 PSU MB	200 to 240 V	13.5 W
911401522522	SM304C P15 940 PSU WB	200 to 240 V	13.5 W
911401522622	SM304C P15 950 PSU MB	200 to 240 V	13.5 W
911401522722	SM304C P15 950 PSU WB	200 to 240 V	13.5 W
911401541248	SM303C P8S 927 PSU MB PLUS	100–242 V	8 W
911401541348	SM303C P8S 927 PSU NB PLUS	100–242 V	8 W
911401541448	SM303C P8S 927 PSU VWB PLUS	100–242 V	8 W
911401541548	SM303C P8S 927 PSU WB PLUS	100–242 V	8 W
911401541648	SM303C P8S 930 PSU MB PLUS	100–242 V	8 W
911401541748	SM303C P8S 930 PSU NB PLUS	100–242 V	8 W
911401541848	SM303C P8S 930 PSU VWB PLUS	100–242 V	8 W
911401541948	SM303C P8S 930 PSU WB PLUS	100–242 V	8 W

Order Code	Full Product Name	Input Voltage	Power Consumption
911401542048	SM303C P8S 940 PSU MB PLUS	100–242 V	8 W
911401542148	SM303C P8S 940 PSU NB PLUS	100–242 V	8 W
911401542248	SM303C P8S 940 PSU VWB PLUS	100–242 V	8 W
911401542348	SM303C P8S 940 PSU WB PLUS	100–242 V	8 W
911401542448	SM303C P8S 950 PSU MB PLUS	100–242 V	8 W
911401542548	SM303C P8S 950 PSU NB PLUS	100–242 V	8 W
911401542648	SM303C P8S 950 PSU VWB PLUS	100–242 V	8 W
911401542748	SM303C P8S 950 PSU WB PLUS	100–242 V	8 W
911401582812	SM303C P6S 927 PSU NB	200 to 240 V	5.4 W
911401582912	SM303C P6S 927 PSU MB	200 to 240 V	5.4 W
911401583012	SM303C P6S 927 PSU WB	200 to 240 V	5.4 W
911401583112	SM303C P6S 927 PSU VWB	200 to 240 V	5.4 W
911401583212	SM303C P6S 930 PSU NB	200 to 240 V	5.4 W
911401583312	SM303C P6S 930 PSU MB	200 to 240 V	5.4 W
911401583412	SM303C P6S 930 PSU WB	200 to 240 V	5.4 W
911401583512	SM303C P6S 930 PSU VWB	200 to 240 V	5.4 W
911401584012	SM303C P6S 940 PSU NB	200 to 240 V	5.4 W
911401584112	SM303C P6S 940 PSU MB	200 to 240 V	5.4 W
911401584212	SM303C P6S 940 PSU WB	200 to 240 V	5.4 W
911401584312	SM303C P6S 940 PSU VWB	200 to 240 V	5.4 W
911401584412	SM303C P6S 950 PSU NB	200 to 240 V	5.4 W
911401584512	SM303C P6S 950 PSU MB	200 to 240 V	5.4 W
911401584612	SM303C P6S 950 PSU WB	200 to 240 V	5.4 W
911401584712	SM303C P6S 950 PSU VWB	200 to 240 V	5.4 W
911401586812	SM303C P9S 927 PSU NB	200 to 240 V	8.1 W
911401586912	SM303C P9S 927 PSU MB	200 to 240 V	8.1 W
911401587012	SM303C P9S 927 PSU WB	200 to 240 V	8.1 W
911401587112	SM303C P9S 927 PSU VWB	200 to 240 V	8.1 W
911401587212	SM303C P9S 930 PSU NB	200 to 240 V	8.1 W
911401587312	SM303C P9S 930 PSU MB	200 to 240 V	8.1 W
911401587412	SM303C P9S 930 PSU WB	200 to 240 V	8.1 W
911401587512	SM303C P9S 930 PSU VWB	200 to 240 V	8.1 W
911401588012	SM303C P9S 940 PSU NB	200 to 240 V	8.1 W
911401588112	SM303C P9S 940 PSU MB	200 to 240 V	8.1 W
911401588212	SM303C P9S 940 PSU WB	200 to 240 V	8.1 W
911401588312	SM303C P9S 940 PSU VWB	200 to 240 V	8.1 W
911401588412	SM303C P9S 950 PSU NB	200 to 240 V	8.1 W
911401588512	SM303C P9S 950 PSU MB	200 to 240 V	8.1 W
911401588612	SM303C P9S 950 PSU WB	200 to 240 V	8.1 W
911401588712	SM303C P9S 950 PSU VWB	200 to 240 V	8.1 W
911401506822	SM303C P20 927 PSU NB	200 to 240 V	18 W
911401506922	SM303C P20 927 PSU MB	200 to 240 V	18 W
911401507022	SM303C P20 927 PSU WB	200 to 240 V	18 W
911401507122	SM303C P20 927 PSU VWB	200 to 240 V	18 W
911401507222	SM303C P20 930 PSU NB	200 to 240 V	18 W
911401507322	SM303C P20 930 PSU MB	200 to 240 V	18 W
911401507422	SM303C P20 930 PSU WB	200 to 240 V	18 W
911401507522	SM303C P20 930 PSU VWB	200 to 240 V	18 W
911401508022	SM303C P20 940 PSU NB	200 to 240 V	18 W
911401508122	SM303C P20 940 PSU MB	200 to 240 V	18 W
911401508222	SM303C P20 940 PSU WB	200 to 240 V	18 W
911401508322	SM303C P20 940 PSU VWB	200 to 240 V	18 W

GreenSpace Surface Mount

Order Code	Full Product Name	Input Voltage	Power Consumption
911401508422	SM303C P20 950 PSU NB	200 to 240 V	18 W
911401508522	SM303C P20 950 PSU MB	200 to 240 V	18 W
911401508848	SM303C P20 927 PSU MB PLUS	100–242 V	20 W
911401508948	SM303C P20 927 PSU NB PLUS	100–242 V	20 W
911401509048	SM303C P20 927 PSU VWB PLUS	100–242 V	20 W
911401509148	SM303C P20 927 PSU WB PLUS	100–242 V	20 W
911401509248	SM303C P20 930 PSU MB PLUS	100–242 V	20 W
911401509348	SM303C P20 930 PSU NB PLUS	100–242 V	20 W
911401509448	SM303C P20 930 PSU VWB PLUS	100–242 V	20 W
911401509548	SM303C P20 930 PSU WB PLUS	100–242 V	20 W
911401509648	SM303C P20 940 PSU MB PLUS	100–242 V	20 W
911401509748	SM303C P20 940 PSU NB PLUS	100–242 V	20 W
911401509848	SM303C P20 940 PSU VWB PLUS	100–242 V	20 W
911401509948	SM303C P20 940 PSU WB PLUS	100–242 V	20 W
911401510048	SM303C P20 950 PSU MB PLUS	100–242 V	20 W
911401510148	SM303C P20 950 PSU NB PLUS	100–242 V	20 W
911401539648	SM303C P8 927 PSU MB PLUS	100–242 V	8 W
911401539748	SM303C P8 927 PSU NB PLUS	100–242 V	8 W
911401539848	SM303C P8 927 PSU VWB PLUS	100–242 V	8 W
911401539948	SM303C P8 927 PSU WB PLUS	100–242 V	8 W
911401540048	SM303C P8 930 PSU MB PLUS	100–242 V	8 W
911401540148	SM303C P8 930 PSU NB PLUS	100–242 V	8 W
911401540248	SM303C P8 930 PSU VWB PLUS	100–242 V	8 W
911401540348	SM303C P8 930 PSU WB PLUS	100–242 V	8 W
911401540448	SM303C P8 940 PSU MB PLUS	100–242 V	8 W
911401540548	SM303C P8 940 PSU NB PLUS	100–242 V	8 W
911401540648	SM303C P8 940 PSU VWB PLUS	100–242 V	8 W
911401540748	SM303C P8 940 PSU WB PLUS	100–242 V	8 W
911401540848	SM303C P8 950 PSU MB PLUS	100–242 V	8 W
911401540948	SM303C P8 950 PSU NB PLUS	100–242 V	8 W
911401541048	SM303C P8 950 PSU VWB PLUS	100–242 V	8 W
911401541148	SM303C P8 950 PSU WB PLUS	100–242 V	8 W

Order Code	Full Product Name	Input Voltage	Power Consumption
911401574812	SM303C P6 927 PSU NB	200 to 240 V	5.4 W
911401574912	SM303C P6 927 PSU MB	200 to 240 V	5.4 W
911401575012	SM303C P6 927 PSU WB	200 to 240 V	5.4 W
911401575112	SM303C P6 927 PSU VWB	200 to 240 V	5.4 W
911401575212	SM303C P6 930 PSU NB	200 to 240 V	5.4 W
911401575312	SM303C P6 930 PSU MB	200 to 240 V	5.4 W
911401575412	SM303C P6 930 PSU WB	200 to 240 V	5.4 W
911401575512	SM303C P6 930 PSU VWB	200 to 240 V	5.4 W
911401576012	SM303C P6 940 PSU NB	200 to 240 V	5.4 W
911401576112	SM303C P6 940 PSU MB	200 to 240 V	5.4 W
911401576212	SM303C P6 940 PSU WB	200 to 240 V	5.4 W
911401576312	SM303C P6 940 PSU VWB	200 to 240 V	5.4 W
911401576412	SM303C P6 950 PSU NB	200 to 240 V	5.4 W
911401576512	SM303C P6 950 PSU MB	200 to 240 V	5.4 W
911401576612	SM303C P6 950 PSU WB	200 to 240 V	5.4 W
911401576712	SM303C P6 950 PSU VWB	200 to 240 V	5.4 W
911401578812	SM303C P9 927 PSU NB	200 to 240 V	8.1 W
911401578912	SM303C P9 927 PSU MB	200 to 240 V	8.1 W
911401579012	SM303C P9 927 PSU WB	200 to 240 V	8.1 W
911401579112	SM303C P9 927 PSU VWB	200 to 240 V	8.1 W
911401579212	SM303C P9 930 PSU NB	200 to 240 V	8.1 W
911401579312	SM303C P9 930 PSU MB	200 to 240 V	8.1 W
911401579412	SM303C P9 930 PSU WB	200 to 240 V	8.1 W
911401579512	SM303C P9 930 PSU VWB	200 to 240 V	8.1 W
911401580012	SM303C P9 940 PSU NB	200 to 240 V	8.1 W
911401580112	SM303C P9 940 PSU MB	200 to 240 V	8.1 W
911401580212	SM303C P9 940 PSU WB	200 to 240 V	8.1 W
911401580312	SM303C P9 940 PSU VWB	200 to 240 V	8.1 W
911401580412	SM303C P9 950 PSU NB	200 to 240 V	8.1 W
911401580512	SM303C P9 950 PSU MB	200 to 240 V	8.1 W
911401580612	SM303C P9 950 PSU WB	200 to 240 V	8.1 W
911401580712	SM303C P9 950 PSU VWB	200 to 240 V	8.1 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401513348	SP303P P8 927 PSU MB PLUS	Fixed
911401513448	SP303P P8 927 PSU NB PLUS	Fixed
911401513548	SP303P P8 927 PSU VWB PLUS	Fixed
911401513648	SP303P P8 927 PSU WB PLUS	Fixed
911401513748	SP303P P8 930 PSU MB PLUS	Fixed
911401513848	SP303P P8 930 PSU NB PLUS	Fixed
911401513948	SP303P P8 930 PSU VWB PLUS	Fixed
911401514048	SP303P P8 930 PSU WB PLUS	Fixed
911401514148	SP303P P8 940 PSU MB PLUS	Fixed
911401514248	SP303P P8 940 PSU NB PLUS	Fixed
911401514348	SP303P P8 940 PSU VWB PLUS	Fixed
911401514448	SP303P P8 940 PSU WB PLUS	Fixed
911401514548	SP303P P8 950 PSU MB PLUS	Fixed
911401514648	SP303P P8 950 PSU NB PLUS	Fixed
911401514748	SP303P P8 950 PSU VWB PLUS	Fixed
911401514848	SP303P P8 950 PSU WB PLUS	Fixed

Order Code	Full Product Name	Dimmable
911401592012	SP303P P6 940 PSU NB	No
911401592112	SP303P P6 940 PSU MB	No
911401592212	SP303P P6 940 PSU WB	No
911401592312	SP303P P6 940 PSU VWB	No
911401592412	SP303P P6 950 PSU NB	No
911401592512	SP303P P6 950 PSU MB	No
911401592612	SP303P P6 950 PSU WB	No
911401592712	SP303P P6 950 PSU VWB	No
911401594812	SP303P P9 927 PSU NB	No
911401594912	SP303P P9 927 PSU MB	No
911401595012	SP303P P9 927 PSU WB	No
911401595112	SP303P P9 927 PSU VWB	No
911401595212	SP303P P9 930 PSU NB	No
911401595312	SP303P P9 930 PSU MB	No
911401595412	SP303P P9 930 PSU WB	No
911401595512	SP303P P9 930 PSU VWB	No

GreenSpace Surface Mount

Order Code	Full Product Name	Dimmable
911401596012	SP303P P9 940 PSU NB	No
911401596112	SP303P P9 940 PSU MB	No
911401596212	SP303P P9 940 PSU WB	No
911401596312	SP303P P9 940 PSU VWB	No
911401596412	SP303P P9 950 PSU NB	No
911401596512	SP303P P9 950 PSU MB	No
911401596612	SP303P P9 950 PSU WB	No
911401596712	SP303P P9 950 PSU VWB	No
911401598812	SP303P P6S 927 PSU NB	No
911401598912	SP303P P6S 927 PSU MB	No
911401599012	SP303P P6S 927 PSU WB	No
911401599112	SP303P P6S 927 PSU VWB	No
911401599212	SP303P P6S 930 PSU NB	No
911401599312	SP303P P6S 930 PSU MB	No
911401599412	SP303P P6S 930 PSU WB	No
911401599512	SP303P P6S 930 PSU VWB	No
911401500022	SP303P P6S 940 PSU NB	No
911401500122	SP303P P6S 940 PSU MB	No
911401500222	SP303P P6S 940 PSU WB	No
911401500322	SP303P P6S 940 PSU VWB	No
911401500422	SP303P P6S 950 PSU NB	No
911401500522	SP303P P6S 950 PSU MB	No
911401500622	SP303P P6S 950 PSU WB	No
911401500722	SP303P P6S 950 PSU VWB	No
911401502822	SP303P P9S 927 PSU NB	No
911401502922	SP303P P9S 927 PSU MB	No
911401503022	SP303P P9S 927 PSU WB	No
911401503122	SP303P P9S 927 PSU VWB	No
911401503222	SP303P P9S 930 PSU NB	No
911401503322	SP303P P9S 930 PSU MB	No
911401503422	SP303P P9S 930 PSU WB	No
911401503522	SP303P P9S 930 PSU VWB	No
911401504022	SP303P P9S 940 PSU NB	No
911401504122	SP303P P9S 940 PSU MB	No
911401504222	SP303P P9S 940 PSU WB	No
911401504322	SP303P P9S 940 PSU VWB	No
911401504422	SP303P P9S 950 PSU NB	No
911401504522	SP303P P9S 950 PSU MB	No
911401504622	SP303P P9S 950 PSU WB	No
911401504722	SP303P P9S 950 PSU VWB	No
911401514948	SP303P P8S 927 PSU MB PLUS	Fixed
911401515048	SP303P P8S 927 PSU NB PLUS	Fixed
911401515148	SP303P P8S 927 PSU VWB PLUS	Fixed
911401515248	SP303P P8S 927 PSU WB PLUS	Fixed
911401515348	SP303P P8S 930 PSU MB PLUS	Fixed
911401515448	SP303P P8S 930 PSU NB PLUS	Fixed
911401515548	SP303P P8S 930 PSU VWB PLUS	Fixed
911401515648	SP303P P8S 930 PSU WB PLUS	Fixed
911401515748	SP303P P8S 940 PSU MB PLUS	Fixed
911401515848	SP303P P8S 940 PSU NB PLUS	Fixed
911401515948	SP303P P8S 940 PSU VWB PLUS	Fixed
911401516048	SP303P P8S 940 PSU WB PLUS	Fixed

Order Code	Full Product Name	Dimmable
911401516148	SP303P P8S 950 PSU MB PLUS	Fixed
911401516248	SP303P P8S 950 PSU NB PLUS	Fixed
911401516348	SP303P P8S 950 PSU VWB PLUS	Fixed
911401516448	SP303P P8S 950 PSU WB PLUS	Fixed
911401590812	SP303P P6 927 PSU NB	No
911401590912	SP303P P6 927 PSU MB	No
911401591012	SP303P P6 927 PSU WB	No
911401591112	SP303P P6 927 PSU VWB	No
911401591212	SP303P P6 930 PSU NB	No
911401591312	SP303P P6 930 PSU MB	No
911401591412	SP303P P6 930 PSU WB	No
911401591512	SP303P P6 930 PSU VWB	No
911401510248	SM303C P24 927 PSU MB PLUS	Fixed
911401510348	SM303C P24 927 PSU NB PLUS	Fixed
911401510448	SM303C P24 927 PSU VWB PLUS	Fixed
911401510548	SM303C P24 927 PSU WB PLUS	Fixed
911401510648	SM303C P24 930 PSU MB PLUS	Fixed
911401510748	SM303C P24 930 PSU NB PLUS	Fixed
911401510822	SM303C P24 927 PSU NB	No
911401510848	SM303C P24 930 PSU VWB PLUS	Fixed
911401510922	SM303C P24 927 PSU MB	No
911401510948	SM303C P24 930 PSU WB PLUS	Fixed
911401511022	SM303C P24 927 PSU WB	No
911401511048	SM303C P24 940 PSU MB PLUS	Fixed
911401511122	SM303C P24 927 PSU VWB	No
911401511148	SM303C P24 940 PSU NB PLUS	Fixed
911401511222	SM303C P24 930 PSU NB	No
911401511248	SM303C P24 940 PSU WB PLUS	Fixed
911401511322	SM303C P24 930 PSU MB	No
911401511348	SM303C P24 950 PSU MB PLUS	Fixed
911401511422	SM303C P24 930 PSU WB	No
911401511448	SM303C P24 950 PSU NB PLUS	Fixed
911401511522	SM303C P24 930 PSU VWB	No
911401511548	SM303C P24 950 PSU VWB PLUS	Fixed
911401511648	SM303C P24 950 PSU WB PLUS	Fixed
911401511748	SM303C P28 927 PSU MB PLUS	Fixed
911401511848	SM303C P28 927 PSU NB PLUS	Fixed
911401511948	SM303C P28 927 PSU VWB PLUS	Fixed
911401512022	SM303C P24 940 PSU NB	No
911401512048	SM303C P28 927 PSU WB PLUS	Fixed
911401512122	SM303C P24 940 PSU MB	No
911401512148	SM303C P28 930 PSU MB PLUS	Fixed
911401512222	SM303C P24 940 PSU WB	No
911401512248	SM303C P28 930 PSU NB PLUS	Fixed
911401512348	SM303C P28 930 PSU VWB PLUS	Fixed
911401512422	SM303C P24 950 PSU NB	No
911401512448	SM303C P28 930 PSU WB PLUS	Fixed
911401512522	SM303C P24 950 PSU MB	No
911401512548	SM303C P28 940 PSU MB PLUS	Fixed
911401512622	SM303C P24 950 PSU WB	No
911401512648	SM303C P28 940 PSU NB PLUS	Fixed
911401512722	SM303C P24 950 PSU VWB	No

GreenSpace Surface Mount

Order Code	Full Product Name	Dimmable
911401512748	SM303C P28 940 PSU VWB PLUS	Fixed
911401512848	SM303C P28 940 PSU WB PLUS	Fixed
911401512948	SM303C P28 950 PSU MB PLUS	Fixed
911401513048	SM303C P28 950 PSU NB PLUS	Fixed
911401513148	SM303C P28 950 PSU VWB PLUS	Fixed
911401513248	SM303C P28 950 PSU WB PLUS	Fixed
911401514822	SM303C P28 927 PSU NB	No
911401514922	SM303C P28 927 PSU MB	No
911401515022	SM303C P28 927 PSU WB	No
911401515122	SM303C P28 927 PSU VWB	No
911401515222	SM303C P28 930 PSU NB	No
911401515322	SM303C P28 930 PSU MB	No
911401515422	SM303C P28 930 PSU WB	No
911401515522	SM303C P28 930 PSU VWB	No
911401516022	SM303C P28 940 PSU NB	No
911401516122	SM303C P28 940 PSU MB	No
911401516222	SM303C P28 940 PSU WB	No
911401516322	SM303C P28 940 PSU VWB	No
911401516422	SM303C P28 950 PSU NB	No
911401516522	SM303C P28 950 PSU MB	No
911401516622	SM303C P28 950 PSU WB	No
911401516722	SM303C P28 950 PSU VWB	No
911401517822	SM304C P10 927 PSU MB	No
911401517922	SM304C P10 927 PSU WB	No
911401518022	SM304C P10 930 PSU MB	No
911401518122	SM304C P10 930 PSU WB	No
911401518422	SM304C P10 940 PSU MB	No
911401518522	SM304C P10 940 PSU WB	No
911401518622	SM304C P10 950 PSU MB	No
911401518722	SM304C P10 950 PSU WB	No
911401519822	SM304C P12 927 PSU MB	No
911401519922	SM304C P12 927 PSU WB	No
911401520022	SM304C P12 930 PSU MB	No
911401520122	SM304C P12 930 PSU WB	No
911401520422	SM304C P12 940 PSU MB	No
911401520522	SM304C P12 940 PSU WB	No
911401520622	SM304C P12 950 PSU MB	No
911401520722	SM304C P12 950 PSU WB	No
911401521822	SM304C P15 927 PSU MB	No
911401521922	SM304C P15 927 PSU WB	No
911401522022	SM304C P15 930 PSU MB	No
911401522122	SM304C P15 930 PSU WB	No
911401522422	SM304C P15 940 PSU MB	No
911401522522	SM304C P15 940 PSU WB	No
911401522622	SM304C P15 950 PSU MB	No
911401522722	SM304C P15 950 PSU WB	No
911401541248	SM303C P8S 927 PSU MB PLUS	Fixed
911401541348	SM303C P8S 927 PSU NB PLUS	Fixed
911401541448	SM303C P8S 927 PSU VWB PLUS	Fixed
911401541548	SM303C P8S 927 PSU WB PLUS	Fixed
911401541648	SM303C P8S 930 PSU MB PLUS	Fixed
911401541748	SM303C P8S 930 PSU NB PLUS	Fixed

Order Code	Full Product Name	Dimmable
911401541848	SM303C P8S 930 PSU VWB PLUS	Fixed
911401541948	SM303C P8S 930 PSU WB PLUS	Fixed
911401542048	SM303C P8S 940 PSU MB PLUS	Fixed
911401542148	SM303C P8S 940 PSU NB PLUS	Fixed
911401542248	SM303C P8S 940 PSU VWB PLUS	Fixed
911401542348	SM303C P8S 940 PSU WB PLUS	Fixed
911401542448	SM303C P8S 950 PSU MB PLUS	Fixed
911401542548	SM303C P8S 950 PSU NB PLUS	Fixed
911401542648	SM303C P8S 950 PSU VWB PLUS	Fixed
911401542748	SM303C P8S 950 PSU WB PLUS	Fixed
911401582812	SM303C P6S 927 PSU NB	No
911401582912	SM303C P6S 927 PSU MB	No
911401583012	SM303C P6S 927 PSU WB	No
911401583112	SM303C P6S 927 PSU VWB	No
911401583212	SM303C P6S 930 PSU NB	No
911401583312	SM303C P6S 930 PSU MB	No
911401583412	SM303C P6S 930 PSU WB	No
911401583512	SM303C P6S 930 PSU VWB	No
911401584012	SM303C P6S 940 PSU NB	No
911401584112	SM303C P6S 940 PSU MB	No
911401584212	SM303C P6S 940 PSU WB	No
911401584312	SM303C P6S 940 PSU VWB	No
911401584412	SM303C P6S 950 PSU NB	No
911401584512	SM303C P6S 950 PSU MB	No
911401584612	SM303C P6S 950 PSU WB	No
911401584712	SM303C P6S 950 PSU VWB	No
911401586812	SM303C P9S 927 PSU NB	No
911401586912	SM303C P9S 927 PSU MB	No
911401587012	SM303C P9S 927 PSU WB	No
911401587112	SM303C P9S 927 PSU VWB	No
911401587212	SM303C P9S 930 PSU NB	No
911401587312	SM303C P9S 930 PSU MB	No
911401587412	SM303C P9S 930 PSU WB	No
911401587512	SM303C P9S 930 PSU VWB	No
911401588012	SM303C P9S 940 PSU NB	No
911401588112	SM303C P9S 940 PSU MB	No
911401588212	SM303C P9S 940 PSU WB	No
911401588312	SM303C P9S 940 PSU VWB	No
911401588412	SM303C P9S 950 PSU NB	No
911401588512	SM303C P9S 950 PSU MB	No
911401588612	SM303C P9S 950 PSU WB	No
911401588712	SM303C P9S 950 PSU VWB	No
911401506822	SM303C P20 927 PSU NB	No
911401506922	SM303C P20 927 PSU MB	No
911401507022	SM303C P20 927 PSU WB	No
911401507122	SM303C P20 927 PSU VWB	No
911401507222	SM303C P20 930 PSU NB	No
911401507322	SM303C P20 930 PSU MB	No
911401507422	SM303C P20 930 PSU WB	No
911401507522	SM303C P20 930 PSU VWB	No
911401508022	SM303C P20 940 PSU NB	No
911401508122	SM303C P20 940 PSU MB	No

GreenSpace Surface Mount

Order Code	Full Product Name	Dimmable
911401508222	SM303C P20 940 PSU WB	No
911401508322	SM303C P20 940 PSU VWB	No
911401508422	SM303C P20 950 PSU NB	No
911401508522	SM303C P20 950 PSU MB	No
911401508848	SM303C P20 927 PSU MB PLUS	Fixed
911401508948	SM303C P20 927 PSU NB PLUS	Fixed
911401509048	SM303C P20 927 PSU VWB PLUS	Fixed
911401509148	SM303C P20 927 PSU WB PLUS	Fixed
911401509248	SM303C P20 930 PSU MB PLUS	Fixed
911401509348	SM303C P20 930 PSU NB PLUS	Fixed
911401509448	SM303C P20 930 PSU VWB PLUS	Fixed
911401509548	SM303C P20 930 PSU WB PLUS	Fixed
911401509648	SM303C P20 940 PSU MB PLUS	Fixed
911401509748	SM303C P20 940 PSU NB PLUS	Fixed
911401509848	SM303C P20 940 PSU VWB PLUS	Fixed
911401509948	SM303C P20 940 PSU WB PLUS	Fixed
911401510048	SM303C P20 950 PSU MB PLUS	Fixed
911401510148	SM303C P20 950 PSU NB PLUS	Fixed
911401539648	SM303C P8 927 PSU MB PLUS	Fixed
911401539748	SM303C P8 927 PSU NB PLUS	Fixed
911401539848	SM303C P8 927 PSU VWB PLUS	Fixed
911401539948	SM303C P8 927 PSU WB PLUS	Fixed
911401540048	SM303C P8 930 PSU MB PLUS	Fixed
911401540148	SM303C P8 930 PSU NB PLUS	Fixed
911401540248	SM303C P8 930 PSU VWB PLUS	Fixed
911401540348	SM303C P8 930 PSU WB PLUS	Fixed
911401540448	SM303C P8 940 PSU MB PLUS	Fixed
911401540548	SM303C P8 940 PSU NB PLUS	Fixed
911401540648	SM303C P8 940 PSU VWB PLUS	Fixed
911401540748	SM303C P8 940 PSU WB PLUS	Fixed
911401540848	SM303C P8 950 PSU MB PLUS	Fixed
911401540948	SM303C P8 950 PSU NB PLUS	Fixed
911401541048	SM303C P8 950 PSU VWB PLUS	Fixed

Order Code	Full Product Name	Dimmable
911401541148	SM303C P8 950 PSU WB PLUS	Fixed
911401574812	SM303C P6 927 PSU NB	No
911401574912	SM303C P6 927 PSU MB	No
911401575012	SM303C P6 927 PSU WB	No
911401575112	SM303C P6 927 PSU VWB	No
911401575212	SM303C P6 930 PSU NB	No
911401575312	SM303C P6 930 PSU MB	No
911401575412	SM303C P6 930 PSU WB	No
911401575512	SM303C P6 930 PSU VWB	No
911401576012	SM303C P6 940 PSU NB	No
911401576112	SM303C P6 940 PSU MB	No
911401576212	SM303C P6 940 PSU WB	No
911401576312	SM303C P6 940 PSU VWB	No
911401576412	SM303C P6 950 PSU NB	No
911401576512	SM303C P6 950 PSU MB	No
911401576612	SM303C P6 950 PSU WB	No
911401576712	SM303C P6 950 PSU VWB	No
911401578812	SM303C P9 927 PSU NB	No
911401578912	SM303C P9 927 PSU MB	No
911401579012	SM303C P9 927 PSU WB	No
911401579112	SM303C P9 927 PSU VWB	No
911401579212	SM303C P9 930 PSU NB	No
911401579312	SM303C P9 930 PSU MB	No
911401579412	SM303C P9 930 PSU WB	No
911401579512	SM303C P9 930 PSU VWB	No
911401580012	SM303C P9 940 PSU NB	No
911401580112	SM303C P9 940 PSU MB	No
911401580212	SM303C P9 940 PSU WB	No
911401580312	SM303C P9 940 PSU VWB	No
911401580412	SM303C P9 950 PSU NB	No
911401580512	SM303C P9 950 PSU MB	No
911401580612	SM303C P9 950 PSU WB	No
911401580712	SM303C P9 950 PSU VWB	No

Mechanical and Housing

Order Code	Full Product Name	Optical cover type	Housing Color	Mech. impact protection code
911401513348	SP303P P8 927 PSU MB PLUS	Polycarbonate	White RAL 9003	IK02
911401513448	SP303P P8 927 PSU NB PLUS	Polycarbonate	White RAL 9003	IK02
911401513548	SP303P P8 927 PSU VWB PLUS	Polycarbonate	White RAL 9003	IK02
911401513648	SP303P P8 927 PSU WB PLUS	Polycarbonate	White RAL 9003	IK02
911401513748	SP303P P8 930 PSU MB PLUS	Polycarbonate	White RAL 9003	IK02
911401513848	SP303P P8 930 PSU NB PLUS	Polycarbonate	White RAL 9003	IK02

Order Code	Full Product Name	Optical cover type	Housing Color	Mech. impact protection code
911401513948	SP303P P8 930 PSU VWB PLUS	Polycarbonate	White RAL 9003	IK02
911401514048	SP303P P8 930 PSU WB PLUS	Polycarbonate	White RAL 9003	IK02
911401514148	SP303P P8 940 PSU MB PLUS	Polycarbonate	White RAL 9003	IK02
911401514248	SP303P P8 940 PSU NB PLUS	Polycarbonate	White RAL 9003	IK02
911401514348	SP303P P8 940 PSU VWB PLUS	Polycarbonate	White RAL 9003	IK02
911401514448	SP303P P8 940 PSU WB PLUS	Polycarbonate	White RAL 9003	IK02

GreenSpace Surface Mount

Order Code	Full Product Name	Optical cover type	Housing Color	Mech. impact protection code
911401514548	SP303P P8 950 PSU MB PLUS	Polycarbonate	White RAL 9003	IK02
911401514648	SP303P P8 950 PSU NB PLUS	Polycarbonate	White RAL 9003	IK02
911401514748	SP303P P8 950 PSU VWB PLUS	Polycarbonate	White RAL 9003	IK02
911401514848	SP303P P8 950 PSU WB PLUS	Polycarbonate	White RAL 9003	IK02
911401592012	SP303P P6 940 PSU NB	Acrylate	White	IK03
911401592112	SP303P P6 940 PSU MB	Acrylate	White	IK03
911401592212	SP303P P6 940 PSU WB	Acrylate	White	IK03
911401592312	SP303P P6 940 PSU VWB	Acrylate	White	IK03
911401592412	SP303P P6 950 PSU NB	Acrylate	White	IK03
911401592512	SP303P P6 950 PSU MB	Acrylate	White	IK03
911401592612	SP303P P6 950 PSU WB	Acrylate	White	IK03
911401592712	SP303P P6 950 PSU VWB	Acrylate	White	IK03
911401594812	SP303P P9 927 PSU NB	Acrylate	White	IK03
911401594912	SP303P P9 927 PSU MB	Acrylate	White	IK03
911401595012	SP303P P9 927 PSU WB	Acrylate	White	IK03
911401595112	SP303P P9 927 PSU VWB	Acrylate	White	IK03
911401595212	SP303P P9 930 PSU NB	Acrylate	White	IK03
911401595312	SP303P P9 930 PSU MB	Acrylate	White	IK03
911401595412	SP303P P9 930 PSU WB	Acrylate	White	IK03
911401595512	SP303P P9 930 PSU VWB	Acrylate	White	IK03
911401596012	SP303P P9 940 PSU NB	Acrylate	White	IK03
911401596112	SP303P P9 940 PSU MB	Acrylate	White	IK03
911401596212	SP303P P9 940 PSU WB	Acrylate	White	IK03
911401596312	SP303P P9 940 PSU VWB	Acrylate	White	IK03
911401596412	SP303P P9 950 PSU NB	Acrylate	White	IK03

Order Code	Full Product Name	Optical cover type	Housing Color	Mech. impact protection code
911401596512	SP303P P9 950 PSU MB	Acrylate	White	IK03
911401596612	SP303P P9 950 PSU WB	Acrylate	White	IK03
911401596712	SP303P P9 950 PSU VWB	Acrylate	White	IK03
911401598812	SP303P P6S 927 PSU NB	Acrylate	White	IK03
911401598912	SP303P P6S 927 PSU MB	Acrylate	White	IK03
911401599012	SP303P P6S 927 PSU WB	Acrylate	White	IK03
911401599112	SP303P P6S 927 PSU VWB	Acrylate	White	IK03
911401599212	SP303P P6S 930 PSU NB	Acrylate	White	IK03
911401599312	SP303P P6S 930 PSU MB	Acrylate	White	IK03
911401599412	SP303P P6S 930 PSU WB	Acrylate	White	IK03
911401599512	SP303P P6S 930 PSU VWB	Acrylate	White	IK03
911401500022	SP303P P6S 940 PSU NB	Acrylate	White	IK03
911401500122	SP303P P6S 940 PSU MB	Acrylate	White	IK03
911401500222	SP303P P6S 940 PSU WB	Acrylate	White	IK03
911401500322	SP303P P6S 940 PSU VWB	Acrylate	White	IK03
911401500422	SP303P P6S 950 PSU NB	Acrylate	White	IK03
911401500522	SP303P P6S 950 PSU MB	Acrylate	White	IK03
911401500622	SP303P P6S 950 PSU WB	Acrylate	White	IK03
911401500722	SP303P P6S 950 PSU VWB	Acrylate	White	IK03
911401502822	SP303P P9S 927 PSU NB	Acrylate	White	IK03
911401502922	SP303P P9S 927 PSU MB	Acrylate	White	IK03
911401503022	SP303P P9S 927 PSU WB	Acrylate	White	IK03
911401503122	SP303P P9S 927 PSU VWB	Acrylate	White	IK03
911401503222	SP303P P9S 930 PSU NB	Acrylate	White	IK03

GreenSpace Surface Mount

Order Code	Full Product Name	Optical cover type	Housing Color	Mech. impact protection code
911401503322	SP303P P9S 930 PSU MB	Acrylate	White	IK03
911401503422	SP303P P9S 930 PSU WB	Acrylate	White	IK03
911401503522	SP303P P9S 930 PSU VWB	Acrylate	White	IK03
911401504022	SP303P P9S 940 PSU NB	Acrylate	White	IK03
911401504122	SP303P P9S 940 PSU MB	Acrylate	White	IK03
911401504222	SP303P P9S 940 PSU WB	Acrylate	White	IK03
911401504322	SP303P P9S 940 PSU VWB	Acrylate	White	IK03
911401504422	SP303P P9S 950 PSU NB	Acrylate	White	IK03
911401504522	SP303P P9S 950 PSU MB	Acrylate	White	IK03
911401504622	SP303P P9S 950 PSU WB	Acrylate	White	IK03
911401504722	SP303P P9S 950 PSU VWB	Acrylate	White	IK03
911401514948	SP303P P8S 927 PSU MB PLUS	Polycarbonate	White RAL 9003	IK02
911401515048	SP303P P8S 927 PSU NB PLUS	Polycarbonate	White RAL 9003	IK02
911401515148	SP303P P8S 927 PSU VWB PLUS	Polycarbonate	White RAL 9003	IK02
911401515248	SP303P P8S 927 PSU WB PLUS	Polycarbonate	White RAL 9003	IK02
911401515348	SP303P P8S 930 PSU MB PLUS	Polycarbonate	White RAL 9003	IK02
911401515448	SP303P P8S 930 PSU NB PLUS	Polycarbonate	White RAL 9003	IK02
911401515548	SP303P P8S 930 PSU VWB PLUS	Polycarbonate	White RAL 9003	IK02
911401515648	SP303P P8S 930 PSU WB PLUS	Polycarbonate	White RAL 9003	IK02
911401515748	SP303P P8S 940 PSU MB PLUS	Polycarbonate	White RAL 9003	IK02
911401515848	SP303P P8S 940 PSU NB PLUS	Polycarbonate	White RAL 9003	IK02
911401515948	SP303P P8S 940 PSU VWB PLUS	Polycarbonate	White RAL 9003	IK02
911401516048	SP303P P8S 940 PSU WB PLUS	Polycarbonate	White RAL 9003	IK02
911401516148	SP303P P8S 950 PSU MB PLUS	Polycarbonate	White RAL 9003	IK02

Order Code	Full Product Name	Optical cover type	Housing Color	Mech. impact protection code
911401516248	SP303P P8S 950 PSU NB PLUS	Polycarbonate	White RAL 9003	IK02
911401516348	SP303P P8S 950 PSU VWB PLUS	Polycarbonate	White RAL 9003	IK02
911401516448	SP303P P8S 950 PSU WB PLUS	Polycarbonate	White RAL 9003	IK02
911401590812	SP303P P6 927 PSU NB	Acrylate	White	IK03
911401590912	SP303P P6 927 PSU MB	Acrylate	White	IK03
911401591012	SP303P P6 927 PSU WB	Acrylate	White	IK03
911401591112	SP303P P6 927 PSU VWB	Acrylate	White	IK03
911401591212	SP303P P6 930 PSU NB	Acrylate	White	IK03
911401591312	SP303P P6 930 PSU MB	Acrylate	White	IK03
911401591412	SP303P P6 930 PSU WB	Acrylate	White	IK03
911401591512	SP303P P6 930 PSU VWB	Acrylate	White	IK03
911401510248	SM303C P24 927 PSU MB PLUS	Polycarbonate	White RAL 9003	IK02
911401510348	SM303C P24 927 PSU NB PLUS	Polycarbonate	White RAL 9003	IK02
911401510448	SM303C P24 927 PSU VWB PLUS	Polycarbonate	White RAL 9003	IK02
911401510548	SM303C P24 927 PSU WB PLUS	Polycarbonate	White RAL 9003	IK02
911401510648	SM303C P24 930 PSU MB PLUS	Polycarbonate	White RAL 9003	IK02
911401510748	SM303C P24 930 PSU NB PLUS	Polycarbonate	White RAL 9003	IK02
911401510822	SM303C P24 927 PSU NB	Acrylate	White	IK03
911401510848	SM303C P24 930 PSU VWB PLUS	Polycarbonate	White RAL 9003	IK02
911401510922	SM303C P24 927 PSU MB	Acrylate	White	IK03
911401510948	SM303C P24 930 PSU WB PLUS	Polycarbonate	White RAL 9003	IK02
911401511022	SM303C P24 927 PSU WB	Acrylate	White	IK03
911401511048	SM303C P24 940 PSU MB PLUS	Polycarbonate	White RAL 9003	IK02
911401511122	SM303C P24 927 PSU VWB	Acrylate	White	IK03
911401511148	SM303C P24 940 PSU NB PLUS	Polycarbonate	White RAL 9003	IK02

GreenSpace Surface Mount

Order Code	Full Product Name	Optical cover type	Housing Color	Mech. impact protection code
911401511222	SM303C P24 930 PSU NB	Acrylate	White	IK03
911401511248	SM303C P24 940 PSU WB PLUS	Polycarbonate	White RAL 9003	IK02
911401511322	SM303C P24 930 PSU MB	Acrylate	White	IK03
911401511348	SM303C P24 950 PSU MB PLUS	Polycarbonate	White RAL 9003	IK02
911401511422	SM303C P24 930 PSU WB	Acrylate	White	IK03
911401511448	SM303C P24 950 PSU NB PLUS	Polycarbonate	White RAL 9003	IK02
911401511522	SM303C P24 930 PSU VWB	Acrylate	White	IK03
911401511548	SM303C P24 950 PSU VWB PLUS	Polycarbonate	White RAL 9003	IK02
911401511648	SM303C P24 950 PSU WB PLUS	Polycarbonate	White RAL 9003	IK02
911401511748	SM303C P28 927 PSU MB PLUS	Polycarbonate	White RAL 9003	IK02
911401511848	SM303C P28 927 PSU NB PLUS	Polycarbonate	White RAL 9003	IK02
911401511948	SM303C P28 927 PSU VWB PLUS	Polycarbonate	White RAL 9003	IK02
911401512022	SM303C P24 940 PSU NB	Acrylate	White	IK03
911401512048	SM303C P28 927 PSU WB PLUS	Polycarbonate	White RAL 9003	IK02
911401512122	SM303C P24 940 PSU MB	Acrylate	White	IK03
911401512148	SM303C P28 930 PSU MB PLUS	Polycarbonate	White RAL 9003	IK02
911401512222	SM303C P24 940 PSU WB	Acrylate	White	IK03
911401512248	SM303C P28 930 PSU NB PLUS	Polycarbonate	White RAL 9003	IK02
911401512348	SM303C P28 930 PSU VWB PLUS	Polycarbonate	White RAL 9003	IK02
911401512422	SM303C P24 950 PSU NB	Acrylate	White	IK03
911401512448	SM303C P28 930 PSU WB PLUS	Polycarbonate	White RAL 9003	IK02
911401512522	SM303C P24 950 PSU MB	Acrylate	White	IK03
911401512548	SM303C P28 940 PSU MB PLUS	Polycarbonate	White RAL 9003	IK02
911401512622	SM303C P24 950 PSU WB	Acrylate	White	IK03

Order Code	Full Product Name	Optical cover type	Housing Color	Mech. impact protection code
911401512648	SM303C P28 940 PSU NB PLUS	Polycarbonate	White RAL 9003	IK02
911401512722	SM303C P24 950 PSU VWB	Acrylate	White	IK03
911401512748	SM303C P28 940 PSU VWB PLUS	Polycarbonate	White RAL 9003	IK02
911401512848	SM303C P28 940 PSU WB PLUS	Polycarbonate	White RAL 9003	IK02
911401512948	SM303C P28 950 PSU MB PLUS	Polycarbonate	White RAL 9003	IK02
911401513048	SM303C P28 950 PSU NB PLUS	Polycarbonate	White RAL 9003	IK02
911401513148	SM303C P28 950 PSU VWB PLUS	Polycarbonate	White RAL 9003	IK02
911401513248	SM303C P28 950 PSU WB PLUS	Polycarbonate	White RAL 9003	IK02
911401514822	SM303C P28 927 PSU NB	Acrylate	White	IK03
911401514922	SM303C P28 927 PSU MB	Acrylate	White	IK03
911401515022	SM303C P28 927 PSU WB	Acrylate	White	IK03
911401515122	SM303C P28 927 PSU VWB	Acrylate	White	IK03
911401515222	SM303C P28 930 PSU NB	Acrylate	White	IK03
911401515322	SM303C P28 930 PSU MB	Acrylate	White	IK03
911401515422	SM303C P28 930 PSU WB	Acrylate	White	IK03
911401515522	SM303C P28 930 PSU VWB	Acrylate	White	IK03
911401516022	SM303C P28 940 PSU NB	Acrylate	White	IK03
911401516122	SM303C P28 940 PSU MB	Acrylate	White	IK03
911401516222	SM303C P28 940 PSU WB	Acrylate	White	IK03
911401516322	SM303C P28 940 PSU VWB	Acrylate	White	IK03
911401516422	SM303C P28 950 PSU NB	Acrylate	White	IK03
911401516522	SM303C P28 950 PSU MB	Acrylate	White	IK03
911401516622	SM303C P28 950 PSU WB	Acrylate	White	IK03
911401516722	SM303C P28 950 PSU VWB	Acrylate	White	IK03

GreenSpace Surface Mount

Order Code	Full Product Name	Optical cover type	Housing Color	Mech. impact protection code
911401517822	SM304C P10 927 PSU MB	Acrylate	White	IK03
911401517922	SM304C P10 927 PSU WB	Acrylate	White	IK03
911401518022	SM304C P10 930 PSU MB	Acrylate	White	IK03
911401518122	SM304C P10 930 PSU WB	Acrylate	White	IK03
911401518422	SM304C P10 940 PSU MB	Acrylate	White	IK03
911401518522	SM304C P10 940 PSU WB	Acrylate	White	IK03
911401518622	SM304C P10 950 PSU MB	Acrylate	White	IK03
911401518722	SM304C P10 950 PSU WB	Acrylate	White	IK03
911401519822	SM304C P12 927 PSU MB	Acrylate	White	IK03
911401519922	SM304C P12 927 PSU WB	Acrylate	White	IK03
911401520022	SM304C P12 930 PSU MB	Acrylate	White	IK03
911401520122	SM304C P12 930 PSU WB	Acrylate	White	IK03
911401520422	SM304C P12 940 PSU MB	Acrylate	White	IK03
911401520522	SM304C P12 940 PSU WB	Acrylate	White	IK03
911401520622	SM304C P12 950 PSU MB	Acrylate	White	IK03
911401520722	SM304C P12 950 PSU WB	Acrylate	White	IK03
911401521822	SM304C P15 927 PSU MB	Acrylate	White	IK03
911401521922	SM304C P15 927 PSU WB	Acrylate	White	IK03
911401522022	SM304C P15 930 PSU MB	Acrylate	White	IK03
911401522122	SM304C P15 930 PSU WB	Acrylate	White	IK03
911401522422	SM304C P15 940 PSU MB	Acrylate	White	IK03
911401522522	SM304C P15 940 PSU WB	Acrylate	White	IK03
911401522622	SM304C P15 950 PSU MB	Acrylate	White	IK03
911401522722	SM304C P15 950 PSU WB	Acrylate	White	IK03

Order Code	Full Product Name	Optical cover type	Housing Color	Mech. impact protection code
911401541248	SM303C P8S 927 PSU MB PLUS	Polycarbonate	White RAL 9003	IK02
911401541348	SM303C P8S 927 PSU NB PLUS	Polycarbonate	White RAL 9003	IK02
911401541448	SM303C P8S 927 PSU VWB PLUS	Polycarbonate	White RAL 9003	IK02
911401541548	SM303C P8S 927 PSU WB PLUS	Polycarbonate	White RAL 9003	IK02
911401541648	SM303C P8S 930 PSU MB PLUS	Polycarbonate	White RAL 9003	IK02
911401541748	SM303C P8S 930 PSU NB PLUS	Polycarbonate	White RAL 9003	IK02
911401541848	SM303C P8S 930 PSU VWB PLUS	Polycarbonate	White RAL 9003	IK02
911401541948	SM303C P8S 930 PSU WB PLUS	Polycarbonate	White RAL 9003	IK02
911401542048	SM303C P8S 940 PSU MB PLUS	Polycarbonate	White RAL 9003	IK02
911401542148	SM303C P8S 940 PSU NB PLUS	Polycarbonate	White RAL 9003	IK02
911401542248	SM303C P8S 940 PSU VWB PLUS	Polycarbonate	White RAL 9003	IK02
911401542348	SM303C P8S 940 PSU WB PLUS	Polycarbonate	White RAL 9003	IK02
911401542448	SM303C P8S 950 PSU MB PLUS	Polycarbonate	White RAL 9003	IK02
911401542548	SM303C P8S 950 PSU NB PLUS	Polycarbonate	White RAL 9003	IK02
911401542648	SM303C P8S 950 PSU VWB PLUS	Polycarbonate	White RAL 9003	IK02
911401542748	SM303C P8S 950 PSU WB PLUS	Polycarbonate	White RAL 9003	IK02
911401582812	SM303C P6S 927 PSU NB	Acrylate	White	IK03
911401582912	SM303C P6S 927 PSU MB	Acrylate	White	IK03
911401583012	SM303C P6S 927 PSU WB	Acrylate	White	IK03
911401583112	SM303C P6S 927 PSU VWB	Acrylate	White	IK03
911401583212	SM303C P6S 930 PSU NB	Acrylate	White	IK03
911401583312	SM303C P6S 930 PSU MB	Acrylate	White	IK03
911401583412	SM303C P6S 930 PSU WB	Acrylate	White	IK03
911401583512	SM303C P6S 930 PSU VWB	Acrylate	White	IK03

GreenSpace Surface Mount

Order Code	Full Product Name	Optical cover type	Housing Color	Mech. impact protection code
911401584012	SM303C P6S 940 PSU NB	Acrylate	White	IK03
911401584112	SM303C P6S 940 PSU MB	Acrylate	White	IK03
911401584212	SM303C P6S 940 PSU WB	Acrylate	White	IK03
911401584312	SM303C P6S 940 PSU VWB	Acrylate	White	IK03
911401584412	SM303C P6S 950 PSU NB	Acrylate	White	IK03
911401584512	SM303C P6S 950 PSU MB	Acrylate	White	IK03
911401584612	SM303C P6S 950 PSU WB	Acrylate	White	IK03
911401584712	SM303C P6S 950 PSU VWB	Acrylate	White	IK03
911401586812	SM303C P9S 927 PSU NB	Acrylate	White	IK03
911401586912	SM303C P9S 927 PSU MB	Acrylate	White	IK03
911401587012	SM303C P9S 927 PSU WB	Acrylate	White	IK03
911401587112	SM303C P9S 927 PSU VWB	Acrylate	White	IK03
911401587212	SM303C P9S 930 PSU NB	Acrylate	White	IK03
911401587312	SM303C P9S 930 PSU MB	Acrylate	White	IK03
911401587412	SM303C P9S 930 PSU WB	Acrylate	White	IK03
911401587512	SM303C P9S 930 PSU VWB	Acrylate	White	IK03
911401588012	SM303C P9S 940 PSU NB	Acrylate	White	IK03
911401588112	SM303C P9S 940 PSU MB	Acrylate	White	IK03
911401588212	SM303C P9S 940 PSU WB	Acrylate	White	IK03
911401588312	SM303C P9S 940 PSU VWB	Acrylate	White	IK03
911401588412	SM303C P9S 950 PSU NB	Acrylate	White	IK03
911401588512	SM303C P9S 950 PSU MB	Acrylate	White	IK03
911401588612	SM303C P9S 950 PSU WB	Acrylate	White	IK03
911401588712	SM303C P9S 950 PSU VWB	Acrylate	White	IK03

Order Code	Full Product Name	Optical cover type	Housing Color	Mech. impact protection code
911401506822	SM303C P20 927 PSU NB	Acrylate	White	IK03
911401506922	SM303C P20 927 PSU MB	Acrylate	White	IK03
911401507022	SM303C P20 927 PSU WB	Acrylate	White	IK03
911401507122	SM303C P20 927 PSU VWB	Acrylate	White	IK03
911401507222	SM303C P20 930 PSU NB	Acrylate	White	IK03
911401507322	SM303C P20 930 PSU MB	Acrylate	White	IK03
911401507422	SM303C P20 930 PSU WB	Acrylate	White	IK03
911401507522	SM303C P20 930 PSU VWB	Acrylate	White	IK03
911401508022	SM303C P20 940 PSU NB	Acrylate	White	IK03
911401508122	SM303C P20 940 PSU MB	Acrylate	White	IK03
911401508222	SM303C P20 940 PSU WB	Acrylate	White	IK03
911401508322	SM303C P20 940 PSU VWB	Acrylate	White	IK03
911401508422	SM303C P20 950 PSU NB	Acrylate	White	IK03
911401508522	SM303C P20 950 PSU MB	Acrylate	White	IK03
911401508848	SM303C P20 927 PSU MB PLUS	Polycarbonate	White RAL 9003	IK02
911401508948	SM303C P20 927 PSU NB PLUS	Polycarbonate	White RAL 9003	IK02
911401509048	SM303C P20 927 PSU VWB PLUS	Polycarbonate	White RAL 9003	IK02
911401509148	SM303C P20 927 PSU WB PLUS	Polycarbonate	White RAL 9003	IK02
911401509248	SM303C P20 930 PSU MB PLUS	Polycarbonate	White RAL 9003	IK02
911401509348	SM303C P20 930 PSU NB PLUS	Polycarbonate	White RAL 9003	IK02
911401509448	SM303C P20 930 PSU VWB PLUS	Polycarbonate	White RAL 9003	IK02
911401509548	SM303C P20 930 PSU WB PLUS	Polycarbonate	White RAL 9003	IK02
911401509648	SM303C P20 940 PSU MB PLUS	Polycarbonate	White RAL 9003	IK02
911401509748	SM303C P20 940 PSU NB PLUS	Polycarbonate	White RAL 9003	IK02

GreenSpace Surface Mount

Order Code	Full Product Name	Optical cover type	Housing Color	Mech. impact protection code
911401509848	SM303C P20 940 PSU VWB PLUS	Polycarbonate	White RAL 9003	IK02
911401509948	SM303C P20 940 PSU WB PLUS	Polycarbonate	White RAL 9003	IK02
911401510048	SM303C P20 950 PSU MB PLUS	Polycarbonate	White RAL 9003	IK02
911401510148	SM303C P20 950 PSU NB PLUS	Polycarbonate	White RAL 9003	IK02
911401539648	SM303C P8 927 PSU MB PLUS	Polycarbonate	White RAL 9003	IK02
911401539748	SM303C P8 927 PSU NB PLUS	Polycarbonate	White RAL 9003	IK02
911401539848	SM303C P8 927 PSU VWB PLUS	Polycarbonate	White RAL 9003	IK02
911401539948	SM303C P8 927 PSU WB PLUS	Polycarbonate	White RAL 9003	IK02
911401540048	SM303C P8 930 PSU MB PLUS	Polycarbonate	White RAL 9003	IK02
911401540148	SM303C P8 930 PSU NB PLUS	Polycarbonate	White RAL 9003	IK02
911401540248	SM303C P8 930 PSU VWB PLUS	Polycarbonate	White RAL 9003	IK02
911401540348	SM303C P8 930 PSU WB PLUS	Polycarbonate	White RAL 9003	IK02
911401540448	SM303C P8 940 PSU MB PLUS	Polycarbonate	White RAL 9003	IK02
911401540548	SM303C P8 940 PSU NB PLUS	Polycarbonate	White RAL 9003	IK02
911401540648	SM303C P8 940 PSU VWB PLUS	Polycarbonate	White RAL 9003	IK02
911401540748	SM303C P8 940 PSU WB PLUS	Polycarbonate	White RAL 9003	IK02
911401540848	SM303C P8 950 PSU MB PLUS	Polycarbonate	White RAL 9003	IK02
911401540948	SM303C P8 950 PSU NB PLUS	Polycarbonate	White RAL 9003	IK02
911401541048	SM303C P8 950 PSU VWB PLUS	Polycarbonate	White RAL 9003	IK02
911401541148	SM303C P8 950 PSU WB PLUS	Polycarbonate	White RAL 9003	IK02
911401574812	SM303C P6 927 PSU NB	Acrylate	White	IK03
911401574912	SM303C P6 927 PSU MB	Acrylate	White	IK03
911401575012	SM303C P6 927 PSU WB	Acrylate	White	IK03
911401575112	SM303C P6 927 PSU VWB	Acrylate	White	IK03

Order Code	Full Product Name	Optical cover type	Housing Color	Mech. impact protection code
911401575212	SM303C P6 930 PSU NB	Acrylate	White	IK03
911401575312	SM303C P6 930 PSU MB	Acrylate	White	IK03
911401575412	SM303C P6 930 PSU WB	Acrylate	White	IK03
911401575512	SM303C P6 930 PSU VWB	Acrylate	White	IK03
911401576012	SM303C P6 940 PSU NB	Acrylate	White	IK03
911401576112	SM303C P6 940 PSU MB	Acrylate	White	IK03
911401576212	SM303C P6 940 PSU WB	Acrylate	White	IK03
911401576312	SM303C P6 940 PSU VWB	Acrylate	White	IK03
911401576412	SM303C P6 950 PSU NB	Acrylate	White	IK03
911401576512	SM303C P6 950 PSU MB	Acrylate	White	IK03
911401576612	SM303C P6 950 PSU WB	Acrylate	White	IK03
911401576712	SM303C P6 950 PSU VWB	Acrylate	White	IK03
911401578812	SM303C P9 927 PSU NB	Acrylate	White	IK03
911401578912	SM303C P9 927 PSU MB	Acrylate	White	IK03
911401579012	SM303C P9 927 PSU WB	Acrylate	White	IK03
911401579112	SM303C P9 927 PSU VWB	Acrylate	White	IK03
911401579212	SM303C P9 930 PSU NB	Acrylate	White	IK03
911401579312	SM303C P9 930 PSU MB	Acrylate	White	IK03
911401579412	SM303C P9 930 PSU WB	Acrylate	White	IK03
911401579512	SM303C P9 930 PSU VWB	Acrylate	White	IK03
911401580012	SM303C P9 940 PSU NB	Acrylate	White	IK03
911401580112	SM303C P9 940 PSU MB	Acrylate	White	IK03
911401580212	SM303C P9 940 PSU WB	Acrylate	White	IK03
911401580312	SM303C P9 940 PSU VWB	Acrylate	White	IK03

GreenSpace Surface Mount

Order Code	Full Product Name	Optical cover type	Housing Color	Mech. impact protection code
911401580412	SM303C P9 950 PSU NB	Acrylate	White	IK03
911401580512	SM303C P9 950 PSU MB	Acrylate	White	IK03

Order Code	Full Product Name	Optical cover type	Housing Color	Mech. impact protection code
911401580612	SM303C P9 950 PSU WB	Acrylate	White	IK03
911401580712	SM303C P9 950 PSU VWB	Acrylate	White	IK03

Approval and Application

Order Code	Full Product Name	CE mark
911401513348	SP303P P8 927 PSU MB PLUS	Yes
911401513448	SP303P P8 927 PSU NB PLUS	Yes
911401513548	SP303P P8 927 PSU VWB PLUS	Yes
911401513648	SP303P P8 927 PSU WB PLUS	Yes
911401513748	SP303P P8 930 PSU MB PLUS	Yes
911401513848	SP303P P8 930 PSU NB PLUS	Yes
911401513948	SP303P P8 930 PSU VWB PLUS	Yes
911401514048	SP303P P8 930 PSU WB PLUS	Yes
911401514148	SP303P P8 940 PSU MB PLUS	Yes
911401514248	SP303P P8 940 PSU NB PLUS	Yes
911401514348	SP303P P8 940 PSU VWB PLUS	Yes
911401514448	SP303P P8 940 PSU WB PLUS	Yes
911401514548	SP303P P8 950 PSU MB PLUS	Yes
911401514648	SP303P P8 950 PSU NB PLUS	Yes
911401514748	SP303P P8 950 PSU VWB PLUS	Yes
911401514848	SP303P P8 950 PSU WB PLUS	Yes
911401592012	SP303P P6 940 PSU NB	No
911401592112	SP303P P6 940 PSU MB	No
911401592212	SP303P P6 940 PSU WB	No
911401592312	SP303P P6 940 PSU VWB	No
911401592412	SP303P P6 950 PSU NB	No
911401592512	SP303P P6 950 PSU MB	No
911401592612	SP303P P6 950 PSU WB	No
911401592712	SP303P P6 950 PSU VWB	No
911401594812	SP303P P9 927 PSU NB	No
911401594912	SP303P P9 927 PSU MB	No
911401595012	SP303P P9 927 PSU WB	No
911401595112	SP303P P9 927 PSU VWB	No
911401595212	SP303P P9 930 PSU NB	No
911401595312	SP303P P9 930 PSU MB	No
911401595412	SP303P P9 930 PSU WB	No
911401595512	SP303P P9 930 PSU VWB	No
911401596012	SP303P P9 940 PSU NB	No
911401596112	SP303P P9 940 PSU MB	No
911401596212	SP303P P9 940 PSU WB	No
911401596312	SP303P P9 940 PSU VWB	No
911401596412	SP303P P9 950 PSU NB	No
911401596512	SP303P P9 950 PSU MB	No
911401596612	SP303P P9 950 PSU WB	No
911401596712	SP303P P9 950 PSU VWB	No
911401598812	SP303P P6S 927 PSU NB	No

Order Code	Full Product Name	CE mark
911401598912	SP303P P6S 927 PSU MB	No
911401599012	SP303P P6S 927 PSU WB	No
911401599112	SP303P P6S 927 PSU VWB	No
911401599212	SP303P P6S 930 PSU NB	No
911401599312	SP303P P6S 930 PSU MB	No
911401599412	SP303P P6S 930 PSU WB	No
911401599512	SP303P P6S 930 PSU VWB	No
911401500022	SP303P P6S 940 PSU NB	No
911401500122	SP303P P6S 940 PSU MB	No
911401500222	SP303P P6S 940 PSU WB	No
911401500322	SP303P P6S 940 PSU VWB	No
911401500422	SP303P P6S 950 PSU NB	No
911401500522	SP303P P6S 950 PSU MB	No
911401500622	SP303P P6S 950 PSU WB	No
911401500722	SP303P P6S 950 PSU VWB	No
911401502822	SP303P P9S 927 PSU NB	No
911401502922	SP303P P9S 927 PSU MB	No
911401503022	SP303P P9S 927 PSU WB	No
911401503122	SP303P P9S 927 PSU VWB	No
911401503222	SP303P P9S 930 PSU NB	No
911401503322	SP303P P9S 930 PSU MB	No
911401503422	SP303P P9S 930 PSU WB	No
911401503522	SP303P P9S 930 PSU VWB	No
911401504022	SP303P P9S 940 PSU NB	No
911401504122	SP303P P9S 940 PSU MB	No
911401504222	SP303P P9S 940 PSU WB	No
911401504322	SP303P P9S 940 PSU VWB	No
911401504422	SP303P P9S 950 PSU NB	No
911401504522	SP303P P9S 950 PSU MB	No
911401504622	SP303P P9S 950 PSU WB	No
911401504722	SP303P P9S 950 PSU VWB	No
911401514948	SP303P P8S 927 PSU MB PLUS	Yes
911401515048	SP303P P8S 927 PSU NB PLUS	Yes
911401515148	SP303P P8S 927 PSU VWB PLUS	Yes
911401515248	SP303P P8S 927 PSU WB PLUS	Yes
911401515348	SP303P P8S 930 PSU MB PLUS	Yes
911401515448	SP303P P8S 930 PSU NB PLUS	Yes
911401515548	SP303P P8S 930 PSU VWB PLUS	Yes
911401515648	SP303P P8S 930 PSU WB PLUS	Yes
911401515748	SP303P P8S 940 PSU MB PLUS	Yes
911401515848	SP303P P8S 940 PSU NB PLUS	Yes

GreenSpace Surface Mount

Order Code	Full Product Name	CE mark
911401515948	SP303P P8S 940 PSU VWB PLUS	Yes
911401516048	SP303P P8S 940 PSU WB PLUS	Yes
911401516148	SP303P P8S 950 PSU MB PLUS	Yes
911401516248	SP303P P8S 950 PSU NB PLUS	Yes
911401516348	SP303P P8S 950 PSU VWB PLUS	Yes
911401516448	SP303P P8S 950 PSU WB PLUS	Yes
911401590812	SP303P P6 927 PSU NB	No
911401590912	SP303P P6 927 PSU MB	No
911401591012	SP303P P6 927 PSU WB	No
911401591112	SP303P P6 927 PSU VWB	No
911401591212	SP303P P6 930 PSU NB	No
911401591312	SP303P P6 930 PSU MB	No
911401591412	SP303P P6 930 PSU WB	No
911401591512	SP303P P6 930 PSU VWB	No
911401510248	SM303C P24 927 PSU MB PLUS	Yes
911401510348	SM303C P24 927 PSU NB PLUS	Yes
911401510448	SM303C P24 927 PSU VWB PLUS	Yes
911401510548	SM303C P24 927 PSU WB PLUS	Yes
911401510648	SM303C P24 930 PSU MB PLUS	Yes
911401510748	SM303C P24 930 PSU NB PLUS	Yes
911401510822	SM303C P24 927 PSU NB	No
911401510848	SM303C P24 930 PSU VWB PLUS	Yes
911401510922	SM303C P24 927 PSU MB	No
911401510948	SM303C P24 930 PSU WB PLUS	Yes
911401511022	SM303C P24 927 PSU WB	No
911401511048	SM303C P24 940 PSU MB PLUS	Yes
911401511122	SM303C P24 927 PSU VWB	No
911401511148	SM303C P24 940 PSU NB PLUS	Yes
911401511222	SM303C P24 930 PSU NB	No
911401511248	SM303C P24 940 PSU WB PLUS	Yes
911401511322	SM303C P24 930 PSU MB	No
911401511348	SM303C P24 950 PSU MB PLUS	Yes
911401511422	SM303C P24 930 PSU WB	No
911401511448	SM303C P24 950 PSU NB PLUS	Yes
911401511522	SM303C P24 930 PSU VWB	No
911401511548	SM303C P24 950 PSU VWB PLUS	Yes
911401511648	SM303C P24 950 PSU WB PLUS	Yes
911401511748	SM303C P28 927 PSU MB PLUS	Yes
911401511848	SM303C P28 927 PSU NB PLUS	Yes
911401511948	SM303C P28 927 PSU VWB PLUS	Yes
911401512022	SM303C P24 940 PSU NB	No
911401512048	SM303C P28 927 PSU WB PLUS	Yes
911401512122	SM303C P24 940 PSU MB	No
911401512148	SM303C P28 930 PSU MB PLUS	Yes
911401512222	SM303C P24 940 PSU WB	No
911401512248	SM303C P28 930 PSU NB PLUS	Yes
911401512348	SM303C P28 930 PSU VWB PLUS	Yes
911401512422	SM303C P24 950 PSU NB	No
911401512448	SM303C P28 930 PSU WB PLUS	Yes
911401512522	SM303C P24 950 PSU MB	No
911401512548	SM303C P28 940 PSU MB PLUS	Yes
911401512622	SM303C P24 950 PSU WB	No

Order Code	Full Product Name	CE mark
911401512648	SM303C P28 940 PSU NB PLUS	Yes
911401512722	SM303C P24 950 PSU VWB	No
911401512748	SM303C P28 940 PSU VWB PLUS	Yes
911401512848	SM303C P28 940 PSU WB PLUS	Yes
911401512948	SM303C P28 950 PSU MB PLUS	Yes
911401513048	SM303C P28 950 PSU NB PLUS	Yes
911401513148	SM303C P28 950 PSU VWB PLUS	Yes
911401513248	SM303C P28 950 PSU WB PLUS	Yes
911401514822	SM303C P28 927 PSU NB	No
911401514922	SM303C P28 927 PSU MB	No
911401515022	SM303C P28 927 PSU WB	No
911401515122	SM303C P28 927 PSU VWB	No
911401515222	SM303C P28 930 PSU NB	No
911401515322	SM303C P28 930 PSU MB	No
911401515422	SM303C P28 930 PSU WB	No
911401515522	SM303C P28 930 PSU VWB	No
911401516022	SM303C P28 940 PSU NB	No
911401516122	SM303C P28 940 PSU MB	No
911401516222	SM303C P28 940 PSU WB	No
911401516322	SM303C P28 940 PSU VWB	No
911401516422	SM303C P28 950 PSU NB	No
911401516522	SM303C P28 950 PSU MB	No
911401516622	SM303C P28 950 PSU WB	No
911401516722	SM303C P28 950 PSU VWB	No
911401517822	SM304C P10 927 PSU MB	No
911401517922	SM304C P10 927 PSU WB	No
911401518022	SM304C P10 930 PSU MB	No
911401518122	SM304C P10 930 PSU WB	No
911401518422	SM304C P10 940 PSU MB	No
911401518522	SM304C P10 940 PSU WB	No
911401518622	SM304C P10 950 PSU MB	No
911401518722	SM304C P10 950 PSU WB	No
911401519822	SM304C P12 927 PSU MB	No
911401519922	SM304C P12 927 PSU WB	No
911401520022	SM304C P12 930 PSU MB	No
911401520122	SM304C P12 930 PSU WB	No
911401520422	SM304C P12 940 PSU MB	No
911401520522	SM304C P12 940 PSU WB	No
911401520622	SM304C P12 950 PSU MB	No
911401520722	SM304C P12 950 PSU WB	No
911401521822	SM304C P15 927 PSU MB	No
911401521922	SM304C P15 927 PSU WB	No
911401522022	SM304C P15 930 PSU MB	No
911401522122	SM304C P15 930 PSU WB	No
911401522422	SM304C P15 940 PSU MB	No
911401522522	SM304C P15 940 PSU WB	No
911401522622	SM304C P15 950 PSU MB	No
911401522722	SM304C P15 950 PSU WB	No
911401541248	SM303C P8S 927 PSU MB PLUS	Yes
911401541348	SM303C P8S 927 PSU NB PLUS	Yes
911401541448	SM303C P8S 927 PSU VWB PLUS	Yes
911401541548	SM303C P8S 927 PSU WB PLUS	Yes

GreenSpace Surface Mount

Order Code	Full Product Name	CE mark
911401541648	SM303C P8S 930 PSU MB PLUS	Yes
911401541748	SM303C P8S 930 PSU NB PLUS	Yes
911401541848	SM303C P8S 930 PSU VWB PLUS	Yes
911401541948	SM303C P8S 930 PSU WB PLUS	Yes
911401542048	SM303C P8S 940 PSU MB PLUS	Yes
911401542148	SM303C P8S 940 PSU NB PLUS	Yes
911401542248	SM303C P8S 940 PSU VWB PLUS	Yes
911401542348	SM303C P8S 940 PSU WB PLUS	Yes
911401542448	SM303C P8S 950 PSU MB PLUS	Yes
911401542548	SM303C P8S 950 PSU NB PLUS	Yes
911401542648	SM303C P8S 950 PSU VWB PLUS	Yes
911401542748	SM303C P8S 950 PSU WB PLUS	Yes
911401582812	SM303C P6S 927 PSU NB	No
911401582912	SM303C P6S 927 PSU MB	No
911401583012	SM303C P6S 927 PSU WB	No
911401583112	SM303C P6S 927 PSU VWB	No
911401583212	SM303C P6S 930 PSU NB	No
911401583312	SM303C P6S 930 PSU MB	No
911401583412	SM303C P6S 930 PSU WB	No
911401583512	SM303C P6S 930 PSU VWB	No
911401584012	SM303C P6S 940 PSU NB	No
911401584112	SM303C P6S 940 PSU MB	No
911401584212	SM303C P6S 940 PSU WB	No
911401584312	SM303C P6S 940 PSU VWB	No
911401584412	SM303C P6S 950 PSU NB	No
911401584512	SM303C P6S 950 PSU MB	No
911401584612	SM303C P6S 950 PSU WB	No
911401584712	SM303C P6S 950 PSU VWB	No
911401586812	SM303C P9S 927 PSU NB	No
911401586912	SM303C P9S 927 PSU MB	No
911401587012	SM303C P9S 927 PSU WB	No
911401587112	SM303C P9S 927 PSU VWB	No
911401587212	SM303C P9S 930 PSU NB	No
911401587312	SM303C P9S 930 PSU MB	No
911401587412	SM303C P9S 930 PSU WB	No
911401587512	SM303C P9S 930 PSU VWB	No
911401588012	SM303C P9S 940 PSU NB	No
911401588112	SM303C P9S 940 PSU MB	No
911401588212	SM303C P9S 940 PSU WB	No
911401588312	SM303C P9S 940 PSU VWB	No
911401588412	SM303C P9S 950 PSU NB	No
911401588512	SM303C P9S 950 PSU MB	No
911401588612	SM303C P9S 950 PSU WB	No
911401588712	SM303C P9S 950 PSU VWB	No
911401506822	SM303C P20 927 PSU NB	No
911401506922	SM303C P20 927 PSU MB	No
911401507022	SM303C P20 927 PSU WB	No
911401507122	SM303C P20 927 PSU VWB	No
911401507222	SM303C P20 930 PSU NB	No
911401507322	SM303C P20 930 PSU MB	No
911401507422	SM303C P20 930 PSU WB	No
911401507522	SM303C P20 930 PSU VWB	No

Order Code	Full Product Name	CE mark
911401508022	SM303C P20 940 PSU NB	No
911401508122	SM303C P20 940 PSU MB	No
911401508222	SM303C P20 940 PSU WB	No
911401508322	SM303C P20 940 PSU VWB	No
911401508422	SM303C P20 950 PSU NB	No
911401508522	SM303C P20 950 PSU MB	No
911401508848	SM303C P20 927 PSU MB PLUS	Yes
911401508948	SM303C P20 927 PSU NB PLUS	Yes
911401509048	SM303C P20 927 PSU VWB PLUS	Yes
911401509148	SM303C P20 927 PSU WB PLUS	Yes
911401509248	SM303C P20 930 PSU MB PLUS	Yes
911401509348	SM303C P20 930 PSU NB PLUS	Yes
911401509448	SM303C P20 930 PSU VWB PLUS	Yes
911401509548	SM303C P20 930 PSU WB PLUS	Yes
911401509648	SM303C P20 940 PSU MB PLUS	Yes
911401509748	SM303C P20 940 PSU NB PLUS	Yes
911401509848	SM303C P20 940 PSU VWB PLUS	Yes
911401509948	SM303C P20 940 PSU WB PLUS	Yes
911401510048	SM303C P20 950 PSU MB PLUS	Yes
911401510148	SM303C P20 950 PSU NB PLUS	Yes
911401539648	SM303C P8 927 PSU MB PLUS	Yes
911401539748	SM303C P8 927 PSU NB PLUS	Yes
911401539848	SM303C P8 927 PSU VWB PLUS	Yes
911401539948	SM303C P8 927 PSU WB PLUS	Yes
911401540048	SM303C P8 930 PSU MB PLUS	Yes
911401540148	SM303C P8 930 PSU NB PLUS	Yes
911401540248	SM303C P8 930 PSU VWB PLUS	Yes
911401540348	SM303C P8 930 PSU WB PLUS	Yes
911401540448	SM303C P8 940 PSU MB PLUS	Yes
911401540548	SM303C P8 940 PSU NB PLUS	Yes
911401540648	SM303C P8 940 PSU VWB PLUS	Yes
911401540748	SM303C P8 940 PSU WB PLUS	Yes
911401540848	SM303C P8 950 PSU MB PLUS	Yes
911401540948	SM303C P8 950 PSU NB PLUS	Yes
911401541048	SM303C P8 950 PSU VWB PLUS	Yes
911401541148	SM303C P8 950 PSU WB PLUS	Yes
911401574812	SM303C P6 927 PSU NB	No
911401574912	SM303C P6 927 PSU MB	No
911401575012	SM303C P6 927 PSU WB	No
911401575112	SM303C P6 927 PSU VWB	No
911401575212	SM303C P6 930 PSU NB	No
911401575312	SM303C P6 930 PSU MB	No
911401575412	SM303C P6 930 PSU WB	No
911401575512	SM303C P6 930 PSU VWB	No
911401576012	SM303C P6 940 PSU NB	No
911401576112	SM303C P6 940 PSU MB	No
911401576212	SM303C P6 940 PSU WB	No
911401576312	SM303C P6 940 PSU VWB	No
911401576412	SM303C P6 950 PSU NB	No
911401576512	SM303C P6 950 PSU MB	No
911401576612	SM303C P6 950 PSU WB	No
911401576712	SM303C P6 950 PSU VWB	No

Order Code	Full Product Name	CE mark
911401578812	SM303C P9 927 PSU NB	No
911401578912	SM303C P9 927 PSU MB	No
911401579012	SM303C P9 927 PSU WB	No
911401579112	SM303C P9 927 PSU VWB	No
911401579212	SM303C P9 930 PSU NB	No
911401579312	SM303C P9 930 PSU MB	No
911401579412	SM303C P9 930 PSU WB	No
911401579512	SM303C P9 930 PSU VWB	No

Order Code	Full Product Name	CE mark
911401580012	SM303C P9 940 PSU NB	No
911401580112	SM303C P9 940 PSU MB	No
911401580212	SM303C P9 940 PSU WB	No
911401580312	SM303C P9 940 PSU VWB	No
911401580412	SM303C P9 950 PSU NB	No
911401580512	SM303C P9 950 PSU MB	No
911401580612	SM303C P9 950 PSU WB	No
911401580712	SM303C P9 950 PSU VWB	No

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Luminous flux tolerance
911401513348	SP303P P8 927 PSU MB PLUS	-10% / +10%
911401513448	SP303P P8 927 PSU NB PLUS	-10% / +10%
911401513548	SP303P P8 927 PSU VWB PLUS	-10% / +10%
911401513648	SP303P P8 927 PSU WB PLUS	-10% / +10%
911401513748	SP303P P8 930 PSU MB PLUS	-10% / +10%
911401513848	SP303P P8 930 PSU NB PLUS	-10% / +10%
911401513948	SP303P P8 930 PSU VWB PLUS	-10% / +10%
911401514048	SP303P P8 930 PSU WB PLUS	-10% / +10%
911401514148	SP303P P8 940 PSU MB PLUS	-10% / +10%
911401514248	SP303P P8 940 PSU NB PLUS	-10% / +10%
911401514348	SP303P P8 940 PSU VWB PLUS	-10% / +10%
911401514448	SP303P P8 940 PSU WB PLUS	-10% / +10%
911401514548	SP303P P8 950 PSU MB PLUS	-10% / +10%
911401514648	SP303P P8 950 PSU NB PLUS	-10% / +10%
911401514748	SP303P P8 950 PSU VWB PLUS	-10% / +10%
911401514848	SP303P P8 950 PSU WB PLUS	-10% / +10%
911401592012	SP303P P6 940 PSU NB	+/-10%
911401592112	SP303P P6 940 PSU MB	+/-10%
911401592212	SP303P P6 940 PSU WB	+/-10%
911401592312	SP303P P6 940 PSU VWB	+/-10%
911401592412	SP303P P6 950 PSU NB	+/-10%
911401592512	SP303P P6 950 PSU MB	+/-10%
911401592612	SP303P P6 950 PSU WB	+/-10%
911401592712	SP303P P6 950 PSU VWB	+/-10%
911401594812	SP303P P9 927 PSU NB	+/-10%
911401594912	SP303P P9 927 PSU MB	+/-10%
911401595012	SP303P P9 927 PSU WB	+/-10%
911401595112	SP303P P9 927 PSU VWB	+/-10%
911401595212	SP303P P9 930 PSU NB	+/-10%
911401595312	SP303P P9 930 PSU MB	+/-10%
911401595412	SP303P P9 930 PSU WB	+/-10%
911401595512	SP303P P9 930 PSU VWB	+/-10%
911401596012	SP303P P9 940 PSU NB	+/-10%
911401596112	SP303P P9 940 PSU MB	+/-10%
911401596212	SP303P P9 940 PSU WB	+/-10%
911401596312	SP303P P9 940 PSU VWB	+/-10%
911401596412	SP303P P9 950 PSU NB	+/-10%
911401596512	SP303P P9 950 PSU MB	+/-10%
911401596612	SP303P P9 950 PSU WB	+/-10%
911401596712	SP303P P9 950 PSU VWB	+/-10%

Order Code	Full Product Name	Luminous flux tolerance
911401598812	SP303P P6S 927 PSU NB	+/-10%
911401598912	SP303P P6S 927 PSU MB	+/-10%
911401599012	SP303P P6S 927 PSU WB	+/-10%
911401599112	SP303P P6S 927 PSU VWB	+/-10%
911401599212	SP303P P6S 930 PSU NB	+/-10%
911401599312	SP303P P6S 930 PSU MB	+/-10%
911401599412	SP303P P6S 930 PSU WB	+/-10%
911401599512	SP303P P6S 930 PSU VWB	+/-10%
911401500022	SP303P P6S 940 PSU NB	+/-10%
911401500122	SP303P P6S 940 PSU MB	+/-10%
911401500222	SP303P P6S 940 PSU WB	+/-10%
911401500322	SP303P P6S 940 PSU VWB	+/-10%
911401500422	SP303P P6S 950 PSU NB	+/-10%
911401500522	SP303P P6S 950 PSU MB	+/-10%
911401500622	SP303P P6S 950 PSU WB	+/-10%
911401500722	SP303P P6S 950 PSU VWB	+/-10%
911401502822	SP303P P9S 927 PSU NB	+/-10%
911401502922	SP303P P9S 927 PSU MB	+/-10%
911401503022	SP303P P9S 927 PSU WB	+/-10%
911401503122	SP303P P9S 927 PSU VWB	+/-10%
911401503222	SP303P P9S 930 PSU NB	+/-10%
911401503322	SP303P P9S 930 PSU MB	+/-10%
911401503422	SP303P P9S 930 PSU WB	+/-10%
911401503522	SP303P P9S 930 PSU VWB	+/-10%
911401504022	SP303P P9S 940 PSU NB	+/-10%
911401504122	SP303P P9S 940 PSU MB	+/-10%
911401504222	SP303P P9S 940 PSU WB	+/-10%
911401504322	SP303P P9S 940 PSU VWB	+/-10%
911401504422	SP303P P9S 950 PSU NB	+/-10%
911401504522	SP303P P9S 950 PSU MB	+/-10%
911401504622	SP303P P9S 950 PSU WB	+/-10%
911401504722	SP303P P9S 950 PSU VWB	+/-10%
911401514948	SP303P P8S 927 PSU MB PLUS	-10% / +10%
911401515048	SP303P P8S 927 PSU NB PLUS	-10% / +10%
911401515148	SP303P P8S 927 PSU VWB PLUS	-10% / +10%
911401515248	SP303P P8S 927 PSU WB PLUS	-10% / +10%
911401515348	SP303P P8S 930 PSU MB PLUS	-10% / +10%
911401515448	SP303P P8S 930 PSU NB PLUS	-10% / +10%
911401515548	SP303P P8S 930 PSU VWB PLUS	-10% / +10%
911401515648	SP303P P8S 930 PSU WB PLUS	-10% / +10%

GreenSpace Surface Mount

Order Code	Full Product Name	Luminous flux tolerance
911401515748	SP303P P8S 940 PSU MB PLUS	-10% / +10%
911401515848	SP303P P8S 940 PSU NB PLUS	-10% / +10%
911401515948	SP303P P8S 940 PSU VWB PLUS	-10% / +10%
911401516048	SP303P P8S 940 PSU WB PLUS	-10% / +10%
911401516148	SP303P P8S 950 PSU MB PLUS	-10% / +10%
911401516248	SP303P P8S 950 PSU NB PLUS	-10% / +10%
911401516348	SP303P P8S 950 PSU VWB PLUS	-10% / +10%
911401516448	SP303P P8S 950 PSU WB PLUS	-10% / +10%
911401590812	SP303P P6 927 PSU NB	+/-10%
911401590912	SP303P P6 927 PSU MB	+/-10%
911401591012	SP303P P6 927 PSU WB	+/-10%
911401591112	SP303P P6 927 PSU VWB	+/-10%
911401591212	SP303P P6 930 PSU NB	+/-10%
911401591312	SP303P P6 930 PSU MB	+/-10%
911401591412	SP303P P6 930 PSU WB	+/-10%
911401591512	SP303P P6 930 PSU VWB	+/-10%
911401510248	SM303C P24 927 PSU MB PLUS	-10% / +10%
911401510348	SM303C P24 927 PSU NB PLUS	-10% / +10%
911401510448	SM303C P24 927 PSU VWB PLUS	-10% / +10%
911401510548	SM303C P24 927 PSU WB PLUS	-10% / +10%
911401510648	SM303C P24 930 PSU MB PLUS	-10% / +10%
911401510748	SM303C P24 930 PSU NB PLUS	-10% / +10%
911401510822	SM303C P24 927 PSU NB	+/-10%
911401510848	SM303C P24 930 PSU VWB PLUS	-10% / +10%
911401510922	SM303C P24 927 PSU MB	+/-10%
911401510948	SM303C P24 930 PSU WB PLUS	-10% / +10%
911401511022	SM303C P24 927 PSU WB	+/-10%
911401511048	SM303C P24 940 PSU MB PLUS	-10% / +10%
911401511122	SM303C P24 927 PSU VWB	+/-10%
911401511148	SM303C P24 940 PSU NB PLUS	-10% / +10%
911401511222	SM303C P24 930 PSU NB	+/-10%
911401511248	SM303C P24 940 PSU WB PLUS	-10% / +10%
911401511322	SM303C P24 930 PSU MB	+/-10%
911401511348	SM303C P24 950 PSU MB PLUS	-10% / +10%
911401511422	SM303C P24 930 PSU WB	+/-10%
911401511448	SM303C P24 950 PSU NB PLUS	-10% / +10%
911401511522	SM303C P24 930 PSU VWB	+/-10%
911401511548	SM303C P24 950 PSU VWB PLUS	-10% / +10%
911401511648	SM303C P24 950 PSU WB PLUS	-10% / +10%
911401511748	SM303C P28 927 PSU MB PLUS	-10% / +10%
911401511848	SM303C P28 927 PSU NB PLUS	-10% / +10%
911401511948	SM303C P28 927 PSU VWB PLUS	-10% / +10%
911401512022	SM303C P24 940 PSU NB	+/-10%
911401512048	SM303C P28 927 PSU WB PLUS	-10% / +10%
911401512122	SM303C P24 940 PSU MB	+/-10%
911401512148	SM303C P28 930 PSU MB PLUS	-10% / +10%
911401512222	SM303C P24 940 PSU WB	+/-10%
911401512248	SM303C P28 930 PSU NB PLUS	-10% / +10%
911401512348	SM303C P28 930 PSU VWB PLUS	-10% / +10%
911401512422	SM303C P24 950 PSU NB	+/-10%
911401512448	SM303C P28 930 PSU WB PLUS	-10% / +10%
911401512522	SM303C P24 950 PSU MB	+/-10%

Order Code	Full Product Name	Luminous flux tolerance
911401512548	SM303C P28 940 PSU MB PLUS	-10% / +10%
911401512622	SM303C P24 950 PSU WB	+/-10%
911401512648	SM303C P28 940 PSU NB PLUS	-10% / +10%
911401512722	SM303C P24 950 PSU VWB	+/-10%
911401512748	SM303C P28 940 PSU VWB PLUS	-10% / +10%
911401512848	SM303C P28 940 PSU WB PLUS	-10% / +10%
911401512948	SM303C P28 950 PSU MB PLUS	-10% / +10%
911401513048	SM303C P28 950 PSU NB PLUS	-10% / +10%
911401513148	SM303C P28 950 PSU VWB PLUS	-10% / +10%
911401513248	SM303C P28 950 PSU WB PLUS	-10% / +10%
911401514822	SM303C P28 927 PSU NB	+/-10%
911401514922	SM303C P28 927 PSU MB	+/-10%
911401515022	SM303C P28 927 PSU WB	+/-10%
911401515122	SM303C P28 927 PSU VWB	+/-10%
911401515222	SM303C P28 930 PSU NB	+/-10%
911401515322	SM303C P28 930 PSU MB	+/-10%
911401515422	SM303C P28 930 PSU WB	+/-10%
911401515522	SM303C P28 930 PSU VWB	+/-10%
911401516022	SM303C P28 940 PSU NB	+/-10%
911401516122	SM303C P28 940 PSU MB	+/-10%
911401516222	SM303C P28 940 PSU WB	+/-10%
911401516322	SM303C P28 940 PSU VWB	+/-10%
911401516422	SM303C P28 950 PSU NB	+/-10%
911401516522	SM303C P28 950 PSU MB	+/-10%
911401516622	SM303C P28 950 PSU WB	+/-10%
911401516722	SM303C P28 950 PSU VWB	+/-10%
911401517822	SM304C P10 927 PSU MB	+/-10%
911401517922	SM304C P10 927 PSU WB	+/-10%
911401518022	SM304C P10 930 PSU MB	+/-10%
911401518122	SM304C P10 930 PSU WB	+/-10%
911401518422	SM304C P10 940 PSU MB	+/-10%
911401518522	SM304C P10 940 PSU WB	+/-10%
911401518622	SM304C P10 950 PSU MB	+/-10%
911401518722	SM304C P10 950 PSU WB	+/-10%
911401519822	SM304C P12 927 PSU MB	+/-10%
911401519922	SM304C P12 927 PSU WB	+/-10%
911401520022	SM304C P12 930 PSU MB	+/-10%
911401520122	SM304C P12 930 PSU WB	+/-10%
911401520422	SM304C P12 940 PSU MB	+/-10%
911401520522	SM304C P12 940 PSU WB	+/-10%
911401520622	SM304C P12 950 PSU MB	+/-10%
911401520722	SM304C P12 950 PSU WB	+/-10%
911401521822	SM304C P15 927 PSU MB	+/-10%
911401521922	SM304C P15 927 PSU WB	+/-10%
911401522022	SM304C P15 930 PSU MB	+/-10%
911401522122	SM304C P15 930 PSU WB	+/-10%
911401522422	SM304C P15 940 PSU MB	+/-10%
911401522522	SM304C P15 940 PSU WB	+/-10%
911401522622	SM304C P15 950 PSU MB	+/-10%
911401522722	SM304C P15 950 PSU WB	+/-10%
911401541248	SM303C P8S 927 PSU MB PLUS	-10% / +10%
911401541348	SM303C P8S 927 PSU NB PLUS	-10% / +10%

GreenSpace Surface Mount

Order Code	Full Product Name	Luminous flux tolerance
911401541448	SM303C P8S 927 PSU VWB PLUS	-10% / +10%
911401541548	SM303C P8S 927 PSU WB PLUS	-10% / +10%
911401541648	SM303C P8S 930 PSU MB PLUS	-10% / +10%
911401541748	SM303C P8S 930 PSU NB PLUS	-10% / +10%
911401541848	SM303C P8S 930 PSU VWB PLUS	-10% / +10%
911401541948	SM303C P8S 930 PSU WB PLUS	-10% / +10%
911401542048	SM303C P8S 940 PSU MB PLUS	-10% / +10%
911401542148	SM303C P8S 940 PSU NB PLUS	-10% / +10%
911401542248	SM303C P8S 940 PSU VWB PLUS	-10% / +10%
911401542348	SM303C P8S 940 PSU WB PLUS	-10% / +10%
911401542448	SM303C P8S 950 PSU MB PLUS	-10% / +10%
911401542548	SM303C P8S 950 PSU NB PLUS	-10% / +10%
911401542648	SM303C P8S 950 PSU VWB PLUS	-10% / +10%
911401542748	SM303C P8S 950 PSU WB PLUS	-10% / +10%
911401582812	SM303C P6S 927 PSU NB	+/-10%
911401582912	SM303C P6S 927 PSU MB	+/-10%
911401583012	SM303C P6S 927 PSU WB	+/-10%
911401583112	SM303C P6S 927 PSU VWB	+/-10%
911401583212	SM303C P6S 930 PSU NB	+/-10%
911401583312	SM303C P6S 930 PSU MB	+/-10%
911401583412	SM303C P6S 930 PSU WB	+/-10%
911401583512	SM303C P6S 930 PSU VWB	+/-10%
911401584012	SM303C P6S 940 PSU NB	+/-10%
911401584112	SM303C P6S 940 PSU MB	+/-10%
911401584212	SM303C P6S 940 PSU WB	+/-10%
911401584312	SM303C P6S 940 PSU VWB	+/-10%
911401584412	SM303C P6S 950 PSU NB	+/-10%
911401584512	SM303C P6S 950 PSU MB	+/-10%
911401584612	SM303C P6S 950 PSU WB	+/-10%
911401584712	SM303C P6S 950 PSU VWB	+/-10%
911401586812	SM303C P9S 927 PSU NB	+/-10%
911401586912	SM303C P9S 927 PSU MB	+/-10%
911401587012	SM303C P9S 927 PSU WB	+/-10%
911401587112	SM303C P9S 927 PSU VWB	+/-10%
911401587212	SM303C P9S 930 PSU NB	+/-10%
911401587312	SM303C P9S 930 PSU MB	+/-10%
911401587412	SM303C P9S 930 PSU WB	+/-10%
911401587512	SM303C P9S 930 PSU VWB	+/-10%
911401588012	SM303C P9S 940 PSU NB	+/-10%
911401588112	SM303C P9S 940 PSU MB	+/-10%
911401588212	SM303C P9S 940 PSU WB	+/-10%
911401588312	SM303C P9S 940 PSU VWB	+/-10%
911401588412	SM303C P9S 950 PSU NB	+/-10%
911401588512	SM303C P9S 950 PSU MB	+/-10%
911401588612	SM303C P9S 950 PSU WB	+/-10%
911401588712	SM303C P9S 950 PSU VWB	+/-10%
911401506822	SM303C P20 927 PSU NB	+/-10%
911401506922	SM303C P20 927 PSU MB	+/-10%
911401507022	SM303C P20 927 PSU WB	+/-10%
911401507122	SM303C P20 927 PSU VWB	+/-10%
911401507222	SM303C P20 930 PSU NB	+/-10%
911401507322	SM303C P20 930 PSU MB	+/-10%

Order Code	Full Product Name	Luminous flux tolerance
911401507422	SM303C P20 930 PSU WB	+/-10%
911401507522	SM303C P20 930 PSU VWB	+/-10%
911401508022	SM303C P20 940 PSU NB	+/-10%
911401508122	SM303C P20 940 PSU MB	+/-10%
911401508222	SM303C P20 940 PSU WB	+/-10%
911401508322	SM303C P20 940 PSU VWB	+/-10%
911401508422	SM303C P20 950 PSU NB	+/-10%
911401508522	SM303C P20 950 PSU MB	+/-10%
911401508848	SM303C P20 927 PSU MB PLUS	-10% / +10%
911401508948	SM303C P20 927 PSU NB PLUS	-10% / +10%
911401509048	SM303C P20 927 PSU VWB PLUS	-10% / +10%
911401509148	SM303C P20 927 PSU WB PLUS	-10% / +10%
911401509248	SM303C P20 930 PSU MB PLUS	-10% / +10%
911401509348	SM303C P20 930 PSU NB PLUS	-10% / +10%
911401509448	SM303C P20 930 PSU VWB PLUS	-10% / +10%
911401509548	SM303C P20 930 PSU WB PLUS	-10% / +10%
911401509648	SM303C P20 940 PSU MB PLUS	-10% / +10%
911401509748	SM303C P20 940 PSU NB PLUS	-10% / +10%
911401509848	SM303C P20 940 PSU VWB PLUS	-10% / +10%
911401509948	SM303C P20 940 PSU WB PLUS	-10% / +10%
911401510048	SM303C P20 950 PSU MB PLUS	-10% / +10%
911401510148	SM303C P20 950 PSU NB PLUS	-10% / +10%
911401539648	SM303C P8 927 PSU MB PLUS	-10% / +10%
911401539748	SM303C P8 927 PSU NB PLUS	-10% / +10%
911401539848	SM303C P8 927 PSU VWB PLUS	-10% / +10%
911401539948	SM303C P8 927 PSU WB PLUS	-10% / +10%
911401540048	SM303C P8 930 PSU MB PLUS	-10% / +10%
911401540148	SM303C P8 930 PSU NB PLUS	-10% / +10%
911401540248	SM303C P8 930 PSU VWB PLUS	-10% / +10%
911401540348	SM303C P8 930 PSU WB PLUS	-10% / +10%
911401540448	SM303C P8 940 PSU MB PLUS	-10% / +10%
911401540548	SM303C P8 940 PSU NB PLUS	-10% / +10%
911401540648	SM303C P8 940 PSU VWB PLUS	-10% / +10%
911401540748	SM303C P8 940 PSU WB PLUS	-10% / +10%
911401540848	SM303C P8 950 PSU MB PLUS	-10% / +10%
911401540948	SM303C P8 950 PSU NB PLUS	-10% / +10%
911401541048	SM303C P8 950 PSU VWB PLUS	-10% / +10%
911401541148	SM303C P8 950 PSU WB PLUS	-10% / +10%
911401574812	SM303C P6 927 PSU NB	+/-10%
911401574912	SM303C P6 927 PSU MB	+/-10%
911401575012	SM303C P6 927 PSU WB	+/-10%
911401575112	SM303C P6 927 PSU VWB	+/-10%
911401575212	SM303C P6 930 PSU NB	+/-10%
911401575312	SM303C P6 930 PSU MB	+/-10%
911401575412	SM303C P6 930 PSU WB	+/-10%
911401575512	SM303C P6 930 PSU VWB	+/-10%
911401576012	SM303C P6 940 PSU NB	+/-10%
911401576112	SM303C P6 940 PSU MB	+/-10%
911401576212	SM303C P6 940 PSU WB	+/-10%
911401576312	SM303C P6 940 PSU VWB	+/-10%
911401576412	SM303C P6 950 PSU NB	+/-10%
911401576512	SM303C P6 950 PSU MB	+/-10%

GreenSpace Surface Mount

Order Code	Full Product Name	Luminous flux tolerance
911401576612	SM303C P6 950 PSU WB	+/-10%
911401576712	SM303C P6 950 PSU VWB	+/-10%
911401578812	SM303C P9 927 PSU NB	+/-10%
911401578912	SM303C P9 927 PSU MB	+/-10%
911401579012	SM303C P9 927 PSU WB	+/-10%
911401579112	SM303C P9 927 PSU VWB	+/-10%
911401579212	SM303C P9 930 PSU NB	+/-10%
911401579312	SM303C P9 930 PSU MB	+/-10%
911401579412	SM303C P9 930 PSU WB	+/-10%

Order Code	Full Product Name	Luminous flux tolerance
911401579512	SM303C P9 930 PSU VWB	+/-10%
911401580012	SM303C P9 940 PSU NB	+/-10%
911401580112	SM303C P9 940 PSU MB	+/-10%
911401580212	SM303C P9 940 PSU WB	+/-10%
911401580312	SM303C P9 940 PSU VWB	+/-10%
911401580412	SM303C P9 950 PSU NB	+/-10%
911401580512	SM303C P9 950 PSU MB	+/-10%
911401580612	SM303C P9 950 PSU WB	+/-10%
911401580712	SM303C P9 950 PSU VWB	+/-10%

