

FlexBlend, Surface Mounted

SM340C



FlexBlend heading the way to efficient and flexible furnished offices areas

Philips FlexBlend is an attractive family of surface mounted and suspended luminaires, next to Flexblend recessed. The luminaire range is enabling building owners to advance their lighting operations, by offering office-compliant lighting with a return on investment of less than 3 years. FlexBlend provides the required flexibility through the adaptability in design. This gives the possibility to install the luminaires easily in the field, at any moment. Even when today's luminaire is suspended, tomorrow this can be adapted to a surface mounted installation at the venue. And the other way around. . The surface mounted and suspended luminaire range fit to many different office spaces like open plan office, corridors, reception or meeting rooms. FlexBlend is offered in both lines and as standalone, using the same lighting module. This gives the option to the users to use FlexBlend as standalone now, and tomorrow, as line. The controller is integrated in the luminaire. As technology is changing fast, the ideal lighting solution is also expected to be ready to incorporate innovations that

can help optimize operations further. For this reason, FlexBlend holds all connectivity and future ready options available. As System Ready luminaire it can be paired with lighting management systems such as the Philips Interact Office wired (PoE) and Interact Office wireless and/or existing and upcoming sensor innovations. The luminaire range is therefore future ready and can be delivered without any system component, and in a next phase, in the field to be upgraded. An attractive opportunity for new installations and renovations.

Benefits

- Return of investment less than 3 years
- A flexible office, with application flexibility to the choice of luminaires to fit many office areas
- Future ready: scalable and ready to be connected to controls and lighting systems

Applications

- Offices
- Education
- Healthcare

Features

- Fully office compliant (UGR <19, L65 < 3000cd/sm) , light level according to office applications requirements
- Homogenous and uniform light effect

Versions

- Various mounting options, dimensional variety and local options
- Integrated sensors
- Ready to be connected to software based lighting systems such as Interact Office
- The product is IPX0 & as such is not protected against water ingress & as such we strongly recommend that The environment in which The luminaire is to be installed is suitably checked
- If The above advice is not taken and The luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure & product warranty will become void



FlexBlend Surface Mounted
SM340C MLO WH



FlexBlend Surface Mounted
SM340C O WH



FlexBlend Surface Mounted
SM340C PCS SI



FlexBlend Surface Mounted
SM340C O BK



FlexBlend Surface Mounted-Suspended Emergency Lighting



FlexBlend Surface Mounted SM340C MLO SI



FlexBlend Surface Mounted SM340C O SI



FlexBlend Surface Mounted SM340C MLO BK



FlexBlend Surface Mounted-SM340C-MLO-WH-SENS1-L150





FlexBlend Surface Mounted SM340C PCS WH




FlexBlend Surface Mounted SM340C PCS BK

Dimensional drawing

FlexBlend SM L150 DIR





LINE
FlexBlend SM L150 DIR




FLEXBLEND LINE

FlexBlend SM L120 DIR




LINE
FlexBlend SM L120 DIR



FLEXBLEND STAND-ALONE - Power supply unit with DALI and SystemReady interface, InterAct ready - Wide beam - 120°

Product details



FlexBlend_Surface_Mounted-Suspended_Emergency Lighting



FlexBlend Surface Mounted SM340C WH




FlexBlend_Surface_Mounted-Suspended_Emergency Lighting



FlexBlend Surface Mounted SM340C WH



FlexBlend Surface Mounted SM340C PCS BK



FlexBlend Surface Mounted SM340C O SI



FlexBlend Surface Mounted SM340C




FlexBlend Surface Mounted SM340C SI



FlexBlend_Surface_Mounted-Suspended_Emergency Lighting



FlexBlend_Surface_Mounted-Suspended_Emergency Lighting



FlexBlend Surface Mounted
SM340C O SI



FlexBlend_Surface_Mounted-
Suspended_Emergency
Lighting



FlexBlend_Surface_Mounted-
SM340C-MLO-WH-
SWZU-12DPP




FlexBlend Surface Mounted
SM340C WH



FlexBlend Surface Mounted
SM340C BK



FlexBlend Surface Mounted
SM340C BK



FlexBlend Suspended SP340P
WH



FlexBlend Surface Mounted
SM340C BK



FlexBlend Surface Mounted
SM340C MLO BK



FlexBlend_Surface_Mounted-
Suspended_Emergency
Lighting



FlexBlend Surface Mounted
SM340C MLO WH



FlexBlend Surface Mounted
SM340C BK



FlexBlend Surface Mounted
SM340C brackets



FlexBlend Surface Mounted
SM340C SI



FlexBlend Suspended SP340P
BK



FlexBlend_Surface_Mounted-
Suspended_Emergency
Lighting




FlexBlend_Surface_Mounted-
Suspended_Emergency
Lighting



FlexBlend_Surface_Mounted-
Suspended_Emergency
Lighting



FlexBlend Surface Mounted
SM340C O BK



FlexBlend Suspended SP340P
SI

General Information

Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Service tag	Yes

Light Technical

Color rendering index (CRI)	>90
Optic type	Wide beam

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Protection class IEC	Safety class I

Controls and Dimming

Maximum dim level	1%
-------------------	----

Mechanical and Housing

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]

Emergency Operation

Rated duration of the emergency lighting (when fully charged)	3 hour(s)
---	-----------

Approval and Application

Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.05 %
-------------------------------	--------

Light Technical

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Beam angle of light source
910925867108	SM340C 35S/940 DEIA MLO L150 WH	3,500 lm	4000 K	101 lm/W	120 degree(s)
910925867136	SM340C 36S/940 DEIA MLO L120 WH	3,600 lm	4000 K	95 lm/W	120 degree(s)
910925867137	SM340C 40S/940 DEIA MLO L120 WH	4,000 lm	4000 K	94 lm/W	120 degree(s)
910925867262	SM341C 35S/940 DEIA MLO L150 WH	3,500 lm	4000 K	101 lm/W	120 degree(s)
910925867866	SM340C 28S/940 DEIA MLO L120 WH	2,800 lm	4000 K	98 lm/W	120 degree(s)
910925867870	SM340C 28S/930 DEIA MLO L120 WH	2,800 lm	3000 K	98 lm/W	120 degree(s)
910925867871	SM340C 36S/930 DEIA MLO L120 WH	3,600 lm	3000 K	95 lm/W	120 degree(s)
910925867880	SM340C 45S/940 DEIA MLO L150 WH	4,500 lm	4000 K	98 lm/W	120 degree(s)
910925867881	SM340C 50S/940 DEIA MLO L150 WH	5,000 lm	4000 K	96 lm/W	120 degree(s)
910925867884	SM340C 35S/930 DEIA MLO L150 WH	3,500 lm	3000 K	101 lm/W	120 degree(s)
910925867885	SM340C 45S/930 DEIA MLO L150 WH	4,500 lm	3000 K	98 lm/W	120 degree(s)
910925867904	SM341C 26S/940 DEIA MLO L150 WH	2,600 lm	4000 K	108 lm/W	120 degree(s)
910925867116	SM340C 35S/940 DEIA O L150 WH	3,500 lm	4000 K	129 lm/W	120 degree(s)
910925867867	SM340C 36S/940 DEIA O L120 WH	3,600 lm	4000 K	126 lm/W	120 degree(s)
910925867872	SM340C 36S/930 DEIA O L120 WH	3,600 lm	3000 K	116 lm/W	120 degree(s)
910925867886	SM340C 35S/930 DEIA O L150 WH	3,500 lm	3000 K	129 lm/W	120 degree(s)
910925867905	SM341C 26S/940 DEIA O L150 WH	2,600 lm	4000 K	121 lm/W	120 degree(s)
910925867101	SM340C 35S/940 DEIA PCS L150 SI	3,500 lm	4000 K	140 lm/W	120 degree(s)
910925867873	SM340C 28S/940 DEIA PCS L120 SI	2,800 lm	4000 K	136 lm/W	120 degree(s)
910925867874	SM340C 36S/940 DEIA PCS L120 SI	3,600 lm	4000 K	138 lm/W	120 degree(s)
910925867887	SM340C 45S/940 DEIA PCS L150 SI	4,500 lm	4000 K	140 lm/W	120 degree(s)
910925867888	SM340C 52S/940 DEIA PCS L150 SI	5,200 lm	4000 K	137 lm/W	120 degree(s)
910925867906	SM341C 26S/940 DEIA PCS L150 SI	2,600 lm	4000 K	133 lm/W	120 degree(s)
910925867907	SM341C 35S/940 DEIA PCS L150 SI	3,500 lm	4000 K	140 lm/W	120 degree(s)
910925867892	SM340C 35S/940 DEIA O L150 BK	3,500 lm	4000 K	129 lm/W	120 degree(s)
910925868098	SM340C 36S/940 DIA MLO ELP3 L120 WH	3,600 lm	4000 K	95 lm/W	120 degree(s)
910925867109	SM340C 35S/940 DEIA MLO L150 SI	3,500 lm	4000 K	101 lm/W	120 degree(s)
910925867875	SM340C 28S/940 DEIA MLO L120 SI	2,800 lm	4000 K	98 lm/W	120 degree(s)
910925867876	SM340C 36S/940 DEIA MLO L120 SI	3,600 lm	4000 K	98 lm/W	120 degree(s)
910925867889	SM340C 45S/940 DEIA MLO L150 SI	4,500 lm	4000 K	98 lm/W	120 degree(s)
910925867890	SM340C 50S/940 DEIA MLO L150 SI	5,000 lm	4000 K	96 lm/W	120 degree(s)
910925867908	SM341C 26S/940 DEIA MLO L150 SI	2,600 lm	4000 K	108 lm/W	120 degree(s)
910925867909	SM341C 35S/940 DEIA MLO L150 SI	3,500 lm	4000 K	101 lm/W	120 degree(s)
910925867877	SM340C 36S/940 DEIA O L120 SI	3,600 lm	4000 K	126 lm/W	120 degree(s)
910925867891	SM340C 35S/940 DEIA O L150 SI	3,500 lm	4000 K	129 lm/W	120 degree(s)
910925867110	SM340C 35S/940 DEIA MLO L150 BK	3,500 lm	4000 K	101 lm/W	120 degree(s)
910925868898	SM340C 45S/940 SEIA MLO U4 L150 WH	4,500 lm	4000 K	98 lm/W	- degree(s)
910925868899	SM340C 52S/940 SEIA PCS U4 L150 WH	5,200 lm	4000 K	140 lm/W	- degree(s)
910925868901	SM340C 45S/940 SEIA PCS U4 L150 WH	4,500 lm	4000 K	140 lm/W	- degree(s)

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Beam angle of light source
910925868902	SM340C 35S/940 SEIA PCS U4 L150 WH	3,500 lm	4000 K	146 lm/W	- degree(s)
910925868903	SM340C 42S/940 SEIA PCS U4 L120 WH	4,200 lm	4000 K	140 lm/W	- degree(s)
910925868904	SM340C 36S/940 SEIA PCS U4 L120 WH	3,600 lm	4000 K	138 lm/W	- degree(s)
910925867099	SM340C 35S/940 DEIA PCS L150 WH	3,500 lm	4000 K	140 lm/W	120 degree(s)
910925867134	SM340C 36S/940 DEIA PCS L120 WH	3,600 lm	4000 K	138 lm/W	120 degree(s)
910925867135	SM340C 42S/940 DEIA PCS L120 WH	4,200 lm	4000 K	138 lm/W	120 degree(s)
910925867865	SM340C 28S/940 DEIA PCS L120 WH	2,800 lm	4000 K	136 lm/W	120 degree(s)
910925867868	SM340C 28S/930 DEIA PCS L120 WH	2,800 lm	3000 K	136 lm/W	120 degree(s)
910925867869	SM340C 36S/930 DEIA PCS L120 WH	3,600 lm	3000 K	138 lm/W	120 degree(s)
910925867878	SM340C 45S/940 DEIA PCS L150 WH	4,500 lm	4000 K	140 lm/W	120 degree(s)
910925867879	SM340C 52S/940 DEIA PCS L150 WH	5,200 lm	4000 K	137 lm/W	120 degree(s)
910925867882	SM340C 35S/930 DEIA PCS L150 WH	3,500 lm	3000 K	140 lm/W	120 degree(s)
910925867883	SM340C 45S/930 DEIA PCS L150 WH	4,500 lm	3000 K	140 lm/W	120 degree(s)
910925867902	SM341C 26S/940 DEIA PCS L150 WH	2,600 lm	4000 K	133 lm/W	120 degree(s)
910925867903	SM341C 35S/940 DEIA PCS L150 WH	3,500 lm	4000 K	140 lm/W	120 degree(s)
910925867102	SM340C 35S/940 DEIA PCS L150 BK	3,500 lm	4000 K	140 lm/W	120 degree(s)

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Suitable for random switching
910925867108	SM340C 35S/940 DEIA MLO L150 WH	34.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867136	SM340C 36S/940 DEIA MLO L120 WH	38 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867137	SM340C 40S/940 DEIA MLO L120 WH	42.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867262	SM341C 35S/940 DEIA MLO L150 WH	34.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867866	SM340C 28S/940 DEIA MLO L120 WH	28.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867870	SM340C 28S/930 DEIA MLO L120 WH	28.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867871	SM340C 36S/930 DEIA MLO L120 WH	38 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867880	SM340C 45S/940 DEIA MLO L150 WH	46 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867881	SM340C 50S/940 DEIA MLO L150 WH	52 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867884	SM340C 35S/930 DEIA MLO L150 WH	34.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867885	SM340C 45S/930 DEIA MLO L150 WH	46 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867904	SM341C 26S/940 DEIA MLO L150 WH	26 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867116	SM340C 35S/940 DEIA O L150 WH	27 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867867	SM340C 36S/940 DEIA O L120 WH	28.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867872	SM340C 36S/930 DEIA O L120 WH	28.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867886	SM340C 35S/930 DEIA O L150 WH	27 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867905	SM341C 26S/940 DEIA O L150 WH	20.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867101	SM340C 35S/940 DEIA PCS L150 SI	25 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867873	SM340C 28S/940 DEIA PCS L120 SI	20.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867874	SM340C 36S/940 DEIA PCS L120 SI	26 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867887	SM340C 45S/940 DEIA PCS L150 SI	32 W	Yes (relates to presence/ movement detection and daylight harvesting)

Order Code	Full Product Name	Power Consumption	Suitable for random switching
910925867888	SM340C 52S/940 DEIA PCS L150 SI	38 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867906	SM341C 26S/940 DEIA PCS L150 SI	18.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867907	SM341C 35S/940 DEIA PCS L150 SI	25 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867892	SM340C 35S/940 DEIA O L150 BK	27 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925868098	SM340C 36S/940 DIA MLO ELP3 L120 WH	38 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867109	SM340C 35S/940 DEIA MLO L150 SI	34.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867875	SM340C 28S/940 DEIA MLO L120 SI	28.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867876	SM340C 36S/940 DEIA MLO L120 SI	38 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867889	SM340C 45S/940 DEIA MLO L150 SI	46 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867890	SM340C 50S/940 DEIA MLO L150 SI	52 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867908	SM341C 26S/940 DEIA MLO L150 SI	26 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867909	SM341C 35S/940 DEIA MLO L150 SI	34.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867877	SM340C 36S/940 DEIA O L120 SI	28.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867891	SM340C 35S/940 DEIA O L150 SI	27 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867110	SM340C 35S/940 DEIA MLO L150 BK	34.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925868898	SM340C 45S/940 SEIA MLO U4 L150 WH	46 W	No
910925868899	SM340C 52S/940 SEIA PCS U4 L150 WH	37 W	No
910925868901	SM340C 45S/940 SEIA PCS U4 L150 WH	32 W	No
910925868902	SM340C 35S/940 SEIA PCS U4 L150 WH	24 W	No
910925868903	SM340C 42S/940 SEIA PCS U4 L120 WH	30 W	No
910925868904	SM340C 36S/940 SEIA PCS U4 L120 WH	26 W	No
910925867099	SM340C 35S/940 DEIA PCS L150 WH	25 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867134	SM340C 36S/940 DEIA PCS L120 WH	26 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867135	SM340C 42S/940 DEIA PCS L120 WH	30.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867865	SM340C 28S/940 DEIA PCS L120 WH	20.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867868	SM340C 28S/930 DEIA PCS L120 WH	20.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867869	SM340C 36S/930 DEIA PCS L120 WH	26 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867878	SM340C 45S/940 DEIA PCS L150 WH	32 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867879	SM340C 52S/940 DEIA PCS L150 WH	38 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867882	SM340C 35S/930 DEIA PCS L150 WH	25 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867883	SM340C 45S/930 DEIA PCS L150 WH	32 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867902	SM341C 26S/940 DEIA PCS L150 WH	18.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867903	SM341C 35S/940 DEIA PCS L150 WH	25 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867102	SM340C 35S/940 DEIA PCS L150 BK	25 W	Yes (relates to presence/ movement detection and daylight harvesting)

Controls and Dimming

Order Code	Full Product Name	Dimmable
910925867108	SM340C 35S/940 DEIA MLO L150 WH	Yes
910925867136	SM340C 36S/940 DEIA MLO L120 WH	Yes
910925867137	SM340C 40S/940 DEIA MLO L120 WH	Yes

Order Code	Full Product Name	Dimmable
910925867262	SM341C 35S/940 DEIA MLO L150 WH	Yes
910925867866	SM340C 28S/940 DEIA MLO L120 WH	Yes
910925867870	SM340C 28S/930 DEIA MLO L120 WH	Yes
910925867871	SM340C 36S/930 DEIA MLO L120 WH	Yes
910925867880	SM340C 45S/940 DEIA MLO L150 WH	Yes
910925867881	SM340C 50S/940 DEIA MLO L150 WH	Yes
910925867884	SM340C 35S/930 DEIA MLO L150 WH	Yes
910925867885	SM340C 45S/930 DEIA MLO L150 WH	Yes
910925867904	SM341C 26S/940 DEIA MLO L150 WH	Yes
910925867116	SM340C 35S/940 DEIA O L150 WH	Yes
910925867867	SM340C 36S/940 DEIA O L120 WH	Yes
910925867872	SM340C 36S/930 DEIA O L120 WH	Yes
910925867886	SM340C 35S/930 DEIA O L150 WH	Yes
910925867905	SM341C 26S/940 DEIA O L150 WH	Yes
910925867101	SM340C 35S/940 DEIA PCS L150 SI	Yes
910925867873	SM340C 28S/940 DEIA PCS L120 SI	Yes
910925867874	SM340C 36S/940 DEIA PCS L120 SI	Yes
910925867887	SM340C 45S/940 DEIA PCS L150 SI	Yes
910925867888	SM340C 52S/940 DEIA PCS L150 SI	Yes
910925867906	SM341C 26S/940 DEIA PCS L150 SI	Yes
910925867907	SM341C 35S/940 DEIA PCS L150 SI	Yes
910925867892	SM340C 35S/940 DEIA O L150 BK	Yes
910925868098	SM340C 36S/940 DIA MLO ELP3 L120 WH	Yes
910925867109	SM340C 35S/940 DEIA MLO L150 SI	Yes
910925867875	SM340C 28S/940 DEIA MLO L120 SI	Yes
910925867876	SM340C 36S/940 DEIA MLO L120 SI	Yes
910925867889	SM340C 45S/940 DEIA MLO L150 SI	Yes
910925867890	SM340C 50S/940 DEIA MLO L150 SI	Yes
910925867908	SM341C 26S/940 DEIA MLO L150 SI	Yes
910925867909	SM341C 35S/940 DEIA MLO L150 SI	Yes
910925867877	SM340C 36S/940 DEIA O L120 SI	Yes
910925867891	SM340C 35S/940 DEIA O L150 SI	Yes
910925867110	SM340C 35S/940 DEIA MLO L150 BK	Yes
910925868898	SM340C 45S/940 SEIA MLO U4 L150 WH	No
910925868899	SM340C 52S/940 SEIA PCS U4 L150 WH	No
910925868901	SM340C 45S/940 SEIA PCS U4 L150 WH	No
910925868902	SM340C 35S/940 SEIA PCS U4 L150 WH	No
910925868903	SM340C 42S/940 SEIA PCS U4 L120 WH	No
910925868904	SM340C 36S/940 SEIA PCS U4 L120 WH	No
910925867099	SM340C 35S/940 DEIA PCS L150 WH	Yes
910925867134	SM340C 36S/940 DEIA PCS L120 WH	Yes
910925867135	SM340C 42S/940 DEIA PCS L120 WH	Yes

Order Code	Full Product Name	Dimmable
910925867865	SM340C 28S/940 DEIA PCS L120 WH	Yes
910925867868	SM340C 28S/930 DEIA PCS L120 WH	Yes
910925867869	SM340C 36S/930 DEIA PCS L120 WH	Yes
910925867878	SM340C 45S/940 DEIA PCS L150 WH	Yes
910925867879	SM340C 52S/940 DEIA PCS L150 WH	Yes
910925867882	SM340C 35S/930 DEIA PCS L150 WH	Yes
910925867883	SM340C 45S/930 DEIA PCS L150 WH	Yes
910925867902	SM341C 26S/940 DEIA PCS L150 WH	Yes
910925867903	SM341C 35S/940 DEIA PCS L150 WH	Yes
910925867102	SM340C 35S/940 DEIA PCS L150 BK	Yes

Mechanical and Housing

Order Code	Full Product Name	Housing Color
910925867108	SM340C 35S/940 DEIA MLO L150 WH	White
910925867136	SM340C 36S/940 DEIA MLO L120 WH	White
910925867137	SM340C 40S/940 DEIA MLO L120 WH	White
910925867262	SM341C 35S/940 DEIA MLO L150 WH	White
910925867866	SM340C 28S/940 DEIA MLO L120 WH	White
910925867870	SM340C 28S/930 DEIA MLO L120 WH	White
910925867871	SM340C 36S/930 DEIA MLO L120 WH	White
910925867880	SM340C 45S/940 DEIA MLO L150 WH	White
910925867881	SM340C 50S/940 DEIA MLO L150 WH	White
910925867884	SM340C 35S/930 DEIA MLO L150 WH	White
910925867885	SM340C 45S/930 DEIA MLO L150 WH	White
910925867904	SM341C 26S/940 DEIA MLO L150 WH	White
910925867116	SM340C 35S/940 DEIA O L150 WH	White
910925867867	SM340C 36S/940 DEIA O L120 WH	White
910925867872	SM340C 36S/930 DEIA O L120 WH	White
910925867886	SM340C 35S/930 DEIA O L150 WH	White
910925867905	SM341C 26S/940 DEIA O L150 WH	White
910925867101	SM340C 35S/940 DEIA PCS L150 SI	Silver
910925867873	SM340C 28S/940 DEIA PCS L120 SI	Silver
910925867874	SM340C 36S/940 DEIA PCS L120 SI	Silver
910925867887	SM340C 45S/940 DEIA PCS L150 SI	Silver
910925867888	SM340C 52S/940 DEIA PCS L150 SI	Silver
910925867906	SM341C 26S/940 DEIA PCS L150 SI	Silver
910925867907	SM341C 35S/940 DEIA PCS L150 SI	Silver
910925867892	SM340C 35S/940 DEIA O L150 BK	Black
910925868098	SM340C 36S/940 DIA MLO ELP3 L120 WH	White
910925867109	SM340C 35S/940 DEIA MLO L150 SI	Silver
910925867875	SM340C 28S/940 DEIA MLO L120 SI	Silver
910925867876	SM340C 36S/940 DEIA MLO L120 SI	Silver

Order Code	Full Product Name	Housing Color
910925867889	SM340C 45S/940 DEIA MLO L150 SI	Silver
910925867890	SM340C 50S/940 DEIA MLO L150 SI	Silver
910925867908	SM341C 26S/940 DEIA MLO L150 SI	Silver
910925867909	SM341C 35S/940 DEIA MLO L150 SI	Silver
910925867877	SM340C 36S/940 DEIA O L120 SI	Silver
910925867891	SM340C 35S/940 DEIA O L150 SI	Silver
910925867110	SM340C 35S/940 DEIA MLO L150 BK	Black
910925868898	SM340C 45S/940 SEIA MLO U4 L150 WH	White
910925868899	SM340C 52S/940 SEIA PCS U4 L150 WH	White
910925868901	SM340C 45S/940 SEIA PCS U4 L150 WH	White
910925868902	SM340C 35S/940 SEIA PCS U4 L150 WH	White
910925868903	SM340C 42S/940 SEIA PCS U4 L120 WH	White
910925868904	SM340C 36S/940 SEIA PCS U4 L120 WH	White
910925867099	SM340C 35S/940 DEIA PCS L150 WH	White
910925867134	SM340C 36S/940 DEIA PCS L120 WH	White
910925867135	SM340C 42S/940 DEIA PCS L120 WH	White
910925867865	SM340C 28S/940 DEIA PCS L120 WH	White
910925867868	SM340C 28S/930 DEIA PCS L120 WH	White
910925867869	SM340C 36S/930 DEIA PCS L120 WH	White
910925867878	SM340C 45S/940 DEIA PCS L150 WH	White
910925867879	SM340C 52S/940 DEIA PCS L150 WH	White
910925867882	SM340C 35S/930 DEIA PCS L150 WH	White
910925867883	SM340C 45S/930 DEIA PCS L150 WH	White
910925867902	SM341C 26S/940 DEIA PCS L150 WH	White
910925867903	SM341C 35S/940 DEIA PCS L150 WH	White
910925867102	SM340C 35S/940 DEIA PCS L150 BK	Black

Emergency Operation

Order Code	Full Product Name	Central Emergency	Emergency lighting
910925867108	SM340C 35S/940 DEIA MLO L150 WH	Yes	DC operated central emergency lighting
910925867136	SM340C 36S/940 DEIA MLO L120 WH	Yes	DC operated central emergency lighting
910925867137	SM340C 40S/940 DEIA MLO L120 WH	Yes	DC operated central emergency lighting
910925867262	SM341C 35S/940 DEIA MLO L150 WH	Yes	DC operated central emergency lighting
910925867866	SM340C 28S/940 DEIA MLO L120 WH	Yes	DC operated central emergency lighting
910925867870	SM340C 28S/930 DEIA MLO L120 WH	Yes	DC operated central emergency lighting
910925867871	SM340C 36S/930 DEIA MLO L120 WH	Yes	DC operated central emergency lighting
910925867880	SM340C 45S/940 DEIA MLO L150 WH	Yes	DC operated central emergency lighting
910925867881	SM340C 50S/940 DEIA MLO L150 WH	Yes	DC operated central emergency lighting
910925867884	SM340C 35S/930 DEIA MLO L150 WH	Yes	DC operated central emergency lighting
910925867885	SM340C 45S/930 DEIA MLO L150 WH	Yes	DC operated central emergency lighting
910925867904	SM341C 26S/940 DEIA MLO L150 WH	Yes	DC operated central emergency lighting
910925867116	SM340C 35S/940 DEIA O L150 WH	Yes	DC operated central emergency lighting

Order Code	Full Product Name	Central Emergency	Emergency lighting
910925867867	SM340C 36S/940 DEIA O L120 WH	Yes	DC operated central emergency lighting
910925867872	SM340C 36S/930 DEIA O L120 WH	Yes	DC operated central emergency lighting
910925867886	SM340C 35S/930 DEIA O L150 WH	Yes	DC operated central emergency lighting
910925867905	SM341C 26S/940 DEIA O L150 WH	Yes	DC operated central emergency lighting
910925867101	SM340C 35S/940 DEIA PCS L150 SI	Yes	DC operated central emergency lighting
910925867873	SM340C 28S/940 DEIA PCS L120 SI	Yes	DC operated central emergency lighting
910925867874	SM340C 36S/940 DEIA PCS L120 SI	Yes	DC operated central emergency lighting
910925867887	SM340C 45S/940 DEIA PCS L150 SI	Yes	DC operated central emergency lighting
910925867888	SM340C 52S/940 DEIA PCS L150 SI	Yes	DC operated central emergency lighting
910925867906	SM341C 26S/940 DEIA PCS L150 SI	Yes	DC operated central emergency lighting
910925867907	SM341C 35S/940 DEIA PCS L150 SI	Yes	DC operated central emergency lighting
910925867892	SM340C 35S/940 DEIA O L150 BK	Yes	DC operated central emergency lighting
910925868098	SM340C 36S/940 DIA MLO ELP3 L120 WH	No	Emergency lighting 3 hours duration Pro version
910925867109	SM340C 35S/940 DEIA MLO L150 SI	Yes	DC operated central emergency lighting
910925867875	SM340C 28S/940 DEIA MLO L120 SI	Yes	DC operated central emergency lighting
910925867876	SM340C 36S/940 DEIA MLO L120 SI	Yes	DC operated central emergency lighting
910925867889	SM340C 45S/940 DEIA MLO L150 SI	Yes	DC operated central emergency lighting
910925867890	SM340C 50S/940 DEIA MLO L150 SI	Yes	DC operated central emergency lighting
910925867908	SM341C 26S/940 DEIA MLO L150 SI	Yes	DC operated central emergency lighting
910925867909	SM341C 35S/940 DEIA MLO L150 SI	Yes	DC operated central emergency lighting
910925867877	SM340C 36S/940 DEIA O L120 SI	Yes	DC operated central emergency lighting
910925867891	SM340C 35S/940 DEIA O L150 SI	Yes	DC operated central emergency lighting
910925867110	SM340C 35S/940 DEIA MLO L150 BK	Yes	DC operated central emergency lighting
910925868898	SM340C 45S/940 SEIA MLO U4 L150 WH	Yes	DC operated central emergency lighting
910925868899	SM340C 52S/940 SEIA PCS U4 L150 WH	Yes	DC operated central emergency lighting
910925868901	SM340C 45S/940 SEIA PCS U4 L150 WH	Yes	DC operated central emergency lighting
910925868902	SM340C 35S/940 SEIA PCS U4 L150 WH	Yes	DC operated central emergency lighting
910925868903	SM340C 42S/940 SEIA PCS U4 L120 WH	Yes	DC operated central emergency lighting
910925868904	SM340C 36S/940 SEIA PCS U4 L120 WH	Yes	DC operated central emergency lighting
910925867099	SM340C 35S/940 DEIA PCS L150 WH	Yes	DC operated central emergency lighting
910925867134	SM340C 36S/940 DEIA PCS L120 WH	Yes	DC operated central emergency lighting
910925867135	SM340C 42S/940 DEIA PCS L120 WH	Yes	DC operated central emergency lighting
910925867865	SM340C 28S/940 DEIA PCS L120 WH	Yes	DC operated central emergency lighting
910925867868	SM340C 28S/930 DEIA PCS L120 WH	Yes	DC operated central emergency lighting
910925867869	SM340C 36S/930 DEIA PCS L120 WH	Yes	DC operated central emergency lighting
910925867878	SM340C 45S/940 DEIA PCS L150 WH	Yes	DC operated central emergency lighting
910925867879	SM340C 52S/940 DEIA PCS L150 WH	Yes	DC operated central emergency lighting
910925867882	SM340C 35S/930 DEIA PCS L150 WH	Yes	DC operated central emergency lighting
910925867883	SM340C 45S/930 DEIA PCS L150 WH	Yes	DC operated central emergency lighting
910925867902	SM341C 26S/940 DEIA PCS L150 WH	Yes	DC operated central emergency lighting
910925867903	SM341C 35S/940 DEIA PCS L150 WH	Yes	DC operated central emergency lighting
910925867102	SM340C 35S/940 DEIA PCS L150 BK	Yes	DC operated central emergency lighting

Approval and Application

Order Code	Full Product Name	Glow-wire test	ENEC mark	Ambient temperature range
910925867108	SM340C 35S/940 DEIA MLO L150 WH	Temperature 650 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867136	SM340C 36S/940 DEIA MLO L120 WH	Temperature 650 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867137	SM340C 40S/940 DEIA MLO L120 WH	Temperature 650 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867262	SM341C 35S/940 DEIA MLO L150 WH	Temperature 650 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867866	SM340C 28S/940 DEIA MLO L120 WH	Temperature 650 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867870	SM340C 28S/930 DEIA MLO L120 WH	Temperature 650 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867871	SM340C 36S/930 DEIA MLO L120 WH	Temperature 650 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867880	SM340C 45S/940 DEIA MLO L150 WH	Temperature 650 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867881	SM340C 50S/940 DEIA MLO L150 WH	Temperature 650 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867884	SM340C 35S/930 DEIA MLO L150 WH	Temperature 650 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867885	SM340C 45S/930 DEIA MLO L150 WH	Temperature 650 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867904	SM341C 26S/940 DEIA MLO L150 WH	Temperature 650 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867116	SM340C 35S/940 DEIA O L150 WH	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867867	SM340C 36S/940 DEIA O L120 WH	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867872	SM340C 36S/930 DEIA O L120 WH	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867886	SM340C 35S/930 DEIA O L150 WH	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867905	SM341C 26S/940 DEIA O L150 WH	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867101	SM340C 35S/940 DEIA PCS L150 SI	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867873	SM340C 28S/940 DEIA PCS L120 SI	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867874	SM340C 36S/940 DEIA PCS L120 SI	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867887	SM340C 45S/940 DEIA PCS L150 SI	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867888	SM340C 52S/940 DEIA PCS L150 SI	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867906	SM341C 26S/940 DEIA PCS L150 SI	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867907	SM341C 35S/940 DEIA PCS L150 SI	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867892	SM340C 35S/940 DEIA O L150 BK	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925868098	SM340C 36S/940 DIA MLO ELP3 L120 WH	Temperature 650 °C, duration 30 s	ENEC plus mark	+10 to +25 °C
910925867109	SM340C 35S/940 DEIA MLO L150 SI	Temperature 650 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867875	SM340C 28S/940 DEIA MLO L120 SI	Temperature 650 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867876	SM340C 36S/940 DEIA MLO L120 SI	Temperature 650 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867889	SM340C 45S/940 DEIA MLO L150 SI	Temperature 650 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867890	SM340C 50S/940 DEIA MLO L150 SI	Temperature 650 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867908	SM341C 26S/940 DEIA MLO L150 SI	Temperature 650 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867909	SM341C 35S/940 DEIA MLO L150 SI	Temperature 650 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867877	SM340C 36S/940 DEIA O L120 SI	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867891	SM340C 35S/940 DEIA O L150 SI	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867110	SM340C 35S/940 DEIA MLO L150 BK	Temperature 650 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925868898	SM340C 45S/940 SEIA MLO U4 L150 WH	Temperature 650 °C, duration 30 s	ENEC mark	+10 to +40 °C
910925868899	SM340C 52S/940 SEIA PCS U4 L150 WH	Temperature 850 °C, duration 30 s	ENEC mark	+10 to +40 °C
910925868901	SM340C 45S/940 SEIA PCS U4 L150 WH	Temperature 850 °C, duration 30 s	ENEC mark	+10 to +40 °C
910925868902	SM340C 35S/940 SEIA PCS U4 L150 WH	Temperature 850 °C, duration 30 s	ENEC mark	+10 to +40 °C
910925868903	SM340C 42S/940 SEIA PCS U4 L120 WH	Temperature 850 °C, duration 30 s	ENEC mark	+10 to +40 °C

Order Code	Full Product Name	Glow-wire test	ENEC mark	Ambient temperature range
910925868904	SM340C 36S/940 SEIA PCS U4 L120 WH	Temperature 850 °C, duration 30 s	ENEC mark	+10 to +40 °C
910925867099	SM340C 35S/940 DEIA PCS L150 WH	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867134	SM340C 36S/940 DEIA PCS L120 WH	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867135	SM340C 42S/940 DEIA PCS L120 WH	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867865	SM340C 28S/940 DEIA PCS L120 WH	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867868	SM340C 28S/930 DEIA PCS L120 WH	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867869	SM340C 36S/930 DEIA PCS L120 WH	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867878	SM340C 45S/940 DEIA PCS L150 WH	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867879	SM340C 52S/940 DEIA PCS L150 WH	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867882	SM340C 35S/930 DEIA PCS L150 WH	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867883	SM340C 45S/930 DEIA PCS L150 WH	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867902	SM341C 26S/940 DEIA PCS L150 WH	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867903	SM341C 35S/940 DEIA PCS L150 WH	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867102	SM340C 35S/940 DEIA PCS L150 BK	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910925867108	SM340C 35S/940 DEIA MLO L150 WH	(0.38, 0.38) SDCM <3
910925867136	SM340C 36S/940 DEIA MLO L120 WH	(0.38, 0.38) SDCM <3
910925867137	SM340C 40S/940 DEIA MLO L120 WH	(0.38, 0.38) SDCM <3
910925867262	SM341C 35S/940 DEIA MLO L150 WH	(0.38, 0.38) SDCM <3
910925867866	SM340C 28S/940 DEIA MLO L120 WH	(0.38, 0.38) SDCM <3
910925867870	SM340C 28S/930 DEIA MLO L120 WH	(0.43, 0.40) SDCM <3
910925867871	SM340C 36S/930 DEIA MLO L120 WH	(0.43, 0.40) SDCM <3
910925867880	SM340C 45S/940 DEIA MLO L150 WH	(0.38, 0.38) SDCM <3
910925867881	SM340C 50S/940 DEIA MLO L150 WH	(0.38, 0.38) SDCM <3
910925867884	SM340C 35S/930 DEIA MLO L150 WH	(0.43, 0.40) SDCM <3
910925867885	SM340C 45S/930 DEIA MLO L150 WH	(0.43, 0.40) SDCM <3
910925867904	SM341C 26S/940 DEIA MLO L150 WH	(0.38, 0.38) SDCM <3
910925867116	SM340C 35S/940 DEIA O L150 WH	(0.38, 0.38) SDCM <3
910925867867	SM340C 36S/940 DEIA O L120 WH	(0.38, 0.38) SDCM <3
910925867872	SM340C 36S/930 DEIA O L120 WH	(0.43, 0.40) SDCM <3
910925867886	SM340C 35S/930 DEIA O L150 WH	(0.43, 0.40) SDCM <3
910925867905	SM341C 26S/940 DEIA O L150 WH	(0.38, 0.38) SDCM <3
910925867101	SM340C 35S/940 DEIA PCS L150 SI	(0.38, 0.38) SDCM <3
910925867873	SM340C 28S/940 DEIA PCS L120 SI	(0.38, 0.38) SDCM <3
910925867874	SM340C 36S/940 DEIA PCS L120 SI	(0.38, 0.38) SDCM <3
910925867887	SM340C 45S/940 DEIA PCS L150 SI	(0.38, 0.38) SDCM <3
910925867888	SM340C 52S/940 DEIA PCS L150 SI	(0.38, 0.38) SDCM <3
910925867906	SM341C 26S/940 DEIA PCS L150 SI	(0.38, 0.38) SDCM <3
910925867907	SM341C 35S/940 DEIA PCS L150 SI	(0.38, 0.38) SDCM <3
910925867892	SM340C 35S/940 DEIA O L150 BK	(0.38, 0.38) SDCM <3

Order Code	Full Product Name	Initial chromaticity
910925868098	SM340C 36S/940 DIA MLO ELP3 L120 WH	(0.38, 0.37) SDCM <3
910925867109	SM340C 35S/940 DEIA MLO L150 SI	(0.38, 0.38) SDCM <3
910925867875	SM340C 28S/940 DEIA MLO L120 SI	(0.38, 0.38) SDCM <3
910925867876	SM340C 36S/940 DEIA MLO L120 SI	(0.38, 0.38) SDCM <3
910925867889	SM340C 45S/940 DEIA MLO L150 SI	(0.38, 0.38) SDCM <3
910925867890	SM340C 50S/940 DEIA MLO L150 SI	(0.38, 0.38) SDCM <3
910925867908	SM341C 26S/940 DEIA MLO L150 SI	(0.38, 0.38) SDCM <3
910925867909	SM341C 35S/940 DEIA MLO L150 SI	(0.38, 0.38) SDCM <3
910925867877	SM340C 36S/940 DEIA O L120 SI	(0.38, 0.38) SDCM <3
910925867891	SM340C 35S/940 DEIA O L150 SI	(0.38, 0.38) SDCM <3
910925867110	SM340C 35S/940 DEIA MLO L150 BK	(0.38, 0.38) SDCM <3
910925868898	SM340C 45S/940 SEIA MLO U4 L150 WH	0.38,0.37
910925868899	SM340C 52S/940 SEIA PCS U4 L150 WH	0.38,0.37
910925868901	SM340C 45S/940 SEIA PCS U4 L150 WH	0.38,0.37
910925868902	SM340C 35S/940 SEIA PCS U4 L150 WH	0.38,0.37
910925868903	SM340C 42S/940 SEIA PCS U4 L120 WH	0.38,0.37
910925868904	SM340C 36S/940 SEIA PCS U4 L120 WH	0.38,0.37
910925867099	SM340C 35S/940 DEIA PCS L150 WH	(0.38, 0.38) SDCM <3
910925867134	SM340C 36S/940 DEIA PCS L120 WH	(0.38, 0.38) SDCM <3
910925867135	SM340C 42S/940 DEIA PCS L120 WH	(0.38, 0.38) SDCM <3
910925867865	SM340C 28S/940 DEIA PCS L120 WH	(0.38, 0.38) SDCM <3
910925867868	SM340C 28S/930 DEIA PCS L120 WH	(0.43, 0.40) SDCM <3
910925867869	SM340C 36S/930 DEIA PCS L120 WH	(0.43, 0.40) SDCM <3
910925867878	SM340C 45S/940 DEIA PCS L150 WH	(0.38, 0.38) SDCM <3
910925867879	SM340C 52S/940 DEIA PCS L150 WH	(0.38, 0.38) SDCM <3
910925867882	SM340C 35S/930 DEIA PCS L150 WH	(0.43, 0.40) SDCM <3
910925867883	SM340C 45S/930 DEIA PCS L150 WH	(0.43, 0.40) SDCM <3
910925867902	SM341C 26S/940 DEIA PCS L150 WH	(0.38, 0.38) SDCM <3
910925867903	SM341C 35S/940 DEIA PCS L150 WH	(0.38, 0.38) SDCM <3
910925867102	SM340C 35S/940 DEIA PCS L150 BK	(0.38, 0.38) SDCM <3


Product Data

Order Code	Full Product Name	Product family code
910925867108	SM340C 35S/940 DEIA MLO L150 WH	SM340C
910925867136	SM340C 36S/940 DEIA MLO L120 WH	SM340C
910925867137	SM340C 40S/940 DEIA MLO L120 WH	SM340C
910925867262	SM341C 35S/940 DEIA MLO L150 WH	SM341C
910925867866	SM340C 28S/940 DEIA MLO L120 WH	SM340C
910925867870	SM340C 28S/930 DEIA MLO L120 WH	SM340C
910925867871	SM340C 36S/930 DEIA MLO L120 WH	SM340C
910925867880	SM340C 45S/940 DEIA MLO L150 WH	SM340C
910925867881	SM340C 50S/940 DEIA MLO L150 WH	SM340C

Order Code	Full Product Name	Product family code
910925867884	SM340C 35S/930 DEIA MLO L150 WH	SM340C
910925867885	SM340C 45S/930 DEIA MLO L150 WH	SM340C
910925867904	SM341C 26S/940 DEIA MLO L150 WH	SM341C
910925867116	SM340C 35S/940 DEIA O L150 WH	SM340C
910925867867	SM340C 36S/940 DEIA O L120 WH	SM340C
910925867872	SM340C 36S/930 DEIA O L120 WH	SM340C
910925867886	SM340C 35S/930 DEIA O L150 WH	SM340C
910925867905	SM341C 26S/940 DEIA O L150 WH	SM341C
910925867101	SM340C 35S/940 DEIA PCS L150 SI	SM340C
910925867873	SM340C 28S/940 DEIA PCS L120 SI	SM340C
910925867874	SM340C 36S/940 DEIA PCS L120 SI	SM340C
910925867887	SM340C 45S/940 DEIA PCS L150 SI	SM340C
910925867888	SM340C 52S/940 DEIA PCS L150 SI	SM340C
910925867906	SM341C 26S/940 DEIA PCS L150 SI	SM341C
910925867907	SM341C 35S/940 DEIA PCS L150 SI	SM341C
910925867892	SM340C 35S/940 DEIA O L150 BK	SM340C
910925868098	SM340C 36S/940 DIA MLO ELP3 L120 WH	SM340C
910925867109	SM340C 35S/940 DEIA MLO L150 SI	SM340C
910925867875	SM340C 28S/940 DEIA MLO L120 SI	SM340C
910925867876	SM340C 36S/940 DEIA MLO L120 SI	SM340C
910925867889	SM340C 45S/940 DEIA MLO L150 SI	SM340C
910925867890	SM340C 50S/940 DEIA MLO L150 SI	SM340C
910925867908	SM341C 26S/940 DEIA MLO L150 SI	SM341C
910925867909	SM341C 35S/940 DEIA MLO L150 SI	SM341C
910925867877	SM340C 36S/940 DEIA O L120 SI	SM340C
910925867891	SM340C 35S/940 DEIA O L150 SI	SM340C
910925867110	SM340C 35S/940 DEIA MLO L150 BK	SM340C
910925868898	SM340C 45S/940 SEIA MLO U4 L150 WH	SM340C
910925868899	SM340C 52S/940 SEIA PCS U4 L150 WH	SM340C
910925868901	SM340C 45S/940 SEIA PCS U4 L150 WH	SM340C
910925868902	SM340C 35S/940 SEIA PCS U4 L150 WH	SM340C
910925868903	SM340C 42S/940 SEIA PCS U4 L120 WH	SM340C
910925868904	SM340C 36S/940 SEIA PCS U4 L120 WH	SM340C
910925867099	SM340C 35S/940 DEIA PCS L150 WH	SM340C
910925867134	SM340C 36S/940 DEIA PCS L120 WH	SM340C
910925867135	SM340C 42S/940 DEIA PCS L120 WH	SM340C
910925867865	SM340C 28S/940 DEIA PCS L120 WH	SM340C
910925867868	SM340C 28S/930 DEIA PCS L120 WH	SM340C
910925867869	SM340C 36S/930 DEIA PCS L120 WH	SM340C
910925867878	SM340C 45S/940 DEIA PCS L150 WH	SM340C
910925867879	SM340C 52S/940 DEIA PCS L150 WH	SM340C
910925867882	SM340C 35S/930 DEIA PCS L150 WH	SM340C

Order Code	Full Product Name	Product family code
910925867883	SM340C 45S/930 DEIA PCS L150 WH	SM340C
910925867902	SM341C 26S/940 DEIA PCS L150 WH	SM341C
910925867903	SM341C 35S/940 DEIA PCS L150 WH	SM341C
910925867102	SM340C 35S/940 DEIA PCS L150 BK	SM340C


Polar normal diagrams



SM340CI - 910925868902

SM340CI - 910925868898


SM340CI - 910925868899




SM340CI - 910925868901

SM340CI - 910925868903


SM340CI - 910925868904




SM340CI - 910925867137




SM340CI - 910925867099




SM340CI - 910925867101




SM340CI - 910925867108




SM340CI - 910925867110




SM340CI - 910925867135




SM340CI - 910925867102




SM340CI - 910925867116




SM340CI - 910925867134




SM340CI - 910925867109




SM340CI - 910925867869




SM340CI - 910925867865




SM340CI - 910925867878




SM340CI - 910925867136




SM340CI - 910925867876




SM340CI - 910925867881




SM340CI - 910925867879




SM340CI - 910925867262




SM340CI - 910925867866




SM340CI - 910925867867




SM340CI - 910925867868




SM340CI - 910925867870




SM340CI - 910925867871




SM340CI - 910925867873




SM340CI - 910925867872




SM340CI - 910925867874




SM340CI - 910925867877




SM340CI - 910925867880




SM340CI - 910925867883




SM340CI - 910925867884




SM340CI - 910925867885




SM340CI - 910925867886




SM340CI - 910925867887




SM340CI - 910925867889




SM340CI - 910925867888




SM340CI - 910925867891




SM340CI - 910925867875




SM340CI - 910925867882




SM340CI - 910925867892




SM340CI - 910925867902




SM340CI - 910925867903




SM340CI - 910925867905




SM340CI - 910925867904




SM340CI - 910925867906




SM340CI - 910925867907




SM340CI - 910925867909



SM340CI - 910925867908



SM340CI - 910925867890



SM340CI - 910925868098