



FlexBlend heading the way to efficient and flexible furnished offices areas

FlexBlend, Surface Mounted

Philips FlexBlend is an attractive family of surface mounted and suspended luminaires, next to Flexblend recessed. The luminaire range is enabling building owners to advance their lighting operations, by offering office-compliant lighting with a return on investment of less than 3 years. FlexBlend provides the required flexibility through the adaptability in design. This gives the possibility to install the luminaires easily in the field, at any moment. Even when today's luminaire is suspended, tomorrow this can be adapted to a surface mounted installation at the venue. And the other way around. . The surface mounted and suspended luminaire range fit to many different office spaces like open plan office, corridors, reception or meeting rooms. FlexBlend is offered in both lines and as standalone, using the same lighting module. This gives the option to the users to use FlexBlend as standalone now, and tomorrow, as line. The controller is integrated in the luminaire. As technology is changing fast, the ideal lighting solution is also expected to be ready to incorporate innovations that can help optimize operations further. For this reason, FlexBlend holds all connectivity and future ready options available. As System Ready luminaire it can be paired with lighting management systems such as the Philips Interact Office wired (PoE) and Interact Office wireless and/or existing and upcoming sensor innovations. The luminaire range is therefore future ready and can be delivered without any system component, and in a next phase, in the field to be upgraded. An attractive opportunity for new installations and renovations.

FlexBlend, Surface Mounted

Benefits

- Return of investment less than 3 years
- A flexible office, with application flexibility to the choice of luminaires to fit many office areas
- Future ready: scalable and ready to be connected to controls and lighting systems

Features

- Fully office compliant (UGR <19, L65< 3000cd/sm) , light level according to office applications requirements
- Homogenous and uniform light effect
- Various mounting options, dimensional variety and local options
- Integrated sensors
- Ready to be connected to software based lighting systems such as Interact Office


Application

- Offices
- Education
- Healthcare

Warnings and Safety


- The product is IPX0 & as such is not protected against water ingress & as such we strongly recommend that The environment in which The luminaire is to be installed is suitably checked
- If The above advice is not taken and The luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure & product warranty will become void

Versions



FlexBlend, Surface Mounted

Versions





FlexBlend Surface Mounted
SM340C MLO BK



FlexBlend Surface Mounted
SM340C PCS BK

Dimensional drawing



Product details



FlexBlend_Surface_Mounted-
Suspended_Emergency Lighting



FlexBlend Surface Mounted
SM340C WH



FlexBlend_Surface_Mounted-
Suspended_Emergency Lighting



FlexBlend Surface Mounted
SM340C WH

FlexBlend, Surface Mounted

Product details



FlexBlend Surface Mounted
SM340C PCS BK



FlexBlend Surface Mounted
SM340C O SI



FlexBlend Surface Mounted
SM340C



FlexBlend Surface Mounted
SM340C SI




FlexBlend_Surface_Mounted-
Suspended_Emergency Lighting

FlexBlend_Surface_Mounted-
Suspended_Emergency Lighting




FlexBlend Surface Mounted
SM340C O SI



FlexBlend, Surface Mounted

Product details

FlexBlend_Surface_Mounted-
Suspended_Emergency Lighting



FlexBlend_Surface_Mounted-
SM340C-MLO-WH-SWZU-12DPP



FlexBlend Surface Mounted
SM340C WH




FlexBlend Surface Mounted
SM340C BK



FlexBlend Surface Mounted
SM340C BK




FlexBlend Suspended SP340P WH



FlexBlend Surface Mounted
SM340C BK



FlexBlend Surface Mounted
SM340C MLO BK



FlexBlend_Surface_Mounted-
Suspended_Emergency Lighting



FlexBlend, Surface Mounted

Product details



FlexBlend Surface Mounted
SM340C MLO WH



FlexBlend Surface Mounted
SM340C BK



FlexBlend Surface Mounted
SM340C brackets



FlexBlend Surface Mounted
SM340C SI



FlexBlend Suspended SP340P BK



FlexBlend_Surface_Mounted-
Suspended_ Emergency Lighting



FlexBlend_Surface_Mounted-
Suspended_ Emergency Lighting




FlexBlend_Surface_Mounted-
Suspended_ Emergency Lighting

FlexBlend, Surface Mounted

Product details



FlexBlend Surface Mounted
SM340C O BK



FlexBlend Suspended SP340P SI

General Information

Driver included	Yes
Light source replaceable	No
Number of gear units	1 unit
Service tag	Yes

Light Technical

Color rendering index (CRI)	>90
Optic type	Wide beam

Operating and Electrical

Protection class IEC	Safety class I
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz

Controls and Dimming

Maximum dim level	1%
-------------------	----

Mechanical and Housing

Mech. impact protection code	IK02
Ingress protection code	IP20

Approval and Application

CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces

Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
---	---

Stroboscopic effect visibility measure (SVM)	0.4
--	-----

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Light Technical

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910925867108	SM340C 35S/940 DEIA MLO L150 WH	120 degree(s)	4000 K	101 lm/W	3,500 lm
910925867136	SM340C 36S/940 DEIA MLO L120 WH	120 degree(s)	4000 K	95 lm/W	3,600 lm
910925867137	SM340C 40S/940 DEIA MLO L120 WH	120 degree(s)	4000 K	94 lm/W	4,000 lm
910925867262	SM341C 35S/940 DEIA MLO L150 WH	120 degree(s)	4000 K	101 lm/W	3,500 lm
910925867866	SM340C 28S/940 DEIA MLO L120 WH	120 degree(s)	4000 K	98 lm/W	2,800 lm
910925867870	SM340C 28S/930 DEIA MLO L120 WH	120 degree(s)	3000 K	98 lm/W	2,800 lm
910925867871	SM340C 36S/930 DEIA MLO L120 WH	120 degree(s)	3000 K	95 lm/W	3,600 lm
910925867880	SM340C 45S/940 DEIA MLO L150 WH	120 degree(s)	4000 K	98 lm/W	4,500 lm
910925867881	SM340C 50S/940 DEIA MLO L150 WH	120 degree(s)	4000 K	96 lm/W	5,000 lm
910925867884	SM340C 35S/930 DEIA MLO L150 WH	120 degree(s)	3000 K	101 lm/W	3,500 lm
910925867885	SM340C 45S/930 DEIA MLO L150 WH	120 degree(s)	3000 K	98 lm/W	4,500 lm
910925867904	SM341C 26S/940 DEIA MLO L150 WH	120 degree(s)	4000 K	108 lm/W	2,600 lm
910925867116	SM340C 35S/940 DEIA O L150 WH	120 degree(s)	4000 K	129 lm/W	3,500 lm
910925867867	SM340C 36S/940 DEIA O L120 WH	120 degree(s)	4000 K	126 lm/W	3,600 lm
910925867872	SM340C 36S/930 DEIA O L120 WH	120 degree(s)	3000 K	116 lm/W	3,600 lm
910925867886	SM340C 35S/930 DEIA O L150 WH	120 degree(s)	3000 K	129 lm/W	3,500 lm
910925867905	SM341C 26S/940 DEIA O L150 WH	120 degree(s)	4000 K	121 lm/W	2,600 lm

FlexBlend, Surface Mounted

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910925867101	SM340C 35S/940 DEIA PCS L150 SI	120 degree(s)	4000 K	140 lm/W	3,500 lm
910925867873	SM340C 28S/940 DEIA PCS L120 SI	120 degree(s)	4000 K	136 lm/W	2,800 lm
910925867874	SM340C 36S/940 DEIA PCS L120 SI	120 degree(s)	4000 K	138 lm/W	3,600 lm
910925867887	SM340C 45S/940 DEIA PCS L150 SI	120 degree(s)	4000 K	140 lm/W	4,500 lm
910925867888	SM340C 52S/940 DEIA PCS L150 SI	120 degree(s)	4000 K	137 lm/W	5,200 lm
910925867906	SM341C 26S/940 DEIA PCS L150 SI	120 degree(s)	4000 K	133 lm/W	2,600 lm
910925867907	SM341C 35S/940 DEIA PCS L150 SI	120 degree(s)	4000 K	140 lm/W	3,500 lm
910925867892	SM340C 35S/940 DEIA O L150 BK	120 degree(s)	4000 K	129 lm/W	3,500 lm
910925868098	SM340C 36S/940 DIA MLO ELP3 L120 WH	120 degree(s)	4000 K	95 lm/W	3,600 lm
910925867109	SM340C 35S/940 DEIA MLO L150 SI	120 degree(s)	4000 K	101 lm/W	3,500 lm
910925867875	SM340C 28S/940 DEIA MLO L120 SI	120 degree(s)	4000 K	98 lm/W	2,800 lm
910925867876	SM340C 36S/940 DEIA MLO L120 SI	120 degree(s)	4000 K	98 lm/W	3,600 lm
910925867889	SM340C 45S/940 DEIA MLO L150 SI	120 degree(s)	4000 K	98 lm/W	4,500 lm
910925867890	SM340C 50S/940 DEIA MLO L150 SI	120 degree(s)	4000 K	96 lm/W	5,000 lm
910925867908	SM341C 26S/940 DEIA MLO L150 SI	120 degree(s)	4000 K	108 lm/W	2,600 lm
910925867909	SM341C 35S/940 DEIA MLO L150 SI	120 degree(s)	4000 K	101 lm/W	3,500 lm
910925867877	SM340C 36S/940 DEIA O L120 SI	120 degree(s)	4000 K	126 lm/W	3,600 lm
910925867891	SM340C 35S/940 DEIA O L150 SI	120 degree(s)	4000 K	129 lm/W	3,500 lm
910925867110	SM340C 35S/940 DEIA MLO L150 BK	120 degree(s)	4000 K	101 lm/W	3,500 lm
910925868898	SM340C 45S/940 SEIA MLO U4 L150 WH	- degree(s)	4000 K	98 lm/W	4,500 lm
910925868899	SM340C 52S/940 SEIA PCS U4 L150 WH	- degree(s)	4000 K	140 lm/W	5,200 lm
910925868901	SM340C 45S/940 SEIA PCS U4 L150 WH	- degree(s)	4000 K	140 lm/W	4,500 lm
910925868902	SM340C 35S/940 SEIA PCS U4 L150 WH	- degree(s)	4000 K	146 lm/W	3,500 lm
910925868903	SM340C 42S/940 SEIA PCS U4 L120 WH	- degree(s)	4000 K	140 lm/W	4,200 lm
910925868904	SM340C 36S/940 SEIA PCS U4 L120 WH	- degree(s)	4000 K	138 lm/W	3,600 lm

FlexBlend, Surface Mounted

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910925867099	SM340C 35S/940 DEIA PCS L150 WH	120 degree(s)	4000 K	140 lm/W	3,500 lm
910925867134	SM340C 36S/940 DEIA PCS L120 WH	120 degree(s)	4000 K	138 lm/W	3,600 lm
910925867135	SM340C 42S/940 DEIA PCS L120 WH	120 degree(s)	4000 K	138 lm/W	4,200 lm
910925867865	SM340C 28S/940 DEIA PCS L120 WH	120 degree(s)	4000 K	136 lm/W	2,800 lm
910925867868	SM340C 28S/930 DEIA PCS L120 WH	120 degree(s)	3000 K	136 lm/W	2,800 lm
910925867869	SM340C 36S/930 DEIA PCS L120 WH	120 degree(s)	3000 K	138 lm/W	3,600 lm
910925867878	SM340C 45S/940 DEIA PCS L150 WH	120 degree(s)	4000 K	140 lm/W	4,500 lm
910925867879	SM340C 52S/940 DEIA PCS L150 WH	120 degree(s)	4000 K	137 lm/W	5,200 lm
910925867882	SM340C 35S/930 DEIA PCS L150 WH	120 degree(s)	3000 K	140 lm/W	3,500 lm
910925867883	SM340C 45S/930 DEIA PCS L150 WH	120 degree(s)	3000 K	140 lm/W	4,500 lm
910925867902	SM341C 26S/940 DEIA PCS L150 WH	120 degree(s)	4000 K	133 lm/W	2,600 lm
910925867903	SM341C 35S/940 DEIA PCS L150 WH	120 degree(s)	4000 K	140 lm/W	3,500 lm
910925867102	SM340C 35S/940 DEIA PCS L150 BK	120 degree(s)	4000 K	140 lm/W	3,500 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Suitable for random switching	Order Code	Full Product Name	Power Consumption	Suitable for random switching
910925867108	SM340C 35S/940 DEIA MLO L150 WH	34.5 W	Yes (relates to presence/movement detection and daylight harvesting)	910925867871	SM340C 36S/930 DEIA MLO L120 WH	38 W	Yes (relates to presence/movement detection and daylight harvesting)
910925867136	SM340C 36S/940 DEIA MLO L120 WH	38 W	Yes (relates to presence/movement detection and daylight harvesting)	910925867880	SM340C 45S/940 DEIA MLO L150 WH	46 W	Yes (relates to presence/movement detection and daylight harvesting)
910925867137	SM340C 40S/940 DEIA MLO L120 WH	42.5 W	Yes (relates to presence/movement detection and daylight harvesting)	910925867881	SM340C 50S/940 DEIA MLO L150 WH	52 W	Yes (relates to presence/movement detection and daylight harvesting)
910925867262	SM341C 35S/940 DEIA MLO L150 WH	34.5 W	Yes (relates to presence/movement detection and daylight harvesting)	910925867884	SM340C 35S/930 DEIA MLO L150 WH	34.5 W	Yes (relates to presence/movement detection and daylight harvesting)
910925867866	SM340C 28S/940 DEIA MLO L120 WH	28.5 W	Yes (relates to presence/movement detection and daylight harvesting)	910925867885	SM340C 45S/930 DEIA MLO L150 WH	46 W	Yes (relates to presence/movement detection and daylight harvesting)
910925867870	SM340C 28S/930 DEIA MLO L120 WH	28.5 W	Yes (relates to presence/movement detection and daylight harvesting)	910925867904	SM341C 26S/940 DEIA MLO L150 WH	26 W	Yes (relates to presence/movement detection and daylight harvesting)

FlexBlend, Surface Mounted

Order Code	Full Product Name	Power Consumption	Suitable for random switching
910925867116	SM340C 35S/940 DEIA O L150 WH	27 W	Yes (relates to presence/movement detection and daylight harvesting)
910925867867	SM340C 36S/940 DEIA O L120 WH	28.5 W	Yes (relates to presence/movement detection and daylight harvesting)
910925867872	SM340C 36S/930 DEIA O L120 WH	28.5 W	Yes (relates to presence/movement detection and daylight harvesting)
910925867886	SM340C 35S/930 DEIA O L150 WH	27 W	Yes (relates to presence/movement detection and daylight harvesting)
910925867905	SM341C 26S/940 DEIA O L150 WH	20.5 W	Yes (relates to presence/movement detection and daylight harvesting)
910925867101	SM340C 35S/940 DEIA PCS L150 SI	25 W	Yes (relates to presence/movement detection and daylight harvesting)
910925867873	SM340C 28S/940 DEIA PCS L120 SI	20.5 W	Yes (relates to presence/movement detection and daylight harvesting)
910925867874	SM340C 36S/940 DEIA PCS L120 SI	26 W	Yes (relates to presence/movement detection and daylight harvesting)
910925867887	SM340C 45S/940 DEIA PCS L150 SI	32 W	Yes (relates to presence/movement detection and daylight harvesting)
910925867888	SM340C 52S/940 DEIA PCS L150 SI	38 W	Yes (relates to presence/movement detection and daylight harvesting)
910925867906	SM341C 26S/940 DEIA PCS L150 SI	18.5 W	Yes (relates to presence/movement detection and daylight harvesting)
910925867907	SM341C 35S/940 DEIA PCS L150 SI	25 W	Yes (relates to presence/movement detection and daylight harvesting)
910925867892	SM340C 35S/940 DEIA O L150 BK	27 W	Yes (relates to presence/movement detection and daylight harvesting)
910925868098	SM340C 36S/940 DIA MLO ELP3 L120 WH	38 W	Yes (relates to presence/movement detection and daylight harvesting)
910925867109	SM340C 35S/940 DEIA MLO L150 SI	34.5 W	Yes (relates to presence/movement detection and daylight harvesting)
910925867875	SM340C 28S/940 DEIA MLO L120 SI	28.5 W	Yes (relates to presence/movement detection and daylight harvesting)
910925867876	SM340C 36S/940 DEIA MLO L120 SI	38 W	Yes (relates to presence/movement detection and daylight harvesting)

Order Code	Full Product Name	Power Consumption	Suitable for random switching
910925867889	SM340C 45S/940 DEIA MLO L150 SI	46 W	Yes (relates to presence/movement detection and daylight harvesting)
910925867890	SM340C 50S/940 DEIA MLO L150 SI	52 W	Yes (relates to presence/movement detection and daylight harvesting)
910925867908	SM341C 26S/940 DEIA MLO L150 SI	26 W	Yes (relates to presence/movement detection and daylight harvesting)
910925867909	SM341C 35S/940 DEIA MLO L150 SI	34.5 W	Yes (relates to presence/movement detection and daylight harvesting)
910925867877	SM340C 36S/940 DEIA O L120 SI	28.5 W	Yes (relates to presence/movement detection and daylight harvesting)
910925867891	SM340C 35S/940 DEIA O L150 SI	27 W	Yes (relates to presence/movement detection and daylight harvesting)
910925867110	SM340C 35S/940 DEIA MLO L150 BK	34.5 W	Yes (relates to presence/movement detection and daylight harvesting)
910925868898	SM340C 45S/940 SEIA MLO U4 L150 WH	46 W	No
910925868899	SM340C 52S/940 SEIA PCS U4 L150 WH	37 W	No
910925868901	SM340C 45S/940 SEIA PCS U4 L150 WH	32 W	No
910925868902	SM340C 35S/940 SEIA PCS U4 L150 WH	24 W	No
910925868903	SM340C 42S/940 SEIA PCS U4 L120 WH	30 W	No
910925868904	SM340C 36S/940 SEIA PCS U4 L120 WH	26 W	No
910925867099	SM340C 35S/940 DEIA PCS L150 WH	25 W	Yes (relates to presence/movement detection and daylight harvesting)
910925867134	SM340C 36S/940 DEIA PCS L120 WH	26 W	Yes (relates to presence/movement detection and daylight harvesting)
910925867135	SM340C 42S/940 DEIA PCS L120 WH	30.5 W	Yes (relates to presence/movement detection and daylight harvesting)
910925867865	SM340C 28S/940 DEIA PCS L120 WH	20.5 W	Yes (relates to presence/movement detection and daylight harvesting)
910925867868	SM340C 28S/930 DEIA PCS L120 WH	20.5 W	Yes (relates to presence/movement detection and daylight harvesting)
910925867869	SM340C 36S/930 DEIA PCS L120 WH	26 W	Yes (relates to presence/movement detection and daylight harvesting)

FlexBlend, Surface Mounted

Order Code	Full Product Name	Power Consumption	Suitable for random switching
910925867878	SM340C 45S/940 DEIA PCS L150 WH	32 W	Yes (relates to presence/movement detection and daylight harvesting)
910925867879	SM340C 52S/940 DEIA PCS L150 WH	38 W	Yes (relates to presence/movement detection and daylight harvesting)
910925867882	SM340C 35S/930 DEIA PCS L150 WH	25 W	Yes (relates to presence/movement detection and daylight harvesting)
910925867883	SM340C 45S/930 DEIA PCS L150 WH	32 W	Yes (relates to presence/movement detection and daylight harvesting)

Order Code	Full Product Name	Power Consumption	Suitable for random switching
910925867902	SM341C 26S/940 DEIA PCS L150 WH	18.5 W	Yes (relates to presence/movement detection and daylight harvesting)
910925867903	SM341C 35S/940 DEIA PCS L150 WH	25 W	Yes (relates to presence/movement detection and daylight harvesting)
910925867102	SM340C 35S/940 DEIA PCS L150 BK	25 W	Yes (relates to presence/movement detection and daylight harvesting)

Controls and Dimming

Order Code	Full Product Name	Dimmable
910925867108	SM340C 35S/940 DEIA MLO L150 WH	Yes
910925867136	SM340C 36S/940 DEIA MLO L120 WH	Yes
910925867137	SM340C 40S/940 DEIA MLO L120 WH	Yes
910925867262	SM341C 35S/940 DEIA MLO L150 WH	Yes
910925867866	SM340C 28S/940 DEIA MLO L120 WH	Yes
910925867870	SM340C 28S/930 DEIA MLO L120 WH	Yes
910925867871	SM340C 36S/930 DEIA MLO L120 WH	Yes
910925867880	SM340C 45S/940 DEIA MLO L150 WH	Yes
910925867881	SM340C 50S/940 DEIA MLO L150 WH	Yes
910925867884	SM340C 35S/930 DEIA MLO L150 WH	Yes
910925867885	SM340C 45S/930 DEIA MLO L150 WH	Yes
910925867904	SM341C 26S/940 DEIA MLO L150 WH	Yes
910925867116	SM340C 35S/940 DEIA O L150 WH	Yes
910925867867	SM340C 36S/940 DEIA O L120 WH	Yes
910925867872	SM340C 36S/930 DEIA O L120 WH	Yes
910925867886	SM340C 35S/930 DEIA O L150 WH	Yes
910925867905	SM341C 26S/940 DEIA O L150 WH	Yes
910925867101	SM340C 35S/940 DEIA PCS L150 SI	Yes
910925867873	SM340C 28S/940 DEIA PCS L120 SI	Yes
910925867874	SM340C 36S/940 DEIA PCS L120 SI	Yes
910925867887	SM340C 45S/940 DEIA PCS L150 SI	Yes
910925867888	SM340C 52S/940 DEIA PCS L150 SI	Yes
910925867906	SM341C 26S/940 DEIA PCS L150 SI	Yes
910925867907	SM341C 35S/940 DEIA PCS L150 SI	Yes
910925867892	SM340C 35S/940 DEIA O L150 BK	Yes
910925868098	SM340C 36S/940 DIA MLO ELP3 L120 WH	Yes
910925867109	SM340C 35S/940 DEIA MLO L150 SI	Yes
910925867875	SM340C 28S/940 DEIA MLO L120 SI	Yes

Order Code	Full Product Name	Dimmable
910925867876	SM340C 36S/940 DEIA MLO L120 SI	Yes
910925867889	SM340C 45S/940 DEIA MLO L150 SI	Yes
910925867890	SM340C 50S/940 DEIA MLO L150 SI	Yes
910925867908	SM341C 26S/940 DEIA MLO L150 SI	Yes
910925867909	SM341C 35S/940 DEIA MLO L150 SI	Yes
910925867877	SM340C 36S/940 DEIA O L120 SI	Yes
910925867891	SM340C 35S/940 DEIA O L150 SI	Yes
910925867110	SM340C 35S/940 DEIA MLO L150 BK	Yes
910925868898	SM340C 45S/940 SEIA MLO U4 L150 WH	No
910925868899	SM340C 52S/940 SEIA PCS U4 L150 WH	No
910925868901	SM340C 45S/940 SEIA PCS U4 L150 WH	No
910925868902	SM340C 35S/940 SEIA PCS U4 L150 WH	No
910925868903	SM340C 42S/940 SEIA PCS U4 L120 WH	No
910925868904	SM340C 36S/940 SEIA PCS U4 L120 WH	No
910925867099	SM340C 35S/940 DEIA PCS L150 WH	Yes
910925867134	SM340C 36S/940 DEIA PCS L120 WH	Yes
910925867135	SM340C 42S/940 DEIA PCS L120 WH	Yes
910925867865	SM340C 28S/940 DEIA PCS L120 WH	Yes
910925867868	SM340C 28S/930 DEIA PCS L120 WH	Yes
910925867869	SM340C 36S/930 DEIA PCS L120 WH	Yes
910925867878	SM340C 45S/940 DEIA PCS L150 WH	Yes
910925867879	SM340C 52S/940 DEIA PCS L150 WH	Yes
910925867882	SM340C 35S/930 DEIA PCS L150 WH	Yes
910925867883	SM340C 45S/930 DEIA PCS L150 WH	Yes
910925867902	SM341C 26S/940 DEIA PCS L150 WH	Yes
910925867903	SM341C 35S/940 DEIA PCS L150 WH	Yes
910925867102	SM340C 35S/940 DEIA PCS L150 BK	Yes

Mechanical and Housing

Order Code	Full Product Name	Housing Color
910925867108	SM340C 35S/940 DEIA MLO L150 WH	White
910925867136	SM340C 36S/940 DEIA MLO L120 WH	White

Order Code	Full Product Name	Housing Color
910925867137	SM340C 40S/940 DEIA MLO L120 WH	White
910925867262	SM341C 35S/940 DEIA MLO L150 WH	White

FlexBlend, Surface Mounted

Order Code	Full Product Name	Housing Color
910925867866	SM340C 28S/940 DEIA MLO L120 WH	White
910925867870	SM340C 28S/930 DEIA MLO L120 WH	White
910925867871	SM340C 36S/930 DEIA MLO L120 WH	White
910925867880	SM340C 45S/940 DEIA MLO L150 WH	White
910925867881	SM340C 50S/940 DEIA MLO L150 WH	White
910925867884	SM340C 35S/930 DEIA MLO L150 WH	White
910925867885	SM340C 45S/930 DEIA MLO L150 WH	White
910925867904	SM341C 26S/940 DEIA MLO L150 WH	White
910925867116	SM340C 35S/940 DEIA O L150 WH	White
910925867867	SM340C 36S/940 DEIA O L120 WH	White
910925867872	SM340C 36S/930 DEIA O L120 WH	White
910925867886	SM340C 35S/930 DEIA O L150 WH	White
910925867905	SM341C 26S/940 DEIA O L150 WH	White
910925867101	SM340C 35S/940 DEIA PCS L150 SI	Silver
910925867873	SM340C 28S/940 DEIA PCS L120 SI	Silver
910925867874	SM340C 36S/940 DEIA PCS L120 SI	Silver
910925867887	SM340C 45S/940 DEIA PCS L150 SI	Silver
910925867888	SM340C 52S/940 DEIA PCS L150 SI	Silver
910925867906	SM341C 26S/940 DEIA PCS L150 SI	Silver
910925867907	SM341C 35S/940 DEIA PCS L150 SI	Silver
910925867892	SM340C 35S/940 DEIA O L150 BK	Black
910925868098	SM340C 36S/940 DIA MLO ELP3 L120 WH	White
910925867109	SM340C 35S/940 DEIA MLO L150 SI	Silver
910925867875	SM340C 28S/940 DEIA MLO L120 SI	Silver
910925867876	SM340C 36S/940 DEIA MLO L120 SI	Silver
910925867889	SM340C 45S/940 DEIA MLO L150 SI	Silver

Order Code	Full Product Name	Housing Color
910925867890	SM340C 50S/940 DEIA MLO L150 SI	Silver
910925867908	SM341C 26S/940 DEIA MLO L150 SI	Silver
910925867909	SM341C 35S/940 DEIA MLO L150 SI	Silver
910925867877	SM340C 36S/940 DEIA O L120 SI	Silver
910925867891	SM340C 35S/940 DEIA O L150 SI	Silver
910925867110	SM340C 35S/940 DEIA MLO L150 BK	Black
910925868898	SM340C 45S/940 SEIA MLO U4 L150 WH	White
910925868899	SM340C 52S/940 SEIA PCS U4 L150 WH	White
910925868901	SM340C 45S/940 SEIA PCS U4 L150 WH	White
910925868902	SM340C 35S/940 SEIA PCS U4 L150 WH	White
910925868903	SM340C 42S/940 SEIA PCS U4 L120 WH	White
910925868904	SM340C 36S/940 SEIA PCS U4 L120 WH	White
910925867099	SM340C 35S/940 DEIA PCS L150 WH	White
910925867134	SM340C 36S/940 DEIA PCS L120 WH	White
910925867135	SM340C 42S/940 DEIA PCS L120 WH	White
910925867865	SM340C 28S/940 DEIA PCS L120 WH	White
910925867868	SM340C 28S/930 DEIA PCS L120 WH	White
910925867869	SM340C 36S/930 DEIA PCS L120 WH	White
910925867878	SM340C 45S/940 DEIA PCS L150 WH	White
910925867879	SM340C 52S/940 DEIA PCS L150 WH	White
910925867882	SM340C 35S/930 DEIA PCS L150 WH	White
910925867883	SM340C 45S/930 DEIA PCS L150 WH	White
910925867902	SM341C 26S/940 DEIA PCS L150 WH	White
910925867903	SM341C 35S/940 DEIA PCS L150 WH	White
910925867102	SM340C 35S/940 DEIA PCS L150 BK	Black

Emergency Operation

Order Code	Full Product Name	Central Emergency	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910925867108	SM340C 35S/940 DEIA MLO L150 WH	-	-	-
910925867136	SM340C 36S/940 DEIA MLO L120 WH	-	-	-
910925867137	SM340C 40S/940 DEIA MLO L120 WH	-	-	-
910925867262	SM341C 35S/940 DEIA MLO L150 WH	-	-	-
910925867866	SM340C 28S/940 DEIA MLO L120 WH	-	-	-
910925867870	SM340C 28S/930 DEIA MLO L120 WH	-	-	-
910925867871	SM340C 36S/930 DEIA MLO L120 WH	-	-	-
910925867880	SM340C 45S/940 DEIA MLO L150 WH	-	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910925867881	SM340C 50S/940 DEIA MLO L150 WH	-	-	-
910925867884	SM340C 35S/930 DEIA MLO L150 WH	-	-	-
910925867885	SM340C 45S/930 DEIA MLO L150 WH	-	-	-
910925867904	SM341C 26S/940 DEIA MLO L150 WH	-	-	-
910925867116	SM340C 35S/940 DEIA O L150 WH	-	-	-
910925867867	SM340C 36S/940 DEIA O L120 WH	-	-	-
910925867872	SM340C 36S/930 DEIA O L120 WH	-	-	-
910925867886	SM340C 35S/930 DEIA O L150 WH	-	-	-

FlexBlend, Surface Mounted

Order Code	Full Product Name	Central Emergency	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910925867905	SM341C 26S/940 DEIA O L150 WH	-	-	-
910925867101	SM340C 35S/940 DEIA PCS L150 SI	-	-	-
910925867873	SM340C 28S/940 DEIA PCS L120 SI	-	-	-
910925867874	SM340C 36S/940 DEIA PCS L120 SI	-	-	-
910925867887	SM340C 45S/940 DEIA PCS L150 SI	-	-	-
910925867888	SM340C 52S/940 DEIA PCS L150 SI	-	-	-
910925867906	SM341C 26S/940 DEIA PCS L150 SI	-	-	-
910925867907	SM341C 35S/940 DEIA PCS L150 SI	-	-	-
910925867892	SM340C 35S/940 DEIA O L150 BK	-	-	-
910925868098	SM340C 36S/940 DIA MLO ELP3 L120 WH	No	Emergency lighting 3 hours duration Pro version	3 hour(s)
910925867109	SM340C 35S/940 DEIA MLO L150 SI	-	-	-
910925867875	SM340C 28S/940 DEIA MLO L120 SI	-	-	-
910925867876	SM340C 36S/940 DEIA MLO L120 SI	-	-	-
910925867889	SM340C 45S/940 DEIA MLO L150 SI	-	-	-
910925867890	SM340C 50S/940 DEIA MLO L150 SI	-	-	-
910925867908	SM341C 26S/940 DEIA MLO L150 SI	-	-	-
910925867909	SM341C 35S/940 DEIA MLO L150 SI	-	-	-
910925867877	SM340C 36S/940 DEIA O L120 SI	-	-	-
910925867891	SM340C 35S/940 DEIA O L150 SI	-	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910925867110	SM340C 35S/940 DEIA MLO L150 BK	-	-	-
910925868898	SM340C 45S/940 SEIA MLO U4 L150 WH	-	-	-
910925868899	SM340C 52S/940 SEIA PCS U4 L150 WH	-	-	-
910925868901	SM340C 45S/940 SEIA PCS U4 L150 WH	-	-	-
910925868902	SM340C 35S/940 SEIA PCS U4 L150 WH	-	-	-
910925868903	SM340C 42S/940 SEIA PCS U4 L120 WH	-	-	-
910925868904	SM340C 36S/940 SEIA PCS U4 L120 WH	-	-	-
910925867099	SM340C 35S/940 DEIA PCS L150 WH	-	-	-
910925867134	SM340C 36S/940 DEIA PCS L120 WH	-	-	-
910925867135	SM340C 42S/940 DEIA PCS L120 WH	-	-	-
910925867865	SM340C 28S/940 DEIA PCS L120 WH	-	-	-
910925867868	SM340C 28S/930 DEIA PCS L120 WH	-	-	-
910925867869	SM340C 36S/930 DEIA PCS L120 WH	-	-	-
910925867878	SM340C 45S/940 DEIA PCS L150 WH	-	-	-
910925867879	SM340C 52S/940 DEIA PCS L150 WH	-	-	-
910925867882	SM340C 35S/930 DEIA PCS L150 WH	-	-	-
910925867883	SM340C 45S/930 DEIA PCS L150 WH	-	-	-
910925867902	SM341C 26S/940 DEIA PCS L150 WH	-	-	-
910925867903	SM341C 35S/940 DEIA PCS L150 WH	-	-	-
910925867102	SM340C 35S/940 DEIA PCS L150 BK	-	-	-

Approval and Application

FlexBlend, Surface Mounted

Order Code	Full Product Name	Ambient temperature range	ENEC	
			mark	Glow-wire test
910925867108	SM340C 35S/940 DEIA MLO L150 WH	+10 to +40 °C	ENEC plus mark	Temperature 650 °C, duration 30 s
910925867136	SM340C 36S/940 DEIA MLO L120 WH	+10 to +40 °C	ENEC plus mark	Temperature 650 °C, duration 30 s
910925867137	SM340C 40S/940 DEIA MLO L120 WH	+10 to +40 °C	ENEC plus mark	Temperature 650 °C, duration 30 s
910925867262	SM341C 35S/940 DEIA MLO L150 WH	+10 to +40 °C	ENEC plus mark	Temperature 650 °C, duration 30 s
910925867866	SM340C 28S/940 DEIA MLO L120 WH	+10 to +40 °C	ENEC plus mark	Temperature 650 °C, duration 30 s
910925867870	SM340C 28S/930 DEIA MLO L120 WH	+10 to +40 °C	ENEC plus mark	Temperature 650 °C, duration 30 s
910925867871	SM340C 36S/930 DEIA MLO L120 WH	+10 to +40 °C	ENEC plus mark	Temperature 650 °C, duration 30 s
910925867880	SM340C 45S/940 DEIA MLO L150 WH	+10 to +40 °C	ENEC plus mark	Temperature 650 °C, duration 30 s
910925867881	SM340C 50S/940 DEIA MLO L150 WH	+10 to +40 °C	ENEC plus mark	Temperature 650 °C, duration 30 s
910925867884	SM340C 35S/930 DEIA MLO L150 WH	+10 to +40 °C	ENEC plus mark	Temperature 650 °C, duration 30 s
910925867885	SM340C 45S/930 DEIA MLO L150 WH	+10 to +40 °C	ENEC plus mark	Temperature 650 °C, duration 30 s
910925867904	SM341C 26S/940 DEIA MLO L150 WH	+10 to +40 °C	ENEC plus mark	Temperature 650 °C, duration 30 s
910925867116	SM340C 35S/940 DEIA O L150 WH	+10 to +40 °C	ENEC plus mark	Temperature 850 °C, duration 30 s
910925867867	SM340C 36S/940 DEIA O L120 WH	+10 to +40 °C	ENEC plus mark	Temperature 850 °C, duration 30 s
910925867872	SM340C 36S/930 DEIA O L120 WH	+10 to +40 °C	ENEC plus mark	Temperature 850 °C, duration 30 s
910925867886	SM340C 35S/930 DEIA O L150 WH	+10 to +40 °C	ENEC plus mark	Temperature 850 °C, duration 30 s
910925867905	SM341C 26S/940 DEIA O L150 WH	+10 to +40 °C	ENEC plus mark	Temperature 850 °C, duration 30 s
910925867101	SM340C 35S/940 DEIA PCS L150 SI	+10 to +40 °C	ENEC plus mark	Temperature 850 °C, duration 30 s
910925867873	SM340C 28S/940 DEIA PCS L120 SI	+10 to +40 °C	ENEC plus mark	Temperature 850 °C, duration 30 s

Order Code	Full Product Name	Ambient temperature range	ENEC	
			mark	Glow-wire test
910925867874	SM340C 36S/940 DEIA PCS L120 SI	+10 to +40 °C	ENEC plus mark	Temperature 850 °C, duration 30 s
910925867887	SM340C 45S/940 DEIA PCS L150 SI	+10 to +40 °C	ENEC plus mark	Temperature 850 °C, duration 30 s
910925867888	SM340C 52S/940 DEIA PCS L150 SI	+10 to +40 °C	ENEC plus mark	Temperature 850 °C, duration 30 s
910925867906	SM341C 26S/940 DEIA PCS L150 SI	+10 to +40 °C	ENEC plus mark	Temperature 850 °C, duration 30 s
910925867907	SM341C 35S/940 DEIA PCS L150 SI	+10 to +40 °C	ENEC plus mark	Temperature 850 °C, duration 30 s
910925867892	SM340C 35S/940 DEIA O L150 BK	+10 to +40 °C	ENEC plus mark	Temperature 850 °C, duration 30 s
910925868098	SM340C 36S/940 DIA MLO ELP3 L120 WH	+10 to +25 °C	ENEC plus mark	Temperature 650 °C, duration 30 s
910925867109	SM340C 35S/940 DEIA MLO L150 SI	+10 to +40 °C	ENEC plus mark	Temperature 650 °C, duration 30 s
910925867875	SM340C 28S/940 DEIA MLO L120 SI	+10 to +40 °C	ENEC plus mark	Temperature 650 °C, duration 30 s
910925867876	SM340C 36S/940 DEIA MLO L120 SI	+10 to +40 °C	ENEC plus mark	Temperature 650 °C, duration 30 s
910925867889	SM340C 45S/940 DEIA MLO L150 SI	+10 to +40 °C	ENEC plus mark	Temperature 650 °C, duration 30 s
910925867890	SM340C 50S/940 DEIA MLO L150 SI	+10 to +40 °C	ENEC plus mark	Temperature 650 °C, duration 30 s
910925867908	SM341C 26S/940 DEIA MLO L150 SI	+10 to +40 °C	ENEC plus mark	Temperature 650 °C, duration 30 s
910925867909	SM341C 35S/940 DEIA MLO L150 SI	+10 to +40 °C	ENEC plus mark	Temperature 650 °C, duration 30 s
910925867877	SM340C 36S/940 DEIA O L120 SI	+10 to +40 °C	ENEC plus mark	Temperature 850 °C, duration 30 s
910925867891	SM340C 35S/940 DEIA O L150 SI	+10 to +40 °C	ENEC plus mark	Temperature 850 °C, duration 30 s
910925867110	SM340C 35S/940 DEIA MLO L150 BK	+10 to +40 °C	ENEC plus mark	Temperature 650 °C, duration 30 s
910925868898	SM340C 45S/940 SEIA MLO U4 L150 WH	+10 to +40 °C	ENEC mark	Temperature 650 °C, duration 30 s
910925868899	SM340C 52S/940 SEIA PCS U4 L150 WH	+10 to +40 °C	ENEC mark	Temperature 850 °C, duration 30 s
910925868901	SM340C 45S/940 SEIA PCS U4 L150 WH	+10 to +40 °C	ENEC mark	Temperature 850 °C, duration 30 s
910925868902	SM340C 35S/940 SEIA PCS U4 L150 WH	+10 to +40 °C	ENEC mark	Temperature 850 °C, duration 30 s

FlexBlend, Surface Mounted

Order Code	Full Product Name	Ambient temperature range	ENEC mark	Glow-wire test
910925868903	SM340C 42S/940 SEIA PCS U4 L120 WH	+10 to +40 °C	ENEC mark	Temperature 850 °C, duration 30 s
910925868904	SM340C 36S/940 SEIA PCS U4 L120 WH	+10 to +40 °C	ENEC mark	Temperature 850 °C, duration 30 s
910925867099	SM340C 35S/940 DEIA PCS L150 WH	+10 to +40 °C	ENEC plus mark	Temperature 850 °C, duration 30 s
910925867134	SM340C 36S/940 DEIA PCS L120 WH	+10 to +40 °C	ENEC plus mark	Temperature 850 °C, duration 30 s
910925867135	SM340C 42S/940 DEIA PCS L120 WH	+10 to +40 °C	ENEC plus mark	Temperature 850 °C, duration 30 s
910925867865	SM340C 28S/940 DEIA PCS L120 WH	+10 to +40 °C	ENEC plus mark	Temperature 850 °C, duration 30 s
910925867868	SM340C 28S/930 DEIA PCS L120 WH	+10 to +40 °C	ENEC plus mark	Temperature 850 °C, duration 30 s
910925867869	SM340C 36S/930 DEIA PCS L120 WH	+10 to +40 °C	ENEC plus mark	Temperature 850 °C, duration 30 s

Order Code	Full Product Name	Ambient temperature range	ENEC mark	Glow-wire test
910925867878	SM340C 45S/940 DEIA PCS L150 WH	+10 to +40 °C	ENEC plus mark	Temperature 850 °C, duration 30 s
910925867879	SM340C 52S/940 DEIA PCS L150 WH	+10 to +40 °C	ENEC plus mark	Temperature 850 °C, duration 30 s
910925867882	SM340C 35S/930 DEIA PCS L150 WH	+10 to +40 °C	ENEC plus mark	Temperature 850 °C, duration 30 s
910925867883	SM340C 45S/930 DEIA PCS L150 WH	+10 to +40 °C	ENEC plus mark	Temperature 850 °C, duration 30 s
910925867902	SM341C 26S/940 DEIA PCS L150 WH	+10 to +40 °C	ENEC plus mark	Temperature 850 °C, duration 30 s
910925867903	SM341C 35S/940 DEIA PCS L150 WH	+10 to +40 °C	ENEC plus mark	Temperature 850 °C, duration 30 s
910925867102	SM340C 35S/940 DEIA PCS L150 BK	+10 to +40 °C	ENEC plus mark	Temperature 850 °C, duration 30 s

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910925867108	SM340C 35S/940 DEIA MLO L150 WH	(0.38, 0.38) SDCM <3
910925867136	SM340C 36S/940 DEIA MLO L120 WH	(0.38, 0.38) SDCM <3
910925867137	SM340C 40S/940 DEIA MLO L120 WH	(0.38, 0.38) SDCM <3
910925867262	SM341C 35S/940 DEIA MLO L150 WH	(0.38, 0.38) SDCM <3
910925867866	SM340C 28S/940 DEIA MLO L120 WH	(0.38, 0.38) SDCM <3
910925867870	SM340C 28S/930 DEIA MLO L120 WH	(0.43, 0.40) SDCM <3
910925867871	SM340C 36S/930 DEIA MLO L120 WH	(0.43, 0.40) SDCM <3
910925867880	SM340C 45S/940 DEIA MLO L150 WH	(0.38, 0.38) SDCM <3
910925867881	SM340C 50S/940 DEIA MLO L150 WH	(0.38, 0.38) SDCM <3
910925867884	SM340C 35S/930 DEIA MLO L150 WH	(0.43, 0.40) SDCM <3
910925867885	SM340C 45S/930 DEIA MLO L150 WH	(0.43, 0.40) SDCM <3
910925867904	SM341C 26S/940 DEIA MLO L150 WH	(0.38, 0.38) SDCM <3
910925867116	SM340C 35S/940 DEIA O L150 WH	(0.38, 0.38) SDCM <3
910925867867	SM340C 36S/940 DEIA O L120 WH	(0.38, 0.38) SDCM <3
910925867872	SM340C 36S/930 DEIA O L120 WH	(0.43, 0.40) SDCM <3
910925867886	SM340C 35S/930 DEIA O L150 WH	(0.43, 0.40) SDCM <3
910925867905	SM341C 26S/940 DEIA O L150 WH	(0.38, 0.38) SDCM <3
910925867101	SM340C 35S/940 DEIA PCS L150 SI	(0.38, 0.38) SDCM <3
910925867873	SM340C 28S/940 DEIA PCS L120 SI	(0.38, 0.38) SDCM <3
910925867874	SM340C 36S/940 DEIA PCS L120 SI	(0.38, 0.38) SDCM <3
910925867887	SM340C 45S/940 DEIA PCS L150 SI	(0.38, 0.38) SDCM <3
910925867888	SM340C 52S/940 DEIA PCS L150 SI	(0.38, 0.38) SDCM <3

Order Code	Full Product Name	Initial chromaticity
910925867906	SM341C 26S/940 DEIA PCS L150 SI	(0.38, 0.38) SDCM <3
910925867907	SM341C 35S/940 DEIA PCS L150 SI	(0.38, 0.38) SDCM <3
910925867892	SM340C 35S/940 DEIA O L150 BK	(0.38, 0.38) SDCM <3
910925868098	SM340C 36S/940 DEIA MLO ELP3 L120 WH	(0.38, 0.37) SDCM <3
910925867109	SM340C 35S/940 DEIA MLO L150 SI	(0.38, 0.38) SDCM <3
910925867875	SM340C 28S/940 DEIA MLO L120 SI	(0.38, 0.38) SDCM <3
910925867876	SM340C 36S/940 DEIA MLO L120 SI	(0.38, 0.38) SDCM <3
910925867889	SM340C 45S/940 DEIA MLO L150 SI	(0.38, 0.38) SDCM <3
910925867890	SM340C 50S/940 DEIA MLO L150 SI	(0.38, 0.38) SDCM <3
910925867908	SM341C 26S/940 DEIA MLO L150 SI	(0.38, 0.38) SDCM <3
910925867909	SM341C 35S/940 DEIA MLO L150 SI	(0.38, 0.38) SDCM <3
910925867877	SM340C 36S/940 DEIA O L120 SI	(0.38, 0.38) SDCM <3
910925867891	SM340C 35S/940 DEIA O L150 SI	(0.38, 0.38) SDCM <3
910925867110	SM340C 35S/940 DEIA MLO L150 BK	(0.38, 0.38) SDCM <3
910925868898	SM340C 45S/940 SEIA MLO U4 L150 WH	0.38, 0.37
910925868899	SM340C 52S/940 SEIA PCS U4 L150 WH	0.38, 0.37
910925868901	SM340C 45S/940 SEIA PCS U4 L150 WH	0.38, 0.37
910925868902	SM340C 35S/940 SEIA PCS U4 L150 WH	0.38, 0.37
910925868903	SM340C 42S/940 SEIA PCS U4 L120 WH	0.38, 0.37
910925868904	SM340C 36S/940 SEIA PCS U4 L120 WH	0.38, 0.37
910925867099	SM340C 35S/940 DEIA PCS L150 WH	(0.38, 0.38) SDCM <3
910925867134	SM340C 36S/940 DEIA PCS L120 WH	(0.38, 0.38) SDCM <3

FlexBlend, Surface Mounted

Order Code	Full Product Name	Initial chromaticity
910925867135	SM340C 42S/940 DEIA PCS L120 WH	(0.38, 0.38) SDCM <3
910925867865	SM340C 28S/940 DEIA PCS L120 WH	(0.38, 0.38) SDCM <3
910925867868	SM340C 28S/930 DEIA PCS L120 WH	(0.43, 0.40) SDCM <3
910925867869	SM340C 36S/930 DEIA PCS L120 WH	(0.43, 0.40) SDCM <3
910925867878	SM340C 45S/940 DEIA PCS L150 WH	(0.38, 0.38) SDCM <3
910925867879	SM340C 52S/940 DEIA PCS L150 WH	(0.38, 0.38) SDCM <3

Order Code	Full Product Name	Initial chromaticity
910925867882	SM340C 35S/930 DEIA PCS L150 WH	(0.43, 0.40) SDCM <3
910925867883	SM340C 45S/930 DEIA PCS L150 WH	(0.43, 0.40) SDCM <3
910925867902	SM341C 26S/940 DEIA PCS L150 WH	(0.38, 0.38) SDCM <3
910925867903	SM341C 35S/940 DEIA PCS L150 WH	(0.38, 0.38) SDCM <3
910925867102	SM340C 35S/940 DEIA PCS L150 BK	(0.38, 0.38) SDCM <3

Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Driver failure rate at 5000 h
910925867108	SM340C 35S/940 DEIA MLO L150 WH	-
910925867136	SM340C 36S/940 DEIA MLO L120 WH	-
910925867137	SM340C 40S/940 DEIA MLO L120 WH	-
910925867262	SM341C 35S/940 DEIA MLO L150 WH	-
910925867866	SM340C 28S/940 DEIA MLO L120 WH	-
910925867870	SM340C 28S/930 DEIA MLO L120 WH	-
910925867871	SM340C 36S/930 DEIA MLO L120 WH	-
910925867880	SM340C 45S/940 DEIA MLO L150 WH	-
910925867881	SM340C 50S/940 DEIA MLO L150 WH	-
910925867884	SM340C 35S/930 DEIA MLO L150 WH	-
910925867885	SM340C 45S/930 DEIA MLO L150 WH	-
910925867904	SM341C 26S/940 DEIA MLO L150 WH	-
910925867116	SM340C 35S/940 DEIA O L150 WH	-
910925867867	SM340C 36S/940 DEIA O L120 WH	-
910925867872	SM340C 36S/930 DEIA O L120 WH	-
910925867886	SM340C 35S/930 DEIA O L150 WH	-
910925867905	SM341C 26S/940 DEIA O L150 WH	-
910925867101	SM340C 35S/940 DEIA PCS L150 SI	-
910925867873	SM340C 28S/940 DEIA PCS L120 SI	-
910925867874	SM340C 36S/940 DEIA PCS L120 SI	-
910925867887	SM340C 45S/940 DEIA PCS L150 SI	-
910925867888	SM340C 52S/940 DEIA PCS L150 SI	-
910925867906	SM341C 26S/940 DEIA PCS L150 SI	-
910925867907	SM341C 35S/940 DEIA PCS L150 SI	-
910925867892	SM340C 35S/940 DEIA O L150 BK	-
910925868098	SM340C 36S/940 DIA MLO ELP3 L120 WH	0.05 %
910925867109	SM340C 35S/940 DEIA MLO L150 SI	-
910925867875	SM340C 28S/940 DEIA MLO L120 SI	-

Order Code	Full Product Name	Driver failure rate at 5000 h
910925867876	SM340C 36S/940 DEIA MLO L120 SI	-
910925867889	SM340C 45S/940 DEIA MLO L150 SI	-
910925867890	SM340C 50S/940 DEIA MLO L150 SI	-
910925867908	SM341C 26S/940 DEIA MLO L150 SI	-
910925867909	SM341C 35S/940 DEIA MLO L150 SI	-
910925867877	SM340C 36S/940 DEIA O L120 SI	-
910925867891	SM340C 35S/940 DEIA O L150 SI	-
910925867110	SM340C 35S/940 DEIA MLO L150 BK	-
910925868898	SM340C 45S/940 SEIA MLO U4 L150 WH	-
910925868899	SM340C 52S/940 SEIA PCS U4 L150 WH	-
910925868901	SM340C 45S/940 SEIA PCS U4 L150 WH	-
910925868902	SM340C 35S/940 SEIA PCS U4 L150 WH	-
910925868903	SM340C 42S/940 SEIA PCS U4 L120 WH	-
910925868904	SM340C 36S/940 SEIA PCS U4 L120 WH	-
910925867099	SM340C 35S/940 DEIA PCS L150 WH	-
910925867134	SM340C 36S/940 DEIA PCS L120 WH	-
910925867135	SM340C 42S/940 DEIA PCS L120 WH	-
910925867865	SM340C 28S/940 DEIA PCS L120 WH	-
910925867868	SM340C 28S/930 DEIA PCS L120 WH	-
910925867869	SM340C 36S/930 DEIA PCS L120 WH	-
910925867878	SM340C 45S/940 DEIA PCS L150 WH	-
910925867879	SM340C 52S/940 DEIA PCS L150 WH	-
910925867882	SM340C 35S/930 DEIA PCS L150 WH	-
910925867883	SM340C 45S/930 DEIA PCS L150 WH	-
910925867902	SM341C 26S/940 DEIA PCS L150 WH	-
910925867903	SM341C 35S/940 DEIA PCS L150 WH	-
910925867102	SM340C 35S/940 DEIA PCS L150 BK	-

Product Data

Order Code	Full Product Name	Product family code
910925867108	SM340C 35S/940 DEIA MLO L150 WH	SM340C
910925867136	SM340C 36S/940 DEIA MLO L120 WH	SM340C
910925867137	SM340C 40S/940 DEIA MLO L120 WH	SM340C
910925867262	SM341C 35S/940 DEIA MLO L150 WH	SM341C
910925867866	SM340C 28S/940 DEIA MLO L120 WH	SM340C
910925867870	SM340C 28S/930 DEIA MLO L120 WH	SM340C
910925867871	SM340C 36S/930 DEIA MLO L120 WH	SM340C
910925867880	SM340C 45S/940 DEIA MLO L150 WH	SM340C


Order Code	Full Product Name	Product family code
910925867881	SM340C 50S/940 DEIA MLO L150 WH	SM340C
910925867884	SM340C 35S/930 DEIA MLO L150 WH	SM340C
910925867885	SM340C 45S/930 DEIA MLO L150 WH	SM340C
910925867904	SM341C 26S/940 DEIA MLO L150 WH	SM341C
910925867116	SM340C 35S/940 DEIA O L150 WH	SM340C
910925867867	SM340C 36S/940 DEIA O L120 WH	SM340C
910925867872	SM340C 36S/930 DEIA O L120 WH	SM340C
910925867886	SM340C 35S/930 DEIA O L150 WH	SM340C

FlexBlend, Surface Mounted


Order Code	Full Product Name	Product family code
910925867905	SM341C 26S/940 DEIA O L150 WH	SM341C
910925867101	SM340C 35S/940 DEIA PCS L150 SI	SM340C
910925867873	SM340C 28S/940 DEIA PCS L120 SI	SM340C
910925867874	SM340C 36S/940 DEIA PCS L120 SI	SM340C
910925867887	SM340C 45S/940 DEIA PCS L150 SI	SM340C
910925867888	SM340C 52S/940 DEIA PCS L150 SI	SM340C
910925867906	SM341C 26S/940 DEIA PCS L150 SI	SM341C
910925867907	SM341C 35S/940 DEIA PCS L150 SI	SM341C
910925867892	SM340C 35S/940 DEIA O L150 BK	SM340C
910925868098	SM340C 36S/940 DIA MLO ELP3 L120 WH	SM340C
910925867109	SM340C 35S/940 DEIA MLO L150 SI	SM340C
910925867875	SM340C 28S/940 DEIA MLO L120 SI	SM340C
910925867876	SM340C 36S/940 DEIA MLO L120 SI	SM340C
910925867889	SM340C 45S/940 DEIA MLO L150 SI	SM340C
910925867890	SM340C 50S/940 DEIA MLO L150 SI	SM340C
910925867908	SM341C 26S/940 DEIA MLO L150 SI	SM341C
910925867909	SM341C 35S/940 DEIA MLO L150 SI	SM341C
910925867877	SM340C 36S/940 DEIA O L120 SI	SM340C
910925867891	SM340C 35S/940 DEIA O L150 SI	SM340C
910925867110	SM340C 35S/940 DEIA MLO L150 BK	SM340C

Order Code	Full Product Name	Product family code
910925868898	SM340C 45S/940 SEIA MLO U4 L150 WH	SM340C
910925868899	SM340C 52S/940 SEIA PCS U4 L150 WH	SM340C
910925868901	SM340C 45S/940 SEIA PCS U4 L150 WH	SM340C
910925868902	SM340C 35S/940 SEIA PCS U4 L150 WH	SM340C
910925868903	SM340C 42S/940 SEIA PCS U4 L120 WH	SM340C
910925868904	SM340C 36S/940 SEIA PCS U4 L120 WH	SM340C
910925867099	SM340C 35S/940 DEIA PCS L150 WH	SM340C
910925867134	SM340C 36S/940 DEIA PCS L120 WH	SM340C
910925867135	SM340C 42S/940 DEIA PCS L120 WH	SM340C
910925867865	SM340C 28S/940 DEIA PCS L120 WH	SM340C
910925867868	SM340C 28S/930 DEIA PCS L120 WH	SM340C
910925867869	SM340C 36S/930 DEIA PCS L120 WH	SM340C
910925867878	SM340C 45S/940 DEIA PCS L150 WH	SM340C
910925867879	SM340C 52S/940 DEIA PCS L150 WH	SM340C
910925867882	SM340C 35S/930 DEIA PCS L150 WH	SM340C
910925867883	SM340C 45S/930 DEIA PCS L150 WH	SM340C
910925867902	SM341C 26S/940 DEIA PCS L150 WH	SM341C
910925867903	SM341C 35S/940 DEIA PCS L150 WH	SM341C
910925867102	SM340C 35S/940 DEIA PCS L150 BK	SM340C


Polar Wide Diagrams




Polar Normal (separate) - SM340CI - 910925868902




Polar Normal (separate) - SM340CI - 910925868898




Polar Normal (separate) - SM340CI - 910925868899



Polar Normal (separate) - SM340CI - 910925868901




Polar Normal (separate) - SM340CI - 910925868903




Polar Normal (separate) - SM340CI - 910925868904


Polar Wide Diagrams




Polar Normal (separate) - SM340CI - 910925867137




Polar Normal (separate) - SM340CI - 910925867099




Polar Normal (separate) - SM340CI - 910925867101




Polar Normal (separate) - SM340CI - 910925867108




Polar Normal (separate) - SM340CI - 910925867110




Polar Normal (separate) - SM340CI - 910925867135



Polar Normal (separate) - SM340CI - 910925867102




Polar Normal (separate) - SM340CI - 910925867116




Polar Normal (separate) - SM340CI - 910925867134


Polar Wide Diagrams




Polar Normal (separate) - SM340CI - 910925867109




Polar Normal (separate) - SM340CI - 910925867869




Polar Normal (separate) - SM340CI - 910925867865




Polar Normal (separate) - SM340CI - 910925867878




Polar Normal (separate) - SM340CI - 910925867136




Polar Normal (separate) - SM340CI - 910925867876



Polar Normal (separate) - SM340CI - 910925867881




Polar Normal (separate) - SM340CI - 910925867879




Polar Normal (separate) - SM340CI - 910925867262


Polar Wide Diagrams




Polar Normal (separate) - SM340CI - 910925867866




Polar Normal (separate) - SM340CI - 910925867867




Polar Normal (separate) - SM340CI - 910925867868




Polar Normal (separate) - SM340CI - 910925867870




Polar Normal (separate) - SM340CI - 910925867871




Polar Normal (separate) - SM340CI - 910925867873



Polar Normal (separate) - SM340CI - 910925867872




Polar Normal (separate) - SM340CI - 910925867874




Polar Normal (separate) - SM340CI - 910925867877


Polar Wide Diagrams




Polar Normal (separate) - SM340CI - 910925867880




Polar Normal (separate) - SM340CI - 910925867883




Polar Normal (separate) - SM340CI - 910925867884




Polar Normal (separate) - SM340CI - 910925867885




Polar Normal (separate) - SM340CI - 910925867886




Polar Normal (separate) - SM340CI - 910925867887



Polar Normal (separate) - SM340CI - 910925867889




Polar Normal (separate) - SM340CI - 910925867888




Polar Normal (separate) - SM340CI - 910925867891


Polar Wide Diagrams




Polar Normal (separate) - SM340CI - 91092586785




Polar Normal (separate) - SM340CI - 91092586788




Polar Normal (separate) - SM340CI - 91092586789




Polar Normal (separate) - SM340CI - 91092586790




Polar Normal (separate) - SM340CI - 91092586793




Polar Normal (separate) - SM340CI - 91092586795



Polar Normal (separate) - SM340CI - 91092586794




Polar Normal (separate) - SM340CI - 91092586796




Polar Normal (separate) - SM340CI - 91092586797

FlexBlend, Surface Mounted


Polar Wide Diagrams




**Polar Normal (separate) - SM340CI -
910925867909**



**Polar Normal (separate) - SM340CI -
910925867908**



**Polar Normal (separate) - SM340CI -
910925867890**



**Polar Normal (separate) - SM340CI -
910925868098**

