



The flexible light line

These days, many office owners and office lighting designers prefer lines of light. The reason is simple. Not only do light lines come in a minimalistic design; they also offer far more choice and flexibility. Short or long lines and luminaires, standalone luminaires, different optics including asymmetric, different shapes and even a variety of colors; anything is possible. And with KeyLine, all these benefits come at a competitive price while still complying with office lighting norms. KeyLine is a superb light line range with a slim, minimalistic design and a high lumen output to illuminate the brightest office spaces. But with comfortable, low levels of glare it's also easy on the eye and complies with UGR19. That makes KeyLine ideal for linear applications, as well as standalone suspended or surface-mounted luminaires (Accessories to be ordered separately). A range that offers the ultimate flexibility and unlimited possibilities. KeyLine design flexibility comes in the form of different lengths, colors and light outputs - including L-shapes, as well as straight lines. All with high efficiency up to 142 lm/W, and the option to upgrade with wireless connectivity and control.

Add to that attractive pricing, and with KeyLine you can also enjoy excellent value that ensures a superb total cost of ownership.

Benefits

- Suitable for office applications
- Excellent total cost of ownership
- Wide range of options to suit the demands of different offices

Applications

- Offices
- Retail
- Education

Features

- Comfortable, low glare: <UGR19 for the full range
- High lumen output, up to 4000lm for 1.2m version

Versions



KeyLine L-corner, black



KeyLine suspended L1500, bk



KeyLine suspended L1200, alu



KeyLine L-corner, alu



KeyLine suspended L1500, alu






KeyLine suspended L1500, white

- Interact Connectivity ready with wireless drivers
- Standard options in different lengths, colors and light outputs
- Customization options
- KeyLine luminaires have an IP20 classification and are not protected against water ingress. We strongly recommend that the installation environment is checked for suitability.
- If – despite the IPX0 classification warning – luminaires are subject to water ingress, Philips and Signify cannot guarantee safety or prevent failure. In this case the product warranty does not apply and becomes void.




Dimensional drawing





SM351C 40S/840 PSD A PCS L1200 WH



SM351C 50S/840 PSU A PCS L1500 WH

Product details



KeyLine line coupling, alu



KeyLine black with ceiling bracket accessory for surface mounting



KeyLine black with coupling piece accessory for line mounting



KeyLine Asymmetric SM531C detailed



KeyLine_SM350C_WIA_DPP1



KeyLine line configuration, white



KeyLine SM350C, white



KeyLine configuration with L-corner SM350X




KeyLine black with end-cap accessory



KeyLine line coupling, white



KeyLine alu with suspension set for suspended mounting



KeyLine white line coupling with coupling piece accessory



KeyLine_SM350C_WIA_DPP3



KeyLine alu with end-cap accessory



KeyLine white with coupling piece accessory for line mounting




KeyLine structured optics UGR19 (PCS)



KeyLine line coupling, black



KeyLine SM350C, alu



KeyLine alu line coupling with coupling piece accessory



KeyLine line configuration, black



KeyLine alu with ceiling bracket accessory for surface mounting



KeyLine white with suspension set for suspended mounting



KeyLine white with ceiling bracket accessory for surface mounting



KeyLine white with end-cap accessory




KeyLine alu with coupling piece accessory for line mounting



KeyLine SM350C, black



KeyLine L-corner, black



KeyLine black line coupling with coupling piece accessory




KeyLine black with suspension set for suspended mounting



KeyLine_SM350C_WIA_DPP2



KeyLine L-corner, alu



KeyLine L-corner, white

General Information

Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Service tag	Yes

Light Technical

Color rendering index (CRI)	>80
Beam angle of light source	120 degree(s)

Operating and Electrical

Line Frequency	50 to 60 Hz
Protection class IEC	Safety class I

Mechanical and Housing

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK06 [1 J]

Emergency Operation

Central Emergency	No
-------------------	----

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
CE mark	Yes
ENEC mark	ENEC mark
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	+10 to +35 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Light Technical

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Optic type
910925868390	SM350X 27S/840 PSD PCS N BK	2,700 lm	4000 K	135 lm/W	Medium beam
910925868378	SM350C 34S/840 PSU PCS L1500 BK	3,400 lm	4000 K	142 lm/W	Medium beam
910925868381	SM350C 50S/840 PSU PCS L1500 BK	5,000 lm	4000 K	135 lm/W	Medium beam

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Optic type
910925868384	SM350C 34S/840 PSD PCS L1500 BK	3,400 lm	4000 K	136 lm/W	Medium beam
910925868387	SM350C 50S/840 PSD PCS L1500 BK	5,000 lm	4000 K	135 lm/W	Medium beam
910925868303	SM350C 27S/840 PSU PCS L1200 ALU	2,700 lm	4000 K	138 lm/W	Medium beam
910925868353	SM350C 40S/840 PSU PCS L1200 ALU	4,000 lm	4000 K	133 lm/W	Medium beam
910925868356	SM350C 27S/840 PSD PCS L1200 ALU	2,700 lm	4000 K	135 lm/W	Medium beam
910925868359	SM350C 40S/840 PSD PCS L1200 ALU	4,000 lm	4000 K	133 lm/W	Medium beam
910925868368	SM350C 27S/830 PSU PCS L1200 ALU	2,700 lm	3000 K	132 lm/W	Medium beam
910925868370	SM350C 40S/830 PSU PCS L1200 ALU	4,000 lm	3000 K	133 lm/W	Medium beam
910925868372	SM350C 27S/830 PSD PCS L1200 ALU	2,700 lm	3000 K	135 lm/W	Medium beam
910925868374	SM350C 40S/830 PSD PCS L1200 ALU	4,000 lm	3000 K	129 lm/W	Medium beam
910925868388	SM350X 27S/840 PSD L60L60 PCS ALU	2,700 lm	4000 K	135 lm/W	Medium beam
910925868376	SM350C 34S/840 PSU PCS L1500 ALU	3,400 lm	4000 K	142 lm/W	Medium beam
910925868379	SM350C 50S/840 PSU PCS L1500 ALU	5,000 lm	4000 K	135 lm/W	Medium beam
910925868382	SM350C 34S/840 PSD PCS L1500 ALU	3,400 lm	4000 K	136 lm/W	Medium beam
910925868385	SM350C 50S/840 PSD PCS L1500 ALU	5,000 lm	4000 K	135 lm/W	Medium beam
910925868377	SM350C 34S/840 PSU PCS L1500 WH	3,400 lm	4000 K	142 lm/W	Medium beam
910925868380	SM350C 50S/840 PSU PCS L1500 WH	5,000 lm	4000 K	135 lm/W	Medium beam
910925868383	SM350C 34S/840 PSD PCS L1500 WH	3,400 lm	4000 K	136 lm/W	Medium beam
910925868386	SM350C 50S/840 PSD PCS L1500 WH	5,000 lm	4000 K	135 lm/W	Medium beam
910925868362	SM350C 27S/840 WIA PCS L1200 ALU	2,700 lm	4000 K	135 lm/W	Medium beam
910925868363	SM350C 27S/840 WIA PCS L1200 WH	2,700 lm	4000 K	135 lm/W	Medium beam
910925868364	SM350C 27S/840 WIA PCS L1200 BK	2,700 lm	4000 K	135 lm/W	Medium beam
910925868365	SM350C 40S/840 WIA PCS L1200 ALU	4,000 lm	4000 K	133 lm/W	Medium beam
910925868366	SM350C 40S/840 WIA PCS L1200 WH	4,000 lm	4000 K	133 lm/W	Medium beam
910925868367	SM350C 40S/840 WIA PCS L1200 BK	4,000 lm	4000 K	133 lm/W	Medium beam
910925868351	SM350C 27S/840 PSU PCS L1200 WH	2,700 lm	4000 K	138 lm/W	Medium beam
910925868354	SM350C 40S/840 PSU PCS L1200 WH	4,000 lm	4000 K	133 lm/W	Medium beam
910925868357	SM350C 27S/840 PSD PCS L1200 WH	2,700 lm	4000 K	135 lm/W	Medium beam
910925868360	SM350C 40S/840 PSD PCS L1200 WH	4,000 lm	4000 K	133 lm/W	Medium beam
910925868369	SM350C 27S/830 PSU PCS L1200 WH	2,700 lm	3000 K	132 lm/W	Medium beam
910925868371	SM350C 40S/830 PSU PCS L1200 WH	4,000 lm	3000 K	133 lm/W	Medium beam
910925868373	SM350C 27S/830 PSD PCS L1200 WH	2,700 lm	3000 K	135 lm/W	Medium beam
910925868375	SM350C 40S/830 PSD PCS L1200 WH	4,000 lm	3000 K	129 lm/W	Medium beam
910925868352	SM350C 27S/840 PSU PCS L1200 BK	2,700 lm	4000 K	138 lm/W	Medium beam
910925868355	SM350C 40S/840 PSU PCS L1200 BK	4,000 lm	4000 K	133 lm/W	Medium beam
910925868358	SM350C 27S/840 PSD PCS L1200 BK	2,700 lm	4000 K	135 lm/W	Medium beam
910925868361	SM350C 40S/840 PSD PCS L1200 BK	4,000 lm	4000 K	133 lm/W	Medium beam
910925868389	SM350X 27S/840 PSD L60L60 PCS WH	2,700 lm	4000 K	135 lm/W	Medium beam
910505103701	SM351C 40S/840 PSU A PCS L1200 WH	4,000 lm	4000 K	133 lm/W	Assymetric Beam angle
910505103702	SM351C 40S/840 PSD A PCS L1200 WH	4,000 lm	4000 K	129 lm/W	Assymetric Beam angle
910505103703	SM351C 50S/840 PSU A PCS L1500 WH	5,000 lm	4000 K	135 lm/W	Assymetric Beam angle
910505103704	SM351C 50S/840 PSD A PCS L1500 WH	5,000 lm	4000 K	132 lm/W	Assymetric Beam angle

Operating and Electrical

Order Code	Full Product Name	Input Voltage	Power Consumption	Suitable for random switching
910925868390	SM350X 27S/840 PSD PCS N BK	220 to 240 V	21 W	No
910925868378	SM350C 34S/840 PSU PCS L1500 BK	220 to 240 V	25 W	No
910925868381	SM350C 50S/840 PSU PCS L1500 BK	220 to 240 V	36.5 W	No
910925868384	SM350C 34S/840 PSD PCS L1500 BK	220 to 240 V	26 W	No
910925868387	SM350C 50S/840 PSD PCS L1500 BK	220 to 240 V	38 W	No
910925868303	SM350C 27S/840 PSU PCS L1200 ALU	220 to 240 V	20.5 W	No
910925868353	SM350C 40S/840 PSU PCS L1200 ALU	220 to 240 V	30 W	No
910925868356	SM350C 27S/840 PSD PCS L1200 ALU	220 to 240 V	21 W	No
910925868359	SM350C 40S/840 PSD PCS L1200 ALU	220 to 240 V	31 W	No
910925868368	SM350C 27S/830 PSU PCS L1200 ALU	220 to 240 V	20.5 W	No
910925868370	SM350C 40S/830 PSU PCS L1200 ALU	220 to 240 V	30 W	No
910925868372	SM350C 27S/830 PSD PCS L1200 ALU	220 to 240 V	21 W	No
910925868374	SM350C 40S/830 PSD PCS L1200 ALU	220 to 240 V	31 W	No
910925868388	SM350X 27S/840 PSD L60L60 PCS ALU	220 to 240 V	21 W	No
910925868376	SM350C 34S/840 PSU PCS L1500 ALU	220 to 240 V	25 W	No
910925868379	SM350C 50S/840 PSU PCS L1500 ALU	220 to 240 V	36.5 W	No
910925868382	SM350C 34S/840 PSD PCS L1500 ALU	220 to 240 V	26 W	No
910925868385	SM350C 50S/840 PSD PCS L1500 ALU	220 to 240 V	38 W	No
910925868377	SM350C 34S/840 PSU PCS L1500 WH	220 to 240 V	25 W	No
910925868380	SM350C 50S/840 PSU PCS L1500 WH	220 to 240 V	36.5 W	No
910925868383	SM350C 34S/840 PSD PCS L1500 WH	220 to 240 V	26 W	No
910925868386	SM350C 50S/840 PSD PCS L1500 WH	220 to 240 V	38 W	No
910925868362	SM350C 27S/840 WIA PCS L1200 ALU	220 to 240 V	20.5 W	No
910925868363	SM350C 27S/840 WIA PCS L1200 WH	220 to 240 V	20.5 W	No
910925868364	SM350C 27S/840 WIA PCS L1200 BK	220 to 240 V	20.5 W	No
910925868365	SM350C 40S/840 WIA PCS L1200 ALU	220 to 240 V	30 W	No
910925868366	SM350C 40S/840 WIA PCS L1200 WH	220 to 240 V	30 W	No
910925868367	SM350C 40S/840 WIA PCS L1200 BK	220 to 240 V	30 W	No
910925868351	SM350C 27S/840 PSU PCS L1200 WH	220 to 240 V	20.5 W	No
910925868354	SM350C 40S/840 PSU PCS L1200 WH	220 to 240 V	30 W	No
910925868357	SM350C 27S/840 PSD PCS L1200 WH	220 to 240 V	21 W	No
910925868360	SM350C 40S/840 PSD PCS L1200 WH	220 to 240 V	31 W	No
910925868369	SM350C 27S/830 PSU PCS L1200 WH	220 to 240 V	20.5 W	No
910925868371	SM350C 40S/830 PSU PCS L1200 WH	220 to 240 V	30 W	No
910925868373	SM350C 27S/830 PSD PCS L1200 WH	220 to 240 V	21 W	No
910925868375	SM350C 40S/830 PSD PCS L1200 WH	220 to 240 V	31 W	No
910925868352	SM350C 27S/840 PSU PCS L1200 BK	220 to 240 V	20.5 W	No
910925868355	SM350C 40S/840 PSU PCS L1200 BK	220 to 240 V	30 W	No
910925868358	SM350C 27S/840 PSD PCS L1200 BK	220 to 240 V	21 W	No
910925868361	SM350C 40S/840 PSD PCS L1200 BK	220 to 240 V	31 W	No
910925868389	SM350X 27S/840 PSD L60L60 PCS WH	220 to 240 V	21 W	No

Order Code	Full Product Name	Input Voltage	Power Consumption	Suitable for random switching
910505103701	SM351C 40S/840 PSU A PCS L1200 WH	220-240 V	30 W	Not applicable
910505103702	SM351C 40S/840 PSD A PCS L1200 WH	220-240 V	31 W	Not applicable
910505103703	SM351C 50S/840 PSU A PCS L1500 WH	220-240 V	37 W	Not applicable
910505103704	SM351C 50S/840 PSD A PCS L1500 WH	220-240 V	38 W	Not applicable

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
910925868390	SM350X 27S/840 PSD PCS N BK	Yes	1%
910925868378	SM350C 34S/840 PSU PCS L1500 BK	No	Not applicable
910925868381	SM350C 50S/840 PSU PCS L1500 BK	No	Not applicable
910925868384	SM350C 34S/840 PSD PCS L1500 BK	Yes	1%
910925868387	SM350C 50S/840 PSD PCS L1500 BK	Yes	1%
910925868303	SM350C 27S/840 PSU PCS L1200 ALU	No	Not applicable
910925868353	SM350C 40S/840 PSU PCS L1200 ALU	No	Not applicable
910925868356	SM350C 27S/840 PSD PCS L1200 ALU	Yes	1%
910925868359	SM350C 40S/840 PSD PCS L1200 ALU	Yes	1%
910925868368	SM350C 27S/830 PSU PCS L1200 ALU	No	Not applicable
910925868370	SM350C 40S/830 PSU PCS L1200 ALU	No	Not applicable
910925868372	SM350C 27S/830 PSD PCS L1200 ALU	Yes	1%
910925868374	SM350C 40S/830 PSD PCS L1200 ALU	Yes	1%
910925868388	SM350X 27S/840 PSD L60L60 PCS ALU	Yes	1%
910925868376	SM350C 34S/840 PSU PCS L1500 ALU	No	Not applicable
910925868379	SM350C 50S/840 PSU PCS L1500 ALU	No	Not applicable
910925868382	SM350C 34S/840 PSD PCS L1500 ALU	Yes	1%
910925868385	SM350C 50S/840 PSD PCS L1500 ALU	Yes	1%
910925868377	SM350C 34S/840 PSU PCS L1500 WH	No	Not applicable
910925868380	SM350C 50S/840 PSU PCS L1500 WH	No	Not applicable
910925868383	SM350C 34S/840 PSD PCS L1500 WH	Yes	1%
910925868386	SM350C 50S/840 PSD PCS L1500 WH	Yes	1%
910925868362	SM350C 27S/840 WIA PCS L1200 ALU	No	1%
910925868363	SM350C 27S/840 WIA PCS L1200 WH	No	1%
910925868364	SM350C 27S/840 WIA PCS L1200 BK	No	1%
910925868365	SM350C 40S/840 WIA PCS L1200 ALU	No	1%
910925868366	SM350C 40S/840 WIA PCS L1200 WH	No	1%
910925868367	SM350C 40S/840 WIA PCS L1200 BK	No	1%
910925868351	SM350C 27S/840 PSU PCS L1200 WH	No	Not applicable
910925868354	SM350C 40S/840 PSU PCS L1200 WH	No	Not applicable
910925868357	SM350C 27S/840 PSD PCS L1200 WH	Yes	1%
910925868360	SM350C 40S/840 PSD PCS L1200 WH	Yes	1%
910925868369	SM350C 27S/830 PSU PCS L1200 WH	No	Not applicable
910925868371	SM350C 40S/830 PSU PCS L1200 WH	No	Not applicable
910925868373	SM350C 27S/830 PSD PCS L1200 WH	Yes	1%

Order Code	Full Product Name	Dimmable	Maximum dim level
910925868375	SM350C 40S/830 PSD PCS L1200 WH	Yes	1%
910925868352	SM350C 27S/840 PSU PCS L1200 BK	No	Not applicable
910925868355	SM350C 40S/840 PSU PCS L1200 BK	No	Not applicable
910925868358	SM350C 27S/840 PSD PCS L1200 BK	Yes	1%
910925868361	SM350C 40S/840 PSD PCS L1200 BK	Yes	1%
910925868389	SM350X 27S/840 PSD L60L60 PCS WH	Yes	1%
910505103701	SM351C 40S/840 PSU A PCS L1200 WH	No	Not applicable
910505103702	SM351C 40S/840 PSD A PCS L1200 WH	-	1%
910505103703	SM351C 50S/840 PSU A PCS L1500 WH	No	Not applicable
910505103704	SM351C 50S/840 PSD A PCS L1500 WH	-	1%

Mechanical and Housing

Order Code	Full Product Name	Housing Color
910925868390	SM350X 27S/840 PSD PCS N BK	Black
910925868378	SM350C 34S/840 PSU PCS L1500 BK	Black
910925868381	SM350C 50S/840 PSU PCS L1500 BK	Black
910925868384	SM350C 34S/840 PSD PCS L1500 BK	Black
910925868387	SM350C 50S/840 PSD PCS L1500 BK	Black
910925868303	SM350C 27S/840 PSU PCS L1200 ALU	Aluminum
910925868353	SM350C 40S/840 PSU PCS L1200 ALU	Aluminum
910925868356	SM350C 27S/840 PSD PCS L1200 ALU	Aluminum
910925868359	SM350C 40S/840 PSD PCS L1200 ALU	Aluminum
910925868368	SM350C 27S/830 PSU PCS L1200 ALU	Aluminum
910925868370	SM350C 40S/830 PSU PCS L1200 ALU	Aluminum
910925868372	SM350C 27S/830 PSD PCS L1200 ALU	Aluminum
910925868374	SM350C 40S/830 PSD PCS L1200 ALU	Aluminum
910925868388	SM350X 27S/840 PSD L60L60 PCS ALU	Aluminum
910925868376	SM350C 34S/840 PSU PCS L1500 ALU	Aluminum
910925868379	SM350C 50S/840 PSU PCS L1500 ALU	Aluminum
910925868382	SM350C 34S/840 PSD PCS L1500 ALU	Aluminum
910925868385	SM350C 50S/840 PSD PCS L1500 ALU	Aluminum
910925868377	SM350C 34S/840 PSU PCS L1500 WH	White
910925868380	SM350C 50S/840 PSU PCS L1500 WH	White
910925868383	SM350C 34S/840 PSD PCS L1500 WH	White
910925868386	SM350C 50S/840 PSD PCS L1500 WH	White
910925868362	SM350C 27S/840 WIA PCS L1200 ALU	Aluminum
910925868363	SM350C 27S/840 WIA PCS L1200 WH	White
910925868364	SM350C 27S/840 WIA PCS L1200 BK	Black
910925868365	SM350C 40S/840 WIA PCS L1200 ALU	Aluminum
910925868366	SM350C 40S/840 WIA PCS L1200 WH	White
910925868367	SM350C 40S/840 WIA PCS L1200 BK	Black
910925868351	SM350C 27S/840 PSU PCS L1200 WH	White

Order Code	Full Product Name	Housing Color
910925868354	SM350C 40S/840 PSU PCS L1200 WH	White
910925868357	SM350C 27S/840 PSD PCS L1200 WH	White
910925868360	SM350C 40S/840 PSD PCS L1200 WH	White
910925868369	SM350C 27S/830 PSU PCS L1200 WH	White
910925868371	SM350C 40S/830 PSU PCS L1200 WH	White
910925868373	SM350C 27S/830 PSD PCS L1200 WH	White
910925868375	SM350C 40S/830 PSD PCS L1200 WH	White
910925868352	SM350C 27S/840 PSU PCS L1200 BK	Black
910925868355	SM350C 40S/840 PSU PCS L1200 BK	Black
910925868358	SM350C 27S/840 PSD PCS L1200 BK	Black
910925868361	SM350C 40S/840 PSD PCS L1200 BK	Black
910925868389	SM350X 27S/840 PSD L60L60 PCS WH	White
910505103701	SM351C 40S/840 PSU A PCS L1200 WH	White
910505103702	SM351C 40S/840 PSD A PCS L1200 WH	White
910505103703	SM351C 50S/840 PSU A PCS L1500 WH	White
910505103704	SM351C 50S/840 PSD A PCS L1500 WH	White

Approval and Application

Order Code	Full Product Name	Flammability mark
910925868390	SM350X 27S/840 PSD PCS N BK	For mounting on normally flammable surfaces
910925868378	SM350C 34S/840 PSU PCS L1500 BK	For mounting on normally flammable surfaces
910925868381	SM350C 50S/840 PSU PCS L1500 BK	For mounting on normally flammable surfaces
910925868384	SM350C 34S/840 PSD PCS L1500 BK	For mounting on normally flammable surfaces
910925868387	SM350C 50S/840 PSD PCS L1500 BK	For mounting on normally flammable surfaces
910925868303	SM350C 27S/840 PSU PCS L1200 ALU	For mounting on normally flammable surfaces
910925868353	SM350C 40S/840 PSU PCS L1200 ALU	For mounting on normally flammable surfaces
910925868356	SM350C 27S/840 PSD PCS L1200 ALU	For mounting on normally flammable surfaces
910925868359	SM350C 40S/840 PSD PCS L1200 ALU	For mounting on normally flammable surfaces
910925868368	SM350C 27S/830 PSU PCS L1200 ALU	For mounting on normally flammable surfaces
910925868370	SM350C 40S/830 PSU PCS L1200 ALU	For mounting on normally flammable surfaces
910925868372	SM350C 27S/830 PSD PCS L1200 ALU	For mounting on normally flammable surfaces
910925868374	SM350C 40S/830 PSD PCS L1200 ALU	For mounting on normally flammable surfaces
910925868388	SM350X 27S/840 PSD L60L60 PCS ALU	For mounting on normally flammable surfaces
910925868376	SM350C 34S/840 PSU PCS L1500 ALU	For mounting on normally flammable surfaces
910925868379	SM350C 50S/840 PSU PCS L1500 ALU	For mounting on normally flammable surfaces
910925868382	SM350C 34S/840 PSD PCS L1500 ALU	For mounting on normally flammable surfaces
910925868385	SM350C 50S/840 PSD PCS L1500 ALU	For mounting on normally flammable surfaces
910925868377	SM350C 34S/840 PSU PCS L1500 WH	For mounting on normally flammable surfaces
910925868380	SM350C 50S/840 PSU PCS L1500 WH	For mounting on normally flammable surfaces
910925868383	SM350C 34S/840 PSD PCS L1500 WH	For mounting on normally flammable surfaces
910925868386	SM350C 50S/840 PSD PCS L1500 WH	For mounting on normally flammable surfaces
910925868362	SM350C 27S/840 WIA PCS L1200 ALU	For mounting on normally flammable surfaces

Order Code	Full Product Name	Flammability mark
910925868363	SM350C 27S/840 WIA PCS L1200 WH	For mounting on normally flammable surfaces
910925868364	SM350C 27S/840 WIA PCS L1200 BK	For mounting on normally flammable surfaces
910925868365	SM350C 40S/840 WIA PCS L1200 ALU	For mounting on normally flammable surfaces
910925868366	SM350C 40S/840 WIA PCS L1200 WH	For mounting on normally flammable surfaces
910925868367	SM350C 40S/840 WIA PCS L1200 BK	For mounting on normally flammable surfaces
910925868351	SM350C 27S/840 PSU PCS L1200 WH	For mounting on normally flammable surfaces
910925868354	SM350C 40S/840 PSU PCS L1200 WH	For mounting on normally flammable surfaces
910925868357	SM350C 27S/840 PSD PCS L1200 WH	For mounting on normally flammable surfaces
910925868360	SM350C 40S/840 PSD PCS L1200 WH	For mounting on normally flammable surfaces
910925868369	SM350C 27S/830 PSU PCS L1200 WH	For mounting on normally flammable surfaces
910925868371	SM350C 40S/830 PSU PCS L1200 WH	For mounting on normally flammable surfaces
910925868373	SM350C 27S/830 PSD PCS L1200 WH	For mounting on normally flammable surfaces
910925868375	SM350C 40S/830 PSD PCS L1200 WH	For mounting on normally flammable surfaces
910925868352	SM350C 27S/840 PSU PCS L1200 BK	For mounting on normally flammable surfaces
910925868355	SM350C 40S/840 PSU PCS L1200 BK	For mounting on normally flammable surfaces
910925868358	SM350C 27S/840 PSD PCS L1200 BK	For mounting on normally flammable surfaces
910925868361	SM350C 40S/840 PSD PCS L1200 BK	For mounting on normally flammable surfaces
910925868389	SM350X 27S/840 PSD L60L60 PCS WH	For mounting on normally flammable surfaces
910505103701	SM351C 40S/840 PSU A PCS L1200 WH	-
910505103702	SM351C 40S/840 PSD A PCS L1200 WH	-
910505103703	SM351C 50S/840 PSU A PCS L1500 WH	-
910505103704	SM351C 50S/840 PSD A PCS L1500 WH	-

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910925868390	SM350X 27S/840 PSD PCS N BK	(0.39, 0.38) SDCM <3
910925868378	SM350C 34S/840 PSU PCS L1500 BK	(0.39, 0.38) SDCM <3
910925868381	SM350C 50S/840 PSU PCS L1500 BK	(0.39, 0.38) SDCM <3
910925868384	SM350C 34S/840 PSD PCS L1500 BK	(0.39, 0.38) SDCM <3
910925868387	SM350C 50S/840 PSD PCS L1500 BK	(0.39, 0.38) SDCM <3
910925868303	SM350C 27S/840 PSU PCS L1200 ALU	(0.39, 0.38) SDCM <3
910925868353	SM350C 40S/840 PSU PCS L1200 ALU	(0.39, 0.38) SDCM <3
910925868356	SM350C 27S/840 PSD PCS L1200 ALU	(0.39, 0.38) SDCM <3
910925868359	SM350C 40S/840 PSD PCS L1200 ALU	(0.39, 0.38) SDCM <3
910925868368	SM350C 27S/830 PSU PCS L1200 ALU	(0.43, 0.40) SDCM <3
910925868370	SM350C 40S/830 PSU PCS L1200 ALU	(0.43, 0.40) SDCM <3
910925868372	SM350C 27S/830 PSD PCS L1200 ALU	(0.43, 0.40) SDCM <3
910925868374	SM350C 40S/830 PSD PCS L1200 ALU	(0.43, 0.40) SDCM <3
910925868388	SM350X 27S/840 PSD L60L60 PCS ALU	(0.39, 0.38) SDCM <3
910925868376	SM350C 34S/840 PSU PCS L1500 ALU	(0.39, 0.38) SDCM <3
910925868379	SM350C 50S/840 PSU PCS L1500 ALU	(0.39, 0.38) SDCM <3
910925868382	SM350C 34S/840 PSD PCS L1500 ALU	(0.39, 0.38) SDCM <3


Order Code	Full Product Name	Initial chromaticity
910925868385	SM350C 50S/840 PSD PCS L1500 ALU	(0.39, 0.38) SDCM <3
910925868377	SM350C 34S/840 PSU PCS L1500 WH	(0.39, 0.38) SDCM <3
910925868380	SM350C 50S/840 PSU PCS L1500 WH	(0.39, 0.38) SDCM <3
910925868383	SM350C 34S/840 PSD PCS L1500 WH	(0.39, 0.38) SDCM <3
910925868386	SM350C 50S/840 PSD PCS L1500 WH	(0.39, 0.38) SDCM <3
910925868362	SM350C 27S/840 WIA PCS L1200 ALU	(0.39, 0.38) SDCM <3
910925868363	SM350C 27S/840 WIA PCS L1200 WH	(0.39, 0.38) SDCM <3
910925868364	SM350C 27S/840 WIA PCS L1200 BK	(0.39, 0.38) SDCM <3
910925868365	SM350C 40S/840 WIA PCS L1200 ALU	(0.39, 0.38) SDCM <3
910925868366	SM350C 40S/840 WIA PCS L1200 WH	(0.39, 0.38) SDCM <3
910925868367	SM350C 40S/840 WIA PCS L1200 BK	(0.39, 0.38) SDCM <3
910925868351	SM350C 27S/840 PSU PCS L1200 WH	(0.39, 0.38) SDCM <3
910925868354	SM350C 40S/840 PSU PCS L1200 WH	(0.39, 0.38) SDCM <3
910925868357	SM350C 27S/840 PSD PCS L1200 WH	(0.39, 0.38) SDCM <3
910925868360	SM350C 40S/840 PSD PCS L1200 WH	(0.39, 0.38) SDCM <3
910925868369	SM350C 27S/830 PSU PCS L1200 WH	(0.43, 0.40) SDCM <3
910925868371	SM350C 40S/830 PSU PCS L1200 WH	(0.43, 0.40) SDCM <3
910925868373	SM350C 27S/830 PSD PCS L1200 WH	(0.43, 0.40) SDCM <3
910925868375	SM350C 40S/830 PSD PCS L1200 WH	(0.43, 0.40) SDCM <3
910925868352	SM350C 27S/840 PSU PCS L1200 BK	(0.39, 0.38) SDCM <3
910925868355	SM350C 40S/840 PSU PCS L1200 BK	(0.39, 0.38) SDCM <3
910925868358	SM350C 27S/840 PSD PCS L1200 BK	(0.39, 0.38) SDCM <3
910925868361	SM350C 40S/840 PSD PCS L1200 BK	(0.39, 0.38) SDCM <3
910925868389	SM350X 27S/840 PSD L60L60 PCS WH	(0.39, 0.38) SDCM <3
910505103701	SM351C 40S/840 PSU A PCS L1200 WH	(0.39, 0.38) SDCM <3
910505103702	SM351C 40S/840 PSD A PCS L1200 WH	(0.39, 0.38) SDCM <3
910505103703	SM351C 50S/840 PSU A PCS L1500 WH	(0.39, 0.38) SDCM <3
910505103704	SM351C 50S/840 PSD A PCS L1500 WH	(0.39, 0.38) SDCM <3

Product Data

Order Code	Full Product Name	Product family code
910925868390	SM350X 27S/840 PSD PCS N BK	SM350X
910925868378	SM350C 34S/840 PSU PCS L1500 BK	SM350C
910925868381	SM350C 50S/840 PSU PCS L1500 BK	SM350C
910925868384	SM350C 34S/840 PSD PCS L1500 BK	SM350C
910925868387	SM350C 50S/840 PSD PCS L1500 BK	SM350C
910925868303	SM350C 27S/840 PSU PCS L1200 ALU	SM350C
910925868353	SM350C 40S/840 PSU PCS L1200 ALU	SM350C
910925868356	SM350C 27S/840 PSD PCS L1200 ALU	SM350C
910925868359	SM350C 40S/840 PSD PCS L1200 ALU	SM350C
910925868368	SM350C 27S/830 PSU PCS L1200 ALU	SM350C
910925868370	SM350C 40S/830 PSU PCS L1200 ALU	SM350C

Order Code	Full Product Name	Product family code
910925868372	SM350C 27S/830 PSD PCS L1200 ALU	SM350C
910925868374	SM350C 40S/830 PSD PCS L1200 ALU	SM350C
910925868388	SM350X 27S/840 PSD L60L60 PCS ALU	SM350X
910925868376	SM350C 34S/840 PSU PCS L1500 ALU	SM350C
910925868379	SM350C 50S/840 PSU PCS L1500 ALU	SM350C
910925868382	SM350C 34S/840 PSD PCS L1500 ALU	SM350C
910925868385	SM350C 50S/840 PSD PCS L1500 ALU	SM350C
910925868377	SM350C 34S/840 PSU PCS L1500 WH	SM350C
910925868380	SM350C 50S/840 PSU PCS L1500 WH	SM350C
910925868383	SM350C 34S/840 PSD PCS L1500 WH	SM350C
910925868386	SM350C 50S/840 PSD PCS L1500 WH	SM350C
910925868362	SM350C 27S/840 WIA PCS L1200 ALU	SM350C
910925868363	SM350C 27S/840 WIA PCS L1200 WH	SM350C
910925868364	SM350C 27S/840 WIA PCS L1200 BK	SM350C
910925868365	SM350C 40S/840 WIA PCS L1200 ALU	SM350C
910925868366	SM350C 40S/840 WIA PCS L1200 WH	SM350C
910925868367	SM350C 40S/840 WIA PCS L1200 BK	SM350C
910925868351	SM350C 27S/840 PSU PCS L1200 WH	SM350C
910925868354	SM350C 40S/840 PSU PCS L1200 WH	SM350C
910925868357	SM350C 27S/840 PSD PCS L1200 WH	SM350C
910925868360	SM350C 40S/840 PSD PCS L1200 WH	SM350C
910925868369	SM350C 27S/830 PSU PCS L1200 WH	SM350C
910925868371	SM350C 40S/830 PSU PCS L1200 WH	SM350C
910925868373	SM350C 27S/830 PSD PCS L1200 WH	SM350C
910925868375	SM350C 40S/830 PSD PCS L1200 WH	SM350C
910925868352	SM350C 27S/840 PSU PCS L1200 BK	SM350C
910925868355	SM350C 40S/840 PSU PCS L1200 BK	SM350C
910925868358	SM350C 27S/840 PSD PCS L1200 BK	SM350C
910925868361	SM350C 40S/840 PSD PCS L1200 BK	SM350C
910925868389	SM350X 27S/840 PSD L60L60 PCS WH	SM350X
910505103701	SM351C 40S/840 PSU A PCS L1200 WH	SM350C
910505103702	SM351C 40S/840 PSD A PCS L1200 WH	SM350C
910505103703	SM351C 50S/840 PSU A PCS L1500 WH	SM350C
910505103704	SM351C 50S/840 PSD A PCS L1500 WH	SM350C


Polar normal diagrams



SM350CI - 910925868303

SM350CI - 910925868353


SM350CI - 910925868366



SM350CI - 910925868379

SM350CI - 910925868355


SM350CI - 910925868356




SM350CI - 910925868383

SM350CI - 910925868352


SM350CI - 910925868359




SM350CI - 910925868363




SM350CI - 910925868375




SM350CI - 910925868381




SM350CI - 910925868385




SM350CI - 910925868388




SM350CI - 910925868389




SM350CI - 910925868354




SM350CI - 910925868387




SM350CI - 910925868362




SM350CI - 910925868365




SM350CI - 910925868370




SM350CI - 910925868384




SM350CI - 910925868386




SM350CI - 910925868360




SM350CI - 910925868361




SM350CI - 910925868367




SM350CI - 910925868357




SM350CI - 910925868368




SM350CI - 910925868358




SM350CI - 910925868364




SM350CI - 910925868372




SM350CI - 910925868376




SM350CI - 910925868378




SM350CI - 910925868380




SM350CI - 910925868351




SM350CI - 910925868369




SM350CI - 910925868371




SM350CI - 910925868374




SM350CI - 910925868373



SM350CI - 910925868377



SM350CI - 910925868382



SM350CI - 910925868390