



The flexible light line

These days, many office owners and office lighting designers prefer lines of light. The reason is simple. Not only do light lines come in a minimalistic design; they also offer far more choice and flexibility. Short or long lines and luminaires, standalone luminaires, different shapes and even a variety of colours; anything is possible. And with KeyLine, all these benefits come at a competitive price while still complying with office lighting norms. KeyLine is a superb light line range with a slim, minimalistic design and a high lumen output to illuminate the brightest office spaces. But with comfortable, low levels of glare it's also easy on the eye and complies with UGR19. This makes KeyLine ideal for linear applications, as well as standalone suspended or surface-mounted luminaires. A range that offers the ultimate flexibility and unlimited possibilities. KeyLine design flexibility comes in the form of different lengths, colours and light outputs – including L-shapes, as well as straight lines. All with high efficiency up to 130 lm/W, and the option to upgrade with wireless connectivity and control. Add to that attractive pricing, and with KeyLine you can also enjoy excellent value that ensures a superb total cost of ownership.

Benefits

- Suitable for office applications
- Excellent total cost of ownership
- Wide range of options to suit the demands of different offices

Applications

- Offices
- Retail
- Education

Features

- Comfortable, low glare: <UGR19 for the full range
- High lumen output, up to 4000lm for 1.2m version

Versions

	KeyLine L-corner, black		KeyLine suspended L1500, bk
	KeyLine suspended L1200, alu		KeyLine L-corner, alu
	KeyLine suspended L1500, alu		KeyLine suspended L1500, white
	KeyLine SP350P WIA		KeyLine suspended L1200, white

- Interact Connectivity ready with wireless drivers
- Standard options in different lengths, colors and light outputs
- Customization options
- KeyLine luminaires have an IP20 classification and are not protected against water ingress. We strongly recommend that the installation environment is checked for suitability.
- If – despite the IPX0 classification warning – luminaires are subject to water ingress, Philips and Signify cannot guarantee safety or prevent failure. In this case the product warranty does not apply and becomes void.




KeyLine suspended L1200, bk




KeyLine L-corner, white

Dimensional drawing



KeyLine_DD_L-corner



KeyLine_DD_linear


Product details



KeyLine line coupling, alu



KeyLine black with ceiling bracket accessory for surface mounting



KeyLine black with coupling piece accessory for line mounting



KeyLine_SM350C_WIA_DPP1



KeyLine line configuration, white



KeyLine SM350C, white



KeyLine configuration with L-corner SM350X




KeyLine black with end-cap accessory



KeyLine line coupling, white



KeyLine alu with suspension set for suspended mounting



KeyLine white line coupling with coupling piece accessory



KeyLine_SM350C_WIA_DPP3



KeyLine alu with end-cap accessory



KeyLine white with coupling piece accessory for line mounting




KeyLine structured optics UGR19 (PCS)



KeyLine line coupling, black



KeyLine SM350C, alu



KeyLine alu line coupling with coupling piece accessory



KeyLine line configuration, black



KeyLine alu with ceiling bracket accessory for surface mounting



KeyLine white with suspension set for suspended mounting



KeyLine white with ceiling bracket accessory for surface mounting



KeyLine white with end-cap accessory




KeyLine alu with coupling piece accessory for line mounting



KeyLine SM350C, black



KeyLine L-corner, black



KeyLine black line coupling with coupling piece accessory



KeyLine black with suspension set for suspended mounting



KeyLine_SM350C_WIA_DPP2



KeyLine L-corner, alu



KeyLine L-corner, white

General Information

Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Service tag	Yes

Light Technical

Color rendering index (CRI)	>80
Beam angle of light source	120 degree(s)
Optic type	Medium beam

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	No
Protection class IEC	Safety class I

Mechanical and Housing

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK06 [1 J]

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	+10 to +35 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Light Technical

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)
62454200	SM350X 27S/840 PSD PCS N BK	2,700 lm	4000 K	135 lm/W
62442900	SM350C 34S/840 PSU PCS L1500 BK	3,400 lm	4000 K	142 lm/W
62445000	SM350C 50S/840 PSU PCS L1500 BK	5,000 lm	4000 K	135 lm/W
62448100	SM350C 34S/840 PSD PCS L1500 BK	3,400 lm	4000 K	136 lm/W
62451100	SM350C 50S/840 PSD PCS L1500 BK	5,000 lm	4000 K	135 lm/W
62367500	SM350C 27S/840 PSU PCS L1200 ALU	2,700 lm	4000 K	138 lm/W
62417700	SM350C 40S/840 PSU PCS L1200 ALU	4,000 lm	4000 K	133 lm/W
62420700	SM350C 27S/840 PSD PCS L1200 ALU	2,700 lm	4000 K	135 lm/W
62423800	SM350C 40S/840 PSD PCS L1200 ALU	4,000 lm	4000 K	133 lm/W
62432000	SM350C 27S/830 PSU PCS L1200 ALU	2,700 lm	3000 K	132 lm/W
62434400	SM350C 40S/830 PSU PCS L1200 ALU	4,000 lm	3000 K	133 lm/W
62436800	SM350C 27S/830 PSD PCS L1200 ALU	2,700 lm	3000 K	135 lm/W
62438200	SM350C 40S/830 PSD PCS L1200 ALU	4,000 lm	3000 K	129 lm/W
62452800	SM350X 27S/840 PSD L60L60 PCS ALU	2,700 lm	4000 K	135 lm/W
62440500	SM350C 34S/840 PSU PCS L1500 ALU	3,400 lm	4000 K	142 lm/W
62443600	SM350C 50S/840 PSU PCS L1500 ALU	5,000 lm	4000 K	135 lm/W
62446700	SM350C 34S/840 PSD PCS L1500 ALU	3,400 lm	4000 K	136 lm/W
62449800	SM350C 50S/840 PSD PCS L1500 ALU	5,000 lm	4000 K	135 lm/W
62441200	SM350C 34S/840 PSU PCS L1500 WH	3,400 lm	4000 K	142 lm/W
62444300	SM350C 50S/840 PSU PCS L1500 WH	5,000 lm	4000 K	135 lm/W
62447400	SM350C 34S/840 PSD PCS L1500 WH	3,400 lm	4000 K	136 lm/W
62450400	SM350C 50S/840 PSD PCS L1500 WH	5,000 lm	4000 K	135 lm/W
62426900	SM350C 27S/840 WIA PCS L1200 ALU	2,700 lm	4000 K	135 lm/W
62427600	SM350C 27S/840 WIA PCS L1200 WH	2,700 lm	4000 K	135 lm/W
62429000	SM350C 40S/840 WIA PCS L1200 ALU	4,000 lm	4000 K	133 lm/W

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)
62430600	SM350C 40S/840 WIA PCS L1200 WH	4,000 lm	4000 K	133 lm/W
62415300	SM350C 27S/840 PSU PCS L1200 WH	2,700 lm	4000 K	138 lm/W
62418400	SM350C 40S/840 PSU PCS L1200 WH	4,000 lm	4000 K	133 lm/W
62421400	SM350C 27S/840 PSD PCS L1200 WH	2,700 lm	4000 K	135 lm/W
62424500	SM350C 40S/840 PSD PCS L1200 WH	4,000 lm	4000 K	133 lm/W
62433700	SM350C 27S/830 PSU PCS L1200 WH	2,700 lm	3000 K	132 lm/W
62435100	SM350C 40S/830 PSU PCS L1200 WH	4,000 lm	3000 K	133 lm/W
62437500	SM350C 27S/830 PSD PCS L1200 WH	2,700 lm	3000 K	135 lm/W
62439900	SM350C 40S/830 PSD PCS L1200 WH	4,000 lm	3000 K	129 lm/W
62416000	SM350C 27S/840 PSU PCS L1200 BK	2,700 lm	4000 K	138 lm/W
62419100	SM350C 40S/840 PSU PCS L1200 BK	4,000 lm	4000 K	133 lm/W
62422100	SM350C 27S/840 PSD PCS L1200 BK	2,700 lm	4000 K	135 lm/W
62425200	SM350C 40S/840 PSD PCS L1200 BK	4,000 lm	4000 K	133 lm/W
62453500	SM350X 27S/840 PSD L60L60 PCS WH	2,700 lm	4000 K	135 lm/W

Operating and Electrical

Order Code	Full Product Name	Power Consumption
62454200	SM350X 27S/840 PSD PCS N BK	21 W
62442900	SM350C 34S/840 PSU PCS L1500 BK	25 W
62445000	SM350C 50S/840 PSU PCS L1500 BK	36.5 W
62448100	SM350C 34S/840 PSD PCS L1500 BK	26 W
62451100	SM350C 50S/840 PSD PCS L1500 BK	38 W
62367500	SM350C 27S/840 PSU PCS L1200 ALU	20.5 W
62417700	SM350C 40S/840 PSU PCS L1200 ALU	30 W
62420700	SM350C 27S/840 PSD PCS L1200 ALU	21 W
62423800	SM350C 40S/840 PSD PCS L1200 ALU	31 W
62432000	SM350C 27S/830 PSU PCS L1200 ALU	20.5 W
62434400	SM350C 40S/830 PSU PCS L1200 ALU	30 W
62436800	SM350C 27S/830 PSD PCS L1200 ALU	21 W
62438200	SM350C 40S/830 PSD PCS L1200 ALU	31 W
62452800	SM350X 27S/840 PSD L60L60 PCS ALU	21 W
62440500	SM350C 34S/840 PSU PCS L1500 ALU	25 W
62443600	SM350C 50S/840 PSU PCS L1500 ALU	36.5 W
62446700	SM350C 34S/840 PSD PCS L1500 ALU	26 W
62449800	SM350C 50S/840 PSD PCS L1500 ALU	38 W
62441200	SM350C 34S/840 PSU PCS L1500 WH	25 W
62444300	SM350C 50S/840 PSU PCS L1500 WH	36.5 W
62447400	SM350C 34S/840 PSD PCS L1500 WH	26 W
62450400	SM350C 50S/840 PSD PCS L1500 WH	38 W
62426900	SM350C 27S/840 WIA PCS L1200 ALU	20.5 W
62427600	SM350C 27S/840 WIA PCS L1200 WH	20.5 W
62429000	SM350C 40S/840 WIA PCS L1200 ALU	30 W

Order Code	Full Product Name	Power Consumption
62430600	SM350C 40S/840 WIA PCS L1200 WH	30 W
62415300	SM350C 27S/840 PSU PCS L1200 WH	20.5 W
62418400	SM350C 40S/840 PSU PCS L1200 WH	30 W
62421400	SM350C 27S/840 PSD PCS L1200 WH	21 W
62424500	SM350C 40S/840 PSD PCS L1200 WH	31 W
62433700	SM350C 27S/830 PSU PCS L1200 WH	20.5 W
62435100	SM350C 40S/830 PSU PCS L1200 WH	30 W
62437500	SM350C 27S/830 PSD PCS L1200 WH	21 W
62439900	SM350C 40S/830 PSD PCS L1200 WH	31 W
62416000	SM350C 27S/840 PSU PCS L1200 BK	20.5 W
62419100	SM350C 40S/840 PSU PCS L1200 BK	30 W
62422100	SM350C 27S/840 PSD PCS L1200 BK	21 W
62425200	SM350C 40S/840 PSD PCS L1200 BK	31 W
62453500	SM350X 27S/840 PSD L60L60 PCS WH	21 W

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
62454200	SM350X 27S/840 PSD PCS N BK	Yes	1%
62442900	SM350C 34S/840 PSU PCS L1500 BK	No	Not applicable
62445000	SM350C 50S/840 PSU PCS L1500 BK	No	Not applicable
62448100	SM350C 34S/840 PSD PCS L1500 BK	Yes	1%
62451100	SM350C 50S/840 PSD PCS L1500 BK	Yes	1%
62367500	SM350C 27S/840 PSU PCS L1200 ALU	No	Not applicable
62417700	SM350C 40S/840 PSU PCS L1200 ALU	No	Not applicable
62420700	SM350C 27S/840 PSD PCS L1200 ALU	Yes	1%
62423800	SM350C 40S/840 PSD PCS L1200 ALU	Yes	1%
62432000	SM350C 27S/830 PSU PCS L1200 ALU	No	Not applicable
62434400	SM350C 40S/830 PSU PCS L1200 ALU	No	Not applicable
62436800	SM350C 27S/830 PSD PCS L1200 ALU	Yes	1%
62438200	SM350C 40S/830 PSD PCS L1200 ALU	Yes	1%
62452800	SM350X 27S/840 PSD L60L60 PCS ALU	Yes	1%
62440500	SM350C 34S/840 PSU PCS L1500 ALU	No	Not applicable
62443600	SM350C 50S/840 PSU PCS L1500 ALU	No	Not applicable
62446700	SM350C 34S/840 PSD PCS L1500 ALU	Yes	1%
62449800	SM350C 50S/840 PSD PCS L1500 ALU	Yes	1%
62441200	SM350C 34S/840 PSU PCS L1500 WH	No	Not applicable
62444300	SM350C 50S/840 PSU PCS L1500 WH	No	Not applicable
62447400	SM350C 34S/840 PSD PCS L1500 WH	Yes	1%
62450400	SM350C 50S/840 PSD PCS L1500 WH	Yes	1%
62426900	SM350C 27S/840 WIA PCS L1200 ALU	No	1%
62427600	SM350C 27S/840 WIA PCS L1200 WH	No	1%
62429000	SM350C 40S/840 WIA PCS L1200 ALU	No	1%

Order Code	Full Product Name	Dimmable	Maximum dim level
62430600	SM350C 40S/840 WIA PCS L1200 WH	No	1%
62415300	SM350C 27S/840 PSU PCS L1200 WH	No	Not applicable
62418400	SM350C 40S/840 PSU PCS L1200 WH	No	Not applicable
62421400	SM350C 27S/840 PSD PCS L1200 WH	Yes	1%
62424500	SM350C 40S/840 PSD PCS L1200 WH	Yes	1%
62433700	SM350C 27S/830 PSU PCS L1200 WH	No	Not applicable
62435100	SM350C 40S/830 PSU PCS L1200 WH	No	Not applicable
62437500	SM350C 27S/830 PSD PCS L1200 WH	Yes	1%
62439900	SM350C 40S/830 PSD PCS L1200 WH	Yes	1%
62416000	SM350C 27S/840 PSU PCS L1200 BK	No	Not applicable
62419100	SM350C 40S/840 PSU PCS L1200 BK	No	Not applicable
62422100	SM350C 27S/840 PSD PCS L1200 BK	Yes	1%
62425200	SM350C 40S/840 PSD PCS L1200 BK	Yes	1%
62453500	SM350X 27S/840 PSD L60L60 PCS WH	Yes	1%

Mechanical and Housing

Order Code	Full Product Name	Housing Color
62454200	SM350X 27S/840 PSD PCS N BK	Black
62442900	SM350C 34S/840 PSU PCS L1500 BK	Black
62445000	SM350C 50S/840 PSU PCS L1500 BK	Black
62448100	SM350C 34S/840 PSD PCS L1500 BK	Black
62451100	SM350C 50S/840 PSD PCS L1500 BK	Black
62367500	SM350C 27S/840 PSU PCS L1200 ALU	Aluminum
62417700	SM350C 40S/840 PSU PCS L1200 ALU	Aluminum
62420700	SM350C 27S/840 PSD PCS L1200 ALU	Aluminum
62423800	SM350C 40S/840 PSD PCS L1200 ALU	Aluminum
62432000	SM350C 27S/830 PSU PCS L1200 ALU	Aluminum
62434400	SM350C 40S/830 PSU PCS L1200 ALU	Aluminum
62436800	SM350C 27S/830 PSD PCS L1200 ALU	Aluminum
62438200	SM350C 40S/830 PSD PCS L1200 ALU	Aluminum
62452800	SM350X 27S/840 PSD L60L60 PCS ALU	Aluminum
62440500	SM350C 34S/840 PSU PCS L1500 ALU	Aluminum
62443600	SM350C 50S/840 PSU PCS L1500 ALU	Aluminum
62446700	SM350C 34S/840 PSD PCS L1500 ALU	Aluminum
62449800	SM350C 50S/840 PSD PCS L1500 ALU	Aluminum
62441200	SM350C 34S/840 PSU PCS L1500 WH	White
62444300	SM350C 50S/840 PSU PCS L1500 WH	White
62447400	SM350C 34S/840 PSD PCS L1500 WH	White
62450400	SM350C 50S/840 PSD PCS L1500 WH	White
62426900	SM350C 27S/840 WIA PCS L1200 ALU	Aluminum
62427600	SM350C 27S/840 WIA PCS L1200 WH	White
62429000	SM350C 40S/840 WIA PCS L1200 ALU	Aluminum

Order Code	Full Product Name	Housing Color
62430600	SM350C 40S/840 WIA PCS L1200 WH	White
62415300	SM350C 27S/840 PSU PCS L1200 WH	White
62418400	SM350C 40S/840 PSU PCS L1200 WH	White
62421400	SM350C 27S/840 PSD PCS L1200 WH	White
62424500	SM350C 40S/840 PSD PCS L1200 WH	White
62433700	SM350C 27S/830 PSU PCS L1200 WH	White
62435100	SM350C 40S/830 PSU PCS L1200 WH	White
62437500	SM350C 27S/830 PSD PCS L1200 WH	White
62439900	SM350C 40S/830 PSD PCS L1200 WH	White
62416000	SM350C 27S/840 PSU PCS L1200 BK	Black
62419100	SM350C 40S/840 PSU PCS L1200 BK	Black
62422100	SM350C 27S/840 PSD PCS L1200 BK	Black
62425200	SM350C 40S/840 PSD PCS L1200 BK	Black
62453500	SM350X 27S/840 PSD L60L60 PCS WH	White

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
62454200	SM350X 27S/840 PSD PCS N BK	(0.39, 0.38) SDCM <3
62442900	SM350C 34S/840 PSU PCS L1500 BK	(0.39, 0.38) SDCM <3
62445000	SM350C 50S/840 PSU PCS L1500 BK	(0.39, 0.38) SDCM <3
62448100	SM350C 34S/840 PSD PCS L1500 BK	(0.39, 0.38) SDCM <3
62451100	SM350C 50S/840 PSD PCS L1500 BK	(0.39, 0.38) SDCM <3
62367500	SM350C 27S/840 PSU PCS L1200 ALU	(0.39, 0.38) SDCM <3
62417700	SM350C 40S/840 PSU PCS L1200 ALU	(0.39, 0.38) SDCM <3
62420700	SM350C 27S/840 PSD PCS L1200 ALU	(0.39, 0.38) SDCM <3
62423800	SM350C 40S/840 PSD PCS L1200 ALU	(0.39, 0.38) SDCM <3
62432000	SM350C 27S/830 PSU PCS L1200 ALU	(0.43, 0.40) SDCM <3
62434400	SM350C 40S/830 PSU PCS L1200 ALU	(0.43, 0.40) SDCM <3
62436800	SM350C 27S/830 PSD PCS L1200 ALU	(0.43, 0.40) SDCM <3
62438200	SM350C 40S/830 PSD PCS L1200 ALU	(0.43, 0.40) SDCM <3
62452800	SM350X 27S/840 PSD L60L60 PCS ALU	(0.39, 0.38) SDCM <3
62440500	SM350C 34S/840 PSU PCS L1500 ALU	(0.39, 0.38) SDCM <3
62443600	SM350C 50S/840 PSU PCS L1500 ALU	(0.39, 0.38) SDCM <3
62446700	SM350C 34S/840 PSD PCS L1500 ALU	(0.39, 0.38) SDCM <3
62449800	SM350C 50S/840 PSD PCS L1500 ALU	(0.39, 0.38) SDCM <3
62441200	SM350C 34S/840 PSU PCS L1500 WH	(0.39, 0.38) SDCM <3
62444300	SM350C 50S/840 PSU PCS L1500 WH	(0.39, 0.38) SDCM <3
62447400	SM350C 34S/840 PSD PCS L1500 WH	(0.39, 0.38) SDCM <3
62450400	SM350C 50S/840 PSD PCS L1500 WH	(0.39, 0.38) SDCM <3
62426900	SM350C 27S/840 WIA PCS L1200 ALU	(0.39, 0.38) SDCM <3
62427600	SM350C 27S/840 WIA PCS L1200 WH	(0.39, 0.38) SDCM <3
62429000	SM350C 40S/840 WIA PCS L1200 ALU	(0.39, 0.38) SDCM <3


Order Code	Full Product Name	Initial chromaticity
62430600	SM350C 40S/840 WIA PCS L1200 WH	(0.39, 0.38) SDCM <3
62415300	SM350C 27S/840 PSU PCS L1200 WH	(0.39, 0.38) SDCM <3
62418400	SM350C 40S/840 PSU PCS L1200 WH	(0.39, 0.38) SDCM <3
62421400	SM350C 27S/840 PSD PCS L1200 WH	(0.39, 0.38) SDCM <3
62424500	SM350C 40S/840 PSD PCS L1200 WH	(0.39, 0.38) SDCM <3
62433700	SM350C 27S/830 PSU PCS L1200 WH	(0.43, 0.40) SDCM <3
62435100	SM350C 40S/830 PSU PCS L1200 WH	(0.43, 0.40) SDCM <3
62437500	SM350C 27S/830 PSD PCS L1200 WH	(0.43, 0.40) SDCM <3
62439900	SM350C 40S/830 PSD PCS L1200 WH	(0.43, 0.40) SDCM <3
62416000	SM350C 27S/840 PSU PCS L1200 BK	(0.39, 0.38) SDCM <3
62419100	SM350C 40S/840 PSU PCS L1200 BK	(0.39, 0.38) SDCM <3
62422100	SM350C 27S/840 PSD PCS L1200 BK	(0.39, 0.38) SDCM <3
62425200	SM350C 40S/840 PSD PCS L1200 BK	(0.39, 0.38) SDCM <3
62453500	SM350X 27S/840 PSD L60L60 PCS WH	(0.39, 0.38) SDCM <3

Product Data


Order Code	Full Product Name	Product family code
62454200	SM350X 27S/840 PSD PCS N BK	SM350X
62442900	SM350C 34S/840 PSU PCS L1500 BK	SM350C
62445000	SM350C 50S/840 PSU PCS L1500 BK	SM350C
62448100	SM350C 34S/840 PSD PCS L1500 BK	SM350C
62451100	SM350C 50S/840 PSD PCS L1500 BK	SM350C
62367500	SM350C 27S/840 PSU PCS L1200 ALU	SM350C
62417700	SM350C 40S/840 PSU PCS L1200 ALU	SM350C
62420700	SM350C 27S/840 PSD PCS L1200 ALU	SM350C
62423800	SM350C 40S/840 PSD PCS L1200 ALU	SM350C
62432000	SM350C 27S/830 PSU PCS L1200 ALU	SM350C
62434400	SM350C 40S/830 PSU PCS L1200 ALU	SM350C
62436800	SM350C 27S/830 PSD PCS L1200 ALU	SM350C
62438200	SM350C 40S/830 PSD PCS L1200 ALU	SM350C
62452800	SM350X 27S/840 PSD L60L60 PCS ALU	SM350X
62440500	SM350C 34S/840 PSU PCS L1500 ALU	SM350C
62443600	SM350C 50S/840 PSU PCS L1500 ALU	SM350C
62446700	SM350C 34S/840 PSD PCS L1500 ALU	SM350C
62449800	SM350C 50S/840 PSD PCS L1500 ALU	SM350C
62441200	SM350C 34S/840 PSU PCS L1500 WH	SM350C
62444300	SM350C 50S/840 PSU PCS L1500 WH	SM350C
62447400	SM350C 34S/840 PSD PCS L1500 WH	SM350C
62450400	SM350C 50S/840 PSD PCS L1500 WH	SM350C
62426900	SM350C 27S/840 WIA PCS L1200 ALU	SM350C
62427600	SM350C 27S/840 WIA PCS L1200 WH	SM350C
62429000	SM350C 40S/840 WIA PCS L1200 ALU	SM350C

Order Code	Full Product Name	Product family code
62430600	SM350C 40S/840 WIA PCS L1200 WH	SM350C
62415300	SM350C 27S/840 PSU PCS L1200 WH	SM350C
62418400	SM350C 40S/840 PSU PCS L1200 WH	SM350C
62421400	SM350C 27S/840 PSD PCS L1200 WH	SM350C
62424500	SM350C 40S/840 PSD PCS L1200 WH	SM350C
62433700	SM350C 27S/830 PSU PCS L1200 WH	SM350C
62435100	SM350C 40S/830 PSU PCS L1200 WH	SM350C
62437500	SM350C 27S/830 PSD PCS L1200 WH	SM350C
62439900	SM350C 40S/830 PSD PCS L1200 WH	SM350C
62416000	SM350C 27S/840 PSU PCS L1200 BK	SM350C
62419100	SM350C 40S/840 PSU PCS L1200 BK	SM350C
62422100	SM350C 27S/840 PSD PCS L1200 BK	SM350C
62425200	SM350C 40S/840 PSD PCS L1200 BK	SM350C
62453500	SM350X 27S/840 PSD L60L60 PCS WH	SM350X


Polar normal diagrams




SM350CI - 910925868303




SM350CI - 910925868353




SM350CI - 910925868366




SM350CI - 910925868379




SM350CI - 910925868355




SM350CI - 910925868356




SM350CI - 910925868383




SM350CI - 910925868352




SM350CI - 910925868359




SM350CI - 910925868363




SM350CI - 910925868375




SM350CI - 910925868381




SM350CI - 910925868385




SM350CI - 910925868388




SM350CI - 910925868389




SM350CI - 910925868354




SM350CI - 910925868387




SM350CI - 910925868362




SM350CI - 910925868365




SM350CI - 910925868370




SM350CI - 910925868384




SM350CI - 910925868386




SM350CI - 910925868360




SM350CI - 910925868361




SM350CI - 910925868357




SM350CI - 910925868368




SM350CI - 910925868358




SM350CI - 910925868372




SM350CI - 910925868376




SM350CI - 910925868378




SM350CI - 910925868380




SM350CI - 910925868351




SM350CI - 910925868369




SM350CI - 910925868371




SM350CI - 910925868374




SM350CI - 910925868373



SM350CI - 910925868377



SM350CI - 910925868382



SM350CI - 910925868390