



The flexible light line

KeyLine, Surface & Suspended

These days, many office owners and office lighting designers prefer lines of light. The reason is simple. Not only do light lines come in a minimalistic design; they also offer far more choice and flexibility. Short or long lines and luminaires, standalone luminaires, different shapes and even a variety of colours; anything is possible. And with KeyLine, all these benefits come at a competitive price while still complying with office lighting norms. KeyLine is a superb light line range with a slim, minimalistic design and a high lumen output to illuminate the brightest office spaces. But with comfortable, low levels of glare it's also easy on the eye and complies with UGR19. This makes KeyLine ideal for linear applications, as well as standalone suspended or surface-mounted luminaires. A range that offers the ultimate flexibility and unlimited possibilities. KeyLine design flexibility comes in the form of different lengths, colours and light outputs – including L-shapes, as well as straight lines. All with high efficiency up to 130 lm/W, and the option to upgrade with wireless connectivity and control. Add to that attractive pricing, and with KeyLine you can also enjoy excellent value that ensures a superb total cost of ownership.

Benefits

- Suitable for office applications
- Excellent total cost of ownership
- Wide range of options to suit the demands of different offices

Features

- Comfortable, low glare: <UGR19 for the full range
- High lumen output, up to 4000lm for 1.2m version
- Interact Connectivity ready with wireless drivers
- Standard options in different lengths, colors and light outputs
- Customization options

Application

- Offices
- Retail
- Education

KeyLine, Surface & Suspended

Warnings and Safety

- KeyLine luminaires have an IP20 classification and are not protected against water ingress. We strongly recommend that the installation environment is checked for suitability.
- If – despite the IPX0 classification warning – luminaires are subject to water ingress, Philips and Signify cannot guarantee safety or prevent failure. In this case the product warranty does not apply and becomes void.

Versions



KeyLine L-corner, black

KeyLine L-corner, alu



KeyLine suspended L1500, white

KeyLine suspended L1200, bk



KeyLine L-corner, white

Dimensional drawing



KeyLine, Surface & Suspended


Product details



KeyLine line coupling, alu



KeyLine black with ceiling bracket
accessory for surface mounting



KeyLine black with coupling piece
accessory for line mounting



KeyLine_SM350C_WIA_DPP1



KeyLine line configuration, white



KeyLine SM350C, white



KeyLine configuration with L-
corner SM350X



KeyLine black with end-cap
accessory




KeyLine line coupling, white



KeyLine alu with suspension set
for suspended mounting

KeyLine, Surface & Suspended

Product details



KeyLine white line coupling with coupling piece accessory

KeyLine_SM350C_WIA_DPP3



KeyLine alu with end-cap accessory



KeyLine white with coupling piece accessory for line mounting



KeyLine structured optics UGR19 (PCS)




KeyLine line coupling, black



KeyLine SM350C, alu

KeyLine alu line coupling with coupling piece accessory



KeyLine line configuration, black

KeyLine alu with ceiling bracket accessory for surface mounting



KeyLine, Surface & Suspended

Product details



KeyLine white with suspension set for suspended mounting



KeyLine white with ceiling bracket accessory for surface mounting



KeyLine white with end-cap accessory




KeyLine alu with coupling piece accessory for line mounting



KeyLine SM350C, black



KeyLine L-corner, black



KeyLine black line coupling with coupling piece accessory



KeyLine black with suspension set for suspended mounting



KeyLine_SM350C_WIA_DPP2




KeyLine L-corner, alu

KeyLine, Surface & Suspended

Product details

KeyLine L-corner, white



General Information

Driver included	Yes
Light source replaceable	No
Number of gear units	1 unit
Service tag	Yes

Light Technical

Beam angle of light source	120 degree(s)
Color rendering index (CRI)	>80
Optic type	Medium beam

Operating and Electrical

Protection class IEC	Safety class I
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	No

Mechanical and Housing

Mech. impact protection code	IK06
Ingress protection code	IP20

Approval and Application

Ambient temperature range	+10 to +35 °C
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
62454200	SM350X 27S/840 PSD PCS N BK	4000 K	135 lm/W	2,700 lm
62442900	SM350C 34S/840 PSU PCS L1500 BK	4000 K	142 lm/W	3,400 lm
62445000	SM350C 50S/840 PSU PCS L1500 BK	4000 K	135 lm/W	5,000 lm
62448100	SM350C 34S/840 PSD PCS L1500 BK	4000 K	136 lm/W	3,400 lm
62451100	SM350C 50S/840 PSD PCS L1500 BK	4000 K	135 lm/W	5,000 lm
62367500	SM350C 27S/840 PSU PCS L1200 ALU	4000 K	138 lm/W	2,700 lm
62417700	SM350C 40S/840 PSU PCS L1200 ALU	4000 K	133 lm/W	4,000 lm
62420700	SM350C 27S/840 PSD PCS L1200 ALU	4000 K	135 lm/W	2,700 lm
62423800	SM350C 40S/840 PSD PCS L1200 ALU	4000 K	133 lm/W	4,000 lm
62432000	SM350C 27S/830 PSU PCS L1200 ALU	3000 K	132 lm/W	2,700 lm
62434400	SM350C 40S/830 PSU PCS L1200 ALU	3000 K	133 lm/W	4,000 lm
62436800	SM350C 27S/830 PSD PCS L1200 ALU	3000 K	135 lm/W	2,700 lm
62438200	SM350C 40S/830 PSD PCS L1200 ALU	3000 K	129 lm/W	4,000 lm
62452800	SM350X 27S/840 PSD L60L60 PCS ALU	4000 K	135 lm/W	2,700 lm
62440500	SM350C 34S/840 PSU PCS L1500 ALU	4000 K	142 lm/W	3,400 lm
62443600	SM350C 50S/840 PSU PCS L1500 ALU	4000 K	135 lm/W	5,000 lm
62446700	SM350C 34S/840 PSD PCS L1500 ALU	4000 K	136 lm/W	3,400 lm
62449800	SM350C 50S/840 PSD PCS L1500 ALU	4000 K	135 lm/W	5,000 lm
62441200	SM350C 34S/840 PSU PCS L1500 WH	4000 K	142 lm/W	3,400 lm

KeyLine, Surface & Suspended

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
62444300	SM350C 50S/840 PSU PCS L1500 WH	4000 K	135 lm/W	5,000 lm
62447400	SM350C 34S/840 PSD PCS L1500 WH	4000 K	136 lm/W	3,400 lm
62450400	SM350C 50S/840 PSD PCS L1500 WH	4000 K	135 lm/W	5,000 lm
62426900	SM350C 27S/840 WIA PCS L1200 ALU	4000 K	138 lm/W	2,700 lm
62427600	SM350C 27S/840 WIA PCS L1200 WH	4000 K	138 lm/W	2,700 lm
62429000	SM350C 40S/840 WIA PCS L1200 ALU	4000 K	133 lm/W	4,000 lm
62430600	SM350C 40S/840 WIA PCS L1200 WH	4000 K	133 lm/W	4,000 lm
62415300	SM350C 27S/840 PSU PCS L1200 WH	4000 K	138 lm/W	2,700 lm
62418400	SM350C 40S/840 PSU PCS L1200 WH	4000 K	133 lm/W	4,000 lm
62421400	SM350C 27S/840 PSD PCS L1200 WH	4000 K	135 lm/W	2,700 lm
62424500	SM350C 40S/840 PSD PCS L1200 WH	4000 K	133 lm/W	4,000 lm
62433700	SM350C 27S/830 PSU PCS L1200 WH	3000 K	132 lm/W	2,700 lm
62435100	SM350C 40S/830 PSU PCS L1200 WH	3000 K	133 lm/W	4,000 lm
62437500	SM350C 27S/830 PSD PCS L1200 WH	3000 K	135 lm/W	2,700 lm
62439900	SM350C 40S/830 PSD PCS L1200 WH	3000 K	129 lm/W	4,000 lm
62416000	SM350C 27S/840 PSU PCS L1200 BK	4000 K	138 lm/W	2,700 lm
62419100	SM350C 40S/840 PSU PCS L1200 BK	4000 K	133 lm/W	4,000 lm
62422100	SM350C 27S/840 PSD PCS L1200 BK	4000 K	135 lm/W	2,700 lm
62425200	SM350C 40S/840 PSD PCS L1200 BK	4000 K	133 lm/W	4,000 lm
62453500	SM350X 27S/840 PSD L60L60 PCS WH	4000 K	135 lm/W	2,700 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
62454200	SM350X 27S/840 PSD PCS N BK	21 W	62420700	SM350C 27S/840 PSD PCS L1200 ALU	21 W
62442900	SM350C 34S/840 PSU PCS L1500 BK	25 W	62423800	SM350C 40S/840 PSD PCS L1200 ALU	31 W
62445000	SM350C 50S/840 PSU PCS L1500 BK	36.5 W	62432000	SM350C 27S/830 PSU PCS L1200 ALU	20.5 W
62448100	SM350C 34S/840 PSD PCS L1500 BK	26 W	62434400	SM350C 40S/830 PSU PCS L1200 ALU	30 W
62451100	SM350C 50S/840 PSD PCS L1500 BK	38 W	62436800	SM350C 27S/830 PSD PCS L1200 ALU	21 W
62367500	SM350C 27S/840 PSU PCS L1200 ALU	20.5 W	62438200	SM350C 40S/830 PSD PCS L1200 ALU	31 W
62417700	SM350C 40S/840 PSU PCS L1200 ALU	30 W	62452800	SM350X 27S/840 PSD L60L60 PCS ALU	21 W

KeyLine, Surface & Suspended

Order Code	Full Product Name	Power Consumption
62440500	SM350C 34S/840 PSU PCS L1500 ALU	25 W
62443600	SM350C 50S/840 PSU PCS L1500 ALU	36.5 W
62446700	SM350C 34S/840 PSD PCS L1500 ALU	26 W
62449800	SM350C 50S/840 PSD PCS L1500 ALU	38 W
62441200	SM350C 34S/840 PSU PCS L1500 WH	25 W
62444300	SM350C 50S/840 PSU PCS L1500 WH	36.5 W
62447400	SM350C 34S/840 PSD PCS L1500 WH	26 W
62450400	SM350C 50S/840 PSD PCS L1500 WH	38 W
62426900	SM350C 27S/840 WIA PCS L1200 ALU	20.5 W
62427600	SM350C 27S/840 WIA PCS L1200 WH	20.5 W
62429000	SM350C 40S/840 WIA PCS L1200 ALU	30 W
62430600	SM350C 40S/840 WIA PCS L1200 WH	30 W
62415300	SM350C 27S/840 PSU PCS L1200 WH	20.5 W

Order Code	Full Product Name	Power Consumption
62418400	SM350C 40S/840 PSU PCS L1200 WH	30 W
62421400	SM350C 27S/840 PSD PCS L1200 WH	21 W
62424500	SM350C 40S/840 PSD PCS L1200 WH	31 W
62433700	SM350C 27S/830 PSU PCS L1200 WH	20.5 W
62435100	SM350C 40S/830 PSU PCS L1200 WH	30 W
62437500	SM350C 27S/830 PSD PCS L1200 WH	21 W
62439900	SM350C 40S/830 PSD PCS L1200 WH	31 W
62416000	SM350C 27S/840 PSU PCS L1200 BK	20.5 W
62419100	SM350C 40S/840 PSU PCS L1200 BK	30 W
62422100	SM350C 27S/840 PSD PCS L1200 BK	21 W
62425200	SM350C 40S/840 PSD PCS L1200 BK	31 W
62453500	SM350X 27S/840 PSD L60L60 PCS WH	21 W

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
62454200	SM350X 27S/840 PSD PCS N BK	Yes	1%
62442900	SM350C 34S/840 PSU PCS L1500 BK	No	Not applicable
62445000	SM350C 50S/840 PSU PCS L1500 BK	No	Not applicable
62448100	SM350C 34S/840 PSD PCS L1500 BK	Yes	1%
62451100	SM350C 50S/840 PSD PCS L1500 BK	Yes	1%
62367500	SM350C 27S/840 PSU PCS L1200 ALU	No	Not applicable
62417700	SM350C 40S/840 PSU PCS L1200 ALU	No	Not applicable
62420700	SM350C 27S/840 PSD PCS L1200 ALU	Yes	1%
62423800	SM350C 40S/840 PSD PCS L1200 ALU	Yes	1%
62432000	SM350C 27S/830 PSU PCS L1200 ALU	No	Not applicable
62434400	SM350C 40S/830 PSU PCS L1200 ALU	No	Not applicable
62436800	SM350C 27S/830 PSD PCS L1200 ALU	Yes	1%
62438200	SM350C 40S/830 PSD PCS L1200 ALU	Yes	1%
62452800	SM350X 27S/840 PSD L60L60 PCS ALU	Yes	1%
62440500	SM350C 34S/840 PSU PCS L1500 ALU	No	Not applicable
62443600	SM350C 50S/840 PSU PCS L1500 ALU	No	Not applicable
62446700	SM350C 34S/840 PSD PCS L1500 ALU	Yes	1%
62449800	SM350C 50S/840 PSD PCS L1500 ALU	Yes	1%
62441200	SM350C 34S/840 PSU PCS L1500 WH	No	Not applicable
62444300	SM350C 50S/840 PSU PCS L1500 WH	No	Not applicable

Order Code	Full Product Name	Dimmable	Maximum dim level
62447400	SM350C 34S/840 PSD PCS L1500 WH	Yes	1%
62450400	SM350C 50S/840 PSD PCS L1500 WH	Yes	1%
62426900	SM350C 27S/840 WIA PCS L1200 ALU	No	1%
62427600	SM350C 27S/840 WIA PCS L1200 WH	No	1%
62429000	SM350C 40S/840 WIA PCS L1200 ALU	No	1%
62430600	SM350C 40S/840 WIA PCS L1200 WH	No	1%
62415300	SM350C 27S/840 PSU PCS L1200 WH	No	Not applicable
62418400	SM350C 40S/840 PSU PCS L1200 WH	No	Not applicable
62421400	SM350C 27S/840 PSD PCS L1200 WH	Yes	1%
62424500	SM350C 40S/840 PSD PCS L1200 WH	Yes	1%
62433700	SM350C 27S/830 PSU PCS L1200 WH	No	Not applicable
62435100	SM350C 40S/830 PSU PCS L1200 WH	No	Not applicable
62437500	SM350C 27S/830 PSD PCS L1200 WH	Yes	1%
62439900	SM350C 40S/830 PSD PCS L1200 WH	Yes	1%
62416000	SM350C 27S/840 PSU PCS L1200 BK	No	Not applicable
62419100	SM350C 40S/840 PSU PCS L1200 BK	No	Not applicable
62422100	SM350C 27S/840 PSD PCS L1200 BK	Yes	1%
62425200	SM350C 40S/840 PSD PCS L1200 BK	Yes	1%
62453500	SM350X 27S/840 PSD L60L60 PCS WH	Yes	1%

Mechanical and Housing

Order Code	Full Product Name	Housing Color
62454200	SM350X 27S/840 PSD PCS N BK	Black
62442900	SM350C 34S/840 PSU PCS L1500 BK	Black
62445000	SM350C 50S/840 PSU PCS L1500 BK	Black
62448100	SM350C 34S/840 PSD PCS L1500 BK	Black
62451100	SM350C 50S/840 PSD PCS L1500 BK	Black
62367500	SM350C 27S/840 PSU PCS L1200 ALU	Aluminum
62417700	SM350C 40S/840 PSU PCS L1200 ALU	Aluminum
62420700	SM350C 27S/840 PSD PCS L1200 ALU	Aluminum
62423800	SM350C 40S/840 PSD PCS L1200 ALU	Aluminum
62432000	SM350C 27S/830 PSU PCS L1200 ALU	Aluminum

Order Code	Full Product Name	Housing Color
62434400	SM350C 40S/830 PSU PCS L1200 ALU	Aluminum
62436800	SM350C 27S/830 PSD PCS L1200 ALU	Aluminum
62438200	SM350C 40S/830 PSD PCS L1200 ALU	Aluminum
62452800	SM350X 27S/840 PSD L60L60 PCS ALU	Aluminum
62440500	SM350C 34S/840 PSU PCS L1500 ALU	Aluminum
62443600	SM350C 50S/840 PSU PCS L1500 ALU	Aluminum
62446700	SM350C 34S/840 PSD PCS L1500 ALU	Aluminum
62449800	SM350C 50S/840 PSD PCS L1500 ALU	Aluminum
62441200	SM350C 34S/840 PSU PCS L1500 WH	White
62444300	SM350C 50S/840 PSU PCS L1500 WH	White

KeyLine, Surface & Suspended

Order Code	Full Product Name	Housing Color
62447400	SM350C 34S/840 PSD PCS L1500 WH	White
62450400	SM350C 50S/840 PSD PCS L1500 WH	White
62426900	SM350C 27S/840 WIA PCS L1200 ALU	Aluminum
62427600	SM350C 27S/840 WIA PCS L1200 WH	White
62429000	SM350C 40S/840 WIA PCS L1200 ALU	Aluminum
62430600	SM350C 40S/840 WIA PCS L1200 WH	White
62415300	SM350C 27S/840 PSU PCS L1200 WH	White
62418400	SM350C 40S/840 PSU PCS L1200 WH	White
62421400	SM350C 27S/840 PSD PCS L1200 WH	White
62424500	SM350C 40S/840 PSD PCS L1200 WH	White

Order Code	Full Product Name	Housing Color
62433700	SM350C 27S/830 PSU PCS L1200 WH	White
62435100	SM350C 40S/830 PSU PCS L1200 WH	White
62437500	SM350C 27S/830 PSD PCS L1200 WH	White
62439900	SM350C 40S/830 PSD PCS L1200 WH	White
62416000	SM350C 27S/840 PSU PCS L1200 BK	Black
62419100	SM350C 40S/840 PSU PCS L1200 BK	Black
62422100	SM350C 27S/840 PSD PCS L1200 BK	Black
62425200	SM350C 40S/840 PSD PCS L1200 BK	Black
62453500	SM350X 27S/840 PSD L60L60 PCS WH	White

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
62454200	SM350X 27S/840 PSD PCS N BK	(0.39, 0.38) SDCM <3
62442900	SM350C 34S/840 PSU PCS L1500 BK	(0.39, 0.38) SDCM <3
62445000	SM350C 50S/840 PSU PCS L1500 BK	(0.39, 0.38) SDCM <3
62448100	SM350C 34S/840 PSD PCS L1500 BK	(0.39, 0.38) SDCM <3
62451100	SM350C 50S/840 PSD PCS L1500 BK	(0.39, 0.38) SDCM <3
62367500	SM350C 27S/840 PSU PCS L1200 ALU	(0.39, 0.38) SDCM <3
62417700	SM350C 40S/840 PSU PCS L1200 ALU	(0.39, 0.38) SDCM <3
62420700	SM350C 27S/840 PSD PCS L1200 ALU	(0.39, 0.38) SDCM <3
62423800	SM350C 40S/840 PSD PCS L1200 ALU	(0.39, 0.38) SDCM <3
62432000	SM350C 27S/830 PSU PCS L1200 ALU	(0.43, 0.40) SDCM <3
62434400	SM350C 40S/830 PSU PCS L1200 ALU	(0.43, 0.40) SDCM <3
62436800	SM350C 27S/830 PSD PCS L1200 ALU	(0.43, 0.40) SDCM <3
62438200	SM350C 40S/830 PSD PCS L1200 ALU	(0.43, 0.40) SDCM <3
62452800	SM350X 27S/840 PSD L60L60 PCS ALU	(0.39, 0.38) SDCM <3
62440500	SM350C 34S/840 PSU PCS L1500 ALU	(0.39, 0.38) SDCM <3
62443600	SM350C 50S/840 PSU PCS L1500 ALU	(0.39, 0.38) SDCM <3
62446700	SM350C 34S/840 PSD PCS L1500 ALU	(0.39, 0.38) SDCM <3
62449800	SM350C 50S/840 PSD PCS L1500 ALU	(0.39, 0.38) SDCM <3
62441200	SM350C 34S/840 PSU PCS L1500 WH	(0.39, 0.38) SDCM <3
62444300	SM350C 50S/840 PSU PCS L1500 WH	(0.39, 0.38) SDCM <3

Order Code	Full Product Name	Initial chromaticity
62447400	SM350C 34S/840 PSD PCS L1500 WH	(0.39, 0.38) SDCM <3
62450400	SM350C 50S/840 PSD PCS L1500 WH	(0.39, 0.38) SDCM <3
62426900	SM350C 27S/840 WIA PCS L1200 ALU	(0.39, 0.38) SDCM <3
62427600	SM350C 27S/840 WIA PCS L1200 WH	(0.39, 0.38) SDCM <3
62429000	SM350C 40S/840 WIA PCS L1200 ALU	(0.39, 0.38) SDCM <3
62430600	SM350C 40S/840 WIA PCS L1200 WH	(0.39, 0.38) SDCM <3
62415300	SM350C 27S/840 PSU PCS L1200 WH	(0.39, 0.38) SDCM <3
62418400	SM350C 40S/840 PSU PCS L1200 WH	(0.39, 0.38) SDCM <3
62421400	SM350C 27S/840 PSD PCS L1200 WH	(0.39, 0.38) SDCM <3
62424500	SM350C 40S/840 PSD PCS L1200 WH	(0.39, 0.38) SDCM <3
62433700	SM350C 27S/830 PSU PCS L1200 WH	(0.43, 0.40) SDCM <3
62435100	SM350C 40S/830 PSU PCS L1200 WH	(0.43, 0.40) SDCM <3
62437500	SM350C 27S/830 PSD PCS L1200 WH	(0.43, 0.40) SDCM <3
62439900	SM350C 40S/830 PSD PCS L1200 WH	(0.43, 0.40) SDCM <3
62416000	SM350C 27S/840 PSU PCS L1200 BK	(0.39, 0.38) SDCM <3
62419100	SM350C 40S/840 PSU PCS L1200 BK	(0.39, 0.38) SDCM <3
62422100	SM350C 27S/840 PSD PCS L1200 BK	(0.39, 0.38) SDCM <3
62425200	SM350C 40S/840 PSD PCS L1200 BK	(0.39, 0.38) SDCM <3
62453500	SM350X 27S/840 PSD L60L60 PCS WH	(0.39, 0.38) SDCM <3

Product Data

Order Code	Full Product Name	Product family code
62454200	SM350X 27S/840 PSD PCS N BK	SM350X
62442900	SM350C 34S/840 PSU PCS L1500 BK	SM350C
62445000	SM350C 50S/840 PSU PCS L1500 BK	SM350C
62448100	SM350C 34S/840 PSD PCS L1500 BK	SM350C
62451100	SM350C 50S/840 PSD PCS L1500 BK	SM350C
62367500	SM350C 27S/840 PSU PCS L1200 ALU	SM350C
62417700	SM350C 40S/840 PSU PCS L1200 ALU	SM350C
62420700	SM350C 27S/840 PSD PCS L1200 ALU	SM350C
62423800	SM350C 40S/840 PSD PCS L1200 ALU	SM350C
62432000	SM350C 27S/830 PSU PCS L1200 ALU	SM350C
62434400	SM350C 40S/830 PSU PCS L1200 ALU	SM350C
62436800	SM350C 27S/830 PSD PCS L1200 ALU	SM350C
62438200	SM350C 40S/830 PSD PCS L1200 ALU	SM350C




Order Code	Full Product Name	Product family code
62452800	SM350X 27S/840 PSD L60L60 PCS ALU	SM350X
62440500	SM350C 34S/840 PSU PCS L1500 ALU	SM350C
62443600	SM350C 50S/840 PSU PCS L1500 ALU	SM350C
62446700	SM350C 34S/840 PSD PCS L1500 ALU	SM350C
62449800	SM350C 50S/840 PSD PCS L1500 ALU	SM350C
62441200	SM350C 34S/840 PSU PCS L1500 WH	SM350C
62444300	SM350C 50S/840 PSU PCS L1500 WH	SM350C
62447400	SM350C 34S/840 PSD PCS L1500 WH	SM350C
62450400	SM350C 50S/840 PSD PCS L1500 WH	SM350C
62426900	SM350C 27S/840 WIA PCS L1200 ALU	SM350C
62427600	SM350C 27S/840 WIA PCS L1200 WH	SM350C
62429000	SM350C 40S/840 WIA PCS L1200 ALU	SM350C
62430600	SM350C 40S/840 WIA PCS L1200 WH	SM350C

KeyLine, Surface & Suspended

Order Code	Full Product Name	Product family code
62415300	SM350C 27S/840 PSU PCS L1200 WH	SM350C
62418400	SM350C 40S/840 PSU PCS L1200 WH	SM350C
62421400	SM350C 27S/840 PSD PCS L1200 WH	SM350C
62424500	SM350C 40S/840 PSD PCS L1200 WH	SM350C
62433700	SM350C 27S/830 PSU PCS L1200 WH	SM350C
62435100	SM350C 40S/830 PSU PCS L1200 WH	SM350C
62437500	SM350C 27S/830 PSD PCS L1200 WH	SM350C

Order Code	Full Product Name	Product family code
62439900	SM350C 40S/830 PSD PCS L1200 WH	SM350C
62416000	SM350C 27S/840 PSU PCS L1200 BK	SM350C
62419100	SM350C 40S/840 PSU PCS L1200 BK	SM350C
62422100	SM350C 27S/840 PSD PCS L1200 BK	SM350C
62425200	SM350C 40S/840 PSD PCS L1200 BK	SM350C
62453500	SM350X 27S/840 PSD L60L60 PCS WH	SM350X




Polar Wide Diagrams



Polar Normal (separate) - SM350CI - 910925868303

Polar Normal (separate) - SM350CI - 910925868353




Polar Normal (separate) - SM350CI - 910925868366



Polar Normal (separate) - SM350CI - 910925868379

Polar Normal (separate) - SM350CI - 910925868355

Polar Normal (separate) - SM350CI - 910925868356




Polar Normal (separate) - SM350CI - 910925868383


Polar Normal (separate) - SM350CI - 910925868352

Polar Normal (separate) - SM350CI - 910925868359


Polar Wide Diagrams




Polar Normal (separate) - SM350CI - 910925868363




Polar Normal (separate) - SM350CI - 910925868375




Polar Normal (separate) - SM350CI - 910925868381




Polar Normal (separate) - SM350CI - 910925868385




Polar Normal (separate) - SM350CI - 910925868388




Polar Normal (separate) - SM350CI - 910925868389



Polar Normal (separate) - SM350CI - 910925868354




Polar Normal (separate) - SM350CI - 910925868387




Polar Normal (separate) - SM350CI - 910925868362


Polar Wide Diagrams




Polar Normal (separate) - SM350CI - 910925868365




Polar Normal (separate) - SM350CI - 910925868370




Polar Normal (separate) - SM350CI - 910925868384




Polar Normal (separate) - SM350CI - 910925868386




Polar Normal (separate) - SM350CI - 910925868360




Polar Normal (separate) - SM350CI - 910925868361



Polar Normal (separate) - SM350CI - 910925868357




Polar Normal (separate) - SM350CI - 910925868368




Polar Normal (separate) - SM350CI - 910925868358


Polar Wide Diagrams




Polar Normal (separate) - SM350CI - 910925868372




Polar Normal (separate) - SM350CI - 910925868376




Polar Normal (separate) - SM350CI - 910925868378




Polar Normal (separate) - SM350CI - 910925868380




Polar Normal (separate) - SM350CI - 910925868351




Polar Normal (separate) - SM350CI - 910925868369



Polar Normal (separate) - SM350CI - 910925868371




Polar Normal (separate) - SM350CI - 910925868374




Polar Normal (separate) - SM350CI - 910925868373

KeyLine, Surface & Suspended


Polar Wide Diagrams



**Polar Normal (separate) - SM350CI -
910925868377**



**Polar Normal (separate) - SM350CI -
910925868382**



**Polar Normal (separate) - SM350CI -
910925868390**

