



The flexible light line

These days, many office owners and office lighting designers prefer lines of light. The reason is simple. Not only do light lines come in a minimalistic design; they also offer far more choice and flexibility. Short or long lines and luminaires, standalone luminaires, different optics including asymmetric, different shapes and even a variety of colors; anything is possible. And with KeyLine, all these benefits come at a competitive price while still complying with office lighting norms. KeyLine is a superb light line range with a slim, minimalistic design and a high lumen output to illuminate the brightest office spaces. But with comfortable, low levels of glare it's also easy on the eye and complies with UGR19. That makes KeyLine ideal for linear applications, as well as standalone suspended or surface-mounted luminaires (Accessories to be ordered separately). A range that offers the ultimate flexibility and unlimited possibilities. KeyLine design flexibility comes in the form of different lengths, colors and light outputs - including L-shapes, as well as straight lines. All with high efficiency up to 142 lm/W, and the option to upgrade with wireless connectivity and control.

Add to that attractive pricing, and with KeyLine you can also enjoy excellent value that ensures a superb total cost of ownership.

Benefits

- Suitable for office applications
- Excellent total cost of ownership
- Wide range of options to suit the demands of different offices

Applications

- Offices
- Retail
- Education

Features

- Comfortable, low glare: <UGR19 for the full range
- High lumen output, up to 4000lm for 1.2m version

Versions



- Interact Connectivity ready with wireless drivers
- Standard options in different lengths, colors and light outputs
- Customization options
- KeyLine luminaires have an IP20 classification and are not protected against water ingress. We strongly recommend that the installation environment is checked for suitability.
- If – despite the IPX0 classification warning – luminaires are subject to water ingress, Philips and Signify cannot guarantee safety or prevent failure. In this case the product warranty does not apply and becomes void.



KeyLine SP350P WIA



KeyLine suspended L1200, white




KeyLine suspended L1200, bk




KeyLine L-corner, white

Dimensional drawing



KeyLine_DD_L-corner



KeyLine_DD_linear

Product details



KeyLine line coupling, alu



KeyLine black with ceiling bracket accessory for surface mounting



KeyLine black with coupling piece accessory for line mounting



KeyLine_SM350C_WIA_DPP1



KeyLine line configuration, white



KeyLine SM350C, white



KeyLine configuration with L-corner SM350X




KeyLine black with end-cap accessory




KeyLine line coupling, white



KeyLine alu with suspension set for suspended mounting



KeyLine white line coupling with coupling piece accessory



KeyLine_SM350C_WIA_DPP3



KeyLine alu with end-cap accessory



KeyLine white with coupling piece accessory for line mounting




KeyLine structured optics
UGR19 (PCS)



KeyLine line coupling, black



KeyLine SM350C, alu



KeyLine alu line coupling with
coupling piece accessory



KeyLine line configuration,
black



KeyLine alu with ceiling
bracket accessory for surface
mounting



KeyLine white with
suspension set for suspended
mounting



KeyLine white with ceiling
bracket accessory for surface
mounting



KeyLine white with end-cap
accessory



KeyLine alu with coupling
piece accessory for line
mounting



KeyLine SM350C, black



KeyLine L-corner, black



KeyLine black line coupling
with coupling piece accessory




KeyLine black with
suspension set for suspended
mounting



KeyLine_SM350C_WIA_DPP2



KeyLine L-corner, alu



KeyLine L-corner, white

General Information

Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Service tag	Yes

Light Technical

Color rendering index (CRI)	>80
Beam angle of light source	120 degree(s)
Optic type	Medium beam

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	No
Protection class IEC	Safety class I

Mechanical and Housing

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK06 [1 J]

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	+10 to +35 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Light Technical

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)
910925868390	SM350X 27S/840 PSD PCS N BK	2,700 lm	4000 K	135 lm/W
910925868378	SM350C 34S/840 PSU PCS L1500 BK	3,400 lm	4000 K	142 lm/W
910925868381	SM350C 50S/840 PSU PCS L1500 BK	5,000 lm	4000 K	135 lm/W
910925868384	SM350C 34S/840 PSD PCS L1500 BK	3,400 lm	4000 K	136 lm/W
910925868387	SM350C 50S/840 PSD PCS L1500 BK	5,000 lm	4000 K	135 lm/W
910925868303	SM350C 27S/840 PSU PCS L1200 ALU	2,700 lm	4000 K	138 lm/W
910925868353	SM350C 40S/840 PSU PCS L1200 ALU	4,000 lm	4000 K	133 lm/W
910925868356	SM350C 27S/840 PSD PCS L1200 ALU	2,700 lm	4000 K	135 lm/W
910925868359	SM350C 40S/840 PSD PCS L1200 ALU	4,000 lm	4000 K	133 lm/W
910925868368	SM350C 27S/830 PSU PCS L1200 ALU	2,700 lm	3000 K	132 lm/W
910925868370	SM350C 40S/830 PSU PCS L1200 ALU	4,000 lm	3000 K	133 lm/W
910925868372	SM350C 27S/830 PSD PCS L1200 ALU	2,700 lm	3000 K	135 lm/W
910925868374	SM350C 40S/830 PSD PCS L1200 ALU	4,000 lm	3000 K	129 lm/W
910925868388	SM350X 27S/840 PSD L60L60 PCS ALU	2,700 lm	4000 K	135 lm/W
910925868376	SM350C 34S/840 PSU PCS L1500 ALU	3,400 lm	4000 K	142 lm/W
910925868379	SM350C 50S/840 PSU PCS L1500 ALU	5,000 lm	4000 K	135 lm/W
910925868382	SM350C 34S/840 PSD PCS L1500 ALU	3,400 lm	4000 K	136 lm/W
910925868385	SM350C 50S/840 PSD PCS L1500 ALU	5,000 lm	4000 K	135 lm/W
910925868377	SM350C 34S/840 PSU PCS L1500 WH	3,400 lm	4000 K	142 lm/W
910925868380	SM350C 50S/840 PSU PCS L1500 WH	5,000 lm	4000 K	135 lm/W
910925868383	SM350C 34S/840 PSD PCS L1500 WH	3,400 lm	4000 K	136 lm/W
910925868386	SM350C 50S/840 PSD PCS L1500 WH	5,000 lm	4000 K	135 lm/W
910925868362	SM350C 27S/840 WIA PCS L1200 ALU	2,700 lm	4000 K	135 lm/W
910925868363	SM350C 27S/840 WIA PCS L1200 WH	2,700 lm	4000 K	135 lm/W
910925868365	SM350C 40S/840 WIA PCS L1200 ALU	4,000 lm	4000 K	133 lm/W

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)
910925868366	SM350C 40S/840 WIA PCS L1200 WH	4,000 lm	4000 K	133 lm/W
910925868351	SM350C 27S/840 PSU PCS L1200 WH	2,700 lm	4000 K	138 lm/W
910925868354	SM350C 40S/840 PSU PCS L1200 WH	4,000 lm	4000 K	133 lm/W
910925868357	SM350C 27S/840 PSD PCS L1200 WH	2,700 lm	4000 K	135 lm/W
910925868360	SM350C 40S/840 PSD PCS L1200 WH	4,000 lm	4000 K	133 lm/W
910925868369	SM350C 27S/830 PSU PCS L1200 WH	2,700 lm	3000 K	132 lm/W
910925868371	SM350C 40S/830 PSU PCS L1200 WH	4,000 lm	3000 K	133 lm/W
910925868373	SM350C 27S/830 PSD PCS L1200 WH	2,700 lm	3000 K	135 lm/W
910925868375	SM350C 40S/830 PSD PCS L1200 WH	4,000 lm	3000 K	129 lm/W
910925868352	SM350C 27S/840 PSU PCS L1200 BK	2,700 lm	4000 K	138 lm/W
910925868355	SM350C 40S/840 PSU PCS L1200 BK	4,000 lm	4000 K	133 lm/W
910925868358	SM350C 27S/840 PSD PCS L1200 BK	2,700 lm	4000 K	135 lm/W
910925868361	SM350C 40S/840 PSD PCS L1200 BK	4,000 lm	4000 K	133 lm/W
910925868389	SM350X 27S/840 PSD L60L60 PCS WH	2,700 lm	4000 K	135 lm/W

Operating and Electrical

Order Code	Full Product Name	Power Consumption
910925868390	SM350X 27S/840 PSD PCS N BK	21 W
910925868378	SM350C 34S/840 PSU PCS L1500 BK	25 W
910925868381	SM350C 50S/840 PSU PCS L1500 BK	36.5 W
910925868384	SM350C 34S/840 PSD PCS L1500 BK	26 W
910925868387	SM350C 50S/840 PSD PCS L1500 BK	38 W
910925868303	SM350C 27S/840 PSU PCS L1200 ALU	20.5 W
910925868353	SM350C 40S/840 PSU PCS L1200 ALU	30 W
910925868356	SM350C 27S/840 PSD PCS L1200 ALU	21 W
910925868359	SM350C 40S/840 PSD PCS L1200 ALU	31 W
910925868368	SM350C 27S/830 PSU PCS L1200 ALU	20.5 W
910925868370	SM350C 40S/830 PSU PCS L1200 ALU	30 W
910925868372	SM350C 27S/830 PSD PCS L1200 ALU	21 W
910925868374	SM350C 40S/830 PSD PCS L1200 ALU	31 W
910925868388	SM350X 27S/840 PSD L60L60 PCS ALU	21 W
910925868376	SM350C 34S/840 PSU PCS L1500 ALU	25 W
910925868379	SM350C 50S/840 PSU PCS L1500 ALU	36.5 W
910925868382	SM350C 34S/840 PSD PCS L1500 ALU	26 W
910925868385	SM350C 50S/840 PSD PCS L1500 ALU	38 W
910925868377	SM350C 34S/840 PSU PCS L1500 WH	25 W
910925868380	SM350C 50S/840 PSU PCS L1500 WH	36.5 W
910925868383	SM350C 34S/840 PSD PCS L1500 WH	26 W
910925868386	SM350C 50S/840 PSD PCS L1500 WH	38 W
910925868362	SM350C 27S/840 WIA PCS L1200 ALU	20.5 W
910925868363	SM350C 27S/840 WIA PCS L1200 WH	20.5 W
910925868365	SM350C 40S/840 WIA PCS L1200 ALU	30 W

Order Code	Full Product Name	Power Consumption
910925868366	SM350C 40S/840 WIA PCS L1200 WH	30 W
910925868351	SM350C 27S/840 PSU PCS L1200 WH	20.5 W
910925868354	SM350C 40S/840 PSU PCS L1200 WH	30 W
910925868357	SM350C 27S/840 PSD PCS L1200 WH	21 W
910925868360	SM350C 40S/840 PSD PCS L1200 WH	31 W
910925868369	SM350C 27S/830 PSU PCS L1200 WH	20.5 W
910925868371	SM350C 40S/830 PSU PCS L1200 WH	30 W
910925868373	SM350C 27S/830 PSD PCS L1200 WH	21 W
910925868375	SM350C 40S/830 PSD PCS L1200 WH	31 W
910925868352	SM350C 27S/840 PSU PCS L1200 BK	20.5 W
910925868355	SM350C 40S/840 PSU PCS L1200 BK	30 W
910925868358	SM350C 27S/840 PSD PCS L1200 BK	21 W
910925868361	SM350C 40S/840 PSD PCS L1200 BK	31 W
910925868389	SM350X 27S/840 PSD L60L60 PCS WH	21 W

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
910925868390	SM350X 27S/840 PSD PCS N BK	Yes	1%
910925868378	SM350C 34S/840 PSU PCS L1500 BK	No	Not applicable
910925868381	SM350C 50S/840 PSU PCS L1500 BK	No	Not applicable
910925868384	SM350C 34S/840 PSD PCS L1500 BK	Yes	1%
910925868387	SM350C 50S/840 PSD PCS L1500 BK	Yes	1%
910925868303	SM350C 27S/840 PSU PCS L1200 ALU	No	Not applicable
910925868353	SM350C 40S/840 PSU PCS L1200 ALU	No	Not applicable
910925868356	SM350C 27S/840 PSD PCS L1200 ALU	Yes	1%
910925868359	SM350C 40S/840 PSD PCS L1200 ALU	Yes	1%
910925868368	SM350C 27S/830 PSU PCS L1200 ALU	No	Not applicable
910925868370	SM350C 40S/830 PSU PCS L1200 ALU	No	Not applicable
910925868372	SM350C 27S/830 PSD PCS L1200 ALU	Yes	1%
910925868374	SM350C 40S/830 PSD PCS L1200 ALU	Yes	1%
910925868388	SM350X 27S/840 PSD L60L60 PCS ALU	Yes	1%
910925868376	SM350C 34S/840 PSU PCS L1500 ALU	No	Not applicable
910925868379	SM350C 50S/840 PSU PCS L1500 ALU	No	Not applicable
910925868382	SM350C 34S/840 PSD PCS L1500 ALU	Yes	1%
910925868385	SM350C 50S/840 PSD PCS L1500 ALU	Yes	1%
910925868377	SM350C 34S/840 PSU PCS L1500 WH	No	Not applicable
910925868380	SM350C 50S/840 PSU PCS L1500 WH	No	Not applicable
910925868383	SM350C 34S/840 PSD PCS L1500 WH	Yes	1%
910925868386	SM350C 50S/840 PSD PCS L1500 WH	Yes	1%
910925868362	SM350C 27S/840 WIA PCS L1200 ALU	No	1%
910925868363	SM350C 27S/840 WIA PCS L1200 WH	No	1%
910925868365	SM350C 40S/840 WIA PCS L1200 ALU	No	1%

Order Code	Full Product Name	Dimmable	Maximum dim level
910925868366	SM350C 40S/840 WIA PCS L1200 WH	No	1%
910925868351	SM350C 27S/840 PSU PCS L1200 WH	No	Not applicable
910925868354	SM350C 40S/840 PSU PCS L1200 WH	No	Not applicable
910925868357	SM350C 27S/840 PSD PCS L1200 WH	Yes	1%
910925868360	SM350C 40S/840 PSD PCS L1200 WH	Yes	1%
910925868369	SM350C 27S/830 PSU PCS L1200 WH	No	Not applicable
910925868371	SM350C 40S/830 PSU PCS L1200 WH	No	Not applicable
910925868373	SM350C 27S/830 PSD PCS L1200 WH	Yes	1%
910925868375	SM350C 40S/830 PSD PCS L1200 WH	Yes	1%
910925868352	SM350C 27S/840 PSU PCS L1200 BK	No	Not applicable
910925868355	SM350C 40S/840 PSU PCS L1200 BK	No	Not applicable
910925868358	SM350C 27S/840 PSD PCS L1200 BK	Yes	1%
910925868361	SM350C 40S/840 PSD PCS L1200 BK	Yes	1%
910925868389	SM350X 27S/840 PSD L60L60 PCS WH	Yes	1%

Mechanical and Housing

Order Code	Full Product Name	Housing Color
910925868390	SM350X 27S/840 PSD PCS N BK	Black
910925868378	SM350C 34S/840 PSU PCS L1500 BK	Black
910925868381	SM350C 50S/840 PSU PCS L1500 BK	Black
910925868384	SM350C 34S/840 PSD PCS L1500 BK	Black
910925868387	SM350C 50S/840 PSD PCS L1500 BK	Black
910925868303	SM350C 27S/840 PSU PCS L1200 ALU	Aluminum
910925868353	SM350C 40S/840 PSU PCS L1200 ALU	Aluminum
910925868356	SM350C 27S/840 PSD PCS L1200 ALU	Aluminum
910925868359	SM350C 40S/840 PSD PCS L1200 ALU	Aluminum
910925868368	SM350C 27S/830 PSU PCS L1200 ALU	Aluminum
910925868370	SM350C 40S/830 PSU PCS L1200 ALU	Aluminum
910925868372	SM350C 27S/830 PSD PCS L1200 ALU	Aluminum
910925868374	SM350C 40S/830 PSD PCS L1200 ALU	Aluminum
910925868388	SM350X 27S/840 PSD L60L60 PCS ALU	Aluminum
910925868376	SM350C 34S/840 PSU PCS L1500 ALU	Aluminum
910925868379	SM350C 50S/840 PSU PCS L1500 ALU	Aluminum
910925868382	SM350C 34S/840 PSD PCS L1500 ALU	Aluminum
910925868385	SM350C 50S/840 PSD PCS L1500 ALU	Aluminum
910925868377	SM350C 34S/840 PSU PCS L1500 WH	White
910925868380	SM350C 50S/840 PSU PCS L1500 WH	White
910925868383	SM350C 34S/840 PSD PCS L1500 WH	White
910925868386	SM350C 50S/840 PSD PCS L1500 WH	White
910925868362	SM350C 27S/840 WIA PCS L1200 ALU	Aluminum
910925868363	SM350C 27S/840 WIA PCS L1200 WH	White
910925868365	SM350C 40S/840 WIA PCS L1200 ALU	Aluminum

Order Code	Full Product Name	Housing Color
910925868366	SM350C 40S/840 WIA PCS L1200 WH	White
910925868351	SM350C 27S/840 PSU PCS L1200 WH	White
910925868354	SM350C 40S/840 PSU PCS L1200 WH	White
910925868357	SM350C 27S/840 PSD PCS L1200 WH	White
910925868360	SM350C 40S/840 PSD PCS L1200 WH	White
910925868369	SM350C 27S/830 PSU PCS L1200 WH	White
910925868371	SM350C 40S/830 PSU PCS L1200 WH	White
910925868373	SM350C 27S/830 PSD PCS L1200 WH	White
910925868375	SM350C 40S/830 PSD PCS L1200 WH	White
910925868352	SM350C 27S/840 PSU PCS L1200 BK	Black
910925868355	SM350C 40S/840 PSU PCS L1200 BK	Black
910925868358	SM350C 27S/840 PSD PCS L1200 BK	Black
910925868361	SM350C 40S/840 PSD PCS L1200 BK	Black
910925868389	SM350X 27S/840 PSD L60L60 PCS WH	White

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910925868390	SM350X 27S/840 PSD PCS N BK	(0.39, 0.38) SDCM <3
910925868378	SM350C 34S/840 PSU PCS L1500 BK	(0.39, 0.38) SDCM <3
910925868381	SM350C 50S/840 PSU PCS L1500 BK	(0.39, 0.38) SDCM <3
910925868384	SM350C 34S/840 PSD PCS L1500 BK	(0.39, 0.38) SDCM <3
910925868387	SM350C 50S/840 PSD PCS L1500 BK	(0.39, 0.38) SDCM <3
910925868303	SM350C 27S/840 PSU PCS L1200 ALU	(0.39, 0.38) SDCM <3
910925868353	SM350C 40S/840 PSU PCS L1200 ALU	(0.39, 0.38) SDCM <3
910925868356	SM350C 27S/840 PSD PCS L1200 ALU	(0.39, 0.38) SDCM <3
910925868359	SM350C 40S/840 PSD PCS L1200 ALU	(0.39, 0.38) SDCM <3
910925868368	SM350C 27S/830 PSU PCS L1200 ALU	(0.43, 0.40) SDCM <3
910925868370	SM350C 40S/830 PSU PCS L1200 ALU	(0.43, 0.40) SDCM <3
910925868372	SM350C 27S/830 PSD PCS L1200 ALU	(0.43, 0.40) SDCM <3
910925868374	SM350C 40S/830 PSD PCS L1200 ALU	(0.43, 0.40) SDCM <3
910925868388	SM350X 27S/840 PSD L60L60 PCS ALU	(0.39, 0.38) SDCM <3
910925868376	SM350C 34S/840 PSU PCS L1500 ALU	(0.39, 0.38) SDCM <3
910925868379	SM350C 50S/840 PSU PCS L1500 ALU	(0.39, 0.38) SDCM <3
910925868382	SM350C 34S/840 PSD PCS L1500 ALU	(0.39, 0.38) SDCM <3
910925868385	SM350C 50S/840 PSD PCS L1500 ALU	(0.39, 0.38) SDCM <3
910925868377	SM350C 34S/840 PSU PCS L1500 WH	(0.39, 0.38) SDCM <3
910925868380	SM350C 50S/840 PSU PCS L1500 WH	(0.39, 0.38) SDCM <3
910925868383	SM350C 34S/840 PSD PCS L1500 WH	(0.39, 0.38) SDCM <3
910925868386	SM350C 50S/840 PSD PCS L1500 WH	(0.39, 0.38) SDCM <3
910925868362	SM350C 27S/840 WIA PCS L1200 ALU	(0.39, 0.38) SDCM <3
910925868363	SM350C 27S/840 WIA PCS L1200 WH	(0.39, 0.38) SDCM <3
910925868365	SM350C 40S/840 WIA PCS L1200 ALU	(0.39, 0.38) SDCM <3


Order Code	Full Product Name	Initial chromaticity
910925868366	SM350C 40S/840 WIA PCS L1200 WH	(0.39, 0.38) SDCM <3
910925868351	SM350C 27S/840 PSU PCS L1200 WH	(0.39, 0.38) SDCM <3
910925868354	SM350C 40S/840 PSU PCS L1200 WH	(0.39, 0.38) SDCM <3
910925868357	SM350C 27S/840 PSD PCS L1200 WH	(0.39, 0.38) SDCM <3
910925868360	SM350C 40S/840 PSD PCS L1200 WH	(0.39, 0.38) SDCM <3
910925868369	SM350C 27S/830 PSU PCS L1200 WH	(0.43, 0.40) SDCM <3
910925868371	SM350C 40S/830 PSU PCS L1200 WH	(0.43, 0.40) SDCM <3
910925868373	SM350C 27S/830 PSD PCS L1200 WH	(0.43, 0.40) SDCM <3
910925868375	SM350C 40S/830 PSD PCS L1200 WH	(0.43, 0.40) SDCM <3
910925868352	SM350C 27S/840 PSU PCS L1200 BK	(0.39, 0.38) SDCM <3
910925868355	SM350C 40S/840 PSU PCS L1200 BK	(0.39, 0.38) SDCM <3
910925868358	SM350C 27S/840 PSD PCS L1200 BK	(0.39, 0.38) SDCM <3
910925868361	SM350C 40S/840 PSD PCS L1200 BK	(0.39, 0.38) SDCM <3
910925868389	SM350X 27S/840 PSD L60L60 PCS WH	(0.39, 0.38) SDCM <3

Product Data


Order Code	Full Product Name	Product family code
910925868390	SM350X 27S/840 PSD PCS N BK	SM350X
910925868378	SM350C 34S/840 PSU PCS L1500 BK	SM350C
910925868381	SM350C 50S/840 PSU PCS L1500 BK	SM350C
910925868384	SM350C 34S/840 PSD PCS L1500 BK	SM350C
910925868387	SM350C 50S/840 PSD PCS L1500 BK	SM350C
910925868303	SM350C 27S/840 PSU PCS L1200 ALU	SM350C
910925868353	SM350C 40S/840 PSU PCS L1200 ALU	SM350C
910925868356	SM350C 27S/840 PSD PCS L1200 ALU	SM350C
910925868359	SM350C 40S/840 PSD PCS L1200 ALU	SM350C
910925868368	SM350C 27S/830 PSU PCS L1200 ALU	SM350C
910925868370	SM350C 40S/830 PSU PCS L1200 ALU	SM350C
910925868372	SM350C 27S/830 PSD PCS L1200 ALU	SM350C
910925868374	SM350C 40S/830 PSD PCS L1200 ALU	SM350C
910925868388	SM350X 27S/840 PSD L60L60 PCS ALU	SM350X
910925868376	SM350C 34S/840 PSU PCS L1500 ALU	SM350C
910925868379	SM350C 50S/840 PSU PCS L1500 ALU	SM350C
910925868382	SM350C 34S/840 PSD PCS L1500 ALU	SM350C
910925868385	SM350C 50S/840 PSD PCS L1500 ALU	SM350C
910925868377	SM350C 34S/840 PSU PCS L1500 WH	SM350C
910925868380	SM350C 50S/840 PSU PCS L1500 WH	SM350C
910925868383	SM350C 34S/840 PSD PCS L1500 WH	SM350C
910925868386	SM350C 50S/840 PSD PCS L1500 WH	SM350C
910925868362	SM350C 27S/840 WIA PCS L1200 ALU	SM350C
910925868363	SM350C 27S/840 WIA PCS L1200 WH	SM350C
910925868365	SM350C 40S/840 WIA PCS L1200 ALU	SM350C

Order Code	Full Product Name	Product family code
910925868366	SM350C 40S/840 WIA PCS L1200 WH	SM350C
910925868351	SM350C 27S/840 PSU PCS L1200 WH	SM350C
910925868354	SM350C 40S/840 PSU PCS L1200 WH	SM350C
910925868357	SM350C 27S/840 PSD PCS L1200 WH	SM350C
910925868360	SM350C 40S/840 PSD PCS L1200 WH	SM350C
910925868369	SM350C 27S/830 PSU PCS L1200 WH	SM350C
910925868371	SM350C 40S/830 PSU PCS L1200 WH	SM350C
910925868373	SM350C 27S/830 PSD PCS L1200 WH	SM350C
910925868375	SM350C 40S/830 PSD PCS L1200 WH	SM350C
910925868352	SM350C 27S/840 PSU PCS L1200 BK	SM350C
910925868355	SM350C 40S/840 PSU PCS L1200 BK	SM350C
910925868358	SM350C 27S/840 PSD PCS L1200 BK	SM350C
910925868361	SM350C 40S/840 PSD PCS L1200 BK	SM350C
910925868389	SM350X 27S/840 PSD L60L60 PCS WH	SM350X


Polar normal diagrams




SM350CI - 910925868303




SM350CI - 910925868353




SM350CI - 910925868366




SM350CI - 910925868379




SM350CI - 910925868355




SM350CI - 910925868356




SM350CI - 910925868383




SM350CI - 910925868352




SM350CI - 910925868359




SM350CI - 910925868363




SM350CI - 910925868375




SM350CI - 910925868381




SM350CI - 910925868385




SM350CI - 910925868388




SM350CI - 910925868389




SM350CI - 910925868354




SM350CI - 910925868387




SM350CI - 910925868362




SM350CI - 910925868365




SM350CI - 910925868370




SM350CI - 910925868384




SM350CI - 910925868386




SM350CI - 910925868360




SM350CI - 910925868361




SM350CI - 910925868357




SM350CI - 910925868368




SM350CI - 910925868358




SM350CI - 910925868372




SM350CI - 910925868376




SM350CI - 910925868378




SM350CI - 910925868380




SM350CI - 910925868351




SM350CI - 910925868369




SM350CI - 910925868371




SM350CI - 910925868374




SM350CI - 910925868373



SM350CI - 910925868377



SM350CI - 910925868382



SM350CI - 910925868390