

The flexible light line

KeyLine, Suspended

These days, many office owners and office lighting designers prefer lines of light. The reason is simple. Not only do light lines come in a minimalistic design; they also offer far more choice and flexibility. Short or long lines and luminaires, standalone luminaires, different optics including asymmetric, different shapes and even a variety of colors; anything is possible. And with KeyLine, all these benefits come at a competitive price while still complying with office lighting norms. KeyLine is a superb light line range with a slim, minimalistic design and a high lumen output to illuminate the brightest office spaces. But with comfortable, low levels of glare it's also easy on the eye and complies with UGR19. That makes KeyLine ideal for linear applications, as well as standalone suspended or surface-mounted luminaires. A range that offers the ultimate flexibility and unlimited possibilities. KeyLine design flexibility comes in the form of different lengths, colors and light outputs - including L-shapes, as well as straight lines. All with high efficiency up to 142 lm/W, and the option to upgrade with wireless connectivity and control. Add to that attractive pricing, and with KeyLine you can also enjoy excellent value that ensures a superb total cost of ownership.

Benefits

- Suitable for office applications
- Excellent total cost of ownership
- Wide range of options to suit the demands of different offices

Features

- Comfortable, low glare: <UGR19 for the full range
- High lumen output, up to 4000lm for 1.2m version
- Interact Connectivity ready with wireless drivers
- Standard options in different lengths, colors and light outputs
- Customization options

KeyLine, Suspended

Application

- Offices
- Retail
- Education

Warnings and Safety

- KeyLine luminaires have an IP20 classification and are not protected against water ingress. We strongly recommend that the installation environment is checked for suitability.
- If – despite the IPX0 classification warning – luminaires are subject to water ingress, Philips and Signify cannot guarantee safety or prevent failure. In this case the product warranty does not apply and becomes void.

Versions



KeyLine L-corner, black



KeyLine L-corner, alu





KeyLine suspended L1200, white



KeyLine L-corner, white

Dimensional drawing





Product details




KeyLine line coupling, alu



KeyLine black with ceiling bracket accessory for surface mounting

KeyLine, Suspended

Product details



KeyLine black with coupling piece accessory for line mounting



KeyLine_SM350C_WIA_DPP1




KeyLine line configuration, white



KeyLine SM350C, white



KeyLine configuration with L-corner SM350X




KeyLine black with end-cap accessory



KeyLine line coupling, white



KeyLine alu with suspension set for suspended mounting



KeyLine white line coupling with coupling piece accessory



KeyLine_SM350C_WIA_DPP3



KeyLine alu with end-cap accessory

KeyLine, Suspended

Product details



KeyLine white with coupling piece accessory for line mounting



KeyLine structured optics UGR19 (PCS)



KeyLine line coupling, black



KeyLine SM350C, alu



KeyLine alu line coupling with coupling piece accessory



KeyLine line configuration, black

KeyLine alu with ceiling bracket accessory for surface mounting





KeyLine white with suspension set for suspended mounting

KeyLine white with ceiling bracket accessory for surface mounting



KeyLine, Suspended

Product details



KeyLine white with end-cap accessory




KeyLine alu with coupling piece accessory for line mounting



KeyLine SM350C, black



KeyLine L-corner, black



KeyLine black line coupling with coupling piece accessory




KeyLine black with suspension set for suspended mounting



KeyLine_SM350C_WIA_DPP2



KeyLine L-corner, alu



KeyLine L-corner, white

KeyLine, Suspended

General Information	
CE mark	Yes
Driver included	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Light source replaceable	No
Number of gear units	1 unit
Light Technical	
Beam angle of light source	120 degree(s)
Color rendering index (CRI)	>80
Optic type	Medium beam
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Temperature	
Ambient temperature range	+10 to +35 °C
Approval and Application	
Protection class IEC	Safety class I
Mech. impact protection code	IK06
Ingress protection code	IP20
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Application Conditions	
Suitable for random switching	No

General Information

Order Code	Full Product Name	Glow-wire test	Product family code
910925868390	SM350X 27S/840 PSD L60L60 PCS BK	Temperature 850 °C, duration 30 s	SM350X
910925868378	SM350C 34S/840 PSU PCS L1500 BK	Temperature 850 °C, duration 30 s	SM350C
910925868381	SM350C 50S/840 PSU PCS L1500 BK	Temperature 850 °C, duration 30 s	SM350C
910925868384	SM350C 34S/840 PSD PCS L1500 BK	Temperature 850 °C, duration 30 s	SM350C
910925868387	SM350C 50S/840 PSD PCS L1500 BK	Temperature 850 °C, duration 30 s	SM350C
910925868303	SM350C 27S/840 PSU PCS L1200 ALU	Temperature 850 °C, duration 30 s	SM350C
910925868353	SM350C 40S/840 PSU PCS L1200 ALU	Temperature 850 °C, duration 30 s	SM350C
910925868356	SM350C 27S/840 PSD PCS L1200 ALU	Temperature 850 °C, duration 30 s	SM350C
910925868359	SM350C 40S/840 PSD PCS L1200 ALU	Temperature 850 °C, duration 30 s	SM350C
910925868368	SM350C 27S/830 PSU PCS L1200 ALU	Temperature 850 °C, duration 30 s	SM350C
910925868370	SM350C 40S/830 PSU PCS L1200 ALU	Temperature 850 °C, duration 30 s	SM350C
910925868372	SM350C 27S/830 PSD PCS L1200 ALU	Temperature 850 °C, duration 30 s	SM350C
910925868374	SM350C 40S/830 PSD PCS L1200 ALU	Temperature 850 °C, duration 30 s	SM350C
910925868388	SM350X 27S/840 PSD L60L60 PCS ALU	Temperature 850 °C, duration 30 s	SM350X
910925868376	SM350C 34S/840 PSU PCS L1500 ALU	Temperature 850 °C, duration 30 s	SM350C
910925868379	SM350C 50S/840 PSU PCS L1500 ALU	Temperature 850 °C, duration 30 s	SM350C
910925868382	SM350C 34S/840 PSD PCS L1500 ALU	Temperature 850 °C, duration 30 s	SM350C
910925868385	SM350C 50S/840 PSD PCS L1500 ALU	Temperature 850 °C, duration 30 s	SM350C
910925868377	SM350C 34S/840 PSU PCS L1500 WH	Temperature 850 °C, duration 30 s	SM350C
910925868380	SM350C 50S/840 PSU PCS L1500 WH	Temperature 850 °C, duration 30 s	SM350C
910925868383	SM350C 34S/840 PSD PCS L1500 WH	Temperature 850 °C, duration 30 s	SM350C
910925868386	SM350C 50S/840 PSD PCS L1500 WH	Temperature 850 °C, duration 30 s	SM350C
910925868362	SM350C 27S/840 WIA PCS L1200 ALU	Temperature 650 °C, duration 30 s	SM350C
910925868363	SM350C 27S/840 WIA PCS L1200 WH	Temperature 650 °C, duration 30 s	SM350C
910925868364	SM350C 27S/840 WIA PCS L1200 BK	Temperature 650 °C, duration 30 s	SM350C
910925868365	SM350C 40S/840 WIA PCS L1200 ALU	Temperature 650 °C, duration 30 s	SM350C
910925868366	SM350C 40S/840 WIA PCS L1200 WH	Temperature 650 °C, duration 30 s	SM350C
910925868367	SM350C 40S/840 WIA PCS L1200 BK	Temperature 650 °C, duration 30 s	SM350C
910925868351	SM350C 27S/840 PSU PCS L1200 WH	Temperature 850 °C, duration 30 s	SM350C
910925868354	SM350C 40S/840 PSU PCS L1200 WH	Temperature 850 °C, duration 30 s	SM350C
910925868357	SM350C 27S/840 PSD PCS L1200 WH	Temperature 850 °C, duration 30 s	SM350C
910925868360	SM350C 40S/840 PSD PCS L1200 WH	Temperature 850 °C, duration 30 s	SM350C
910925868369	SM350C 27S/830 PSU PCS L1200 WH	Temperature 850 °C, duration 30 s	SM350C
910925868371	SM350C 40S/830 PSU PCS L1200 WH	Temperature 850 °C, duration 30 s	SM350C
910925868373	SM350C 27S/830 PSD PCS L1200 WH	Temperature 850 °C, duration 30 s	SM350C
910925868375	SM350C 40S/830 PSD PCS L1200 WH	Temperature 850 °C, duration 30 s	SM350C
910925868352	SM350C 27S/840 PSU PCS L1200 BK	Temperature 850 °C, duration 30 s	SM350C
910925868355	SM350C 40S/840 PSU PCS L1200 BK	Temperature 850 °C, duration 30 s	SM350C
910925868358	SM350C 27S/840 PSD PCS L1200 BK	Temperature 850 °C, duration 30 s	SM350C
910925868361	SM350C 40S/840 PSD PCS L1200 BK	Temperature 850 °C, duration 30 s	SM350C
910925868389	SM350X 27S/840 PSD L60L60 PCS WH	Temperature 850 °C, duration 30 s	SM350X

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910925868390	SM350X 27S/840 PSD L60L60 PCS BK	4000 K	138 lm/W	2,900 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910925868378	SM350C 34S/840 PSU PCS L1500 BK	4000 K	144 lm/W	3,600 lm

KeyLine, Suspended

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910925868381	SM350C 50S/840 PSU PCS L1500 BK	4000 K	142 lm/W	5,200 lm
910925868384	SM350C 34S/840 PSD PCS L1500 BK	4000 K	138 lm/W	3,600 lm
910925868387	SM350C 50S/840 PSD PCS L1500 BK	4000 K	137 lm/W	5,200 lm
910925868303	SM350C 27S/840 PSU PCS L1200 ALU	4000 K	141 lm/W	2,900 lm
910925868353	SM350C 40S/840 PSU PCS L1200 ALU	4000 K	140 lm/W	4,200 lm
910925868356	SM350C 27S/840 PSD PCS L1200 ALU	4000 K	138 lm/W	2,900 lm
910925868359	SM350C 40S/840 PSD PCS L1200 ALU	4000 K	135 lm/W	4,200 lm
910925868368	SM350C 27S/830 PSU PCS L1200 ALU	3000 K	132 lm/W	2,600 lm
910925868370	SM350C 40S/830 PSU PCS L1200 ALU	3000 K	133 lm/W	4,000 lm
910925868372	SM350C 27S/830 PSD PCS L1200 ALU	3000 K	130 lm/W	2,600 lm
910925868374	SM350C 40S/830 PSD PCS L1200 ALU	3000 K	129 lm/W	4,000 lm
910925868388	SM350X 27S/840 PSD L60L60 PCS ALU	4000 K	138 lm/W	2,900 lm
910925868376	SM350C 34S/840 PSU PCS L1500 ALU	4000 K	144 lm/W	3,600 lm
910925868379	SM350C 50S/840 PSU PCS L1500 ALU	4000 K	142 lm/W	5,200 lm
910925868382	SM350C 34S/840 PSD PCS L1500 ALU	4000 K	138 lm/W	3,600 lm
910925868385	SM350C 50S/840 PSD PCS L1500 ALU	4000 K	137 lm/W	5,200 lm
910925868377	SM350C 34S/840 PSU PCS L1500 WH	4000 K	144 lm/W	3,600 lm
910925868380	SM350C 50S/840 PSU PCS L1500 WH	4000 K	142 lm/W	5,200 lm
910925868383	SM350C 34S/840 PSD PCS L1500 WH	4000 K	138 lm/W	3,600 lm
910925868386	SM350C 50S/840 PSD PCS L1500 WH	4000 K	137 lm/W	5,200 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910925868362	SM350C 27S/840 WIA PCS L1200 ALU	4000 K	141 lm/W	2,900 lm
910925868363	SM350C 27S/840 WIA PCS L1200 WH	4000 K	141 lm/W	2,900 lm
910925868364	SM350C 27S/840 WIA PCS L1200 BK	4000 K	141 lm/W	2,900 lm
910925868365	SM350C 40S/840 WIA PCS L1200 ALU	4000 K	140 lm/W	4,200 lm
910925868366	SM350C 40S/840 WIA PCS L1200 WH	4000 K	140 lm/W	4,200 lm
910925868367	SM350C 40S/840 WIA PCS L1200 BK	4000 K	140 lm/W	4,200 lm
910925868351	SM350C 27S/840 PSU PCS L1200 WH	4000 K	141 lm/W	2,900 lm
910925868354	SM350C 40S/840 PSU PCS L1200 WH	4000 K	140 lm/W	4,200 lm
910925868357	SM350C 27S/840 PSD PCS L1200 WH	4000 K	138 lm/W	2,900 lm
910925868360	SM350C 40S/840 PSD PCS L1200 WH	4000 K	135 lm/W	4,200 lm
910925868369	SM350C 27S/830 PSU PCS L1200 WH	3000 K	132 lm/W	2,600 lm
910925868371	SM350C 40S/830 PSU PCS L1200 WH	3000 K	133 lm/W	4,000 lm
910925868373	SM350C 27S/830 PSD PCS L1200 WH	3000 K	130 lm/W	2,600 lm
910925868375	SM350C 40S/830 PSD PCS L1200 WH	3000 K	129 lm/W	4,000 lm
910925868352	SM350C 27S/840 PSU PCS L1200 BK	4000 K	141 lm/W	2,900 lm
910925868355	SM350C 40S/840 PSU PCS L1200 BK	4000 K	140 lm/W	4,200 lm
910925868358	SM350C 27S/840 PSD PCS L1200 BK	4000 K	138 lm/W	2,900 lm
910925868361	SM350C 40S/840 PSD PCS L1200 BK	4000 K	135 lm/W	4,200 lm
910925868389	SM350X 27S/840 PSD L60L60 PCS WH	4000 K	138 lm/W	2,900 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
910925868390	SM350X 27S/840 PSD L60L60 PCS BK	21 W
910925868378	SM350C 34S/840 PSU PCS L1500 BK	25 W
910925868381	SM350C 50S/840 PSU PCS L1500 BK	36.5 W
910925868384	SM350C 34S/840 PSD PCS L1500 BK	26 W
910925868387	SM350C 50S/840 PSD PCS L1500 BK	38 W

Order Code	Full Product Name	Power Consumption
910925868303	SM350C 27S/840 PSU PCS L1200 ALU	20.5 W
910925868353	SM350C 40S/840 PSU PCS L1200 ALU	30 W
910925868356	SM350C 27S/840 PSD PCS L1200 ALU	21 W
910925868359	SM350C 40S/840 PSD PCS L1200 ALU	31 W
910925868368	SM350C 27S/830 PSU PCS L1200 ALU	20.5 W

KeyLine, Suspended

Order Code	Full Product Name	Power Consumption
910925868370	SM350C 40S/830 PSU PCS L1200 ALU	30 W
910925868372	SM350C 27S/830 PSD PCS L1200 ALU	21 W
910925868374	SM350C 40S/830 PSD PCS L1200 ALU	31 W
910925868388	SM350X 27S/840 PSD L60L60 PCS ALU	21 W
910925868376	SM350C 34S/840 PSU PCS L1500 ALU	25 W
910925868379	SM350C 50S/840 PSU PCS L1500 ALU	36.5 W
910925868382	SM350C 34S/840 PSD PCS L1500 ALU	26 W
910925868385	SM350C 50S/840 PSD PCS L1500 ALU	38 W
910925868377	SM350C 34S/840 PSU PCS L1500 WH	25 W
910925868380	SM350C 50S/840 PSU PCS L1500 WH	36.5 W
910925868383	SM350C 34S/840 PSD PCS L1500 WH	26 W
910925868386	SM350C 50S/840 PSD PCS L1500 WH	38 W
910925868362	SM350C 27S/840 WIA PCS L1200 ALU	20.5 W
910925868363	SM350C 27S/840 WIA PCS L1200 WH	20.5 W
910925868364	SM350C 27S/840 WIA PCS L1200 BK	20.5 W
910925868365	SM350C 40S/840 WIA PCS L1200 ALU	30 W

Order Code	Full Product Name	Power Consumption
910925868366	SM350C 40S/840 WIA PCS L1200 WH	30 W
910925868367	SM350C 40S/840 WIA PCS L1200 BK	30 W
910925868351	SM350C 27S/840 PSU PCS L1200 WH	20.5 W
910925868354	SM350C 40S/840 PSU PCS L1200 WH	30 W
910925868357	SM350C 27S/840 PSD PCS L1200 WH	21 W
910925868360	SM350C 40S/840 PSD PCS L1200 WH	31 W
910925868369	SM350C 27S/830 PSU PCS L1200 WH	20.5 W
910925868371	SM350C 40S/830 PSU PCS L1200 WH	30 W
910925868373	SM350C 27S/830 PSD PCS L1200 WH	21 W
910925868375	SM350C 40S/830 PSD PCS L1200 WH	31 W
910925868352	SM350C 27S/840 PSU PCS L1200 BK	20.5 W
910925868355	SM350C 40S/840 PSU PCS L1200 BK	30 W
910925868358	SM350C 27S/840 PSD PCS L1200 BK	21 W
910925868361	SM350C 40S/840 PSD PCS L1200 BK	31 W
910925868389	SM350X 27S/840 PSD L60L60 PCS WH	21 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
910925868390	SM350X 27S/840 PSD L60L60 PCS BK	Yes
910925868378	SM350C 34S/840 PSU PCS L1500 BK	No
910925868381	SM350C 50S/840 PSU PCS L1500 BK	No
910925868384	SM350C 34S/840 PSD PCS L1500 BK	Yes
910925868387	SM350C 50S/840 PSD PCS L1500 BK	Yes
910925868303	SM350C 27S/840 PSU PCS L1200 ALU	No
910925868353	SM350C 40S/840 PSU PCS L1200 ALU	No
910925868356	SM350C 27S/840 PSD PCS L1200 ALU	Yes
910925868359	SM350C 40S/840 PSD PCS L1200 ALU	Yes
910925868368	SM350C 27S/830 PSU PCS L1200 ALU	No
910925868370	SM350C 40S/830 PSU PCS L1200 ALU	No
910925868372	SM350C 27S/830 PSD PCS L1200 ALU	Yes
910925868374	SM350C 40S/830 PSD PCS L1200 ALU	Yes
910925868388	SM350X 27S/840 PSD L60L60 PCS ALU	Yes
910925868376	SM350C 34S/840 PSU PCS L1500 ALU	No
910925868379	SM350C 50S/840 PSU PCS L1500 ALU	No
910925868382	SM350C 34S/840 PSD PCS L1500 ALU	Yes
910925868385	SM350C 50S/840 PSD PCS L1500 ALU	Yes
910925868377	SM350C 34S/840 PSU PCS L1500 WH	No
910925868380	SM350C 50S/840 PSU PCS L1500 WH	No
910925868383	SM350C 34S/840 PSD PCS L1500 WH	Yes

Order Code	Full Product Name	Dimmable
910925868386	SM350C 50S/840 PSD PCS L1500 WH	Yes
910925868362	SM350C 27S/840 WIA PCS L1200 ALU	Yes
910925868363	SM350C 27S/840 WIA PCS L1200 WH	Yes
910925868364	SM350C 27S/840 WIA PCS L1200 BK	Yes
910925868365	SM350C 40S/840 WIA PCS L1200 ALU	Yes
910925868366	SM350C 40S/840 WIA PCS L1200 WH	Yes
910925868367	SM350C 40S/840 WIA PCS L1200 BK	Yes
910925868351	SM350C 27S/840 PSU PCS L1200 WH	No
910925868354	SM350C 40S/840 PSU PCS L1200 WH	No
910925868357	SM350C 27S/840 PSD PCS L1200 WH	Yes
910925868360	SM350C 40S/840 PSD PCS L1200 WH	Yes
910925868369	SM350C 27S/830 PSU PCS L1200 WH	No
910925868371	SM350C 40S/830 PSU PCS L1200 WH	No
910925868373	SM350C 27S/830 PSD PCS L1200 WH	Yes
910925868375	SM350C 40S/830 PSD PCS L1200 WH	Yes
910925868352	SM350C 27S/840 PSU PCS L1200 BK	No
910925868355	SM350C 40S/840 PSU PCS L1200 BK	No
910925868358	SM350C 27S/840 PSD PCS L1200 BK	Yes
910925868361	SM350C 40S/840 PSD PCS L1200 BK	Yes
910925868389	SM350X 27S/840 PSD L60L60 PCS WH	Yes

Mechanical and Housing

Order Code	Full Product Name	Housing Color
910925868390	SM350X 27S/840 PSD L60L60 PCS BK	Black RAL 9004
910925868378	SM350C 34S/840 PSU PCS L1500 BK	Black RAL 9004
910925868381	SM350C 50S/840 PSU PCS L1500 BK	Black RAL 9004
910925868384	SM350C 34S/840 PSD PCS L1500 BK	Black RAL 9004
910925868387	SM350C 50S/840 PSD PCS L1500 BK	Black RAL 9004
910925868303	SM350C 27S/840 PSU PCS L1200 ALU	Aluminum

Order Code	Full Product Name	Housing Color
910925868353	SM350C 40S/840 PSU PCS L1200 ALU	Aluminum
910925868356	SM350C 27S/840 PSD PCS L1200 ALU	Aluminum
910925868359	SM350C 40S/840 PSD PCS L1200 ALU	Aluminum
910925868368	SM350C 27S/830 PSU PCS L1200 ALU	Aluminum
910925868370	SM350C 40S/830 PSU PCS L1200 ALU	Aluminum
910925868372	SM350C 27S/830 PSD PCS L1200 ALU	Aluminum

KeyLine, Suspended

Order Code	Full Product Name	Housing Color
910925868374	SM350C 40S/830 PSD PCS L1200 ALU	Aluminum
910925868388	SM350X 27S/840 PSD L60L60 PCS ALU	Aluminum
910925868376	SM350C 34S/840 PSU PCS L1500 ALU	Aluminum
910925868379	SM350C 50S/840 PSU PCS L1500 ALU	Aluminum
910925868382	SM350C 34S/840 PSD PCS L1500 ALU	Aluminum
910925868385	SM350C 50S/840 PSD PCS L1500 ALU	Aluminum
910925868377	SM350C 34S/840 PSU PCS L1500 WH	White RAL 9003
910925868380	SM350C 50S/840 PSU PCS L1500 WH	White RAL 9003
910925868383	SM350C 34S/840 PSD PCS L1500 WH	White RAL 9003
910925868386	SM350C 50S/840 PSD PCS L1500 WH	White RAL 9003
910925868362	SM350C 27S/840 WIA PCS L1200 ALU	Aluminum
910925868363	SM350C 27S/840 WIA PCS L1200 WH	White RAL 9003
910925868364	SM350C 27S/840 WIA PCS L1200 BK	Black RAL 9004
910925868365	SM350C 40S/840 WIA PCS L1200 ALU	Aluminum
910925868366	SM350C 40S/840 WIA PCS L1200 WH	White RAL 9003

Order Code	Full Product Name	Housing Color
910925868367	SM350C 40S/840 WIA PCS L1200 BK	Black RAL 9004
910925868351	SM350C 27S/840 PSU PCS L1200 WH	White RAL 9003
910925868354	SM350C 40S/840 PSU PCS L1200 WH	White RAL 9003
910925868357	SM350C 27S/840 PSD PCS L1200 WH	White RAL 9003
910925868360	SM350C 40S/840 PSD PCS L1200 WH	White RAL 9003
910925868369	SM350C 27S/830 PSU PCS L1200 WH	White RAL 9003
910925868371	SM350C 40S/830 PSU PCS L1200 WH	White RAL 9003
910925868373	SM350C 27S/830 PSD PCS L1200 WH	White RAL 9003
910925868375	SM350C 40S/830 PSD PCS L1200 WH	White RAL 9003
910925868352	SM350C 27S/840 PSU PCS L1200 BK	Black RAL 9004
910925868355	SM350C 40S/840 PSU PCS L1200 BK	Black RAL 9004
910925868358	SM350C 27S/840 PSD PCS L1200 BK	Black RAL 9004
910925868361	SM350C 40S/840 PSD PCS L1200 BK	Black RAL 9004
910925868389	SM350X 27S/840 PSD L60L60 PCS WH	White RAL 9003

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910925868390	SM350X 27S/840 PSD L60L60 PCS BK	(0.39, 0.38) SDCM <3
910925868378	SM350C 34S/840 PSU PCS L1500 BK	(0.39, 0.38) SDCM <3
910925868381	SM350C 50S/840 PSU PCS L1500 BK	(0.39, 0.38) SDCM <3
910925868384	SM350C 34S/840 PSD PCS L1500 BK	(0.39, 0.38) SDCM <3
910925868387	SM350C 50S/840 PSD PCS L1500 BK	(0.39, 0.38) SDCM <3
910925868303	SM350C 27S/840 PSU PCS L1200 ALU	(0.39, 0.38) SDCM <3
910925868353	SM350C 40S/840 PSU PCS L1200 ALU	(0.39, 0.38) SDCM <3
910925868356	SM350C 27S/840 PSD PCS L1200 ALU	(0.39, 0.38) SDCM <3
910925868359	SM350C 40S/840 PSD PCS L1200 ALU	(0.39, 0.38) SDCM <3
910925868368	SM350C 27S/830 PSU PCS L1200 ALU	(0.43, 0.40) SDCM <3
910925868370	SM350C 40S/830 PSU PCS L1200 ALU	(0.43, 0.40) SDCM <3
910925868372	SM350C 27S/830 PSD PCS L1200 ALU	(0.43, 0.40) SDCM <3
910925868374	SM350C 40S/830 PSD PCS L1200 ALU	(0.43, 0.40) SDCM <3
910925868388	SM350X 27S/840 PSD L60L60 PCS ALU	(0.39, 0.38) SDCM <3
910925868376	SM350C 34S/840 PSU PCS L1500 ALU	(0.39, 0.38) SDCM <3
910925868379	SM350C 50S/840 PSU PCS L1500 ALU	(0.39, 0.38) SDCM <3
910925868382	SM350C 34S/840 PSD PCS L1500 ALU	(0.39, 0.38) SDCM <3
910925868385	SM350C 50S/840 PSD PCS L1500 ALU	(0.39, 0.38) SDCM <3
910925868377	SM350C 34S/840 PSU PCS L1500 WH	(0.39, 0.38) SDCM <3
910925868380	SM350C 50S/840 PSU PCS L1500 WH	(0.39, 0.38) SDCM <3
910925868383	SM350C 34S/840 PSD PCS L1500 WH	(0.39, 0.38) SDCM <3

Order Code	Full Product Name	Initial chromaticity
910925868386	SM350C 50S/840 PSD PCS L1500 WH	(0.39, 0.38) SDCM <3
910925868362	SM350C 27S/840 WIA PCS L1200 ALU	(0.39, 0.38) SDCM <3
910925868363	SM350C 27S/840 WIA PCS L1200 WH	(0.39, 0.38) SDCM <3
910925868364	SM350C 27S/840 WIA PCS L1200 BK	(0.39, 0.38) SDCM <3
910925868365	SM350C 40S/840 WIA PCS L1200 ALU	(0.39, 0.38) SDCM <3
910925868366	SM350C 40S/840 WIA PCS L1200 WH	(0.39, 0.38) SDCM <3
910925868367	SM350C 40S/840 WIA PCS L1200 BK	(0.39, 0.38) SDCM <3
910925868351	SM350C 27S/840 PSU PCS L1200 WH	(0.39, 0.38) SDCM <3
910925868354	SM350C 40S/840 PSU PCS L1200 WH	(0.39, 0.38) SDCM <3
910925868357	SM350C 27S/840 PSD PCS L1200 WH	(0.39, 0.38) SDCM <3
910925868360	SM350C 40S/840 PSD PCS L1200 WH	(0.39, 0.38) SDCM <3
910925868369	SM350C 27S/830 PSU PCS L1200 WH	(0.43, 0.40) SDCM <3
910925868371	SM350C 40S/830 PSU PCS L1200 WH	(0.43, 0.40) SDCM <3
910925868373	SM350C 27S/830 PSD PCS L1200 WH	(0.43, 0.40) SDCM <3
910925868375	SM350C 40S/830 PSD PCS L1200 WH	(0.43, 0.40) SDCM <3
910925868352	SM350C 27S/840 PSU PCS L1200 BK	(0.39, 0.38) SDCM <3
910925868355	SM350C 40S/840 PSU PCS L1200 BK	(0.39, 0.38) SDCM <3
910925868358	SM350C 27S/840 PSD PCS L1200 BK	(0.39, 0.38) SDCM <3
910925868361	SM350C 40S/840 PSD PCS L1200 BK	(0.39, 0.38) SDCM <3
910925868389	SM350X 27S/840 PSD L60L60 PCS WH	(0.39, 0.38) SDCM <3

Application Conditions

Order Code	Full Product Name	Maximum dim level
910925868390	SM350X 27S/840 PSD L60L60 PCS BK	1%
910925868378	SM350C 34S/840 PSU PCS L1500 BK	Not applicable
910925868381	SM350C 50S/840 PSU PCS L1500 BK	Not applicable
910925868384	SM350C 34S/840 PSD PCS L1500 BK	1%
910925868387	SM350C 50S/840 PSD PCS L1500 BK	1%
910925868303	SM350C 27S/840 PSU PCS L1200 ALU	Not applicable
910925868353	SM350C 40S/840 PSU PCS L1200 ALU	Not applicable

Order Code	Full Product Name	Maximum dim level
910925868356	SM350C 27S/840 PSD PCS L1200 ALU	1%
910925868359	SM350C 40S/840 PSD PCS L1200 ALU	1%
910925868368	SM350C 27S/830 PSU PCS L1200 ALU	Not applicable
910925868370	SM350C 40S/830 PSU PCS L1200 ALU	Not applicable
910925868372	SM350C 27S/830 PSD PCS L1200 ALU	1%
910925868374	SM350C 40S/830 PSD PCS L1200 ALU	1%
910925868388	SM350X 27S/840 PSD L60L60 PCS ALU	1%

KeyLine, Suspended

Order Code	Full Product Name	Maximum dim level
910925868376	SM350C 34S/840 PSU PCS L1500 ALU	Not applicable
910925868379	SM350C 50S/840 PSU PCS L1500 ALU	Not applicable
910925868382	SM350C 34S/840 PSD PCS L1500 ALU	1%
910925868385	SM350C 50S/840 PSD PCS L1500 ALU	1%
910925868377	SM350C 34S/840 PSU PCS L1500 WH	Not applicable
910925868380	SM350C 50S/840 PSU PCS L1500 WH	Not applicable
910925868383	SM350C 34S/840 PSD PCS L1500 WH	1%
910925868386	SM350C 50S/840 PSD PCS L1500 WH	1%
910925868362	SM350C 27S/840 WIA PCS L1200 ALU	1%
910925868363	SM350C 27S/840 WIA PCS L1200 WH	1%
910925868364	SM350C 27S/840 WIA PCS L1200 BK	1%
910925868365	SM350C 40S/840 WIA PCS L1200 ALU	1%
910925868366	SM350C 40S/840 WIA PCS L1200 WH	1%
910925868367	SM350C 40S/840 WIA PCS L1200 BK	1%

Order Code	Full Product Name	Maximum dim level
910925868351	SM350C 27S/840 PSU PCS L1200 WH	Not applicable
910925868354	SM350C 40S/840 PSU PCS L1200 WH	Not applicable
910925868357	SM350C 27S/840 PSD PCS L1200 WH	1%
910925868360	SM350C 40S/840 PSD PCS L1200 WH	1%
910925868369	SM350C 27S/830 PSU PCS L1200 WH	Not applicable
910925868371	SM350C 40S/830 PSU PCS L1200 WH	Not applicable
910925868373	SM350C 27S/830 PSD PCS L1200 WH	1%
910925868375	SM350C 40S/830 PSD PCS L1200 WH	1%
910925868352	SM350C 27S/840 PSU PCS L1200 BK	Not applicable
910925868355	SM350C 40S/840 PSU PCS L1200 BK	Not applicable
910925868358	SM350C 27S/840 PSD PCS L1200 BK	1%
910925868361	SM350C 40S/840 PSD PCS L1200 BK	1%
910925868389	SM350X 27S/840 PSD L60L60 PCS WH	1%

© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.