



Shining in a linear way

GreenSpace linear accent

GreenSpace Linear accent is a comprehensive product offer with multiple modules available. By means of its modular design, it offers flexible lumen output for different indoor applications, such as office, retail and hospitality. This family provides both surface mounted and recessed installations with high CRI90 and 3 different beam angles to perfectly fit the light requirement of the indoor applications. Dali and 1-10V control interfaces give the way for future system connections as well.

Benefits

- Flexible lumen output by means of multiple modules design
- High color rendering index helps better visual comfort in office and retail applications
- 3 different beams facilitate the lighting designer for wide lighting applications
- System interface available to easily control the lights

Features





- Multiple modules combinations available
- Both surface mounted and recessed installations are offered
- CRI 90 high color rendering index available
- Narrow/medium/wide beams options
- Dali / 1-10V control system interface available

Application

- Open offices
- Retail
- Meeting rooms
- Hospitality

GreenSpace linear accent

Dimensional drawing



Light Technical	
Color rendering index (CRI)	>90
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Mechanical and Housing	
Optical cover type	Polycarbonate cover and gloss high-reflective optic
Housing Color	Black and white
Mech. impact protection code	IK02
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	-20 to +40 °C
CE mark	No
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

Light Technical		Correlated Color	Luminous Efficacy	Luminous Flux
Order Code	Full Product Name	Temperature (Nom)	(rated) (Nom)	
66262299	RS386B S5 P10 930 PSU-E WB WH	3000 K	64 lm/W	575 lm
66265399	RS386B S5 P10 935 PSU-E WB WH	3500 K	64 lm/W	575 lm
66266099	RS386B S5 P10 940 PSU-E WB WH	4000 K	64 lm/W	575 lm
66378099	RS386B S5 P10 940 PSD-E WB WH	4000 K	64 lm/W	575 lm
66338499	SM386C S10 P20 930 PSU MB BK	3000 K	65 lm/W	1,150 lm
66343899	SM386C S10 P20 940 PSU WB BK	4000 K	65 lm/W	1,150 lm
66435099	SM386C S10 P20 940 PSD WB BK	4000 K	65 lm/W	1,150 lm
66335399	SM386C S10 P20 935 PSU WB WH	3500 K	65 lm/W	1,150 lm
66336099	SM386C S10 P20 940 PSU WB WH	4000 K	65 lm/W	1,150 lm
66426899	SM386C S10 P20 940 PSD WB WH	4000 K	65 lm/W	1,150 lm
66321699	SM386C S5 P10 935 PSU WB WH	3500 K	64 lm/W	575 lm
66322399	SM386C S5 P10 940 PSU WB WH	4000 K	64 lm/W	575 lm
66408499	SM386C S5 P10 940 PSD WB WH	4000 K	64 lm/W	575 lm
66276999	RS386B S10 P20 930 PSU-E WB WH	3000 K	65 lm/W	1,150 lm
66277699	RS386B S10 P20 935 PSU-E NB WH	3500 K	65 lm/W	1,150 lm
66280699	RS386B S10 P20 940 PSU-E WB WH	4000 K	65 lm/W	1,150 lm
66392699	RS386B S10 P20 940 PSD-E WB WH	4000 K	65 lm/W	1,150 lm
66325499	SM386C S5 P10 930 PSU WB BK	3000 K	64 lm/W	575 lm
66328599	SM386C S5 P10 935 PSU WB BK	3500 K	64 lm/W	575 lm
66329299	SM386C S5 P10 940 PSU WB BK	4000 K	64 lm/W	575 lm
66417699	SM386C S5 P10 940 PSD WB BK	4000 K	64 lm/W	575 lm
66269199	RS386B S5 P10 930 PSU-E WB BK	3000 K	64 lm/W	575 lm
66273899	RS386B S5 P10 940 PSU-E WB BK	4000 K	64 lm/W	575 lm
66297499	RS386B S5 P10 930 PSR-E WB BK	3000 K	64 lm/W	575 lm

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	
		Temperature (Nom)	(rated) (Nom)	Luminous Flux
66381099	RS386B S5 P10 930 PSD-E WB BK	3000 K	64 lm/W	575 lm
66383499	RS386B S5 P10 935 PSD-E MB BK	3500 K	64 lm/W	575 lm
66385899	RS386B S5 P10 940 PSD-E WB BK	4000 K	64 lm/W	575 lm
66283799	RS386B S10 P20 930 PSU-E WB BK	3000 K	65 lm/W	1,150 lm
66287599	RS386B S10 P20 940 PSU-E WB BK	4000 K	65 lm/W	1,150 lm
66315599	RS386B S10 P20 940 PSR-E WB BK	4000 K	65 lm/W	1,150 lm
66398899	RS386B S10 P20 935 PSD-E WB BK	3500 K	65 lm/W	1,150 lm
66399599	RS386B S10 P20 940 PSD-E WB BK	4000 K	65 lm/W	1,150 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
66262299	RS386B S5 P10 930 PSU-E WB WH	9 W	66392699	RS386B S10 P20 940 PSD-E WB WH	18 W
66265399	RS386B S5 P10 935 PSU-E WB WH	9 W	66325499	SM386C S5 P10 930 PSU WB BK	9 W
66266099	RS386B S5 P10 940 PSU-E WB WH	9 W	66328599	SM386C S5 P10 935 PSU WB BK	9 W
66378099	RS386B S5 P10 940 PSD-E WB WH	10 W	66329299	SM386C S5 P10 940 PSU WB BK	9 W
66338499	SM386C S10 P20 930 PSU MB BK	18 W	66417699	SM386C S5 P10 940 PSD WB BK	10 W
66343899	SM386C S10 P20 940 PSU WB BK	18 W	66269199	RS386B S5 P10 930 PSU-E WB BK	9 W
66435099	SM386C S10 P20 940 PSD WB BK	18 W	66273899	RS386B S5 P10 940 PSU-E WB BK	9 W
66335399	SM386C S10 P20 935 PSU WB WH	18 W	66297499	RS386B S5 P10 930 PSR-E WB BK	10 W
66336099	SM386C S10 P20 940 PSU WB WH	18 W	66381099	RS386B S5 P10 930 PSD-E WB BK	10 W
66426899	SM386C S10 P20 940 PSD WB WH	18 W	66383499	RS386B S5 P10 935 PSD-E MB BK	10 W
66321699	SM386C S5 P10 935 PSU WB WH	9 W	66385899	RS386B S5 P10 940 PSD-E WB BK	10 W
66322399	SM386C S5 P10 940 PSU WB WH	9 W	66283799	RS386B S10 P20 930 PSU-E WB BK	18 W
66408499	SM386C S5 P10 940 PSD WB WH	10 W	66287599	RS386B S10 P20 940 PSU-E WB BK	18 W
66276999	RS386B S10 P20 930 PSU-E WB WH	18 W	66315599	RS386B S10 P20 940 PSR-E WB BK	18 W
66277699	RS386B S10 P20 935 PSU-E NB WH	18 W	66398899	RS386B S10 P20 935 PSD-E WB BK	18 W
66280699	RS386B S10 P20 940 PSU-E WB WH	18 W	66399599	RS386B S10 P20 940 PSD-E WB BK	18 W

Controls and Dimming

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
66262299	RS386B S5 P10 930 PSU-E WB WH	No	66392699	RS386B S10 P20 940 PSD-E WB WH	Yes
66265399	RS386B S5 P10 935 PSU-E WB WH	No	66325499	SM386C S5 P10 930 PSU WB BK	No
66266099	RS386B S5 P10 940 PSU-E WB WH	No	66328599	SM386C S5 P10 935 PSU WB BK	No
66378099	RS386B S5 P10 940 PSD-E WB WH	Yes	66329299	SM386C S5 P10 940 PSU WB BK	No
66338499	SM386C S10 P20 930 PSU MB BK	No	66417699	SM386C S5 P10 940 PSD WB BK	Yes
66343899	SM386C S10 P20 940 PSU WB BK	No	66269199	RS386B S5 P10 930 PSU-E WB BK	No
66435099	SM386C S10 P20 940 PSD WB BK	Yes	66273899	RS386B S5 P10 940 PSU-E WB BK	No
66335399	SM386C S10 P20 935 PSU WB WH	No	66297499	RS386B S5 P10 930 PSR-E WB BK	Yes
66336099	SM386C S10 P20 940 PSU WB WH	No	66381099	RS386B S5 P10 930 PSD-E WB BK	Yes
66426899	SM386C S10 P20 940 PSD WB WH	Yes	66383499	RS386B S5 P10 935 PSD-E MB BK	Yes
66321699	SM386C S5 P10 935 PSU WB WH	No	66385899	RS386B S5 P10 940 PSD-E WB BK	Yes
66322399	SM386C S5 P10 940 PSU WB WH	No	66283799	RS386B S10 P20 930 PSU-E WB BK	No
66408499	SM386C S5 P10 940 PSD WB WH	Yes	66287599	RS386B S10 P20 940 PSU-E WB BK	No
66276999	RS386B S10 P20 930 PSU-E WB WH	No	66315599	RS386B S10 P20 940 PSR-E WB BK	Yes
66277699	RS386B S10 P20 935 PSU-E NB WH	No	66398899	RS386B S10 P20 935 PSD-E WB BK	Yes
66280699	RS386B S10 P20 940 PSU-E WB WH	No	66399599	RS386B S10 P20 940 PSD-E WB BK	Yes

GreenSpace linear accent

