



Shining in a linear way

GreenSpace linear accent

GreenSpace Linear accent is a comprehensive product offer with multiple modules available. By means of its modular design, it offers flexible lumen output for different indoor applications, such as office, retail and hospitality. This family provides both surface mounted and recessed installations with high CRI90 and 3 different beam angles to perfectly fit the light requirement of the indoor applications. Dali and 1-10V control interfaces give the way for future system connections as well.

Benefits

- Flexible lumen output by means of multiple modules design
- High color rendering index helps better visual comfort in office and retail applications
- 3 different beams facilitate the lighting designer for wide lighting applications
- System interface available to easily control the lights

Features

- Multiple modules combinations available
- Both surface mounted and recessed installations are offered
- CRI 90 high color rendering index available
- Narrow/medium/wide beams options
- Dali / 1-10V control system interface available

Application

- Open offices
- Retail
- Meeting rooms
- Hospitality





GreenSpace linear accent

Versions



GreenSpace Linear Accent

Dimensional drawing



Light Technical	
Color rendering index (CRI)	>90
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Mechanical and Housing	
Optical cover type	Polycarbonate cover and gloss high-reflective optic
Housing Color	Black and white
Mech. impact protection code	IK02
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	-20 to +40 °C
CE mark	No
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

Light Technical

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux
		Temperature (Nom)	(rated) (Nom)	
911401510402	RS386B S5 P10 930 PSU-E WB WH	3000 K	64 lm/W	575 lm
911401510702	RS386B S5 P10 935 PSU-E WB WH	3500 K	64 lm/W	575 lm
911401510802	RS386B S5 P10 940 PSU-E WB WH	4000 K	64 lm/W	575 lm
911401522002	RS386B S5 P10 940 PSD-E WB WH	4000 K	64 lm/W	575 lm
911401518002	SM386C S10 P20 930 PSU MB BK	3000 K	65 lm/W	1,150 lm
911401518502	SM386C S10 P20 940 PSU WB BK	4000 K	65 lm/W	1,150 lm
911401526902	SM386C S10 P20 940 PSD WB BK	4000 K	65 lm/W	1,150 lm
911401517702	SM386C S10 P20 935 PSU WB WH	3500 K	65 lm/W	1,150 lm
911401517802	SM386C S10 P20 940 PSU WB WH	4000 K	65 lm/W	1,150 lm
911401526202	SM386C S10 P20 940 PSD WB WH	4000 K	65 lm/W	1,150 lm
911401516302	SM386C S5 P10 935 PSU WB WH	3500 K	64 lm/W	575 lm
911401516402	SM386C S5 P10 940 PSU WB WH	4000 K	64 lm/W	575 lm
911401524802	SM386C S5 P10 940 PSD WB WH	4000 K	64 lm/W	575 lm
911401511802	RS386B S10 P20 930 PSU-E WB WH	3000 K	65 lm/W	1,150 lm
911401511902	RS386B S10 P20 935 PSU-E NB WH	3500 K	65 lm/W	1,150 lm
911401512202	RS386B S10 P20 940 PSU-E WB WH	4000 K	65 lm/W	1,150 lm
911401523402	RS386B S10 P20 940 PSD-E WB WH	4000 K	65 lm/W	1,150 lm
911401516702	SM386C S5 P10 930 PSU WB BK	3000 K	64 lm/W	575 lm
911401517002	SM386C S5 P10 935 PSU WB BK	3500 K	64 lm/W	575 lm
911401517102	SM386C S5 P10 940 PSU WB BK	4000 K	64 lm/W	575 lm
911401525502	SM386C S5 P10 940 PSD WB BK	4000 K	64 lm/W	575 lm
911401511102	RS386B S5 P10 930 PSU-E WB BK	3000 K	64 lm/W	575 lm
911401511502	RS386B S5 P10 940 PSU-E WB BK	4000 K	64 lm/W	575 lm
911401513902	RS386B S5 P10 930 PSR-E WB BK	3000 K	64 lm/W	575 lm
911401522302	RS386B S5 P10 930 PSD-E WB BK	3000 K	64 lm/W	575 lm
911401522502	RS386B S5 P10 935 PSD-E MB BK	3500 K	64 lm/W	575 lm
911401522702	RS386B S5 P10 940 PSD-E WB BK	4000 K	64 lm/W	575 lm
911401512502	RS386B S10 P20 930 PSU-E WB BK	3000 K	65 lm/W	1,150 lm
911401512902	RS386B S10 P20 940 PSU-E WB BK	4000 K	65 lm/W	1,150 lm
911401515702	RS386B S10 P20 940 PSR-E WB BK	4000 K	65 lm/W	1,150 lm
911401524002	RS386B S10 P20 935 PSD-E WB BK	3500 K	65 lm/W	1,150 lm
911401524102	RS386B S10 P20 940 PSD-E WB BK	4000 K	65 lm/W	1,150 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
911401510402	RS386B S5 P10 930 PSU-E WB WH	9 W	911401518002	SM386C S10 P20 930 PSU MB BK	18 W
911401510702	RS386B S5 P10 935 PSU-E WB WH	9 W	911401518502	SM386C S10 P20 940 PSU WB BK	18 W
911401510802	RS386B S5 P10 940 PSU-E WB WH	9 W	911401526902	SM386C S10 P20 940 PSD WB BK	18 W
911401522002	RS386B S5 P10 940 PSD-E WB WH	10 W	911401517702	SM386C S10 P20 935 PSU WB WH	18 W

GreenSpace linear accent

Order Code	Full Product Name	Power Consumption
911401517802	SM386C S10 P20 940 PSU WB WH	18 W
911401526202	SM386C S10 P20 940 PSD WB WH	18 W
911401516302	SM386C S5 P10 935 PSU WB WH	9 W
911401516402	SM386C S5 P10 940 PSU WB WH	9 W
911401524802	SM386C S5 P10 940 PSD WB WH	10 W
911401511802	RS386B S10 P20 930 PSU-E WB WH	18 W
911401511902	RS386B S10 P20 935 PSU-E NB WH	18 W
911401512202	RS386B S10 P20 940 PSU-E WB WH	18 W
911401523402	RS386B S10 P20 940 PSD-E WB WH	18 W
911401516702	SM386C S5 P10 930 PSU WB BK	9 W
911401517002	SM386C S5 P10 935 PSU WB BK	9 W
911401517102	SM386C S5 P10 940 PSU WB BK	9 W

Order Code	Full Product Name	Power Consumption
911401525502	SM386C S5 P10 940 PSD WB BK	10 W
911401511102	RS386B S5 P10 930 PSU-E WB BK	9 W
911401511502	RS386B S5 P10 940 PSU-E WB BK	9 W
911401513902	RS386B S5 P10 930 PSR-E WB BK	10 W
911401522302	RS386B S5 P10 930 PSD-E WB BK	10 W
911401522502	RS386B S5 P10 935 PSD-E MB BK	10 W
911401522702	RS386B S5 P10 940 PSD-E WB BK	10 W
911401512502	RS386B S10 P20 930 PSU-E WB BK	18 W
911401512902	RS386B S10 P20 940 PSU-E WB BK	18 W
911401515702	RS386B S10 P20 940 PSR-E WB BK	18 W
911401524002	RS386B S10 P20 935 PSD-E WB BK	18 W
911401524102	RS386B S10 P20 940 PSD-E WB BK	18 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401510402	RS386B S5 P10 930 PSU-E WB WH	No
911401510702	RS386B S5 P10 935 PSU-E WB WH	No
911401510802	RS386B S5 P10 940 PSU-E WB WH	No
911401522002	RS386B S5 P10 940 PSD-E WB WH	Yes
911401518002	SM386C S10 P20 930 PSU MB BK	No
911401518502	SM386C S10 P20 940 PSU WB BK	No
911401526902	SM386C S10 P20 940 PSD WB BK	Yes
911401517702	SM386C S10 P20 935 PSU WB WH	No
911401517802	SM386C S10 P20 940 PSU WB WH	No
911401526202	SM386C S10 P20 940 PSD WB WH	Yes
911401516302	SM386C S5 P10 935 PSU WB WH	No
911401516402	SM386C S5 P10 940 PSU WB WH	No
911401524802	SM386C S5 P10 940 PSD WB WH	Yes
911401511802	RS386B S10 P20 930 PSU-E WB WH	No
911401511902	RS386B S10 P20 935 PSU-E NB WH	No
911401512202	RS386B S10 P20 940 PSU-E WB WH	No

Order Code	Full Product Name	Dimmable
911401523402	RS386B S10 P20 940 PSD-E WB WH	Yes
911401516702	SM386C S5 P10 930 PSU WB BK	No
911401517002	SM386C S5 P10 935 PSU WB BK	No
911401517102	SM386C S5 P10 940 PSU WB BK	No
911401525502	SM386C S5 P10 940 PSD WB BK	Yes
911401511102	RS386B S5 P10 930 PSU-E WB BK	No
911401511502	RS386B S5 P10 940 PSU-E WB BK	No
911401513902	RS386B S5 P10 930 PSR-E WB BK	Yes
911401522302	RS386B S5 P10 930 PSD-E WB BK	Yes
911401522502	RS386B S5 P10 935 PSD-E MB BK	Yes
911401522702	RS386B S5 P10 940 PSD-E WB BK	Yes
911401512502	RS386B S10 P20 930 PSU-E WB BK	No
911401512902	RS386B S10 P20 940 PSU-E WB BK	No
911401515702	RS386B S10 P20 940 PSR-E WB BK	Yes
911401524002	RS386B S10 P20 935 PSD-E WB BK	Yes
911401524102	RS386B S10 P20 940 PSD-E WB BK	Yes

