



# Shining in a linear way

## GreenSpace linear accent

GreenSpace Linear accent is a comprehensive product offer with multiple modules available. By means of its modular design, it offers flexible lumen output for different indoor applications, such as office, retail and hospitality. This family provides both surface mounted and recessed installations with high CRI90 and 3 different beam angles to perfectly fit the light requirement of the indoor applications. Dali and 1-10V control interfaces give the way for future system connections as well.

### Benefits

- Flexible lumen output by means of multiple modules design
- High color rendering index helps better visual comfort in office and retail applications
- 3 different beams facilitate the lighting designer for wide lighting applications
- System interface available to easily control the lights

### Features

- Multiple modules combinations available
- Both surface mounted and recessed installations are offered
- CRI 90 high color rendering index available
- Narrow/medium/wide beams options
- Dali / 1-10V control system interface available

### Application

- Open offices
- Retail
- Meeting rooms
- Hospitality




# GreenSpace linear accent

## Versions



GreenSpace Linear Accent

## Dimensional drawing



GreenSpace linear accent

| Light Technical                     |                                                     |
|-------------------------------------|-----------------------------------------------------|
| Color rendering index (CRI)         | >90                                                 |
| Operating and Electrical            |                                                     |
| Protection class IEC                | Safety class II                                     |
| Input Voltage                       | 220 to 240 V                                        |
| Line Frequency                      | 50 or 60 Hz                                         |
| Mechanical and Housing              |                                                     |
| Optical cover type                  | Polycarbonate cover and gloss high-reflective optic |
| Housing Color                       | Black and white                                     |
| Mech. impact protection code        | IK02                                                |
| Ingress protection code             | IP20                                                |
| Approval and Application            |                                                     |
| Ambient temperature range           | -20 to +40 °C                                       |
| CE mark                             | No                                                  |
| Initial Performance (IEC Compliant) |                                                     |
| Luminous flux tolerance             | +/-10%                                              |

Light Technical

| Order Code   | Full Product Name              | Correlated Color  | Luminous Efficacy |               |
|--------------|--------------------------------|-------------------|-------------------|---------------|
|              |                                | Temperature (Nom) | (rated) (Nom)     | Luminous Flux |
| 911401510402 | RS386B S5 P10 930 PSU-E WB WH  | 3000 K            | 64 lm/W           | 575 lm        |
| 911401510702 | RS386B S5 P10 935 PSU-E WB WH  | 3500 K            | 64 lm/W           | 575 lm        |
| 911401510802 | RS386B S5 P10 940 PSU-E WB WH  | 4000 K            | 64 lm/W           | 575 lm        |
| 911401522002 | RS386B S5 P10 940 PSD-E WB WH  | 4000 K            | 64 lm/W           | 575 lm        |
| 911401526902 | SM386C S10 P20 940 PSD WB BK   | 4000 K            | 65 lm/W           | 1,150 lm      |
| 911401511802 | RS386B S10 P20 930 PSU-E WB WH | 3000 K            | 65 lm/W           | 1,150 lm      |
| 911401511902 | RS386B S10 P20 935 PSU-E NB WH | 3500 K            | 65 lm/W           | 1,150 lm      |
| 911401512202 | RS386B S10 P20 940 PSU-E WB WH | 4000 K            | 65 lm/W           | 1,150 lm      |
| 911401523402 | RS386B S10 P20 940 PSD-E WB WH | 4000 K            | 65 lm/W           | 1,150 lm      |
| 911401511102 | RS386B S5 P10 930 PSU-E WB BK  | 3000 K            | 64 lm/W           | 575 lm        |
| 911401511502 | RS386B S5 P10 940 PSU-E WB BK  | 4000 K            | 64 lm/W           | 575 lm        |
| 911401513902 | RS386B S5 P10 930 PSR-E WB BK  | 3000 K            | 64 lm/W           | 575 lm        |
| 911401522302 | RS386B S5 P10 930 PSD-E WB BK  | 3000 K            | 64 lm/W           | 575 lm        |
| 911401522502 | RS386B S5 P10 935 PSD-E MB BK  | 3500 K            | 64 lm/W           | 575 lm        |
| 911401522702 | RS386B S5 P10 940 PSD-E WB BK  | 4000 K            | 64 lm/W           | 575 lm        |
| 911401512502 | RS386B S10 P20 930 PSU-E WB BK | 3000 K            | 65 lm/W           | 1,150 lm      |
| 911401512902 | RS386B S10 P20 940 PSU-E WB BK | 4000 K            | 65 lm/W           | 1,150 lm      |
| 911401515702 | RS386B S10 P20 940 PSR-E WB BK | 4000 K            | 65 lm/W           | 1,150 lm      |
| 911401524002 | RS386B S10 P20 935 PSD-E WB BK | 3500 K            | 65 lm/W           | 1,150 lm      |
| 911401524102 | RS386B S10 P20 940 PSD-E WB BK | 4000 K            | 65 lm/W           | 1,150 lm      |

Operating and Electrical

| Order Code   | Full Product Name              | Power Consumption |
|--------------|--------------------------------|-------------------|
| 911401510402 | RS386B S5 P10 930 PSU-E WB WH  | 9 W               |
| 911401510702 | RS386B S5 P10 935 PSU-E WB WH  | 9 W               |
| 911401510802 | RS386B S5 P10 940 PSU-E WB WH  | 9 W               |
| 911401522002 | RS386B S5 P10 940 PSD-E WB WH  | 10 W              |
| 911401526902 | SM386C S10 P20 940 PSD WB BK   | 18 W              |
| 911401511802 | RS386B S10 P20 930 PSU-E WB WH | 18 W              |
| 911401511902 | RS386B S10 P20 935 PSU-E NB WH | 18 W              |
| 911401512202 | RS386B S10 P20 940 PSU-E WB WH | 18 W              |
| 911401523402 | RS386B S10 P20 940 PSD-E WB WH | 18 W              |
| 911401511102 | RS386B S5 P10 930 PSU-E WB BK  | 9 W               |

| Order Code   | Full Product Name              | Power Consumption |
|--------------|--------------------------------|-------------------|
| 911401511502 | RS386B S5 P10 940 PSU-E WB BK  | 9 W               |
| 911401513902 | RS386B S5 P10 930 PSR-E WB BK  | 10 W              |
| 911401522302 | RS386B S5 P10 930 PSD-E WB BK  | 10 W              |
| 911401522502 | RS386B S5 P10 935 PSD-E MB BK  | 10 W              |
| 911401522702 | RS386B S5 P10 940 PSD-E WB BK  | 10 W              |
| 911401512502 | RS386B S10 P20 930 PSU-E WB BK | 18 W              |
| 911401512902 | RS386B S10 P20 940 PSU-E WB BK | 18 W              |
| 911401515702 | RS386B S10 P20 940 PSR-E WB BK | 18 W              |
| 911401524002 | RS386B S10 P20 935 PSD-E WB BK | 18 W              |
| 911401524102 | RS386B S10 P20 940 PSD-E WB BK | 18 W              |

Controls and Dimming

| Order Code   | Full Product Name             | Dimmable |
|--------------|-------------------------------|----------|
| 911401510402 | RS386B S5 P10 930 PSU-E WB WH | No       |
| 911401510702 | RS386B S5 P10 935 PSU-E WB WH | No       |
| 911401510802 | RS386B S5 P10 940 PSU-E WB WH | No       |
| 911401522002 | RS386B S5 P10 940 PSD-E WB WH | Yes      |
| 911401526902 | SM386C S10 P20 940 PSD WB BK  | Yes      |

| Order Code   | Full Product Name              | Dimmable |
|--------------|--------------------------------|----------|
| 911401511802 | RS386B S10 P20 930 PSU-E WB WH | No       |
| 911401511902 | RS386B S10 P20 935 PSU-E NB WH | No       |
| 911401512202 | RS386B S10 P20 940 PSU-E WB WH | No       |
| 911401523402 | RS386B S10 P20 940 PSD-E WB WH | Yes      |
| 911401511102 | RS386B S5 P10 930 PSU-E WB BK  | No       |

GreenSpace linear accent

| Order Code   | Full Product Name             | Dimmable |
|--------------|-------------------------------|----------|
| 911401511502 | RS386B S5 P10 940 PSU-E WB BK | No       |
| 911401513902 | RS386B S5 P10 930 PSR-E WB BK | Yes      |
| 911401522302 | RS386B S5 P10 930 PSD-E WB BK | Yes      |
| 911401522502 | RS386B S5 P10 935 PSD-E MB BK | Yes      |
| 911401522702 | RS386B S5 P10 940 PSD-E WB BK | Yes      |

| Order Code   | Full Product Name              | Dimmable |
|--------------|--------------------------------|----------|
| 911401512502 | RS386B S10 P20 930 PSU-E WB BK | No       |
| 911401512902 | RS386B S10 P20 940 PSU-E WB BK | No       |
| 911401515702 | RS386B S10 P20 940 PSR-E WB BK | Yes      |
| 911401524002 | RS386B S10 P20 935 PSD-E WB BK | Yes      |
| 911401524102 | RS386B S10 P20 940 PSD-E WB BK | Yes      |

