



StoreSet Evo: Sustainable lighting for the stores of the future

StoreSet Evo combines slim, contemporary design and uniform light distribution, with a wide range of OptiSuit optics to meet various applications. This system meets our strict Lighting for Circularity criteria, creating a pleasant in-store ambience while contributing to your sustainability goals. StoreSet Evo can be used across a wide range of retail applications: can be easily connected to power tracks, Maxos fusion backbone or recessed ceilings.

Benefits

- Appealing look and feel: StoreSet evo's slim and contemporary design blends unobtrusively into your store's layout
- Ease of installation: One-point central track suspension with rotation offers you complete flexibility when installing, repositioning, and maintaining your luminaires
- Future-proof application: Its modular components, drivers and light engines, are designed for easy maintenance and replacement to extend product life

Applications

- Food and Large Retailers
- Supermarkets and hypermarkets

Features

- Slim and contemporary design blends seamlessly into store interiors
- Outstanding light quality with best-in-class efficiency

- Wide range of OptiSuit optics to meet various applications
- Provides uniform lighting distribution while saving energy

- Easy maintenance with fast and toolless driver access
- Meets Lighting for Circularity criteria
- The canopy and optical surfaces must only ever be cleaned with a lint-free cloth and without detergents. During maintenance, the product must be switched off and cooled down.

Versions



Storeset Evo track-mounted,
SM515T black



Storeset Evo recessed-mounted, RC516B, black, standard product photo, tilted view from below



StoreSet Evo SM515T-SI




Storeset Evo recessed-mounted, RC517B white




Storeset Evo track-mounted,
SM515T white



Dimensional drawing



SM515S 66S/830 DIA-VLC WB WH



RC516B 80S/830 PSU DA25N WH



SM515T 90S/840 PSU DA45 BK

RC517B 66S/830 PSU WB WH HE

Product details



Storeset Evo track-mounted,
SM515T black



Storeset Evo track-mounted,
SM515T black



Storeset Evo track-mounted,
SM515T black



Storeset Evo track-mounted,
SM515T, silver



Storeset Evo track-mounted,
SM515T black




Storeset Evo recessed-
mounted, RC517B white

StoreSet Evo SM515T SI05



StoreSet Evo SM515T-SI-2DPP




Storeset Evo track-mounted,
SM515T white



Storeset Evo track-mounted,
SM515T white

Storeset Evo track-mounted,
SM515T black



Storeset Evo recessed-
mounted, RC517B white

Storeset Evo track-mounted,
SM515T, silver




Storeset Evo track-mounted,
SM515T white

Storeset Evo track-mounted,
SM515T black



Storeset Evo trunking-
mounted, SM515S, white

StoreSet Evo SM515T-SI02



StoreSet Evo SM515S-SI-2DPP



Storeset Evo track-mounted,
SM515T, silver



Storeset Evo recessed-
mounted, RC517B white



Storeset Evo track-mounted,
SM515T, silver



Storeset Evo track-mounted,
SM515T black



Storeset Evo track-mounted,
SM515T white



Storeset Evo recessed-
mounted, RC517B white




Storeset Evo track-mounted,
SM515T black



Storeset Evo track-mounted,
SM515T white



Storeset Evo track-mounted,
SM515T black



Storeset Evo track-mounted,
SM515T, silver



Storeset Evo track-mounted,
SM515T white




Storeset Evo trunking-
mounted, SM515S, silver



Storeset Evo track-mounted,
SM515T black



StoreSet Evo SM515T SI04



Storeset Evo track-mounted,
SM515T black

General Information

Number of gear units	1 unit
Driver included	Yes
Service tag	Yes

Light Technical

Beam angle of light source	120 degree(s)
----------------------------	---------------

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	Yes
Protection class IEC	Safety class I

Controls and Dimming

Embedded control	Visible light communication
------------------	-----------------------------

Mechanical and Housing

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]

Emergency Operation

Central Emergency	No
-------------------	----

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	+10 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Light Technical

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Color rendering index (CRI)	Optic type
910505102662	SM515T 90S/830 PSU WB BK	9,200 lm	3000 K	124 lm/W	>80	Wide beam
910505102663	SM515T 90S/830 PSU DA35W BK	9,200 lm	3000 K	124 lm/W	>80	Double asymmetric optic 35° wide beam
910505102667	SM515T 66S/840 PSU A20 BK	6,600 lm	4000 K	143 lm/W	>80	Asymmetrical mirror axis angle 20°
910505102668	SM515T 66S/830 PSU A20 BK	6,700 lm	3000 K	134 lm/W	>80	Asymmetrical mirror axis angle 20°
910505102669	SM515T 90S/840 PSU DA35W BK	9,200 lm	4000 K	137 lm/W	>80	Double asymmetric optic 35° wide beam
910505102674	SM515T 90S/830 WIA DA35W BK HE	8,700 lm	3000 K	152 lm/W	>80	Double asymmetric optic 35° wide beam
910505102675	SM515T 90S/830 WIA WB BK HE	8,700 lm	3000 K	152 lm/W	>80	Wide beam
910505102676	SM515T 66S/830 WIA A20 BK HE	6,600 lm	3000 K	157 lm/W	>80	Asymmetrical mirror axis angle 20°
910505102691	SM515S 66S/830 DIA-VLC WB BK HE	6,600 lm	3000 K	157 lm/W	>80	Wide beam
910505102693	SM515S 66S/840 DIA-VLC A20 BK HE	6,700 lm	4000 K	157 lm/W	>80	Asymmetrical mirror axis angle 20°
910505102695	SM515S 66S/840 DIA-VLC WB BK HE	6,700 lm	4000 K	163 lm/W	>80	Wide beam

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Color rendering index (CRI)	Optic type
910505102697	SM515T 66S/830 PSU WB BK HE	6,600 lm	3000 K	157 lm/W	>80	Wide beam
910505102701	SM515T 66S/930 DIA-VLC WB BK HE	6,900 lm	3000 K	153 lm/W	>90	Wide beam
910505102705	SM515T 80S/830 PSU WB BK	8,100 lm	3000 K	126 lm/W	>80	Wide beam
910505102706	SM515T 80S/830 PSU WB BK HE	8,000 lm	3000 K	154 lm/W	>80	Wide beam
910505102707	SM515T 80S/840 DIA-VLC MB BK HE	8,000 lm	4000 K	160 lm/W	>80	Medium beam
910505102708	SM515T 80S/840 DIA-VLC WB BK	8,100 lm	4000 K	139 lm/W	>80	Wide beam
910505102710	SM515T 80S/940 DIA-VLC MB BK HE	8,300 lm	4000 K	156 lm/W	>90	Medium beam
910505102711	SM515T 80S/940 DIA-VLC WB BK HE	8,300 lm	4000 K	156 lm/W	>90	Wide beam
910505102712	SM515T 90S/830 DIA-VLC DA25W BK HE	8,700 lm	3000 K	152 lm/W	>80	Double asymmetric optic 25° wide beam
910505102713	SM515T 90S/830 DIA-VLC WB BK HE	8,700 lm	3000 K	152 lm/W	>80	Wide beam
910505102714	SM515T 90S/840 DIA-VLC DA25N BK	9,200 lm	4000 K	160 lm/W	>80	Double asymmetric optic 25° narrow beam
910505102715	SM515T 90S/840 DIA-VLC DA25W BK	9,200 lm	4000 K	124 lm/W	>80	Double asymmetric optic 25° wide beam
910505102718	SM515T 90S/840 DIA-VLC WB BK	9,200 lm	4000 K	124 lm/W	>80	Wide beam
910505102719	SM515T 90S/840 PSU A20 BK	9,200 lm	4000 K	137 lm/W	>80	Asymmetrical mirror axis angle 20°
910505102721	SM515T 90S/840 PSU DA25N BK	9,200 lm	4000 K	137 lm/W	>80	Double asymmetric optic 25° narrow beam
910505102723	SM515T 90S/840 PSU DA45 BK	9,200 lm	4000 K	137 lm/W	>80	Double asymmetric optic 45°
910505102725	SM515T 90S/840 PSU WB BK	9,200 lm	4000 K	137 lm/W	>80	Wide beam
910505102727	SM515T 90S/930 DIA-VLC WB BK HE	9,500 lm	3000 K	146 lm/W	>90	Wide beam
910505102728	SM515T 90S/940 DIA-VLC WB BK HE	9,400 lm	4000 K	154 lm/W	>90	Wide beam
910505102682	RC516B 80S/830 PSU DA25N WH	8,100 lm	3000 K	126 lm/W	>80	Double asymmetric optic 25° narrow beam
910505102704	SM515T 80S/830 PSU DA35W SI	8,100 lm	3000 K	126 lm/W	>80	Double asymmetric optic 35° wide beam
910505102720	SM515T 90S/840 PSU A20 SI	9,200 lm	4000 K	137 lm/W	>80	Asymmetrical mirror axis angle 20°
910505102722	SM515T 90S/840 PSU DA25N SI	9,200 lm	4000 K	137 lm/W	>80	Double asymmetric optic 25° narrow beam
910505102724	SM515T 90S/840 PSU DA45 SI	9,200 lm	4000 K	137 lm/W	>80	Double asymmetric optic 45°
910505102726	SM515T 90S/840 PSU WB SI	9,200 lm	4000 K	137 lm/W	>80	Wide beam
910505102677	RC517B 66S/840 DIA-CLO-VLC WB WH	6,600 lm	4000 K	143 lm/W	>80	Wide beam
910505102683	RC517B 66S/830 DIA-CLO-VLC WB WH	6,700 lm	3000 K	134 lm/W	>80	Wide beam
910505102684	RC517B 66S/830 DIA-CLO-VLC WB WH HE	6,600 lm	3000 K	157 lm/W	>80	Wide beam
910505102685	RC517B 66S/830 PSU WB WH	6,700 lm	3000 K	134 lm/W	>80	Wide beam
910505102686	RC517B 66S/830 PSU WB WH HE	6,600 lm	3000 K	157 lm/W	>80	Wide beam
910505102687	RC517B 66S/840 DIA-CLO-VLC WB WH HE	6,700 lm	4000 K	163 lm/W	>80	Wide beam
910505102688	RC517B 66S/840 PSU WB WH	6,600 lm	4000 K	143 lm/W	>80	Wide beam
910505102689	RC517B 66S/840 PSU WB WH HE	6,600 lm	4000 K	163 lm/W	>80	Wide beam
910505102664	SM515T 90S/830 PSU WB WH	9,200 lm	3000 K	124 lm/W	>80	Wide beam

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Color rendering index (CRI)	Optic type
910505102665	SM515T 66S/830 PSU A20 WH	6,700 lm	3000 K	134 lm/W	>80	Asymmetrical mirror axis angle 20°
910505102666	SM515T 90S/830 PSU DA35W WH	9,200 lm	3000 K	124 lm/W	>80	Double asymmetric optic 35° wide beam
910505102670	SM515T 66S/840 WIA A20 WH HE	6,700 lm	4000 K	163 lm/W	>80	Asymmetrical mirror axis angle 20°
910505102671	SM515T 90S/830 WIA DA35W WH HE	8,700 lm	3000 K	152 lm/W	>80	Double asymmetric optic 35° wide beam
910505102672	SM515T 90S/830 WIA WB WH HE	8,700 lm	3000 K	152 lm/W	>80	Wide beam
910505102673	SM515T 66S/830 WIA A20 WH HE	6,600 lm	3000 K	157 lm/W	>80	Asymmetrical mirror axis angle 20°
910505102679	SM515T 90S/840 WIA WB WH HE	9,000 lm	4000 K	160 lm/W	>80	Wide beam
910505102690	SM515S 66S/830 DIA-VLC DA25N WH	6,700 lm	3000 K	134 lm/W	>80	Double asymmetric optic 25° narrow beam
910505102692	SM515S 66S/830 DIA-VLC WB WH	6,700 lm	3000 K	134 lm/W	>80	Wide beam
910505102694	SM515S 66S/840 DIA-VLC DA25N WH	6,600 lm	4000 K	143 lm/W	>80	Double asymmetric optic 25° narrow beam
910505102696	SM515S 66S/840 DIA-VLC WB WH	6,600 lm	4000 K	143 lm/W	>80	Wide beam
910505102698	SM515T 66S/830 PSU WB WH HE	6,600 lm	3000 K	157 lm/W	>80	Wide beam
910505102699	SM515T 66S/840 PSU WB WH	6,600 lm	4000 K	143 lm/W	>80	Wide beam
910505102702	SM515T 80S/830 DIA-VLC A20 WH	8,100 lm	3000 K	126 lm/W	>80	Asymmetrical mirror axis angle 20°
910505102703	SM515T 80S/830 PSU DA25W WH HE	8,000 lm	3000 K	154 lm/W	>80	Double asymmetric optic 25° wide beam
910505102709	SM515T 80S/840 DIA-VLC WB WH	8,100 lm	4000 K	139 lm/W	>80	Wide beam
910505102716	SM515T 90S/840 DIA-VLC DA25W WH	9,200 lm	4000 K	124 lm/W	>80	Double asymmetric optic 25° wide beam
910505102717	SM515T 90S/840 DIA-VLC DA45 WH	9,200 lm	4000 K	124 lm/W	>80	Double asymmetric optic 45°

Operating and Electrical

Order Code	Full Product Name	Power Consumption
910505102662	SM515T 90S/830 PSU WB BK	74 W
910505102663	SM515T 90S/830 PSU DA35W BK	74 W
910505102667	SM515T 66S/840 PSU A20 BK	46 W
910505102668	SM515T 66S/830 PSU A20 BK	50 W
910505102669	SM515T 90S/840 PSU DA35W BK	67 W
910505102674	SM515T 90S/830 WIA DA35W BK HE	59 W
910505102675	SM515T 90S/830 WIA WB BK HE	59 W
910505102676	SM515T 66S/830 WIA A20 BK HE	43 W
910505102691	SM515S 66S/830 DIA-VLC WB BK HE	43 W
910505102693	SM515S 66S/840 DIA-VLC A20 BK HE	41 W
910505102695	SM515S 66S/840 DIA-VLC WB BK HE	41 W
910505102697	SM515T 66S/830 PSU WB BK HE	43 W
910505102701	SM515T 66S/930 DIA-VLC WB BK HE	45 W

Order Code	Full Product Name	Power Consumption
910505102705	SM515T 80S/830 PSU WB BK	64 W
910505102706	SM515T 80S/830 PSU WB BK HE	52 W
910505102707	SM515T 80S/840 DIA-VLC MB BK HE	50 W
910505102708	SM515T 80S/840 DIA-VLC WB BK	58 W
910505102710	SM515T 80S/940 DIA-VLC MB BK HE	53 W
910505102711	SM515T 80S/940 DIA-VLC WB BK HE	53 W
910505102712	SM515T 90S/830 DIA-VLC DA25W BK HE	59 W
910505102713	SM515T 90S/830 DIA-VLC WB BK HE	59 W
910505102714	SM515T 90S/840 DIA-VLC DA25N BK	67 W
910505102715	SM515T 90S/840 DIA-VLC DA25W BK	67 W
910505102718	SM515T 90S/840 DIA-VLC WB BK	67 W
910505102719	SM515T 90S/840 PSU A20 BK	67 W
910505102721	SM515T 90S/840 PSU DA25N BK	67 W
910505102723	SM515T 90S/840 PSU DA45 BK	67 W
910505102725	SM515T 90S/840 PSU WB BK	67 W
910505102727	SM515T 90S/930 DIA-VLC WB BK HE	65 W
910505102728	SM515T 90S/940 DIA-VLC WB BK HE	61 W
910505102682	RC516B 80S/830 PSU DA25N WH	64 W
910505102704	SM515T 80S/830 PSU DA35W SI	64 W
910505102720	SM515T 90S/840 PSU A20 SI	67 W
910505102722	SM515T 90S/840 PSU DA25N SI	67 W
910505102724	SM515T 90S/840 PSU DA45 SI	67 W
910505102726	SM515T 90S/840 PSU WB SI	67 W
910505102677	RC517B 66S/840 DIA-CLO-VLC WB WH	46 W
910505102683	RC517B 66S/830 DIA-CLO-VLC WB WH	50 W
910505102684	RC517B 66S/830 DIA-CLO-VLC WB WH HE	43 W
910505102685	RC517B 66S/830 PSU WB WH	50 W
910505102686	RC517B 66S/830 PSU WB WH HE	43 W
910505102687	RC517B 66S/840 DIA-CLO-VLC WB WH HE	41 W
910505102688	RC517B 66S/840 PSU WB WH	46 W
910505102689	RC517B 66S/840 PSU WB WH HE	41 W
910505102664	SM515T 90S/830 PSU WB WH	74 W
910505102665	SM515T 66S/830 PSU A20 WH	50 W
910505102666	SM515T 90S/830 PSU DA35W WH	74 W
910505102670	SM515T 66S/840 WIA A20 WH HE	41 W
910505102671	SM515T 90S/830 WIA DA35W WH HE	59 W
910505102672	SM515T 90S/830 WIA WB WH HE	59 W
910505102673	SM515T 66S/830 WIA A20 WH HE	43 W
910505102679	SM515T 90S/840 WIA WB WH HE	56 W
910505102690	SM515S 66S/830 DIA-VLC DA25N WH	50 W
910505102692	SM515S 66S/830 DIA-VLC WB WH	50 W
910505102694	SM515S 66S/840 DIA-VLC DA25N WH	46 W

Order Code	Full Product Name	Power Consumption
910505102696	SM515S 66S/840 DIA-VLC WB WH	46 W
910505102698	SM515T 66S/830 PSU WB WH HE	43 W
910505102699	SM515T 66S/840 PSU WB WH	46 W
910505102702	SM515T 80S/830 DIA-VLC A20 WH	64 W
910505102703	SM515T 80S/830 PSU DA25W WH HE	52 W
910505102709	SM515T 80S/840 DIA-VLC WB WH	58 W
910505102716	SM515T 90S/840 DIA-VLC DA25W WH	67 W
910505102717	SM515T 90S/840 DIA-VLC DA45 WH	67 W

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
910505102662	SM515T 90S/830 PSU WB BK	No	Not applicable
910505102663	SM515T 90S/830 PSU DA35W BK	No	Not applicable
910505102667	SM515T 66S/840 PSU A20 BK	No	Not applicable
910505102668	SM515T 66S/830 PSU A20 BK	No	Not applicable
910505102669	SM515T 90S/840 PSU DA35W BK	No	Not applicable
910505102674	SM515T 90S/830 WIA DA35W BK HE	Yes	1%
910505102675	SM515T 90S/830 WIA WB BK HE	Yes	1%
910505102676	SM515T 66S/830 WIA A20 BK HE	Yes	1%
910505102691	SM515S 66S/830 DIA-VLC WB BK HE	Yes	1%
910505102693	SM515S 66S/840 DIA-VLC A20 BK HE	Yes	1%
910505102695	SM515S 66S/840 DIA-VLC WB BK HE	Yes	1%
910505102697	SM515T 66S/830 PSU WB BK HE	No	Not applicable
910505102701	SM515T 66S/930 DIA-VLC WB BK HE	Yes	1%
910505102705	SM515T 80S/830 PSU WB BK	No	Not applicable
910505102706	SM515T 80S/830 PSU WB BK HE	No	Not applicable
910505102707	SM515T 80S/840 DIA-VLC MB BK HE	Yes	1%
910505102708	SM515T 80S/840 DIA-VLC WB BK	Yes	1%
910505102710	SM515T 80S/940 DIA-VLC MB BK HE	Yes	1%
910505102711	SM515T 80S/940 DIA-VLC WB BK HE	Yes	1%
910505102712	SM515T 90S/830 DIA-VLC DA25W BK HE	Yes	1%
910505102713	SM515T 90S/830 DIA-VLC WB BK HE	Yes	1%
910505102714	SM515T 90S/840 DIA-VLC DA25N BK	Yes	1%
910505102715	SM515T 90S/840 DIA-VLC DA25W BK	Yes	1%
910505102718	SM515T 90S/840 DIA-VLC WB BK	Yes	1%
910505102719	SM515T 90S/840 PSU A20 BK	No	Not applicable
910505102721	SM515T 90S/840 PSU DA25N BK	No	Not applicable
910505102723	SM515T 90S/840 PSU DA45 BK	No	Not applicable
910505102725	SM515T 90S/840 PSU WB BK	No	Not applicable
910505102727	SM515T 90S/930 DIA-VLC WB BK HE	Yes	1%
910505102728	SM515T 90S/940 DIA-VLC WB BK HE	Yes	1%
910505102682	RC516B 80S/830 PSU DA25N WH	No	Not applicable

Order Code	Full Product Name	Dimmable	Maximum dim level
910505102704	SM515T 80S/830 PSU DA35W SI	No	Not applicable
910505102720	SM515T 90S/840 PSU A20 SI	No	Not applicable
910505102722	SM515T 90S/840 PSU DA25N SI	No	Not applicable
910505102724	SM515T 90S/840 PSU DA45 SI	No	Not applicable
910505102726	SM515T 90S/840 PSU WB SI	No	Not applicable
910505102677	RC517B 66S/840 DIA-CLO-VLC WB WH	Yes	1%
910505102683	RC517B 66S/830 DIA-CLO-VLC WB WH	Yes	1%
910505102684	RC517B 66S/830 DIA-CLO-VLC WB WH HE	Yes	1%
910505102685	RC517B 66S/830 PSU WB WH	No	Not applicable
910505102686	RC517B 66S/830 PSU WB WH HE	No	Not applicable
910505102687	RC517B 66S/840 DIA-CLO-VLC WB WH HE	Yes	1%
910505102688	RC517B 66S/840 PSU WB WH	No	Not applicable
910505102689	RC517B 66S/840 PSU WB WH HE	No	Not applicable
910505102664	SM515T 90S/830 PSU WB WH	No	Not applicable
910505102665	SM515T 66S/830 PSU A20 WH	No	Not applicable
910505102666	SM515T 90S/830 PSU DA35W WH	No	Not applicable
910505102670	SM515T 66S/840 WIA A20 WH HE	Yes	1%
910505102671	SM515T 90S/830 WIA DA35W WH HE	Yes	1%
910505102672	SM515T 90S/830 WIA WB WH HE	Yes	1%
910505102673	SM515T 66S/830 WIA A20 WH HE	Yes	1%
910505102679	SM515T 90S/840 WIA WB WH HE	Yes	1%
910505102690	SM515S 66S/830 DIA-VLC DA25N WH	Yes	1%
910505102692	SM515S 66S/830 DIA-VLC WB WH	Yes	1%
910505102694	SM515S 66S/840 DIA-VLC DA25N WH	Yes	1%
910505102696	SM515S 66S/840 DIA-VLC WB WH	Yes	1%
910505102698	SM515T 66S/830 PSU WB WH HE	No	Not applicable
910505102699	SM515T 66S/840 PSU WB WH	No	Not applicable
910505102702	SM515T 80S/830 DIA-VLC A20 WH	Yes	1%
910505102703	SM515T 80S/830 PSU DA25W WH HE	No	Not applicable
910505102709	SM515T 80S/840 DIA-VLC WB WH	Yes	1%
910505102716	SM515T 90S/840 DIA-VLC DA25W WH	Yes	1%
910505102717	SM515T 90S/840 DIA-VLC DA45 WH	Yes	1%

Mechanical and Housing

Order Code	Full Product Name	Housing Color
910505102662	SM515T 90S/830 PSU WB BK	Black
910505102663	SM515T 90S/830 PSU DA35W BK	Black
910505102667	SM515T 66S/840 PSU A20 BK	Black
910505102668	SM515T 66S/830 PSU A20 BK	Black
910505102669	SM515T 90S/840 PSU DA35W BK	Black
910505102674	SM515T 90S/830 WIA DA35W BK HE	Black
910505102675	SM515T 90S/830 WIA WB BK HE	Black

Order Code	Full Product Name	Housing Color
910505102676	SM515T 66S/830 WIA A20 BK HE	Black
910505102691	SM515S 66S/830 DIA-VLC WB BK HE	Black
910505102693	SM515S 66S/840 DIA-VLC A20 BK HE	Black
910505102695	SM515S 66S/840 DIA-VLC WB BK HE	Black
910505102697	SM515T 66S/830 PSU WB BK HE	Black
910505102701	SM515T 66S/930 DIA-VLC WB BK HE	Black
910505102705	SM515T 80S/830 PSU WB BK	Black
910505102706	SM515T 80S/830 PSU WB BK HE	Black
910505102707	SM515T 80S/840 DIA-VLC MB BK HE	Black
910505102708	SM515T 80S/840 DIA-VLC WB BK	Black
910505102710	SM515T 80S/940 DIA-VLC MB BK HE	Black
910505102711	SM515T 80S/940 DIA-VLC WB BK HE	Black
910505102712	SM515T 90S/830 DIA-VLC DA25W BK HE	Black
910505102713	SM515T 90S/830 DIA-VLC WB BK HE	Black
910505102714	SM515T 90S/840 DIA-VLC DA25N BK	Black
910505102715	SM515T 90S/840 DIA-VLC DA25W BK	Black
910505102718	SM515T 90S/840 DIA-VLC WB BK	Black
910505102719	SM515T 90S/840 PSU A20 BK	Black
910505102721	SM515T 90S/840 PSU DA25N BK	Black
910505102723	SM515T 90S/840 PSU DA45 BK	Black
910505102725	SM515T 90S/840 PSU WB BK	Black
910505102727	SM515T 90S/930 DIA-VLC WB BK HE	Black
910505102728	SM515T 90S/940 DIA-VLC WB BK HE	Black
910505102682	RC516B 80S/830 PSU DA25N WH	White
910505102704	SM515T 80S/830 PSU DA35W SI	Silver
910505102720	SM515T 90S/840 PSU A20 SI	Silver
910505102722	SM515T 90S/840 PSU DA25N SI	Silver
910505102724	SM515T 90S/840 PSU DA45 SI	Silver
910505102726	SM515T 90S/840 PSU WB SI	Silver
910505102677	RC517B 66S/840 DIA-CLO-VLC WB WH	White
910505102683	RC517B 66S/830 DIA-CLO-VLC WB WH	White
910505102684	RC517B 66S/830 DIA-CLO-VLC WB WH HE	White
910505102685	RC517B 66S/830 PSU WB WH	White
910505102686	RC517B 66S/830 PSU WB WH HE	White
910505102687	RC517B 66S/840 DIA-CLO-VLC WB WH HE	White
910505102688	RC517B 66S/840 PSU WB WH	White
910505102689	RC517B 66S/840 PSU WB WH HE	White
910505102664	SM515T 90S/830 PSU WB WH	White
910505102665	SM515T 66S/830 PSU A20 WH	White
910505102666	SM515T 90S/830 PSU DA35W WH	White
910505102670	SM515T 66S/840 WIA A20 WH HE	White
910505102671	SM515T 90S/830 WIA DA35W WH HE	White

Order Code	Full Product Name	Housing Color
910505102672	SM515T 90S/830 WIA WB WH HE	White
910505102673	SM515T 66S/830 WIA A20 WH HE	White
910505102679	SM515T 90S/840 WIA WB WH HE	White
910505102690	SM515S 66S/830 DIA-VLC DA25N WH	White
910505102692	SM515S 66S/830 DIA-VLC WB WH	White
910505102694	SM515S 66S/840 DIA-VLC DA25N WH	White
910505102696	SM515S 66S/840 DIA-VLC WB WH	White
910505102698	SM515T 66S/830 PSU WB WH HE	White
910505102699	SM515T 66S/840 PSU WB WH	White
910505102702	SM515T 80S/830 DIA-VLC A20 WH	White
910505102703	SM515T 80S/830 PSU DA25W WH HE	White
910505102709	SM515T 80S/840 DIA-VLC WB WH	White
910505102716	SM515T 90S/840 DIA-VLC DA25W WH	White
910505102717	SM515T 90S/840 DIA-VLC DA45 WH	White

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910505102662	SM515T 90S/830 PSU WB BK	(0.43, 0.40) SDCM<3
910505102663	SM515T 90S/830 PSU DA35W BK	(0.43, 0.40) SDCM<3
910505102667	SM515T 66S/840 PSU A20 BK	(0.38, 0.38) SDCM<3
910505102668	SM515T 66S/830 PSU A20 BK	(0.43, 0.40) SDCM<3
910505102669	SM515T 90S/840 PSU DA35W BK	(0.38, 0.38) SDCM<3
910505102674	SM515T 90S/830 WIA DA35W BK HE	(0.43, 0.40) SDCM<3
910505102675	SM515T 90S/830 WIA WB BK HE	(0.43, 0.40) SDCM<3
910505102676	SM515T 66S/830 WIA A20 BK HE	(0.43, 0.40) SDCM<3
910505102691	SM515S 66S/830 DIA-VLC WB BK HE	(0.43, 0.40) SDCM<3
910505102693	SM515S 66S/840 DIA-VLC A20 BK HE	(0.38, 0.38) SDCM<3
910505102695	SM515S 66S/840 DIA-VLC WB BK HE	(0.38, 0.38) SDCM<3
910505102697	SM515T 66S/830 PSU WB BK HE	(0.43, 0.40) SDCM<3
910505102701	SM515T 66S/930 DIA-VLC WB BK HE	(0.43, 0.40) SDCM<3
910505102705	SM515T 80S/830 PSU WB BK	(0.43, 0.40) SDCM<3
910505102706	SM515T 80S/830 PSU WB BK HE	(0.43, 0.40) SDCM<3
910505102707	SM515T 80S/840 DIA-VLC MB BK HE	(0.38, 0.38) SDCM<3
910505102708	SM515T 80S/840 DIA-VLC WB BK	(0.38, 0.38) SDCM<3
910505102710	SM515T 80S/940 DIA-VLC MB BK HE	(0.38, 0.38) SDCM<3
910505102711	SM515T 80S/940 DIA-VLC WB BK HE	(0.38, 0.38) SDCM<3
910505102712	SM515T 90S/830 DIA-VLC DA25W BK HE	(0.43, 0.40) SDCM<3
910505102713	SM515T 90S/830 DIA-VLC WB BK HE	(0.43, 0.40) SDCM<3
910505102714	SM515T 90S/840 DIA-VLC DA25N BK	(0.38, 0.38) SDCM<3
910505102715	SM515T 90S/840 DIA-VLC DA25W BK	(0.38, 0.38) SDCM<3
910505102718	SM515T 90S/840 DIA-VLC WB BK	(0.38, 0.38) SDCM<3
910505102719	SM515T 90S/840 PSU A20 BK	(0.38, 0.38) SDCM<3

Order Code	Full Product Name	Initial chromaticity
910505102721	SM515T 90S/840 PSU DA25N BK	(0.38, 0.38) SDCM<3
910505102723	SM515T 90S/840 PSU DA45 BK	(0.38, 0.38) SDCM<3
910505102725	SM515T 90S/840 PSU WB BK	(0.38, 0.38) SDCM<3
910505102727	SM515T 90S/930 DIA-VLC WB BK HE	(0.43, 0.40) SDCM<3
910505102728	SM515T 90S/940 DIA-VLC WB BK HE	(0.38, 0.38) SDCM<3
910505102682	RC516B 80S/830 PSU DA25N WH	(0.43, 0.40) SDCM<3
910505102704	SM515T 80S/830 PSU DA35W SI	(0.43, 0.40) SDCM<3
910505102720	SM515T 90S/840 PSU A20 SI	(0.38, 0.38) SDCM<3
910505102722	SM515T 90S/840 PSU DA25N SI	(0.38, 0.38) SDCM<3
910505102724	SM515T 90S/840 PSU DA45 SI	(0.38, 0.38) SDCM<3
910505102726	SM515T 90S/840 PSU WB SI	(0.38, 0.38) SDCM<3
910505102677	RC517B 66S/840 DIA-CLO-VLC WB WH	(0.38, 0.38) SDCM<3
910505102683	RC517B 66S/830 DIA-CLO-VLC WB WH	(0.38, 0.38) SDCM<3
910505102684	RC517B 66S/830 DIA-CLO-VLC WB WH HE	(0.38, 0.38) SDCM<3
910505102685	RC517B 66S/830 PSU WB WH	(0.43, 0.40) SDCM<3
910505102686	RC517B 66S/830 PSU WB WH HE	(0.43, 0.40) SDCM<3
910505102687	RC517B 66S/840 DIA-CLO-VLC WB WH HE	(0.38, 0.38) SDCM<3
910505102688	RC517B 66S/840 PSU WB WH	(0.38, 0.38) SDCM<3
910505102689	RC517B 66S/840 PSU WB WH HE	(0.38, 0.38) SDCM<3
910505102664	SM515T 90S/830 PSU WB WH	(0.43, 0.40) SDCM<3
910505102665	SM515T 66S/830 PSU A20 WH	(0.43, 0.40) SDCM<3
910505102666	SM515T 90S/830 PSU DA35W WH	(0.43, 0.40) SDCM<3
910505102670	SM515T 66S/840 WIA A20 WH HE	(0.38, 0.38) SDCM<3
910505102671	SM515T 90S/830 WIA DA35W WH HE	(0.43, 0.40) SDCM<3
910505102672	SM515T 90S/830 WIA WB WH HE	(0.43, 0.40) SDCM<3
910505102673	SM515T 66S/830 WIA A20 WH HE	(0.43, 0.40) SDCM<3
910505102679	SM515T 90S/840 WIA WB WH HE	(0.38, 0.38) SDCM<3
910505102690	SM515S 66S/830 DIA-VLC DA25N WH	(0.43, 0.40) SDCM<3
910505102692	SM515S 66S/830 DIA-VLC WB WH	(0.43, 0.40) SDCM<3
910505102694	SM515S 66S/840 DIA-VLC DA25N WH	(0.38, 0.38) SDCM<3
910505102696	SM515S 66S/840 DIA-VLC WB WH	(0.38, 0.38) SDCM<3
910505102698	SM515T 66S/830 PSU WB WH HE	(0.43, 0.40) SDCM<3
910505102699	SM515T 66S/840 PSU WB WH	(0.38, 0.38) SDCM<3
910505102702	SM515T 80S/830 DIA-VLC A20 WH	(0.43, 0.40) SDCM<3
910505102703	SM515T 80S/830 PSU DA25W WH HE	(0.43, 0.40) SDCM<3
910505102709	SM515T 80S/840 DIA-VLC WB WH	(0.38, 0.38) SDCM<3
910505102716	SM515T 90S/840 DIA-VLC DA25W WH	(0.38, 0.38) SDCM<3
910505102717	SM515T 90S/840 DIA-VLC DA45 WH	(0.38, 0.38) SDCM<3


Product Data

Order Code	Full Product Name	Product family code
910505102662	SM515T 90S/830 PSU WB BK	SM515T


Order Code	Full Product Name	Product family code
910505102663	SM515T 90S/830 PSU DA35W BK	SM515T
910505102667	SM515T 66S/840 PSU A20 BK	SM515T
910505102668	SM515T 66S/830 PSU A20 BK	SM515T
910505102669	SM515T 90S/840 PSU DA35W BK	SM515T
910505102674	SM515T 90S/830 WIA DA35W BK HE	SM515T
910505102675	SM515T 90S/830 WIA WB BK HE	SM515T
910505102676	SM515T 66S/830 WIA A20 BK HE	SM515T
910505102691	SM515S 66S/830 DIA-VLC WB BK HE	SM515S
910505102693	SM515S 66S/840 DIA-VLC A20 BK HE	SM515S
910505102695	SM515S 66S/840 DIA-VLC WB BK HE	SM515S
910505102697	SM515T 66S/830 PSU WB BK HE	SM515T
910505102701	SM515T 66S/930 DIA-VLC WB BK HE	SM515T
910505102705	SM515T 80S/830 PSU WB BK	SM515T
910505102706	SM515T 80S/830 PSU WB BK HE	SM515T
910505102707	SM515T 80S/840 DIA-VLC MB BK HE	SM515T
910505102708	SM515T 80S/840 DIA-VLC WB BK	SM515T
910505102710	SM515T 80S/940 DIA-VLC MB BK HE	SM515T
910505102711	SM515T 80S/940 DIA-VLC WB BK HE	SM515T
910505102712	SM515T 90S/830 DIA-VLC DA25W BK HE	SM515T
910505102713	SM515T 90S/830 DIA-VLC WB BK HE	SM515T
910505102714	SM515T 90S/840 DIA-VLC DA25N BK	SM515T
910505102715	SM515T 90S/840 DIA-VLC DA25W BK	SM515T
910505102718	SM515T 90S/840 DIA-VLC WB BK	SM515T
910505102719	SM515T 90S/840 PSU A20 BK	SM515T
910505102721	SM515T 90S/840 PSU DA25N BK	SM515T
910505102723	SM515T 90S/840 PSU DA45 BK	SM515T
910505102725	SM515T 90S/840 PSU WB BK	SM515T
910505102727	SM515T 90S/930 DIA-VLC WB BK HE	SM515T
910505102728	SM515T 90S/940 DIA-VLC WB BK HE	SM515T
910505102682	RC516B 80S/830 PSU DA25N WH	RC516B
910505102704	SM515T 80S/830 PSU DA35W SI	SM515T
910505102720	SM515T 90S/840 PSU A20 SI	SM515T
910505102722	SM515T 90S/840 PSU DA25N SI	SM515T
910505102724	SM515T 90S/840 PSU DA45 SI	SM515T
910505102726	SM515T 90S/840 PSU WB SI	SM515T
910505102677	RC517B 66S/840 DIA-CLO-VLC WB WH	RC517B
910505102683	RC517B 66S/830 DIA-CLO-VLC WB WH	RC517B
910505102684	RC517B 66S/830 DIA-CLO-VLC WB WH HE	RC517B
910505102685	RC517B 66S/830 PSU WB WH	RC517B
910505102686	RC517B 66S/830 PSU WB WH HE	RC517B
910505102687	RC517B 66S/840 DIA-CLO-VLC WB WH HE	RC517B
910505102688	RC517B 66S/840 PSU WB WH	RC517B

Order Code	Full Product Name	Product family code
910505102689	RC517B 66S/840 PSU WB WH HE	RC517B
910505102664	SM515T 90S/830 PSU WB WH	SM515T
910505102665	SM515T 66S/830 PSU A20 WH	SM515T
910505102666	SM515T 90S/830 PSU DA35W WH	SM515T
910505102670	SM515T 66S/840 WIA A20 WH HE	SM515T
910505102671	SM515T 90S/830 WIA DA35W WH HE	SM515T
910505102672	SM515T 90S/830 WIA WB WH HE	SM515T
910505102673	SM515T 66S/830 WIA A20 WH HE	SM515T
910505102679	SM515T 90S/840 WIA WB WH HE	SM515T
910505102690	SM515S 66S/830 DIA-VLC DA25N WH	SM515S
910505102692	SM515S 66S/830 DIA-VLC WB WH	SM515S
910505102694	SM515S 66S/840 DIA-VLC DA25N WH	SM515S
910505102696	SM515S 66S/840 DIA-VLC WB WH	SM515S
910505102698	SM515T 66S/830 PSU WB WH HE	SM515T
910505102699	SM515T 66S/840 PSU WB WH	SM515T
910505102702	SM515T 80S/830 DIA-VLC A20 WH	SM515T
910505102703	SM515T 80S/830 PSU DA25W WH HE	SM515T
910505102709	SM515T 80S/840 DIA-VLC WB WH	SM515T
910505102716	SM515T 90S/840 DIA-VLC DA25W WH	SM515T
910505102717	SM515T 90S/840 DIA-VLC DA45 WH	SM515T


Polar normal diagrams




SM515TI - 910505102665




SM515TI - 910505102662




SM515TI - 910505102663




SM515TI - 910505102671




SM515TI - 910505102664




SM515TI - 910505102674




SM515TI - 910505102670




SM515TI - 910505102669




SM515TI - 910505102676




SM515TI - 910505102666




SM515TI - 910505102675




SM515TI - 910505102668




SM515TI - 910505102673




SM515TI - 910505102672




SM515TI - 910505102667




SM515TI - 910505102703




SM515TI - 910505102725




SM515TI - 910505102709




SM515TI - 910505102679




SM515TI - 910505102720




SM515TI - 910505102710




SM515TI - 910505102682




SM515TI - 910505102708




SM515TI - 910505102714




SM515TI - 910505102691




SM515TI - 910505102688




SM515TI - 910505102728




SM515TI - 910505102712




SM515TI - 910505102685




SM515TI - 910505102707




SM515TI - 910505102694




SM515TI - 910505102723




SM515TI - 910505102693




SM515TI - 910505102705




SM515TI - 910505102716




SM515TI - 910505102695




SM515TI - 910505102715




SM515TI - 910505102726




SM515TI - 910505102701




SM515TI - 910505102698




SM515TI - 910505102721




SM515TI - 910505102689




SM515TI - 910505102697




SM515TI - 910505102692




SM515TI - 910505102711




SM515TI - 910505102690




SM515TI - 910505102686




SM515TI - 910505102727




SM515TI - 910505102696




SM515TI - 910505102713




SM515TI - 910505102724




SM515TI - 910505102702




SM515TI - 910505102706




SM515TI - 910505102699




SM515TI - 910505102722




SM515TI - 910505102719




SM515TI - 910505102718




SM515TI - 910505102717




SM515TI - 910505102704




SM515TI - 910505102677



SM515TI - 910505102683



SM515TI - 910505102687



SM515TI - 910505102684