

Functional and Affordable

GreenUp Linear

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenUp Linear is the entry level linear product family, which offers the basic functional lighting performance, with multiple choices of installations, lumen outputs and product dimensions.

Benefits

- Slim body while delivering powerful lumen outputs.
- Complete family offering, meet basic functional lighting requirements.
- Energy efficiency
- Ensured quality and reliability.


Features

- Wide range of product dimensions and installation options.
- Multiple options of lumen outputs and optics.
- System efficacy up to 95lm/W.

Application

- Retail
- Hospitality
- Fashion

Dimensional drawing



Light Technical

Color rendering index (CRI) >80

Operating and Electrical

Protection class IEC Safety class II

Input Voltage 220-240 V

Line Frequency 50 or 60 Hz

Controls and Dimming

Dimmable No

Mechanical and Housing

Optical cover type Polycarbonate

Diffuser

Housing Color White RAL 9003

Mech. impact protection code IK03

Ingress protection code IP20

Approval and Application

Ambient temperature range +20 to +40 °C

CE mark No

Initial Performance (IEC Compliant)

Luminous flux tolerance +/-10%

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401584122	SM308C P22/830 L75W3 PSU WB WH	3000 K	95 lm/W	2,090 lm
911401584222	SM308C P22/840 L75W3 PSU MB WH	4000 K	98 lm/W	2,150 lm
911401584522	SM308C P22/865 L75W3 PSU WB WH	6500 K	98 lm/W	2,150 lm
911401585122	SM308C P30/865 L120W3 PSU WB WH	6500 K	98 lm/W	2,950 lm
911401585222	SM308C P38/830 L140W3 PSU MB WH	3000 K	95 lm/W	3,610 lm
911401585722	SM308C P38/865 L140W3 PSU WB WH	6500 K	98 lm/W	3,750 lm
911401586022	SM308C P45/840 L170W3 PSU MB WH	4000 K	98 lm/W	4,410 lm
911401586322	SM308C P45/865 L170W3 PSU WB WH	6500 K	98 lm/W	4,410 lm
911401586522	SP308P P22/830 L75W3 PSU WB WH	3000 K	95 lm/W	2,090 lm
911401586922	SP308P P22/865 L75W3 PSU WB WH	6500 K	98 lm/W	2,150 lm
911401587522	SP308P P30/865 L120W3 PSU WB WH	6500 K	98 lm/W	2,950 lm
911401587722	SP308P P38/830 L140W3 PSU WB WH	3000 K	95 lm/W	3,610 lm

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux
		Temperature (Nom)	(rated) (Nom)	
911401588122	SP308P P38/865 L140W3 PSU WB WH	6500 K	98 lm/W	3,750 lm
911401588422	SP308P P45/840 L170W3 PSU MB WH	4000 K	98 lm/W	4,410 lm
911401588722	SP308P P45/865 L170W3 PSU WB WH	6500 K	98 lm/W	4,410 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401584122	SM308C P22/830 L75W3 PSU WB WH	22 W
911401584222	SM308C P22/840 L75W3 PSU MB WH	22 W
911401584522	SM308C P22/865 L75W3 PSU WB WH	22 W
911401585122	SM308C P30/865 L120W3 PSU WB WH	30 W
911401585222	SM308C P38/830 L140W3 PSU MB WH	38 W
911401585722	SM308C P38/865 L140W3 PSU WB WH	38 W
911401586022	SM308C P45/840 L170W3 PSU MB WH	45 W
911401586322	SM308C P45/865 L170W3 PSU WB WH	45 W

Order Code	Full Product Name	Power Consumption
911401586522	SP308P P22/830 L75W3 PSU WB WH	22 W
911401586922	SP308P P22/865 L75W3 PSU WB WH	22 W
911401587522	SP308P P30/865 L120W3 PSU WB WH	30 W
911401587722	SP308P P38/830 L140W3 PSU WB WH	38 W
911401588122	SP308P P38/865 L140W3 PSU WB WH	38 W
911401588422	SP308P P45/840 L170W3 PSU MB WH	45 W
911401588722	SP308P P45/865 L170W3 PSU WB WH	45 W

