




Functional and Affordable

GreenUp Linear

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenUp Linear is the entry level linear product family, which offers the basic functional lighting performance, with multiple choices of installations, lumen outputs and product dimensions.

Benefits

- Slim body while delivering powerful lumen outputs.
- Complete family offering, meet basic functional lighting requirements.
- Energy efficiency
- Ensured quality and reliability.


Features

- Wide range of product dimensions and installation options.
- Multiple options of lumen outputs and optics.
- System efficacy up to 95lm/W.

Application

- Retail
- Hospitality
- Fashion

Dimensional drawing



Light Technical	
Color rendering index (CRI)	>80
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Optical cover type	Polycarbonate Diffuser
Housing Color	White RAL 9003
Mech. impact protection code	IK03
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	+20 to +40 °C
CE mark	No
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
53028799	SM308C P22/830 L75W3 PSU WB WH	3000 K	95 lm/W	2,090 lm
52524599	SM308C P22/840 L75W3 PSU MB WH	4000 K	98 lm/W	2,150 lm
52869799	SM308C P22/865 L75W3 PSU WB WH	6500 K	98 lm/W	2,150 lm
52351799	SM308C P30/865 L120W3 PSU WB WH	6500 K	98 lm/W	2,950 lm
52768399	SM308C P38/830 L140W3 PSU MB WH	3000 K	95 lm/W	3,610 lm
52606899	SM308C P38/865 L140W3 PSU WB WH	6500 K	98 lm/W	3,750 lm
52527699	SM308C P45/840 L170W3 PSU MB WH	4000 K	98 lm/W	4,410 lm
52872799	SM308C P45/865 L170W3 PSU WB WH	6500 K	98 lm/W	4,410 lm
52769099	SP308P P22/830 L75W3 PSU WB WH	3000 K	95 lm/W	2,090 lm
52443999	SP308P P22/865 L75W3 PSU WB WH	6500 K	98 lm/W	2,150 lm
52609999	SP308P P30/865 L120W3 PSU WB WH	6500 K	98 lm/W	2,950 lm
52357999	SP308P P38/830 L140W3 PSU WB WH	3000 K	95 lm/W	3,610 lm

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	
		Temperature (Nom)	(rated) (Nom)	Luminous Flux
52878999	SP308P P38/865 L140W3 PSU WB WH	6500 K	98 lm/W	3,750 lm
53167399	SP308P P45/840 L170W3 PSU MB WH	4000 K	98 lm/W	4,410 lm
52450799	SP308P P45/865 L170W3 PSU WB WH	6500 K	98 lm/W	4,410 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
53028799	SM308C P22/830 L75W3 PSU WB WH	22 W
52524599	SM308C P22/840 L75W3 PSU MB WH	22 W
52869799	SM308C P22/865 L75W3 PSU WB WH	22 W
52351799	SM308C P30/865 L120W3 PSU WB WH	30 W
52768399	SM308C P38/830 L140W3 PSU MB WH	38 W
52606899	SM308C P38/865 L140W3 PSU WB WH	38 W
52527699	SM308C P45/840 L170W3 PSU MB WH	45 W
52872799	SM308C P45/865 L170W3 PSU WB WH	45 W

Order Code	Full Product Name	Power Consumption
52769099	SP308P P22/830 L75W3 PSU WB WH	22 W
52443999	SP308P P22/865 L75W3 PSU WB WH	22 W
52609999	SP308P P30/865 L120W3 PSU WB WH	30 W
52357999	SP308P P38/830 L140W3 PSU WB WH	38 W
52878999	SP308P P38/865 L140W3 PSU WB WH	38 W
53167399	SP308P P45/840 L170W3 PSU MB WH	45 W
52450799	SP308P P45/865 L170W3 PSU WB WH	45 W

