

FlexBlend, Suspended

SP340P



FlexBlend heading the way to efficient and flexible furnished offices areas

Philips FlexBlend is an attractive family of surface mounted and suspended luminaires, next to Flexblend recessed. The luminaire range is enabling building owners to advance their lighting operations, by offering office-compliant lighting with a return on investment of less than 3 to 4 years. FlexBlend provides the required flexibility through the adaptability in design. This gives the possibility to install the luminaires easily in the field, at any moment. Even when today's luminaire is suspended, tomorrow this can be adapted to a surface mounted installation at the venue. And the other way around. . The surface mounted and suspended luminaire range fit to many different office spaces like open plan office, corridors, reception or meeting rooms. FlexBlend is offered in both lines and as standalone, using the same lighting module. This gives the option to the users to use FlexBlend as standalone now, and tomorrow, as line. The controller is integrated in the luminaire. As technology is changing fast, the ideal lighting solution is also expected to be ready to incorporate

innovations that can help optimize operations further. For this reason, FlexBlend holds all connectivity and future ready options available. As System Ready luminaire it can be paired with lighting management systems such as the Philips SpaceWise, and to software-based lighting systems as Interact Office wired (PoE) and Interact Office wireless and/or existing and upcoming sensor innovations. The luminaire range is therefore future ready and can be delivered without any system component, and in a next phase, in the field to be upgraded. An attractive opportunity for new installations and renovations.

Benefits

- Return of investment less than 3 years
- A flexible office, with application flexibility to the choice of luminaires to fit many office areas
- Future ready: scalable and ready to be connected to controls and lighting systems

Applications

- Offices
- Education
- Healthcare

Features

- Fully office compliant (UGR <19, L65 < 3000cd/sm) , light level according to office applications requirements
- Homogenous and uniform light effect

Versions



FlexBlend Suspended SP340P
O WH



FlexBlend Surface Mounted-
Suspended Emergency
Lighting



FlexBlend Suspended SP340P
PCS BK



FlexBlend Suspended SP340P
PCS WH



FlexBlend Suspended-
SM340C-MLO-WH-SENS1-
L150



FlexBlend Suspended SP340P
MLO BK



FlexBlend Suspended SP340P
PCS SI



FlexBlend Suspended SP340P
MLO SI



FlexBlend Suspended SP340P
O SI






FlexBlend Suspended SP340P
MLO WH




FlexBlend Suspended SP340P
O BK

Dimensional drawing

FlexBlend SS L150 DIR IND






LINE
FlexBlend SS L150 DIR IND




FLEXBLEND SUSPENDED D/I LINE

FlexBlend SS L120 DIR IND






LINE
FlexBlend SS L120 DIR IND




FLEXBLEND SUSPENDED D/I STAND-ALONE

FlexBlend SM L120 DIR



LINE
FlexBlend SM L120 DIR




FLEXBLEND SUSPENDED D STAND-ALONE - Power supply unit with DALI and SystemReady interface, InterAct ready - Wide beam - 120°

Product details



FlexBlend Suspended SP340P
WH



FlexBlend_Surface_Mounted-
Suspended_Emergency
Lighting



FlexBlend Suspended SP340P




FlexBlend Suspended SP340P
O BK



FlexBlend_Surface_Mounted-
Suspended_Emergency
Lighting



FlexBlend Suspended SP340P
SI



FlexBlend Suspended SP340P
MLO SI




FlexBlend_Surface_Mounted-
Suspended_Emergency
Lighting




FlexBlend_Surface_Mounted-
Suspended_Emergency
Lighting



FlexBlend Suspended SP340P
PCS WH



FlexBlend Suspended SP340P
O SI



FlexBlend Suspended SP340P
O SI



FlexBlend_Surface_Mounted-
Suspended_Emergency
Lighting



FlexBlend Suspended SP340P
PCS SI



FlexBlend Suspended SP340P
PCS BK



FlexBlend Suspended SP340P
SI




FlexBlend Suspended SP340P
WH



FlexBlend Suspended SP340P
BK



FlexBlend_Suspended_SP340
P-line-MLO-WH-SWZU



FlexBlend Suspended SP340P
MLO BK




FlexBlend Suspended SP340P
MLO BK



FlexBlend_Surface_Mounted-
Suspended_Emergency
Lighting



FlexBlend Suspended SP340P
BK



FlexBlend Suspended SP340P
MLO SI



FlexBlend Surface Mounted
SM340C




FlexBlend Suspended SP340P
O WH



FlexBlend Suspended SP340P
MLO WH



FlexBlend Suspended SP340P
SI



FlexBlend Suspended SP340P
PCS BK



FlexBlend Suspended SP340P
BK



FlexBlend Suspended SP340P
O WH




FlexBlend Suspended SP340P
WH



FlexBlend Suspended SP340P
WH



FlexBlend_Surface_Mounted-
Suspended_Emergency
Lighting



FlexBlend Suspended SP340P
PCS SI




FlexBlend_Surface_Mounted-
Suspended_Emergency
Lighting



FlexBlend_Surface_Mounted-
Suspended_Emergency
Lighting



FlexBlend Suspended SP340P
WH



FlexBlend Suspended SP340P
MLO WH




FlexBlend Suspended SP340P
BK




FlexBlend Suspended SP340P
SI




FlexBlend Suspended SP340P
BK



FlexBlend Suspended SP340P
PCS WH



FlexBlend Suspended SP340P
SI



FlexBlend Suspended SP340P
O BK

General Information

Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Service tag	Yes

Light Technical

Color rendering index (CRI)	>90
Optic type	Wide beam

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Protection class IEC	Safety class I

Controls and Dimming

Dimmable	Yes
Maximum dim level	1%
Embedded control	Upgradable sensor slot with SC200 sensor

Mechanical and Housing

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]

Emergency Operation

Rated duration of the emergency lighting (when fully charged)	3 hour(s)
---	-----------

Approval and Application

Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.05 %
-------------------------------	--------

Light Technical

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Beam angle of light source
910925867117	SP342P 45S/940 DEIA O SMT L150 WH	4,500 lm	4000 K	136 lm/W	120 degree(s)
910925867924	SP342P 36S/940 DEIA O SMT L120 WH	3,600 lm	4000 K	128 lm/W	120 degree(s)
910925867940	SP342P 45S/930 DEIA O SMT L150 WH	4,500 lm	3000 K	136 lm/W	120 degree(s)
910925867958	SP343P 35S/940 DEIA O SMT L150 WH	3,500 lm	4000 K	140 lm/W	120 degree(s)
910925868101	SP342P 52S/940 DIA MLO ELP3 SMT L120 WH	5,200 lm	4000 K	108 lm/W	120 degree(s)
910925867106	SP342P 45S/940 DEIA PCS SMT L150 BK	4,500 lm	4000 K	145 lm/W	120 degree(s)
910925867104	SP342P 45S/940 DEIA PCS SMT L150 WH	4,500 lm	4000 K	145 lm/W	120 degree(s)
910925867126	SP340P 36S/940 DEIA PCS SMT L120 WH	3,600 lm	4000 K	138 lm/W	120 degree(s)
910925867127	SP340P 42S/940 DEIA PCS SMT L120 WH	4,200 lm	4000 K	143 lm/W	120 degree(s)

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Beam angle of light source
910925867130	SP342P 48S/940 DEIA PCS SMT L120 WH	4,800 lm	4000 K	141 lm/W	120 degree(s)
910925867918	SP342P 36S/940 DEIA PCS SMT L120 WH	3,600 lm	4000 K	141 lm/W	120 degree(s)
910925867932	SP342P 60S/940 DEIA PCS SMT L150 WH	6,000 lm	4000 K	140 lm/W	120 degree(s)
910925867933	SP342P 70S/940 DEIA PCS SMT L150 WH	7,000 lm	4000 K	137 lm/W	120 degree(s)
910925867936	SP342P 45S/930 DEIA PCS SMT L150 WH	4,500 lm	3000 K	145 lm/W	120 degree(s)
910925867937	SP342P 60S/930 DEIA PCS SMT L150 WH	6,000 lm	3000 K	140 lm/W	120 degree(s)
910925867954	SP343P 35S/940 DEIA PCS SMT L150 WH	3,500 lm	4000 K	140 lm/W	120 degree(s)
910925867955	SP343P 45S/940 DEIA PCS SMT L150 WH	4,500 lm	4000 K	145 lm/W	120 degree(s)
910925868894	SP340P 42S/930 SEIA PCS U4 SMT L120 WH	4,200 lm	3000 K	143 lm/W	- degree(s)
910925868895	SP340P 42S/940 SEIA PCS U4 SMT L120 WH	4,200 lm	4000 K	143 lm/W	- degree(s)
910925868896	SP342P 45S/930 SEIA MLO U4 SMT L150 WH	4,500 lm	3000 K	110 lm/W	- degree(s)
910925868897	SP342P 45S/940 SEIA MLO U4 SMT L150 WH	4,500 lm	4000 K	110 lm/W	- degree(s)
910925868905	SP342P 60S/940 SEIA PCS U4 SMT L150 WH	6,000 lm	4000 K	140 lm/W	- degree(s)
910925868906	SP342P 45S/940 SEIA PCS U4 SMT L150 WH	4,500 lm	4000 K	140 lm/W	- degree(s)
910925868907	SP340P 40S/940 SEIA MLO U4 SMT L120 WH	4,000 lm	4000 K	96 lm/W	- degree(s)
910925868908	SP340P 36S/940 SEIA PCS U4 SMT L120 WH	3,600 lm	4000 K	141 lm/W	- degree(s)
910925868909	SP340P 36S/940 SEIA MLO U4 SMT L120 WH	3,600 lm	4000 K	97 lm/W	- degree(s)
910925867114	SP342P 45S/940 DEIA MLO SMT L150 BK	4,500 lm	4000 K	112 lm/W	120 degree(s)
910925867105	SP342P 45S/940 DEIA PCS SMT L150 SI	4,500 lm	4000 K	145 lm/W	120 degree(s)
910925867925	SP342P 36S/940 DEIA PCS SMT L120 SI	3,600 lm	4000 K	141 lm/W	120 degree(s)
910925867926	SP342P 48S/940 DEIA PCS SMT L120 SI	4,800 lm	4000 K	138 lm/W	120 degree(s)
910925867927	SP342P 56S/940 DEIA PCS SMT L120 SI	5,200 lm	4000 K	130 lm/W	120 degree(s)
910925867941	SP342P 60S/940 DEIA PCS SMT L150 SI	6,000 lm	4000 K	140 lm/W	120 degree(s)
910925867959	SP343P 35S/940 DEIA PCS SMT L150 SI	3,500 lm	4000 K	140 lm/W	120 degree(s)
910925867960	SP343P 45S/940 DEIA PCS SMT L150 SI	4,500 lm	4000 K	145 lm/W	120 degree(s)
910925867113	SP342P 45S/940 DEIA MLO SMT L150 SI	4,500 lm	4000 K	112 lm/W	120 degree(s)
910925867928	SP342P 36S/940 DEIA MLO SMT L120 SI	3,600 lm	4000 K	110 lm/W	120 degree(s)
910925867929	SP342P 48S/940 DEIA MLO SMT L120 SI	4,800 lm	4000 K	109 lm/W	120 degree(s)
910925867930	SP342P 52S/940 DEIA MLO SMT L120 SI	5,200 lm	4000 K	108 lm/W	120 degree(s)
910925867942	SP342P 60S/940 DEIA MLO SMT L150 SI	6,000 lm	4000 K	102 lm/W	120 degree(s)
910925867943	SP342P 66S/940 DEIA MLO SMT L150 SI	6,600 lm	4000 K	106 lm/W	120 degree(s)
910925867961	SP343P 35S/940 DEIA MLO SMT L150 SI	3,500 lm	4000 K	110 lm/W	120 degree(s)
910925867962	SP343P 45S/940 DEIA MLO SMT L150 SI	4,500 lm	4000 K	112 lm/W	120 degree(s)
910925867931	SP342P 36S/940 DEIA O SMT L120 SI	3,600 lm	4000 K	128 lm/W	120 degree(s)
910925867944	SP342P 45S/940 DEIA O SMT L150 SI	4,500 lm	4000 K	136 lm/W	120 degree(s)
910925867963	SP343P 35S/940 DEIA O SMT L150 SI	3,500 lm	4000 K	140 lm/W	120 degree(s)
910925867112	SP342P 45S/940 DEIA MLO SMT L150 WH	4,500 lm	4000 K	112 lm/W	120 degree(s)
910925867128	SP340P 36S/940 DEIA MLO SMT L120 WH	3,600 lm	4000 K	95 lm/W	120 degree(s)
910925867129	SP340P 40S/940 DEIA MLO SMT L120 WH	4,000 lm	4000 K	94 lm/W	120 degree(s)
910925867132	SP342P 48S/940 DEIA MLO SMT L120 WH	4,800 lm	4000 K	109 lm/W	120 degree(s)
910925867133	SP342P 52S/940 DEIA MLO SMT L120 WH	5,200 lm	4000 K	108 lm/W	120 degree(s)
910925867921	SP342P 36S/940 DEIA MLO SMT L120 WH	3,600 lm	4000 K	110 lm/W	120 degree(s)

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Beam angle of light source
910925867934	SP342P 60S/940 DEIA MLO SMT L150 WH	6,000 lm	4000 K	111 lm/W	120 degree(s)
910925867935	SP342P 66S/940 DEIA MLO SMT L150 WH	6,600 lm	4000 K	106 lm/W	120 degree(s)
910925867938	SP342P 45S/930 DEIA MLO SMT L150 WH	4,500 lm	3000 K	112 lm/W	120 degree(s)
910925867939	SP342P 60S/930 DEIA MLO SMT L150 WH	6,000 lm	3000 K	98.5 lm/W	120 degree(s)
910925867956	SP343P 35S/940 DEIA MLO SMT L150 WH	3,500 lm	4000 K	110 lm/W	120 degree(s)
910925867957	SP343P 45S/940 DEIA MLO SMT L150 WH	4,500 lm	4000 K	112 lm/W	120 degree(s)
910925867945	SP342P 45S/940 DEIA O SMT L150 BK	4,500 lm	4000 K	136 lm/W	120 degree(s)

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Suitable for random switching
910925867117	SP342P 45S/940 DEIA O SMT L150 WH	37.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867924	SP342P 36S/940 DEIA O SMT L120 WH	29 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867940	SP342P 45S/930 DEIA O SMT L150 WH	39 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867958	SP343P 35S/940 DEIA O SMT L150 WH	29 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925868101	SP342P 52S/940 DIA MLO ELP3 SMT L120 WH	52.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867106	SP342P 45S/940 DEIA PCS SMT L150 BK	35 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867104	SP342P 45S/940 DEIA PCS SMT L150 WH	35 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867126	SP340P 36S/940 DEIA PCS SMT L120 WH	26.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867127	SP340P 42S/940 DEIA PCS SMT L120 WH	32 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867130	SP342P 48S/940 DEIA PCS SMT L120 WH	36 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867918	SP342P 36S/940 DEIA PCS SMT L120 WH	27 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867932	SP342P 60S/940 DEIA PCS SMT L150 WH	46.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867933	SP342P 70S/940 DEIA PCS SMT L150 WH	52 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867936	SP342P 45S/930 DEIA PCS SMT L150 WH	36.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867937	SP342P 60S/930 DEIA PCS SMT L150 WH	49.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867954	SP343P 35S/940 DEIA PCS SMT L150 WH	27.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867955	SP343P 45S/940 DEIA PCS SMT L150 WH	35 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925868894	SP340P 42S/930 SEIA PCS U4 SMT L120 WH	27 W	No
910925868895	SP340P 42S/940 SEIA PCS U4 SMT L120 WH	27 W	No

Order Code	Full Product Name	Power Consumption	Suitable for random switching
910925868896	SP342P 45S/930 SEIA MLO U4 SMT L150 WH	44.5 W	No
910925868897	SP342P 45S/940 SEIA MLO U4 SMT L150 WH	42.5 W	No
910925868905	SP342P 60S/940 SEIA PCS U4 SMT L150 WH	46.5 W	No
910925868906	SP342P 45S/940 SEIA PCS U4 SMT L150 WH	35 W	No
910925868907	SP340P 40S/940 SEIA MLO U4 SMT L120 WH	38.5 W	No
910925868908	SP340P 36S/940 SEIA PCS U4 SMT L120 WH	26 W	No
910925868909	SP340P 36S/940 SEIA MLO U4 SMT L120 WH	32.5 W	No
910925867114	SP342P 45S/940 DEIA MLO SMT L150 BK	42.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867105	SP342P 45S/940 DEIA PCS SMT L150 SI	35 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867925	SP342P 36S/940 DEIA PCS SMT L120 SI	27 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867926	SP342P 48S/940 DEIA PCS SMT L120 SI	36 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867927	SP342P 56S/940 DEIA PCS SMT L120 SI	40 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867941	SP342P 60S/940 DEIA PCS SMT L150 SI	46.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867959	SP343P 35S/940 DEIA PCS SMT L150 SI	27.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867960	SP343P 45S/940 DEIA PCS SMT L150 SI	35 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867113	SP342P 45S/940 DEIA MLO SMT L150 SI	42.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867928	SP342P 36S/940 DEIA MLO SMT L120 SI	32.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867929	SP342P 48S/940 DEIA MLO SMT L120 SI	44.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867930	SP342P 52S/940 DEIA MLO SMT L120 SI	48.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867942	SP342P 60S/940 DEIA MLO SMT L150 SI	59 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867943	SP342P 66S/940 DEIA MLO SMT L150 SI	64 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867961	SP343P 35S/940 DEIA MLO SMT L150 SI	32.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867962	SP343P 45S/940 DEIA MLO SMT L150 SI	42.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867931	SP342P 36S/940 DEIA O SMT L120 SI	29 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867944	SP342P 45S/940 DEIA O SMT L150 SI	37.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867963	SP343P 35S/940 DEIA O SMT L150 SI	29 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867112	SP342P 45S/940 DEIA MLO SMT L150 WH	42.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867128	SP340P 36S/940 DEIA MLO SMT L120 WH	35 W	Yes (relates to presence/ movement detection and daylight harvesting)

Order Code	Full Product Name	Power Consumption	Suitable for random switching
910925867129	SP340P 40S/940 DEIA MLO SMT L120 WH	39 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867132	SP342P 48S/940 DEIA MLO SMT L120 WH	44.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867133	SP342P 52S/940 DEIA MLO SMT L120 WH	48.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867921	SP342P 36S/940 DEIA MLO SMT L120 WH	32.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867934	SP342P 60S/940 DEIA MLO SMT L150 WH	59 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867935	SP342P 66S/940 DEIA MLO SMT L150 WH	64 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867938	SP342P 45S/930 DEIA MLO SMT L150 WH	48 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867939	SP342P 60S/930 DEIA MLO SMT L150 WH	61 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867956	SP343P 35S/940 DEIA MLO SMT L150 WH	32.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867957	SP343P 45S/940 DEIA MLO SMT L150 WH	42.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867945	SP342P 45S/940 DEIA O SMT L150 BK	37.5 W	Yes (relates to presence/ movement detection and daylight harvesting)

Mechanical and Housing

Order Code	Full Product Name	Housing Color
910925867117	SP342P 45S/940 DEIA O SMT L150 WH	White
910925867924	SP342P 36S/940 DEIA O SMT L120 WH	White
910925867940	SP342P 45S/930 DEIA O SMT L150 WH	White
910925867958	SP343P 35S/940 DEIA O SMT L150 WH	White
910925868101	SP342P 52S/940 DIA MLO ELP3 SMT L120 WH	White
910925867106	SP342P 45S/940 DEIA PCS SMT L150 BK	Black
910925867104	SP342P 45S/940 DEIA PCS SMT L150 WH	White
910925867126	SP340P 36S/940 DEIA PCS SMT L120 WH	White
910925867127	SP340P 42S/940 DEIA PCS SMT L120 WH	White
910925867130	SP342P 48S/940 DEIA PCS SMT L120 WH	White
910925867918	SP342P 36S/940 DEIA PCS SMT L120 WH	White
910925867932	SP342P 60S/940 DEIA PCS SMT L150 WH	White
910925867933	SP342P 70S/940 DEIA PCS SMT L150 WH	White
910925867936	SP342P 45S/930 DEIA PCS SMT L150 WH	White
910925867937	SP342P 60S/930 DEIA PCS SMT L150 WH	White
910925867954	SP343P 35S/940 DEIA PCS SMT L150 WH	White
910925867955	SP343P 45S/940 DEIA PCS SMT L150 WH	White
910925868894	SP340P 42S/930 SEIA PCS U4 SMT L120 WH	White
910925868895	SP340P 42S/940 SEIA PCS U4 SMT L120 WH	White
910925868896	SP342P 45S/930 SEIA MLO U4 SMT L150 WH	White
910925868897	SP342P 45S/940 SEIA MLO U4 SMT L150 WH	White

Order Code	Full Product Name	Housing Color
910925868905	SP342P 60S/940 SEIA PCS U4 SMT L150 WH	White
910925868906	SP342P 45S/940 SEIA PCS U4 SMT L150 WH	White
910925868907	SP340P 40S/940 SEIA MLO U4 SMT L120 WH	White
910925868908	SP340P 36S/940 SEIA PCS U4 SMT L120 WH	White
910925868909	SP340P 36S/940 SEIA MLO U4 SMT L120 WH	White
910925867114	SP342P 45S/940 DEIA MLO SMT L150 BK	Black
910925867105	SP342P 45S/940 DEIA PCS SMT L150 SI	Silver
910925867925	SP342P 36S/940 DEIA PCS SMT L120 SI	Silver
910925867926	SP342P 48S/940 DEIA PCS SMT L120 SI	Silver
910925867927	SP342P 56S/940 DEIA PCS SMT L120 SI	Silver
910925867941	SP342P 60S/940 DEIA PCS SMT L150 SI	Silver
910925867959	SP343P 35S/940 DEIA PCS SMT L150 SI	Silver
910925867960	SP343P 45S/940 DEIA PCS SMT L150 SI	Silver
910925867113	SP342P 45S/940 DEIA MLO SMT L150 SI	Silver
910925867928	SP342P 36S/940 DEIA MLO SMT L120 SI	Silver
910925867929	SP342P 48S/940 DEIA MLO SMT L120 SI	Silver
910925867930	SP342P 52S/940 DEIA MLO SMT L120 SI	Silver
910925867942	SP342P 60S/940 DEIA MLO SMT L150 SI	Silver
910925867943	SP342P 66S/940 DEIA MLO SMT L150 SI	Silver
910925867961	SP343P 35S/940 DEIA MLO SMT L150 SI	Silver
910925867962	SP343P 45S/940 DEIA MLO SMT L150 SI	Silver
910925867931	SP342P 36S/940 DEIA O SMT L120 SI	Silver
910925867944	SP342P 45S/940 DEIA O SMT L150 SI	Silver
910925867963	SP343P 35S/940 DEIA O SMT L150 SI	Silver
910925867112	SP342P 45S/940 DEIA MLO SMT L150 WH	White
910925867128	SP340P 36S/940 DEIA MLO SMT L120 WH	White
910925867129	SP340P 40S/940 DEIA MLO SMT L120 WH	White
910925867132	SP342P 48S/940 DEIA MLO SMT L120 WH	White
910925867133	SP342P 52S/940 DEIA MLO SMT L120 WH	White
910925867921	SP342P 36S/940 DEIA MLO SMT L120 WH	White
910925867934	SP342P 60S/940 DEIA MLO SMT L150 WH	White
910925867935	SP342P 66S/940 DEIA MLO SMT L150 WH	White
910925867938	SP342P 45S/930 DEIA MLO SMT L150 WH	White
910925867939	SP342P 60S/930 DEIA MLO SMT L150 WH	White
910925867956	SP343P 35S/940 DEIA MLO SMT L150 WH	White
910925867957	SP343P 45S/940 DEIA MLO SMT L150 WH	White
910925867945	SP342P 45S/940 DEIA O SMT L150 BK	Black

Emergency Operation

Order Code	Full Product Name	Central Emergency	Emergency lighting
910925867117	SP342P 45S/940 DEIA O SMT L150 WH	Yes	DC operated central emergency lighting

Order Code	Full Product Name	Central Emergency	Emergency lighting
910925867924	SP342P 36S/940 DEIA O SMT L120 WH	Yes	DC operated central emergency lighting
910925867940	SP342P 45S/930 DEIA O SMT L150 WH	Yes	DC operated central emergency lighting
910925867958	SP343P 35S/940 DEIA O SMT L150 WH	Yes	DC operated central emergency lighting
910925868101	SP342P 52S/940 DIA MLO ELP3 SMT L120 WH	No	Emergency lighting 3 hours duration Pro version
910925867106	SP342P 45S/940 DEIA PCS SMT L150 BK	Yes	DC operated central emergency lighting
910925867104	SP342P 45S/940 DEIA PCS SMT L150 WH	Yes	DC operated central emergency lighting
910925867126	SP340P 36S/940 DEIA PCS SMT L120 WH	Yes	DC operated central emergency lighting
910925867127	SP340P 42S/940 DEIA PCS SMT L120 WH	Yes	DC operated central emergency lighting
910925867130	SP342P 48S/940 DEIA PCS SMT L120 WH	Yes	DC operated central emergency lighting
910925867918	SP342P 36S/940 DEIA PCS SMT L120 WH	Yes	DC operated central emergency lighting
910925867932	SP342P 60S/940 DEIA PCS SMT L150 WH	Yes	DC operated central emergency lighting
910925867933	SP342P 70S/940 DEIA PCS SMT L150 WH	Yes	DC operated central emergency lighting
910925867936	SP342P 45S/930 DEIA PCS SMT L150 WH	Yes	DC operated central emergency lighting
910925867937	SP342P 60S/930 DEIA PCS SMT L150 WH	Yes	DC operated central emergency lighting
910925867954	SP343P 35S/940 DEIA PCS SMT L150 WH	Yes	DC operated central emergency lighting
910925867955	SP343P 45S/940 DEIA PCS SMT L150 WH	Yes	DC operated central emergency lighting
910925868894	SP340P 42S/930 SEIA PCS U4 SMT L120 WH	Yes	DC operated central emergency lighting
910925868895	SP340P 42S/940 SEIA PCS U4 SMT L120 WH	Yes	DC operated central emergency lighting
910925868896	SP342P 45S/930 SEIA MLO U4 SMT L150 WH	Yes	DC operated central emergency lighting
910925868897	SP342P 45S/940 SEIA MLO U4 SMT L150 WH	Yes	DC operated central emergency lighting
910925868905	SP342P 60S/940 SEIA PCS U4 SMT L150 WH	Yes	DC operated central emergency lighting
910925868906	SP342P 45S/940 SEIA PCS U4 SMT L150 WH	Yes	DC operated central emergency lighting
910925868907	SP340P 40S/940 SEIA MLO U4 SMT L120 WH	Yes	DC operated central emergency lighting
910925868908	SP340P 36S/940 SEIA PCS U4 SMT L120 WH	Yes	DC operated central emergency lighting
910925868909	SP340P 36S/940 SEIA MLO U4 SMT L120 WH	Yes	DC operated central emergency lighting
910925867114	SP342P 45S/940 DEIA MLO SMT L150 BK	Yes	DC operated central emergency lighting
910925867105	SP342P 45S/940 DEIA PCS SMT L150 SI	Yes	DC operated central emergency lighting
910925867925	SP342P 36S/940 DEIA PCS SMT L120 SI	Yes	DC operated central emergency lighting
910925867926	SP342P 48S/940 DEIA PCS SMT L120 SI	Yes	DC operated central emergency lighting
910925867927	SP342P 56S/940 DEIA PCS SMT L120 SI	Yes	DC operated central emergency lighting
910925867941	SP342P 60S/940 DEIA PCS SMT L150 SI	Yes	DC operated central emergency lighting
910925867959	SP343P 35S/940 DEIA PCS SMT L150 SI	Yes	DC operated central emergency lighting
910925867960	SP343P 45S/940 DEIA PCS SMT L150 SI	Yes	DC operated central emergency lighting
910925867113	SP342P 45S/940 DEIA MLO SMT L150 SI	Yes	DC operated central emergency lighting
910925867928	SP342P 36S/940 DEIA MLO SMT L120 SI	Yes	DC operated central emergency lighting
910925867929	SP342P 48S/940 DEIA MLO SMT L120 SI	Yes	DC operated central emergency lighting
910925867930	SP342P 52S/940 DEIA MLO SMT L120 SI	Yes	DC operated central emergency lighting
910925867942	SP342P 60S/940 DEIA MLO SMT L150 SI	Yes	DC operated central emergency lighting
910925867943	SP342P 66S/940 DEIA MLO SMT L150 SI	Yes	DC operated central emergency lighting
910925867961	SP343P 35S/940 DEIA MLO SMT L150 SI	Yes	DC operated central emergency lighting
910925867962	SP343P 45S/940 DEIA MLO SMT L150 SI	Yes	DC operated central emergency lighting
910925867931	SP342P 36S/940 DEIA O SMT L120 SI	Yes	DC operated central emergency lighting

Order Code	Full Product Name	Central Emergency	Emergency lighting
910925867944	SP342P 45S/940 DEIA O SMT L150 SI	Yes	DC operated central emergency lighting
910925867963	SP343P 35S/940 DEIA O SMT L150 SI	Yes	DC operated central emergency lighting
910925867112	SP342P 45S/940 DEIA MLO SMT L150 WH	Yes	DC operated central emergency lighting
910925867128	SP340P 36S/940 DEIA MLO SMT L120 WH	Yes	DC operated central emergency lighting
910925867129	SP340P 40S/940 DEIA MLO SMT L120 WH	Yes	DC operated central emergency lighting
910925867132	SP342P 48S/940 DEIA MLO SMT L120 WH	Yes	DC operated central emergency lighting
910925867133	SP342P 52S/940 DEIA MLO SMT L120 WH	Yes	DC operated central emergency lighting
910925867921	SP342P 36S/940 DEIA MLO SMT L120 WH	Yes	DC operated central emergency lighting
910925867934	SP342P 60S/940 DEIA MLO SMT L150 WH	Yes	DC operated central emergency lighting
910925867935	SP342P 66S/940 DEIA MLO SMT L150 WH	Yes	DC operated central emergency lighting
910925867938	SP342P 45S/930 DEIA MLO SMT L150 WH	Yes	DC operated central emergency lighting
910925867939	SP342P 60S/930 DEIA MLO SMT L150 WH	Yes	DC operated central emergency lighting
910925867956	SP343P 35S/940 DEIA MLO SMT L150 WH	Yes	DC operated central emergency lighting
910925867957	SP343P 45S/940 DEIA MLO SMT L150 WH	Yes	DC operated central emergency lighting
910925867945	SP342P 45S/940 DEIA O SMT L150 BK	Yes	DC operated central emergency lighting

Approval and Application

Order Code	Full Product Name	Glow-wire test	ENEC mark	Ambient temperature range
910925867117	SP342P 45S/940 DEIA O SMT L150 WH	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867924	SP342P 36S/940 DEIA O SMT L120 WH	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867940	SP342P 45S/930 DEIA O SMT L150 WH	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867958	SP343P 35S/940 DEIA O SMT L150 WH	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925868101	SP342P 52S/940 DIA MLO ELP3 SMT L120 WH	Temperature 650 °C, duration 30 s	ENEC plus mark	+10 to +25 °C
910925867106	SP342P 45S/940 DEIA PCS SMT L150 BK	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867104	SP342P 45S/940 DEIA PCS SMT L150 WH	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867126	SP340P 36S/940 DEIA PCS SMT L120 WH	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867127	SP340P 42S/940 DEIA PCS SMT L120 WH	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867130	SP342P 48S/940 DEIA PCS SMT L120 WH	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867918	SP342P 36S/940 DEIA PCS SMT L120 WH	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867932	SP342P 60S/940 DEIA PCS SMT L150 WH	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867933	SP342P 70S/940 DEIA PCS SMT L150 WH	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867936	SP342P 45S/930 DEIA PCS SMT L150 WH	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867937	SP342P 60S/930 DEIA PCS SMT L150 WH	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867954	SP343P 35S/940 DEIA PCS SMT L150 WH	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867955	SP343P 45S/940 DEIA PCS SMT L150 WH	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925868894	SP340P 42S/930 SEIA PCS U4 SMT L120 WH	Temperature 850 °C, duration 30 s	ENEC mark	+10 to +40 °C
910925868895	SP340P 42S/940 SEIA PCS U4 SMT L120 WH	Temperature 850 °C, duration 30 s	ENEC mark	+10 to +40 °C
910925868896	SP342P 45S/930 SEIA MLO U4 SMT L150 WH	Temperature 650 °C, duration 30 s	ENEC mark	+10 to +40 °C
910925868897	SP342P 45S/940 SEIA MLO U4 SMT L150 WH	Temperature 650 °C, duration 30 s	ENEC mark	+10 to +40 °C
910925868905	SP342P 60S/940 SEIA PCS U4 SMT L150 WH	Temperature 850 °C, duration 30 s	ENEC mark	+10 to +40 °C
910925868906	SP342P 45S/940 SEIA PCS U4 SMT L150 WH	Temperature 850 °C, duration 30 s	ENEC mark	+10 to +40 °C

Order Code	Full Product Name	Glow-wire test	ENEC mark	Ambient temperature range
910925868907	SP340P 40S/940 SEIA MLO U4 SMT L120 WH	Temperature 650 °C, duration 30 s	ENEC mark	+10 to +40 °C
910925868908	SP340P 36S/940 SEIA PCS U4 SMT L120 WH	Temperature 850 °C, duration 30 s	ENEC mark	+10 to +40 °C
910925868909	SP340P 36S/940 SEIA MLO U4 SMT L120 WH	Temperature 650 °C, duration 30 s	ENEC mark	+10 to +40 °C
910925867114	SP342P 45S/940 DEIA MLO SMT L150 BK	Temperature 650 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867105	SP342P 45S/940 DEIA PCS SMT L150 SI	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867925	SP342P 36S/940 DEIA PCS SMT L120 SI	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867926	SP342P 48S/940 DEIA PCS SMT L120 SI	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867927	SP342P 56S/940 DEIA PCS SMT L120 SI	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867941	SP342P 60S/940 DEIA PCS SMT L150 SI	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867959	SP343P 35S/940 DEIA PCS SMT L150 SI	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867960	SP343P 45S/940 DEIA PCS SMT L150 SI	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867113	SP342P 45S/940 DEIA MLO SMT L150 SI	Temperature 650 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867928	SP342P 36S/940 DEIA MLO SMT L120 SI	Temperature 650 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867929	SP342P 48S/940 DEIA MLO SMT L120 SI	Temperature 650 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867930	SP342P 52S/940 DEIA MLO SMT L120 SI	Temperature 650 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867942	SP342P 60S/940 DEIA MLO SMT L150 SI	Temperature 650 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867943	SP342P 66S/940 DEIA MLO SMT L150 SI	Temperature 650 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867961	SP343P 35S/940 DEIA MLO SMT L150 SI	Temperature 650 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867962	SP343P 45S/940 DEIA MLO SMT L150 SI	Temperature 650 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867931	SP342P 36S/940 DEIA O SMT L120 SI	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867944	SP342P 45S/940 DEIA O SMT L150 SI	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867963	SP343P 35S/940 DEIA O SMT L150 SI	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867112	SP342P 45S/940 DEIA MLO SMT L150 WH	Temperature 650 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867128	SP340P 36S/940 DEIA MLO SMT L120 WH	Temperature 650 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867129	SP340P 40S/940 DEIA MLO SMT L120 WH	Temperature 650 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867132	SP342P 48S/940 DEIA MLO SMT L120 WH	Temperature 650 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867133	SP342P 52S/940 DEIA MLO SMT L120 WH	Temperature 650 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867921	SP342P 36S/940 DEIA MLO SMT L120 WH	Temperature 650 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867934	SP342P 60S/940 DEIA MLO SMT L150 WH	Temperature 650 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867935	SP342P 66S/940 DEIA MLO SMT L150 WH	Temperature 650 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867938	SP342P 45S/930 DEIA MLO SMT L150 WH	Temperature 650 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867939	SP342P 60S/930 DEIA MLO SMT L150 WH	Temperature 650 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867956	SP343P 35S/940 DEIA MLO SMT L150 WH	Temperature 650 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867957	SP343P 45S/940 DEIA MLO SMT L150 WH	Temperature 650 °C, duration 30 s	ENEC plus mark	+10 to +40 °C
910925867945	SP342P 45S/940 DEIA O SMT L150 BK	Temperature 850 °C, duration 30 s	ENEC plus mark	+10 to +40 °C

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910925867117	SP342P 45S/940 DEIA O SMT L150 WH	(0.38, 0.38) SDCM <3
910925867924	SP342P 36S/940 DEIA O SMT L120 WH	(0.38, 0.38) SDCM <3
910925867940	SP342P 45S/930 DEIA O SMT L150 WH	(0.43, 0.40) SDCM <3

Order Code	Full Product Name	Initial chromaticity
910925867958	SP343P 35S/940 DEIA O SMT L150 WH	(0.38, 0.38) SDCM <3
910925868101	SP342P 52S/940 DIA MLO ELP3 SMT L120 WH	(0.38, 0.37) SDCM <3
910925867106	SP342P 45S/940 DEIA PCS SMT L150 BK	(0.38, 0.38) SDCM <3
910925867104	SP342P 45S/940 DEIA PCS SMT L150 WH	(0.38, 0.38) SDCM <3
910925867126	SP340P 36S/940 DEIA PCS SMT L120 WH	(0.38, 0.38) SDCM <3
910925867127	SP340P 42S/940 DEIA PCS SMT L120 WH	(0.38, 0.38) SDCM <3
910925867130	SP342P 48S/940 DEIA PCS SMT L120 WH	(0.38, 0.38) SDCM <3
910925867918	SP342P 36S/940 DEIA PCS SMT L120 WH	(0.38, 0.38) SDCM <3
910925867932	SP342P 60S/940 DEIA PCS SMT L150 WH	(0.38, 0.38) SDCM <3
910925867933	SP342P 70S/940 DEIA PCS SMT L150 WH	(0.38, 0.38) SDCM <3
910925867936	SP342P 45S/930 DEIA PCS SMT L150 WH	(0.43, 0.40) SDCM <3
910925867937	SP342P 60S/930 DEIA PCS SMT L150 WH	(0.43, 0.40) SDCM <3
910925867954	SP343P 35S/940 DEIA PCS SMT L150 WH	(0.38, 0.38) SDCM <3
910925867955	SP343P 45S/940 DEIA PCS SMT L150 WH	(0.38, 0.38) SDCM <3
910925868894	SP340P 42S/930 SEIA PCS U4 SMT L120 WH	0.43,0.39
910925868895	SP340P 42S/940 SEIA PCS U4 SMT L120 WH	0.38,0.37
910925868896	SP342P 45S/930 SEIA MLO U4 SMT L150 WH	0.43,0.39
910925868897	SP342P 45S/940 SEIA MLO U4 SMT L150 WH	0.38,0.37
910925868905	SP342P 60S/940 SEIA PCS U4 SMT L150 WH	0.38,0.37
910925868906	SP342P 45S/940 SEIA PCS U4 SMT L150 WH	0.38,0.37
910925868907	SP340P 40S/940 SEIA MLO U4 SMT L120 WH	0.38,0.37
910925868908	SP340P 36S/940 SEIA PCS U4 SMT L120 WH	0.38,0.37
910925868909	SP340P 36S/940 SEIA MLO U4 SMT L120 WH	0.38,0.37
910925867114	SP342P 45S/940 DEIA MLO SMT L150 BK	(0.38, 0.38) SDCM <3
910925867105	SP342P 45S/940 DEIA PCS SMT L150 SI	(0.38, 0.38) SDCM <3
910925867925	SP342P 36S/940 DEIA PCS SMT L120 SI	(0.38, 0.38) SDCM <3
910925867926	SP342P 48S/940 DEIA PCS SMT L120 SI	(0.38, 0.38) SDCM <3
910925867927	SP342P 56S/940 DEIA PCS SMT L120 SI	(0.43, 0.40) SDCM <3
910925867941	SP342P 60S/940 DEIA PCS SMT L150 SI	(0.38, 0.38) SDCM <3
910925867959	SP343P 35S/940 DEIA PCS SMT L150 SI	(0.38, 0.38) SDCM <3
910925867960	SP343P 45S/940 DEIA PCS SMT L150 SI	(0.38, 0.38) SDCM <3
910925867113	SP342P 45S/940 DEIA MLO SMT L150 SI	(0.38, 0.38) SDCM <3
910925867928	SP342P 36S/940 DEIA MLO SMT L120 SI	(0.38, 0.38) SDCM <3
910925867929	SP342P 48S/940 DEIA MLO SMT L120 SI	(0.38, 0.38) SDCM <3
910925867930	SP342P 52S/940 DEIA MLO SMT L120 SI	(0.38, 0.38) SDCM <3
910925867942	SP342P 60S/940 DEIA MLO SMT L150 SI	(0.43, 0.40) SDCM <3
910925867943	SP342P 66S/940 DEIA MLO SMT L150 SI	(0.38, 0.38) SDCM <3
910925867961	SP343P 35S/940 DEIA MLO SMT L150 SI	(0.38, 0.38) SDCM <3
910925867962	SP343P 45S/940 DEIA MLO SMT L150 SI	(0.38, 0.38) SDCM <3
910925867931	SP342P 36S/940 DEIA O SMT L120 SI	(0.38, 0.38) SDCM <3
910925867944	SP342P 45S/940 DEIA O SMT L150 SI	(0.38, 0.38) SDCM <3
910925867963	SP343P 35S/940 DEIA O SMT L150 SI	(0.38, 0.38) SDCM <3


Order Code	Full Product Name	Initial chromaticity
910925867112	SP342P 45S/940 DEIA MLO SMT L150 WH	(0.38, 0.38) SDCM <3
910925867128	SP340P 36S/940 DEIA MLO SMT L120 WH	(0.38, 0.38) SDCM <3
910925867129	SP340P 40S/940 DEIA MLO SMT L120 WH	(0.38, 0.38) SDCM <3
910925867132	SP342P 48S/940 DEIA MLO SMT L120 WH	(0.38, 0.38) SDCM <3
910925867133	SP342P 52S/940 DEIA MLO SMT L120 WH	(0.38, 0.38) SDCM <3
910925867921	SP342P 36S/940 DEIA MLO SMT L120 WH	(0.38, 0.38) SDCM <3
910925867934	SP342P 60S/940 DEIA MLO SMT L150 WH	(0.43, 0.40) SDCM <3
910925867935	SP342P 66S/940 DEIA MLO SMT L150 WH	(0.38, 0.38) SDCM <3
910925867938	SP342P 45S/930 DEIA MLO SMT L150 WH	(0.43, 0.40) SDCM <3
910925867939	SP342P 60S/930 DEIA MLO SMT L150 WH	(0.43, 0.40) SDCM <3
910925867956	SP343P 35S/940 DEIA MLO SMT L150 WH	(0.38, 0.38) SDCM <3
910925867957	SP343P 45S/940 DEIA MLO SMT L150 WH	(0.38, 0.38) SDCM <3
910925867945	SP342P 45S/940 DEIA O SMT L150 BK	(0.38, 0.38) SDCM <3

Product Data

Order Code	Full Product Name	Product family code
910925867117	SP342P 45S/940 DEIA O SMT L150 WH	SP342P
910925867924	SP342P 36S/940 DEIA O SMT L120 WH	SP342P
910925867940	SP342P 45S/930 DEIA O SMT L150 WH	SP342P
910925867958	SP343P 35S/940 DEIA O SMT L150 WH	SP343P
910925868101	SP342P 52S/940 DIA MLO ELP3 SMT L120 WH	SP342P
910925867106	SP342P 45S/940 DEIA PCS SMT L150 BK	SP342P
910925867104	SP342P 45S/940 DEIA PCS SMT L150 WH	SP342P
910925867126	SP340P 36S/940 DEIA PCS SMT L120 WH	SP340P
910925867127	SP340P 42S/940 DEIA PCS SMT L120 WH	SP340P
910925867130	SP342P 48S/940 DEIA PCS SMT L120 WH	SP342P
910925867918	SP342P 36S/940 DEIA PCS SMT L120 WH	SP342P
910925867932	SP342P 60S/940 DEIA PCS SMT L150 WH	SP342P
910925867933	SP342P 70S/940 DEIA PCS SMT L150 WH	SP342P
910925867936	SP342P 45S/930 DEIA PCS SMT L150 WH	SP342P
910925867937	SP342P 60S/930 DEIA PCS SMT L150 WH	SP342P
910925867954	SP343P 35S/940 DEIA PCS SMT L150 WH	SP343P
910925867955	SP343P 45S/940 DEIA PCS SMT L150 WH	SP343P
910925868894	SP340P 42S/930 SEIA PCS U4 SMT L120 WH	SP340P
910925868895	SP340P 42S/940 SEIA PCS U4 SMT L120 WH	SP340P
910925868896	SP342P 45S/930 SEIA MLO U4 SMT L150 WH	SP342P
910925868897	SP342P 45S/940 SEIA MLO U4 SMT L150 WH	SP342P
910925868905	SP342P 60S/940 SEIA PCS U4 SMT L150 WH	SP342P
910925868906	SP342P 45S/940 SEIA PCS U4 SMT L150 WH	SP342P
910925868907	SP340P 40S/940 SEIA MLO U4 SMT L120 WH	SP340P
910925868908	SP340P 36S/940 SEIA PCS U4 SMT L120 WH	SP340P

Order Code	Full Product Name	Product family code
910925868909	SP340P 36S/940 SEIA MLO U4 SMT L120 WH	SP340P
910925867114	SP342P 45S/940 DEIA MLO SMT L150 BK	SP342P
910925867105	SP342P 45S/940 DEIA PCS SMT L150 SI	SP342P
910925867925	SP342P 36S/940 DEIA PCS SMT L120 SI	SP342P
910925867926	SP342P 48S/940 DEIA PCS SMT L120 SI	SP342P
910925867927	SP342P 56S/940 DEIA PCS SMT L120 SI	SP342P
910925867941	SP342P 60S/940 DEIA PCS SMT L150 SI	SP342P
910925867959	SP343P 35S/940 DEIA PCS SMT L150 SI	SP343P
910925867960	SP343P 45S/940 DEIA PCS SMT L150 SI	SP343P
910925867113	SP342P 45S/940 DEIA MLO SMT L150 SI	SP342P
910925867928	SP342P 36S/940 DEIA MLO SMT L120 SI	SP342P
910925867929	SP342P 48S/940 DEIA MLO SMT L120 SI	SP342P
910925867930	SP342P 52S/940 DEIA MLO SMT L120 SI	SP342P
910925867942	SP342P 60S/940 DEIA MLO SMT L150 SI	SP342P
910925867943	SP342P 66S/940 DEIA MLO SMT L150 SI	SP342P
910925867961	SP343P 35S/940 DEIA MLO SMT L150 SI	SP343P
910925867962	SP343P 45S/940 DEIA MLO SMT L150 SI	SP343P
910925867931	SP342P 36S/940 DEIA O SMT L120 SI	SP342P
910925867944	SP342P 45S/940 DEIA O SMT L150 SI	SP342P
910925867963	SP343P 35S/940 DEIA O SMT L150 SI	SP343P
910925867112	SP342P 45S/940 DEIA MLO SMT L150 WH	SP342P
910925867128	SP340P 36S/940 DEIA MLO SMT L120 WH	SP340P
910925867129	SP340P 40S/940 DEIA MLO SMT L120 WH	SP340P
910925867132	SP342P 48S/940 DEIA MLO SMT L120 WH	SP342P
910925867133	SP342P 52S/940 DEIA MLO SMT L120 WH	SP342P
910925867921	SP342P 36S/940 DEIA MLO SMT L120 WH	SP342P
910925867934	SP342P 60S/940 DEIA MLO SMT L150 WH	SP342P
910925867935	SP342P 66S/940 DEIA MLO SMT L150 WH	SP342P
910925867938	SP342P 45S/930 DEIA MLO SMT L150 WH	SP342P
910925867939	SP342P 60S/930 DEIA MLO SMT L150 WH	SP342P
910925867956	SP343P 35S/940 DEIA MLO SMT L150 WH	SP343P
910925867957	SP343P 45S/940 DEIA MLO SMT L150 WH	SP343P
910925867945	SP342P 45S/940 DEIA O SMT L150 BK	SP342P


Polar normal diagrams



SM340CI - 910925868905

SM340CI - 910925868897


SM340CI - 910925868896



SM340CI - 910925868908

SM340CI - 910925868895


SM340CI - 910925868909




SM340CI - 910925867117

SM340CI - 910925867127


SM340CI - 910925867128




SM340CI - 910925867105




SM340CI - 910925867129




SM340CI - 910925867112




SM340CI - 910925867113




SM340CI - 910925867114




SM340CI - 910925867925




SM340CI - 910925867933




SM340CI - 910925867957




SM340CI - 910925867104




SM340CI - 910925867106




SM340CI - 910925867126




SM340CI - 910925867130




SM340CI - 910925867132




SM340CI - 910925867133




SM340CI - 910925867918




SM340CI - 910925867931




SM340CI - 910925867932




SM340CI - 910925867937




SM340CI - 910925868894




SM340CI - 910925868906




SM340CI - 910925868907




SM340CI - 910925867921




SM340CI - 910925867924




SM340CI - 910925867927




SM340CI - 910925867928




SM340CI - 910925867929




SM340CI - 910925867930




SM340CI - 910925867934




SM340CI - 910925867935




SM340CI - 910925867939




SM340CI - 910925867938




SM340CI - 910925867940




SM340CI - 910925867936




SM340CI - 910925867941




SM340CI - 910925867943




SM340CI - 910925867944




SM340CI - 910925867954




SM340CI - 910925867945




SM340CI - 910925867955




SM340CI - 910925867942




SM340CI - 910925867926




SM340CI - 910925867956




SM340CI - 910925867960




SM340CI - 910925867958




SM340CI - 910925867961




SM340CI - 910925867962



SM340CI - 910925867963



SM340CI - 910925867959



SM340CI - 910925868101