



Philips TrueLine suspended: True line of light

TrueLine, suspended

Architects need a lighting solution that matches the interior architecture of the space they are enhancing. They want a light line with elegant proportions and high light levels that offers maximum design freedom. Philips TrueLine is a flexible linear luminaire for indoor office applications that offers excellent quality with the promise of future-proof upgrades. Specifiers need luminaires that save energy, at the same time as providing the right level of light. TrueLine recessed meets both these sets of requirements. Not only is it compliant with the WELL Building Standard for Light, TrueLine surface is rated UGR<19, which is compliant with all office norms (OC). TrueLine also comes in surface and recess-mounted versions. All the luminaires in the family are available in different lengths, shapes, colors and light outputs. This offers the ultimate design flexibility and unlimited possibilities. TrueLine luminaires are also a sustainable, future-proof choice with high efficiency up to 174 lm/W and the option to upgrade to wireless connectivity and control.

Benefits

- Extremely high efficacy for a line luminaire
- Office compliant lighting
- Future-ready, scalable smart office capabilities
- Compatible with the Interact connected lighting system
- Supports sustainable building design and energy-saving subsidy criteria

TrueLine, suspended

Features

- Highly-uniform lighting with excellent glare control (UGR<19, L65<3000cd/m2)
- Best-in-class efficacy up to 174 lm/W with our Ultra efficient offering
- 3000K, 4000K, and Tunable White versions, all CRI>90; Bio-up & Ultra efficient with CRI>80
- Long lifetime L90@50,000 hours
- Integrated sensors/wireless drivers for data collection, occupancy, daylight regulation and wayfinding
- Environmental Product Declaration (EPD)
- Recessed, suspended and surface mounted options, including all accessories

Application

- Offices
- Education
- Retail

Warnings and Safety

- The product is IPX0 and, as such, is not protected against water ingress. Therefore, we strongly recommend that the environment in which the luminaire is to be installed is suitably checked.
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure and the product warranty will become void

Versions



TrueLine-SP534P



SP530P with U4 BK sensor



TrueLine-SP530 L570 WH



TrueLine-SP530 L2810 BK



TrueLine-SP530 U3 SNS210 L2850 Alu




TrueLine-SP530 L2810 WH




TrueLine Suspended black housing

Dimensional drawing



Dimensional drawing



TrueLine, suspended

Product details



TrueLine_Suspended-line-side-view



TrueLine_Suspended-line-top-view



TrueLine Suspended black housing



TrueLine_Suspended-top-view



TrueLine_Suspended-U3



TrueLine_Suspended-U0



TrueLine Suspended-SP530P-LF-power-cable-03



TrueLine-SP-line-U3

Product details



TrueLine Suspended black housing



SP530P U4 BK DPP



TrueLine_SM_SP-line-connection-side-view-2

General Information	
Driver included	Yes
Light source replaceable	No
Service tag	Yes
Light Technical	
Beam angle of light source	120 degree(s)
Color rendering index (CRI)	>90
Operating and Electrical	
Line Frequency	50 to 60 Hz
Suitable for random switching	No
Controls and Dimming	
Maximum dim level	1%
Mechanical and Housing	
Mech. impact protection code	IK03
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	+10 to +40 °C
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Initial Performance (IEC Compliant)	
Initial chromaticity	(0.38, 0.38) SDCM <3
Luminous flux tolerance	+/-10%

General Information

Order Code	Full Product Name	Number of gear units
910505103203	SP532P 47S/940 DEIA LS SM2 L1410 ALU	1 unit
910505103206	SP534P 34S/940 DEIA LS SM2 L1130 ALU	1 unit
910505103210	SP532P 29S/940 DEIA LS SM2 L1410 ALU	1 unit
910505103213	SP534P 43S/940 DEIA LS SM2 L1410 ALU	1 unit
910505103246	SP530P 17S/940 DEIA LE SM2 L570 BK	1 unit
910505103248	SP532P 24S/930 DEIA LE SM2 L570 BK	1 unit
910505103161	SP533P 41S/940 DEIA SM2 L1130 ALU	1 unit
910505103162	SP532P 29S/940 DEIA SM2 L1410 WH	1 unit
910505103163	SP530P 50S/940 DEIA SM2 L1410 ALU	1 unit
910505103164	SP532P 47S/940 DEIA SM2 L1410 ALU	1 unit
910505103165	SP530P 25S/940 POE SW2 L1130 ALU	1 unit
910505103166	SP531P 15S/940 DEIA SM2 L1130 ALU	1 unit
910505103167	SP530P 43S/940 DEIA SM2 L1410 ALU	1 unit
910505103168	SP532P 77S/940 DEIA SM2 L1410 ALU	1 unit
910505103169	SP532P 36S/940 DEIA SM2 L1130 ALU	1 unit
910505103170	SP532P 58S/940 DEIA SM2 L1130 ALU	1 unit
910505103171	SP530P 34S/940 DEIA SM2 L1130 ALU	1 unit
910505103172	SP533P 33S/930 DEIA SM2 L1410 ALU	1 unit
910505103173	SP532P 49S/930 DEIA SM2 L1130 ALU	1 unit
910505103174	SP532P 77S/930 DEIA SM2 L1410 ALU	1 unit
910505103175	SP532P 36S/940 DEIA SM2 L1130 WH	1 unit
910505103176	SP533P 33S/930 DEIA SM2 L1410 WH	1 unit
910505103177	SP534P 40S/940 DEIA SM2 L1130 ALU	1 unit
910505103180	SP533P 24S/940 DEIA SM2 L1130 ALU	1 unit
910505103181	SP532P 21S/940 DEIA SM2 L1130 ALU	1 unit
910505103182	SP533P 33S/940 DEIA SM2 L1410 ALU	1 unit
910505103183	SP532P 29S/940 DEIA SM2 L1410 ALU	1 unit
910505103185	SP532P 66S/940 DEIA SM2 L1410 ALU	1 unit
910505103186	SP533P 54S/940 DEIA SM2 L1410 ALU	1 unit
910505103187	SP532P 49S/940 DEIA SM2 L1130 ALU	1 unit
910505103188	SP532P 66S/940 DEIA SM2 L1410 WH	1 unit
910505103189	SP532P 47S/940 DEIA SM2 L1410 WH	1 unit
910505103191	SP530P 31S/940 POE U3 SW2 L1450 ALU	1 unit
910505103192	SP530P 40S/940 POE U3 SW2 L1170 ALU	1 unit
910505103193	SP530P 40S/940 POE U0 SW2 L1170 ALU	1 unit
910505103194	SP530P 43S/940 POE U0 SW2 L1450 ALU	1 unit
910505103196	SP530P 40S/940 DEIA SM2 L1130 ALU	1 unit
910505103184	SP534P 50S/940 DEIA SM2 L1410 ALU	1 unit
910505103281	SP532P 66S/TW9 SEIA U4 SM2 L1450 BK	2 units
910505103245	SP531P 7S/940 DEIA LE SM2 L570 WH	1 unit
910505103249	SP533P 12S/930 DEIA LE SM2 L570 WH	1 unit
910505103256	SP530P 30S/930 DEIA LN SM2 L2250 BK	1 unit
910505103282	SP530P 50S/TW9 SEIA SM2 U4 L2290 ALU	2 units
910505103283	SP530P 86S/TW9 SEIA U4 SM2 L2850 ALU	2 units
910505103257	SP531P 30S/930 SEIA LN U4 SW2 L2290 ALU	1 unit
910505103260	SP532P 72S/940 DEIA SM2 L2250 ALU	1 unit
910505103261	SP533P 48S/940 DEIA SM2 L2250 ALU	1 unit
910505103263	SP533P 82S/940 DEIA SM2 L2250 ALU	1 unit
910505103269	SP530P 38S/930 DEIA LN SW2 L2810 ALU	1 unit
910505103273	SP532P 58S/930 DEIA LN SM2 L2810 ALU	1 unit
910505103274	SP533P 66S/930 DEIA LN SW2 L2810 ALU	1 unit

Order Code	Full Product Name	Number of gear units
910505103258	SP530P 50S/940 SEIA U4 SM2 L2290 BK	1 unit
910505103262	SP532P 98S/940 SEIA U4 SM2 L2290 BK	1 unit
910505103270	SP530P 62S/940 SEIA U4 SM2 L2850 BK	1 unit
910505103244	SP530P 7S/940 DEIA LE SM2 L570 ALU	1 unit
910505103247	SP532P 10S/930 DEIA LE SM2 L570 ALU	1 unit
910505103259	SP530P 50S/930 DEIA SM2 L2250 WH	1 unit
910505103271	SP531P 62S/930 DEIA SM2 L2810 WH	1 unit
910505103272	SP532P 94S/940 DEIA SM2 L2810 WH	1 unit
910505103197	SP532P 47S/940 DEIA SM2 L1410 BK	1 unit
910505103198	SP531P 15S/940 DEIA SM2 L1130 BK	1 unit
910505103199	SP530P 34S/940 DEIA SM2 L1130 BK	1 unit
910505103201	SP532P 29S/930 DEIA LNP SM2 L1410 BK	1 unit
910505103202	SP532P 29S/940 DEIA LNP SM2 L1410 BK	1 unit
910505103207	SP532P 36S/940 DEIA LNP SM2T L1130 BK	1 unit
910505103204	SP532P 29S/940 DEIA LN SW2 L1410 ALU	1 unit
910505103205	SP532P 36S/940 DEIA LNP SM2T L1130 ALU	1 unit
910505103208	SP532P 29S/940 DEIA LNP SM2 L1410 ALU	1 unit
910505103209	SP534P 43S/940 DEIA LN SW2 L1410 ALU	1 unit
910505103211	SP532P 47S/940 DEIA LN SW2 L1410 ALU	1 unit
910505103212	SP532P 36S/940 DEIA LN SW2 L1130 ALU	1 unit
910505103279	SP532P 36S/TW9 DEIA LN SW2 L1130 ALU	1 unit
910505103280	SP533P 33S/TW9 DEIA LN SW2 L1410 ALU	2 units
910505103214	SP532P 47S/940 SEIA U4 SM2 L1450 ALU	1 unit
910505103215	SP530P 40S/940 SEIA U4 SM2 L1170 ALU	1 unit
910505103216	SP532P 66S/940 SEIA U4 SM2 L1450 ALU	1 unit

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux		Optic type
910505103203	SP532P 47S/940 DEIA LS SM2 L1410 ALU	4000 K	138 lm/W	4,700 lm		Wide beam
910505103206	SP534P 34S/940 DEIA LS SM2 L1130 ALU	4000 K	131 lm/W	3,400 lm		Asymmetrical mirror
910505103210	SP532P 29S/940 DEIA LS SM2 L1410 ALU	4000 K	138 lm/W	2,900 lm		Wide beam
910505103213	SP534P 43S/940 DEIA LS SM2 L1410 ALU	4000 K	132 lm/W	4,300 lm		Asymmetrical mirror
910505103246	SP530P 17S/940 DEIA LE SM2 L570 BK	4000 K	139 lm/W	1,700 lm		Wide beam
910505103248	SP532P 24S/930 DEIA LE SM2 L570 BK	3000 K	125 lm/W	2,400 lm		Wide beam
910505103161	SP533P 41S/940 DEIA SM2 L1130 ALU	4000 K	115 lm/W	4,100 lm		Wide beam
910505103162	SP532P 29S/940 DEIA SM2 L1410 WH	4000 K	138 lm/W	2,900 lm		Wide beam
910505103163	SP530P 50S/940 DEIA SM2 L1410 ALU	4000 K	139 lm/W	5,000 lm		Wide beam
910505103164	SP532P 47S/940 DEIA SM2 L1410 ALU	4000 K	138 lm/W	4,700 lm		Wide beam

TrueLine, suspended

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
910505103165	SP530P 25S/940 POE SW2 L1130 ALU	4000 K	149 lm/W	2,500 lm	Wide beam
910505103166	SP531P 15S/940 DEIA SM2 L1130 ALU	4000 K	104 lm/W	1,500 lm	Wide beam
910505103167	SP530P 43S/940 DEIA SM2 L1410 ALU	4000 K	141 lm/W	4,300 lm	Wide beam
910505103168	SP532P 77S/940 DEIA SM2 L1410 ALU	4000 K	135 lm/W	7,700 lm	Wide beam
910505103169	SP532P 36S/940 DEIA SM2 L1130 ALU	4000 K	136 lm/W	3,600 lm	Wide beam
910505103170	SP532P 58S/940 DEIA SM2 L1130 ALU	4000 K	133 lm/W	5,800 lm	Wide beam
910505103171	SP530P 34S/940 DEIA SM2 L1130 ALU	4000 K	139 lm/W	3,400 lm	Wide beam
910505103172	SP533P 33S/930 DEIA SM2 L1410 ALU	3000 K	112 lm/W	3,300 lm	Wide beam
910505103173	SP532P 49S/930 DEIA SM2 L1130 ALU	3000 K	134 lm/W	4,900 lm	Wide beam
910505103174	SP532P 77S/930 DEIA SM2 L1410 ALU	3000 K	128 lm/W	7,700 lm	Wide beam
910505103175	SP532P 36S/940 DEIA SM2 L1130 WH	4000 K	136 lm/W	3,600 lm	Wide beam
910505103176	SP533P 33S/930 DEIA SM2 L1410 WH	3000 K	112 lm/W	3,300 lm	Wide beam

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
910505103177	SP534P 40S/940 DEIA SM2 L1130 ALU	4000 K	129 lm/W	4,000 lm	Asymmetrical mirror
910505103180	SP533P 24S/940 DEIA SM2 L1130 ALU	4000 K	114 lm/W	2,400 lm	Wide beam
910505103181	SP532P 21S/940 DEIA SM2 L1130 ALU	4000 K	141 lm/W	2,100 lm	Wide beam
910505103182	SP533P 33S/940 DEIA SM2 L1410 ALU	4000 K	118 lm/W	3,300 lm	Wide beam
910505103183	SP532P 29S/940 DEIA SM2 L1410 ALU	4000 K	138 lm/W	2,900 lm	Wide beam
910505103185	SP532P 66S/940 DEIA SM2 L1410 ALU	4000 K	138 lm/W	6,600 lm	Wide beam
910505103186	SP533P 54S/940 DEIA SM2 L1410 ALU	4000 K	116 lm/W	5,400 lm	Wide beam
910505103187	SP532P 49S/940 DEIA SM2 L1130 ALU	4000 K	143 lm/W	4,900 lm	Wide beam
910505103188	SP532P 66S/940 DEIA SM2 L1410 WH	4000 K	138 lm/W	6,600 lm	Wide beam
910505103189	SP532P 47S/940 DEIA SM2 L1410 WH	4000 K	138 lm/W	4,700 lm	Wide beam
910505103191	SP530P 31S/940 POE U3 SW2 L1450 ALU	4000 K	148 lm/W	3,100 lm	Wide beam
910505103192	SP530P 40S/940 POE U3 SW2 L1170 ALU	4000 K	149 lm/W	4,000 lm	Wide beam

TrueLine, suspended

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
910505103193	SP530P 40S/940 POE U0 SW2 L1170 ALU	4000 K	149 lm/W	4,000 lm	Wide beam
910505103194	SP530P 43S/940 POE U0 SW2 L1450 ALU	4000 K	143 lm/W	4,300 lm	Wide beam
910505103196	SP530P 40S/940 DEIA SM2 L1130 ALU	4000 K	140 lm/W	4,000 lm	Wide beam
910505103184	SP534P 50S/940 DEIA SM2 L1410 ALU	4000 K	130 lm/W	5,000 lm	Asymmetrical mirror
910505103281	SP532P 66S/TW9 SEIA U4 SM2 L1450 BK	Tunable white 2700-6500 K	116 lm/W	6,600 lm	Wide beam
910505103245	SP531P 7S/940 DEIA LE SM2 L570 WH	4000 K	103 lm/W	700 lm	Wide beam
910505103249	SP533P 12S/930 DEIA LE SM2 L570 WH	3000 K	109 lm/W	1,200 lm	Wide beam
910505103256	SP530P 30S/930 DEIA LN SM2 L2250 BK	3000 K	130 lm/W	3,000 lm	Wide beam
910505103282	SP530P 50S/TW9 SEIA SM2 U4 L2290 ALU	Tunable white 2700-6500 K	125 lm/W	5,000 lm	Wide beam
910505103283	SP530P 86S/TW9 SEIA U4 SM2 L2850 ALU	Tunable white 2700-6500 K	121 lm/W	8,600 lm	Wide beam
910505103257	SP531P 30S/930 SEIA LN U4 SW2 L2290 ALU	3000 K	103 lm/W	3,000 lm	Wide beam
910505103260	SP532P 72S/940 DEIA SM2 L2250 ALU	4000 K	138 lm/W	7,200 lm	Wide beam

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
910505103261	SP533P 48S/940 DEIA SM2 L2250 ALU	4000 K	122 lm/W	4,800 lm	Wide beam
910505103263	SP533P 82S/940 DEIA SM2 L2250 ALU	4000 K	119 lm/W	8,200 lm	Wide beam
910505103269	SP530P 38S/930 DEIA LN SW2 L2810 ALU	3000 K	136 lm/W	3,800 lm	Wide beam
910505103273	SP532P 58S/930 DEIA LN SM2 L2810 ALU	3000 K	132 lm/W	5,800 lm	Wide beam
910505103274	SP533P 66S/930 DEIA LN SW2 L2810 ALU	3000 K	114 lm/W	6,600 lm	Wide beam
910505103258	SP530P 50S/940 SEIA U4 SM2 L2290 BK	4000 K	139 lm/W	5,000 lm	Wide beam
910505103262	SP532P 98S/940 SEIA U4 SM2 L2290 BK	4000 K	138 lm/W	9,800 lm	Wide beam
910505103270	SP530P 62S/940 SEIA U4 SM2 L2850 BK	4000 K	141 lm/W	6,200 lm	Wide beam
910505103244	SP530P 7S/940 DEIA LE SM2 L570 ALU	4000 K	133 lm/W	700 lm	Wide beam
910505103247	SP532P 10S/930 DEIA LE SM2 L570 ALU	3000 K	127 lm/W	1,000 lm	Wide beam
910505103259	SP530P 50S/930 DEIA SM2 L2250 WH	3000 K	133 lm/W	5,000 lm	Wide beam
910505103271	SP531P 62S/930	3000 K	135 lm/W	6,200 lm	Wide beam

TrueLine, suspended

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
	DEIA SM2 L2810 WH				
910505103272	SP532P 94S/940 DEIA SM2 L2810 WH	4000 K	140 lm/W	9,400 lm	Wide beam
910505103197	SP532P 47S/940 DEIA SM2 L1410 BK	4000 K	138 lm/W	4,700 lm	Wide beam
910505103198	SP531P 15S/940 DEIA SM2 L1130 BK	4000 K	104 lm/W	1,500 lm	Wide beam
910505103199	SP530P 34S/940 DEIA SM2 L1130 BK	4000 K	139 lm/W	3,400 lm	Wide beam
910505103201	SP532P 29S/930 DEIA LNP SM2 L1410 BK	3000 K	132 lm/W	2,900 lm	Wide beam
910505103202	SP532P 29S/940 DEIA LNP SM2 L1410 BK	4000 K	138 lm/W	2,900 lm	Wide beam
910505103207	SP532P 36S/940 DEIA LNP SM2T L1130 BK	4000 K	136 lm/W	3,600 lm	Wide beam
910505103204	SP532P 29S/940 DEIA LN SW2 L1410 ALU	4000 K	138 lm/W	2,900 lm	Wide beam
910505103205	SP532P 36S/940 DEIA LNP	4000 K	136 lm/W	3,600 lm	Wide beam

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
	SM2T L1130 ALU				
910505103208	SP532P 29S/940 DEIA LNP SM2 L1410 ALU	4000 K	138 lm/W	2,900 lm	Wide beam
910505103209	SP534P 43S/940 DEIA LN SW2 L1410 ALU	4000 K	132 lm/W	4,300 lm	Asymmetrical mirror
910505103211	SP532P 47S/940 DEIA LN SW2 L1410 ALU	4000 K	138 lm/W	4,700 lm	Wide beam
910505103212	SP532P 36S/940 DEIA LN SW2 L1130 ALU	4000 K	136 lm/W	3,600 lm	Wide beam
910505103279	SP532P 36S/TW9 DEIA LN SW2 L1130 ALU	Tunable white 2700-6500 K	124 lm/W	3,600 lm	Wide beam
910505103280	SP533P 33S/TW9 DEIA LN SW2 L1410 ALU	Tunable white 2700-6500 K	100 lm/W	3,300 lm	Wide beam
910505103214	SP532P 47S/940 SEIA U4 SM2 L1450 ALU	4000 K	138 lm/W	4,700 lm	Wide beam
910505103215	SP530P 40S/940 SEIA U4 SM2 L1170 ALU	4000 K	143 lm/W	4,000 lm	Wide beam
910505103216	SP532P 66S/940 SEIA U4 SM2 L1450 ALU	4000 K	139 lm/W	6,600 lm	Wide beam

Operating and Electrical

Order Code	Full Product Name	Protection class IEC	Input Voltage	Power Consumption
910505103203	SP532P 47S/940 DEIA LS SM2 L1410 ALU	Safety class I	220 to 240 V	34 W
910505103206	SP534P 34S/940 DEIA LS SM2 L1130 ALU	Safety class I	220 to 240 V	26 W
910505103210	SP532P 29S/940 DEIA LS SM2 L1410 ALU	Safety class I	220 to 240 V	21 W
910505103213	SP534P 43S/940 DEIA LS SM2 L1410 ALU	Safety class I	220 to 240 V	32.5 W
910505103246	SP530P 17S/940 DEIA LE SM2 L570 BK	Safety class I	220 to 240 V	12.2 W
910505103248	SP532P 24S/930 DEIA LE SM2 L570 BK	Safety class I	220 to 240 V	18.6 W
910505103161	SP533P 41S/940 DEIA SM2 L1130 ALU	Safety class I	220 to 240 V	35.5 W
910505103162	SP532P 29S/940 DEIA SM2 L1410 WH	Safety class I	220 to 240 V	21 W
910505103163	SP530P 50S/940 DEIA SM2 L1410 ALU	Safety class I	220 to 240 V	36 W
910505103164	SP532P 47S/940 DEIA SM2 L1410 ALU	Safety class I	220 to 240 V	34 W
910505103165	SP530P 25S/940 POE SW2 L1130 ALU	Safety class III	51 to 54 V	16.8 W
910505103166	SP531P 15S/940 DEIA SM2 L1130 ALU	Safety class I	220 to 240 V	14.4 W
910505103167	SP530P 43S/940 DEIA SM2 L1410 ALU	Safety class I	220 to 240 V	30.5 W
910505103168	SP532P 77S/940 DEIA SM2 L1410 ALU	Safety class I	220 to 240 V	57 W
910505103169	SP532P 36S/940 DEIA SM2 L1130 ALU	Safety class I	220 to 240 V	26.5 W
910505103170	SP532P 58S/940 DEIA SM2 L1130 ALU	Safety class I	220 to 240 V	44 W
910505103171	SP530P 34S/940 DEIA SM2 L1130 ALU	Safety class I	220 to 240 V	24.5 W
910505103172	SP533P 33S/930 DEIA SM2 L1410 ALU	Safety class I	220 to 240 V	29.5 W
910505103173	SP532P 49S/930 DEIA SM2 L1130 ALU	Safety class I	220 to 240 V	38.5 W
910505103174	SP532P 77S/930 DEIA SM2 L1410 ALU	Safety class I	220 to 240 V	60 W
910505103175	SP532P 36S/940 DEIA SM2 L1130 WH	Safety class I	220 to 240 V	26.5 W
910505103176	SP533P 33S/930 DEIA SM2 L1410 WH	Safety class I	220 to 240 V	29.5 W

Order Code	Full Product Name	Protection class IEC	Input Voltage	Power Consumption
910505103177	SP534P 40S/940 DEIA SM2 L1130 ALU	Safety class I	220 to 240 V	31 W
910505103180	SP533P 24S/940 DEIA SM2 L1130 ALU	Safety class I	220 to 240 V	21 W
910505103181	SP532P 21S/940 DEIA SM2 L1130 ALU	Safety class I	220 to 240 V	16.4 W
910505103182	SP533P 33S/940 DEIA SM2 L1410 ALU	Safety class I	220 to 240 V	28 W
910505103183	SP532P 29S/940 DEIA SM2 L1410 ALU	Safety class I	220 to 240 V	21 W
910505103185	SP532P 66S/940 DEIA SM2 L1410 ALU	Safety class I	220 to 240 V	48 W
910505103186	SP533P 54S/940 DEIA SM2 L1410 ALU	Safety class I	220 to 240 V	46.5 W
910505103187	SP532P 49S/940 DEIA SM2 L1130 ALU	Safety class I	220 to 240 V	36.5 W
910505103188	SP532P 66S/940 DEIA SM2 L1410 WH	Safety class I	220 to 240 V	48 W
910505103189	SP532P 47S/940 DEIA SM2 L1410 WH	Safety class I	220 to 240 V	34 W
910505103191	SP530P 31S/940 POE U3 SW2 L1450 ALU	Safety class III	51 to 54 V	21 W
910505103192	SP530P 40S/940 POE U3 SW2 L1170 ALU	Safety class III	51 to 54 V	28 W
910505103193	SP530P 40S/940 POE U0 SW2 L1170 ALU	Safety class III	51 to 54 V	28 W
910505103194	SP530P 43S/940 POE U0 SW2 L1450 ALU	Safety class III	51 to 54 V	30 W
910505103196	SP530P 40S/940 DEIA SM2 L1130 ALU	Safety class I	220 to 240 V	28.5 W
910505103184	SP534P 50S/940 DEIA SM2 L1410 ALU	Safety class I	220 to 240 V	38.5 W
910505103281	SP532P 66S/TW9 SEIA U4 SM2 L1450 BK	Safety class I	220 to 240 V	57 W
910505103245	SP531P 7S/940 DEIA LE SM2 L570 WH	Safety class I	220 to 240 V	7.2 W
910505103249	SP533P 12S/930 DEIA LE SM2 L570 WH	Safety class I	220 to 240 V	11 W
910505103256	SP530P 30S/930 DEIA LN SM2 L2250 BK	Safety class I	220 to 240 V	23 W
910505103282	SP530P 50S/TW9 SEIA SM2 U4 L2290 ALU	Safety class I	220 to 240 V	40 W

TrueLine, suspended

Order Code	Full Product Name	Protection	Input Voltage	Power
		class IEC		Consumption
910505103283	SP530P 86S/TW9 SEIA U4 SM2 L2850 ALU	Safety class I	220 to 240 V	71 W
910505103257	SP531P 30S/930 SEIA LN U4 SW2 L2290 ALU	Safety class I	220 to 240 V	29 W
910505103260	SP532P 72S/940 DEIA SM2 L2250 ALU	Safety class I	220 to 240 V	52 W
910505103261	SP533P 48S/940 DEIA SM2 L2250 ALU	Safety class I	220 to 240 V	39.5 W
910505103263	SP533P 82S/940 DEIA SM2 L2250 ALU	Safety class I	220 to 240 V	69 W
910505103269	SP530P 38S/930 DEIA LN SW2 L2810 ALU	Safety class I	220 to 240 V	28 W
910505103273	SP532P 58S/930 DEIA LN SM2 L2810 ALU	Safety class I	220 to 240 V	44 W
910505103274	SP533P 66S/930 DEIA LN SW2 L2810 ALU	Safety class I	220 to 240 V	58 W
910505103258	SP530P 50S/940 SEIA U4 SM2 L2290 BK	Safety class I	220 to 240 V	36 W
910505103262	SP532P 98S/940 SEIA U4 SM2 L2290 BK	Safety class I	220 to 240 V	71 W
910505103270	SP530P 62S/940 SEIA U4 SM2 L2850 BK	Safety class I	220 to 240 V	44 W
910505103244	SP530P 75/940 DEIA LE SM2 L570 ALU	Safety class I	220 to 240 V	6 W
910505103247	SP532P 10S/930 DEIA LE SM2 L570 ALU	Safety class I	220 to 240 V	8.5 W
910505103259	SP530P 50S/930 DEIA SM2 L2250 WH	Safety class I	220 to 240 V	37.5 W
910505103271	SP531P 62S/930 DEIA SM2 L2810 WH	Safety class I	220 to 240 V	46 W
910505103272	SP532P 94S/940 DEIA SM2 L2810 WH	Safety class I	220 to 240 V	67 W
910505103197	SP532P 47S/940 DEIA SM2 L1410 BK	Safety class I	220 to 240 V	34 W

Order Code	Full Product Name	Protection	Input Voltage	Power
		class IEC		Consumption
910505103198	SP531P 15S/940 DEIA SM2 L1130 BK	Safety class I	220 to 240 V	14.4 W
910505103199	SP530P 34S/940 DEIA SM2 L1130 BK	Safety class I	220 to 240 V	24.5 W
910505103201	SP532P 29S/930 DEIA LNP SM2 L1410 BK	Safety class I	220 to 240 V	22 W
910505103202	SP532P 29S/940 DEIA LNP SM2 L1410 BK	Safety class I	220 to 240 V	21 W
910505103207	SP532P 36S/940 DEIA LNP SM2T L1130 BK	Safety class I	220 to 240 V	26.5 W
910505103204	SP532P 29S/940 DEIA LN SW2 L1410 ALU	Safety class I	220 to 240 V	21 W
910505103205	SP532P 36S/940 DEIA LNP SM2T L1130 ALU	Safety class I	220 to 240 V	26.5 W
910505103208	SP532P 29S/940 DEIA LNP SM2 L1410 ALU	Safety class I	220 to 240 V	21 W
910505103209	SP534P 43S/940 DEIA LN SW2 L1410 ALU	Safety class I	220 to 240 V	32.5 W
910505103211	SP532P 47S/940 DEIA LN SW2 L1410 ALU	Safety class I	220 to 240 V	34 W
910505103212	SP532P 36S/940 DEIA LN SW2 L1130 ALU	Safety class I	220 to 240 V	26.5 W
910505103279	SP532P 36S/TW9 DEIA LN SW2 L1130 ALU	Safety class I	220 to 240 V	29 W
910505103280	SP533P 33S/TW9 DEIA LN SW2 L1410 ALU	Safety class I	220 to 240 V	33 W
910505103214	SP532P 47S/940 SEIA U4 SM2 L1450 ALU	Safety class I	220 to 240 V	34 W
910505103215	SP530P 40S/940 SEIA U4 SM2 L1170 ALU	Safety class I	220 to 240 V	28 W
910505103216	SP532P 66S/940 SEIA U4 SM2 L1450 ALU	Safety class I	220 to 240 V	47.5 W

Controls and Dimming

TrueLine, suspended

Order Code	Full Product Name	Dimmable	Embedded control
910505103203	SP532P 47S/940 DEIA LS SM2 L1410 ALU	Yes	-
910505103206	SP534P 34S/940 DEIA LS SM2 L1130 ALU	Yes	-
910505103210	SP532P 29S/940 DEIA LS SM2 L1410 ALU	Yes	-
910505103213	SP534P 43S/940 DEIA LS SM2 L1410 ALU	Yes	-
910505103246	SP530P 17S/940 DEIA LE SM2 L570 BK	Yes	-
910505103248	SP532P 24S/930 DEIA LE SM2 L570 BK	Yes	-
910505103161	SP533P 41S/940 DEIA SM2 L1130 ALU	Yes	-
910505103162	SP532P 29S/940 DEIA SM2 L1410 WH	Yes	-
910505103163	SP530P 50S/940 DEIA SM2 L1410 ALU	Yes	-
910505103164	SP532P 47S/940 DEIA SM2 L1410 ALU	Yes	-
910505103165	SP530P 25S/940 POE SW2 L1130 ALU	No	-
910505103166	SP531P 15S/940 DEIA SM2 L1130 ALU	Yes	-
910505103167	SP530P 43S/940 DEIA SM2 L1410 ALU	Yes	-
910505103168	SP532P 77S/940 DEIA SM2 L1410 ALU	Yes	-
910505103169	SP532P 36S/940 DEIA SM2 L1130 ALU	Yes	-
910505103170	SP532P 58S/940 DEIA SM2 L1130 ALU	Yes	-
910505103171	SP530P 34S/940 DEIA SM2 L1130 ALU	Yes	-
910505103172	SP533P 33S/930 DEIA SM2 L1410 ALU	Yes	-
910505103173	SP532P 49S/930 DEIA SM2 L1130 ALU	Yes	-
910505103174	SP532P 77S/930 DEIA SM2 L1410 ALU	Yes	-
910505103175	SP532P 36S/940 DEIA SM2 L1130 WH	Yes	-
910505103176	SP533P 33S/930 DEIA SM2 L1410 WH	Yes	-
910505103177	SP534P 40S/940 DEIA SM2 L1130 ALU	Yes	-
910505103180	SP533P 24S/940 DEIA SM2 L1130 ALU	Yes	-
910505103181	SP532P 21S/940 DEIA SM2 L1130 ALU	Yes	-
910505103182	SP533P 33S/940 DEIA SM2 L1410 ALU	Yes	-
910505103183	SP532P 29S/940 DEIA SM2 L1410 ALU	Yes	-
910505103185	SP532P 66S/940 DEIA SM2 L1410 ALU	Yes	-
910505103186	SP533P 54S/940 DEIA SM2 L1410 ALU	Yes	-
910505103187	SP532P 49S/940 DEIA SM2 L1130 ALU	Yes	-
910505103188	SP532P 66S/940 DEIA SM2 L1410 WH	Yes	-
910505103189	SP532P 47S/940 DEIA SM2 L1410 WH	Yes	-
910505103191	SP530P 31S/940 POE U3 SW2 L1450 ALU	No	-
910505103192	SP530P 40S/940 POE U3 SW2 L1170 ALU	No	-
910505103193	SP530P 40S/940 POE U0 SW2 L1170 ALU	No	-
910505103194	SP530P 43S/940 POE U0 SW2 L1450 ALU	No	-
910505103196	SP530P 40S/940 DEIA SM2 L1130 ALU	Yes	-
910505103184	SP534P 50S/940 DEIA SM2 L1410 ALU	Yes	-
910505103281	SP532P 66S/TW9 SEIA U4 SM2 L1450 BK	Yes	Upgradable sensor slot with SNS210 sensor
910505103245	SP531P 7S/940 DEIA LE SM2 L570 WH	Yes	-
910505103249	SP533P 12S/930 DEIA LE SM2 L570 WH	Yes	-

Order Code	Full Product Name	Dimmable	Embedded control
910505103256	SP530P 30S/930 DEIA LN SM2 L2250 BK	Yes	-
910505103282	SP530P 50S/TW9 SEIA SM2 U4 L2290 ALU	Yes	Upgradable sensor slot with SNS210 sensor
910505103283	SP530P 86S/TW9 SEIA U4 SM2 L2850 ALU	Yes	Upgradable sensor slot with SNS210 sensor
910505103257	SP531P 30S/930 SEIA LN U4 SW2 L2290 ALU	Yes	Upgradable sensor slot with SNS210 sensor
910505103260	SP532P 72S/940 DEIA SM2 L2250 ALU	Yes	-
910505103261	SP533P 48S/940 DEIA SM2 L2250 ALU	Yes	-
910505103263	SP533P 82S/940 DEIA SM2 L2250 ALU	Yes	-
910505103269	SP530P 38S/930 DEIA LN SW2 L2810 ALU	Yes	-
910505103273	SP532P 58S/930 DEIA LN SM2 L2810 ALU	Yes	-
910505103274	SP533P 66S/930 DEIA LN SW2 L2810 ALU	Yes	-
910505103258	SP530P 50S/940 SEIA U4 SM2 L2290 BK	Yes	Upgradable sensor slot with SNS210 sensor
910505103262	SP532P 98S/940 SEIA U4 SM2 L2290 BK	Yes	Upgradable sensor slot with SNS210 sensor
910505103270	SP530P 62S/940 SEIA U4 SM2 L2850 BK	Yes	Upgradable sensor slot with SNS210 sensor
910505103244	SP530P 7S/940 DEIA LE SM2 L570 ALU	Yes	-
910505103247	SP532P 10S/930 DEIA LE SM2 L570 ALU	Yes	-
910505103259	SP530P 50S/930 DEIA SM2 L2250 WH	Yes	-
910505103271	SP531P 62S/930 DEIA SM2 L2810 WH	Yes	-
910505103272	SP532P 94S/940 DEIA SM2 L2810 WH	Yes	-
910505103197	SP532P 47S/940 DEIA SM2 L1410 BK	Yes	-
910505103198	SP531P 15S/940 DEIA SM2 L1130 BK	Yes	-
910505103199	SP530P 34S/940 DEIA SM2 L1130 BK	Yes	-
910505103201	SP532P 29S/930 DEIA LNP SM2 L1410 BK	Yes	-
910505103202	SP532P 29S/940 DEIA LNP SM2 L1410 BK	Yes	-
910505103207	SP532P 36S/940 DEIA LNP SM2T L1130 BK	Yes	-
910505103204	SP532P 29S/940 DEIA LN SW2 L1410 ALU	Yes	-
910505103205	SP532P 36S/940 DEIA LNP SM2T L1130 ALU	Yes	-
910505103208	SP532P 29S/940 DEIA LNP SM2 L1410 ALU	Yes	-

TrueLine, suspended

Order Code	Full Product Name	Dimmable	Embedded control
910505103209	SP534P 43S/940 DEIA LN SW2 L1410 ALU	Yes	-
910505103211	SP532P 47S/940 DEIA LN SW2 L1410 ALU	Yes	-
910505103212	SP532P 36S/940 DEIA LN SW2 L1130 ALU	Yes	-
910505103279	SP532P 36S/TW9 DEIA LN SW2 L1130 ALU	Yes	-
910505103280	SP533P 33S/TW9 DEIA LN SW2 L1410 ALU	Yes	-

Mechanical and Housing

Order Code	Full Product Name	Housing Color
910505103203	SP532P 47S/940 DEIA LS SM2 L1410 ALU	Aluminum
910505103206	SP534P 34S/940 DEIA LS SM2 L1130 ALU	Aluminum
910505103210	SP532P 29S/940 DEIA LS SM2 L1410 ALU	Aluminum
910505103213	SP534P 43S/940 DEIA LS SM2 L1410 ALU	Aluminum
910505103246	SP530P 17S/940 DEIA LE SM2 L570 BK	Black
910505103248	SP532P 24S/930 DEIA LE SM2 L570 BK	Black
910505103161	SP533P 41S/940 DEIA SM2 L1130 ALU	Aluminum
910505103162	SP532P 29S/940 DEIA SM2 L1410 WH	White
910505103163	SP530P 50S/940 DEIA SM2 L1410 ALU	Aluminum
910505103164	SP532P 47S/940 DEIA SM2 L1410 ALU	Aluminum
910505103165	SP530P 25S/940 POE SW2 L1130 ALU	Aluminum
910505103166	SP531P 15S/940 DEIA SM2 L1130 ALU	Aluminum
910505103167	SP530P 43S/940 DEIA SM2 L1410 ALU	Aluminum
910505103168	SP532P 77S/940 DEIA SM2 L1410 ALU	Aluminum
910505103169	SP532P 36S/940 DEIA SM2 L1130 ALU	Aluminum
910505103170	SP532P 58S/940 DEIA SM2 L1130 ALU	Aluminum
910505103171	SP530P 34S/940 DEIA SM2 L1130 ALU	Aluminum
910505103172	SP533P 33S/930 DEIA SM2 L1410 ALU	Aluminum
910505103173	SP532P 49S/930 DEIA SM2 L1130 ALU	Aluminum
910505103174	SP532P 77S/930 DEIA SM2 L1410 ALU	Aluminum
910505103175	SP532P 36S/940 DEIA SM2 L1130 WH	White
910505103176	SP533P 33S/930 DEIA SM2 L1410 WH	White
910505103177	SP534P 40S/940 DEIA SM2 L1130 ALU	Aluminum
910505103180	SP533P 24S/940 DEIA SM2 L1130 ALU	Aluminum
910505103181	SP532P 21S/940 DEIA SM2 L1130 ALU	Aluminum
910505103182	SP533P 33S/940 DEIA SM2 L1410 ALU	Aluminum
910505103183	SP532P 29S/940 DEIA SM2 L1410 ALU	Aluminum
910505103185	SP532P 66S/940 DEIA SM2 L1410 ALU	Aluminum
910505103186	SP533P 54S/940 DEIA SM2 L1410 ALU	Aluminum
910505103187	SP532P 49S/940 DEIA SM2 L1130 ALU	Aluminum
910505103188	SP532P 66S/940 DEIA SM2 L1410 WH	White
910505103189	SP532P 47S/940 DEIA SM2 L1410 WH	White
910505103191	SP530P 31S/940 POE U3 SW2 L1450 ALU	Aluminum
910505103192	SP530P 40S/940 POE U3 SW2 L1170 ALU	Aluminum
910505103193	SP530P 40S/940 POE U0 SW2 L1170 ALU	Aluminum
910505103194	SP530P 43S/940 POE U0 SW2 L1450 ALU	Aluminum
910505103196	SP530P 40S/940 DEIA SM2 L1130 ALU	Aluminum

Order Code	Full Product Name	Dimmable	Embedded control
910505103214	SP532P 47S/940 SEIA U4 SM2 L1450 ALU	Yes	Upgradable sensor slot with SNS210 sensor
910505103215	SP530P 40S/940 SEIA U4 SM2 L1170 ALU	Yes	Upgradable sensor slot with SNS210 sensor
910505103216	SP532P 66S/940 SEIA U4 SM2 L1450 ALU	Yes	Upgradable sensor slot with SNS210 sensor

Order Code	Full Product Name	Housing Color
910505103184	SP534P 50S/940 DEIA SM2 L1410 ALU	Aluminum
910505103281	SP532P 66S/TW9 SEIA U4 SM2 L1450 BK	Black
910505103245	SP531P 7S/940 DEIA LE SM2 L570 WH	White
910505103249	SP533P 12S/930 DEIA LE SM2 L570 WH	White
910505103256	SP530P 30S/930 DEIA LN SM2 L2250 BK	Black
910505103282	SP530P 50S/TW9 SEIA SM2 U4 L2290 ALU	Aluminum
910505103283	SP530P 86S/TW9 SEIA U4 SM2 L2850 ALU	Aluminum
910505103257	SP531P 30S/930 SEIA LN U4 SW2 L2290 ALU	Aluminum
910505103260	SP532P 72S/940 DEIA SM2 L2250 ALU	Aluminum
910505103261	SP533P 48S/940 DEIA SM2 L2250 ALU	Aluminum
910505103263	SP533P 82S/940 DEIA SM2 L2250 ALU	Aluminum
910505103269	SP530P 38S/930 DEIA LN SW2 L2810 ALU	Aluminum
910505103273	SP532P 58S/930 DEIA LN SM2 L2810 ALU	Aluminum
910505103274	SP533P 66S/930 DEIA LN SW2 L2810 ALU	Aluminum
910505103258	SP530P 50S/940 SEIA U4 SM2 L2290 BK	Black
910505103262	SP532P 98S/940 SEIA U4 SM2 L2290 BK	Black
910505103270	SP530P 62S/940 SEIA U4 SM2 L2850 BK	Black
910505103244	SP530P 7S/940 DEIA LE SM2 L570 ALU	Aluminum
910505103247	SP532P 10S/930 DEIA LE SM2 L570 ALU	Aluminum
910505103259	SP530P 50S/930 DEIA SM2 L2250 WH	White
910505103271	SP531P 62S/930 DEIA SM2 L2810 WH	White
910505103272	SP532P 94S/940 DEIA SM2 L2810 WH	White
910505103197	SP532P 47S/940 DEIA SM2 L1410 BK	Black
910505103198	SP531P 15S/940 DEIA SM2 L1130 BK	Black
910505103199	SP530P 34S/940 DEIA SM2 L1130 BK	Black
910505103201	SP532P 29S/930 DEIA LNP SM2 L1410 BK	Black
910505103202	SP532P 29S/940 DEIA LNP SM2 L1410 BK	Black
910505103207	SP532P 36S/940 DEIA LNP SM2T L1130 BK	Black
910505103204	SP532P 29S/940 DEIA LN SW2 L1410 ALU	Aluminum
910505103205	SP532P 36S/940 DEIA LNP SM2T L1130 ALU	Aluminum
910505103208	SP532P 29S/940 DEIA LNP SM2 L1410 ALU	Aluminum
910505103209	SP534P 43S/940 DEIA LN SW2 L1410 ALU	Aluminum
910505103211	SP532P 47S/940 DEIA LN SW2 L1410 ALU	Aluminum
910505103212	SP532P 36S/940 DEIA LN SW2 L1130 ALU	Aluminum
910505103279	SP532P 36S/TW9 DEIA LN SW2 L1130 ALU	Aluminum
910505103280	SP533P 33S/TW9 DEIA LN SW2 L1410 ALU	Aluminum
910505103214	SP532P 47S/940 SEIA U4 SM2 L1450 ALU	Aluminum

Order Code	Full Product Name	Housing Color
910505103215	SP530P 40S/940 SEIA U4 SM2 L1170 ALU	Aluminum

Order Code	Full Product Name	Housing Color
910505103216	SP532P 66S/940 SEIA U4 SM2 L1450 ALU	Aluminum

Emergency Operation

Order Code	Full Product Name	Central Emergency	Emergency lighting
910505103203	SP532P 47S/940 DEIA LS SM2 L1410 ALU	Yes	DC operated central emergency lighting
910505103206	SP534P 34S/940 DEIA LS SM2 L1130 ALU	Yes	DC operated central emergency lighting
910505103210	SP532P 29S/940 DEIA LS SM2 L1410 ALU	Yes	DC operated central emergency lighting
910505103213	SP534P 43S/940 DEIA LS SM2 L1410 ALU	Yes	DC operated central emergency lighting
910505103246	SP530P 17S/940 DEIA LE SM2 L570 BK	Yes	DC operated central emergency lighting
910505103248	SP532P 24S/930 DEIA LE SM2 L570 BK	Yes	DC operated central emergency lighting
910505103161	SP533P 41S/940 DEIA SM2 L1130 ALU	Yes	DC operated central emergency lighting
910505103162	SP532P 29S/940 DEIA SM2 L1410 WH	Yes	DC operated central emergency lighting
910505103163	SP530P 50S/940 DEIA SM2 L1410 ALU	Yes	DC operated central emergency lighting
910505103164	SP532P 47S/940 DEIA SM2 L1410 ALU	Yes	DC operated central emergency lighting
910505103165	SP530P 25S/940 POE SW2 L1130 ALU	-	-
910505103166	SP531P 15S/940 DEIA SM2 L1130 ALU	Yes	DC operated central emergency lighting
910505103167	SP530P 43S/940 DEIA SM2 L1410 ALU	Yes	DC operated central emergency lighting
910505103168	SP532P 77S/940 DEIA SM2 L1410 ALU	Yes	DC operated central emergency lighting
910505103169	SP532P 36S/940 DEIA SM2 L1130 ALU	Yes	DC operated central emergency lighting
910505103170	SP532P 58S/940 DEIA SM2 L1130 ALU	Yes	DC operated central emergency lighting
910505103171	SP530P 34S/940 DEIA SM2 L1130 ALU	Yes	DC operated central emergency lighting
910505103172	SP533P 33S/930 DEIA SM2 L1410 ALU	Yes	DC operated central emergency lighting
910505103173	SP532P 49S/930 DEIA SM2 L1130 ALU	Yes	DC operated central emergency lighting
910505103174	SP532P 77S/930 DEIA SM2 L1410 ALU	Yes	DC operated central emergency lighting
910505103175	SP532P 36S/940 DEIA SM2 L1130 WH	Yes	DC operated central emergency lighting
910505103176	SP533P 33S/930 DEIA SM2 L1410 WH	Yes	DC operated central emergency lighting
910505103177	SP534P 40S/940 DEIA SM2 L1130 ALU	Yes	DC operated central emergency lighting

Order Code	Full Product Name	Central Emergency	Emergency lighting
910505103180	SP533P 24S/940 DEIA SM2 L1130 ALU	Yes	DC operated central emergency lighting
910505103181	SP532P 21S/940 DEIA SM2 L1130 ALU	Yes	DC operated central emergency lighting
910505103182	SP533P 33S/940 DEIA SM2 L1410 ALU	Yes	DC operated central emergency lighting
910505103183	SP532P 29S/940 DEIA SM2 L1410 ALU	Yes	DC operated central emergency lighting
910505103185	SP532P 66S/940 DEIA SM2 L1410 ALU	Yes	DC operated central emergency lighting
910505103186	SP533P 54S/940 DEIA SM2 L1410 ALU	Yes	DC operated central emergency lighting
910505103187	SP532P 49S/940 DEIA SM2 L1130 ALU	Yes	DC operated central emergency lighting
910505103188	SP532P 66S/940 DEIA SM2 L1410 WH	Yes	DC operated central emergency lighting
910505103189	SP532P 47S/940 DEIA SM2 L1410 WH	Yes	DC operated central emergency lighting
910505103191	SP530P 31S/940 POE U3 SW2 L1450 ALU	-	-
910505103192	SP530P 40S/940 POE U3 SW2 L1170 ALU	-	-
910505103193	SP530P 40S/940 POE U0 SW2 L1170 ALU	-	-
910505103194	SP530P 43S/940 POE U0 SW2 L1450 ALU	-	-
910505103196	SP530P 40S/940 DEIA SM2 L1130 ALU	Yes	DC operated central emergency lighting
910505103184	SP534P 50S/940 DEIA SM2 L1410 ALU	Yes	DC operated central emergency lighting
910505103281	SP532P 66S/TW9 SEIA U4 SM2 L1450 BK	-	-
910505103245	SP531P 7S/940 DEIA LE SM2 L570 WH	Yes	DC operated central emergency lighting
910505103249	SP533P 12S/930 DEIA LE SM2 L570 WH	Yes	DC operated central emergency lighting
910505103256	SP530P 30S/930 DEIA LN SM2 L2250 BK	Yes	DC operated central emergency lighting
910505103282	SP530P 50S/TW9 SEIA SM2 U4 L2290 ALU	-	-
910505103283	SP530P 86S/TW9 SEIA U4 SM2 L2850 ALU	-	-
910505103257	SP531P 30S/930 SEIA LN U4 SW2 L2290 ALU	-	-
910505103260	SP532P 72S/940 DEIA SM2 L2250 ALU	Yes	DC operated central emergency lighting

TrueLine, suspended

Order Code	Full Product Name	Central Emergency	Emergency lighting
910505103261	SP533P 48S/940 DEIA SM2 L2250 ALU	Yes	DC operated central emergency lighting
910505103263	SP533P 82S/940 DEIA SM2 L2250 ALU	Yes	DC operated central emergency lighting
910505103269	SP530P 38S/930 DEIA LN SW2 L2810 ALU	Yes	DC operated central emergency lighting
910505103273	SP532P 58S/930 DEIA LN SM2 L2810 ALU	Yes	DC operated central emergency lighting
910505103274	SP533P 66S/930 DEIA LN SW2 L2810 ALU	Yes	DC operated central emergency lighting
910505103258	SP530P 50S/940 SEIA U4 SM2 L2290 BK	-	-
910505103262	SP532P 98S/940 SEIA U4 SM2 L2290 BK	-	-
910505103270	SP530P 62S/940 SEIA U4 SM2 L2850 BK	-	-
910505103244	SP530P 75/940 DEIA LE SM2 L570 ALU	Yes	DC operated central emergency lighting
910505103247	SP532P 10S/930 DEIA LE SM2 L570 ALU	Yes	DC operated central emergency lighting
910505103259	SP530P 50S/930 DEIA SM2 L2250 WH	Yes	DC operated central emergency lighting
910505103271	SP531P 62S/930 DEIA SM2 L2810 WH	Yes	DC operated central emergency lighting
910505103272	SP532P 94S/940 DEIA SM2 L2810 WH	Yes	DC operated central emergency lighting
910505103197	SP532P 47S/940 DEIA SM2 L1410 BK	Yes	DC operated central emergency lighting
910505103198	SP531P 15S/940 DEIA SM2 L1130 BK	Yes	DC operated central emergency lighting

Order Code	Full Product Name	Central Emergency	Emergency lighting
910505103199	SP530P 34S/940 DEIA SM2 L1130 BK	Yes	DC operated central emergency lighting
910505103201	SP532P 29S/930 DEIA LNP SM2 L1410 BK	Yes	DC operated central emergency lighting
910505103202	SP532P 29S/940 DEIA LNP SM2 L1410 BK	Yes	DC operated central emergency lighting
910505103207	SP532P 36S/940 DEIA LNP SM2T L1130 BK	Yes	DC operated central emergency lighting
910505103204	SP532P 29S/940 DEIA LN SW2 L1410 ALU	Yes	DC operated central emergency lighting
910505103205	SP532P 36S/940 DEIA LNP SM2T L1130 ALU	Yes	DC operated central emergency lighting
910505103208	SP532P 29S/940 DEIA LNP SM2 L1410 ALU	Yes	DC operated central emergency lighting
910505103209	SP534P 43S/940 DEIA LN SW2 L1410 ALU	Yes	DC operated central emergency lighting
910505103211	SP532P 47S/940 DEIA LN SW2 L1410 ALU	Yes	DC operated central emergency lighting
910505103212	SP532P 36S/940 DEIA LN SW2 L1130 ALU	Yes	DC operated central emergency lighting
910505103279	SP532P 36S/TW9 DEIA LN SW2 L1130 ALU	-	-
910505103280	SP533P 33S/TW9 DEIA LN SW2 L1410 ALU	-	-
910505103214	SP532P 47S/940 SEIA U4 SM2 L1450 ALU	-	-
910505103215	SP530P 40S/940 SEIA U4 SM2 L1170 ALU	-	-
910505103216	SP532P 66S/940 SEIA U4 SM2 L1450 ALU	-	-

Product Data


Order Code	Full Product Name	Product family code
910505103203	SP532P 47S/940 DEIA LS SM2 L1410 ALU	SP532P
910505103206	SP534P 34S/940 DEIA LS SM2 L1130 ALU	SP534P
910505103210	SP532P 29S/940 DEIA LS SM2 L1410 ALU	SP532P
910505103213	SP534P 43S/940 DEIA LS SM2 L1410 ALU	SP534P
910505103246	SP530P 17S/940 DEIA LE SM2 L570 BK	SP530P
910505103248	SP532P 24S/930 DEIA LE SM2 L570 BK	SP532P
910505103161	SP533P 41S/940 DEIA SM2 L1130 ALU	SP533P
910505103162	SP532P 29S/940 DEIA SM2 L1410 WH	SP532P
910505103163	SP530P 50S/940 DEIA SM2 L1410 ALU	SP530P
910505103164	SP532P 47S/940 DEIA SM2 L1410 ALU	SP532P
910505103165	SP530P 25S/940 POE SW2 L1130 ALU	SP530P
910505103166	SP531P 15S/940 DEIA SM2 L1130 ALU	SP531P
910505103167	SP530P 43S/940 DEIA SM2 L1410 ALU	SP530P
910505103168	SP532P 77S/940 DEIA SM2 L1410 ALU	SP532P
910505103169	SP532P 36S/940 DEIA SM2 L1130 ALU	SP532P
910505103170	SP532P 58S/940 DEIA SM2 L1130 ALU	SP532P
910505103171	SP530P 34S/940 DEIA SM2 L1130 ALU	SP530P

Order Code	Full Product Name	Product family code
910505103172	SP533P 33S/930 DEIA SM2 L1410 ALU	SP533P
910505103173	SP532P 49S/930 DEIA SM2 L1130 ALU	SP532P
910505103174	SP532P 77S/930 DEIA SM2 L1410 ALU	SP532P
910505103175	SP532P 36S/940 DEIA SM2 L1130 WH	SP532P
910505103176	SP533P 33S/930 DEIA SM2 L1410 WH	SP533P
910505103177	SP534P 40S/940 DEIA SM2 L1130 ALU	SP534P
910505103180	SP533P 24S/940 DEIA SM2 L1130 ALU	SP533P
910505103181	SP532P 21S/940 DEIA SM2 L1130 ALU	SP532P
910505103182	SP533P 33S/940 DEIA SM2 L1410 ALU	SP533P
910505103183	SP532P 29S/940 DEIA SM2 L1410 ALU	SP532P
910505103185	SP532P 66S/940 DEIA SM2 L1410 ALU	SP532P
910505103186	SP533P 54S/940 DEIA SM2 L1410 ALU	SP533P
910505103187	SP532P 49S/940 DEIA SM2 L1130 ALU	SP532P
910505103188	SP532P 66S/940 DEIA SM2 L1410 WH	SP532P
910505103189	SP532P 47S/940 DEIA SM2 L1410 WH	SP532P
910505103191	SP530P 31S/940 POE U3 SW2 L1450 ALU	SP530P
910505103192	SP530P 40S/940 POE U3 SW2 L1170 ALU	SP530P


Order Code	Full Product Name	Product family code
910505103193	SP530P 40S/940 POE U0 SW2 L1170 ALU	SP530P
910505103194	SP530P 43S/940 POE U0 SW2 L1450 ALU	SP530P
910505103196	SP530P 40S/940 DEIA SM2 L1130 ALU	SP530P
910505103184	SP534P 50S/940 DEIA SM2 L1410 ALU	SP534P
910505103281	SP532P 66S/TW9 SEIA U4 SM2 L1450 BK	SP532P
910505103245	SP531P 7S/940 DEIA LE SM2 L570 WH	SP531P
910505103249	SP533P 12S/930 DEIA LE SM2 L570 WH	SP533P
910505103256	SP530P 30S/930 DEIA LN SM2 L2250 BK	SP530P
910505103282	SP530P 50S/TW9 SEIA SM2 U4 L2290 ALU	SP530P
910505103283	SP530P 86S/TW9 SEIA U4 SM2 L2850 ALU	SP532P
910505103257	SP531P 30S/930 SEIA LN U4 SW2 L2290 ALU	SP531P
910505103260	SP532P 72S/940 DEIA SM2 L2250 ALU	SP532P
910505103261	SP533P 48S/940 DEIA SM2 L2250 ALU	SP533P
910505103263	SP533P 82S/940 DEIA SM2 L2250 ALU	SP533P
910505103269	SP530P 38S/930 DEIA LN SW2 L2810 ALU	SP530P
910505103273	SP532P 58S/930 DEIA LN SM2 L2810 ALU	SP532P
910505103274	SP533P 66S/930 DEIA LN SW2 L2810 ALU	SP533P
910505103258	SP530P 50S/940 SEIA U4 SM2 L2290 BK	SP530P
910505103262	SP532P 98S/940 SEIA U4 SM2 L2290 BK	SP532P
910505103270	SP530P 62S/940 SEIA U4 SM2 L2850 BK	SP530P
910505103244	SP530P 7S/940 DEIA LE SM2 L570 ALU	SP530P

Order Code	Full Product Name	Product family code
910505103247	SP532P 10S/930 DEIA LE SM2 L570 ALU	SP532P
910505103259	SP530P 50S/930 DEIA SM2 L2250 WH	SP530P
910505103271	SP531P 62S/930 DEIA SM2 L2810 WH	SP531P
910505103272	SP532P 94S/940 DEIA SM2 L2810 WH	SP532P
910505103197	SP532P 47S/940 DEIA SM2 L1410 BK	SP532P
910505103198	SP531P 15S/940 DEIA SM2 L1130 BK	SP531P
910505103199	SP530P 34S/940 DEIA SM2 L1130 BK	SP530P
910505103201	SP532P 29S/930 DEIA LNP SM2 L1410 BK	SP532P
910505103202	SP532P 29S/940 DEIA LNP SM2 L1410 BK	SP532P
910505103207	SP532P 36S/940 DEIA LNP SM2T L1130 BK	SP532P
910505103204	SP532P 29S/940 DEIA LN SW2 L1410 ALU	SP532P
910505103205	SP532P 36S/940 DEIA LNP SM2T L1130 ALU	SP532P
910505103208	SP532P 29S/940 DEIA LNP SM2 L1410 ALU	SP532P
910505103209	SP534P 43S/940 DEIA LN SW2 L1410 ALU	SP534P
910505103211	SP532P 47S/940 DEIA LN SW2 L1410 ALU	SP532P
910505103212	SP532P 36S/940 DEIA LN SW2 L1130 ALU	SP532P
910505103279	SP532P 36S/TW9 DEIA LN SW2 L1130 ALU	SP532P
910505103280	SP533P 33S/TW9 DEIA LN SW2 L1410 ALU	SP533P
910505103214	SP532P 47S/940 SEIA U4 SM2 L1450 ALU	SP532P
910505103215	SP530P 40S/940 SEIA U4 SM2 L1170 ALU	SP530P
910505103216	SP532P 66S/940 SEIA U4 SM2 L1450 ALU	SP532P


Polar Wide Diagrams




Polar Normal (separate) - SM530CI - 910505103202




Polar Normal (separate) - SM530CI - 910505103257




Polar Normal (separate) - SM530CI - 910505103162



Polar Normal (separate) - SM530CI - 910505103262




Polar Normal (separate) - SM530CI - 910505103197




Polar Normal (separate) - SM530CI - 910505103203


Polar Wide Diagrams




Polar Normal (separate) - SM530CI - 910505103205




Polar Normal (separate) - SM530CI - 910505103214




Polar Normal (separate) - SM530CI - 910505103249




Polar Normal (separate) - SM530CI - 910505103194




Polar Normal (separate) - SM530CI - 910505103283




Polar Normal (separate) - SM530CI - 910505103189



Polar Normal (separate) - SM530CI - 910505103248




Polar Normal (separate) - SM530CI - 910505103207




Polar Normal (separate) - SM530CI - 910505103183


Polar Wide Diagrams




Polar Normal (separate) - SM530CI - 910505103206




Polar Normal (separate) - SM530CI - 910505103247




Polar Normal (separate) - SM530CI - 910505103193




Polar Normal (separate) - SM530CI - 910505103180




Polar Normal (separate) - SM530CI - 910505103192




Polar Normal (separate) - SM530CI - 910505103273



Polar Normal (separate) - SM530CI - 910505103161




Polar Normal (separate) - SM530CI - 910505103201




Polar Normal (separate) - SM530CI - 910505103263


Polar Wide Diagrams




Polar Normal (separate) - SM530CI - 910505103212




Polar Normal (separate) - SM530CI - 910505103172




Polar Normal (separate) - SM530CI - 910505103208




Polar Normal (separate) - SM530CI - 910505103246




Polar Normal (separate) - SM530CI - 910505103177




Polar Normal (separate) - SM530CI - 910505103174



Polar Normal (separate) - SM530CI - 910505103245




Polar Normal (separate) - SM530CI - 910505103279




Polar Normal (separate) - SM530CI - 910505103199


Polar Wide Diagrams




Polar Normal (separate) - SM530CI - 910505103261




Polar Normal (separate) - SM530CI - 910505103274




Polar Normal (separate) - SM530CI - 910505103169




Polar Normal (separate) - SM530CI - 910505103166




Polar Normal (separate) - SM530CI - 910505103184




Polar Normal (separate) - SM530CI - 910505103216



Polar Normal (separate) - SM530CI - 910505103271




Polar Normal (separate) - SM530CI - 910505103280




Polar Normal (separate) - SM530CI - 910505103210


Polar Wide Diagrams




Polar Normal (separate) - SM530CI - 910505103211




Polar Normal (separate) - SM530CI - 910505103256




Polar Normal (separate) - SM530CI - 910505103281




Polar Normal (separate) - SM530CI - 910505103244




Polar Normal (separate) - SM530CI - 910505103173




Polar Normal (separate) - SM530CI - 910505103258



Polar Normal (separate) - SM530CI - 910505103259




Polar Normal (separate) - SM530CI - 910505103182




Polar Normal (separate) - SM530CI - 910505103196


Polar Wide Diagrams




Polar Normal (separate) - SM530CI - 910505103209




Polar Normal (separate) - SM530CI - 910505103188




Polar Normal (separate) - SM530CI - 910505103186




Polar Normal (separate) - SM530CI - 910505103215




Polar Normal (separate) - SM530CI - 910505103187




Polar Normal (separate) - SM530CI - 910505103163



Polar Normal (separate) - SM530CI - 910505103204




Polar Normal (separate) - SM530CI - 910505103185




Polar Normal (separate) - SM530CI - 910505103176


Polar Wide Diagrams




Polar Normal (separate) - SM530CI - 910505103260




Polar Normal (separate) - SM530CI - 910505103269




Polar Normal (separate) - SM530CI - 910505103282




Polar Normal (separate) - SM530CI - 910505103164




Polar Normal (separate) - SM530CI - 910505103165




Polar Normal (separate) - SM530CI - 910505103167



Polar Normal (separate) - SM530CI - 910505103168




Polar Normal (separate) - SM530CI - 910505103170




Polar Normal (separate) - SM530CI - 910505103171


Polar Wide Diagrams




Polar Normal (separate) - SM530CI - 910505103181




Polar Normal (separate) - SM530CI - 910505103175




Polar Normal (separate) - SM530CI - 910505103191




Polar Normal (separate) - SM530CI - 910505103198



Polar Normal (separate) - SM530CI - 910505103213



Polar Normal (separate) - SM530CI - 910505103270



Polar Normal (separate) - SM530CI - 910505103272

TrueLine, suspended

