



Flexible and Elegant

SlimBalance G3

SlimBalance G3 SP570P is a flexible linear office offer which fits a variety of spaces like office, education. It offers flexible width of 35/60/90/120mm and length of 600/1200/1500mm to fit multiple applications. Geometric shapes help further create differentiated space. By means of its special designed structure, it offers quick and easy installation and maintenance. UGR19 is available for certain types through customized solution to provide a better visual comfort office environment.

Benefits

- High lm/w provides better energy saving
- Flexible width offers the feasibility to fit multiple ceiling spaces
- Dali and Interact interfaces available for easy system control
- Low UGR offer for visual comfort
- Multiple mounting installations and geometric shapes to cater for various applications
- Easy installation mechanism and modular design help save installation and maintenance time

Features

- System efficiency: max 130lm/W
- Product width with 35/60/90/120mm options
- CRI 80 and 90 available
- Lifetime: 50k hours (L70@ta=25deg)
- UGR19 available for certain types through customized solution
- Easy 'Slide and Click' mechanism for quick continuous installation

Application

- Open plan office
- Public indoor area
- Meeting/Training room
- Library

Specifications

SlimBalance G3

Ceiling type	Open ceiling office for suspension installation
	Plaster board ceiling for recessed installation and surface mounted installation
Mains Voltage	220-240V / 50 - 60Hz
Dimming	PSU: non-dimmable
	PSD: Dimmable via Dali-broadcasting
	WIA: Wireless control, compatible with Interact
	SIA: Wireless control, compatible with SNS210 sensor
Control system input	Dali
Integrated sensors	SNS210 available for SIA version
Material	Extrusion aluminium
Luminaire efficacy	130lm/w

Correlated color temperature - CCT	840
Color Rendering index - CRI	840, 940
Optic	UGR19 is available through lens design
Ingress protection	IP20
Driver replaceable	Yes
UGR	19 is available through lens design
Installation	Suspension
	Recessed
	Surface mounted

Versions



SlimBalance G3



SlimBalance G3



SlimBalance G3


Dimensional drawing



SP570 W6L150 CD shop drawing



SP570 W6L120 CD shop drawing



SP570 W6L60 SD shop drawing

SlimBalance G3

Product details

SlimBalance G3



SlimBalance G3



General Information	
Driver included	Yes
Gear	-
Number of gear units	1 unit
Service tag	Yes
Light Technical	
Beam angle of light source	120 degree(s)
Correlated Color Temperature (Nom)	4000 K
Optic type	Beam angle 100°
Operating and Electrical	
Protection class IEC	Safety class I
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Suitable for random switching	No
Mechanical and Housing	
Optical cover type	Opal
Housing Color	White
Mech. impact protection code	IK03
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	-20 °C to 40 °C
CE mark	Yes
ENEC mark	-
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Initial Performance (IEC Compliant)	
Initial chromaticity	SDCM<=4
Luminous flux tolerance	-10% / +10%

Light Technical

Order Code	Full Product Name	Color	Luminous Efficacy (rated) (Nom)	Luminous Flux	Number of light sources
		rendering index (CRI)			
911401537342	SP570P LED50/840 L150W6 CD PSU	80	132 lm/W	5,340 lm	2
911401537142	SP570P LED40/840 L120W6 CD PSU	80	133 lm/W	4,270 lm	1
911401538542	SP570P LED40/940 L120W6 CD PSD	90	123 lm/W	4,130 lm	1
911401536942	SP570P LED20/840 L60W6 CD PSU	80	119 lm/W	2,080 lm	1

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401537342	SP570P LED50/840 L150W6 CD PSU	40.5 W

Order Code	Full Product Name	Power Consumption
911401537142	SP570P LED40/840 L120W6 CD PSU	32 W

SlimBalance G3

Order Code	Full Product Name	Power Consumption
911401538542	SP570P LED40/940 L120W6 CD PSD	33.5 W

Order Code	Full Product Name	Power Consumption
911401536942	SP570P LED20/840 L60W6 CD PSU	17.5 W

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
911401537342	SP570P LED50/840 L150W6 CD PSU	No	Not applicable
911401537142	SP570P LED40/840 L120W6 CD PSU	No	Not applicable

Order Code	Full Product Name	Dimmable	Maximum dim level
911401538542	SP570P LED40/940 L120W6 CD PSD	DALI	1%
911401536942	SP570P LED20/840 L60W6 CD PSU	No	Not applicable

