



# Aesthetic, Comprehensive and Reliable

## GreenUp Track

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenUp Track product family offers a complete track light solutions with aesthetic and compact product design, comprehensive control availability and specification options. It offers an outstanding color rendering performance and glare control effect, tailored for retail and hospitality applications.

### Benefits

- Aesthetic product design with compact and integrated concept.
- Comprehensive offerings to meet various application requirements.
- Outstanding color rendering performance and visual comfort design

### Features

- Multiple options of lumen output, wattage and optics.
- Full control availability including on/off, 1-10v, triac and DALI.
- CRI 90, R9 $\geq$ 50
- UGR 19, cut off angle 50°

### Application




- Retail
- Hospitality
- Fashion

Versions



GreenUp Track

Dimensional drawing



| Light Technical                     |               |
|-------------------------------------|---------------|
| Color rendering index (CRI)         | >90           |
| Operating and Electrical            |               |
| Input Voltage                       | 220-240 V     |
| Line Frequency                      | 50 or 60 Hz   |
| Mechanical and Housing              |               |
| Optical cover type                  | Lens          |
| Mech. impact protection code        | IK03          |
| Ingress protection code             | IP20          |
| Approval and Application            |               |
| Ambient temperature range           | -20 to +40 °C |
| CE mark                             | No            |
| Initial Performance (IEC Compliant) |               |
| Luminous flux tolerance             | +/-10%        |

Light Technical

| Order Code   | Full Product Name           | Correlated Color  | Luminous Efficacy |               |
|--------------|-----------------------------|-------------------|-------------------|---------------|
|              |                             | Temperature (Nom) | (rated) (Nom)     | Luminous Flux |
| 911401530522 | ST306T P20 940 PSU WB WH BR | 4000 K            | 90 lm/W           | 1,800 lm      |
| 911401542222 | ST306T P10 940 PSD WB WH SR | 4000 K            | 90 lm/W           | 900 lm        |
| 911401545522 | ST306T P20 930 PSD WB WH SR | 3000 K            | 85 lm/W           | 1,700 lm      |
| 911401556422 | ST306T P10 940 PSD NB BK BR | 4000 K            | 90 lm/W           | 900 lm        |
| 911401559022 | ST306T P20 930 PSU WB BK BR | 3000 K            | 85 lm/W           | 1,700 lm      |
| 911401559322 | ST306T P20 940 PSU WB BK BR | 4000 K            | 90 lm/W           | 1,800 lm      |
| 911401566222 | ST306T P40 930 PSU WB BK BR | 3000 K            | 93 lm/W           | 3,720 lm      |
| 911401569822 | ST306T P10 930 PSU WB BK SR | 3000 K            | 85 lm/W           | 850 lm        |
| 911401580622 | ST306T P40 930 PSU WB BK SR | 3000 K            | 93 lm/W           | 3,720 lm      |
| 911401580922 | ST306T P40 940 PSU WB BK SR | 4000 K            | 95 lm/W           | 3,800 lm      |

Operating and Electrical

| Order Code   | Full Product Name           | Protection class IEC | Power       |
|--------------|-----------------------------|----------------------|-------------|
|              |                             |                      | Consumption |
| 911401530522 | ST306T P20 940 PSU WB WH BR | Safety class II      | 20 W        |
| 911401542222 | ST306T P10 940 PSD WB WH SR | Safety class I       | 10 W        |
| 911401545522 | ST306T P20 930 PSD WB WH SR | Safety class I       | 20 W        |
| 911401556422 | ST306T P10 940 PSD NB BK BR | Safety class I       | 10 W        |
| 911401559022 | ST306T P20 930 PSU WB BK BR | Safety class II      | 20 W        |

| Order Code   | Full Product Name           | Protection class IEC | Power       |
|--------------|-----------------------------|----------------------|-------------|
|              |                             |                      | Consumption |
| 911401559322 | ST306T P20 940 PSU WB BK BR | Safety class II      | 20 W        |
| 911401566222 | ST306T P40 930 PSU WB BK BR | Safety class II      | 40 W        |
| 911401569822 | ST306T P10 930 PSU WB BK SR | Safety class II      | 10 W        |
| 911401580622 | ST306T P40 930 PSU WB BK SR | Safety class II      | 40 W        |
| 911401580922 | ST306T P40 940 PSU WB BK SR | Safety class II      | 40 W        |

Controls and Dimming

| Order Code   | Full Product Name           | Dimmable |
|--------------|-----------------------------|----------|
| 911401530522 | ST306T P20 940 PSU WB WH BR | No       |
| 911401542222 | ST306T P10 940 PSD WB WH SR | Yes      |
| 911401545522 | ST306T P20 930 PSD WB WH SR | Yes      |
| 911401556422 | ST306T P10 940 PSD NB BK BR | Yes      |
| 911401559022 | ST306T P20 930 PSU WB BK BR | No       |

| Order Code   | Full Product Name           | Dimmable |
|--------------|-----------------------------|----------|
| 911401559322 | ST306T P20 940 PSU WB BK BR | No       |
| 911401566222 | ST306T P40 930 PSU WB BK BR | No       |
| 911401569822 | ST306T P10 930 PSU WB BK SR | No       |
| 911401580622 | ST306T P40 930 PSU WB BK SR | No       |
| 911401580922 | ST306T P40 940 PSU WB BK SR | No       |

Mechanical and Housing

| Order Code   | Full Product Name           | Housing Color |
|--------------|-----------------------------|---------------|
| 911401530522 | ST306T P20 940 PSU WB WH BR | White         |
| 911401542222 | ST306T P10 940 PSD WB WH SR | White         |
| 911401545522 | ST306T P20 930 PSD WB WH SR | White         |
| 911401556422 | ST306T P10 940 PSD NB BK BR | Black         |
| 911401559022 | ST306T P20 930 PSU WB BK BR | Black         |

| Order Code   | Full Product Name           | Housing Color |
|--------------|-----------------------------|---------------|
| 911401559322 | ST306T P20 940 PSU WB BK BR | Black         |
| 911401566222 | ST306T P40 930 PSU WB BK BR | Black         |
| 911401569822 | ST306T P10 930 PSU WB BK SR | Black         |
| 911401580622 | ST306T P40 930 PSU WB BK SR | Black         |
| 911401580922 | ST306T P40 940 PSU WB BK SR | Black         |

