

Flexible, Comprehensive and Reliable

GreenUp Magnetic Flex

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenUp Magnetic Flex is a comprehensive product family with magnetic design which supports an easier and flexible way of installation and commissioning. It offers a complete range of options with product diversity and control availability. GreenUp Magnetic Flex gives you a plenty of flexibility to create the lighting magics.

Benefits

- Easy & Flexible for installation & commissioning.
- Comprehensive offerings to meet various application requirements.
- Good lighting quality with well controlled glare and color rendering performance.
- Ensured quality and reliability.

Features

- Product diversities with magnetic design, including spot, flood, suspension, gridlight and tiltable grid.
- Multiple control availability including on/off and 1-10v.
- CRI $\geq$ 90, SDCM $\leq$ 5

Application

- Retail
- Hospitality
- Fashion



Versions



GreenUp Magnetic Flex

GreenUp Magnetic Flex

Dimensional drawing



GreenUp Magnetic Flex

Light Technical	
Color rendering index (CRI)	>90
Operating and Electrical	
Protection class IEC	Safety class III
Input Voltage	48 V
Line Frequency	- Hz
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Optical cover type	Polycarbonate bowl/cover
Housing Color	Black
Mech. impact protection code	IK03
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	-20 to +40 °C
CE mark	No
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

Light Technical

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux
		Temperature (Nom)	(rated) (Nom)	
911401554802	ST307M GD P15 930 PSU-E MB	3000 K	70 lm/W	1,050 lm
911401554902	ST307M GD P8 940 PSU-E MB	4000 K	80 lm/W	640 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401554802	ST307M GD P15 930 PSU-E MB	15 W

Order Code	Full Product Name	Power Consumption
911401554902	ST307M GD P8 940 PSU-E MB	8 W

